

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332357-927

Luminaire Tested: **S123RDIP-S1000D1195U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332357-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1000D1195U927-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1195 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6784.5 lumens  
Efficiency: N/A  
Efficacy: 103.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332357-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332357-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	93	89	85	89	85	82	79	71	68	66	58	56	55	45	44	44	38
2	88	81	75	70	81	75	70	65	62	59	55	51	48	46	40	39	37	32
3	81	72	64	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28
4	74	63	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	29	26	24	21
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21	18
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19	16
8	54	42	34	29	49	39	32	27	33	28	24	27	23	21	22	19	17	15
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	16	13
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14310	14310	14310
5°	14364	14166	14249
10°	14283	13988	13941
15°	14130	13661	13517
20°	13919	13252	12944
25°	13702	12792	12383
30°	13415	12263	11591
35°	13119	11730	10867
40°	12847	11105	9969
45°	12490	10488	9159
50°	12097	9786	8251
55°	11695	8983	7405
60°	11328	8125	6476
65°	10847	7195	5547
70°	10247	6039	4482
75°	9374	4754	4213
80°	8356	4209	3874
85°	7052	3730	3458



TEST NUMBER: P332357-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	124.8	1.8
10°-20°	347.3	5.1
20°-30°	500.2	7.4
30°-40°	563.4	8.3
40°-50°	539.0	7.9
50°-60°	441.4	6.5
60°-70°	297.8	4.4
70°-80°	149.8	2.2
80°-90°	43.1	0.6
90°-100°	45.0	0.7
100°-110°	214.7	3.2
110°-120°	515.6	7.6
120°-130°	656.6	9.7
130°-140°	701.5	10.3
140°-150°	656.0	9.7
150°-160°	529.2	7.8
160°-170°	341.5	5.0
170°-180°	117.7	1.7
0°-30°	972.3	14.3
0°-40°	1535.7	22.6
0°-60°	2516.0	37.1
0°-90°	3006.7	44.3
90°-120°	775.3	11.4
90°-150°	2789.4	41.1
90°-180°	3778.0	55.7
0°-180°	6784.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1329	1329	1329	1329	1329	
5°	1329	1324	1311	1320	1319	126
15°	1268	1255	1226	1220	1213	357
25°	1154	1125	1077	1055	1043	530
35°	998	958	893	848	827	625
45°	820	770	689	629	602	633
55°	623	568	479	418	395	559
65°	426	365	282	232	218	421
75°	225	173	114	104	101	240
85°	57	34	30	28	28	64
90°	1	10	22	26	28	5
95°	56	21	28	35	35	69
105°	274	279	202	48	40	291
115°	514	520	528	537	541	508
125°	725	732	736	738	740	647
135°	903	908	912	915	912	695
145°	1042	1048	1050	1052	1052	652
155°	1148	1146	1147	1151	1146	529
165°	1210	1208	1207	1213	1208	342
175°	1239	1234	1235	1241	1234	118
180°	1239	1239	1239	1239	1239	



TEST NUMBER: P332357-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4
2.5°	1333.7	1332.9	1332.2	1331.4	1330.6	1329.1	1326.8	1324.5	1322.2	1319.9	1322.0
5°	1329.4	1328.2	1327.0	1325.8	1324.6	1322.5	1319.7	1316.8	1314.0	1311.1	1313.2
7.5°	1317.1	1315.8	1314.5	1313.2	1311.9	1309.4	1305.7	1302.0	1298.2	1294.5	1295.7
10°	1306.8	1305.1	1303.4	1301.7	1300.1	1297.0	1292.8	1288.4	1284.1	1279.8	1280.1
12.5°	1292.1	1290.2	1288.4	1286.5	1284.6	1281.0	1275.8	1270.5	1265.3	1260.0	1259.8
15°	1268.0	1265.4	1262.7	1260.0	1257.4	1252.8	1246.0	1239.3	1232.6	1225.9	1224.7
17.5°	1237.5	1234.5	1231.4	1228.4	1225.3	1219.5	1210.9	1202.5	1193.9	1185.3	1182.8
20°	1215.1	1211.3	1207.4	1203.6	1199.8	1193.3	1184.2	1175.1	1166.0	1156.9	1153.8
22.5°	1190.1	1185.7	1181.3	1176.9	1172.5	1165.5	1155.7	1146.1	1136.4	1126.7	1122.8
25°	1153.7	1147.7	1141.7	1135.7	1129.7	1121.2	1110.2	1099.2	1088.1	1077.1	1072.1
27.5°	1109.5	1102.9	1096.2	1089.6	1083.0	1073.6	1061.3	1049.0	1036.7	1024.5	1017.5
30°	1079.3	1072.1	1064.9	1057.7	1050.5	1040.2	1026.8	1013.4	1000.0	986.6	978.4
32.5°	1049.1	1040.9	1032.8	1024.6	1016.5	1005.4	991.2	977.0	962.7	948.6	939.7
35°	998.4	989.8	981.1	972.6	963.9	952.1	937.3	922.4	907.6	892.7	882.4
37.5°	947.1	937.5	927.9	918.3	908.7	896.0	880.2	864.3	848.4	832.6	820.9
40°	914.3	903.8	893.2	882.6	872.1	858.3	841.4	824.3	807.3	790.3	777.8
42.5°	877.2	866.6	856.1	845.6	835.0	821.0	803.4	785.8	768.3	750.7	737.0
45°	820.5	809.7	798.9	788.1	777.4	762.8	744.3	725.9	707.4	689.0	675.3
47.5°	763.8	751.9	740.1	728.3	716.4	701.3	682.9	664.4	645.9	627.5	612.7
50°	722.4	711.1	699.9	688.6	677.3	662.0	642.6	623.2	603.8	584.4	569.5
52.5°	685.3	673.1	660.8	648.6	636.4	620.7	601.5	582.3	563.1	543.8	528.4
55°	623.2	611.5	599.7	588.0	576.2	560.2	539.8	519.4	499.1	478.7	464.9
57.5°	565.9	553.0	540.3	527.4	514.7	498.0	477.5	457.1	436.7	416.2	403.1
60°	526.2	513.0	499.8	486.6	473.4	456.9	437.0	417.2	397.3	377.4	364.4
62.5°	486.5	473.3	460.1	446.9	433.8	417.2	397.4	377.5	357.6	337.7	325.5
65°	425.9	412.7	399.5	386.3	373.2	357.3	338.6	319.9	301.2	282.5	270.8
67.5°	365.3	352.0	338.7	325.3	312.0	296.4	278.5	260.5	242.6	224.7	215.9
70°	325.6	312.7	299.8	286.8	273.9	259.0	242.2	225.5	208.7	191.9	183.5
72.5°	285.9	273.2	260.5	247.7	235.0	220.9	205.7	190.5	175.2	160.0	153.1
75°	225.4	213.8	202.3	190.8	179.4	167.0	153.8	140.6	127.5	114.3	111.9
77.5°	170.2	159.7	149.3	138.9	128.6	119.1	110.6	102.1	93.6	85.2	83.9
80°	134.8	124.9	115.1	105.3	95.5	88.1	83.0	78.0	73.0	67.9	67.2
82.5°	101.2	92.7	84.2	75.7	67.2	61.8	59.4	57.1	54.7	52.4	51.7
85°	57.1	51.9	46.6	41.4	36.0	33.0	32.3	31.6	30.9	30.2	29.7
87.5°	20.9	19.2	17.5	15.8	14.1	13.5	14.0	14.6	15.1	15.6	15.6
90°	1.0	2.9	5.0	7.1	9.1	11.5	14.1	16.8	19.4	22.1	22.9
92.5°	17.1	16.6	16.0	15.4	14.8	15.5	17.6	19.6	21.5	23.5	24.9
95°	56.2	47.8	39.4	31.0	22.6	19.6	21.8	24.0	26.3	28.5	29.9
97.5°	112.8	109.1	105.3	101.6	97.8	88.6	73.8	59.1	44.4	29.6	31.3
100°	155.5	159.6	163.7	167.8	171.9	158.0	126.1	94.2	62.3	30.3	32.0
102.5°	204.1	207.1	210.0	212.9	215.9	199.9	165.1	130.2	95.4	60.5	55.5
105°	274.3	276.6	278.8	281.0	283.3	275.2	256.7	238.4	220.0	201.5	165.3
107.5°	348.2	350.1	351.9	353.6	355.5	357.8	360.8	363.6	366.5	369.5	342.9
110°	397.6	399.3	400.8	402.5	404.2	406.1	408.4	410.6	412.8	415.1	408.4



TEST NUMBER: P332357-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	444.7	446.2	447.7	449.2	450.6	452.5	454.7	457.0	459.2	461.4	461.6
115°	514.5	515.7	516.9	518.2	519.4	520.9	522.8	524.6	526.5	528.3	530.4
117.5°	582.0	583.5	585.0	586.6	588.1	589.3	590.3	591.2	592.2	593.1	594.7
120°	624.0	625.8	627.7	629.5	631.4	632.6	633.2	633.8	634.5	635.0	636.7
122.5°	666.7	668.2	669.7	671.2	672.8	673.9	674.7	675.5	676.2	677.0	678.2
125°	725.2	726.9	728.5	730.2	731.8	733.0	733.8	734.7	735.5	736.3	736.7
127.5°	782.0	783.5	785.2	786.9	788.5	789.8	790.8	791.8	792.7	793.7	794.4
130°	817.3	819.0	820.5	822.2	823.8	825.1	825.9	826.7	827.5	828.3	829.2
132.5°	851.1	852.8	854.4	856.0	857.7	858.8	859.5	860.2	860.8	861.5	862.3
135°	902.9	904.1	905.3	906.6	907.8	908.8	909.7	910.5	911.2	912.1	912.7
137.5°	947.1	948.6	950.1	951.7	953.3	954.3	954.7	955.2	955.6	956.1	957.0
140°	976.5	977.7	979.0	980.2	981.4	982.3	982.9	983.6	984.2	984.8	985.6
142.5°	1003.8	1005.0	1006.2	1007.4	1008.7	1009.6	1010.2	1010.8	1011.5	1012.0	1012.7
145°	1041.9	1043.3	1044.7	1046.2	1047.6	1048.5	1048.9	1049.3	1049.7	1050.1	1050.5
147.5°	1077.8	1078.7	1079.7	1080.5	1081.5	1082.2	1082.6	1083.0	1083.4	1083.8	1084.3
150°	1099.9	1100.4	1101.1	1101.7	1102.3	1102.8	1103.2	1103.6	1104.1	1104.5	1104.9
152.5°	1119.7	1120.0	1120.3	1120.5	1120.9	1121.1	1121.3	1121.7	1121.9	1122.1	1122.8
155°	1147.7	1147.3	1146.8	1146.4	1146.1	1146.0	1146.1	1146.4	1146.6	1146.8	1147.8
157.5°	1169.4	1169.3	1169.3	1169.3	1169.3	1169.1	1168.9	1168.7	1168.5	1168.3	1169.6
160°	1182.6	1182.5	1182.3	1182.1	1181.9	1181.6	1181.5	1181.2	1181.1	1180.8	1182.1
162.5°	1195.2	1194.7	1194.1	1193.6	1193.0	1192.7	1192.5	1192.3	1192.1	1191.8	1193.3
165°	1210.3	1209.7	1209.0	1208.5	1207.8	1207.4	1207.2	1207.0	1206.8	1206.6	1208.2
167.5°	1222.1	1221.2	1220.4	1219.6	1218.8	1218.4	1218.4	1218.4	1218.4	1218.4	1220.0
170°	1228.7	1227.9	1227.1	1226.2	1225.4	1225.0	1225.0	1225.0	1225.0	1225.0	1226.6
172.5°	1233.1	1232.2	1231.1	1230.2	1229.2	1228.8	1228.9	1229.1	1229.2	1229.4	1231.1
175°	1238.8	1237.8	1236.8	1235.7	1234.7	1234.3	1234.5	1234.7	1234.9	1235.1	1236.6
177.5°	1240.3	1239.4	1238.7	1237.9	1237.0	1236.7	1236.8	1237.0	1237.2	1237.3	1238.7
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P332357-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4
2.5°	1324.1	1326.3	1328.3	1329.2	1328.8	1328.5	1328.1	1327.7
5°	1315.4	1317.6	1319.7	1320.6	1320.1	1319.6	1319.1	1318.7
7.5°	1296.9	1298.1	1299.3	1299.5	1298.6	1297.8	1297.0	1296.2
10°	1280.3	1280.6	1280.8	1280.3	1279.1	1277.9	1276.7	1275.5
12.5°	1259.6	1259.6	1259.4	1258.6	1257.3	1255.8	1254.5	1253.1
15°	1223.5	1222.3	1221.1	1219.6	1218.0	1216.3	1214.7	1213.0
17.5°	1180.3	1177.7	1175.2	1172.7	1170.2	1167.7	1165.2	1162.7
20°	1150.6	1147.6	1144.5	1141.5	1138.6	1135.7	1132.8	1130.0
22.5°	1119.0	1115.1	1111.2	1107.9	1105.3	1102.6	1099.9	1097.2
25°	1067.1	1062.0	1057.0	1053.1	1050.5	1047.9	1045.3	1042.6
27.5°	1010.5	1003.5	996.5	991.0	987.0	982.9	978.9	974.9
30°	970.3	962.1	953.9	948.0	944.1	940.3	936.4	932.6
32.5°	930.7	921.9	912.9	906.5	902.5	898.4	894.4	890.3
35°	872.1	861.8	851.5	844.2	840.0	835.6	831.3	827.0
37.5°	809.2	797.5	785.8	777.3	772.0	766.7	761.4	756.1
40°	765.4	753.0	740.5	731.5	726.0	720.5	714.9	709.5
42.5°	723.4	709.8	696.2	686.9	682.0	677.1	672.1	667.2
45°	661.6	648.0	634.3	624.6	618.9	613.1	607.4	601.7
47.5°	597.8	583.0	568.1	558.1	552.9	547.9	542.7	537.6
50°	554.7	539.8	525.0	514.8	509.3	503.7	498.3	492.7
52.5°	513.0	497.6	482.1	471.9	467.0	462.1	457.2	452.2
55°	450.9	437.0	423.1	413.8	409.0	404.2	399.4	394.6
57.5°	389.9	376.8	363.7	355.1	351.0	346.9	342.9	338.7
60°	351.5	338.6	325.6	317.1	313.1	309.0	304.9	300.8
62.5°	313.3	301.2	289.0	280.7	276.6	272.3	268.0	263.7
65°	259.0	247.2	235.5	228.3	225.7	223.1	220.5	217.8
67.5°	207.2	198.4	189.6	183.8	181.0	178.2	175.3	172.5
70°	175.2	166.8	158.4	152.9	150.2	147.6	145.0	142.4
72.5°	146.3	139.4	132.6	128.7	127.5	126.4	125.3	124.2
75°	109.5	107.1	104.7	103.3	102.8	102.3	101.8	101.3
77.5°	82.6	81.3	80.0	79.1	78.7	78.2	77.7	77.2
80°	66.5	65.8	65.0	64.5	64.0	63.5	63.0	62.5
82.5°	50.9	50.2	49.5	49.1	49.0	49.0	48.8	48.7
85°	29.2	28.8	28.3	28.0	28.0	28.0	28.0	28.0
87.5°	15.6	15.5	15.5	15.4	15.4	15.2	15.1	15.0
90°	23.7	24.6	25.3	26.0	26.4	26.8	27.2	27.6
92.5°	26.1	27.5	28.8	29.5	29.8	30.1	30.3	30.6
95°	31.4	32.8	34.2	34.9	34.9	34.9	34.9	34.9
97.5°	32.9	34.5	36.2	37.1	37.3	37.5	37.7	37.9
100°	33.7	35.3	36.9	37.9	38.0	38.3	38.4	38.7
102.5°	50.4	45.3	40.2	37.9	38.3	38.7	39.1	39.4
105°	129.1	92.9	56.7	38.9	39.3	39.7	40.1	40.5
107.5°	316.3	289.8	263.2	236.3	209.1	181.7	154.5	127.2
110°	401.6	394.8	388.1	370.1	340.9	311.6	282.3	253.1





TEST NUMBER: P332357-927

CATALOG NUMBER: S123RDIP-S1000D1195U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	461.7	461.8	462.0	458.9	452.7	446.6	440.4	434.2
115°	532.3	534.4	536.5	537.9	538.7	539.6	540.3	541.1
117.5°	596.4	598.0	599.6	600.6	600.7	600.9	601.0	601.2
120°	638.3	639.9	641.6	642.4	642.4	642.4	642.4	642.4
122.5°	679.3	680.5	681.6	682.2	682.4	682.5	682.8	682.9
125°	737.1	737.5	737.9	738.3	738.7	739.2	739.6	740.0
127.5°	795.0	795.7	796.3	796.5	796.1	795.7	795.3	794.8
130°	830.0	830.8	831.6	831.8	831.4	831.0	830.6	830.2
132.5°	863.1	864.0	864.7	864.8	864.3	863.7	863.2	862.5
135°	913.3	913.9	914.6	914.6	913.9	913.3	912.7	912.1
137.5°	958.1	959.0	960.0	960.3	959.9	959.5	959.1	958.6
140°	986.4	987.2	988.1	988.2	987.9	987.5	987.1	986.7
142.5°	1013.4	1014.0	1014.6	1014.7	1014.2	1013.5	1013.0	1012.4
145°	1051.0	1051.4	1051.8	1051.9	1051.9	1051.9	1051.9	1051.9
147.5°	1084.7	1085.1	1085.4	1085.2	1084.3	1083.3	1082.4	1081.4
150°	1105.3	1105.6	1106.0	1106.0	1105.3	1104.8	1104.1	1103.5
152.5°	1123.6	1124.3	1125.1	1125.0	1124.0	1123.1	1122.1	1121.2
155°	1148.8	1149.9	1150.9	1150.7	1149.5	1148.3	1147.1	1145.9
157.5°	1170.8	1172.0	1173.2	1173.1	1171.5	1169.8	1168.2	1166.6
160°	1183.3	1184.5	1185.7	1185.7	1184.2	1182.8	1181.3	1179.9
162.5°	1194.7	1196.0	1197.5	1197.5	1196.2	1194.9	1193.7	1192.4
165°	1209.9	1211.5	1213.1	1213.2	1211.8	1210.4	1208.9	1207.5
167.5°	1221.6	1223.3	1225.0	1225.0	1223.3	1221.6	1220.0	1218.4
170°	1228.3	1229.9	1231.5	1231.5	1229.9	1228.3	1226.6	1225.0
172.5°	1232.7	1234.3	1236.0	1235.9	1234.1	1232.3	1230.5	1228.7
175°	1238.0	1239.4	1240.9	1240.7	1239.1	1237.5	1235.9	1234.2
177.5°	1239.9	1241.3	1242.5	1242.4	1240.8	1239.1	1237.5	1235.9
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

(END OF REPORT)