

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332261-930

Luminaire Tested: **S123RDIP-S340D1025U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332261-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D1025U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4401.6 lumens
Efficiency: N/A
Efficacy: 118.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332261-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332261-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	84	81	82	78	75	73	60	58	57	44	43	42	29	28	28	21
2	84	77	71	66	74	69	64	60	53	50	47	39	37	35	25	24	23	17
3	77	68	61	55	68	61	55	50	47	43	40	34	32	30	23	21	20	15
4	70	60	52	47	62	54	47	42	42	37	34	31	28	25	20	19	17	13
5	64	53	46	40	57	48	41	36	37	33	29	27	24	22	18	17	15	11
6	59	48	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13	10
7	55	43	35	30	48	39	32	27	30	26	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	29	24	27	23	20	21	17	15	14	12	11	8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	13	13	11	10	7
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5042	5042	5042
5°	5061	4991	5020
10°	5032	4928	4912
15°	4979	4813	4763
20°	4904	4669	4560
25°	4828	4507	4363
30°	4727	4320	4084
35°	4623	4133	3829
40°	4526	3912	3513
45°	4401	3694	3227
50°	4262	3448	2907
55°	4121	3166	2609
60°	3991	2863	2282
65°	3823	2534	1954
70°	3610	2127	1577
75°	3302	1676	1485
80°	2944	1488	1364
85°	2482	1309	1223



TEST NUMBER: P332261-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.0	1.0
10°-20°	122.4	2.8
20°-30°	176.2	4.0
30°-40°	198.5	4.5
40°-50°	189.9	4.3
50°-60°	155.5	3.5
60°-70°	104.9	2.4
70°-80°	52.8	1.2
80°-90°	17.0	0.4
90°-100°	39.8	0.9
100°-110°	189.8	4.3
110°-120°	455.9	10.4
120°-130°	580.5	13.2
130°-140°	620.3	14.1
140°-150°	580.0	13.2
150°-160°	467.9	10.6
160°-170°	302.0	6.9
170°-180°	104.1	2.4
0°-30°	342.6	7.8
0°-40°	541.1	12.3
0°-60°	886.5	20.1
0°-90°	1061.2	24.1
90°-120°	685.5	15.6
90°-150°	2466.4	56.0
90°-180°	3340.0	75.9
0°-180°	4401.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	468	468	468	468	468	
5°	468	466	462	465	465	44
15°	447	442	432	430	427	126
25°	406	396	380	372	367	187
35°	352	338	314	299	291	220
45°	289	271	243	222	212	223
55°	220	200	169	147	139	197
65°	150	129	100	82	77	148
75°	79	61	40	37	36	85
85°	20	12	11	10	10	23
90°	1	9	20	23	24	3
95°	50	19	25	31	31	61
105°	242	247	178	42	36	257
115°	455	460	467	475	478	449
125°	641	648	651	653	654	572
135°	798	803	806	809	806	614
145°	921	927	928	930	930	576
155°	1015	1013	1014	1018	1013	467
165°	1070	1068	1067	1073	1068	302
175°	1095	1092	1092	1097	1091	104
180°	1095	1095	1095	1095	1095	



TEST NUMBER: P332261-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4
2.5°	469.9	469.6	469.4	469.1	468.9	468.3	467.5	466.7	465.9	465.0	465.8
5°	468.4	468.0	467.6	467.2	466.7	466.0	465.0	464.0	462.9	461.9	462.7
7.5°	464.1	463.6	463.2	462.7	462.3	461.4	460.1	458.8	457.4	456.1	456.5
10°	460.4	459.8	459.3	458.7	458.0	457.0	455.5	454.0	452.4	450.9	451.0
12.5°	455.3	454.6	454.0	453.3	452.7	451.3	449.5	447.7	445.8	443.9	443.8
15°	446.8	445.8	444.9	443.9	443.0	441.4	439.0	436.7	434.3	431.9	431.5
17.5°	436.0	435.0	433.9	432.8	431.7	429.7	426.6	423.6	420.7	417.7	416.8
20°	428.1	426.8	425.4	424.1	422.7	420.4	417.3	414.0	410.8	407.6	406.5
22.5°	419.3	417.8	416.2	414.7	413.1	410.7	407.2	403.8	400.4	397.0	395.6
25°	406.5	404.4	402.3	400.1	398.0	395.0	391.2	387.3	383.4	379.5	377.7
27.5°	390.9	388.6	386.2	383.9	381.6	378.3	374.0	369.6	365.3	360.9	358.5
30°	380.3	377.7	375.2	372.7	370.1	366.5	361.7	357.0	352.3	347.6	344.7
32.5°	369.7	366.7	363.9	361.0	358.2	354.2	349.2	344.2	339.2	334.2	331.1
35°	351.8	348.7	345.7	342.7	339.7	335.5	330.3	325.0	319.8	314.5	311.0
37.5°	333.7	330.3	326.9	323.6	320.2	315.7	310.1	304.5	299.0	293.3	289.3
40°	322.1	318.5	314.7	311.0	307.3	302.4	296.4	290.4	284.5	278.4	274.1
42.5°	309.1	305.3	301.7	297.9	294.2	289.3	283.1	276.9	270.7	264.5	259.7
45°	289.1	285.3	281.5	277.7	273.9	268.7	262.3	255.8	249.2	242.7	237.9
47.5°	269.1	265.0	260.7	256.6	252.4	247.1	240.6	234.1	227.6	221.1	215.9
50°	254.5	250.5	246.6	242.6	238.6	233.3	226.4	219.6	212.7	205.9	200.6
52.5°	241.5	237.2	232.8	228.5	224.2	218.7	211.9	205.1	198.4	191.6	186.2
55°	219.6	215.4	211.3	207.2	203.0	197.4	190.2	183.0	175.9	168.7	163.8
57.5°	199.3	194.9	190.4	185.8	181.3	175.5	168.3	161.0	153.8	146.7	142.0
60°	185.4	180.8	176.1	171.5	166.8	161.0	154.0	147.0	140.0	133.0	128.4
62.5°	171.4	166.7	162.1	157.5	152.9	147.0	140.0	133.0	126.0	119.0	114.7
65°	150.1	145.4	140.8	136.2	131.5	125.9	119.3	112.7	106.2	99.5	95.4
67.5°	128.7	124.0	119.3	114.6	109.9	104.4	98.1	91.8	85.4	79.2	76.1
70°	114.7	110.1	105.6	101.0	96.5	91.2	85.4	79.4	73.5	67.6	64.7
72.5°	100.8	96.3	91.8	87.2	82.8	77.9	72.5	67.1	61.7	56.3	54.0
75°	79.4	75.3	71.3	67.3	63.2	58.9	54.2	49.6	44.9	40.3	39.5
77.5°	59.9	56.3	52.6	48.9	45.3	42.0	39.0	36.0	33.0	30.0	29.6
80°	47.5	44.0	40.6	37.1	33.7	31.1	29.3	27.5	25.7	24.0	23.6
82.5°	35.6	32.6	29.7	26.7	23.6	21.8	21.0	20.1	19.3	18.4	18.2
85°	20.1	18.3	16.4	14.6	12.7	11.7	11.4	11.2	10.9	10.6	10.4
87.5°	7.4	7.1	6.7	6.3	6.0	6.0	6.4	6.9	7.4	7.8	7.9
90°	0.8	2.6	4.4	6.3	8.1	10.1	12.5	14.8	17.2	19.6	20.2
92.5°	15.2	14.6	14.1	13.6	13.1	13.8	15.5	17.3	19.1	20.9	22.0
95°	49.7	42.2	34.8	27.4	20.0	17.3	19.2	21.3	23.2	25.2	26.5
97.5°	99.8	96.4	93.1	89.8	86.4	78.3	65.3	52.3	39.2	26.2	27.6
100°	137.5	141.1	144.8	148.4	152.0	139.7	111.5	83.2	55.0	26.8	28.3
102.5°	180.5	183.1	185.7	188.3	190.9	176.8	146.0	115.2	84.4	53.6	49.1
105°	242.5	244.5	246.5	248.5	250.5	243.3	227.1	210.8	194.5	178.2	146.2
107.5°	307.9	309.6	311.1	312.7	314.3	316.4	318.9	321.6	324.1	326.7	303.2
110°	351.6	353.0	354.4	355.9	357.3	359.1	361.0	363.1	365.0	367.0	361.0



TEST NUMBER: P332261-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	393.2	394.5	395.8	397.1	398.4	400.1	402.1	404.1	406.0	408.1	408.1
115°	454.9	456.0	457.1	458.2	459.3	460.6	462.2	463.8	465.5	467.1	469.0
117.5°	514.6	516.0	517.3	518.7	520.0	521.1	521.9	522.8	523.6	524.4	525.9
120°	551.7	553.3	555.0	556.6	558.2	559.4	559.9	560.4	561.0	561.5	563.0
122.5°	589.5	590.8	592.2	593.5	594.8	595.9	596.6	597.3	597.9	598.6	599.7
125°	641.2	642.7	644.2	645.6	647.0	648.2	648.9	649.5	650.3	651.0	651.4
127.5°	691.4	692.8	694.3	695.7	697.2	698.3	699.2	700.1	700.9	701.8	702.4
130°	722.7	724.1	725.5	727.0	728.5	729.5	730.3	731.0	731.6	732.4	733.1
132.5°	752.6	754.1	755.5	756.9	758.4	759.4	759.9	760.5	761.2	761.7	762.5
135°	798.3	799.4	800.5	801.6	802.7	803.6	804.3	805.0	805.8	806.5	807.0
137.5°	837.4	838.8	840.2	841.6	842.9	843.8	844.2	844.6	845.0	845.4	846.2
140°	863.4	864.5	865.6	866.7	867.8	868.6	869.1	869.7	870.3	870.7	871.5
142.5°	887.5	888.6	889.7	890.8	891.9	892.7	893.2	893.7	894.3	894.9	895.4
145°	921.2	922.5	923.7	925.0	926.3	927.1	927.5	927.8	928.1	928.5	928.9
147.5°	952.9	953.8	954.6	955.4	956.3	956.8	957.2	957.6	958.0	958.3	958.7
150°	972.5	973.1	973.5	974.1	974.6	975.1	975.4	975.8	976.2	976.6	976.9
152.5°	990.0	990.3	990.6	990.8	991.1	991.3	991.5	991.7	992.0	992.1	992.8
155°	1014.8	1014.4	1014.1	1013.7	1013.3	1013.3	1013.4	1013.6	1013.8	1014.0	1014.9
157.5°	1034.0	1034.0	1034.0	1033.9	1033.9	1033.7	1033.6	1033.4	1033.2	1033.0	1034.1
160°	1045.7	1045.5	1045.4	1045.2	1045.0	1044.8	1044.6	1044.5	1044.2	1044.1	1045.2
162.5°	1056.8	1056.3	1055.8	1055.4	1054.9	1054.6	1054.4	1054.2	1054.0	1053.9	1055.1
165°	1070.2	1069.6	1069.0	1068.5	1068.0	1067.6	1067.4	1067.2	1067.1	1066.9	1068.3
167.5°	1080.5	1079.9	1079.1	1078.4	1077.7	1077.3	1077.3	1077.3	1077.3	1077.3	1078.7
170°	1086.4	1085.7	1085.0	1084.3	1083.5	1083.1	1083.1	1083.1	1083.1	1083.1	1084.6
172.5°	1090.3	1089.5	1088.6	1087.7	1086.9	1086.5	1086.6	1086.8	1086.9	1087.0	1088.5
175°	1095.4	1094.5	1093.6	1092.7	1091.8	1091.4	1091.5	1091.8	1091.9	1092.1	1093.4
177.5°	1096.7	1095.9	1095.2	1094.5	1093.8	1093.5	1093.6	1093.8	1093.9	1094.1	1095.2
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P332261-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4
2.5°	466.5	467.2	468.1	468.3	468.2	468.1	467.9	467.8
5°	463.5	464.2	465.0	465.3	465.1	465.0	464.8	464.6
7.5°	457.0	457.4	457.8	457.9	457.5	457.3	457.0	456.7
10°	451.1	451.2	451.3	451.1	450.7	450.3	449.8	449.4
12.5°	443.8	443.8	443.8	443.4	443.0	442.5	442.0	441.5
15°	431.0	430.6	430.2	429.7	429.2	428.5	428.0	427.4
17.5°	415.9	415.0	414.1	413.2	412.3	411.4	410.6	409.7
20°	405.4	404.3	403.2	402.2	401.1	400.1	399.2	398.1
22.5°	394.3	392.9	391.5	390.4	389.4	388.5	387.5	386.6
25°	375.9	374.2	372.4	371.0	370.1	369.2	368.3	367.4
27.5°	356.0	353.6	351.1	349.2	347.7	346.3	345.0	343.5
30°	341.9	339.0	336.1	334.0	332.6	331.3	330.0	328.6
32.5°	327.9	324.8	321.6	319.4	318.0	316.6	315.1	313.7
35°	307.3	303.6	300.0	297.4	296.0	294.4	292.9	291.4
37.5°	285.1	281.0	276.9	273.9	272.0	270.1	268.2	266.4
40°	269.7	265.3	260.9	257.7	255.8	253.9	251.9	250.0
42.5°	254.9	250.1	245.3	242.1	240.3	238.6	236.8	235.1
45°	233.1	228.3	223.5	220.0	218.1	216.1	214.0	212.0
47.5°	210.6	205.4	200.2	196.7	194.9	193.1	191.2	189.4
50°	195.4	190.2	185.0	181.4	179.4	177.5	175.5	173.6
52.5°	180.8	175.3	169.9	166.3	164.5	162.8	161.1	159.3
55°	158.9	154.0	149.1	145.8	144.1	142.4	140.7	139.0
57.5°	137.4	132.7	128.2	125.1	123.7	122.2	120.8	119.4
60°	123.8	119.3	114.7	111.7	110.3	108.8	107.5	106.0
62.5°	110.4	106.2	101.8	98.9	97.4	96.0	94.4	92.9
65°	91.2	87.2	83.0	80.5	79.5	78.6	77.7	76.7
67.5°	73.0	69.9	66.8	64.7	63.8	62.8	61.8	60.8
70°	61.7	58.8	55.8	53.9	52.9	52.0	51.0	50.1
72.5°	51.5	49.2	46.7	45.3	44.9	44.5	44.2	43.8
75°	38.6	37.7	36.9	36.4	36.2	36.0	35.9	35.7
77.5°	29.1	28.6	28.2	27.9	27.7	27.6	27.4	27.2
80°	23.4	23.2	22.9	22.7	22.5	22.3	22.2	22.0
82.5°	17.9	17.7	17.4	17.3	17.3	17.2	17.2	17.2
85°	10.3	10.1	9.9	9.9	9.9	9.9	9.9	9.9
87.5°	8.0	8.1	8.2	8.2	8.2	8.2	8.2	8.2
90°	21.0	21.7	22.4	23.0	23.3	23.7	24.1	24.4
92.5°	23.2	24.3	25.4	26.2	26.3	26.6	26.8	27.0
95°	27.7	29.0	30.3	30.9	30.9	30.9	30.9	30.9
97.5°	29.1	30.6	32.0	32.8	33.0	33.2	33.3	33.5
100°	29.8	31.2	32.6	33.4	33.7	33.8	34.0	34.2
102.5°	44.6	40.1	35.6	33.5	33.8	34.2	34.5	34.8
105°	114.2	82.2	50.2	34.3	34.7	35.1	35.5	35.8
107.5°	279.7	256.2	232.8	209.0	184.8	160.7	136.6	112.4
110°	355.1	349.1	343.2	327.3	301.3	275.5	249.6	223.8



TEST NUMBER: P332261-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	408.2	408.4	408.5	405.8	400.3	394.8	389.4	383.9
115°	470.8	472.5	474.3	475.6	476.3	477.0	477.8	478.5
117.5°	527.3	528.7	530.2	531.0	531.2	531.2	531.4	531.6
120°	564.4	565.8	567.3	568.0	568.0	568.0	568.0	568.0
122.5°	600.6	601.7	602.7	603.2	603.4	603.6	603.6	603.8
125°	651.8	652.1	652.5	652.8	653.2	653.5	654.0	654.3
127.5°	703.0	703.5	704.1	704.3	703.8	703.5	703.1	702.8
130°	733.9	734.6	735.3	735.5	735.2	734.7	734.4	734.0
132.5°	763.1	763.9	764.6	764.7	764.2	763.7	763.2	762.7
135°	807.6	808.1	808.6	808.6	808.1	807.6	807.0	806.5
137.5°	847.1	848.0	848.8	849.1	848.7	848.4	848.0	847.7
140°	872.2	872.9	873.7	873.8	873.4	873.1	872.8	872.4
142.5°	896.0	896.6	897.2	897.2	896.7	896.2	895.7	895.2
145°	929.3	929.6	930.0	930.2	930.2	930.2	930.2	930.2
147.5°	959.0	959.4	959.8	959.5	958.7	957.9	957.0	956.2
150°	977.3	977.6	978.0	977.9	977.4	976.8	976.2	975.8
152.5°	993.4	994.1	994.7	994.7	993.8	993.0	992.2	991.3
155°	1015.8	1016.7	1017.6	1017.5	1016.4	1015.4	1014.2	1013.2
157.5°	1035.2	1036.2	1037.4	1037.2	1035.8	1034.4	1033.0	1031.6
160°	1046.3	1047.3	1048.4	1048.3	1047.1	1045.8	1044.6	1043.3
162.5°	1056.3	1057.5	1058.7	1058.8	1057.7	1056.5	1055.5	1054.3
165°	1069.8	1071.2	1072.7	1072.8	1071.5	1070.2	1068.9	1067.7
167.5°	1080.2	1081.7	1083.0	1083.0	1081.7	1080.2	1078.7	1077.3
170°	1086.1	1087.5	1088.9	1088.9	1087.5	1086.1	1084.6	1083.1
172.5°	1090.0	1091.4	1092.8	1092.7	1091.2	1089.6	1088.0	1086.4
175°	1094.6	1095.9	1097.1	1097.1	1095.6	1094.2	1092.7	1091.3
177.5°	1096.3	1097.6	1098.7	1098.5	1097.1	1095.7	1094.2	1092.7
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4

(END OF REPORT)