

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832051

Luminaire Tested: S123RDIP-S340D1025U930-4F0-1E-UDD-G1

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832051
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D1025U930-4F0-1E-UDD-G1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4073.7 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 38.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832051

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-G1

Luminous Intensity Polar Plot





TEST NUMBER: P832051

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-G1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	30		
1	94	90	86	83	84	81	78	75	64	62	60	48	47	46	34	33	32	26		
2	86	79	73	68	77	71	66	62	56	53	50	43	41	39	30	29	28	22		
3	78	70	63	58	70	63	57	53	50	46	43	38	36	33	27	26	24	20		
4	72	62	55	49	64	56	50	45	45	40	37	34	31	29	25	23	22	17		
5	66	55	48	42	59	50	44	39	40	36	32	31	28	26	23	21	19	15		
6	61	50	42	37	55	45	39	34	36	32	28	28	25	23	21	19	17	14		
7	57	45	38	32	51	41	35	30	33	28	25	26	23	20	19	17	15	13		
8	53	41	34	29	47	37	31	27	30	26	22	24	21	18	18	16	14	12		
9	49	37	30	26	44	34	28	24	28	23	20	22	19	17	16	14	13	11		
10	46	34	28	23	41	31	25	21	26	21	18	20	17	15	15	13	12	10		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	9749	9749	9749	9749	9749
5°	11577	11207	9811	7931	7363
10°	10488	11384	9762	6355	5451
15°	7221	9760	9658	5194	4313
20°	5024	7514	9465	4379	3790
25°	3828	5727	9183	3892	3493
30°	3332	4579	8830	3614	3235
35°	3059	3862	8330	3380	3001
40°	2792	3450	7676	3149	2786
45°	2521	3154	6970	2930	2573
50°	2289	2910	6137	2718	2308
55°	2070	2672	5339	2509	1980
60°	1856	2430	4637	2278	1871
65°	1712	2157	3991	2048	1768
70°	1391	1863	3484	1854	1438
75°	1219	1485	2949	1535	1268
80°	1103	1252	2417	1289	1196
85°	1013	1099	1840	1173	1099

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 7354 cd/sqm



TEST NUMBER: P832051

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-G1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.6	2.0
10°-20°	191.0	4.7
20°-30°	219.2	5.4
30°-40°	216.0	5.3
40°-50°	190.5	4.7
50°-60°	146.6	3.6
60°-70°	96.4	2.4
70°-80°	46.8	1.1
80°-90°	14.0	0.3
90°-100°	66.7	1.6
100°-110°	201.9	5.0
110°-120°	343.6	8.4
120°-130°	452.1	11.1
130°-140°	508.1	12.5
140°-150°	499.6	12.3
150°-160°	420.6	10.3
160°-170°	280.0	6.9
170°-180°	98.0	2.4
0°-30°	492.8	12.1
0°-40°	708.8	17.4
0°-60°	1045.9	25.7
0°-90°	1203.1	29.5
90°-120°	612.2	15.0
90°-150°	2072.0	50.9
90°-180°	2871.0	70.5
0°-180°	4073.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	906	906	906	906	906	
5°	1071	1037	908	734	681	98
15°	648	876	867	466	387	183
25°	322	482	773	328	294	152
35°	233	294	634	257	228	145
45°	166	207	458	192	169	129
55°	110	142	284	134	106	99
65°	67	85	157	80	69	66
75°	29	36	71	37	30	32
85°	8	9	15	10	9	9
90°	24	20	1	20	24	12
95°	64	60	48	60	64	64
105°	194	192	183	192	194	205
115°	347	347	346	347	347	343
125°	500	507	506	507	500	448
135°	656	661	657	661	656	505
145°	797	801	797	801	797	498
155°	911	913	912	913	911	420
165°	990	991	994	991	990	279
175°	1030	1030	1034	1030	1030	98
180°	1036	1036	1036	1036	1036	



TEST NUMBER: P832051

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7
2.5°	1003.8	1000.6	997.5	996.5	995.6	992.6	989.7	983.0	976.3	969.4	962.6
5°	1071.4	1071.7	1072.1	1071.2	1070.2	1066.3	1062.4	1054.3	1046.1	1037.2	1028.3
7.5°	1050.6	1056.5	1062.4	1063.6	1064.7	1067.6	1070.6	1068.8	1066.9	1063.6	1060.2
10°	959.6	959.2	958.8	965.5	972.2	992.1	1011.9	1022.2	1032.4	1041.5	1050.6
12.5°	811.0	811.6	812.2	834.1	856.0	874.7	893.5	919.5	945.5	973.5	1001.5
15°	648.0	657.1	666.2	685.7	705.2	733.4	761.7	796.6	831.5	875.8	920.2
17.5°	532.2	536.1	540.0	558.7	577.5	604.2	630.9	670.5	710.0	767.2	824.4
20°	438.6	442.1	445.6	459.2	472.7	498.4	524.0	561.7	599.4	656.0	712.6
22.5°	366.2	373.0	379.9	389.0	398.1	416.7	435.2	473.7	512.1	563.7	615.3
25°	322.3	325.5	328.7	336.4	344.2	362.1	379.9	405.3	430.8	482.2	533.6
27.5°	292.6	293.6	294.5	300.2	306.0	317.5	329.0	352.6	376.2	418.5	460.9
30°	268.1	269.8	271.5	275.9	280.4	288.7	297.1	313.8	330.5	368.4	406.3
32.5°	249.2	250.1	251.0	254.8	258.5	264.6	270.7	283.9	297.1	326.1	355.0
35°	232.8	233.0	233.2	236.0	238.8	244.7	250.7	261.6	272.6	293.9	315.3
37.5°	214.3	215.6	216.9	218.9	221.0	226.2	231.4	240.3	249.2	266.8	284.5
40°	198.7	199.8	200.9	203.3	205.7	209.8	213.9	222.1	230.2	245.5	260.7
42.5°	183.1	183.8	184.6	187.0	189.4	194.4	199.4	205.9	212.4	225.0	237.7
45°	165.6	167.5	169.3	171.9	174.5	178.8	183.1	189.8	196.4	207.2	218.0
47.5°	151.1	152.1	153.0	155.2	157.5	162.7	167.9	173.8	179.7	189.8	199.8
50°	136.7	137.0	137.4	139.4	141.5	146.1	150.8	157.6	164.5	173.8	183.1
52.5°	122.9	123.8	124.8	126.8	128.9	132.0	135.2	142.2	149.3	158.4	167.5
55°	110.3	110.8	111.4	112.9	114.4	118.1	121.8	127.9	134.1	142.4	150.8
57.5°	98.4	99.2	99.9	101.0	102.1	105.5	108.8	114.2	119.6	127.9	136.3
60°	86.2	87.1	88.0	89.3	90.6	93.2	95.8	100.6	105.5	112.9	120.3
62.5°	77.2	77.4	77.6	78.7	79.8	81.7	83.6	87.5	91.4	98.8	106.2
65°	67.2	67.8	68.3	68.9	69.4	70.9	72.4	75.8	79.1	84.7	90.2
67.5°	56.8	57.4	57.9	58.9	59.8	61.1	62.4	64.6	66.8	72.0	77.2
70°	44.2	44.2	44.2	45.7	47.2	49.4	51.6	53.3	55.0	59.2	63.5
72.5°	36.0	36.2	36.4	36.6	36.8	38.1	39.4	42.1	44.9	47.5	50.1
75°	29.3	29.5	29.7	29.9	30.1	30.5	30.8	31.8	32.7	35.7	38.6
77.5°	23.4	23.6	23.8	24.0	24.1	24.5	24.9	25.3	25.6	26.7	27.9
80°	17.8	18.0	18.2	18.4	18.6	18.8	18.9	19.3	19.7	20.2	20.8
82.5°	13.0	13.0	13.0	13.0	13.0	13.4	13.7	13.7	13.7	14.1	14.5
85°	8.2	8.2	8.2	8.4	8.5	8.5	8.5	8.7	8.9	8.9	8.9
87.5°	3.7	3.5	3.3	3.5	3.7	3.7	3.7	3.9	4.1	4.1	4.1
90°	24.4	24.1	23.7	23.3	23.0	22.4	21.7	21.0	20.3	19.5	17.2
92.5°	35.0	35.4	35.7	36.1	36.4	36.4	35.8	35.3	34.7	34.2	33.1
95°	63.5	63.5	63.5	63.5	63.5	63.1	62.4	61.7	60.9	60.2	58.8
97.5°	91.1	91.3	91.5	91.7	91.9	91.5	90.6	89.7	88.8	87.9	86.8
100°	123.7	123.3	123.0	122.6	122.3	121.8	121.3	120.7	120.2	119.6	118.7
102.5°	157.1	157.3	157.4	157.6	157.8	157.6	157.1	156.5	156.0	155.4	154.2
105°	193.7	193.3	193.0	192.6	192.2	192.1	192.1	192.1	192.1	192.1	190.4
107.5°	231.1	231.3	231.5	231.7	231.9	231.7	231.1	230.6	230.0	229.5	228.8
110°	269.4	269.7	270.1	270.5	270.8	270.6	269.9	269.2	268.5	267.8	267.4



TEST NUMBER: P832051

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	310.1	310.1	310.1	310.1	310.1	309.6	308.7	307.8	306.9	306.0	306.0
115°	346.7	346.9	347.1	347.2	347.4	347.4	347.2	347.1	346.9	346.7	347.1
117.5°	384.1	384.7	385.2	385.8	386.3	386.6	386.6	386.6	386.6	386.6	386.9
120°	424.0	424.4	424.7	425.1	425.5	425.7	425.9	426.1	426.3	426.5	427.4
122.5°	462.3	462.8	463.3	463.9	464.4	465.0	465.5	466.1	466.6	467.1	467.5
125°	500.5	501.2	502.0	502.7	503.4	504.1	504.9	505.6	506.3	507.0	507.4
127.5°	538.8	539.5	540.2	540.9	541.7	542.6	543.6	544.7	545.8	546.9	547.3
130°	576.2	577.5	578.7	580.0	581.3	582.3	583.0	583.7	584.4	585.1	585.7
132.5°	615.3	616.2	617.1	618.0	618.9	619.8	620.7	621.6	622.5	623.4	623.8
135°	656.0	656.3	656.7	657.0	657.4	657.9	658.7	659.4	660.1	660.8	661.0
137.5°	691.8	692.3	692.8	693.4	693.9	694.7	695.6	696.5	697.4	698.3	697.7
140°	726.8	728.0	729.3	730.6	731.8	732.5	732.7	732.9	733.1	733.3	733.1
142.5°	762.6	763.5	764.4	765.3	766.2	766.7	766.9	767.1	767.3	767.4	767.1
145°	796.7	797.5	798.2	798.9	799.6	800.1	800.3	800.5	800.6	800.8	800.3
147.5°	827.7	828.8	829.8	830.9	832.0	832.6	832.6	832.6	832.6	832.6	832.0
150°	857.0	858.1	859.1	860.2	861.3	861.9	861.9	861.9	861.9	861.9	861.5
152.5°	885.5	886.4	887.3	888.2	889.1	889.3	889.0	888.6	888.3	887.9	887.7
155°	910.7	912.0	913.2	914.5	915.7	916.0	915.3	914.6	913.8	913.1	912.9
157.5°	934.3	935.4	936.5	937.5	938.6	938.8	938.1	937.4	936.6	935.9	935.7
160°	957.1	957.8	958.5	959.2	960.0	959.9	959.0	958.1	957.2	956.3	956.3
162.5°	974.2	975.4	976.7	978.0	979.2	979.4	978.5	977.6	976.7	975.8	975.6
165°	990.4	991.7	993.0	994.2	995.5	995.6	994.5	993.4	992.3	991.3	991.3
167.5°	1005.1	1006.2	1007.3	1008.3	1009.4	1009.4	1008.3	1007.3	1006.2	1005.1	1004.9
170°	1015.7	1016.9	1018.2	1019.5	1020.7	1020.7	1019.5	1018.2	1016.9	1015.7	1015.7
172.5°	1023.8	1025.1	1026.3	1027.6	1028.9	1029.0	1027.9	1026.8	1025.7	1024.6	1024.6
175°	1029.5	1030.8	1032.0	1033.3	1034.6	1034.7	1033.6	1032.5	1031.4	1030.3	1030.3
177.5°	1032.8	1034.0	1035.3	1036.6	1037.8	1037.9	1036.8	1035.7	1034.7	1033.6	1033.6
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P832051

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7
2.5°	961.6	960.7	951.8	942.9	934.1	925.4	918.9	912.4	901.5	890.5	883.6
5°	1021.2	1014.2	1000.1	986.0	964.8	943.6	925.8	908.0	885.3	862.7	843.7
7.5°	1054.5	1048.7	1031.6	1014.5	986.5	958.5	930.6	902.8	869.3	835.9	807.3
10°	1055.4	1060.2	1046.1	1032.0	1000.4	968.9	931.0	893.1	848.2	803.2	766.3
12.5°	1022.3	1043.1	1040.2	1037.2	1005.1	973.0	926.9	880.9	825.7	770.6	724.3
15°	960.5	1000.8	1012.7	1024.6	998.0	971.5	919.1	866.7	801.9	737.1	684.0
17.5°	880.9	937.3	968.7	1000.1	980.8	961.4	904.1	846.7	773.7	700.7	643.0
20°	786.5	860.4	909.6	958.8	951.8	944.7	885.5	826.3	747.5	668.8	606.2
22.5°	693.3	771.3	839.3	907.2	914.5	921.7	861.9	802.1	716.0	629.8	566.1
25°	612.9	692.2	773.2	854.1	870.5	886.8	830.0	773.2	683.9	594.5	531.2
27.5°	536.2	611.6	700.7	789.9	819.6	849.3	797.3	745.3	652.3	559.3	496.1
30°	473.7	541.1	632.0	723.0	764.4	805.8	758.1	710.4	618.1	525.8	464.0
32.5°	415.4	475.7	567.1	658.4	706.5	754.6	713.4	672.2	583.4	494.6	433.6
35°	369.3	423.3	508.6	593.8	647.6	701.5	667.7	633.9	547.2	460.5	402.7
37.5°	329.8	375.1	455.1	535.1	592.3	649.5	621.3	593.1	511.5	430.0	375.4
40°	297.1	333.5	407.9	482.4	538.5	594.5	570.4	546.3	473.3	400.3	349.3
42.5°	269.0	300.4	367.3	434.1	485.5	537.0	521.0	505.0	438.9	372.8	325.5
45°	244.4	270.7	329.6	388.4	435.8	483.1	470.5	457.9	400.9	343.9	300.4
47.5°	222.4	245.1	297.6	350.2	392.7	435.2	423.5	411.8	364.7	317.5	278.0
50°	202.4	221.7	265.5	309.3	347.6	385.8	376.2	366.5	327.5	288.5	254.4
52.5°	183.4	199.4	238.8	278.1	309.0	339.8	332.4	324.9	294.9	264.8	233.8
55°	165.4	180.1	213.3	246.6	272.9	299.3	291.9	284.5	261.1	237.7	210.4
57.5°	149.1	161.9	188.8	215.8	236.7	257.7	254.2	250.7	231.2	211.7	189.2
60°	131.8	143.3	166.6	189.8	206.7	223.6	219.5	215.4	201.5	187.5	168.2
62.5°	116.4	126.6	145.2	163.8	177.5	191.2	188.3	185.3	174.7	164.1	148.2
65°	100.3	110.3	125.3	140.4	151.1	161.9	159.3	156.7	148.7	140.7	127.9
67.5°	85.6	94.0	107.0	119.9	127.2	134.4	132.9	131.5	125.3	119.2	109.2
70°	70.7	78.0	88.8	99.5	104.5	109.6	110.1	110.7	105.1	99.5	92.1
72.5°	55.9	61.6	71.7	81.7	85.6	89.5	89.3	89.1	85.8	82.4	75.8
75°	42.9	47.2	55.0	62.8	66.1	69.4	70.2	70.9	67.8	64.6	60.9
77.5°	30.8	33.8	39.7	45.7	49.4	53.1	53.5	53.8	52.4	50.9	47.3
80°	21.7	22.7	26.4	30.1	34.0	37.9	38.4	39.0	37.5	36.0	33.8
82.5°	15.0	15.6	16.9	18.2	21.4	24.5	25.3	26.0	25.3	24.5	22.1
85°	9.1	9.3	9.8	10.4	11.9	13.4	14.1	14.9	14.5	14.1	12.8
87.5°	4.1	4.1	4.3	4.5	4.8	5.2	6.1	7.1	6.5	5.9	5.4
90°	14.8	12.5	10.1	8.0	6.2	4.4	2.6	0.8	2.6	4.4	6.2
92.5°	32.0	30.9	29.8	28.8	27.7	26.6	25.5	24.4	25.5	26.6	27.7
95°	57.3	55.9	54.4	53.1	51.8	50.5	49.3	48.0	49.3	50.5	51.8
97.5°	85.7	84.6	83.6	82.6	81.7	80.8	79.8	78.9	79.8	80.8	81.7
100°	117.8	116.9	116.0	115.0	113.9	112.9	111.8	110.7	111.8	112.9	113.9
102.5°	152.9	151.6	150.4	149.5	148.9	148.4	147.8	147.3	147.8	148.4	148.9
105°	188.8	187.2	185.6	184.6	184.2	183.8	183.5	183.1	183.5	183.8	184.2
107.5°	228.1	227.3	226.6	226.2	226.0	225.8	225.6	225.4	225.6	225.8	226.0
110°	267.0	266.7	266.3	265.9	265.6	265.2	264.9	264.5	264.9	265.2	265.6



TEST NUMBER: P832051

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	306.0	306.0	306.0	305.9	305.7	305.6	305.4	305.2	305.4	305.6	305.7
115°	347.4	347.8	348.1	348.1	347.5	347.0	346.4	345.9	346.4	347.0	347.5
117.5°	387.3	387.7	388.0	388.1	387.9	387.7	387.6	387.4	387.6	387.7	387.9
120°	428.3	429.2	430.1	430.0	428.9	427.8	426.7	425.6	426.7	427.8	428.9
122.5°	467.9	468.2	468.6	468.4	467.7	467.0	466.2	465.5	466.2	467.0	467.7
125°	507.7	508.1	508.5	508.4	507.8	507.3	506.7	506.2	506.7	507.3	507.8
127.5°	547.6	548.0	548.3	548.0	546.9	545.8	544.7	543.6	544.7	545.8	546.9
130°	586.2	586.8	587.3	586.9	585.4	584.0	582.5	581.1	582.5	584.0	585.4
132.5°	624.1	624.5	624.8	624.3	622.9	621.4	620.0	618.5	620.0	621.4	622.9
135°	661.2	661.4	661.6	661.1	660.0	658.9	657.9	656.8	657.9	658.9	660.0
137.5°	697.2	696.6	696.1	695.4	694.5	693.6	692.7	691.8	692.7	693.6	694.5
140°	732.9	732.7	732.5	732.0	731.1	730.2	729.3	728.4	729.3	730.2	731.1
142.5°	766.7	766.4	766.0	765.4	764.5	763.6	762.7	761.8	762.7	763.6	764.5
145°	799.7	799.2	798.6	798.2	797.8	797.5	797.1	796.7	797.1	797.5	797.8
147.5°	831.5	830.9	830.4	829.8	829.0	828.3	827.6	826.9	827.6	828.3	829.0
150°	861.1	860.8	860.4	860.0	859.7	859.3	859.0	858.6	859.0	859.3	859.7
152.5°	887.5	887.4	887.2	886.8	886.3	885.7	885.2	884.6	885.2	885.7	886.3
155°	912.8	912.6	912.4	912.3	912.3	912.3	912.3	912.3	912.3	912.3	912.3
157.5°	935.6	935.4	935.2	935.2	935.4	935.6	935.7	935.9	935.7	935.6	935.4
160°	956.3	956.3	956.3	956.4	956.8	957.2	957.5	957.9	957.5	957.2	956.8
162.5°	975.4	975.2	975.1	975.2	975.8	976.3	976.9	977.4	976.9	976.3	975.8
165°	991.3	991.3	991.3	991.5	992.1	992.6	993.2	993.7	993.2	992.6	992.1
167.5°	1004.7	1004.5	1004.4	1004.6	1005.4	1006.1	1006.8	1007.5	1006.8	1006.1	1005.4
170°	1015.7	1015.7	1015.7	1016.0	1016.8	1017.5	1018.2	1018.9	1018.2	1017.5	1016.8
172.5°	1024.6	1024.6	1024.6	1025.0	1025.7	1026.4	1027.2	1027.9	1027.2	1026.4	1025.7
175°	1030.3	1030.3	1030.3	1030.7	1031.4	1032.1	1032.9	1033.6	1032.9	1032.1	1031.4
177.5°	1033.6	1033.6	1033.6	1033.9	1034.7	1035.4	1036.1	1036.8	1036.1	1035.4	1034.7
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P832051

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7
2.5°	876.8	866.2	855.6	848.0	840.4	830.9	821.4	821.1	820.7	813.6	806.6
5°	824.8	806.4	788.0	770.0	752.0	734.0	716.0	711.9	707.8	701.7	695.6
7.5°	778.7	749.4	720.1	697.0	674.0	656.0	638.0	625.7	613.5	604.0	594.5
10°	729.3	693.0	656.6	628.7	600.9	581.4	561.9	547.8	533.6	527.0	520.3
12.5°	678.1	638.5	599.0	571.7	544.4	521.0	497.6	484.8	472.0	462.7	453.4
15°	630.9	588.4	545.9	516.9	488.0	466.1	444.1	431.3	418.5	409.2	400.0
17.5°	585.3	542.4	499.5	470.1	440.8	420.9	401.1	388.6	376.2	370.4	364.7
20°	543.7	500.4	457.1	429.5	401.8	382.3	362.8	356.1	349.4	344.1	338.7
22.5°	502.4	460.9	419.3	392.7	366.2	352.0	337.9	332.5	327.2	323.1	319.0
25°	467.9	426.5	385.1	361.9	338.7	327.7	316.8	313.2	309.7	305.6	301.5
27.5°	433.0	393.6	354.3	335.7	317.1	308.2	299.3	294.9	290.4	287.1	283.7
30°	402.2	365.8	329.4	314.0	298.6	290.8	283.0	278.1	273.3	270.2	267.0
32.5°	372.5	340.2	307.9	294.7	281.5	273.9	266.3	261.6	257.0	253.3	249.6
35°	345.0	317.0	288.9	276.8	264.8	257.2	249.6	244.9	240.3	236.6	232.8
37.5°	320.9	295.4	270.0	258.6	247.3	240.6	234.0	229.1	224.3	220.4	216.5
40°	298.2	275.7	253.3	242.3	231.4	224.1	216.9	212.6	208.3	204.8	201.3
42.5°	278.1	257.5	236.9	226.2	215.4	208.5	201.6	196.6	191.6	189.6	187.5
45°	257.0	238.8	220.6	210.2	199.8	192.5	185.3	181.0	176.8	174.9	173.1
47.5°	238.4	221.5	204.6	194.4	184.2	177.7	171.2	167.9	164.5	161.9	159.3
50°	220.2	203.9	187.5	177.7	167.9	162.3	156.7	152.6	148.5	146.7	144.8
52.5°	202.8	187.9	173.1	163.0	153.0	147.6	142.2	138.7	135.2	131.3	127.4
55°	183.1	170.1	157.1	148.2	139.3	133.7	128.1	124.0	119.9	115.9	111.8
57.5°	166.7	153.9	141.1	133.1	125.1	119.8	114.4	109.9	105.5	102.1	98.8
60°	148.9	137.8	126.6	118.8	111.0	105.8	100.6	96.4	92.1	90.4	88.8
62.5°	132.2	121.8	111.4	104.5	97.7	92.7	87.6	84.9	82.1	81.0	79.8
65°	115.1	106.2	97.3	91.0	84.7	80.4	76.1	74.8	73.5	72.6	71.7
67.5°	99.2	91.5	83.9	78.4	72.8	69.8	66.8	65.4	63.9	62.8	61.6
70°	84.7	78.0	71.3	66.5	61.6	58.9	56.1	54.8	53.5	51.4	49.4
72.5°	69.1	63.9	58.7	55.0	51.2	48.8	46.4	43.8	41.2	39.4	37.5
75°	57.2	52.0	46.8	43.3	39.7	36.9	34.2	33.2	32.3	31.8	31.2
77.5°	43.8	39.4	34.9	32.1	29.3	28.0	26.7	26.2	25.6	25.4	25.3
80°	31.6	27.9	24.1	22.7	21.2	20.8	20.4	20.1	19.7	19.5	19.3
82.5°	19.7	17.8	16.0	15.6	15.2	15.0	14.9	14.7	14.5	14.3	14.1
85°	11.5	10.8	10.0	9.8	9.7	9.5	9.3	9.3	9.3	9.3	9.3
87.5°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.6	4.5
90°	8.0	10.1	12.5	14.8	17.2	19.5	20.3	21.0	21.7	22.4	23.0
92.5°	28.8	29.8	30.9	32.0	33.1	34.2	34.7	35.3	35.8	36.4	36.4
95°	53.1	54.4	55.9	57.3	58.8	60.2	60.9	61.7	62.4	63.1	63.5
97.5°	82.6	83.6	84.6	85.7	86.8	87.9	88.8	89.7	90.6	91.5	91.9
100°	115.0	116.0	116.9	117.8	118.7	119.6	120.2	120.7	121.3	121.8	122.3
102.5°	149.5	150.4	151.6	152.9	154.2	155.4	156.0	156.5	157.1	157.6	157.8
105°	184.6	185.6	187.2	188.8	190.4	192.1	192.1	192.1	192.1	192.1	192.2
107.5°	226.2	226.6	227.3	228.1	228.8	229.5	230.0	230.6	231.1	231.7	231.9
110°	265.9	266.3	266.7	267.0	267.4	267.8	268.5	269.2	269.9	270.6	270.8



TEST NUMBER: P832051

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	305.9	306.0	306.0	306.0	306.0	306.0	306.9	307.8	308.7	309.6	310.1
115°	348.1	348.1	347.8	347.4	347.1	346.7	346.9	347.1	347.2	347.4	347.4
117.5°	388.1	388.0	387.7	387.3	386.9	386.6	386.6	386.6	386.6	386.6	386.3
120°	430.0	430.1	429.2	428.3	427.4	426.5	426.3	426.1	425.9	425.7	425.5
122.5°	468.4	468.6	468.2	467.9	467.5	467.1	466.6	466.1	465.5	465.0	464.4
125°	508.4	508.5	508.1	507.7	507.4	507.0	506.3	505.6	504.9	504.1	503.4
127.5°	548.0	548.3	548.0	547.6	547.3	546.9	545.8	544.7	543.6	542.6	541.7
130°	586.9	587.3	586.8	586.2	585.7	585.1	584.4	583.7	583.0	582.3	581.3
132.5°	624.3	624.8	624.5	624.1	623.8	623.4	622.5	621.6	620.7	619.8	618.9
135°	661.1	661.6	661.4	661.2	661.0	660.8	660.1	659.4	658.7	657.9	657.4
137.5°	695.4	696.1	696.6	697.2	697.7	698.3	697.4	696.5	695.6	694.7	693.9
140°	732.0	732.5	732.7	732.9	733.1	733.3	733.1	732.9	732.7	732.5	731.8
142.5°	765.4	766.0	766.4	766.7	767.1	767.4	767.3	767.1	766.9	766.7	766.2
145°	798.2	798.6	799.2	799.7	800.3	800.8	800.6	800.5	800.3	800.1	799.6
147.5°	829.8	830.4	830.9	831.5	832.0	832.6	832.6	832.6	832.6	832.6	832.0
150°	860.0	860.4	860.8	861.1	861.5	861.9	861.9	861.9	861.9	861.9	861.3
152.5°	886.8	887.2	887.4	887.5	887.7	887.9	888.3	888.6	889.0	889.3	889.1
155°	912.3	912.4	912.6	912.8	912.9	913.1	913.8	914.6	915.3	916.0	915.7
157.5°	935.2	935.2	935.4	935.6	935.7	935.9	936.6	937.4	938.1	938.8	938.6
160°	956.4	956.3	956.3	956.3	956.3	956.3	957.2	958.1	959.0	959.9	960.0
162.5°	975.2	975.1	975.2	975.4	975.6	975.8	976.7	977.6	978.5	979.4	979.2
165°	991.5	991.3	991.3	991.3	991.3	991.3	992.3	993.4	994.5	995.6	995.5
167.5°	1004.6	1004.4	1004.5	1004.7	1004.9	1005.1	1006.2	1007.3	1008.3	1009.4	1009.4
170°	1016.0	1015.7	1015.7	1015.7	1015.7	1015.7	1016.9	1018.2	1019.5	1020.7	1020.7
172.5°	1025.0	1024.6	1024.6	1024.6	1024.6	1024.6	1025.7	1026.8	1027.9	1029.0	1028.9
175°	1030.7	1030.3	1030.3	1030.3	1030.3	1030.3	1031.4	1032.5	1033.6	1034.7	1034.6
177.5°	1033.9	1033.6	1033.6	1033.6	1033.6	1033.6	1034.7	1035.7	1036.8	1037.9	1037.8
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P832051

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	905.7	905.7	905.7	905.7
2.5°	804.7	802.9	802.1	801.4
5°	689.8	684.0	682.7	681.4
7.5°	592.1	589.7	581.7	573.7
10°	512.8	505.4	502.1	498.7
12.5°	446.6	439.7	438.6	437.5
15°	395.1	390.3	388.6	387.0
17.5°	361.3	358.0	355.9	353.9
20°	336.3	333.8	332.4	330.9
22.5°	317.1	315.3	314.2	313.1
25°	298.8	296.0	295.0	294.1
27.5°	281.3	278.9	278.0	277.0
30°	265.0	262.9	261.6	260.3
32.5°	247.1	244.7	244.0	243.2
35°	231.4	229.9	229.1	228.4
37.5°	214.6	212.8	211.7	210.6
40°	200.3	199.4	198.9	198.3
42.5°	185.9	184.2	184.0	183.8
45°	171.4	169.7	169.3	169.0
47.5°	157.8	156.3	156.2	156.0
50°	142.8	140.7	139.3	137.8
52.5°	125.5	123.7	122.4	121.1
55°	109.7	107.7	106.6	105.5
57.5°	97.9	96.9	96.4	95.8
60°	88.2	87.6	87.3	86.9
62.5°	79.3	78.7	78.7	78.7
65°	71.1	70.6	70.0	69.4
67.5°	60.5	59.4	59.2	59.0
70°	47.7	46.0	45.9	45.7
72.5°	37.3	37.1	36.8	36.4
75°	30.8	30.5	30.5	30.5
77.5°	24.9	24.5	24.5	24.5
80°	19.1	18.9	19.1	19.3
82.5°	14.1	14.1	13.9	13.7
85°	9.1	8.9	8.9	8.9
87.5°	4.5	4.5	4.5	4.5
90°	23.3	23.7	24.1	24.4
92.5°	36.1	35.7	35.4	35.0
95°	63.5	63.5	63.5	63.5
97.5°	91.7	91.5	91.3	91.1
100°	122.6	123.0	123.3	123.7
102.5°	157.6	157.4	157.3	157.1
105°	192.6	193.0	193.3	193.7
107.5°	231.7	231.5	231.3	231.1
110°	270.5	270.1	269.7	269.4



TEST NUMBER: P832051

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	310.1	310.1	310.1	310.1
115°	347.2	347.1	346.9	346.7
117.5°	385.8	385.2	384.7	384.1
120°	425.1	424.7	424.4	424.0
122.5°	463.9	463.3	462.8	462.3
125°	502.7	502.0	501.2	500.5
127.5°	540.9	540.2	539.5	538.8
130°	580.0	578.7	577.5	576.2
132.5°	618.0	617.1	616.2	615.3
135°	657.0	656.7	656.3	656.0
137.5°	693.4	692.8	692.3	691.8
140°	730.6	729.3	728.0	726.8
142.5°	765.3	764.4	763.5	762.6
145°	798.9	798.2	797.5	796.7
147.5°	830.9	829.8	828.8	827.7
150°	860.2	859.1	858.1	857.0
152.5°	888.2	887.3	886.4	885.5
155°	914.5	913.2	912.0	910.7
157.5°	937.5	936.5	935.4	934.3
160°	959.2	958.5	957.8	957.1
162.5°	978.0	976.7	975.4	974.2
165°	994.2	993.0	991.7	990.4
167.5°	1008.3	1007.3	1006.2	1005.1
170°	1019.5	1018.2	1016.9	1015.7
172.5°	1027.6	1026.3	1025.1	1023.8
175°	1033.3	1032.0	1030.8	1029.5
177.5°	1036.6	1035.3	1034.0	1032.8
180°	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P832051

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-G1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.35	7.02	7.47	8.13	9.67	11.01	11.69	12.13	12.80	14.34
	3H	7.56	8.16	8.69	9.28	10.84	12.50	13.10	13.63	14.22	15.78
	4H	7.93	8.50	9.07	9.62	11.19	12.98	13.55	14.12	14.67	16.23
	6H	8.20	8.73	9.35	9.85	11.43	13.28	13.81	14.43	14.93	16.51
	8H	8.29	8.79	9.44	9.93	11.49	13.36	13.86	14.51	15.00	16.56
	12H	8.34	8.81	9.49	9.94	11.53	13.39	13.86	14.54	14.99	16.58
4H	2H	7.05	7.62	8.20	8.74	10.31	10.99	11.56	12.14	12.68	14.24
	3H	8.41	8.88	9.56	10.03	11.60	12.63	13.11	13.78	14.25	15.83
	4H	8.86	9.29	10.01	10.43	12.02	13.23	13.67	14.39	14.81	16.40
	6H	9.22	9.59	10.38	10.75	12.33	13.66	14.04	14.82	15.19	16.78
	8H	9.34	9.69	10.50	10.84	12.44	13.79	14.14	14.95	15.29	16.89
	12H	9.41	9.73	10.59	10.89	12.49	13.85	14.16	15.02	15.32	16.93
8H	4H	9.16	9.51	10.32	10.66	12.26	13.19	13.54	14.35	14.69	16.29
	6H	9.62	9.91	10.80	11.10	12.69	13.68	13.97	14.86	15.16	16.76
	8H	9.81	10.06	11.00	11.23	12.85	13.87	14.12	15.05	15.29	16.90
	12H	9.95	10.17	11.14	11.34	12.99	13.98	14.20	15.16	15.36	17.01
12H	4H	9.16	9.48	10.34	10.64	12.25	13.13	13.45	14.31	14.61	16.21
	6H	9.68	9.93	10.86	11.10	12.71	13.65	13.91	14.84	15.08	16.69
	8H	9.89	10.11	11.08	11.28	12.93	13.84	14.06	15.03	15.23	16.88