

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332265-930

Luminaire Tested: **S123RDIP-S340D1195U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332265-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D1195U930-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4449.4 lumens  
Efficiency: N/A  
Efficacy: 105.4 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332265-930

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332265-930

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	25				25
1	92	88	85	81	82	79	76	73	61	59	57	45	43	42	30	29	28	22				22
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	26	25	24	18				18
3	77	68	61	56	68	61	55	51	48	44	40	35	33	31	24	22	21	16				16
4	71	60	53	47	63	54	48	43	42	38	35	31	29	26	21	20	18	14				14
5	65	54	46	41	57	48	42	37	38	33	30	28	25	23	19	17	16	12				12
6	60	48	41	35	53	43	37	32	34	29	26	26	22	20	18	16	14	11				11
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10				10
8	51	39	32	27	45	35	29	25	28	24	20	21	18	16	15	13	11	9				9
9	47	36	29	24	42	32	26	22	26	21	18	19	16	14	14	12	10	8				8
10	44	33	26	21	39	30	24	20	24	19	16	18	15	13	13	11	9	7				7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4776	4776	4776	4776
5°	5693	4796	4224	4796
10°	7109	4769	3816	4769
15°	8344	4719	3480	4719
20°	9313	4647	3194	4647
25°	9164	4570	3018	4570
30°	6586	4501	2838	4501
35°	4398	4407	2720	4407
40°	3240	4297	2599	4297
45°	2719	4102	2481	4102
50°	2398	3848	2316	3848
55°	2104	3558	2089	3558
60°	1873	3279	1914	3279
65°	1645	2980	1780	2980
70°	1290	2716	1627	2716
75°	1135	2371	1485	2371
80°	992	2008	1463	2008
85°	790	1618	1556	1618



TEST NUMBER: P332265-930

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	43.6	1.0
10°-20°	136.3	3.1
20°-30°	214.2	4.8
30°-40°	223.4	5.0
40°-50°	191.2	4.3
50°-60°	145.7	3.3
60°-70°	93.4	2.1
70°-80°	44.9	1.0
80°-90°	15.5	0.3
90°-100°	78.6	1.8
100°-110°	235.1	5.3
110°-120°	399.9	9.0
120°-130°	526.0	11.8
130°-140°	591.2	13.3
140°-150°	581.2	13.1
150°-160°	489.3	11.0
160°-170°	325.7	7.3
170°-180°	114.0	2.6
0°-30°	394.1	8.9
0°-40°	617.6	13.9
0°-60°	954.5	21.5
0°-90°	1108.3	24.9
90°-120°	713.6	16.0
90°-150°	2412.1	54.2
90°-180°	3341.0	75.1
0°-180°	4449.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	444	444	444	444	444	
5°	527	444	391	444	527	54
15°	749	424	312	424	749	212
25°	772	385	254	385	772	332
35°	335	335	207	335	335	219
45°	179	270	163	270	179	140
55°	112	190	111	190	112	101
65°	65	117	70	117	65	64
75°	27	57	36	57	27	29
85°	6	13	13	13	6	8
90°	28	1	28	1	28	14
95°	74	56	74	56	74	76
105°	225	213	225	213	225	239
115°	404	403	404	403	404	400
125°	583	589	583	589	583	521
135°	764	764	764	764	764	587
145°	927	927	927	927	927	579
155°	1060	1062	1060	1062	1060	488
165°	1153	1157	1153	1157	1153	325
175°	1198	1203	1198	1203	1198	114
180°	1206	1206	1206	1206	1206	



TEST NUMBER: P332265-930

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	472.6	473.2	471.2	470.9	468.6	468.1	468.1	464.8	462.8	460.3	458.8
5°	526.9	529.9	528.4	525.1	519.3	518.0	514.4	508.7	502.2	494.2	490.5
7.5°	594.8	598.9	597.3	592.1	586.0	581.2	571.0	561.6	548.4	536.7	526.8
10°	650.4	646.0	642.6	637.5	631.9	623.1	612.4	597.8	580.9	567.5	552.8
12.5°	692.0	691.3	687.0	681.7	673.9	665.4	652.3	634.5	614.9	595.7	578.7
15°	748.8	749.9	747.1	741.6	730.5	715.5	695.8	688.4	660.2	639.4	618.5
17.5°	788.1	787.8	787.4	779.8	768.6	757.9	739.6	720.1	694.6	665.2	637.1
20°	813.0	811.1	811.5	802.9	794.6	782.2	764.3	736.1	715.2	681.2	652.1
22.5°	812.4	812.0	813.4	810.5	804.5	795.0	780.9	757.0	730.3	696.0	663.3
25°	771.6	770.1	778.9	781.5	791.2	792.9	788.6	775.6	750.3	714.9	674.5
27.5°	645.7	644.9	661.5	682.2	708.5	729.0	748.7	758.2	750.3	725.0	684.4
30°	529.9	547.8	556.2	586.2	619.6	659.5	694.5	727.7	735.9	724.8	691.6
32.5°	440.0	455.6	462.6	488.3	519.5	566.2	618.6	665.7	699.0	707.4	687.4
35°	334.7	334.8	350.8	362.2	391.1	439.1	490.1	553.1	615.8	663.3	668.2
37.5°	267.1	268.0	277.7	289.0	310.7	336.1	380.9	433.3	505.7	578.6	621.4
40°	230.6	232.3	239.5	250.7	266.3	285.5	320.4	369.8	430.2	511.4	577.6
42.5°	207.2	209.9	213.7	222.3	232.0	250.0	278.2	316.3	371.3	448.0	524.5
45°	178.6	180.1	183.0	186.9	195.7	208.1	227.1	252.8	298.4	360.1	436.7
47.5°	157.5	156.7	159.7	162.9	168.8	177.3	190.0	210.9	243.4	293.0	357.9
50°	143.2	143.0	145.1	147.6	153.1	159.4	169.8	185.6	211.4	252.4	311.9
52.5°	129.9	130.5	132.1	135.1	139.1	144.1	153.5	164.9	187.1	222.5	272.1
55°	112.1	112.7	114.7	116.4	119.3	124.4	130.3	139.8	155.0	179.7	220.5
57.5°	97.0	96.8	98.7	99.2	102.4	106.6	111.1	118.5	129.6	147.9	175.4
60°	87.0	86.4	88.1	89.4	91.2	94.6	98.4	105.6	114.4	127.8	151.4
62.5°	77.9	77.6	78.8	80.2	81.6	84.7	87.9	93.4	100.4	111.7	130.4
65°	64.6	65.1	65.7	66.3	67.0	69.0	72.0	75.8	80.6	88.5	102.0
67.5°	50.8	51.4	51.5	52.7	54.3	55.5	57.4	60.7	64.1	70.8	78.4
70°	41.0	40.8	41.0	41.6	43.7	45.7	48.3	50.7	52.8	57.6	64.0
72.5°	35.2	34.9	35.4	35.5	36.5	37.1	38.6	41.0	43.7	46.9	51.5
75°	27.3	27.3	27.3	27.3	28.1	28.5	29.0	29.6	30.6	32.1	35.5
77.5°	20.2	20.2	20.5	20.7	20.9	21.1	21.4	22.0	22.3	23.2	24.6
80°	16.0	16.1	16.0	16.1	16.1	16.6	16.7	17.3	17.4	18.4	19.0
82.5°	12.0	11.9	12.0	12.2	12.2	12.6	12.6	13.0	13.0	13.5	14.1
85°	6.4	6.1	6.4	6.3	6.7	6.3	6.4	6.8	6.8	7.0	7.8
87.5°	7.2	7.4	7.0	7.1	7.0	7.0	6.8	6.7	6.8	6.5	6.1
90°	28.5	28.0	27.6	27.1	26.7	26.1	25.3	24.5	23.6	22.7	20.0
92.5°	38.2	38.5	38.8	39.1	39.3	39.1	38.4	37.7	37.0	36.4	34.8
95°	73.9	73.9	73.9	73.9	73.9	73.5	72.6	71.7	70.9	70.1	68.4
97.5°	113.7	113.7	113.8	113.9	114.0	113.6	112.6	111.6	110.6	109.7	108.4
100°	144.0	143.6	143.2	142.8	142.3	141.8	141.1	140.5	139.9	139.3	138.2
102.5°	175.0	175.1	175.2	175.3	175.4	175.1	174.5	173.8	173.3	172.6	171.2
105°	225.4	225.0	224.6	224.2	223.8	223.6	223.6	223.6	223.6	223.6	221.7
107.5°	277.9	278.2	278.4	278.7	278.9	278.8	278.1	277.4	276.7	276.1	275.2
110°	313.6	314.0	314.4	314.8	315.2	315.0	314.2	313.3	312.5	311.7	311.2



TEST NUMBER: P332265-930

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	351.5	351.6	351.6	351.7	351.8	351.3	350.3	349.3	348.3	347.2	347.2
115°	403.6	403.7	404.0	404.1	404.4	404.4	404.1	404.0	403.7	403.6	404.0
117.5°	456.4	457.0	457.5	458.2	458.8	459.1	459.1	459.2	459.2	459.3	459.8
120°	493.5	494.0	494.4	494.8	495.2	495.5	495.8	495.9	496.2	496.4	497.4
122.5°	529.1	529.7	530.4	530.9	531.5	532.1	532.6	533.2	533.7	534.3	534.8
125°	582.6	583.4	584.2	585.1	586.0	586.8	587.7	588.5	589.3	590.2	590.6
127.5°	635.9	636.7	637.7	638.7	639.7	640.7	642.0	643.1	644.3	645.5	646.0
130°	670.7	672.1	673.6	675.1	676.5	677.8	678.6	679.4	680.3	681.1	681.8
132.5°	707.0	708.2	709.3	710.5	711.6	712.7	713.7	714.7	715.7	716.7	717.1
135°	763.5	763.9	764.3	764.8	765.2	765.8	766.6	767.5	768.3	769.2	769.4
137.5°	813.3	814.2	815.0	815.7	816.5	817.3	818.2	819.1	820.0	820.9	820.4
140°	846.0	847.4	848.9	850.4	851.8	852.6	852.9	853.0	853.3	853.5	853.3
142.5°	879.3	880.4	881.5	882.6	883.8	884.5	884.7	884.9	885.1	885.3	884.9
145°	927.4	928.2	929.0	929.9	930.7	931.3	931.5	931.7	931.9	932.1	931.5
147.5°	970.2	971.4	972.7	974.0	975.3	975.9	975.9	975.9	975.9	975.9	975.3
150°	997.5	998.7	1000.0	1001.3	1002.6	1003.1	1003.1	1003.1	1003.1	1003.1	1002.7
152.5°	1024.0	1025.1	1026.2	1027.3	1028.4	1028.7	1028.4	1028.1	1027.8	1027.4	1027.2
155°	1060.0	1061.5	1063.0	1064.5	1065.9	1066.2	1065.4	1064.5	1063.7	1062.8	1062.7
157.5°	1092.7	1094.0	1095.1	1096.3	1097.5	1097.6	1096.7	1095.8	1095.0	1094.1	1094.0
160°	1114.0	1114.8	1115.7	1116.6	1117.4	1117.3	1116.2	1115.2	1114.1	1113.0	1113.0
162.5°	1129.9	1131.2	1132.6	1133.9	1135.3	1135.5	1134.4	1133.3	1132.3	1131.2	1131.1
165°	1152.8	1154.3	1155.8	1157.2	1158.7	1158.9	1157.6	1156.3	1155.0	1153.8	1153.8
167.5°	1172.3	1173.6	1174.9	1176.2	1177.5	1177.5	1176.2	1174.9	1173.6	1172.3	1172.2
170°	1182.2	1183.7	1185.1	1186.7	1188.1	1188.1	1186.7	1185.1	1183.7	1182.2	1182.2
172.5°	1189.8	1191.2	1192.7	1194.2	1195.7	1195.8	1194.5	1193.2	1191.9	1190.6	1190.6
175°	1198.3	1199.8	1201.3	1202.7	1204.2	1204.3	1203.1	1201.8	1200.5	1199.2	1199.2
177.5°	1202.9	1204.0	1205.2	1206.4	1207.5	1207.6	1206.6	1205.7	1204.6	1203.6	1203.6
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P332265-930

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	458.1	457.7	455.6	453.1	450.0	447.8	446.1	445.2	442.5	439.1	436.9
5°	486.5	480.8	474.7	467.2	460.4	453.4	449.1	443.9	437.7	430.6	425.7
7.5°	516.7	505.6	493.6	481.1	468.9	457.9	448.1	439.8	429.8	419.7	412.7
10°	540.1	523.7	506.8	489.5	473.8	458.9	447.5	436.3	424.4	412.8	404.0
12.5°	561.2	539.6	520.2	498.9	478.7	461.1	444.7	431.5	417.0	404.7	394.8
15°	587.9	565.8	542.3	510.0	483.2	460.8	440.8	423.5	406.1	390.9	381.2
17.5°	612.9	579.8	548.0	521.1	486.3	458.4	434.0	413.4	394.1	378.1	366.1
20°	623.2	591.1	556.8	522.4	488.2	456.8	428.5	405.7	385.8	367.5	356.5
22.5°	629.4	593.1	556.8	519.9	483.6	451.0	423.1	397.9	376.3	359.1	345.4
25°	636.7	593.4	553.5	517.1	480.0	444.7	411.4	384.8	361.5	343.1	328.6
27.5°	641.5	590.5	543.4	502.9	465.3	430.2	399.7	371.5	347.7	328.2	312.7
30°	642.4	588.2	535.7	491.8	453.6	421.3	389.0	362.1	337.0	316.3	301.8
32.5°	643.6	582.6	525.1	478.6	439.4	407.5	378.2	352.5	326.8	306.4	291.6
35°	638.6	579.5	509.2	455.7	416.5	385.6	359.2	335.4	310.2	290.4	275.4
37.5°	617.0	567.2	492.8	429.9	389.0	360.4	338.8	318.1	295.0	273.6	259.5
40°	595.3	555.1	480.0	414.3	371.5	342.1	322.7	305.8	283.4	263.4	248.3
42.5°	563.0	538.4	467.8	397.9	351.8	323.4	307.0	291.2	271.6	251.3	237.0
45°	503.5	506.8	443.0	371.7	324.4	296.0	280.5	269.5	252.1	235.4	220.7
47.5°	429.1	459.3	413.8	343.9	295.6	268.9	255.4	245.8	234.0	217.6	204.2
50°	380.5	423.5	390.4	325.2	277.5	250.9	237.7	229.8	219.6	206.7	194.0
52.5°	335.7	382.0	362.1	304.4	257.9	233.6	220.6	214.2	206.0	193.9	182.4
55°	273.7	320.7	316.1	273.0	228.5	206.7	196.8	189.6	184.1	175.0	165.8
57.5°	221.4	265.9	268.2	238.0	202.6	181.0	172.5	167.1	163.5	156.6	148.1
60°	188.4	229.3	237.3	214.4	184.1	165.1	156.7	152.3	149.5	144.0	137.5
62.5°	161.1	195.8	204.9	188.5	166.3	148.5	141.9	137.8	135.8	131.1	125.4
65°	123.3	152.1	160.9	151.8	140.1	126.0	120.6	117.0	115.3	112.7	108.4
67.5°	92.7	113.7	123.4	116.9	112.7	103.7	100.4	98.4	96.9	95.1	91.6
70°	74.4	90.0	99.9	98.2	94.8	90.0	87.6	86.3	84.7	83.2	80.1
72.5°	59.8	70.6	79.8	80.7	77.9	77.0	74.8	74.2	73.3	71.5	69.8
75°	39.7	47.1	53.6	56.0	57.2	58.1	57.2	57.0	56.8	55.3	54.3
77.5°	26.0	30.0	34.1	38.3	40.1	41.3	41.7	42.4	41.8	41.1	40.6
80°	20.0	20.9	23.7	27.3	30.2	31.3	32.1	32.4	32.3	32.1	31.3
82.5°	14.5	15.2	16.6	19.2	21.5	23.4	23.9	23.8	24.2	24.4	23.7
85°	7.8	8.0	8.4	8.7	10.0	12.1	12.7	13.1	13.5	13.5	12.3
87.5°	5.9	5.2	5.0	4.5	4.5	4.2	4.7	5.1	5.6	5.5	5.9
90°	17.3	14.5	11.8	9.4	7.3	5.1	3.0	1.0	3.0	5.1	7.3
92.5°	33.3	31.7	30.2	28.6	27.2	25.8	24.4	22.9	24.4	25.8	27.2
95°	66.7	65.1	63.3	61.8	60.3	58.9	57.4	55.9	57.4	58.9	60.3
97.5°	107.3	106.1	104.8	103.6	102.6	101.5	100.4	99.3	100.4	101.5	102.6
100°	137.1	136.1	135.0	133.9	132.6	131.3	130.1	128.8	130.1	131.3	132.6
102.5°	169.8	168.4	167.1	166.0	165.2	164.4	163.7	162.9	163.7	164.4	165.2
105°	219.8	217.8	216.0	214.8	214.4	214.0	213.5	213.1	213.5	214.0	214.4
107.5°	274.5	273.8	273.0	272.5	272.2	272.0	271.7	271.5	271.7	272.0	272.2
110°	310.8	310.4	310.0	309.6	309.2	308.7	308.3	307.9	308.3	308.7	309.2





TEST NUMBER: P332265-930

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	347.1	347.0	346.9	346.7	346.5	346.3	346.0	345.8	346.0	346.3	346.5
115°	404.4	404.8	405.2	405.1	404.5	403.8	403.2	402.6	403.2	403.8	404.5
117.5°	460.3	460.9	461.5	461.5	461.1	460.6	460.2	459.8	460.2	460.6	461.1
120°	498.5	499.5	500.6	500.5	499.2	498.0	496.7	495.5	496.7	498.0	499.2
122.5°	535.3	535.9	536.5	536.3	535.3	534.4	533.5	532.6	533.5	534.4	535.3
125°	591.0	591.4	591.8	591.7	591.1	590.4	589.9	589.2	589.9	590.4	591.1
127.5°	646.4	646.9	647.3	646.9	645.6	644.2	642.9	641.5	642.9	644.2	645.6
130°	682.3	683.0	683.6	683.1	681.4	679.7	678.0	676.4	678.0	679.7	681.4
132.5°	717.6	718.1	718.6	718.0	716.2	714.6	712.9	711.2	712.9	714.6	716.2
135°	769.6	769.8	770.1	769.5	768.3	767.0	765.7	764.4	765.7	767.0	768.3
137.5°	819.8	819.3	818.7	817.9	816.8	815.8	814.7	813.8	814.7	815.8	816.8
140°	853.0	852.9	852.6	852.0	851.0	849.9	848.9	847.8	848.9	849.9	851.0
142.5°	884.6	884.2	883.8	883.1	882.1	881.0	880.0	878.9	880.0	881.0	882.1
145°	930.8	930.3	929.6	929.0	928.6	928.2	927.8	927.4	927.8	928.2	928.6
147.5°	974.7	974.1	973.5	972.9	972.1	971.3	970.6	969.8	970.6	971.3	972.1
150°	1002.3	1001.9	1001.5	1001.1	1000.6	1000.2	999.8	999.4	999.8	1000.2	1000.6
152.5°	1027.0	1026.6	1026.4	1026.0	1025.4	1024.8	1024.3	1023.6	1024.3	1024.8	1025.4
155°	1062.4	1062.3	1062.0	1061.9	1061.9	1061.9	1061.9	1061.9	1061.9	1061.9	1061.9
157.5°	1093.8	1093.6	1093.4	1093.5	1093.7	1094.0	1094.2	1094.5	1094.2	1094.0	1093.7
160°	1113.0	1113.0	1113.0	1113.3	1113.7	1114.1	1114.5	1114.9	1114.5	1114.1	1113.7
162.5°	1130.9	1130.7	1130.6	1130.8	1131.4	1132.0	1132.5	1133.1	1132.5	1132.0	1131.4
165°	1153.8	1153.8	1153.8	1154.1	1154.7	1155.4	1156.0	1156.7	1156.0	1155.4	1154.7
167.5°	1172.0	1171.8	1171.7	1172.0	1172.9	1173.7	1174.5	1175.4	1174.5	1173.7	1172.9
170°	1182.2	1182.2	1182.2	1182.6	1183.5	1184.3	1185.1	1186.0	1185.1	1184.3	1183.5
172.5°	1190.6	1190.6	1190.6	1191.0	1191.8	1192.6	1193.5	1194.3	1193.5	1192.6	1191.8
175°	1199.2	1199.2	1199.2	1199.7	1200.5	1201.3	1202.2	1203.1	1202.2	1201.3	1200.5
177.5°	1203.6	1203.6	1203.6	1204.0	1204.6	1205.3	1206.0	1206.6	1206.0	1205.3	1204.6
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P332265-930

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	436.1	434.1	432.8	429.7	427.8	425.7	423.5	424.9	424.7	424.6	424.6
5°	421.5	417.1	413.1	408.0	404.8	400.8	397.8	397.4	398.1	395.5	394.0
7.5°	407.0	401.0	395.3	389.7	383.7	378.9	375.9	374.5	372.6	371.0	369.2
10°	396.8	389.8	384.3	377.2	370.8	365.1	361.5	359.0	357.7	356.4	353.8
12.5°	386.3	379.4	372.4	364.4	358.3	351.7	349.0	346.3	343.7	342.2	338.8
15°	371.0	362.1	354.7	346.3	339.4	333.0	329.2	323.7	322.9	321.0	317.6
17.5°	355.6	345.9	335.7	329.5	321.8	315.0	309.2	307.4	302.0	299.9	296.9
20°	343.4	334.5	326.7	318.5	307.4	301.1	296.5	294.1	289.7	287.0	285.1
22.5°	333.0	323.8	314.9	305.3	296.1	289.0	285.7	281.8	279.5	275.7	273.7
25°	318.0	308.1	297.3	287.0	280.4	275.1	269.7	266.3	262.9	261.1	257.4
27.5°	300.6	290.2	280.1	272.3	264.2	258.9	254.1	251.1	247.0	244.1	242.0
30°	291.0	278.8	270.1	263.1	252.7	247.7	244.1	240.3	237.3	234.2	232.1
32.5°	279.9	268.8	260.6	251.8	243.9	238.4	233.7	230.4	227.8	224.9	222.8
35°	262.5	253.2	244.7	235.9	230.0	224.5	219.0	216.1	213.7	211.0	209.1
37.5°	246.8	238.1	229.9	221.7	214.3	209.9	205.5	203.3	199.9	198.1	196.2
40°	237.1	228.5	219.8	211.8	204.2	200.8	196.8	193.6	190.5	189.1	187.1
42.5°	226.4	217.8	210.5	201.9	195.7	191.0	187.4	183.8	181.6	179.6	178.5
45°	210.7	203.1	195.8	187.3	181.4	177.4	173.3	170.0	168.0	166.6	164.5
47.5°	195.3	187.8	180.4	173.0	167.3	162.7	158.5	156.3	153.5	151.9	150.5
50°	184.3	177.4	169.7	162.8	157.1	152.5	149.1	146.3	143.8	141.7	140.7
52.5°	174.1	166.8	160.0	153.7	147.7	142.5	139.4	136.4	134.5	132.2	131.0
55°	157.3	150.3	144.6	138.3	132.4	128.0	124.3	121.6	119.7	117.0	115.5
57.5°	141.5	135.2	128.4	122.9	116.9	113.2	110.1	106.5	104.1	102.1	100.5
60°	130.9	123.7	117.7	112.7	107.3	102.6	99.7	96.9	94.4	92.3	91.0
62.5°	119.8	113.5	107.9	102.3	97.4	93.3	90.0	87.6	85.4	84.1	82.8
65°	102.7	97.8	92.1	87.6	83.0	80.0	77.3	75.3	73.7	72.7	71.6
67.5°	87.1	82.3	77.4	72.9	69.8	67.5	65.8	64.0	63.2	62.0	61.2
70°	77.0	72.0	67.6	64.2	61.1	59.4	58.3	57.0	56.3	54.7	54.0
72.5°	65.9	62.3	59.1	56.3	53.9	52.3	50.9	49.2	48.0	46.3	45.6
75°	51.9	48.6	46.1	44.3	42.7	40.7	38.6	36.9	36.3	35.7	35.5
77.5°	38.4	36.4	34.6	32.9	31.1	29.6	29.1	28.7	28.6	28.3	28.3
80°	30.2	28.3	27.0	25.1	24.0	24.0	24.0	23.6	23.7	23.7	23.7
82.5°	22.4	20.7	20.0	19.3	19.1	19.2	19.2	19.3	19.2	19.5	19.3
85°	11.6	11.7	12.1	12.0	12.1	12.1	12.6	12.3	12.6	12.1	12.6
87.5°	6.1	7.1	7.7	8.5	9.1	9.5	9.9	10.0	10.4	10.5	10.7
90°	9.4	11.8	14.5	17.3	20.0	22.7	23.6	24.5	25.3	26.1	26.7
92.5°	28.6	30.2	31.7	33.3	34.8	36.4	37.0	37.7	38.4	39.1	39.3
95°	61.8	63.3	65.1	66.7	68.4	70.1	70.9	71.7	72.6	73.5	73.9
97.5°	103.6	104.8	106.1	107.3	108.4	109.7	110.6	111.6	112.6	113.6	114.0
100°	133.9	135.0	136.1	137.1	138.2	139.3	139.9	140.5	141.1	141.8	142.3
102.5°	166.0	167.1	168.4	169.8	171.2	172.6	173.3	173.8	174.5	175.1	175.4
105°	214.8	216.0	217.8	219.8	221.7	223.6	223.6	223.6	223.6	223.6	223.8
107.5°	272.5	273.0	273.8	274.5	275.2	276.1	276.7	277.4	278.1	278.8	278.9
110°	309.6	310.0	310.4	310.8	311.2	311.7	312.5	313.3	314.2	315.0	315.2



TEST NUMBER: P332265-930

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	346.7	346.9	347.0	347.1	347.2	347.2	348.3	349.3	350.3	351.3	351.8
115°	405.1	405.2	404.8	404.4	404.0	403.6	403.7	404.0	404.1	404.4	404.4
117.5°	461.5	461.5	460.9	460.3	459.8	459.3	459.2	459.2	459.1	459.1	458.8
120°	500.5	500.6	499.5	498.5	497.4	496.4	496.2	495.9	495.8	495.5	495.2
122.5°	536.3	536.5	535.9	535.3	534.8	534.3	533.7	533.2	532.6	532.1	531.5
125°	591.7	591.8	591.4	591.0	590.6	590.2	589.3	588.5	587.7	586.8	586.0
127.5°	646.9	647.3	646.9	646.4	646.0	645.5	644.3	643.1	642.0	640.7	639.7
130°	683.1	683.6	683.0	682.3	681.8	681.1	680.3	679.4	678.6	677.8	676.5
132.5°	718.0	718.6	718.1	717.6	717.1	716.7	715.7	714.7	713.7	712.7	711.6
135°	769.5	770.1	769.8	769.6	769.4	769.2	768.3	767.5	766.6	765.8	765.2
137.5°	817.9	818.7	819.3	819.8	820.4	820.9	820.0	819.1	818.2	817.3	816.5
140°	852.0	852.6	852.9	853.0	853.3	853.5	853.3	853.0	852.9	852.6	851.8
142.5°	883.1	883.8	884.2	884.6	884.9	885.3	885.1	884.9	884.7	884.5	883.8
145°	929.0	929.6	930.3	930.8	931.5	932.1	931.9	931.7	931.5	931.3	930.7
147.5°	972.9	973.5	974.1	974.7	975.3	975.9	975.9	975.9	975.9	975.9	975.3
150°	1001.1	1001.5	1001.9	1002.3	1002.7	1003.1	1003.1	1003.1	1003.1	1003.1	1002.6
152.5°	1026.0	1026.4	1026.6	1027.0	1027.2	1027.4	1027.8	1028.1	1028.4	1028.7	1028.4
155°	1061.9	1062.0	1062.3	1062.4	1062.7	1062.8	1063.7	1064.5	1065.4	1066.2	1065.9
157.5°	1093.5	1093.4	1093.6	1093.8	1094.0	1094.1	1095.0	1095.8	1096.7	1097.6	1097.5
160°	1113.3	1113.0	1113.0	1113.0	1113.0	1113.0	1114.1	1115.2	1116.2	1117.3	1117.4
162.5°	1130.8	1130.6	1130.7	1130.9	1131.1	1131.2	1132.3	1133.3	1134.4	1135.5	1135.3
165°	1154.1	1153.8	1153.8	1153.8	1153.8	1153.8	1155.0	1156.3	1157.6	1158.9	1158.7
167.5°	1172.0	1171.7	1171.8	1172.0	1172.2	1172.3	1173.6	1174.9	1176.2	1177.5	1177.5
170°	1182.6	1182.2	1182.2	1182.2	1182.2	1182.2	1183.7	1185.1	1186.7	1188.1	1188.1
172.5°	1191.0	1190.6	1190.6	1190.6	1190.6	1190.6	1191.9	1193.2	1194.5	1195.8	1195.7
175°	1199.7	1199.2	1199.2	1199.2	1199.2	1199.2	1200.5	1201.8	1203.1	1204.3	1204.2
177.5°	1204.0	1203.6	1203.6	1203.6	1203.6	1203.6	1204.6	1205.7	1206.6	1207.6	1207.5
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P332265-930

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	422.7	422.6	422.7	422.2	422.7	422.6	422.7	424.6	424.6	424.7	424.9
5°	393.4	393.2	392.6	390.9	392.6	393.2	393.4	394.0	395.5	398.1	397.4
7.5°	367.7	367.5	365.8	365.8	365.8	367.5	367.7	369.2	371.0	372.6	374.5
10°	352.5	352.7	350.4	349.1	350.4	352.7	352.5	353.8	356.4	357.7	359.0
12.5°	337.8	337.0	335.1	333.6	335.1	337.0	337.8	338.8	342.2	343.7	346.3
15°	318.4	316.4	311.9	312.3	311.9	316.4	318.4	317.6	321.0	322.9	323.7
17.5°	295.5	294.1	294.0	291.3	294.0	294.1	295.5	296.9	299.9	302.0	307.4
20°	282.1	281.1	281.5	278.8	281.5	281.1	282.1	285.1	287.0	289.7	294.1
22.5°	271.6	270.6	269.0	268.2	269.0	270.6	271.6	273.7	275.7	279.5	281.8
25°	256.2	254.7	253.2	254.1	253.2	254.7	256.2	257.4	261.1	262.9	266.3
27.5°	240.9	239.8	238.2	238.1	238.2	239.8	240.9	242.0	244.1	247.0	251.1
30°	231.1	230.0	229.3	228.3	229.3	230.0	231.1	232.1	234.2	237.3	240.3
32.5°	221.3	221.0	219.7	219.5	219.7	221.0	221.3	222.8	224.9	227.8	230.4
35°	208.4	207.2	206.8	207.0	206.8	207.2	208.4	209.1	211.0	213.7	216.1
37.5°	196.1	194.6	193.9	193.2	193.9	194.6	196.1	196.2	198.1	199.9	203.3
40°	187.3	185.8	185.4	185.0	185.4	185.8	187.3	187.1	189.1	190.5	193.6
42.5°	177.4	176.8	176.6	175.9	176.6	176.8	177.4	178.5	179.6	181.6	183.8
45°	164.0	163.7	162.6	163.0	162.6	163.7	164.0	164.5	166.6	168.0	170.0
47.5°	149.7	148.9	148.1	148.6	148.1	148.9	149.7	150.5	151.9	153.5	156.3
50°	140.0	139.6	137.9	138.3	137.9	139.6	140.0	140.7	141.7	143.8	146.3
52.5°	130.3	128.8	128.2	127.9	128.2	128.8	130.3	131.0	132.2	134.5	136.4
55°	114.1	112.4	111.7	111.3	111.7	112.4	114.1	115.5	117.0	119.7	121.6
57.5°	98.3	97.9	97.3	97.7	97.3	97.9	98.3	100.5	102.1	104.1	106.5
60°	89.1	89.1	89.1	88.9	89.1	89.1	89.1	91.0	92.3	94.4	96.9
62.5°	81.9	81.4	81.4	81.6	81.4	81.4	81.9	82.8	84.1	85.4	87.6
65°	71.0	70.8	70.1	69.9	70.1	70.8	71.0	71.6	72.7	73.7	75.3
67.5°	60.7	60.1	59.8	59.6	59.8	60.1	60.7	61.2	62.0	63.2	64.0
70°	53.0	52.6	51.4	51.7	51.4	52.6	53.0	54.0	54.7	56.3	57.0
72.5°	44.7	44.3	44.0	43.8	44.0	44.3	44.7	45.6	46.3	48.0	49.2
75°	35.3	35.1	35.0	35.7	35.0	35.1	35.3	35.5	35.7	36.3	36.9
77.5°	28.3	28.3	28.5	28.1	28.5	28.3	28.3	28.3	28.3	28.6	28.7
80°	23.7	23.7	23.6	23.6	23.6	23.7	23.7	23.7	23.7	23.7	23.6
82.5°	19.0	19.2	19.3	19.0	19.3	19.2	19.0	19.3	19.5	19.2	19.3
85°	12.6	12.3	12.7	12.6	12.7	12.3	12.6	12.6	12.1	12.6	12.3
87.5°	11.1	10.8	10.9	11.2	10.9	10.8	11.1	10.7	10.5	10.4	10.0
90°	27.1	27.6	28.0	28.5	28.0	27.6	27.1	26.7	26.1	25.3	24.5
92.5°	39.1	38.8	38.5	38.2	38.5	38.8	39.1	39.3	39.1	38.4	37.7
95°	73.9	73.9	73.9	73.9	73.9	73.9	73.9	73.9	73.5	72.6	71.7
97.5°	113.9	113.8	113.7	113.7	113.7	113.8	113.9	114.0	113.6	112.6	111.6
100°	142.8	143.2	143.6	144.0	143.6	143.2	142.8	142.3	141.8	141.1	140.5
102.5°	175.3	175.2	175.1	175.0	175.1	175.2	175.3	175.4	175.1	174.5	173.8
105°	224.2	224.6	225.0	225.4	225.0	224.6	224.2	223.8	223.6	223.6	223.6
107.5°	278.7	278.4	278.2	277.9	278.2	278.4	278.7	278.9	278.8	278.1	277.4
110°	314.8	314.4	314.0	313.6	314.0	314.4	314.8	315.2	315.0	314.2	313.3



TEST NUMBER: P332265-930

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	351.7	351.6	351.6	351.5	351.6	351.6	351.7	351.8	351.3	350.3	349.3
115°	404.1	404.0	403.7	403.6	403.7	404.0	404.1	404.4	404.4	404.1	404.0
117.5°	458.2	457.5	457.0	456.4	457.0	457.5	458.2	458.8	459.1	459.1	459.2
120°	494.8	494.4	494.0	493.5	494.0	494.4	494.8	495.2	495.5	495.8	495.9
122.5°	530.9	530.4	529.7	529.1	529.7	530.4	530.9	531.5	532.1	532.6	533.2
125°	585.1	584.2	583.4	582.6	583.4	584.2	585.1	586.0	586.8	587.7	588.5
127.5°	638.7	637.7	636.7	635.9	636.7	637.7	638.7	639.7	640.7	642.0	643.1
130°	675.1	673.6	672.1	670.7	672.1	673.6	675.1	676.5	677.8	678.6	679.4
132.5°	710.5	709.3	708.2	707.0	708.2	709.3	710.5	711.6	712.7	713.7	714.7
135°	764.8	764.3	763.9	763.5	763.9	764.3	764.8	765.2	765.8	766.6	767.5
137.5°	815.7	815.0	814.2	813.3	814.2	815.0	815.7	816.5	817.3	818.2	819.1
140°	850.4	848.9	847.4	846.0	847.4	848.9	850.4	851.8	852.6	852.9	853.0
142.5°	882.6	881.5	880.4	879.3	880.4	881.5	882.6	883.8	884.5	884.7	884.9
145°	929.9	929.0	928.2	927.4	928.2	929.0	929.9	930.7	931.3	931.5	931.7
147.5°	974.0	972.7	971.4	970.2	971.4	972.7	974.0	975.3	975.9	975.9	975.9
150°	1001.3	1000.0	998.7	997.5	998.7	1000.0	1001.3	1002.6	1003.1	1003.1	1003.1
152.5°	1027.3	1026.2	1025.1	1024.0	1025.1	1026.2	1027.3	1028.4	1028.7	1028.4	1028.1
155°	1064.5	1063.0	1061.5	1060.0	1061.5	1063.0	1064.5	1065.9	1066.2	1065.4	1064.5
157.5°	1096.3	1095.1	1094.0	1092.7	1094.0	1095.1	1096.3	1097.5	1097.6	1096.7	1095.8
160°	1116.6	1115.7	1114.8	1114.0	1114.8	1115.7	1116.6	1117.4	1117.3	1116.2	1115.2
162.5°	1133.9	1132.6	1131.2	1129.9	1131.2	1132.6	1133.9	1135.3	1135.5	1134.4	1133.3
165°	1157.2	1155.8	1154.3	1152.8	1154.3	1155.8	1157.2	1158.7	1158.9	1157.6	1156.3
167.5°	1176.2	1174.9	1173.6	1172.3	1173.6	1174.9	1176.2	1177.5	1177.5	1176.2	1174.9
170°	1186.7	1185.1	1183.7	1182.2	1183.7	1185.1	1186.7	1188.1	1188.1	1186.7	1185.1
172.5°	1194.2	1192.7	1191.2	1189.8	1191.2	1192.7	1194.2	1195.7	1195.8	1194.5	1193.2
175°	1202.7	1201.3	1199.8	1198.3	1199.8	1201.3	1202.7	1204.2	1204.3	1203.1	1201.8
177.5°	1206.4	1205.2	1204.0	1202.9	1204.0	1205.2	1206.4	1207.5	1207.6	1206.6	1205.7
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P332265-930

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	423.5	425.7	427.8	429.7	432.8	434.1	436.1	436.9	439.1	442.5	445.2
5°	397.8	400.8	404.8	408.0	413.1	417.1	421.5	425.7	430.6	437.7	443.9
7.5°	375.9	378.9	383.7	389.7	395.3	401.0	407.0	412.7	419.7	429.8	439.8
10°	361.5	365.1	370.8	377.2	384.3	389.8	396.8	404.0	412.8	424.4	436.3
12.5°	349.0	351.7	358.3	364.4	372.4	379.4	386.3	394.8	404.7	417.0	431.5
15°	329.2	333.0	339.4	346.3	354.7	362.1	371.0	381.2	390.9	406.1	423.5
17.5°	309.2	315.0	321.8	329.5	335.7	345.9	355.6	366.1	378.1	394.1	413.4
20°	296.5	301.1	307.4	318.5	326.7	334.5	343.4	356.5	367.5	385.8	405.7
22.5°	285.7	289.0	296.1	305.3	314.9	323.8	333.0	345.4	359.1	376.3	397.9
25°	269.7	275.1	280.4	287.0	297.3	308.1	318.0	328.6	343.1	361.5	384.8
27.5°	254.1	258.9	264.2	272.3	280.1	290.2	300.6	312.7	328.2	347.7	371.5
30°	244.1	247.7	252.7	263.1	270.1	278.8	291.0	301.8	316.3	337.0	362.1
32.5°	233.7	238.4	243.9	251.8	260.6	268.8	279.9	291.6	306.4	326.8	352.5
35°	219.0	224.5	230.0	235.9	244.7	253.2	262.5	275.4	290.4	310.2	335.4
37.5°	205.5	209.9	214.3	221.7	229.9	238.1	246.8	259.5	273.6	295.0	318.1
40°	196.8	200.8	204.2	211.8	219.8	228.5	237.1	248.3	263.4	283.4	305.8
42.5°	187.4	191.0	195.7	201.9	210.5	217.8	226.4	237.0	251.3	271.6	291.2
45°	173.3	177.4	181.4	187.3	195.8	203.1	210.7	220.7	235.4	252.1	269.5
47.5°	158.5	162.7	167.3	173.0	180.4	187.8	195.3	204.2	217.6	234.0	245.8
50°	149.1	152.5	157.1	162.8	169.7	177.4	184.3	194.0	206.7	219.6	229.8
52.5°	139.4	142.5	147.7	153.7	160.0	166.8	174.1	182.4	193.9	206.0	214.2
55°	124.3	128.0	132.4	138.3	144.6	150.3	157.3	165.8	175.0	184.1	189.6
57.5°	110.1	113.2	116.9	122.9	128.4	135.2	141.5	148.1	156.6	163.5	167.1
60°	99.7	102.6	107.3	112.7	117.7	123.7	130.9	137.5	144.0	149.5	152.3
62.5°	90.0	93.3	97.4	102.3	107.9	113.5	119.8	125.4	131.1	135.8	137.8
65°	77.3	80.0	83.0	87.6	92.1	97.8	102.7	108.4	112.7	115.3	117.0
67.5°	65.8	67.5	69.8	72.9	77.4	82.3	87.1	91.6	95.1	96.9	98.4
70°	58.3	59.4	61.1	64.2	67.6	72.0	77.0	80.1	83.2	84.7	86.3
72.5°	50.9	52.3	53.9	56.3	59.1	62.3	65.9	69.8	71.5	73.3	74.2
75°	38.6	40.7	42.7	44.3	46.1	48.6	51.9	54.3	55.3	56.8	57.0
77.5°	29.1	29.6	31.1	32.9	34.6	36.4	38.4	40.6	41.1	41.8	42.4
80°	24.0	24.0	24.0	25.1	27.0	28.3	30.2	31.3	32.1	32.3	32.4
82.5°	19.2	19.2	19.1	19.3	20.0	20.7	22.4	23.7	24.4	24.2	23.8
85°	12.6	12.1	12.1	12.0	12.1	11.7	11.6	12.3	13.5	13.5	13.1
87.5°	9.9	9.5	9.1	8.5	7.7	7.1	6.1	5.9	5.5	5.6	5.1
90°	23.6	22.7	20.0	17.3	14.5	11.8	9.4	7.3	5.1	3.0	1.0
92.5°	37.0	36.4	34.8	33.3	31.7	30.2	28.6	27.2	25.8	24.4	22.9
95°	70.9	70.1	68.4	66.7	65.1	63.3	61.8	60.3	58.9	57.4	55.9
97.5°	110.6	109.7	108.4	107.3	106.1	104.8	103.6	102.6	101.5	100.4	99.3
100°	139.9	139.3	138.2	137.1	136.1	135.0	133.9	132.6	131.3	130.1	128.8
102.5°	173.3	172.6	171.2	169.8	168.4	167.1	166.0	165.2	164.4	163.7	162.9
105°	223.6	223.6	221.7	219.8	217.8	216.0	214.8	214.4	214.0	213.5	213.1
107.5°	276.7	276.1	275.2	274.5	273.8	273.0	272.5	272.2	272.0	271.7	271.5
110°	312.5	311.7	311.2	310.8	310.4	310.0	309.6	309.2	308.7	308.3	307.9



TEST NUMBER: P332265-930

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	348.3	347.2	347.2	347.1	347.0	346.9	346.7	346.5	346.3	346.0	345.8
115°	403.7	403.6	404.0	404.4	404.8	405.2	405.1	404.5	403.8	403.2	402.6
117.5°	459.2	459.3	459.8	460.3	460.9	461.5	461.5	461.1	460.6	460.2	459.8
120°	496.2	496.4	497.4	498.5	499.5	500.6	500.5	499.2	498.0	496.7	495.5
122.5°	533.7	534.3	534.8	535.3	535.9	536.5	536.3	535.3	534.4	533.5	532.6
125°	589.3	590.2	590.6	591.0	591.4	591.8	591.7	591.1	590.4	589.9	589.2
127.5°	644.3	645.5	646.0	646.4	646.9	647.3	646.9	645.6	644.2	642.9	641.5
130°	680.3	681.1	681.8	682.3	683.0	683.6	683.1	681.4	679.7	678.0	676.4
132.5°	715.7	716.7	717.1	717.6	718.1	718.6	718.0	716.2	714.6	712.9	711.2
135°	768.3	769.2	769.4	769.6	769.8	770.1	769.5	768.3	767.0	765.7	764.4
137.5°	820.0	820.9	820.4	819.8	819.3	818.7	817.9	816.8	815.8	814.7	813.8
140°	853.3	853.5	853.3	853.0	852.9	852.6	852.0	851.0	849.9	848.9	847.8
142.5°	885.1	885.3	884.9	884.6	884.2	883.8	883.1	882.1	881.0	880.0	878.9
145°	931.9	932.1	931.5	930.8	930.3	929.6	929.0	928.6	928.2	927.8	927.4
147.5°	975.9	975.9	975.3	974.7	974.1	973.5	972.9	972.1	971.3	970.6	969.8
150°	1003.1	1003.1	1002.7	1002.3	1001.9	1001.5	1001.1	1000.6	1000.2	999.8	999.4
152.5°	1027.8	1027.4	1027.2	1027.0	1026.6	1026.4	1026.0	1025.4	1024.8	1024.3	1023.6
155°	1063.7	1062.8	1062.7	1062.4	1062.3	1062.0	1061.9	1061.9	1061.9	1061.9	1061.9
157.5°	1095.0	1094.1	1094.0	1093.8	1093.6	1093.4	1093.5	1093.7	1094.0	1094.2	1094.5
160°	1114.1	1113.0	1113.0	1113.0	1113.0	1113.0	1113.3	1113.7	1114.1	1114.5	1114.9
162.5°	1132.3	1131.2	1131.1	1130.9	1130.7	1130.6	1130.8	1131.4	1132.0	1132.5	1133.1
165°	1155.0	1153.8	1153.8	1153.8	1153.8	1153.8	1154.1	1154.7	1155.4	1156.0	1156.7
167.5°	1173.6	1172.3	1172.2	1172.0	1171.8	1171.7	1172.0	1172.9	1173.7	1174.5	1175.4
170°	1183.7	1182.2	1182.2	1182.2	1182.2	1182.2	1182.6	1183.5	1184.3	1185.1	1186.0
172.5°	1191.9	1190.6	1190.6	1190.6	1190.6	1190.6	1191.0	1191.8	1192.6	1193.5	1194.3
175°	1200.5	1199.2	1199.2	1199.2	1199.2	1199.2	1199.7	1200.5	1201.3	1202.2	1203.1
177.5°	1204.6	1203.6	1203.6	1203.6	1203.6	1203.6	1204.0	1204.6	1205.3	1206.0	1206.6
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P332265-930

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	446.1	447.8	450.0	453.1	455.6	457.7	458.1	458.8	460.3	462.8	464.8
5°	449.1	453.4	460.4	467.2	474.7	480.8	486.5	490.5	494.2	502.2	508.7
7.5°	448.1	457.9	468.9	481.1	493.6	505.6	516.7	526.8	536.7	548.4	561.6
10°	447.5	458.9	473.8	489.5	506.8	523.7	540.1	552.8	567.5	580.9	597.8
12.5°	444.7	461.1	478.7	498.9	520.2	539.6	561.2	578.7	595.7	614.9	634.5
15°	440.8	460.8	483.2	510.0	542.3	565.8	587.9	618.5	639.4	660.2	688.4
17.5°	434.0	458.4	486.3	521.1	548.0	579.8	612.9	637.1	665.2	694.6	720.1
20°	428.5	456.8	488.2	522.4	556.8	591.1	623.2	652.1	681.2	715.2	736.1
22.5°	423.1	451.0	483.6	519.9	556.8	593.1	629.4	663.3	696.0	730.3	757.0
25°	411.4	444.7	480.0	517.1	553.5	593.4	636.7	674.5	714.9	750.3	775.6
27.5°	399.7	430.2	465.3	502.9	543.4	590.5	641.5	684.4	725.0	750.3	758.2
30°	389.0	421.3	453.6	491.8	535.7	588.2	642.4	691.6	724.8	735.9	727.7
32.5°	378.2	407.5	439.4	478.6	525.1	582.6	643.6	687.4	707.4	699.0	665.7
35°	359.2	385.6	416.5	455.7	509.2	579.5	638.6	668.2	663.3	615.8	553.1
37.5°	338.8	360.4	389.0	429.9	492.8	567.2	617.0	621.4	578.6	505.7	433.3
40°	322.7	342.1	371.5	414.3	480.0	555.1	595.3	577.6	511.4	430.2	369.8
42.5°	307.0	323.4	351.8	397.9	467.8	538.4	563.0	524.5	448.0	371.3	316.3
45°	280.5	296.0	324.4	371.7	443.0	506.8	503.5	436.7	360.1	298.4	252.8
47.5°	255.4	268.9	295.6	343.9	413.8	459.3	429.1	357.9	293.0	243.4	210.9
50°	237.7	250.9	277.5	325.2	390.4	423.5	380.5	311.9	252.4	211.4	185.6
52.5°	220.6	233.6	257.9	304.4	362.1	382.0	335.7	272.1	222.5	187.1	164.9
55°	196.8	206.7	228.5	273.0	316.1	320.7	273.7	220.5	179.7	155.0	139.8
57.5°	172.5	181.0	202.6	238.0	268.2	265.9	221.4	175.4	147.9	129.6	118.5
60°	156.7	165.1	184.1	214.4	237.3	229.3	188.4	151.4	127.8	114.4	105.6
62.5°	141.9	148.5	166.3	188.5	204.9	195.8	161.1	130.4	111.7	100.4	93.4
65°	120.6	126.0	140.1	151.8	160.9	152.1	123.3	102.0	88.5	80.6	75.8
67.5°	100.4	103.7	112.7	116.9	123.4	113.7	92.7	78.4	70.8	64.1	60.7
70°	87.6	90.0	94.8	98.2	99.9	90.0	74.4	64.0	57.6	52.8	50.7
72.5°	74.8	77.0	77.9	80.7	79.8	70.6	59.8	51.5	46.9	43.7	41.0
75°	57.2	58.1	57.2	56.0	53.6	47.1	39.7	35.5	32.1	30.6	29.6
77.5°	41.7	41.3	40.1	38.3	34.1	30.0	26.0	24.6	23.2	22.3	22.0
80°	32.1	31.3	30.2	27.3	23.7	20.9	20.0	19.0	18.4	17.4	17.3
82.5°	23.9	23.4	21.5	19.2	16.6	15.2	14.5	14.1	13.5	13.0	13.0
85°	12.7	12.1	10.0	8.7	8.4	8.0	7.8	7.8	7.0	6.8	6.8
87.5°	4.7	4.2	4.5	4.5	5.0	5.2	5.9	6.1	6.5	6.8	6.7
90°	3.0	5.1	7.3	9.4	11.8	14.5	17.3	20.0	22.7	23.6	24.5
92.5°	24.4	25.8	27.2	28.6	30.2	31.7	33.3	34.8	36.4	37.0	37.7
95°	57.4	58.9	60.3	61.8	63.3	65.1	66.7	68.4	70.1	70.9	71.7
97.5°	100.4	101.5	102.6	103.6	104.8	106.1	107.3	108.4	109.7	110.6	111.6
100°	130.1	131.3	132.6	133.9	135.0	136.1	137.1	138.2	139.3	139.9	140.5
102.5°	163.7	164.4	165.2	166.0	167.1	168.4	169.8	171.2	172.6	173.3	173.8
105°	213.5	214.0	214.4	214.8	216.0	217.8	219.8	221.7	223.6	223.6	223.6
107.5°	271.7	272.0	272.2	272.5	273.0	273.8	274.5	275.2	276.1	276.7	277.4
110°	308.3	308.7	309.2	309.6	310.0	310.4	310.8	311.2	311.7	312.5	313.3





TEST NUMBER: P332265-930

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	346.0	346.3	346.5	346.7	346.9	347.0	347.1	347.2	347.2	348.3	349.3
115°	403.2	403.8	404.5	405.1	405.2	404.8	404.4	404.0	403.6	403.7	404.0
117.5°	460.2	460.6	461.1	461.5	461.5	460.9	460.3	459.8	459.3	459.2	459.2
120°	496.7	498.0	499.2	500.5	500.6	499.5	498.5	497.4	496.4	496.2	495.9
122.5°	533.5	534.4	535.3	536.3	536.5	535.9	535.3	534.8	534.3	533.7	533.2
125°	589.9	590.4	591.1	591.7	591.8	591.4	591.0	590.6	590.2	589.3	588.5
127.5°	642.9	644.2	645.6	646.9	647.3	646.9	646.4	646.0	645.5	644.3	643.1
130°	678.0	679.7	681.4	683.1	683.6	683.0	682.3	681.8	681.1	680.3	679.4
132.5°	712.9	714.6	716.2	718.0	718.6	718.1	717.6	717.1	716.7	715.7	714.7
135°	765.7	767.0	768.3	769.5	770.1	769.8	769.6	769.4	769.2	768.3	767.5
137.5°	814.7	815.8	816.8	817.9	818.7	819.3	819.8	820.4	820.9	820.0	819.1
140°	848.9	849.9	851.0	852.0	852.6	852.9	853.0	853.3	853.5	853.3	853.0
142.5°	880.0	881.0	882.1	883.1	883.8	884.2	884.6	884.9	885.3	885.1	884.9
145°	927.8	928.2	928.6	929.0	929.6	930.3	930.8	931.5	932.1	931.9	931.7
147.5°	970.6	971.3	972.1	972.9	973.5	974.1	974.7	975.3	975.9	975.9	975.9
150°	999.8	1000.2	1000.6	1001.1	1001.5	1001.9	1002.3	1002.7	1003.1	1003.1	1003.1
152.5°	1024.3	1024.8	1025.4	1026.0	1026.4	1026.6	1027.0	1027.2	1027.4	1027.8	1028.1
155°	1061.9	1061.9	1061.9	1061.9	1062.0	1062.3	1062.4	1062.7	1062.8	1063.7	1064.5
157.5°	1094.2	1094.0	1093.7	1093.5	1093.4	1093.6	1093.8	1094.0	1094.1	1095.0	1095.8
160°	1114.5	1114.1	1113.7	1113.3	1113.0	1113.0	1113.0	1113.0	1113.0	1114.1	1115.2
162.5°	1132.5	1132.0	1131.4	1130.8	1130.6	1130.7	1130.9	1131.1	1131.2	1132.3	1133.3
165°	1156.0	1155.4	1154.7	1154.1	1153.8	1153.8	1153.8	1153.8	1153.8	1155.0	1156.3
167.5°	1174.5	1173.7	1172.9	1172.0	1171.7	1171.8	1172.0	1172.2	1172.3	1173.6	1174.9
170°	1185.1	1184.3	1183.5	1182.6	1182.2	1182.2	1182.2	1182.2	1182.2	1183.7	1185.1
172.5°	1193.5	1192.6	1191.8	1191.0	1190.6	1190.6	1190.6	1190.6	1190.6	1191.9	1193.2
175°	1202.2	1201.3	1200.5	1199.7	1199.2	1199.2	1199.2	1199.2	1199.2	1200.5	1201.8
177.5°	1206.0	1205.3	1204.6	1204.0	1203.6	1203.6	1203.6	1203.6	1203.6	1204.6	1205.7
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P332265-930

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	468.1	468.1	468.6	470.9	471.2	473.2	472.6
5°	514.4	518.0	519.3	525.1	528.4	529.9	526.9
7.5°	571.0	581.2	586.0	592.1	597.3	598.9	594.8
10°	612.4	623.1	631.9	637.5	642.6	646.0	650.4
12.5°	652.3	665.4	673.9	681.7	687.0	691.3	692.0
15°	695.8	715.5	730.5	741.6	747.1	749.9	748.8
17.5°	739.6	757.9	768.6	779.8	787.4	787.8	788.1
20°	764.3	782.2	794.6	802.9	811.5	811.1	813.0
22.5°	780.9	795.0	804.5	810.5	813.4	812.0	812.4
25°	788.6	792.9	791.2	781.5	778.9	770.1	771.6
27.5°	748.7	729.0	708.5	682.2	661.5	644.9	645.7
30°	694.5	659.5	619.6	586.2	556.2	547.8	529.9
32.5°	618.6	566.2	519.5	488.3	462.6	455.6	440.0
35°	490.1	439.1	391.1	362.2	350.8	334.8	334.7
37.5°	380.9	336.1	310.7	289.0	277.7	268.0	267.1
40°	320.4	285.5	266.3	250.7	239.5	232.3	230.6
42.5°	278.2	250.0	232.0	222.3	213.7	209.9	207.2
45°	227.1	208.1	195.7	186.9	183.0	180.1	178.6
47.5°	190.0	177.3	168.8	162.9	159.7	156.7	157.5
50°	169.8	159.4	153.1	147.6	145.1	143.0	143.2
52.5°	153.5	144.1	139.1	135.1	132.1	130.5	129.9
55°	130.3	124.4	119.3	116.4	114.7	112.7	112.1
57.5°	111.1	106.6	102.4	99.2	98.7	96.8	97.0
60°	98.4	94.6	91.2	89.4	88.1	86.4	87.0
62.5°	87.9	84.7	81.6	80.2	78.8	77.6	77.9
65°	72.0	69.0	67.0	66.3	65.7	65.1	64.6
67.5°	57.4	55.5	54.3	52.7	51.5	51.4	50.8
70°	48.3	45.7	43.7	41.6	41.0	40.8	41.0
72.5°	38.6	37.1	36.5	35.5	35.4	34.9	35.2
75°	29.0	28.5	28.1	27.3	27.3	27.3	27.3
77.5°	21.4	21.1	20.9	20.7	20.5	20.2	20.2
80°	16.7	16.6	16.1	16.1	16.0	16.1	16.0
82.5°	12.6	12.6	12.2	12.2	12.0	11.9	12.0
85°	6.4	6.3	6.7	6.3	6.4	6.1	6.4
87.5°	6.8	7.0	7.0	7.1	7.0	7.4	7.2
90°	25.3	26.1	26.7	27.1	27.6	28.0	28.5
92.5°	38.4	39.1	39.3	39.1	38.8	38.5	38.2
95°	72.6	73.5	73.9	73.9	73.9	73.9	73.9
97.5°	112.6	113.6	114.0	113.9	113.8	113.7	113.7
100°	141.1	141.8	142.3	142.8	143.2	143.6	144.0
102.5°	174.5	175.1	175.4	175.3	175.2	175.1	175.0
105°	223.6	223.6	223.8	224.2	224.6	225.0	225.4
107.5°	278.1	278.8	278.9	278.7	278.4	278.2	277.9
110°	314.2	315.0	315.2	314.8	314.4	314.0	313.6



TEST NUMBER: P332265-930

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	350.3	351.3	351.8	351.7	351.6	351.6	351.5
115°	404.1	404.4	404.4	404.1	404.0	403.7	403.6
117.5°	459.1	459.1	458.8	458.2	457.5	457.0	456.4
120°	495.8	495.5	495.2	494.8	494.4	494.0	493.5
122.5°	532.6	532.1	531.5	530.9	530.4	529.7	529.1
125°	587.7	586.8	586.0	585.1	584.2	583.4	582.6
127.5°	642.0	640.7	639.7	638.7	637.7	636.7	635.9
130°	678.6	677.8	676.5	675.1	673.6	672.1	670.7
132.5°	713.7	712.7	711.6	710.5	709.3	708.2	707.0
135°	766.6	765.8	765.2	764.8	764.3	763.9	763.5
137.5°	818.2	817.3	816.5	815.7	815.0	814.2	813.3
140°	852.9	852.6	851.8	850.4	848.9	847.4	846.0
142.5°	884.7	884.5	883.8	882.6	881.5	880.4	879.3
145°	931.5	931.3	930.7	929.9	929.0	928.2	927.4
147.5°	975.9	975.9	975.3	974.0	972.7	971.4	970.2
150°	1003.1	1003.1	1002.6	1001.3	1000.0	998.7	997.5
152.5°	1028.4	1028.7	1028.4	1027.3	1026.2	1025.1	1024.0
155°	1065.4	1066.2	1065.9	1064.5	1063.0	1061.5	1060.0
157.5°	1096.7	1097.6	1097.5	1096.3	1095.1	1094.0	1092.7
160°	1116.2	1117.3	1117.4	1116.6	1115.7	1114.8	1114.0
162.5°	1134.4	1135.5	1135.3	1133.9	1132.6	1131.2	1129.9
165°	1157.6	1158.9	1158.7	1157.2	1155.8	1154.3	1152.8
167.5°	1176.2	1177.5	1177.5	1176.2	1174.9	1173.6	1172.3
170°	1186.7	1188.1	1188.1	1186.7	1185.1	1183.7	1182.2
172.5°	1194.5	1195.8	1195.7	1194.2	1192.7	1191.2	1189.8
175°	1203.1	1204.3	1204.2	1202.7	1201.3	1199.8	1198.3
177.5°	1206.6	1207.6	1207.5	1206.4	1205.2	1204.0	1202.9
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9

(END OF REPORT)