

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332339-927

Luminaire Tested: **S123RDIP-S1000D585U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332339-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D585U927-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4859.6 lumens
Efficiency: N/A
Efficacy: 99.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332339-927

CATALOG NUMBER: S123RDIP-S1000D585U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332339-927

CATALOG NUMBER: S123RDIP-S1000D585U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	97	93	89	94	91	87	84	80	77	75	69	67	66	60	59	57	53
2	92	85	79	74	86	80	74	70	70	66	63	61	58	56	53	51	49	45
3	84	75	68	62	79	71	64	59	62	57	53	55	51	47	47	45	42	39
4	77	67	59	53	72	63	56	50	56	50	46	49	45	41	43	39	37	33
5	71	60	51	45	67	56	49	44	50	44	40	44	39	36	39	35	32	29
6	66	54	46	40	61	51	43	38	45	39	35	40	35	32	35	31	28	26
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	32	28	25	23
8	57	44	37	31	53	42	35	30	38	32	28	34	29	25	30	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	27	24	21	19
10	49	37	30	25	46	36	29	24	32	26	23	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14310	14310	14310
5°	14364	14166	14249
10°	14283	13988	13941
15°	14130	13661	13517
20°	13919	13252	12944
25°	13702	12792	12383
30°	13415	12263	11591
35°	13119	11730	10867
40°	12847	11105	9969
45°	12490	10488	9159
50°	12097	9786	8251
55°	11695	8983	7405
60°	11328	8125	6476
65°	10847	7195	5547
70°	10247	6039	4482
75°	9374	4754	4213
80°	8356	4209	3874
85°	7052	3730	3458



TEST NUMBER: P332339-927

CATALOG NUMBER: S123RDIP-S1000D585U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.8	2.6
10°-20°	347.3	7.1
20°-30°	500.2	10.3
30°-40°	563.4	11.6
40°-50°	539.0	11.1
50°-60°	441.4	9.1
60°-70°	297.8	6.1
70°-80°	149.8	3.1
80°-90°	41.3	0.9
90°-100°	22.1	0.5
100°-110°	105.4	2.2
110°-120°	253.1	5.2
120°-130°	322.3	6.6
130°-140°	344.4	7.1
140°-150°	322.0	6.6
150°-160°	259.8	5.3
160°-170°	167.7	3.5
170°-180°	57.8	1.2
0°-30°	972.3	20.0
0°-40°	1535.7	31.6
0°-60°	2516.0	51.8
0°-90°	3005.0	61.8
90°-120°	380.6	7.8
90°-150°	1369.4	28.2
90°-180°	1855.0	38.2
0°-180°	4859.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1329	1329	1329	1329	1329	
5°	1329	1324	1311	1320	1319	126
15°	1268	1255	1226	1220	1213	357
25°	1154	1125	1077	1055	1043	530
35°	998	958	893	848	827	625
45°	820	770	689	629	602	633
55°	623	568	479	418	395	559
65°	426	365	282	232	218	421
75°	225	173	114	104	101	240
85°	57	34	30	28	28	64
90°	0	5	11	13	14	4
95°	28	10	14	17	17	34
105°	135	137	99	24	20	143
115°	252	255	259	264	266	249
125°	356	360	362	362	363	318
135°	443	446	448	449	448	341
145°	511	515	516	516	516	320
155°	563	563	563	565	562	259
165°	594	593	592	596	593	168
175°	608	606	606	609	606	58
180°	608	608	608	608	608	



TEST NUMBER: P332339-927

CATALOG NUMBER: S123RDIP-S1000D585U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4
2.5°	1333.7	1332.9	1332.2	1331.4	1330.6	1329.1	1326.8	1324.5	1322.2	1319.9	1322.0
5°	1329.4	1328.2	1327.0	1325.8	1324.6	1322.5	1319.7	1316.8	1314.0	1311.1	1313.2
7.5°	1317.1	1315.8	1314.5	1313.2	1311.9	1309.4	1305.7	1302.0	1298.2	1294.5	1295.7
10°	1306.8	1305.1	1303.4	1301.7	1300.1	1297.0	1292.8	1288.4	1284.1	1279.8	1280.1
12.5°	1292.1	1290.2	1288.4	1286.5	1284.6	1281.0	1275.8	1270.5	1265.3	1260.0	1259.8
15°	1268.0	1265.4	1262.7	1260.0	1257.4	1252.8	1246.0	1239.3	1232.6	1225.9	1224.7
17.5°	1237.5	1234.5	1231.4	1228.4	1225.3	1219.5	1210.9	1202.5	1193.9	1185.3	1182.8
20°	1215.1	1211.3	1207.4	1203.6	1199.8	1193.3	1184.2	1175.1	1166.0	1156.9	1153.8
22.5°	1190.1	1185.7	1181.3	1176.9	1172.5	1165.5	1155.7	1146.1	1136.4	1126.7	1122.8
25°	1153.7	1147.7	1141.7	1135.7	1129.7	1121.2	1110.2	1099.2	1088.1	1077.1	1072.1
27.5°	1109.5	1102.9	1096.2	1089.6	1083.0	1073.6	1061.3	1049.0	1036.7	1024.5	1017.5
30°	1079.3	1072.1	1064.9	1057.7	1050.5	1040.2	1026.8	1013.4	1000.0	986.6	978.4
32.5°	1049.1	1040.9	1032.8	1024.6	1016.5	1005.4	991.2	977.0	962.7	948.6	939.7
35°	998.4	989.8	981.1	972.6	963.9	952.1	937.3	922.4	907.6	892.7	882.4
37.5°	947.1	937.5	927.9	918.3	908.7	896.0	880.2	864.3	848.4	832.6	820.9
40°	914.3	903.8	893.2	882.6	872.1	858.3	841.4	824.3	807.3	790.3	777.8
42.5°	877.2	866.6	856.1	845.6	835.0	821.0	803.4	785.8	768.3	750.7	737.0
45°	820.5	809.7	798.9	788.1	777.4	762.8	744.3	725.9	707.4	689.0	675.3
47.5°	763.8	751.9	740.1	728.3	716.4	701.3	682.9	664.4	645.9	627.5	612.7
50°	722.4	711.1	699.9	688.6	677.3	662.0	642.6	623.2	603.8	584.4	569.5
52.5°	685.3	673.1	660.8	648.6	636.4	620.7	601.5	582.3	563.1	543.8	528.4
55°	623.2	611.5	599.7	588.0	576.2	560.2	539.8	519.4	499.1	478.7	464.9
57.5°	565.9	553.0	540.3	527.4	514.7	498.0	477.5	457.1	436.7	416.2	403.1
60°	526.2	513.0	499.8	486.6	473.4	456.9	437.0	417.2	397.3	377.4	364.4
62.5°	486.5	473.3	460.1	446.9	433.8	417.2	397.4	377.5	357.6	337.7	325.5
65°	425.9	412.7	399.5	386.3	373.2	357.3	338.6	319.9	301.2	282.5	270.8
67.5°	365.3	352.0	338.7	325.3	312.0	296.4	278.5	260.5	242.6	224.7	215.9
70°	325.6	312.7	299.8	286.8	273.9	259.0	242.2	225.5	208.7	191.9	183.5
72.5°	285.9	273.2	260.5	247.7	235.0	220.9	205.7	190.5	175.2	160.0	153.1
75°	225.4	213.8	202.3	190.8	179.4	167.0	153.8	140.6	127.5	114.3	111.9
77.5°	170.2	159.7	149.3	138.9	128.6	119.1	110.6	102.1	93.6	85.2	83.9
80°	134.8	124.9	115.1	105.3	95.5	88.1	83.0	78.0	73.0	67.9	67.2
82.5°	101.2	92.7	84.2	75.7	67.2	61.8	59.4	57.1	54.7	52.4	51.7
85°	57.1	51.9	46.6	41.4	36.0	33.0	32.3	31.6	30.9	30.2	29.7
87.5°	20.8	18.9	17.0	15.1	13.2	12.4	12.6	12.8	13.2	13.4	13.3
90°	0.5	1.4	2.5	3.5	4.4	5.6	6.9	8.2	9.5	10.9	11.2
92.5°	8.4	8.2	7.8	7.5	7.3	7.6	8.6	9.6	10.6	11.6	12.2
95°	27.6	23.4	19.3	15.2	11.1	9.6	10.7	11.8	12.9	14.0	14.7
97.5°	55.4	53.6	51.7	49.8	48.0	43.5	36.2	29.0	21.8	14.6	15.4
100°	76.4	78.3	80.4	82.4	84.4	77.6	61.9	46.3	30.6	14.9	15.7
102.5°	100.2	101.6	103.1	104.6	106.0	98.2	81.0	63.9	46.8	29.7	27.3
105°	134.7	135.8	136.9	137.9	139.0	135.1	126.0	117.0	108.0	98.9	81.2
107.5°	171.0	171.8	172.8	173.6	174.5	175.6	177.1	178.5	179.9	181.3	168.3
110°	195.2	196.0	196.8	197.6	198.4	199.4	200.4	201.5	202.6	203.7	200.4



TEST NUMBER: P332339-927

CATALOG NUMBER: S123RDIP-S1000D585U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	218.3	219.0	219.8	220.5	221.2	222.1	223.2	224.3	225.5	226.6	226.6
115°	252.5	253.2	253.7	254.4	255.0	255.7	256.7	257.5	258.4	259.4	260.4
117.5°	285.7	286.5	287.2	288.0	288.7	289.3	289.8	290.3	290.7	291.1	292.0
120°	306.3	307.2	308.2	309.0	310.0	310.5	310.9	311.2	311.5	311.7	312.6
122.5°	327.3	328.0	328.8	329.5	330.3	330.8	331.2	331.6	332.0	332.4	333.0
125°	356.0	356.9	357.7	358.5	359.3	359.9	360.3	360.7	361.1	361.5	361.6
127.5°	383.9	384.7	385.5	386.3	387.1	387.7	388.2	388.7	389.2	389.7	390.0
130°	401.2	402.0	402.8	403.6	404.4	405.0	405.4	405.8	406.2	406.6	407.0
132.5°	417.9	418.7	419.5	420.3	421.0	421.6	421.9	422.2	422.6	422.9	423.3
135°	443.2	443.9	444.4	445.0	445.7	446.2	446.6	446.9	447.3	447.7	448.1
137.5°	464.9	465.7	466.4	467.2	467.9	468.5	468.7	468.9	469.1	469.4	469.8
140°	479.3	480.0	480.6	481.2	481.8	482.3	482.5	482.8	483.2	483.5	483.9
142.5°	492.7	493.4	494.0	494.6	495.2	495.6	495.9	496.2	496.5	496.9	497.2
145°	511.4	512.1	512.9	513.6	514.3	514.8	514.9	515.2	515.3	515.6	515.7
147.5°	529.1	529.6	530.0	530.4	530.9	531.2	531.5	531.6	531.9	532.1	532.3
150°	540.0	540.3	540.5	540.8	541.1	541.4	541.6	541.8	542.0	542.2	542.4
152.5°	549.7	549.9	549.9	550.1	550.2	550.4	550.5	550.6	550.7	550.9	551.2
155°	563.4	563.2	563.0	562.8	562.6	562.6	562.7	562.8	562.8	563.0	563.5
157.5°	574.1	574.1	574.0	574.0	574.0	573.9	573.9	573.8	573.6	573.5	574.2
160°	580.6	580.5	580.4	580.3	580.2	580.1	580.0	579.9	579.8	579.7	580.3
162.5°	586.8	586.5	586.2	586.0	585.7	585.5	585.4	585.3	585.2	585.1	585.8
165°	594.1	593.8	593.6	593.3	592.9	592.7	592.6	592.6	592.5	592.3	593.2
167.5°	599.9	599.5	599.1	598.7	598.3	598.1	598.1	598.1	598.1	598.1	599.0
170°	603.2	602.8	602.4	602.0	601.6	601.3	601.3	601.3	601.3	601.3	602.2
172.5°	605.4	604.9	604.4	603.9	603.4	603.2	603.3	603.4	603.5	603.6	604.4
175°	608.2	607.7	607.1	606.7	606.2	605.9	606.0	606.2	606.3	606.3	607.0
177.5°	608.9	608.5	608.1	607.7	607.3	607.1	607.2	607.3	607.4	607.4	608.1
180°	608.2	608.2	608.2	608.2	608.2	608.2	608.2	608.2	608.2	608.2	608.2



TEST NUMBER: P332339-927

CATALOG NUMBER: S123RDIP-S1000D585U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4
2.5°	1324.1	1326.3	1328.3	1329.2	1328.8	1328.5	1328.1	1327.7
5°	1315.4	1317.6	1319.7	1320.6	1320.1	1319.6	1319.1	1318.7
7.5°	1296.9	1298.1	1299.3	1299.5	1298.6	1297.8	1297.0	1296.2
10°	1280.3	1280.6	1280.8	1280.3	1279.1	1277.9	1276.7	1275.5
12.5°	1259.6	1259.6	1259.4	1258.6	1257.3	1255.8	1254.5	1253.1
15°	1223.5	1222.3	1221.1	1219.6	1218.0	1216.3	1214.7	1213.0
17.5°	1180.3	1177.7	1175.2	1172.7	1170.2	1167.7	1165.2	1162.7
20°	1150.6	1147.6	1144.5	1141.5	1138.6	1135.7	1132.8	1130.0
22.5°	1119.0	1115.1	1111.2	1107.9	1105.3	1102.6	1099.9	1097.2
25°	1067.1	1062.0	1057.0	1053.1	1050.5	1047.9	1045.3	1042.6
27.5°	1010.5	1003.5	996.5	991.0	987.0	982.9	978.9	974.9
30°	970.3	962.1	953.9	948.0	944.1	940.3	936.4	932.6
32.5°	930.7	921.9	912.9	906.5	902.5	898.4	894.4	890.3
35°	872.1	861.8	851.5	844.2	840.0	835.6	831.3	827.0
37.5°	809.2	797.5	785.8	777.3	772.0	766.7	761.4	756.1
40°	765.4	753.0	740.5	731.5	726.0	720.5	714.9	709.5
42.5°	723.4	709.8	696.2	686.9	682.0	677.1	672.1	667.2
45°	661.6	648.0	634.3	624.6	618.9	613.1	607.4	601.7
47.5°	597.8	583.0	568.1	558.1	552.9	547.9	542.7	537.6
50°	554.7	539.8	525.0	514.8	509.3	503.7	498.3	492.7
52.5°	513.0	497.6	482.1	471.9	467.0	462.1	457.2	452.2
55°	450.9	437.0	423.1	413.8	409.0	404.2	399.4	394.6
57.5°	389.9	376.8	363.7	355.1	351.0	346.9	342.9	338.7
60°	351.5	338.6	325.6	317.1	313.1	309.0	304.9	300.8
62.5°	313.3	301.2	289.0	280.7	276.6	272.3	268.0	263.7
65°	259.0	247.2	235.5	228.3	225.7	223.1	220.5	217.8
67.5°	207.2	198.4	189.6	183.8	181.0	178.2	175.3	172.5
70°	175.2	166.8	158.4	152.9	150.2	147.6	145.0	142.4
72.5°	146.3	139.4	132.6	128.7	127.5	126.4	125.3	124.2
75°	109.5	107.1	104.7	103.3	102.8	102.3	101.8	101.3
77.5°	82.6	81.3	80.0	79.1	78.7	78.2	77.7	77.2
80°	66.5	65.8	65.0	64.5	64.0	63.5	63.0	62.5
82.5°	50.9	50.2	49.5	49.1	49.0	49.0	48.8	48.7
85°	29.2	28.8	28.3	28.0	28.0	28.0	28.0	28.0
87.5°	13.2	13.1	12.9	12.8	12.7	12.5	12.4	12.2
90°	11.6	12.0	12.4	12.8	13.0	13.2	13.4	13.5
92.5°	12.8	13.5	14.1	14.5	14.7	14.7	14.9	15.0
95°	15.4	16.1	16.8	17.2	17.2	17.2	17.2	17.2
97.5°	16.2	17.0	17.7	18.2	18.3	18.4	18.5	18.6
100°	16.5	17.3	18.1	18.5	18.7	18.8	18.9	19.0
102.5°	24.7	22.3	19.8	18.6	18.8	19.0	19.2	19.3
105°	63.4	45.6	27.9	19.1	19.3	19.5	19.6	19.9
107.5°	155.3	142.3	129.2	116.1	102.6	89.2	75.8	62.4
110°	197.2	193.8	190.5	181.6	167.3	153.0	138.6	124.2



TEST NUMBER: P332339-927

CATALOG NUMBER: S123RDIP-S1000D585U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	226.6	226.7	226.8	225.3	222.3	219.2	216.2	213.2
115°	261.3	262.4	263.4	264.0	264.4	264.9	265.3	265.7
117.5°	292.8	293.6	294.4	294.9	294.9	295.0	295.1	295.2
120°	313.4	314.2	315.0	315.4	315.4	315.4	315.4	315.4
122.5°	333.5	334.1	334.6	334.9	335.0	335.1	335.2	335.3
125°	361.9	362.0	362.3	362.5	362.7	362.9	363.1	363.3
127.5°	390.3	390.6	390.9	391.0	390.8	390.6	390.4	390.2
130°	407.4	407.8	408.2	408.4	408.1	408.0	407.7	407.6
132.5°	423.7	424.1	424.5	424.6	424.3	424.0	423.7	423.4
135°	448.4	448.7	448.9	448.9	448.7	448.4	448.1	447.7
137.5°	470.3	470.8	471.3	471.4	471.2	471.0	470.8	470.6
140°	484.3	484.7	485.1	485.1	485.0	484.7	484.6	484.3
142.5°	497.5	497.8	498.1	498.1	497.9	497.6	497.3	497.0
145°	515.9	516.1	516.3	516.4	516.4	516.4	516.4	516.4
147.5°	532.5	532.7	532.9	532.7	532.3	531.8	531.4	530.9
150°	542.6	542.8	543.0	543.0	542.6	542.3	542.0	541.8
152.5°	551.6	551.9	552.3	552.2	551.8	551.4	550.9	550.4
155°	564.0	564.5	565.0	564.9	564.4	563.7	563.2	562.5
157.5°	574.7	575.4	576.0	575.8	575.0	574.3	573.5	572.7
160°	580.9	581.5	582.1	582.0	581.4	580.7	580.0	579.2
162.5°	586.5	587.2	587.9	587.9	587.2	586.6	586.0	585.4
165°	594.0	594.8	595.6	595.6	594.9	594.2	593.5	592.8
167.5°	599.8	600.6	601.3	601.3	600.6	599.8	599.0	598.1
170°	603.0	603.8	604.6	604.6	603.8	603.0	602.2	601.3
172.5°	605.1	605.9	606.7	606.7	605.9	605.0	604.0	603.2
175°	607.8	608.5	609.2	609.1	608.3	607.5	606.7	605.9
177.5°	608.7	609.3	610.0	609.9	609.1	608.3	607.5	606.7
180°	608.2	608.2	608.2	608.2	608.2	608.2	608.2	608.2

(END OF REPORT)