

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332269-930

Luminaire Tested: **S123RDIP-S340D1195U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332269-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D1195U930-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4582.4 lumens  
Efficiency: N/A  
Efficacy: 108.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332269-930

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332269-930

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	23
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	27	20
2	84	77	71	66	74	68	64	60	53	49	47	38	36	34	25	24	23	17
3	76	68	61	55	68	60	54	50	47	43	39	34	31	29	22	21	19	14
4	70	60	52	47	62	53	47	42	41	37	33	30	27	25	20	18	17	12
5	64	53	45	40	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	40	34	52	43	36	31	33	28	25	24	21	19	16	14	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	41	32	25	21	25	20	17	19	15	13	13	11	9	7
10	44	32	25	21	39	29	23	19	23	18	15	17	14	12	12	10	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5042	5042	5042
5°	5061	4991	5020
10°	5032	4928	4912
15°	4979	4813	4763
20°	4904	4669	4560
25°	4828	4507	4363
30°	4727	4320	4084
35°	4623	4133	3829
40°	4526	3912	3513
45°	4401	3694	3227
50°	4262	3448	2907
55°	4121	3166	2609
60°	3991	2863	2282
65°	3823	2534	1954
70°	3610	2127	1577
75°	3302	1676	1485
80°	2944	1488	1364
85°	2482	1309	1223



TEST NUMBER: P332269-930

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.0	1.0
10°-20°	122.4	2.7
20°-30°	176.2	3.8
30°-40°	198.5	4.3
40°-50°	189.9	4.1
50°-60°	155.5	3.4
60°-70°	104.9	2.3
70°-80°	52.8	1.2
80°-90°	17.6	0.4
90°-100°	260.4	5.7
100°-110°	737.4	16.1
110°-120°	725.4	15.8
120°-130°	578.6	12.6
130°-140°	456.2	10.0
140°-150°	340.5	7.4
150°-160°	237.3	5.2
160°-170°	139.4	3.0
170°-180°	45.4	1.0
0°-30°	342.6	7.5
0°-40°	541.1	11.8
0°-60°	886.5	19.3
0°-90°	1061.8	23.2
90°-120°	1723.2	37.6
90°-150°	3098.5	67.6
90°-180°	3521.0	76.8
0°-180°	4582.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	468	468	468	468	468	
5°	468	466	462	465	465	44
15°	447	442	432	430	427	126
25°	406	396	380	372	367	187
35°	352	338	314	299	291	220
45°	289	271	243	222	212	223
55°	220	200	169	147	139	197
65°	150	129	100	82	77	148
75°	79	61	40	37	36	85
85°	20	12	11	10	10	23
90°	2	11	24	27	28	3
95°	32	105	562	164	110	35
105°	110	162	762	1332	1205	117
115°	194	242	582	1277	1465	192
125°	270	319	544	985	1156	239
135°	316	378	536	811	937	244
145°	361	414	530	665	732	226
155°	410	442	512	583	607	189
165°	448	461	491	520	530	126
175°	467	468	471	477	476	44
180°	468	468	468	468	468	



TEST NUMBER: P332269-930

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4
2.5°	469.9	469.6	469.4	469.1	468.9	468.3	467.5	466.7	465.9	465.0	465.8
5°	468.4	468.0	467.6	467.2	466.7	466.0	465.0	464.0	462.9	461.9	462.7
7.5°	464.1	463.6	463.2	462.7	462.3	461.4	460.1	458.8	457.4	456.1	456.5
10°	460.4	459.8	459.3	458.7	458.0	457.0	455.5	454.0	452.4	450.9	451.0
12.5°	455.3	454.6	454.0	453.3	452.7	451.3	449.5	447.7	445.8	443.9	443.8
15°	446.8	445.8	444.9	443.9	443.0	441.4	439.0	436.7	434.3	431.9	431.5
17.5°	436.0	435.0	433.9	432.8	431.7	429.7	426.6	423.6	420.7	417.7	416.8
20°	428.1	426.8	425.4	424.1	422.7	420.4	417.3	414.0	410.8	407.6	406.5
22.5°	419.3	417.8	416.2	414.7	413.1	410.7	407.2	403.8	400.4	397.0	395.6
25°	406.5	404.4	402.3	400.1	398.0	395.0	391.2	387.3	383.4	379.5	377.7
27.5°	390.9	388.6	386.2	383.9	381.6	378.3	374.0	369.6	365.3	360.9	358.5
30°	380.3	377.7	375.2	372.7	370.1	366.5	361.7	357.0	352.3	347.6	344.7
32.5°	369.7	366.7	363.9	361.0	358.2	354.2	349.2	344.2	339.2	334.2	331.1
35°	351.8	348.7	345.7	342.7	339.7	335.5	330.3	325.0	319.8	314.5	311.0
37.5°	333.7	330.3	326.9	323.6	320.2	315.7	310.1	304.5	299.0	293.3	289.3
40°	322.1	318.5	314.7	311.0	307.3	302.4	296.4	290.4	284.5	278.4	274.1
42.5°	309.1	305.3	301.7	297.9	294.2	289.3	283.1	276.9	270.7	264.5	259.7
45°	289.1	285.3	281.5	277.7	273.9	268.7	262.3	255.8	249.2	242.7	237.9
47.5°	269.1	265.0	260.7	256.6	252.4	247.1	240.6	234.1	227.6	221.1	215.9
50°	254.5	250.5	246.6	242.6	238.6	233.3	226.4	219.6	212.7	205.9	200.6
52.5°	241.5	237.2	232.8	228.5	224.2	218.7	211.9	205.1	198.4	191.6	186.2
55°	219.6	215.4	211.3	207.2	203.0	197.4	190.2	183.0	175.9	168.7	163.8
57.5°	199.3	194.9	190.4	185.8	181.3	175.5	168.3	161.0	153.8	146.7	142.0
60°	185.4	180.8	176.1	171.5	166.8	161.0	154.0	147.0	140.0	133.0	128.4
62.5°	171.4	166.7	162.1	157.5	152.9	147.0	140.0	133.0	126.0	119.0	114.7
65°	150.1	145.4	140.8	136.2	131.5	125.9	119.3	112.7	106.2	99.5	95.4
67.5°	128.7	124.0	119.3	114.6	109.9	104.4	98.1	91.8	85.4	79.2	76.1
70°	114.7	110.1	105.6	101.0	96.5	91.2	85.4	79.4	73.5	67.6	64.7
72.5°	100.8	96.3	91.8	87.2	82.8	77.9	72.5	67.1	61.7	56.3	54.0
75°	79.4	75.3	71.3	67.3	63.2	58.9	54.2	49.6	44.9	40.3	39.5
77.5°	59.9	56.3	52.6	48.9	45.3	42.0	39.0	36.0	33.0	30.0	29.6
80°	47.5	44.0	40.6	37.1	33.7	31.1	29.3	27.5	25.7	24.0	23.6
82.5°	35.6	32.6	29.7	26.7	23.6	21.8	21.0	20.1	19.3	18.4	18.2
85°	20.1	18.3	16.4	14.6	12.7	11.7	11.4	11.2	10.9	10.6	10.4
87.5°	7.7	7.3	6.9	6.8	6.4	6.4	7.0	7.6	8.2	8.7	8.4
90°	1.9	3.8	5.7	8.6	10.4	12.3	15.2	18.0	20.9	23.6	22.7
92.5°	11.7	17.4	25.4	32.8	40.8	54.8	79.6	120.3	160.3	145.7	109.9
95°	32.2	35.1	45.5	61.6	86.2	123.1	203.7	344.8	500.2	561.7	455.6
97.5°	55.0	55.8	64.0	78.0	102.3	142.3	219.2	378.3	637.3	870.5	931.3
100°	70.1	71.0	77.7	90.9	113.7	150.6	217.0	357.1	606.3	897.1	1083.7
102.5°	86.0	87.7	93.6	106.1	126.5	160.5	220.0	338.9	560.8	847.8	1091.2
105°	109.9	112.8	118.4	129.8	147.7	177.2	228.3	325.9	504.9	761.6	1033.5
107.5°	135.3	138.1	143.6	154.7	171.6	198.9	243.9	324.9	469.3	685.4	932.3
110°	153.4	156.3	161.0	171.5	187.5	214.1	256.7	328.7	455.6	642.2	868.6



TEST NUMBER: P332269-930

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	170.2	173.0	177.7	188.1	204.2	230.0	269.6	336.3	448.1	613.4	813.3
115°	194.2	198.0	203.7	213.1	229.3	254.8	290.8	348.6	445.2	582.5	746.4
117.5°	218.3	222.6	227.3	236.0	254.0	277.8	313.3	364.8	446.9	564.4	706.0
120°	234.9	237.7	242.5	252.0	269.9	293.7	327.8	377.0	450.0	556.0	684.9
122.5°	249.3	252.2	256.9	267.1	284.4	309.6	342.9	388.4	455.3	550.7	667.4
125°	269.9	271.9	277.5	288.0	306.0	331.5	364.7	406.3	463.2	543.7	645.1
127.5°	285.7	288.5	295.5	306.1	326.0	351.6	383.6	421.2	472.3	540.3	625.4
130°	295.5	298.4	306.9	318.3	338.2	363.7	395.0	431.0	478.3	538.0	614.7
132.5°	303.1	306.7	316.0	329.6	349.5	374.4	404.9	440.1	482.9	537.3	605.0
135°	316.4	320.2	330.6	344.8	364.7	390.3	419.6	451.8	489.8	536.1	592.1
137.5°	328.9	332.9	343.1	358.2	378.0	401.6	429.8	460.6	494.3	534.0	580.8
140°	337.2	341.9	351.4	366.6	385.6	409.2	436.7	465.1	497.3	533.3	574.1
142.5°	346.3	350.3	360.5	374.1	393.1	415.3	442.0	469.6	499.6	531.8	567.9
145°	360.9	363.7	372.3	386.5	402.6	424.4	449.0	474.6	501.1	529.5	559.9
147.5°	375.7	377.4	385.7	398.0	413.6	432.1	454.7	477.6	501.1	525.9	551.9
150°	385.6	386.5	394.0	406.3	419.6	436.7	458.4	478.3	501.1	522.9	546.6
152.5°	395.4	395.6	403.2	413.9	425.7	442.0	460.7	479.9	498.8	519.1	540.5
155°	410.2	410.2	415.9	425.3	435.7	449.0	465.1	480.3	496.4	512.5	531.4
157.5°	421.9	422.7	427.2	435.5	444.4	454.7	467.6	481.2	493.2	506.6	521.1
160°	431.0	431.0	434.8	442.4	449.0	458.4	469.9	481.2	491.6	502.1	514.4
162.5°	437.8	437.8	440.8	446.9	452.8	460.7	470.6	480.5	488.6	497.5	507.5
165°	448.1	447.1	449.0	453.7	457.5	464.1	471.7	478.3	484.0	490.6	498.2
167.5°	455.8	454.7	455.6	459.3	461.9	466.0	471.6	476.9	479.5	483.9	489.3
170°	460.4	458.4	459.4	462.3	464.1	466.0	470.8	474.6	476.5	479.3	484.0
172.5°	463.4	462.3	462.4	464.6	465.7	466.8	470.8	473.9	474.2	475.5	478.7
175°	467.0	466.0	465.1	467.0	467.0	468.0	469.9	471.7	470.8	470.8	472.7
177.5°	468.7	468.0	467.2	468.0	468.0	468.0	468.7	470.2	468.7	468.0	468.7
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0



TEST NUMBER: P332269-930

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4
2.5°	466.5	467.2	468.1	468.3	468.2	468.1	467.9	467.8
5°	463.5	464.2	465.0	465.3	465.1	465.0	464.8	464.6
7.5°	457.0	457.4	457.8	457.9	457.5	457.3	457.0	456.7
10°	451.1	451.2	451.3	451.1	450.7	450.3	449.8	449.4
12.5°	443.8	443.8	443.8	443.4	443.0	442.5	442.0	441.5
15°	431.0	430.6	430.2	429.7	429.2	428.5	428.0	427.4
17.5°	415.9	415.0	414.1	413.2	412.3	411.4	410.6	409.7
20°	405.4	404.3	403.2	402.2	401.1	400.1	399.2	398.1
22.5°	394.3	392.9	391.5	390.4	389.4	388.5	387.5	386.6
25°	375.9	374.2	372.4	371.0	370.1	369.2	368.3	367.4
27.5°	356.0	353.6	351.1	349.2	347.7	346.3	345.0	343.5
30°	341.9	339.0	336.1	334.0	332.6	331.3	330.0	328.6
32.5°	327.9	324.8	321.6	319.4	318.0	316.6	315.1	313.7
35°	307.3	303.6	300.0	297.4	296.0	294.4	292.9	291.4
37.5°	285.1	281.0	276.9	273.9	272.0	270.1	268.2	266.4
40°	269.7	265.3	260.9	257.7	255.8	253.9	251.9	250.0
42.5°	254.9	250.1	245.3	242.1	240.3	238.6	236.8	235.1
45°	233.1	228.3	223.5	220.0	218.1	216.1	214.0	212.0
47.5°	210.6	205.4	200.2	196.7	194.9	193.1	191.2	189.4
50°	195.4	190.2	185.0	181.4	179.4	177.5	175.5	173.6
52.5°	180.8	175.3	169.9	166.3	164.5	162.8	161.1	159.3
55°	158.9	154.0	149.1	145.8	144.1	142.4	140.7	139.0
57.5°	137.4	132.7	128.2	125.1	123.7	122.2	120.8	119.4
60°	123.8	119.3	114.7	111.7	110.3	108.8	107.5	106.0
62.5°	110.4	106.2	101.8	98.9	97.4	96.0	94.4	92.9
65°	91.2	87.2	83.0	80.5	79.5	78.6	77.7	76.7
67.5°	73.0	69.9	66.8	64.7	63.8	62.8	61.8	60.8
70°	61.7	58.8	55.8	53.9	52.9	52.0	51.0	50.1
72.5°	51.5	49.2	46.7	45.3	44.9	44.5	44.2	43.8
75°	38.6	37.7	36.9	36.4	36.2	36.0	35.9	35.7
77.5°	29.1	28.6	28.2	27.9	27.7	27.6	27.4	27.2
80°	23.4	23.2	22.9	22.7	22.5	22.3	22.2	22.0
82.5°	17.9	17.7	17.4	17.3	17.3	17.2	17.2	17.2
85°	10.3	10.1	9.9	9.9	9.9	9.9	9.9	9.9
87.5°	8.6	8.6	8.8	9.1	8.9	9.0	9.1	8.8
90°	23.6	24.6	25.6	27.5	26.5	27.5	28.5	27.5
92.5°	79.7	63.3	55.8	51.0	49.2	46.4	47.4	45.7
95°	341.0	231.1	180.9	146.8	128.8	120.3	113.7	109.9
97.5°	850.0	680.9	558.7	445.4	375.5	332.9	307.3	299.1
100°	1116.8	1040.1	929.3	794.8	699.0	629.9	593.0	593.9
102.5°	1205.5	1203.0	1138.4	1053.1	978.7	924.0	893.1	871.3
105°	1231.4	1326.2	1344.2	1319.6	1275.9	1240.0	1209.7	1204.9
107.5°	1156.7	1310.6	1393.6	1427.3	1428.1	1415.9	1405.7	1397.0
110°	1085.6	1259.9	1379.2	1445.5	1472.0	1479.6	1477.7	1475.9





TEST NUMBER: P332269-930

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1015.0	1193.2	1326.9	1412.2	1460.7	1484.2	1491.3	1491.8
115°	921.7	1086.5	1225.7	1329.0	1400.0	1441.7	1460.7	1465.4
117.5°	854.0	996.3	1121.4	1226.1	1300.2	1347.9	1375.2	1381.7
120°	818.4	946.3	1060.0	1155.7	1230.4	1283.5	1306.3	1312.0
122.5°	790.4	906.1	1011.5	1100.3	1166.9	1214.6	1239.6	1246.8
125°	753.1	856.3	947.2	1023.0	1083.7	1125.4	1149.0	1155.7
127.5°	720.5	812.5	894.5	963.5	1017.6	1053.1	1074.6	1080.6
130°	700.0	785.3	862.0	926.4	976.6	1010.7	1030.6	1038.2
132.5°	681.1	759.5	831.0	892.3	939.5	973.5	991.2	996.5
135°	655.5	722.8	784.3	838.3	884.8	913.1	930.2	936.9
137.5°	632.2	687.3	740.4	787.2	826.2	855.0	869.4	873.8
140°	618.6	666.8	712.3	753.1	789.0	815.6	830.7	829.8
142.5°	605.7	647.2	686.6	722.0	752.7	776.2	789.8	788.9
145°	590.1	621.4	651.8	679.1	702.9	722.8	730.3	732.2
147.5°	577.5	602.3	626.7	646.2	664.2	677.7	684.9	685.6
150°	568.3	590.1	610.0	628.0	642.2	652.6	658.4	658.4
152.5°	560.0	578.8	596.4	611.4	622.6	632.2	635.6	635.6
155°	547.5	562.6	576.9	588.2	596.8	604.4	606.3	607.2
157.5°	534.3	547.0	557.9	566.8	574.2	579.9	581.4	581.2
160°	526.7	537.1	546.6	553.2	559.9	565.5	565.5	564.6
162.5°	517.6	526.5	535.2	541.0	545.4	550.3	550.3	549.4
165°	505.8	511.5	518.1	522.9	526.7	530.4	529.5	529.5
167.5°	495.6	499.9	503.8	507.2	508.8	511.5	510.5	510.5
170°	488.8	491.6	495.4	497.3	498.2	500.2	499.2	499.2
172.5°	482.7	484.8	487.9	488.9	489.2	491.1	489.3	488.6
175°	474.6	475.5	477.4	477.4	477.4	478.3	477.4	476.5
177.5°	469.4	470.2	471.0	471.0	470.2	471.0	469.4	469.4
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0

(END OF REPORT)