

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332291-930

Luminaire Tested: **S123RDIP-S560D1025U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332291-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D1025U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5083.0 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332291-930

CATALOG NUMBER: S123RDIP-S560D1025U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332291-930

CATALOG NUMBER: S123RDIP-S560D1025U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42
1	94	90	87	83	85	82	79	76	66	63	62	51	49	48	37	36	36
2	86	79	73	68	78	72	67	62	58	54	51	45	43	41	33	32	30
3	79	70	63	57	71	63	57	52	51	47	43	40	37	34	29	28	26
4	72	62	54	48	65	56	50	44	45	41	37	36	32	30	26	24	23
5	66	55	47	41	60	50	43	38	41	36	32	32	28	26	24	22	20
6	61	49	41	36	55	45	38	33	37	32	28	29	25	23	22	19	17
7	56	44	37	31	51	41	34	29	33	28	24	26	23	20	20	17	16
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	49	37	29	25	44	34	27	23	28	23	19	22	19	16	17	14	13
10	45	34	27	22	41	31	25	20	25	21	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8289	8289	8289
5°	8321	8206	8253
10°	8273	8103	8075
15°	8184	7913	7830
20°	8062	7676	7497
25°	7936	7410	7172
30°	7771	7102	6714
35°	7599	6795	6294
40°	7442	6433	5774
45°	7234	6075	5305
50°	7006	5668	4779
55°	6775	5204	4290
60°	6562	4706	3750
65°	6283	4167	3212
70°	5936	3500	2593
75°	5427	2753	2441
80°	4841	2442	2244
85°	4088	2149	2001



TEST NUMBER: P332291-930

CATALOG NUMBER: S123RDIP-S560D1025U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.3	1.4
10°-20°	201.2	4.0
20°-30°	289.7	5.7
30°-40°	326.3	6.4
40°-50°	312.2	6.1
50°-60°	255.7	5.0
60°-70°	172.5	3.4
70°-80°	86.8	1.7
80°-90°	26.0	0.5
90°-100°	39.8	0.8
100°-110°	189.8	3.7
110°-120°	455.9	9.0
120°-130°	580.5	11.4
130°-140°	620.3	12.2
140°-150°	580.0	11.4
150°-160°	467.9	9.2
160°-170°	302.0	5.9
170°-180°	104.1	2.0
0°-30°	563.2	11.1
0°-40°	889.5	17.5
0°-60°	1457.4	28.7
0°-90°	1742.7	34.3
90°-120°	685.5	13.5
90°-150°	2466.4	48.5
90°-180°	3340.0	65.7
0°-180°	5083.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	770	770	770	770	770	
5°	770	767	760	765	764	73
15°	734	727	710	707	703	207
25°	668	652	624	611	604	307
35°	578	555	517	491	479	362
45°	475	446	399	365	348	367
55°	361	329	277	242	229	324
65°	247	212	164	134	126	244
75°	130	100	66	60	59	139
85°	33	20	17	16	16	37
90°	1	9	20	23	24	4
95°	50	19	25	31	31	61
105°	242	247	178	42	36	257
115°	455	460	467	475	478	449
125°	641	648	651	653	654	572
135°	798	803	806	809	806	614
145°	921	927	928	930	930	576
155°	1015	1013	1014	1018	1013	467
165°	1070	1068	1067	1073	1068	302
175°	1095	1092	1092	1097	1091	104
180°	1095	1095	1095	1095	1095	



TEST NUMBER: P332291-930

CATALOG NUMBER: S123RDIP-S560D1025U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1
2.5°	772.6	772.1	771.7	771.2	770.8	769.9	768.6	767.2	765.9	764.6	765.8
5°	770.1	769.4	768.7	768.0	767.3	766.1	764.4	762.8	761.1	759.5	760.7
7.5°	763.0	762.2	761.4	760.7	759.9	758.5	756.4	754.2	752.0	749.8	750.5
10°	756.9	755.9	755.0	754.0	753.1	751.3	748.9	746.3	743.8	741.4	741.4
12.5°	748.4	747.4	746.2	745.2	744.1	742.1	739.0	736.0	732.9	729.9	729.8
15°	734.4	733.0	731.4	729.9	728.4	725.6	721.8	717.9	714.0	710.1	709.4
17.5°	716.8	715.1	713.3	711.5	709.7	706.4	701.4	696.5	691.5	686.6	685.2
20°	703.8	701.6	699.4	697.2	695.0	691.2	685.9	680.7	675.4	670.1	668.3
22.5°	689.3	686.8	684.3	681.7	679.1	675.1	669.4	663.8	658.3	652.6	650.4
25°	668.2	664.8	661.3	657.9	654.4	649.5	643.0	636.7	630.3	623.9	621.0
27.5°	642.6	638.8	635.0	631.1	627.3	621.8	614.7	607.6	600.5	593.5	589.4
30°	625.2	621.0	616.9	612.7	608.5	602.5	594.8	587.0	579.2	571.4	566.7
32.5°	607.6	603.0	598.3	593.5	588.8	582.4	574.1	565.9	557.7	549.4	544.3
35°	578.3	573.3	568.3	563.4	558.3	551.5	542.9	534.3	525.7	517.1	511.1
37.5°	548.6	543.1	537.5	531.9	526.4	519.0	509.8	500.7	491.5	482.2	475.5
40°	529.6	523.5	517.4	511.3	505.2	497.2	487.4	477.5	467.7	457.8	450.5
42.5°	508.1	502.0	495.9	489.8	483.7	475.6	465.4	455.2	445.0	434.8	426.9
45°	475.2	469.0	462.8	456.6	450.3	441.8	431.1	420.4	409.8	399.1	391.2
47.5°	442.4	435.5	428.7	421.8	415.0	406.3	395.5	384.8	374.1	363.5	354.9
50°	418.4	411.9	405.4	398.8	392.3	383.4	372.2	361.0	349.8	338.5	329.9
52.5°	397.0	389.9	382.8	375.7	368.7	359.5	348.4	337.3	326.1	315.0	306.1
55°	361.0	354.2	347.4	340.6	333.8	324.5	312.7	300.9	289.1	277.3	269.2
57.5°	327.8	320.3	312.9	305.5	298.1	288.5	276.6	264.8	252.9	241.1	233.5
60°	304.8	297.2	289.5	281.8	274.3	264.6	253.2	241.7	230.1	218.6	211.1
62.5°	281.8	274.2	266.5	258.9	251.3	241.7	230.2	218.7	207.1	195.6	188.6
65°	246.7	239.0	231.5	223.8	216.1	206.9	196.1	185.3	174.5	163.6	156.9
67.5°	211.6	203.9	196.2	188.4	180.8	171.7	161.3	150.9	140.6	130.1	125.1
70°	188.6	181.1	173.7	166.2	158.7	150.0	140.3	130.6	120.9	111.2	106.3
72.5°	165.6	158.2	150.8	143.5	136.1	128.0	119.2	110.3	101.5	92.7	88.7
75°	130.5	123.8	117.2	110.6	103.9	96.7	89.1	81.4	73.9	66.2	64.8
77.5°	98.6	92.5	86.5	80.5	74.4	69.0	64.1	59.2	54.2	49.3	48.6
80°	78.1	72.4	66.7	61.0	55.3	51.0	48.1	45.2	42.2	39.4	38.9
82.5°	58.6	53.6	48.8	43.9	38.9	35.8	34.4	33.1	31.7	30.3	29.9
85°	33.1	30.1	27.0	24.0	20.9	19.2	18.8	18.3	17.9	17.4	17.2
87.5°	12.1	11.3	10.4	9.5	8.7	8.6	9.0	9.5	9.9	10.4	10.4
90°	0.8	2.6	4.4	6.3	8.1	10.1	12.5	14.8	17.2	19.6	20.2
92.5°	15.2	14.6	14.1	13.6	13.1	13.8	15.5	17.3	19.1	20.9	22.0
95°	49.7	42.2	34.8	27.4	20.0	17.3	19.2	21.3	23.2	25.2	26.5
97.5°	99.8	96.4	93.1	89.8	86.4	78.3	65.3	52.3	39.2	26.2	27.6
100°	137.5	141.1	144.8	148.4	152.0	139.7	111.5	83.2	55.0	26.8	28.3
102.5°	180.5	183.1	185.7	188.3	190.9	176.8	146.0	115.2	84.4	53.6	49.1
105°	242.5	244.5	246.5	248.5	250.5	243.3	227.1	210.8	194.5	178.2	146.2
107.5°	307.9	309.6	311.1	312.7	314.3	316.4	318.9	321.6	324.1	326.7	303.2
110°	351.6	353.0	354.4	355.9	357.3	359.1	361.0	363.1	365.0	367.0	361.0



TEST NUMBER: P332291-930

CATALOG NUMBER: S123RDIP-S560D1025U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	393.2	394.5	395.8	397.1	398.4	400.1	402.1	404.1	406.0	408.1	408.1
115°	454.9	456.0	457.1	458.2	459.3	460.6	462.2	463.8	465.5	467.1	469.0
117.5°	514.6	516.0	517.3	518.7	520.0	521.1	521.9	522.8	523.6	524.4	525.9
120°	551.7	553.3	555.0	556.6	558.2	559.4	559.9	560.4	561.0	561.5	563.0
122.5°	589.5	590.8	592.2	593.5	594.8	595.9	596.6	597.3	597.9	598.6	599.7
125°	641.2	642.7	644.2	645.6	647.0	648.2	648.9	649.5	650.3	651.0	651.4
127.5°	691.4	692.8	694.3	695.7	697.2	698.3	699.2	700.1	700.9	701.8	702.4
130°	722.7	724.1	725.5	727.0	728.5	729.5	730.3	731.0	731.6	732.4	733.1
132.5°	752.6	754.1	755.5	756.9	758.4	759.4	759.9	760.5	761.2	761.7	762.5
135°	798.3	799.4	800.5	801.6	802.7	803.6	804.3	805.0	805.8	806.5	807.0
137.5°	837.4	838.8	840.2	841.6	842.9	843.8	844.2	844.6	845.0	845.4	846.2
140°	863.4	864.5	865.6	866.7	867.8	868.6	869.1	869.7	870.3	870.7	871.5
142.5°	887.5	888.6	889.7	890.8	891.9	892.7	893.2	893.7	894.3	894.9	895.4
145°	921.2	922.5	923.7	925.0	926.3	927.1	927.5	927.8	928.1	928.5	928.9
147.5°	952.9	953.8	954.6	955.4	956.3	956.8	957.2	957.6	958.0	958.3	958.7
150°	972.5	973.1	973.5	974.1	974.6	975.1	975.4	975.8	976.2	976.6	976.9
152.5°	990.0	990.3	990.6	990.8	991.1	991.3	991.5	991.7	992.0	992.1	992.8
155°	1014.8	1014.4	1014.1	1013.7	1013.3	1013.3	1013.4	1013.6	1013.8	1014.0	1014.9
157.5°	1034.0	1034.0	1034.0	1033.9	1033.9	1033.7	1033.6	1033.4	1033.2	1033.0	1034.1
160°	1045.7	1045.5	1045.4	1045.2	1045.0	1044.8	1044.6	1044.5	1044.2	1044.1	1045.2
162.5°	1056.8	1056.3	1055.8	1055.4	1054.9	1054.6	1054.4	1054.2	1054.0	1053.9	1055.1
165°	1070.2	1069.6	1069.0	1068.5	1068.0	1067.6	1067.4	1067.2	1067.1	1066.9	1068.3
167.5°	1080.5	1079.9	1079.1	1078.4	1077.7	1077.3	1077.3	1077.3	1077.3	1077.3	1078.7
170°	1086.4	1085.7	1085.0	1084.3	1083.5	1083.1	1083.1	1083.1	1083.1	1083.1	1084.6
172.5°	1090.3	1089.5	1088.6	1087.7	1086.9	1086.5	1086.6	1086.8	1086.9	1087.0	1088.5
175°	1095.4	1094.5	1093.6	1092.7	1091.8	1091.4	1091.5	1091.8	1091.9	1092.1	1093.4
177.5°	1096.7	1095.9	1095.2	1094.5	1093.8	1093.5	1093.6	1093.8	1093.9	1094.1	1095.2
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P332291-930

CATALOG NUMBER: S123RDIP-S560D1025U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1
2.5°	767.0	768.3	769.5	770.0	769.7	769.5	769.3	769.1
5°	761.9	763.2	764.4	764.9	764.7	764.3	764.1	763.8
7.5°	751.2	751.9	752.6	752.7	752.2	751.8	751.3	750.8
10°	741.6	741.8	741.8	741.6	740.9	740.2	739.6	738.8
12.5°	729.7	729.6	729.5	729.0	728.2	727.4	726.7	725.9
15°	708.7	708.0	707.4	706.5	705.5	704.6	703.6	702.6
17.5°	683.7	682.2	680.7	679.3	677.8	676.4	674.9	673.5
20°	666.5	664.7	662.9	661.2	659.5	657.9	656.2	654.5
22.5°	648.2	645.9	643.7	641.7	640.2	638.6	637.1	635.5
25°	618.1	615.1	612.3	610.0	608.5	607.0	605.4	603.9
27.5°	585.3	581.3	577.2	574.1	571.7	569.4	567.0	564.7
30°	562.0	557.3	552.6	549.1	546.9	544.7	542.4	540.2
32.5°	539.2	533.9	528.8	525.1	522.8	520.4	518.0	515.8
35°	505.2	499.2	493.3	489.0	486.5	484.0	481.5	479.0
37.5°	468.7	461.9	455.2	450.3	447.2	444.1	441.0	437.9
40°	443.4	436.1	428.9	423.7	420.5	417.4	414.2	410.9
42.5°	419.1	411.2	403.2	397.9	395.0	392.2	389.3	386.5
45°	383.3	375.4	367.5	361.8	358.5	355.1	351.8	348.5
47.5°	346.3	337.7	329.1	323.3	320.3	317.3	314.4	311.4
50°	321.3	312.7	304.1	298.2	295.0	291.8	288.6	285.4
52.5°	297.2	288.2	279.2	273.4	270.5	267.7	264.8	262.0
55°	261.2	253.2	245.1	239.7	236.9	234.2	231.4	228.6
57.5°	225.8	218.3	210.7	205.7	203.3	201.0	198.6	196.2
60°	203.6	196.1	188.6	183.7	181.3	179.0	176.6	174.2
62.5°	181.5	174.5	167.4	162.7	160.2	157.7	155.2	152.8
65°	150.0	143.2	136.4	132.2	130.8	129.2	127.7	126.1
67.5°	120.0	114.9	109.8	106.5	104.8	103.2	101.6	100.0
70°	101.4	96.6	91.7	88.5	87.0	85.5	84.0	82.4
72.5°	84.7	80.8	76.8	74.5	73.9	73.2	72.6	71.9
75°	63.4	62.0	60.7	59.8	59.5	59.3	58.9	58.7
77.5°	47.9	47.1	46.3	45.8	45.6	45.2	45.0	44.7
80°	38.5	38.1	37.7	37.3	37.1	36.8	36.5	36.2
82.5°	29.5	29.1	28.7	28.5	28.4	28.4	28.3	28.2
85°	17.0	16.6	16.4	16.2	16.2	16.2	16.2	16.2
87.5°	10.4	10.5	10.5	10.5	10.5	10.4	10.4	10.4
90°	21.0	21.7	22.4	23.0	23.3	23.7	24.1	24.4
92.5°	23.2	24.3	25.4	26.2	26.3	26.6	26.8	27.0
95°	27.7	29.0	30.3	30.9	30.9	30.9	30.9	30.9
97.5°	29.1	30.6	32.0	32.8	33.0	33.2	33.3	33.5
100°	29.8	31.2	32.6	33.4	33.7	33.8	34.0	34.2
102.5°	44.6	40.1	35.6	33.5	33.8	34.2	34.5	34.8
105°	114.2	82.2	50.2	34.3	34.7	35.1	35.5	35.8
107.5°	279.7	256.2	232.8	209.0	184.8	160.7	136.6	112.4
110°	355.1	349.1	343.2	327.3	301.3	275.5	249.6	223.8



TEST NUMBER: P332291-930

CATALOG NUMBER: S123RDIP-S560D1025U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	408.2	408.4	408.5	405.8	400.3	394.8	389.4	383.9
115°	470.8	472.5	474.3	475.6	476.3	477.0	477.8	478.5
117.5°	527.3	528.7	530.2	531.0	531.2	531.2	531.4	531.6
120°	564.4	565.8	567.3	568.0	568.0	568.0	568.0	568.0
122.5°	600.6	601.7	602.7	603.2	603.4	603.6	603.6	603.8
125°	651.8	652.1	652.5	652.8	653.2	653.5	654.0	654.3
127.5°	703.0	703.5	704.1	704.3	703.8	703.5	703.1	702.8
130°	733.9	734.6	735.3	735.5	735.2	734.7	734.4	734.0
132.5°	763.1	763.9	764.6	764.7	764.2	763.7	763.2	762.7
135°	807.6	808.1	808.6	808.6	808.1	807.6	807.0	806.5
137.5°	847.1	848.0	848.8	849.1	848.7	848.4	848.0	847.7
140°	872.2	872.9	873.7	873.8	873.4	873.1	872.8	872.4
142.5°	896.0	896.6	897.2	897.2	896.7	896.2	895.7	895.2
145°	929.3	929.6	930.0	930.2	930.2	930.2	930.2	930.2
147.5°	959.0	959.4	959.8	959.5	958.7	957.9	957.0	956.2
150°	977.3	977.6	978.0	977.9	977.4	976.8	976.2	975.8
152.5°	993.4	994.1	994.7	994.7	993.8	993.0	992.2	991.3
155°	1015.8	1016.7	1017.6	1017.5	1016.4	1015.4	1014.2	1013.2
157.5°	1035.2	1036.2	1037.4	1037.2	1035.8	1034.4	1033.0	1031.6
160°	1046.3	1047.3	1048.4	1048.3	1047.1	1045.8	1044.6	1043.3
162.5°	1056.3	1057.5	1058.7	1058.8	1057.7	1056.5	1055.5	1054.3
165°	1069.8	1071.2	1072.7	1072.8	1071.5	1070.2	1068.9	1067.7
167.5°	1080.2	1081.7	1083.0	1083.0	1081.7	1080.2	1078.7	1077.3
170°	1086.1	1087.5	1088.9	1088.9	1087.5	1086.1	1084.6	1083.1
172.5°	1090.0	1091.4	1092.8	1092.7	1091.2	1089.6	1088.0	1086.4
175°	1094.6	1095.9	1097.1	1097.1	1095.6	1094.2	1092.7	1091.3
177.5°	1096.3	1097.6	1098.7	1098.5	1097.1	1095.7	1094.2	1092.7
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4

(END OF REPORT)