

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332344-927

Luminaire Tested: **S123RDIP-S1000D805U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332344-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D805U927-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5439.8 lumens
Efficiency: N/A
Efficacy: 100.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332344-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332344-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58				
1	100	96	92	89	93	90	87	84	78	76	73	67	65	64	57	56	55	50				
2	92	85	79	74	85	79	74	70	69	65	62	60	57	54	51	49	47	43				
3	84	75	68	62	78	70	64	59	61	57	53	53	50	47	46	43	41	37				
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	41	38	36	32				
5	71	60	52	46	66	56	49	44	50	44	40	43	39	36	37	34	32	29				
6	66	54	46	40	61	51	44	39	45	39	35	39	35	32	34	31	28	25				
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	31	28	25	23				
8	57	45	37	32	53	42	35	31	38	32	28	33	29	25	29	25	23	20				
9	53	41	34	29	49	39	32	27	35	29	25	31	26	23	27	23	21	19				
10	50	38	31	26	46	36	29	25	32	27	23	28	24	21	25	21	19	17				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13555	13555	13555	13555
5°	16159	13613	11988	13613
10°	20176	13535	10831	13535
15°	23682	13397	9877	13397
20°	26431	13190	9065	13190
25°	26008	12973	8568	12973
30°	18695	12771	8054	12771
35°	12482	12510	7721	12510
40°	9197	12197	7378	12197
45°	7715	11645	7042	11645
50°	6807	10923	6571	10923
55°	5970	10098	5928	10098
60°	5315	9309	5431	9309
65°	4669	8458	5053	8458
70°	3666	7704	4614	7704
75°	3227	6729	4213	6729
80°	2808	5715	4147	5715
85°	2260	4594	4397	4594



TEST NUMBER: P332344-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.8	2.3
10°-20°	386.9	7.1
20°-30°	607.8	11.2
30°-40°	634.2	11.7
40°-50°	542.7	10.0
50°-60°	413.6	7.6
60°-70°	265.1	4.9
70°-80°	127.5	2.3
80°-90°	36.1	0.7
90°-100°	170.3	3.1
100°-110°	482.1	8.9
110°-120°	474.3	8.7
120°-130°	378.3	7.0
130°-140°	298.3	5.5
140°-150°	222.6	4.1
150°-160°	155.2	2.9
160°-170°	91.2	1.7
170°-180°	29.7	0.5
0°-30°	1118.6	20.6
0°-40°	1752.8	32.2
0°-60°	2709.1	49.8
0°-90°	3137.9	57.7
90°-120°	1126.7	20.7
90°-150°	2025.9	37.2
90°-180°	2302.0	42.3
0°-180°	5439.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1259	1259	1259	1259	1259	
5°	1496	1260	1110	1260	1496	154
15°	2125	1202	886	1202	2125	603
25°	2190	1092	721	1092	2190	941
35°	950	952	588	952	950	623
45°	507	765	463	765	507	398
55°	318	538	316	538	318	288
65°	183	332	198	332	183	180
75°	78	162	101	162	78	83
85°	18	37	36	37	18	21
90°	18	1	18	1	18	10
95°	72	21	72	21	72	129
105°	788	72	788	72	788	777
115°	958	127	958	127	958	931
125°	756	176	756	176	756	685
135°	612	207	612	207	612	475
145°	479	236	479	236	479	304
155°	397	268	397	268	397	185
165°	346	293	346	293	346	99
175°	312	305	312	305	312	30
180°	306	306	306	306	306	



TEST NUMBER: P332344-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1341.3	1343.0	1337.4	1336.6	1330.1	1328.3	1328.3	1319.3	1313.7	1306.4	1302.0
5°	1495.5	1504.1	1499.8	1490.1	1473.9	1470.1	1459.9	1443.8	1425.4	1402.7	1391.9
7.5°	1688.1	1699.8	1695.3	1680.3	1663.3	1649.6	1620.8	1593.9	1556.3	1523.3	1495.1
10°	1845.9	1833.5	1823.8	1809.3	1793.6	1768.2	1738.0	1696.5	1648.6	1610.8	1568.8
12.5°	1964.1	1962.0	1949.7	1934.7	1912.6	1888.6	1851.5	1800.9	1745.2	1690.7	1642.5
15°	2125.2	2128.4	2120.3	2104.7	2073.4	2030.8	1974.8	1953.8	1873.9	1814.7	1755.3
17.5°	2236.6	2236.0	2234.9	2213.3	2181.4	2151.0	2099.0	2043.8	1971.5	1887.9	1808.1
20°	2307.4	2302.0	2303.0	2278.8	2255.1	2220.0	2169.4	2089.1	2029.7	1933.2	1850.8
22.5°	2305.6	2304.5	2308.7	2300.3	2283.1	2256.3	2216.4	2148.6	2072.8	1975.5	1882.7
25°	2189.8	2185.6	2210.9	2217.9	2245.4	2250.2	2238.4	2201.2	2129.5	2029.2	1914.4
27.5°	1832.7	1830.3	1877.4	1936.3	2010.9	2068.9	2124.9	2152.0	2129.5	2057.7	1942.6
30°	1504.1	1554.8	1578.5	1663.7	1758.6	1871.8	1970.9	2065.3	2088.5	2057.2	1962.9
32.5°	1248.8	1293.0	1312.8	1385.9	1474.3	1606.9	1755.8	1889.4	1983.7	2007.6	1950.8
35°	949.9	950.5	995.7	1028.1	1110.0	1246.4	1390.9	1569.9	1747.8	1882.5	1896.6
37.5°	758.0	760.7	788.1	820.3	881.8	953.9	1081.1	1229.9	1435.4	1642.4	1763.6
40°	654.5	659.3	679.9	711.6	755.8	810.2	909.5	1049.6	1221.1	1451.3	1639.4
42.5°	588.0	596.0	606.5	631.0	658.4	709.3	789.6	897.9	1053.8	1271.5	1488.5
45°	506.8	511.0	519.2	530.4	555.2	590.9	644.8	717.6	846.9	1022.2	1239.4
47.5°	447.0	444.7	453.3	462.5	479.0	503.2	539.3	598.7	691.0	831.6	1015.9
50°	406.5	405.9	411.9	418.9	434.5	452.3	482.0	526.7	600.0	716.4	885.2
52.5°	368.5	370.6	374.8	383.5	394.8	409.2	435.8	468.0	531.0	631.5	772.2
55°	318.1	319.7	325.6	330.5	338.6	353.1	369.8	396.8	439.9	510.0	625.9
57.5°	275.4	274.6	280.4	281.5	290.7	302.5	315.4	336.4	367.7	419.8	497.8
60°	246.9	245.3	250.2	253.9	258.8	268.5	279.2	299.8	324.6	362.8	429.7
62.5°	221.0	220.3	223.9	227.6	231.6	240.4	249.5	265.2	284.9	317.1	370.2
65°	183.3	184.9	186.6	188.1	190.3	195.7	204.3	215.1	228.5	251.2	289.5
67.5°	144.0	145.7	146.2	149.6	154.2	157.6	162.8	172.4	181.8	200.9	222.7
70°	116.5	115.9	116.5	118.0	124.0	129.9	137.0	143.9	149.9	163.3	181.6
72.5°	100.1	99.1	100.5	100.8	103.7	105.4	109.8	116.4	124.0	133.2	146.3
75°	77.6	77.6	77.6	77.6	79.8	80.9	82.5	84.1	86.8	91.1	100.8
77.5°	57.4	57.4	58.2	58.8	59.2	59.8	60.8	62.4	63.4	65.7	69.9
80°	45.3	45.8	45.3	45.8	45.8	46.9	47.5	49.0	49.6	52.3	53.9
82.5°	34.1	33.7	34.1	34.6	34.6	35.7	35.8	37.0	37.1	38.5	40.1
85°	18.3	17.3	18.3	17.8	18.9	17.8	18.3	19.4	19.4	20.0	22.1
87.5°	7.9	8.9	7.9	8.2	8.3	8.6	8.4	8.2	9.0	8.7	8.8
90°	18.0	18.6	18.0	17.3	18.0	16.7	16.1	15.4	14.9	15.4	13.6
92.5°	29.9	31.0	30.3	32.2	33.4	36.5	41.4	52.1	71.9	95.2	104.8
95°	71.9	74.3	78.7	84.2	96.0	118.3	151.1	223.0	297.9	367.3	327.0
97.5°	195.6	200.9	217.6	245.5	291.2	365.3	445.2	555.8	609.0	569.2	416.7
100°	388.3	387.7	411.9	457.1	519.6	607.6	680.0	730.2	708.5	586.5	396.4
102.5°	569.7	583.9	604.1	639.9	688.6	744.3	786.6	788.1	713.5	554.3	366.6
105°	787.8	790.9	810.7	834.2	862.8	878.8	867.0	805.2	675.7	498.0	330.1
107.5°	913.4	919.1	925.8	933.7	933.2	911.2	856.9	756.4	609.6	448.1	306.8
110°	965.0	966.1	967.4	962.4	945.2	901.7	823.7	709.8	567.9	419.9	297.9



TEST NUMBER: P332344-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	975.3	975.1	970.4	955.1	923.3	867.6	780.1	663.7	531.8	401.1	292.9
115°	958.1	955.1	942.6	915.4	868.9	801.5	710.3	602.6	488.1	380.9	291.1
117.5°	903.4	899.1	881.3	850.1	801.7	733.2	651.4	558.4	461.7	369.0	292.2
120°	857.8	854.1	839.2	804.5	755.6	693.1	618.7	535.1	447.8	363.5	294.2
122.5°	815.2	810.5	794.1	762.9	719.5	661.3	592.5	516.8	436.4	360.1	297.6
125°	755.6	751.2	735.8	708.5	668.9	619.3	559.9	492.3	421.8	355.5	302.9
127.5°	706.5	702.6	688.6	665.3	630.0	584.9	531.2	471.1	408.9	353.3	308.8
130°	678.8	673.8	660.8	638.6	605.7	563.6	513.4	457.7	402.0	351.8	312.8
132.5°	651.6	648.1	636.6	614.3	583.4	543.3	496.6	445.3	395.5	351.3	315.8
135°	612.5	608.2	597.1	578.5	548.1	512.8	472.5	428.6	387.1	350.5	320.2
137.5°	571.3	568.5	559.0	540.2	514.7	484.1	449.4	413.4	379.8	349.2	323.2
140°	542.6	543.2	533.2	515.9	492.3	465.7	436.0	404.4	375.3	348.7	325.2
142.5°	515.8	516.4	507.5	492.1	472.1	448.9	423.1	396.0	371.4	347.7	326.6
145°	478.7	477.5	472.5	459.5	444.1	426.1	406.3	385.9	366.1	346.2	327.6
147.5°	448.3	447.8	443.1	434.3	422.6	409.8	393.8	377.6	360.8	343.9	327.6
150°	430.5	430.5	426.7	419.9	410.6	398.9	385.9	371.6	357.4	341.9	327.6
152.5°	415.6	415.6	413.4	407.0	399.7	389.9	378.4	366.1	353.4	339.4	326.1
155°	397.0	396.4	395.1	390.1	384.6	377.2	367.9	358.0	347.5	335.1	324.6
157.5°	380.0	380.2	379.1	375.4	370.6	364.8	357.6	349.3	340.8	331.2	322.4
160°	369.2	369.7	369.7	366.1	361.7	357.4	351.2	344.4	336.3	328.3	321.5
162.5°	359.3	359.8	359.8	356.6	353.8	349.9	344.2	338.4	331.8	325.3	319.5
165°	346.2	346.2	346.8	344.4	341.9	338.8	334.5	330.7	325.7	320.8	316.5
167.5°	333.8	333.8	334.5	332.7	331.6	329.4	326.9	324.0	320.0	316.4	313.5
170°	326.4	326.4	327.0	325.7	325.2	323.9	321.5	319.6	316.5	313.4	311.6
172.5°	319.5	320.0	321.1	319.8	319.7	318.9	317.0	315.6	313.0	310.9	310.1
175°	311.6	312.1	312.8	312.1	312.1	312.1	310.9	310.3	309.0	307.8	307.8
177.5°	307.0	307.0	307.9	307.4	307.9	307.9	307.4	307.0	306.4	305.9	306.4
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9



TEST NUMBER: P332344-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1300.3	1299.0	1293.0	1286.1	1277.0	1271.0	1266.2	1263.7	1255.9	1246.4	1239.9
5°	1380.6	1364.5	1347.3	1326.2	1306.8	1286.8	1274.5	1259.9	1242.1	1222.2	1208.2
7.5°	1466.7	1435.0	1400.8	1365.6	1330.7	1299.5	1271.8	1248.2	1219.9	1191.3	1171.2
10°	1532.7	1486.3	1438.4	1389.3	1344.5	1302.5	1270.1	1238.3	1204.4	1171.5	1146.7
12.5°	1592.6	1531.6	1476.3	1416.0	1358.8	1308.5	1261.9	1224.6	1183.7	1148.6	1120.4
15°	1668.5	1606.0	1539.1	1447.5	1371.5	1307.9	1251.3	1202.2	1152.6	1109.5	1082.0
17.5°	1739.5	1645.4	1555.5	1479.1	1380.3	1300.8	1231.8	1173.1	1118.6	1072.9	1039.1
20°	1768.8	1677.7	1580.1	1482.6	1385.5	1296.6	1216.2	1151.5	1095.0	1043.1	1011.9
22.5°	1786.5	1683.3	1580.6	1475.7	1372.5	1280.2	1200.7	1129.6	1068.2	1019.0	980.4
25°	1807.0	1684.2	1571.0	1467.4	1362.3	1262.0	1167.7	1092.3	1026.0	973.6	932.6
27.5°	1820.7	1676.1	1542.3	1427.2	1320.6	1220.8	1134.2	1054.2	987.0	931.7	887.7
30°	1823.3	1669.6	1520.3	1395.7	1287.4	1195.7	1104.1	1027.5	956.4	897.6	856.7
32.5°	1826.7	1653.7	1490.5	1358.2	1247.3	1156.5	1073.5	1000.4	927.5	869.6	827.8
35°	1812.5	1644.8	1445.3	1293.3	1182.3	1094.4	1019.5	952.0	880.4	824.3	781.7
37.5°	1751.2	1609.8	1398.5	1220.2	1104.1	1022.7	961.6	902.9	837.1	776.7	736.5
40°	1689.6	1575.3	1362.3	1175.8	1054.5	970.9	915.9	868.0	804.4	747.7	704.6
42.5°	1597.7	1528.3	1327.9	1129.2	998.4	917.9	871.5	826.6	770.7	713.2	672.7
45°	1429.2	1438.4	1257.2	1055.0	920.8	840.0	796.2	765.0	715.4	668.0	626.5
47.5°	1217.8	1303.5	1174.3	976.0	838.9	763.0	724.8	697.6	664.2	617.6	579.7
50°	1079.8	1202.2	1107.9	923.0	787.7	712.2	674.4	652.3	623.2	586.5	550.4
52.5°	952.6	1084.0	1027.6	863.9	732.0	663.0	626.1	607.9	584.8	550.3	517.6
55°	776.8	910.0	897.1	774.7	648.6	586.5	558.5	538.1	522.4	496.5	470.6
57.5°	628.4	754.6	761.3	675.5	575.0	513.7	489.6	474.2	464.0	444.4	420.5
60°	534.8	650.7	673.4	608.6	522.4	468.5	444.7	432.4	424.3	408.6	390.3
62.5°	457.2	555.8	581.5	534.9	471.9	421.4	402.9	390.9	385.5	372.0	355.8
65°	349.9	431.8	456.6	430.7	397.8	357.4	342.3	332.1	327.3	319.7	307.8
67.5°	263.1	322.8	350.0	331.8	319.9	294.4	284.8	279.2	275.0	269.7	259.8
70°	211.4	255.6	283.6	278.7	269.0	255.6	248.5	244.8	240.4	236.1	227.5
72.5°	169.9	200.3	226.6	229.1	221.2	218.5	212.3	210.7	208.1	203.0	198.2
75°	112.6	133.7	152.0	159.1	162.2	164.9	162.2	161.8	161.2	156.9	154.2
77.5°	73.8	85.2	96.7	108.7	113.8	117.4	118.3	120.3	118.8	116.5	115.3
80°	56.6	59.3	67.4	77.6	85.7	89.0	91.1	92.2	91.7	91.1	89.0
82.5°	41.1	43.3	47.1	54.3	61.2	66.5	67.8	67.6	68.8	69.1	67.4
85°	22.1	22.7	23.7	24.8	28.6	34.5	36.1	37.2	38.3	38.3	35.0
87.5°	9.3	8.5	9.0	8.7	9.7	9.8	12.1	14.0	14.7	13.2	13.6
90°	11.8	9.9	8.1	6.8	5.5	3.7	2.5	1.3	2.5	3.7	5.5
92.5°	78.7	52.0	35.8	26.6	21.5	16.6	11.4	7.7	11.4	16.6	21.5
95°	225.5	133.2	80.5	56.3	40.2	29.7	22.9	21.1	22.9	29.7	40.2
97.5°	247.4	143.3	93.0	66.9	51.0	41.9	36.5	35.9	36.5	41.9	51.0
100°	233.5	141.8	98.5	74.3	59.5	50.8	46.4	45.9	46.4	50.8	59.5
102.5°	221.6	143.8	104.9	82.8	69.4	61.2	57.4	56.2	57.4	61.2	69.4
105°	213.0	149.2	115.8	96.6	84.8	77.4	73.7	71.9	73.7	77.4	84.8
107.5°	212.5	159.4	130.1	112.3	101.2	93.9	90.3	88.4	90.3	93.9	101.2
110°	214.9	167.9	140.0	122.6	112.1	105.3	102.2	100.4	102.2	105.3	112.1



TEST NUMBER: P332344-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	219.8	176.3	150.4	133.6	123.0	116.2	113.1	111.2	113.1	116.2	123.0
115°	227.9	190.1	166.6	149.9	139.3	133.2	129.4	127.0	129.4	133.2	139.3
117.5°	238.6	204.9	181.6	166.1	154.3	148.6	145.5	142.7	145.5	148.6	154.3
120°	246.5	214.3	192.0	176.5	164.8	158.5	155.4	153.6	155.4	158.5	164.8
122.5°	253.9	224.2	202.4	185.9	174.7	167.9	164.9	163.0	164.9	167.9	174.7
125°	265.7	238.4	216.7	200.0	188.3	181.5	177.8	176.5	177.8	181.5	188.3
127.5°	275.4	250.8	229.9	213.2	200.2	193.2	188.6	186.8	188.6	193.2	200.2
130°	281.8	258.3	237.8	221.1	208.1	200.7	195.1	193.2	195.1	200.7	208.1
132.5°	287.7	264.7	244.8	228.5	215.6	206.6	200.6	198.2	200.6	206.6	215.6
135°	295.4	274.3	255.2	238.4	225.5	216.2	209.4	206.8	209.4	216.2	225.5
137.5°	301.1	281.1	262.6	247.1	234.2	224.3	217.6	215.0	217.6	224.3	234.2
140°	304.1	285.5	267.5	252.1	239.7	229.8	223.6	220.5	223.6	229.8	239.7
142.5°	307.0	289.0	271.5	257.1	244.6	235.8	229.0	226.4	229.0	235.8	244.6
145°	310.3	293.6	277.5	263.2	252.7	243.4	237.8	236.0	237.8	243.4	252.7
147.5°	312.3	297.3	282.6	270.4	260.2	252.2	246.8	245.7	246.8	252.2	260.2
150°	312.8	299.8	285.5	274.3	265.7	257.6	252.7	252.1	252.7	257.6	265.7
152.5°	313.8	301.3	289.0	278.3	270.7	263.6	258.6	258.5	258.6	263.6	270.7
155°	314.0	304.1	293.6	284.9	278.1	271.9	268.2	268.2	268.2	271.9	278.1
157.5°	314.7	305.7	297.3	290.6	284.8	279.3	276.3	275.8	276.3	279.3	284.8
160°	314.7	307.2	299.8	293.6	289.2	284.3	281.8	281.8	281.8	284.3	289.2
162.5°	314.1	307.7	301.3	296.0	292.2	288.3	286.3	286.3	286.3	288.3	292.2
165°	312.8	308.4	303.5	299.1	296.7	293.6	292.3	292.9	292.3	293.6	296.7
167.5°	311.8	308.3	304.8	302.0	300.2	297.9	297.3	298.0	297.3	297.9	300.2
170°	310.3	307.8	304.8	303.5	302.2	300.4	299.8	301.0	299.8	300.4	302.2
172.5°	309.8	307.8	305.2	304.4	303.7	302.4	302.2	303.0	302.2	302.4	303.7
175°	308.4	307.2	305.9	305.3	305.3	304.1	304.8	305.3	304.8	304.1	305.3
177.5°	307.4	306.4	305.9	305.9	305.9	305.5	305.9	306.4	305.9	305.5	305.9
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9



TEST NUMBER: P332344-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1237.8	1232.2	1228.3	1219.6	1214.1	1208.0	1202.0	1205.9	1205.5	1205.0	1205.0
5°	1196.3	1183.8	1172.6	1158.0	1148.8	1137.5	1128.9	1127.8	1130.0	1122.4	1118.1
7.5°	1155.1	1138.1	1122.1	1106.0	1089.0	1075.4	1066.9	1062.9	1057.4	1052.7	1047.9
10°	1126.2	1106.3	1090.6	1070.6	1052.3	1036.2	1026.0	1018.9	1015.1	1011.4	1004.3
12.5°	1096.5	1076.9	1057.0	1034.4	1017.0	998.2	990.5	982.7	975.5	971.2	961.6
15°	1052.9	1027.5	1006.5	982.8	963.4	945.1	934.3	918.6	916.5	911.1	901.4
17.5°	1009.2	981.7	952.7	935.2	913.2	894.1	877.7	872.5	857.1	851.3	842.8
20°	974.7	949.4	927.2	904.1	872.3	854.4	841.5	834.6	822.1	814.6	809.2
22.5°	944.9	919.2	893.7	866.6	840.3	820.4	811.0	800.0	793.2	782.7	776.8
25°	902.5	874.4	843.7	814.6	795.7	780.6	765.6	755.8	746.2	741.2	730.5
27.5°	853.1	823.8	795.0	772.9	749.8	734.9	721.2	712.6	700.9	692.8	686.8
30°	825.9	791.4	766.6	746.6	717.0	703.0	692.8	682.0	673.4	664.7	658.8
32.5°	794.4	763.0	739.4	714.8	692.0	676.7	663.5	653.9	646.6	638.4	632.5
35°	745.0	718.7	694.3	669.6	652.8	637.2	621.6	613.5	606.5	599.0	593.6
37.5°	700.4	675.7	652.7	629.2	608.4	595.7	583.1	576.9	567.4	562.4	556.9
40°	672.8	648.6	623.8	601.1	579.6	569.8	558.5	549.4	540.7	536.9	531.0
42.5°	642.6	618.4	597.5	573.1	555.4	542.2	531.8	521.7	515.3	509.8	506.4
45°	597.9	576.3	555.8	531.6	514.8	503.5	491.6	482.5	476.6	472.8	466.8
47.5°	554.4	532.8	512.1	490.9	474.8	461.8	450.0	443.5	435.7	431.1	427.1
50°	522.9	503.5	481.4	462.0	445.8	432.9	423.2	415.1	408.1	402.2	399.5
52.5°	494.0	473.3	454.2	436.2	419.1	404.4	395.6	387.1	381.8	375.0	371.9
55°	446.4	426.4	410.3	392.4	375.7	363.4	352.6	345.0	339.6	332.1	327.8
57.5°	401.6	383.7	364.4	349.0	331.8	321.3	312.4	302.1	295.6	289.6	285.4
60°	371.5	350.9	334.2	319.7	304.6	291.1	283.0	275.0	267.9	262.0	258.3
62.5°	339.9	322.1	306.2	290.3	276.6	264.8	255.4	248.7	242.5	238.7	235.0
65°	291.7	277.7	261.5	248.5	235.6	227.0	219.4	213.5	209.1	206.4	203.3
67.5°	247.2	233.6	219.5	206.8	198.2	191.6	186.6	181.6	179.4	175.9	173.8
70°	218.3	204.3	191.9	182.2	173.6	168.7	165.5	161.8	159.5	155.3	153.1
72.5°	186.9	176.7	167.8	159.8	152.9	148.5	144.3	139.7	136.3	131.5	129.4
75°	147.2	138.0	131.0	125.6	121.3	115.3	109.4	104.6	103.0	101.3	100.8
77.5°	109.0	103.2	98.2	93.6	88.2	83.9	82.6	81.5	81.2	80.3	80.3
80°	85.7	80.3	76.5	71.1	67.9	67.9	67.9	66.9	67.4	67.4	67.4
82.5°	63.7	58.8	56.7	54.7	54.1	54.6	54.6	54.7	54.4	55.3	54.9
85°	32.9	33.4	34.5	34.0	34.5	34.5	35.6	35.0	35.6	34.5	35.6
87.5°	13.5	15.0	15.8	16.6	17.4	17.3	17.7	17.7	18.3	18.5	18.7
90°	6.8	8.1	9.9	11.8	13.6	15.4	14.9	15.4	16.1	16.7	18.0
92.5°	26.6	35.8	52.0	78.7	104.8	95.2	71.9	52.1	41.4	36.5	33.4
95°	56.3	80.5	133.2	225.5	327.0	367.3	297.9	223.0	151.1	118.3	96.0
97.5°	66.9	93.0	143.3	247.4	416.7	569.2	609.0	555.8	445.2	365.3	291.2
100°	74.3	98.5	141.8	233.5	396.4	586.5	708.5	730.2	680.0	607.6	519.6
102.5°	82.8	104.9	143.8	221.6	366.6	554.3	713.5	788.1	786.6	744.3	688.6
105°	96.6	115.8	149.2	213.0	330.1	498.0	675.7	805.2	867.0	878.8	862.8
107.5°	112.3	130.1	159.4	212.5	306.8	448.1	609.6	756.4	856.9	911.2	933.2
110°	122.6	140.0	167.9	214.9	297.9	419.9	567.9	709.8	823.7	901.7	945.2



TEST NUMBER: P332344-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	133.6	150.4	176.3	219.8	292.9	401.1	531.8	663.7	780.1	867.6	923.3
115°	149.9	166.6	190.1	227.9	291.1	380.9	488.1	602.6	710.3	801.5	868.9
117.5°	166.1	181.6	204.9	238.6	292.2	369.0	461.7	558.4	651.4	733.2	801.7
120°	176.5	192.0	214.3	246.5	294.2	363.5	447.8	535.1	618.7	693.1	755.6
122.5°	185.9	202.4	224.2	253.9	297.6	360.1	436.4	516.8	592.5	661.3	719.5
125°	200.0	216.7	238.4	265.7	302.9	355.5	421.8	492.3	559.9	619.3	668.9
127.5°	213.2	229.9	250.8	275.4	308.8	353.3	408.9	471.1	531.2	584.9	630.0
130°	221.1	237.8	258.3	281.8	312.8	351.8	402.0	457.7	513.4	563.6	605.7
132.5°	228.5	244.8	264.7	287.7	315.8	351.3	395.5	445.3	496.6	543.3	583.4
135°	238.4	255.2	274.3	295.4	320.2	350.5	387.1	428.6	472.5	512.8	548.1
137.5°	247.1	262.6	281.1	301.1	323.2	349.2	379.8	413.4	449.4	484.1	514.7
140°	252.1	267.5	285.5	304.1	325.2	348.7	375.3	404.4	436.0	465.7	492.3
142.5°	257.1	271.5	289.0	307.0	326.6	347.7	371.4	396.0	423.1	448.9	472.1
145°	263.2	277.5	293.6	310.3	327.6	346.2	366.1	385.9	406.3	426.1	444.1
147.5°	270.4	282.6	297.3	312.3	327.6	343.9	360.8	377.6	393.8	409.8	422.6
150°	274.3	285.5	299.8	312.8	327.6	341.9	357.4	371.6	385.9	398.9	410.6
152.5°	278.3	289.0	301.3	313.8	326.1	339.4	353.4	366.1	378.4	389.9	399.7
155°	284.9	293.6	304.1	314.0	324.6	335.1	347.5	358.0	367.9	377.2	384.6
157.5°	290.6	297.3	305.7	314.7	322.4	331.2	340.8	349.3	357.6	364.8	370.6
160°	293.6	299.8	307.2	314.7	321.5	328.3	336.3	344.4	351.2	357.4	361.7
162.5°	296.0	301.3	307.7	314.1	319.5	325.3	331.8	338.4	344.2	349.9	353.8
165°	299.1	303.5	308.4	312.8	316.5	320.8	325.7	330.7	334.5	338.8	341.9
167.5°	302.0	304.8	308.3	311.8	313.5	316.4	320.0	324.0	326.9	329.4	331.6
170°	303.5	304.8	307.8	310.3	311.6	313.4	316.5	319.6	321.5	323.9	325.2
172.5°	304.4	305.2	307.8	309.8	310.1	310.9	313.0	315.6	317.0	318.9	319.7
175°	305.3	305.9	307.2	308.4	307.8	307.8	309.0	310.3	310.9	312.1	312.1
177.5°	305.9	305.9	306.4	307.4	306.4	305.9	306.4	307.0	307.4	307.9	307.9
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9



TEST NUMBER: P332344-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1199.8	1199.4	1199.8	1198.1	1199.8	1199.4	1199.8	1205.0	1205.0	1205.5	1205.9
5°	1116.5	1115.9	1114.4	1109.5	1114.4	1115.9	1116.5	1118.1	1122.4	1130.0	1127.8
7.5°	1043.7	1043.0	1038.2	1038.3	1038.2	1043.0	1043.7	1047.9	1052.7	1057.4	1062.9
10°	1000.6	1001.1	994.7	990.9	994.7	1001.1	1000.6	1004.3	1011.4	1015.1	1018.9
12.5°	958.8	956.2	951.1	946.9	951.1	956.2	958.8	961.6	971.2	975.5	982.7
15°	903.6	898.2	885.2	886.3	885.2	898.2	903.6	901.4	911.1	916.5	918.6
17.5°	838.5	834.6	834.3	826.8	834.3	834.6	838.5	842.8	851.3	857.1	872.5
20°	800.6	797.9	798.9	791.4	798.9	797.9	800.6	809.2	814.6	822.1	834.6
22.5°	770.8	768.1	763.6	761.2	763.6	768.1	770.8	776.8	782.7	793.2	800.0
25°	727.2	722.9	718.7	721.4	718.7	722.9	727.2	730.5	741.2	746.2	755.8
27.5°	683.7	680.5	676.1	675.6	676.1	680.5	683.7	686.8	692.8	700.9	712.6
30°	656.1	652.8	650.7	648.0	650.7	652.8	656.1	658.8	664.7	673.4	682.0
32.5°	628.0	627.4	623.5	623.0	623.5	627.4	628.0	632.5	638.4	646.6	653.9
35°	591.4	588.2	587.1	587.6	587.1	588.2	591.4	593.6	599.0	606.5	613.5
37.5°	556.6	552.2	550.3	548.3	550.3	552.2	556.6	556.9	562.4	567.4	576.9
40°	531.6	527.3	526.2	525.1	526.2	527.3	531.6	531.0	536.9	540.7	549.4
42.5°	503.5	501.8	501.1	499.2	501.1	501.8	503.5	506.4	509.8	515.3	521.7
45°	465.2	464.7	461.4	462.6	461.4	464.7	465.2	466.8	472.8	476.6	482.5
47.5°	424.9	422.6	420.3	421.8	420.3	422.6	424.9	427.1	431.1	435.7	443.5
50°	397.4	396.2	391.4	392.4	391.4	396.2	397.4	399.5	402.2	408.1	415.1
52.5°	369.7	365.6	363.8	363.1	363.8	365.6	369.7	371.9	375.0	381.8	387.1
55°	324.0	319.2	317.0	315.9	317.0	319.2	324.0	327.8	332.1	339.6	345.0
57.5°	279.2	277.8	276.2	277.3	276.2	277.8	279.2	285.4	289.6	295.6	302.1
60°	252.9	252.9	252.9	252.3	252.9	252.9	252.9	258.3	262.0	267.9	275.0
62.5°	232.6	231.2	230.8	231.6	230.8	231.2	232.6	235.0	238.7	242.5	248.7
65°	201.6	201.1	198.9	198.4	198.9	201.1	201.6	203.3	206.4	209.1	213.5
67.5°	172.4	170.5	169.8	169.1	169.8	170.5	172.4	173.8	175.9	179.4	181.6
70°	150.4	149.3	146.1	146.6	146.1	149.3	150.4	153.1	155.3	159.5	161.8
72.5°	126.7	125.6	124.9	124.2	124.9	125.6	126.7	129.4	131.5	136.3	139.7
75°	100.3	99.7	99.2	101.3	99.2	99.7	100.3	100.8	101.3	103.0	104.6
77.5°	80.3	80.3	80.6	79.8	80.6	80.3	80.3	80.3	80.3	81.2	81.5
80°	67.4	67.4	66.9	66.9	66.9	67.4	67.4	67.4	67.4	67.4	66.9
82.5°	54.0	54.4	54.7	53.9	54.7	54.4	54.0	54.9	55.3	54.4	54.7
85°	35.6	35.0	36.1	35.6	36.1	35.0	35.6	35.6	34.5	35.6	35.0
87.5°	19.4	18.7	18.8	19.1	18.8	18.7	19.4	18.7	18.5	18.3	17.7
90°	17.3	18.0	18.6	18.0	18.6	18.0	17.3	18.0	16.7	16.1	15.4
92.5°	32.2	30.3	31.0	29.9	31.0	30.3	32.2	33.4	36.5	41.4	52.1
95°	84.2	78.7	74.3	71.9	74.3	78.7	84.2	96.0	118.3	151.1	223.0
97.5°	245.5	217.6	200.9	195.6	200.9	217.6	245.5	291.2	365.3	445.2	555.8
100°	457.1	411.9	387.7	388.3	387.7	411.9	457.1	519.6	607.6	680.0	730.2
102.5°	639.9	604.1	583.9	569.7	583.9	604.1	639.9	688.6	744.3	786.6	788.1
105°	834.2	810.7	790.9	787.8	790.9	810.7	834.2	862.8	878.8	867.0	805.2
107.5°	933.7	925.8	919.1	913.4	919.1	925.8	933.7	933.2	911.2	856.9	756.4
110°	962.4	967.4	966.1	965.0	966.1	967.4	962.4	945.2	901.7	823.7	709.8



TEST NUMBER: P332344-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	955.1	970.4	975.1	975.3	975.1	970.4	955.1	923.3	867.6	780.1	663.7
115°	915.4	942.6	955.1	958.1	955.1	942.6	915.4	868.9	801.5	710.3	602.6
117.5°	850.1	881.3	899.1	903.4	899.1	881.3	850.1	801.7	733.2	651.4	558.4
120°	804.5	839.2	854.1	857.8	854.1	839.2	804.5	755.6	693.1	618.7	535.1
122.5°	762.9	794.1	810.5	815.2	810.5	794.1	762.9	719.5	661.3	592.5	516.8
125°	708.5	735.8	751.2	755.6	751.2	735.8	708.5	668.9	619.3	559.9	492.3
127.5°	665.3	688.6	702.6	706.5	702.6	688.6	665.3	630.0	584.9	531.2	471.1
130°	638.6	660.8	673.8	678.8	673.8	660.8	638.6	605.7	563.6	513.4	457.7
132.5°	614.3	636.6	648.1	651.6	648.1	636.6	614.3	583.4	543.3	496.6	445.3
135°	578.5	597.1	608.2	612.5	608.2	597.1	578.5	548.1	512.8	472.5	428.6
137.5°	540.2	559.0	568.5	571.3	568.5	559.0	540.2	514.7	484.1	449.4	413.4
140°	515.9	533.2	543.2	542.6	543.2	533.2	515.9	492.3	465.7	436.0	404.4
142.5°	492.1	507.5	516.4	515.8	516.4	507.5	492.1	472.1	448.9	423.1	396.0
145°	459.5	472.5	477.5	478.7	477.5	472.5	459.5	444.1	426.1	406.3	385.9
147.5°	434.3	443.1	447.8	448.3	447.8	443.1	434.3	422.6	409.8	393.8	377.6
150°	419.9	426.7	430.5	430.5	430.5	426.7	419.9	410.6	398.9	385.9	371.6
152.5°	407.0	413.4	415.6	415.6	415.6	413.4	407.0	399.7	389.9	378.4	366.1
155°	390.1	395.1	396.4	397.0	396.4	395.1	390.1	384.6	377.2	367.9	358.0
157.5°	375.4	379.1	380.2	380.0	380.2	379.1	375.4	370.6	364.8	357.6	349.3
160°	366.1	369.7	369.7	369.2	369.7	369.7	366.1	361.7	357.4	351.2	344.4
162.5°	356.6	359.8	359.8	359.3	359.8	359.8	356.6	353.8	349.9	344.2	338.4
165°	344.4	346.8	346.2	346.2	346.2	346.8	344.4	341.9	338.8	334.5	330.7
167.5°	332.7	334.5	333.8	333.8	333.8	334.5	332.7	331.6	329.4	326.9	324.0
170°	325.7	327.0	326.4	326.4	326.4	327.0	325.7	325.2	323.9	321.5	319.6
172.5°	319.8	321.1	320.0	319.5	320.0	321.1	319.8	319.7	318.9	317.0	315.6
175°	312.1	312.8	312.1	311.6	312.1	312.8	312.1	312.1	312.1	310.9	310.3
177.5°	307.4	307.9	307.0	307.0	307.0	307.9	307.4	307.9	307.9	307.4	307.0
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9



TEST NUMBER: P332344-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1202.0	1208.0	1214.1	1219.6	1228.3	1232.2	1237.8	1239.9	1246.4	1255.9	1263.7
5°	1128.9	1137.5	1148.8	1158.0	1172.6	1183.8	1196.3	1208.2	1222.2	1242.1	1259.9
7.5°	1066.9	1075.4	1089.0	1106.0	1122.1	1138.1	1155.1	1171.2	1191.3	1219.9	1248.2
10°	1026.0	1036.2	1052.3	1070.6	1090.6	1106.3	1126.2	1146.7	1171.5	1204.4	1238.3
12.5°	990.5	998.2	1017.0	1034.4	1057.0	1076.9	1096.5	1120.4	1148.6	1183.7	1224.6
15°	934.3	945.1	963.4	982.8	1006.5	1027.5	1052.9	1082.0	1109.5	1152.6	1202.2
17.5°	877.7	894.1	913.2	935.2	952.7	981.7	1009.2	1039.1	1072.9	1118.6	1173.1
20°	841.5	854.4	872.3	904.1	927.2	949.4	974.7	1011.9	1043.1	1095.0	1151.5
22.5°	811.0	820.4	840.3	866.6	893.7	919.2	944.9	980.4	1019.0	1068.2	1129.6
25°	765.6	780.6	795.7	814.6	843.7	874.4	902.5	932.6	973.6	1026.0	1092.3
27.5°	721.2	734.9	749.8	772.9	795.0	823.8	853.1	887.7	931.7	987.0	1054.2
30°	692.8	703.0	717.0	746.6	766.6	791.4	825.9	856.7	897.6	956.4	1027.5
32.5°	663.5	676.7	692.0	714.8	739.4	763.0	794.4	827.8	869.6	927.5	1000.4
35°	621.6	637.2	652.8	669.6	694.3	718.7	745.0	781.7	824.3	880.4	952.0
37.5°	583.1	595.7	608.4	629.2	652.7	675.7	700.4	736.5	776.7	837.1	902.9
40°	558.5	569.8	579.6	601.1	623.8	648.6	672.8	704.6	747.7	804.4	868.0
42.5°	531.8	542.2	555.4	573.1	597.5	618.4	642.6	672.7	713.2	770.7	826.6
45°	491.6	503.5	514.8	531.6	555.8	576.3	597.9	626.5	668.0	715.4	765.0
47.5°	450.0	461.8	474.8	490.9	512.1	532.8	554.4	579.7	617.6	664.2	697.6
50°	423.2	432.9	445.8	462.0	481.4	503.5	522.9	550.4	586.5	623.2	652.3
52.5°	395.6	404.4	419.1	436.2	454.2	473.3	494.0	517.6	550.3	584.8	607.9
55°	352.6	363.4	375.7	392.4	410.3	426.4	446.4	470.6	496.5	522.4	538.1
57.5°	312.4	321.3	331.8	349.0	364.4	383.7	401.6	420.5	444.4	464.0	474.2
60°	283.0	291.1	304.6	319.7	334.2	350.9	371.5	390.3	408.6	424.3	432.4
62.5°	255.4	264.8	276.6	290.3	306.2	322.1	339.9	355.8	372.0	385.5	390.9
65°	219.4	227.0	235.6	248.5	261.5	277.7	291.7	307.8	319.7	327.3	332.1
67.5°	186.6	191.6	198.2	206.8	219.5	233.6	247.2	259.8	269.7	275.0	279.2
70°	165.5	168.7	173.6	182.2	191.9	204.3	218.3	227.5	236.1	240.4	244.8
72.5°	144.3	148.5	152.9	159.8	167.8	176.7	186.9	198.2	203.0	208.1	210.7
75°	109.4	115.3	121.3	125.6	131.0	138.0	147.2	154.2	156.9	161.2	161.8
77.5°	82.6	83.9	88.2	93.6	98.2	103.2	109.0	115.3	116.5	118.8	120.3
80°	67.9	67.9	67.9	71.1	76.5	80.3	85.7	89.0	91.1	91.7	92.2
82.5°	54.6	54.6	54.1	54.7	56.7	58.8	63.7	67.4	69.1	68.8	67.6
85°	35.6	34.5	34.5	34.0	34.5	33.4	32.9	35.0	38.3	38.3	37.2
87.5°	17.7	17.3	17.4	16.6	15.8	15.0	13.5	13.6	13.2	14.7	14.0
90°	14.9	15.4	13.6	11.8	9.9	8.1	6.8	5.5	3.7	2.5	1.3
92.5°	71.9	95.2	104.8	78.7	52.0	35.8	26.6	21.5	16.6	11.4	7.7
95°	297.9	367.3	327.0	225.5	133.2	80.5	56.3	40.2	29.7	22.9	21.1
97.5°	609.0	569.2	416.7	247.4	143.3	93.0	66.9	51.0	41.9	36.5	35.9
100°	708.5	586.5	396.4	233.5	141.8	98.5	74.3	59.5	50.8	46.4	45.9
102.5°	713.5	554.3	366.6	221.6	143.8	104.9	82.8	69.4	61.2	57.4	56.2
105°	675.7	498.0	330.1	213.0	149.2	115.8	96.6	84.8	77.4	73.7	71.9
107.5°	609.6	448.1	306.8	212.5	159.4	130.1	112.3	101.2	93.9	90.3	88.4
110°	567.9	419.9	297.9	214.9	167.9	140.0	122.6	112.1	105.3	102.2	100.4



TEST NUMBER: P332344-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	531.8	401.1	292.9	219.8	176.3	150.4	133.6	123.0	116.2	113.1	111.2
115°	488.1	380.9	291.1	227.9	190.1	166.6	149.9	139.3	133.2	129.4	127.0
117.5°	461.7	369.0	292.2	238.6	204.9	181.6	166.1	154.3	148.6	145.5	142.7
120°	447.8	363.5	294.2	246.5	214.3	192.0	176.5	164.8	158.5	155.4	153.6
122.5°	436.4	360.1	297.6	253.9	224.2	202.4	185.9	174.7	167.9	164.9	163.0
125°	421.8	355.5	302.9	265.7	238.4	216.7	200.0	188.3	181.5	177.8	176.5
127.5°	408.9	353.3	308.8	275.4	250.8	229.9	213.2	200.2	193.2	188.6	186.8
130°	402.0	351.8	312.8	281.8	258.3	237.8	221.1	208.1	200.7	195.1	193.2
132.5°	395.5	351.3	315.8	287.7	264.7	244.8	228.5	215.6	206.6	200.6	198.2
135°	387.1	350.5	320.2	295.4	274.3	255.2	238.4	225.5	216.2	209.4	206.8
137.5°	379.8	349.2	323.2	301.1	281.1	262.6	247.1	234.2	224.3	217.6	215.0
140°	375.3	348.7	325.2	304.1	285.5	267.5	252.1	239.7	229.8	223.6	220.5
142.5°	371.4	347.7	326.6	307.0	289.0	271.5	257.1	244.6	235.8	229.0	226.4
145°	366.1	346.2	327.6	310.3	293.6	277.5	263.2	252.7	243.4	237.8	236.0
147.5°	360.8	343.9	327.6	312.3	297.3	282.6	270.4	260.2	252.2	246.8	245.7
150°	357.4	341.9	327.6	312.8	299.8	285.5	274.3	265.7	257.6	252.7	252.1
152.5°	353.4	339.4	326.1	313.8	301.3	289.0	278.3	270.7	263.6	258.6	258.5
155°	347.5	335.1	324.6	314.0	304.1	293.6	284.9	278.1	271.9	268.2	268.2
157.5°	340.8	331.2	322.4	314.7	305.7	297.3	290.6	284.8	279.3	276.3	275.8
160°	336.3	328.3	321.5	314.7	307.2	299.8	293.6	289.2	284.3	281.8	281.8
162.5°	331.8	325.3	319.5	314.1	307.7	301.3	296.0	292.2	288.3	286.3	286.3
165°	325.7	320.8	316.5	312.8	308.4	303.5	299.1	296.7	293.6	292.3	292.9
167.5°	320.0	316.4	313.5	311.8	308.3	304.8	302.0	300.2	297.9	297.3	298.0
170°	316.5	313.4	311.6	310.3	307.8	304.8	303.5	302.2	300.4	299.8	301.0
172.5°	313.0	310.9	310.1	309.8	307.8	305.2	304.4	303.7	302.4	302.2	303.0
175°	309.0	307.8	307.8	308.4	307.2	305.9	305.3	305.3	304.1	304.8	305.3
177.5°	306.4	305.9	306.4	307.4	306.4	305.9	305.9	305.9	305.5	305.9	306.4
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9



TEST NUMBER: P332344-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1266.2	1271.0	1277.0	1286.1	1293.0	1299.0	1300.3	1302.0	1306.4	1313.7	1319.3
5°	1274.5	1286.8	1306.8	1326.2	1347.3	1364.5	1380.6	1391.9	1402.7	1425.4	1443.8
7.5°	1271.8	1299.5	1330.7	1365.6	1400.8	1435.0	1466.7	1495.1	1523.3	1556.3	1593.9
10°	1270.1	1302.5	1344.5	1389.3	1438.4	1486.3	1532.7	1568.8	1610.8	1648.6	1696.5
12.5°	1261.9	1308.5	1358.8	1416.0	1476.3	1531.6	1592.6	1642.5	1690.7	1745.2	1800.9
15°	1251.3	1307.9	1371.5	1447.5	1539.1	1606.0	1668.5	1755.3	1814.7	1873.9	1953.8
17.5°	1231.8	1300.8	1380.3	1479.1	1555.5	1645.4	1739.5	1808.1	1887.9	1971.5	2043.8
20°	1216.2	1296.6	1385.5	1482.6	1580.1	1677.7	1768.8	1850.8	1933.2	2029.7	2089.1
22.5°	1200.7	1280.2	1372.5	1475.7	1580.6	1683.3	1786.5	1882.7	1975.5	2072.8	2148.6
25°	1167.7	1262.0	1362.3	1467.4	1571.0	1684.2	1807.0	1914.4	2029.2	2129.5	2201.2
27.5°	1134.2	1220.8	1320.6	1427.2	1542.3	1676.1	1820.7	1942.6	2057.7	2129.5	2152.0
30°	1104.1	1195.7	1287.4	1395.7	1520.3	1669.6	1823.3	1962.9	2057.2	2088.5	2065.3
32.5°	1073.5	1156.5	1247.3	1358.2	1490.5	1653.7	1826.7	1950.8	2007.6	1983.7	1889.4
35°	1019.5	1094.4	1182.3	1293.3	1445.3	1644.8	1812.5	1896.6	1882.5	1747.8	1569.9
37.5°	961.6	1022.7	1104.1	1220.2	1398.5	1609.8	1751.2	1763.6	1642.4	1435.4	1229.9
40°	915.9	970.9	1054.5	1175.8	1362.3	1575.3	1689.6	1639.4	1451.3	1221.1	1049.6
42.5°	871.5	917.9	998.4	1129.2	1327.9	1528.3	1597.7	1488.5	1271.5	1053.8	897.9
45°	796.2	840.0	920.8	1055.0	1257.2	1438.4	1429.2	1239.4	1022.2	846.9	717.6
47.5°	724.8	763.0	838.9	976.0	1174.3	1303.5	1217.8	1015.9	831.6	691.0	598.7
50°	674.4	712.2	787.7	923.0	1107.9	1202.2	1079.8	885.2	716.4	600.0	526.7
52.5°	626.1	663.0	732.0	863.9	1027.6	1084.0	952.6	772.2	631.5	531.0	468.0
55°	558.5	586.5	648.6	774.7	897.1	910.0	776.8	625.9	510.0	439.9	396.8
57.5°	489.6	513.7	575.0	675.5	761.3	754.6	628.4	497.8	419.8	367.7	336.4
60°	444.7	468.5	522.4	608.6	673.4	650.7	534.8	429.7	362.8	324.6	299.8
62.5°	402.9	421.4	471.9	534.9	581.5	555.8	457.2	370.2	317.1	284.9	265.2
65°	342.3	357.4	397.8	430.7	456.6	431.8	349.9	289.5	251.2	228.5	215.1
67.5°	284.8	294.4	319.9	331.8	350.0	322.8	263.1	222.7	200.9	181.8	172.4
70°	248.5	255.6	269.0	278.7	283.6	255.6	211.4	181.6	163.3	149.9	143.9
72.5°	212.3	218.5	221.2	229.1	226.6	200.3	169.9	146.3	133.2	124.0	116.4
75°	162.2	164.9	162.2	159.1	152.0	133.7	112.6	100.8	91.1	86.8	84.1
77.5°	118.3	117.4	113.8	108.7	96.7	85.2	73.8	69.9	65.7	63.4	62.4
80°	91.1	89.0	85.7	77.6	67.4	59.3	56.6	53.9	52.3	49.6	49.0
82.5°	67.8	66.5	61.2	54.3	47.1	43.3	41.1	40.1	38.5	37.1	37.0
85°	36.1	34.5	28.6	24.8	23.7	22.7	22.1	22.1	20.0	19.4	19.4
87.5°	12.1	9.8	9.7	8.7	9.0	8.5	9.3	8.8	8.7	9.0	8.2
90°	2.5	3.7	5.5	6.8	8.1	9.9	11.8	13.6	15.4	14.9	15.4
92.5°	11.4	16.6	21.5	26.6	35.8	52.0	78.7	104.8	95.2	71.9	52.1
95°	22.9	29.7	40.2	56.3	80.5	133.2	225.5	327.0	367.3	297.9	223.0
97.5°	36.5	41.9	51.0	66.9	93.0	143.3	247.4	416.7	569.2	609.0	555.8
100°	46.4	50.8	59.5	74.3	98.5	141.8	233.5	396.4	586.5	708.5	730.2
102.5°	57.4	61.2	69.4	82.8	104.9	143.8	221.6	366.6	554.3	713.5	788.1
105°	73.7	77.4	84.8	96.6	115.8	149.2	213.0	330.1	498.0	675.7	805.2
107.5°	90.3	93.9	101.2	112.3	130.1	159.4	212.5	306.8	448.1	609.6	756.4
110°	102.2	105.3	112.1	122.6	140.0	167.9	214.9	297.9	419.9	567.9	709.8



TEST NUMBER: P332344-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	113.1	116.2	123.0	133.6	150.4	176.3	219.8	292.9	401.1	531.8	663.7
115°	129.4	133.2	139.3	149.9	166.6	190.1	227.9	291.1	380.9	488.1	602.6
117.5°	145.5	148.6	154.3	166.1	181.6	204.9	238.6	292.2	369.0	461.7	558.4
120°	155.4	158.5	164.8	176.5	192.0	214.3	246.5	294.2	363.5	447.8	535.1
122.5°	164.9	167.9	174.7	185.9	202.4	224.2	253.9	297.6	360.1	436.4	516.8
125°	177.8	181.5	188.3	200.0	216.7	238.4	265.7	302.9	355.5	421.8	492.3
127.5°	188.6	193.2	200.2	213.2	229.9	250.8	275.4	308.8	353.3	408.9	471.1
130°	195.1	200.7	208.1	221.1	237.8	258.3	281.8	312.8	351.8	402.0	457.7
132.5°	200.6	206.6	215.6	228.5	244.8	264.7	287.7	315.8	351.3	395.5	445.3
135°	209.4	216.2	225.5	238.4	255.2	274.3	295.4	320.2	350.5	387.1	428.6
137.5°	217.6	224.3	234.2	247.1	262.6	281.1	301.1	323.2	349.2	379.8	413.4
140°	223.6	229.8	239.7	252.1	267.5	285.5	304.1	325.2	348.7	375.3	404.4
142.5°	229.0	235.8	244.6	257.1	271.5	289.0	307.0	326.6	347.7	371.4	396.0
145°	237.8	243.4	252.7	263.2	277.5	293.6	310.3	327.6	346.2	366.1	385.9
147.5°	246.8	252.2	260.2	270.4	282.6	297.3	312.3	327.6	343.9	360.8	377.6
150°	252.7	257.6	265.7	274.3	285.5	299.8	312.8	327.6	341.9	357.4	371.6
152.5°	258.6	263.6	270.7	278.3	289.0	301.3	313.8	326.1	339.4	353.4	366.1
155°	268.2	271.9	278.1	284.9	293.6	304.1	314.0	324.6	335.1	347.5	358.0
157.5°	276.3	279.3	284.8	290.6	297.3	305.7	314.7	322.4	331.2	340.8	349.3
160°	281.8	284.3	289.2	293.6	299.8	307.2	314.7	321.5	328.3	336.3	344.4
162.5°	286.3	288.3	292.2	296.0	301.3	307.7	314.1	319.5	325.3	331.8	338.4
165°	292.3	293.6	296.7	299.1	303.5	308.4	312.8	316.5	320.8	325.7	330.7
167.5°	297.3	297.9	300.2	302.0	304.8	308.3	311.8	313.5	316.4	320.0	324.0
170°	299.8	300.4	302.2	303.5	304.8	307.8	310.3	311.6	313.4	316.5	319.6
172.5°	302.2	302.4	303.7	304.4	305.2	307.8	309.8	310.1	310.9	313.0	315.6
175°	304.8	304.1	305.3	305.3	305.9	307.2	308.4	307.8	307.8	309.0	310.3
177.5°	305.9	305.5	305.9	305.9	305.9	306.4	307.4	306.4	305.9	306.4	307.0
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9



TEST NUMBER: P332344-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1328.3	1328.3	1330.1	1336.6	1337.4	1343.0	1341.3
5°	1459.9	1470.1	1473.9	1490.1	1499.8	1504.1	1495.5
7.5°	1620.8	1649.6	1663.3	1680.3	1695.3	1699.8	1688.1
10°	1738.0	1768.2	1793.6	1809.3	1823.8	1833.5	1845.9
12.5°	1851.5	1888.6	1912.6	1934.7	1949.7	1962.0	1964.1
15°	1974.8	2030.8	2073.4	2104.7	2120.3	2128.4	2125.2
17.5°	2099.0	2151.0	2181.4	2213.3	2234.9	2236.0	2236.6
20°	2169.4	2220.0	2255.1	2278.8	2303.0	2302.0	2307.4
22.5°	2216.4	2256.3	2283.1	2300.3	2308.7	2304.5	2305.6
25°	2238.4	2250.2	2245.4	2217.9	2210.9	2185.6	2189.8
27.5°	2124.9	2068.9	2010.9	1936.3	1877.4	1830.3	1832.7
30°	1970.9	1871.8	1758.6	1663.7	1578.5	1554.8	1504.1
32.5°	1755.8	1606.9	1474.3	1385.9	1312.8	1293.0	1248.8
35°	1390.9	1246.4	1110.0	1028.1	995.7	950.5	949.9
37.5°	1081.1	953.9	881.8	820.3	788.1	760.7	758.0
40°	909.5	810.2	755.8	711.6	679.9	659.3	654.5
42.5°	789.6	709.3	658.4	631.0	606.5	596.0	588.0
45°	644.8	590.9	555.2	530.4	519.2	511.0	506.8
47.5°	539.3	503.2	479.0	462.5	453.3	444.7	447.0
50°	482.0	452.3	434.5	418.9	411.9	405.9	406.5
52.5°	435.8	409.2	394.8	383.5	374.8	370.6	368.5
55°	369.8	353.1	338.6	330.5	325.6	319.7	318.1
57.5°	315.4	302.5	290.7	281.5	280.4	274.6	275.4
60°	279.2	268.5	258.8	253.9	250.2	245.3	246.9
62.5°	249.5	240.4	231.6	227.6	223.9	220.3	221.0
65°	204.3	195.7	190.3	188.1	186.6	184.9	183.3
67.5°	162.8	157.6	154.2	149.6	146.2	145.7	144.0
70°	137.0	129.9	124.0	118.0	116.5	115.9	116.5
72.5°	109.8	105.4	103.7	100.8	100.5	99.1	100.1
75°	82.5	80.9	79.8	77.6	77.6	77.6	77.6
77.5°	60.8	59.8	59.2	58.8	58.2	57.4	57.4
80°	47.5	46.9	45.8	45.8	45.3	45.8	45.3
82.5°	35.8	35.7	34.6	34.6	34.1	33.7	34.1
85°	18.3	17.8	18.9	17.8	18.3	17.3	18.3
87.5°	8.4	8.6	8.3	8.2	7.9	8.9	7.9
90°	16.1	16.7	18.0	17.3	18.0	18.6	18.0
92.5°	41.4	36.5	33.4	32.2	30.3	31.0	29.9
95°	151.1	118.3	96.0	84.2	78.7	74.3	71.9
97.5°	445.2	365.3	291.2	245.5	217.6	200.9	195.6
100°	680.0	607.6	519.6	457.1	411.9	387.7	388.3
102.5°	786.6	744.3	688.6	639.9	604.1	583.9	569.7
105°	867.0	878.8	862.8	834.2	810.7	790.9	787.8
107.5°	856.9	911.2	933.2	933.7	925.8	919.1	913.4
110°	823.7	901.7	945.2	962.4	967.4	966.1	965.0



TEST NUMBER: P332344-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	780.1	867.6	923.3	955.1	970.4	975.1	975.3
115°	710.3	801.5	868.9	915.4	942.6	955.1	958.1
117.5°	651.4	733.2	801.7	850.1	881.3	899.1	903.4
120°	618.7	693.1	755.6	804.5	839.2	854.1	857.8
122.5°	592.5	661.3	719.5	762.9	794.1	810.5	815.2
125°	559.9	619.3	668.9	708.5	735.8	751.2	755.6
127.5°	531.2	584.9	630.0	665.3	688.6	702.6	706.5
130°	513.4	563.6	605.7	638.6	660.8	673.8	678.8
132.5°	496.6	543.3	583.4	614.3	636.6	648.1	651.6
135°	472.5	512.8	548.1	578.5	597.1	608.2	612.5
137.5°	449.4	484.1	514.7	540.2	559.0	568.5	571.3
140°	436.0	465.7	492.3	515.9	533.2	543.2	542.6
142.5°	423.1	448.9	472.1	492.1	507.5	516.4	515.8
145°	406.3	426.1	444.1	459.5	472.5	477.5	478.7
147.5°	393.8	409.8	422.6	434.3	443.1	447.8	448.3
150°	385.9	398.9	410.6	419.9	426.7	430.5	430.5
152.5°	378.4	389.9	399.7	407.0	413.4	415.6	415.6
155°	367.9	377.2	384.6	390.1	395.1	396.4	397.0
157.5°	357.6	364.8	370.6	375.4	379.1	380.2	380.0
160°	351.2	357.4	361.7	366.1	369.7	369.7	369.2
162.5°	344.2	349.9	353.8	356.6	359.8	359.8	359.3
165°	334.5	338.8	341.9	344.4	346.8	346.2	346.2
167.5°	326.9	329.4	331.6	332.7	334.5	333.8	333.8
170°	321.5	323.9	325.2	325.7	327.0	326.4	326.4
172.5°	317.0	318.9	319.7	319.8	321.1	320.0	319.5
175°	310.9	312.1	312.1	312.1	312.8	312.1	311.6
177.5°	307.4	307.9	307.9	307.4	307.9	307.0	307.0
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9

(END OF REPORT)