

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332273-930

Luminaire Tested: **S123RDIP-S560D365U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332273-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D365U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2923.3 lumens
Efficiency: N/A
Efficacy: 106.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332273-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332273-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	60
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56	51
2	92	84	78	73	85	79	74	69	69	65	62	60	57	54	51	49	47	43
3	84	74	67	61	78	70	64	58	61	56	52	53	50	46	46	43	41	37
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	41	38	35	32
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	37	34	31	28
6	65	53	45	39	61	50	43	38	44	39	34	39	34	31	34	30	28	25
7	61	48	40	35	56	46	38	33	40	35	30	36	31	27	31	27	25	22
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	22	20
9	53	40	33	28	49	38	31	27	34	28	24	30	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8289	8289	8289
5°	8321	8206	8253
10°	8273	8103	8075
15°	8184	7913	7830
20°	8062	7676	7497
25°	7936	7410	7172
30°	7771	7102	6714
35°	7599	6795	6294
40°	7442	6433	5774
45°	7234	6075	5305
50°	7006	5668	4779
55°	6775	5204	4290
60°	6562	4706	3750
65°	6283	4167	3212
70°	5936	3500	2593
75°	5427	2753	2441
80°	4841	2442	2244
85°	4088	2149	2001



TEST NUMBER: P332273-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.3	2.5
10°-20°	201.2	6.9
20°-30°	289.7	9.9
30°-40°	326.3	11.2
40°-50°	312.2	10.7
50°-60°	255.7	8.7
60°-70°	172.5	5.9
70°-80°	86.8	3.0
80°-90°	24.0	0.8
90°-100°	14.1	0.5
100°-110°	67.2	2.3
110°-120°	161.4	5.5
120°-130°	205.5	7.0
130°-140°	219.6	7.5
140°-150°	205.4	7.0
150°-160°	165.6	5.7
160°-170°	106.9	3.7
170°-180°	36.8	1.3
0°-30°	563.2	19.3
0°-40°	889.5	30.4
0°-60°	1457.4	49.9
0°-90°	1740.7	59.5
90°-120°	242.7	8.3
90°-150°	873.2	29.9
90°-180°	1183.0	40.5
0°-180°	2923.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	770	770	770	770	770	
5°	770	767	760	765	764	73
15°	734	727	710	707	703	207
25°	668	652	624	611	604	307
35°	578	555	517	491	479	362
45°	475	446	399	365	348	367
55°	361	329	277	242	229	324
65°	247	212	164	134	126	244
75°	130	100	66	60	59	139
85°	33	20	17	16	16	37
90°	0	3	7	8	9	2
95°	18	7	9	11	11	22
105°	86	87	63	15	13	91
115°	161	163	165	168	169	159
125°	227	229	230	231	232	203
135°	283	284	286	286	286	217
145°	326	328	329	329	329	204
155°	359	359	359	360	359	165
165°	379	378	378	380	378	107
175°	388	386	387	388	386	37
180°	388	388	388	388	388	



TEST NUMBER: P332273-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1
2.5°	772.6	772.1	771.7	771.2	770.8	769.9	768.6	767.2	765.9	764.6	765.8
5°	770.1	769.4	768.7	768.0	767.3	766.1	764.4	762.8	761.1	759.5	760.7
7.5°	763.0	762.2	761.4	760.7	759.9	758.5	756.4	754.2	752.0	749.8	750.5
10°	756.9	755.9	755.0	754.0	753.1	751.3	748.9	746.3	743.8	741.4	741.4
12.5°	748.4	747.4	746.2	745.2	744.1	742.1	739.0	736.0	732.9	729.9	729.8
15°	734.4	733.0	731.4	729.9	728.4	725.6	721.8	717.9	714.0	710.1	709.4
17.5°	716.8	715.1	713.3	711.5	709.7	706.4	701.4	696.5	691.5	686.6	685.2
20°	703.8	701.6	699.4	697.2	695.0	691.2	685.9	680.7	675.4	670.1	668.3
22.5°	689.3	686.8	684.3	681.7	679.1	675.1	669.4	663.8	658.3	652.6	650.4
25°	668.2	664.8	661.3	657.9	654.4	649.5	643.0	636.7	630.3	623.9	621.0
27.5°	642.6	638.8	635.0	631.1	627.3	621.8	614.7	607.6	600.5	593.5	589.4
30°	625.2	621.0	616.9	612.7	608.5	602.5	594.8	587.0	579.2	571.4	566.7
32.5°	607.6	603.0	598.3	593.5	588.8	582.4	574.1	565.9	557.7	549.4	544.3
35°	578.3	573.3	568.3	563.4	558.3	551.5	542.9	534.3	525.7	517.1	511.1
37.5°	548.6	543.1	537.5	531.9	526.4	519.0	509.8	500.7	491.5	482.2	475.5
40°	529.6	523.5	517.4	511.3	505.2	497.2	487.4	477.5	467.7	457.8	450.5
42.5°	508.1	502.0	495.9	489.8	483.7	475.6	465.4	455.2	445.0	434.8	426.9
45°	475.2	469.0	462.8	456.6	450.3	441.8	431.1	420.4	409.8	399.1	391.2
47.5°	442.4	435.5	428.7	421.8	415.0	406.3	395.5	384.8	374.1	363.5	354.9
50°	418.4	411.9	405.4	398.8	392.3	383.4	372.2	361.0	349.8	338.5	329.9
52.5°	397.0	389.9	382.8	375.7	368.7	359.5	348.4	337.3	326.1	315.0	306.1
55°	361.0	354.2	347.4	340.6	333.8	324.5	312.7	300.9	289.1	277.3	269.2
57.5°	327.8	320.3	312.9	305.5	298.1	288.5	276.6	264.8	252.9	241.1	233.5
60°	304.8	297.2	289.5	281.8	274.3	264.6	253.2	241.7	230.1	218.6	211.1
62.5°	281.8	274.2	266.5	258.9	251.3	241.7	230.2	218.7	207.1	195.6	188.6
65°	246.7	239.0	231.5	223.8	216.1	206.9	196.1	185.3	174.5	163.6	156.9
67.5°	211.6	203.9	196.2	188.4	180.8	171.7	161.3	150.9	140.6	130.1	125.1
70°	188.6	181.1	173.7	166.2	158.7	150.0	140.3	130.6	120.9	111.2	106.3
72.5°	165.6	158.2	150.8	143.5	136.1	128.0	119.2	110.3	101.5	92.7	88.7
75°	130.5	123.8	117.2	110.6	103.9	96.7	89.1	81.4	73.9	66.2	64.8
77.5°	98.6	92.5	86.5	80.5	74.4	69.0	64.1	59.2	54.2	49.3	48.6
80°	78.1	72.4	66.7	61.0	55.3	51.0	48.1	45.2	42.2	39.4	38.9
82.5°	58.6	53.6	48.8	43.9	38.9	35.8	34.4	33.1	31.7	30.3	29.9
85°	33.1	30.1	27.0	24.0	20.9	19.2	18.8	18.3	17.9	17.4	17.2
87.5°	12.1	10.9	9.9	8.8	7.7	7.2	7.4	7.6	7.7	7.9	7.8
90°	0.3	0.9	1.5	2.2	2.9	3.6	4.4	5.2	6.1	6.9	7.2
92.5°	5.4	5.2	5.0	4.8	4.6	4.9	5.5	6.1	6.8	7.3	7.7
95°	17.6	14.9	12.3	9.7	7.1	6.1	6.8	7.5	8.2	9.0	9.4
97.5°	35.3	34.2	32.9	31.8	30.6	27.7	23.1	18.5	13.9	9.3	9.8
100°	48.7	50.0	51.3	52.5	53.8	49.5	39.5	29.5	19.5	9.5	10.0
102.5°	63.9	64.8	65.7	66.7	67.6	62.6	51.7	40.8	29.8	19.0	17.4
105°	85.9	86.6	87.2	88.0	88.7	86.2	80.4	74.6	68.9	63.1	51.8
107.5°	109.0	109.6	110.1	110.7	111.3	112.0	112.9	113.8	114.7	115.6	107.3
110°	124.5	125.0	125.5	126.0	126.5	127.1	127.8	128.5	129.2	130.0	127.8



TEST NUMBER: P332273-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	139.2	139.7	140.1	140.6	141.0	141.6	142.4	143.1	143.7	144.5	144.5
115°	161.0	161.4	161.8	162.2	162.6	163.1	163.6	164.2	164.8	165.3	166.0
117.5°	182.2	182.7	183.1	183.6	184.1	184.5	184.7	185.1	185.4	185.6	186.1
120°	195.3	195.9	196.5	197.1	197.6	198.0	198.2	198.4	198.6	198.8	199.3
122.5°	208.7	209.2	209.6	210.1	210.6	210.9	211.2	211.4	211.7	211.9	212.3
125°	227.1	227.6	228.0	228.5	229.1	229.4	229.8	230.0	230.2	230.5	230.6
127.5°	244.8	245.3	245.8	246.3	246.8	247.2	247.5	247.9	248.2	248.4	248.7
130°	255.8	256.3	256.8	257.4	257.9	258.3	258.5	258.8	259.0	259.3	259.5
132.5°	266.4	266.9	267.5	268.0	268.5	268.8	269.0	269.3	269.5	269.7	269.9
135°	282.7	283.0	283.4	283.8	284.1	284.5	284.7	285.0	285.3	285.5	285.7
137.5°	296.4	296.9	297.4	297.9	298.4	298.7	298.9	299.0	299.1	299.3	299.6
140°	305.7	306.1	306.5	306.8	307.2	307.5	307.7	307.9	308.1	308.3	308.5
142.5°	314.2	314.6	315.0	315.4	315.8	316.0	316.3	316.4	316.6	316.8	317.0
145°	326.1	326.6	327.0	327.5	327.9	328.2	328.3	328.5	328.6	328.7	328.9
147.5°	337.4	337.7	337.9	338.3	338.5	338.8	338.9	339.0	339.2	339.2	339.4
150°	344.3	344.5	344.6	344.9	345.0	345.2	345.4	345.4	345.6	345.7	345.8
152.5°	350.5	350.6	350.7	350.7	350.8	351.0	351.0	351.1	351.1	351.2	351.5
155°	359.3	359.1	359.0	358.9	358.7	358.7	358.8	358.8	358.9	359.0	359.3
157.5°	366.1	366.1	366.1	366.0	366.0	366.0	365.9	365.8	365.7	365.7	366.1
160°	370.2	370.1	370.1	370.0	370.0	369.9	369.8	369.7	369.7	369.7	370.0
162.5°	374.1	374.0	373.8	373.7	373.5	373.3	373.2	373.2	373.2	373.1	373.5
165°	378.9	378.6	378.5	378.3	378.1	378.0	377.9	377.8	377.7	377.7	378.2
167.5°	382.5	382.3	382.0	381.8	381.5	381.4	381.4	381.4	381.4	381.4	381.9
170°	384.6	384.3	384.1	383.8	383.6	383.4	383.4	383.4	383.4	383.4	384.0
172.5°	386.0	385.7	385.4	385.1	384.7	384.7	384.7	384.7	384.8	384.8	385.4
175°	387.8	387.4	387.1	386.9	386.5	386.4	386.5	386.5	386.5	386.6	387.1
177.5°	388.2	388.0	387.8	387.5	387.2	387.1	387.2	387.2	387.3	387.3	387.8
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P332273-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1
2.5°	767.0	768.3	769.5	770.0	769.7	769.5	769.3	769.1
5°	761.9	763.2	764.4	764.9	764.7	764.3	764.1	763.8
7.5°	751.2	751.9	752.6	752.7	752.2	751.8	751.3	750.8
10°	741.6	741.8	741.8	741.6	740.9	740.2	739.6	738.8
12.5°	729.7	729.6	729.5	729.0	728.2	727.4	726.7	725.9
15°	708.7	708.0	707.4	706.5	705.5	704.6	703.6	702.6
17.5°	683.7	682.2	680.7	679.3	677.8	676.4	674.9	673.5
20°	666.5	664.7	662.9	661.2	659.5	657.9	656.2	654.5
22.5°	648.2	645.9	643.7	641.7	640.2	638.6	637.1	635.5
25°	618.1	615.1	612.3	610.0	608.5	607.0	605.4	603.9
27.5°	585.3	581.3	577.2	574.1	571.7	569.4	567.0	564.7
30°	562.0	557.3	552.6	549.1	546.9	544.7	542.4	540.2
32.5°	539.2	533.9	528.8	525.1	522.8	520.4	518.0	515.8
35°	505.2	499.2	493.3	489.0	486.5	484.0	481.5	479.0
37.5°	468.7	461.9	455.2	450.3	447.2	444.1	441.0	437.9
40°	443.4	436.1	428.9	423.7	420.5	417.4	414.2	410.9
42.5°	419.1	411.2	403.2	397.9	395.0	392.2	389.3	386.5
45°	383.3	375.4	367.5	361.8	358.5	355.1	351.8	348.5
47.5°	346.3	337.7	329.1	323.3	320.3	317.3	314.4	311.4
50°	321.3	312.7	304.1	298.2	295.0	291.8	288.6	285.4
52.5°	297.2	288.2	279.2	273.4	270.5	267.7	264.8	262.0
55°	261.2	253.2	245.1	239.7	236.9	234.2	231.4	228.6
57.5°	225.8	218.3	210.7	205.7	203.3	201.0	198.6	196.2
60°	203.6	196.1	188.6	183.7	181.3	179.0	176.6	174.2
62.5°	181.5	174.5	167.4	162.7	160.2	157.7	155.2	152.8
65°	150.0	143.2	136.4	132.2	130.8	129.2	127.7	126.1
67.5°	120.0	114.9	109.8	106.5	104.8	103.2	101.6	100.0
70°	101.4	96.6	91.7	88.5	87.0	85.5	84.0	82.4
72.5°	84.7	80.8	76.8	74.5	73.9	73.2	72.6	71.9
75°	63.4	62.0	60.7	59.8	59.5	59.3	58.9	58.7
77.5°	47.9	47.1	46.3	45.8	45.6	45.2	45.0	44.7
80°	38.5	38.1	37.7	37.3	37.1	36.8	36.5	36.2
82.5°	29.5	29.1	28.7	28.5	28.4	28.4	28.3	28.2
85°	17.0	16.6	16.4	16.2	16.2	16.2	16.2	16.2
87.5°	7.7	7.7	7.7	7.6	7.5	7.4	7.3	7.3
90°	7.4	7.7	7.9	8.2	8.2	8.4	8.5	8.6
92.5°	8.2	8.6	9.0	9.3	9.3	9.4	9.5	9.5
95°	9.9	10.3	10.8	10.9	10.9	10.9	10.9	10.9
97.5°	10.3	10.8	11.3	11.6	11.7	11.7	11.8	11.9
100°	10.5	11.0	11.6	11.8	11.9	12.0	12.1	12.1
102.5°	15.8	14.2	12.6	11.9	12.0	12.1	12.2	12.3
105°	40.4	29.1	17.8	12.1	12.3	12.4	12.6	12.6
107.5°	99.1	90.7	82.4	73.9	65.5	56.9	48.3	39.8
110°	125.7	123.6	121.5	115.9	106.7	97.5	88.4	79.2



TEST NUMBER: P332273-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	144.6	144.6	144.6	143.7	141.7	139.8	137.9	135.9
115°	166.6	167.3	168.0	168.4	168.6	168.9	169.2	169.4
117.5°	186.7	187.2	187.7	188.0	188.0	188.1	188.2	188.2
120°	199.8	200.3	200.8	201.1	201.1	201.1	201.1	201.1
122.5°	212.6	213.0	213.4	213.5	213.6	213.7	213.7	213.8
125°	230.7	230.9	231.0	231.1	231.2	231.4	231.5	231.6
127.5°	248.8	249.1	249.3	249.3	249.2	249.1	248.9	248.8
130°	259.8	260.1	260.3	260.4	260.2	260.2	260.0	259.8
132.5°	270.2	270.4	270.7	270.8	270.5	270.4	270.2	270.0
135°	285.9	286.1	286.3	286.3	286.1	285.9	285.7	285.5
137.5°	299.9	300.2	300.5	300.6	300.4	300.4	300.2	300.1
140°	308.8	309.0	309.3	309.3	309.2	309.1	309.0	308.8
142.5°	317.2	317.4	317.6	317.6	317.5	317.2	317.1	316.9
145°	329.0	329.1	329.2	329.3	329.3	329.3	329.3	329.3
147.5°	339.5	339.7	339.8	339.7	339.4	339.1	338.8	338.5
150°	346.0	346.1	346.3	346.2	346.0	345.8	345.6	345.4
152.5°	351.7	352.0	352.2	352.1	351.9	351.6	351.2	351.0
155°	359.6	360.0	360.3	360.2	359.9	359.5	359.1	358.7
157.5°	366.5	366.9	367.3	367.2	366.7	366.2	365.7	365.2
160°	370.4	370.8	371.2	371.1	370.7	370.2	369.8	369.3
162.5°	374.0	374.4	374.8	374.9	374.5	374.1	373.7	373.2
165°	378.7	379.3	379.8	379.8	379.4	378.9	378.5	378.0
167.5°	382.4	382.9	383.4	383.4	382.9	382.4	381.9	381.4
170°	384.5	385.0	385.5	385.5	385.0	384.5	384.0	383.4
172.5°	385.9	386.4	386.9	386.9	386.3	385.7	385.1	384.6
175°	387.5	388.0	388.4	388.4	387.9	387.3	386.9	386.4
177.5°	388.2	388.6	389.0	388.9	388.4	387.9	387.3	386.9
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8

(END OF REPORT)