

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332345-927

Luminaire Tested: **S123RDIP-S1000D805U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332345-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D805U927-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5547.7 lumens
Efficiency: N/A
Efficacy: 102.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332345-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332345-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	54	52	51	46
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	39
3	83	73	66	61	77	68	62	57	59	54	50	50	47	44	42	40	38	34
4	76	65	57	51	70	61	54	49	53	47	43	45	41	38	38	35	33	29
5	70	58	50	44	65	55	47	42	47	42	37	41	36	33	34	31	29	26
6	64	52	44	39	60	49	42	37	43	37	33	37	32	29	31	28	25	23
7	60	47	40	34	55	45	37	32	39	33	29	34	29	26	29	25	23	20
8	55	43	36	30	51	41	34	29	36	30	26	31	26	23	26	23	20	18
9	52	40	32	27	48	37	30	26	33	27	23	28	24	21	24	21	19	16
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14310	14310	14310
5°	14364	14166	14249
10°	14283	13988	13941
15°	14130	13661	13517
20°	13919	13252	12944
25°	13702	12792	12383
30°	13415	12263	11591
35°	13119	11730	10867
40°	12847	11105	9969
45°	12490	10488	9159
50°	12097	9786	8251
55°	11695	8983	7405
60°	11328	8125	6476
65°	10847	7195	5547
70°	10247	6039	4482
75°	9374	4754	4213
80°	8356	4209	3874
85°	7052	3730	3458



TEST NUMBER: P332345-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.8	2.3
10°-20°	347.3	6.3
20°-30°	500.2	9.0
30°-40°	563.4	10.2
40°-50°	539.0	9.7
50°-60°	441.4	8.0
60°-70°	297.8	5.4
70°-80°	149.8	2.7
80°-90°	42.0	0.8
90°-100°	30.3	0.5
100°-110°	144.4	2.6
110°-120°	347.0	6.3
120°-130°	441.8	8.0
130°-140°	472.1	8.5
140°-150°	441.4	8.0
150°-160°	356.1	6.4
160°-170°	229.8	4.1
170°-180°	79.2	1.4
0°-30°	972.3	17.5
0°-40°	1535.7	27.7
0°-60°	2516.0	45.4
0°-90°	3005.6	54.2
90°-120°	521.7	9.4
90°-150°	1877.0	33.8
90°-180°	2542.0	45.8
0°-180°	5547.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1329	1329	1329	1329	1329	
5°	1329	1324	1311	1320	1319	126
15°	1268	1255	1226	1220	1213	357
25°	1154	1125	1077	1055	1043	530
35°	998	958	893	848	827	625
45°	820	770	689	629	602	633
55°	623	568	479	418	395	559
65°	426	365	282	232	218	421
75°	225	173	114	104	101	240
85°	57	34	30	28	28	64
90°	1	7	15	17	19	5
95°	38	14	19	23	24	47
105°	185	188	136	32	27	196
115°	346	350	356	361	364	342
125°	488	493	495	497	498	436
135°	608	611	614	615	614	468
145°	701	705	707	708	708	439
155°	772	771	772	774	771	356
165°	814	813	812	816	812	230
175°	834	831	831	835	830	79
180°	834	834	834	834	834	



TEST NUMBER: P332345-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4
2.5°	1333.7	1332.9	1332.2	1331.4	1330.6	1329.1	1326.8	1324.5	1322.2	1319.9	1322.0
5°	1329.4	1328.2	1327.0	1325.8	1324.6	1322.5	1319.7	1316.8	1314.0	1311.1	1313.2
7.5°	1317.1	1315.8	1314.5	1313.2	1311.9	1309.4	1305.7	1302.0	1298.2	1294.5	1295.7
10°	1306.8	1305.1	1303.4	1301.7	1300.1	1297.0	1292.8	1288.4	1284.1	1279.8	1280.1
12.5°	1292.1	1290.2	1288.4	1286.5	1284.6	1281.0	1275.8	1270.5	1265.3	1260.0	1259.8
15°	1268.0	1265.4	1262.7	1260.0	1257.4	1252.8	1246.0	1239.3	1232.6	1225.9	1224.7
17.5°	1237.5	1234.5	1231.4	1228.4	1225.3	1219.5	1210.9	1202.5	1193.9	1185.3	1182.8
20°	1215.1	1211.3	1207.4	1203.6	1199.8	1193.3	1184.2	1175.1	1166.0	1156.9	1153.8
22.5°	1190.1	1185.7	1181.3	1176.9	1172.5	1165.5	1155.7	1146.1	1136.4	1126.7	1122.8
25°	1153.7	1147.7	1141.7	1135.7	1129.7	1121.2	1110.2	1099.2	1088.1	1077.1	1072.1
27.5°	1109.5	1102.9	1096.2	1089.6	1083.0	1073.6	1061.3	1049.0	1036.7	1024.5	1017.5
30°	1079.3	1072.1	1064.9	1057.7	1050.5	1040.2	1026.8	1013.4	1000.0	986.6	978.4
32.5°	1049.1	1040.9	1032.8	1024.6	1016.5	1005.4	991.2	977.0	962.7	948.6	939.7
35°	998.4	989.8	981.1	972.6	963.9	952.1	937.3	922.4	907.6	892.7	882.4
37.5°	947.1	937.5	927.9	918.3	908.7	896.0	880.2	864.3	848.4	832.6	820.9
40°	914.3	903.8	893.2	882.6	872.1	858.3	841.4	824.3	807.3	790.3	777.8
42.5°	877.2	866.6	856.1	845.6	835.0	821.0	803.4	785.8	768.3	750.7	737.0
45°	820.5	809.7	798.9	788.1	777.4	762.8	744.3	725.9	707.4	689.0	675.3
47.5°	763.8	751.9	740.1	728.3	716.4	701.3	682.9	664.4	645.9	627.5	612.7
50°	722.4	711.1	699.9	688.6	677.3	662.0	642.6	623.2	603.8	584.4	569.5
52.5°	685.3	673.1	660.8	648.6	636.4	620.7	601.5	582.3	563.1	543.8	528.4
55°	623.2	611.5	599.7	588.0	576.2	560.2	539.8	519.4	499.1	478.7	464.9
57.5°	565.9	553.0	540.3	527.4	514.7	498.0	477.5	457.1	436.7	416.2	403.1
60°	526.2	513.0	499.8	486.6	473.4	456.9	437.0	417.2	397.3	377.4	364.4
62.5°	486.5	473.3	460.1	446.9	433.8	417.2	397.4	377.5	357.6	337.7	325.5
65°	425.9	412.7	399.5	386.3	373.2	357.3	338.6	319.9	301.2	282.5	270.8
67.5°	365.3	352.0	338.7	325.3	312.0	296.4	278.5	260.5	242.6	224.7	215.9
70°	325.6	312.7	299.8	286.8	273.9	259.0	242.2	225.5	208.7	191.9	183.5
72.5°	285.9	273.2	260.5	247.7	235.0	220.9	205.7	190.5	175.2	160.0	153.1
75°	225.4	213.8	202.3	190.8	179.4	167.0	153.8	140.6	127.5	114.3	111.9
77.5°	170.2	159.7	149.3	138.9	128.6	119.1	110.6	102.1	93.6	85.2	83.9
80°	134.8	124.9	115.1	105.3	95.5	88.1	83.0	78.0	73.0	67.9	67.2
82.5°	101.2	92.7	84.2	75.7	67.2	61.8	59.4	57.1	54.7	52.4	51.7
85°	57.1	51.9	46.6	41.4	36.0	33.0	32.3	31.6	30.9	30.2	29.7
87.5°	20.8	19.0	17.2	15.3	13.5	12.8	13.2	13.5	13.9	14.2	14.1
90°	0.6	2.0	3.4	4.8	6.1	7.7	9.5	11.2	13.1	14.9	15.4
92.5°	11.5	11.2	10.8	10.4	10.0	10.5	11.8	13.2	14.5	15.8	16.7
95°	37.8	32.2	26.5	20.8	15.2	13.2	14.7	16.2	17.7	19.2	20.2
97.5°	75.9	73.4	70.9	68.4	65.8	59.6	49.7	39.8	29.9	20.0	21.1
100°	104.6	107.4	110.2	112.9	115.7	106.3	84.8	63.4	41.9	20.4	21.5
102.5°	137.4	139.3	141.3	143.3	145.3	134.6	111.1	87.6	64.2	40.7	37.3
105°	184.6	186.1	187.6	189.1	190.6	185.2	172.8	160.4	148.0	135.6	111.3
107.5°	234.3	235.6	236.8	238.0	239.2	240.7	242.7	244.7	246.6	248.6	230.8
110°	267.5	268.6	269.7	270.8	272.0	273.2	274.8	276.3	277.8	279.3	274.8



TEST NUMBER: P332345-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	299.3	300.2	301.3	302.2	303.2	304.4	306.0	307.5	309.0	310.5	310.6
115°	346.2	347.1	347.8	348.7	349.5	350.5	351.8	353.0	354.3	355.5	356.9
117.5°	391.7	392.7	393.7	394.7	395.7	396.6	397.2	397.8	398.5	399.1	400.2
120°	419.9	421.1	422.4	423.6	424.8	425.7	426.1	426.5	426.9	427.3	428.4
122.5°	448.6	449.6	450.7	451.7	452.7	453.4	454.0	454.6	455.0	455.6	456.4
125°	488.1	489.1	490.2	491.3	492.4	493.3	493.8	494.3	494.9	495.4	495.7
127.5°	526.2	527.3	528.4	529.5	530.6	531.5	532.1	532.8	533.5	534.1	534.6
130°	549.9	551.0	552.2	553.3	554.4	555.2	555.7	556.3	556.8	557.4	557.9
132.5°	572.7	573.9	575.0	576.1	577.2	577.9	578.4	578.8	579.2	579.7	580.3
135°	607.5	608.4	609.2	610.1	610.9	611.6	612.1	612.7	613.2	613.8	614.2
137.5°	637.3	638.3	639.4	640.4	641.4	642.1	642.5	642.8	643.0	643.3	644.0
140°	657.1	657.9	658.8	659.6	660.4	661.0	661.5	661.9	662.3	662.7	663.2
142.5°	675.4	676.3	677.1	677.9	678.7	679.4	679.8	680.2	680.6	681.0	681.4
145°	701.1	702.0	703.0	703.9	705.0	705.5	705.8	706.1	706.4	706.6	706.9
147.5°	725.2	725.9	726.5	727.1	727.8	728.3	728.5	728.7	729.0	729.3	729.6
150°	740.1	740.5	740.9	741.3	741.7	742.1	742.4	742.7	742.9	743.2	743.5
152.5°	753.4	753.7	753.8	754.1	754.2	754.4	754.6	754.7	754.9	755.1	755.6
155°	772.3	772.1	771.7	771.5	771.2	771.1	771.3	771.4	771.5	771.7	772.4
157.5°	786.9	786.9	786.9	786.8	786.8	786.7	786.6	786.5	786.3	786.2	787.0
160°	795.8	795.7	795.6	795.4	795.3	795.1	795.0	794.9	794.7	794.6	795.4
162.5°	804.2	803.9	803.5	803.2	802.8	802.6	802.4	802.3	802.2	802.0	803.0
165°	814.4	814.0	813.6	813.2	812.8	812.5	812.4	812.2	812.1	811.9	813.0
167.5°	822.4	821.8	821.3	820.7	820.1	819.8	819.8	819.8	819.8	819.8	820.9
170°	826.8	826.2	825.7	825.1	824.6	824.3	824.3	824.3	824.3	824.3	825.5
172.5°	829.7	829.1	828.5	827.8	827.1	826.9	827.0	827.0	827.2	827.3	828.4
175°	833.6	832.9	832.3	831.6	830.8	830.6	830.7	830.8	831.0	831.2	832.1
177.5°	834.6	834.1	833.5	833.0	832.4	832.2	832.3	832.4	832.5	832.6	833.5
180°	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6



TEST NUMBER: P332345-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4
2.5°	1324.1	1326.3	1328.3	1329.2	1328.8	1328.5	1328.1	1327.7
5°	1315.4	1317.6	1319.7	1320.6	1320.1	1319.6	1319.1	1318.7
7.5°	1296.9	1298.1	1299.3	1299.5	1298.6	1297.8	1297.0	1296.2
10°	1280.3	1280.6	1280.8	1280.3	1279.1	1277.9	1276.7	1275.5
12.5°	1259.6	1259.6	1259.4	1258.6	1257.3	1255.8	1254.5	1253.1
15°	1223.5	1222.3	1221.1	1219.6	1218.0	1216.3	1214.7	1213.0
17.5°	1180.3	1177.7	1175.2	1172.7	1170.2	1167.7	1165.2	1162.7
20°	1150.6	1147.6	1144.5	1141.5	1138.6	1135.7	1132.8	1130.0
22.5°	1119.0	1115.1	1111.2	1107.9	1105.3	1102.6	1099.9	1097.2
25°	1067.1	1062.0	1057.0	1053.1	1050.5	1047.9	1045.3	1042.6
27.5°	1010.5	1003.5	996.5	991.0	987.0	982.9	978.9	974.9
30°	970.3	962.1	953.9	948.0	944.1	940.3	936.4	932.6
32.5°	930.7	921.9	912.9	906.5	902.5	898.4	894.4	890.3
35°	872.1	861.8	851.5	844.2	840.0	835.6	831.3	827.0
37.5°	809.2	797.5	785.8	777.3	772.0	766.7	761.4	756.1
40°	765.4	753.0	740.5	731.5	726.0	720.5	714.9	709.5
42.5°	723.4	709.8	696.2	686.9	682.0	677.1	672.1	667.2
45°	661.6	648.0	634.3	624.6	618.9	613.1	607.4	601.7
47.5°	597.8	583.0	568.1	558.1	552.9	547.9	542.7	537.6
50°	554.7	539.8	525.0	514.8	509.3	503.7	498.3	492.7
52.5°	513.0	497.6	482.1	471.9	467.0	462.1	457.2	452.2
55°	450.9	437.0	423.1	413.8	409.0	404.2	399.4	394.6
57.5°	389.9	376.8	363.7	355.1	351.0	346.9	342.9	338.7
60°	351.5	338.6	325.6	317.1	313.1	309.0	304.9	300.8
62.5°	313.3	301.2	289.0	280.7	276.6	272.3	268.0	263.7
65°	259.0	247.2	235.5	228.3	225.7	223.1	220.5	217.8
67.5°	207.2	198.4	189.6	183.8	181.0	178.2	175.3	172.5
70°	175.2	166.8	158.4	152.9	150.2	147.6	145.0	142.4
72.5°	146.3	139.4	132.6	128.7	127.5	126.4	125.3	124.2
75°	109.5	107.1	104.7	103.3	102.8	102.3	101.8	101.3
77.5°	82.6	81.3	80.0	79.1	78.7	78.2	77.7	77.2
80°	66.5	65.8	65.0	64.5	64.0	63.5	63.0	62.5
82.5°	50.9	50.2	49.5	49.1	49.0	49.0	48.8	48.7
85°	29.2	28.8	28.3	28.0	28.0	28.0	28.0	28.0
87.5°	14.0	13.9	13.9	13.8	13.6	13.5	13.3	13.2
90°	16.0	16.5	17.0	17.5	17.7	18.1	18.3	18.6
92.5°	17.6	18.5	19.4	19.9	20.0	20.2	20.4	20.6
95°	21.2	22.1	23.1	23.5	23.5	23.5	23.5	23.5
97.5°	22.2	23.2	24.3	25.0	25.1	25.3	25.3	25.5
100°	22.7	23.8	24.9	25.4	25.6	25.7	25.9	26.0
102.5°	33.9	30.5	27.1	25.5	25.7	26.0	26.2	26.5
105°	86.9	62.6	38.2	26.1	26.5	26.7	27.0	27.3
107.5°	212.9	195.0	177.1	159.0	140.7	122.3	103.9	85.6
110°	270.2	265.7	261.2	249.1	229.3	209.7	190.0	170.3



TEST NUMBER: P332345-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	310.7	310.8	310.9	308.8	304.7	300.5	296.4	292.2
115°	358.2	359.7	361.0	361.9	362.5	363.1	363.6	364.2
117.5°	401.3	402.4	403.5	404.1	404.3	404.3	404.4	404.6
120°	429.5	430.6	431.7	432.3	432.3	432.3	432.3	432.3
122.5°	457.1	457.9	458.7	459.1	459.2	459.3	459.5	459.5
125°	496.0	496.3	496.5	496.9	497.1	497.4	497.6	498.0
127.5°	535.0	535.4	535.8	535.9	535.7	535.4	535.1	534.9
130°	558.5	559.0	559.6	559.8	559.4	559.2	558.9	558.6
132.5°	580.7	581.3	581.9	581.9	581.6	581.2	580.8	580.4
135°	614.6	615.0	615.4	615.4	615.0	614.6	614.2	613.8
137.5°	644.7	645.3	646.0	646.2	645.9	645.6	645.4	645.1
140°	663.8	664.3	664.9	665.0	664.7	664.5	664.2	663.9
142.5°	681.9	682.3	682.8	682.8	682.4	682.0	681.7	681.3
145°	707.2	707.5	707.7	707.9	707.9	707.9	707.9	707.9
147.5°	729.8	730.2	730.4	730.2	729.6	729.0	728.3	727.7
150°	743.7	744.0	744.3	744.3	743.8	743.4	743.0	742.6
152.5°	756.1	756.5	757.1	757.0	756.4	755.7	755.1	754.5
155°	773.1	773.7	774.4	774.4	773.6	772.7	771.9	771.0
157.5°	787.8	788.6	789.5	789.3	788.3	787.2	786.2	785.1
160°	796.2	797.1	797.9	797.8	796.9	795.9	795.0	794.0
162.5°	803.9	804.9	805.7	805.8	804.9	804.1	803.3	802.4
165°	814.1	815.2	816.3	816.4	815.5	814.4	813.5	812.5
167.5°	822.0	823.2	824.3	824.3	823.2	822.0	820.9	819.8
170°	826.5	827.6	828.7	828.7	827.6	826.5	825.5	824.3
172.5°	829.5	830.6	831.7	831.6	830.4	829.3	828.0	826.8
175°	833.1	834.0	835.0	834.9	833.9	832.7	831.6	830.5
177.5°	834.4	835.3	836.1	836.1	835.0	833.9	832.7	831.6
180°	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6

(END OF REPORT)