

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332274-930

Luminaire Tested: **S123RDIP-S560D365U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332274-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D365U930-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2756.9 lumens
Efficiency: N/A
Efficacy: 100.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332274-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332274-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63
1	101	97	93	90	95	91	88	85	80	78	75	70	68	67	61	60	58	54
2	92	85	79	74	87	80	75	70	71	67	63	62	59	56	54	52	50	46
3	85	75	68	62	79	71	64	59	63	58	54	55	51	48	48	45	43	39
4	78	67	59	53	73	63	56	51	56	50	46	50	45	42	43	40	37	34
5	71	60	52	46	67	57	49	44	50	45	40	45	40	36	39	36	33	30
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	26
7	61	49	41	35	57	46	39	34	42	36	31	37	32	29	33	29	26	24
8	57	44	37	31	53	42	35	30	38	32	28	34	29	26	30	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	27	23	28	24	21	19
10	50	38	30	25	47	36	29	25	32	27	23	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8289	8289	8289
5°	8321	8206	8253
10°	8273	8103	8075
15°	8184	7913	7830
20°	8062	7676	7497
25°	7936	7410	7172
30°	7771	7102	6714
35°	7599	6795	6294
40°	7442	6433	5774
45°	7234	6075	5305
50°	7006	5668	4779
55°	6775	5204	4290
60°	6562	4706	3750
65°	6283	4167	3212
70°	5936	3500	2593
75°	5427	2753	2441
80°	4841	2442	2244
85°	4088	2149	2001



TEST NUMBER: P332274-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.3	2.6
10°-20°	201.2	7.3
20°-30°	289.7	10.5
30°-40°	326.3	11.8
40°-50°	312.2	11.3
50°-60°	255.7	9.3
60°-70°	172.5	6.3
70°-80°	86.8	3.1
80°-90°	24.0	0.9
90°-100°	23.9	0.9
100°-110°	71.5	2.6
110°-120°	121.6	4.4
120°-130°	160.0	5.8
130°-140°	179.8	6.5
140°-150°	176.8	6.4
150°-160°	148.8	5.4
160°-170°	99.1	3.6
170°-180°	34.7	1.3
0°-30°	563.2	20.4
0°-40°	889.5	32.3
0°-60°	1457.4	52.9
0°-90°	1740.7	63.1
90°-120°	217.1	7.9
90°-150°	733.7	26.6
90°-180°	1016.0	36.9
0°-180°	2756.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	770	770	770	770	770	
5°	770	767	760	765	764	73
15°	734	727	710	707	703	207
25°	668	652	624	611	604	307
35°	578	555	517	491	479	362
45°	475	446	399	365	348	367
55°	361	329	277	242	229	324
65°	247	212	164	134	126	244
75°	130	100	66	60	59	139
85°	33	20	17	16	16	37
90°	0	3	7	8	9	3
95°	17	19	21	22	22	19
105°	65	66	68	68	69	69
115°	122	123	123	123	123	121
125°	179	180	180	178	177	160
135°	232	234	234	233	232	179
145°	282	283	284	283	282	176
155°	323	323	323	324	322	149
165°	352	351	351	352	351	99
175°	366	365	365	366	364	35
180°	367	367	367	367	367	



TEST NUMBER: P332274-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1
2.5°	772.6	772.1	771.7	771.2	770.8	769.9	768.6	767.2	765.9	764.6	765.8
5°	770.1	769.4	768.7	768.0	767.3	766.1	764.4	762.8	761.1	759.5	760.7
7.5°	763.0	762.2	761.4	760.7	759.9	758.5	756.4	754.2	752.0	749.8	750.5
10°	756.9	755.9	755.0	754.0	753.1	751.3	748.9	746.3	743.8	741.4	741.4
12.5°	748.4	747.4	746.2	745.2	744.1	742.1	739.0	736.0	732.9	729.9	729.8
15°	734.4	733.0	731.4	729.9	728.4	725.6	721.8	717.9	714.0	710.1	709.4
17.5°	716.8	715.1	713.3	711.5	709.7	706.4	701.4	696.5	691.5	686.6	685.2
20°	703.8	701.6	699.4	697.2	695.0	691.2	685.9	680.7	675.4	670.1	668.3
22.5°	689.3	686.8	684.3	681.7	679.1	675.1	669.4	663.8	658.3	652.6	650.4
25°	668.2	664.8	661.3	657.9	654.4	649.5	643.0	636.7	630.3	623.9	621.0
27.5°	642.6	638.8	635.0	631.1	627.3	621.8	614.7	607.6	600.5	593.5	589.4
30°	625.2	621.0	616.9	612.7	608.5	602.5	594.8	587.0	579.2	571.4	566.7
32.5°	607.6	603.0	598.3	593.5	588.8	582.4	574.1	565.9	557.7	549.4	544.3
35°	578.3	573.3	568.3	563.4	558.3	551.5	542.9	534.3	525.7	517.1	511.1
37.5°	548.6	543.1	537.5	531.9	526.4	519.0	509.8	500.7	491.5	482.2	475.5
40°	529.6	523.5	517.4	511.3	505.2	497.2	487.4	477.5	467.7	457.8	450.5
42.5°	508.1	502.0	495.9	489.8	483.7	475.6	465.4	455.2	445.0	434.8	426.9
45°	475.2	469.0	462.8	456.6	450.3	441.8	431.1	420.4	409.8	399.1	391.2
47.5°	442.4	435.5	428.7	421.8	415.0	406.3	395.5	384.8	374.1	363.5	354.9
50°	418.4	411.9	405.4	398.8	392.3	383.4	372.2	361.0	349.8	338.5	329.9
52.5°	397.0	389.9	382.8	375.7	368.7	359.5	348.4	337.3	326.1	315.0	306.1
55°	361.0	354.2	347.4	340.6	333.8	324.5	312.7	300.9	289.1	277.3	269.2
57.5°	327.8	320.3	312.9	305.5	298.1	288.5	276.6	264.8	252.9	241.1	233.5
60°	304.8	297.2	289.5	281.8	274.3	264.6	253.2	241.7	230.1	218.6	211.1
62.5°	281.8	274.2	266.5	258.9	251.3	241.7	230.2	218.7	207.1	195.6	188.6
65°	246.7	239.0	231.5	223.8	216.1	206.9	196.1	185.3	174.5	163.6	156.9
67.5°	211.6	203.9	196.2	188.4	180.8	171.7	161.3	150.9	140.6	130.1	125.1
70°	188.6	181.1	173.7	166.2	158.7	150.0	140.3	130.6	120.9	111.2	106.3
72.5°	165.6	158.2	150.8	143.5	136.1	128.0	119.2	110.3	101.5	92.7	88.7
75°	130.5	123.8	117.2	110.6	103.9	96.7	89.1	81.4	73.9	66.2	64.8
77.5°	98.6	92.5	86.5	80.5	74.4	69.0	64.1	59.2	54.2	49.3	48.6
80°	78.1	72.4	66.7	61.0	55.3	51.0	48.1	45.2	42.2	39.4	38.9
82.5°	58.6	53.6	48.8	43.9	38.9	35.8	34.4	33.1	31.7	30.3	29.9
85°	33.1	30.1	27.0	24.0	20.9	19.2	18.8	18.3	17.9	17.4	17.2
87.5°	12.1	10.9	9.9	8.8	7.7	7.2	7.4	7.6	7.7	7.9	7.8
90°	0.3	0.9	1.5	2.2	2.9	3.6	4.4	5.2	6.1	6.9	7.2
92.5°	7.0	7.4	7.8	8.3	8.7	9.1	9.6	10.1	10.6	11.1	11.3
95°	17.0	17.4	17.9	18.3	18.8	19.2	19.8	20.3	20.8	21.4	21.6
97.5°	30.2	30.5	30.9	31.2	31.6	31.9	32.3	32.6	33.0	33.3	33.7
100°	39.2	39.5	39.9	40.4	40.7	41.1	41.4	41.7	42.1	42.3	42.6
102.5°	49.6	49.8	50.0	50.2	50.5	50.8	51.2	51.7	52.1	52.5	52.7
105°	64.8	65.0	65.1	65.2	65.3	65.7	66.3	66.9	67.4	68.0	68.0
107.5°	82.6	82.7	82.8	82.8	82.9	83.0	83.2	83.5	83.7	84.0	84.1
110°	93.7	93.8	93.9	94.0	94.2	94.2	94.4	94.6	94.7	94.8	95.1



TEST NUMBER: P332274-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	105.2	105.3	105.3	105.4	105.5	105.5	105.6	105.6	105.6	105.7	105.9
115°	122.5	122.6	122.9	123.0	123.2	123.3	123.1	123.0	122.9	122.7	122.8
117.5°	139.8	140.0	140.1	140.2	140.4	140.3	140.1	140.0	139.8	139.7	139.7
120°	150.7	151.1	151.5	151.8	152.2	152.2	152.0	151.6	151.3	151.0	150.9
122.5°	162.0	162.2	162.6	162.8	163.1	163.1	163.0	162.8	162.7	162.5	162.3
125°	179.2	179.4	179.6	179.8	180.0	180.0	179.9	179.8	179.6	179.5	179.2
127.5°	195.1	195.5	195.9	196.3	196.7	196.9	196.7	196.6	196.5	196.3	196.0
130°	205.7	206.2	206.8	207.2	207.7	207.9	207.7	207.6	207.3	207.2	206.9
132.5°	216.3	216.9	217.4	217.8	218.3	218.6	218.4	218.3	218.1	218.0	217.7
135°	232.5	232.9	233.3	233.7	234.1	234.2	234.2	234.1	234.0	234.0	233.7
137.5°	247.5	247.9	248.1	248.4	248.7	249.0	249.2	249.3	249.5	249.6	249.4
140°	257.9	258.2	258.5	258.9	259.2	259.3	259.4	259.4	259.5	259.6	259.5
142.5°	267.3	267.7	268.0	268.3	268.6	268.8	269.0	269.0	269.1	269.3	269.2
145°	282.1	282.2	282.3	282.4	282.6	282.7	282.9	283.2	283.3	283.5	283.5
147.5°	295.0	295.2	295.5	295.7	295.9	296.1	296.3	296.4	296.6	296.9	296.9
150°	303.9	304.1	304.2	304.4	304.5	304.6	304.8	304.8	305.0	305.1	305.1
152.5°	311.4	311.5	311.7	311.9	312.1	312.2	312.3	312.3	312.4	312.5	312.6
155°	323.0	323.0	323.0	323.0	323.0	323.0	323.1	323.1	323.2	323.3	323.5
157.5°	332.9	332.8	332.7	332.6	332.6	332.6	332.6	332.6	332.7	332.8	333.0
160°	339.1	339.0	338.8	338.8	338.6	338.5	338.5	338.5	338.5	338.5	338.8
162.5°	344.6	344.5	344.3	344.1	343.9	343.9	343.9	344.0	344.1	344.1	344.4
165°	351.8	351.6	351.4	351.2	351.0	350.9	350.9	350.9	350.9	350.9	351.3
167.5°	357.5	357.3	357.0	356.7	356.4	356.4	356.4	356.4	356.5	356.6	356.9
170°	360.7	360.4	360.2	360.0	359.7	359.5	359.5	359.5	359.5	359.5	360.0
172.5°	363.3	363.0	362.7	362.5	362.2	362.1	362.1	362.1	362.1	362.1	362.5
175°	365.9	365.7	365.4	365.2	364.9	364.8	364.8	364.8	364.8	364.8	365.2
177.5°	367.0	366.8	366.6	366.4	366.2	366.1	366.1	366.1	366.1	366.1	366.4
180°	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8



TEST NUMBER: P332274-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1
2.5°	767.0	768.3	769.5	770.0	769.7	769.5	769.3	769.1
5°	761.9	763.2	764.4	764.9	764.7	764.3	764.1	763.8
7.5°	751.2	751.9	752.6	752.7	752.2	751.8	751.3	750.8
10°	741.6	741.8	741.8	741.6	740.9	740.2	739.6	738.8
12.5°	729.7	729.6	729.5	729.0	728.2	727.4	726.7	725.9
15°	708.7	708.0	707.4	706.5	705.5	704.6	703.6	702.6
17.5°	683.7	682.2	680.7	679.3	677.8	676.4	674.9	673.5
20°	666.5	664.7	662.9	661.2	659.5	657.9	656.2	654.5
22.5°	648.2	645.9	643.7	641.7	640.2	638.6	637.1	635.5
25°	618.1	615.1	612.3	610.0	608.5	607.0	605.4	603.9
27.5°	585.3	581.3	577.2	574.1	571.7	569.4	567.0	564.7
30°	562.0	557.3	552.6	549.1	546.9	544.7	542.4	540.2
32.5°	539.2	533.9	528.8	525.1	522.8	520.4	518.0	515.8
35°	505.2	499.2	493.3	489.0	486.5	484.0	481.5	479.0
37.5°	468.7	461.9	455.2	450.3	447.2	444.1	441.0	437.9
40°	443.4	436.1	428.9	423.7	420.5	417.4	414.2	410.9
42.5°	419.1	411.2	403.2	397.9	395.0	392.2	389.3	386.5
45°	383.3	375.4	367.5	361.8	358.5	355.1	351.8	348.5
47.5°	346.3	337.7	329.1	323.3	320.3	317.3	314.4	311.4
50°	321.3	312.7	304.1	298.2	295.0	291.8	288.6	285.4
52.5°	297.2	288.2	279.2	273.4	270.5	267.7	264.8	262.0
55°	261.2	253.2	245.1	239.7	236.9	234.2	231.4	228.6
57.5°	225.8	218.3	210.7	205.7	203.3	201.0	198.6	196.2
60°	203.6	196.1	188.6	183.7	181.3	179.0	176.6	174.2
62.5°	181.5	174.5	167.4	162.7	160.2	157.7	155.2	152.8
65°	150.0	143.2	136.4	132.2	130.8	129.2	127.7	126.1
67.5°	120.0	114.9	109.8	106.5	104.8	103.2	101.6	100.0
70°	101.4	96.6	91.7	88.5	87.0	85.5	84.0	82.4
72.5°	84.7	80.8	76.8	74.5	73.9	73.2	72.6	71.9
75°	63.4	62.0	60.7	59.8	59.5	59.3	58.9	58.7
77.5°	47.9	47.1	46.3	45.8	45.6	45.2	45.0	44.7
80°	38.5	38.1	37.7	37.3	37.1	36.8	36.5	36.2
82.5°	29.5	29.1	28.7	28.5	28.4	28.4	28.3	28.2
85°	17.0	16.6	16.4	16.2	16.2	16.2	16.2	16.2
87.5°	7.7	7.7	7.7	7.6	7.5	7.4	7.3	7.3
90°	7.4	7.7	7.9	8.2	8.2	8.4	8.5	8.6
92.5°	11.5	11.7	11.9	12.0	11.9	11.8	11.7	11.7
95°	21.9	22.1	22.3	22.5	22.5	22.5	22.5	22.5
97.5°	33.9	34.2	34.6	34.7	34.7	34.7	34.6	34.6
100°	42.7	43.0	43.1	43.3	43.4	43.5	43.7	43.8
102.5°	52.9	53.1	53.2	53.3	53.3	53.3	53.2	53.2
105°	68.0	68.0	68.0	68.1	68.2	68.3	68.5	68.6
107.5°	84.4	84.5	84.8	84.9	84.8	84.7	84.6	84.5
110°	95.3	95.6	95.8	95.9	95.7	95.6	95.5	95.4



TEST NUMBER: P332274-930

CATALOG NUMBER: S123RDIP-S560D365U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	106.2	106.6	106.9	107.0	107.0	107.0	106.9	106.9
115°	122.9	122.9	123.0	123.0	122.9	122.9	122.8	122.7
117.5°	139.7	139.7	139.7	139.5	139.3	139.2	139.0	138.8
120°	150.8	150.7	150.7	150.6	150.5	150.3	150.3	150.1
122.5°	162.2	162.0	161.8	161.7	161.5	161.3	161.1	160.9
125°	179.0	178.7	178.5	178.2	178.0	177.7	177.4	177.2
127.5°	195.6	195.3	194.9	194.5	194.3	194.0	193.7	193.4
130°	206.7	206.4	206.1	205.8	205.4	204.9	204.5	204.0
132.5°	217.4	217.0	216.8	216.5	216.1	215.7	215.4	215.1
135°	233.4	233.2	232.9	232.8	232.6	232.4	232.4	232.2
137.5°	249.2	248.9	248.6	248.3	248.1	247.9	247.6	247.4
140°	259.4	259.4	259.3	259.1	258.6	258.2	257.7	257.3
142.5°	269.1	269.0	269.0	268.8	268.5	268.2	267.7	267.4
145°	283.4	283.3	283.2	283.1	282.8	282.6	282.3	282.1
147.5°	296.9	296.9	296.9	296.6	296.3	295.9	295.5	295.1
150°	305.1	305.1	305.1	304.9	304.5	304.2	303.8	303.4
152.5°	312.7	312.8	312.9	312.7	312.4	312.1	311.8	311.4
155°	323.8	324.0	324.3	324.2	323.8	323.3	322.9	322.4
157.5°	333.3	333.6	333.9	333.8	333.5	333.1	332.7	332.4
160°	339.2	339.5	339.8	339.8	339.6	339.3	339.1	338.8
162.5°	344.7	345.0	345.4	345.3	344.9	344.5	344.1	343.6
165°	351.7	352.0	352.5	352.5	352.0	351.6	351.1	350.7
167.5°	357.3	357.8	358.2	358.2	357.8	357.3	356.9	356.6
170°	360.4	360.9	361.3	361.3	360.9	360.4	360.0	359.5
172.5°	362.9	363.3	363.7	363.7	363.2	362.8	362.3	361.9
175°	365.5	365.9	366.3	366.2	365.8	365.3	364.9	364.4
177.5°	366.7	367.0	367.3	367.3	367.0	366.6	366.2	365.8
180°	366.8	366.8	366.8	366.8	366.8	366.8	366.8	366.8

(END OF REPORT)