

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332347-927

Luminaire Tested: **S123RDIP-S1000D805U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332347-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1000D805U927-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5307.5 lumens  
Efficiency: N/A  
Efficacy: 97.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332347-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332347-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	100	95	92	88	93	89	86	83	77	74	72	66	64	62	56	54	53	48
2	91	84	78	73	84	78	73	68	68	64	60	58	55	53	49	47	45	41
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	41	39	35
4	76	66	58	52	71	62	55	49	54	48	44	46	42	39	40	36	34	31
5	70	59	51	45	65	55	48	43	48	43	38	42	37	34	36	32	30	27
6	65	53	45	39	60	50	42	37	44	38	33	38	33	30	33	29	26	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	26	24	21
8	56	44	36	31	52	41	34	29	36	31	26	32	27	24	27	24	21	19
9	52	40	32	27	48	38	31	26	33	28	24	29	25	22	25	22	19	17
10	49	37	29	25	45	35	28	24	31	25	22	27	23	20	24	20	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14310	14310	14310
5°	14364	14166	14249
10°	14283	13988	13941
15°	14130	13661	13517
20°	13919	13252	12944
25°	13702	12792	12383
30°	13415	12263	11591
35°	13119	11730	10867
40°	12847	11105	9969
45°	12490	10488	9159
50°	12097	9786	8251
55°	11695	8983	7405
60°	11328	8125	6476
65°	10847	7195	5547
70°	10247	6039	4482
75°	9374	4754	4213
80°	8356	4209	3874
85°	7052	3730	3458



TEST NUMBER: P332347-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	124.8	2.4
10°-20°	347.3	6.5
20°-30°	500.2	9.4
30°-40°	563.4	10.6
40°-50°	539.0	10.2
50°-60°	441.4	8.3
60°-70°	297.8	5.6
70°-80°	149.8	2.8
80°-90°	42.0	0.8
90°-100°	170.3	3.2
100°-110°	482.1	9.1
110°-120°	474.3	8.9
120°-130°	378.3	7.1
130°-140°	298.3	5.6
140°-150°	222.6	4.2
150°-160°	155.2	2.9
160°-170°	91.2	1.7
170°-180°	29.7	0.6
0°-30°	972.3	18.3
0°-40°	1535.7	28.9
0°-60°	2516.0	47.4
0°-90°	3005.6	56.6
90°-120°	1126.7	21.2
90°-150°	2025.9	38.2
90°-180°	2302.0	43.4
0°-180°	5307.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1329	1329	1329	1329	1329	
5°	1329	1324	1311	1320	1319	126
15°	1268	1255	1226	1220	1213	357
25°	1154	1125	1077	1055	1043	530
35°	998	958	893	848	827	625
45°	820	770	689	629	602	633
55°	623	568	479	418	395	559
65°	426	365	282	232	218	421
75°	225	173	114	104	101	240
85°	57	34	30	28	28	64
90°	1	7	15	17	18	4
95°	21	68	367	107	72	23
105°	72	106	498	871	788	76
115°	127	158	381	835	958	126
125°	176	208	356	644	756	157
135°	207	247	350	530	612	160
145°	236	270	346	435	479	148
155°	268	289	335	381	397	123
165°	293	301	321	340	346	83
175°	305	306	308	312	312	29
180°	306	306	306	306	306	



TEST NUMBER: P332347-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4
2.5°	1333.7	1332.9	1332.2	1331.4	1330.6	1329.1	1326.8	1324.5	1322.2	1319.9	1322.0
5°	1329.4	1328.2	1327.0	1325.8	1324.6	1322.5	1319.7	1316.8	1314.0	1311.1	1313.2
7.5°	1317.1	1315.8	1314.5	1313.2	1311.9	1309.4	1305.7	1302.0	1298.2	1294.5	1295.7
10°	1306.8	1305.1	1303.4	1301.7	1300.1	1297.0	1292.8	1288.4	1284.1	1279.8	1280.1
12.5°	1292.1	1290.2	1288.4	1286.5	1284.6	1281.0	1275.8	1270.5	1265.3	1260.0	1259.8
15°	1268.0	1265.4	1262.7	1260.0	1257.4	1252.8	1246.0	1239.3	1232.6	1225.9	1224.7
17.5°	1237.5	1234.5	1231.4	1228.4	1225.3	1219.5	1210.9	1202.5	1193.9	1185.3	1182.8
20°	1215.1	1211.3	1207.4	1203.6	1199.8	1193.3	1184.2	1175.1	1166.0	1156.9	1153.8
22.5°	1190.1	1185.7	1181.3	1176.9	1172.5	1165.5	1155.7	1146.1	1136.4	1126.7	1122.8
25°	1153.7	1147.7	1141.7	1135.7	1129.7	1121.2	1110.2	1099.2	1088.1	1077.1	1072.1
27.5°	1109.5	1102.9	1096.2	1089.6	1083.0	1073.6	1061.3	1049.0	1036.7	1024.5	1017.5
30°	1079.3	1072.1	1064.9	1057.7	1050.5	1040.2	1026.8	1013.4	1000.0	986.6	978.4
32.5°	1049.1	1040.9	1032.8	1024.6	1016.5	1005.4	991.2	977.0	962.7	948.6	939.7
35°	998.4	989.8	981.1	972.6	963.9	952.1	937.3	922.4	907.6	892.7	882.4
37.5°	947.1	937.5	927.9	918.3	908.7	896.0	880.2	864.3	848.4	832.6	820.9
40°	914.3	903.8	893.2	882.6	872.1	858.3	841.4	824.3	807.3	790.3	777.8
42.5°	877.2	866.6	856.1	845.6	835.0	821.0	803.4	785.8	768.3	750.7	737.0
45°	820.5	809.7	798.9	788.1	777.4	762.8	744.3	725.9	707.4	689.0	675.3
47.5°	763.8	751.9	740.1	728.3	716.4	701.3	682.9	664.4	645.9	627.5	612.7
50°	722.4	711.1	699.9	688.6	677.3	662.0	642.6	623.2	603.8	584.4	569.5
52.5°	685.3	673.1	660.8	648.6	636.4	620.7	601.5	582.3	563.1	543.8	528.4
55°	623.2	611.5	599.7	588.0	576.2	560.2	539.8	519.4	499.1	478.7	464.9
57.5°	565.9	553.0	540.3	527.4	514.7	498.0	477.5	457.1	436.7	416.2	403.1
60°	526.2	513.0	499.8	486.6	473.4	456.9	437.0	417.2	397.3	377.4	364.4
62.5°	486.5	473.3	460.1	446.9	433.8	417.2	397.4	377.5	357.6	337.7	325.5
65°	425.9	412.7	399.5	386.3	373.2	357.3	338.6	319.9	301.2	282.5	270.8
67.5°	365.3	352.0	338.7	325.3	312.0	296.4	278.5	260.5	242.6	224.7	215.9
70°	325.6	312.7	299.8	286.8	273.9	259.0	242.2	225.5	208.7	191.9	183.5
72.5°	285.9	273.2	260.5	247.7	235.0	220.9	205.7	190.5	175.2	160.0	153.1
75°	225.4	213.8	202.3	190.8	179.4	167.0	153.8	140.6	127.5	114.3	111.9
77.5°	170.2	159.7	149.3	138.9	128.6	119.1	110.6	102.1	93.6	85.2	83.9
80°	134.8	124.9	115.1	105.3	95.5	88.1	83.0	78.0	73.0	67.9	67.2
82.5°	101.2	92.7	84.2	75.7	67.2	61.8	59.4	57.1	54.7	52.4	51.7
85°	57.1	51.9	46.6	41.4	36.0	33.0	32.3	31.6	30.9	30.2	29.7
87.5°	20.9	19.1	17.2	15.5	13.6	12.8	13.2	13.5	13.9	14.3	14.0
90°	1.3	2.5	3.7	5.5	6.8	8.1	9.9	11.8	13.6	15.4	14.9
92.5°	7.7	11.4	16.6	21.5	26.6	35.8	52.0	78.7	104.8	95.2	71.9
95°	21.1	22.9	29.7	40.2	56.3	80.5	133.2	225.5	327.0	367.3	297.9
97.5°	35.9	36.5	41.9	51.0	66.9	93.0	143.3	247.4	416.7	569.2	609.0
100°	45.9	46.4	50.8	59.5	74.3	98.5	141.8	233.5	396.4	586.5	708.5
102.5°	56.2	57.4	61.2	69.4	82.8	104.9	143.8	221.6	366.6	554.3	713.5
105°	71.9	73.7	77.4	84.8	96.6	115.8	149.2	213.0	330.1	498.0	675.7
107.5°	88.4	90.3	93.9	101.2	112.3	130.1	159.4	212.5	306.8	448.1	609.6
110°	100.4	102.2	105.3	112.1	122.6	140.0	167.9	214.9	297.9	419.9	567.9



TEST NUMBER: P332347-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	111.2	113.1	116.2	123.0	133.6	150.4	176.3	219.8	292.9	401.1	531.8
115°	127.0	129.4	133.2	139.3	149.9	166.6	190.1	227.9	291.1	380.9	488.1
117.5°	142.7	145.5	148.6	154.3	166.1	181.6	204.9	238.6	292.2	369.0	461.7
120°	153.6	155.4	158.5	164.8	176.5	192.0	214.3	246.5	294.2	363.5	447.8
122.5°	163.0	164.9	167.9	174.7	185.9	202.4	224.2	253.9	297.6	360.1	436.4
125°	176.5	177.8	181.5	188.3	200.0	216.7	238.4	265.7	302.9	355.5	421.8
127.5°	186.8	188.6	193.2	200.2	213.2	229.9	250.8	275.4	308.8	353.3	408.9
130°	193.2	195.1	200.7	208.1	221.1	237.8	258.3	281.8	312.8	351.8	402.0
132.5°	198.2	200.6	206.6	215.6	228.5	244.8	264.7	287.7	315.8	351.3	395.5
135°	206.8	209.4	216.2	225.5	238.4	255.2	274.3	295.4	320.2	350.5	387.1
137.5°	215.0	217.6	224.3	234.2	247.1	262.6	281.1	301.1	323.2	349.2	379.8
140°	220.5	223.6	229.8	239.7	252.1	267.5	285.5	304.1	325.2	348.7	375.3
142.5°	226.4	229.0	235.8	244.6	257.1	271.5	289.0	307.0	326.6	347.7	371.4
145°	236.0	237.8	243.4	252.7	263.2	277.5	293.6	310.3	327.6	346.2	366.1
147.5°	245.7	246.8	252.2	260.2	270.4	282.6	297.3	312.3	327.6	343.9	360.8
150°	252.1	252.7	257.6	265.7	274.3	285.5	299.8	312.8	327.6	341.9	357.4
152.5°	258.5	258.6	263.6	270.7	278.3	289.0	301.3	313.8	326.1	339.4	353.4
155°	268.2	268.2	271.9	278.1	284.9	293.6	304.1	314.0	324.6	335.1	347.5
157.5°	275.8	276.3	279.3	284.8	290.6	297.3	305.7	314.7	322.4	331.2	340.8
160°	281.8	281.8	284.3	289.2	293.6	299.8	307.2	314.7	321.5	328.3	336.3
162.5°	286.3	286.3	288.3	292.2	296.0	301.3	307.7	314.1	319.5	325.3	331.8
165°	292.9	292.3	293.6	296.7	299.1	303.5	308.4	312.8	316.5	320.8	325.7
167.5°	298.0	297.3	297.9	300.2	302.0	304.8	308.3	311.8	313.5	316.4	320.0
170°	301.0	299.8	300.4	302.2	303.5	304.8	307.8	310.3	311.6	313.4	316.5
172.5°	303.0	302.2	302.4	303.7	304.4	305.2	307.8	309.8	310.1	310.9	313.0
175°	305.3	304.8	304.1	305.3	305.3	305.9	307.2	308.4	307.8	307.8	309.0
177.5°	306.4	305.9	305.5	305.9	305.9	305.9	306.4	307.4	306.4	305.9	306.4
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9



TEST NUMBER: P332347-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4
2.5°	1324.1	1326.3	1328.3	1329.2	1328.8	1328.5	1328.1	1327.7
5°	1315.4	1317.6	1319.7	1320.6	1320.1	1319.6	1319.1	1318.7
7.5°	1296.9	1298.1	1299.3	1299.5	1298.6	1297.8	1297.0	1296.2
10°	1280.3	1280.6	1280.8	1280.3	1279.1	1277.9	1276.7	1275.5
12.5°	1259.6	1259.6	1259.4	1258.6	1257.3	1255.8	1254.5	1253.1
15°	1223.5	1222.3	1221.1	1219.6	1218.0	1216.3	1214.7	1213.0
17.5°	1180.3	1177.7	1175.2	1172.7	1170.2	1167.7	1165.2	1162.7
20°	1150.6	1147.6	1144.5	1141.5	1138.6	1135.7	1132.8	1130.0
22.5°	1119.0	1115.1	1111.2	1107.9	1105.3	1102.6	1099.9	1097.2
25°	1067.1	1062.0	1057.0	1053.1	1050.5	1047.9	1045.3	1042.6
27.5°	1010.5	1003.5	996.5	991.0	987.0	982.9	978.9	974.9
30°	970.3	962.1	953.9	948.0	944.1	940.3	936.4	932.6
32.5°	930.7	921.9	912.9	906.5	902.5	898.4	894.4	890.3
35°	872.1	861.8	851.5	844.2	840.0	835.6	831.3	827.0
37.5°	809.2	797.5	785.8	777.3	772.0	766.7	761.4	756.1
40°	765.4	753.0	740.5	731.5	726.0	720.5	714.9	709.5
42.5°	723.4	709.8	696.2	686.9	682.0	677.1	672.1	667.2
45°	661.6	648.0	634.3	624.6	618.9	613.1	607.4	601.7
47.5°	597.8	583.0	568.1	558.1	552.9	547.9	542.7	537.6
50°	554.7	539.8	525.0	514.8	509.3	503.7	498.3	492.7
52.5°	513.0	497.6	482.1	471.9	467.0	462.1	457.2	452.2
55°	450.9	437.0	423.1	413.8	409.0	404.2	399.4	394.6
57.5°	389.9	376.8	363.7	355.1	351.0	346.9	342.9	338.7
60°	351.5	338.6	325.6	317.1	313.1	309.0	304.9	300.8
62.5°	313.3	301.2	289.0	280.7	276.6	272.3	268.0	263.7
65°	259.0	247.2	235.5	228.3	225.7	223.1	220.5	217.8
67.5°	207.2	198.4	189.6	183.8	181.0	178.2	175.3	172.5
70°	175.2	166.8	158.4	152.9	150.2	147.6	145.0	142.4
72.5°	146.3	139.4	132.6	128.7	127.5	126.4	125.3	124.2
75°	109.5	107.1	104.7	103.3	102.8	102.3	101.8	101.3
77.5°	82.6	81.3	80.0	79.1	78.7	78.2	77.7	77.2
80°	66.5	65.8	65.0	64.5	64.0	63.5	63.0	62.5
82.5°	50.9	50.2	49.5	49.1	49.0	49.0	48.8	48.7
85°	29.2	28.8	28.3	28.0	28.0	28.0	28.0	28.0
87.5°	13.9	13.9	13.8	13.9	13.5	13.5	13.4	13.1
90°	15.4	16.1	16.7	18.0	17.3	18.0	18.6	18.0
92.5°	52.1	41.4	36.5	33.4	32.2	30.3	31.0	29.9
95°	223.0	151.1	118.3	96.0	84.2	78.7	74.3	71.9
97.5°	555.8	445.2	365.3	291.2	245.5	217.6	200.9	195.6
100°	730.2	680.0	607.6	519.6	457.1	411.9	387.7	388.3
102.5°	788.1	786.6	744.3	688.6	639.9	604.1	583.9	569.7
105°	805.2	867.0	878.8	862.8	834.2	810.7	790.9	787.8
107.5°	756.4	856.9	911.2	933.2	933.7	925.8	919.1	913.4
110°	709.8	823.7	901.7	945.2	962.4	967.4	966.1	965.0





TEST NUMBER: P332347-927

CATALOG NUMBER: S123RDIP-S1000D805U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	663.7	780.1	867.6	923.3	955.1	970.4	975.1	975.3
115°	602.6	710.3	801.5	868.9	915.4	942.6	955.1	958.1
117.5°	558.4	651.4	733.2	801.7	850.1	881.3	899.1	903.4
120°	535.1	618.7	693.1	755.6	804.5	839.2	854.1	857.8
122.5°	516.8	592.5	661.3	719.5	762.9	794.1	810.5	815.2
125°	492.3	559.9	619.3	668.9	708.5	735.8	751.2	755.6
127.5°	471.1	531.2	584.9	630.0	665.3	688.6	702.6	706.5
130°	457.7	513.4	563.6	605.7	638.6	660.8	673.8	678.8
132.5°	445.3	496.6	543.3	583.4	614.3	636.6	648.1	651.6
135°	428.6	472.5	512.8	548.1	578.5	597.1	608.2	612.5
137.5°	413.4	449.4	484.1	514.7	540.2	559.0	568.5	571.3
140°	404.4	436.0	465.7	492.3	515.9	533.2	543.2	542.6
142.5°	396.0	423.1	448.9	472.1	492.1	507.5	516.4	515.8
145°	385.9	406.3	426.1	444.1	459.5	472.5	477.5	478.7
147.5°	377.6	393.8	409.8	422.6	434.3	443.1	447.8	448.3
150°	371.6	385.9	398.9	410.6	419.9	426.7	430.5	430.5
152.5°	366.1	378.4	389.9	399.7	407.0	413.4	415.6	415.6
155°	358.0	367.9	377.2	384.6	390.1	395.1	396.4	397.0
157.5°	349.3	357.6	364.8	370.6	375.4	379.1	380.2	380.0
160°	344.4	351.2	357.4	361.7	366.1	369.7	369.7	369.2
162.5°	338.4	344.2	349.9	353.8	356.6	359.8	359.8	359.3
165°	330.7	334.5	338.8	341.9	344.4	346.8	346.2	346.2
167.5°	324.0	326.9	329.4	331.6	332.7	334.5	333.8	333.8
170°	319.6	321.5	323.9	325.2	325.7	327.0	326.4	326.4
172.5°	315.6	317.0	318.9	319.7	319.8	321.1	320.0	319.5
175°	310.3	310.9	312.1	312.1	312.1	312.8	312.1	311.6
177.5°	307.0	307.4	307.9	307.9	307.4	307.9	307.0	307.0
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9

(END OF REPORT)