

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332381-927

Luminaire Tested: **S123RDIP-S1165D1025U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332381-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D1025U927-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6717.2 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332381-927

CATALOG NUMBER: S123RDIP-S1165D1025U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332381-927

CATALOG NUMBER: S123RDIP-S1165D1025U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	108	108	108	108	99	99	99	99	84	84	84		70	70	70		58	58	58	52
1	99	94	91	87	91	87	84	81	74	72	70		62	61	59		51	50	49	44
2	90	83	77	72	83	77	72	67	66	62	58		55	52	50		46	44	42	38
3	82	73	66	60	76	68	62	56	58	53	49		49	46	43		41	38	36	32
4	75	65	57	51	70	60	53	48	52	47	42		44	40	37		37	34	31	28
5	69	58	50	44	64	54	47	42	47	41	37		40	35	32		33	30	28	24
6	64	52	44	38	59	49	41	36	42	36	32		36	32	28		30	27	24	22
7	59	47	39	34	55	44	37	32	38	33	29		33	28	25		28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25		30	26	23		25	22	20	17
9	51	39	32	27	47	37	30	25	32	27	23		28	23	20		24	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21		26	21	18		22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16527	16527	16527
5°	16590	16361	16455
10°	16497	16156	16101
15°	16319	15778	15611
20°	16076	15306	14948
25°	15824	14775	14301
30°	15493	14162	13387
35°	15152	13548	12550
40°	14838	12826	11514
45°	14425	12113	10577
50°	13971	11302	9530
55°	13508	10376	8552
60°	13082	9384	7481
65°	12528	8308	6406
70°	11833	6977	5174
75°	10821	5490	4870
80°	9651	4860	4475
85°	8151	4310	4001



TEST NUMBER: P332381-927

CATALOG NUMBER: S123RDIP-S1165D1025U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.2	2.1
10°-20°	401.2	6.0
20°-30°	577.6	8.6
30°-40°	650.7	9.7
40°-50°	622.5	9.3
50°-60°	509.7	7.6
60°-70°	343.9	5.1
70°-80°	173.0	2.6
80°-90°	48.8	0.7
90°-100°	38.7	0.6
100°-110°	184.4	2.7
110°-120°	443.0	6.6
120°-130°	564.1	8.4
130°-140°	602.7	9.0
140°-150°	563.6	8.4
150°-160°	454.6	6.8
160°-170°	293.4	4.4
170°-180°	101.1	1.5
0°-30°	1123.0	16.7
0°-40°	1773.6	26.4
0°-60°	2905.8	43.3
0°-90°	3471.5	51.7
90°-120°	666.1	9.9
90°-150°	2396.5	35.7
90°-180°	3246.0	48.3
0°-180°	6717.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1535	1535	1535	1535	1535	
5°	1535	1529	1514	1525	1523	146
15°	1464	1450	1416	1410	1401	412
25°	1332	1300	1244	1219	1204	613
35°	1153	1106	1031	979	955	721
45°	948	889	796	727	695	731
55°	720	656	553	483	456	645
65°	492	422	326	268	252	487
75°	260	200	132	120	117	278
85°	66	40	35	32	32	74
90°	1	9	19	22	24	6
95°	48	18	24	30	30	60
105°	236	240	173	41	35	250
115°	442	447	454	462	465	436
125°	623	629	633	634	636	556
135°	776	780	784	786	784	597
145°	895	900	902	904	904	560
155°	986	985	985	989	984	454
165°	1040	1038	1037	1042	1037	294
175°	1064	1061	1061	1066	1060	101
180°	1064	1064	1064	1064	1064	



TEST NUMBER: P332381-927

CATALOG NUMBER: S123RDIP-S1165D1025U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4
2.5°	1540.4	1539.4	1538.6	1537.7	1536.8	1535.0	1532.4	1529.7	1527.1	1524.4	1526.9
5°	1535.4	1534.0	1532.6	1531.2	1529.9	1527.5	1524.2	1520.8	1517.5	1514.2	1516.7
7.5°	1521.1	1519.7	1518.2	1516.7	1515.2	1512.3	1508.0	1503.6	1499.4	1495.0	1496.4
10°	1509.3	1507.3	1505.4	1503.4	1501.5	1498.0	1493.0	1488.0	1483.0	1478.1	1478.4
12.5°	1492.3	1490.2	1488.0	1485.8	1483.7	1479.6	1473.5	1467.4	1461.3	1455.2	1455.0
15°	1464.4	1461.3	1458.3	1455.2	1452.2	1446.8	1439.1	1431.3	1423.6	1415.9	1414.4
17.5°	1429.3	1425.8	1422.2	1418.6	1415.2	1408.4	1398.6	1388.7	1378.9	1369.0	1366.1
20°	1403.4	1399.0	1394.6	1390.1	1385.7	1378.2	1367.7	1357.2	1346.6	1336.2	1332.5
22.5°	1374.5	1369.4	1364.3	1359.2	1354.2	1346.0	1334.8	1323.7	1312.5	1301.2	1296.8
25°	1332.4	1325.5	1318.6	1311.6	1304.7	1294.9	1282.1	1269.5	1256.7	1244.0	1238.2
27.5°	1281.4	1273.7	1266.1	1258.5	1250.8	1239.9	1225.7	1211.6	1197.4	1183.2	1175.1
30°	1246.5	1238.2	1229.9	1221.5	1213.3	1201.3	1185.9	1170.4	1154.9	1139.4	1130.0
32.5°	1211.6	1202.2	1192.8	1183.4	1174.0	1161.1	1144.7	1128.3	1111.9	1095.6	1085.3
35°	1153.1	1143.1	1133.1	1123.2	1113.3	1099.7	1082.5	1065.4	1048.2	1031.0	1019.1
37.5°	1093.8	1082.8	1071.7	1060.6	1049.6	1034.8	1016.5	998.2	979.9	961.6	948.1
40°	1056.0	1043.8	1031.6	1019.5	1007.3	991.3	971.7	952.0	932.4	912.8	898.3
42.5°	1013.1	1000.9	988.8	976.6	964.4	948.2	927.9	907.5	887.2	867.0	851.2
45°	947.6	935.2	922.7	910.3	897.8	880.9	859.6	838.3	817.0	795.7	779.9
47.5°	882.1	868.5	854.8	841.1	827.4	809.9	788.6	767.3	746.0	724.8	707.6
50°	834.3	821.3	808.3	795.3	782.3	764.6	742.2	719.8	697.4	674.9	657.7
52.5°	791.5	777.4	763.3	749.2	735.0	716.8	694.7	672.5	650.3	628.1	610.3
55°	719.8	706.2	692.6	679.1	665.5	647.0	623.4	599.9	576.4	552.9	536.9
57.5°	653.5	638.7	623.9	609.2	594.4	575.2	551.6	527.9	504.3	480.7	465.5
60°	607.7	592.5	577.3	562.1	546.8	527.7	504.7	481.8	458.8	435.9	420.9
62.5°	561.8	546.6	531.4	516.2	501.0	481.9	458.9	435.9	413.0	390.0	376.0
65°	491.9	476.7	461.4	446.2	431.0	412.6	391.0	369.4	347.8	326.2	312.7
67.5°	421.9	406.5	391.1	375.7	360.4	342.3	321.6	300.9	280.2	259.5	249.4
70°	376.0	361.2	346.2	331.2	316.3	299.1	279.8	260.4	241.1	221.7	212.0
72.5°	330.3	315.5	300.8	286.1	271.3	255.2	237.6	220.0	202.4	184.8	176.9
75°	260.2	247.0	233.7	220.4	207.2	192.9	177.7	162.4	147.2	132.0	129.2
77.5°	196.5	184.5	172.5	160.5	148.5	137.5	127.8	118.0	108.1	98.4	96.9
80°	155.7	144.3	132.9	121.6	110.3	101.7	95.9	90.1	84.3	78.4	77.6
82.5°	116.8	107.0	97.2	87.4	77.6	71.4	68.7	65.9	63.2	60.5	59.7
85°	66.0	59.9	53.8	47.8	41.7	38.2	37.4	36.5	35.7	34.9	34.3
87.5°	24.1	21.9	19.9	17.8	15.8	14.9	15.4	15.8	16.3	16.7	16.6
90°	0.8	2.5	4.3	6.1	7.8	9.8	12.1	14.4	16.7	19.0	19.6
92.5°	14.7	14.2	13.7	13.2	12.8	13.4	15.1	16.8	18.5	20.3	21.4
95°	48.2	41.0	33.8	26.6	19.4	16.8	18.7	20.7	22.6	24.5	25.7
97.5°	97.0	93.7	90.5	87.2	84.0	76.0	63.5	50.8	38.1	25.4	26.9
100°	133.6	137.1	140.7	144.2	147.7	135.7	108.3	80.9	53.5	26.1	27.5
102.5°	175.4	177.9	180.5	183.0	185.5	171.8	141.9	111.9	82.0	52.0	47.7
105°	235.6	237.6	239.5	241.5	243.4	236.4	220.6	204.8	189.0	173.2	142.0
107.5°	299.2	300.8	302.3	303.9	305.4	307.4	309.9	312.4	314.9	317.4	294.6
110°	341.6	343.0	344.4	345.8	347.2	348.9	350.8	352.8	354.7	356.6	350.8



TEST NUMBER: P332381-927

CATALOG NUMBER: S123RDIP-S1165D1025U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	382.1	383.3	384.6	385.9	387.1	388.7	390.7	392.6	394.5	396.5	396.6
115°	442.0	443.1	444.1	445.2	446.2	447.6	449.1	450.7	452.3	453.8	455.7
117.5°	500.0	501.4	502.6	504.0	505.3	506.3	507.1	507.9	508.7	509.5	511.0
120°	536.1	537.7	539.2	540.8	542.4	543.5	544.0	544.5	545.1	545.6	547.0
122.5°	572.8	574.1	575.4	576.7	578.0	579.0	579.6	580.4	581.0	581.6	582.7
125°	623.1	624.5	625.9	627.3	628.7	629.8	630.5	631.1	631.8	632.6	633.0
127.5°	671.8	673.2	674.6	676.0	677.4	678.5	679.4	680.2	681.0	681.9	682.5
130°	702.2	703.5	705.0	706.4	707.8	708.8	709.6	710.3	710.9	711.6	712.3
132.5°	731.3	732.7	734.0	735.5	736.9	737.8	738.4	738.9	739.6	740.1	740.8
135°	775.7	776.7	777.8	778.9	779.9	780.8	781.5	782.2	782.9	783.6	784.1
137.5°	813.7	815.0	816.3	817.7	819.0	819.8	820.2	820.6	821.0	821.4	822.2
140°	838.9	840.0	841.1	842.1	843.2	844.0	844.5	845.0	845.6	846.1	846.8
142.5°	862.4	863.4	864.4	865.5	866.6	867.4	867.9	868.4	868.9	869.5	870.1
145°	895.1	896.4	897.5	898.8	900.0	900.8	901.2	901.5	901.8	902.2	902.5
147.5°	925.9	926.8	927.6	928.4	929.2	929.7	930.1	930.4	930.8	931.1	931.5
150°	944.9	945.5	945.9	946.5	947.0	947.5	947.8	948.2	948.5	948.9	949.2
152.5°	961.9	962.3	962.5	962.7	963.0	963.2	963.4	963.6	963.8	964.0	964.6
155°	986.0	985.6	985.3	985.0	984.6	984.5	984.7	984.8	985.1	985.2	986.1
157.5°	1004.6	1004.6	1004.6	1004.6	1004.6	1004.4	1004.2	1004.1	1003.9	1003.7	1004.8
160°	1016.1	1015.9	1015.7	1015.6	1015.3	1015.2	1015.0	1014.9	1014.6	1014.5	1015.6
162.5°	1026.8	1026.4	1025.9	1025.5	1025.0	1024.7	1024.5	1024.3	1024.1	1024.0	1025.2
165°	1039.8	1039.3	1038.7	1038.2	1037.7	1037.4	1037.1	1037.0	1036.8	1036.6	1038.0
167.5°	1049.9	1049.2	1048.5	1047.8	1047.1	1046.7	1046.7	1046.7	1046.7	1046.7	1048.1
170°	1055.6	1054.9	1054.2	1053.5	1052.8	1052.4	1052.4	1052.4	1052.4	1052.4	1053.8
172.5°	1059.4	1058.6	1057.7	1056.9	1056.1	1055.7	1055.8	1056.0	1056.1	1056.2	1057.6
175°	1064.3	1063.4	1062.6	1061.7	1060.8	1060.4	1060.6	1060.8	1061.0	1061.1	1062.4
177.5°	1065.6	1064.9	1064.1	1063.4	1062.8	1062.5	1062.6	1062.8	1062.9	1063.0	1064.1
180°	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3



TEST NUMBER: P332381-927

CATALOG NUMBER: S123RDIP-S1165D1025U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4
2.5°	1529.3	1531.8	1534.1	1535.2	1534.7	1534.3	1533.8	1533.3
5°	1519.2	1521.7	1524.2	1525.1	1524.6	1524.0	1523.4	1522.9
7.5°	1497.8	1499.2	1500.6	1500.8	1499.8	1498.9	1497.9	1497.0
10°	1478.7	1478.9	1479.2	1478.7	1477.3	1475.9	1474.5	1473.1
12.5°	1454.8	1454.7	1454.5	1453.7	1452.1	1450.4	1448.8	1447.2
15°	1413.1	1411.7	1410.3	1408.7	1406.7	1404.8	1402.8	1400.9
17.5°	1363.2	1360.2	1357.2	1354.4	1351.5	1348.6	1345.8	1342.8
20°	1329.0	1325.3	1321.8	1318.3	1314.9	1311.6	1308.4	1305.0
22.5°	1292.3	1287.9	1283.3	1279.5	1276.4	1273.4	1270.3	1267.2
25°	1232.4	1226.5	1220.8	1216.3	1213.3	1210.2	1207.2	1204.1
27.5°	1167.0	1159.0	1150.9	1144.5	1139.9	1135.3	1130.6	1125.9
30°	1120.5	1111.2	1101.8	1094.9	1090.4	1086.0	1081.6	1077.1
32.5°	1075.0	1064.7	1054.4	1046.9	1042.3	1037.6	1033.0	1028.3
35°	1007.3	995.4	983.5	975.0	970.0	965.0	960.0	955.1
37.5°	934.5	921.1	907.5	897.7	891.6	885.4	879.3	873.1
40°	884.0	869.6	855.2	844.9	838.4	832.1	825.8	819.4
42.5°	835.5	819.8	804.1	793.4	787.7	782.0	776.3	770.6
45°	764.1	748.4	732.6	721.4	714.8	708.1	701.5	694.8
47.5°	690.4	673.3	656.1	644.6	638.7	632.7	626.8	620.9
50°	640.6	623.4	606.3	594.5	588.2	581.8	575.4	569.1
52.5°	592.5	574.6	556.8	545.0	539.3	533.7	528.0	522.3
55°	520.8	504.7	488.7	477.9	472.4	466.8	461.3	455.7
57.5°	450.4	435.1	420.0	410.0	405.4	400.7	395.9	391.3
60°	405.9	391.0	376.0	366.2	361.6	356.8	352.1	347.5
62.5°	361.9	347.8	333.7	324.3	319.3	314.4	309.5	304.6
65°	299.1	285.6	272.0	263.7	260.7	257.6	254.6	251.5
67.5°	239.2	229.1	219.0	212.3	209.1	205.7	202.5	199.2
70°	202.2	192.6	182.9	176.6	173.5	170.5	167.4	164.4
72.5°	169.0	161.1	153.1	148.5	147.3	146.0	144.7	143.5
75°	126.4	123.7	120.9	119.3	118.7	118.2	117.6	117.1
77.5°	95.4	93.9	92.4	91.3	90.8	90.2	89.7	89.1
80°	76.8	76.0	75.1	74.5	73.9	73.4	72.8	72.2
82.5°	58.9	58.1	57.2	56.7	56.6	56.5	56.4	56.3
85°	33.7	33.2	32.6	32.4	32.4	32.4	32.4	32.4
87.5°	16.6	16.5	16.4	16.3	16.2	16.0	15.8	15.7
90°	20.4	21.1	21.8	22.3	22.7	23.1	23.4	23.7
92.5°	22.5	23.6	24.7	25.4	25.6	25.8	26.1	26.2
95°	26.9	28.2	29.5	30.0	30.0	30.0	30.0	30.0
97.5°	28.3	29.7	31.1	31.8	32.1	32.2	32.4	32.6
100°	28.9	30.3	31.7	32.5	32.7	32.9	33.0	33.2
102.5°	43.3	39.0	34.6	32.6	32.9	33.2	33.5	33.8
105°	111.0	79.9	48.8	33.4	33.7	34.1	34.5	34.8
107.5°	271.8	249.0	226.2	203.0	179.6	156.1	132.7	109.2
110°	345.0	339.2	333.4	318.0	292.8	267.7	242.6	217.5



TEST NUMBER: P332381-927

CATALOG NUMBER: S123RDIP-S1165D1025U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	396.6	396.8	396.9	394.3	389.0	383.7	378.3	373.0
115°	457.4	459.1	460.9	462.2	462.8	463.5	464.2	464.9
117.5°	512.4	513.7	515.2	515.9	516.1	516.2	516.3	516.5
120°	548.4	549.8	551.2	551.9	551.9	551.9	551.9	551.9
122.5°	583.6	584.6	585.6	586.1	586.3	586.5	586.5	586.7
125°	633.3	633.6	634.0	634.3	634.7	635.0	635.4	635.7
127.5°	683.0	683.6	684.1	684.3	683.9	683.6	683.2	682.9
130°	713.0	713.8	714.5	714.6	714.3	713.9	713.6	713.2
132.5°	741.5	742.2	742.9	743.0	742.5	742.0	741.6	741.1
135°	784.7	785.2	785.7	785.7	785.2	784.7	784.1	783.6
137.5°	823.1	823.9	824.7	825.0	824.7	824.3	823.9	823.6
140°	847.5	848.2	848.9	849.1	848.7	848.3	848.0	847.6
142.5°	870.6	871.2	871.7	871.7	871.2	870.8	870.3	869.8
145°	902.9	903.2	903.6	903.8	903.8	903.8	903.8	903.8
147.5°	931.8	932.2	932.6	932.3	931.5	930.7	929.9	929.1
150°	949.6	949.9	950.3	950.1	949.7	949.1	948.6	948.1
152.5°	965.3	965.9	966.5	966.5	965.7	964.9	964.1	963.2
155°	987.0	987.9	988.7	988.6	987.6	986.6	985.5	984.4
157.5°	1005.8	1006.9	1008.0	1007.8	1006.4	1005.0	1003.7	1002.3
160°	1016.6	1017.6	1018.7	1018.6	1017.4	1016.1	1014.9	1013.7
162.5°	1026.4	1027.5	1028.7	1028.8	1027.7	1026.6	1025.6	1024.5
165°	1039.4	1040.8	1042.3	1042.4	1041.1	1039.9	1038.6	1037.4
167.5°	1049.6	1051.0	1052.3	1052.3	1051.0	1049.6	1048.1	1046.7
170°	1055.3	1056.7	1058.0	1058.0	1056.7	1055.3	1053.8	1052.4
172.5°	1059.1	1060.4	1061.8	1061.8	1060.3	1058.7	1057.2	1055.6
175°	1063.6	1064.9	1066.0	1066.0	1064.5	1063.2	1061.8	1060.3
177.5°	1065.2	1066.4	1067.5	1067.4	1066.0	1064.6	1063.2	1061.8
180°	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3

(END OF REPORT)