

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832347

Luminaire Tested: S123RDIP-S775D1195U930-4F0-1E-UDD-G

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P832347  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S775D1195U930-4F0-1E-UDD-G  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 1195 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6587.8 lumens  
Efficiency: N/A  
Efficacy: 115.8 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P832347

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-G

### Luminous Intensity Polar Plot





TEST NUMBER: P832347

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-G

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41				
1	96	92	89	86	88	84	81	79	70	67	66	56	54	53	43	42	42	36				
2	88	81	76	71	80	75	70	66	62	58	55	50	48	46	39	37	36	31				
3	81	72	65	60	74	66	60	56	55	51	47	45	42	39	35	33	32	27				
4	75	64	57	51	68	59	53	48	49	45	41	40	37	34	32	30	28	24				
5	69	58	50	45	63	53	47	42	45	40	36	37	33	30	29	27	25	22				
6	64	52	45	39	58	48	41	37	41	36	32	33	30	27	27	24	22	19				
7	59	47	40	35	54	44	37	33	37	32	28	31	27	24	25	22	20	18				
8	55	43	36	31	50	40	34	29	34	29	25	28	25	22	23	20	18	16				
9	51	40	33	28	47	37	31	26	31	27	23	26	23	20	21	19	17	15				
10	48	37	30	25	44	34	28	24	29	24	21	24	21	18	20	18	16	14				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	21909	21909	21909	21909	21909
5°	26014	25184	22047	17822	16546
10°	23569	25580	21936	14279	12249
15°	16227	21933	21704	11671	9690
20°	11290	16887	21269	9841	8517
25°	8603	12870	20635	8747	7849
30°	7489	10289	19842	8121	7271
35°	6875	8679	18718	7594	6744
40°	6274	7751	17249	7076	6261
45°	5666	7089	15664	6587	5780
50°	5143	6541	13793	6107	5184
55°	4650	6005	11995	5637	4448
60°	4168	5462	10419	5119	4204
65°	3846	4847	8970	4602	3976
70°	3125	4189	7827	4164	3229
75°	2741	3331	6629	3452	2845
80°	2486	2820	5430	2895	2690
85°	2272	2470	4125	2631	2470

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 16527 cd/sqm



TEST NUMBER: P832347

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-G

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	185.5	2.8
10°-20°	429.3	6.5
20°-30°	492.6	7.5
30°-40°	485.5	7.4
40°-50°	428.1	6.5
50°-60°	329.4	5.0
60°-70°	216.5	3.3
70°-80°	105.2	1.6
80°-90°	29.1	0.4
90°-100°	44.9	0.7
100°-110°	217.3	3.3
110°-120°	532.6	8.1
120°-130°	676.2	10.3
130°-140°	722.4	11.0
140°-150°	675.5	10.3
150°-160°	544.9	8.3
160°-170°	351.6	5.3
170°-180°	121.2	1.8
0°-30°	1107.4	16.8
0°-40°	1592.9	24.2
0°-60°	2350.4	35.7
0°-90°	2701.1	41.0
90°-120°	794.9	12.1
90°-150°	2869.0	43.6
90°-180°	3887.0	59.0
0°-180°	6587.8	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2035	2035	2035	2035	2035	
5°	2408	2331	2040	1649	1531	220
15°	1456	1968	1948	1047	870	411
25°	724	1084	1737	736	661	342
35°	523	660	1424	578	513	326
45°	372	466	1029	433	380	289
55°	248	320	639	300	237	222
65°	151	190	352	181	156	148
75°	66	80	159	83	68	71
85°	18	20	33	21	20	20
90°	28	23	1	23	28	13
95°	36	29	58	29	36	30
105°	42	207	282	207	42	87
115°	557	544	530	544	557	524
125°	762	758	746	758	762	681
135°	939	939	929	939	939	724
145°	1083	1081	1072	1081	1083	676
155°	1179	1180	1181	1180	1179	544
165°	1243	1242	1246	1242	1243	351
175°	1270	1271	1275	1271	1270	121
180°	1275	1275	1275	1275	1275	



TEST NUMBER: P832347

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2035.4	2035.4	2035.4	2035.4	2035.4	2035.4	2035.4	2035.4	2035.4	2035.4	2035.4
2.5°	2255.7	2248.6	2241.5	2239.4	2237.3	2230.6	2224.0	2208.9	2193.9	2178.5	2163.0
5°	2407.6	2408.4	2409.2	2407.1	2405.1	2396.3	2387.5	2369.2	2350.8	2330.8	2310.8
7.5°	2360.8	2374.2	2387.5	2390.0	2392.5	2399.2	2405.9	2401.7	2397.5	2390.0	2382.5
10°	2156.4	2155.5	2154.7	2169.7	2184.7	2229.4	2274.0	2297.0	2319.9	2340.4	2360.8
12.5°	1822.6	1823.8	1825.1	1874.3	1923.5	1965.7	2007.8	2066.2	2124.7	2187.7	2250.7
15°	1456.2	1476.7	1497.1	1540.9	1584.7	1648.2	1711.6	1790.0	1868.5	1968.2	2067.9
17.5°	1195.9	1204.6	1213.4	1255.5	1297.7	1357.7	1417.8	1506.7	1595.6	1724.1	1852.6
20°	985.6	993.5	1001.4	1031.9	1062.3	1119.9	1177.5	1262.2	1346.9	1474.2	1601.4
22.5°	822.8	838.3	853.7	874.1	894.6	936.3	978.0	1064.4	1150.8	1266.8	1382.8
25°	724.4	731.4	738.5	756.1	773.6	813.6	853.7	910.9	968.0	1083.6	1199.2
27.5°	657.6	659.7	661.8	674.7	687.6	713.5	739.4	792.4	845.4	940.5	1035.6
30°	602.5	606.3	610.0	620.0	630.1	648.8	667.6	705.2	742.7	827.8	913.0
32.5°	560.0	562.0	564.1	572.5	580.8	594.6	608.4	638.0	667.6	732.7	797.8
35°	523.2	523.7	524.1	530.3	536.6	549.9	563.3	587.9	612.5	660.5	708.5
37.5°	481.5	484.4	487.4	491.9	496.5	508.2	519.9	539.9	560.0	599.6	639.2
40°	446.5	449.0	451.5	456.9	462.3	471.5	480.7	499.0	517.4	551.6	585.8
42.5°	411.4	413.1	414.8	420.2	425.6	436.9	448.1	462.7	477.3	505.7	534.1
45°	372.2	376.4	380.5	386.4	392.2	401.8	411.4	426.4	441.5	465.7	489.9
47.5°	339.6	341.7	343.8	348.8	353.8	365.5	377.2	390.6	403.9	426.4	449.0
50°	307.1	307.9	308.8	313.4	317.9	328.4	338.8	354.2	369.7	390.6	411.4
52.5°	276.2	278.3	280.4	285.0	289.6	296.7	303.8	319.6	335.5	355.9	376.4
55°	247.8	249.1	250.4	253.7	257.0	265.4	273.7	287.5	301.3	320.0	338.8
57.5°	221.1	222.8	224.5	227.0	229.5	237.0	244.5	256.6	268.7	287.5	306.3
60°	193.6	195.7	197.8	200.7	203.6	209.5	215.3	226.2	237.0	253.7	270.4
62.5°	173.6	174.0	174.4	176.9	179.4	183.6	187.8	196.5	205.3	222.0	238.7
65°	151.0	152.3	153.5	154.8	156.1	159.4	162.7	170.2	177.8	190.3	202.8
67.5°	127.7	128.9	130.2	132.3	134.4	137.3	140.2	145.2	150.2	161.9	173.6
70°	99.3	99.3	99.3	102.6	106.0	111.0	116.0	119.8	123.5	133.1	142.7
72.5°	80.9	81.4	81.8	82.2	82.6	85.5	88.5	94.7	101.0	106.8	112.7
75°	65.9	66.3	66.8	67.2	67.6	68.4	69.3	71.4	73.4	80.1	86.8
77.5°	52.6	53.0	53.4	53.8	54.2	55.1	55.9	56.7	57.6	60.1	62.6
80°	40.1	40.5	40.9	41.3	41.7	42.1	42.6	43.4	44.2	45.5	46.7
82.5°	29.2	29.2	29.2	29.2	29.2	30.0	30.9	30.9	30.9	31.7	32.5
85°	18.4	18.4	18.4	18.8	19.2	19.2	19.2	19.6	20.0	20.0	20.0
87.5°	8.3	7.9	7.5	7.9	8.3	8.3	8.3	8.8	9.2	9.2	9.2
90°	28.4	28.0	27.6	27.2	26.7	26.1	25.3	24.4	23.6	22.7	20.0
92.5°	32.2	32.0	31.8	31.6	31.4	30.5	29.0	27.6	26.1	24.6	22.7
95°	36.0	36.0	36.0	36.0	36.0	35.3	33.8	32.3	30.8	29.4	27.0
97.5°	38.8	38.6	38.4	38.2	38.0	37.0	35.4	33.7	32.0	30.3	41.0
100°	39.8	39.6	39.4	39.2	38.9	38.0	36.3	34.6	32.9	31.3	64.1
102.5°	40.7	40.3	39.9	39.5	39.0	42.3	49.3	56.2	63.1	70.1	106.7
105°	41.7	41.3	40.8	40.4	40.0	58.4	95.7	132.9	170.2	207.4	226.4
107.5°	98.5	126.1	153.7	181.2	208.8	238.8	271.2	303.6	336.1	368.5	365.3
110°	260.5	290.6	320.7	350.8	380.9	399.4	406.4	413.3	420.3	427.2	424.9



TEST NUMBER: P832347

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	493.5	493.9	494.3	494.8	495.2	494.4	492.6	490.7	488.8	486.9	484.6
115°	557.0	556.1	555.3	554.4	553.6	552.1	550.0	547.9	545.8	543.7	541.8
117.5°	608.1	607.9	607.7	607.5	607.3	606.3	604.6	603.0	601.3	599.6	598.5
120°	661.2	661.2	661.2	661.2	661.2	660.3	658.6	657.0	655.3	653.6	653.0
122.5°	713.3	713.0	712.8	712.6	712.4	711.8	710.7	709.7	708.6	707.6	706.7
125°	761.6	761.1	760.7	760.3	759.9	759.5	759.0	758.6	758.2	757.8	756.9
127.5°	808.9	809.3	809.8	810.2	810.6	810.5	809.9	809.2	808.6	808.0	806.9
130°	854.4	854.8	855.2	855.7	856.1	855.9	855.0	854.2	853.3	852.5	851.7
132.5°	896.1	896.7	897.3	898.0	898.6	898.5	897.7	896.8	896.0	895.1	894.5
135°	938.7	939.3	940.0	940.6	941.2	941.2	940.6	940.0	939.3	938.7	937.9
137.5°	979.4	979.8	980.3	980.7	981.1	980.8	979.7	978.7	977.6	976.6	976.2
140°	1015.4	1015.8	1016.3	1016.7	1017.1	1016.9	1016.1	1015.2	1014.4	1013.5	1012.9
142.5°	1048.6	1049.2	1049.8	1050.5	1051.1	1051.1	1050.5	1049.8	1049.2	1048.6	1047.9
145°	1082.7	1082.7	1082.7	1082.7	1082.7	1082.5	1082.0	1081.6	1081.2	1080.8	1080.4
147.5°	1107.3	1108.4	1109.4	1110.5	1111.5	1111.8	1111.4	1111.0	1110.6	1110.1	1109.7
150°	1135.7	1136.4	1137.0	1137.6	1138.2	1138.3	1137.9	1137.5	1137.1	1136.7	1136.2
152.5°	1158.5	1159.5	1160.6	1161.6	1162.7	1162.8	1161.9	1161.1	1160.2	1159.4	1159.2
155°	1179.3	1180.6	1181.8	1183.1	1184.3	1184.4	1183.4	1182.3	1181.3	1180.2	1180.0
157.5°	1197.3	1199.0	1200.7	1202.3	1204.0	1204.2	1203.0	1201.7	1200.4	1199.2	1199.4
160°	1214.3	1215.8	1217.3	1218.8	1220.2	1220.3	1219.1	1217.8	1216.5	1215.3	1215.5
162.5°	1230.4	1231.7	1233.0	1234.2	1235.5	1235.4	1233.9	1232.4	1231.0	1229.5	1229.7
165°	1242.8	1244.2	1245.7	1247.2	1248.6	1248.5	1246.9	1245.2	1243.5	1241.8	1242.0
167.5°	1252.2	1253.9	1255.6	1257.3	1259.0	1259.0	1257.3	1255.6	1253.9	1252.2	1252.2
170°	1260.8	1262.4	1264.1	1265.8	1267.5	1267.5	1265.8	1264.1	1262.4	1260.8	1260.8
172.5°	1265.5	1267.4	1269.3	1271.2	1273.1	1273.2	1271.5	1269.8	1268.1	1266.4	1266.2
175°	1270.2	1271.9	1273.6	1275.3	1277.0	1277.1	1275.6	1274.1	1272.6	1271.2	1271.0
177.5°	1271.2	1273.3	1275.4	1277.5	1279.6	1279.8	1278.1	1276.4	1274.7	1273.1	1272.9
180°	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0



TEST NUMBER: P832347

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2035.4	2035.4	2035.4	2035.4	2035.4	2035.4	2035.4	2035.4	2035.4	2035.4	2035.4
2.5°	2161.0	2158.9	2138.8	2118.8	2099.2	2079.6	2065.0	2050.4	2025.8	2001.2	1985.7
5°	2294.9	2279.0	2247.3	2215.6	2168.1	2120.5	2080.4	2040.4	1989.5	1938.6	1896.0
7.5°	2369.6	2356.7	2318.3	2279.9	2216.9	2153.9	2091.3	2028.7	1953.6	1878.5	1814.2
10°	2371.7	2382.5	2350.8	2319.1	2248.2	2177.2	2092.1	2007.0	1906.0	1805.0	1722.0
12.5°	2297.4	2344.1	2337.5	2330.8	2258.6	2186.4	2082.9	1979.5	1855.5	1731.6	1627.7
15°	2158.5	2249.0	2275.7	2302.4	2242.7	2183.1	2065.4	1947.7	1802.1	1656.5	1537.2
17.5°	1979.5	2106.3	2176.8	2247.3	2203.9	2160.5	2031.6	1902.7	1738.7	1574.7	1445.0
20°	1767.5	1933.6	2044.1	2154.7	2138.8	2123.0	1989.9	1856.8	1679.9	1503.0	1362.3
22.5°	1558.0	1733.3	1886.0	2038.7	2055.0	2071.3	1936.9	1802.5	1608.9	1415.3	1272.2
25°	1377.4	1555.5	1737.4	1919.4	1956.1	1992.8	1865.1	1737.4	1536.7	1336.1	1193.8
27.5°	1205.0	1374.4	1574.7	1775.0	1841.8	1908.5	1791.7	1674.9	1465.8	1256.8	1114.9
30°	1064.4	1215.9	1420.3	1624.8	1717.8	1810.9	1703.7	1596.4	1389.0	1181.7	1042.7
32.5°	933.4	1069.0	1274.3	1479.6	1587.7	1695.7	1603.1	1510.5	1311.0	1111.6	974.3
35°	829.9	951.3	1142.9	1334.4	1455.4	1576.4	1500.4	1424.5	1229.7	1034.8	905.0
37.5°	741.0	842.9	1022.7	1202.5	1331.0	1459.6	1396.1	1332.7	1149.5	966.4	843.7
40°	667.6	749.4	916.7	1084.0	1210.0	1336.1	1281.8	1227.6	1063.6	899.6	784.9
42.5°	604.6	675.1	825.3	975.5	1091.1	1206.7	1170.8	1134.9	986.4	837.8	731.4
45°	549.1	608.4	740.6	872.9	979.3	1085.7	1057.3	1029.0	900.9	772.8	675.1
47.5°	499.9	550.8	668.9	786.9	882.5	978.0	951.8	925.5	819.5	713.5	624.6
50°	454.8	498.2	596.7	695.1	781.1	867.1	845.4	823.7	736.0	648.4	571.6
52.5°	412.2	448.1	536.6	625.0	694.3	763.6	746.9	730.2	662.6	595.0	525.3
55°	371.8	404.7	479.4	554.1	613.4	672.6	655.9	639.2	586.7	534.1	472.7
57.5°	335.1	363.8	424.3	484.9	532.0	579.1	571.2	563.3	519.5	475.7	425.2
60°	296.3	322.1	374.3	426.4	464.4	502.4	493.2	484.0	452.7	421.4	378.0
62.5°	261.6	284.6	326.3	368.0	398.9	429.8	423.1	416.4	392.6	368.9	333.0
65°	225.3	247.8	281.6	315.4	339.6	363.8	358.0	352.2	334.2	316.3	287.5
67.5°	192.4	211.1	240.3	269.5	285.8	302.1	298.8	295.4	281.6	267.9	245.3
70°	159.0	175.2	199.4	223.6	234.9	246.2	247.4	248.7	236.2	223.6	207.0
72.5°	125.6	138.5	161.1	183.6	192.4	201.1	200.7	200.3	192.8	185.3	170.2
75°	96.4	106.0	123.5	141.0	148.5	156.1	157.7	159.4	152.3	145.2	136.9
77.5°	69.3	75.9	89.3	102.6	111.0	119.3	120.2	121.0	117.7	114.3	106.4
80°	48.8	50.9	59.3	67.6	76.4	85.1	86.4	87.6	84.3	80.9	75.9
82.5°	33.8	35.0	38.0	40.9	48.0	55.1	56.7	58.4	56.7	55.1	49.7
85°	20.4	20.9	22.1	23.4	26.7	30.0	31.7	33.4	32.5	31.7	28.8
87.5°	9.2	9.2	9.6	10.0	10.8	11.7	13.8	15.9	14.6	13.4	12.1
90°	17.3	14.5	11.8	9.4	7.3	5.2	3.1	0.9	3.1	5.2	7.3
92.5°	20.8	18.9	17.0	16.7	18.0	19.3	20.5	21.8	20.5	19.3	18.0
95°	24.7	22.4	20.1	23.3	31.9	40.5	49.2	57.8	49.2	40.5	31.9
97.5°	51.8	62.5	73.3	81.6	87.5	93.4	99.2	105.1	99.2	93.4	87.5
100°	96.9	129.8	162.6	176.9	172.7	168.5	164.3	160.1	164.3	168.5	172.7
102.5°	143.3	180.0	216.6	233.5	230.8	228.1	225.3	222.6	225.3	228.1	230.8
105°	245.3	264.3	283.2	291.5	289.2	286.9	284.6	282.3	284.6	286.9	289.2
107.5°	362.2	359.0	355.8	353.3	351.4	349.5	347.6	345.7	347.6	349.5	351.4
110°	422.6	420.3	417.9	415.9	414.3	412.6	410.9	409.2	410.9	412.6	414.3





TEST NUMBER: P832347

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	482.2	479.9	477.6	475.7	474.2	472.8	471.3	469.8	471.3	472.8	474.2
115°	539.9	538.0	536.1	534.5	533.3	532.0	530.8	529.5	530.8	532.0	533.3
117.5°	597.5	596.4	595.4	594.1	592.6	591.2	589.7	588.2	589.7	591.2	592.6
120°	652.3	651.7	651.1	649.8	647.9	646.0	644.1	642.2	644.1	646.0	647.9
122.5°	705.9	705.0	704.2	703.0	701.6	700.1	698.6	697.2	698.6	700.1	701.6
125°	756.1	755.3	754.4	753.1	751.5	749.8	748.1	746.4	748.1	749.8	751.5
127.5°	805.9	804.8	803.8	802.4	800.7	799.0	797.4	795.7	797.4	799.0	800.7
130°	850.8	850.0	849.1	847.9	846.2	844.5	842.8	841.1	842.8	844.5	846.2
132.5°	893.9	893.2	892.6	891.4	889.8	888.1	886.4	884.7	886.4	888.1	889.8
135°	937.0	936.2	935.3	934.3	933.0	931.8	930.5	929.2	930.5	931.8	933.0
137.5°	975.7	975.3	974.9	973.8	972.2	970.5	968.8	967.1	968.8	970.5	972.2
140°	1012.3	1011.6	1011.0	1010.1	1008.8	1007.5	1006.3	1005.0	1006.3	1007.5	1008.8
142.5°	1047.3	1046.7	1046.0	1045.1	1043.8	1042.6	1041.3	1040.0	1041.3	1042.6	1043.8
145°	1079.9	1079.5	1079.1	1078.1	1076.7	1075.2	1073.7	1072.3	1073.7	1075.2	1076.7
147.5°	1109.3	1108.9	1108.5	1107.7	1106.7	1105.6	1104.6	1103.5	1104.6	1105.6	1106.7
150°	1135.8	1135.4	1135.0	1134.5	1133.8	1133.2	1132.6	1131.9	1132.6	1133.2	1133.8
152.5°	1159.0	1158.8	1158.6	1158.3	1158.1	1157.9	1157.7	1157.5	1157.7	1157.9	1158.1
155°	1179.8	1179.6	1179.4	1179.5	1179.9	1180.3	1180.8	1181.2	1180.8	1180.3	1179.9
157.5°	1199.6	1199.8	1200.0	1200.1	1200.1	1200.1	1200.1	1200.1	1200.1	1200.1	1200.1
160°	1215.7	1215.9	1216.1	1216.3	1216.5	1216.8	1217.0	1217.2	1217.0	1216.8	1216.5
162.5°	1229.9	1230.1	1230.3	1230.8	1231.4	1232.0	1232.7	1233.3	1232.7	1232.0	1231.4
165°	1242.2	1242.4	1242.6	1243.1	1243.7	1244.3	1245.0	1245.6	1245.0	1244.3	1243.7
167.5°	1252.2	1252.2	1252.2	1252.6	1253.5	1254.3	1255.2	1256.0	1255.2	1254.3	1253.5
170°	1260.8	1260.8	1260.8	1261.2	1262.0	1262.9	1263.7	1264.5	1263.7	1262.9	1262.0
172.5°	1266.0	1265.8	1265.6	1266.0	1267.1	1268.1	1269.2	1270.2	1269.2	1268.1	1267.1
175°	1270.8	1270.5	1270.3	1270.8	1271.8	1272.9	1273.9	1275.0	1273.9	1272.9	1271.8
177.5°	1272.6	1272.4	1272.2	1272.6	1273.7	1274.7	1275.8	1276.9	1275.8	1274.7	1273.7
180°	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0



TEST NUMBER: P832347

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2035.4	2035.4	2035.4	2035.4	2035.4	2035.4	2035.4	2035.4	2035.4	2035.4	2035.4
2.5°	1970.3	1946.5	1922.7	1905.6	1888.5	1867.2	1845.9	1845.1	1844.3	1828.4	1812.6
5°	1853.4	1812.1	1770.8	1730.4	1689.9	1649.4	1608.9	1599.8	1590.6	1576.8	1563.0
7.5°	1750.0	1684.0	1618.1	1566.4	1514.6	1474.2	1433.7	1406.1	1378.6	1357.3	1336.1
10°	1639.0	1557.2	1475.4	1412.8	1350.2	1306.4	1262.6	1230.9	1199.2	1184.2	1169.1
12.5°	1523.8	1434.9	1346.1	1284.7	1223.4	1170.8	1118.2	1089.5	1060.7	1039.8	1018.9
15°	1417.8	1322.3	1226.7	1161.6	1096.5	1047.3	998.1	969.3	940.5	919.6	898.8
17.5°	1315.2	1218.8	1122.4	1056.5	990.6	945.9	901.3	873.3	845.4	832.4	819.5
20°	1221.7	1124.5	1027.3	965.1	902.9	859.1	815.3	800.3	785.3	773.2	761.1
22.5°	1129.1	1035.6	942.2	882.5	822.8	791.1	759.4	747.3	735.2	726.0	716.8
25°	1051.5	958.4	865.4	813.2	761.1	736.5	711.8	703.9	696.0	686.8	677.6
27.5°	973.0	884.6	796.1	754.4	712.7	692.6	672.6	662.6	652.6	645.1	637.6
30°	903.8	822.0	740.2	705.6	670.9	653.4	635.9	625.0	614.2	607.1	600.0
32.5°	837.0	764.4	691.8	662.2	632.6	615.5	598.3	587.9	577.5	569.1	560.8
35°	775.3	712.3	649.2	622.1	595.0	577.9	560.8	550.4	539.9	531.6	523.2
37.5°	721.0	663.9	606.7	581.2	555.8	540.8	525.7	514.9	504.0	495.3	486.5
40°	670.1	619.6	569.1	544.5	519.9	503.6	487.4	477.8	468.2	460.2	452.3
42.5°	625.0	578.7	532.4	508.2	484.0	468.6	453.1	441.9	430.6	426.0	421.4
45°	577.5	536.6	495.7	472.3	449.0	432.7	416.4	406.8	397.2	393.1	388.9
47.5°	535.8	497.8	459.8	436.9	413.9	399.3	384.7	377.2	369.7	363.8	358.0
50°	494.9	458.1	421.4	399.3	377.2	364.7	352.2	343.0	333.8	329.6	325.5
52.5°	455.6	422.3	388.9	366.3	343.8	331.7	319.6	311.7	303.8	295.0	286.2
55°	411.4	382.2	353.0	333.0	312.9	300.4	287.9	278.7	269.5	260.4	251.2
57.5°	374.7	345.9	317.1	299.2	281.2	269.1	257.0	247.0	237.0	229.5	222.0
60°	334.6	309.6	284.6	267.0	249.5	237.8	226.2	216.6	207.0	203.2	199.4
62.5°	297.1	273.7	250.4	234.9	219.5	208.2	196.9	190.7	184.4	181.9	179.4
65°	258.7	238.7	218.6	204.5	190.3	180.7	171.1	168.2	165.2	163.1	161.1
67.5°	222.8	205.7	188.6	176.1	163.6	156.9	150.2	146.9	143.5	141.0	138.5
70°	190.3	175.2	160.2	149.4	138.5	132.3	126.0	123.1	120.2	115.6	111.0
72.5°	155.2	143.5	131.9	123.5	115.2	109.7	104.3	98.5	92.6	88.5	84.3
75°	128.5	116.8	105.1	97.2	89.3	83.0	76.8	74.7	72.6	71.4	70.1
77.5°	98.5	88.5	78.4	72.2	65.9	63.0	60.1	58.8	57.6	57.2	56.7
80°	70.9	62.6	54.2	50.9	47.6	46.7	45.9	45.1	44.2	43.8	43.4
82.5°	44.2	40.1	35.9	35.0	34.2	33.8	33.4	33.0	32.5	32.1	31.7
85°	25.9	24.2	22.5	22.1	21.7	21.3	20.9	20.9	20.9	20.9	20.9
87.5°	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.4	10.0
90°	9.4	11.8	14.5	17.3	20.0	22.7	23.6	24.4	25.3	26.1	26.7
92.5°	16.7	17.0	18.9	20.8	22.7	24.6	26.1	27.6	29.0	30.5	31.4
95°	23.3	20.1	22.4	24.7	27.0	29.4	30.8	32.3	33.8	35.3	36.0
97.5°	81.6	73.3	62.5	51.8	41.0	30.3	32.0	33.7	35.4	37.0	38.0
100°	176.9	162.6	129.8	96.9	64.1	31.3	32.9	34.6	36.3	38.0	38.9
102.5°	233.5	216.6	180.0	143.3	106.7	70.1	63.1	56.2	49.3	42.3	39.0
105°	291.5	283.2	264.3	245.3	226.4	207.4	170.2	132.9	95.7	58.4	40.0
107.5°	353.3	355.8	359.0	362.2	365.3	368.5	336.1	303.6	271.2	238.8	208.8
110°	415.9	417.9	420.3	422.6	424.9	427.2	420.3	413.3	406.4	399.4	380.9



TEST NUMBER: P832347

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	475.7	477.6	479.9	482.2	484.6	486.9	488.8	490.7	492.6	494.4	495.2
115°	534.5	536.1	538.0	539.9	541.8	543.7	545.8	547.9	550.0	552.1	553.6
117.5°	594.1	595.4	596.4	597.5	598.5	599.6	601.3	603.0	604.6	606.3	607.3
120°	649.8	651.1	651.7	652.3	653.0	653.6	655.3	657.0	658.6	660.3	661.2
122.5°	703.0	704.2	705.0	705.9	706.7	707.6	708.6	709.7	710.7	711.8	712.4
125°	753.1	754.4	755.3	756.1	756.9	757.8	758.2	758.6	759.0	759.5	759.9
127.5°	802.4	803.8	804.8	805.9	806.9	808.0	808.6	809.2	809.9	810.5	810.6
130°	847.9	849.1	850.0	850.8	851.7	852.5	853.3	854.2	855.0	855.9	856.1
132.5°	891.4	892.6	893.2	893.9	894.5	895.1	896.0	896.8	897.7	898.5	898.6
135°	934.3	935.3	936.2	937.0	937.9	938.7	939.3	940.0	940.6	941.2	941.2
137.5°	973.8	974.9	975.3	975.7	976.2	976.6	977.6	978.7	979.7	980.8	981.1
140°	1010.1	1011.0	1011.6	1012.3	1012.9	1013.5	1014.4	1015.2	1016.1	1016.9	1017.1
142.5°	1045.1	1046.0	1046.7	1047.3	1047.9	1048.6	1049.2	1049.8	1050.5	1051.1	1051.1
145°	1078.1	1079.1	1079.5	1079.9	1080.4	1080.8	1081.2	1081.6	1082.0	1082.5	1082.7
147.5°	1107.7	1108.5	1108.9	1109.3	1109.7	1110.1	1110.6	1111.0	1111.4	1111.8	1111.5
150°	1134.5	1135.0	1135.4	1135.8	1136.2	1136.7	1137.1	1137.5	1137.9	1138.3	1138.2
152.5°	1158.3	1158.6	1158.8	1159.0	1159.2	1159.4	1160.2	1161.1	1161.9	1162.8	1162.7
155°	1179.5	1179.4	1179.6	1179.8	1180.0	1180.2	1181.3	1182.3	1183.4	1184.4	1184.3
157.5°	1200.1	1200.0	1199.8	1199.6	1199.4	1199.2	1200.4	1201.7	1203.0	1204.2	1204.0
160°	1216.3	1216.1	1215.9	1215.7	1215.5	1215.3	1216.5	1217.8	1219.1	1220.3	1220.2
162.5°	1230.8	1230.3	1230.1	1229.9	1229.7	1229.5	1231.0	1232.4	1233.9	1235.4	1235.5
165°	1243.1	1242.6	1242.4	1242.2	1242.0	1241.8	1243.5	1245.2	1246.9	1248.5	1248.6
167.5°	1252.6	1252.2	1252.2	1252.2	1252.2	1252.2	1253.9	1255.6	1257.3	1259.0	1259.0
170°	1261.2	1260.8	1260.8	1260.8	1260.8	1260.8	1262.4	1264.1	1265.8	1267.5	1267.5
172.5°	1266.0	1265.6	1265.8	1266.0	1266.2	1266.4	1268.1	1269.8	1271.5	1273.2	1273.1
175°	1270.8	1270.3	1270.5	1270.8	1271.0	1271.2	1272.6	1274.1	1275.6	1277.1	1277.0
177.5°	1272.6	1272.2	1272.4	1272.6	1272.9	1273.1	1274.7	1276.4	1278.1	1279.8	1279.6
180°	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0



TEST NUMBER: P832347

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	2035.4	2035.4	2035.4	2035.4
2.5°	1808.4	1804.2	1802.5	1800.9
5°	1550.1	1537.2	1534.2	1531.3
7.5°	1330.6	1325.2	1307.3	1289.3
10°	1152.5	1135.8	1128.3	1120.7
12.5°	1003.5	988.1	985.6	983.1
15°	887.9	877.1	873.3	869.6
17.5°	812.0	804.5	799.9	795.3
20°	755.6	750.2	746.9	743.5
22.5°	712.7	708.5	706.0	703.5
25°	671.4	665.1	663.0	660.9
27.5°	632.1	626.7	624.6	622.5
30°	595.4	590.8	587.9	585.0
32.5°	555.4	549.9	548.3	546.6
35°	519.9	516.6	514.9	513.2
37.5°	482.3	478.2	475.7	473.2
40°	450.2	448.1	446.9	445.6
42.5°	417.7	413.9	413.5	413.1
45°	385.1	381.4	380.5	379.7
47.5°	354.7	351.3	350.9	350.5
50°	320.9	316.3	312.9	309.6
52.5°	282.1	277.9	275.0	272.1
55°	246.6	242.0	239.5	237.0
57.5°	219.9	217.8	216.6	215.3
60°	198.2	196.9	196.1	195.3
62.5°	178.2	176.9	176.9	176.9
65°	159.8	158.6	157.3	156.1
67.5°	136.0	133.5	133.1	132.7
70°	107.2	103.5	103.1	102.6
72.5°	83.9	83.5	82.6	81.8
75°	69.3	68.4	68.4	68.4
77.5°	55.9	55.1	55.1	55.1
80°	43.0	42.6	43.0	43.4
82.5°	31.7	31.7	31.3	30.9
85°	20.4	20.0	20.0	20.0
87.5°	10.0	10.0	10.0	10.0
90°	27.2	27.6	28.0	28.4
92.5°	31.6	31.8	32.0	32.2
95°	36.0	36.0	36.0	36.0
97.5°	38.2	38.4	38.6	38.8
100°	39.2	39.4	39.6	39.8
102.5°	39.5	39.9	40.3	40.7
105°	40.4	40.8	41.3	41.7
107.5°	181.2	153.7	126.1	98.5
110°	350.8	320.7	290.6	260.5



TEST NUMBER: P832347

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	494.8	494.3	493.9	493.5
115°	554.4	555.3	556.1	557.0
117.5°	607.5	607.7	607.9	608.1
120°	661.2	661.2	661.2	661.2
122.5°	712.6	712.8	713.0	713.3
125°	760.3	760.7	761.1	761.6
127.5°	810.2	809.8	809.3	808.9
130°	855.7	855.2	854.8	854.4
132.5°	898.0	897.3	896.7	896.1
135°	940.6	940.0	939.3	938.7
137.5°	980.7	980.3	979.8	979.4
140°	1016.7	1016.3	1015.8	1015.4
142.5°	1050.5	1049.8	1049.2	1048.6
145°	1082.7	1082.7	1082.7	1082.7
147.5°	1110.5	1109.4	1108.4	1107.3
150°	1137.6	1137.0	1136.4	1135.7
152.5°	1161.6	1160.6	1159.5	1158.5
155°	1183.1	1181.8	1180.6	1179.3
157.5°	1202.3	1200.7	1199.0	1197.3
160°	1218.8	1217.3	1215.8	1214.3
162.5°	1234.2	1233.0	1231.7	1230.4
165°	1247.2	1245.7	1244.2	1242.8
167.5°	1257.3	1255.6	1253.9	1252.2
170°	1265.8	1264.1	1262.4	1260.8
172.5°	1271.2	1269.3	1267.4	1265.5
175°	1275.3	1273.6	1271.9	1270.2
177.5°	1277.5	1275.4	1273.3	1271.2
180°	1275.0	1275.0	1275.0	1275.0



TEST NUMBER: P832347

CATALOG NUMBER: S123RDIP-S775D1195U930-4F0-1E-UDD-G

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.56	11.31	11.60	12.35	13.74	15.23	15.97	16.27	17.01	18.41
	3H	11.78	12.44	12.83	13.49	14.91	16.72	17.38	17.77	18.43	19.85
	4H	12.15	12.78	13.22	13.84	15.26	17.21	17.83	18.27	18.89	20.31
	6H	12.43	13.01	13.50	14.07	15.50	17.51	18.09	18.58	19.15	20.58
	8H	12.52	13.07	13.59	14.14	15.57	17.59	18.14	18.67	19.21	20.64
	12H	12.57	13.09	13.65	14.15	15.61	17.62	18.14	18.70	19.21	20.66
4H	2H	11.28	11.91	12.34	12.96	14.38	15.21	15.84	16.28	16.89	18.32
	3H	12.64	13.16	13.71	14.24	15.68	16.86	17.39	17.94	18.46	19.90
	4H	13.09	13.57	14.17	14.64	16.10	17.47	17.94	18.55	19.01	20.47
	6H	13.45	13.86	14.54	14.96	16.41	17.90	18.31	18.99	19.40	20.86
	8H	13.58	13.96	14.67	15.04	16.51	18.03	18.41	19.12	19.50	20.96
	12H	13.65	14.00	14.76	15.09	16.57	18.09	18.43	19.19	19.53	21.00
8H	4H	13.40	13.78	14.49	14.87	16.33	17.43	17.81	18.52	18.89	20.36
	6H	13.86	14.17	14.97	15.30	16.77	17.92	18.24	19.03	19.36	20.83
	8H	14.05	14.33	15.17	15.44	16.92	18.11	18.38	19.22	19.49	20.98
	12H	14.19	14.43	15.31	15.54	17.06	18.22	18.46	19.34	19.57	21.09
12H	4H	13.40	13.75	14.51	14.85	16.32	17.37	17.72	18.48	18.82	20.29
	6H	13.92	14.19	15.04	15.30	16.79	17.89	18.17	19.01	19.28	20.76
	8H	14.13	14.37	15.25	15.48	17.00	18.08	18.33	19.20	19.43	20.95