

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332385-927

Luminaire Tested: **S123RDIP-S1165D1195U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332385-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1165D1195U927-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6871.2 lumens  
Efficiency: N/A  
Efficacy: 95.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332385-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332385-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	47	45	44	39
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	42	40	38	34
4	76	66	58	52	71	62	55	50	53	48	44	45	42	38	38	35	33	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26
6	65	53	45	40	60	50	43	38	43	38	34	37	33	30	32	29	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	27	29	26	23	21
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	24	21	19
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	22	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	15655	15655	15655	15655
5°	18662	15722	13846	15722
10°	23302	15632	12508	15632
15°	27351	15473	11407	15473
20°	30525	15234	10470	15234
25°	30037	14982	9894	14982
30°	21592	14751	9302	14751
35°	14416	14448	8918	14448
40°	10621	14085	8521	14085
45°	8910	13449	8132	13449
50°	7860	12616	7591	12616
55°	6893	11661	6848	11661
60°	6140	10749	6273	10749
65°	5392	9770	5835	9770
70°	4233	8897	5331	8897
75°	3730	7769	4870	7769
80°	3242	6602	4785	6602
85°	2618	5298	5076	5298



TEST NUMBER: P332385-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	143.0	2.1
10°-20°	446.9	6.5
20°-30°	702.0	10.2
30°-40°	732.4	10.7
40°-50°	626.8	9.1
50°-60°	477.7	7.0
60°-70°	306.2	4.5
70°-80°	147.3	2.1
80°-90°	42.4	0.6
90°-100°	76.3	1.1
100°-110°	228.5	3.3
110°-120°	388.6	5.7
120°-130°	511.1	7.4
130°-140°	574.5	8.4
140°-150°	564.7	8.2
150°-160°	475.4	6.9
160°-170°	316.5	4.6
170°-180°	110.8	1.6
0°-30°	1291.9	18.8
0°-40°	2024.3	29.5
0°-60°	3128.9	45.5
0°-90°	3624.8	52.8
90°-120°	693.4	10.1
90°-150°	2343.7	34.1
90°-180°	3246.0	47.2
0°-180°	6871.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1454	1454	1454	1454	1454	
5°	1727	1455	1281	1455	1727	178
15°	2454	1388	1024	1388	2454	696
25°	2529	1262	833	1262	2529	1087
35°	1097	1100	679	1100	1097	719
45°	585	884	534	884	585	460
55°	367	621	365	621	367	332
65°	212	384	229	384	212	208
75°	90	187	117	187	90	96
85°	21	43	41	43	21	25
90°	28	1	28	1	28	14
95°	72	54	72	54	72	74
105°	219	207	219	207	219	232
115°	392	391	392	391	392	388
125°	566	572	566	572	566	506
135°	742	743	742	743	742	570
145°	901	901	901	901	901	562
155°	1030	1032	1030	1032	1030	474
165°	1120	1124	1120	1124	1120	316
175°	1164	1169	1164	1169	1164	111
180°	1172	1172	1172	1172	1172	



TEST NUMBER: P332385-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1549.1	1551.1	1544.6	1543.6	1536.1	1534.1	1534.1	1523.7	1517.2	1508.8	1503.8
5°	1727.2	1737.2	1732.2	1720.9	1702.2	1697.9	1686.1	1667.4	1646.2	1620.1	1607.7
7.5°	1949.6	1963.2	1958.0	1940.6	1921.0	1905.3	1871.8	1840.9	1797.4	1759.3	1726.6
10°	2131.9	2117.6	2106.3	2089.5	2071.5	2042.2	2007.4	1959.4	1904.0	1860.4	1811.9
12.5°	2268.3	2266.0	2251.8	2234.5	2209.0	2181.2	2138.3	2080.0	2015.5	1952.6	1897.0
15°	2454.4	2458.1	2448.8	2430.7	2394.6	2345.4	2280.7	2256.5	2164.2	2095.8	2027.3
17.5°	2583.1	2582.4	2581.2	2556.1	2519.3	2484.3	2424.2	2360.4	2277.0	2180.5	2088.2
20°	2664.8	2658.6	2659.9	2631.9	2604.5	2564.0	2505.4	2412.7	2344.2	2232.8	2137.5
22.5°	2662.8	2661.7	2666.3	2656.7	2636.9	2605.8	2559.8	2481.4	2394.1	2281.6	2174.4
25°	2529.1	2524.1	2553.4	2561.5	2593.3	2598.8	2585.1	2542.2	2459.4	2343.6	2211.0
27.5°	2116.7	2113.9	2168.3	2236.3	2322.4	2389.4	2454.2	2485.4	2459.4	2376.5	2243.6
30°	1737.2	1795.6	1823.0	1921.4	2031.0	2161.8	2276.3	2385.3	2412.0	2376.0	2267.0
32.5°	1442.2	1493.3	1516.2	1600.7	1702.8	1855.9	2027.7	2182.1	2291.1	2318.6	2253.0
35°	1097.1	1097.7	1150.0	1187.3	1282.0	1439.6	1606.4	1813.1	2018.6	2174.2	2190.4
37.5°	875.4	878.5	910.1	947.4	1018.4	1101.7	1248.6	1420.5	1657.8	1896.8	2036.9
40°	755.9	761.4	785.1	821.9	872.9	935.8	1050.4	1212.3	1410.2	1676.1	1893.4
42.5°	679.1	688.2	700.4	728.7	760.3	819.3	911.9	1037.0	1217.0	1468.4	1719.1
45°	585.3	590.3	599.6	612.7	641.3	682.4	744.7	828.7	978.2	1180.5	1431.4
47.5°	516.3	513.7	523.5	534.1	553.2	581.1	622.9	691.5	798.1	960.4	1173.3
50°	469.4	468.8	475.7	483.8	501.8	522.4	556.7	608.3	693.0	827.5	1022.4
52.5°	425.6	428.0	432.8	442.9	456.0	472.6	503.4	540.6	613.3	729.4	891.8
55°	367.3	369.2	376.0	381.7	391.0	407.8	427.1	458.3	508.1	589.0	722.9
57.5°	318.1	317.2	323.8	325.1	335.7	349.4	364.3	388.5	424.6	484.8	575.0
60°	285.2	283.3	288.9	293.3	298.9	310.1	322.5	346.2	374.9	419.1	496.2
62.5°	255.2	254.4	258.5	262.8	267.5	277.7	288.1	306.3	329.0	366.2	427.5
65°	211.7	213.6	215.4	217.3	219.8	226.0	236.0	248.4	264.0	290.2	334.4
67.5°	166.4	168.3	168.9	172.7	178.1	182.0	188.1	199.2	209.9	232.0	257.1
70°	134.5	133.9	134.5	136.3	143.2	150.0	158.1	166.3	173.1	188.6	209.8
72.5°	115.6	114.5	116.1	116.5	119.8	121.7	126.7	134.4	143.2	153.8	169.0
75°	89.7	89.7	89.7	89.7	92.1	93.4	95.3	97.1	100.2	105.2	116.5
77.5°	66.2	66.4	67.3	67.9	68.4	69.1	70.3	72.1	73.2	75.8	80.7
80°	52.3	52.9	52.3	52.9	52.9	54.2	54.8	56.6	57.3	60.4	62.3
82.5°	39.4	39.0	39.4	40.0	40.0	41.2	41.4	42.7	42.9	44.4	46.3
85°	21.2	20.0	21.2	20.5	21.8	20.5	21.2	22.4	22.4	23.1	25.5
87.5°	10.5	11.4	10.4	10.8	10.7	11.0	10.9	10.7	11.6	10.9	10.9
90°	27.6	27.2	26.8	26.4	26.0	25.3	24.6	23.8	22.9	22.1	19.4
92.5°	37.2	37.4	37.7	37.9	38.2	37.9	37.3	36.7	36.0	35.3	33.8
95°	71.8	71.8	71.8	71.8	71.8	71.4	70.6	69.7	68.9	68.1	66.5
97.5°	110.4	110.5	110.6	110.7	110.7	110.4	109.4	108.4	107.5	106.5	105.4
100°	139.9	139.5	139.1	138.7	138.2	137.8	137.1	136.5	135.9	135.3	134.3
102.5°	170.1	170.2	170.2	170.3	170.4	170.2	169.5	168.9	168.3	167.7	166.4
105°	219.0	218.6	218.2	217.9	217.5	217.2	217.2	217.2	217.2	217.2	215.4
107.5°	270.1	270.3	270.5	270.8	271.0	270.8	270.2	269.5	268.9	268.2	267.4
110°	304.7	305.1	305.5	305.9	306.3	306.1	305.3	304.4	303.6	302.9	302.4



TEST NUMBER: P332385-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	341.5	341.6	341.7	341.7	341.8	341.4	340.4	339.4	338.4	337.4	337.3
115°	392.1	392.3	392.5	392.7	392.9	392.9	392.7	392.5	392.3	392.1	392.5
117.5°	443.5	444.0	444.6	445.2	445.8	446.1	446.1	446.2	446.2	446.2	446.8
120°	479.5	480.0	480.4	480.8	481.2	481.5	481.7	481.9	482.1	482.3	483.3
122.5°	514.1	514.7	515.3	515.9	516.4	517.0	517.5	518.1	518.6	519.1	519.7
125°	566.1	566.9	567.7	568.5	569.3	570.1	571.0	571.8	572.6	573.5	573.9
127.5°	617.8	618.7	619.6	620.6	621.5	622.6	623.8	624.9	626.1	627.2	627.6
130°	651.6	653.1	654.5	655.9	657.4	658.5	659.3	660.1	661.0	661.8	662.4
132.5°	687.0	688.1	689.2	690.3	691.4	692.4	693.5	694.4	695.4	696.4	696.8
135°	741.9	742.3	742.7	743.1	743.5	744.1	744.9	745.8	746.6	747.3	747.6
137.5°	790.3	791.1	791.9	792.6	793.4	794.2	795.0	795.9	796.8	797.6	797.1
140°	822.0	823.4	824.8	826.2	827.7	828.5	828.7	828.9	829.1	829.3	829.1
142.5°	854.4	855.5	856.5	857.6	858.7	859.4	859.6	859.8	860.0	860.2	859.8
145°	901.1	901.9	902.7	903.6	904.4	904.9	905.1	905.3	905.5	905.7	905.1
147.5°	942.7	943.9	945.2	946.3	947.6	948.2	948.2	948.2	948.2	948.2	947.6
150°	969.2	970.4	971.7	972.9	974.1	974.7	974.7	974.7	974.7	974.7	974.3
152.5°	995.0	996.0	997.1	998.1	999.3	999.6	999.3	998.9	998.6	998.3	998.1
155°	1029.9	1031.4	1032.8	1034.3	1035.7	1036.0	1035.1	1034.4	1033.6	1032.7	1032.5
157.5°	1061.8	1063.0	1064.1	1065.2	1066.4	1066.5	1065.6	1064.8	1064.0	1063.1	1063.0
160°	1082.4	1083.2	1084.0	1084.9	1085.7	1085.6	1084.6	1083.5	1082.5	1081.5	1081.5
162.5°	1097.9	1099.2	1100.5	1101.8	1103.1	1103.3	1102.2	1101.2	1100.2	1099.2	1099.0
165°	1120.1	1121.6	1123.0	1124.4	1125.8	1126.0	1124.7	1123.6	1122.3	1121.1	1121.1
167.5°	1139.1	1140.3	1141.6	1142.9	1144.1	1144.1	1142.9	1141.6	1140.3	1139.1	1138.9
170°	1148.7	1150.1	1151.5	1153.0	1154.4	1154.4	1153.0	1151.5	1150.1	1148.7	1148.7
172.5°	1156.0	1157.5	1158.9	1160.3	1161.8	1161.9	1160.6	1159.4	1158.1	1156.8	1156.8
175°	1164.3	1165.8	1167.2	1168.6	1170.1	1170.1	1168.9	1167.7	1166.5	1165.2	1165.2
177.5°	1168.8	1169.9	1171.0	1172.2	1173.3	1173.4	1172.4	1171.5	1170.4	1169.5	1169.5
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P332385-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1501.8	1500.3	1493.3	1485.3	1474.9	1467.9	1462.4	1459.4	1450.5	1439.6	1432.0
5°	1594.6	1575.9	1555.9	1531.7	1509.3	1486.2	1471.9	1455.1	1434.6	1411.5	1395.3
7.5°	1693.9	1657.3	1617.9	1577.2	1536.9	1500.8	1468.9	1441.6	1408.9	1375.9	1352.7
10°	1770.1	1716.6	1661.2	1604.5	1552.8	1504.3	1466.9	1430.2	1391.0	1353.0	1324.4
12.5°	1839.4	1768.9	1705.0	1635.4	1569.3	1511.2	1457.5	1414.2	1367.1	1326.6	1294.0
15°	1927.1	1854.8	1777.6	1671.7	1584.0	1510.5	1445.1	1388.5	1331.2	1281.4	1249.6
17.5°	2009.0	1900.3	1796.5	1708.3	1594.2	1502.4	1422.6	1354.9	1292.0	1239.1	1200.1
20°	2042.9	1937.6	1825.0	1712.2	1600.1	1497.5	1404.6	1329.9	1264.6	1204.8	1168.7
22.5°	2063.2	1944.1	1825.4	1704.3	1585.2	1478.5	1386.7	1304.6	1233.7	1176.9	1132.3
25°	2087.1	1945.1	1814.3	1694.8	1573.4	1457.6	1348.6	1261.5	1184.9	1124.5	1077.1
27.5°	2102.8	1935.8	1781.2	1648.4	1525.2	1409.8	1310.0	1217.6	1140.0	1076.0	1025.2
30°	2105.7	1928.3	1755.8	1612.0	1486.8	1381.0	1275.2	1186.8	1104.5	1036.6	989.4
32.5°	2109.7	1909.9	1721.4	1568.7	1440.5	1335.7	1239.8	1155.3	1071.2	1004.3	956.0
35°	2093.3	1899.7	1669.3	1493.7	1365.4	1263.9	1177.4	1099.5	1016.8	952.0	902.9
37.5°	2022.5	1859.2	1615.3	1409.3	1275.2	1181.1	1110.6	1042.7	966.9	897.0	850.6
40°	1951.3	1819.3	1573.4	1358.0	1217.9	1121.3	1057.9	1002.4	929.0	863.6	813.8
42.5°	1845.2	1765.1	1533.5	1304.2	1153.1	1060.1	1006.5	954.6	890.1	823.7	776.9
45°	1650.6	1661.2	1452.0	1218.5	1063.4	970.0	919.6	883.5	826.2	771.4	723.5
47.5°	1406.5	1505.5	1356.2	1127.2	968.9	881.3	837.2	805.6	767.1	713.3	669.6
50°	1247.1	1388.5	1279.5	1066.0	909.7	822.5	778.9	753.4	719.8	677.4	635.7
52.5°	1100.2	1252.0	1186.8	997.7	845.4	765.7	723.1	702.1	675.4	635.6	597.9
55°	897.2	1051.0	1036.1	894.7	749.0	677.4	645.1	621.4	603.3	573.5	543.6
57.5°	725.7	871.6	879.2	780.1	664.1	593.3	565.5	547.6	535.8	513.3	485.7
60°	617.7	751.5	777.7	703.0	603.3	541.1	513.7	499.3	490.0	472.0	450.8
62.5°	528.0	641.9	671.5	617.7	545.0	486.8	465.3	451.5	445.2	429.6	410.9
65°	404.1	498.8	527.4	497.5	459.5	412.8	395.4	383.6	378.0	369.2	355.5
67.5°	303.9	372.8	404.3	383.2	369.5	339.9	328.8	322.5	317.5	311.6	300.1
70°	244.1	295.1	327.5	321.9	310.7	295.1	287.0	282.7	277.7	272.7	262.8
72.5°	196.2	231.4	261.7	264.6	255.4	252.3	245.2	243.4	240.3	234.3	228.9
75°	130.2	154.4	175.5	183.7	187.4	190.5	187.4	186.8	186.2	181.2	178.1
77.5°	85.3	98.4	111.7	125.6	131.3	135.6	136.6	138.9	137.2	134.6	133.1
80°	65.4	68.5	77.8	89.7	99.0	102.7	105.2	106.5	105.8	105.2	102.7
82.5°	47.5	50.1	54.4	62.7	70.6	76.8	78.3	78.1	79.5	79.9	77.8
85°	25.5	26.1	27.4	28.7	33.0	39.8	41.7	42.9	44.2	44.2	40.5
87.5°	11.3	10.3	10.8	10.3	11.4	11.5	14.0	16.2	17.0	15.4	15.8
90°	16.8	14.1	11.5	9.1	7.1	5.0	2.9	1.0	2.9	5.0	7.1
92.5°	32.3	30.8	29.3	27.8	26.5	25.0	23.7	22.3	23.7	25.0	26.5
95°	64.8	63.2	61.6	60.0	58.6	57.2	55.8	54.3	55.8	57.2	58.6
97.5°	104.3	103.1	101.9	100.7	99.7	98.6	97.5	96.5	97.5	98.6	99.7
100°	133.2	132.2	131.2	130.1	128.9	127.6	126.4	125.2	126.4	127.6	128.9
102.5°	165.0	163.7	162.3	161.3	160.5	159.8	159.1	158.3	159.1	159.8	160.5
105°	213.6	211.7	209.8	208.7	208.3	207.9	207.5	207.1	207.5	207.9	208.3
107.5°	266.7	266.0	265.3	264.7	264.5	264.3	264.0	263.8	264.0	264.3	264.5
110°	302.0	301.6	301.2	300.8	300.4	299.9	299.5	299.1	299.5	299.9	300.4





TEST NUMBER: P332385-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	337.2	337.2	337.1	336.9	336.7	336.4	336.2	336.0	336.2	336.4	336.7
115°	392.9	393.3	393.7	393.6	393.0	392.4	391.8	391.2	391.8	392.4	393.0
117.5°	447.3	447.8	448.4	448.4	448.0	447.6	447.2	446.8	447.2	447.6	448.0
120°	484.3	485.4	486.4	486.3	485.1	483.9	482.6	481.4	482.6	483.9	485.1
122.5°	520.1	520.7	521.3	521.1	520.1	519.3	518.3	517.5	518.3	519.3	520.1
125°	574.3	574.6	575.0	575.0	574.3	573.7	573.1	572.5	573.1	573.7	574.3
127.5°	628.0	628.5	629.0	628.5	627.2	625.9	624.6	623.3	624.6	625.9	627.2
130°	663.0	663.6	664.2	663.7	662.1	660.4	658.8	657.2	658.8	660.4	662.1
132.5°	697.3	697.8	698.2	697.6	695.9	694.3	692.7	691.0	692.7	694.3	695.9
135°	747.8	748.0	748.2	747.7	746.5	745.2	744.0	742.8	744.0	745.2	746.5
137.5°	796.5	796.1	795.5	794.7	793.7	792.7	791.6	790.7	791.6	792.7	793.7
140°	828.9	828.7	828.5	827.8	826.9	825.9	824.8	823.8	824.8	825.9	826.9
142.5°	859.5	859.1	858.7	858.1	857.1	856.0	855.0	854.0	855.0	856.0	857.1
145°	904.4	903.9	903.2	902.7	902.3	901.9	901.5	901.1	901.5	901.9	902.3
147.5°	947.1	946.5	945.9	945.3	944.5	943.8	943.1	942.3	943.1	943.8	944.5
150°	973.9	973.5	973.1	972.7	972.2	971.8	971.5	971.1	971.5	971.8	972.2
152.5°	997.8	997.5	997.3	996.9	996.3	995.8	995.2	994.6	995.2	995.8	996.3
155°	1032.3	1032.1	1031.9	1031.8	1031.8	1031.8	1031.8	1031.8	1031.8	1031.8	1031.8
157.5°	1062.8	1062.6	1062.4	1062.5	1062.7	1063.0	1063.2	1063.4	1063.2	1063.0	1062.7
160°	1081.5	1081.5	1081.5	1081.7	1082.1	1082.5	1082.9	1083.3	1082.9	1082.5	1082.1
162.5°	1098.8	1098.7	1098.5	1098.8	1099.3	1099.9	1100.4	1101.0	1100.4	1099.9	1099.3
165°	1121.1	1121.1	1121.1	1121.4	1122.0	1122.6	1123.2	1123.9	1123.2	1122.6	1122.0
167.5°	1138.8	1138.6	1138.4	1138.8	1139.6	1140.4	1141.2	1142.1	1141.2	1140.4	1139.6
170°	1148.7	1148.7	1148.7	1149.1	1149.9	1150.7	1151.5	1152.4	1151.5	1150.7	1149.9
172.5°	1156.8	1156.8	1156.8	1157.2	1158.0	1158.8	1159.7	1160.5	1159.7	1158.8	1158.0
175°	1165.2	1165.2	1165.2	1165.7	1166.5	1167.3	1168.2	1168.9	1168.2	1167.3	1166.5
177.5°	1169.5	1169.5	1169.5	1169.8	1170.4	1171.2	1171.8	1172.4	1171.8	1171.2	1170.4
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P332385-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1429.6	1423.1	1418.6	1408.7	1402.2	1395.2	1388.2	1392.7	1392.2	1391.7	1391.7
5°	1381.6	1367.3	1354.2	1337.4	1326.8	1313.8	1303.8	1302.5	1305.0	1296.3	1291.3
7.5°	1334.0	1314.5	1295.9	1277.4	1257.7	1242.1	1232.2	1227.6	1221.2	1215.8	1210.3
10°	1300.7	1277.6	1259.6	1236.5	1215.4	1196.7	1184.9	1176.8	1172.4	1168.1	1160.0
12.5°	1266.3	1243.8	1220.8	1194.7	1174.6	1152.9	1144.0	1135.0	1126.6	1121.7	1110.6
15°	1216.0	1186.8	1162.4	1135.0	1112.6	1091.5	1079.0	1061.0	1058.4	1052.3	1041.0
17.5°	1165.5	1133.8	1100.3	1080.0	1054.7	1032.7	1013.8	1007.7	989.8	983.1	973.4
20°	1125.7	1096.5	1071.0	1044.2	1007.4	986.9	971.9	963.8	949.5	940.8	934.5
22.5°	1091.3	1061.6	1032.1	1000.8	970.6	947.5	936.6	924.0	916.2	904.0	897.2
25°	1042.3	1009.9	974.4	940.8	919.0	901.6	884.2	872.9	861.7	856.1	843.7
27.5°	985.2	951.4	918.2	892.7	865.9	848.7	833.0	823.0	809.5	800.1	793.2
30°	953.9	914.0	885.3	862.4	828.1	811.9	800.1	787.7	777.7	767.7	760.9
32.5°	917.5	881.1	854.0	825.5	799.2	781.5	766.2	755.3	746.8	737.3	730.5
35°	860.5	830.0	801.9	773.3	754.0	735.9	717.9	708.5	700.4	691.7	685.6
37.5°	808.9	780.4	753.8	726.6	702.7	688.0	673.4	666.3	655.4	649.5	643.2
40°	777.1	749.0	720.4	694.3	669.3	658.1	645.1	634.5	624.5	620.1	613.3
42.5°	742.2	714.2	690.0	661.9	641.4	626.2	614.2	602.6	595.1	588.7	584.9
45°	690.5	665.6	641.9	613.9	594.6	581.5	567.8	557.2	550.4	546.1	539.2
47.5°	640.3	615.4	591.4	567.0	548.3	533.4	519.7	512.3	503.2	497.9	493.2
50°	604.0	581.5	556.0	533.6	514.9	499.9	488.8	479.4	471.3	464.5	461.4
52.5°	570.6	546.7	524.7	503.7	484.0	467.1	456.9	447.0	440.9	433.1	429.5
55°	515.6	492.5	473.8	453.3	434.0	419.6	407.2	398.5	392.3	383.6	378.6
57.5°	463.8	443.2	420.9	403.1	383.2	371.1	360.8	349.0	341.4	334.5	329.6
60°	429.0	405.4	386.0	369.2	351.8	336.2	326.9	317.5	309.4	302.6	298.3
62.5°	392.6	371.9	353.6	335.3	319.4	305.9	295.0	287.2	280.0	275.7	271.3
65°	336.8	320.7	302.0	287.0	272.1	262.1	253.4	246.5	241.6	238.4	234.7
67.5°	285.5	269.8	253.5	238.8	228.9	221.3	215.6	209.7	207.2	203.2	200.7
70°	252.2	236.0	221.7	210.5	200.5	194.9	191.2	186.8	184.3	179.4	176.8
72.5°	215.8	204.1	193.8	184.6	176.6	171.5	166.8	161.4	157.4	151.9	149.4
75°	170.0	159.4	151.3	145.0	140.1	133.2	126.4	120.8	118.9	117.1	116.5
77.5°	125.9	119.1	113.3	108.1	101.9	96.9	95.4	94.1	93.8	92.8	92.8
80°	99.0	92.8	88.4	82.1	78.4	78.4	78.4	77.2	77.8	77.8	77.8
82.5°	73.6	67.9	65.5	63.3	62.5	63.0	63.0	63.3	62.9	63.8	63.4
85°	37.9	38.6	39.8	39.2	39.8	39.8	41.1	40.5	41.1	39.8	41.1
87.5°	15.8	17.7	18.8	19.8	20.8	20.8	21.5	21.7	22.3	22.5	22.7
90°	9.1	11.5	14.1	16.8	19.4	22.1	22.9	23.8	24.6	25.3	26.0
92.5°	27.8	29.3	30.8	32.3	33.8	35.3	36.0	36.7	37.3	37.9	38.2
95°	60.0	61.6	63.2	64.8	66.5	68.1	68.9	69.7	70.6	71.4	71.8
97.5°	100.7	101.9	103.1	104.3	105.4	106.5	107.5	108.4	109.4	110.4	110.7
100°	130.1	131.2	132.2	133.2	134.3	135.3	135.9	136.5	137.1	137.8	138.2
102.5°	161.3	162.3	163.7	165.0	166.4	167.7	168.3	168.9	169.5	170.2	170.4
105°	208.7	209.8	211.7	213.6	215.4	217.2	217.2	217.2	217.2	217.2	217.5
107.5°	264.7	265.3	266.0	266.7	267.4	268.2	268.9	269.5	270.2	270.8	271.0
110°	300.8	301.2	301.6	302.0	302.4	302.9	303.6	304.4	305.3	306.1	306.3



TEST NUMBER: P332385-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	336.9	337.1	337.2	337.2	337.3	337.4	338.4	339.4	340.4	341.4	341.8
115°	393.6	393.7	393.3	392.9	392.5	392.1	392.3	392.5	392.7	392.9	392.9
117.5°	448.4	448.4	447.8	447.3	446.8	446.2	446.2	446.2	446.1	446.1	445.8
120°	486.3	486.4	485.4	484.3	483.3	482.3	482.1	481.9	481.7	481.5	481.2
122.5°	521.1	521.3	520.7	520.1	519.7	519.1	518.6	518.1	517.5	517.0	516.4
125°	575.0	575.0	574.6	574.3	573.9	573.5	572.6	571.8	571.0	570.1	569.3
127.5°	628.5	629.0	628.5	628.0	627.6	627.2	626.1	624.9	623.8	622.6	621.5
130°	663.7	664.2	663.6	663.0	662.4	661.8	661.0	660.1	659.3	658.5	657.4
132.5°	697.6	698.2	697.8	697.3	696.8	696.4	695.4	694.4	693.5	692.4	691.4
135°	747.7	748.2	748.0	747.8	747.6	747.3	746.6	745.8	744.9	744.1	743.5
137.5°	794.7	795.5	796.1	796.5	797.1	797.6	796.8	795.9	795.0	794.2	793.4
140°	827.8	828.5	828.7	828.9	829.1	829.3	829.1	828.9	828.7	828.5	827.7
142.5°	858.1	858.7	859.1	859.5	859.8	860.2	860.0	859.8	859.6	859.4	858.7
145°	902.7	903.2	903.9	904.4	905.1	905.7	905.5	905.3	905.1	904.9	904.4
147.5°	945.3	945.9	946.5	947.1	947.6	948.2	948.2	948.2	948.2	948.2	947.6
150°	972.7	973.1	973.5	973.9	974.3	974.7	974.7	974.7	974.7	974.7	974.1
152.5°	996.9	997.3	997.5	997.8	998.1	998.3	998.6	998.9	999.3	999.6	999.3
155°	1031.8	1031.9	1032.1	1032.3	1032.5	1032.7	1033.6	1034.4	1035.1	1036.0	1035.7
157.5°	1062.5	1062.4	1062.6	1062.8	1063.0	1063.1	1064.0	1064.8	1065.6	1066.5	1066.4
160°	1081.7	1081.5	1081.5	1081.5	1081.5	1081.5	1082.5	1083.5	1084.6	1085.6	1085.7
162.5°	1098.8	1098.5	1098.7	1098.8	1099.0	1099.2	1100.2	1101.2	1102.2	1103.3	1103.1
165°	1121.4	1121.1	1121.1	1121.1	1121.1	1121.1	1122.3	1123.6	1124.7	1126.0	1125.8
167.5°	1138.8	1138.4	1138.6	1138.8	1138.9	1139.1	1140.3	1141.6	1142.9	1144.1	1144.1
170°	1149.1	1148.7	1148.7	1148.7	1148.7	1148.7	1150.1	1151.5	1153.0	1154.4	1154.4
172.5°	1157.2	1156.8	1156.8	1156.8	1156.8	1156.8	1158.1	1159.4	1160.6	1161.9	1161.8
175°	1165.7	1165.2	1165.2	1165.2	1165.2	1165.2	1166.5	1167.7	1168.9	1170.1	1170.1
177.5°	1169.8	1169.5	1169.5	1169.5	1169.5	1169.5	1170.4	1171.5	1172.4	1173.4	1173.3
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P332385-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1385.8	1385.2	1385.8	1383.7	1385.8	1385.2	1385.8	1391.7	1391.7	1392.2	1392.7
5°	1289.4	1288.9	1287.0	1281.4	1287.0	1288.9	1289.4	1291.3	1296.3	1305.0	1302.5
7.5°	1205.4	1204.5	1199.0	1199.2	1199.0	1204.5	1205.4	1210.3	1215.8	1221.2	1227.6
10°	1155.6	1156.2	1148.7	1144.4	1148.7	1156.2	1155.6	1160.0	1168.1	1172.4	1176.8
12.5°	1107.3	1104.5	1098.4	1093.6	1098.4	1104.5	1107.3	1110.6	1121.7	1126.6	1135.0
15°	1043.5	1037.3	1022.4	1023.6	1022.4	1037.3	1043.5	1041.0	1052.3	1058.4	1061.0
17.5°	968.4	963.8	963.6	954.9	963.6	963.8	968.4	973.4	983.1	989.8	1007.7
20°	924.6	921.5	922.7	914.0	922.7	921.5	924.6	934.5	940.8	949.5	963.8
22.5°	890.3	887.1	881.9	879.2	881.9	887.1	890.3	897.2	904.0	916.2	924.0
25°	840.0	835.0	830.0	833.1	830.0	835.0	840.0	843.7	856.1	861.7	872.9
27.5°	789.6	785.9	780.9	780.3	780.9	785.9	789.6	793.2	800.1	809.5	823.0
30°	757.7	754.0	751.5	748.4	751.5	754.0	757.7	760.9	767.7	777.7	787.7
32.5°	725.4	724.6	720.2	719.5	720.2	724.6	725.4	730.5	737.3	746.8	755.3
35°	683.0	679.3	678.0	678.7	678.0	679.3	683.0	685.6	691.7	700.4	708.5
37.5°	642.8	637.8	635.6	633.3	635.6	637.8	642.8	643.2	649.5	655.4	666.3
40°	613.9	609.0	607.7	606.4	607.7	609.0	613.9	613.3	620.1	624.5	634.5
42.5°	581.5	579.6	578.8	576.6	578.8	579.6	581.5	584.9	588.7	595.1	602.6
45°	537.3	536.7	533.0	534.2	533.0	536.7	537.3	539.2	546.1	550.4	557.2
47.5°	490.8	488.0	485.4	487.1	485.4	488.0	490.8	493.2	497.9	503.2	512.3
50°	458.9	457.6	452.0	453.3	452.0	457.6	458.9	461.4	464.5	471.3	479.4
52.5°	427.0	422.2	420.2	419.4	420.2	422.2	427.0	429.5	433.1	440.9	447.0
55°	374.2	368.6	366.1	364.9	366.1	368.6	374.2	378.6	383.6	392.3	398.5
57.5°	322.4	320.9	318.9	320.3	318.9	320.9	322.4	329.6	334.5	341.4	349.0
60°	292.0	292.0	292.0	291.4	292.0	292.0	292.0	298.3	302.6	309.4	317.5
62.5°	268.6	267.1	266.6	267.5	266.6	267.1	268.6	271.3	275.7	280.0	287.2
65°	232.9	232.3	229.7	229.1	229.7	232.3	232.9	234.7	238.4	241.6	246.5
67.5°	199.2	196.9	196.1	195.3	196.1	196.9	199.2	200.7	203.2	207.2	209.7
70°	173.7	172.5	168.7	169.4	168.7	172.5	173.7	176.8	179.4	184.3	186.8
72.5°	146.3	145.0	144.3	143.5	144.3	145.0	146.3	149.4	151.9	157.4	161.4
75°	115.8	115.2	114.5	117.1	114.5	115.2	115.8	116.5	117.1	118.9	120.8
77.5°	92.8	92.8	93.2	92.1	93.2	92.8	92.8	92.8	92.8	93.8	94.1
80°	77.8	77.8	77.2	77.2	77.2	77.8	77.8	77.8	77.8	77.8	77.2
82.5°	62.4	62.9	63.3	62.3	63.3	62.9	62.4	63.4	63.8	62.9	63.3
85°	41.1	40.5	41.7	41.1	41.7	40.5	41.1	41.1	39.8	41.1	40.5
87.5°	23.7	22.8	22.9	23.4	22.9	22.8	23.7	22.7	22.5	22.3	21.7
90°	26.4	26.8	27.2	27.6	27.2	26.8	26.4	26.0	25.3	24.6	23.8
92.5°	37.9	37.7	37.4	37.2	37.4	37.7	37.9	38.2	37.9	37.3	36.7
95°	71.8	71.8	71.8	71.8	71.8	71.8	71.8	71.8	71.4	70.6	69.7
97.5°	110.7	110.6	110.5	110.4	110.5	110.6	110.7	110.7	110.4	109.4	108.4
100°	138.7	139.1	139.5	139.9	139.5	139.1	138.7	138.2	137.8	137.1	136.5
102.5°	170.3	170.2	170.2	170.1	170.2	170.2	170.3	170.4	170.2	169.5	168.9
105°	217.9	218.2	218.6	219.0	218.6	218.2	217.9	217.5	217.2	217.2	217.2
107.5°	270.8	270.5	270.3	270.1	270.3	270.5	270.8	271.0	270.8	270.2	269.5
110°	305.9	305.5	305.1	304.7	305.1	305.5	305.9	306.3	306.1	305.3	304.4



TEST NUMBER: P332385-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	341.7	341.7	341.6	341.5	341.6	341.7	341.7	341.8	341.4	340.4	339.4
115°	392.7	392.5	392.3	392.1	392.3	392.5	392.7	392.9	392.9	392.7	392.5
117.5°	445.2	444.6	444.0	443.5	444.0	444.6	445.2	445.8	446.1	446.1	446.2
120°	480.8	480.4	480.0	479.5	480.0	480.4	480.8	481.2	481.5	481.7	481.9
122.5°	515.9	515.3	514.7	514.1	514.7	515.3	515.9	516.4	517.0	517.5	518.1
125°	568.5	567.7	566.9	566.1	566.9	567.7	568.5	569.3	570.1	571.0	571.8
127.5°	620.6	619.6	618.7	617.8	618.7	619.6	620.6	621.5	622.6	623.8	624.9
130°	655.9	654.5	653.1	651.6	653.1	654.5	655.9	657.4	658.5	659.3	660.1
132.5°	690.3	689.2	688.1	687.0	688.1	689.2	690.3	691.4	692.4	693.5	694.4
135°	743.1	742.7	742.3	741.9	742.3	742.7	743.1	743.5	744.1	744.9	745.8
137.5°	792.6	791.9	791.1	790.3	791.1	791.9	792.6	793.4	794.2	795.0	795.9
140°	826.2	824.8	823.4	822.0	823.4	824.8	826.2	827.7	828.5	828.7	828.9
142.5°	857.6	856.5	855.5	854.4	855.5	856.5	857.6	858.7	859.4	859.6	859.8
145°	903.6	902.7	901.9	901.1	901.9	902.7	903.6	904.4	904.9	905.1	905.3
147.5°	946.3	945.2	943.9	942.7	943.9	945.2	946.3	947.6	948.2	948.2	948.2
150°	972.9	971.7	970.4	969.2	970.4	971.7	972.9	974.1	974.7	974.7	974.7
152.5°	998.1	997.1	996.0	995.0	996.0	997.1	998.1	999.3	999.6	999.3	998.9
155°	1034.3	1032.8	1031.4	1029.9	1031.4	1032.8	1034.3	1035.7	1036.0	1035.1	1034.4
157.5°	1065.2	1064.1	1063.0	1061.8	1063.0	1064.1	1065.2	1066.4	1066.5	1065.6	1064.8
160°	1084.9	1084.0	1083.2	1082.4	1083.2	1084.0	1084.9	1085.7	1085.6	1084.6	1083.5
162.5°	1101.8	1100.5	1099.2	1097.9	1099.2	1100.5	1101.8	1103.1	1103.3	1102.2	1101.2
165°	1124.4	1123.0	1121.6	1120.1	1121.6	1123.0	1124.4	1125.8	1126.0	1124.7	1123.6
167.5°	1142.9	1141.6	1140.3	1139.1	1140.3	1141.6	1142.9	1144.1	1144.1	1142.9	1141.6
170°	1153.0	1151.5	1150.1	1148.7	1150.1	1151.5	1153.0	1154.4	1154.4	1153.0	1151.5
172.5°	1160.3	1158.9	1157.5	1156.0	1157.5	1158.9	1160.3	1161.8	1161.9	1160.6	1159.4
175°	1168.6	1167.2	1165.8	1164.3	1165.8	1167.2	1168.6	1170.1	1170.1	1168.9	1167.7
177.5°	1172.2	1171.0	1169.9	1168.8	1169.9	1171.0	1172.2	1173.3	1173.4	1172.4	1171.5
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P332385-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1388.2	1395.2	1402.2	1408.7	1418.6	1423.1	1429.6	1432.0	1439.6	1450.5	1459.4
5°	1303.8	1313.8	1326.8	1337.4	1354.2	1367.3	1381.6	1395.3	1411.5	1434.6	1455.1
7.5°	1232.2	1242.1	1257.7	1277.4	1295.9	1314.5	1334.0	1352.7	1375.9	1408.9	1441.6
10°	1184.9	1196.7	1215.4	1236.5	1259.6	1277.6	1300.7	1324.4	1353.0	1391.0	1430.2
12.5°	1144.0	1152.9	1174.6	1194.7	1220.8	1243.8	1266.3	1294.0	1326.6	1367.1	1414.2
15°	1079.0	1091.5	1112.6	1135.0	1162.4	1186.8	1216.0	1249.6	1281.4	1331.2	1388.5
17.5°	1013.8	1032.7	1054.7	1080.0	1100.3	1133.8	1165.5	1200.1	1239.1	1292.0	1354.9
20°	971.9	986.9	1007.4	1044.2	1071.0	1096.5	1125.7	1168.7	1204.8	1264.6	1329.9
22.5°	936.6	947.5	970.6	1000.8	1032.1	1061.6	1091.3	1132.3	1176.9	1233.7	1304.6
25°	884.2	901.6	919.0	940.8	974.4	1009.9	1042.3	1077.1	1124.5	1184.9	1261.5
27.5°	833.0	848.7	865.9	892.7	918.2	951.4	985.2	1025.2	1076.0	1140.0	1217.6
30°	800.1	811.9	828.1	862.4	885.3	914.0	953.9	989.4	1036.6	1104.5	1186.8
32.5°	766.2	781.5	799.2	825.5	854.0	881.1	917.5	956.0	1004.3	1071.2	1155.3
35°	717.9	735.9	754.0	773.3	801.9	830.0	860.5	902.9	952.0	1016.8	1099.5
37.5°	673.4	688.0	702.7	726.6	753.8	780.4	808.9	850.6	897.0	966.9	1042.7
40°	645.1	658.1	669.3	694.3	720.4	749.0	777.1	813.8	863.6	929.0	1002.4
42.5°	614.2	626.2	641.4	661.9	690.0	714.2	742.2	776.9	823.7	890.1	954.6
45°	567.8	581.5	594.6	613.9	641.9	665.6	690.5	723.5	771.4	826.2	883.5
47.5°	519.7	533.4	548.3	567.0	591.4	615.4	640.3	669.6	713.3	767.1	805.6
50°	488.8	499.9	514.9	533.6	556.0	581.5	604.0	635.7	677.4	719.8	753.4
52.5°	456.9	467.1	484.0	503.7	524.7	546.7	570.6	597.9	635.6	675.4	702.1
55°	407.2	419.6	434.0	453.3	473.8	492.5	515.6	543.6	573.5	603.3	621.4
57.5°	360.8	371.1	383.2	403.1	420.9	443.2	463.8	485.7	513.3	535.8	547.6
60°	326.9	336.2	351.8	369.2	386.0	405.4	429.0	450.8	472.0	490.0	499.3
62.5°	295.0	305.9	319.4	335.3	353.6	371.9	392.6	410.9	429.6	445.2	451.5
65°	253.4	262.1	272.1	287.0	302.0	320.7	336.8	355.5	369.2	378.0	383.6
67.5°	215.6	221.3	228.9	238.8	253.5	269.8	285.5	300.1	311.6	317.5	322.5
70°	191.2	194.9	200.5	210.5	221.7	236.0	252.2	262.8	272.7	277.7	282.7
72.5°	166.8	171.5	176.6	184.6	193.8	204.1	215.8	228.9	234.3	240.3	243.4
75°	126.4	133.2	140.1	145.0	151.3	159.4	170.0	178.1	181.2	186.2	186.8
77.5°	95.4	96.9	101.9	108.1	113.3	119.1	125.9	133.1	134.6	137.2	138.9
80°	78.4	78.4	78.4	82.1	88.4	92.8	99.0	102.7	105.2	105.8	106.5
82.5°	63.0	63.0	62.5	63.3	65.5	67.9	73.6	77.8	79.9	79.5	78.1
85°	41.1	39.8	39.8	39.2	39.8	38.6	37.9	40.5	44.2	44.2	42.9
87.5°	21.5	20.8	20.8	19.8	18.8	17.7	15.8	15.8	15.4	17.0	16.2
90°	22.9	22.1	19.4	16.8	14.1	11.5	9.1	7.1	5.0	2.9	1.0
92.5°	36.0	35.3	33.8	32.3	30.8	29.3	27.8	26.5	25.0	23.7	22.3
95°	68.9	68.1	66.5	64.8	63.2	61.6	60.0	58.6	57.2	55.8	54.3
97.5°	107.5	106.5	105.4	104.3	103.1	101.9	100.7	99.7	98.6	97.5	96.5
100°	135.9	135.3	134.3	133.2	132.2	131.2	130.1	128.9	127.6	126.4	125.2
102.5°	168.3	167.7	166.4	165.0	163.7	162.3	161.3	160.5	159.8	159.1	158.3
105°	217.2	217.2	215.4	213.6	211.7	209.8	208.7	208.3	207.9	207.5	207.1
107.5°	268.9	268.2	267.4	266.7	266.0	265.3	264.7	264.5	264.3	264.0	263.8
110°	303.6	302.9	302.4	302.0	301.6	301.2	300.8	300.4	299.9	299.5	299.1



TEST NUMBER: P332385-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	338.4	337.4	337.3	337.2	337.2	337.1	336.9	336.7	336.4	336.2	336.0
115°	392.3	392.1	392.5	392.9	393.3	393.7	393.6	393.0	392.4	391.8	391.2
117.5°	446.2	446.2	446.8	447.3	447.8	448.4	448.4	448.0	447.6	447.2	446.8
120°	482.1	482.3	483.3	484.3	485.4	486.4	486.3	485.1	483.9	482.6	481.4
122.5°	518.6	519.1	519.7	520.1	520.7	521.3	521.1	520.1	519.3	518.3	517.5
125°	572.6	573.5	573.9	574.3	574.6	575.0	575.0	574.3	573.7	573.1	572.5
127.5°	626.1	627.2	627.6	628.0	628.5	629.0	628.5	627.2	625.9	624.6	623.3
130°	661.0	661.8	662.4	663.0	663.6	664.2	663.7	662.1	660.4	658.8	657.2
132.5°	695.4	696.4	696.8	697.3	697.8	698.2	697.6	695.9	694.3	692.7	691.0
135°	746.6	747.3	747.6	747.8	748.0	748.2	747.7	746.5	745.2	744.0	742.8
137.5°	796.8	797.6	797.1	796.5	796.1	795.5	794.7	793.7	792.7	791.6	790.7
140°	829.1	829.3	829.1	828.9	828.7	828.5	827.8	826.9	825.9	824.8	823.8
142.5°	860.0	860.2	859.8	859.5	859.1	858.7	858.1	857.1	856.0	855.0	854.0
145°	905.5	905.7	905.1	904.4	903.9	903.2	902.7	902.3	901.9	901.5	901.1
147.5°	948.2	948.2	947.6	947.1	946.5	945.9	945.3	944.5	943.8	943.1	942.3
150°	974.7	974.7	974.3	973.9	973.5	973.1	972.7	972.2	971.8	971.5	971.1
152.5°	998.6	998.3	998.1	997.8	997.5	997.3	996.9	996.3	995.8	995.2	994.6
155°	1033.6	1032.7	1032.5	1032.3	1032.1	1031.9	1031.8	1031.8	1031.8	1031.8	1031.8
157.5°	1064.0	1063.1	1063.0	1062.8	1062.6	1062.4	1062.5	1062.7	1063.0	1063.2	1063.4
160°	1082.5	1081.5	1081.5	1081.5	1081.5	1081.5	1081.7	1082.1	1082.5	1082.9	1083.3
162.5°	1100.2	1099.2	1099.0	1098.8	1098.7	1098.5	1098.8	1099.3	1099.9	1100.4	1101.0
165°	1122.3	1121.1	1121.1	1121.1	1121.1	1121.1	1121.4	1122.0	1122.6	1123.2	1123.9
167.5°	1140.3	1139.1	1138.9	1138.8	1138.6	1138.4	1138.8	1139.6	1140.4	1141.2	1142.1
170°	1150.1	1148.7	1148.7	1148.7	1148.7	1148.7	1149.1	1149.9	1150.7	1151.5	1152.4
172.5°	1158.1	1156.8	1156.8	1156.8	1156.8	1156.8	1157.2	1158.0	1158.8	1159.7	1160.5
175°	1166.5	1165.2	1165.2	1165.2	1165.2	1165.2	1165.7	1166.5	1167.3	1168.2	1168.9
177.5°	1170.4	1169.5	1169.5	1169.5	1169.5	1169.5	1169.8	1170.4	1171.2	1171.8	1172.4
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P332385-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1462.4	1467.9	1474.9	1485.3	1493.3	1500.3	1501.8	1503.8	1508.8	1517.2	1523.7
5°	1471.9	1486.2	1509.3	1531.7	1555.9	1575.9	1594.6	1607.7	1620.1	1646.2	1667.4
7.5°	1468.9	1500.8	1536.9	1577.2	1617.9	1657.3	1693.9	1726.6	1759.3	1797.4	1840.9
10°	1466.9	1504.3	1552.8	1604.5	1661.2	1716.6	1770.1	1811.9	1860.4	1904.0	1959.4
12.5°	1457.5	1511.2	1569.3	1635.4	1705.0	1768.9	1839.4	1897.0	1952.6	2015.5	2080.0
15°	1445.1	1510.5	1584.0	1671.7	1777.6	1854.8	1927.1	2027.3	2095.8	2164.2	2256.5
17.5°	1422.6	1502.4	1594.2	1708.3	1796.5	1900.3	2009.0	2088.2	2180.5	2277.0	2360.4
20°	1404.6	1497.5	1600.1	1712.2	1825.0	1937.6	2042.9	2137.5	2232.8	2344.2	2412.7
22.5°	1386.7	1478.5	1585.2	1704.3	1825.4	1944.1	2063.2	2174.4	2281.6	2394.1	2481.4
25°	1348.6	1457.6	1573.4	1694.8	1814.3	1945.1	2087.1	2211.0	2343.6	2459.4	2542.2
27.5°	1310.0	1409.8	1525.2	1648.4	1781.2	1935.8	2102.8	2243.6	2376.5	2459.4	2485.4
30°	1275.2	1381.0	1486.8	1612.0	1755.8	1928.3	2105.7	2267.0	2376.0	2412.0	2385.3
32.5°	1239.8	1335.7	1440.5	1568.7	1721.4	1909.9	2109.7	2253.0	2318.6	2291.1	2182.1
35°	1177.4	1263.9	1365.4	1493.7	1669.3	1899.7	2093.3	2190.4	2174.2	2018.6	1813.1
37.5°	1110.6	1181.1	1275.2	1409.3	1615.3	1859.2	2022.5	2036.9	1896.8	1657.8	1420.5
40°	1057.9	1121.3	1217.9	1358.0	1573.4	1819.3	1951.3	1893.4	1676.1	1410.2	1212.3
42.5°	1006.5	1060.1	1153.1	1304.2	1533.5	1765.1	1845.2	1719.1	1468.4	1217.0	1037.0
45°	919.6	970.0	1063.4	1218.5	1452.0	1661.2	1650.6	1431.4	1180.5	978.2	828.7
47.5°	837.2	881.3	968.9	1127.2	1356.2	1505.5	1406.5	1173.3	960.4	798.1	691.5
50°	778.9	822.5	909.7	1066.0	1279.5	1388.5	1247.1	1022.4	827.5	693.0	608.3
52.5°	723.1	765.7	845.4	997.7	1186.8	1252.0	1100.2	891.8	729.4	613.3	540.6
55°	645.1	677.4	749.0	894.7	1036.1	1051.0	897.2	722.9	589.0	508.1	458.3
57.5°	565.5	593.3	664.1	780.1	879.2	871.6	725.7	575.0	484.8	424.6	388.5
60°	513.7	541.1	603.3	703.0	777.7	751.5	617.7	496.2	419.1	374.9	346.2
62.5°	465.3	486.8	545.0	617.7	671.5	641.9	528.0	427.5	366.2	329.0	306.3
65°	395.4	412.8	459.5	497.5	527.4	498.8	404.1	334.4	290.2	264.0	248.4
67.5°	328.8	339.9	369.5	383.2	404.3	372.8	303.9	257.1	232.0	209.9	199.2
70°	287.0	295.1	310.7	321.9	327.5	295.1	244.1	209.8	188.6	173.1	166.3
72.5°	245.2	252.3	255.4	264.6	261.7	231.4	196.2	169.0	153.8	143.2	134.4
75°	187.4	190.5	187.4	183.7	175.5	154.4	130.2	116.5	105.2	100.2	97.1
77.5°	136.6	135.6	131.3	125.6	111.7	98.4	85.3	80.7	75.8	73.2	72.1
80°	105.2	102.7	99.0	89.7	77.8	68.5	65.4	62.3	60.4	57.3	56.6
82.5°	78.3	76.8	70.6	62.7	54.4	50.1	47.5	46.3	44.4	42.9	42.7
85°	41.7	39.8	33.0	28.7	27.4	26.1	25.5	25.5	23.1	22.4	22.4
87.5°	14.0	11.5	11.4	10.3	10.8	10.3	11.3	10.9	10.9	11.6	10.7
90°	2.9	5.0	7.1	9.1	11.5	14.1	16.8	19.4	22.1	22.9	23.8
92.5°	23.7	25.0	26.5	27.8	29.3	30.8	32.3	33.8	35.3	36.0	36.7
95°	55.8	57.2	58.6	60.0	61.6	63.2	64.8	66.5	68.1	68.9	69.7
97.5°	97.5	98.6	99.7	100.7	101.9	103.1	104.3	105.4	106.5	107.5	108.4
100°	126.4	127.6	128.9	130.1	131.2	132.2	133.2	134.3	135.3	135.9	136.5
102.5°	159.1	159.8	160.5	161.3	162.3	163.7	165.0	166.4	167.7	168.3	168.9
105°	207.5	207.9	208.3	208.7	209.8	211.7	213.6	215.4	217.2	217.2	217.2
107.5°	264.0	264.3	264.5	264.7	265.3	266.0	266.7	267.4	268.2	268.9	269.5
110°	299.5	299.9	300.4	300.8	301.2	301.6	302.0	302.4	302.9	303.6	304.4





TEST NUMBER: P332385-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	336.2	336.4	336.7	336.9	337.1	337.2	337.2	337.3	337.4	338.4	339.4
115°	391.8	392.4	393.0	393.6	393.7	393.3	392.9	392.5	392.1	392.3	392.5
117.5°	447.2	447.6	448.0	448.4	448.4	447.8	447.3	446.8	446.2	446.2	446.2
120°	482.6	483.9	485.1	486.3	486.4	485.4	484.3	483.3	482.3	482.1	481.9
122.5°	518.3	519.3	520.1	521.1	521.3	520.7	520.1	519.7	519.1	518.6	518.1
125°	573.1	573.7	574.3	575.0	575.0	574.6	574.3	573.9	573.5	572.6	571.8
127.5°	624.6	625.9	627.2	628.5	629.0	628.5	628.0	627.6	627.2	626.1	624.9
130°	658.8	660.4	662.1	663.7	664.2	663.6	663.0	662.4	661.8	661.0	660.1
132.5°	692.7	694.3	695.9	697.6	698.2	697.8	697.3	696.8	696.4	695.4	694.4
135°	744.0	745.2	746.5	747.7	748.2	748.0	747.8	747.6	747.3	746.6	745.8
137.5°	791.6	792.7	793.7	794.7	795.5	796.1	796.5	797.1	797.6	796.8	795.9
140°	824.8	825.9	826.9	827.8	828.5	828.7	828.9	829.1	829.3	829.1	828.9
142.5°	855.0	856.0	857.1	858.1	858.7	859.1	859.5	859.8	860.2	860.0	859.8
145°	901.5	901.9	902.3	902.7	903.2	903.9	904.4	905.1	905.7	905.5	905.3
147.5°	943.1	943.8	944.5	945.3	945.9	946.5	947.1	947.6	948.2	948.2	948.2
150°	971.5	971.8	972.2	972.7	973.1	973.5	973.9	974.3	974.7	974.7	974.7
152.5°	995.2	995.8	996.3	996.9	997.3	997.5	997.8	998.1	998.3	998.6	998.9
155°	1031.8	1031.8	1031.8	1031.8	1031.9	1032.1	1032.3	1032.5	1032.7	1033.6	1034.4
157.5°	1063.2	1063.0	1062.7	1062.5	1062.4	1062.6	1062.8	1063.0	1063.1	1064.0	1064.8
160°	1082.9	1082.5	1082.1	1081.7	1081.5	1081.5	1081.5	1081.5	1081.5	1082.5	1083.5
162.5°	1100.4	1099.9	1099.3	1098.8	1098.5	1098.7	1098.8	1099.0	1099.2	1100.2	1101.2
165°	1123.2	1122.6	1122.0	1121.4	1121.1	1121.1	1121.1	1121.1	1121.1	1122.3	1123.6
167.5°	1141.2	1140.4	1139.6	1138.8	1138.4	1138.6	1138.8	1138.9	1139.1	1140.3	1141.6
170°	1151.5	1150.7	1149.9	1149.1	1148.7	1148.7	1148.7	1148.7	1148.7	1150.1	1151.5
172.5°	1159.7	1158.8	1158.0	1157.2	1156.8	1156.8	1156.8	1156.8	1156.8	1158.1	1159.4
175°	1168.2	1167.3	1166.5	1165.7	1165.2	1165.2	1165.2	1165.2	1165.2	1166.5	1167.7
177.5°	1171.8	1171.2	1170.4	1169.8	1169.5	1169.5	1169.5	1169.5	1169.5	1170.4	1171.5
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P332385-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1534.1	1534.1	1536.1	1543.6	1544.6	1551.1	1549.1
5°	1686.1	1697.9	1702.2	1720.9	1732.2	1737.2	1727.2
7.5°	1871.8	1905.3	1921.0	1940.6	1958.0	1963.2	1949.6
10°	2007.4	2042.2	2071.5	2089.5	2106.3	2117.6	2131.9
12.5°	2138.3	2181.2	2209.0	2234.5	2251.8	2266.0	2268.3
15°	2280.7	2345.4	2394.6	2430.7	2448.8	2458.1	2454.4
17.5°	2424.2	2484.3	2519.3	2556.1	2581.2	2582.4	2583.1
20°	2505.4	2564.0	2604.5	2631.9	2659.9	2658.6	2664.8
22.5°	2559.8	2605.8	2636.9	2656.7	2666.3	2661.7	2662.8
25°	2585.1	2598.8	2593.3	2561.5	2553.4	2524.1	2529.1
27.5°	2454.2	2389.4	2322.4	2236.3	2168.3	2113.9	2116.7
30°	2276.3	2161.8	2031.0	1921.4	1823.0	1795.6	1737.2
32.5°	2027.7	1855.9	1702.8	1600.7	1516.2	1493.3	1442.2
35°	1606.4	1439.6	1282.0	1187.3	1150.0	1097.7	1097.1
37.5°	1248.6	1101.7	1018.4	947.4	910.1	878.5	875.4
40°	1050.4	935.8	872.9	821.9	785.1	761.4	755.9
42.5°	911.9	819.3	760.3	728.7	700.4	688.2	679.1
45°	744.7	682.4	641.3	612.7	599.6	590.3	585.3
47.5°	622.9	581.1	553.2	534.1	523.5	513.7	516.3
50°	556.7	522.4	501.8	483.8	475.7	468.8	469.4
52.5°	503.4	472.6	456.0	442.9	432.8	428.0	425.6
55°	427.1	407.8	391.0	381.7	376.0	369.2	367.3
57.5°	364.3	349.4	335.7	325.1	323.8	317.2	318.1
60°	322.5	310.1	298.9	293.3	288.9	283.3	285.2
62.5°	288.1	277.7	267.5	262.8	258.5	254.4	255.2
65°	236.0	226.0	219.8	217.3	215.4	213.6	211.7
67.5°	188.1	182.0	178.1	172.7	168.9	168.3	166.4
70°	158.1	150.0	143.2	136.3	134.5	133.9	134.5
72.5°	126.7	121.7	119.8	116.5	116.1	114.5	115.6
75°	95.3	93.4	92.1	89.7	89.7	89.7	89.7
77.5°	70.3	69.1	68.4	67.9	67.3	66.4	66.2
80°	54.8	54.2	52.9	52.9	52.3	52.9	52.3
82.5°	41.4	41.2	40.0	40.0	39.4	39.0	39.4
85°	21.2	20.5	21.8	20.5	21.2	20.0	21.2
87.5°	10.9	11.0	10.7	10.8	10.4	11.4	10.5
90°	24.6	25.3	26.0	26.4	26.8	27.2	27.6
92.5°	37.3	37.9	38.2	37.9	37.7	37.4	37.2
95°	70.6	71.4	71.8	71.8	71.8	71.8	71.8
97.5°	109.4	110.4	110.7	110.7	110.6	110.5	110.4
100°	137.1	137.8	138.2	138.7	139.1	139.5	139.9
102.5°	169.5	170.2	170.4	170.3	170.2	170.2	170.1
105°	217.2	217.2	217.5	217.9	218.2	218.6	219.0
107.5°	270.2	270.8	271.0	270.8	270.5	270.3	270.1
110°	305.3	306.1	306.3	305.9	305.5	305.1	304.7



TEST NUMBER: P332385-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	340.4	341.4	341.8	341.7	341.7	341.6	341.5
115°	392.7	392.9	392.9	392.7	392.5	392.3	392.1
117.5°	446.1	446.1	445.8	445.2	444.6	444.0	443.5
120°	481.7	481.5	481.2	480.8	480.4	480.0	479.5
122.5°	517.5	517.0	516.4	515.9	515.3	514.7	514.1
125°	571.0	570.1	569.3	568.5	567.7	566.9	566.1
127.5°	623.8	622.6	621.5	620.6	619.6	618.7	617.8
130°	659.3	658.5	657.4	655.9	654.5	653.1	651.6
132.5°	693.5	692.4	691.4	690.3	689.2	688.1	687.0
135°	744.9	744.1	743.5	743.1	742.7	742.3	741.9
137.5°	795.0	794.2	793.4	792.6	791.9	791.1	790.3
140°	828.7	828.5	827.7	826.2	824.8	823.4	822.0
142.5°	859.6	859.4	858.7	857.6	856.5	855.5	854.4
145°	905.1	904.9	904.4	903.6	902.7	901.9	901.1
147.5°	948.2	948.2	947.6	946.3	945.2	943.9	942.7
150°	974.7	974.7	974.1	972.9	971.7	970.4	969.2
152.5°	999.3	999.6	999.3	998.1	997.1	996.0	995.0
155°	1035.1	1036.0	1035.7	1034.3	1032.8	1031.4	1029.9
157.5°	1065.6	1066.5	1066.4	1065.2	1064.1	1063.0	1061.8
160°	1084.6	1085.6	1085.7	1084.9	1084.0	1083.2	1082.4
162.5°	1102.2	1103.3	1103.1	1101.8	1100.5	1099.2	1097.9
165°	1124.7	1126.0	1125.8	1124.4	1123.0	1121.6	1120.1
167.5°	1142.9	1144.1	1144.1	1142.9	1141.6	1140.3	1139.1
170°	1153.0	1154.4	1154.4	1153.0	1151.5	1150.1	1148.7
172.5°	1160.6	1161.9	1161.8	1160.3	1158.9	1157.5	1156.0
175°	1168.9	1170.1	1170.1	1168.6	1167.2	1165.8	1164.3
177.5°	1172.4	1173.4	1173.3	1172.2	1171.0	1169.9	1168.8
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7

(END OF REPORT)