

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332386-927

Luminaire Tested: **S123RDIP-S1165D1195U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332386-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D1195U927-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7045.7 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332386-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332386-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	99	95	91	88	91	88	85	82	75	72	70	63	61	60	52	51	50	45
2	90	83	77	73	83	77	72	68	66	62	59	56	53	51	46	44	43	38
3	83	74	67	61	76	69	62	58	59	54	50	50	46	44	41	39	37	33
4	76	66	58	52	70	61	54	49	53	48	44	45	41	38	37	35	32	29
5	70	59	51	45	65	55	48	43	47	42	38	40	36	33	34	31	29	25
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	31	28	25	23
7	60	48	40	35	55	45	38	33	39	34	30	34	29	26	28	25	23	20
8	56	44	36	31	52	41	34	29	36	30	26	31	27	23	26	23	21	18
9	52	40	33	28	48	38	31	26	33	28	24	28	24	21	24	21	19	17
10	49	37	30	25	45	35	28	24	30	25	22	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15655	15655	15655	15655
5°	18662	15722	13846	15722
10°	23302	15632	12508	15632
15°	27351	15473	11407	15473
20°	30525	15234	10470	15234
25°	30037	14982	9894	14982
30°	21592	14751	9302	14751
35°	14416	14448	8918	14448
40°	10621	14085	8521	14085
45°	8910	13449	8132	13449
50°	7860	12616	7591	12616
55°	6893	11661	6848	11661
60°	6140	10749	6273	10749
65°	5392	9770	5835	9770
70°	4233	8897	5331	8897
75°	3730	7769	4870	7769
80°	3242	6602	4785	6602
85°	2618	5298	5076	5298



TEST NUMBER: P332386-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.0	2.0
10°-20°	446.9	6.3
20°-30°	702.0	10.0
30°-40°	732.4	10.4
40°-50°	626.8	8.9
50°-60°	477.7	6.8
60°-70°	306.2	4.3
70°-80°	147.3	2.1
80°-90°	42.5	0.6
90°-100°	253.0	3.6
100°-110°	716.5	10.2
110°-120°	704.8	10.0
120°-130°	562.2	8.0
130°-140°	443.3	6.3
140°-150°	330.8	4.7
150°-160°	230.6	3.3
160°-170°	135.5	1.9
170°-180°	44.1	0.6
0°-30°	1291.9	18.3
0°-40°	2024.3	28.7
0°-60°	3128.9	44.4
0°-90°	3624.9	51.4
90°-120°	1674.3	23.8
90°-150°	3010.6	42.7
90°-180°	3421.0	48.6
0°-180°	7045.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1454	1454	1454	1454	1454	
5°	1727	1455	1281	1455	1727	178
15°	2454	1388	1024	1388	2454	696
25°	2529	1262	833	1262	2529	1087
35°	1097	1100	679	1100	1097	719
45°	585	884	534	884	585	460
55°	367	621	365	621	367	332
65°	212	384	229	384	212	208
75°	90	187	117	187	90	96
85°	21	43	41	43	21	25
90°	27	2	27	2	27	15
95°	107	31	107	31	107	192
105°	1171	107	1171	107	1171	1155
115°	1424	189	1424	189	1424	1383
125°	1123	262	1123	262	1123	1018
135°	910	307	910	307	910	706
145°	712	351	712	351	712	452
155°	590	398	590	398	590	275
165°	514	435	514	435	514	147
175°	463	454	463	454	463	45
180°	455	455	455	455	455	



TEST NUMBER: P332386-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1549.1	1551.1	1544.6	1543.6	1536.1	1534.1	1534.1	1523.7	1517.2	1508.8	1503.8
5°	1727.2	1737.2	1732.2	1720.9	1702.2	1697.9	1686.1	1667.4	1646.2	1620.1	1607.7
7.5°	1949.6	1963.2	1958.0	1940.6	1921.0	1905.3	1871.8	1840.9	1797.4	1759.3	1726.6
10°	2131.9	2117.6	2106.3	2089.5	2071.5	2042.2	2007.4	1959.4	1904.0	1860.4	1811.9
12.5°	2268.3	2266.0	2251.8	2234.5	2209.0	2181.2	2138.3	2080.0	2015.5	1952.6	1897.0
15°	2454.4	2458.1	2448.8	2430.7	2394.6	2345.4	2280.7	2256.5	2164.2	2095.8	2027.3
17.5°	2583.1	2582.4	2581.2	2556.1	2519.3	2484.3	2424.2	2360.4	2277.0	2180.5	2088.2
20°	2664.8	2658.6	2659.9	2631.9	2604.5	2564.0	2505.4	2412.7	2344.2	2232.8	2137.5
22.5°	2662.8	2661.7	2666.3	2656.7	2636.9	2605.8	2559.8	2481.4	2394.1	2281.6	2174.4
25°	2529.1	2524.1	2553.4	2561.5	2593.3	2598.8	2585.1	2542.2	2459.4	2343.6	2211.0
27.5°	2116.7	2113.9	2168.3	2236.3	2322.4	2389.4	2454.2	2485.4	2459.4	2376.5	2243.6
30°	1737.2	1795.6	1823.0	1921.4	2031.0	2161.8	2276.3	2385.3	2412.0	2376.0	2267.0
32.5°	1442.2	1493.3	1516.2	1600.7	1702.8	1855.9	2027.7	2182.1	2291.1	2318.6	2253.0
35°	1097.1	1097.7	1150.0	1187.3	1282.0	1439.6	1606.4	1813.1	2018.6	2174.2	2190.4
37.5°	875.4	878.5	910.1	947.4	1018.4	1101.7	1248.6	1420.5	1657.8	1896.8	2036.9
40°	755.9	761.4	785.1	821.9	872.9	935.8	1050.4	1212.3	1410.2	1676.1	1893.4
42.5°	679.1	688.2	700.4	728.7	760.3	819.3	911.9	1037.0	1217.0	1468.4	1719.1
45°	585.3	590.3	599.6	612.7	641.3	682.4	744.7	828.7	978.2	1180.5	1431.4
47.5°	516.3	513.7	523.5	534.1	553.2	581.1	622.9	691.5	798.1	960.4	1173.3
50°	469.4	468.8	475.7	483.8	501.8	522.4	556.7	608.3	693.0	827.5	1022.4
52.5°	425.6	428.0	432.8	442.9	456.0	472.6	503.4	540.6	613.3	729.4	891.8
55°	367.3	369.2	376.0	381.7	391.0	407.8	427.1	458.3	508.1	589.0	722.9
57.5°	318.1	317.2	323.8	325.1	335.7	349.4	364.3	388.5	424.6	484.8	575.0
60°	285.2	283.3	288.9	293.3	298.9	310.1	322.5	346.2	374.9	419.1	496.2
62.5°	255.2	254.4	258.5	262.8	267.5	277.7	288.1	306.3	329.0	366.2	427.5
65°	211.7	213.6	215.4	217.3	219.8	226.0	236.0	248.4	264.0	290.2	334.4
67.5°	166.4	168.3	168.9	172.7	178.1	182.0	188.1	199.2	209.9	232.0	257.1
70°	134.5	133.9	134.5	136.3	143.2	150.0	158.1	166.3	173.1	188.6	209.8
72.5°	115.6	114.5	116.1	116.5	119.8	121.7	126.7	134.4	143.2	153.8	169.0
75°	89.7	89.7	89.7	89.7	92.1	93.4	95.3	97.1	100.2	105.2	116.5
77.5°	66.2	66.4	67.3	67.9	68.4	69.1	70.3	72.1	73.2	75.8	80.7
80°	52.3	52.9	52.3	52.9	52.9	54.2	54.8	56.6	57.3	60.4	62.3
82.5°	39.4	39.0	39.4	40.0	40.0	41.2	41.4	42.7	42.9	44.4	46.3
85°	21.2	20.0	21.2	20.5	21.8	20.5	21.2	22.4	22.4	23.1	25.5
87.5°	10.3	11.5	10.3	10.6	10.9	10.9	10.8	10.6	11.4	11.1	11.0
90°	26.7	27.6	26.7	25.7	26.7	24.9	23.9	23.0	22.1	23.0	20.3
92.5°	44.4	46.0	45.1	47.8	49.5	54.3	61.5	77.5	106.8	141.6	155.7
95°	106.8	110.4	116.9	125.2	142.7	175.8	224.6	331.4	442.7	545.8	486.0
97.5°	290.7	298.6	323.4	364.9	432.8	542.9	661.6	825.9	904.9	845.8	619.2
100°	577.1	576.2	612.0	679.2	772.2	902.9	1010.6	1085.1	1053.0	871.6	589.1
102.5°	846.6	867.8	897.8	950.9	1023.3	1106.1	1168.9	1171.3	1060.3	823.8	544.9
105°	1170.8	1175.4	1204.8	1239.8	1282.1	1306.1	1288.6	1196.5	1004.2	740.0	490.6
107.5°	1357.4	1365.9	1375.8	1387.6	1386.9	1354.1	1273.4	1123.9	905.9	666.0	456.0
110°	1434.0	1435.8	1437.7	1430.3	1404.5	1340.1	1224.2	1054.8	844.0	624.0	442.7



TEST NUMBER: P332386-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1449.5	1449.1	1442.1	1419.3	1372.1	1289.3	1159.4	986.3	790.3	596.0	435.4
115°	1423.9	1419.3	1400.8	1360.3	1291.3	1191.0	1055.7	895.6	725.2	566.0	432.6
117.5°	1342.5	1336.3	1309.7	1263.4	1191.4	1089.6	968.0	829.8	686.0	548.3	434.3
120°	1274.8	1269.2	1247.1	1195.6	1122.9	1029.9	919.5	795.2	665.4	540.3	437.2
122.5°	1211.4	1204.4	1180.1	1133.8	1069.1	982.8	880.4	767.9	648.5	535.1	442.4
125°	1122.9	1116.4	1093.4	1053.0	994.0	920.4	832.0	731.7	626.8	528.3	450.0
127.5°	1050.0	1044.1	1023.3	988.7	936.2	869.2	789.5	700.1	607.7	525.0	458.9
130°	1008.8	1001.4	982.1	949.0	900.2	837.6	763.0	680.2	597.3	522.8	464.8
132.5°	968.3	963.1	945.9	912.8	867.0	807.4	738.0	661.8	587.8	522.0	469.2
135°	910.3	903.8	887.2	859.7	814.5	762.1	702.3	636.9	575.3	520.9	475.9
137.5°	849.0	844.7	830.8	802.8	764.9	719.4	667.8	614.3	564.4	518.9	480.3
140°	806.3	807.2	792.5	766.7	731.7	692.1	647.9	601.0	557.8	518.2	483.2
142.5°	766.5	767.4	754.2	731.3	701.6	667.1	628.8	588.5	551.8	516.7	485.4
145°	711.5	709.6	702.3	682.9	659.9	633.3	603.8	573.4	544.0	514.5	486.9
147.5°	666.1	665.4	658.5	645.4	627.9	609.0	585.2	561.1	536.2	511.0	486.9
150°	639.7	639.7	634.1	624.0	610.2	592.7	573.4	552.2	531.1	508.0	486.9
152.5°	617.6	617.6	614.3	604.9	594.1	579.5	562.4	544.2	525.2	504.4	484.7
155°	589.9	589.1	587.2	579.9	571.6	560.5	546.7	532.0	516.3	498.0	482.3
157.5°	564.7	564.9	563.5	557.9	550.7	542.1	531.5	519.1	506.4	492.3	479.2
160°	548.6	549.5	549.5	544.0	537.5	531.1	521.9	511.7	499.8	487.8	477.7
162.5°	533.9	534.7	534.7	530.0	525.7	520.0	511.6	502.9	493.1	483.4	474.8
165°	514.5	514.5	515.4	511.7	508.0	503.4	497.0	491.5	484.1	476.7	470.3
167.5°	496.1	496.1	497.0	494.4	492.8	489.5	485.8	481.6	475.5	470.2	465.9
170°	485.1	485.1	486.0	484.1	483.2	481.3	477.7	474.9	470.3	465.7	463.0
172.5°	474.8	475.5	477.1	475.3	475.1	474.0	471.0	469.1	465.2	462.0	460.7
175°	463.0	463.9	464.8	463.9	463.9	463.9	462.0	461.1	459.3	457.4	457.4
177.5°	456.1	456.1	457.6	456.9	457.6	457.6	456.9	456.1	455.4	454.7	455.4
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7



TEST NUMBER: P332386-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1501.8	1500.3	1493.3	1485.3	1474.9	1467.9	1462.4	1459.4	1450.5	1439.6	1432.0
5°	1594.6	1575.9	1555.9	1531.7	1509.3	1486.2	1471.9	1455.1	1434.6	1411.5	1395.3
7.5°	1693.9	1657.3	1617.9	1577.2	1536.9	1500.8	1468.9	1441.6	1408.9	1375.9	1352.7
10°	1770.1	1716.6	1661.2	1604.5	1552.8	1504.3	1466.9	1430.2	1391.0	1353.0	1324.4
12.5°	1839.4	1768.9	1705.0	1635.4	1569.3	1511.2	1457.5	1414.2	1367.1	1326.6	1294.0
15°	1927.1	1854.8	1777.6	1671.7	1584.0	1510.5	1445.1	1388.5	1331.2	1281.4	1249.6
17.5°	2009.0	1900.3	1796.5	1708.3	1594.2	1502.4	1422.6	1354.9	1292.0	1239.1	1200.1
20°	2042.9	1937.6	1825.0	1712.2	1600.1	1497.5	1404.6	1329.9	1264.6	1204.8	1168.7
22.5°	2063.2	1944.1	1825.4	1704.3	1585.2	1478.5	1386.7	1304.6	1233.7	1176.9	1132.3
25°	2087.1	1945.1	1814.3	1694.8	1573.4	1457.6	1348.6	1261.5	1184.9	1124.5	1077.1
27.5°	2102.8	1935.8	1781.2	1648.4	1525.2	1409.8	1310.0	1217.6	1140.0	1076.0	1025.2
30°	2105.7	1928.3	1755.8	1612.0	1486.8	1381.0	1275.2	1186.8	1104.5	1036.6	989.4
32.5°	2109.7	1909.9	1721.4	1568.7	1440.5	1335.7	1239.8	1155.3	1071.2	1004.3	956.0
35°	2093.3	1899.7	1669.3	1493.7	1365.4	1263.9	1177.4	1099.5	1016.8	952.0	902.9
37.5°	2022.5	1859.2	1615.3	1409.3	1275.2	1181.1	1110.6	1042.7	966.9	897.0	850.6
40°	1951.3	1819.3	1573.4	1358.0	1217.9	1121.3	1057.9	1002.4	929.0	863.6	813.8
42.5°	1845.2	1765.1	1533.5	1304.2	1153.1	1060.1	1006.5	954.6	890.1	823.7	776.9
45°	1650.6	1661.2	1452.0	1218.5	1063.4	970.0	919.6	883.5	826.2	771.4	723.5
47.5°	1406.5	1505.5	1356.2	1127.2	968.9	881.3	837.2	805.6	767.1	713.3	669.6
50°	1247.1	1388.5	1279.5	1066.0	909.7	822.5	778.9	753.4	719.8	677.4	635.7
52.5°	1100.2	1252.0	1186.8	997.7	845.4	765.7	723.1	702.1	675.4	635.6	597.9
55°	897.2	1051.0	1036.1	894.7	749.0	677.4	645.1	621.4	603.3	573.5	543.6
57.5°	725.7	871.6	879.2	780.1	664.1	593.3	565.5	547.6	535.8	513.3	485.7
60°	617.7	751.5	777.7	703.0	603.3	541.1	513.7	499.3	490.0	472.0	450.8
62.5°	528.0	641.9	671.5	617.7	545.0	486.8	465.3	451.5	445.2	429.6	410.9
65°	404.1	498.8	527.4	497.5	459.5	412.8	395.4	383.6	378.0	369.2	355.5
67.5°	303.9	372.8	404.3	383.2	369.5	339.9	328.8	322.5	317.5	311.6	300.1
70°	244.1	295.1	327.5	321.9	310.7	295.1	287.0	282.7	277.7	272.7	262.8
72.5°	196.2	231.4	261.7	264.6	255.4	252.3	245.2	243.4	240.3	234.3	228.9
75°	130.2	154.4	175.5	183.7	187.4	190.5	187.4	186.8	186.2	181.2	178.1
77.5°	85.3	98.4	111.7	125.6	131.3	135.6	136.6	138.9	137.2	134.6	133.1
80°	65.4	68.5	77.8	89.7	99.0	102.7	105.2	106.5	105.8	105.2	102.7
82.5°	47.5	50.1	54.4	62.7	70.6	76.8	78.3	78.1	79.5	79.9	77.8
85°	25.5	26.1	27.4	28.7	33.0	39.8	41.7	42.9	44.2	44.2	40.5
87.5°	11.5	10.4	10.9	10.5	11.6	11.6	14.2	16.3	17.2	15.5	16.1
90°	17.5	14.7	12.0	10.1	8.3	5.5	3.6	1.8	3.6	5.5	8.3
92.5°	116.9	77.3	53.2	39.6	31.8	24.6	17.0	11.4	17.0	24.6	31.8
95°	335.0	197.9	119.6	83.7	59.8	44.2	34.1	31.3	34.1	44.2	59.8
97.5°	367.6	213.0	138.2	99.4	75.8	62.2	54.3	53.4	54.3	62.2	75.8
100°	347.0	210.8	146.3	110.4	88.3	75.5	69.0	68.1	69.0	75.5	88.3
102.5°	329.3	213.7	155.9	122.9	103.1	90.9	85.2	83.6	85.2	90.9	103.1
105°	316.6	221.8	172.1	143.5	126.1	115.0	109.6	106.8	109.6	115.0	126.1
107.5°	315.7	236.9	193.3	166.8	150.4	139.5	134.2	131.4	134.2	139.5	150.4
110°	319.4	249.5	208.0	182.2	166.6	156.5	151.9	149.1	151.9	156.5	166.6



TEST NUMBER: P332386-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	326.8	262.0	223.5	198.4	182.8	172.7	168.1	165.3	168.1	172.7	182.8
115°	338.7	282.6	247.6	222.8	207.1	197.9	192.3	188.7	192.3	197.9	207.1
117.5°	354.5	304.4	269.9	246.8	229.3	220.9	216.3	212.1	216.3	220.9	229.3
120°	366.3	318.5	285.3	262.3	244.9	235.6	231.0	228.2	231.0	235.6	244.9
122.5°	377.4	333.2	300.8	276.3	259.5	249.6	245.0	242.2	245.0	249.6	259.5
125°	394.8	354.3	322.1	297.3	279.8	269.7	264.2	262.3	264.2	269.7	279.8
127.5°	409.2	372.7	341.7	316.8	297.5	287.2	280.4	277.6	280.4	287.2	297.5
130°	418.7	383.8	353.4	328.6	309.3	298.2	289.9	287.2	289.9	298.2	309.3
132.5°	427.6	393.4	363.8	339.6	320.3	307.0	298.0	294.5	298.0	307.0	320.3
135°	439.0	407.7	379.2	354.3	335.0	321.2	311.1	307.4	311.1	321.2	335.0
137.5°	447.5	417.6	390.2	367.3	348.1	333.4	323.4	319.6	323.4	333.4	348.1
140°	451.9	424.3	397.6	374.6	356.2	341.4	332.2	327.6	332.2	341.4	356.2
142.5°	456.3	429.4	403.5	382.0	363.5	350.3	340.4	336.5	340.4	350.3	363.5
145°	461.1	436.3	412.3	391.2	375.5	361.7	353.4	350.7	353.4	361.7	375.5
147.5°	464.1	441.8	419.9	401.9	386.7	374.8	366.7	365.0	366.7	374.8	386.7
150°	464.8	445.4	424.3	407.7	394.8	382.9	375.5	374.6	375.5	382.9	394.8
152.5°	466.3	447.7	429.4	413.6	402.2	391.7	384.4	384.2	384.4	391.7	402.2
155°	466.7	451.9	436.3	423.3	413.3	404.1	398.5	398.5	398.5	404.1	413.3
157.5°	467.5	454.3	441.8	431.8	423.2	415.1	410.7	410.0	410.7	415.1	423.2
160°	467.5	456.5	445.4	436.3	429.8	422.5	418.7	418.7	418.7	422.5	429.8
162.5°	466.8	457.2	447.7	440.0	434.3	428.3	425.4	425.4	425.4	428.3	434.3
165°	464.8	458.4	451.0	444.6	440.8	436.3	434.4	435.4	434.4	436.3	440.8
167.5°	463.3	458.2	452.8	448.8	446.2	442.7	441.8	442.9	441.8	442.7	446.2
170°	461.1	457.4	452.8	451.0	449.2	446.4	445.4	447.3	445.4	446.4	449.2
172.5°	460.4	457.4	453.6	452.5	451.4	449.3	449.2	450.3	449.2	449.3	451.4
175°	458.4	456.5	454.7	453.8	453.8	451.9	452.8	453.8	452.8	451.9	453.8
177.5°	456.9	455.4	454.7	454.7	454.7	453.9	454.7	455.4	454.7	453.9	454.7
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7



TEST NUMBER: P332386-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1429.6	1423.1	1418.6	1408.7	1402.2	1395.2	1388.2	1392.7	1392.2	1391.7	1391.7
5°	1381.6	1367.3	1354.2	1337.4	1326.8	1313.8	1303.8	1302.5	1305.0	1296.3	1291.3
7.5°	1334.0	1314.5	1295.9	1277.4	1257.7	1242.1	1232.2	1227.6	1221.2	1215.8	1210.3
10°	1300.7	1277.6	1259.6	1236.5	1215.4	1196.7	1184.9	1176.8	1172.4	1168.1	1160.0
12.5°	1266.3	1243.8	1220.8	1194.7	1174.6	1152.9	1144.0	1135.0	1126.6	1121.7	1110.6
15°	1216.0	1186.8	1162.4	1135.0	1112.6	1091.5	1079.0	1061.0	1058.4	1052.3	1041.0
17.5°	1165.5	1133.8	1100.3	1080.0	1054.7	1032.7	1013.8	1007.7	989.8	983.1	973.4
20°	1125.7	1096.5	1071.0	1044.2	1007.4	986.9	971.9	963.8	949.5	940.8	934.5
22.5°	1091.3	1061.6	1032.1	1000.8	970.6	947.5	936.6	924.0	916.2	904.0	897.2
25°	1042.3	1009.9	974.4	940.8	919.0	901.6	884.2	872.9	861.7	856.1	843.7
27.5°	985.2	951.4	918.2	892.7	865.9	848.7	833.0	823.0	809.5	800.1	793.2
30°	953.9	914.0	885.3	862.4	828.1	811.9	800.1	787.7	777.7	767.7	760.9
32.5°	917.5	881.1	854.0	825.5	799.2	781.5	766.2	755.3	746.8	737.3	730.5
35°	860.5	830.0	801.9	773.3	754.0	735.9	717.9	708.5	700.4	691.7	685.6
37.5°	808.9	780.4	753.8	726.6	702.7	688.0	673.4	666.3	655.4	649.5	643.2
40°	777.1	749.0	720.4	694.3	669.3	658.1	645.1	634.5	624.5	620.1	613.3
42.5°	742.2	714.2	690.0	661.9	641.4	626.2	614.2	602.6	595.1	588.7	584.9
45°	690.5	665.6	641.9	613.9	594.6	581.5	567.8	557.2	550.4	546.1	539.2
47.5°	640.3	615.4	591.4	567.0	548.3	533.4	519.7	512.3	503.2	497.9	493.2
50°	604.0	581.5	556.0	533.6	514.9	499.9	488.8	479.4	471.3	464.5	461.4
52.5°	570.6	546.7	524.7	503.7	484.0	467.1	456.9	447.0	440.9	433.1	429.5
55°	515.6	492.5	473.8	453.3	434.0	419.6	407.2	398.5	392.3	383.6	378.6
57.5°	463.8	443.2	420.9	403.1	383.2	371.1	360.8	349.0	341.4	334.5	329.6
60°	429.0	405.4	386.0	369.2	351.8	336.2	326.9	317.5	309.4	302.6	298.3
62.5°	392.6	371.9	353.6	335.3	319.4	305.9	295.0	287.2	280.0	275.7	271.3
65°	336.8	320.7	302.0	287.0	272.1	262.1	253.4	246.5	241.6	238.4	234.7
67.5°	285.5	269.8	253.5	238.8	228.9	221.3	215.6	209.7	207.2	203.2	200.7
70°	252.2	236.0	221.7	210.5	200.5	194.9	191.2	186.8	184.3	179.4	176.8
72.5°	215.8	204.1	193.8	184.6	176.6	171.5	166.8	161.4	157.4	151.9	149.4
75°	170.0	159.4	151.3	145.0	140.1	133.2	126.4	120.8	118.9	117.1	116.5
77.5°	125.9	119.1	113.3	108.1	101.9	96.9	95.4	94.1	93.8	92.8	92.8
80°	99.0	92.8	88.4	82.1	78.4	78.4	78.4	77.2	77.8	77.8	77.8
82.5°	73.6	67.9	65.5	63.3	62.5	63.0	63.0	63.3	62.9	63.8	63.4
85°	37.9	38.6	39.8	39.2	39.8	39.8	41.1	40.5	41.1	39.8	41.1
87.5°	16.0	17.8	18.9	20.0	21.0	21.1	21.4	21.5	22.2	22.4	22.7
90°	10.1	12.0	14.7	17.5	20.3	23.0	22.1	23.0	23.9	24.9	26.7
92.5°	39.6	53.2	77.3	116.9	155.7	141.6	106.8	77.5	61.5	54.3	49.5
95°	83.7	119.6	197.9	335.0	486.0	545.8	442.7	331.4	224.6	175.8	142.7
97.5°	99.4	138.2	213.0	367.6	619.2	845.8	904.9	825.9	661.6	542.9	432.8
100°	110.4	146.3	210.8	347.0	589.1	871.6	1053.0	1085.1	1010.6	902.9	772.2
102.5°	122.9	155.9	213.7	329.3	544.9	823.8	1060.3	1171.3	1168.9	1106.1	1023.3
105°	143.5	172.1	221.8	316.6	490.6	740.0	1004.2	1196.5	1288.6	1306.1	1282.1
107.5°	166.8	193.3	236.9	315.7	456.0	666.0	905.9	1123.9	1273.4	1354.1	1386.9
110°	182.2	208.0	249.5	319.4	442.7	624.0	844.0	1054.8	1224.2	1340.1	1404.5



TEST NUMBER: P332386-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	198.4	223.5	262.0	326.8	435.4	596.0	790.3	986.3	1159.4	1289.3	1372.1
115°	222.8	247.6	282.6	338.7	432.6	566.0	725.2	895.6	1055.7	1191.0	1291.3
117.5°	246.8	269.9	304.4	354.5	434.3	548.3	686.0	829.8	968.0	1089.6	1191.4
120°	262.3	285.3	318.5	366.3	437.2	540.3	665.4	795.2	919.5	1029.9	1122.9
122.5°	276.3	300.8	333.2	377.4	442.4	535.1	648.5	767.9	880.4	982.8	1069.1
125°	297.3	322.1	354.3	394.8	450.0	528.3	626.8	731.7	832.0	920.4	994.0
127.5°	316.8	341.7	372.7	409.2	458.9	525.0	607.7	700.1	789.5	869.2	936.2
130°	328.6	353.4	383.8	418.7	464.8	522.8	597.3	680.2	763.0	837.6	900.2
132.5°	339.6	363.8	393.4	427.6	469.2	522.0	587.8	661.8	738.0	807.4	867.0
135°	354.3	379.2	407.7	439.0	475.9	520.9	575.3	636.9	702.3	762.1	814.5
137.5°	367.3	390.2	417.6	447.5	480.3	518.9	564.4	614.3	667.8	719.4	764.9
140°	374.6	397.6	424.3	451.9	483.2	518.2	557.8	601.0	647.9	692.1	731.7
142.5°	382.0	403.5	429.4	456.3	485.4	516.7	551.8	588.5	628.8	667.1	701.6
145°	391.2	412.3	436.3	461.1	486.9	514.5	544.0	573.4	603.8	633.3	659.9
147.5°	401.9	419.9	441.8	464.1	486.9	511.0	536.2	561.1	585.2	609.0	627.9
150°	407.7	424.3	445.4	464.8	486.9	508.0	531.1	552.2	573.4	592.7	610.2
152.5°	413.6	429.4	447.7	466.3	484.7	504.4	525.2	544.2	562.4	579.5	594.1
155°	423.3	436.3	451.9	466.7	482.3	498.0	516.3	532.0	546.7	560.5	571.6
157.5°	431.8	441.8	454.3	467.5	479.2	492.3	506.4	519.1	531.5	542.1	550.7
160°	436.3	445.4	456.5	467.5	477.7	487.8	499.8	511.7	521.9	531.1	537.5
162.5°	440.0	447.7	457.2	466.8	474.8	483.4	493.1	502.9	511.6	520.0	525.7
165°	444.6	451.0	458.4	464.8	470.3	476.7	484.1	491.5	497.0	503.4	508.0
167.5°	448.8	452.8	458.2	463.3	465.9	470.2	475.5	481.6	485.8	489.5	492.8
170°	451.0	452.8	457.4	461.1	463.0	465.7	470.3	474.9	477.7	481.3	483.2
172.5°	452.5	453.6	457.4	460.4	460.7	462.0	465.2	469.1	471.0	474.0	475.1
175°	453.8	454.7	456.5	458.4	457.4	457.4	459.3	461.1	462.0	463.9	463.9
177.5°	454.7	454.7	455.4	456.9	455.4	454.7	455.4	456.1	456.9	457.6	457.6
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7



TEST NUMBER: P332386-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1385.8	1385.2	1385.8	1383.7	1385.8	1385.2	1385.8	1391.7	1391.7	1392.2	1392.7
5°	1289.4	1288.9	1287.0	1281.4	1287.0	1288.9	1289.4	1291.3	1296.3	1305.0	1302.5
7.5°	1205.4	1204.5	1199.0	1199.2	1199.0	1204.5	1205.4	1210.3	1215.8	1221.2	1227.6
10°	1155.6	1156.2	1148.7	1144.4	1148.7	1156.2	1155.6	1160.0	1168.1	1172.4	1176.8
12.5°	1107.3	1104.5	1098.4	1093.6	1098.4	1104.5	1107.3	1110.6	1121.7	1126.6	1135.0
15°	1043.5	1037.3	1022.4	1023.6	1022.4	1037.3	1043.5	1041.0	1052.3	1058.4	1061.0
17.5°	968.4	963.8	963.6	954.9	963.6	963.8	968.4	973.4	983.1	989.8	1007.7
20°	924.6	921.5	922.7	914.0	922.7	921.5	924.6	934.5	940.8	949.5	963.8
22.5°	890.3	887.1	881.9	879.2	881.9	887.1	890.3	897.2	904.0	916.2	924.0
25°	840.0	835.0	830.0	833.1	830.0	835.0	840.0	843.7	856.1	861.7	872.9
27.5°	789.6	785.9	780.9	780.3	780.9	785.9	789.6	793.2	800.1	809.5	823.0
30°	757.7	754.0	751.5	748.4	751.5	754.0	757.7	760.9	767.7	777.7	787.7
32.5°	725.4	724.6	720.2	719.5	720.2	724.6	725.4	730.5	737.3	746.8	755.3
35°	683.0	679.3	678.0	678.7	678.0	679.3	683.0	685.6	691.7	700.4	708.5
37.5°	642.8	637.8	635.6	633.3	635.6	637.8	642.8	643.2	649.5	655.4	666.3
40°	613.9	609.0	607.7	606.4	607.7	609.0	613.9	613.3	620.1	624.5	634.5
42.5°	581.5	579.6	578.8	576.6	578.8	579.6	581.5	584.9	588.7	595.1	602.6
45°	537.3	536.7	533.0	534.2	533.0	536.7	537.3	539.2	546.1	550.4	557.2
47.5°	490.8	488.0	485.4	487.1	485.4	488.0	490.8	493.2	497.9	503.2	512.3
50°	458.9	457.6	452.0	453.3	452.0	457.6	458.9	461.4	464.5	471.3	479.4
52.5°	427.0	422.2	420.2	419.4	420.2	422.2	427.0	429.5	433.1	440.9	447.0
55°	374.2	368.6	366.1	364.9	366.1	368.6	374.2	378.6	383.6	392.3	398.5
57.5°	322.4	320.9	318.9	320.3	318.9	320.9	322.4	329.6	334.5	341.4	349.0
60°	292.0	292.0	292.0	291.4	292.0	292.0	292.0	298.3	302.6	309.4	317.5
62.5°	268.6	267.1	266.6	267.5	266.6	267.1	268.6	271.3	275.7	280.0	287.2
65°	232.9	232.3	229.7	229.1	229.7	232.3	232.9	234.7	238.4	241.6	246.5
67.5°	199.2	196.9	196.1	195.3	196.1	196.9	199.2	200.7	203.2	207.2	209.7
70°	173.7	172.5	168.7	169.4	168.7	172.5	173.7	176.8	179.4	184.3	186.8
72.5°	146.3	145.0	144.3	143.5	144.3	145.0	146.3	149.4	151.9	157.4	161.4
75°	115.8	115.2	114.5	117.1	114.5	115.2	115.8	116.5	117.1	118.9	120.8
77.5°	92.8	92.8	93.2	92.1	93.2	92.8	92.8	92.8	92.8	93.8	94.1
80°	77.8	77.8	77.2	77.2	77.2	77.8	77.8	77.8	77.8	77.8	77.2
82.5°	62.4	62.9	63.3	62.3	63.3	62.9	62.4	63.4	63.8	62.9	63.3
85°	41.1	40.5	41.7	41.1	41.7	40.5	41.1	41.1	39.8	41.1	40.5
87.5°	23.6	22.7	23.0	23.3	23.0	22.7	23.6	22.7	22.4	22.2	21.5
90°	25.7	26.7	27.6	26.7	27.6	26.7	25.7	26.7	24.9	23.9	23.0
92.5°	47.8	45.1	46.0	44.4	46.0	45.1	47.8	49.5	54.3	61.5	77.5
95°	125.2	116.9	110.4	106.8	110.4	116.9	125.2	142.7	175.8	224.6	331.4
97.5°	364.9	323.4	298.6	290.7	298.6	323.4	364.9	432.8	542.9	661.6	825.9
100°	679.2	612.0	576.2	577.1	576.2	612.0	679.2	772.2	902.9	1010.6	1085.1
102.5°	950.9	897.8	867.8	846.6	867.8	897.8	950.9	1023.3	1106.1	1168.9	1171.3
105°	1239.8	1204.8	1175.4	1170.8	1175.4	1204.8	1239.8	1282.1	1306.1	1288.6	1196.5
107.5°	1387.6	1375.8	1365.9	1357.4	1365.9	1375.8	1387.6	1386.9	1354.1	1273.4	1123.9
110°	1430.3	1437.7	1435.8	1434.0	1435.8	1437.7	1430.3	1404.5	1340.1	1224.2	1054.8



TEST NUMBER: P332386-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1419.3	1442.1	1449.1	1449.5	1449.1	1442.1	1419.3	1372.1	1289.3	1159.4	986.3
115°	1360.3	1400.8	1419.3	1423.9	1419.3	1400.8	1360.3	1291.3	1191.0	1055.7	895.6
117.5°	1263.4	1309.7	1336.3	1342.5	1336.3	1309.7	1263.4	1191.4	1089.6	968.0	829.8
120°	1195.6	1247.1	1269.2	1274.8	1269.2	1247.1	1195.6	1122.9	1029.9	919.5	795.2
122.5°	1133.8	1180.1	1204.4	1211.4	1204.4	1180.1	1133.8	1069.1	982.8	880.4	767.9
125°	1053.0	1093.4	1116.4	1122.9	1116.4	1093.4	1053.0	994.0	920.4	832.0	731.7
127.5°	988.7	1023.3	1044.1	1050.0	1044.1	1023.3	988.7	936.2	869.2	789.5	700.1
130°	949.0	982.1	1001.4	1008.8	1001.4	982.1	949.0	900.2	837.6	763.0	680.2
132.5°	912.8	945.9	963.1	968.3	963.1	945.9	912.8	867.0	807.4	738.0	661.8
135°	859.7	887.2	903.8	910.3	903.8	887.2	859.7	814.5	762.1	702.3	636.9
137.5°	802.8	830.8	844.7	849.0	844.7	830.8	802.8	764.9	719.4	667.8	614.3
140°	766.7	792.5	807.2	806.3	807.2	792.5	766.7	731.7	692.1	647.9	601.0
142.5°	731.3	754.2	767.4	766.5	767.4	754.2	731.3	701.6	667.1	628.8	588.5
145°	682.9	702.3	709.6	711.5	709.6	702.3	682.9	659.9	633.3	603.8	573.4
147.5°	645.4	658.5	665.4	666.1	665.4	658.5	645.4	627.9	609.0	585.2	561.1
150°	624.0	634.1	639.7	639.7	639.7	634.1	624.0	610.2	592.7	573.4	552.2
152.5°	604.9	614.3	617.6	617.6	617.6	614.3	604.9	594.1	579.5	562.4	544.2
155°	579.9	587.2	589.1	589.9	589.1	587.2	579.9	571.6	560.5	546.7	532.0
157.5°	557.9	563.5	564.9	564.7	564.9	563.5	557.9	550.7	542.1	531.5	519.1
160°	544.0	549.5	549.5	548.6	549.5	549.5	544.0	537.5	531.1	521.9	511.7
162.5°	530.0	534.7	534.7	533.9	534.7	534.7	530.0	525.7	520.0	511.6	502.9
165°	511.7	515.4	514.5	514.5	514.5	515.4	511.7	508.0	503.4	497.0	491.5
167.5°	494.4	497.0	496.1	496.1	496.1	497.0	494.4	492.8	489.5	485.8	481.6
170°	484.1	486.0	485.1	485.1	485.1	486.0	484.1	483.2	481.3	477.7	474.9
172.5°	475.3	477.1	475.5	474.8	475.5	477.1	475.3	475.1	474.0	471.0	469.1
175°	463.9	464.8	463.9	463.0	463.9	464.8	463.9	463.9	463.9	462.0	461.1
177.5°	456.9	457.6	456.1	456.1	456.1	457.6	456.9	457.6	457.6	456.9	456.1
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7



TEST NUMBER: P332386-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1388.2	1395.2	1402.2	1408.7	1418.6	1423.1	1429.6	1432.0	1439.6	1450.5	1459.4
5°	1303.8	1313.8	1326.8	1337.4	1354.2	1367.3	1381.6	1395.3	1411.5	1434.6	1455.1
7.5°	1232.2	1242.1	1257.7	1277.4	1295.9	1314.5	1334.0	1352.7	1375.9	1408.9	1441.6
10°	1184.9	1196.7	1215.4	1236.5	1259.6	1277.6	1300.7	1324.4	1353.0	1391.0	1430.2
12.5°	1144.0	1152.9	1174.6	1194.7	1220.8	1243.8	1266.3	1294.0	1326.6	1367.1	1414.2
15°	1079.0	1091.5	1112.6	1135.0	1162.4	1186.8	1216.0	1249.6	1281.4	1331.2	1388.5
17.5°	1013.8	1032.7	1054.7	1080.0	1100.3	1133.8	1165.5	1200.1	1239.1	1292.0	1354.9
20°	971.9	986.9	1007.4	1044.2	1071.0	1096.5	1125.7	1168.7	1204.8	1264.6	1329.9
22.5°	936.6	947.5	970.6	1000.8	1032.1	1061.6	1091.3	1132.3	1176.9	1233.7	1304.6
25°	884.2	901.6	919.0	940.8	974.4	1009.9	1042.3	1077.1	1124.5	1184.9	1261.5
27.5°	833.0	848.7	865.9	892.7	918.2	951.4	985.2	1025.2	1076.0	1140.0	1217.6
30°	800.1	811.9	828.1	862.4	885.3	914.0	953.9	989.4	1036.6	1104.5	1186.8
32.5°	766.2	781.5	799.2	825.5	854.0	881.1	917.5	956.0	1004.3	1071.2	1155.3
35°	717.9	735.9	754.0	773.3	801.9	830.0	860.5	902.9	952.0	1016.8	1099.5
37.5°	673.4	688.0	702.7	726.6	753.8	780.4	808.9	850.6	897.0	966.9	1042.7
40°	645.1	658.1	669.3	694.3	720.4	749.0	777.1	813.8	863.6	929.0	1002.4
42.5°	614.2	626.2	641.4	661.9	690.0	714.2	742.2	776.9	823.7	890.1	954.6
45°	567.8	581.5	594.6	613.9	641.9	665.6	690.5	723.5	771.4	826.2	883.5
47.5°	519.7	533.4	548.3	567.0	591.4	615.4	640.3	669.6	713.3	767.1	805.6
50°	488.8	499.9	514.9	533.6	556.0	581.5	604.0	635.7	677.4	719.8	753.4
52.5°	456.9	467.1	484.0	503.7	524.7	546.7	570.6	597.9	635.6	675.4	702.1
55°	407.2	419.6	434.0	453.3	473.8	492.5	515.6	543.6	573.5	603.3	621.4
57.5°	360.8	371.1	383.2	403.1	420.9	443.2	463.8	485.7	513.3	535.8	547.6
60°	326.9	336.2	351.8	369.2	386.0	405.4	429.0	450.8	472.0	490.0	499.3
62.5°	295.0	305.9	319.4	335.3	353.6	371.9	392.6	410.9	429.6	445.2	451.5
65°	253.4	262.1	272.1	287.0	302.0	320.7	336.8	355.5	369.2	378.0	383.6
67.5°	215.6	221.3	228.9	238.8	253.5	269.8	285.5	300.1	311.6	317.5	322.5
70°	191.2	194.9	200.5	210.5	221.7	236.0	252.2	262.8	272.7	277.7	282.7
72.5°	166.8	171.5	176.6	184.6	193.8	204.1	215.8	228.9	234.3	240.3	243.4
75°	126.4	133.2	140.1	145.0	151.3	159.4	170.0	178.1	181.2	186.2	186.8
77.5°	95.4	96.9	101.9	108.1	113.3	119.1	125.9	133.1	134.6	137.2	138.9
80°	78.4	78.4	78.4	82.1	88.4	92.8	99.0	102.7	105.2	105.8	106.5
82.5°	63.0	63.0	62.5	63.3	65.5	67.9	73.6	77.8	79.9	79.5	78.1
85°	41.1	39.8	39.8	39.2	39.8	38.6	37.9	40.5	44.2	44.2	42.9
87.5°	21.4	21.1	21.0	20.0	18.9	17.8	16.0	16.1	15.5	17.2	16.3
90°	22.1	23.0	20.3	17.5	14.7	12.0	10.1	8.3	5.5	3.6	1.8
92.5°	106.8	141.6	155.7	116.9	77.3	53.2	39.6	31.8	24.6	17.0	11.4
95°	442.7	545.8	486.0	335.0	197.9	119.6	83.7	59.8	44.2	34.1	31.3
97.5°	904.9	845.8	619.2	367.6	213.0	138.2	99.4	75.8	62.2	54.3	53.4
100°	1053.0	871.6	589.1	347.0	210.8	146.3	110.4	88.3	75.5	69.0	68.1
102.5°	1060.3	823.8	544.9	329.3	213.7	155.9	122.9	103.1	90.9	85.2	83.6
105°	1004.2	740.0	490.6	316.6	221.8	172.1	143.5	126.1	115.0	109.6	106.8
107.5°	905.9	666.0	456.0	315.7	236.9	193.3	166.8	150.4	139.5	134.2	131.4
110°	844.0	624.0	442.7	319.4	249.5	208.0	182.2	166.6	156.5	151.9	149.1



TEST NUMBER: P332386-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	790.3	596.0	435.4	326.8	262.0	223.5	198.4	182.8	172.7	168.1	165.3
115°	725.2	566.0	432.6	338.7	282.6	247.6	222.8	207.1	197.9	192.3	188.7
117.5°	686.0	548.3	434.3	354.5	304.4	269.9	246.8	229.3	220.9	216.3	212.1
120°	665.4	540.3	437.2	366.3	318.5	285.3	262.3	244.9	235.6	231.0	228.2
122.5°	648.5	535.1	442.4	377.4	333.2	300.8	276.3	259.5	249.6	245.0	242.2
125°	626.8	528.3	450.0	394.8	354.3	322.1	297.3	279.8	269.7	264.2	262.3
127.5°	607.7	525.0	458.9	409.2	372.7	341.7	316.8	297.5	287.2	280.4	277.6
130°	597.3	522.8	464.8	418.7	383.8	353.4	328.6	309.3	298.2	289.9	287.2
132.5°	587.8	522.0	469.2	427.6	393.4	363.8	339.6	320.3	307.0	298.0	294.5
135°	575.3	520.9	475.9	439.0	407.7	379.2	354.3	335.0	321.2	311.1	307.4
137.5°	564.4	518.9	480.3	447.5	417.6	390.2	367.3	348.1	333.4	323.4	319.6
140°	557.8	518.2	483.2	451.9	424.3	397.6	374.6	356.2	341.4	332.2	327.6
142.5°	551.8	516.7	485.4	456.3	429.4	403.5	382.0	363.5	350.3	340.4	336.5
145°	544.0	514.5	486.9	461.1	436.3	412.3	391.2	375.5	361.7	353.4	350.7
147.5°	536.2	511.0	486.9	464.1	441.8	419.9	401.9	386.7	374.8	366.7	365.0
150°	531.1	508.0	486.9	464.8	445.4	424.3	407.7	394.8	382.9	375.5	374.6
152.5°	525.2	504.4	484.7	466.3	447.7	429.4	413.6	402.2	391.7	384.4	384.2
155°	516.3	498.0	482.3	466.7	451.9	436.3	423.3	413.3	404.1	398.5	398.5
157.5°	506.4	492.3	479.2	467.5	454.3	441.8	431.8	423.2	415.1	410.7	410.0
160°	499.8	487.8	477.7	467.5	456.5	445.4	436.3	429.8	422.5	418.7	418.7
162.5°	493.1	483.4	474.8	466.8	457.2	447.7	440.0	434.3	428.3	425.4	425.4
165°	484.1	476.7	470.3	464.8	458.4	451.0	444.6	440.8	436.3	434.4	435.4
167.5°	475.5	470.2	465.9	463.3	458.2	452.8	448.8	446.2	442.7	441.8	442.9
170°	470.3	465.7	463.0	461.1	457.4	452.8	451.0	449.2	446.4	445.4	447.3
172.5°	465.2	462.0	460.7	460.4	457.4	453.6	452.5	451.4	449.3	449.2	450.3
175°	459.3	457.4	457.4	458.4	456.5	454.7	453.8	453.8	451.9	452.8	453.8
177.5°	455.4	454.7	455.4	456.9	455.4	454.7	454.7	454.7	453.9	454.7	455.4
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7



TEST NUMBER: P332386-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1462.4	1467.9	1474.9	1485.3	1493.3	1500.3	1501.8	1503.8	1508.8	1517.2	1523.7
5°	1471.9	1486.2	1509.3	1531.7	1555.9	1575.9	1594.6	1607.7	1620.1	1646.2	1667.4
7.5°	1468.9	1500.8	1536.9	1577.2	1617.9	1657.3	1693.9	1726.6	1759.3	1797.4	1840.9
10°	1466.9	1504.3	1552.8	1604.5	1661.2	1716.6	1770.1	1811.9	1860.4	1904.0	1959.4
12.5°	1457.5	1511.2	1569.3	1635.4	1705.0	1768.9	1839.4	1897.0	1952.6	2015.5	2080.0
15°	1445.1	1510.5	1584.0	1671.7	1777.6	1854.8	1927.1	2027.3	2095.8	2164.2	2256.5
17.5°	1422.6	1502.4	1594.2	1708.3	1796.5	1900.3	2009.0	2088.2	2180.5	2277.0	2360.4
20°	1404.6	1497.5	1600.1	1712.2	1825.0	1937.6	2042.9	2137.5	2232.8	2344.2	2412.7
22.5°	1386.7	1478.5	1585.2	1704.3	1825.4	1944.1	2063.2	2174.4	2281.6	2394.1	2481.4
25°	1348.6	1457.6	1573.4	1694.8	1814.3	1945.1	2087.1	2211.0	2343.6	2459.4	2542.2
27.5°	1310.0	1409.8	1525.2	1648.4	1781.2	1935.8	2102.8	2243.6	2376.5	2459.4	2485.4
30°	1275.2	1381.0	1486.8	1612.0	1755.8	1928.3	2105.7	2267.0	2376.0	2412.0	2385.3
32.5°	1239.8	1335.7	1440.5	1568.7	1721.4	1909.9	2109.7	2253.0	2318.6	2291.1	2182.1
35°	1177.4	1263.9	1365.4	1493.7	1669.3	1899.7	2093.3	2190.4	2174.2	2018.6	1813.1
37.5°	1110.6	1181.1	1275.2	1409.3	1615.3	1859.2	2022.5	2036.9	1896.8	1657.8	1420.5
40°	1057.9	1121.3	1217.9	1358.0	1573.4	1819.3	1951.3	1893.4	1676.1	1410.2	1212.3
42.5°	1006.5	1060.1	1153.1	1304.2	1533.5	1765.1	1845.2	1719.1	1468.4	1217.0	1037.0
45°	919.6	970.0	1063.4	1218.5	1452.0	1661.2	1650.6	1431.4	1180.5	978.2	828.7
47.5°	837.2	881.3	968.9	1127.2	1356.2	1505.5	1406.5	1173.3	960.4	798.1	691.5
50°	778.9	822.5	909.7	1066.0	1279.5	1388.5	1247.1	1022.4	827.5	693.0	608.3
52.5°	723.1	765.7	845.4	997.7	1186.8	1252.0	1100.2	891.8	729.4	613.3	540.6
55°	645.1	677.4	749.0	894.7	1036.1	1051.0	897.2	722.9	589.0	508.1	458.3
57.5°	565.5	593.3	664.1	780.1	879.2	871.6	725.7	575.0	484.8	424.6	388.5
60°	513.7	541.1	603.3	703.0	777.7	751.5	617.7	496.2	419.1	374.9	346.2
62.5°	465.3	486.8	545.0	617.7	671.5	641.9	528.0	427.5	366.2	329.0	306.3
65°	395.4	412.8	459.5	497.5	527.4	498.8	404.1	334.4	290.2	264.0	248.4
67.5°	328.8	339.9	369.5	383.2	404.3	372.8	303.9	257.1	232.0	209.9	199.2
70°	287.0	295.1	310.7	321.9	327.5	295.1	244.1	209.8	188.6	173.1	166.3
72.5°	245.2	252.3	255.4	264.6	261.7	231.4	196.2	169.0	153.8	143.2	134.4
75°	187.4	190.5	187.4	183.7	175.5	154.4	130.2	116.5	105.2	100.2	97.1
77.5°	136.6	135.6	131.3	125.6	111.7	98.4	85.3	80.7	75.8	73.2	72.1
80°	105.2	102.7	99.0	89.7	77.8	68.5	65.4	62.3	60.4	57.3	56.6
82.5°	78.3	76.8	70.6	62.7	54.4	50.1	47.5	46.3	44.4	42.9	42.7
85°	41.7	39.8	33.0	28.7	27.4	26.1	25.5	25.5	23.1	22.4	22.4
87.5°	14.2	11.6	11.6	10.5	10.9	10.4	11.5	11.0	11.1	11.4	10.6
90°	3.6	5.5	8.3	10.1	12.0	14.7	17.5	20.3	23.0	22.1	23.0
92.5°	17.0	24.6	31.8	39.6	53.2	77.3	116.9	155.7	141.6	106.8	77.5
95°	34.1	44.2	59.8	83.7	119.6	197.9	335.0	486.0	545.8	442.7	331.4
97.5°	54.3	62.2	75.8	99.4	138.2	213.0	367.6	619.2	845.8	904.9	825.9
100°	69.0	75.5	88.3	110.4	146.3	210.8	347.0	589.1	871.6	1053.0	1085.1
102.5°	85.2	90.9	103.1	122.9	155.9	213.7	329.3	544.9	823.8	1060.3	1171.3
105°	109.6	115.0	126.1	143.5	172.1	221.8	316.6	490.6	740.0	1004.2	1196.5
107.5°	134.2	139.5	150.4	166.8	193.3	236.9	315.7	456.0	666.0	905.9	1123.9
110°	151.9	156.5	166.6	182.2	208.0	249.5	319.4	442.7	624.0	844.0	1054.8



TEST NUMBER: P332386-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	168.1	172.7	182.8	198.4	223.5	262.0	326.8	435.4	596.0	790.3	986.3
115°	192.3	197.9	207.1	222.8	247.6	282.6	338.7	432.6	566.0	725.2	895.6
117.5°	216.3	220.9	229.3	246.8	269.9	304.4	354.5	434.3	548.3	686.0	829.8
120°	231.0	235.6	244.9	262.3	285.3	318.5	366.3	437.2	540.3	665.4	795.2
122.5°	245.0	249.6	259.5	276.3	300.8	333.2	377.4	442.4	535.1	648.5	767.9
125°	264.2	269.7	279.8	297.3	322.1	354.3	394.8	450.0	528.3	626.8	731.7
127.5°	280.4	287.2	297.5	316.8	341.7	372.7	409.2	458.9	525.0	607.7	700.1
130°	289.9	298.2	309.3	328.6	353.4	383.8	418.7	464.8	522.8	597.3	680.2
132.5°	298.0	307.0	320.3	339.6	363.8	393.4	427.6	469.2	522.0	587.8	661.8
135°	311.1	321.2	335.0	354.3	379.2	407.7	439.0	475.9	520.9	575.3	636.9
137.5°	323.4	333.4	348.1	367.3	390.2	417.6	447.5	480.3	518.9	564.4	614.3
140°	332.2	341.4	356.2	374.6	397.6	424.3	451.9	483.2	518.2	557.8	601.0
142.5°	340.4	350.3	363.5	382.0	403.5	429.4	456.3	485.4	516.7	551.8	588.5
145°	353.4	361.7	375.5	391.2	412.3	436.3	461.1	486.9	514.5	544.0	573.4
147.5°	366.7	374.8	386.7	401.9	419.9	441.8	464.1	486.9	511.0	536.2	561.1
150°	375.5	382.9	394.8	407.7	424.3	445.4	464.8	486.9	508.0	531.1	552.2
152.5°	384.4	391.7	402.2	413.6	429.4	447.7	466.3	484.7	504.4	525.2	544.2
155°	398.5	404.1	413.3	423.3	436.3	451.9	466.7	482.3	498.0	516.3	532.0
157.5°	410.7	415.1	423.2	431.8	441.8	454.3	467.5	479.2	492.3	506.4	519.1
160°	418.7	422.5	429.8	436.3	445.4	456.5	467.5	477.7	487.8	499.8	511.7
162.5°	425.4	428.3	434.3	440.0	447.7	457.2	466.8	474.8	483.4	493.1	502.9
165°	434.4	436.3	440.8	444.6	451.0	458.4	464.8	470.3	476.7	484.1	491.5
167.5°	441.8	442.7	446.2	448.8	452.8	458.2	463.3	465.9	470.2	475.5	481.6
170°	445.4	446.4	449.2	451.0	452.8	457.4	461.1	463.0	465.7	470.3	474.9
172.5°	449.2	449.3	451.4	452.5	453.6	457.4	460.4	460.7	462.0	465.2	469.1
175°	452.8	451.9	453.8	453.8	454.7	456.5	458.4	457.4	457.4	459.3	461.1
177.5°	454.7	453.9	454.7	454.7	454.7	455.4	456.9	455.4	454.7	455.4	456.1
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7	454.7



TEST NUMBER: P332386-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1534.1	1534.1	1536.1	1543.6	1544.6	1551.1	1549.1
5°	1686.1	1697.9	1702.2	1720.9	1732.2	1737.2	1727.2
7.5°	1871.8	1905.3	1921.0	1940.6	1958.0	1963.2	1949.6
10°	2007.4	2042.2	2071.5	2089.5	2106.3	2117.6	2131.9
12.5°	2138.3	2181.2	2209.0	2234.5	2251.8	2266.0	2268.3
15°	2280.7	2345.4	2394.6	2430.7	2448.8	2458.1	2454.4
17.5°	2424.2	2484.3	2519.3	2556.1	2581.2	2582.4	2583.1
20°	2505.4	2564.0	2604.5	2631.9	2659.9	2658.6	2664.8
22.5°	2559.8	2605.8	2636.9	2656.7	2666.3	2661.7	2662.8
25°	2585.1	2598.8	2593.3	2561.5	2553.4	2524.1	2529.1
27.5°	2454.2	2389.4	2322.4	2236.3	2168.3	2113.9	2116.7
30°	2276.3	2161.8	2031.0	1921.4	1823.0	1795.6	1737.2
32.5°	2027.7	1855.9	1702.8	1600.7	1516.2	1493.3	1442.2
35°	1606.4	1439.6	1282.0	1187.3	1150.0	1097.7	1097.1
37.5°	1248.6	1101.7	1018.4	947.4	910.1	878.5	875.4
40°	1050.4	935.8	872.9	821.9	785.1	761.4	755.9
42.5°	911.9	819.3	760.3	728.7	700.4	688.2	679.1
45°	744.7	682.4	641.3	612.7	599.6	590.3	585.3
47.5°	622.9	581.1	553.2	534.1	523.5	513.7	516.3
50°	556.7	522.4	501.8	483.8	475.7	468.8	469.4
52.5°	503.4	472.6	456.0	442.9	432.8	428.0	425.6
55°	427.1	407.8	391.0	381.7	376.0	369.2	367.3
57.5°	364.3	349.4	335.7	325.1	323.8	317.2	318.1
60°	322.5	310.1	298.9	293.3	288.9	283.3	285.2
62.5°	288.1	277.7	267.5	262.8	258.5	254.4	255.2
65°	236.0	226.0	219.8	217.3	215.4	213.6	211.7
67.5°	188.1	182.0	178.1	172.7	168.9	168.3	166.4
70°	158.1	150.0	143.2	136.3	134.5	133.9	134.5
72.5°	126.7	121.7	119.8	116.5	116.1	114.5	115.6
75°	95.3	93.4	92.1	89.7	89.7	89.7	89.7
77.5°	70.3	69.1	68.4	67.9	67.3	66.4	66.2
80°	54.8	54.2	52.9	52.9	52.3	52.9	52.3
82.5°	41.4	41.2	40.0	40.0	39.4	39.0	39.4
85°	21.2	20.5	21.8	20.5	21.2	20.0	21.2
87.5°	10.8	10.9	10.9	10.6	10.3	11.5	10.3
90°	23.9	24.9	26.7	25.7	26.7	27.6	26.7
92.5°	61.5	54.3	49.5	47.8	45.1	46.0	44.4
95°	224.6	175.8	142.7	125.2	116.9	110.4	106.8
97.5°	661.6	542.9	432.8	364.9	323.4	298.6	290.7
100°	1010.6	902.9	772.2	679.2	612.0	576.2	577.1
102.5°	1168.9	1106.1	1023.3	950.9	897.8	867.8	846.6
105°	1288.6	1306.1	1282.1	1239.8	1204.8	1175.4	1170.8
107.5°	1273.4	1354.1	1386.9	1387.6	1375.8	1365.9	1357.4
110°	1224.2	1340.1	1404.5	1430.3	1437.7	1435.8	1434.0



TEST NUMBER: P332386-927

CATALOG NUMBER: S123RDIP-S1165D1195U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1159.4	1289.3	1372.1	1419.3	1442.1	1449.1	1449.5
115°	1055.7	1191.0	1291.3	1360.3	1400.8	1419.3	1423.9
117.5°	968.0	1089.6	1191.4	1263.4	1309.7	1336.3	1342.5
120°	919.5	1029.9	1122.9	1195.6	1247.1	1269.2	1274.8
122.5°	880.4	982.8	1069.1	1133.8	1180.1	1204.4	1211.4
125°	832.0	920.4	994.0	1053.0	1093.4	1116.4	1122.9
127.5°	789.5	869.2	936.2	988.7	1023.3	1044.1	1050.0
130°	763.0	837.6	900.2	949.0	982.1	1001.4	1008.8
132.5°	738.0	807.4	867.0	912.8	945.9	963.1	968.3
135°	702.3	762.1	814.5	859.7	887.2	903.8	910.3
137.5°	667.8	719.4	764.9	802.8	830.8	844.7	849.0
140°	647.9	692.1	731.7	766.7	792.5	807.2	806.3
142.5°	628.8	667.1	701.6	731.3	754.2	767.4	766.5
145°	603.8	633.3	659.9	682.9	702.3	709.6	711.5
147.5°	585.2	609.0	627.9	645.4	658.5	665.4	666.1
150°	573.4	592.7	610.2	624.0	634.1	639.7	639.7
152.5°	562.4	579.5	594.1	604.9	614.3	617.6	617.6
155°	546.7	560.5	571.6	579.9	587.2	589.1	589.9
157.5°	531.5	542.1	550.7	557.9	563.5	564.9	564.7
160°	521.9	531.1	537.5	544.0	549.5	549.5	548.6
162.5°	511.6	520.0	525.7	530.0	534.7	534.7	533.9
165°	497.0	503.4	508.0	511.7	515.4	514.5	514.5
167.5°	485.8	489.5	492.8	494.4	497.0	496.1	496.1
170°	477.7	481.3	483.2	484.1	486.0	485.1	485.1
172.5°	471.0	474.0	475.1	475.3	477.1	475.5	474.8
175°	462.0	463.9	463.9	463.9	464.8	463.9	463.0
177.5°	456.9	457.6	457.6	456.9	457.6	456.1	456.1
180°	454.7	454.7	454.7	454.7	454.7	454.7	454.7

(END OF REPORT)