

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332309-930

Luminaire Tested: **S123RDIP-S775D585U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332309-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D585U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4288.3 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332309-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332309-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	55	53	52	47
2	91	84	77	72	84	78	73	68	67	63	60	58	55	52	49	46	45	40
3	83	74	67	61	77	69	62	57	60	55	51	51	48	44	43	41	38	35
4	76	65	58	52	71	61	54	49	53	48	44	46	42	38	39	36	33	30
5	70	59	50	45	65	55	48	42	48	42	38	41	37	34	35	32	29	26
6	65	53	45	39	60	49	42	37	43	37	33	37	33	30	32	29	26	23
7	60	48	40	34	56	45	38	33	39	34	29	34	30	26	29	26	23	21
8	56	43	36	30	52	41	34	29	36	30	26	31	27	24	27	23	21	19
9	52	40	32	27	48	37	31	26	33	27	24	29	24	21	25	21	19	17
10	49	36	29	25	45	34	28	23	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11330	11330	11330
5°	11373	11217	11282
10°	11309	11075	11038
15°	11188	10816	10702
20°	11021	10493	10247
25°	10849	10128	9804
30°	10621	9708	9178
35°	10387	9289	8604
40°	10172	8792	7893
45°	9889	8304	7252
50°	9577	7748	6532
55°	9259	7112	5863
60°	8968	6433	5126
65°	8588	5695	4391
70°	8113	4784	3547
75°	7419	3764	3335
80°	6614	3335	3068
85°	5582	2952	2742



TEST NUMBER: P332309-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.8	2.3
10°-20°	275.0	6.4
20°-30°	396.0	9.2
30°-40°	446.1	10.4
40°-50°	426.7	10.0
50°-60°	349.5	8.1
60°-70°	235.8	5.5
70°-80°	118.6	2.8
80°-90°	33.1	0.8
90°-100°	22.8	0.5
100°-110°	108.4	2.5
110°-120°	260.5	6.1
120°-130°	331.7	7.7
130°-140°	354.4	8.3
140°-150°	331.4	7.7
150°-160°	267.4	6.2
160°-170°	172.6	4.0
170°-180°	59.5	1.4
0°-30°	769.9	18.0
0°-40°	1215.9	28.4
0°-60°	1992.1	46.5
0°-90°	2379.6	55.5
90°-120°	391.7	9.1
90°-150°	1409.3	32.9
90°-180°	1909.0	44.5
0°-180°	4288.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1053	1053	1053	1053	1053	
5°	1053	1048	1038	1045	1044	100
15°	1004	994	971	966	960	283
25°	914	891	853	835	826	420
35°	790	759	707	671	655	495
45°	650	610	546	498	476	501
55°	493	450	379	331	312	442
65°	337	289	224	184	172	334
75°	178	137	90	82	80	190
85°	45	27	24	22	22	51
90°	0	5	11	13	14	4
95°	28	11	14	18	18	35
105°	139	141	102	24	20	147
115°	260	263	267	271	274	257
125°	366	370	372	373	374	327
135°	456	459	461	462	461	351
145°	526	530	531	531	532	329
155°	580	579	579	581	579	267
165°	612	610	610	613	610	173
175°	626	624	624	627	624	60
180°	626	626	626	626	626	



TEST NUMBER: P332309-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6
2.5°	1056.0	1055.4	1054.8	1054.2	1053.6	1052.4	1050.5	1048.7	1046.9	1045.1	1046.8
5°	1052.6	1051.7	1050.7	1049.8	1048.8	1047.2	1044.9	1042.6	1040.3	1038.1	1039.8
7.5°	1042.8	1041.9	1040.8	1039.8	1038.8	1036.7	1033.8	1030.9	1027.9	1024.9	1025.9
10°	1034.7	1033.3	1032.0	1030.7	1029.3	1027.0	1023.5	1020.2	1016.8	1013.3	1013.5
12.5°	1023.0	1021.6	1020.1	1018.6	1017.2	1014.3	1010.2	1006.0	1001.8	997.6	997.5
15°	1004.0	1001.8	999.7	997.7	995.6	991.9	986.6	981.3	975.9	970.6	969.7
17.5°	979.8	977.5	975.0	972.6	970.1	965.6	958.8	952.0	945.3	938.6	936.5
20°	962.1	959.0	956.0	953.0	950.0	944.9	937.6	930.4	923.2	916.0	913.5
22.5°	942.3	938.8	935.3	931.8	928.3	922.8	915.1	907.4	899.8	892.1	889.0
25°	913.5	908.7	903.9	899.2	894.5	887.7	879.0	870.3	861.5	852.8	848.8
27.5°	878.4	873.2	868.0	862.7	857.5	850.0	840.3	830.6	820.8	811.1	805.6
30°	854.5	848.8	843.2	837.5	831.8	823.6	813.0	802.3	791.7	781.1	774.7
32.5°	830.6	824.2	817.7	811.3	804.9	796.0	784.7	773.6	762.3	751.1	744.0
35°	790.5	783.7	776.8	770.1	763.2	753.9	742.2	730.3	718.6	706.9	698.7
37.5°	749.9	742.2	734.7	727.1	719.5	709.5	696.9	684.4	671.8	659.3	650.0
40°	723.9	715.6	707.2	698.9	690.6	679.6	666.2	652.7	639.2	625.7	615.9
42.5°	694.6	686.2	677.8	669.5	661.2	650.0	636.1	622.2	608.3	594.4	583.6
45°	649.6	641.2	632.6	624.0	615.5	604.0	589.3	574.7	560.1	545.5	534.7
47.5°	604.8	595.4	586.0	576.7	567.3	555.3	540.7	526.0	511.4	496.8	485.1
50°	571.9	563.0	554.2	545.2	536.3	524.2	508.8	493.4	478.1	462.7	450.9
52.5°	542.6	533.0	523.3	513.6	503.9	491.5	476.2	461.1	445.8	430.6	418.4
55°	493.4	484.1	474.8	465.5	456.2	443.5	427.4	411.3	395.2	379.0	368.0
57.5°	448.0	437.9	427.8	417.6	407.5	394.4	378.1	361.9	345.7	329.5	319.1
60°	416.6	406.2	395.7	385.3	374.9	361.7	346.0	330.3	314.5	298.8	288.5
62.5°	385.1	374.7	364.3	353.8	343.5	330.4	314.6	298.9	283.2	267.3	257.7
65°	337.2	326.8	316.3	305.9	295.5	282.8	268.1	253.2	238.5	223.6	214.3
67.5°	289.3	278.7	268.2	257.6	247.0	234.6	220.5	206.3	192.1	177.9	171.0
70°	257.8	247.6	237.3	227.1	216.9	205.0	191.8	178.6	165.3	152.0	145.3
72.5°	226.4	216.3	206.2	196.1	186.1	175.0	162.9	150.8	138.8	126.7	121.2
75°	178.4	169.3	160.2	151.1	142.0	132.2	121.8	111.4	100.9	90.5	88.6
77.5°	134.7	126.5	118.2	110.0	101.7	94.3	87.6	80.9	74.2	67.4	66.4
80°	106.7	98.9	91.2	83.4	75.6	69.7	65.7	61.7	57.8	53.8	53.2
82.5°	80.1	73.4	66.6	59.9	53.2	48.9	47.0	45.2	43.4	41.5	40.9
85°	45.2	41.1	36.9	32.7	28.5	26.2	25.6	25.0	24.5	23.9	23.6
87.5°	16.5	15.0	13.5	12.1	10.6	10.0	10.3	10.6	10.8	11.1	11.0
90°	0.5	1.5	2.5	3.6	4.6	5.8	7.1	8.5	9.8	11.2	11.6
92.5°	8.6	8.4	8.1	7.7	7.5	7.8	8.9	9.9	10.9	11.9	12.6
95°	28.4	24.1	19.9	15.7	11.4	9.9	11.0	12.1	13.3	14.4	15.2
97.5°	57.0	55.1	53.2	51.3	49.4	44.8	37.3	29.8	22.4	15.0	15.8
100°	78.6	80.6	82.8	84.8	86.8	79.8	63.7	47.6	31.5	15.3	16.1
102.5°	103.1	104.6	106.2	107.6	109.1	101.0	83.4	65.8	48.2	30.6	28.0
105°	138.6	139.7	140.9	141.9	143.1	139.0	129.7	120.4	111.1	101.8	83.6
107.5°	175.9	176.8	177.8	178.7	179.6	180.8	182.2	183.7	185.2	186.6	173.3
110°	200.9	201.7	202.5	203.3	204.2	205.2	206.3	207.4	208.6	209.7	206.3



TEST NUMBER: P332309-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	224.7	225.4	226.2	226.9	227.6	228.6	229.8	230.9	232.0	233.2	233.3
115°	259.9	260.6	261.1	261.8	262.4	263.2	264.2	265.1	266.0	266.9	268.0
117.5°	294.1	294.8	295.6	296.4	297.1	297.7	298.2	298.7	299.2	299.6	300.5
120°	315.3	316.2	317.2	318.0	319.0	319.6	319.9	320.2	320.6	320.8	321.7
122.5°	336.9	337.6	338.3	339.2	339.9	340.5	340.9	341.3	341.7	342.1	342.7
125°	366.4	367.3	368.1	368.9	369.7	370.4	370.8	371.2	371.6	372.0	372.2
127.5°	395.1	395.9	396.7	397.5	398.4	399.0	399.5	400.1	400.6	401.0	401.4
130°	412.9	413.8	414.6	415.4	416.2	416.9	417.3	417.7	418.1	418.5	418.9
132.5°	430.1	430.9	431.7	432.5	433.3	433.9	434.2	434.6	434.9	435.3	435.7
135°	456.2	456.8	457.4	458.0	458.7	459.2	459.6	460.0	460.4	460.8	461.1
137.5°	478.5	479.3	480.0	480.9	481.6	482.2	482.3	482.6	482.8	483.1	483.6
140°	493.3	494.0	494.6	495.2	495.9	496.4	496.6	496.9	497.3	497.6	498.0
142.5°	507.1	507.8	508.4	509.0	509.6	510.1	510.4	510.7	511.0	511.4	511.7
145°	526.4	527.1	527.8	528.6	529.3	529.8	529.9	530.2	530.4	530.6	530.8
147.5°	544.5	545.0	545.5	545.9	546.4	546.7	547.0	547.1	547.4	547.6	547.8
150°	555.7	556.0	556.3	556.6	556.9	557.2	557.4	557.6	557.8	558.0	558.2
152.5°	565.7	565.9	566.0	566.1	566.3	566.5	566.6	566.7	566.8	567.0	567.3
155°	579.8	579.7	579.4	579.3	579.0	579.0	579.1	579.2	579.3	579.4	579.9
157.5°	590.8	590.8	590.8	590.8	590.8	590.7	590.6	590.5	590.4	590.3	590.9
160°	597.5	597.5	597.4	597.2	597.1	597.0	596.9	596.8	596.7	596.6	597.2
162.5°	603.9	603.6	603.3	603.1	602.8	602.6	602.5	602.4	602.3	602.2	602.9
165°	611.5	611.1	610.9	610.6	610.3	610.0	609.9	609.8	609.8	609.6	610.5
167.5°	617.4	617.0	616.6	616.2	615.8	615.6	615.6	615.6	615.6	615.6	616.4
170°	620.8	620.4	620.0	619.5	619.1	618.9	618.9	618.9	618.9	618.9	619.8
172.5°	623.1	622.6	622.0	621.5	621.0	620.9	620.9	621.0	621.1	621.2	622.0
175°	625.9	625.4	624.8	624.4	623.9	623.6	623.7	623.9	623.9	624.0	624.8
177.5°	626.6	626.2	625.8	625.4	625.0	624.8	624.9	625.0	625.1	625.2	625.8
180°	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9



TEST NUMBER: P332309-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6
2.5°	1048.4	1050.1	1051.7	1052.5	1052.1	1051.8	1051.5	1051.2
5°	1041.5	1043.2	1044.9	1045.5	1045.2	1044.8	1044.4	1044.1
7.5°	1026.9	1027.8	1028.7	1028.9	1028.3	1027.6	1027.0	1026.3
10°	1013.7	1013.9	1014.1	1013.7	1012.8	1011.8	1010.9	1009.9
12.5°	997.4	997.3	997.2	996.5	995.5	994.3	993.3	992.1
15°	968.7	967.8	966.9	965.7	964.4	963.0	961.7	960.4
17.5°	934.5	932.5	930.5	928.5	926.5	924.5	922.6	920.6
20°	911.1	908.6	906.1	903.8	901.5	899.2	896.9	894.6
22.5°	886.0	882.9	879.8	877.2	875.1	872.9	870.8	868.7
25°	844.9	840.9	836.9	833.9	831.8	829.6	827.6	825.5
27.5°	800.1	794.6	789.0	784.6	781.5	778.3	775.1	771.9
30°	768.3	761.7	755.3	750.6	747.5	744.5	741.4	738.4
32.5°	736.9	729.9	722.8	717.7	714.5	711.3	708.2	705.0
35°	690.6	682.4	674.3	668.5	665.0	661.6	658.2	654.8
37.5°	640.7	631.4	622.2	615.5	611.2	607.0	602.8	598.6
40°	606.0	596.1	586.3	579.2	574.8	570.5	566.1	561.7
42.5°	572.7	562.0	551.2	543.9	540.0	536.1	532.1	528.2
45°	523.9	513.1	502.2	494.6	490.0	485.4	480.9	476.4
47.5°	473.3	461.5	449.8	441.9	437.8	433.7	429.7	425.7
50°	439.2	427.4	415.6	407.6	403.2	398.8	394.5	390.1
52.5°	406.2	394.0	381.7	373.7	369.7	365.8	361.9	358.0
55°	357.0	346.0	335.0	327.6	323.8	320.0	316.3	312.4
57.5°	308.8	298.3	288.0	281.1	277.9	274.7	271.4	268.2
60°	278.3	268.1	257.8	251.1	247.9	244.6	241.4	238.1
62.5°	248.1	238.5	228.9	222.3	218.9	215.6	212.2	208.8
65°	205.0	195.8	186.5	180.8	178.7	176.6	174.6	172.4
67.5°	164.0	157.1	150.1	145.5	143.3	141.0	138.8	136.6
70°	138.7	132.0	125.4	121.1	119.0	116.8	114.8	112.7
72.5°	115.9	110.4	105.0	101.8	100.9	100.1	99.2	98.3
75°	86.7	84.8	82.9	81.8	81.4	81.0	80.6	80.2
77.5°	65.4	64.3	63.3	62.6	62.3	61.9	61.5	61.1
80°	52.7	52.1	51.5	51.0	50.6	50.3	49.9	49.5
82.5°	40.4	39.8	39.2	38.9	38.8	38.7	38.6	38.6
85°	23.2	22.7	22.4	22.2	22.2	22.2	22.2	22.2
87.5°	11.0	10.9	10.8	10.8	10.6	10.5	10.4	10.3
90°	12.0	12.4	12.8	13.1	13.4	13.5	13.8	13.9
92.5°	13.2	13.9	14.5	14.9	15.1	15.2	15.3	15.4
95°	15.9	16.6	17.3	17.7	17.7	17.7	17.7	17.7
97.5°	16.6	17.4	18.3	18.8	18.8	18.9	19.1	19.2
100°	17.0	17.9	18.7	19.1	19.2	19.3	19.4	19.6
102.5°	25.4	22.9	20.4	19.2	19.3	19.6	19.7	19.9
105°	65.2	47.0	28.7	19.6	19.8	20.1	20.2	20.5
107.5°	159.8	146.4	133.0	119.4	105.6	91.8	78.0	64.2
110°	202.9	199.5	196.1	186.9	172.2	157.4	142.7	127.8



TEST NUMBER: P332309-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	233.3	233.3	233.4	231.9	228.8	225.6	222.5	219.4
115°	269.0	270.0	271.1	271.7	272.1	272.6	273.0	273.5
117.5°	301.3	302.1	303.0	303.5	303.5	303.6	303.7	303.8
120°	322.5	323.3	324.2	324.6	324.6	324.6	324.6	324.6
122.5°	343.2	343.8	344.4	344.7	344.8	344.9	345.0	345.0
125°	372.4	372.6	372.8	373.1	373.2	373.5	373.7	373.9
127.5°	401.7	402.0	402.4	402.4	402.2	402.0	401.8	401.6
130°	419.3	419.7	420.1	420.3	420.0	419.9	419.6	419.5
132.5°	436.1	436.5	436.9	437.0	436.7	436.3	436.1	435.8
135°	461.5	461.8	462.0	462.0	461.8	461.5	461.1	460.8
137.5°	484.0	484.5	485.0	485.2	484.9	484.8	484.5	484.4
140°	498.4	498.8	499.2	499.3	499.1	498.9	498.7	498.5
142.5°	512.0	512.3	512.7	512.7	512.4	512.1	511.8	511.5
145°	531.0	531.2	531.4	531.5	531.5	531.5	531.5	531.5
147.5°	548.0	548.2	548.5	548.3	547.8	547.3	546.9	546.4
150°	558.4	558.6	558.8	558.8	558.5	558.2	557.8	557.6
152.5°	567.7	568.0	568.4	568.3	567.9	567.4	567.0	566.5
155°	580.4	581.0	581.5	581.4	580.8	580.2	579.6	578.9
157.5°	591.5	592.2	592.8	592.6	591.8	591.1	590.3	589.5
160°	597.9	598.4	599.1	599.0	598.3	597.6	596.9	596.1
162.5°	603.6	604.3	605.0	605.0	604.4	603.7	603.1	602.5
165°	611.3	612.1	612.9	613.0	612.3	611.6	610.8	610.1
167.5°	617.3	618.1	618.9	618.9	618.1	617.3	616.4	615.6
170°	620.6	621.4	622.2	622.2	621.4	620.6	619.8	618.9
172.5°	622.8	623.6	624.4	624.4	623.5	622.6	621.7	620.8
175°	625.5	626.2	627.0	626.9	626.1	625.3	624.4	623.5
177.5°	626.5	627.1	627.8	627.7	626.9	626.1	625.3	624.4
180°	625.9	625.9	625.9	625.9	625.9	625.9	625.9	625.9

(END OF REPORT)