

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332310-930

Luminaire Tested: **S123RDIP-S775D585U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332310-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D585U930-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4019.8 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332310-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332310-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	109	109	109	109	102	102	102	102	88	88	88		76	76	76		65	65	65	59
1	100	96	92	89	93	90	87	84	78	76	74		68	66	64		58	56	55	51
2	92	84	78	73	85	79	74	69	69	65	61		60	57	54		51	49	47	43
3	84	74	67	61	78	70	63	58	61	56	52		53	49	46		46	43	41	37
4	77	66	58	52	72	62	55	50	55	49	45		48	43	40		41	38	35	32
5	71	59	51	45	66	56	48	43	49	43	39		43	38	35		37	34	31	28
6	65	53	45	39	61	50	43	38	44	39	34		39	34	31		34	30	27	25
7	60	48	40	35	56	46	38	33	40	35	30		36	31	27		31	27	24	22
8	56	44	36	31	52	42	34	30	37	31	27		33	28	25		29	25	22	20
9	52	40	33	28	49	38	31	27	34	28	24		30	25	22		26	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22		28	23	20		25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11330	11330	11330
5°	11373	11217	11282
10°	11309	11075	11038
15°	11188	10816	10702
20°	11021	10493	10247
25°	10849	10128	9804
30°	10621	9708	9178
35°	10387	9289	8604
40°	10172	8792	7893
45°	9889	8304	7252
50°	9577	7748	6532
55°	9259	7112	5863
60°	8968	6433	5126
65°	8588	5695	4391
70°	8113	4784	3547
75°	7419	3764	3335
80°	6614	3335	3068
85°	5582	2952	2742



TEST NUMBER: P332310-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.8	2.5
10°-20°	275.0	6.8
20°-30°	396.0	9.9
30°-40°	446.1	11.1
40°-50°	426.7	10.6
50°-60°	349.5	8.7
60°-70°	235.8	5.9
70°-80°	118.6	3.0
80°-90°	33.1	0.8
90°-100°	38.6	1.0
100°-110°	115.4	2.9
110°-120°	196.3	4.9
120°-130°	258.2	6.4
130°-140°	290.3	7.2
140°-150°	285.3	7.1
150°-160°	240.2	6.0
160°-170°	159.9	4.0
170°-180°	56.0	1.4
0°-30°	769.9	19.2
0°-40°	1215.9	30.2
0°-60°	1992.1	49.6
0°-90°	2379.6	59.2
90°-120°	350.3	8.7
90°-150°	1184.1	29.5
90°-180°	1640.0	40.8
0°-180°	4019.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1053	1053	1053	1053	1053	
5°	1053	1048	1038	1045	1044	100
15°	1004	994	971	966	960	283
25°	914	891	853	835	826	420
35°	790	759	707	671	655	495
45°	650	610	546	498	476	501
55°	493	450	379	331	312	442
65°	337	289	224	184	172	334
75°	178	137	90	82	80	190
85°	45	27	24	22	22	51
90°	0	5	11	13	14	4
95°	28	31	34	36	36	31
105°	105	106	110	110	111	112
115°	198	199	198	198	198	195
125°	289	291	290	288	286	258
135°	375	378	378	376	375	289
145°	455	456	458	457	455	284
155°	521	521	522	523	520	240
165°	568	566	566	569	566	160
175°	591	589	589	591	588	56
180°	592	592	592	592	592	



TEST NUMBER: P332310-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6
2.5°	1056.0	1055.4	1054.8	1054.2	1053.6	1052.4	1050.5	1048.7	1046.9	1045.1	1046.8
5°	1052.6	1051.7	1050.7	1049.8	1048.8	1047.2	1044.9	1042.6	1040.3	1038.1	1039.8
7.5°	1042.8	1041.9	1040.8	1039.8	1038.8	1036.7	1033.8	1030.9	1027.9	1024.9	1025.9
10°	1034.7	1033.3	1032.0	1030.7	1029.3	1027.0	1023.5	1020.2	1016.8	1013.3	1013.5
12.5°	1023.0	1021.6	1020.1	1018.6	1017.2	1014.3	1010.2	1006.0	1001.8	997.6	997.5
15°	1004.0	1001.8	999.7	997.7	995.6	991.9	986.6	981.3	975.9	970.6	969.7
17.5°	979.8	977.5	975.0	972.6	970.1	965.6	958.8	952.0	945.3	938.6	936.5
20°	962.1	959.0	956.0	953.0	950.0	944.9	937.6	930.4	923.2	916.0	913.5
22.5°	942.3	938.8	935.3	931.8	928.3	922.8	915.1	907.4	899.8	892.1	889.0
25°	913.5	908.7	903.9	899.2	894.5	887.7	879.0	870.3	861.5	852.8	848.8
27.5°	878.4	873.2	868.0	862.7	857.5	850.0	840.3	830.6	820.8	811.1	805.6
30°	854.5	848.8	843.2	837.5	831.8	823.6	813.0	802.3	791.7	781.1	774.7
32.5°	830.6	824.2	817.7	811.3	804.9	796.0	784.7	773.6	762.3	751.1	744.0
35°	790.5	783.7	776.8	770.1	763.2	753.9	742.2	730.3	718.6	706.9	698.7
37.5°	749.9	742.2	734.7	727.1	719.5	709.5	696.9	684.4	671.8	659.3	650.0
40°	723.9	715.6	707.2	698.9	690.6	679.6	666.2	652.7	639.2	625.7	615.9
42.5°	694.6	686.2	677.8	669.5	661.2	650.0	636.1	622.2	608.3	594.4	583.6
45°	649.6	641.2	632.6	624.0	615.5	604.0	589.3	574.7	560.1	545.5	534.7
47.5°	604.8	595.4	586.0	576.7	567.3	555.3	540.7	526.0	511.4	496.8	485.1
50°	571.9	563.0	554.2	545.2	536.3	524.2	508.8	493.4	478.1	462.7	450.9
52.5°	542.6	533.0	523.3	513.6	503.9	491.5	476.2	461.1	445.8	430.6	418.4
55°	493.4	484.1	474.8	465.5	456.2	443.5	427.4	411.3	395.2	379.0	368.0
57.5°	448.0	437.9	427.8	417.6	407.5	394.4	378.1	361.9	345.7	329.5	319.1
60°	416.6	406.2	395.7	385.3	374.9	361.7	346.0	330.3	314.5	298.8	288.5
62.5°	385.1	374.7	364.3	353.8	343.5	330.4	314.6	298.9	283.2	267.3	257.7
65°	337.2	326.8	316.3	305.9	295.5	282.8	268.1	253.2	238.5	223.6	214.3
67.5°	289.3	278.7	268.2	257.6	247.0	234.6	220.5	206.3	192.1	177.9	171.0
70°	257.8	247.6	237.3	227.1	216.9	205.0	191.8	178.6	165.3	152.0	145.3
72.5°	226.4	216.3	206.2	196.1	186.1	175.0	162.9	150.8	138.8	126.7	121.2
75°	178.4	169.3	160.2	151.1	142.0	132.2	121.8	111.4	100.9	90.5	88.6
77.5°	134.7	126.5	118.2	110.0	101.7	94.3	87.6	80.9	74.2	67.4	66.4
80°	106.7	98.9	91.2	83.4	75.6	69.7	65.7	61.7	57.8	53.8	53.2
82.5°	80.1	73.4	66.6	59.9	53.2	48.9	47.0	45.2	43.4	41.5	40.9
85°	45.2	41.1	36.9	32.7	28.5	26.2	25.6	25.0	24.5	23.9	23.6
87.5°	16.5	15.0	13.5	12.1	10.6	10.0	10.3	10.6	10.8	11.1	11.0
90°	0.5	1.5	2.5	3.6	4.6	5.8	7.1	8.5	9.8	11.2	11.6
92.5°	11.3	12.0	12.6	13.4	14.1	14.8	15.6	16.3	17.1	17.9	18.2
95°	27.5	28.1	28.9	29.6	30.3	31.1	32.0	32.8	33.6	34.4	34.8
97.5°	48.8	49.2	49.8	50.4	50.9	51.4	52.0	52.7	53.2	53.9	54.3
100°	63.3	63.8	64.5	65.1	65.7	66.3	66.8	67.3	67.8	68.3	68.6
102.5°	80.0	80.4	80.7	81.1	81.4	82.0	82.7	83.4	84.1	84.7	85.0
105°	104.6	104.8	105.0	105.3	105.5	106.0	107.0	107.9	108.8	109.7	109.7
107.5°	133.3	133.4	133.5	133.6	133.8	134.0	134.4	134.8	135.2	135.5	135.8
110°	151.2	151.3	151.6	151.7	152.0	152.1	152.4	152.6	152.8	153.0	153.4



TEST NUMBER: P332310-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	169.7	169.8	170.0	170.1	170.2	170.3	170.4	170.4	170.5	170.5	171.0
115°	197.6	198.0	198.3	198.6	198.9	198.9	198.7	198.5	198.3	198.1	198.2
117.5°	225.8	225.9	226.2	226.3	226.6	226.5	226.2	226.0	225.8	225.4	225.4
120°	243.2	243.9	244.4	245.1	245.7	245.7	245.2	244.8	244.2	243.7	243.6
122.5°	261.5	261.9	262.4	262.8	263.3	263.3	263.1	262.9	262.5	262.3	262.0
125°	289.3	289.6	289.8	290.2	290.5	290.6	290.3	290.2	289.9	289.8	289.3
127.5°	315.0	315.6	316.3	316.9	317.6	317.8	317.6	317.3	317.1	316.9	316.3
130°	332.1	332.9	333.7	334.5	335.3	335.6	335.3	335.0	334.7	334.4	333.9
132.5°	349.1	350.0	350.8	351.6	352.5	352.8	352.5	352.3	352.0	351.9	351.3
135°	375.3	375.9	376.5	377.2	377.7	378.1	377.9	377.8	377.7	377.6	377.2
137.5°	399.5	400.0	400.5	401.0	401.5	401.9	402.2	402.4	402.8	403.0	402.6
140°	416.2	416.7	417.3	417.8	418.2	418.6	418.7	418.8	418.9	419.0	418.9
142.5°	431.5	431.9	432.5	433.0	433.5	433.9	434.1	434.2	434.5	434.6	434.6
145°	455.3	455.5	455.7	455.9	456.1	456.3	456.6	457.0	457.3	457.6	457.5
147.5°	476.1	476.5	476.9	477.2	477.6	477.9	478.3	478.5	478.8	479.1	479.1
150°	490.6	490.8	491.1	491.2	491.5	491.6	491.9	492.0	492.3	492.4	492.4
152.5°	502.6	502.8	503.1	503.4	503.7	503.9	504.0	504.1	504.3	504.3	504.5
155°	521.3	521.3	521.3	521.3	521.3	521.4	521.5	521.5	521.7	521.8	522.2
157.5°	537.3	537.2	537.0	537.0	536.8	536.8	536.9	537.0	537.0	537.1	537.5
160°	547.3	547.1	546.9	546.7	546.5	546.4	546.4	546.4	546.4	546.4	546.9
162.5°	556.3	556.0	555.7	555.4	555.1	555.1	555.1	555.2	555.3	555.4	555.9
165°	567.8	567.5	567.2	566.9	566.6	566.4	566.4	566.4	566.4	566.4	567.0
167.5°	577.0	576.6	576.2	575.8	575.4	575.2	575.3	575.4	575.4	575.5	576.2
170°	582.2	581.8	581.4	581.0	580.6	580.3	580.3	580.3	580.3	580.3	581.1
172.5°	586.3	585.9	585.5	585.1	584.7	584.5	584.5	584.5	584.5	584.5	585.1
175°	590.6	590.2	589.8	589.4	589.0	588.7	588.7	588.7	588.7	588.7	589.4
177.5°	592.4	592.1	591.7	591.3	591.0	590.8	590.8	590.8	590.8	590.8	591.3
180°	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0



TEST NUMBER: P332310-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6
2.5°	1048.4	1050.1	1051.7	1052.5	1052.1	1051.8	1051.5	1051.2
5°	1041.5	1043.2	1044.9	1045.5	1045.2	1044.8	1044.4	1044.1
7.5°	1026.9	1027.8	1028.7	1028.9	1028.3	1027.6	1027.0	1026.3
10°	1013.7	1013.9	1014.1	1013.7	1012.8	1011.8	1010.9	1009.9
12.5°	997.4	997.3	997.2	996.5	995.5	994.3	993.3	992.1
15°	968.7	967.8	966.9	965.7	964.4	963.0	961.7	960.4
17.5°	934.5	932.5	930.5	928.5	926.5	924.5	922.6	920.6
20°	911.1	908.6	906.1	903.8	901.5	899.2	896.9	894.6
22.5°	886.0	882.9	879.8	877.2	875.1	872.9	870.8	868.7
25°	844.9	840.9	836.9	833.9	831.8	829.6	827.6	825.5
27.5°	800.1	794.6	789.0	784.6	781.5	778.3	775.1	771.9
30°	768.3	761.7	755.3	750.6	747.5	744.5	741.4	738.4
32.5°	736.9	729.9	722.8	717.7	714.5	711.3	708.2	705.0
35°	690.6	682.4	674.3	668.5	665.0	661.6	658.2	654.8
37.5°	640.7	631.4	622.2	615.5	611.2	607.0	602.8	598.6
40°	606.0	596.1	586.3	579.2	574.8	570.5	566.1	561.7
42.5°	572.7	562.0	551.2	543.9	540.0	536.1	532.1	528.2
45°	523.9	513.1	502.2	494.6	490.0	485.4	480.9	476.4
47.5°	473.3	461.5	449.8	441.9	437.8	433.7	429.7	425.7
50°	439.2	427.4	415.6	407.6	403.2	398.8	394.5	390.1
52.5°	406.2	394.0	381.7	373.7	369.7	365.8	361.9	358.0
55°	357.0	346.0	335.0	327.6	323.8	320.0	316.3	312.4
57.5°	308.8	298.3	288.0	281.1	277.9	274.7	271.4	268.2
60°	278.3	268.1	257.8	251.1	247.9	244.6	241.4	238.1
62.5°	248.1	238.5	228.9	222.3	218.9	215.6	212.2	208.8
65°	205.0	195.8	186.5	180.8	178.7	176.6	174.6	172.4
67.5°	164.0	157.1	150.1	145.5	143.3	141.0	138.8	136.6
70°	138.7	132.0	125.4	121.1	119.0	116.8	114.8	112.7
72.5°	115.9	110.4	105.0	101.8	100.9	100.1	99.2	98.3
75°	86.7	84.8	82.9	81.8	81.4	81.0	80.6	80.2
77.5°	65.4	64.3	63.3	62.6	62.3	61.9	61.5	61.1
80°	52.7	52.1	51.5	51.0	50.6	50.3	49.9	49.5
82.5°	40.4	39.8	39.2	38.9	38.8	38.7	38.6	38.6
85°	23.2	22.7	22.4	22.2	22.2	22.2	22.2	22.2
87.5°	11.0	10.9	10.8	10.8	10.6	10.5	10.4	10.3
90°	12.0	12.4	12.8	13.1	13.4	13.5	13.8	13.9
92.5°	18.5	18.8	19.2	19.3	19.2	19.0	18.9	18.8
95°	35.2	35.6	36.0	36.3	36.3	36.3	36.3	36.3
97.5°	54.8	55.3	55.8	55.9	55.9	55.8	55.8	55.8
100°	69.0	69.3	69.6	69.9	70.0	70.3	70.4	70.7
102.5°	85.4	85.7	85.9	86.1	86.1	86.0	86.0	85.9
105°	109.7	109.7	109.7	109.8	110.1	110.2	110.5	110.7
107.5°	136.2	136.5	136.8	137.0	136.8	136.7	136.6	136.5
110°	153.8	154.3	154.7	154.7	154.6	154.3	154.2	153.9



TEST NUMBER: P332310-930

CATALOG NUMBER: S123RDIP-S775D585U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	171.5	171.9	172.4	172.7	172.7	172.6	172.6	172.5
115°	198.3	198.4	198.5	198.5	198.4	198.3	198.2	198.1
117.5°	225.4	225.3	225.3	225.2	224.9	224.6	224.4	224.0
120°	243.4	243.4	243.3	243.1	242.9	242.7	242.5	242.3
122.5°	261.7	261.5	261.2	260.9	260.7	260.3	260.1	259.8
125°	288.9	288.5	288.0	287.6	287.2	286.8	286.4	286.0
127.5°	315.7	315.1	314.5	314.1	313.6	313.1	312.6	312.1
130°	333.5	333.1	332.7	332.2	331.4	330.7	330.0	329.2
132.5°	350.8	350.3	349.8	349.4	348.8	348.2	347.6	347.1
135°	376.7	376.3	375.9	375.6	375.4	375.2	375.0	374.8
137.5°	402.1	401.7	401.3	400.9	400.5	400.1	399.7	399.3
140°	418.8	418.7	418.6	418.2	417.4	416.7	416.0	415.3
142.5°	434.4	434.3	434.2	433.9	433.3	432.8	432.2	431.6
145°	457.4	457.3	457.2	456.9	456.5	456.1	455.7	455.3
147.5°	479.1	479.1	479.1	478.7	478.2	477.5	477.0	476.3
150°	492.4	492.4	492.4	492.2	491.5	490.9	490.3	489.7
152.5°	504.8	504.9	505.1	504.8	504.3	503.8	503.3	502.7
155°	522.6	523.0	523.4	523.3	522.5	521.8	521.1	520.4
157.5°	538.0	538.4	538.8	538.7	538.2	537.6	537.0	536.5
160°	547.5	548.0	548.5	548.5	548.1	547.7	547.3	546.9
162.5°	556.4	556.9	557.4	557.3	556.7	556.0	555.4	554.7
165°	567.7	568.3	568.9	568.8	568.1	567.4	566.7	566.0
167.5°	576.8	577.5	578.1	578.1	577.5	576.8	576.2	575.5
170°	581.8	582.5	583.3	583.3	582.5	581.8	581.1	580.3
172.5°	585.7	586.4	587.0	587.0	586.3	585.5	584.8	584.1
175°	590.0	590.6	591.3	591.2	590.4	589.7	589.0	588.2
177.5°	591.9	592.4	592.9	592.8	592.2	591.7	591.1	590.5
180°	592.0	592.0	592.0	592.0	592.0	592.0	592.0	592.0

(END OF REPORT)