

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332368-927

Luminaire Tested: **S123RDIP-S1165D585U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332368-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D585U927-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5302.4 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332368-927

CATALOG NUMBER: S123RDIP-S1165D585U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332368-927

CATALOG NUMBER: S123RDIP-S1165D585U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	68
1	103	99	95	92	97	93	90	87	83	81	79	74	72	71	66	64	63	59
2	94	87	81	76	89	82	77	73	74	70	66	66	63	60	59	57	54	51
3	86	77	70	64	81	73	67	62	66	61	57	59	55	52	53	50	47	44
4	80	69	61	55	75	66	59	53	59	54	49	53	49	45	48	44	41	38
5	73	62	54	48	69	59	52	46	53	48	43	48	43	40	43	40	37	34
6	68	56	48	42	64	53	46	41	48	42	38	44	39	35	40	36	33	30
7	63	51	43	37	60	49	41	36	44	38	34	40	35	32	36	32	29	27
8	59	46	39	33	55	44	37	32	41	35	30	37	32	28	34	29	26	24
9	55	43	35	30	52	41	34	29	37	32	27	34	29	26	31	27	24	22
10	51	39	32	27	49	38	31	26	35	29	25	32	27	23	29	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15655	15655	15655	15655
5°	18662	15722	13846	15722
10°	23302	15632	12508	15632
15°	27351	15473	11407	15473
20°	30525	15234	10470	15234
25°	30037	14982	9894	14982
30°	21592	14751	9302	14751
35°	14416	14448	8918	14448
40°	10621	14085	8521	14085
45°	8910	13449	8132	13449
50°	7860	12616	7591	12616
55°	6893	11661	6848	11661
60°	6140	10749	6273	10749
65°	5392	9770	5835	9770
70°	4233	8897	5331	8897
75°	3730	7769	4870	7769
80°	3242	6602	4785	6602
85°	2618	5298	5076	5298



TEST NUMBER: P332368-927

CATALOG NUMBER: S123RDIP-S1165D585U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.0	2.7
10°-20°	446.9	8.4
20°-30°	702.0	13.2
30°-40°	732.4	13.8
40°-50°	626.8	11.8
50°-60°	477.7	9.0
60°-70°	306.2	5.8
70°-80°	147.3	2.8
80°-90°	40.7	0.8
90°-100°	124.2	2.3
100°-110°	351.7	6.6
110°-120°	346.0	6.5
120°-130°	276.0	5.2
130°-140°	217.6	4.1
140°-150°	162.4	3.1
150°-160°	113.2	2.1
160°-170°	66.5	1.3
170°-180°	21.6	0.4
0°-30°	1291.9	24.4
0°-40°	2024.3	38.2
0°-60°	3128.9	59.0
0°-90°	3623.1	68.3
90°-120°	822.0	15.5
90°-150°	1478.0	27.9
90°-180°	1679.0	31.7
0°-180°	5302.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1454	1454	1454	1454	1454	
5°	1727	1455	1281	1455	1727	178
15°	2454	1388	1024	1388	2454	696
25°	2529	1262	833	1262	2529	1087
35°	1097	1100	679	1100	1097	719
45°	585	884	534	884	585	460
55°	367	621	365	621	367	332
65°	212	384	229	384	212	208
75°	90	187	117	187	90	96
85°	21	43	41	43	21	25
90°	13	1	13	1	13	8
95°	52	15	52	15	52	94
105°	575	52	575	52	575	567
115°	699	93	699	93	699	679
125°	551	129	551	129	551	500
135°	447	151	447	151	447	347
145°	349	172	349	172	349	222
155°	290	196	290	196	290	135
165°	252	214	252	214	252	72
175°	227	223	227	223	227	22
180°	223	223	223	223	223	



TEST NUMBER: P332368-927

CATALOG NUMBER: S123RDIP-S1165D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1549.1	1551.1	1544.6	1543.6	1536.1	1534.1	1534.1	1523.7	1517.2	1508.8	1503.8
5°	1727.2	1737.2	1732.2	1720.9	1702.2	1697.9	1686.1	1667.4	1646.2	1620.1	1607.7
7.5°	1949.6	1963.2	1958.0	1940.6	1921.0	1905.3	1871.8	1840.9	1797.4	1759.3	1726.6
10°	2131.9	2117.6	2106.3	2089.5	2071.5	2042.2	2007.4	1959.4	1904.0	1860.4	1811.9
12.5°	2268.3	2266.0	2251.8	2234.5	2209.0	2181.2	2138.3	2080.0	2015.5	1952.6	1897.0
15°	2454.4	2458.1	2448.8	2430.7	2394.6	2345.4	2280.7	2256.5	2164.2	2095.8	2027.3
17.5°	2583.1	2582.4	2581.2	2556.1	2519.3	2484.3	2424.2	2360.4	2277.0	2180.5	2088.2
20°	2664.8	2658.6	2659.9	2631.9	2604.5	2564.0	2505.4	2412.7	2344.2	2232.8	2137.5
22.5°	2662.8	2661.7	2666.3	2656.7	2636.9	2605.8	2559.8	2481.4	2394.1	2281.6	2174.4
25°	2529.1	2524.1	2553.4	2561.5	2593.3	2598.8	2585.1	2542.2	2459.4	2343.6	2211.0
27.5°	2116.7	2113.9	2168.3	2236.3	2322.4	2389.4	2454.2	2485.4	2459.4	2376.5	2243.6
30°	1737.2	1795.6	1823.0	1921.4	2031.0	2161.8	2276.3	2385.3	2412.0	2376.0	2267.0
32.5°	1442.2	1493.3	1516.2	1600.7	1702.8	1855.9	2027.7	2182.1	2291.1	2318.6	2253.0
35°	1097.1	1097.7	1150.0	1187.3	1282.0	1439.6	1606.4	1813.1	2018.6	2174.2	2190.4
37.5°	875.4	878.5	910.1	947.4	1018.4	1101.7	1248.6	1420.5	1657.8	1896.8	2036.9
40°	755.9	761.4	785.1	821.9	872.9	935.8	1050.4	1212.3	1410.2	1676.1	1893.4
42.5°	679.1	688.2	700.4	728.7	760.3	819.3	911.9	1037.0	1217.0	1468.4	1719.1
45°	585.3	590.3	599.6	612.7	641.3	682.4	744.7	828.7	978.2	1180.5	1431.4
47.5°	516.3	513.7	523.5	534.1	553.2	581.1	622.9	691.5	798.1	960.4	1173.3
50°	469.4	468.8	475.7	483.8	501.8	522.4	556.7	608.3	693.0	827.5	1022.4
52.5°	425.6	428.0	432.8	442.9	456.0	472.6	503.4	540.6	613.3	729.4	891.8
55°	367.3	369.2	376.0	381.7	391.0	407.8	427.1	458.3	508.1	589.0	722.9
57.5°	318.1	317.2	323.8	325.1	335.7	349.4	364.3	388.5	424.6	484.8	575.0
60°	285.2	283.3	288.9	293.3	298.9	310.1	322.5	346.2	374.9	419.1	496.2
62.5°	255.2	254.4	258.5	262.8	267.5	277.7	288.1	306.3	329.0	366.2	427.5
65°	211.7	213.6	215.4	217.3	219.8	226.0	236.0	248.4	264.0	290.2	334.4
67.5°	166.4	168.3	168.9	172.7	178.1	182.0	188.1	199.2	209.9	232.0	257.1
70°	134.5	133.9	134.5	136.3	143.2	150.0	158.1	166.3	173.1	188.6	209.8
72.5°	115.6	114.5	116.1	116.5	119.8	121.7	126.7	134.4	143.2	153.8	169.0
75°	89.7	89.7	89.7	89.7	92.1	93.4	95.3	97.1	100.2	105.2	116.5
77.5°	66.2	66.4	67.3	67.9	68.4	69.1	70.3	72.1	73.2	75.8	80.7
80°	52.3	52.9	52.3	52.9	52.9	54.2	54.8	56.6	57.3	60.4	62.3
82.5°	39.4	39.0	39.4	40.0	40.0	41.2	41.4	42.7	42.9	44.4	46.3
85°	21.2	20.0	21.2	20.5	21.8	20.5	21.2	22.4	22.4	23.1	25.5
87.5°	7.6	8.7	7.6	8.0	8.1	8.4	8.3	8.2	9.1	8.7	9.0
90°	13.1	13.5	13.1	12.7	13.1	12.2	11.7	11.3	10.9	11.3	9.9
92.5°	21.8	22.6	22.1	23.5	24.3	26.7	30.2	38.0	52.4	69.5	76.4
95°	52.4	54.2	57.4	61.5	70.0	86.3	110.3	162.6	217.3	267.9	238.6
97.5°	142.7	146.6	158.8	179.1	212.5	266.5	324.8	405.5	444.3	415.3	304.0
100°	283.3	282.9	300.5	333.4	379.1	443.2	496.1	532.7	516.9	427.9	289.1
102.5°	415.6	426.0	440.7	466.8	502.3	543.0	573.9	575.0	520.5	404.4	267.5
105°	574.7	577.0	591.4	608.6	629.4	641.2	632.6	587.4	493.0	363.3	240.8
107.5°	666.4	670.5	675.4	681.2	680.8	664.7	625.2	551.8	444.7	326.9	223.9
110°	703.9	704.9	705.8	702.2	689.5	657.9	600.9	517.8	414.3	306.3	217.3



TEST NUMBER: P332368-927

CATALOG NUMBER: S123RDIP-S1165D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	711.5	711.4	708.0	696.7	673.6	633.0	569.1	484.2	387.9	292.6	213.7
115°	699.0	696.7	687.7	667.8	633.9	584.7	518.2	439.7	356.1	277.9	212.4
117.5°	659.0	656.0	642.9	620.2	584.9	534.9	475.2	407.3	336.8	269.2	213.2
120°	625.8	623.1	612.3	586.9	551.3	505.6	451.4	390.4	326.7	265.2	214.6
122.5°	594.7	591.3	579.3	556.6	524.8	482.4	432.2	377.0	318.4	262.7	217.1
125°	551.3	548.1	536.8	516.9	488.0	451.9	408.4	359.2	307.7	259.4	220.9
127.5°	515.5	512.5	502.3	485.4	459.6	426.7	387.6	343.6	298.3	257.7	225.3
130°	495.2	491.6	482.1	465.9	441.9	411.1	374.5	333.9	293.3	256.7	228.1
132.5°	475.3	472.8	464.4	448.1	425.6	396.3	362.3	324.9	288.5	256.3	230.4
135°	446.9	443.7	435.5	422.0	399.9	374.1	344.8	312.7	282.4	255.7	233.6
137.5°	416.8	414.7	407.8	394.1	375.5	353.2	327.9	301.6	277.1	254.8	235.8
140°	395.8	396.2	389.0	376.4	359.2	339.8	318.1	295.1	273.8	254.4	237.2
142.5°	376.3	376.8	370.3	359.0	344.4	327.5	308.7	288.9	270.9	253.7	238.3
145°	349.3	348.4	344.8	335.3	324.0	310.9	296.4	281.5	267.0	252.5	239.0
147.5°	327.0	326.7	323.2	316.8	308.2	299.0	287.2	275.4	263.2	250.9	239.0
150°	314.0	314.0	311.3	306.3	299.6	291.0	281.5	271.1	260.7	249.4	239.0
152.5°	303.2	303.2	301.6	296.9	291.6	284.5	276.1	267.1	257.9	247.6	238.0
155°	289.6	289.1	288.3	284.6	280.6	275.2	268.4	261.2	253.5	244.5	236.8
157.5°	277.3	277.3	276.6	273.9	270.4	266.2	260.9	254.8	248.6	241.6	235.2
160°	269.3	269.7	269.7	267.0	263.9	260.7	256.2	251.2	245.3	239.5	234.5
162.5°	262.1	262.5	262.5	260.2	258.1	255.3	251.1	246.9	242.1	237.3	233.1
165°	252.5	252.5	253.0	251.2	249.4	247.2	244.0	241.3	237.7	234.1	230.9
167.5°	243.5	243.5	244.0	242.7	241.9	240.3	238.4	236.4	233.5	230.8	228.7
170°	238.1	238.1	238.6	237.7	237.2	236.3	234.5	233.1	230.9	228.6	227.3
172.5°	233.1	233.5	234.2	233.3	233.2	232.7	231.2	230.3	228.4	226.8	226.2
175°	227.3	227.8	228.1	227.8	227.8	227.8	226.8	226.4	225.5	224.6	224.6
177.5°	223.9	223.9	224.7	224.3	224.7	224.7	224.3	223.9	223.6	223.2	223.6
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P332368-927

CATALOG NUMBER: S123RDIP-S1165D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1501.8	1500.3	1493.3	1485.3	1474.9	1467.9	1462.4	1459.4	1450.5	1439.6	1432.0
5°	1594.6	1575.9	1555.9	1531.7	1509.3	1486.2	1471.9	1455.1	1434.6	1411.5	1395.3
7.5°	1693.9	1657.3	1617.9	1577.2	1536.9	1500.8	1468.9	1441.6	1408.9	1375.9	1352.7
10°	1770.1	1716.6	1661.2	1604.5	1552.8	1504.3	1466.9	1430.2	1391.0	1353.0	1324.4
12.5°	1839.4	1768.9	1705.0	1635.4	1569.3	1511.2	1457.5	1414.2	1367.1	1326.6	1294.0
15°	1927.1	1854.8	1777.6	1671.7	1584.0	1510.5	1445.1	1388.5	1331.2	1281.4	1249.6
17.5°	2009.0	1900.3	1796.5	1708.3	1594.2	1502.4	1422.6	1354.9	1292.0	1239.1	1200.1
20°	2042.9	1937.6	1825.0	1712.2	1600.1	1497.5	1404.6	1329.9	1264.6	1204.8	1168.7
22.5°	2063.2	1944.1	1825.4	1704.3	1585.2	1478.5	1386.7	1304.6	1233.7	1176.9	1132.3
25°	2087.1	1945.1	1814.3	1694.8	1573.4	1457.6	1348.6	1261.5	1184.9	1124.5	1077.1
27.5°	2102.8	1935.8	1781.2	1648.4	1525.2	1409.8	1310.0	1217.6	1140.0	1076.0	1025.2
30°	2105.7	1928.3	1755.8	1612.0	1486.8	1381.0	1275.2	1186.8	1104.5	1036.6	989.4
32.5°	2109.7	1909.9	1721.4	1568.7	1440.5	1335.7	1239.8	1155.3	1071.2	1004.3	956.0
35°	2093.3	1899.7	1669.3	1493.7	1365.4	1263.9	1177.4	1099.5	1016.8	952.0	902.9
37.5°	2022.5	1859.2	1615.3	1409.3	1275.2	1181.1	1110.6	1042.7	966.9	897.0	850.6
40°	1951.3	1819.3	1573.4	1358.0	1217.9	1121.3	1057.9	1002.4	929.0	863.6	813.8
42.5°	1845.2	1765.1	1533.5	1304.2	1153.1	1060.1	1006.5	954.6	890.1	823.7	776.9
45°	1650.6	1661.2	1452.0	1218.5	1063.4	970.0	919.6	883.5	826.2	771.4	723.5
47.5°	1406.5	1505.5	1356.2	1127.2	968.9	881.3	837.2	805.6	767.1	713.3	669.6
50°	1247.1	1388.5	1279.5	1066.0	909.7	822.5	778.9	753.4	719.8	677.4	635.7
52.5°	1100.2	1252.0	1186.8	997.7	845.4	765.7	723.1	702.1	675.4	635.6	597.9
55°	897.2	1051.0	1036.1	894.7	749.0	677.4	645.1	621.4	603.3	573.5	543.6
57.5°	725.7	871.6	879.2	780.1	664.1	593.3	565.5	547.6	535.8	513.3	485.7
60°	617.7	751.5	777.7	703.0	603.3	541.1	513.7	499.3	490.0	472.0	450.8
62.5°	528.0	641.9	671.5	617.7	545.0	486.8	465.3	451.5	445.2	429.6	410.9
65°	404.1	498.8	527.4	497.5	459.5	412.8	395.4	383.6	378.0	369.2	355.5
67.5°	303.9	372.8	404.3	383.2	369.5	339.9	328.8	322.5	317.5	311.6	300.1
70°	244.1	295.1	327.5	321.9	310.7	295.1	287.0	282.7	277.7	272.7	262.8
72.5°	196.2	231.4	261.7	264.6	255.4	252.3	245.2	243.4	240.3	234.3	228.9
75°	130.2	154.4	175.5	183.7	187.4	190.5	187.4	186.8	186.2	181.2	178.1
77.5°	85.3	98.4	111.7	125.6	131.3	135.6	136.6	138.9	137.2	134.6	133.1
80°	65.4	68.5	77.8	89.7	99.0	102.7	105.2	106.5	105.8	105.2	102.7
82.5°	47.5	50.1	54.4	62.7	70.6	76.8	78.3	78.1	79.5	79.9	77.8
85°	25.5	26.1	27.4	28.7	33.0	39.8	41.7	42.9	44.2	44.2	40.5
87.5°	9.7	9.0	9.7	9.4	10.8	11.0	13.8	16.1	16.8	15.0	15.3
90°	8.6	7.2	5.9	5.0	4.0	2.7	1.8	0.9	1.8	2.7	4.0
92.5°	57.4	37.9	26.1	19.4	15.6	12.1	8.3	5.6	8.3	12.1	15.6
95°	164.5	97.1	58.7	41.1	29.4	21.7	16.7	15.4	16.7	21.7	29.4
97.5°	180.5	104.6	67.9	48.8	37.2	30.6	26.7	26.2	26.7	30.6	37.2
100°	170.3	103.5	71.9	54.2	43.4	37.1	33.9	33.4	33.9	37.1	43.4
102.5°	161.7	104.9	76.5	60.4	50.6	44.7	41.8	41.0	41.8	44.7	50.6
105°	155.4	108.9	84.5	70.5	61.9	56.5	53.8	52.4	53.8	56.5	61.9
107.5°	155.0	116.3	94.9	81.9	73.8	68.5	65.9	64.5	65.9	68.5	73.8
110°	156.8	122.5	102.1	89.4	81.8	76.8	74.5	73.2	74.5	76.8	81.8



TEST NUMBER: P332368-927

CATALOG NUMBER: S123RDIP-S1165D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	160.4	128.6	109.7	97.4	89.8	84.8	82.5	81.1	82.5	84.8	89.8
115°	166.3	138.7	121.5	109.3	101.6	97.1	94.4	92.6	94.4	97.1	101.6
117.5°	174.0	149.5	132.5	121.2	112.6	108.4	106.2	104.1	106.2	108.4	112.6
120°	179.8	156.3	140.1	128.8	120.2	115.7	113.4	112.1	113.4	115.7	120.2
122.5°	185.3	163.6	147.7	135.6	127.4	122.6	120.3	118.9	120.3	122.6	127.4
125°	193.8	174.0	158.1	145.9	137.4	132.4	129.7	128.8	129.7	132.4	137.4
127.5°	200.9	183.0	167.7	155.5	146.0	141.0	137.6	136.3	137.6	141.0	146.0
130°	205.6	188.4	173.5	161.3	151.8	146.4	142.4	141.0	142.4	146.4	151.8
132.5°	209.9	193.1	178.6	166.8	157.2	150.8	146.3	144.6	146.3	150.8	157.2
135°	215.6	200.2	186.2	174.0	164.5	157.7	152.7	150.9	152.7	157.7	164.5
137.5°	219.7	205.0	191.5	180.3	170.9	163.7	158.8	156.9	158.8	163.7	170.9
140°	221.9	208.3	195.2	183.9	174.8	167.6	163.1	160.9	163.1	167.6	174.8
142.5°	224.0	210.8	198.1	187.5	178.5	172.0	167.1	165.2	167.1	172.0	178.5
145°	226.4	214.2	202.4	192.0	184.3	177.6	173.5	172.1	173.5	177.6	184.3
147.5°	227.8	216.9	206.1	197.3	189.9	184.0	180.0	179.2	180.0	184.0	189.9
150°	228.1	218.7	208.3	200.2	193.8	188.0	184.3	183.9	184.3	188.0	193.8
152.5°	228.9	219.8	210.8	203.0	197.5	192.3	188.7	188.6	188.7	192.3	197.5
155°	229.1	221.9	214.2	207.9	202.9	198.4	195.7	195.7	195.7	198.4	202.9
157.5°	229.6	223.0	216.9	212.0	207.8	203.7	201.6	201.2	201.6	203.7	207.8
160°	229.6	224.1	218.7	214.2	211.0	207.4	205.6	205.6	205.6	207.4	211.0
162.5°	229.2	224.5	219.8	215.9	213.2	210.3	208.8	208.8	208.8	210.3	213.2
165°	228.1	225.0	221.4	218.2	216.4	214.2	213.3	213.7	213.3	214.2	216.4
167.5°	227.4	224.9	222.3	220.3	219.0	217.3	216.9	217.5	216.9	217.3	219.0
170°	226.4	224.6	222.3	221.4	220.5	219.1	218.7	219.6	218.7	219.1	220.5
172.5°	226.0	224.6	222.7	222.1	221.6	220.6	220.5	221.0	220.5	220.6	221.6
175°	225.0	224.1	223.2	222.8	222.8	221.9	222.3	222.8	222.3	221.9	222.8
177.5°	224.3	223.6	223.2	223.2	223.2	222.8	223.2	223.6	223.2	222.8	223.2
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P332368-927

CATALOG NUMBER: S123RDIP-S1165D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1429.6	1423.1	1418.6	1408.7	1402.2	1395.2	1388.2	1392.7	1392.2	1391.7	1391.7
5°	1381.6	1367.3	1354.2	1337.4	1326.8	1313.8	1303.8	1302.5	1305.0	1296.3	1291.3
7.5°	1334.0	1314.5	1295.9	1277.4	1257.7	1242.1	1232.2	1227.6	1221.2	1215.8	1210.3
10°	1300.7	1277.6	1259.6	1236.5	1215.4	1196.7	1184.9	1176.8	1172.4	1168.1	1160.0
12.5°	1266.3	1243.8	1220.8	1194.7	1174.6	1152.9	1144.0	1135.0	1126.6	1121.7	1110.6
15°	1216.0	1186.8	1162.4	1135.0	1112.6	1091.5	1079.0	1061.0	1058.4	1052.3	1041.0
17.5°	1165.5	1133.8	1100.3	1080.0	1054.7	1032.7	1013.8	1007.7	989.8	983.1	973.4
20°	1125.7	1096.5	1071.0	1044.2	1007.4	986.9	971.9	963.8	949.5	940.8	934.5
22.5°	1091.3	1061.6	1032.1	1000.8	970.6	947.5	936.6	924.0	916.2	904.0	897.2
25°	1042.3	1009.9	974.4	940.8	919.0	901.6	884.2	872.9	861.7	856.1	843.7
27.5°	985.2	951.4	918.2	892.7	865.9	848.7	833.0	823.0	809.5	800.1	793.2
30°	953.9	914.0	885.3	862.4	828.1	811.9	800.1	787.7	777.7	767.7	760.9
32.5°	917.5	881.1	854.0	825.5	799.2	781.5	766.2	755.3	746.8	737.3	730.5
35°	860.5	830.0	801.9	773.3	754.0	735.9	717.9	708.5	700.4	691.7	685.6
37.5°	808.9	780.4	753.8	726.6	702.7	688.0	673.4	666.3	655.4	649.5	643.2
40°	777.1	749.0	720.4	694.3	669.3	658.1	645.1	634.5	624.5	620.1	613.3
42.5°	742.2	714.2	690.0	661.9	641.4	626.2	614.2	602.6	595.1	588.7	584.9
45°	690.5	665.6	641.9	613.9	594.6	581.5	567.8	557.2	550.4	546.1	539.2
47.5°	640.3	615.4	591.4	567.0	548.3	533.4	519.7	512.3	503.2	497.9	493.2
50°	604.0	581.5	556.0	533.6	514.9	499.9	488.8	479.4	471.3	464.5	461.4
52.5°	570.6	546.7	524.7	503.7	484.0	467.1	456.9	447.0	440.9	433.1	429.5
55°	515.6	492.5	473.8	453.3	434.0	419.6	407.2	398.5	392.3	383.6	378.6
57.5°	463.8	443.2	420.9	403.1	383.2	371.1	360.8	349.0	341.4	334.5	329.6
60°	429.0	405.4	386.0	369.2	351.8	336.2	326.9	317.5	309.4	302.6	298.3
62.5°	392.6	371.9	353.6	335.3	319.4	305.9	295.0	287.2	280.0	275.7	271.3
65°	336.8	320.7	302.0	287.0	272.1	262.1	253.4	246.5	241.6	238.4	234.7
67.5°	285.5	269.8	253.5	238.8	228.9	221.3	215.6	209.7	207.2	203.2	200.7
70°	252.2	236.0	221.7	210.5	200.5	194.9	191.2	186.8	184.3	179.4	176.8
72.5°	215.8	204.1	193.8	184.6	176.6	171.5	166.8	161.4	157.4	151.9	149.4
75°	170.0	159.4	151.3	145.0	140.1	133.2	126.4	120.8	118.9	117.1	116.5
77.5°	125.9	119.1	113.3	108.1	101.9	96.9	95.4	94.1	93.8	92.8	92.8
80°	99.0	92.8	88.4	82.1	78.4	78.4	78.4	77.2	77.8	77.8	77.8
82.5°	73.6	67.9	65.5	63.3	62.5	63.0	63.0	63.3	62.9	63.8	63.4
85°	37.9	38.6	39.8	39.2	39.8	39.8	41.1	40.5	41.1	39.8	41.1
87.5°	15.0	16.6	17.3	18.1	18.9	18.7	19.1	19.2	19.8	19.9	20.0
90°	5.0	5.9	7.2	8.6	9.9	11.3	10.9	11.3	11.7	12.2	13.1
92.5°	19.4	26.1	37.9	57.4	76.4	69.5	52.4	38.0	30.2	26.7	24.3
95°	41.1	58.7	97.1	164.5	238.6	267.9	217.3	162.6	110.3	86.3	70.0
97.5°	48.8	67.9	104.6	180.5	304.0	415.3	444.3	405.5	324.8	266.5	212.5
100°	54.2	71.9	103.5	170.3	289.1	427.9	516.9	532.7	496.1	443.2	379.1
102.5°	60.4	76.5	104.9	161.7	267.5	404.4	520.5	575.0	573.9	543.0	502.3
105°	70.5	84.5	108.9	155.4	240.8	363.3	493.0	587.4	632.6	641.2	629.4
107.5°	81.9	94.9	116.3	155.0	223.9	326.9	444.7	551.8	625.2	664.7	680.8
110°	89.4	102.1	122.5	156.8	217.3	306.3	414.3	517.8	600.9	657.9	689.5



TEST NUMBER: P332368-927

CATALOG NUMBER: S123RDIP-S1165D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	97.4	109.7	128.6	160.4	213.7	292.6	387.9	484.2	569.1	633.0	673.6
115°	109.3	121.5	138.7	166.3	212.4	277.9	356.1	439.7	518.2	584.7	633.9
117.5°	121.2	132.5	149.5	174.0	213.2	269.2	336.8	407.3	475.2	534.9	584.9
120°	128.8	140.1	156.3	179.8	214.6	265.2	326.7	390.4	451.4	505.6	551.3
122.5°	135.6	147.7	163.6	185.3	217.1	262.7	318.4	377.0	432.2	482.4	524.8
125°	145.9	158.1	174.0	193.8	220.9	259.4	307.7	359.2	408.4	451.9	488.0
127.5°	155.5	167.7	183.0	200.9	225.3	257.7	298.3	343.6	387.6	426.7	459.6
130°	161.3	173.5	188.4	205.6	228.1	256.7	293.3	333.9	374.5	411.1	441.9
132.5°	166.8	178.6	193.1	209.9	230.4	256.3	288.5	324.9	362.3	396.3	425.6
135°	174.0	186.2	200.2	215.6	233.6	255.7	282.4	312.7	344.8	374.1	399.9
137.5°	180.3	191.5	205.0	219.7	235.8	254.8	277.1	301.6	327.9	353.2	375.5
140°	183.9	195.2	208.3	221.9	237.2	254.4	273.8	295.1	318.1	339.8	359.2
142.5°	187.5	198.1	210.8	224.0	238.3	253.7	270.9	288.9	308.7	327.5	344.4
145°	192.0	202.4	214.2	226.4	239.0	252.5	267.0	281.5	296.4	310.9	324.0
147.5°	197.3	206.1	216.9	227.8	239.0	250.9	263.2	275.4	287.2	299.0	308.2
150°	200.2	208.3	218.7	228.1	239.0	249.4	260.7	271.1	281.5	291.0	299.6
152.5°	203.0	210.8	219.8	228.9	238.0	247.6	257.9	267.1	276.1	284.5	291.6
155°	207.9	214.2	221.9	229.1	236.8	244.5	253.5	261.2	268.4	275.2	280.6
157.5°	212.0	216.9	223.0	229.6	235.2	241.6	248.6	254.8	260.9	266.2	270.4
160°	214.2	218.7	224.1	229.6	234.5	239.5	245.3	251.2	256.2	260.7	263.9
162.5°	215.9	219.8	224.5	229.2	233.1	237.3	242.1	246.9	251.1	255.3	258.1
165°	218.2	221.4	225.0	228.1	230.9	234.1	237.7	241.3	244.0	247.2	249.4
167.5°	220.3	222.3	224.9	227.4	228.7	230.8	233.5	236.4	238.4	240.3	241.9
170°	221.4	222.3	224.6	226.4	227.3	228.6	230.9	233.1	234.5	236.3	237.2
172.5°	222.1	222.7	224.6	226.0	226.2	226.8	228.4	230.3	231.2	232.7	233.2
175°	222.8	223.2	224.1	225.0	224.6	224.6	225.5	226.4	226.8	227.8	227.8
177.5°	223.2	223.2	223.6	224.3	223.6	223.2	223.6	223.9	224.3	224.7	224.7
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P332368-927

CATALOG NUMBER: S123RDIP-S1165D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1385.8	1385.2	1385.8	1383.7	1385.8	1385.2	1385.8	1391.7	1391.7	1392.2	1392.7
5°	1289.4	1288.9	1287.0	1281.4	1287.0	1288.9	1289.4	1291.3	1296.3	1305.0	1302.5
7.5°	1205.4	1204.5	1199.0	1199.2	1199.0	1204.5	1205.4	1210.3	1215.8	1221.2	1227.6
10°	1155.6	1156.2	1148.7	1144.4	1148.7	1156.2	1155.6	1160.0	1168.1	1172.4	1176.8
12.5°	1107.3	1104.5	1098.4	1093.6	1098.4	1104.5	1107.3	1110.6	1121.7	1126.6	1135.0
15°	1043.5	1037.3	1022.4	1023.6	1022.4	1037.3	1043.5	1041.0	1052.3	1058.4	1061.0
17.5°	968.4	963.8	963.6	954.9	963.6	963.8	968.4	973.4	983.1	989.8	1007.7
20°	924.6	921.5	922.7	914.0	922.7	921.5	924.6	934.5	940.8	949.5	963.8
22.5°	890.3	887.1	881.9	879.2	881.9	887.1	890.3	897.2	904.0	916.2	924.0
25°	840.0	835.0	830.0	833.1	830.0	835.0	840.0	843.7	856.1	861.7	872.9
27.5°	789.6	785.9	780.9	780.3	780.9	785.9	789.6	793.2	800.1	809.5	823.0
30°	757.7	754.0	751.5	748.4	751.5	754.0	757.7	760.9	767.7	777.7	787.7
32.5°	725.4	724.6	720.2	719.5	720.2	724.6	725.4	730.5	737.3	746.8	755.3
35°	683.0	679.3	678.0	678.7	678.0	679.3	683.0	685.6	691.7	700.4	708.5
37.5°	642.8	637.8	635.6	633.3	635.6	637.8	642.8	643.2	649.5	655.4	666.3
40°	613.9	609.0	607.7	606.4	607.7	609.0	613.9	613.3	620.1	624.5	634.5
42.5°	581.5	579.6	578.8	576.6	578.8	579.6	581.5	584.9	588.7	595.1	602.6
45°	537.3	536.7	533.0	534.2	533.0	536.7	537.3	539.2	546.1	550.4	557.2
47.5°	490.8	488.0	485.4	487.1	485.4	488.0	490.8	493.2	497.9	503.2	512.3
50°	458.9	457.6	452.0	453.3	452.0	457.6	458.9	461.4	464.5	471.3	479.4
52.5°	427.0	422.2	420.2	419.4	420.2	422.2	427.0	429.5	433.1	440.9	447.0
55°	374.2	368.6	366.1	364.9	366.1	368.6	374.2	378.6	383.6	392.3	398.5
57.5°	322.4	320.9	318.9	320.3	318.9	320.9	322.4	329.6	334.5	341.4	349.0
60°	292.0	292.0	292.0	291.4	292.0	292.0	292.0	298.3	302.6	309.4	317.5
62.5°	268.6	267.1	266.6	267.5	266.6	267.1	268.6	271.3	275.7	280.0	287.2
65°	232.9	232.3	229.7	229.1	229.7	232.3	232.9	234.7	238.4	241.6	246.5
67.5°	199.2	196.9	196.1	195.3	196.1	196.9	199.2	200.7	203.2	207.2	209.7
70°	173.7	172.5	168.7	169.4	168.7	172.5	173.7	176.8	179.4	184.3	186.8
72.5°	146.3	145.0	144.3	143.5	144.3	145.0	146.3	149.4	151.9	157.4	161.4
75°	115.8	115.2	114.5	117.1	114.5	115.2	115.8	116.5	117.1	118.9	120.8
77.5°	92.8	92.8	93.2	92.1	93.2	92.8	92.8	92.8	92.8	93.8	94.1
80°	77.8	77.8	77.2	77.2	77.2	77.8	77.8	77.8	77.8	77.8	77.2
82.5°	62.4	62.9	63.3	62.3	63.3	62.9	62.4	63.4	63.8	62.9	63.3
85°	41.1	40.5	41.7	41.1	41.7	40.5	41.1	41.1	39.8	41.1	40.5
87.5°	21.0	20.0	20.1	20.5	20.1	20.0	21.0	20.0	19.9	19.8	19.2
90°	12.7	13.1	13.5	13.1	13.5	13.1	12.7	13.1	12.2	11.7	11.3
92.5°	23.5	22.1	22.6	21.8	22.6	22.1	23.5	24.3	26.7	30.2	38.0
95°	61.5	57.4	54.2	52.4	54.2	57.4	61.5	70.0	86.3	110.3	162.6
97.5°	179.1	158.8	146.6	142.7	146.6	158.8	179.1	212.5	266.5	324.8	405.5
100°	333.4	300.5	282.9	283.3	282.9	300.5	333.4	379.1	443.2	496.1	532.7
102.5°	466.8	440.7	426.0	415.6	426.0	440.7	466.8	502.3	543.0	573.9	575.0
105°	608.6	591.4	577.0	574.7	577.0	591.4	608.6	629.4	641.2	632.6	587.4
107.5°	681.2	675.4	670.5	666.4	670.5	675.4	681.2	680.8	664.7	625.2	551.8
110°	702.2	705.8	704.9	703.9	704.9	705.8	702.2	689.5	657.9	600.9	517.8



TEST NUMBER: P332368-927

CATALOG NUMBER: S123RDIP-S1165D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	696.7	708.0	711.4	711.5	711.4	708.0	696.7	673.6	633.0	569.1	484.2
115°	667.8	687.7	696.7	699.0	696.7	687.7	667.8	633.9	584.7	518.2	439.7
117.5°	620.2	642.9	656.0	659.0	656.0	642.9	620.2	584.9	534.9	475.2	407.3
120°	586.9	612.3	623.1	625.8	623.1	612.3	586.9	551.3	505.6	451.4	390.4
122.5°	556.6	579.3	591.3	594.7	591.3	579.3	556.6	524.8	482.4	432.2	377.0
125°	516.9	536.8	548.1	551.3	548.1	536.8	516.9	488.0	451.9	408.4	359.2
127.5°	485.4	502.3	512.5	515.5	512.5	502.3	485.4	459.6	426.7	387.6	343.6
130°	465.9	482.1	491.6	495.2	491.6	482.1	465.9	441.9	411.1	374.5	333.9
132.5°	448.1	464.4	472.8	475.3	472.8	464.4	448.1	425.6	396.3	362.3	324.9
135°	422.0	435.5	443.7	446.9	443.7	435.5	422.0	399.9	374.1	344.8	312.7
137.5°	394.1	407.8	414.7	416.8	414.7	407.8	394.1	375.5	353.2	327.9	301.6
140°	376.4	389.0	396.2	395.8	396.2	389.0	376.4	359.2	339.8	318.1	295.1
142.5°	359.0	370.3	376.8	376.3	376.8	370.3	359.0	344.4	327.5	308.7	288.9
145°	335.3	344.8	348.4	349.3	348.4	344.8	335.3	324.0	310.9	296.4	281.5
147.5°	316.8	323.2	326.7	327.0	326.7	323.2	316.8	308.2	299.0	287.2	275.4
150°	306.3	311.3	314.0	314.0	314.0	311.3	306.3	299.6	291.0	281.5	271.1
152.5°	296.9	301.6	303.2	303.2	303.2	301.6	296.9	291.6	284.5	276.1	267.1
155°	284.6	288.3	289.1	289.6	289.1	288.3	284.6	280.6	275.2	268.4	261.2
157.5°	273.9	276.6	277.3	277.3	277.3	276.6	273.9	270.4	266.2	260.9	254.8
160°	267.0	269.7	269.7	269.3	269.7	269.7	267.0	263.9	260.7	256.2	251.2
162.5°	260.2	262.5	262.5	262.1	262.5	262.5	260.2	258.1	255.3	251.1	246.9
165°	251.2	253.0	252.5	252.5	252.5	253.0	251.2	249.4	247.2	244.0	241.3
167.5°	242.7	244.0	243.5	243.5	243.5	244.0	242.7	241.9	240.3	238.4	236.4
170°	237.7	238.6	238.1	238.1	238.1	238.6	237.7	237.2	236.3	234.5	233.1
172.5°	233.3	234.2	233.5	233.1	233.5	234.2	233.3	233.2	232.7	231.2	230.3
175°	227.8	228.1	227.8	227.3	227.8	228.1	227.8	227.8	227.8	226.8	226.4
177.5°	224.3	224.7	223.9	223.9	223.9	224.7	224.3	224.7	224.7	224.3	223.9
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P332368-927

CATALOG NUMBER: S123RDIP-S1165D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1388.2	1395.2	1402.2	1408.7	1418.6	1423.1	1429.6	1432.0	1439.6	1450.5	1459.4
5°	1303.8	1313.8	1326.8	1337.4	1354.2	1367.3	1381.6	1395.3	1411.5	1434.6	1455.1
7.5°	1232.2	1242.1	1257.7	1277.4	1295.9	1314.5	1334.0	1352.7	1375.9	1408.9	1441.6
10°	1184.9	1196.7	1215.4	1236.5	1259.6	1277.6	1300.7	1324.4	1353.0	1391.0	1430.2
12.5°	1144.0	1152.9	1174.6	1194.7	1220.8	1243.8	1266.3	1294.0	1326.6	1367.1	1414.2
15°	1079.0	1091.5	1112.6	1135.0	1162.4	1186.8	1216.0	1249.6	1281.4	1331.2	1388.5
17.5°	1013.8	1032.7	1054.7	1080.0	1100.3	1133.8	1165.5	1200.1	1239.1	1292.0	1354.9
20°	971.9	986.9	1007.4	1044.2	1071.0	1096.5	1125.7	1168.7	1204.8	1264.6	1329.9
22.5°	936.6	947.5	970.6	1000.8	1032.1	1061.6	1091.3	1132.3	1176.9	1233.7	1304.6
25°	884.2	901.6	919.0	940.8	974.4	1009.9	1042.3	1077.1	1124.5	1184.9	1261.5
27.5°	833.0	848.7	865.9	892.7	918.2	951.4	985.2	1025.2	1076.0	1140.0	1217.6
30°	800.1	811.9	828.1	862.4	885.3	914.0	953.9	989.4	1036.6	1104.5	1186.8
32.5°	766.2	781.5	799.2	825.5	854.0	881.1	917.5	956.0	1004.3	1071.2	1155.3
35°	717.9	735.9	754.0	773.3	801.9	830.0	860.5	902.9	952.0	1016.8	1099.5
37.5°	673.4	688.0	702.7	726.6	753.8	780.4	808.9	850.6	897.0	966.9	1042.7
40°	645.1	658.1	669.3	694.3	720.4	749.0	777.1	813.8	863.6	929.0	1002.4
42.5°	614.2	626.2	641.4	661.9	690.0	714.2	742.2	776.9	823.7	890.1	954.6
45°	567.8	581.5	594.6	613.9	641.9	665.6	690.5	723.5	771.4	826.2	883.5
47.5°	519.7	533.4	548.3	567.0	591.4	615.4	640.3	669.6	713.3	767.1	805.6
50°	488.8	499.9	514.9	533.6	556.0	581.5	604.0	635.7	677.4	719.8	753.4
52.5°	456.9	467.1	484.0	503.7	524.7	546.7	570.6	597.9	635.6	675.4	702.1
55°	407.2	419.6	434.0	453.3	473.8	492.5	515.6	543.6	573.5	603.3	621.4
57.5°	360.8	371.1	383.2	403.1	420.9	443.2	463.8	485.7	513.3	535.8	547.6
60°	326.9	336.2	351.8	369.2	386.0	405.4	429.0	450.8	472.0	490.0	499.3
62.5°	295.0	305.9	319.4	335.3	353.6	371.9	392.6	410.9	429.6	445.2	451.5
65°	253.4	262.1	272.1	287.0	302.0	320.7	336.8	355.5	369.2	378.0	383.6
67.5°	215.6	221.3	228.9	238.8	253.5	269.8	285.5	300.1	311.6	317.5	322.5
70°	191.2	194.9	200.5	210.5	221.7	236.0	252.2	262.8	272.7	277.7	282.7
72.5°	166.8	171.5	176.6	184.6	193.8	204.1	215.8	228.9	234.3	240.3	243.4
75°	126.4	133.2	140.1	145.0	151.3	159.4	170.0	178.1	181.2	186.2	186.8
77.5°	95.4	96.9	101.9	108.1	113.3	119.1	125.9	133.1	134.6	137.2	138.9
80°	78.4	78.4	78.4	82.1	88.4	92.8	99.0	102.7	105.2	105.8	106.5
82.5°	63.0	63.0	62.5	63.3	65.5	67.9	73.6	77.8	79.9	79.5	78.1
85°	41.1	39.8	39.8	39.2	39.8	38.6	37.9	40.5	44.2	44.2	42.9
87.5°	19.1	18.7	18.9	18.1	17.3	16.6	15.0	15.3	15.0	16.8	16.1
90°	10.9	11.3	9.9	8.6	7.2	5.9	5.0	4.0	2.7	1.8	0.9
92.5°	52.4	69.5	76.4	57.4	37.9	26.1	19.4	15.6	12.1	8.3	5.6
95°	217.3	267.9	238.6	164.5	97.1	58.7	41.1	29.4	21.7	16.7	15.4
97.5°	444.3	415.3	304.0	180.5	104.6	67.9	48.8	37.2	30.6	26.7	26.2
100°	516.9	427.9	289.1	170.3	103.5	71.9	54.2	43.4	37.1	33.9	33.4
102.5°	520.5	404.4	267.5	161.7	104.9	76.5	60.4	50.6	44.7	41.8	41.0
105°	493.0	363.3	240.8	155.4	108.9	84.5	70.5	61.9	56.5	53.8	52.4
107.5°	444.7	326.9	223.9	155.0	116.3	94.9	81.9	73.8	68.5	65.9	64.5
110°	414.3	306.3	217.3	156.8	122.5	102.1	89.4	81.8	76.8	74.5	73.2



TEST NUMBER: P332368-927

CATALOG NUMBER: S123RDIP-S1165D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	387.9	292.6	213.7	160.4	128.6	109.7	97.4	89.8	84.8	82.5	81.1
115°	356.1	277.9	212.4	166.3	138.7	121.5	109.3	101.6	97.1	94.4	92.6
117.5°	336.8	269.2	213.2	174.0	149.5	132.5	121.2	112.6	108.4	106.2	104.1
120°	326.7	265.2	214.6	179.8	156.3	140.1	128.8	120.2	115.7	113.4	112.1
122.5°	318.4	262.7	217.1	185.3	163.6	147.7	135.6	127.4	122.6	120.3	118.9
125°	307.7	259.4	220.9	193.8	174.0	158.1	145.9	137.4	132.4	129.7	128.8
127.5°	298.3	257.7	225.3	200.9	183.0	167.7	155.5	146.0	141.0	137.6	136.3
130°	293.3	256.7	228.1	205.6	188.4	173.5	161.3	151.8	146.4	142.4	141.0
132.5°	288.5	256.3	230.4	209.9	193.1	178.6	166.8	157.2	150.8	146.3	144.6
135°	282.4	255.7	233.6	215.6	200.2	186.2	174.0	164.5	157.7	152.7	150.9
137.5°	277.1	254.8	235.8	219.7	205.0	191.5	180.3	170.9	163.7	158.8	156.9
140°	273.8	254.4	237.2	221.9	208.3	195.2	183.9	174.8	167.6	163.1	160.9
142.5°	270.9	253.7	238.3	224.0	210.8	198.1	187.5	178.5	172.0	167.1	165.2
145°	267.0	252.5	239.0	226.4	214.2	202.4	192.0	184.3	177.6	173.5	172.1
147.5°	263.2	250.9	239.0	227.8	216.9	206.1	197.3	189.9	184.0	180.0	179.2
150°	260.7	249.4	239.0	228.1	218.7	208.3	200.2	193.8	188.0	184.3	183.9
152.5°	257.9	247.6	238.0	228.9	219.8	210.8	203.0	197.5	192.3	188.7	188.6
155°	253.5	244.5	236.8	229.1	221.9	214.2	207.9	202.9	198.4	195.7	195.7
157.5°	248.6	241.6	235.2	229.6	223.0	216.9	212.0	207.8	203.7	201.6	201.2
160°	245.3	239.5	234.5	229.6	224.1	218.7	214.2	211.0	207.4	205.6	205.6
162.5°	242.1	237.3	233.1	229.2	224.5	219.8	215.9	213.2	210.3	208.8	208.8
165°	237.7	234.1	230.9	228.1	225.0	221.4	218.2	216.4	214.2	213.3	213.7
167.5°	233.5	230.8	228.7	227.4	224.9	222.3	220.3	219.0	217.3	216.9	217.5
170°	230.9	228.6	227.3	226.4	224.6	222.3	221.4	220.5	219.1	218.7	219.6
172.5°	228.4	226.8	226.2	226.0	224.6	222.7	222.1	221.6	220.6	220.5	221.0
175°	225.5	224.6	224.6	225.0	224.1	223.2	222.8	222.8	221.9	222.3	222.8
177.5°	223.6	223.2	223.6	224.3	223.6	223.2	223.2	223.2	222.8	223.2	223.6
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P332368-927

CATALOG NUMBER: S123RDIP-S1165D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1462.4	1467.9	1474.9	1485.3	1493.3	1500.3	1501.8	1503.8	1508.8	1517.2	1523.7
5°	1471.9	1486.2	1509.3	1531.7	1555.9	1575.9	1594.6	1607.7	1620.1	1646.2	1667.4
7.5°	1468.9	1500.8	1536.9	1577.2	1617.9	1657.3	1693.9	1726.6	1759.3	1797.4	1840.9
10°	1466.9	1504.3	1552.8	1604.5	1661.2	1716.6	1770.1	1811.9	1860.4	1904.0	1959.4
12.5°	1457.5	1511.2	1569.3	1635.4	1705.0	1768.9	1839.4	1897.0	1952.6	2015.5	2080.0
15°	1445.1	1510.5	1584.0	1671.7	1777.6	1854.8	1927.1	2027.3	2095.8	2164.2	2256.5
17.5°	1422.6	1502.4	1594.2	1708.3	1796.5	1900.3	2009.0	2088.2	2180.5	2277.0	2360.4
20°	1404.6	1497.5	1600.1	1712.2	1825.0	1937.6	2042.9	2137.5	2232.8	2344.2	2412.7
22.5°	1386.7	1478.5	1585.2	1704.3	1825.4	1944.1	2063.2	2174.4	2281.6	2394.1	2481.4
25°	1348.6	1457.6	1573.4	1694.8	1814.3	1945.1	2087.1	2211.0	2343.6	2459.4	2542.2
27.5°	1310.0	1409.8	1525.2	1648.4	1781.2	1935.8	2102.8	2243.6	2376.5	2459.4	2485.4
30°	1275.2	1381.0	1486.8	1612.0	1755.8	1928.3	2105.7	2267.0	2376.0	2412.0	2385.3
32.5°	1239.8	1335.7	1440.5	1568.7	1721.4	1909.9	2109.7	2253.0	2318.6	2291.1	2182.1
35°	1177.4	1263.9	1365.4	1493.7	1669.3	1899.7	2093.3	2190.4	2174.2	2018.6	1813.1
37.5°	1110.6	1181.1	1275.2	1409.3	1615.3	1859.2	2022.5	2036.9	1896.8	1657.8	1420.5
40°	1057.9	1121.3	1217.9	1358.0	1573.4	1819.3	1951.3	1893.4	1676.1	1410.2	1212.3
42.5°	1006.5	1060.1	1153.1	1304.2	1533.5	1765.1	1845.2	1719.1	1468.4	1217.0	1037.0
45°	919.6	970.0	1063.4	1218.5	1452.0	1661.2	1650.6	1431.4	1180.5	978.2	828.7
47.5°	837.2	881.3	968.9	1127.2	1356.2	1505.5	1406.5	1173.3	960.4	798.1	691.5
50°	778.9	822.5	909.7	1066.0	1279.5	1388.5	1247.1	1022.4	827.5	693.0	608.3
52.5°	723.1	765.7	845.4	997.7	1186.8	1252.0	1100.2	891.8	729.4	613.3	540.6
55°	645.1	677.4	749.0	894.7	1036.1	1051.0	897.2	722.9	589.0	508.1	458.3
57.5°	565.5	593.3	664.1	780.1	879.2	871.6	725.7	575.0	484.8	424.6	388.5
60°	513.7	541.1	603.3	703.0	777.7	751.5	617.7	496.2	419.1	374.9	346.2
62.5°	465.3	486.8	545.0	617.7	671.5	641.9	528.0	427.5	366.2	329.0	306.3
65°	395.4	412.8	459.5	497.5	527.4	498.8	404.1	334.4	290.2	264.0	248.4
67.5°	328.8	339.9	369.5	383.2	404.3	372.8	303.9	257.1	232.0	209.9	199.2
70°	287.0	295.1	310.7	321.9	327.5	295.1	244.1	209.8	188.6	173.1	166.3
72.5°	245.2	252.3	255.4	264.6	261.7	231.4	196.2	169.0	153.8	143.2	134.4
75°	187.4	190.5	187.4	183.7	175.5	154.4	130.2	116.5	105.2	100.2	97.1
77.5°	136.6	135.6	131.3	125.6	111.7	98.4	85.3	80.7	75.8	73.2	72.1
80°	105.2	102.7	99.0	89.7	77.8	68.5	65.4	62.3	60.4	57.3	56.6
82.5°	78.3	76.8	70.6	62.7	54.4	50.1	47.5	46.3	44.4	42.9	42.7
85°	41.7	39.8	33.0	28.7	27.4	26.1	25.5	25.5	23.1	22.4	22.4
87.5°	13.8	11.0	10.8	9.4	9.7	9.0	9.7	9.0	8.7	9.1	8.2
90°	1.8	2.7	4.0	5.0	5.9	7.2	8.6	9.9	11.3	10.9	11.3
92.5°	8.3	12.1	15.6	19.4	26.1	37.9	57.4	76.4	69.5	52.4	38.0
95°	16.7	21.7	29.4	41.1	58.7	97.1	164.5	238.6	267.9	217.3	162.6
97.5°	26.7	30.6	37.2	48.8	67.9	104.6	180.5	304.0	415.3	444.3	405.5
100°	33.9	37.1	43.4	54.2	71.9	103.5	170.3	289.1	427.9	516.9	532.7
102.5°	41.8	44.7	50.6	60.4	76.5	104.9	161.7	267.5	404.4	520.5	575.0
105°	53.8	56.5	61.9	70.5	84.5	108.9	155.4	240.8	363.3	493.0	587.4
107.5°	65.9	68.5	73.8	81.9	94.9	116.3	155.0	223.9	326.9	444.7	551.8
110°	74.5	76.8	81.8	89.4	102.1	122.5	156.8	217.3	306.3	414.3	517.8



TEST NUMBER: P332368-927

CATALOG NUMBER: S123RDIP-S1165D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	82.5	84.8	89.8	97.4	109.7	128.6	160.4	213.7	292.6	387.9	484.2
115°	94.4	97.1	101.6	109.3	121.5	138.7	166.3	212.4	277.9	356.1	439.7
117.5°	106.2	108.4	112.6	121.2	132.5	149.5	174.0	213.2	269.2	336.8	407.3
120°	113.4	115.7	120.2	128.8	140.1	156.3	179.8	214.6	265.2	326.7	390.4
122.5°	120.3	122.6	127.4	135.6	147.7	163.6	185.3	217.1	262.7	318.4	377.0
125°	129.7	132.4	137.4	145.9	158.1	174.0	193.8	220.9	259.4	307.7	359.2
127.5°	137.6	141.0	146.0	155.5	167.7	183.0	200.9	225.3	257.7	298.3	343.6
130°	142.4	146.4	151.8	161.3	173.5	188.4	205.6	228.1	256.7	293.3	333.9
132.5°	146.3	150.8	157.2	166.8	178.6	193.1	209.9	230.4	256.3	288.5	324.9
135°	152.7	157.7	164.5	174.0	186.2	200.2	215.6	233.6	255.7	282.4	312.7
137.5°	158.8	163.7	170.9	180.3	191.5	205.0	219.7	235.8	254.8	277.1	301.6
140°	163.1	167.6	174.8	183.9	195.2	208.3	221.9	237.2	254.4	273.8	295.1
142.5°	167.1	172.0	178.5	187.5	198.1	210.8	224.0	238.3	253.7	270.9	288.9
145°	173.5	177.6	184.3	192.0	202.4	214.2	226.4	239.0	252.5	267.0	281.5
147.5°	180.0	184.0	189.9	197.3	206.1	216.9	227.8	239.0	250.9	263.2	275.4
150°	184.3	188.0	193.8	200.2	208.3	218.7	228.1	239.0	249.4	260.7	271.1
152.5°	188.7	192.3	197.5	203.0	210.8	219.8	228.9	238.0	247.6	257.9	267.1
155°	195.7	198.4	202.9	207.9	214.2	221.9	229.1	236.8	244.5	253.5	261.2
157.5°	201.6	203.7	207.8	212.0	216.9	223.0	229.6	235.2	241.6	248.6	254.8
160°	205.6	207.4	211.0	214.2	218.7	224.1	229.6	234.5	239.5	245.3	251.2
162.5°	208.8	210.3	213.2	215.9	219.8	224.5	229.2	233.1	237.3	242.1	246.9
165°	213.3	214.2	216.4	218.2	221.4	225.0	228.1	230.9	234.1	237.7	241.3
167.5°	216.9	217.3	219.0	220.3	222.3	224.9	227.4	228.7	230.8	233.5	236.4
170°	218.7	219.1	220.5	221.4	222.3	224.6	226.4	227.3	228.6	230.9	233.1
172.5°	220.5	220.6	221.6	222.1	222.7	224.6	226.0	226.2	226.8	228.4	230.3
175°	222.3	221.9	222.8	222.8	223.2	224.1	225.0	224.6	224.6	225.5	226.4
177.5°	223.2	222.8	223.2	223.2	223.2	223.6	224.3	223.6	223.2	223.6	223.9
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P332368-927

CATALOG NUMBER: S123RDIP-S1165D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4	1454.4
2.5°	1534.1	1534.1	1536.1	1543.6	1544.6	1551.1	1549.1
5°	1686.1	1697.9	1702.2	1720.9	1732.2	1737.2	1727.2
7.5°	1871.8	1905.3	1921.0	1940.6	1958.0	1963.2	1949.6
10°	2007.4	2042.2	2071.5	2089.5	2106.3	2117.6	2131.9
12.5°	2138.3	2181.2	2209.0	2234.5	2251.8	2266.0	2268.3
15°	2280.7	2345.4	2394.6	2430.7	2448.8	2458.1	2454.4
17.5°	2424.2	2484.3	2519.3	2556.1	2581.2	2582.4	2583.1
20°	2505.4	2564.0	2604.5	2631.9	2659.9	2658.6	2664.8
22.5°	2559.8	2605.8	2636.9	2656.7	2666.3	2661.7	2662.8
25°	2585.1	2598.8	2593.3	2561.5	2553.4	2524.1	2529.1
27.5°	2454.2	2389.4	2322.4	2236.3	2168.3	2113.9	2116.7
30°	2276.3	2161.8	2031.0	1921.4	1823.0	1795.6	1737.2
32.5°	2027.7	1855.9	1702.8	1600.7	1516.2	1493.3	1442.2
35°	1606.4	1439.6	1282.0	1187.3	1150.0	1097.7	1097.1
37.5°	1248.6	1101.7	1018.4	947.4	910.1	878.5	875.4
40°	1050.4	935.8	872.9	821.9	785.1	761.4	755.9
42.5°	911.9	819.3	760.3	728.7	700.4	688.2	679.1
45°	744.7	682.4	641.3	612.7	599.6	590.3	585.3
47.5°	622.9	581.1	553.2	534.1	523.5	513.7	516.3
50°	556.7	522.4	501.8	483.8	475.7	468.8	469.4
52.5°	503.4	472.6	456.0	442.9	432.8	428.0	425.6
55°	427.1	407.8	391.0	381.7	376.0	369.2	367.3
57.5°	364.3	349.4	335.7	325.1	323.8	317.2	318.1
60°	322.5	310.1	298.9	293.3	288.9	283.3	285.2
62.5°	288.1	277.7	267.5	262.8	258.5	254.4	255.2
65°	236.0	226.0	219.8	217.3	215.4	213.6	211.7
67.5°	188.1	182.0	178.1	172.7	168.9	168.3	166.4
70°	158.1	150.0	143.2	136.3	134.5	133.9	134.5
72.5°	126.7	121.7	119.8	116.5	116.1	114.5	115.6
75°	95.3	93.4	92.1	89.7	89.7	89.7	89.7
77.5°	70.3	69.1	68.4	67.9	67.3	66.4	66.2
80°	54.8	54.2	52.9	52.9	52.3	52.9	52.3
82.5°	41.4	41.2	40.0	40.0	39.4	39.0	39.4
85°	21.2	20.5	21.8	20.5	21.2	20.0	21.2
87.5°	8.3	8.4	8.1	8.0	7.6	8.7	7.6
90°	11.7	12.2	13.1	12.7	13.1	13.5	13.1
92.5°	30.2	26.7	24.3	23.5	22.1	22.6	21.8
95°	110.3	86.3	70.0	61.5	57.4	54.2	52.4
97.5°	324.8	266.5	212.5	179.1	158.8	146.6	142.7
100°	496.1	443.2	379.1	333.4	300.5	282.9	283.3
102.5°	573.9	543.0	502.3	466.8	440.7	426.0	415.6
105°	632.6	641.2	629.4	608.6	591.4	577.0	574.7
107.5°	625.2	664.7	680.8	681.2	675.4	670.5	666.4
110°	600.9	657.9	689.5	702.2	705.8	704.9	703.9



TEST NUMBER: P332368-927

CATALOG NUMBER: S123RDIP-S1165D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	569.1	633.0	673.6	696.7	708.0	711.4	711.5
115°	518.2	584.7	633.9	667.8	687.7	696.7	699.0
117.5°	475.2	534.9	584.9	620.2	642.9	656.0	659.0
120°	451.4	505.6	551.3	586.9	612.3	623.1	625.8
122.5°	432.2	482.4	524.8	556.6	579.3	591.3	594.7
125°	408.4	451.9	488.0	516.9	536.8	548.1	551.3
127.5°	387.6	426.7	459.6	485.4	502.3	512.5	515.5
130°	374.5	411.1	441.9	465.9	482.1	491.6	495.2
132.5°	362.3	396.3	425.6	448.1	464.4	472.8	475.3
135°	344.8	374.1	399.9	422.0	435.5	443.7	446.9
137.5°	327.9	353.2	375.5	394.1	407.8	414.7	416.8
140°	318.1	339.8	359.2	376.4	389.0	396.2	395.8
142.5°	308.7	327.5	344.4	359.0	370.3	376.8	376.3
145°	296.4	310.9	324.0	335.3	344.8	348.4	349.3
147.5°	287.2	299.0	308.2	316.8	323.2	326.7	327.0
150°	281.5	291.0	299.6	306.3	311.3	314.0	314.0
152.5°	276.1	284.5	291.6	296.9	301.6	303.2	303.2
155°	268.4	275.2	280.6	284.6	288.3	289.1	289.6
157.5°	260.9	266.2	270.4	273.9	276.6	277.3	277.3
160°	256.2	260.7	263.9	267.0	269.7	269.7	269.3
162.5°	251.1	255.3	258.1	260.2	262.5	262.5	262.1
165°	244.0	247.2	249.4	251.2	253.0	252.5	252.5
167.5°	238.4	240.3	241.9	242.7	244.0	243.5	243.5
170°	234.5	236.3	237.2	237.7	238.6	238.1	238.1
172.5°	231.2	232.7	233.2	233.3	234.2	233.5	233.1
175°	226.8	227.8	227.8	227.8	228.1	227.8	227.3
177.5°	224.3	224.7	224.7	224.3	224.7	223.9	223.9
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2

(END OF REPORT)