

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332038

Luminaire Tested: **S123DIP-S1000D1195U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332038
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D1195U835-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8561.7 lumens
Efficiency: N/A
Efficacy: 130.9 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332038

CATALOG NUMBER: S123DIP-S1000D1195U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332038

CATALOG NUMBER: S123DIP-S1000D1195U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50																												
1	98	94	90	87	90	87	83	80	73	71	69	61	59	58	50	49	48	42																												
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40	36																												
3	82	72	65	59	75	67	61	56	57	52	48	48	44	41	39	37	35	31																												
4	75	64	56	50	69	60	53	47	51	46	41	43	39	36	35	32	30	26																												
5	69	57	49	43	63	53	46	41	46	40	36	38	34	31	32	29	26	23																												
6	63	51	43	38	58	48	41	36	41	36	31	35	30	27	29	26	23	20																												
7	59	46	39	33	54	43	36	31	37	32	28	32	27	24	26	23	21	18																												
8	54	42	34	29	50	39	32	28	34	28	25	29	25	22	24	21	19	16																												
9	51	38	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17	15																												
10	47	35	28	23	44	33	27	22	29	23	20	25	20	17	21	17	15	13																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15118	15118	15118	15118
5°	18029	15183	13456	15183
10°	22566	15106	12153	15106
15°	27679	14985	11314	14985
20°	32972	14795	10772	14795
25°	35011	14563	10652	14563
30°	30009	14395	10708	14395
35°	20871	14155	10820	14155
40°	15719	13874	10786	13874
45°	13052	13457	10648	13457
50°	11692	12603	10551	12603
55°	10931	11684	10421	11684
60°	10254	10723	10314	10723
65°	9638	9775	9984	9775
70°	9039	8696	9508	8696
75°	8093	7615	8717	7615
80°	7085	6242	7507	6242
85°	5545	4533	5039	4533



TEST NUMBER: P332038

CATALOG NUMBER: S123DIP-S1000D1195U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.4	1.6
10°-20°	443.6	5.2
20°-30°	744.6	8.7
30°-40°	843.1	9.8
40°-50°	756.1	8.8
50°-60°	610.1	7.1
60°-70°	425.2	5.0
70°-80°	223.5	2.6
80°-90°	59.1	0.7
90°-100°	319.4	3.7
100°-110°	904.4	10.6
110°-120°	889.7	10.4
120°-130°	709.7	8.3
130°-140°	559.5	6.5
140°-150°	417.6	4.9
150°-160°	291.1	3.4
160°-170°	171.0	2.0
170°-180°	55.6	0.6
0°-30°	1326.6	15.5
0°-40°	2169.7	25.3
0°-60°	3535.9	41.3
0°-90°	4243.6	49.6
90°-120°	2113.6	24.7
90°-150°	3800.4	44.4
90°-180°	4318.0	50.4
0°-180°	8561.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1404	1404	1404	1404	1404	
5°	1669	1405	1245	1405	1669	173
15°	2484	1345	1015	1345	2484	717
25°	2948	1226	897	1226	2948	1293
35°	1588	1077	823	1077	1588	1032
45°	857	884	700	884	857	678
55°	582	623	555	623	582	523
65°	378	384	392	384	378	377
75°	195	183	210	183	195	208
85°	45	37	41	37	45	54
90°	34	2	34	2	34	20
95°	135	40	135	40	135	243
105°	1478	135	1478	135	1478	1458
115°	1797	238	1797	238	1797	1746
125°	1418	331	1418	331	1418	1285
135°	1149	388	1149	388	1149	891
145°	898	443	898	443	898	571
155°	745	503	745	503	745	347
165°	650	550	650	550	650	186
175°	584	573	584	573	584	57
180°	574	574	574	574	574	



TEST NUMBER: P332038

CATALOG NUMBER: S123DIP-S1000D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1490.5	1489.5	1486.7	1488.9	1484.6	1478.6	1478.0	1472.6	1456.8	1455.7	1451.4
5°	1668.6	1663.1	1662.4	1661.8	1652.2	1639.3	1614.8	1612.8	1580.1	1563.8	1544.0
7.5°	1899.1	1902.0	1892.0	1883.3	1854.2	1835.0	1808.7	1775.1	1735.0	1694.3	1667.2
10°	2064.6	2087.1	2059.2	2040.1	2022.4	1989.1	1950.3	1902.0	1853.7	1797.2	1754.3
12.5°	2242.1	2253.1	2247.5	2229.6	2202.1	2151.3	2082.6	2029.4	1984.9	1890.8	1852.8
15°	2483.8	2525.3	2498.8	2437.5	2438.9	2390.6	2300.7	2202.1	2149.7	2067.3	1955.1
17.5°	2741.3	2746.5	2735.2	2684.1	2650.1	2583.7	2500.8	2406.2	2300.1	2200.4	2081.4
20°	2878.5	2874.4	2850.6	2824.0	2765.5	2713.8	2623.3	2517.8	2381.7	2283.7	2153.8
22.5°	2954.7	2947.9	2936.6	2914.4	2865.7	2810.2	2728.9	2613.6	2484.1	2349.1	2198.9
25°	2947.9	2956.7	2958.1	2952.0	2935.0	2901.6	2837.6	2745.8	2616.5	2443.0	2286.5
27.5°	2681.1	2693.7	2730.0	2762.3	2798.3	2835.1	2830.2	2784.6	2688.9	2539.0	2347.7
30°	2414.4	2387.2	2454.5	2539.6	2597.4	2699.5	2756.7	2760.1	2706.3	2577.7	2391.2
32.5°	2044.2	2074.1	2103.9	2208.6	2335.0	2449.6	2563.4	2655.0	2665.5	2579.9	2416.8
35°	1588.3	1625.7	1680.1	1734.6	1870.7	1987.7	2187.8	2362.0	2500.8	2519.2	2419.1
37.5°	1279.9	1298.4	1332.8	1387.4	1476.4	1615.2	1770.0	1990.2	2191.3	2340.9	2347.4
40°	1118.7	1124.2	1163.0	1204.5	1276.6	1390.9	1530.4	1725.0	1965.9	2174.9	2262.0
42.5°	997.9	1009.8	1026.3	1066.2	1123.6	1209.6	1339.3	1500.2	1721.0	1961.4	2131.8
45°	857.4	871.0	881.2	907.8	948.6	1006.4	1097.0	1243.9	1412.0	1660.4	1889.7
47.5°	764.6	765.7	773.3	793.3	821.1	864.5	928.5	1022.9	1177.2	1378.7	1614.1
50°	698.2	709.1	711.8	727.4	749.2	781.2	834.3	914.6	1041.2	1218.1	1434.5
52.5°	651.4	654.6	662.3	673.6	692.6	717.5	763.5	826.4	925.7	1076.5	1275.5
55°	582.5	582.5	590.0	598.8	609.7	632.2	662.8	709.1	784.6	901.7	1066.3
57.5°	518.8	522.2	527.5	530.2	539.5	554.3	579.9	615.0	671.4	761.5	892.4
60°	476.3	482.5	481.8	487.2	495.4	507.0	528.7	557.3	607.7	679.8	790.1
62.5°	439.3	438.9	438.8	445.3	453.5	464.5	478.7	503.4	546.2	610.1	704.0
65°	378.4	377.0	381.8	385.8	388.6	396.7	407.6	429.4	458.0	505.6	578.4
67.5°	324.2	320.2	322.8	324.2	328.8	335.2	345.4	358.9	381.6	419.9	474.7
70°	287.2	283.8	283.1	284.4	288.5	293.3	300.8	313.7	334.8	365.4	405.6
72.5°	249.1	246.7	246.6	249.6	251.5	254.6	259.9	271.8	288.5	311.5	349.0
75°	194.6	194.6	194.6	195.3	197.3	200.1	204.1	210.3	223.2	239.5	264.7
77.5°	145.9	145.8	144.9	144.8	147.8	149.0	150.0	155.7	162.9	173.9	192.3
80°	114.3	110.9	112.3	114.3	115.7	116.4	118.4	119.8	125.9	132.0	144.9
82.5°	84.9	82.1	82.3	85.5	85.7	86.4	88.5	90.4	92.7	98.3	105.2
85°	44.9	44.9	45.6	45.6	46.3	45.6	47.6	48.3	48.3	51.7	55.8
87.5°	23.1	22.2	22.5	22.8	22.5	22.6	22.9	23.2	23.5	24.3	24.2
90°	33.7	34.9	33.7	32.5	33.7	31.4	30.2	29.0	27.9	29.0	25.6
92.5°	56.0	58.1	56.9	60.4	62.5	68.5	77.6	97.8	134.8	178.7	196.6
95°	134.8	139.4	147.6	158.0	180.1	221.9	283.5	418.3	558.8	689.0	613.5
97.5°	366.9	376.9	408.3	460.6	546.3	685.3	835.1	1042.6	1142.3	1067.7	781.7
100°	728.5	727.3	772.6	857.4	974.8	1139.8	1275.7	1369.8	1329.2	1100.3	743.6
102.5°	1068.7	1095.4	1133.3	1200.4	1291.7	1396.3	1475.5	1478.6	1338.4	1039.9	687.8
105°	1477.9	1483.7	1520.9	1565.0	1618.5	1648.7	1626.6	1510.4	1267.6	934.1	619.3
107.5°	1713.5	1724.2	1736.7	1751.6	1750.7	1709.3	1607.5	1418.8	1143.5	840.7	575.6
110°	1810.2	1812.5	1814.8	1805.5	1773.0	1691.7	1545.3	1331.5	1065.4	787.7	558.8



TEST NUMBER: P332038

CATALOG NUMBER: S123DIP-S1000D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1829.7	1829.2	1820.4	1791.6	1732.1	1627.5	1463.5	1245.0	997.6	752.4	549.6
115°	1797.4	1791.6	1768.3	1717.2	1630.1	1503.4	1332.6	1130.5	915.5	714.5	546.1
117.5°	1694.7	1686.8	1653.3	1594.8	1503.9	1375.4	1222.0	1047.5	866.0	692.2	548.2
120°	1609.2	1602.2	1574.3	1509.2	1417.5	1300.1	1160.7	1003.8	840.0	682.0	551.9
122.5°	1529.2	1520.4	1489.7	1431.2	1349.6	1240.6	1111.4	969.4	818.6	675.5	558.4
125°	1417.5	1409.3	1380.3	1329.2	1254.8	1161.8	1050.3	923.7	791.2	666.9	568.1
127.5°	1325.4	1318.0	1291.7	1248.1	1181.8	1097.2	996.6	883.7	767.1	662.7	579.3
130°	1273.4	1264.1	1239.7	1197.9	1136.3	1057.3	963.2	858.6	754.0	659.9	586.7
132.5°	1222.3	1215.8	1194.1	1152.3	1094.5	1019.2	931.6	835.4	742.0	659.0	592.3
135°	1149.1	1140.9	1120.0	1085.2	1028.2	962.0	886.5	804.0	726.2	657.6	600.7
137.5°	1071.7	1066.3	1048.7	1013.4	965.5	908.1	843.0	775.4	712.4	655.0	606.3
140°	1017.8	1018.9	1000.4	967.8	923.7	873.7	817.9	758.7	704.1	654.1	610.0
142.5°	967.6	968.7	952.0	923.2	885.6	842.1	793.8	742.9	696.6	652.3	612.8
145°	898.1	895.8	886.5	862.1	833.0	799.4	762.2	723.8	686.7	649.5	614.6
147.5°	840.9	840.0	831.2	814.7	792.6	768.7	738.7	708.3	676.9	645.1	614.6
150°	807.5	807.5	800.5	787.7	770.3	748.2	723.8	697.1	670.4	641.3	614.6
152.5°	779.6	779.6	775.4	763.6	749.9	731.5	709.9	686.9	663.0	636.7	611.8
155°	744.7	743.6	741.3	732.0	721.5	707.6	690.1	671.5	651.8	628.6	608.8
157.5°	712.9	713.1	711.3	704.3	695.2	684.3	670.9	655.3	639.2	621.4	604.9
160°	692.5	693.6	693.6	686.7	678.5	670.4	658.8	646.0	630.9	615.8	603.0
162.5°	673.9	675.0	675.0	669.0	663.6	656.4	645.8	634.8	622.5	610.2	599.3
165°	649.5	649.5	650.6	646.0	641.3	635.5	627.4	620.4	611.1	601.8	593.7
167.5°	626.2	626.2	627.4	624.1	622.1	617.9	613.2	607.9	600.2	593.5	588.1
170°	612.3	612.3	613.5	611.1	610.0	607.6	603.0	599.5	593.7	587.9	584.4
172.5°	599.3	600.2	602.3	600.0	599.7	598.4	594.6	592.1	587.2	583.2	581.6
175°	584.4	585.6	586.7	585.6	585.6	585.6	583.2	582.1	579.8	577.4	577.4
177.5°	575.8	575.8	577.7	576.7	577.7	577.7	576.7	575.8	574.9	574.0	574.9
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0



TEST NUMBER: P332038

CATALOG NUMBER: S123DIP-S1000D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1448.1	1443.7	1439.4	1431.8	1425.2	1416.0	1413.2	1410.0	1400.2	1391.5	1384.9
5°	1536.5	1520.2	1496.4	1474.6	1456.9	1433.1	1419.5	1405.2	1384.8	1366.4	1351.5
7.5°	1629.1	1597.0	1560.0	1519.9	1482.7	1446.7	1417.7	1391.9	1363.3	1336.2	1315.1
10°	1702.6	1656.3	1604.6	1548.8	1501.2	1454.9	1416.1	1382.1	1345.3	1313.3	1286.8
12.5°	1786.4	1717.8	1646.5	1578.7	1522.4	1458.2	1411.2	1367.9	1326.3	1287.8	1258.0
15°	1885.6	1798.5	1714.2	1620.9	1535.2	1454.9	1399.1	1344.7	1296.3	1256.9	1218.8
17.5°	1976.0	1877.3	1766.1	1652.8	1549.3	1454.1	1376.0	1314.4	1254.0	1205.7	1167.7
20°	2027.2	1914.9	1789.0	1671.3	1557.0	1450.8	1365.1	1291.6	1226.2	1175.2	1132.3
22.5°	2071.3	1939.9	1809.7	1683.8	1556.4	1442.1	1344.9	1269.3	1198.5	1148.5	1102.9
25°	2117.0	1959.8	1829.2	1681.5	1539.3	1420.9	1312.0	1226.2	1155.5	1097.0	1050.0
27.5°	2156.2	1958.5	1803.4	1644.6	1512.3	1393.6	1277.4	1185.4	1110.3	1046.7	999.1
30°	2182.3	1961.2	1776.8	1619.6	1486.2	1363.7	1250.7	1158.2	1079.3	1014.6	969.7
32.5°	2198.7	1959.5	1752.3	1584.7	1444.8	1336.5	1221.9	1126.1	1045.0	981.4	938.1
35°	2208.2	1947.6	1710.1	1512.7	1378.0	1272.5	1176.6	1077.2	992.2	933.0	884.0
37.5°	2189.1	1922.4	1661.1	1443.3	1295.8	1191.9	1111.2	1026.6	945.2	880.0	837.8
40°	2159.2	1906.1	1623.0	1394.3	1239.2	1139.1	1070.4	987.4	907.1	845.2	805.7
42.5°	2102.0	1872.8	1581.1	1339.9	1180.4	1080.3	1017.1	947.7	871.7	813.6	774.1
45°	1962.5	1800.6	1518.2	1258.2	1093.5	990.1	934.3	884.0	815.2	758.7	724.7
47.5°	1769.0	1691.8	1427.3	1172.1	1002.9	903.4	845.4	804.9	754.7	709.1	676.4
50°	1634.5	1602.6	1365.7	1113.3	942.5	845.2	789.4	752.6	716.6	671.0	641.0
52.5°	1479.4	1499.1	1293.9	1052.3	881.0	785.3	732.8	703.6	670.8	633.4	607.3
55°	1261.0	1332.4	1169.8	950.0	789.4	698.2	648.5	622.6	603.6	575.7	553.2
57.5°	1056.4	1147.3	1035.6	844.5	699.4	620.7	573.1	544.9	532.7	518.1	500.4
60°	935.0	1024.8	939.8	773.7	639.0	564.1	521.9	498.1	485.9	475.7	460.7
62.5°	826.7	917.6	846.1	701.9	579.6	510.2	473.5	450.2	440.7	435.4	422.6
65°	677.8	756.0	708.4	590.0	494.7	433.5	400.1	383.8	375.0	372.9	364.7
67.5°	551.6	611.2	576.5	489.4	414.4	361.5	333.2	319.3	312.5	311.8	305.7
70°	468.9	524.7	498.1	419.2	354.5	313.0	288.5	276.3	272.2	271.5	268.1
72.5°	404.6	443.5	422.4	356.6	306.6	268.9	251.0	238.2	233.5	234.5	232.2
75°	299.4	328.7	316.4	270.8	230.7	206.2	191.2	183.1	179.0	181.0	178.3
77.5°	215.4	234.0	222.9	191.4	166.6	148.9	137.9	132.8	129.2	129.0	127.8
80°	162.6	173.5	167.4	148.3	127.9	113.0	104.1	100.7	98.7	98.0	97.3
82.5°	115.8	125.1	117.9	104.8	90.9	81.9	76.9	72.4	70.9	71.3	70.6
85°	58.5	61.9	59.2	51.0	45.6	41.5	38.8	36.7	35.4	36.1	34.7
87.5°	24.6	24.4	22.1	19.4	17.9	15.5	15.1	13.5	12.9	13.4	13.5
90°	22.1	18.6	15.1	12.8	10.5	7.0	4.6	2.3	4.6	7.0	10.5
92.5°	147.6	97.6	67.2	50.0	40.2	31.1	21.4	14.4	21.4	31.1	40.2
95°	422.9	249.8	151.0	105.7	75.5	55.8	43.0	39.5	43.0	55.8	75.5
97.5°	464.0	268.9	174.5	125.5	95.7	78.5	68.5	67.4	68.5	78.5	95.7
100°	438.0	266.1	184.7	139.4	111.5	95.3	87.1	86.0	87.1	95.3	111.5
102.5°	415.7	269.8	196.8	155.2	130.1	114.8	107.6	105.5	107.6	114.8	130.1
105°	399.7	280.0	217.3	181.2	159.2	145.2	138.3	134.8	138.3	145.2	159.2
107.5°	398.5	299.1	244.0	210.5	189.8	176.1	169.4	165.9	169.4	176.1	189.8
110°	403.2	314.9	262.6	230.0	210.3	197.5	191.7	188.2	191.7	197.5	210.3



TEST NUMBER: P332038

CATALOG NUMBER: S123DIP-S1000D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	412.5	330.7	282.1	250.5	230.7	218.0	212.2	208.7	212.2	218.0	230.7
115°	427.6	356.7	312.5	281.2	261.4	249.8	242.8	238.2	242.8	249.8	261.4
117.5°	447.5	384.3	340.7	311.6	289.5	278.8	273.0	267.7	273.0	278.8	289.5
120°	462.4	402.0	360.2	331.1	309.1	297.4	291.6	288.1	291.6	297.4	309.1
122.5°	476.4	420.6	379.7	348.8	327.6	315.1	309.3	305.8	309.3	315.1	327.6
125°	498.4	447.3	406.6	375.3	353.2	340.4	333.5	331.1	333.5	340.4	353.2
127.5°	516.6	470.5	431.3	399.9	375.5	362.5	353.9	350.4	353.9	362.5	375.5
130°	528.6	484.5	446.1	414.8	390.4	376.4	366.0	362.5	366.0	376.4	390.4
132.5°	539.8	496.6	459.2	428.7	404.3	387.6	376.2	371.8	376.2	387.6	404.3
135°	554.2	514.7	478.7	447.3	422.9	405.5	392.7	388.1	392.7	405.5	422.9
137.5°	564.9	527.2	492.6	463.6	439.4	420.8	408.3	403.4	408.3	420.8	439.4
140°	570.5	535.6	501.9	472.9	449.6	431.0	419.4	413.6	419.4	431.0	449.6
142.5°	576.0	542.1	509.4	482.2	458.9	442.2	429.7	424.8	429.7	442.2	458.9
145°	582.1	550.7	520.5	493.8	474.0	456.6	446.1	442.7	446.1	456.6	474.0
147.5°	585.8	557.7	530.0	507.3	488.2	473.1	462.9	460.8	462.9	473.1	488.2
150°	586.7	562.3	535.6	514.7	498.4	483.3	474.0	472.9	474.0	483.3	498.4
152.5°	588.6	565.1	542.1	522.1	507.7	494.5	485.2	485.0	485.2	494.5	507.7
155°	589.1	570.5	550.7	534.4	521.7	510.1	503.1	503.1	503.1	510.1	521.7
157.5°	590.2	573.5	557.7	545.1	534.2	524.0	518.4	517.5	518.4	524.0	534.2
160°	590.2	576.3	562.3	550.7	542.6	533.3	528.6	528.6	528.6	533.3	542.6
162.5°	589.3	577.2	565.1	555.4	548.2	540.7	537.0	537.0	537.0	540.7	548.2
165°	586.7	578.6	569.3	561.2	556.5	550.7	548.4	549.6	548.4	550.7	556.5
167.5°	584.9	578.4	571.6	566.5	563.3	558.8	557.7	559.1	557.7	558.8	563.3
170°	582.1	577.4	571.6	569.3	567.0	563.5	562.3	564.7	562.3	563.5	567.0
172.5°	581.2	577.4	572.6	571.2	569.8	567.2	567.0	568.4	567.0	567.2	569.8
175°	578.6	576.3	574.0	572.8	572.8	570.5	571.6	572.8	571.6	570.5	572.8
177.5°	576.7	574.9	574.0	574.0	574.0	573.0	574.0	574.9	574.0	573.0	574.0
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0



TEST NUMBER: P332038

CATALOG NUMBER: S123DIP-S1000D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1381.1	1377.3	1371.9	1363.7	1357.2	1346.8	1346.8	1348.5	1348.5	1347.9	1346.8
5°	1339.2	1329.0	1316.8	1302.5	1287.5	1272.5	1269.8	1264.4	1260.3	1257.5	1254.1
7.5°	1295.0	1276.9	1259.0	1239.0	1220.8	1205.7	1195.2	1186.5	1180.9	1174.9	1170.6
10°	1265.0	1242.6	1221.5	1200.4	1177.2	1158.9	1147.3	1139.1	1133.0	1127.6	1124.9
12.5°	1229.6	1203.9	1180.7	1160.6	1135.3	1116.4	1105.4	1101.6	1094.4	1082.9	1076.9
15°	1177.9	1154.1	1126.2	1095.6	1083.3	1060.2	1047.3	1041.2	1037.1	1028.2	1025.5
17.5°	1133.7	1102.5	1071.2	1048.4	1025.6	1006.9	999.6	992.0	986.6	979.4	977.2
20°	1098.3	1070.4	1041.8	1017.3	993.5	973.1	967.0	961.5	956.1	952.7	950.0
22.5°	1062.4	1034.5	1010.8	987.9	962.5	949.1	942.5	936.5	932.7	930.4	927.6
25°	1011.9	987.4	960.9	940.4	920.0	911.2	907.1	903.7	901.0	897.6	896.9
27.5°	966.7	940.0	918.5	899.5	884.8	877.4	873.5	871.8	872.4	873.6	874.4
30°	933.0	908.5	890.8	874.4	860.8	854.0	853.3	853.3	856.1	856.7	858.1
32.5°	901.9	881.8	864.1	848.3	838.0	833.3	835.9	835.9	838.1	839.9	842.3
35°	856.7	839.0	825.4	811.8	803.0	805.0	806.4	807.7	811.1	815.2	818.0
37.5°	813.6	798.2	784.1	773.4	769.4	773.0	776.3	779.2	783.1	786.2	789.0
40°	782.6	771.0	757.4	747.9	749.2	751.3	754.0	757.4	760.8	762.8	765.6
42.5°	753.7	741.6	731.3	723.4	725.3	727.9	729.5	731.3	735.2	738.9	740.5
45°	709.8	700.2	690.7	685.9	687.3	688.7	690.0	692.1	695.5	698.2	698.9
47.5°	660.3	653.7	647.3	642.7	644.8	644.3	646.1	650.4	651.5	653.1	656.9
50°	628.8	622.6	615.2	613.8	613.8	613.8	614.5	619.9	619.9	622.6	625.4
52.5°	593.9	590.0	585.2	582.8	581.7	581.7	584.5	587.3	588.4	592.2	594.9
55°	542.4	538.3	534.2	532.1	530.8	532.1	537.6	538.9	542.4	544.4	546.4
57.5°	488.6	485.5	482.2	481.1	480.8	482.6	485.6	489.7	490.5	496.8	499.9
60°	453.2	448.4	445.7	445.7	444.4	450.5	449.1	455.9	457.3	461.4	466.1
62.5°	416.7	410.3	409.2	409.2	411.2	412.9	414.8	417.8	421.4	426.5	430.2
65°	357.9	354.5	359.3	358.6	357.3	361.3	361.3	364.7	368.8	373.6	381.1
67.5°	302.3	300.5	300.9	300.9	303.0	305.3	307.2	310.2	315.1	320.1	325.0
70°	264.7	266.8	263.4	266.1	268.1	268.8	270.2	274.2	279.7	283.1	288.5
72.5°	228.2	228.1	228.5	229.6	231.6	232.9	234.2	238.9	244.8	247.7	252.1
75°	175.6	174.9	176.9	176.9	180.3	181.7	183.1	185.1	190.5	194.6	198.0
77.5°	128.2	129.0	128.6	130.9	130.0	130.2	134.5	136.5	137.1	145.1	146.9
80°	96.6	98.0	98.7	99.4	100.0	98.7	103.4	105.5	105.5	110.2	113.6
82.5°	69.4	70.2	72.0	72.7	72.8	74.2	74.6	76.1	77.7	79.8	84.2
85°	34.7	36.7	37.4	36.7	37.4	36.1	38.1	38.8	39.5	39.5	39.5
87.5°	13.4	14.5	14.6	15.8	16.0	17.2	17.0	16.2	16.4	18.3	16.5
90°	12.8	15.1	18.6	22.1	25.6	29.0	27.9	29.0	30.2	31.4	33.7
92.5°	50.0	67.2	97.6	147.6	196.6	178.7	134.8	97.8	77.6	68.5	62.5
95°	105.7	151.0	249.8	422.9	613.5	689.0	558.8	418.3	283.5	221.9	180.1
97.5°	125.5	174.5	268.9	464.0	781.7	1067.7	1142.3	1042.6	835.1	685.3	546.3
100°	139.4	184.7	266.1	438.0	743.6	1100.3	1329.2	1369.8	1275.7	1139.8	974.8
102.5°	155.2	196.8	269.8	415.7	687.8	1039.9	1338.4	1478.6	1475.5	1396.3	1291.7
105°	181.2	217.3	280.0	399.7	619.3	934.1	1267.6	1510.4	1626.6	1648.7	1618.5
107.5°	210.5	244.0	299.1	398.5	575.6	840.7	1143.5	1418.8	1607.5	1709.3	1750.7
110°	230.0	262.6	314.9	403.2	558.8	787.7	1065.4	1331.5	1545.3	1691.7	1773.0



TEST NUMBER: P332038

CATALOG NUMBER: S123DIP-S1000D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	250.5	282.1	330.7	412.5	549.6	752.4	997.6	1245.0	1463.5	1627.5	1732.1
115°	281.2	312.5	356.7	427.6	546.1	714.5	915.5	1130.5	1332.6	1503.4	1630.1
117.5°	311.6	340.7	384.3	447.5	548.2	692.2	866.0	1047.5	1222.0	1375.4	1503.9
120°	331.1	360.2	402.0	462.4	551.9	682.0	840.0	1003.8	1160.7	1300.1	1417.5
122.5°	348.8	379.7	420.6	476.4	558.4	675.5	818.6	969.4	1111.4	1240.6	1349.6
125°	375.3	406.6	447.3	498.4	568.1	666.9	791.2	923.7	1050.3	1161.8	1254.8
127.5°	399.9	431.3	470.5	516.6	579.3	662.7	767.1	883.7	996.6	1097.2	1181.8
130°	414.8	446.1	484.5	528.6	586.7	659.9	754.0	858.6	963.2	1057.3	1136.3
132.5°	428.7	459.2	496.6	539.8	592.3	659.0	742.0	835.4	931.6	1019.2	1094.5
135°	447.3	478.7	514.7	554.2	600.7	657.6	726.2	804.0	886.5	962.0	1028.2
137.5°	463.6	492.6	527.2	564.9	606.3	655.0	712.4	775.4	843.0	908.1	965.5
140°	472.9	501.9	535.6	570.5	610.0	654.1	704.1	758.7	817.9	873.7	923.7
142.5°	482.2	509.4	542.1	576.0	612.8	652.3	696.6	742.9	793.8	842.1	885.6
145°	493.8	520.5	550.7	582.1	614.6	649.5	686.7	723.8	762.2	799.4	833.0
147.5°	507.3	530.0	557.7	585.8	614.6	645.1	676.9	708.3	738.7	768.7	792.6
150°	514.7	535.6	562.3	586.7	614.6	641.3	670.4	697.1	723.8	748.2	770.3
152.5°	522.1	542.1	565.1	588.6	611.8	636.7	663.0	686.9	709.9	731.5	749.9
155°	534.4	550.7	570.5	589.1	608.8	628.6	651.8	671.5	690.1	707.6	721.5
157.5°	545.1	557.7	573.5	590.2	604.9	621.4	639.2	655.3	670.9	684.3	695.2
160°	550.7	562.3	576.3	590.2	603.0	615.8	630.9	646.0	658.8	670.4	678.5
162.5°	555.4	565.1	577.2	589.3	599.3	610.2	622.5	634.8	645.8	656.4	663.6
165°	561.2	569.3	578.6	586.7	593.7	601.8	611.1	620.4	627.4	635.5	641.3
167.5°	566.5	571.6	578.4	584.9	588.1	593.5	600.2	607.9	613.2	617.9	622.1
170°	569.3	571.6	577.4	582.1	584.4	587.9	593.7	599.5	603.0	607.6	610.0
172.5°	571.2	572.6	577.4	581.2	581.6	583.2	587.2	592.1	594.6	598.4	599.7
175°	572.8	574.0	576.3	578.6	577.4	577.4	579.8	582.1	583.2	585.6	585.6
177.5°	574.0	574.0	574.9	576.7	574.9	574.0	574.9	575.8	576.7	577.7	577.7
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0



TEST NUMBER: P332038

CATALOG NUMBER: S123DIP-S1000D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1343.0	1342.5	1346.3	1343.6	1346.3	1342.5	1343.0	1346.8	1347.9	1348.5	1348.5
5°	1250.1	1252.1	1245.3	1245.3	1245.3	1252.1	1250.1	1254.1	1257.5	1260.3	1264.4
7.5°	1167.3	1164.3	1164.6	1160.9	1164.6	1164.3	1167.3	1170.6	1174.9	1180.9	1186.5
10°	1116.7	1112.6	1111.2	1111.9	1111.2	1112.6	1116.7	1124.9	1127.6	1133.0	1139.1
12.5°	1074.8	1074.0	1065.0	1065.1	1065.0	1074.0	1074.8	1076.9	1082.9	1094.4	1101.6
15°	1025.5	1012.6	1011.2	1015.3	1011.2	1012.6	1025.5	1025.5	1028.2	1037.1	1041.2
17.5°	976.1	969.3	969.7	967.7	969.7	969.3	976.1	977.2	979.4	986.6	992.0
20°	950.0	945.9	945.2	940.4	945.2	945.9	950.0	950.0	952.7	956.1	961.5
22.5°	926.0	924.7	925.1	919.8	925.1	924.7	926.0	927.6	930.4	932.7	936.5
25°	896.2	899.6	896.9	896.9	896.9	899.6	896.2	896.9	897.6	901.0	903.7
27.5°	876.1	875.9	874.6	874.6	874.6	875.9	876.1	874.4	873.6	872.4	871.8
30°	860.8	860.1	861.5	861.5	861.5	860.1	860.8	858.1	856.7	856.1	853.3
32.5°	845.6	846.5	846.8	847.3	846.8	846.5	845.6	842.3	839.9	838.1	835.9
35°	822.0	822.7	824.8	823.4	824.8	822.7	822.0	818.0	815.2	811.1	807.7
37.5°	790.2	793.3	792.6	793.7	792.6	793.3	790.2	789.0	786.2	783.1	779.2
40°	766.2	768.3	767.6	767.6	767.6	768.3	766.2	765.6	762.8	760.8	757.4
42.5°	741.7	743.2	741.5	740.4	741.5	743.2	741.7	740.5	738.9	735.2	731.3
45°	701.6	700.2	702.3	699.5	702.3	700.2	701.6	698.9	698.2	695.5	692.1
47.5°	656.7	658.0	658.6	660.6	658.6	658.0	656.7	656.9	653.1	651.5	650.4
50°	626.7	630.8	630.8	630.1	630.8	630.8	626.7	625.4	622.6	619.9	619.9
52.5°	597.3	599.2	602.0	601.8	602.0	599.2	597.3	594.9	592.2	588.4	587.3
55°	551.9	553.2	554.6	555.3	554.6	553.2	551.9	546.4	544.4	542.4	538.9
57.5°	504.8	504.2	507.5	508.5	507.5	504.2	504.8	499.9	496.8	490.5	489.7
60°	471.6	471.6	477.0	479.1	477.0	471.6	471.6	466.1	461.4	457.3	455.9
62.5°	436.2	438.4	443.8	441.0	443.8	438.4	436.2	430.2	426.5	421.4	417.8
65°	384.5	389.9	389.2	392.0	389.2	389.9	384.5	381.1	373.6	368.8	364.7
67.5°	330.4	333.8	338.7	339.2	338.7	333.8	330.4	325.0	320.1	315.1	310.2
70°	294.0	297.4	300.1	302.1	300.1	297.4	294.0	288.5	283.1	279.7	274.2
72.5°	258.6	260.4	266.9	264.0	266.9	260.4	258.6	252.1	247.7	244.8	238.9
75°	202.8	207.5	211.6	209.6	211.6	207.5	202.8	198.0	194.6	190.5	185.1
77.5°	150.0	154.7	156.6	154.9	156.6	154.7	150.0	146.9	145.1	137.1	136.5
80°	118.4	117.7	121.8	121.1	121.8	117.7	118.4	113.6	110.2	105.5	105.5
82.5°	86.8	86.2	88.1	88.5	88.1	86.2	86.8	84.2	79.8	77.7	76.1
85°	42.2	44.2	41.5	40.8	41.5	44.2	42.2	39.5	39.5	39.5	38.8
87.5°	16.3	16.5	16.2	15.4	16.2	16.5	16.3	16.5	18.3	16.4	16.2
90°	32.5	33.7	34.9	33.7	34.9	33.7	32.5	33.7	31.4	30.2	29.0
92.5°	60.4	56.9	58.1	56.0	58.1	56.9	60.4	62.5	68.5	77.6	97.8
95°	158.0	147.6	139.4	134.8	139.4	147.6	158.0	180.1	221.9	283.5	418.3
97.5°	460.6	408.3	376.9	366.9	376.9	408.3	460.6	546.3	685.3	835.1	1042.6
100°	857.4	772.6	727.3	728.5	727.3	772.6	857.4	974.8	1139.8	1275.7	1369.8
102.5°	1200.4	1133.3	1095.4	1068.7	1095.4	1133.3	1200.4	1291.7	1396.3	1475.5	1478.6
105°	1565.0	1520.9	1483.7	1477.9	1483.7	1520.9	1565.0	1618.5	1648.7	1626.6	1510.4
107.5°	1751.6	1736.7	1724.2	1713.5	1724.2	1736.7	1751.6	1750.7	1709.3	1607.5	1418.8
110°	1805.5	1814.8	1812.5	1810.2	1812.5	1814.8	1805.5	1773.0	1691.7	1545.3	1331.5



TEST NUMBER: P332038

CATALOG NUMBER: S123DIP-S1000D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1791.6	1820.4	1829.2	1829.7	1829.2	1820.4	1791.6	1732.1	1627.5	1463.5	1245.0
115°	1717.2	1768.3	1791.6	1797.4	1791.6	1768.3	1717.2	1630.1	1503.4	1332.6	1130.5
117.5°	1594.8	1653.3	1686.8	1694.7	1686.8	1653.3	1594.8	1503.9	1375.4	1222.0	1047.5
120°	1509.2	1574.3	1602.2	1609.2	1602.2	1574.3	1509.2	1417.5	1300.1	1160.7	1003.8
122.5°	1431.2	1489.7	1520.4	1529.2	1520.4	1489.7	1431.2	1349.6	1240.6	1111.4	969.4
125°	1329.2	1380.3	1409.3	1417.5	1409.3	1380.3	1329.2	1254.8	1161.8	1050.3	923.7
127.5°	1248.1	1291.7	1318.0	1325.4	1318.0	1291.7	1248.1	1181.8	1097.2	996.6	883.7
130°	1197.9	1239.7	1264.1	1273.4	1264.1	1239.7	1197.9	1136.3	1057.3	963.2	858.6
132.5°	1152.3	1194.1	1215.8	1222.3	1215.8	1194.1	1152.3	1094.5	1019.2	931.6	835.4
135°	1085.2	1120.0	1140.9	1149.1	1140.9	1120.0	1085.2	1028.2	962.0	886.5	804.0
137.5°	1013.4	1048.7	1066.3	1071.7	1066.3	1048.7	1013.4	965.5	908.1	843.0	775.4
140°	967.8	1000.4	1018.9	1017.8	1018.9	1000.4	967.8	923.7	873.7	817.9	758.7
142.5°	923.2	952.0	968.7	967.6	968.7	952.0	923.2	885.6	842.1	793.8	742.9
145°	862.1	886.5	895.8	898.1	895.8	886.5	862.1	833.0	799.4	762.2	723.8
147.5°	814.7	831.2	840.0	840.9	840.0	831.2	814.7	792.6	768.7	738.7	708.3
150°	787.7	800.5	807.5	807.5	807.5	800.5	787.7	770.3	748.2	723.8	697.1
152.5°	763.6	775.4	779.6	779.6	779.6	775.4	763.6	749.9	731.5	709.9	686.9
155°	732.0	741.3	743.6	744.7	743.6	741.3	732.0	721.5	707.6	690.1	671.5
157.5°	704.3	711.3	713.1	712.9	713.1	711.3	704.3	695.2	684.3	670.9	655.3
160°	686.7	693.6	693.6	692.5	693.6	693.6	686.7	678.5	670.4	658.8	646.0
162.5°	669.0	675.0	675.0	673.9	675.0	675.0	669.0	663.6	656.4	645.8	634.8
165°	646.0	650.6	649.5	649.5	649.5	650.6	646.0	641.3	635.5	627.4	620.4
167.5°	624.1	627.4	626.2	626.2	626.2	627.4	624.1	622.1	617.9	613.2	607.9
170°	611.1	613.5	612.3	612.3	612.3	613.5	611.1	610.0	607.6	603.0	599.5
172.5°	600.0	602.3	600.2	599.3	600.2	602.3	600.0	599.7	598.4	594.6	592.1
175°	585.6	586.7	585.6	584.4	585.6	586.7	585.6	585.6	585.6	583.2	582.1
177.5°	576.7	577.7	575.8	575.8	575.8	577.7	576.7	577.7	577.7	576.7	575.8
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0



TEST NUMBER: P332038

CATALOG NUMBER: S123DIP-S1000D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1346.8	1346.8	1357.2	1363.7	1371.9	1377.3	1381.1	1384.9	1391.5	1400.2	1410.0
5°	1269.8	1272.5	1287.5	1302.5	1316.8	1329.0	1339.2	1351.5	1366.4	1384.8	1405.2
7.5°	1195.2	1205.7	1220.8	1239.0	1259.0	1276.9	1295.0	1315.1	1336.2	1363.3	1391.9
10°	1147.3	1158.9	1177.2	1200.4	1221.5	1242.6	1265.0	1286.8	1313.3	1345.3	1382.1
12.5°	1105.4	1116.4	1135.3	1160.6	1180.7	1203.9	1229.6	1258.0	1287.8	1326.3	1367.9
15°	1047.3	1060.2	1083.3	1095.6	1126.2	1154.1	1177.9	1218.8	1256.9	1296.3	1344.7
17.5°	999.6	1006.9	1025.6	1048.4	1071.2	1102.5	1133.7	1167.7	1205.7	1254.0	1314.4
20°	967.0	973.1	993.5	1017.3	1041.8	1070.4	1098.3	1132.3	1175.2	1226.2	1291.6
22.5°	942.5	949.1	962.5	987.9	1010.8	1034.5	1062.4	1102.9	1148.5	1198.5	1269.3
25°	907.1	911.2	920.0	940.4	960.9	987.4	1011.9	1050.0	1097.0	1155.5	1226.2
27.5°	873.5	877.4	884.8	899.5	918.5	940.0	966.7	999.1	1046.7	1110.3	1185.4
30°	853.3	854.0	860.8	874.4	890.8	908.5	933.0	969.7	1014.6	1079.3	1158.2
32.5°	835.9	833.3	838.0	848.3	864.1	881.8	901.9	938.1	981.4	1045.0	1126.1
35°	806.4	805.0	803.0	811.8	825.4	839.0	856.7	884.0	933.0	992.2	1077.2
37.5°	776.3	773.0	769.4	773.4	784.1	798.2	813.6	837.8	880.0	945.2	1026.6
40°	754.0	751.3	749.2	747.9	757.4	771.0	782.6	805.7	845.2	907.1	987.4
42.5°	729.5	727.9	725.3	723.4	731.3	741.6	753.7	774.1	813.6	871.7	947.7
45°	690.0	688.7	687.3	685.9	690.7	700.2	709.8	724.7	758.7	815.2	884.0
47.5°	646.1	644.3	644.8	642.7	647.3	653.7	660.3	676.4	709.1	754.7	804.9
50°	614.5	613.8	613.8	613.8	615.2	622.6	628.8	641.0	671.0	716.6	752.6
52.5°	584.5	581.7	581.7	582.8	585.2	590.0	593.9	607.3	633.4	670.8	703.6
55°	537.6	532.1	530.8	532.1	534.2	538.3	542.4	553.2	575.7	603.6	622.6
57.5°	485.6	482.6	480.8	481.1	482.2	485.5	488.6	500.4	518.1	532.7	544.9
60°	449.1	450.5	444.4	445.7	445.7	448.4	453.2	460.7	475.7	485.9	498.1
62.5°	414.8	412.9	411.2	409.2	409.2	410.3	416.7	422.6	435.4	440.7	450.2
65°	361.3	361.3	357.3	358.6	359.3	354.5	357.9	364.7	372.9	375.0	383.8
67.5°	307.2	305.3	303.0	300.9	300.9	300.5	302.3	305.7	311.8	312.5	319.3
70°	270.2	268.8	268.1	266.1	263.4	266.8	264.7	268.1	271.5	272.2	276.3
72.5°	234.2	232.9	231.6	229.6	228.5	228.1	228.2	232.2	234.5	233.5	238.2
75°	183.1	181.7	180.3	176.9	176.9	174.9	175.6	178.3	181.0	179.0	183.1
77.5°	134.5	130.2	130.0	130.9	128.6	129.0	128.2	127.8	129.0	129.2	132.8
80°	103.4	98.7	100.0	99.4	98.7	98.0	96.6	97.3	98.0	98.7	100.7
82.5°	74.6	74.2	72.8	72.7	72.0	70.2	69.4	70.6	71.3	70.9	72.4
85°	38.1	36.1	37.4	36.7	37.4	36.7	34.7	34.7	36.1	35.4	36.7
87.5°	17.0	17.2	16.0	15.8	14.6	14.5	13.4	13.5	13.4	12.9	13.5
90°	27.9	29.0	25.6	22.1	18.6	15.1	12.8	10.5	7.0	4.6	2.3
92.5°	134.8	178.7	196.6	147.6	97.6	67.2	50.0	40.2	31.1	21.4	14.4
95°	558.8	689.0	613.5	422.9	249.8	151.0	105.7	75.5	55.8	43.0	39.5
97.5°	1142.3	1067.7	781.7	464.0	268.9	174.5	125.5	95.7	78.5	68.5	67.4
100°	1329.2	1100.3	743.6	438.0	266.1	184.7	139.4	111.5	95.3	87.1	86.0
102.5°	1338.4	1039.9	687.8	415.7	269.8	196.8	155.2	130.1	114.8	107.6	105.5
105°	1267.6	934.1	619.3	399.7	280.0	217.3	181.2	159.2	145.2	138.3	134.8
107.5°	1143.5	840.7	575.6	398.5	299.1	244.0	210.5	189.8	176.1	169.4	165.9
110°	1065.4	787.7	558.8	403.2	314.9	262.6	230.0	210.3	197.5	191.7	188.2



TEST NUMBER: P332038

CATALOG NUMBER: S123DIP-S1000D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	997.6	752.4	549.6	412.5	330.7	282.1	250.5	230.7	218.0	212.2	208.7
115°	915.5	714.5	546.1	427.6	356.7	312.5	281.2	261.4	249.8	242.8	238.2
117.5°	866.0	692.2	548.2	447.5	384.3	340.7	311.6	289.5	278.8	273.0	267.7
120°	840.0	682.0	551.9	462.4	402.0	360.2	331.1	309.1	297.4	291.6	288.1
122.5°	818.6	675.5	558.4	476.4	420.6	379.7	348.8	327.6	315.1	309.3	305.8
125°	791.2	666.9	568.1	498.4	447.3	406.6	375.3	353.2	340.4	333.5	331.1
127.5°	767.1	662.7	579.3	516.6	470.5	431.3	399.9	375.5	362.5	353.9	350.4
130°	754.0	659.9	586.7	528.6	484.5	446.1	414.8	390.4	376.4	366.0	362.5
132.5°	742.0	659.0	592.3	539.8	496.6	459.2	428.7	404.3	387.6	376.2	371.8
135°	726.2	657.6	600.7	554.2	514.7	478.7	447.3	422.9	405.5	392.7	388.1
137.5°	712.4	655.0	606.3	564.9	527.2	492.6	463.6	439.4	420.8	408.3	403.4
140°	704.1	654.1	610.0	570.5	535.6	501.9	472.9	449.6	431.0	419.4	413.6
142.5°	696.6	652.3	612.8	576.0	542.1	509.4	482.2	458.9	442.2	429.7	424.8
145°	686.7	649.5	614.6	582.1	550.7	520.5	493.8	474.0	456.6	446.1	442.7
147.5°	676.9	645.1	614.6	585.8	557.7	530.0	507.3	488.2	473.1	462.9	460.8
150°	670.4	641.3	614.6	586.7	562.3	535.6	514.7	498.4	483.3	474.0	472.9
152.5°	663.0	636.7	611.8	588.6	565.1	542.1	522.1	507.7	494.5	485.2	485.0
155°	651.8	628.6	608.8	589.1	570.5	550.7	534.4	521.7	510.1	503.1	503.1
157.5°	639.2	621.4	604.9	590.2	573.5	557.7	545.1	534.2	524.0	518.4	517.5
160°	630.9	615.8	603.0	590.2	576.3	562.3	550.7	542.6	533.3	528.6	528.6
162.5°	622.5	610.2	599.3	589.3	577.2	565.1	555.4	548.2	540.7	537.0	537.0
165°	611.1	601.8	593.7	586.7	578.6	569.3	561.2	556.5	550.7	548.4	549.6
167.5°	600.2	593.5	588.1	584.9	578.4	571.6	566.5	563.3	558.8	557.7	559.1
170°	593.7	587.9	584.4	582.1	577.4	571.6	569.3	567.0	563.5	562.3	564.7
172.5°	587.2	583.2	581.6	581.2	577.4	572.6	571.2	569.8	567.2	567.0	568.4
175°	579.8	577.4	577.4	578.6	576.3	574.0	572.8	572.8	570.5	571.6	572.8
177.5°	574.9	574.0	574.9	576.7	574.9	574.0	574.0	574.0	573.0	574.0	574.9
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0



TEST NUMBER: P332038

CATALOG NUMBER: S123DIP-S1000D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1413.2	1416.0	1425.2	1431.8	1439.4	1443.7	1448.1	1451.4	1455.7	1456.8	1472.6
5°	1419.5	1433.1	1456.9	1474.6	1496.4	1520.2	1536.5	1544.0	1563.8	1580.1	1612.8
7.5°	1417.7	1446.7	1482.7	1519.9	1560.0	1597.0	1629.1	1667.2	1694.3	1735.0	1775.1
10°	1416.1	1454.9	1501.2	1548.8	1604.6	1656.3	1702.6	1754.3	1797.2	1853.7	1902.0
12.5°	1411.2	1458.2	1522.4	1578.7	1646.5	1717.8	1786.4	1852.8	1890.8	1984.9	2029.4
15°	1399.1	1454.9	1535.2	1620.9	1714.2	1798.5	1885.6	1955.1	2067.3	2149.7	2202.1
17.5°	1376.0	1454.1	1549.3	1652.8	1766.1	1877.3	1976.0	2081.4	2200.4	2300.1	2406.2
20°	1365.1	1450.8	1557.0	1671.3	1789.0	1914.9	2027.2	2153.8	2283.7	2381.7	2517.8
22.5°	1344.9	1442.1	1556.4	1683.8	1809.7	1939.9	2071.3	2198.9	2349.1	2484.1	2613.6
25°	1312.0	1420.9	1539.3	1681.5	1829.2	1959.8	2117.0	2286.5	2443.0	2616.5	2745.8
27.5°	1277.4	1393.6	1512.3	1644.6	1803.4	1958.5	2156.2	2347.7	2539.0	2688.9	2784.6
30°	1250.7	1363.7	1486.2	1619.6	1776.8	1961.2	2182.3	2391.2	2577.7	2706.3	2760.1
32.5°	1221.9	1336.5	1444.8	1584.7	1752.3	1959.5	2198.7	2416.8	2579.9	2665.5	2655.0
35°	1176.6	1272.5	1378.0	1512.7	1710.1	1947.6	2208.2	2419.1	2519.2	2500.8	2362.0
37.5°	1111.2	1191.9	1295.8	1443.3	1661.1	1922.4	2189.1	2347.4	2340.9	2191.3	1990.2
40°	1070.4	1139.1	1239.2	1394.3	1623.0	1906.1	2159.2	2262.0	2174.9	1965.9	1725.0
42.5°	1017.1	1080.3	1180.4	1339.9	1581.1	1872.8	2102.0	2131.8	1961.4	1721.0	1500.2
45°	934.3	990.1	1093.5	1258.2	1518.2	1800.6	1962.5	1889.7	1660.4	1412.0	1243.9
47.5°	845.4	903.4	1002.9	1172.1	1427.3	1691.8	1769.0	1614.1	1378.7	1177.2	1022.9
50°	789.4	845.2	942.5	1113.3	1365.7	1602.6	1634.5	1434.5	1218.1	1041.2	914.6
52.5°	732.8	785.3	881.0	1052.3	1293.9	1499.1	1479.4	1275.5	1076.5	925.7	826.4
55°	648.5	698.2	789.4	950.0	1169.8	1332.4	1261.0	1066.3	901.7	784.6	709.1
57.5°	573.1	620.7	699.4	844.5	1035.6	1147.3	1056.4	892.4	761.5	671.4	615.0
60°	521.9	564.1	639.0	773.7	939.8	1024.8	935.0	790.1	679.8	607.7	557.3
62.5°	473.5	510.2	579.6	701.9	846.1	917.6	826.7	704.0	610.1	546.2	503.4
65°	400.1	433.5	494.7	590.0	708.4	756.0	677.8	578.4	505.6	458.0	429.4
67.5°	333.2	361.5	414.4	489.4	576.5	611.2	551.6	474.7	419.9	381.6	358.9
70°	288.5	313.0	354.5	419.2	498.1	524.7	468.9	405.6	365.4	334.8	313.7
72.5°	251.0	268.9	306.6	356.6	422.4	443.5	404.6	349.0	311.5	288.5	271.8
75°	191.2	206.2	230.7	270.8	316.4	328.7	299.4	264.7	239.5	223.2	210.3
77.5°	137.9	148.9	166.6	191.4	222.9	234.0	215.4	192.3	173.9	162.9	155.7
80°	104.1	113.0	127.9	148.3	167.4	173.5	162.6	144.9	132.0	125.9	119.8
82.5°	76.9	81.9	90.9	104.8	117.9	125.1	115.8	105.2	98.3	92.7	90.4
85°	38.8	41.5	45.6	51.0	59.2	61.9	58.5	55.8	51.7	48.3	48.3
87.5°	15.1	15.5	17.9	19.4	22.1	24.4	24.6	24.2	24.3	23.5	23.2
90°	4.6	7.0	10.5	12.8	15.1	18.6	22.1	25.6	29.0	27.9	29.0
92.5°	21.4	31.1	40.2	50.0	67.2	97.6	147.6	196.6	178.7	134.8	97.8
95°	43.0	55.8	75.5	105.7	151.0	249.8	422.9	613.5	689.0	558.8	418.3
97.5°	68.5	78.5	95.7	125.5	174.5	268.9	464.0	781.7	1067.7	1142.3	1042.6
100°	87.1	95.3	111.5	139.4	184.7	266.1	438.0	743.6	1100.3	1329.2	1369.8
102.5°	107.6	114.8	130.1	155.2	196.8	269.8	415.7	687.8	1039.9	1338.4	1478.6
105°	138.3	145.2	159.2	181.2	217.3	280.0	399.7	619.3	934.1	1267.6	1510.4
107.5°	169.4	176.1	189.8	210.5	244.0	299.1	398.5	575.6	840.7	1143.5	1418.8
110°	191.7	197.5	210.3	230.0	262.6	314.9	403.2	558.8	787.7	1065.4	1331.5



TEST NUMBER: P332038

CATALOG NUMBER: S123DIP-S1000D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	212.2	218.0	230.7	250.5	282.1	330.7	412.5	549.6	752.4	997.6	1245.0
115°	242.8	249.8	261.4	281.2	312.5	356.7	427.6	546.1	714.5	915.5	1130.5
117.5°	273.0	278.8	289.5	311.6	340.7	384.3	447.5	548.2	692.2	866.0	1047.5
120°	291.6	297.4	309.1	331.1	360.2	402.0	462.4	551.9	682.0	840.0	1003.8
122.5°	309.3	315.1	327.6	348.8	379.7	420.6	476.4	558.4	675.5	818.6	969.4
125°	333.5	340.4	353.2	375.3	406.6	447.3	498.4	568.1	666.9	791.2	923.7
127.5°	353.9	362.5	375.5	399.9	431.3	470.5	516.6	579.3	662.7	767.1	883.7
130°	366.0	376.4	390.4	414.8	446.1	484.5	528.6	586.7	659.9	754.0	858.6
132.5°	376.2	387.6	404.3	428.7	459.2	496.6	539.8	592.3	659.0	742.0	835.4
135°	392.7	405.5	422.9	447.3	478.7	514.7	554.2	600.7	657.6	726.2	804.0
137.5°	408.3	420.8	439.4	463.6	492.6	527.2	564.9	606.3	655.0	712.4	775.4
140°	419.4	431.0	449.6	472.9	501.9	535.6	570.5	610.0	654.1	704.1	758.7
142.5°	429.7	442.2	458.9	482.2	509.4	542.1	576.0	612.8	652.3	696.6	742.9
145°	446.1	456.6	474.0	493.8	520.5	550.7	582.1	614.6	649.5	686.7	723.8
147.5°	462.9	473.1	488.2	507.3	530.0	557.7	585.8	614.6	645.1	676.9	708.3
150°	474.0	483.3	498.4	514.7	535.6	562.3	586.7	614.6	641.3	670.4	697.1
152.5°	485.2	494.5	507.7	522.1	542.1	565.1	588.6	611.8	636.7	663.0	686.9
155°	503.1	510.1	521.7	534.4	550.7	570.5	589.1	608.8	628.6	651.8	671.5
157.5°	518.4	524.0	534.2	545.1	557.7	573.5	590.2	604.9	621.4	639.2	655.3
160°	528.6	533.3	542.6	550.7	562.3	576.3	590.2	603.0	615.8	630.9	646.0
162.5°	537.0	540.7	548.2	555.4	565.1	577.2	589.3	599.3	610.2	622.5	634.8
165°	548.4	550.7	556.5	561.2	569.3	578.6	586.7	593.7	601.8	611.1	620.4
167.5°	557.7	558.8	563.3	566.5	571.6	578.4	584.9	588.1	593.5	600.2	607.9
170°	562.3	563.5	567.0	569.3	571.6	577.4	582.1	584.4	587.9	593.7	599.5
172.5°	567.0	567.2	569.8	571.2	572.6	577.4	581.2	581.6	583.2	587.2	592.1
175°	571.6	570.5	572.8	572.8	574.0	576.3	578.6	577.4	577.4	579.8	582.1
177.5°	574.0	573.0	574.0	574.0	574.0	574.9	576.7	574.9	574.0	574.9	575.8
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0



TEST NUMBER: P332038

CATALOG NUMBER: S123DIP-S1000D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1478.0	1478.6	1484.6	1488.9	1486.7	1489.5	1490.5
5°	1614.8	1639.3	1652.2	1661.8	1662.4	1663.1	1668.6
7.5°	1808.7	1835.0	1854.2	1883.3	1892.0	1902.0	1899.1
10°	1950.3	1989.1	2022.4	2040.1	2059.2	2087.1	2064.6
12.5°	2082.6	2151.3	2202.1	2229.6	2247.5	2253.1	2242.1
15°	2300.7	2390.6	2438.9	2437.5	2498.8	2525.3	2483.8
17.5°	2500.8	2583.7	2650.1	2684.1	2735.2	2746.5	2741.3
20°	2623.3	2713.8	2765.5	2824.0	2850.6	2874.4	2878.5
22.5°	2728.9	2810.2	2865.7	2914.4	2936.6	2947.9	2954.7
25°	2837.6	2901.6	2935.0	2952.0	2958.1	2956.7	2947.9
27.5°	2830.2	2835.1	2798.3	2762.3	2730.0	2693.7	2681.1
30°	2756.7	2699.5	2597.4	2539.6	2454.5	2387.2	2414.4
32.5°	2563.4	2449.6	2335.0	2208.6	2103.9	2074.1	2044.2
35°	2187.8	1987.7	1870.7	1734.6	1680.1	1625.7	1588.3
37.5°	1770.0	1615.2	1476.4	1387.4	1332.8	1298.4	1279.9
40°	1530.4	1390.9	1276.6	1204.5	1163.0	1124.2	1118.7
42.5°	1339.3	1209.6	1123.6	1066.2	1026.3	1009.8	997.9
45°	1097.0	1006.4	948.6	907.8	881.2	871.0	857.4
47.5°	928.5	864.5	821.1	793.3	773.3	765.7	764.6
50°	834.3	781.2	749.2	727.4	711.8	709.1	698.2
52.5°	763.5	717.5	692.6	673.6	662.3	654.6	651.4
55°	662.8	632.2	609.7	598.8	590.0	582.5	582.5
57.5°	579.9	554.3	539.5	530.2	527.5	522.2	518.8
60°	528.7	507.0	495.4	487.2	481.8	482.5	476.3
62.5°	478.7	464.5	453.5	445.3	438.8	438.9	439.3
65°	407.6	396.7	388.6	385.8	381.8	377.0	378.4
67.5°	345.4	335.2	328.8	324.2	322.8	320.2	324.2
70°	300.8	293.3	288.5	284.4	283.1	283.8	287.2
72.5°	259.9	254.6	251.5	249.6	246.6	246.7	249.1
75°	204.1	200.1	197.3	195.3	194.6	194.6	194.6
77.5°	150.0	149.0	147.8	144.8	144.9	145.8	145.9
80°	118.4	116.4	115.7	114.3	112.3	110.9	114.3
82.5°	88.5	86.4	85.7	85.5	82.3	82.1	84.9
85°	47.6	45.6	46.3	45.6	45.6	44.9	44.9
87.5°	22.9	22.6	22.5	22.8	22.5	22.2	23.1
90°	30.2	31.4	33.7	32.5	33.7	34.9	33.7
92.5°	77.6	68.5	62.5	60.4	56.9	58.1	56.0
95°	283.5	221.9	180.1	158.0	147.6	139.4	134.8
97.5°	835.1	685.3	546.3	460.6	408.3	376.9	366.9
100°	1275.7	1139.8	974.8	857.4	772.6	727.3	728.5
102.5°	1475.5	1396.3	1291.7	1200.4	1133.3	1095.4	1068.7
105°	1626.6	1648.7	1618.5	1565.0	1520.9	1483.7	1477.9
107.5°	1607.5	1709.3	1750.7	1751.6	1736.7	1724.2	1713.5
110°	1545.3	1691.7	1773.0	1805.5	1814.8	1812.5	1810.2



TEST NUMBER: P332038

CATALOG NUMBER: S123DIP-S1000D1195U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1463.5	1627.5	1732.1	1791.6	1820.4	1829.2	1829.7
115°	1332.6	1503.4	1630.1	1717.2	1768.3	1791.6	1797.4
117.5°	1222.0	1375.4	1503.9	1594.8	1653.3	1686.8	1694.7
120°	1160.7	1300.1	1417.5	1509.2	1574.3	1602.2	1609.2
122.5°	1111.4	1240.6	1349.6	1431.2	1489.7	1520.4	1529.2
125°	1050.3	1161.8	1254.8	1329.2	1380.3	1409.3	1417.5
127.5°	996.6	1097.2	1181.8	1248.1	1291.7	1318.0	1325.4
130°	963.2	1057.3	1136.3	1197.9	1239.7	1264.1	1273.4
132.5°	931.6	1019.2	1094.5	1152.3	1194.1	1215.8	1222.3
135°	886.5	962.0	1028.2	1085.2	1120.0	1140.9	1149.1
137.5°	843.0	908.1	965.5	1013.4	1048.7	1066.3	1071.7
140°	817.9	873.7	923.7	967.8	1000.4	1018.9	1017.8
142.5°	793.8	842.1	885.6	923.2	952.0	968.7	967.6
145°	762.2	799.4	833.0	862.1	886.5	895.8	898.1
147.5°	738.7	768.7	792.6	814.7	831.2	840.0	840.9
150°	723.8	748.2	770.3	787.7	800.5	807.5	807.5
152.5°	709.9	731.5	749.9	763.6	775.4	779.6	779.6
155°	690.1	707.6	721.5	732.0	741.3	743.6	744.7
157.5°	670.9	684.3	695.2	704.3	711.3	713.1	712.9
160°	658.8	670.4	678.5	686.7	693.6	693.6	692.5
162.5°	645.8	656.4	663.6	669.0	675.0	675.0	673.9
165°	627.4	635.5	641.3	646.0	650.6	649.5	649.5
167.5°	613.2	617.9	622.1	624.1	627.4	626.2	626.2
170°	603.0	607.6	610.0	611.1	613.5	612.3	612.3
172.5°	594.6	598.4	599.7	600.0	602.3	600.2	599.3
175°	583.2	585.6	585.6	585.6	586.7	585.6	584.4
177.5°	576.7	577.7	577.7	576.7	577.7	575.8	575.8
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0

(END OF REPORT)