

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332042

Luminaire Tested: **S123DIP-S1000D1195U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332042
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D1195U835-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8892.0 lumens
Efficiency: N/A
Efficacy: 136.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332042

CATALOG NUMBER: S123DIP-S1000D1195U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332042

CATALOG NUMBER: S123DIP-S1000D1195U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53	46																				
1	97	93	89	85	89	85	82	79	71	69	67	58	57	55	47	45	44	39																				
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	41	39	37	33																				
3	80	71	64	58	74	65	59	54	55	50	46	45	42	39	36	34	32	28																				
4	74	63	55	49	67	58	51	46	49	44	39	40	36	33	32	30	27	24																				
5	67	56	48	42	62	52	44	39	44	38	34	36	32	29	29	26	24	20																				
6	62	50	42	36	57	46	39	34	39	34	30	33	28	25	26	23	21	18																				
7	57	45	37	32	53	42	35	30	36	30	26	30	25	22	24	21	19	16																				
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17	14																				
9	50	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15	13																				
10	46	34	27	22	43	32	25	21	27	22	19	23	19	16	19	16	14	12																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17038	17038	17038
5°	17117	16883	17001
10°	17004	16736	16840
15°	16805	16547	16577
20°	16573	16276	16292
25°	16262	15954	15922
30°	15918	15597	15478
35°	15559	15219	15023
40°	15185	14802	14573
45°	14772	14420	14067
50°	14359	13949	13561
55°	13818	13461	13052
60°	13272	12893	12482
65°	12791	12271	11889
70°	12079	11566	11050
75°	11038	10643	10189
80°	9955	9534	9447
85°	8744	8410	8065



TEST NUMBER: P332042

CATALOG NUMBER: S123DIP-S1000D1195U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.1	1.7
10°-20°	421.0	4.7
20°-30°	621.9	7.0
30°-40°	726.5	8.2
40°-50°	730.4	8.2
50°-60°	641.5	7.2
60°-70°	478.0	5.4
70°-80°	272.3	3.1
80°-90°	82.5	0.9
90°-100°	56.9	0.6
100°-110°	271.0	3.0
110°-120°	650.9	7.3
120°-130°	828.8	9.3
130°-140°	885.6	10.0
140°-150°	828.1	9.3
150°-160°	668.0	7.5
160°-170°	431.1	4.8
170°-180°	148.6	1.7
0°-30°	1192.0	13.4
0°-40°	1918.5	21.6
0°-60°	3290.4	37.0
0°-90°	4123.2	46.4
90°-120°	978.7	11.0
90°-150°	3521.2	39.6
90°-180°	4769.0	53.6
0°-180°	8892.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1583	1583	1583	1583	1583	
5°	1584	1577	1562	1575	1573	150
15°	1508	1502	1485	1495	1488	425
25°	1369	1360	1343	1344	1341	630
35°	1184	1175	1158	1150	1143	740
45°	970	964	947	932	924	749
55°	736	734	717	703	696	659
65°	502	495	482	471	467	495
75°	265	260	256	249	245	284
85°	71	68	68	65	65	78
90°	1	13	28	32	35	7
95°	71	27	36	44	44	88
105°	346	352	254	60	51	367
115°	650	657	667	678	683	641
125°	916	925	929	932	934	817
135°	1140	1147	1151	1154	1151	877
145°	1315	1323	1326	1328	1328	823
155°	1449	1447	1448	1453	1446	667
165°	1528	1524	1523	1531	1524	431
175°	1564	1558	1559	1566	1558	149
180°	1564	1564	1564	1564	1564	



TEST NUMBER: P332042

CATALOG NUMBER: S123DIP-S1000D1195U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9
2.5°	1588.3	1587.4	1586.4	1585.4	1584.5	1582.6	1580.0	1577.3	1574.7	1572.0	1574.4
5°	1584.2	1582.7	1581.2	1579.7	1578.2	1575.8	1572.5	1569.1	1565.8	1562.5	1565.5
7.5°	1568.7	1567.2	1565.7	1564.2	1562.7	1560.2	1556.8	1553.3	1549.9	1546.4	1549.1
10°	1555.7	1554.2	1552.6	1551.1	1549.6	1546.9	1543.0	1539.0	1535.1	1531.2	1533.9
12.5°	1538.2	1537.0	1535.7	1534.4	1533.2	1530.7	1527.0	1523.3	1519.6	1515.9	1517.9
15°	1508.0	1506.8	1505.6	1504.4	1503.2	1500.6	1496.7	1492.8	1488.8	1484.9	1487.3
17.5°	1472.9	1471.3	1469.8	1468.2	1466.6	1463.9	1459.9	1456.0	1452.1	1448.1	1449.8
20°	1446.8	1445.0	1443.2	1441.3	1439.5	1436.6	1432.7	1428.8	1424.9	1420.9	1422.1
22.5°	1417.4	1415.6	1413.8	1411.9	1410.1	1407.3	1403.3	1399.4	1395.5	1391.5	1392.5
25°	1369.2	1367.4	1365.6	1363.8	1361.9	1359.1	1355.1	1351.2	1347.3	1343.3	1343.6
27.5°	1317.8	1316.0	1314.2	1312.5	1310.7	1307.7	1303.5	1299.3	1295.0	1290.8	1291.0
30°	1280.7	1279.2	1277.7	1276.2	1274.7	1271.8	1267.6	1263.3	1259.1	1254.9	1254.9
32.5°	1243.7	1241.7	1239.7	1237.7	1235.7	1233.1	1229.8	1226.6	1223.3	1220.0	1218.3
35°	1184.1	1182.3	1180.5	1178.7	1176.8	1174.0	1170.0	1166.1	1162.2	1158.2	1156.4
37.5°	1123.1	1120.8	1118.5	1116.2	1113.9	1110.8	1106.8	1102.8	1098.8	1094.8	1092.6
40°	1080.7	1078.8	1077.0	1075.2	1073.4	1070.4	1066.1	1061.9	1057.7	1053.4	1051.0
42.5°	1038.2	1036.1	1034.1	1032.0	1030.0	1026.8	1022.6	1018.4	1014.1	1009.9	1007.5
45°	970.4	969.2	968.0	966.8	965.6	963.0	959.1	955.1	951.2	947.3	943.7
47.5°	903.2	901.4	899.7	897.9	896.2	893.4	889.8	886.1	882.4	878.7	875.1
50°	857.5	855.9	854.4	852.9	851.4	848.7	844.7	840.8	836.9	833.0	829.6
52.5°	809.5	808.5	807.5	806.5	805.4	802.8	798.7	794.5	790.3	786.1	783.3
55°	736.3	736.0	735.7	735.4	735.1	733.0	729.1	725.1	721.2	717.3	713.9
57.5°	666.6	665.6	664.6	663.6	662.5	660.4	657.3	654.1	651.0	647.9	644.9
60°	616.5	616.2	615.9	615.6	615.3	613.4	609.7	606.1	602.5	598.9	596.1
62.5°	571.9	571.1	570.3	569.5	568.8	566.6	562.9	559.3	555.7	552.0	549.3
65°	502.2	500.7	499.2	497.7	496.2	493.9	490.9	487.9	484.8	481.8	479.4
67.5°	428.5	427.1	425.8	424.5	423.1	421.3	419.0	416.7	414.4	412.1	410.0
70°	383.8	382.0	380.2	378.4	376.6	374.7	372.9	371.1	369.3	367.5	365.4
72.5°	337.0	335.7	334.3	333.0	331.7	330.0	327.9	325.9	323.8	321.7	319.9
75°	265.4	264.2	263.0	261.8	260.6	259.5	258.6	257.7	256.8	255.9	254.4
77.5°	202.0	201.3	200.6	200.0	199.3	198.4	197.4	196.3	195.2	194.1	193.1
80°	160.6	159.7	158.8	157.9	157.0	156.2	155.6	155.0	154.4	153.8	153.5
82.5°	120.3	120.1	120.0	119.8	119.6	119.4	119.3	119.2	119.1	119.0	118.4
85°	70.8	70.2	69.6	69.0	68.4	68.1	68.1	68.1	68.1	68.1	67.4
87.5°	28.5	28.3	28.1	27.9	27.7	27.8	28.2	28.7	29.1	29.5	29.5
90°	1.2	3.7	6.3	8.9	11.5	14.5	17.8	21.2	24.5	27.9	28.9
92.5°	21.6	20.9	20.2	19.4	18.7	19.6	22.2	24.7	27.2	29.7	31.4
95°	70.9	60.3	49.7	39.1	28.5	24.7	27.5	30.3	33.2	36.0	37.8
97.5°	142.4	137.7	132.9	128.2	123.4	111.8	93.2	74.6	56.0	37.4	39.5
100°	196.3	201.5	206.7	211.8	217.0	199.4	159.2	118.9	78.6	38.3	40.4
102.5°	257.7	261.4	265.1	268.8	272.6	252.4	208.4	164.4	120.4	76.4	70.0
105°	346.2	349.1	351.9	354.7	357.6	347.4	324.1	300.9	277.7	254.4	208.7
107.5°	439.6	441.9	444.2	446.4	448.7	451.7	455.4	459.0	462.7	466.4	432.8
110°	501.9	504.0	506.0	508.1	510.2	512.6	515.5	518.3	521.1	524.0	515.5



TEST NUMBER: P332042

CATALOG NUMBER: S123DIP-S1000D1195U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	561.4	563.2	565.1	567.0	568.8	571.2	574.0	576.9	579.7	582.5	582.7
115°	649.5	651.0	652.5	654.1	655.6	657.6	659.9	662.2	664.6	666.9	669.5
117.5°	734.7	736.6	738.5	740.5	742.4	743.9	745.1	746.3	747.5	748.7	750.7
120°	787.7	790.0	792.4	794.7	797.0	798.6	799.3	800.1	800.9	801.6	803.7
122.5°	841.6	843.5	845.4	847.3	849.3	850.7	851.7	852.7	853.6	854.6	856.1
125°	915.5	917.6	919.6	921.7	923.8	925.3	926.3	927.4	928.4	929.4	930.0
127.5°	987.1	989.1	991.2	993.3	995.3	997.0	998.2	999.5	1000.7	1001.9	1002.8
130°	1031.7	1033.8	1035.8	1037.9	1039.9	1041.5	1042.5	1043.6	1044.6	1045.6	1046.7
132.5°	1074.4	1076.5	1078.6	1080.6	1082.7	1084.1	1085.0	1085.8	1086.6	1087.5	1088.5
135°	1139.7	1141.3	1142.8	1144.4	1145.9	1147.2	1148.3	1149.3	1150.3	1151.4	1152.1
137.5°	1195.5	1197.5	1199.4	1201.4	1203.4	1204.6	1205.2	1205.8	1206.3	1206.9	1208.1
140°	1232.7	1234.2	1235.8	1237.3	1238.9	1240.0	1240.8	1241.6	1242.4	1243.1	1244.2
142.5°	1267.1	1268.6	1270.2	1271.7	1273.3	1274.4	1275.2	1276.0	1276.8	1277.5	1278.4
145°	1315.2	1317.0	1318.8	1320.6	1322.4	1323.6	1324.1	1324.6	1325.1	1325.6	1326.1
147.5°	1360.5	1361.7	1362.9	1364.0	1365.2	1366.1	1366.6	1367.1	1367.6	1368.1	1368.7
150°	1388.4	1389.1	1389.9	1390.7	1391.5	1392.1	1392.6	1393.1	1393.7	1394.2	1394.7
152.5°	1413.5	1413.8	1414.2	1414.5	1414.9	1415.2	1415.5	1415.9	1416.2	1416.5	1417.4
155°	1448.8	1448.3	1447.7	1447.2	1446.7	1446.6	1446.8	1447.1	1447.4	1447.6	1448.9
157.5°	1476.2	1476.1	1476.1	1476.0	1476.0	1475.8	1475.6	1475.3	1475.1	1474.8	1476.4
160°	1492.9	1492.7	1492.4	1492.2	1491.9	1491.6	1491.4	1491.1	1490.9	1490.6	1492.2
162.5°	1508.7	1508.1	1507.4	1506.7	1506.0	1505.6	1505.3	1505.1	1504.8	1504.5	1506.3
165°	1527.8	1527.0	1526.2	1525.5	1524.7	1524.2	1523.9	1523.6	1523.4	1523.1	1525.2
167.5°	1542.7	1541.6	1540.6	1539.6	1538.5	1538.0	1538.0	1538.0	1538.0	1538.0	1540.1
170°	1551.0	1550.0	1549.0	1547.9	1546.9	1546.4	1546.4	1546.4	1546.4	1546.4	1548.4
172.5°	1556.6	1555.4	1554.1	1552.9	1551.6	1551.1	1551.3	1551.5	1551.7	1551.9	1554.0
175°	1563.8	1562.5	1561.2	1559.9	1558.6	1558.1	1558.4	1558.6	1558.9	1559.1	1561.0
177.5°	1565.7	1564.6	1563.6	1562.6	1561.5	1561.1	1561.3	1561.5	1561.7	1561.9	1563.6
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P332042

CATALOG NUMBER: S123DIP-S1000D1195U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9
2.5°	1576.8	1579.3	1581.7	1582.8	1582.5	1582.3	1582.0	1581.8
5°	1568.5	1571.5	1574.6	1575.8	1575.2	1574.6	1574.0	1573.4
7.5°	1551.9	1554.6	1557.3	1558.5	1558.1	1557.8	1557.4	1557.0
10°	1536.6	1539.3	1542.1	1543.1	1542.5	1541.9	1541.3	1540.7
12.5°	1519.9	1521.9	1523.9	1524.7	1524.4	1524.0	1523.6	1523.3
15°	1489.7	1492.1	1494.6	1494.9	1493.1	1491.2	1489.4	1487.6
17.5°	1451.5	1453.2	1454.9	1455.4	1454.8	1454.1	1453.4	1452.8
20°	1423.3	1424.6	1425.8	1425.9	1425.0	1424.1	1423.2	1422.3
22.5°	1393.5	1394.4	1395.4	1395.3	1394.2	1393.0	1391.9	1390.7
25°	1343.9	1344.3	1344.6	1344.3	1343.3	1342.4	1341.5	1340.6
27.5°	1291.3	1291.5	1291.8	1291.3	1290.2	1289.0	1287.9	1286.7
30°	1254.9	1254.9	1254.9	1253.8	1251.7	1249.6	1247.5	1245.3
32.5°	1216.6	1215.0	1213.3	1211.8	1210.7	1209.5	1208.4	1207.2
35°	1154.6	1152.8	1151.0	1149.3	1147.8	1146.3	1144.8	1143.3
37.5°	1090.5	1088.3	1086.1	1084.5	1083.6	1082.6	1081.6	1080.7
40°	1048.6	1046.2	1043.8	1041.9	1040.7	1039.5	1038.3	1037.1
42.5°	1005.0	1002.6	1000.2	998.4	997.2	996.0	994.8	993.6
45°	940.0	936.4	932.8	930.2	928.7	927.2	925.7	924.1
47.5°	871.5	868.0	864.4	862.0	860.6	859.3	858.0	856.6
50°	826.3	823.0	819.6	817.1	815.3	813.4	811.6	809.8
52.5°	780.4	777.6	774.8	772.4	770.6	768.8	767.0	765.2
55°	710.6	707.3	704.0	701.5	700.0	698.5	697.0	695.5
57.5°	641.9	639.0	636.0	633.6	631.9	630.1	628.4	626.6
60°	593.4	590.7	588.0	585.9	584.3	582.8	581.3	579.8
62.5°	546.6	543.9	541.1	539.3	538.2	537.2	536.2	535.2
65°	477.0	474.5	472.1	470.5	469.6	468.7	467.7	466.8
67.5°	407.9	405.8	403.7	402.0	400.7	399.4	398.1	396.9
70°	363.2	361.1	359.0	357.2	355.7	354.2	352.7	351.1
72.5°	318.0	316.1	314.2	312.9	312.1	311.3	310.6	309.8
75°	252.9	251.3	249.8	248.6	247.7	246.8	245.9	245.0
77.5°	192.0	191.0	190.0	189.5	189.5	189.5	189.5	189.5
80°	153.2	152.9	152.6	152.4	152.4	152.4	152.4	152.4
82.5°	117.9	117.3	116.8	116.4	116.1	115.9	115.7	115.4
85°	66.8	66.2	65.6	65.3	65.3	65.3	65.3	65.3
87.5°	29.5	29.4	29.4	29.4	29.5	29.6	29.7	29.8
90°	29.9	31.0	32.0	32.8	33.3	33.8	34.3	34.9
92.5°	33.0	34.7	36.4	37.3	37.6	38.0	38.3	38.6
95°	39.6	41.4	43.2	44.1	44.1	44.1	44.1	44.1
97.5°	41.5	43.6	45.7	46.8	47.1	47.4	47.6	47.9
100°	42.5	44.5	46.6	47.8	48.0	48.3	48.5	48.8
102.5°	63.6	57.2	50.8	47.9	48.3	48.8	49.3	49.7
105°	163.0	117.3	71.6	49.1	49.6	50.1	50.6	51.1
107.5°	399.3	365.8	332.3	298.3	263.9	229.4	195.0	160.6
110°	506.9	498.4	489.9	467.2	430.3	393.3	356.4	319.5



TEST NUMBER: P332042

CATALOG NUMBER: S123DIP-S1000D1195U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	582.8	583.0	583.2	579.3	571.5	563.7	555.9	548.1
115°	672.0	674.6	677.2	679.0	680.0	681.1	682.1	683.1
117.5°	752.8	754.9	756.9	758.1	758.3	758.5	758.7	758.9
120°	805.8	807.8	809.9	810.9	810.9	810.9	810.9	810.9
122.5°	857.5	859.0	860.4	861.2	861.4	861.6	861.9	862.1
125°	930.5	931.0	931.5	932.0	932.5	933.1	933.6	934.1
127.5°	1003.6	1004.4	1005.2	1005.4	1004.9	1004.4	1003.9	1003.3
130°	1047.7	1048.7	1049.8	1050.0	1049.5	1049.0	1048.5	1048.0
132.5°	1089.5	1090.6	1091.6	1091.7	1091.0	1090.3	1089.6	1088.8
135°	1152.9	1153.7	1154.5	1154.5	1153.7	1152.9	1152.1	1151.4
137.5°	1209.4	1210.6	1211.8	1212.2	1211.7	1211.2	1210.7	1210.1
140°	1245.2	1246.2	1247.3	1247.5	1247.0	1246.5	1246.0	1245.5
142.5°	1279.2	1280.0	1280.8	1280.9	1280.2	1279.4	1278.7	1278.0
145°	1326.7	1327.2	1327.7	1327.9	1327.9	1327.9	1327.9	1327.9
147.5°	1369.2	1369.7	1370.2	1369.9	1368.7	1367.5	1366.3	1365.1
150°	1395.2	1395.7	1396.2	1396.1	1395.3	1394.6	1393.8	1393.0
152.5°	1418.3	1419.3	1420.2	1420.1	1418.9	1417.7	1416.5	1415.3
155°	1450.2	1451.5	1452.8	1452.6	1451.1	1449.6	1448.0	1446.5
157.5°	1477.9	1479.4	1481.0	1480.8	1478.8	1476.7	1474.7	1472.7
160°	1493.7	1495.2	1496.8	1496.7	1494.9	1493.1	1491.2	1489.4
162.5°	1508.1	1509.8	1511.6	1511.6	1510.0	1508.4	1506.8	1505.2
165°	1527.3	1529.3	1531.4	1531.5	1529.7	1527.9	1526.1	1524.3
167.5°	1542.1	1544.2	1546.3	1546.3	1544.2	1542.1	1540.1	1538.0
170°	1550.5	1552.6	1554.6	1554.6	1552.6	1550.5	1548.4	1546.4
172.5°	1556.1	1558.1	1560.2	1560.1	1557.8	1555.6	1553.3	1551.0
175°	1562.8	1564.6	1566.4	1566.2	1564.2	1562.1	1560.1	1558.0
177.5°	1565.2	1566.9	1568.5	1568.3	1566.3	1564.2	1562.1	1560.1
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8

(END OF REPORT)