

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332259-927

Luminaire Tested: **S123RDIP-S340D1025U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332259-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D1025U927-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3865.5 lumens  
Efficiency: N/A  
Efficacy: 103.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332259-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - · - · 90°-270°    - · - · 135°-315°



TEST NUMBER: P332259-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	77	74	63	61	59	47	45	44	32	31	31	24
2	85	78	72	68	76	70	65	61	55	52	49	41	39	37	29	27	26	21
3	78	69	62	57	69	62	56	51	49	45	42	37	34	32	26	24	23	18
4	71	61	54	48	63	55	49	44	44	39	36	33	30	28	23	21	20	16
5	65	54	47	41	58	49	42	38	39	34	31	30	26	24	21	19	17	14
6	60	49	41	36	54	44	37	33	35	30	27	27	24	21	19	17	15	12
7	56	44	36	31	50	40	33	29	32	27	24	24	21	19	17	15	14	11
8	51	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	12	10
9	48	36	29	24	43	33	27	22	27	22	19	20	17	15	15	13	11	9
10	45	33	26	22	40	30	24	20	24	20	17	19	16	13	14	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4640	4640	4640	4640
5°	5532	4660	4105	4660
10°	6907	4634	3707	4634
15°	8107	4586	3381	4586
20°	9049	4515	3103	4515
25°	8904	4441	2932	4441
30°	6400	4373	2757	4373
35°	4273	4282	2643	4282
40°	3147	4175	2525	4175
45°	2641	3987	2411	3987
50°	2331	3739	2251	3739
55°	2044	3457	2029	3457
60°	1819	3186	1858	3186
65°	1597	2896	1729	2896
70°	1253	2637	1580	2637
75°	1102	2304	1443	2304
80°	961	1953	1420	1953
85°	778	1581	1507	1581



TEST NUMBER: P332259-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.4	1.1
10°-20°	132.5	3.4
20°-30°	208.1	5.4
30°-40°	217.1	5.6
40°-50°	185.8	4.8
50°-60°	141.6	3.7
60°-70°	90.8	2.3
70°-80°	43.7	1.1
80°-90°	14.5	0.4
90°-100°	65.6	1.7
100°-110°	196.3	5.1
110°-120°	333.8	8.6
120°-130°	439.1	11.4
130°-140°	493.6	12.8
140°-150°	485.2	12.6
150°-160°	408.4	10.6
160°-170°	271.9	7.0
170°-180°	95.2	2.5
0°-30°	382.9	9.9
0°-40°	600.1	15.5
0°-60°	927.5	24.0
0°-90°	1076.4	27.8
90°-120°	595.7	15.4
90°-150°	2013.5	52.1
90°-180°	2789.0	72.2
0°-180°	3865.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	431	431	431	431	431	
5°	512	431	380	431	512	53
15°	728	412	303	412	728	206
25°	750	374	247	374	750	322
35°	325	326	201	326	325	213
45°	174	262	158	262	174	136
55°	109	184	108	184	109	98
65°	63	114	68	114	63	62
75°	26	55	35	55	26	28
85°	6	13	12	13	6	8
90°	24	1	24	1	24	12
95°	62	47	62	47	62	63
105°	188	178	188	178	188	200
115°	337	336	337	336	337	333
125°	486	492	486	492	486	435
135°	637	638	637	638	637	490
145°	774	774	774	774	774	483
155°	885	886	885	886	885	407
165°	962	966	962	966	962	271
175°	1000	1004	1000	1004	1000	95
180°	1007	1007	1007	1007	1007	



TEST NUMBER: P332259-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	459.2	459.8	457.9	457.6	455.3	454.8	454.8	451.6	449.7	447.3	445.8
5°	512.0	514.9	513.4	510.2	504.6	503.3	499.8	494.2	488.0	480.2	476.6
7.5°	577.9	581.9	580.4	575.3	569.4	564.7	554.8	545.7	532.8	521.5	511.8
10°	631.9	627.7	624.4	619.4	614.0	605.4	595.0	580.8	564.4	551.4	537.1
12.5°	672.4	671.7	667.5	662.3	654.8	646.6	633.8	616.6	597.5	578.8	562.3
15°	727.5	728.6	725.9	720.6	709.8	695.2	676.0	668.8	641.5	621.2	600.9
17.5°	765.7	765.5	765.1	757.7	746.8	736.4	718.6	699.7	674.9	646.3	619.0
20°	790.0	788.1	788.5	780.1	772.1	760.0	742.7	715.2	694.9	661.9	633.6
22.5°	789.3	788.9	790.4	787.5	781.6	772.5	758.8	735.5	709.6	676.3	644.5
25°	749.7	748.2	756.9	759.3	768.7	770.4	766.3	753.6	729.0	694.7	655.4
27.5°	627.4	626.6	642.7	662.9	688.4	708.3	727.5	736.7	729.0	704.4	665.0
30°	514.9	532.3	540.4	569.6	602.1	640.8	674.8	707.0	715.0	704.3	672.0
32.5°	427.5	442.7	449.5	474.4	504.8	550.2	601.1	646.8	679.1	687.3	667.9
35°	325.2	325.3	340.9	352.0	380.0	426.7	476.2	537.4	598.3	644.5	649.3
37.5°	259.5	260.4	269.8	280.8	301.9	326.5	370.1	421.0	491.4	562.2	603.8
40°	224.0	225.7	232.7	243.6	258.7	277.4	311.3	359.3	418.0	496.9	561.3
42.5°	201.3	204.0	207.6	216.0	225.4	242.9	270.3	307.4	360.8	435.3	509.6
45°	173.5	175.0	177.8	181.6	190.1	202.2	220.7	245.7	289.9	349.9	424.3
47.5°	153.0	152.3	155.2	158.3	164.0	172.3	184.7	204.9	236.5	284.7	347.8
50°	139.2	138.9	141.0	143.4	148.8	154.9	165.0	180.3	205.4	245.3	303.1
52.5°	126.2	126.8	128.3	131.3	135.1	140.1	149.2	160.3	181.8	216.2	264.4
55°	108.9	109.5	111.5	113.1	115.9	120.9	126.6	135.9	150.6	174.6	214.3
57.5°	94.3	94.0	95.9	96.4	99.5	103.5	108.0	115.2	125.9	143.7	170.4
60°	84.5	84.0	85.6	86.9	88.6	91.9	95.6	102.6	111.1	124.2	147.1
62.5°	75.7	75.4	76.6	78.0	79.3	82.3	85.4	90.8	97.5	108.5	126.7
65°	62.7	63.3	63.8	64.4	65.1	67.0	69.9	73.7	78.3	86.0	99.1
67.5°	49.4	49.9	50.1	51.2	52.8	53.9	55.8	59.0	62.3	68.8	76.2
70°	39.8	39.7	39.8	40.4	42.5	44.4	46.9	49.3	51.3	55.9	62.2
72.5°	34.2	33.9	34.4	34.5	35.5	36.0	37.5	39.8	42.5	45.6	50.1
75°	26.5	26.5	26.5	26.5	27.3	27.6	28.2	28.8	29.7	31.2	34.5
77.5°	19.6	19.6	20.0	20.1	20.3	20.5	20.8	21.4	21.7	22.5	23.9
80°	15.5	15.7	15.5	15.7	15.7	16.1	16.2	16.8	17.0	17.9	18.5
82.5°	11.6	11.6	11.6	11.9	11.9	12.2	12.3	12.7	12.7	13.2	13.7
85°	6.3	5.9	6.3	6.1	6.5	6.1	6.3	6.7	6.7	6.8	7.6
87.5°	6.3	6.4	6.1	6.2	6.1	6.1	6.0	5.9	6.0	5.7	5.4
90°	23.7	23.4	23.1	22.7	22.3	21.8	21.1	20.4	19.6	19.0	16.7
92.5°	31.9	32.2	32.4	32.6	32.8	32.6	32.1	31.5	30.9	30.3	29.1
95°	61.7	61.7	61.7	61.7	61.7	61.3	60.6	59.9	59.3	58.5	57.1
97.5°	94.9	95.0	95.1	95.1	95.1	94.8	94.0	93.2	92.4	91.6	90.5
100°	120.2	119.9	119.5	119.1	118.8	118.4	117.8	117.3	116.8	116.2	115.3
102.5°	146.2	146.2	146.2	146.3	146.4	146.2	145.7	145.1	144.6	144.1	142.9
105°	188.2	187.8	187.5	187.1	186.8	186.6	186.6	186.6	186.6	186.6	185.1
107.5°	232.0	232.2	232.4	232.7	232.8	232.7	232.1	231.6	231.0	230.4	229.8
110°	261.7	262.1	262.4	262.8	263.2	263.0	262.3	261.6	260.9	260.2	259.8



TEST NUMBER: P332259-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	293.3	293.4	293.5	293.6	293.7	293.3	292.4	291.6	290.7	289.9	289.9
115°	336.8	337.1	337.2	337.4	337.5	337.5	337.4	337.2	337.1	336.8	337.2
117.5°	381.0	381.5	382.0	382.5	382.9	383.3	383.3	383.3	383.3	383.3	383.8
120°	412.0	412.3	412.7	413.0	413.4	413.7	413.8	414.0	414.2	414.4	415.3
122.5°	441.7	442.2	442.7	443.2	443.7	444.2	444.7	445.0	445.5	446.0	446.5
125°	486.3	487.0	487.7	488.5	489.1	489.8	490.5	491.2	491.9	492.7	493.0
127.5°	530.8	531.6	532.3	533.2	534.0	534.9	535.9	536.9	537.8	538.8	539.2
130°	559.8	561.1	562.3	563.6	564.7	565.8	566.4	567.1	567.8	568.5	569.1
132.5°	590.3	591.2	592.2	593.1	594.1	594.9	595.8	596.6	597.5	598.3	598.7
135°	637.4	637.7	638.0	638.4	638.7	639.3	640.0	640.7	641.4	642.1	642.3
137.5°	679.0	679.6	680.2	681.0	681.6	682.3	683.1	683.8	684.5	685.2	684.8
140°	706.2	707.4	708.6	709.9	711.1	711.8	711.9	712.1	712.3	712.5	712.3
142.5°	734.0	734.9	735.9	736.8	737.8	738.3	738.6	738.7	738.9	739.0	738.7
145°	774.1	774.8	775.5	776.3	777.0	777.4	777.6	777.8	777.9	778.1	777.6
147.5°	809.9	811.0	812.0	813.1	814.1	814.7	814.7	814.7	814.7	814.7	814.1
150°	832.7	833.7	834.8	835.8	836.9	837.4	837.4	837.4	837.4	837.4	837.1
152.5°	854.8	855.7	856.7	857.5	858.5	858.8	858.5	858.3	857.9	857.7	857.5
155°	884.9	886.1	887.3	888.6	889.8	890.0	889.4	888.7	888.0	887.2	887.1
157.5°	912.2	913.2	914.2	915.2	916.2	916.3	915.5	914.8	914.1	913.3	913.2
160°	929.9	930.7	931.4	932.1	932.7	932.6	931.8	930.9	930.0	929.2	929.2
162.5°	943.3	944.4	945.5	946.6	947.7	947.8	947.0	946.1	945.2	944.4	944.2
165°	962.3	963.6	964.8	966.1	967.3	967.3	966.3	965.3	964.2	963.1	963.1
167.5°	978.7	979.8	980.8	981.9	983.0	983.0	981.9	980.8	979.8	978.7	978.5
170°	986.9	988.1	989.4	990.5	991.8	991.8	990.5	989.4	988.1	986.9	986.9
172.5°	993.2	994.4	995.7	996.9	998.1	998.1	997.1	996.0	994.9	993.8	993.8
175°	1000.3	1001.6	1002.7	1004.0	1005.2	1005.4	1004.2	1003.2	1002.2	1001.1	1001.1
177.5°	1004.1	1005.1	1006.1	1007.1	1008.1	1008.1	1007.3	1006.5	1005.6	1004.7	1004.7
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6



TEST NUMBER: P332259-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	445.1	444.7	442.7	440.3	437.2	435.1	433.5	432.6	429.9	426.7	424.5
5°	472.7	467.1	461.2	454.0	447.3	440.5	436.3	431.3	425.2	418.4	413.6
7.5°	502.1	491.2	479.6	467.5	455.6	444.9	435.4	427.3	417.6	407.8	401.0
10°	524.7	508.8	492.4	475.6	460.3	445.9	434.8	424.0	412.3	401.1	392.5
12.5°	545.3	524.3	505.4	484.7	465.2	448.0	432.1	419.2	405.2	393.2	383.6
15°	571.2	549.8	527.0	495.5	469.5	447.7	428.3	411.5	394.6	379.9	370.4
17.5°	595.5	563.3	532.5	506.4	472.5	445.4	421.7	401.6	382.9	367.3	355.7
20°	605.5	574.3	541.0	507.6	474.4	443.9	416.4	394.2	374.9	357.1	346.4
22.5°	611.6	576.3	541.1	505.2	469.9	438.2	411.1	386.7	365.7	348.9	335.6
25°	618.6	576.6	537.8	502.4	466.4	432.1	399.7	373.9	351.3	333.4	319.3
27.5°	623.3	573.8	528.0	488.6	452.1	418.0	388.3	360.9	337.9	318.9	303.9
30°	624.2	571.6	520.5	477.8	440.8	409.3	378.0	351.8	327.4	307.3	293.3
32.5°	625.3	566.1	510.2	465.0	427.0	395.9	367.5	342.5	317.5	297.7	283.4
35°	620.5	563.1	494.8	442.8	404.7	374.6	349.0	325.9	301.4	282.2	267.6
37.5°	599.5	551.1	478.8	417.7	378.0	350.1	329.2	309.1	286.6	265.9	252.2
40°	578.5	539.3	466.4	402.5	361.0	332.4	313.5	297.1	275.4	256.0	241.2
42.5°	547.0	523.2	454.6	386.6	341.8	314.3	298.3	283.0	263.9	244.2	230.3
45°	489.3	492.4	430.4	361.2	315.2	287.6	272.6	261.9	244.9	228.7	214.4
47.5°	416.9	446.2	402.0	334.1	287.2	261.3	248.2	238.8	227.4	211.4	198.4
50°	369.7	411.5	379.3	316.0	269.7	243.8	230.9	223.3	213.3	200.8	188.5
52.5°	326.1	371.1	351.8	295.7	250.6	227.0	214.4	208.1	200.2	188.4	177.2
55°	265.9	311.6	307.1	265.2	222.0	200.8	191.2	184.2	178.9	170.0	161.1
57.5°	215.2	258.3	260.6	231.2	196.9	175.9	167.6	162.3	158.8	152.2	143.9
60°	183.1	222.8	230.5	208.3	178.9	160.4	152.3	148.0	145.3	139.9	133.6
62.5°	156.5	190.3	199.1	183.2	161.6	144.3	137.9	133.9	132.0	127.4	121.8
65°	119.8	147.8	156.3	147.5	136.2	122.4	117.2	113.7	112.0	109.5	105.4
67.5°	90.1	110.5	119.9	113.6	109.5	100.8	97.5	95.6	94.1	92.4	89.0
70°	72.3	87.5	97.0	95.5	92.1	87.5	85.1	83.8	82.3	80.8	77.9
72.5°	58.1	68.6	77.6	78.4	75.7	74.8	72.6	72.1	71.2	69.5	67.8
75°	38.6	45.8	52.0	54.4	55.5	56.5	55.5	55.4	55.2	53.7	52.8
77.5°	25.3	29.2	33.1	37.2	39.0	40.2	40.5	41.2	40.6	39.9	39.5
80°	19.4	20.3	23.1	26.5	29.3	30.4	31.2	31.5	31.4	31.2	30.4
82.5°	14.1	14.8	16.2	18.6	20.9	22.7	23.2	23.1	23.5	23.7	23.1
85°	7.6	7.8	8.2	8.5	9.7	11.8	12.4	12.8	13.1	13.1	12.0
87.5°	5.2	4.7	4.5	4.0	4.2	4.0	4.5	4.9	5.4	5.1	5.5
90°	14.4	12.1	9.8	7.8	6.1	4.3	2.5	0.8	2.5	4.3	6.1
92.5°	27.7	26.5	25.2	23.9	22.7	21.5	20.4	19.2	20.4	21.5	22.7
95°	55.7	54.3	52.9	51.6	50.4	49.1	47.8	46.7	47.8	49.1	50.4
97.5°	89.5	88.5	87.5	86.5	85.6	84.7	83.8	82.9	83.8	84.7	85.6
100°	114.5	113.6	112.7	111.8	110.7	109.6	108.6	107.6	108.6	109.6	110.7
102.5°	141.7	140.6	139.4	138.6	137.9	137.3	136.7	136.0	136.7	137.3	137.9
105°	183.5	181.9	180.3	179.4	179.0	178.6	178.2	177.9	178.2	178.6	179.0
107.5°	229.2	228.5	227.9	227.5	227.3	227.0	226.9	226.6	226.9	227.0	227.3
110°	259.4	259.1	258.7	258.4	258.0	257.7	257.4	257.0	257.4	257.7	258.0





TEST NUMBER: P332259-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	289.8	289.7	289.6	289.5	289.2	289.1	288.8	288.6	288.8	289.1	289.2
115°	337.5	337.9	338.3	338.2	337.6	337.2	336.6	336.0	336.6	337.2	337.6
117.5°	384.3	384.8	385.2	385.2	384.9	384.5	384.2	383.8	384.2	384.5	384.9
120°	416.1	417.0	417.9	417.8	416.8	415.7	414.6	413.6	414.6	415.7	416.8
122.5°	446.9	447.3	447.8	447.7	446.9	446.1	445.4	444.6	445.4	446.1	446.9
125°	493.4	493.7	494.1	493.9	493.5	492.9	492.4	491.9	492.4	492.9	493.5
127.5°	539.6	540.0	540.3	540.0	538.8	537.7	536.6	535.5	536.6	537.7	538.8
130°	569.6	570.1	570.7	570.2	568.8	567.4	566.0	564.6	566.0	567.4	568.8
132.5°	599.0	599.4	599.8	599.4	597.9	596.5	595.1	593.7	595.1	596.5	597.9
135°	642.5	642.6	642.8	642.4	641.3	640.2	639.2	638.2	639.2	640.2	641.3
137.5°	684.4	683.9	683.4	682.8	681.9	681.0	680.2	679.3	680.2	681.0	681.9
140°	712.1	711.9	711.8	711.2	710.3	709.5	708.6	707.7	708.6	709.5	710.3
142.5°	738.4	738.1	737.8	737.2	736.3	735.5	734.5	733.6	734.5	735.5	736.3
145°	777.1	776.5	776.0	775.5	775.2	774.8	774.5	774.1	774.5	774.8	775.2
147.5°	813.7	813.2	812.7	812.1	811.5	810.9	810.2	809.6	810.2	810.9	811.5
150°	836.7	836.4	836.0	835.7	835.3	835.0	834.6	834.2	834.6	835.0	835.3
152.5°	857.2	857.1	856.8	856.4	856.0	855.5	855.0	854.5	855.0	855.5	856.0
155°	886.8	886.7	886.5	886.5	886.5	886.5	886.5	886.5	886.5	886.5	886.5
157.5°	913.1	912.9	912.8	912.8	913.0	913.2	913.5	913.6	913.5	913.2	913.0
160°	929.2	929.2	929.2	929.3	929.7	930.0	930.3	930.7	930.3	930.0	929.7
162.5°	944.0	943.9	943.8	944.0	944.4	944.9	945.4	945.9	945.4	944.9	944.4
165°	963.1	963.1	963.1	963.5	963.9	964.5	965.0	965.5	965.0	964.5	963.9
167.5°	978.3	978.3	978.1	978.3	979.1	979.8	980.5	981.2	980.5	979.8	979.1
170°	986.9	986.9	986.9	987.2	987.9	988.6	989.4	990.1	989.4	988.6	987.9
172.5°	993.8	993.8	993.8	994.2	994.9	995.6	996.3	997.0	996.3	995.6	994.9
175°	1001.1	1001.1	1001.1	1001.5	1002.2	1002.8	1003.5	1004.2	1003.5	1002.8	1002.2
177.5°	1004.7	1004.7	1004.7	1005.0	1005.6	1006.2	1006.7	1007.3	1006.7	1006.2	1005.6
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6



TEST NUMBER: P332259-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	423.7	421.8	420.5	417.6	415.7	413.6	411.5	412.8	412.6	412.6	412.6
5°	409.6	405.3	401.4	396.4	393.3	389.4	386.5	386.1	386.8	384.3	382.8
7.5°	395.5	389.7	384.1	378.7	372.8	368.1	365.3	363.8	362.0	360.4	358.8
10°	385.6	378.7	373.4	366.5	360.3	354.7	351.3	348.8	347.5	346.3	343.8
12.5°	375.3	368.7	361.9	354.1	348.2	341.7	339.1	336.4	334.0	332.5	329.2
15°	360.4	351.8	344.6	336.4	329.8	323.5	319.9	314.5	313.8	311.9	308.6
17.5°	345.5	336.1	326.1	320.1	312.7	306.1	300.5	298.7	293.4	291.4	288.5
20°	333.7	325.0	317.4	309.5	298.7	292.6	288.1	285.7	281.5	278.8	277.0
22.5°	323.5	314.7	305.9	296.7	287.7	280.8	277.6	273.9	271.6	267.9	265.9
25°	309.0	299.4	288.8	278.8	272.4	267.3	262.1	258.7	255.4	253.7	250.1
27.5°	292.1	282.0	272.2	264.6	256.7	251.6	246.9	244.0	240.0	237.2	235.1
30°	282.7	270.9	262.4	255.6	245.5	240.7	237.2	233.5	230.5	227.6	225.5
32.5°	272.0	261.2	253.2	244.7	236.9	231.6	227.1	223.9	221.3	218.6	216.5
35°	255.1	246.1	237.7	229.3	223.5	218.2	212.8	210.0	207.6	205.0	203.2
37.5°	239.8	231.3	223.4	215.4	208.3	203.9	199.6	197.5	194.2	192.5	190.7
40°	230.4	222.0	213.6	205.8	198.4	195.1	191.2	188.1	185.1	183.8	181.8
42.5°	220.0	211.7	204.5	196.2	190.1	185.6	182.0	178.6	176.4	174.5	173.4
45°	204.7	197.3	190.3	182.0	176.3	172.4	168.3	165.2	163.2	161.8	159.9
47.5°	189.8	182.4	175.3	168.1	162.6	158.1	154.0	151.9	149.2	147.6	146.2
50°	179.0	172.4	164.9	158.2	152.7	148.2	144.9	142.1	139.7	137.7	136.7
52.5°	169.1	162.1	155.5	149.3	143.5	138.5	135.5	132.5	130.7	128.4	127.3
55°	152.8	146.0	140.5	134.4	128.7	124.4	120.7	118.1	116.3	113.7	112.3
57.5°	137.5	131.3	124.8	119.5	113.6	110.0	106.9	103.5	101.2	99.2	97.7
60°	127.1	120.2	114.4	109.5	104.3	99.7	96.9	94.1	91.7	89.7	88.4
62.5°	116.4	110.3	104.8	99.4	94.7	90.6	87.5	85.2	83.0	81.8	80.4
65°	99.8	95.1	89.5	85.1	80.6	77.7	75.1	73.1	71.6	70.7	69.6
67.5°	84.6	80.0	75.2	70.8	67.8	65.6	63.9	62.2	61.4	60.2	59.5
70°	74.8	69.9	65.7	62.3	59.4	57.8	56.6	55.4	54.7	53.2	52.4
72.5°	64.0	60.5	57.4	54.7	52.4	50.9	49.4	47.8	46.7	45.0	44.3
75°	50.4	47.2	44.8	43.0	41.5	39.5	37.5	35.8	35.3	34.7	34.5
77.5°	37.3	35.3	33.6	32.0	30.2	28.8	28.3	27.9	27.8	27.5	27.5
80°	29.3	27.5	26.2	24.4	23.3	23.3	23.3	22.9	23.1	23.1	23.1
82.5°	21.8	20.1	19.4	18.8	18.5	18.7	18.7	18.8	18.6	18.9	18.8
85°	11.2	11.4	11.8	11.6	11.8	11.8	12.2	12.0	12.2	11.8	12.2
87.5°	5.7	6.6	7.1	7.8	8.4	8.6	9.0	9.1	9.3	9.5	9.7
90°	7.8	9.8	12.1	14.4	16.7	19.0	19.6	20.4	21.1	21.8	22.3
92.5°	23.9	25.2	26.5	27.7	29.1	30.3	30.9	31.5	32.1	32.6	32.8
95°	51.6	52.9	54.3	55.7	57.1	58.5	59.3	59.9	60.6	61.3	61.7
97.5°	86.5	87.5	88.5	89.5	90.5	91.6	92.4	93.2	94.0	94.8	95.1
100°	111.8	112.7	113.6	114.5	115.3	116.2	116.8	117.3	117.8	118.4	118.8
102.5°	138.6	139.4	140.6	141.7	142.9	144.1	144.6	145.1	145.7	146.2	146.4
105°	179.4	180.3	181.9	183.5	185.1	186.6	186.6	186.6	186.6	186.6	186.8
107.5°	227.5	227.9	228.5	229.2	229.8	230.4	231.0	231.6	232.1	232.7	232.8
110°	258.4	258.7	259.1	259.4	259.8	260.2	260.9	261.6	262.3	263.0	263.2



TEST NUMBER: P332259-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	289.5	289.6	289.7	289.8	289.9	289.9	290.7	291.6	292.4	293.3	293.7
115°	338.2	338.3	337.9	337.5	337.2	336.8	337.1	337.2	337.4	337.5	337.5
117.5°	385.2	385.2	384.8	384.3	383.8	383.3	383.3	383.3	383.3	383.3	382.9
120°	417.8	417.9	417.0	416.1	415.3	414.4	414.2	414.0	413.8	413.7	413.4
122.5°	447.7	447.8	447.3	446.9	446.5	446.0	445.5	445.0	444.7	444.2	443.7
125°	493.9	494.1	493.7	493.4	493.0	492.7	491.9	491.2	490.5	489.8	489.1
127.5°	540.0	540.3	540.0	539.6	539.2	538.8	537.8	536.9	535.9	534.9	534.0
130°	570.2	570.7	570.1	569.6	569.1	568.5	567.8	567.1	566.4	565.8	564.7
132.5°	599.4	599.8	599.4	599.0	598.7	598.3	597.5	596.6	595.8	594.9	594.1
135°	642.4	642.8	642.6	642.5	642.3	642.1	641.4	640.7	640.0	639.3	638.7
137.5°	682.8	683.4	683.9	684.4	684.8	685.2	684.5	683.8	683.1	682.3	681.6
140°	711.2	711.8	711.9	712.1	712.3	712.5	712.3	712.1	711.9	711.8	711.1
142.5°	737.2	737.8	738.1	738.4	738.7	739.0	738.9	738.7	738.6	738.3	737.8
145°	775.5	776.0	776.5	777.1	777.6	778.1	777.9	777.8	777.6	777.4	777.0
147.5°	812.1	812.7	813.2	813.7	814.1	814.7	814.7	814.7	814.7	814.7	814.1
150°	835.7	836.0	836.4	836.7	837.1	837.4	837.4	837.4	837.4	837.4	836.9
152.5°	856.4	856.8	857.1	857.2	857.5	857.7	857.9	858.3	858.5	858.8	858.5
155°	886.5	886.5	886.7	886.8	887.1	887.2	888.0	888.7	889.4	890.0	889.8
157.5°	912.8	912.8	912.9	913.1	913.2	913.3	914.1	914.8	915.5	916.3	916.2
160°	929.3	929.2	929.2	929.2	929.2	929.2	930.0	930.9	931.8	932.6	932.7
162.5°	944.0	943.8	943.9	944.0	944.2	944.4	945.2	946.1	947.0	947.8	947.7
165°	963.5	963.1	963.1	963.1	963.1	963.1	964.2	965.3	966.3	967.3	967.3
167.5°	978.3	978.1	978.3	978.3	978.5	978.7	979.8	980.8	981.9	983.0	983.0
170°	987.2	986.9	986.9	986.9	986.9	986.9	988.1	989.4	990.5	991.8	991.8
172.5°	994.2	993.8	993.8	993.8	993.8	993.8	994.9	996.0	997.1	998.1	998.1
175°	1001.5	1001.1	1001.1	1001.1	1001.1	1001.1	1002.2	1003.2	1004.2	1005.4	1005.2
177.5°	1005.0	1004.7	1004.7	1004.7	1004.7	1004.7	1005.6	1006.5	1007.3	1008.1	1008.1
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6



TEST NUMBER: P332259-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	410.7	410.6	410.7	410.2	410.7	410.6	410.7	412.6	412.6	412.6	412.8
5°	382.2	382.1	381.5	379.9	381.5	382.1	382.2	382.8	384.3	386.8	386.1
7.5°	357.3	357.0	355.5	355.5	355.5	357.0	357.3	358.8	360.4	362.0	363.8
10°	342.5	342.7	340.5	339.2	340.5	342.7	342.5	343.8	346.3	347.5	348.8
12.5°	328.2	327.4	325.6	324.2	325.6	327.4	328.2	329.2	332.5	334.0	336.4
15°	309.3	307.4	303.1	303.4	303.1	307.4	309.3	308.6	311.9	313.8	314.5
17.5°	287.1	285.7	285.7	283.0	285.7	285.7	287.1	288.5	291.4	293.4	298.7
20°	274.1	273.1	273.5	270.9	273.5	273.1	274.1	277.0	278.8	281.5	285.7
22.5°	263.9	262.9	261.4	260.6	261.4	262.9	263.9	265.9	267.9	271.6	273.9
25°	249.0	247.5	246.1	246.9	246.1	247.5	249.0	250.1	253.7	255.4	258.7
27.5°	234.1	233.0	231.5	231.3	231.5	233.0	234.1	235.1	237.2	240.0	244.0
30°	224.6	223.5	222.8	221.8	222.8	223.5	224.6	225.5	227.6	230.5	233.5
32.5°	215.0	214.8	213.5	213.3	213.5	214.8	215.0	216.5	218.6	221.3	223.9
35°	202.5	201.4	201.0	201.1	201.0	201.4	202.5	203.2	205.0	207.6	210.0
37.5°	190.5	189.1	188.4	187.7	188.4	189.1	190.5	190.7	192.5	194.2	197.5
40°	182.0	180.5	180.1	179.7	180.1	180.5	182.0	181.8	183.8	185.1	188.1
42.5°	172.4	171.8	171.6	170.9	171.6	171.8	172.4	173.4	174.5	176.4	178.6
45°	159.3	159.1	158.0	158.4	158.0	159.1	159.3	159.9	161.8	163.2	165.2
47.5°	145.4	144.7	143.9	144.4	143.9	144.7	145.4	146.2	147.6	149.2	151.9
50°	136.0	135.6	134.0	134.4	134.0	135.6	136.0	136.7	137.7	139.7	142.1
52.5°	126.6	125.2	124.5	124.3	124.5	125.2	126.6	127.3	128.4	130.7	132.5
55°	110.9	109.2	108.5	108.1	108.5	109.2	110.9	112.3	113.7	116.3	118.1
57.5°	95.5	95.1	94.5	94.9	94.5	95.1	95.5	97.7	99.2	101.2	103.5
60°	86.6	86.6	86.6	86.3	86.6	86.6	86.6	88.4	89.7	91.7	94.1
62.5°	79.6	79.1	79.1	79.3	79.1	79.1	79.6	80.4	81.8	83.0	85.2
65°	69.0	68.8	68.1	67.9	68.1	68.8	69.0	69.6	70.7	71.6	73.1
67.5°	59.0	58.4	58.1	57.9	58.1	58.4	59.0	59.5	60.2	61.4	62.2
70°	51.5	51.1	50.0	50.2	50.0	51.1	51.5	52.4	53.2	54.7	55.4
72.5°	43.4	43.0	42.8	42.5	42.8	43.0	43.4	44.3	45.0	46.7	47.8
75°	34.3	34.1	34.0	34.7	34.0	34.1	34.3	34.5	34.7	35.3	35.8
77.5°	27.5	27.5	27.6	27.3	27.6	27.5	27.5	27.5	27.5	27.8	27.9
80°	23.1	23.1	22.9	22.9	22.9	23.1	23.1	23.1	23.1	23.1	22.9
82.5°	18.5	18.6	18.8	18.5	18.8	18.6	18.5	18.8	18.9	18.6	18.8
85°	12.2	12.0	12.4	12.2	12.4	12.0	12.2	12.2	11.8	12.2	12.0
87.5°	10.0	9.7	9.8	10.1	9.8	9.7	10.0	9.7	9.5	9.3	9.1
90°	22.7	23.1	23.4	23.7	23.4	23.1	22.7	22.3	21.8	21.1	20.4
92.5°	32.6	32.4	32.2	31.9	32.2	32.4	32.6	32.8	32.6	32.1	31.5
95°	61.7	61.7	61.7	61.7	61.7	61.7	61.7	61.7	61.3	60.6	59.9
97.5°	95.1	95.1	95.0	94.9	95.0	95.1	95.1	95.1	94.8	94.0	93.2
100°	119.1	119.5	119.9	120.2	119.9	119.5	119.1	118.8	118.4	117.8	117.3
102.5°	146.3	146.2	146.2	146.2	146.2	146.2	146.3	146.4	146.2	145.7	145.1
105°	187.1	187.5	187.8	188.2	187.8	187.5	187.1	186.8	186.6	186.6	186.6
107.5°	232.7	232.4	232.2	232.0	232.2	232.4	232.7	232.8	232.7	232.1	231.6
110°	262.8	262.4	262.1	261.7	262.1	262.4	262.8	263.2	263.0	262.3	261.6



TEST NUMBER: P332259-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	293.6	293.5	293.4	293.3	293.4	293.5	293.6	293.7	293.3	292.4	291.6
115°	337.4	337.2	337.1	336.8	337.1	337.2	337.4	337.5	337.5	337.4	337.2
117.5°	382.5	382.0	381.5	381.0	381.5	382.0	382.5	382.9	383.3	383.3	383.3
120°	413.0	412.7	412.3	412.0	412.3	412.7	413.0	413.4	413.7	413.8	414.0
122.5°	443.2	442.7	442.2	441.7	442.2	442.7	443.2	443.7	444.2	444.7	445.0
125°	488.5	487.7	487.0	486.3	487.0	487.7	488.5	489.1	489.8	490.5	491.2
127.5°	533.2	532.3	531.6	530.8	531.6	532.3	533.2	534.0	534.9	535.9	536.9
130°	563.6	562.3	561.1	559.8	561.1	562.3	563.6	564.7	565.8	566.4	567.1
132.5°	593.1	592.2	591.2	590.3	591.2	592.2	593.1	594.1	594.9	595.8	596.6
135°	638.4	638.0	637.7	637.4	637.7	638.0	638.4	638.7	639.3	640.0	640.7
137.5°	681.0	680.2	679.6	679.0	679.6	680.2	681.0	681.6	682.3	683.1	683.8
140°	709.9	708.6	707.4	706.2	707.4	708.6	709.9	711.1	711.8	711.9	712.1
142.5°	736.8	735.9	734.9	734.0	734.9	735.9	736.8	737.8	738.3	738.6	738.7
145°	776.3	775.5	774.8	774.1	774.8	775.5	776.3	777.0	777.4	777.6	777.8
147.5°	813.1	812.0	811.0	809.9	811.0	812.0	813.1	814.1	814.7	814.7	814.7
150°	835.8	834.8	833.7	832.7	833.7	834.8	835.8	836.9	837.4	837.4	837.4
152.5°	857.5	856.7	855.7	854.8	855.7	856.7	857.5	858.5	858.8	858.5	858.3
155°	888.6	887.3	886.1	884.9	886.1	887.3	888.6	889.8	890.0	889.4	888.7
157.5°	915.2	914.2	913.2	912.2	913.2	914.2	915.2	916.2	916.3	915.5	914.8
160°	932.1	931.4	930.7	929.9	930.7	931.4	932.1	932.7	932.6	931.8	930.9
162.5°	946.6	945.5	944.4	943.3	944.4	945.5	946.6	947.7	947.8	947.0	946.1
165°	966.1	964.8	963.6	962.3	963.6	964.8	966.1	967.3	967.3	966.3	965.3
167.5°	981.9	980.8	979.8	978.7	979.8	980.8	981.9	983.0	983.0	981.9	980.8
170°	990.5	989.4	988.1	986.9	988.1	989.4	990.5	991.8	991.8	990.5	989.4
172.5°	996.9	995.7	994.4	993.2	994.4	995.7	996.9	998.1	998.1	997.1	996.0
175°	1004.0	1002.7	1001.6	1000.3	1001.6	1002.7	1004.0	1005.2	1005.4	1004.2	1003.2
177.5°	1007.1	1006.1	1005.1	1004.1	1005.1	1006.1	1007.1	1008.1	1008.1	1007.3	1006.5
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6



TEST NUMBER: P332259-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	411.5	413.6	415.7	417.6	420.5	421.8	423.7	424.5	426.7	429.9	432.6
5°	386.5	389.4	393.3	396.4	401.4	405.3	409.6	413.6	418.4	425.2	431.3
7.5°	365.3	368.1	372.8	378.7	384.1	389.7	395.5	401.0	407.8	417.6	427.3
10°	351.3	354.7	360.3	366.5	373.4	378.7	385.6	392.5	401.1	412.3	424.0
12.5°	339.1	341.7	348.2	354.1	361.9	368.7	375.3	383.6	393.2	405.2	419.2
15°	319.9	323.5	329.8	336.4	344.6	351.8	360.4	370.4	379.9	394.6	411.5
17.5°	300.5	306.1	312.7	320.1	326.1	336.1	345.5	355.7	367.3	382.9	401.6
20°	288.1	292.6	298.7	309.5	317.4	325.0	333.7	346.4	357.1	374.9	394.2
22.5°	277.6	280.8	287.7	296.7	305.9	314.7	323.5	335.6	348.9	365.7	386.7
25°	262.1	267.3	272.4	278.8	288.8	299.4	309.0	319.3	333.4	351.3	373.9
27.5°	246.9	251.6	256.7	264.6	272.2	282.0	292.1	303.9	318.9	337.9	360.9
30°	237.2	240.7	245.5	255.6	262.4	270.9	282.7	293.3	307.3	327.4	351.8
32.5°	227.1	231.6	236.9	244.7	253.2	261.2	272.0	283.4	297.7	317.5	342.5
35°	212.8	218.2	223.5	229.3	237.7	246.1	255.1	267.6	282.2	301.4	325.9
37.5°	199.6	203.9	208.3	215.4	223.4	231.3	239.8	252.2	265.9	286.6	309.1
40°	191.2	195.1	198.4	205.8	213.6	222.0	230.4	241.2	256.0	275.4	297.1
42.5°	182.0	185.6	190.1	196.2	204.5	211.7	220.0	230.3	244.2	263.9	283.0
45°	168.3	172.4	176.3	182.0	190.3	197.3	204.7	214.4	228.7	244.9	261.9
47.5°	154.0	158.1	162.6	168.1	175.3	182.4	189.8	198.4	211.4	227.4	238.8
50°	144.9	148.2	152.7	158.2	164.9	172.4	179.0	188.5	200.8	213.3	223.3
52.5°	135.5	138.5	143.5	149.3	155.5	162.1	169.1	177.2	188.4	200.2	208.1
55°	120.7	124.4	128.7	134.4	140.5	146.0	152.8	161.1	170.0	178.9	184.2
57.5°	106.9	110.0	113.6	119.5	124.8	131.3	137.5	143.9	152.2	158.8	162.3
60°	96.9	99.7	104.3	109.5	114.4	120.2	127.1	133.6	139.9	145.3	148.0
62.5°	87.5	90.6	94.7	99.4	104.8	110.3	116.4	121.8	127.4	132.0	133.9
65°	75.1	77.7	80.6	85.1	89.5	95.1	99.8	105.4	109.5	112.0	113.7
67.5°	63.9	65.6	67.8	70.8	75.2	80.0	84.6	89.0	92.4	94.1	95.6
70°	56.6	57.8	59.4	62.3	65.7	69.9	74.8	77.9	80.8	82.3	83.8
72.5°	49.4	50.9	52.4	54.7	57.4	60.5	64.0	67.8	69.5	71.2	72.1
75°	37.5	39.5	41.5	43.0	44.8	47.2	50.4	52.8	53.7	55.2	55.4
77.5°	28.3	28.8	30.2	32.0	33.6	35.3	37.3	39.5	39.9	40.6	41.2
80°	23.3	23.3	23.3	24.4	26.2	27.5	29.3	30.4	31.2	31.4	31.5
82.5°	18.7	18.7	18.5	18.8	19.4	20.1	21.8	23.1	23.7	23.5	23.1
85°	12.2	11.8	11.8	11.6	11.8	11.4	11.2	12.0	13.1	13.1	12.8
87.5°	9.0	8.6	8.4	7.8	7.1	6.6	5.7	5.5	5.1	5.4	4.9
90°	19.6	19.0	16.7	14.4	12.1	9.8	7.8	6.1	4.3	2.5	0.8
92.5°	30.9	30.3	29.1	27.7	26.5	25.2	23.9	22.7	21.5	20.4	19.2
95°	59.3	58.5	57.1	55.7	54.3	52.9	51.6	50.4	49.1	47.8	46.7
97.5°	92.4	91.6	90.5	89.5	88.5	87.5	86.5	85.6	84.7	83.8	82.9
100°	116.8	116.2	115.3	114.5	113.6	112.7	111.8	110.7	109.6	108.6	107.6
102.5°	144.6	144.1	142.9	141.7	140.6	139.4	138.6	137.9	137.3	136.7	136.0
105°	186.6	186.6	185.1	183.5	181.9	180.3	179.4	179.0	178.6	178.2	177.9
107.5°	231.0	230.4	229.8	229.2	228.5	227.9	227.5	227.3	227.0	226.9	226.6
110°	260.9	260.2	259.8	259.4	259.1	258.7	258.4	258.0	257.7	257.4	257.0



TEST NUMBER: P332259-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	290.7	289.9	289.9	289.8	289.7	289.6	289.5	289.2	289.1	288.8	288.6
115°	337.1	336.8	337.2	337.5	337.9	338.3	338.2	337.6	337.2	336.6	336.0
117.5°	383.3	383.3	383.8	384.3	384.8	385.2	385.2	384.9	384.5	384.2	383.8
120°	414.2	414.4	415.3	416.1	417.0	417.9	417.8	416.8	415.7	414.6	413.6
122.5°	445.5	446.0	446.5	446.9	447.3	447.8	447.7	446.9	446.1	445.4	444.6
125°	491.9	492.7	493.0	493.4	493.7	494.1	493.9	493.5	492.9	492.4	491.9
127.5°	537.8	538.8	539.2	539.6	540.0	540.3	540.0	538.8	537.7	536.6	535.5
130°	567.8	568.5	569.1	569.6	570.1	570.7	570.2	568.8	567.4	566.0	564.6
132.5°	597.5	598.3	598.7	599.0	599.4	599.8	599.4	597.9	596.5	595.1	593.7
135°	641.4	642.1	642.3	642.5	642.6	642.8	642.4	641.3	640.2	639.2	638.2
137.5°	684.5	685.2	684.8	684.4	683.9	683.4	682.8	681.9	681.0	680.2	679.3
140°	712.3	712.5	712.3	712.1	711.9	711.8	711.2	710.3	709.5	708.6	707.7
142.5°	738.9	739.0	738.7	738.4	738.1	737.8	737.2	736.3	735.5	734.5	733.6
145°	777.9	778.1	777.6	777.1	776.5	776.0	775.5	775.2	774.8	774.5	774.1
147.5°	814.7	814.7	814.1	813.7	813.2	812.7	812.1	811.5	810.9	810.2	809.6
150°	837.4	837.4	837.1	836.7	836.4	836.0	835.7	835.3	835.0	834.6	834.2
152.5°	857.9	857.7	857.5	857.2	857.1	856.8	856.4	856.0	855.5	855.0	854.5
155°	888.0	887.2	887.1	886.8	886.7	886.5	886.5	886.5	886.5	886.5	886.5
157.5°	914.1	913.3	913.2	913.1	912.9	912.8	912.8	913.0	913.2	913.5	913.6
160°	930.0	929.2	929.2	929.2	929.2	929.2	929.3	929.7	930.0	930.3	930.7
162.5°	945.2	944.4	944.2	944.0	943.9	943.8	944.0	944.4	944.9	945.4	945.9
165°	964.2	963.1	963.1	963.1	963.1	963.1	963.5	963.9	964.5	965.0	965.5
167.5°	979.8	978.7	978.5	978.3	978.3	978.1	978.3	979.1	979.8	980.5	981.2
170°	988.1	986.9	986.9	986.9	986.9	986.9	987.2	987.9	988.6	989.4	990.1
172.5°	994.9	993.8	993.8	993.8	993.8	993.8	994.2	994.9	995.6	996.3	997.0
175°	1002.2	1001.1	1001.1	1001.1	1001.1	1001.1	1001.5	1002.2	1002.8	1003.5	1004.2
177.5°	1005.6	1004.7	1004.7	1004.7	1004.7	1004.7	1005.0	1005.6	1006.2	1006.7	1007.3
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6



TEST NUMBER: P332259-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	433.5	435.1	437.2	440.3	442.7	444.7	445.1	445.8	447.3	449.7	451.6
5°	436.3	440.5	447.3	454.0	461.2	467.1	472.7	476.6	480.2	488.0	494.2
7.5°	435.4	444.9	455.6	467.5	479.6	491.2	502.1	511.8	521.5	532.8	545.7
10°	434.8	445.9	460.3	475.6	492.4	508.8	524.7	537.1	551.4	564.4	580.8
12.5°	432.1	448.0	465.2	484.7	505.4	524.3	545.3	562.3	578.8	597.5	616.6
15°	428.3	447.7	469.5	495.5	527.0	549.8	571.2	600.9	621.2	641.5	668.8
17.5°	421.7	445.4	472.5	506.4	532.5	563.3	595.5	619.0	646.3	674.9	699.7
20°	416.4	443.9	474.4	507.6	541.0	574.3	605.5	633.6	661.9	694.9	715.2
22.5°	411.1	438.2	469.9	505.2	541.1	576.3	611.6	644.5	676.3	709.6	735.5
25°	399.7	432.1	466.4	502.4	537.8	576.6	618.6	655.4	694.7	729.0	753.6
27.5°	388.3	418.0	452.1	488.6	528.0	573.8	623.3	665.0	704.4	729.0	736.7
30°	378.0	409.3	440.8	477.8	520.5	571.6	624.2	672.0	704.3	715.0	707.0
32.5°	367.5	395.9	427.0	465.0	510.2	566.1	625.3	667.9	687.3	679.1	646.8
35°	349.0	374.6	404.7	442.8	494.8	563.1	620.5	649.3	644.5	598.3	537.4
37.5°	329.2	350.1	378.0	417.7	478.8	551.1	599.5	603.8	562.2	491.4	421.0
40°	313.5	332.4	361.0	402.5	466.4	539.3	578.5	561.3	496.9	418.0	359.3
42.5°	298.3	314.3	341.8	386.6	454.6	523.2	547.0	509.6	435.3	360.8	307.4
45°	272.6	287.6	315.2	361.2	430.4	492.4	489.3	424.3	349.9	289.9	245.7
47.5°	248.2	261.3	287.2	334.1	402.0	446.2	416.9	347.8	284.7	236.5	204.9
50°	230.9	243.8	269.7	316.0	379.3	411.5	369.7	303.1	245.3	205.4	180.3
52.5°	214.4	227.0	250.6	295.7	351.8	371.1	326.1	264.4	216.2	181.8	160.3
55°	191.2	200.8	222.0	265.2	307.1	311.6	265.9	214.3	174.6	150.6	135.9
57.5°	167.6	175.9	196.9	231.2	260.6	258.3	215.2	170.4	143.7	125.9	115.2
60°	152.3	160.4	178.9	208.3	230.5	222.8	183.1	147.1	124.2	111.1	102.6
62.5°	137.9	144.3	161.6	183.2	199.1	190.3	156.5	126.7	108.5	97.5	90.8
65°	117.2	122.4	136.2	147.5	156.3	147.8	119.8	99.1	86.0	78.3	73.7
67.5°	97.5	100.8	109.5	113.6	119.9	110.5	90.1	76.2	68.8	62.3	59.0
70°	85.1	87.5	92.1	95.5	97.0	87.5	72.3	62.2	55.9	51.3	49.3
72.5°	72.6	74.8	75.7	78.4	77.6	68.6	58.1	50.1	45.6	42.5	39.8
75°	55.5	56.5	55.5	54.4	52.0	45.8	38.6	34.5	31.2	29.7	28.8
77.5°	40.5	40.2	39.0	37.2	33.1	29.2	25.3	23.9	22.5	21.7	21.4
80°	31.2	30.4	29.3	26.5	23.1	20.3	19.4	18.5	17.9	17.0	16.8
82.5°	23.2	22.7	20.9	18.6	16.2	14.8	14.1	13.7	13.2	12.7	12.7
85°	12.4	11.8	9.7	8.5	8.2	7.8	7.6	7.6	6.8	6.7	6.7
87.5°	4.5	4.0	4.2	4.0	4.5	4.7	5.2	5.4	5.7	6.0	5.9
90°	2.5	4.3	6.1	7.8	9.8	12.1	14.4	16.7	19.0	19.6	20.4
92.5°	20.4	21.5	22.7	23.9	25.2	26.5	27.7	29.1	30.3	30.9	31.5
95°	47.8	49.1	50.4	51.6	52.9	54.3	55.7	57.1	58.5	59.3	59.9
97.5°	83.8	84.7	85.6	86.5	87.5	88.5	89.5	90.5	91.6	92.4	93.2
100°	108.6	109.6	110.7	111.8	112.7	113.6	114.5	115.3	116.2	116.8	117.3
102.5°	136.7	137.3	137.9	138.6	139.4	140.6	141.7	142.9	144.1	144.6	145.1
105°	178.2	178.6	179.0	179.4	180.3	181.9	183.5	185.1	186.6	186.6	186.6
107.5°	226.9	227.0	227.3	227.5	227.9	228.5	229.2	229.8	230.4	231.0	231.6
110°	257.4	257.7	258.0	258.4	258.7	259.1	259.4	259.8	260.2	260.9	261.6





TEST NUMBER: P332259-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	288.8	289.1	289.2	289.5	289.6	289.7	289.8	289.9	289.9	290.7	291.6
115°	336.6	337.2	337.6	338.2	338.3	337.9	337.5	337.2	336.8	337.1	337.2
117.5°	384.2	384.5	384.9	385.2	385.2	384.8	384.3	383.8	383.3	383.3	383.3
120°	414.6	415.7	416.8	417.8	417.9	417.0	416.1	415.3	414.4	414.2	414.0
122.5°	445.4	446.1	446.9	447.7	447.8	447.3	446.9	446.5	446.0	445.5	445.0
125°	492.4	492.9	493.5	493.9	494.1	493.7	493.4	493.0	492.7	491.9	491.2
127.5°	536.6	537.7	538.8	540.0	540.3	540.0	539.6	539.2	538.8	537.8	536.9
130°	566.0	567.4	568.8	570.2	570.7	570.1	569.6	569.1	568.5	567.8	567.1
132.5°	595.1	596.5	597.9	599.4	599.8	599.4	599.0	598.7	598.3	597.5	596.6
135°	639.2	640.2	641.3	642.4	642.8	642.6	642.5	642.3	642.1	641.4	640.7
137.5°	680.2	681.0	681.9	682.8	683.4	683.9	684.4	684.8	685.2	684.5	683.8
140°	708.6	709.5	710.3	711.2	711.8	711.9	712.1	712.3	712.5	712.3	712.1
142.5°	734.5	735.5	736.3	737.2	737.8	738.1	738.4	738.7	739.0	738.9	738.7
145°	774.5	774.8	775.2	775.5	776.0	776.5	777.1	777.6	778.1	777.9	777.8
147.5°	810.2	810.9	811.5	812.1	812.7	813.2	813.7	814.1	814.7	814.7	814.7
150°	834.6	835.0	835.3	835.7	836.0	836.4	836.7	837.1	837.4	837.4	837.4
152.5°	855.0	855.5	856.0	856.4	856.8	857.1	857.2	857.5	857.7	857.9	858.3
155°	886.5	886.5	886.5	886.5	886.5	886.7	886.8	887.1	887.2	888.0	888.7
157.5°	913.5	913.2	913.0	912.8	912.8	912.9	913.1	913.2	913.3	914.1	914.8
160°	930.3	930.0	929.7	929.3	929.2	929.2	929.2	929.2	929.2	930.0	930.9
162.5°	945.4	944.9	944.4	944.0	943.8	943.9	944.0	944.2	944.4	945.2	946.1
165°	965.0	964.5	963.9	963.5	963.1	963.1	963.1	963.1	963.1	964.2	965.3
167.5°	980.5	979.8	979.1	978.3	978.1	978.3	978.3	978.5	978.7	979.8	980.8
170°	989.4	988.6	987.9	987.2	986.9	986.9	986.9	986.9	986.9	988.1	989.4
172.5°	996.3	995.6	994.9	994.2	993.8	993.8	993.8	993.8	993.8	994.9	996.0
175°	1003.5	1002.8	1002.2	1001.5	1001.1	1001.1	1001.1	1001.1	1001.1	1002.2	1003.2
177.5°	1006.7	1006.2	1005.6	1005.0	1004.7	1004.7	1004.7	1004.7	1004.7	1005.6	1006.5
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6



TEST NUMBER: P332259-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	454.8	454.8	455.3	457.6	457.9	459.8	459.2
5°	499.8	503.3	504.6	510.2	513.4	514.9	512.0
7.5°	554.8	564.7	569.4	575.3	580.4	581.9	577.9
10°	595.0	605.4	614.0	619.4	624.4	627.7	631.9
12.5°	633.8	646.6	654.8	662.3	667.5	671.7	672.4
15°	676.0	695.2	709.8	720.6	725.9	728.6	727.5
17.5°	718.6	736.4	746.8	757.7	765.1	765.5	765.7
20°	742.7	760.0	772.1	780.1	788.5	788.1	790.0
22.5°	758.8	772.5	781.6	787.5	790.4	788.9	789.3
25°	766.3	770.4	768.7	759.3	756.9	748.2	749.7
27.5°	727.5	708.3	688.4	662.9	642.7	626.6	627.4
30°	674.8	640.8	602.1	569.6	540.4	532.3	514.9
32.5°	601.1	550.2	504.8	474.4	449.5	442.7	427.5
35°	476.2	426.7	380.0	352.0	340.9	325.3	325.2
37.5°	370.1	326.5	301.9	280.8	269.8	260.4	259.5
40°	311.3	277.4	258.7	243.6	232.7	225.7	224.0
42.5°	270.3	242.9	225.4	216.0	207.6	204.0	201.3
45°	220.7	202.2	190.1	181.6	177.8	175.0	173.5
47.5°	184.7	172.3	164.0	158.3	155.2	152.3	153.0
50°	165.0	154.9	148.8	143.4	141.0	138.9	139.2
52.5°	149.2	140.1	135.1	131.3	128.3	126.8	126.2
55°	126.6	120.9	115.9	113.1	111.5	109.5	108.9
57.5°	108.0	103.5	99.5	96.4	95.9	94.0	94.3
60°	95.6	91.9	88.6	86.9	85.6	84.0	84.5
62.5°	85.4	82.3	79.3	78.0	76.6	75.4	75.7
65°	69.9	67.0	65.1	64.4	63.8	63.3	62.7
67.5°	55.8	53.9	52.8	51.2	50.1	49.9	49.4
70°	46.9	44.4	42.5	40.4	39.8	39.7	39.8
72.5°	37.5	36.0	35.5	34.5	34.4	33.9	34.2
75°	28.2	27.6	27.3	26.5	26.5	26.5	26.5
77.5°	20.8	20.5	20.3	20.1	20.0	19.6	19.6
80°	16.2	16.1	15.7	15.7	15.5	15.7	15.5
82.5°	12.3	12.2	11.9	11.9	11.6	11.6	11.6
85°	6.3	6.1	6.5	6.1	6.3	5.9	6.3
87.5°	6.0	6.1	6.1	6.2	6.1	6.4	6.3
90°	21.1	21.8	22.3	22.7	23.1	23.4	23.7
92.5°	32.1	32.6	32.8	32.6	32.4	32.2	31.9
95°	60.6	61.3	61.7	61.7	61.7	61.7	61.7
97.5°	94.0	94.8	95.1	95.1	95.1	95.0	94.9
100°	117.8	118.4	118.8	119.1	119.5	119.9	120.2
102.5°	145.7	146.2	146.4	146.3	146.2	146.2	146.2
105°	186.6	186.6	186.8	187.1	187.5	187.8	188.2
107.5°	232.1	232.7	232.8	232.7	232.4	232.2	232.0
110°	262.3	263.0	263.2	262.8	262.4	262.1	261.7



TEST NUMBER: P332259-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	292.4	293.3	293.7	293.6	293.5	293.4	293.3
115°	337.4	337.5	337.5	337.4	337.2	337.1	336.8
117.5°	383.3	383.3	382.9	382.5	382.0	381.5	381.0
120°	413.8	413.7	413.4	413.0	412.7	412.3	412.0
122.5°	444.7	444.2	443.7	443.2	442.7	442.2	441.7
125°	490.5	489.8	489.1	488.5	487.7	487.0	486.3
127.5°	535.9	534.9	534.0	533.2	532.3	531.6	530.8
130°	566.4	565.8	564.7	563.6	562.3	561.1	559.8
132.5°	595.8	594.9	594.1	593.1	592.2	591.2	590.3
135°	640.0	639.3	638.7	638.4	638.0	637.7	637.4
137.5°	683.1	682.3	681.6	681.0	680.2	679.6	679.0
140°	711.9	711.8	711.1	709.9	708.6	707.4	706.2
142.5°	738.6	738.3	737.8	736.8	735.9	734.9	734.0
145°	777.6	777.4	777.0	776.3	775.5	774.8	774.1
147.5°	814.7	814.7	814.1	813.1	812.0	811.0	809.9
150°	837.4	837.4	836.9	835.8	834.8	833.7	832.7
152.5°	858.5	858.8	858.5	857.5	856.7	855.7	854.8
155°	889.4	890.0	889.8	888.6	887.3	886.1	884.9
157.5°	915.5	916.3	916.2	915.2	914.2	913.2	912.2
160°	931.8	932.6	932.7	932.1	931.4	930.7	929.9
162.5°	947.0	947.8	947.7	946.6	945.5	944.4	943.3
165°	966.3	967.3	967.3	966.1	964.8	963.6	962.3
167.5°	981.9	983.0	983.0	981.9	980.8	979.8	978.7
170°	990.5	991.8	991.8	990.5	989.4	988.1	986.9
172.5°	997.1	998.1	998.1	996.9	995.7	994.4	993.2
175°	1004.2	1005.4	1005.2	1004.0	1002.7	1001.6	1000.3
177.5°	1007.3	1008.1	1008.1	1007.1	1006.1	1005.1	1004.1
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6

(END OF REPORT)