

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332262-927

Luminaire Tested: **S123RDIP-S340D1025U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332262-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D1025U927-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3820.2 lumens  
Efficiency: N/A  
Efficacy: 102.4 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332262-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332262-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	74	62	60	58	46	45	43	31	30	30	23
2	85	78	72	67	75	70	65	61	54	51	48	40	38	37	28	26	25	20
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	25	23	22	17
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	15
5	65	54	46	40	58	48	42	37	38	33	30	29	26	23	20	18	16	13
6	60	48	40	35	53	43	37	32	34	30	26	26	23	20	18	16	15	11
7	55	43	36	30	49	39	33	28	31	26	23	24	20	18	17	14	13	10
8	51	39	32	27	45	35	29	25	28	24	20	22	18	16	15	13	12	9
9	47	36	29	24	42	32	26	22	26	21	18	20	17	14	14	12	10	8
10	44	33	26	21	39	30	24	19	24	19	16	18	15	13	13	11	10	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4899	4899	4899
5°	4917	4850	4878
10°	4889	4790	4773
15°	4837	4677	4628
20°	4765	4537	4431
25°	4691	4380	4240
30°	4593	4197	3967
35°	4491	4016	3720
40°	4398	3801	3413
45°	4276	3589	3136
50°	4141	3349	2825
55°	4003	3076	2535
60°	3877	2781	2217
65°	3713	2463	1897
70°	3509	2068	1533
75°	3211	1626	1443
80°	2858	1444	1327
85°	2421	1272	1186



TEST NUMBER: P332262-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.7	1.1
10°-20°	118.9	3.1
20°-30°	171.2	4.5
30°-40°	192.9	5.0
40°-50°	184.5	4.8
50°-60°	151.1	4.0
60°-70°	101.9	2.7
70°-80°	51.3	1.3
80°-90°	16.5	0.4
90°-100°	65.6	1.7
100°-110°	196.3	5.1
110°-120°	333.8	8.7
120°-130°	439.1	11.5
130°-140°	493.6	12.9
140°-150°	485.2	12.7
150°-160°	408.4	10.7
160°-170°	271.9	7.1
170°-180°	95.2	2.5
0°-30°	332.9	8.7
0°-40°	525.7	13.8
0°-60°	861.4	22.5
0°-90°	1031.1	27.0
90°-120°	595.7	15.6
90°-150°	2013.5	52.7
90°-180°	2789.0	73.0
0°-180°	3820.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	455	455	455	455	455	
5°	455	453	449	452	452	43
15°	434	430	420	418	415	122
25°	395	385	369	361	357	182
35°	342	328	306	290	283	214
45°	281	264	236	215	206	217
55°	213	195	164	143	135	191
65°	146	125	97	79	74	144
75°	77	59	39	36	35	82
85°	20	12	10	10	10	22
90°	1	9	19	22	24	4
95°	47	52	58	62	62	52
105°	178	180	187	187	188	191
115°	336	338	337	338	337	332
125°	492	494	493	489	486	438
135°	638	643	642	639	637	492
145°	774	776	778	777	774	483
155°	886	886	887	890	885	408
165°	966	963	963	967	962	272
175°	1004	1001	1001	1005	1000	95
180°	1007	1007	1007	1007	1007	



TEST NUMBER: P332262-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1
2.5°	456.6	456.3	456.1	455.8	455.6	455.0	454.2	453.4	452.7	451.9	452.6
5°	455.1	454.7	454.3	453.9	453.4	452.8	451.8	450.8	449.8	448.9	449.6
7.5°	450.9	450.4	450.0	449.6	449.2	448.3	447.0	445.8	444.4	443.1	443.5
10°	447.3	446.8	446.2	445.7	445.0	444.0	442.6	441.1	439.6	438.2	438.2
12.5°	442.4	441.7	441.1	440.5	439.8	438.6	436.7	435.0	433.2	431.3	431.3
15°	434.1	433.2	432.3	431.3	430.5	428.9	426.6	424.3	422.0	419.7	419.3
17.5°	423.7	422.6	421.6	420.5	419.5	417.5	414.5	411.6	408.8	405.8	405.0
20°	416.0	414.7	413.4	412.1	410.7	408.5	405.4	402.3	399.2	396.1	395.0
22.5°	407.4	405.9	404.4	402.9	401.4	399.0	395.7	392.4	389.0	385.7	384.4
25°	395.0	392.9	390.9	388.8	386.7	383.8	380.1	376.3	372.5	368.8	367.0
27.5°	379.9	377.6	375.3	373.0	370.7	367.6	363.4	359.1	354.9	350.7	348.3
30°	369.5	367.0	364.6	362.1	359.7	356.1	351.5	346.9	342.3	337.7	334.9
32.5°	359.2	356.3	353.6	350.8	348.0	344.2	339.3	334.5	329.6	324.7	321.7
35°	341.8	338.8	335.9	333.0	330.0	326.0	320.9	315.8	310.7	305.6	302.1
37.5°	324.2	320.9	317.7	314.4	311.1	306.7	301.3	295.9	290.5	285.0	281.1
40°	313.0	309.4	305.8	302.2	298.6	293.8	288.0	282.2	276.4	270.5	266.3
42.5°	300.3	296.7	293.1	289.5	285.9	281.1	275.0	269.0	263.0	257.0	252.3
45°	280.9	277.2	273.5	269.8	266.1	261.1	254.8	248.5	242.2	235.8	231.2
47.5°	261.5	257.5	253.3	249.3	245.3	240.1	233.8	227.4	221.2	214.8	209.8
50°	247.3	243.4	239.6	235.8	231.9	226.6	220.0	213.3	206.7	200.0	195.0
52.5°	234.6	230.4	226.2	222.0	217.9	212.5	205.9	199.3	192.7	186.2	180.9
55°	213.3	209.3	205.3	201.3	197.3	191.8	184.8	177.8	170.9	163.9	159.1
57.5°	193.7	189.3	185.0	180.5	176.2	170.5	163.5	156.5	149.5	142.5	138.0
60°	180.1	175.6	171.1	166.6	162.1	156.5	149.6	142.8	136.0	129.2	124.8
62.5°	166.5	162.0	157.5	153.0	148.5	142.8	136.0	129.2	122.4	115.6	111.5
65°	145.8	141.3	136.8	132.3	127.8	122.3	115.9	109.5	103.1	96.7	92.7
67.5°	125.1	120.5	115.9	111.4	106.8	101.5	95.3	89.2	83.0	76.9	73.9
70°	111.5	107.0	102.6	98.2	93.8	88.6	82.9	77.2	71.5	65.7	62.8
72.5°	97.9	93.6	89.2	84.8	80.4	75.7	70.4	65.2	60.0	54.7	52.4
75°	77.2	73.2	69.2	65.4	61.4	57.2	52.7	48.2	43.6	39.1	38.3
77.5°	58.2	54.7	51.1	47.5	44.0	40.8	37.9	34.9	32.1	29.2	28.8
80°	46.1	42.8	39.5	36.0	32.7	30.2	28.4	26.7	25.0	23.3	23.0
82.5°	34.6	31.7	28.8	25.9	23.0	21.2	20.4	19.6	18.8	17.9	17.7
85°	19.6	17.7	15.9	14.2	12.4	11.3	11.1	10.9	10.6	10.3	10.1
87.5°	7.2	6.9	6.5	6.1	5.8	5.8	6.3	6.7	7.2	7.6	7.7
90°	0.8	2.5	4.3	6.1	7.8	9.8	12.1	14.4	16.7	19.0	19.6
92.5°	19.2	20.4	21.5	22.7	23.9	25.2	26.5	27.7	29.1	30.3	30.9
95°	46.7	47.8	49.1	50.4	51.6	52.9	54.3	55.7	57.1	58.5	59.3
97.5°	82.9	83.8	84.7	85.6	86.5	87.5	88.5	89.5	90.5	91.6	92.4
100°	107.6	108.6	109.6	110.7	111.8	112.7	113.6	114.5	115.3	116.2	116.8
102.5°	136.0	136.7	137.3	137.9	138.6	139.4	140.6	141.7	142.9	144.1	144.6
105°	177.9	178.2	178.6	179.0	179.4	180.3	181.9	183.5	185.1	186.6	186.6
107.5°	226.6	226.9	227.0	227.3	227.5	227.9	228.5	229.2	229.8	230.4	231.0
110°	257.0	257.4	257.7	258.0	258.4	258.7	259.1	259.4	259.8	260.2	260.9



TEST NUMBER: P332262-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	288.6	288.8	289.1	289.2	289.5	289.6	289.7	289.8	289.9	289.9	290.7
115°	336.0	336.6	337.2	337.6	338.2	338.3	337.9	337.5	337.2	336.8	337.1
117.5°	383.8	384.2	384.5	384.9	385.2	385.2	384.8	384.3	383.8	383.3	383.3
120°	413.6	414.6	415.7	416.8	417.8	417.9	417.0	416.1	415.3	414.4	414.2
122.5°	444.6	445.4	446.1	446.9	447.7	447.8	447.3	446.9	446.5	446.0	445.5
125°	491.9	492.4	492.9	493.5	493.9	494.1	493.7	493.4	493.0	492.7	491.9
127.5°	535.5	536.6	537.7	538.8	540.0	540.3	540.0	539.6	539.2	538.8	537.8
130°	564.6	566.0	567.4	568.8	570.2	570.7	570.1	569.6	569.1	568.5	567.8
132.5°	593.7	595.1	596.5	597.9	599.4	599.8	599.4	599.0	598.7	598.3	597.5
135°	638.2	639.2	640.2	641.3	642.4	642.8	642.6	642.5	642.3	642.1	641.4
137.5°	679.3	680.2	681.0	681.9	682.8	683.4	683.9	684.4	684.8	685.2	684.5
140°	707.7	708.6	709.5	710.3	711.2	711.8	711.9	712.1	712.3	712.5	712.3
142.5°	733.6	734.5	735.5	736.3	737.2	737.8	738.1	738.4	738.7	739.0	738.9
145°	774.1	774.5	774.8	775.2	775.5	776.0	776.5	777.1	777.6	778.1	777.9
147.5°	809.6	810.2	810.9	811.5	812.1	812.7	813.2	813.7	814.1	814.7	814.7
150°	834.2	834.6	835.0	835.3	835.7	836.0	836.4	836.7	837.1	837.4	837.4
152.5°	854.5	855.0	855.5	856.0	856.4	856.8	857.1	857.2	857.5	857.7	857.9
155°	886.5	886.5	886.5	886.5	886.5	886.5	886.7	886.8	887.1	887.2	888.0
157.5°	913.6	913.5	913.2	913.0	912.8	912.8	912.9	913.1	913.2	913.3	914.1
160°	930.7	930.3	930.0	929.7	929.3	929.2	929.2	929.2	929.2	929.2	930.0
162.5°	945.9	945.4	944.9	944.4	944.0	943.8	943.9	944.0	944.2	944.4	945.2
165°	965.5	965.0	964.5	963.9	963.5	963.1	963.1	963.1	963.1	963.1	964.2
167.5°	981.2	980.5	979.8	979.1	978.3	978.1	978.3	978.3	978.5	978.7	979.8
170°	990.1	989.4	988.6	987.9	987.2	986.9	986.9	986.9	986.9	986.9	988.1
172.5°	997.0	996.3	995.6	994.9	994.2	993.8	993.8	993.8	993.8	993.8	994.9
175°	1004.2	1003.5	1002.8	1002.2	1001.5	1001.1	1001.1	1001.1	1001.1	1001.1	1002.2
177.5°	1007.3	1006.7	1006.2	1005.6	1005.0	1004.7	1004.7	1004.7	1004.7	1004.7	1005.6
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6



TEST NUMBER: P332262-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1
2.5°	453.3	454.0	454.8	455.0	455.0	454.8	454.6	454.6
5°	450.4	451.1	451.8	452.1	451.9	451.8	451.6	451.5
7.5°	444.0	444.4	444.8	444.9	444.6	444.3	444.0	443.8
10°	438.3	438.4	438.5	438.3	437.9	437.5	437.0	436.7
12.5°	431.3	431.2	431.2	430.9	430.4	429.9	429.4	429.0
15°	418.8	418.4	418.0	417.6	417.0	416.4	415.8	415.3
17.5°	404.1	403.2	402.3	401.5	400.6	399.7	398.9	398.1
20°	394.0	392.8	391.8	390.8	389.8	388.8	387.9	386.8
22.5°	383.1	381.8	380.4	379.3	378.3	377.5	376.5	375.7
25°	365.3	363.6	361.9	360.5	359.7	358.8	357.8	357.0
27.5°	345.9	343.6	341.2	339.3	337.9	336.5	335.2	333.7
30°	332.2	329.4	326.6	324.6	323.2	321.9	320.6	319.2
32.5°	318.6	315.6	312.5	310.3	309.0	307.6	306.2	304.8
35°	298.6	295.0	291.5	289.0	287.6	286.1	284.6	283.1
37.5°	277.0	273.0	269.0	266.1	264.3	262.4	260.6	258.8
40°	262.1	257.8	253.5	250.4	248.5	246.7	244.8	242.9
42.5°	247.6	243.0	238.4	235.2	233.5	231.8	230.1	228.4
45°	226.5	221.8	217.1	213.8	211.9	209.9	207.9	206.0
47.5°	204.6	199.6	194.5	191.1	189.3	187.6	185.8	184.0
50°	189.9	184.8	179.7	176.3	174.4	172.5	170.6	168.7
52.5°	175.6	170.3	165.1	161.6	159.9	158.2	156.5	154.8
55°	154.4	149.6	144.9	141.6	140.1	138.4	136.7	135.1
57.5°	133.5	129.0	124.5	121.5	120.2	118.7	117.4	116.0
60°	120.3	115.9	111.5	108.5	107.2	105.8	104.4	103.0
62.5°	107.3	103.1	98.9	96.1	94.7	93.2	91.7	90.3
65°	88.6	84.7	80.6	78.2	77.2	76.4	75.5	74.5
67.5°	70.9	67.9	64.9	62.9	61.9	61.0	60.0	59.1
70°	60.0	57.1	54.2	52.4	51.4	50.5	49.6	48.7
72.5°	50.1	47.8	45.4	44.0	43.6	43.3	42.9	42.5
75°	37.5	36.7	35.8	35.3	35.2	35.0	34.9	34.7
77.5°	28.3	27.8	27.4	27.1	26.9	26.8	26.6	26.5
80°	22.7	22.5	22.3	22.1	21.9	21.7	21.5	21.4
82.5°	17.4	17.2	17.0	16.8	16.8	16.7	16.7	16.7
85°	10.0	9.8	9.7	9.6	9.6	9.6	9.6	9.6
87.5°	7.8	7.8	7.9	8.0	8.0	8.0	8.0	8.0
90°	20.4	21.1	21.8	22.3	22.7	23.1	23.4	23.7
92.5°	31.5	32.1	32.6	32.8	32.6	32.4	32.2	31.9
95°	59.9	60.6	61.3	61.7	61.7	61.7	61.7	61.7
97.5°	93.2	94.0	94.8	95.1	95.1	95.1	95.0	94.9
100°	117.3	117.8	118.4	118.8	119.1	119.5	119.9	120.2
102.5°	145.1	145.7	146.2	146.4	146.3	146.2	146.2	146.2
105°	186.6	186.6	186.6	186.8	187.1	187.5	187.8	188.2
107.5°	231.6	232.1	232.7	232.8	232.7	232.4	232.2	232.0
110°	261.6	262.3	263.0	263.2	262.8	262.4	262.1	261.7





TEST NUMBER: P332262-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	291.6	292.4	293.3	293.7	293.6	293.5	293.4	293.3
115°	337.2	337.4	337.5	337.5	337.4	337.2	337.1	336.8
117.5°	383.3	383.3	383.3	382.9	382.5	382.0	381.5	381.0
120°	414.0	413.8	413.7	413.4	413.0	412.7	412.3	412.0
122.5°	445.0	444.7	444.2	443.7	443.2	442.7	442.2	441.7
125°	491.2	490.5	489.8	489.1	488.5	487.7	487.0	486.3
127.5°	536.9	535.9	534.9	534.0	533.2	532.3	531.6	530.8
130°	567.1	566.4	565.8	564.7	563.6	562.3	561.1	559.8
132.5°	596.6	595.8	594.9	594.1	593.1	592.2	591.2	590.3
135°	640.7	640.0	639.3	638.7	638.4	638.0	637.7	637.4
137.5°	683.8	683.1	682.3	681.6	681.0	680.2	679.6	679.0
140°	712.1	711.9	711.8	711.1	709.9	708.6	707.4	706.2
142.5°	738.7	738.6	738.3	737.8	736.8	735.9	734.9	734.0
145°	777.8	777.6	777.4	777.0	776.3	775.5	774.8	774.1
147.5°	814.7	814.7	814.7	814.1	813.1	812.0	811.0	809.9
150°	837.4	837.4	837.4	836.9	835.8	834.8	833.7	832.7
152.5°	858.3	858.5	858.8	858.5	857.5	856.7	855.7	854.8
155°	888.7	889.4	890.0	889.8	888.6	887.3	886.1	884.9
157.5°	914.8	915.5	916.3	916.2	915.2	914.2	913.2	912.2
160°	930.9	931.8	932.6	932.7	932.1	931.4	930.7	929.9
162.5°	946.1	947.0	947.8	947.7	946.6	945.5	944.4	943.3
165°	965.3	966.3	967.3	967.3	966.1	964.8	963.6	962.3
167.5°	980.8	981.9	983.0	983.0	981.9	980.8	979.8	978.7
170°	989.4	990.5	991.8	991.8	990.5	989.4	988.1	986.9
172.5°	996.0	997.1	998.1	998.1	996.9	995.7	994.4	993.2
175°	1003.2	1004.2	1005.4	1005.2	1004.0	1002.7	1001.6	1000.3
177.5°	1006.5	1007.3	1008.1	1008.1	1007.1	1006.1	1005.1	1004.1
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6

(END OF REPORT)