

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332263-927

Luminaire Tested: **S123RDIP-S340D1025U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332263-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D1025U927-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3970.0 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332263-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332263-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26
1	93	88	85	81	82	79	76	73	61	59	58	45	44	43	30	30	29	22
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	68	61	55	50	48	44	40	35	33	31	24	22	21	16
4	70	60	53	47	63	54	48	43	42	38	34	32	29	26	21	20	18	14
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	19	17	16	12
6	59	48	40	35	53	43	37	32	34	29	26	26	22	20	18	16	14	11
7	55	43	36	30	49	39	32	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	36	28	24	42	32	26	22	26	21	18	19	16	14	14	12	10	8
10	44	32	26	21	39	29	23	19	23	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4899	4899	4899
5°	4917	4850	4878
10°	4889	4790	4773
15°	4837	4677	4628
20°	4765	4537	4431
25°	4691	4380	4240
30°	4593	4197	3967
35°	4491	4016	3720
40°	4398	3801	3413
45°	4276	3589	3136
50°	4141	3349	2825
55°	4003	3076	2535
60°	3877	2781	2217
65°	3713	2463	1897
70°	3509	2068	1533
75°	3211	1626	1443
80°	2858	1444	1327
85°	2421	1272	1186



TEST NUMBER: P332263-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.7	1.1
10°-20°	118.9	3.0
20°-30°	171.2	4.3
30°-40°	192.9	4.9
40°-50°	184.5	4.6
50°-60°	151.1	3.8
60°-70°	101.9	2.6
70°-80°	51.3	1.3
80°-90°	16.6	0.4
90°-100°	217.4	5.5
100°-110°	615.6	15.5
110°-120°	605.5	15.3
120°-130°	483.0	12.2
130°-140°	380.8	9.6
140°-150°	284.2	7.2
150°-160°	198.1	5.0
160°-170°	116.4	2.9
170°-180°	37.9	1.0
0°-30°	332.9	8.4
0°-40°	525.7	13.2
0°-60°	861.4	21.7
0°-90°	1031.2	26.0
90°-120°	1438.5	36.2
90°-150°	2586.5	65.2
90°-180°	2939.0	74.0
0°-180°	3970.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	455	455	455	455	455	
5°	455	453	449	452	452	43
15°	434	430	420	418	415	122
25°	395	385	369	361	357	182
35°	342	328	306	290	283	214
45°	281	264	236	215	206	217
55°	213	195	164	143	135	191
65°	146	125	97	79	74	144
75°	77	59	39	36	35	82
85°	20	12	10	10	10	22
90°	2	10	20	22	23	3
95°	27	87	469	137	92	29
105°	92	136	636	1112	1006	97
115°	162	202	486	1066	1223	160
125°	225	266	454	822	965	200
135°	264	315	448	677	782	204
145°	301	345	442	556	611	189
155°	342	369	428	486	507	157
165°	374	385	410	434	442	105
175°	390	390	393	398	398	37
180°	391	391	391	391	391	



TEST NUMBER: P332263-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1
2.5°	456.6	456.3	456.1	455.8	455.6	455.0	454.2	453.4	452.7	451.9	452.6
5°	455.1	454.7	454.3	453.9	453.4	452.8	451.8	450.8	449.8	448.9	449.6
7.5°	450.9	450.4	450.0	449.6	449.2	448.3	447.0	445.8	444.4	443.1	443.5
10°	447.3	446.8	446.2	445.7	445.0	444.0	442.6	441.1	439.6	438.2	438.2
12.5°	442.4	441.7	441.1	440.5	439.8	438.6	436.7	435.0	433.2	431.3	431.3
15°	434.1	433.2	432.3	431.3	430.5	428.9	426.6	424.3	422.0	419.7	419.3
17.5°	423.7	422.6	421.6	420.5	419.5	417.5	414.5	411.6	408.8	405.8	405.0
20°	416.0	414.7	413.4	412.1	410.7	408.5	405.4	402.3	399.2	396.1	395.0
22.5°	407.4	405.9	404.4	402.9	401.4	399.0	395.7	392.4	389.0	385.7	384.4
25°	395.0	392.9	390.9	388.8	386.7	383.8	380.1	376.3	372.5	368.8	367.0
27.5°	379.9	377.6	375.3	373.0	370.7	367.6	363.4	359.1	354.9	350.7	348.3
30°	369.5	367.0	364.6	362.1	359.7	356.1	351.5	346.9	342.3	337.7	334.9
32.5°	359.2	356.3	353.6	350.8	348.0	344.2	339.3	334.5	329.6	324.7	321.7
35°	341.8	338.8	335.9	333.0	330.0	326.0	320.9	315.8	310.7	305.6	302.1
37.5°	324.2	320.9	317.7	314.4	311.1	306.7	301.3	295.9	290.5	285.0	281.1
40°	313.0	309.4	305.8	302.2	298.6	293.8	288.0	282.2	276.4	270.5	266.3
42.5°	300.3	296.7	293.1	289.5	285.9	281.1	275.0	269.0	263.0	257.0	252.3
45°	280.9	277.2	273.5	269.8	266.1	261.1	254.8	248.5	242.2	235.8	231.2
47.5°	261.5	257.5	253.3	249.3	245.3	240.1	233.8	227.4	221.2	214.8	209.8
50°	247.3	243.4	239.6	235.8	231.9	226.6	220.0	213.3	206.7	200.0	195.0
52.5°	234.6	230.4	226.2	222.0	217.9	212.5	205.9	199.3	192.7	186.2	180.9
55°	213.3	209.3	205.3	201.3	197.3	191.8	184.8	177.8	170.9	163.9	159.1
57.5°	193.7	189.3	185.0	180.5	176.2	170.5	163.5	156.5	149.5	142.5	138.0
60°	180.1	175.6	171.1	166.6	162.1	156.5	149.6	142.8	136.0	129.2	124.8
62.5°	166.5	162.0	157.5	153.0	148.5	142.8	136.0	129.2	122.4	115.6	111.5
65°	145.8	141.3	136.8	132.3	127.8	122.3	115.9	109.5	103.1	96.7	92.7
67.5°	125.1	120.5	115.9	111.4	106.8	101.5	95.3	89.2	83.0	76.9	73.9
70°	111.5	107.0	102.6	98.2	93.8	88.6	82.9	77.2	71.5	65.7	62.8
72.5°	97.9	93.6	89.2	84.8	80.4	75.7	70.4	65.2	60.0	54.7	52.4
75°	77.2	73.2	69.2	65.4	61.4	57.2	52.7	48.2	43.6	39.1	38.3
77.5°	58.2	54.7	51.1	47.5	44.0	40.8	37.9	34.9	32.1	29.2	28.8
80°	46.1	42.8	39.5	36.0	32.7	30.2	28.4	26.7	25.0	23.3	23.0
82.5°	34.6	31.7	28.8	25.9	23.0	21.2	20.4	19.6	18.8	17.9	17.7
85°	19.6	17.7	15.9	14.2	12.4	11.3	11.1	10.9	10.6	10.3	10.1
87.5°	7.4	7.0	6.6	6.3	5.9	5.9	6.3	6.8	7.3	7.8	7.6
90°	1.6	3.2	4.8	7.1	8.7	10.3	12.7	15.1	17.4	19.8	19.0
92.5°	9.8	14.6	21.2	27.3	34.0	45.7	66.4	100.4	133.8	121.6	91.7
95°	26.9	29.2	37.9	51.4	71.9	102.8	170.0	287.8	417.5	468.9	380.3
97.5°	45.9	46.7	53.5	65.1	85.4	118.7	183.0	315.8	532.0	726.7	777.4
100°	58.5	59.3	64.9	75.9	94.9	125.7	181.1	298.1	506.0	748.8	904.6
102.5°	71.8	73.2	78.1	88.6	105.7	134.0	183.6	282.9	468.1	707.7	910.9
105°	91.7	94.1	98.9	108.4	123.3	147.9	190.6	272.0	421.4	635.7	862.7
107.5°	112.9	115.3	119.9	129.2	143.3	166.0	203.5	271.2	391.7	572.2	778.2
110°	128.1	130.5	134.4	143.1	156.5	178.7	214.3	274.4	380.3	536.1	725.1



TEST NUMBER: P332263-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	142.0	144.4	148.4	157.0	170.5	192.0	225.1	280.7	374.0	512.1	678.9
115°	162.1	165.2	170.0	177.9	191.4	212.7	242.7	291.0	371.6	486.3	623.1
117.5°	182.2	185.8	189.8	197.0	212.1	231.9	261.6	304.6	373.0	471.1	589.4
120°	196.1	198.4	202.4	210.3	225.4	245.1	273.6	314.7	375.6	464.1	571.7
122.5°	208.1	210.5	214.4	223.0	237.4	258.4	286.2	324.2	380.0	459.7	557.1
125°	225.4	227.0	231.7	240.3	255.4	276.8	304.4	339.2	386.7	453.9	538.5
127.5°	238.5	240.8	246.7	255.6	272.2	293.5	320.3	351.6	394.3	451.1	522.0
130°	246.7	249.1	256.2	265.7	282.3	303.6	329.7	359.8	399.3	449.2	513.2
132.5°	253.0	256.0	263.8	275.2	291.8	312.5	337.9	367.4	403.1	448.5	504.9
135°	264.1	267.3	276.0	287.8	304.4	325.7	350.3	377.2	408.8	447.6	494.2
137.5°	274.6	277.9	286.4	299.0	315.5	335.3	358.9	384.4	412.6	445.8	484.9
140°	281.5	285.4	293.3	306.0	321.9	341.6	364.6	388.2	415.1	445.2	479.2
142.5°	289.1	292.4	301.0	312.4	328.1	346.7	369.0	392.1	417.0	443.9	474.1
145°	301.3	303.6	310.8	322.7	336.0	354.3	374.8	396.2	418.3	442.0	467.3
147.5°	313.6	315.1	322.0	332.2	345.2	360.8	379.5	398.7	418.3	439.0	460.7
150°	321.9	322.7	328.9	339.2	350.3	364.6	382.7	399.3	418.3	436.5	456.2
152.5°	330.0	330.2	336.5	345.5	355.4	369.0	384.6	400.6	416.4	433.3	451.2
155°	342.4	342.4	347.1	355.1	363.8	374.8	388.2	400.9	414.3	427.8	443.6
157.5°	352.2	352.8	356.6	363.6	371.0	379.5	390.3	401.7	411.7	422.9	435.1
160°	359.8	359.8	363.0	369.2	374.8	382.7	392.2	401.7	410.4	419.1	429.4
162.5°	365.5	365.5	368.0	373.0	378.0	384.6	392.8	401.1	407.9	415.3	423.7
165°	374.0	373.2	374.8	378.7	381.9	387.5	393.8	399.3	404.1	409.6	415.9
167.5°	380.5	379.5	380.3	383.3	385.6	389.0	393.6	398.1	400.3	403.9	408.5
170°	384.3	382.7	383.5	385.9	387.5	389.0	393.0	396.2	397.8	400.1	404.1
172.5°	386.8	385.9	386.0	387.8	388.7	389.7	393.0	395.5	395.9	397.0	399.7
175°	389.8	389.0	388.2	389.8	389.8	390.6	392.2	393.8	393.0	393.0	394.6
177.5°	391.3	390.6	390.0	390.6	390.6	390.6	391.3	392.5	391.3	390.6	391.3
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6



TEST NUMBER: P332263-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1
2.5°	453.3	454.0	454.8	455.0	455.0	454.8	454.6	454.6
5°	450.4	451.1	451.8	452.1	451.9	451.8	451.6	451.5
7.5°	444.0	444.4	444.8	444.9	444.6	444.3	444.0	443.8
10°	438.3	438.4	438.5	438.3	437.9	437.5	437.0	436.7
12.5°	431.3	431.2	431.2	430.9	430.4	429.9	429.4	429.0
15°	418.8	418.4	418.0	417.6	417.0	416.4	415.8	415.3
17.5°	404.1	403.2	402.3	401.5	400.6	399.7	398.9	398.1
20°	394.0	392.8	391.8	390.8	389.8	388.8	387.9	386.8
22.5°	383.1	381.8	380.4	379.3	378.3	377.5	376.5	375.7
25°	365.3	363.6	361.9	360.5	359.7	358.8	357.8	357.0
27.5°	345.9	343.6	341.2	339.3	337.9	336.5	335.2	333.7
30°	332.2	329.4	326.6	324.6	323.2	321.9	320.6	319.2
32.5°	318.6	315.6	312.5	310.3	309.0	307.6	306.2	304.8
35°	298.6	295.0	291.5	289.0	287.6	286.1	284.6	283.1
37.5°	277.0	273.0	269.0	266.1	264.3	262.4	260.6	258.8
40°	262.1	257.8	253.5	250.4	248.5	246.7	244.8	242.9
42.5°	247.6	243.0	238.4	235.2	233.5	231.8	230.1	228.4
45°	226.5	221.8	217.1	213.8	211.9	209.9	207.9	206.0
47.5°	204.6	199.6	194.5	191.1	189.3	187.6	185.8	184.0
50°	189.9	184.8	179.7	176.3	174.4	172.5	170.6	168.7
52.5°	175.6	170.3	165.1	161.6	159.9	158.2	156.5	154.8
55°	154.4	149.6	144.9	141.6	140.1	138.4	136.7	135.1
57.5°	133.5	129.0	124.5	121.5	120.2	118.7	117.4	116.0
60°	120.3	115.9	111.5	108.5	107.2	105.8	104.4	103.0
62.5°	107.3	103.1	98.9	96.1	94.7	93.2	91.7	90.3
65°	88.6	84.7	80.6	78.2	77.2	76.4	75.5	74.5
67.5°	70.9	67.9	64.9	62.9	61.9	61.0	60.0	59.1
70°	60.0	57.1	54.2	52.4	51.4	50.5	49.6	48.7
72.5°	50.1	47.8	45.4	44.0	43.6	43.3	42.9	42.5
75°	37.5	36.7	35.8	35.3	35.2	35.0	34.9	34.7
77.5°	28.3	27.8	27.4	27.1	26.9	26.8	26.6	26.5
80°	22.7	22.5	22.3	22.1	21.9	21.7	21.5	21.4
82.5°	17.4	17.2	17.0	16.8	16.8	16.7	16.7	16.7
85°	10.0	9.8	9.7	9.6	9.6	9.6	9.6	9.6
87.5°	7.7	7.8	7.8	8.1	7.8	8.0	8.1	7.8
90°	19.8	20.6	21.4	22.9	22.1	22.9	23.7	22.9
92.5°	66.5	52.8	46.7	42.5	41.1	38.7	39.5	38.1
95°	284.6	193.0	151.1	122.6	107.6	100.4	94.9	91.7
97.5°	709.6	568.4	466.4	371.8	313.5	277.9	256.5	249.7
100°	932.3	868.2	775.7	663.5	583.6	525.9	495.0	495.8
102.5°	1006.3	1004.2	950.3	879.2	817.0	771.3	745.5	727.3
105°	1027.9	1107.1	1122.0	1101.5	1065.1	1035.1	1009.8	1005.8
107.5°	965.7	1094.1	1163.3	1191.5	1192.2	1182.0	1173.5	1166.2
110°	906.2	1051.7	1151.3	1206.7	1228.8	1235.2	1233.6	1232.0



TEST NUMBER: P332263-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	847.3	996.0	1107.6	1178.8	1219.3	1238.9	1244.9	1245.2
115°	769.4	907.0	1023.2	1109.4	1168.7	1203.5	1219.3	1223.3
117.5°	713.0	831.7	936.0	1023.5	1085.4	1125.2	1148.0	1153.3
120°	683.2	790.0	884.9	964.7	1027.1	1071.4	1090.4	1095.2
122.5°	659.8	756.5	844.4	918.5	974.1	1013.9	1034.7	1040.8
125°	628.7	714.9	790.8	854.0	904.6	939.4	959.2	964.7
127.5°	601.4	678.3	746.8	804.3	849.4	879.2	897.0	902.1
130°	584.4	655.5	719.5	773.3	815.2	843.8	860.3	866.6
132.5°	568.5	634.0	693.6	744.9	784.3	812.7	827.4	831.9
135°	547.2	603.3	654.7	699.8	738.6	762.2	776.5	782.0
137.5°	527.8	573.8	618.1	657.1	689.7	713.8	725.7	729.4
140°	516.3	556.7	594.6	628.7	658.7	680.8	693.5	692.7
142.5°	505.6	540.3	573.1	602.7	628.4	647.9	659.3	658.5
145°	492.7	518.7	544.0	567.0	586.7	603.3	609.7	611.2
147.5°	482.0	502.7	523.2	539.5	554.4	565.7	571.7	572.4
150°	474.4	492.7	509.2	524.3	536.1	544.8	549.5	549.5
152.5°	467.5	483.2	497.9	510.3	519.7	527.8	530.6	530.6
155°	457.0	469.7	481.6	491.1	498.2	504.5	506.0	506.8
157.5°	446.0	456.5	465.7	473.2	479.3	484.1	485.4	485.2
160°	439.7	448.4	456.2	461.8	467.3	472.1	472.1	471.3
162.5°	432.1	439.5	446.8	451.7	455.3	459.4	459.4	458.6
165°	422.2	427.0	432.5	436.5	439.7	442.8	442.0	442.0
167.5°	413.7	417.3	420.5	423.3	424.8	427.0	426.2	426.2
170°	408.1	410.4	413.5	415.1	415.9	417.5	416.7	416.7
172.5°	403.0	404.7	407.3	408.2	408.4	410.0	408.5	407.9
175°	396.2	397.0	398.5	398.5	398.5	399.3	398.5	397.8
177.5°	391.9	392.5	393.2	393.2	392.5	393.2	391.9	391.9
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6

(END OF REPORT)