

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332009

Luminaire Tested: **S123DIP-S1000D585U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332009  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1000D585U835-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 585 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6582.4 lumens  
Efficiency: N/A  
Efficacy: 134.9 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 48.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332009

CATALOG NUMBER: S123DIP-S1000D585U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332009

CATALOG NUMBER: S123DIP-S1000D585U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	62	61	59	55
2	93	85	79	74	87	80	75	70	71	67	63	63	60	57	55	53	50	47
3	85	75	68	62	79	71	64	59	63	58	54	56	52	48	49	46	43	40
4	78	67	59	53	73	63	56	50	56	51	46	50	45	42	44	40	38	34
5	71	60	52	45	67	57	49	44	50	45	40	45	40	36	40	36	33	30
6	66	54	46	40	62	51	43	38	46	40	35	41	36	32	36	32	29	26
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	33	29	26	23
8	57	44	36	31	53	42	35	30	38	32	28	34	29	25	30	26	23	21
9	53	40	33	28	50	39	32	27	35	29	25	31	26	23	28	24	21	19
10	49	37	30	25	47	35	29	24	32	26	22	29	24	21	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	15118	15118	15118	15118
5°	18029	15183	13456	15183
10°	22566	15106	12153	15106
15°	27679	14985	11314	14985
20°	32972	14795	10772	14795
25°	35011	14563	10652	14563
30°	30009	14395	10708	14395
35°	20871	14155	10820	14155
40°	15719	13874	10786	13874
45°	13052	13457	10648	13457
50°	11692	12603	10551	12603
55°	10931	11684	10421	11684
60°	10254	10723	10314	10723
65°	9638	9775	9984	9775
70°	9039	8696	9508	8696
75°	8093	7615	8717	7615
80°	7085	6242	7507	6242
85°	5545	4533	5039	4533



TEST NUMBER: P332009

CATALOG NUMBER: S123DIP-S1000D585U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	138.4	2.1
10°-20°	443.6	6.7
20°-30°	744.6	11.3
30°-40°	843.1	12.8
40°-50°	756.1	11.5
50°-60°	610.1	9.3
60°-70°	425.2	6.5
70°-80°	223.5	3.4
80°-90°	56.8	0.9
90°-100°	27.9	0.4
100°-110°	133.0	2.0
110°-120°	319.5	4.9
120°-130°	406.9	6.2
130°-140°	434.7	6.6
140°-150°	406.5	6.2
150°-160°	327.9	5.0
160°-170°	211.6	3.2
170°-180°	72.9	1.1
0°-30°	1326.6	20.2
0°-40°	2169.7	33.0
0°-60°	3535.9	53.7
0°-90°	4241.3	64.4
90°-120°	480.5	7.3
90°-150°	1728.6	26.3
90°-180°	2341.0	35.6
0°-180°	6582.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1404	1404	1404	1404	1404	
5°	1669	1405	1245	1405	1669	173
15°	2484	1345	1015	1345	2484	717
25°	2948	1226	897	1226	2948	1293
35°	1588	1077	823	1077	1588	1032
45°	857	884	700	884	857	678
55°	582	623	555	623	582	523
65°	378	384	392	384	378	377
75°	195	183	210	183	195	208
85°	45	37	41	37	45	54
90°	17	1	17	1	17	10
95°	22	35	22	35	22	18
105°	25	170	25	170	25	57
115°	335	319	335	319	335	310
125°	459	449	459	449	459	410
135°	565	560	565	560	565	436
145°	652	646	652	646	652	407
155°	710	711	710	711	710	327
165°	748	750	748	750	748	211
175°	765	768	765	768	765	73
180°	768	768	768	768	768	



TEST NUMBER: P332009

CATALOG NUMBER: S123DIP-S1000D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1490.5	1489.5	1486.7	1488.9	1484.6	1478.6	1478.0	1472.6	1456.8	1455.7	1451.4
5°	1668.6	1663.1	1662.4	1661.8	1652.2	1639.3	1614.8	1612.8	1580.1	1563.8	1544.0
7.5°	1899.1	1902.0	1892.0	1883.3	1854.2	1835.0	1808.7	1775.1	1735.0	1694.3	1667.2
10°	2064.6	2087.1	2059.2	2040.1	2022.4	1989.1	1950.3	1902.0	1853.7	1797.2	1754.3
12.5°	2242.1	2253.1	2247.5	2229.6	2202.1	2151.3	2082.6	2029.4	1984.9	1890.8	1852.8
15°	2483.8	2525.3	2498.8	2437.5	2438.9	2390.6	2300.7	2202.1	2149.7	2067.3	1955.1
17.5°	2741.3	2746.5	2735.2	2684.1	2650.1	2583.7	2500.8	2406.2	2300.1	2200.4	2081.4
20°	2878.5	2874.4	2850.6	2824.0	2765.5	2713.8	2623.3	2517.8	2381.7	2283.7	2153.8
22.5°	2954.7	2947.9	2936.6	2914.4	2865.7	2810.2	2728.9	2613.6	2484.1	2349.1	2198.9
25°	2947.9	2956.7	2958.1	2952.0	2935.0	2901.6	2837.6	2745.8	2616.5	2443.0	2286.5
27.5°	2681.1	2693.7	2730.0	2762.3	2798.3	2835.1	2830.2	2784.6	2688.9	2539.0	2347.7
30°	2414.4	2387.2	2454.5	2539.6	2597.4	2699.5	2756.7	2760.1	2706.3	2577.7	2391.2
32.5°	2044.2	2074.1	2103.9	2208.6	2335.0	2449.6	2563.4	2655.0	2665.5	2579.9	2416.8
35°	1588.3	1625.7	1680.1	1734.6	1870.7	1987.7	2187.8	2362.0	2500.8	2519.2	2419.1
37.5°	1279.9	1298.4	1332.8	1387.4	1476.4	1615.2	1770.0	1990.2	2191.3	2340.9	2347.4
40°	1118.7	1124.2	1163.0	1204.5	1276.6	1390.9	1530.4	1725.0	1965.9	2174.9	2262.0
42.5°	997.9	1009.8	1026.3	1066.2	1123.6	1209.6	1339.3	1500.2	1721.0	1961.4	2131.8
45°	857.4	871.0	881.2	907.8	948.6	1006.4	1097.0	1243.9	1412.0	1660.4	1889.7
47.5°	764.6	765.7	773.3	793.3	821.1	864.5	928.5	1022.9	1177.2	1378.7	1614.1
50°	698.2	709.1	711.8	727.4	749.2	781.2	834.3	914.6	1041.2	1218.1	1434.5
52.5°	651.4	654.6	662.3	673.6	692.6	717.5	763.5	826.4	925.7	1076.5	1275.5
55°	582.5	582.5	590.0	598.8	609.7	632.2	662.8	709.1	784.6	901.7	1066.3
57.5°	518.8	522.2	527.5	530.2	539.5	554.3	579.9	615.0	671.4	761.5	892.4
60°	476.3	482.5	481.8	487.2	495.4	507.0	528.7	557.3	607.7	679.8	790.1
62.5°	439.3	438.9	438.8	445.3	453.5	464.5	478.7	503.4	546.2	610.1	704.0
65°	378.4	377.0	381.8	385.8	388.6	396.7	407.6	429.4	458.0	505.6	578.4
67.5°	324.2	320.2	322.8	324.2	328.8	335.2	345.4	358.9	381.6	419.9	474.7
70°	287.2	283.8	283.1	284.4	288.5	293.3	300.8	313.7	334.8	365.4	405.6
72.5°	249.1	246.7	246.6	249.6	251.5	254.6	259.9	271.8	288.5	311.5	349.0
75°	194.6	194.6	194.6	195.3	197.3	200.1	204.1	210.3	223.2	239.5	264.7
77.5°	145.9	145.8	144.9	144.8	147.8	149.0	150.0	155.7	162.9	173.9	192.3
80°	114.3	110.9	112.3	114.3	115.7	116.4	118.4	119.8	125.9	132.0	144.9
82.5°	84.9	82.1	82.3	85.5	85.7	86.4	88.5	90.4	92.7	98.3	105.2
85°	44.9	44.9	45.6	45.6	46.3	45.6	47.6	48.3	48.3	51.7	55.8
87.5°	19.8	18.6	19.1	19.6	19.0	19.5	19.9	20.4	20.8	21.2	21.5
90°	17.1	16.9	16.6	16.4	16.1	15.7	15.2	14.7	14.2	13.7	12.0
92.5°	18.9	18.8	18.6	18.5	18.3	17.8	17.0	16.2	15.4	14.6	13.4
95°	21.7	21.7	21.7	21.7	21.7	21.2	20.3	19.5	18.6	17.7	16.3
97.5°	23.5	23.4	23.2	23.1	23.0	22.4	21.4	20.4	19.4	18.4	27.5
100°	24.0	23.8	23.7	23.6	23.4	22.9	21.9	20.8	19.8	18.8	38.6
102.5°	24.4	24.2	24.0	23.7	23.5	25.0	28.1	31.2	34.4	37.5	59.1
105°	25.1	24.8	24.6	24.3	24.1	35.2	57.6	80.0	102.5	124.9	136.3
107.5°	78.8	95.7	112.6	129.5	146.5	163.1	179.6	196.0	212.5	228.9	227.1
110°	156.8	175.0	193.1	211.2	229.3	240.5	244.7	248.9	253.0	257.2	255.8



TEST NUMBER: P332009

CATALOG NUMBER: S123DIP-S1000D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	269.1	272.9	276.7	280.6	284.4	286.3	286.2	286.1	286.1	286.0	284.6
115°	335.4	334.9	334.4	333.8	333.3	332.5	331.2	329.9	328.7	327.4	326.2
117.5°	372.6	372.5	372.4	372.3	372.2	371.6	370.6	369.6	368.6	367.5	367.0
120°	398.1	398.1	398.1	398.1	398.1	397.6	396.6	395.6	394.6	393.5	393.2
122.5°	423.2	423.1	423.0	422.9	422.8	422.4	421.7	421.0	420.3	419.6	419.1
125°	458.6	458.3	458.1	457.8	457.6	457.3	457.0	456.8	456.5	456.3	455.8
127.5°	492.6	492.8	493.1	493.3	493.6	493.5	493.1	492.7	492.3	491.9	491.3
130°	514.5	514.7	515.0	515.2	515.5	515.3	514.8	514.3	513.8	513.3	512.8
132.5°	534.5	534.9	535.2	535.6	536.0	535.9	535.4	534.9	534.4	533.9	533.4
135°	565.2	565.6	566.0	566.4	566.7	566.7	566.4	566.0	565.6	565.2	564.7
137.5°	594.1	594.3	594.6	594.8	595.1	594.9	594.3	593.7	593.1	592.5	592.2
140°	611.4	611.7	611.9	612.2	612.4	612.3	611.8	611.3	610.8	610.3	609.9
142.5°	627.4	627.7	628.1	628.5	628.8	628.8	628.4	628.0	627.6	627.2	626.8
145°	651.9	651.9	651.9	651.9	651.9	651.8	651.5	651.3	651.0	650.8	650.5
147.5°	670.2	670.8	671.3	671.9	672.5	672.7	672.4	672.2	671.9	671.7	671.4
150°	683.9	684.2	684.6	685.0	685.4	685.4	685.2	684.9	684.7	684.4	684.2
152.5°	694.8	695.4	696.0	696.6	697.1	697.2	696.7	696.3	695.8	695.4	695.2
155°	710.1	710.9	711.6	712.4	713.1	713.2	712.6	711.9	711.3	710.7	710.5
157.5°	723.0	724.0	725.0	725.9	726.9	727.1	726.3	725.5	724.8	724.0	724.1
160°	731.2	732.1	733.0	733.9	734.7	734.8	734.0	733.3	732.5	731.8	731.9
162.5°	739.0	739.7	740.5	741.3	742.1	742.1	741.2	740.3	739.5	738.6	738.7
165°	748.3	749.2	750.1	751.0	751.9	751.8	750.8	749.8	748.8	747.7	747.9
167.5°	755.0	756.1	757.1	758.1	759.1	759.1	758.1	757.1	756.1	755.0	755.0
170°	759.1	760.2	761.2	762.2	763.2	763.2	762.2	761.2	760.2	759.1	759.1
172.5°	761.4	762.5	763.7	764.8	765.9	765.9	764.9	763.9	762.9	761.9	761.8
175°	764.8	765.9	766.9	767.9	768.9	769.0	768.1	767.2	766.3	765.4	765.3
177.5°	765.9	766.9	767.9	768.9	769.9	770.0	769.2	768.4	767.6	766.8	766.7
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P332009

CATALOG NUMBER: S123DIP-S1000D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1448.1	1443.7	1439.4	1431.8	1425.2	1416.0	1413.2	1410.0	1400.2	1391.5	1384.9
5°	1536.5	1520.2	1496.4	1474.6	1456.9	1433.1	1419.5	1405.2	1384.8	1366.4	1351.5
7.5°	1629.1	1597.0	1560.0	1519.9	1482.7	1446.7	1417.7	1391.9	1363.3	1336.2	1315.1
10°	1702.6	1656.3	1604.6	1548.8	1501.2	1454.9	1416.1	1382.1	1345.3	1313.3	1286.8
12.5°	1786.4	1717.8	1646.5	1578.7	1522.4	1458.2	1411.2	1367.9	1326.3	1287.8	1258.0
15°	1885.6	1798.5	1714.2	1620.9	1535.2	1454.9	1399.1	1344.7	1296.3	1256.9	1218.8
17.5°	1976.0	1877.3	1766.1	1652.8	1549.3	1454.1	1376.0	1314.4	1254.0	1205.7	1167.7
20°	2027.2	1914.9	1789.0	1671.3	1557.0	1450.8	1365.1	1291.6	1226.2	1175.2	1132.3
22.5°	2071.3	1939.9	1809.7	1683.8	1556.4	1442.1	1344.9	1269.3	1198.5	1148.5	1102.9
25°	2117.0	1959.8	1829.2	1681.5	1539.3	1420.9	1312.0	1226.2	1155.5	1097.0	1050.0
27.5°	2156.2	1958.5	1803.4	1644.6	1512.3	1393.6	1277.4	1185.4	1110.3	1046.7	999.1
30°	2182.3	1961.2	1776.8	1619.6	1486.2	1363.7	1250.7	1158.2	1079.3	1014.6	969.7
32.5°	2198.7	1959.5	1752.3	1584.7	1444.8	1336.5	1221.9	1126.1	1045.0	981.4	938.1
35°	2208.2	1947.6	1710.1	1512.7	1378.0	1272.5	1176.6	1077.2	992.2	933.0	884.0
37.5°	2189.1	1922.4	1661.1	1443.3	1295.8	1191.9	1111.2	1026.6	945.2	880.0	837.8
40°	2159.2	1906.1	1623.0	1394.3	1239.2	1139.1	1070.4	987.4	907.1	845.2	805.7
42.5°	2102.0	1872.8	1581.1	1339.9	1180.4	1080.3	1017.1	947.7	871.7	813.6	774.1
45°	1962.5	1800.6	1518.2	1258.2	1093.5	990.1	934.3	884.0	815.2	758.7	724.7
47.5°	1769.0	1691.8	1427.3	1172.1	1002.9	903.4	845.4	804.9	754.7	709.1	676.4
50°	1634.5	1602.6	1365.7	1113.3	942.5	845.2	789.4	752.6	716.6	671.0	641.0
52.5°	1479.4	1499.1	1293.9	1052.3	881.0	785.3	732.8	703.6	670.8	633.4	607.3
55°	1261.0	1332.4	1169.8	950.0	789.4	698.2	648.5	622.6	603.6	575.7	553.2
57.5°	1056.4	1147.3	1035.6	844.5	699.4	620.7	573.1	544.9	532.7	518.1	500.4
60°	935.0	1024.8	939.8	773.7	639.0	564.1	521.9	498.1	485.9	475.7	460.7
62.5°	826.7	917.6	846.1	701.9	579.6	510.2	473.5	450.2	440.7	435.4	422.6
65°	677.8	756.0	708.4	590.0	494.7	433.5	400.1	383.8	375.0	372.9	364.7
67.5°	551.6	611.2	576.5	489.4	414.4	361.5	333.2	319.3	312.5	311.8	305.7
70°	468.9	524.7	498.1	419.2	354.5	313.0	288.5	276.3	272.2	271.5	268.1
72.5°	404.6	443.5	422.4	356.6	306.6	268.9	251.0	238.2	233.5	234.5	232.2
75°	299.4	328.7	316.4	270.8	230.7	206.2	191.2	183.1	179.0	181.0	178.3
77.5°	215.4	234.0	222.9	191.4	166.6	148.9	137.9	132.8	129.2	129.0	127.8
80°	162.6	173.5	167.4	148.3	127.9	113.0	104.1	100.7	98.7	98.0	97.3
82.5°	115.8	125.1	117.9	104.8	90.9	81.9	76.9	72.4	70.9	71.3	70.6
85°	58.5	61.9	59.2	51.0	45.6	41.5	38.8	36.7	35.4	36.1	34.7
87.5°	22.2	22.4	20.5	18.0	16.7	14.8	14.5	13.2	12.3	12.6	12.3
90°	10.4	8.7	7.1	5.6	4.4	3.1	1.8	0.6	1.8	3.1	4.4
92.5°	12.1	10.9	9.6	9.2	9.5	9.9	10.3	10.6	10.3	9.9	9.5
95°	14.9	13.5	12.1	14.0	19.2	24.4	29.6	34.8	29.6	24.4	19.2
97.5°	36.6	45.7	54.9	60.6	62.9	65.3	67.6	69.9	67.6	65.3	62.9
100°	58.4	78.1	97.9	106.5	104.0	101.5	98.9	96.4	98.9	101.5	104.0
102.5°	80.7	102.3	123.9	133.8	132.0	130.2	128.3	126.5	128.3	130.2	132.0
105°	147.7	159.1	170.5	175.5	174.1	172.8	171.4	170.0	171.4	172.8	174.1
107.5°	225.3	223.5	221.7	220.3	219.2	218.1	216.9	215.8	216.9	218.1	219.2
110°	254.4	253.0	251.7	250.4	249.4	248.4	247.4	246.4	247.4	248.4	249.4





TEST NUMBER: P332009

CATALOG NUMBER: S123DIP-S1000D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	283.2	281.8	280.4	279.2	278.3	277.4	276.5	275.6	276.5	277.4	278.3
115°	325.1	324.0	322.8	321.9	321.1	320.3	319.6	318.8	319.6	320.3	321.1
117.5°	366.4	365.8	365.2	364.4	363.5	362.6	361.6	360.7	361.6	362.6	363.5
120°	392.8	392.4	392.0	391.3	390.1	389.0	387.8	386.7	387.8	389.0	390.1
122.5°	418.6	418.1	417.6	416.9	416.0	415.0	414.1	413.2	414.1	415.0	416.0
125°	455.3	454.8	454.3	453.5	452.5	451.5	450.5	449.4	450.5	451.5	452.5
127.5°	490.7	490.0	489.4	488.6	487.6	486.6	485.6	484.6	485.6	486.6	487.6
130°	512.3	511.8	511.3	510.5	509.5	508.5	507.5	506.5	507.5	508.5	509.5
132.5°	533.0	532.6	532.2	531.5	530.5	529.5	528.5	527.5	528.5	529.5	530.5
135°	564.2	563.7	563.2	562.6	561.8	561.0	560.3	559.5	560.3	561.0	561.8
137.5°	591.9	591.6	591.4	590.7	589.8	588.8	587.9	586.9	587.9	588.8	589.8
140°	609.5	609.1	608.8	608.2	607.4	606.7	605.9	605.1	605.9	606.7	607.4
142.5°	626.4	626.0	625.6	625.1	624.3	623.6	622.8	622.0	622.8	623.6	624.3
145°	650.3	650.0	649.8	649.2	648.3	647.4	646.5	645.6	646.5	647.4	648.3
147.5°	671.1	670.9	670.6	670.2	669.6	669.1	668.5	667.9	668.5	669.1	669.6
150°	683.9	683.7	683.4	683.1	682.7	682.3	682.0	681.6	682.0	682.3	682.7
152.5°	695.1	694.9	694.8	694.6	694.4	694.2	694.1	693.9	694.1	694.2	694.4
155°	710.4	710.3	710.2	710.2	710.5	710.7	711.0	711.2	711.0	710.7	710.5
157.5°	724.3	724.4	724.5	724.6	724.6	724.6	724.7	724.7	724.7	724.6	724.6
160°	732.0	732.1	732.3	732.4	732.5	732.7	732.8	732.9	732.8	732.7	732.5
162.5°	738.9	739.0	739.1	739.3	739.7	740.0	740.3	740.7	740.3	740.0	739.7
165°	748.0	748.1	748.2	748.5	748.9	749.3	749.6	750.0	749.6	749.3	748.9
167.5°	755.0	755.0	755.0	755.3	755.8	756.3	756.8	757.3	756.8	756.3	755.8
170°	759.1	759.1	759.1	759.4	759.9	760.4	760.9	761.4	760.9	760.4	759.9
172.5°	761.7	761.6	761.5	761.7	762.3	762.9	763.6	764.2	763.6	762.9	762.3
175°	765.2	765.0	764.9	765.2	765.8	766.4	767.1	767.7	767.1	766.4	765.8
177.5°	766.6	766.5	766.4	766.6	767.1	767.6	768.1	768.6	768.1	767.6	767.1
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P332009

CATALOG NUMBER: S123DIP-S1000D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1381.1	1377.3	1371.9	1363.7	1357.2	1346.8	1346.8	1348.5	1348.5	1347.9	1346.8
5°	1339.2	1329.0	1316.8	1302.5	1287.5	1272.5	1269.8	1264.4	1260.3	1257.5	1254.1
7.5°	1295.0	1276.9	1259.0	1239.0	1220.8	1205.7	1195.2	1186.5	1180.9	1174.9	1170.6
10°	1265.0	1242.6	1221.5	1200.4	1177.2	1158.9	1147.3	1139.1	1133.0	1127.6	1124.9
12.5°	1229.6	1203.9	1180.7	1160.6	1135.3	1116.4	1105.4	1101.6	1094.4	1082.9	1076.9
15°	1177.9	1154.1	1126.2	1095.6	1083.3	1060.2	1047.3	1041.2	1037.1	1028.2	1025.5
17.5°	1133.7	1102.5	1071.2	1048.4	1025.6	1006.9	999.6	992.0	986.6	979.4	977.2
20°	1098.3	1070.4	1041.8	1017.3	993.5	973.1	967.0	961.5	956.1	952.7	950.0
22.5°	1062.4	1034.5	1010.8	987.9	962.5	949.1	942.5	936.5	932.7	930.4	927.6
25°	1011.9	987.4	960.9	940.4	920.0	911.2	907.1	903.7	901.0	897.6	896.9
27.5°	966.7	940.0	918.5	899.5	884.8	877.4	873.5	871.8	872.4	873.6	874.4
30°	933.0	908.5	890.8	874.4	860.8	854.0	853.3	853.3	856.1	856.7	858.1
32.5°	901.9	881.8	864.1	848.3	838.0	833.3	835.9	835.9	838.1	839.9	842.3
35°	856.7	839.0	825.4	811.8	803.0	805.0	806.4	807.7	811.1	815.2	818.0
37.5°	813.6	798.2	784.1	773.4	769.4	773.0	776.3	779.2	783.1	786.2	789.0
40°	782.6	771.0	757.4	747.9	749.2	751.3	754.0	757.4	760.8	762.8	765.6
42.5°	753.7	741.6	731.3	723.4	725.3	727.9	729.5	731.3	735.2	738.9	740.5
45°	709.8	700.2	690.7	685.9	687.3	688.7	690.0	692.1	695.5	698.2	698.9
47.5°	660.3	653.7	647.3	642.7	644.8	644.3	646.1	650.4	651.5	653.1	656.9
50°	628.8	622.6	615.2	613.8	613.8	613.8	614.5	619.9	619.9	622.6	625.4
52.5°	593.9	590.0	585.2	582.8	581.7	581.7	584.5	587.3	588.4	592.2	594.9
55°	542.4	538.3	534.2	532.1	530.8	532.1	537.6	538.9	542.4	544.4	546.4
57.5°	488.6	485.5	482.2	481.1	480.8	482.6	485.6	489.7	490.5	496.8	499.9
60°	453.2	448.4	445.7	445.7	444.4	450.5	449.1	455.9	457.3	461.4	466.1
62.5°	416.7	410.3	409.2	409.2	411.2	412.9	414.8	417.8	421.4	426.5	430.2
65°	357.9	354.5	359.3	358.6	357.3	361.3	361.3	364.7	368.8	373.6	381.1
67.5°	302.3	300.5	300.9	300.9	303.0	305.3	307.2	310.2	315.1	320.1	325.0
70°	264.7	266.8	263.4	266.1	268.1	268.8	270.2	274.2	279.7	283.1	288.5
72.5°	228.2	228.1	228.5	229.6	231.6	232.9	234.2	238.9	244.8	247.7	252.1
75°	175.6	174.9	176.9	176.9	180.3	181.7	183.1	185.1	190.5	194.6	198.0
77.5°	128.2	129.0	128.6	130.9	130.0	130.2	134.5	136.5	137.1	145.1	146.9
80°	96.6	98.0	98.7	99.4	100.0	98.7	103.4	105.5	105.5	110.2	113.6
82.5°	69.4	70.2	72.0	72.7	72.8	74.2	74.6	76.1	77.7	79.8	84.2
85°	34.7	36.7	37.4	36.7	37.4	36.1	38.1	38.8	39.5	39.5	39.5
87.5°	12.0	12.9	12.6	13.5	13.3	14.2	14.3	13.3	13.4	15.1	13.0
90°	5.6	7.1	8.7	10.4	12.0	13.7	14.2	14.7	15.2	15.7	16.1
92.5°	9.2	9.6	10.9	12.1	13.4	14.6	15.4	16.2	17.0	17.8	18.3
95°	14.0	12.1	13.5	14.9	16.3	17.7	18.6	19.5	20.3	21.2	21.7
97.5°	60.6	54.9	45.7	36.6	27.5	18.4	19.4	20.4	21.4	22.4	23.0
100°	106.5	97.9	78.1	58.4	38.6	18.8	19.8	20.8	21.9	22.9	23.4
102.5°	133.8	123.9	102.3	80.7	59.1	37.5	34.4	31.2	28.1	25.0	23.5
105°	175.5	170.5	159.1	147.7	136.3	124.9	102.5	80.0	57.6	35.2	24.1
107.5°	220.3	221.7	223.5	225.3	227.1	228.9	212.5	196.0	179.6	163.1	146.5
110°	250.4	251.7	253.0	254.4	255.8	257.2	253.0	248.9	244.7	240.5	229.3



TEST NUMBER: P332009

CATALOG NUMBER: S123DIP-S1000D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	279.2	280.4	281.8	283.2	284.6	286.0	286.1	286.1	286.2	286.3	284.4
115°	321.9	322.8	324.0	325.1	326.2	327.4	328.7	329.9	331.2	332.5	333.3
117.5°	364.4	365.2	365.8	366.4	367.0	367.5	368.6	369.6	370.6	371.6	372.2
120°	391.3	392.0	392.4	392.8	393.2	393.5	394.6	395.6	396.6	397.6	398.1
122.5°	416.9	417.6	418.1	418.6	419.1	419.6	420.3	421.0	421.7	422.4	422.8
125°	453.5	454.3	454.8	455.3	455.8	456.3	456.5	456.8	457.0	457.3	457.6
127.5°	488.6	489.4	490.0	490.7	491.3	491.9	492.3	492.7	493.1	493.5	493.6
130°	510.5	511.3	511.8	512.3	512.8	513.3	513.8	514.3	514.8	515.3	515.5
132.5°	531.5	532.2	532.6	533.0	533.4	533.9	534.4	534.9	535.4	535.9	536.0
135°	562.6	563.2	563.7	564.2	564.7	565.2	565.6	566.0	566.4	566.7	566.7
137.5°	590.7	591.4	591.6	591.9	592.2	592.5	593.1	593.7	594.3	594.9	595.1
140°	608.2	608.8	609.1	609.5	609.9	610.3	610.8	611.3	611.8	612.3	612.4
142.5°	625.1	625.6	626.0	626.4	626.8	627.2	627.6	628.0	628.4	628.8	628.8
145°	649.2	649.8	650.0	650.3	650.5	650.8	651.0	651.3	651.5	651.8	651.9
147.5°	670.2	670.6	670.9	671.1	671.4	671.7	671.9	672.2	672.4	672.7	672.5
150°	683.1	683.4	683.7	683.9	684.2	684.4	684.7	684.9	685.2	685.4	685.4
152.5°	694.6	694.8	694.9	695.1	695.2	695.4	695.8	696.3	696.7	697.2	697.1
155°	710.2	710.2	710.3	710.4	710.5	710.7	711.3	711.9	712.6	713.2	713.1
157.5°	724.6	724.5	724.4	724.3	724.1	724.0	724.8	725.5	726.3	727.1	726.9
160°	732.4	732.3	732.1	732.0	731.9	731.8	732.5	733.3	734.0	734.8	734.7
162.5°	739.3	739.1	739.0	738.9	738.7	738.6	739.5	740.3	741.2	742.1	742.1
165°	748.5	748.2	748.1	748.0	747.9	747.7	748.8	749.8	750.8	751.8	751.9
167.5°	755.3	755.0	755.0	755.0	755.0	755.0	756.1	757.1	758.1	759.1	759.1
170°	759.4	759.1	759.1	759.1	759.1	759.1	760.2	761.2	762.2	763.2	763.2
172.5°	761.7	761.5	761.6	761.7	761.8	761.9	762.9	763.9	764.9	765.9	765.9
175°	765.2	764.9	765.0	765.2	765.3	765.4	766.3	767.2	768.1	769.0	768.9
177.5°	766.6	766.4	766.5	766.6	766.7	766.8	767.6	768.4	769.2	770.0	769.9
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P332009

CATALOG NUMBER: S123DIP-S1000D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1343.0	1342.5	1346.3	1343.6	1346.3	1342.5	1343.0	1346.8	1347.9	1348.5	1348.5
5°	1250.1	1252.1	1245.3	1245.3	1245.3	1252.1	1250.1	1254.1	1257.5	1260.3	1264.4
7.5°	1167.3	1164.3	1164.6	1160.9	1164.6	1164.3	1167.3	1170.6	1174.9	1180.9	1186.5
10°	1116.7	1112.6	1111.2	1111.9	1111.2	1112.6	1116.7	1124.9	1127.6	1133.0	1139.1
12.5°	1074.8	1074.0	1065.0	1065.1	1065.0	1074.0	1074.8	1076.9	1082.9	1094.4	1101.6
15°	1025.5	1012.6	1011.2	1015.3	1011.2	1012.6	1025.5	1025.5	1028.2	1037.1	1041.2
17.5°	976.1	969.3	969.7	967.7	969.7	969.3	976.1	977.2	979.4	986.6	992.0
20°	950.0	945.9	945.2	940.4	945.2	945.9	950.0	950.0	952.7	956.1	961.5
22.5°	926.0	924.7	925.1	919.8	925.1	924.7	926.0	927.6	930.4	932.7	936.5
25°	896.2	899.6	896.9	896.9	896.9	899.6	896.2	896.9	897.6	901.0	903.7
27.5°	876.1	875.9	874.6	874.6	874.6	875.9	876.1	874.4	873.6	872.4	871.8
30°	860.8	860.1	861.5	861.5	861.5	860.1	860.8	858.1	856.7	856.1	853.3
32.5°	845.6	846.5	846.8	847.3	846.8	846.5	845.6	842.3	839.9	838.1	835.9
35°	822.0	822.7	824.8	823.4	824.8	822.7	822.0	818.0	815.2	811.1	807.7
37.5°	790.2	793.3	792.6	793.7	792.6	793.3	790.2	789.0	786.2	783.1	779.2
40°	766.2	768.3	767.6	767.6	767.6	768.3	766.2	765.6	762.8	760.8	757.4
42.5°	741.7	743.2	741.5	740.4	741.5	743.2	741.7	740.5	738.9	735.2	731.3
45°	701.6	700.2	702.3	699.5	702.3	700.2	701.6	698.9	698.2	695.5	692.1
47.5°	656.7	658.0	658.6	660.6	658.6	658.0	656.7	656.9	653.1	651.5	650.4
50°	626.7	630.8	630.8	630.1	630.8	630.8	626.7	625.4	622.6	619.9	619.9
52.5°	597.3	599.2	602.0	601.8	602.0	599.2	597.3	594.9	592.2	588.4	587.3
55°	551.9	553.2	554.6	555.3	554.6	553.2	551.9	546.4	544.4	542.4	538.9
57.5°	504.8	504.2	507.5	508.5	507.5	504.2	504.8	499.9	496.8	490.5	489.7
60°	471.6	471.6	477.0	479.1	477.0	471.6	471.6	466.1	461.4	457.3	455.9
62.5°	436.2	438.4	443.8	441.0	443.8	438.4	436.2	430.2	426.5	421.4	417.8
65°	384.5	389.9	389.2	392.0	389.2	389.9	384.5	381.1	373.6	368.8	364.7
67.5°	330.4	333.8	338.7	339.2	338.7	333.8	330.4	325.0	320.1	315.1	310.2
70°	294.0	297.4	300.1	302.1	300.1	297.4	294.0	288.5	283.1	279.7	274.2
72.5°	258.6	260.4	266.9	264.0	266.9	260.4	258.6	252.1	247.7	244.8	238.9
75°	202.8	207.5	211.6	209.6	211.6	207.5	202.8	198.0	194.6	190.5	185.1
77.5°	150.0	154.7	156.6	154.9	156.6	154.7	150.0	146.9	145.1	137.1	136.5
80°	118.4	117.7	121.8	121.1	121.8	117.7	118.4	113.6	110.2	105.5	105.5
82.5°	86.8	86.2	88.1	88.5	88.1	86.2	86.8	84.2	79.8	77.7	76.1
85°	42.2	44.2	41.5	40.8	41.5	44.2	42.2	39.5	39.5	39.5	38.8
87.5°	13.1	13.1	12.6	12.1	12.6	13.1	13.1	13.0	15.1	13.4	13.3
90°	16.4	16.6	16.9	17.1	16.9	16.6	16.4	16.1	15.7	15.2	14.7
92.5°	18.5	18.6	18.8	18.9	18.8	18.6	18.5	18.3	17.8	17.0	16.2
95°	21.7	21.7	21.7	21.7	21.7	21.7	21.7	21.7	21.2	20.3	19.5
97.5°	23.1	23.2	23.4	23.5	23.4	23.2	23.1	23.0	22.4	21.4	20.4
100°	23.6	23.7	23.8	24.0	23.8	23.7	23.6	23.4	22.9	21.9	20.8
102.5°	23.7	24.0	24.2	24.4	24.2	24.0	23.7	23.5	25.0	28.1	31.2
105°	24.3	24.6	24.8	25.1	24.8	24.6	24.3	24.1	35.2	57.6	80.0
107.5°	129.5	112.6	95.7	78.8	95.7	112.6	129.5	146.5	163.1	179.6	196.0
110°	211.2	193.1	175.0	156.8	175.0	193.1	211.2	229.3	240.5	244.7	248.9



TEST NUMBER: P332009

CATALOG NUMBER: S123DIP-S1000D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	280.6	276.7	272.9	269.1	272.9	276.7	280.6	284.4	286.3	286.2	286.1
115°	333.8	334.4	334.9	335.4	334.9	334.4	333.8	333.3	332.5	331.2	329.9
117.5°	372.3	372.4	372.5	372.6	372.5	372.4	372.3	372.2	371.6	370.6	369.6
120°	398.1	398.1	398.1	398.1	398.1	398.1	398.1	398.1	397.6	396.6	395.6
122.5°	422.9	423.0	423.1	423.2	423.1	423.0	422.9	422.8	422.4	421.7	421.0
125°	457.8	458.1	458.3	458.6	458.3	458.1	457.8	457.6	457.3	457.0	456.8
127.5°	493.3	493.1	492.8	492.6	492.8	493.1	493.3	493.6	493.5	493.1	492.7
130°	515.2	515.0	514.7	514.5	514.7	515.0	515.2	515.5	515.3	514.8	514.3
132.5°	535.6	535.2	534.9	534.5	534.9	535.2	535.6	536.0	535.9	535.4	534.9
135°	566.4	566.0	565.6	565.2	565.6	566.0	566.4	566.7	566.7	566.4	566.0
137.5°	594.8	594.6	594.3	594.1	594.3	594.6	594.8	595.1	594.9	594.3	593.7
140°	612.2	611.9	611.7	611.4	611.7	611.9	612.2	612.4	612.3	611.8	611.3
142.5°	628.5	628.1	627.7	627.4	627.7	628.1	628.5	628.8	628.8	628.4	628.0
145°	651.9	651.9	651.9	651.9	651.9	651.9	651.9	651.9	651.8	651.5	651.3
147.5°	671.9	671.3	670.8	670.2	670.8	671.3	671.9	672.5	672.7	672.4	672.2
150°	685.0	684.6	684.2	683.9	684.2	684.6	685.0	685.4	685.4	685.2	684.9
152.5°	696.6	696.0	695.4	694.8	695.4	696.0	696.6	697.1	697.2	696.7	696.3
155°	712.4	711.6	710.9	710.1	710.9	711.6	712.4	713.1	713.2	712.6	711.9
157.5°	725.9	725.0	724.0	723.0	724.0	725.0	725.9	726.9	727.1	726.3	725.5
160°	733.9	733.0	732.1	731.2	732.1	733.0	733.9	734.7	734.8	734.0	733.3
162.5°	741.3	740.5	739.7	739.0	739.7	740.5	741.3	742.1	742.1	741.2	740.3
165°	751.0	750.1	749.2	748.3	749.2	750.1	751.0	751.9	751.8	750.8	749.8
167.5°	758.1	757.1	756.1	755.0	756.1	757.1	758.1	759.1	759.1	758.1	757.1
170°	762.2	761.2	760.2	759.1	760.2	761.2	762.2	763.2	763.2	762.2	761.2
172.5°	764.8	763.7	762.5	761.4	762.5	763.7	764.8	765.9	765.9	764.9	763.9
175°	767.9	766.9	765.9	764.8	765.9	766.9	767.9	768.9	769.0	768.1	767.2
177.5°	768.9	767.9	766.9	765.9	766.9	767.9	768.9	769.9	770.0	769.2	768.4
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P332009

CATALOG NUMBER: S123DIP-S1000D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1346.8	1346.8	1357.2	1363.7	1371.9	1377.3	1381.1	1384.9	1391.5	1400.2	1410.0
5°	1269.8	1272.5	1287.5	1302.5	1316.8	1329.0	1339.2	1351.5	1366.4	1384.8	1405.2
7.5°	1195.2	1205.7	1220.8	1239.0	1259.0	1276.9	1295.0	1315.1	1336.2	1363.3	1391.9
10°	1147.3	1158.9	1177.2	1200.4	1221.5	1242.6	1265.0	1286.8	1313.3	1345.3	1382.1
12.5°	1105.4	1116.4	1135.3	1160.6	1180.7	1203.9	1229.6	1258.0	1287.8	1326.3	1367.9
15°	1047.3	1060.2	1083.3	1095.6	1126.2	1154.1	1177.9	1218.8	1256.9	1296.3	1344.7
17.5°	999.6	1006.9	1025.6	1048.4	1071.2	1102.5	1133.7	1167.7	1205.7	1254.0	1314.4
20°	967.0	973.1	993.5	1017.3	1041.8	1070.4	1098.3	1132.3	1175.2	1226.2	1291.6
22.5°	942.5	949.1	962.5	987.9	1010.8	1034.5	1062.4	1102.9	1148.5	1198.5	1269.3
25°	907.1	911.2	920.0	940.4	960.9	987.4	1011.9	1050.0	1097.0	1155.5	1226.2
27.5°	873.5	877.4	884.8	899.5	918.5	940.0	966.7	999.1	1046.7	1110.3	1185.4
30°	853.3	854.0	860.8	874.4	890.8	908.5	933.0	969.7	1014.6	1079.3	1158.2
32.5°	835.9	833.3	838.0	848.3	864.1	881.8	901.9	938.1	981.4	1045.0	1126.1
35°	806.4	805.0	803.0	811.8	825.4	839.0	856.7	884.0	933.0	992.2	1077.2
37.5°	776.3	773.0	769.4	773.4	784.1	798.2	813.6	837.8	880.0	945.2	1026.6
40°	754.0	751.3	749.2	747.9	757.4	771.0	782.6	805.7	845.2	907.1	987.4
42.5°	729.5	727.9	725.3	723.4	731.3	741.6	753.7	774.1	813.6	871.7	947.7
45°	690.0	688.7	687.3	685.9	690.7	700.2	709.8	724.7	758.7	815.2	884.0
47.5°	646.1	644.3	644.8	642.7	647.3	653.7	660.3	676.4	709.1	754.7	804.9
50°	614.5	613.8	613.8	613.8	615.2	622.6	628.8	641.0	671.0	716.6	752.6
52.5°	584.5	581.7	581.7	582.8	585.2	590.0	593.9	607.3	633.4	670.8	703.6
55°	537.6	532.1	530.8	532.1	534.2	538.3	542.4	553.2	575.7	603.6	622.6
57.5°	485.6	482.6	480.8	481.1	482.2	485.5	488.6	500.4	518.1	532.7	544.9
60°	449.1	450.5	444.4	445.7	445.7	448.4	453.2	460.7	475.7	485.9	498.1
62.5°	414.8	412.9	411.2	409.2	409.2	410.3	416.7	422.6	435.4	440.7	450.2
65°	361.3	361.3	357.3	358.6	359.3	354.5	357.9	364.7	372.9	375.0	383.8
67.5°	307.2	305.3	303.0	300.9	300.9	300.5	302.3	305.7	311.8	312.5	319.3
70°	270.2	268.8	268.1	266.1	263.4	266.8	264.7	268.1	271.5	272.2	276.3
72.5°	234.2	232.9	231.6	229.6	228.5	228.1	228.2	232.2	234.5	233.5	238.2
75°	183.1	181.7	180.3	176.9	176.9	174.9	175.6	178.3	181.0	179.0	183.1
77.5°	134.5	130.2	130.0	130.9	128.6	129.0	128.2	127.8	129.0	129.2	132.8
80°	103.4	98.7	100.0	99.4	98.7	98.0	96.6	97.3	98.0	98.7	100.7
82.5°	74.6	74.2	72.8	72.7	72.0	70.2	69.4	70.6	71.3	70.9	72.4
85°	38.1	36.1	37.4	36.7	37.4	36.7	34.7	34.7	36.1	35.4	36.7
87.5°	14.3	14.2	13.3	13.5	12.6	12.9	12.0	12.3	12.6	12.3	13.2
90°	14.2	13.7	12.0	10.4	8.7	7.1	5.6	4.4	3.1	1.8	0.6
92.5°	15.4	14.6	13.4	12.1	10.9	9.6	9.2	9.5	9.9	10.3	10.6
95°	18.6	17.7	16.3	14.9	13.5	12.1	14.0	19.2	24.4	29.6	34.8
97.5°	19.4	18.4	27.5	36.6	45.7	54.9	60.6	62.9	65.3	67.6	69.9
100°	19.8	18.8	38.6	58.4	78.1	97.9	106.5	104.0	101.5	98.9	96.4
102.5°	34.4	37.5	59.1	80.7	102.3	123.9	133.8	132.0	130.2	128.3	126.5
105°	102.5	124.9	136.3	147.7	159.1	170.5	175.5	174.1	172.8	171.4	170.0
107.5°	212.5	228.9	227.1	225.3	223.5	221.7	220.3	219.2	218.1	216.9	215.8
110°	253.0	257.2	255.8	254.4	253.0	251.7	250.4	249.4	248.4	247.4	246.4



TEST NUMBER: P332009

CATALOG NUMBER: S123DIP-S1000D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	286.1	286.0	284.6	283.2	281.8	280.4	279.2	278.3	277.4	276.5	275.6
115°	328.7	327.4	326.2	325.1	324.0	322.8	321.9	321.1	320.3	319.6	318.8
117.5°	368.6	367.5	367.0	366.4	365.8	365.2	364.4	363.5	362.6	361.6	360.7
120°	394.6	393.5	393.2	392.8	392.4	392.0	391.3	390.1	389.0	387.8	386.7
122.5°	420.3	419.6	419.1	418.6	418.1	417.6	416.9	416.0	415.0	414.1	413.2
125°	456.5	456.3	455.8	455.3	454.8	454.3	453.5	452.5	451.5	450.5	449.4
127.5°	492.3	491.9	491.3	490.7	490.0	489.4	488.6	487.6	486.6	485.6	484.6
130°	513.8	513.3	512.8	512.3	511.8	511.3	510.5	509.5	508.5	507.5	506.5
132.5°	534.4	533.9	533.4	533.0	532.6	532.2	531.5	530.5	529.5	528.5	527.5
135°	565.6	565.2	564.7	564.2	563.7	563.2	562.6	561.8	561.0	560.3	559.5
137.5°	593.1	592.5	592.2	591.9	591.6	591.4	590.7	589.8	588.8	587.9	586.9
140°	610.8	610.3	609.9	609.5	609.1	608.8	608.2	607.4	606.7	605.9	605.1
142.5°	627.6	627.2	626.8	626.4	626.0	625.6	625.1	624.3	623.6	622.8	622.0
145°	651.0	650.8	650.5	650.3	650.0	649.8	649.2	648.3	647.4	646.5	645.6
147.5°	671.9	671.7	671.4	671.1	670.9	670.6	670.2	669.6	669.1	668.5	667.9
150°	684.7	684.4	684.2	683.9	683.7	683.4	683.1	682.7	682.3	682.0	681.6
152.5°	695.8	695.4	695.2	695.1	694.9	694.8	694.6	694.4	694.2	694.1	693.9
155°	711.3	710.7	710.5	710.4	710.3	710.2	710.2	710.5	710.7	711.0	711.2
157.5°	724.8	724.0	724.1	724.3	724.4	724.5	724.6	724.6	724.6	724.7	724.7
160°	732.5	731.8	731.9	732.0	732.1	732.3	732.4	732.5	732.7	732.8	732.9
162.5°	739.5	738.6	738.7	738.9	739.0	739.1	739.3	739.7	740.0	740.3	740.7
165°	748.8	747.7	747.9	748.0	748.1	748.2	748.5	748.9	749.3	749.6	750.0
167.5°	756.1	755.0	755.0	755.0	755.0	755.0	755.3	755.8	756.3	756.8	757.3
170°	760.2	759.1	759.1	759.1	759.1	759.1	759.4	759.9	760.4	760.9	761.4
172.5°	762.9	761.9	761.8	761.7	761.6	761.5	761.7	762.3	762.9	763.6	764.2
175°	766.3	765.4	765.3	765.2	765.0	764.9	765.2	765.8	766.4	767.1	767.7
177.5°	767.6	766.8	766.7	766.6	766.5	766.4	766.6	767.1	767.6	768.1	768.6
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P332009

CATALOG NUMBER: S123DIP-S1000D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1413.2	1416.0	1425.2	1431.8	1439.4	1443.7	1448.1	1451.4	1455.7	1456.8	1472.6
5°	1419.5	1433.1	1456.9	1474.6	1496.4	1520.2	1536.5	1544.0	1563.8	1580.1	1612.8
7.5°	1417.7	1446.7	1482.7	1519.9	1560.0	1597.0	1629.1	1667.2	1694.3	1735.0	1775.1
10°	1416.1	1454.9	1501.2	1548.8	1604.6	1656.3	1702.6	1754.3	1797.2	1853.7	1902.0
12.5°	1411.2	1458.2	1522.4	1578.7	1646.5	1717.8	1786.4	1852.8	1890.8	1984.9	2029.4
15°	1399.1	1454.9	1535.2	1620.9	1714.2	1798.5	1885.6	1955.1	2067.3	2149.7	2202.1
17.5°	1376.0	1454.1	1549.3	1652.8	1766.1	1877.3	1976.0	2081.4	2200.4	2300.1	2406.2
20°	1365.1	1450.8	1557.0	1671.3	1789.0	1914.9	2027.2	2153.8	2283.7	2381.7	2517.8
22.5°	1344.9	1442.1	1556.4	1683.8	1809.7	1939.9	2071.3	2198.9	2349.1	2484.1	2613.6
25°	1312.0	1420.9	1539.3	1681.5	1829.2	1959.8	2117.0	2286.5	2443.0	2616.5	2745.8
27.5°	1277.4	1393.6	1512.3	1644.6	1803.4	1958.5	2156.2	2347.7	2539.0	2688.9	2784.6
30°	1250.7	1363.7	1486.2	1619.6	1776.8	1961.2	2182.3	2391.2	2577.7	2706.3	2760.1
32.5°	1221.9	1336.5	1444.8	1584.7	1752.3	1959.5	2198.7	2416.8	2579.9	2665.5	2655.0
35°	1176.6	1272.5	1378.0	1512.7	1710.1	1947.6	2208.2	2419.1	2519.2	2500.8	2362.0
37.5°	1111.2	1191.9	1295.8	1443.3	1661.1	1922.4	2189.1	2347.4	2340.9	2191.3	1990.2
40°	1070.4	1139.1	1239.2	1394.3	1623.0	1906.1	2159.2	2262.0	2174.9	1965.9	1725.0
42.5°	1017.1	1080.3	1180.4	1339.9	1581.1	1872.8	2102.0	2131.8	1961.4	1721.0	1500.2
45°	934.3	990.1	1093.5	1258.2	1518.2	1800.6	1962.5	1889.7	1660.4	1412.0	1243.9
47.5°	845.4	903.4	1002.9	1172.1	1427.3	1691.8	1769.0	1614.1	1378.7	1177.2	1022.9
50°	789.4	845.2	942.5	1113.3	1365.7	1602.6	1634.5	1434.5	1218.1	1041.2	914.6
52.5°	732.8	785.3	881.0	1052.3	1293.9	1499.1	1479.4	1275.5	1076.5	925.7	826.4
55°	648.5	698.2	789.4	950.0	1169.8	1332.4	1261.0	1066.3	901.7	784.6	709.1
57.5°	573.1	620.7	699.4	844.5	1035.6	1147.3	1056.4	892.4	761.5	671.4	615.0
60°	521.9	564.1	639.0	773.7	939.8	1024.8	935.0	790.1	679.8	607.7	557.3
62.5°	473.5	510.2	579.6	701.9	846.1	917.6	826.7	704.0	610.1	546.2	503.4
65°	400.1	433.5	494.7	590.0	708.4	756.0	677.8	578.4	505.6	458.0	429.4
67.5°	333.2	361.5	414.4	489.4	576.5	611.2	551.6	474.7	419.9	381.6	358.9
70°	288.5	313.0	354.5	419.2	498.1	524.7	468.9	405.6	365.4	334.8	313.7
72.5°	251.0	268.9	306.6	356.6	422.4	443.5	404.6	349.0	311.5	288.5	271.8
75°	191.2	206.2	230.7	270.8	316.4	328.7	299.4	264.7	239.5	223.2	210.3
77.5°	137.9	148.9	166.6	191.4	222.9	234.0	215.4	192.3	173.9	162.9	155.7
80°	104.1	113.0	127.9	148.3	167.4	173.5	162.6	144.9	132.0	125.9	119.8
82.5°	76.9	81.9	90.9	104.8	117.9	125.1	115.8	105.2	98.3	92.7	90.4
85°	38.8	41.5	45.6	51.0	59.2	61.9	58.5	55.8	51.7	48.3	48.3
87.5°	14.5	14.8	16.7	18.0	20.5	22.4	22.2	21.5	21.2	20.8	20.4
90°	1.8	3.1	4.4	5.6	7.1	8.7	10.4	12.0	13.7	14.2	14.7
92.5°	10.3	9.9	9.5	9.2	9.6	10.9	12.1	13.4	14.6	15.4	16.2
95°	29.6	24.4	19.2	14.0	12.1	13.5	14.9	16.3	17.7	18.6	19.5
97.5°	67.6	65.3	62.9	60.6	54.9	45.7	36.6	27.5	18.4	19.4	20.4
100°	98.9	101.5	104.0	106.5	97.9	78.1	58.4	38.6	18.8	19.8	20.8
102.5°	128.3	130.2	132.0	133.8	123.9	102.3	80.7	59.1	37.5	34.4	31.2
105°	171.4	172.8	174.1	175.5	170.5	159.1	147.7	136.3	124.9	102.5	80.0
107.5°	216.9	218.1	219.2	220.3	221.7	223.5	225.3	227.1	228.9	212.5	196.0
110°	247.4	248.4	249.4	250.4	251.7	253.0	254.4	255.8	257.2	253.0	248.9





TEST NUMBER: P332009

CATALOG NUMBER: S123DIP-S1000D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	276.5	277.4	278.3	279.2	280.4	281.8	283.2	284.6	286.0	286.1	286.1
115°	319.6	320.3	321.1	321.9	322.8	324.0	325.1	326.2	327.4	328.7	329.9
117.5°	361.6	362.6	363.5	364.4	365.2	365.8	366.4	367.0	367.5	368.6	369.6
120°	387.8	389.0	390.1	391.3	392.0	392.4	392.8	393.2	393.5	394.6	395.6
122.5°	414.1	415.0	416.0	416.9	417.6	418.1	418.6	419.1	419.6	420.3	421.0
125°	450.5	451.5	452.5	453.5	454.3	454.8	455.3	455.8	456.3	456.5	456.8
127.5°	485.6	486.6	487.6	488.6	489.4	490.0	490.7	491.3	491.9	492.3	492.7
130°	507.5	508.5	509.5	510.5	511.3	511.8	512.3	512.8	513.3	513.8	514.3
132.5°	528.5	529.5	530.5	531.5	532.2	532.6	533.0	533.4	533.9	534.4	534.9
135°	560.3	561.0	561.8	562.6	563.2	563.7	564.2	564.7	565.2	565.6	566.0
137.5°	587.9	588.8	589.8	590.7	591.4	591.6	591.9	592.2	592.5	593.1	593.7
140°	605.9	606.7	607.4	608.2	608.8	609.1	609.5	609.9	610.3	610.8	611.3
142.5°	622.8	623.6	624.3	625.1	625.6	626.0	626.4	626.8	627.2	627.6	628.0
145°	646.5	647.4	648.3	649.2	649.8	650.0	650.3	650.5	650.8	651.0	651.3
147.5°	668.5	669.1	669.6	670.2	670.6	670.9	671.1	671.4	671.7	671.9	672.2
150°	682.0	682.3	682.7	683.1	683.4	683.7	683.9	684.2	684.4	684.7	684.9
152.5°	694.1	694.2	694.4	694.6	694.8	694.9	695.1	695.2	695.4	695.8	696.3
155°	711.0	710.7	710.5	710.2	710.2	710.3	710.4	710.5	710.7	711.3	711.9
157.5°	724.7	724.6	724.6	724.6	724.5	724.4	724.3	724.1	724.0	724.8	725.5
160°	732.8	732.7	732.5	732.4	732.3	732.1	732.0	731.9	731.8	732.5	733.3
162.5°	740.3	740.0	739.7	739.3	739.1	739.0	738.9	738.7	738.6	739.5	740.3
165°	749.6	749.3	748.9	748.5	748.2	748.1	748.0	747.9	747.7	748.8	749.8
167.5°	756.8	756.3	755.8	755.3	755.0	755.0	755.0	755.0	755.0	756.1	757.1
170°	760.9	760.4	759.9	759.4	759.1	759.1	759.1	759.1	759.1	760.2	761.2
172.5°	763.6	762.9	762.3	761.7	761.5	761.6	761.7	761.8	761.9	762.9	763.9
175°	767.1	766.4	765.8	765.2	764.9	765.0	765.2	765.3	765.4	766.3	767.2
177.5°	768.1	767.6	767.1	766.6	766.4	766.5	766.6	766.7	766.8	767.6	768.4
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P332009

CATALOG NUMBER: S123DIP-S1000D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1478.0	1478.6	1484.6	1488.9	1486.7	1489.5	1490.5
5°	1614.8	1639.3	1652.2	1661.8	1662.4	1663.1	1668.6
7.5°	1808.7	1835.0	1854.2	1883.3	1892.0	1902.0	1899.1
10°	1950.3	1989.1	2022.4	2040.1	2059.2	2087.1	2064.6
12.5°	2082.6	2151.3	2202.1	2229.6	2247.5	2253.1	2242.1
15°	2300.7	2390.6	2438.9	2437.5	2498.8	2525.3	2483.8
17.5°	2500.8	2583.7	2650.1	2684.1	2735.2	2746.5	2741.3
20°	2623.3	2713.8	2765.5	2824.0	2850.6	2874.4	2878.5
22.5°	2728.9	2810.2	2865.7	2914.4	2936.6	2947.9	2954.7
25°	2837.6	2901.6	2935.0	2952.0	2958.1	2956.7	2947.9
27.5°	2830.2	2835.1	2798.3	2762.3	2730.0	2693.7	2681.1
30°	2756.7	2699.5	2597.4	2539.6	2454.5	2387.2	2414.4
32.5°	2563.4	2449.6	2335.0	2208.6	2103.9	2074.1	2044.2
35°	2187.8	1987.7	1870.7	1734.6	1680.1	1625.7	1588.3
37.5°	1770.0	1615.2	1476.4	1387.4	1332.8	1298.4	1279.9
40°	1530.4	1390.9	1276.6	1204.5	1163.0	1124.2	1118.7
42.5°	1339.3	1209.6	1123.6	1066.2	1026.3	1009.8	997.9
45°	1097.0	1006.4	948.6	907.8	881.2	871.0	857.4
47.5°	928.5	864.5	821.1	793.3	773.3	765.7	764.6
50°	834.3	781.2	749.2	727.4	711.8	709.1	698.2
52.5°	763.5	717.5	692.6	673.6	662.3	654.6	651.4
55°	662.8	632.2	609.7	598.8	590.0	582.5	582.5
57.5°	579.9	554.3	539.5	530.2	527.5	522.2	518.8
60°	528.7	507.0	495.4	487.2	481.8	482.5	476.3
62.5°	478.7	464.5	453.5	445.3	438.8	438.9	439.3
65°	407.6	396.7	388.6	385.8	381.8	377.0	378.4
67.5°	345.4	335.2	328.8	324.2	322.8	320.2	324.2
70°	300.8	293.3	288.5	284.4	283.1	283.8	287.2
72.5°	259.9	254.6	251.5	249.6	246.6	246.7	249.1
75°	204.1	200.1	197.3	195.3	194.6	194.6	194.6
77.5°	150.0	149.0	147.8	144.8	144.9	145.8	145.9
80°	118.4	116.4	115.7	114.3	112.3	110.9	114.3
82.5°	88.5	86.4	85.7	85.5	82.3	82.1	84.9
85°	47.6	45.6	46.3	45.6	45.6	44.9	44.9
87.5°	19.9	19.5	19.0	19.6	19.1	18.6	19.8
90°	15.2	15.7	16.1	16.4	16.6	16.9	17.1
92.5°	17.0	17.8	18.3	18.5	18.6	18.8	18.9
95°	20.3	21.2	21.7	21.7	21.7	21.7	21.7
97.5°	21.4	22.4	23.0	23.1	23.2	23.4	23.5
100°	21.9	22.9	23.4	23.6	23.7	23.8	24.0
102.5°	28.1	25.0	23.5	23.7	24.0	24.2	24.4
105°	57.6	35.2	24.1	24.3	24.6	24.8	25.1
107.5°	179.6	163.1	146.5	129.5	112.6	95.7	78.8
110°	244.7	240.5	229.3	211.2	193.1	175.0	156.8



TEST NUMBER: P332009

CATALOG NUMBER: S123DIP-S1000D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	286.2	286.3	284.4	280.6	276.7	272.9	269.1
115°	331.2	332.5	333.3	333.8	334.4	334.9	335.4
117.5°	370.6	371.6	372.2	372.3	372.4	372.5	372.6
120°	396.6	397.6	398.1	398.1	398.1	398.1	398.1
122.5°	421.7	422.4	422.8	422.9	423.0	423.1	423.2
125°	457.0	457.3	457.6	457.8	458.1	458.3	458.6
127.5°	493.1	493.5	493.6	493.3	493.1	492.8	492.6
130°	514.8	515.3	515.5	515.2	515.0	514.7	514.5
132.5°	535.4	535.9	536.0	535.6	535.2	534.9	534.5
135°	566.4	566.7	566.7	566.4	566.0	565.6	565.2
137.5°	594.3	594.9	595.1	594.8	594.6	594.3	594.1
140°	611.8	612.3	612.4	612.2	611.9	611.7	611.4
142.5°	628.4	628.8	628.8	628.5	628.1	627.7	627.4
145°	651.5	651.8	651.9	651.9	651.9	651.9	651.9
147.5°	672.4	672.7	672.5	671.9	671.3	670.8	670.2
150°	685.2	685.4	685.4	685.0	684.6	684.2	683.9
152.5°	696.7	697.2	697.1	696.6	696.0	695.4	694.8
155°	712.6	713.2	713.1	712.4	711.6	710.9	710.1
157.5°	726.3	727.1	726.9	725.9	725.0	724.0	723.0
160°	734.0	734.8	734.7	733.9	733.0	732.1	731.2
162.5°	741.2	742.1	742.1	741.3	740.5	739.7	739.0
165°	750.8	751.8	751.9	751.0	750.1	749.2	748.3
167.5°	758.1	759.1	759.1	758.1	757.1	756.1	755.0
170°	762.2	763.2	763.2	762.2	761.2	760.2	759.1
172.5°	764.9	765.9	765.9	764.8	763.7	762.5	761.4
175°	768.1	769.0	768.9	767.9	766.9	765.9	764.8
177.5°	769.2	770.0	769.9	768.9	767.9	766.9	765.9
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7

(END OF REPORT)