

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332020

Luminaire Tested: **S123DIP-S1000D805U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332020
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D805U835-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7147.9 lumens
Efficiency: N/A
Efficacy: 131.4 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332020

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332020

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	59
1	100	96	92	89	93	90	86	83	78	76	73	68	66	64	58	56	55	51
2	92	84	78	73	85	79	74	69	69	65	61	60	57	54	51	49	47	43
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	46	43	40	37
4	77	66	58	52	71	62	55	49	54	49	44	47	43	40	41	38	35	32
5	71	59	51	45	66	55	48	43	49	43	39	43	38	35	37	33	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	30	34	30	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	31	27	24	22
8	56	44	36	30	52	41	34	29	37	31	27	32	28	24	28	24	22	19
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20	17
10	49	37	29	24	46	35	28	23	31	25	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15118	15118	15118	15118
5°	18029	15183	13456	15183
10°	22566	15106	12153	15106
15°	27679	14985	11314	14985
20°	32972	14795	10772	14795
25°	35011	14563	10652	14563
30°	30009	14395	10708	14395
35°	20871	14155	10820	14155
40°	15719	13874	10786	13874
45°	13052	13457	10648	13457
50°	11692	12603	10551	12603
55°	10931	11684	10421	11684
60°	10254	10723	10314	10723
65°	9638	9775	9984	9775
70°	9039	8696	9508	8696
75°	8093	7615	8717	7615
80°	7085	6242	7507	6242
85°	5545	4533	5039	4533



TEST NUMBER: P332020

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.4	1.9
10°-20°	443.6	6.2
20°-30°	744.6	10.4
30°-40°	843.1	11.8
40°-50°	756.1	10.6
50°-60°	610.1	8.5
60°-70°	425.2	5.9
70°-80°	223.5	3.1
80°-90°	57.6	0.8
90°-100°	214.9	3.0
100°-110°	608.6	8.5
110°-120°	598.7	8.4
120°-130°	477.5	6.7
130°-140°	376.5	5.3
140°-150°	281.0	3.9
150°-160°	195.9	2.7
160°-170°	115.1	1.6
170°-180°	37.4	0.5
0°-30°	1326.6	18.6
0°-40°	2169.7	30.4
0°-60°	3535.9	49.5
0°-90°	4242.1	59.3
90°-120°	1422.2	19.9
90°-150°	2557.3	35.8
90°-180°	2906.0	40.7
0°-180°	7147.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1404	1404	1404	1404	1404	
5°	1669	1405	1245	1405	1669	173
15°	2484	1345	1015	1345	2484	717
25°	2948	1226	897	1226	2948	1293
35°	1588	1077	823	1077	1588	1032
45°	857	884	700	884	857	678
55°	582	623	555	623	582	523
65°	378	384	392	384	378	377
75°	195	183	210	183	195	208
85°	45	37	41	37	45	54
90°	23	2	23	2	23	14
95°	91	27	91	27	91	163
105°	994	91	994	91	994	981
115°	1210	160	1210	160	1210	1175
125°	954	223	954	223	954	864
135°	773	261	773	261	773	600
145°	604	298	604	298	604	384
155°	501	338	501	338	501	234
165°	437	370	437	370	437	125
175°	393	385	393	385	393	38
180°	386	386	386	386	386	



TEST NUMBER: P332020

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1490.5	1489.5	1486.7	1488.9	1484.6	1478.6	1478.0	1472.6	1456.8	1455.7	1451.4
5°	1668.6	1663.1	1662.4	1661.8	1652.2	1639.3	1614.8	1612.8	1580.1	1563.8	1544.0
7.5°	1899.1	1902.0	1892.0	1883.3	1854.2	1835.0	1808.7	1775.1	1735.0	1694.3	1667.2
10°	2064.6	2087.1	2059.2	2040.1	2022.4	1989.1	1950.3	1902.0	1853.7	1797.2	1754.3
12.5°	2242.1	2253.1	2247.5	2229.6	2202.1	2151.3	2082.6	2029.4	1984.9	1890.8	1852.8
15°	2483.8	2525.3	2498.8	2437.5	2438.9	2390.6	2300.7	2202.1	2149.7	2067.3	1955.1
17.5°	2741.3	2746.5	2735.2	2684.1	2650.1	2583.7	2500.8	2406.2	2300.1	2200.4	2081.4
20°	2878.5	2874.4	2850.6	2824.0	2765.5	2713.8	2623.3	2517.8	2381.7	2283.7	2153.8
22.5°	2954.7	2947.9	2936.6	2914.4	2865.7	2810.2	2728.9	2613.6	2484.1	2349.1	2198.9
25°	2947.9	2956.7	2958.1	2952.0	2935.0	2901.6	2837.6	2745.8	2616.5	2443.0	2286.5
27.5°	2681.1	2693.7	2730.0	2762.3	2798.3	2835.1	2830.2	2784.6	2688.9	2539.0	2347.7
30°	2414.4	2387.2	2454.5	2539.6	2597.4	2699.5	2756.7	2760.1	2706.3	2577.7	2391.2
32.5°	2044.2	2074.1	2103.9	2208.6	2335.0	2449.6	2563.4	2655.0	2665.5	2579.9	2416.8
35°	1588.3	1625.7	1680.1	1734.6	1870.7	1987.7	2187.8	2362.0	2500.8	2519.2	2419.1
37.5°	1279.9	1298.4	1332.8	1387.4	1476.4	1615.2	1770.0	1990.2	2191.3	2340.9	2347.4
40°	1118.7	1124.2	1163.0	1204.5	1276.6	1390.9	1530.4	1725.0	1965.9	2174.9	2262.0
42.5°	997.9	1009.8	1026.3	1066.2	1123.6	1209.6	1339.3	1500.2	1721.0	1961.4	2131.8
45°	857.4	871.0	881.2	907.8	948.6	1006.4	1097.0	1243.9	1412.0	1660.4	1889.7
47.5°	764.6	765.7	773.3	793.3	821.1	864.5	928.5	1022.9	1177.2	1378.7	1614.1
50°	698.2	709.1	711.8	727.4	749.2	781.2	834.3	914.6	1041.2	1218.1	1434.5
52.5°	651.4	654.6	662.3	673.6	692.6	717.5	763.5	826.4	925.7	1076.5	1275.5
55°	582.5	582.5	590.0	598.8	609.7	632.2	662.8	709.1	784.6	901.7	1066.3
57.5°	518.8	522.2	527.5	530.2	539.5	554.3	579.9	615.0	671.4	761.5	892.4
60°	476.3	482.5	481.8	487.2	495.4	507.0	528.7	557.3	607.7	679.8	790.1
62.5°	439.3	438.9	438.8	445.3	453.5	464.5	478.7	503.4	546.2	610.1	704.0
65°	378.4	377.0	381.8	385.8	388.6	396.7	407.6	429.4	458.0	505.6	578.4
67.5°	324.2	320.2	322.8	324.2	328.8	335.2	345.4	358.9	381.6	419.9	474.7
70°	287.2	283.8	283.1	284.4	288.5	293.3	300.8	313.7	334.8	365.4	405.6
72.5°	249.1	246.7	246.6	249.6	251.5	254.6	259.9	271.8	288.5	311.5	349.0
75°	194.6	194.6	194.6	195.3	197.3	200.1	204.1	210.3	223.2	239.5	264.7
77.5°	145.9	145.8	144.9	144.8	147.8	149.0	150.0	155.7	162.9	173.9	192.3
80°	114.3	110.9	112.3	114.3	115.7	116.4	118.4	119.8	125.9	132.0	144.9
82.5°	84.9	82.1	82.3	85.5	85.7	86.4	88.5	90.4	92.7	98.3	105.2
85°	44.9	44.9	45.6	45.6	46.3	45.6	47.6	48.3	48.3	51.7	55.8
87.5°	20.9	19.9	20.3	20.7	20.3	20.6	20.9	21.3	21.7	22.4	22.5
90°	22.7	23.5	22.7	21.9	22.7	21.1	20.3	19.5	18.8	19.5	17.2
92.5°	37.7	39.1	38.3	40.7	42.1	46.1	52.2	65.8	90.7	120.2	132.3
95°	90.7	93.8	99.3	106.3	121.2	149.3	190.8	281.5	376.1	463.6	412.8
97.5°	246.9	253.6	274.7	309.9	367.6	461.1	562.0	701.6	768.7	718.5	526.0
100°	490.2	489.4	519.9	577.0	655.9	767.0	858.4	921.8	894.4	740.4	500.4
102.5°	719.1	737.1	762.6	807.8	869.2	939.6	992.9	994.9	900.7	699.7	462.8
105°	994.5	998.4	1023.4	1053.1	1089.1	1109.4	1094.5	1016.4	853.0	628.6	416.7
107.5°	1153.0	1160.2	1168.7	1178.7	1178.0	1150.2	1081.7	954.8	769.5	565.7	387.3
110°	1218.1	1219.6	1221.2	1214.9	1193.1	1138.3	1039.8	896.0	716.9	530.1	376.1



TEST NUMBER: P332020

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1231.2	1230.9	1225.0	1205.6	1165.5	1095.2	984.8	837.8	671.3	506.3	369.8
115°	1209.5	1205.6	1189.9	1155.5	1096.9	1011.7	896.7	760.7	616.1	480.8	367.5
117.5°	1140.4	1135.0	1112.5	1073.1	1012.0	925.5	822.3	704.9	582.8	465.8	368.9
120°	1082.8	1078.1	1059.4	1015.6	953.8	874.9	781.0	675.5	565.3	458.9	371.4
122.5°	1029.0	1023.1	1002.4	963.0	908.2	834.8	747.9	652.4	550.9	454.6	375.7
125°	953.8	948.3	928.8	894.4	844.4	781.8	706.8	621.5	532.4	448.8	382.3
127.5°	891.9	886.9	869.2	839.8	795.3	738.4	670.6	594.7	516.2	446.0	389.8
130°	856.9	850.6	834.2	806.1	764.6	711.5	648.1	577.8	507.4	444.1	394.8
132.5°	822.5	818.1	803.6	775.4	736.5	685.8	626.9	562.1	499.3	443.4	398.6
135°	773.2	767.7	753.7	730.2	691.9	647.3	596.5	541.0	488.6	442.5	404.2
137.5°	721.2	717.6	705.7	681.9	649.7	611.1	567.3	521.8	479.4	440.8	408.0
140°	684.9	685.7	673.1	651.3	621.5	587.9	550.4	510.5	473.8	440.2	410.5
142.5°	651.1	651.9	640.6	621.2	595.9	566.7	534.1	499.9	468.8	438.9	412.3
145°	604.3	602.8	596.5	580.1	560.6	537.9	512.9	487.1	462.1	437.0	413.6
147.5°	565.9	565.3	559.3	548.2	533.4	517.3	497.1	476.6	455.5	434.1	413.6
150°	543.4	543.4	538.7	530.1	518.3	503.5	487.1	469.1	451.1	431.6	413.6
152.5°	524.6	524.6	521.8	513.8	504.6	492.2	477.7	462.2	446.1	428.4	411.7
155°	501.1	500.4	498.8	492.5	485.5	476.1	464.4	451.9	438.6	423.0	409.7
157.5°	479.7	479.9	478.6	473.9	467.8	460.5	451.4	440.9	430.2	418.1	407.0
160°	466.0	466.7	466.7	462.1	456.6	451.1	443.3	434.7	424.5	414.4	405.8
162.5°	453.5	454.2	454.2	450.2	446.6	441.7	434.5	427.2	418.9	410.6	403.3
165°	437.0	437.0	437.8	434.7	431.6	427.7	422.2	417.5	411.2	405.0	399.5
167.5°	421.4	421.4	422.2	420.0	418.6	415.8	412.6	409.0	403.9	399.4	395.8
170°	412.0	412.0	412.8	411.2	410.5	408.9	405.8	403.4	399.5	395.6	393.3
172.5°	403.3	403.9	405.3	403.7	403.6	402.6	400.1	398.4	395.1	392.5	391.4
175°	393.3	394.0	394.8	394.0	394.0	394.0	392.5	391.7	390.1	388.6	388.6
177.5°	387.5	387.5	388.7	388.1	388.7	388.7	388.1	387.5	386.8	386.2	386.8
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332020

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1448.1	1443.7	1439.4	1431.8	1425.2	1416.0	1413.2	1410.0	1400.2	1391.5	1384.9
5°	1536.5	1520.2	1496.4	1474.6	1456.9	1433.1	1419.5	1405.2	1384.8	1366.4	1351.5
7.5°	1629.1	1597.0	1560.0	1519.9	1482.7	1446.7	1417.7	1391.9	1363.3	1336.2	1315.1
10°	1702.6	1656.3	1604.6	1548.8	1501.2	1454.9	1416.1	1382.1	1345.3	1313.3	1286.8
12.5°	1786.4	1717.8	1646.5	1578.7	1522.4	1458.2	1411.2	1367.9	1326.3	1287.8	1258.0
15°	1885.6	1798.5	1714.2	1620.9	1535.2	1454.9	1399.1	1344.7	1296.3	1256.9	1218.8
17.5°	1976.0	1877.3	1766.1	1652.8	1549.3	1454.1	1376.0	1314.4	1254.0	1205.7	1167.7
20°	2027.2	1914.9	1789.0	1671.3	1557.0	1450.8	1365.1	1291.6	1226.2	1175.2	1132.3
22.5°	2071.3	1939.9	1809.7	1683.8	1556.4	1442.1	1344.9	1269.3	1198.5	1148.5	1102.9
25°	2117.0	1959.8	1829.2	1681.5	1539.3	1420.9	1312.0	1226.2	1155.5	1097.0	1050.0
27.5°	2156.2	1958.5	1803.4	1644.6	1512.3	1393.6	1277.4	1185.4	1110.3	1046.7	999.1
30°	2182.3	1961.2	1776.8	1619.6	1486.2	1363.7	1250.7	1158.2	1079.3	1014.6	969.7
32.5°	2198.7	1959.5	1752.3	1584.7	1444.8	1336.5	1221.9	1126.1	1045.0	981.4	938.1
35°	2208.2	1947.6	1710.1	1512.7	1378.0	1272.5	1176.6	1077.2	992.2	933.0	884.0
37.5°	2189.1	1922.4	1661.1	1443.3	1295.8	1191.9	1111.2	1026.6	945.2	880.0	837.8
40°	2159.2	1906.1	1623.0	1394.3	1239.2	1139.1	1070.4	987.4	907.1	845.2	805.7
42.5°	2102.0	1872.8	1581.1	1339.9	1180.4	1080.3	1017.1	947.7	871.7	813.6	774.1
45°	1962.5	1800.6	1518.2	1258.2	1093.5	990.1	934.3	884.0	815.2	758.7	724.7
47.5°	1769.0	1691.8	1427.3	1172.1	1002.9	903.4	845.4	804.9	754.7	709.1	676.4
50°	1634.5	1602.6	1365.7	1113.3	942.5	845.2	789.4	752.6	716.6	671.0	641.0
52.5°	1479.4	1499.1	1293.9	1052.3	881.0	785.3	732.8	703.6	670.8	633.4	607.3
55°	1261.0	1332.4	1169.8	950.0	789.4	698.2	648.5	622.6	603.6	575.7	553.2
57.5°	1056.4	1147.3	1035.6	844.5	699.4	620.7	573.1	544.9	532.7	518.1	500.4
60°	935.0	1024.8	939.8	773.7	639.0	564.1	521.9	498.1	485.9	475.7	460.7
62.5°	826.7	917.6	846.1	701.9	579.6	510.2	473.5	450.2	440.7	435.4	422.6
65°	677.8	756.0	708.4	590.0	494.7	433.5	400.1	383.8	375.0	372.9	364.7
67.5°	551.6	611.2	576.5	489.4	414.4	361.5	333.2	319.3	312.5	311.8	305.7
70°	468.9	524.7	498.1	419.2	354.5	313.0	288.5	276.3	272.2	271.5	268.1
72.5°	404.6	443.5	422.4	356.6	306.6	268.9	251.0	238.2	233.5	234.5	232.2
75°	299.4	328.7	316.4	270.8	230.7	206.2	191.2	183.1	179.0	181.0	178.3
77.5°	215.4	234.0	222.9	191.4	166.6	148.9	137.9	132.8	129.2	129.0	127.8
80°	162.6	173.5	167.4	148.3	127.9	113.0	104.1	100.7	98.7	98.0	97.3
82.5°	115.8	125.1	117.9	104.8	90.9	81.9	76.9	72.4	70.9	71.3	70.6
85°	58.5	61.9	59.2	51.0	45.6	41.5	38.8	36.7	35.4	36.1	34.7
87.5°	23.1	23.2	21.1	18.6	17.2	15.1	14.8	13.4	12.6	12.9	12.8
90°	14.9	12.5	10.2	8.6	7.0	4.7	3.1	1.6	3.1	4.7	7.0
92.5°	99.3	65.7	45.2	33.6	27.1	21.0	14.4	9.7	14.4	21.0	27.1
95°	284.6	168.1	101.6	71.1	50.8	37.5	28.9	26.6	28.9	37.5	50.8
97.5°	312.3	180.9	117.4	84.4	64.4	52.9	46.1	45.3	46.1	52.9	64.4
100°	294.7	179.0	124.3	93.8	75.1	64.1	58.6	57.9	58.6	64.1	75.1
102.5°	279.7	181.5	132.4	104.5	87.6	77.2	72.4	71.0	72.4	77.2	87.6
105°	268.9	188.4	146.2	122.0	107.1	97.7	93.0	90.7	93.0	97.7	107.1
107.5°	268.2	201.2	164.2	141.7	127.7	118.5	114.0	111.6	114.0	118.5	127.7
110°	271.3	211.9	176.7	154.8	141.5	132.9	129.0	126.7	129.0	132.9	141.5



TEST NUMBER: P332020

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	277.5	222.5	189.8	168.6	155.3	146.7	142.8	140.4	142.8	146.7	155.3
115°	287.7	240.0	210.3	189.2	175.9	168.1	163.4	160.3	163.4	168.1	175.9
117.5°	301.2	258.6	229.2	209.7	194.8	187.6	183.7	180.1	183.7	187.6	194.8
120°	311.2	270.5	242.4	222.8	208.0	200.1	196.2	193.9	196.2	200.1	208.0
122.5°	320.5	283.0	255.5	234.7	220.5	212.0	208.1	205.8	208.1	212.0	220.5
125°	335.4	301.0	273.6	252.5	237.7	229.1	224.4	222.8	224.4	229.1	237.7
127.5°	347.6	316.6	290.2	269.1	252.7	243.9	238.1	235.8	238.1	243.9	252.7
130°	355.7	326.0	300.2	279.1	262.7	253.3	246.3	243.9	246.3	253.3	262.7
132.5°	363.2	334.1	309.0	288.5	272.1	260.8	253.2	250.2	253.2	260.8	272.1
135°	372.9	346.3	322.1	301.0	284.6	272.9	264.3	261.1	264.3	272.9	284.6
137.5°	380.1	354.8	331.5	311.9	295.7	283.2	274.7	271.4	274.7	283.2	295.7
140°	383.9	360.4	337.7	318.2	302.6	290.1	282.2	278.3	282.2	290.1	302.6
142.5°	387.6	364.8	342.7	324.5	308.8	297.6	289.1	285.8	289.1	297.6	308.8
145°	391.7	370.6	350.3	332.3	319.0	307.3	300.2	297.9	300.2	307.3	319.0
147.5°	394.2	375.3	356.7	341.3	328.5	318.4	311.5	310.1	311.5	318.4	328.5
150°	394.8	378.4	360.4	346.3	335.4	325.2	319.0	318.2	319.0	325.2	335.4
152.5°	396.1	380.3	364.8	351.3	341.7	332.7	326.5	326.3	326.5	332.7	341.7
155°	396.4	383.9	370.6	359.6	351.0	343.2	338.5	338.5	338.5	343.2	351.0
157.5°	397.2	385.9	375.3	366.8	359.5	352.6	348.8	348.2	348.8	352.6	359.5
160°	397.2	387.8	378.4	370.6	365.1	358.9	355.7	355.7	355.7	358.9	365.1
162.5°	396.5	388.4	380.3	373.7	368.9	363.9	361.4	361.4	361.4	363.9	368.9
165°	394.8	389.3	383.1	377.6	374.5	370.6	369.0	369.8	369.0	370.6	374.5
167.5°	393.6	389.2	384.7	381.2	379.0	376.1	375.3	376.2	375.3	376.1	379.0
170°	391.7	388.6	384.7	383.1	381.5	379.2	378.4	380.0	378.4	379.2	381.5
172.5°	391.1	388.6	385.3	384.3	383.4	381.7	381.5	382.5	381.5	381.7	383.4
175°	389.3	387.8	386.2	385.4	385.4	383.9	384.7	385.4	384.7	383.9	385.4
177.5°	388.1	386.8	386.2	386.2	386.2	385.6	386.2	386.8	386.2	385.6	386.2
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332020

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1381.1	1377.3	1371.9	1363.7	1357.2	1346.8	1346.8	1348.5	1348.5	1347.9	1346.8
5°	1339.2	1329.0	1316.8	1302.5	1287.5	1272.5	1269.8	1264.4	1260.3	1257.5	1254.1
7.5°	1295.0	1276.9	1259.0	1239.0	1220.8	1205.7	1195.2	1186.5	1180.9	1174.9	1170.6
10°	1265.0	1242.6	1221.5	1200.4	1177.2	1158.9	1147.3	1139.1	1133.0	1127.6	1124.9
12.5°	1229.6	1203.9	1180.7	1160.6	1135.3	1116.4	1105.4	1101.6	1094.4	1082.9	1076.9
15°	1177.9	1154.1	1126.2	1095.6	1083.3	1060.2	1047.3	1041.2	1037.1	1028.2	1025.5
17.5°	1133.7	1102.5	1071.2	1048.4	1025.6	1006.9	999.6	992.0	986.6	979.4	977.2
20°	1098.3	1070.4	1041.8	1017.3	993.5	973.1	967.0	961.5	956.1	952.7	950.0
22.5°	1062.4	1034.5	1010.8	987.9	962.5	949.1	942.5	936.5	932.7	930.4	927.6
25°	1011.9	987.4	960.9	940.4	920.0	911.2	907.1	903.7	901.0	897.6	896.9
27.5°	966.7	940.0	918.5	899.5	884.8	877.4	873.5	871.8	872.4	873.6	874.4
30°	933.0	908.5	890.8	874.4	860.8	854.0	853.3	853.3	856.1	856.7	858.1
32.5°	901.9	881.8	864.1	848.3	838.0	833.3	835.9	835.9	838.1	839.9	842.3
35°	856.7	839.0	825.4	811.8	803.0	805.0	806.4	807.7	811.1	815.2	818.0
37.5°	813.6	798.2	784.1	773.4	769.4	773.0	776.3	779.2	783.1	786.2	789.0
40°	782.6	771.0	757.4	747.9	749.2	751.3	754.0	757.4	760.8	762.8	765.6
42.5°	753.7	741.6	731.3	723.4	725.3	727.9	729.5	731.3	735.2	738.9	740.5
45°	709.8	700.2	690.7	685.9	687.3	688.7	690.0	692.1	695.5	698.2	698.9
47.5°	660.3	653.7	647.3	642.7	644.8	644.3	646.1	650.4	651.5	653.1	656.9
50°	628.8	622.6	615.2	613.8	613.8	613.8	614.5	619.9	619.9	622.6	625.4
52.5°	593.9	590.0	585.2	582.8	581.7	581.7	584.5	587.3	588.4	592.2	594.9
55°	542.4	538.3	534.2	532.1	530.8	532.1	537.6	538.9	542.4	544.4	546.4
57.5°	488.6	485.5	482.2	481.1	480.8	482.6	485.6	489.7	490.5	496.8	499.9
60°	453.2	448.4	445.7	445.7	444.4	450.5	449.1	455.9	457.3	461.4	466.1
62.5°	416.7	410.3	409.2	409.2	411.2	412.9	414.8	417.8	421.4	426.5	430.2
65°	357.9	354.5	359.3	358.6	357.3	361.3	361.3	364.7	368.8	373.6	381.1
67.5°	302.3	300.5	300.9	300.9	303.0	305.3	307.2	310.2	315.1	320.1	325.0
70°	264.7	266.8	263.4	266.1	268.1	268.8	270.2	274.2	279.7	283.1	288.5
72.5°	228.2	228.1	228.5	229.6	231.6	232.9	234.2	238.9	244.8	247.7	252.1
75°	175.6	174.9	176.9	176.9	180.3	181.7	183.1	185.1	190.5	194.6	198.0
77.5°	128.2	129.0	128.6	130.9	130.0	130.2	134.5	136.5	137.1	145.1	146.9
80°	96.6	98.0	98.7	99.4	100.0	98.7	103.4	105.5	105.5	110.2	113.6
82.5°	69.4	70.2	72.0	72.7	72.8	74.2	74.6	76.1	77.7	79.8	84.2
85°	34.7	36.7	37.4	36.7	37.4	36.1	38.1	38.8	39.5	39.5	39.5
87.5°	12.6	13.5	13.4	14.4	14.3	15.3	15.2	14.3	14.4	16.2	14.3
90°	8.6	10.2	12.5	14.9	17.2	19.5	18.8	19.5	20.3	21.1	22.7
92.5°	33.6	45.2	65.7	99.3	132.3	120.2	90.7	65.8	52.2	46.1	42.1
95°	71.1	101.6	168.1	284.6	412.8	463.6	376.1	281.5	190.8	149.3	121.2
97.5°	84.4	117.4	180.9	312.3	526.0	718.5	768.7	701.6	562.0	461.1	367.6
100°	93.8	124.3	179.0	294.7	500.4	740.4	894.4	921.8	858.4	767.0	655.9
102.5°	104.5	132.4	181.5	279.7	462.8	699.7	900.7	994.9	992.9	939.6	869.2
105°	122.0	146.2	188.4	268.9	416.7	628.6	853.0	1016.4	1094.5	1109.4	1089.1
107.5°	141.7	164.2	201.2	268.2	387.3	565.7	769.5	954.8	1081.7	1150.2	1178.0
110°	154.8	176.7	211.9	271.3	376.1	530.1	716.9	896.0	1039.8	1138.3	1193.1



TEST NUMBER: P332020

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	168.6	189.8	222.5	277.5	369.8	506.3	671.3	837.8	984.8	1095.2	1165.5
115°	189.2	210.3	240.0	287.7	367.5	480.8	616.1	760.7	896.7	1011.7	1096.9
117.5°	209.7	229.2	258.6	301.2	368.9	465.8	582.8	704.9	822.3	925.5	1012.0
120°	222.8	242.4	270.5	311.2	371.4	458.9	565.3	675.5	781.0	874.9	953.8
122.5°	234.7	255.5	283.0	320.5	375.7	454.6	550.9	652.4	747.9	834.8	908.2
125°	252.5	273.6	301.0	335.4	382.3	448.8	532.4	621.5	706.8	781.8	844.4
127.5°	269.1	290.2	316.6	347.6	389.8	446.0	516.2	594.7	670.6	738.4	795.3
130°	279.1	300.2	326.0	355.7	394.8	444.1	507.4	577.8	648.1	711.5	764.6
132.5°	288.5	309.0	334.1	363.2	398.6	443.4	499.3	562.1	626.9	685.8	736.5
135°	301.0	322.1	346.3	372.9	404.2	442.5	488.6	541.0	596.5	647.3	691.9
137.5°	311.9	331.5	354.8	380.1	408.0	440.8	479.4	521.8	567.3	611.1	649.7
140°	318.2	337.7	360.4	383.9	410.5	440.2	473.8	510.5	550.4	587.9	621.5
142.5°	324.5	342.7	364.8	387.6	412.3	438.9	468.8	499.9	534.1	566.7	595.9
145°	332.3	350.3	370.6	391.7	413.6	437.0	462.1	487.1	512.9	537.9	560.6
147.5°	341.3	356.7	375.3	394.2	413.6	434.1	455.5	476.6	497.1	517.3	533.4
150°	346.3	360.4	378.4	394.8	413.6	431.6	451.1	469.1	487.1	503.5	518.3
152.5°	351.3	364.8	380.3	396.1	411.7	428.4	446.1	462.2	477.7	492.2	504.6
155°	359.6	370.6	383.9	396.4	409.7	423.0	438.6	451.9	464.4	476.1	485.5
157.5°	366.8	375.3	385.9	397.2	407.0	418.1	430.2	440.9	451.4	460.5	467.8
160°	370.6	378.4	387.8	397.2	405.8	414.4	424.5	434.7	443.3	451.1	456.6
162.5°	373.7	380.3	388.4	396.5	403.3	410.6	418.9	427.2	434.5	441.7	446.6
165°	377.6	383.1	389.3	394.8	399.5	405.0	411.2	417.5	422.2	427.7	431.6
167.5°	381.2	384.7	389.2	393.6	395.8	399.4	403.9	409.0	412.6	415.8	418.6
170°	383.1	384.7	388.6	391.7	393.3	395.6	399.5	403.4	405.8	408.9	410.5
172.5°	384.3	385.3	388.6	391.1	391.4	392.5	395.1	398.4	400.1	402.6	403.6
175°	385.4	386.2	387.8	389.3	388.6	388.6	390.1	391.7	392.5	394.0	394.0
177.5°	386.2	386.2	386.8	388.1	386.8	386.2	386.8	387.5	388.1	388.7	388.7
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332020

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1343.0	1342.5	1346.3	1343.6	1346.3	1342.5	1343.0	1346.8	1347.9	1348.5	1348.5
5°	1250.1	1252.1	1245.3	1245.3	1245.3	1252.1	1250.1	1254.1	1257.5	1260.3	1264.4
7.5°	1167.3	1164.3	1164.6	1160.9	1164.6	1164.3	1167.3	1170.6	1174.9	1180.9	1186.5
10°	1116.7	1112.6	1111.2	1111.9	1111.2	1112.6	1116.7	1124.9	1127.6	1133.0	1139.1
12.5°	1074.8	1074.0	1065.0	1065.1	1065.0	1074.0	1074.8	1076.9	1082.9	1094.4	1101.6
15°	1025.5	1012.6	1011.2	1015.3	1011.2	1012.6	1025.5	1025.5	1028.2	1037.1	1041.2
17.5°	976.1	969.3	969.7	967.7	969.7	969.3	976.1	977.2	979.4	986.6	992.0
20°	950.0	945.9	945.2	940.4	945.2	945.9	950.0	950.0	952.7	956.1	961.5
22.5°	926.0	924.7	925.1	919.8	925.1	924.7	926.0	927.6	930.4	932.7	936.5
25°	896.2	899.6	896.9	896.9	896.9	899.6	896.2	896.9	897.6	901.0	903.7
27.5°	876.1	875.9	874.6	874.6	874.6	875.9	876.1	874.4	873.6	872.4	871.8
30°	860.8	860.1	861.5	861.5	861.5	860.1	860.8	858.1	856.7	856.1	853.3
32.5°	845.6	846.5	846.8	847.3	846.8	846.5	845.6	842.3	839.9	838.1	835.9
35°	822.0	822.7	824.8	823.4	824.8	822.7	822.0	818.0	815.2	811.1	807.7
37.5°	790.2	793.3	792.6	793.7	792.6	793.3	790.2	789.0	786.2	783.1	779.2
40°	766.2	768.3	767.6	767.6	767.6	768.3	766.2	765.6	762.8	760.8	757.4
42.5°	741.7	743.2	741.5	740.4	741.5	743.2	741.7	740.5	738.9	735.2	731.3
45°	701.6	700.2	702.3	699.5	702.3	700.2	701.6	698.9	698.2	695.5	692.1
47.5°	656.7	658.0	658.6	660.6	658.6	658.0	656.7	656.9	653.1	651.5	650.4
50°	626.7	630.8	630.8	630.1	630.8	630.8	626.7	625.4	622.6	619.9	619.9
52.5°	597.3	599.2	602.0	601.8	602.0	599.2	597.3	594.9	592.2	588.4	587.3
55°	551.9	553.2	554.6	555.3	554.6	553.2	551.9	546.4	544.4	542.4	538.9
57.5°	504.8	504.2	507.5	508.5	507.5	504.2	504.8	499.9	496.8	490.5	489.7
60°	471.6	471.6	477.0	479.1	477.0	471.6	471.6	466.1	461.4	457.3	455.9
62.5°	436.2	438.4	443.8	441.0	443.8	438.4	436.2	430.2	426.5	421.4	417.8
65°	384.5	389.9	389.2	392.0	389.2	389.9	384.5	381.1	373.6	368.8	364.7
67.5°	330.4	333.8	338.7	339.2	338.7	333.8	330.4	325.0	320.1	315.1	310.2
70°	294.0	297.4	300.1	302.1	300.1	297.4	294.0	288.5	283.1	279.7	274.2
72.5°	258.6	260.4	266.9	264.0	266.9	260.4	258.6	252.1	247.7	244.8	238.9
75°	202.8	207.5	211.6	209.6	211.6	207.5	202.8	198.0	194.6	190.5	185.1
77.5°	150.0	154.7	156.6	154.9	156.6	154.7	150.0	146.9	145.1	137.1	136.5
80°	118.4	117.7	121.8	121.1	121.8	117.7	118.4	113.6	110.2	105.5	105.5
82.5°	86.8	86.2	88.1	88.5	88.1	86.2	86.8	84.2	79.8	77.7	76.1
85°	42.2	44.2	41.5	40.8	41.5	44.2	42.2	39.5	39.5	39.5	38.8
87.5°	14.2	14.3	13.9	13.2	13.9	14.3	14.2	14.3	16.2	14.4	14.3
90°	21.9	22.7	23.5	22.7	23.5	22.7	21.9	22.7	21.1	20.3	19.5
92.5°	40.7	38.3	39.1	37.7	39.1	38.3	40.7	42.1	46.1	52.2	65.8
95°	106.3	99.3	93.8	90.7	93.8	99.3	106.3	121.2	149.3	190.8	281.5
97.5°	309.9	274.7	253.6	246.9	253.6	274.7	309.9	367.6	461.1	562.0	701.6
100°	577.0	519.9	489.4	490.2	489.4	519.9	577.0	655.9	767.0	858.4	921.8
102.5°	807.8	762.6	737.1	719.1	737.1	762.6	807.8	869.2	939.6	992.9	994.9
105°	1053.1	1023.4	998.4	994.5	998.4	1023.4	1053.1	1089.1	1109.4	1094.5	1016.4
107.5°	1178.7	1168.7	1160.2	1153.0	1160.2	1168.7	1178.7	1178.0	1150.2	1081.7	954.8
110°	1214.9	1221.2	1219.6	1218.1	1219.6	1221.2	1214.9	1193.1	1138.3	1039.8	896.0



TEST NUMBER: P332020

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1205.6	1225.0	1230.9	1231.2	1230.9	1225.0	1205.6	1165.5	1095.2	984.8	837.8
115°	1155.5	1189.9	1205.6	1209.5	1205.6	1189.9	1155.5	1096.9	1011.7	896.7	760.7
117.5°	1073.1	1112.5	1135.0	1140.4	1135.0	1112.5	1073.1	1012.0	925.5	822.3	704.9
120°	1015.6	1059.4	1078.1	1082.8	1078.1	1059.4	1015.6	953.8	874.9	781.0	675.5
122.5°	963.0	1002.4	1023.1	1029.0	1023.1	1002.4	963.0	908.2	834.8	747.9	652.4
125°	894.4	928.8	948.3	953.8	948.3	928.8	894.4	844.4	781.8	706.8	621.5
127.5°	839.8	869.2	886.9	891.9	886.9	869.2	839.8	795.3	738.4	670.6	594.7
130°	806.1	834.2	850.6	856.9	850.6	834.2	806.1	764.6	711.5	648.1	577.8
132.5°	775.4	803.6	818.1	822.5	818.1	803.6	775.4	736.5	685.8	626.9	562.1
135°	730.2	753.7	767.7	773.2	767.7	753.7	730.2	691.9	647.3	596.5	541.0
137.5°	681.9	705.7	717.6	721.2	717.6	705.7	681.9	649.7	611.1	567.3	521.8
140°	651.3	673.1	685.7	684.9	685.7	673.1	651.3	621.5	587.9	550.4	510.5
142.5°	621.2	640.6	651.9	651.1	651.9	640.6	621.2	595.9	566.7	534.1	499.9
145°	580.1	596.5	602.8	604.3	602.8	596.5	580.1	560.6	537.9	512.9	487.1
147.5°	548.2	559.3	565.3	565.9	565.3	559.3	548.2	533.4	517.3	497.1	476.6
150°	530.1	538.7	543.4	543.4	543.4	538.7	530.1	518.3	503.5	487.1	469.1
152.5°	513.8	521.8	524.6	524.6	524.6	521.8	513.8	504.6	492.2	477.7	462.2
155°	492.5	498.8	500.4	501.1	500.4	498.8	492.5	485.5	476.1	464.4	451.9
157.5°	473.9	478.6	479.9	479.7	479.9	478.6	473.9	467.8	460.5	451.4	440.9
160°	462.1	466.7	466.7	466.0	466.7	466.7	462.1	456.6	451.1	443.3	434.7
162.5°	450.2	454.2	454.2	453.5	454.2	454.2	450.2	446.6	441.7	434.5	427.2
165°	434.7	437.8	437.0	437.0	437.0	437.8	434.7	431.6	427.7	422.2	417.5
167.5°	420.0	422.2	421.4	421.4	421.4	422.2	420.0	418.6	415.8	412.6	409.0
170°	411.2	412.8	412.0	412.0	412.0	412.8	411.2	410.5	408.9	405.8	403.4
172.5°	403.7	405.3	403.9	403.3	403.9	405.3	403.7	403.6	402.6	400.1	398.4
175°	394.0	394.8	394.0	393.3	394.0	394.8	394.0	394.0	394.0	392.5	391.7
177.5°	388.1	388.7	387.5	387.5	387.5	388.7	388.1	388.7	388.7	388.1	387.5
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332020

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1346.8	1346.8	1357.2	1363.7	1371.9	1377.3	1381.1	1384.9	1391.5	1400.2	1410.0
5°	1269.8	1272.5	1287.5	1302.5	1316.8	1329.0	1339.2	1351.5	1366.4	1384.8	1405.2
7.5°	1195.2	1205.7	1220.8	1239.0	1259.0	1276.9	1295.0	1315.1	1336.2	1363.3	1391.9
10°	1147.3	1158.9	1177.2	1200.4	1221.5	1242.6	1265.0	1286.8	1313.3	1345.3	1382.1
12.5°	1105.4	1116.4	1135.3	1160.6	1180.7	1203.9	1229.6	1258.0	1287.8	1326.3	1367.9
15°	1047.3	1060.2	1083.3	1095.6	1126.2	1154.1	1177.9	1218.8	1256.9	1296.3	1344.7
17.5°	999.6	1006.9	1025.6	1048.4	1071.2	1102.5	1133.7	1167.7	1205.7	1254.0	1314.4
20°	967.0	973.1	993.5	1017.3	1041.8	1070.4	1098.3	1132.3	1175.2	1226.2	1291.6
22.5°	942.5	949.1	962.5	987.9	1010.8	1034.5	1062.4	1102.9	1148.5	1198.5	1269.3
25°	907.1	911.2	920.0	940.4	960.9	987.4	1011.9	1050.0	1097.0	1155.5	1226.2
27.5°	873.5	877.4	884.8	899.5	918.5	940.0	966.7	999.1	1046.7	1110.3	1185.4
30°	853.3	854.0	860.8	874.4	890.8	908.5	933.0	969.7	1014.6	1079.3	1158.2
32.5°	835.9	833.3	838.0	848.3	864.1	881.8	901.9	938.1	981.4	1045.0	1126.1
35°	806.4	805.0	803.0	811.8	825.4	839.0	856.7	884.0	933.0	992.2	1077.2
37.5°	776.3	773.0	769.4	773.4	784.1	798.2	813.6	837.8	880.0	945.2	1026.6
40°	754.0	751.3	749.2	747.9	757.4	771.0	782.6	805.7	845.2	907.1	987.4
42.5°	729.5	727.9	725.3	723.4	731.3	741.6	753.7	774.1	813.6	871.7	947.7
45°	690.0	688.7	687.3	685.9	690.7	700.2	709.8	724.7	758.7	815.2	884.0
47.5°	646.1	644.3	644.8	642.7	647.3	653.7	660.3	676.4	709.1	754.7	804.9
50°	614.5	613.8	613.8	613.8	615.2	622.6	628.8	641.0	671.0	716.6	752.6
52.5°	584.5	581.7	581.7	582.8	585.2	590.0	593.9	607.3	633.4	670.8	703.6
55°	537.6	532.1	530.8	532.1	534.2	538.3	542.4	553.2	575.7	603.6	622.6
57.5°	485.6	482.6	480.8	481.1	482.2	485.5	488.6	500.4	518.1	532.7	544.9
60°	449.1	450.5	444.4	445.7	445.7	448.4	453.2	460.7	475.7	485.9	498.1
62.5°	414.8	412.9	411.2	409.2	409.2	410.3	416.7	422.6	435.4	440.7	450.2
65°	361.3	361.3	357.3	358.6	359.3	354.5	357.9	364.7	372.9	375.0	383.8
67.5°	307.2	305.3	303.0	300.9	300.9	300.5	302.3	305.7	311.8	312.5	319.3
70°	270.2	268.8	268.1	266.1	263.4	266.8	264.7	268.1	271.5	272.2	276.3
72.5°	234.2	232.9	231.6	229.6	228.5	228.1	228.2	232.2	234.5	233.5	238.2
75°	183.1	181.7	180.3	176.9	176.9	174.9	175.6	178.3	181.0	179.0	183.1
77.5°	134.5	130.2	130.0	130.9	128.6	129.0	128.2	127.8	129.0	129.2	132.8
80°	103.4	98.7	100.0	99.4	98.7	98.0	96.6	97.3	98.0	98.7	100.7
82.5°	74.6	74.2	72.8	72.7	72.0	70.2	69.4	70.6	71.3	70.9	72.4
85°	38.1	36.1	37.4	36.7	37.4	36.7	34.7	34.7	36.1	35.4	36.7
87.5°	15.2	15.3	14.3	14.4	13.4	13.5	12.6	12.8	12.9	12.6	13.4
90°	18.8	19.5	17.2	14.9	12.5	10.2	8.6	7.0	4.7	3.1	1.6
92.5°	90.7	120.2	132.3	99.3	65.7	45.2	33.6	27.1	21.0	14.4	9.7
95°	376.1	463.6	412.8	284.6	168.1	101.6	71.1	50.8	37.5	28.9	26.6
97.5°	768.7	718.5	526.0	312.3	180.9	117.4	84.4	64.4	52.9	46.1	45.3
100°	894.4	740.4	500.4	294.7	179.0	124.3	93.8	75.1	64.1	58.6	57.9
102.5°	900.7	699.7	462.8	279.7	181.5	132.4	104.5	87.6	77.2	72.4	71.0
105°	853.0	628.6	416.7	268.9	188.4	146.2	122.0	107.1	97.7	93.0	90.7
107.5°	769.5	565.7	387.3	268.2	201.2	164.2	141.7	127.7	118.5	114.0	111.6
110°	716.9	530.1	376.1	271.3	211.9	176.7	154.8	141.5	132.9	129.0	126.7



TEST NUMBER: P332020

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	671.3	506.3	369.8	277.5	222.5	189.8	168.6	155.3	146.7	142.8	140.4
115°	616.1	480.8	367.5	287.7	240.0	210.3	189.2	175.9	168.1	163.4	160.3
117.5°	582.8	465.8	368.9	301.2	258.6	229.2	209.7	194.8	187.6	183.7	180.1
120°	565.3	458.9	371.4	311.2	270.5	242.4	222.8	208.0	200.1	196.2	193.9
122.5°	550.9	454.6	375.7	320.5	283.0	255.5	234.7	220.5	212.0	208.1	205.8
125°	532.4	448.8	382.3	335.4	301.0	273.6	252.5	237.7	229.1	224.4	222.8
127.5°	516.2	446.0	389.8	347.6	316.6	290.2	269.1	252.7	243.9	238.1	235.8
130°	507.4	444.1	394.8	355.7	326.0	300.2	279.1	262.7	253.3	246.3	243.9
132.5°	499.3	443.4	398.6	363.2	334.1	309.0	288.5	272.1	260.8	253.2	250.2
135°	488.6	442.5	404.2	372.9	346.3	322.1	301.0	284.6	272.9	264.3	261.1
137.5°	479.4	440.8	408.0	380.1	354.8	331.5	311.9	295.7	283.2	274.7	271.4
140°	473.8	440.2	410.5	383.9	360.4	337.7	318.2	302.6	290.1	282.2	278.3
142.5°	468.8	438.9	412.3	387.6	364.8	342.7	324.5	308.8	297.6	289.1	285.8
145°	462.1	437.0	413.6	391.7	370.6	350.3	332.3	319.0	307.3	300.2	297.9
147.5°	455.5	434.1	413.6	394.2	375.3	356.7	341.3	328.5	318.4	311.5	310.1
150°	451.1	431.6	413.6	394.8	378.4	360.4	346.3	335.4	325.2	319.0	318.2
152.5°	446.1	428.4	411.7	396.1	380.3	364.8	351.3	341.7	332.7	326.5	326.3
155°	438.6	423.0	409.7	396.4	383.9	370.6	359.6	351.0	343.2	338.5	338.5
157.5°	430.2	418.1	407.0	397.2	385.9	375.3	366.8	359.5	352.6	348.8	348.2
160°	424.5	414.4	405.8	397.2	387.8	378.4	370.6	365.1	358.9	355.7	355.7
162.5°	418.9	410.6	403.3	396.5	388.4	380.3	373.7	368.9	363.9	361.4	361.4
165°	411.2	405.0	399.5	394.8	389.3	383.1	377.6	374.5	370.6	369.0	369.8
167.5°	403.9	399.4	395.8	393.6	389.2	384.7	381.2	379.0	376.1	375.3	376.2
170°	399.5	395.6	393.3	391.7	388.6	384.7	383.1	381.5	379.2	378.4	380.0
172.5°	395.1	392.5	391.4	391.1	388.6	385.3	384.3	383.4	381.7	381.5	382.5
175°	390.1	388.6	388.6	389.3	387.8	386.2	385.4	385.4	383.9	384.7	385.4
177.5°	386.8	386.2	386.8	388.1	386.8	386.2	386.2	386.2	385.6	386.2	386.8
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332020

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1413.2	1416.0	1425.2	1431.8	1439.4	1443.7	1448.1	1451.4	1455.7	1456.8	1472.6
5°	1419.5	1433.1	1456.9	1474.6	1496.4	1520.2	1536.5	1544.0	1563.8	1580.1	1612.8
7.5°	1417.7	1446.7	1482.7	1519.9	1560.0	1597.0	1629.1	1667.2	1694.3	1735.0	1775.1
10°	1416.1	1454.9	1501.2	1548.8	1604.6	1656.3	1702.6	1754.3	1797.2	1853.7	1902.0
12.5°	1411.2	1458.2	1522.4	1578.7	1646.5	1717.8	1786.4	1852.8	1890.8	1984.9	2029.4
15°	1399.1	1454.9	1535.2	1620.9	1714.2	1798.5	1885.6	1955.1	2067.3	2149.7	2202.1
17.5°	1376.0	1454.1	1549.3	1652.8	1766.1	1877.3	1976.0	2081.4	2200.4	2300.1	2406.2
20°	1365.1	1450.8	1557.0	1671.3	1789.0	1914.9	2027.2	2153.8	2283.7	2381.7	2517.8
22.5°	1344.9	1442.1	1556.4	1683.8	1809.7	1939.9	2071.3	2198.9	2349.1	2484.1	2613.6
25°	1312.0	1420.9	1539.3	1681.5	1829.2	1959.8	2117.0	2286.5	2443.0	2616.5	2745.8
27.5°	1277.4	1393.6	1512.3	1644.6	1803.4	1958.5	2156.2	2347.7	2539.0	2688.9	2784.6
30°	1250.7	1363.7	1486.2	1619.6	1776.8	1961.2	2182.3	2391.2	2577.7	2706.3	2760.1
32.5°	1221.9	1336.5	1444.8	1584.7	1752.3	1959.5	2198.7	2416.8	2579.9	2665.5	2655.0
35°	1176.6	1272.5	1378.0	1512.7	1710.1	1947.6	2208.2	2419.1	2519.2	2500.8	2362.0
37.5°	1111.2	1191.9	1295.8	1443.3	1661.1	1922.4	2189.1	2347.4	2340.9	2191.3	1990.2
40°	1070.4	1139.1	1239.2	1394.3	1623.0	1906.1	2159.2	2262.0	2174.9	1965.9	1725.0
42.5°	1017.1	1080.3	1180.4	1339.9	1581.1	1872.8	2102.0	2131.8	1961.4	1721.0	1500.2
45°	934.3	990.1	1093.5	1258.2	1518.2	1800.6	1962.5	1889.7	1660.4	1412.0	1243.9
47.5°	845.4	903.4	1002.9	1172.1	1427.3	1691.8	1769.0	1614.1	1378.7	1177.2	1022.9
50°	789.4	845.2	942.5	1113.3	1365.7	1602.6	1634.5	1434.5	1218.1	1041.2	914.6
52.5°	732.8	785.3	881.0	1052.3	1293.9	1499.1	1479.4	1275.5	1076.5	925.7	826.4
55°	648.5	698.2	789.4	950.0	1169.8	1332.4	1261.0	1066.3	901.7	784.6	709.1
57.5°	573.1	620.7	699.4	844.5	1035.6	1147.3	1056.4	892.4	761.5	671.4	615.0
60°	521.9	564.1	639.0	773.7	939.8	1024.8	935.0	790.1	679.8	607.7	557.3
62.5°	473.5	510.2	579.6	701.9	846.1	917.6	826.7	704.0	610.1	546.2	503.4
65°	400.1	433.5	494.7	590.0	708.4	756.0	677.8	578.4	505.6	458.0	429.4
67.5°	333.2	361.5	414.4	489.4	576.5	611.2	551.6	474.7	419.9	381.6	358.9
70°	288.5	313.0	354.5	419.2	498.1	524.7	468.9	405.6	365.4	334.8	313.7
72.5°	251.0	268.9	306.6	356.6	422.4	443.5	404.6	349.0	311.5	288.5	271.8
75°	191.2	206.2	230.7	270.8	316.4	328.7	299.4	264.7	239.5	223.2	210.3
77.5°	137.9	148.9	166.6	191.4	222.9	234.0	215.4	192.3	173.9	162.9	155.7
80°	104.1	113.0	127.9	148.3	167.4	173.5	162.6	144.9	132.0	125.9	119.8
82.5°	76.9	81.9	90.9	104.8	117.9	125.1	115.8	105.2	98.3	92.7	90.4
85°	38.8	41.5	45.6	51.0	59.2	61.9	58.5	55.8	51.7	48.3	48.3
87.5°	14.8	15.1	17.2	18.6	21.1	23.2	23.1	22.5	22.4	21.7	21.3
90°	3.1	4.7	7.0	8.6	10.2	12.5	14.9	17.2	19.5	18.8	19.5
92.5°	14.4	21.0	27.1	33.6	45.2	65.7	99.3	132.3	120.2	90.7	65.8
95°	28.9	37.5	50.8	71.1	101.6	168.1	284.6	412.8	463.6	376.1	281.5
97.5°	46.1	52.9	64.4	84.4	117.4	180.9	312.3	526.0	718.5	768.7	701.6
100°	58.6	64.1	75.1	93.8	124.3	179.0	294.7	500.4	740.4	894.4	921.8
102.5°	72.4	77.2	87.6	104.5	132.4	181.5	279.7	462.8	699.7	900.7	994.9
105°	93.0	97.7	107.1	122.0	146.2	188.4	268.9	416.7	628.6	853.0	1016.4
107.5°	114.0	118.5	127.7	141.7	164.2	201.2	268.2	387.3	565.7	769.5	954.8
110°	129.0	132.9	141.5	154.8	176.7	211.9	271.3	376.1	530.1	716.9	896.0



TEST NUMBER: P332020

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	142.8	146.7	155.3	168.6	189.8	222.5	277.5	369.8	506.3	671.3	837.8
115°	163.4	168.1	175.9	189.2	210.3	240.0	287.7	367.5	480.8	616.1	760.7
117.5°	183.7	187.6	194.8	209.7	229.2	258.6	301.2	368.9	465.8	582.8	704.9
120°	196.2	200.1	208.0	222.8	242.4	270.5	311.2	371.4	458.9	565.3	675.5
122.5°	208.1	212.0	220.5	234.7	255.5	283.0	320.5	375.7	454.6	550.9	652.4
125°	224.4	229.1	237.7	252.5	273.6	301.0	335.4	382.3	448.8	532.4	621.5
127.5°	238.1	243.9	252.7	269.1	290.2	316.6	347.6	389.8	446.0	516.2	594.7
130°	246.3	253.3	262.7	279.1	300.2	326.0	355.7	394.8	444.1	507.4	577.8
132.5°	253.2	260.8	272.1	288.5	309.0	334.1	363.2	398.6	443.4	499.3	562.1
135°	264.3	272.9	284.6	301.0	322.1	346.3	372.9	404.2	442.5	488.6	541.0
137.5°	274.7	283.2	295.7	311.9	331.5	354.8	380.1	408.0	440.8	479.4	521.8
140°	282.2	290.1	302.6	318.2	337.7	360.4	383.9	410.5	440.2	473.8	510.5
142.5°	289.1	297.6	308.8	324.5	342.7	364.8	387.6	412.3	438.9	468.8	499.9
145°	300.2	307.3	319.0	332.3	350.3	370.6	391.7	413.6	437.0	462.1	487.1
147.5°	311.5	318.4	328.5	341.3	356.7	375.3	394.2	413.6	434.1	455.5	476.6
150°	319.0	325.2	335.4	346.3	360.4	378.4	394.8	413.6	431.6	451.1	469.1
152.5°	326.5	332.7	341.7	351.3	364.8	380.3	396.1	411.7	428.4	446.1	462.2
155°	338.5	343.2	351.0	359.6	370.6	383.9	396.4	409.7	423.0	438.6	451.9
157.5°	348.8	352.6	359.5	366.8	375.3	385.9	397.2	407.0	418.1	430.2	440.9
160°	355.7	358.9	365.1	370.6	378.4	387.8	397.2	405.8	414.4	424.5	434.7
162.5°	361.4	363.9	368.9	373.7	380.3	388.4	396.5	403.3	410.6	418.9	427.2
165°	369.0	370.6	374.5	377.6	383.1	389.3	394.8	399.5	405.0	411.2	417.5
167.5°	375.3	376.1	379.0	381.2	384.7	389.2	393.6	395.8	399.4	403.9	409.0
170°	378.4	379.2	381.5	383.1	384.7	388.6	391.7	393.3	395.6	399.5	403.4
172.5°	381.5	381.7	383.4	384.3	385.3	388.6	391.1	391.4	392.5	395.1	398.4
175°	384.7	383.9	385.4	385.4	386.2	387.8	389.3	388.6	388.6	390.1	391.7
177.5°	386.2	385.6	386.2	386.2	386.2	386.8	388.1	386.8	386.2	386.8	387.5
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332020

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1478.0	1478.6	1484.6	1488.9	1486.7	1489.5	1490.5
5°	1614.8	1639.3	1652.2	1661.8	1662.4	1663.1	1668.6
7.5°	1808.7	1835.0	1854.2	1883.3	1892.0	1902.0	1899.1
10°	1950.3	1989.1	2022.4	2040.1	2059.2	2087.1	2064.6
12.5°	2082.6	2151.3	2202.1	2229.6	2247.5	2253.1	2242.1
15°	2300.7	2390.6	2438.9	2437.5	2498.8	2525.3	2483.8
17.5°	2500.8	2583.7	2650.1	2684.1	2735.2	2746.5	2741.3
20°	2623.3	2713.8	2765.5	2824.0	2850.6	2874.4	2878.5
22.5°	2728.9	2810.2	2865.7	2914.4	2936.6	2947.9	2954.7
25°	2837.6	2901.6	2935.0	2952.0	2958.1	2956.7	2947.9
27.5°	2830.2	2835.1	2798.3	2762.3	2730.0	2693.7	2681.1
30°	2756.7	2699.5	2597.4	2539.6	2454.5	2387.2	2414.4
32.5°	2563.4	2449.6	2335.0	2208.6	2103.9	2074.1	2044.2
35°	2187.8	1987.7	1870.7	1734.6	1680.1	1625.7	1588.3
37.5°	1770.0	1615.2	1476.4	1387.4	1332.8	1298.4	1279.9
40°	1530.4	1390.9	1276.6	1204.5	1163.0	1124.2	1118.7
42.5°	1339.3	1209.6	1123.6	1066.2	1026.3	1009.8	997.9
45°	1097.0	1006.4	948.6	907.8	881.2	871.0	857.4
47.5°	928.5	864.5	821.1	793.3	773.3	765.7	764.6
50°	834.3	781.2	749.2	727.4	711.8	709.1	698.2
52.5°	763.5	717.5	692.6	673.6	662.3	654.6	651.4
55°	662.8	632.2	609.7	598.8	590.0	582.5	582.5
57.5°	579.9	554.3	539.5	530.2	527.5	522.2	518.8
60°	528.7	507.0	495.4	487.2	481.8	482.5	476.3
62.5°	478.7	464.5	453.5	445.3	438.8	438.9	439.3
65°	407.6	396.7	388.6	385.8	381.8	377.0	378.4
67.5°	345.4	335.2	328.8	324.2	322.8	320.2	324.2
70°	300.8	293.3	288.5	284.4	283.1	283.8	287.2
72.5°	259.9	254.6	251.5	249.6	246.6	246.7	249.1
75°	204.1	200.1	197.3	195.3	194.6	194.6	194.6
77.5°	150.0	149.0	147.8	144.8	144.9	145.8	145.9
80°	118.4	116.4	115.7	114.3	112.3	110.9	114.3
82.5°	88.5	86.4	85.7	85.5	82.3	82.1	84.9
85°	47.6	45.6	46.3	45.6	45.6	44.9	44.9
87.5°	20.9	20.6	20.3	20.7	20.3	19.9	20.9
90°	20.3	21.1	22.7	21.9	22.7	23.5	22.7
92.5°	52.2	46.1	42.1	40.7	38.3	39.1	37.7
95°	190.8	149.3	121.2	106.3	99.3	93.8	90.7
97.5°	562.0	461.1	367.6	309.9	274.7	253.6	246.9
100°	858.4	767.0	655.9	577.0	519.9	489.4	490.2
102.5°	992.9	939.6	869.2	807.8	762.6	737.1	719.1
105°	1094.5	1109.4	1089.1	1053.1	1023.4	998.4	994.5
107.5°	1081.7	1150.2	1178.0	1178.7	1168.7	1160.2	1153.0
110°	1039.8	1138.3	1193.1	1214.9	1221.2	1219.6	1218.1



TEST NUMBER: P332020

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	984.8	1095.2	1165.5	1205.6	1225.0	1230.9	1231.2
115°	896.7	1011.7	1096.9	1155.5	1189.9	1205.6	1209.5
117.5°	822.3	925.5	1012.0	1073.1	1112.5	1135.0	1140.4
120°	781.0	874.9	953.8	1015.6	1059.4	1078.1	1082.8
122.5°	747.9	834.8	908.2	963.0	1002.4	1023.1	1029.0
125°	706.8	781.8	844.4	894.4	928.8	948.3	953.8
127.5°	670.6	738.4	795.3	839.8	869.2	886.9	891.9
130°	648.1	711.5	764.6	806.1	834.2	850.6	856.9
132.5°	626.9	685.8	736.5	775.4	803.6	818.1	822.5
135°	596.5	647.3	691.9	730.2	753.7	767.7	773.2
137.5°	567.3	611.1	649.7	681.9	705.7	717.6	721.2
140°	550.4	587.9	621.5	651.3	673.1	685.7	684.9
142.5°	534.1	566.7	595.9	621.2	640.6	651.9	651.1
145°	512.9	537.9	560.6	580.1	596.5	602.8	604.3
147.5°	497.1	517.3	533.4	548.2	559.3	565.3	565.9
150°	487.1	503.5	518.3	530.1	538.7	543.4	543.4
152.5°	477.7	492.2	504.6	513.8	521.8	524.6	524.6
155°	464.4	476.1	485.5	492.5	498.8	500.4	501.1
157.5°	451.4	460.5	467.8	473.9	478.6	479.9	479.7
160°	443.3	451.1	456.6	462.1	466.7	466.7	466.0
162.5°	434.5	441.7	446.6	450.2	454.2	454.2	453.5
165°	422.2	427.7	431.6	434.7	437.8	437.0	437.0
167.5°	412.6	415.8	418.6	420.0	422.2	421.4	421.4
170°	405.8	408.9	410.5	411.2	412.8	412.0	412.0
172.5°	400.1	402.6	403.6	403.7	405.3	403.9	403.3
175°	392.5	394.0	394.0	394.0	394.8	394.0	393.3
177.5°	388.1	388.7	388.7	388.1	388.7	387.5	387.5
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2

(END OF REPORT)