

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332264-927

Luminaire Tested: **S123RDIP-S340D1195U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332264-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D1195U927-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1195 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4854.7 lumens  
Efficiency: N/A  
Efficacy: 115.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332264-927

CATALOG NUMBER: S123RDIP-S340D1195U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - · - 135°-315°



TEST NUMBER: P332264-927

CATALOG NUMBER: S123RDIP-S340D1195U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	89	89	89	89	68	68	68	48	48	48	31	31	31	22
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	27	27	26	19
2	84	77	71	66	74	68	64	60	53	49	47	38	36	34	24	23	22	16
3	76	68	61	55	68	60	55	50	46	43	39	34	31	29	22	20	19	14
4	70	60	53	47	62	53	47	42	41	37	34	30	27	25	20	18	17	12
5	64	53	46	40	57	48	41	36	37	32	29	27	24	22	18	16	15	11
6	59	48	40	35	52	43	36	32	33	29	25	24	21	19	16	14	13	10
7	55	43	36	30	48	39	32	28	30	26	22	22	19	17	15	13	12	9
8	50	39	32	27	45	35	29	24	27	23	20	20	17	15	14	12	10	8
9	47	35	28	24	42	32	26	21	25	21	17	19	16	13	13	11	9	7
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4640	4640	4640	4640
5°	5532	4660	4105	4660
10°	6907	4634	3707	4634
15°	8107	4586	3381	4586
20°	9049	4515	3103	4515
25°	8904	4441	2932	4441
30°	6400	4373	2757	4373
35°	4273	4282	2643	4282
40°	3147	4175	2525	4175
45°	2641	3987	2411	3987
50°	2331	3739	2251	3739
55°	2044	3457	2029	3457
60°	1819	3186	1858	3186
65°	1597	2896	1729	2896
70°	1253	2637	1580	2637
75°	1102	2304	1443	2304
80°	961	1953	1420	1953
85°	778	1581	1507	1581



TEST NUMBER: P332264-927

CATALOG NUMBER: S123RDIP-S340D1195U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.4	0.9
10°-20°	132.5	2.7
20°-30°	208.1	4.3
30°-40°	217.1	4.5
40°-50°	185.8	3.8
50°-60°	141.6	2.9
60°-70°	90.8	1.9
70°-80°	43.7	0.9
80°-90°	15.0	0.3
90°-100°	45.0	0.9
100°-110°	214.7	4.4
110°-120°	515.6	10.6
120°-130°	656.6	13.5
130°-140°	701.5	14.5
140°-150°	656.0	13.5
150°-160°	529.2	10.9
160°-170°	341.5	7.0
170°-180°	117.7	2.4
0°-30°	382.9	7.9
0°-40°	600.1	12.4
0°-60°	927.5	19.1
0°-90°	1076.9	22.2
90°-120°	775.3	16.0
90°-150°	2789.4	57.5
90°-180°	3778.0	77.8
0°-180°	4854.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	431	431	431	431	431	
5°	512	431	380	431	512	53
15°	728	412	303	412	728	206
25°	750	374	247	374	750	322
35°	325	326	201	326	325	213
45°	174	262	158	262	174	136
55°	109	184	108	184	109	98
65°	63	114	68	114	63	62
75°	26	55	35	55	26	28
85°	6	13	12	13	6	8
90°	28	1	28	1	28	13
95°	35	56	35	56	35	29
105°	40	274	40	274	40	93
115°	541	514	541	514	541	500
125°	740	725	740	725	740	661
135°	912	903	912	903	912	703
145°	1052	1042	1052	1042	1052	657
155°	1146	1148	1146	1148	1146	528
165°	1208	1210	1208	1210	1208	341
175°	1234	1239	1234	1239	1234	117
180°	1239	1239	1239	1239	1239	



TEST NUMBER: P332264-927

CATALOG NUMBER: S123RDIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	459.2	459.8	457.9	457.6	455.3	454.8	454.8	451.6	449.7	447.3	445.8
5°	512.0	514.9	513.4	510.2	504.6	503.3	499.8	494.2	488.0	480.2	476.6
7.5°	577.9	581.9	580.4	575.3	569.4	564.7	554.8	545.7	532.8	521.5	511.8
10°	631.9	627.7	624.4	619.4	614.0	605.4	595.0	580.8	564.4	551.4	537.1
12.5°	672.4	671.7	667.5	662.3	654.8	646.6	633.8	616.6	597.5	578.8	562.3
15°	727.5	728.6	725.9	720.6	709.8	695.2	676.0	668.8	641.5	621.2	600.9
17.5°	765.7	765.5	765.1	757.7	746.8	736.4	718.6	699.7	674.9	646.3	619.0
20°	790.0	788.1	788.5	780.1	772.1	760.0	742.7	715.2	694.9	661.9	633.6
22.5°	789.3	788.9	790.4	787.5	781.6	772.5	758.8	735.5	709.6	676.3	644.5
25°	749.7	748.2	756.9	759.3	768.7	770.4	766.3	753.6	729.0	694.7	655.4
27.5°	627.4	626.6	642.7	662.9	688.4	708.3	727.5	736.7	729.0	704.4	665.0
30°	514.9	532.3	540.4	569.6	602.1	640.8	674.8	707.0	715.0	704.3	672.0
32.5°	427.5	442.7	449.5	474.4	504.8	550.2	601.1	646.8	679.1	687.3	667.9
35°	325.2	325.3	340.9	352.0	380.0	426.7	476.2	537.4	598.3	644.5	649.3
37.5°	259.5	260.4	269.8	280.8	301.9	326.5	370.1	421.0	491.4	562.2	603.8
40°	224.0	225.7	232.7	243.6	258.7	277.4	311.3	359.3	418.0	496.9	561.3
42.5°	201.3	204.0	207.6	216.0	225.4	242.9	270.3	307.4	360.8	435.3	509.6
45°	173.5	175.0	177.8	181.6	190.1	202.2	220.7	245.7	289.9	349.9	424.3
47.5°	153.0	152.3	155.2	158.3	164.0	172.3	184.7	204.9	236.5	284.7	347.8
50°	139.2	138.9	141.0	143.4	148.8	154.9	165.0	180.3	205.4	245.3	303.1
52.5°	126.2	126.8	128.3	131.3	135.1	140.1	149.2	160.3	181.8	216.2	264.4
55°	108.9	109.5	111.5	113.1	115.9	120.9	126.6	135.9	150.6	174.6	214.3
57.5°	94.3	94.0	95.9	96.4	99.5	103.5	108.0	115.2	125.9	143.7	170.4
60°	84.5	84.0	85.6	86.9	88.6	91.9	95.6	102.6	111.1	124.2	147.1
62.5°	75.7	75.4	76.6	78.0	79.3	82.3	85.4	90.8	97.5	108.5	126.7
65°	62.7	63.3	63.8	64.4	65.1	67.0	69.9	73.7	78.3	86.0	99.1
67.5°	49.4	49.9	50.1	51.2	52.8	53.9	55.8	59.0	62.3	68.8	76.2
70°	39.8	39.7	39.8	40.4	42.5	44.4	46.9	49.3	51.3	55.9	62.2
72.5°	34.2	33.9	34.4	34.5	35.5	36.0	37.5	39.8	42.5	45.6	50.1
75°	26.5	26.5	26.5	26.5	27.3	27.6	28.2	28.8	29.7	31.2	34.5
77.5°	19.6	19.6	20.0	20.1	20.3	20.5	20.8	21.4	21.7	22.5	23.9
80°	15.5	15.7	15.5	15.7	15.7	16.1	16.2	16.8	17.0	17.9	18.5
82.5°	11.6	11.6	11.6	11.9	11.9	12.2	12.3	12.7	12.7	13.2	13.7
85°	6.3	5.9	6.3	6.1	6.5	6.1	6.3	6.7	6.7	6.8	7.6
87.5°	7.0	7.2	6.8	6.9	6.8	6.8	6.7	6.5	6.7	6.3	5.9
90°	27.6	27.2	26.8	26.4	26.0	25.3	24.6	23.7	22.9	22.1	19.4
92.5°	30.6	30.3	30.1	29.8	29.5	28.8	27.5	26.1	24.9	23.5	21.5
95°	34.9	34.9	34.9	34.9	34.9	34.2	32.8	31.4	29.9	28.5	26.3
97.5°	37.9	37.7	37.5	37.3	37.1	36.2	34.5	32.9	31.3	29.6	44.4
100°	38.7	38.4	38.3	38.0	37.9	36.9	35.3	33.7	32.0	30.3	62.3
102.5°	39.4	39.1	38.7	38.3	37.9	40.2	45.3	50.4	55.5	60.5	95.4
105°	40.5	40.1	39.7	39.3	38.9	56.7	92.9	129.1	165.3	201.5	220.0
107.5°	127.2	154.5	181.7	209.1	236.3	263.2	289.8	316.3	342.9	369.5	366.5
110°	253.1	282.3	311.6	340.9	370.1	388.1	394.8	401.6	408.4	415.1	412.8



TEST NUMBER: P332264-927

CATALOG NUMBER: S123RDIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	434.2	440.4	446.6	452.7	458.9	462.0	461.8	461.7	461.6	461.4	459.2
115°	541.1	540.3	539.6	538.7	537.9	536.5	534.4	532.3	530.4	528.3	526.5
117.5°	601.2	601.0	600.9	600.7	600.6	599.6	598.0	596.4	594.7	593.1	592.2
120°	642.4	642.4	642.4	642.4	642.4	641.6	639.9	638.3	636.7	635.0	634.5
122.5°	682.9	682.8	682.5	682.4	682.2	681.6	680.5	679.3	678.2	677.0	676.2
125°	740.0	739.6	739.2	738.7	738.3	737.9	737.5	737.1	736.7	736.3	735.5
127.5°	794.8	795.3	795.7	796.1	796.5	796.3	795.7	795.0	794.4	793.7	792.7
130°	830.2	830.6	831.0	831.4	831.8	831.6	830.8	830.0	829.2	828.3	827.5
132.5°	862.5	863.2	863.7	864.3	864.8	864.7	864.0	863.1	862.3	861.5	860.8
135°	912.1	912.7	913.3	913.9	914.6	914.6	913.9	913.3	912.7	912.1	911.2
137.5°	958.6	959.1	959.5	959.9	960.3	960.0	959.0	958.1	957.0	956.1	955.6
140°	986.7	987.1	987.5	987.9	988.2	988.1	987.2	986.4	985.6	984.8	984.2
142.5°	1012.4	1013.0	1013.5	1014.2	1014.7	1014.6	1014.0	1013.4	1012.7	1012.0	1011.5
145°	1051.9	1051.9	1051.9	1051.9	1051.9	1051.8	1051.4	1051.0	1050.5	1050.1	1049.7
147.5°	1081.4	1082.4	1083.3	1084.3	1085.2	1085.4	1085.1	1084.7	1084.3	1083.8	1083.4
150°	1103.5	1104.1	1104.8	1105.3	1106.0	1106.0	1105.6	1105.3	1104.9	1104.5	1104.1
152.5°	1121.2	1122.1	1123.1	1124.0	1125.0	1125.1	1124.3	1123.6	1122.8	1122.1	1121.9
155°	1145.9	1147.1	1148.3	1149.5	1150.7	1150.9	1149.9	1148.8	1147.8	1146.8	1146.6
157.5°	1166.6	1168.2	1169.8	1171.5	1173.1	1173.2	1172.0	1170.8	1169.6	1168.3	1168.5
160°	1179.9	1181.3	1182.8	1184.2	1185.7	1185.7	1184.5	1183.3	1182.1	1180.8	1181.1
162.5°	1192.4	1193.7	1194.9	1196.2	1197.5	1197.5	1196.0	1194.7	1193.3	1191.8	1192.1
165°	1207.5	1208.9	1210.4	1211.8	1213.2	1213.1	1211.5	1209.9	1208.2	1206.6	1206.8
167.5°	1218.4	1220.0	1221.6	1223.3	1225.0	1225.0	1223.3	1221.6	1220.0	1218.4	1218.4
170°	1225.0	1226.6	1228.3	1229.9	1231.5	1231.5	1229.9	1228.3	1226.6	1225.0	1225.0
172.5°	1228.7	1230.5	1232.3	1234.1	1235.9	1236.0	1234.3	1232.7	1231.1	1229.4	1229.2
175°	1234.2	1235.9	1237.5	1239.1	1240.7	1240.9	1239.4	1238.0	1236.6	1235.1	1234.9
177.5°	1235.9	1237.5	1239.1	1240.8	1242.4	1242.5	1241.3	1239.9	1238.7	1237.3	1237.2
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P332264-927

CATALOG NUMBER: S123RDIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	445.1	444.7	442.7	440.3	437.2	435.1	433.5	432.6	429.9	426.7	424.5
5°	472.7	467.1	461.2	454.0	447.3	440.5	436.3	431.3	425.2	418.4	413.6
7.5°	502.1	491.2	479.6	467.5	455.6	444.9	435.4	427.3	417.6	407.8	401.0
10°	524.7	508.8	492.4	475.6	460.3	445.9	434.8	424.0	412.3	401.1	392.5
12.5°	545.3	524.3	505.4	484.7	465.2	448.0	432.1	419.2	405.2	393.2	383.6
15°	571.2	549.8	527.0	495.5	469.5	447.7	428.3	411.5	394.6	379.9	370.4
17.5°	595.5	563.3	532.5	506.4	472.5	445.4	421.7	401.6	382.9	367.3	355.7
20°	605.5	574.3	541.0	507.6	474.4	443.9	416.4	394.2	374.9	357.1	346.4
22.5°	611.6	576.3	541.1	505.2	469.9	438.2	411.1	386.7	365.7	348.9	335.6
25°	618.6	576.6	537.8	502.4	466.4	432.1	399.7	373.9	351.3	333.4	319.3
27.5°	623.3	573.8	528.0	488.6	452.1	418.0	388.3	360.9	337.9	318.9	303.9
30°	624.2	571.6	520.5	477.8	440.8	409.3	378.0	351.8	327.4	307.3	293.3
32.5°	625.3	566.1	510.2	465.0	427.0	395.9	367.5	342.5	317.5	297.7	283.4
35°	620.5	563.1	494.8	442.8	404.7	374.6	349.0	325.9	301.4	282.2	267.6
37.5°	599.5	551.1	478.8	417.7	378.0	350.1	329.2	309.1	286.6	265.9	252.2
40°	578.5	539.3	466.4	402.5	361.0	332.4	313.5	297.1	275.4	256.0	241.2
42.5°	547.0	523.2	454.6	386.6	341.8	314.3	298.3	283.0	263.9	244.2	230.3
45°	489.3	492.4	430.4	361.2	315.2	287.6	272.6	261.9	244.9	228.7	214.4
47.5°	416.9	446.2	402.0	334.1	287.2	261.3	248.2	238.8	227.4	211.4	198.4
50°	369.7	411.5	379.3	316.0	269.7	243.8	230.9	223.3	213.3	200.8	188.5
52.5°	326.1	371.1	351.8	295.7	250.6	227.0	214.4	208.1	200.2	188.4	177.2
55°	265.9	311.6	307.1	265.2	222.0	200.8	191.2	184.2	178.9	170.0	161.1
57.5°	215.2	258.3	260.6	231.2	196.9	175.9	167.6	162.3	158.8	152.2	143.9
60°	183.1	222.8	230.5	208.3	178.9	160.4	152.3	148.0	145.3	139.9	133.6
62.5°	156.5	190.3	199.1	183.2	161.6	144.3	137.9	133.9	132.0	127.4	121.8
65°	119.8	147.8	156.3	147.5	136.2	122.4	117.2	113.7	112.0	109.5	105.4
67.5°	90.1	110.5	119.9	113.6	109.5	100.8	97.5	95.6	94.1	92.4	89.0
70°	72.3	87.5	97.0	95.5	92.1	87.5	85.1	83.8	82.3	80.8	77.9
72.5°	58.1	68.6	77.6	78.4	75.7	74.8	72.6	72.1	71.2	69.5	67.8
75°	38.6	45.8	52.0	54.4	55.5	56.5	55.5	55.4	55.2	53.7	52.8
77.5°	25.3	29.2	33.1	37.2	39.0	40.2	40.5	41.2	40.6	39.9	39.5
80°	19.4	20.3	23.1	26.5	29.3	30.4	31.2	31.5	31.4	31.2	30.4
82.5°	14.1	14.8	16.2	18.6	20.9	22.7	23.2	23.1	23.5	23.7	23.1
85°	7.6	7.8	8.2	8.5	9.7	11.8	12.4	12.8	13.1	13.1	12.0
87.5°	5.7	5.1	4.8	4.4	4.4	4.1	4.6	4.9	5.5	5.3	5.7
90°	16.8	14.1	11.5	9.1	7.1	5.0	2.9	1.0	2.9	5.0	7.1
92.5°	19.6	17.6	15.5	14.8	15.4	16.0	16.6	17.1	16.6	16.0	15.4
95°	24.0	21.8	19.6	22.6	31.0	39.4	47.8	56.2	47.8	39.4	31.0
97.5°	59.1	73.8	88.6	97.8	101.6	105.3	109.1	112.8	109.1	105.3	101.6
100°	94.2	126.1	158.0	171.9	167.8	163.7	159.6	155.5	159.6	163.7	167.8
102.5°	130.2	165.1	199.9	215.9	212.9	210.0	207.1	204.1	207.1	210.0	212.9
105°	238.4	256.7	275.2	283.3	281.0	278.8	276.6	274.3	276.6	278.8	281.0
107.5°	363.6	360.8	357.8	355.5	353.6	351.9	350.1	348.2	350.1	351.9	353.6
110°	410.6	408.4	406.1	404.2	402.5	400.8	399.3	397.6	399.3	400.8	402.5





TEST NUMBER: P332264-927

CATALOG NUMBER: S123RDIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	457.0	454.7	452.5	450.6	449.2	447.7	446.2	444.7	446.2	447.7	449.2
115°	524.6	522.8	520.9	519.4	518.2	516.9	515.7	514.5	515.7	516.9	518.2
117.5°	591.2	590.3	589.3	588.1	586.6	585.0	583.5	582.0	583.5	585.0	586.6
120°	633.8	633.2	632.6	631.4	629.5	627.7	625.8	624.0	625.8	627.7	629.5
122.5°	675.5	674.7	673.9	672.8	671.2	669.7	668.2	666.7	668.2	669.7	671.2
125°	734.7	733.8	733.0	731.8	730.2	728.5	726.9	725.2	726.9	728.5	730.2
127.5°	791.8	790.8	789.8	788.5	786.9	785.2	783.5	782.0	783.5	785.2	786.9
130°	826.7	825.9	825.1	823.8	822.2	820.5	819.0	817.3	819.0	820.5	822.2
132.5°	860.2	859.5	858.8	857.7	856.0	854.4	852.8	851.1	852.8	854.4	856.0
135°	910.5	909.7	908.8	907.8	906.6	905.3	904.1	902.9	904.1	905.3	906.6
137.5°	955.2	954.7	954.3	953.3	951.7	950.1	948.6	947.1	948.6	950.1	951.7
140°	983.6	982.9	982.3	981.4	980.2	979.0	977.7	976.5	977.7	979.0	980.2
142.5°	1010.8	1010.2	1009.6	1008.7	1007.4	1006.2	1005.0	1003.8	1005.0	1006.2	1007.4
145°	1049.3	1048.9	1048.5	1047.6	1046.2	1044.7	1043.3	1041.9	1043.3	1044.7	1046.2
147.5°	1083.0	1082.6	1082.2	1081.5	1080.5	1079.7	1078.7	1077.8	1078.7	1079.7	1080.5
150°	1103.6	1103.2	1102.8	1102.3	1101.7	1101.1	1100.4	1099.9	1100.4	1101.1	1101.7
152.5°	1121.7	1121.3	1121.1	1120.9	1120.5	1120.3	1120.0	1119.7	1120.0	1120.3	1120.5
155°	1146.4	1146.1	1146.0	1146.1	1146.4	1146.8	1147.3	1147.7	1147.3	1146.8	1146.4
157.5°	1168.7	1168.9	1169.1	1169.3	1169.3	1169.3	1169.3	1169.4	1169.3	1169.3	1169.3
160°	1181.2	1181.5	1181.6	1181.9	1182.1	1182.3	1182.5	1182.6	1182.5	1182.3	1182.1
162.5°	1192.3	1192.5	1192.7	1193.0	1193.6	1194.1	1194.7	1195.2	1194.7	1194.1	1193.6
165°	1207.0	1207.2	1207.4	1207.8	1208.5	1209.0	1209.7	1210.3	1209.7	1209.0	1208.5
167.5°	1218.4	1218.4	1218.4	1218.8	1219.6	1220.4	1221.2	1222.1	1221.2	1220.4	1219.6
170°	1225.0	1225.0	1225.0	1225.4	1226.2	1227.1	1227.9	1228.7	1227.9	1227.1	1226.2
172.5°	1229.1	1228.9	1228.8	1229.2	1230.2	1231.1	1232.2	1233.1	1232.2	1231.1	1230.2
175°	1234.7	1234.5	1234.3	1234.7	1235.7	1236.8	1237.8	1238.8	1237.8	1236.8	1235.7
177.5°	1237.0	1236.8	1236.7	1237.0	1237.9	1238.7	1239.4	1240.3	1239.4	1238.7	1237.9
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P332264-927

CATALOG NUMBER: S123RDIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	423.7	421.8	420.5	417.6	415.7	413.6	411.5	412.8	412.6	412.6	412.6
5°	409.6	405.3	401.4	396.4	393.3	389.4	386.5	386.1	386.8	384.3	382.8
7.5°	395.5	389.7	384.1	378.7	372.8	368.1	365.3	363.8	362.0	360.4	358.8
10°	385.6	378.7	373.4	366.5	360.3	354.7	351.3	348.8	347.5	346.3	343.8
12.5°	375.3	368.7	361.9	354.1	348.2	341.7	339.1	336.4	334.0	332.5	329.2
15°	360.4	351.8	344.6	336.4	329.8	323.5	319.9	314.5	313.8	311.9	308.6
17.5°	345.5	336.1	326.1	320.1	312.7	306.1	300.5	298.7	293.4	291.4	288.5
20°	333.7	325.0	317.4	309.5	298.7	292.6	288.1	285.7	281.5	278.8	277.0
22.5°	323.5	314.7	305.9	296.7	287.7	280.8	277.6	273.9	271.6	267.9	265.9
25°	309.0	299.4	288.8	278.8	272.4	267.3	262.1	258.7	255.4	253.7	250.1
27.5°	292.1	282.0	272.2	264.6	256.7	251.6	246.9	244.0	240.0	237.2	235.1
30°	282.7	270.9	262.4	255.6	245.5	240.7	237.2	233.5	230.5	227.6	225.5
32.5°	272.0	261.2	253.2	244.7	236.9	231.6	227.1	223.9	221.3	218.6	216.5
35°	255.1	246.1	237.7	229.3	223.5	218.2	212.8	210.0	207.6	205.0	203.2
37.5°	239.8	231.3	223.4	215.4	208.3	203.9	199.6	197.5	194.2	192.5	190.7
40°	230.4	222.0	213.6	205.8	198.4	195.1	191.2	188.1	185.1	183.8	181.8
42.5°	220.0	211.7	204.5	196.2	190.1	185.6	182.0	178.6	176.4	174.5	173.4
45°	204.7	197.3	190.3	182.0	176.3	172.4	168.3	165.2	163.2	161.8	159.9
47.5°	189.8	182.4	175.3	168.1	162.6	158.1	154.0	151.9	149.2	147.6	146.2
50°	179.0	172.4	164.9	158.2	152.7	148.2	144.9	142.1	139.7	137.7	136.7
52.5°	169.1	162.1	155.5	149.3	143.5	138.5	135.5	132.5	130.7	128.4	127.3
55°	152.8	146.0	140.5	134.4	128.7	124.4	120.7	118.1	116.3	113.7	112.3
57.5°	137.5	131.3	124.8	119.5	113.6	110.0	106.9	103.5	101.2	99.2	97.7
60°	127.1	120.2	114.4	109.5	104.3	99.7	96.9	94.1	91.7	89.7	88.4
62.5°	116.4	110.3	104.8	99.4	94.7	90.6	87.5	85.2	83.0	81.8	80.4
65°	99.8	95.1	89.5	85.1	80.6	77.7	75.1	73.1	71.6	70.7	69.6
67.5°	84.6	80.0	75.2	70.8	67.8	65.6	63.9	62.2	61.4	60.2	59.5
70°	74.8	69.9	65.7	62.3	59.4	57.8	56.6	55.4	54.7	53.2	52.4
72.5°	64.0	60.5	57.4	54.7	52.4	50.9	49.4	47.8	46.7	45.0	44.3
75°	50.4	47.2	44.8	43.0	41.5	39.5	37.5	35.8	35.3	34.7	34.5
77.5°	37.3	35.3	33.6	32.0	30.2	28.8	28.3	27.9	27.8	27.5	27.5
80°	29.3	27.5	26.2	24.4	23.3	23.3	23.3	22.9	23.1	23.1	23.1
82.5°	21.8	20.1	19.4	18.8	18.5	18.7	18.7	18.8	18.6	18.9	18.8
85°	11.2	11.4	11.8	11.6	11.8	11.8	12.2	12.0	12.2	11.8	12.2
87.5°	5.9	6.9	7.5	8.2	8.9	9.3	9.6	9.7	10.1	10.2	10.4
90°	9.1	11.5	14.1	16.8	19.4	22.1	22.9	23.7	24.6	25.3	26.0
92.5°	14.8	15.5	17.6	19.6	21.5	23.5	24.9	26.1	27.5	28.8	29.5
95°	22.6	19.6	21.8	24.0	26.3	28.5	29.9	31.4	32.8	34.2	34.9
97.5°	97.8	88.6	73.8	59.1	44.4	29.6	31.3	32.9	34.5	36.2	37.1
100°	171.9	158.0	126.1	94.2	62.3	30.3	32.0	33.7	35.3	36.9	37.9
102.5°	215.9	199.9	165.1	130.2	95.4	60.5	55.5	50.4	45.3	40.2	37.9
105°	283.3	275.2	256.7	238.4	220.0	201.5	165.3	129.1	92.9	56.7	38.9
107.5°	355.5	357.8	360.8	363.6	366.5	369.5	342.9	316.3	289.8	263.2	236.3
110°	404.2	406.1	408.4	410.6	412.8	415.1	408.4	401.6	394.8	388.1	370.1



TEST NUMBER: P332264-927

CATALOG NUMBER: S123RDIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	450.6	452.5	454.7	457.0	459.2	461.4	461.6	461.7	461.8	462.0	458.9
115°	519.4	520.9	522.8	524.6	526.5	528.3	530.4	532.3	534.4	536.5	537.9
117.5°	588.1	589.3	590.3	591.2	592.2	593.1	594.7	596.4	598.0	599.6	600.6
120°	631.4	632.6	633.2	633.8	634.5	635.0	636.7	638.3	639.9	641.6	642.4
122.5°	672.8	673.9	674.7	675.5	676.2	677.0	678.2	679.3	680.5	681.6	682.2
125°	731.8	733.0	733.8	734.7	735.5	736.3	736.7	737.1	737.5	737.9	738.3
127.5°	788.5	789.8	790.8	791.8	792.7	793.7	794.4	795.0	795.7	796.3	796.5
130°	823.8	825.1	825.9	826.7	827.5	828.3	829.2	830.0	830.8	831.6	831.8
132.5°	857.7	858.8	859.5	860.2	860.8	861.5	862.3	863.1	864.0	864.7	864.8
135°	907.8	908.8	909.7	910.5	911.2	912.1	912.7	913.3	913.9	914.6	914.6
137.5°	953.3	954.3	954.7	955.2	955.6	956.1	957.0	958.1	959.0	960.0	960.3
140°	981.4	982.3	982.9	983.6	984.2	984.8	985.6	986.4	987.2	988.1	988.2
142.5°	1008.7	1009.6	1010.2	1010.8	1011.5	1012.0	1012.7	1013.4	1014.0	1014.6	1014.7
145°	1047.6	1048.5	1048.9	1049.3	1049.7	1050.1	1050.5	1051.0	1051.4	1051.8	1051.9
147.5°	1081.5	1082.2	1082.6	1083.0	1083.4	1083.8	1084.3	1084.7	1085.1	1085.4	1085.2
150°	1102.3	1102.8	1103.2	1103.6	1104.1	1104.5	1104.9	1105.3	1105.6	1106.0	1106.0
152.5°	1120.9	1121.1	1121.3	1121.7	1121.9	1122.1	1122.8	1123.6	1124.3	1125.1	1125.0
155°	1146.1	1146.0	1146.1	1146.4	1146.6	1146.8	1147.8	1148.8	1149.9	1150.9	1150.7
157.5°	1169.3	1169.1	1168.9	1168.7	1168.5	1168.3	1169.6	1170.8	1172.0	1173.2	1173.1
160°	1181.9	1181.6	1181.5	1181.2	1181.1	1180.8	1182.1	1183.3	1184.5	1185.7	1185.7
162.5°	1193.0	1192.7	1192.5	1192.3	1192.1	1191.8	1193.3	1194.7	1196.0	1197.5	1197.5
165°	1207.8	1207.4	1207.2	1207.0	1206.8	1206.6	1208.2	1209.9	1211.5	1213.1	1213.2
167.5°	1218.8	1218.4	1218.4	1218.4	1218.4	1218.4	1220.0	1221.6	1223.3	1225.0	1225.0
170°	1225.4	1225.0	1225.0	1225.0	1225.0	1225.0	1226.6	1228.3	1229.9	1231.5	1231.5
172.5°	1229.2	1228.8	1228.9	1229.1	1229.2	1229.4	1231.1	1232.7	1234.3	1236.0	1235.9
175°	1234.7	1234.3	1234.5	1234.7	1234.9	1235.1	1236.6	1238.0	1239.4	1240.9	1240.7
177.5°	1237.0	1236.7	1236.8	1237.0	1237.2	1237.3	1238.7	1239.9	1241.3	1242.5	1242.4
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P332264-927

CATALOG NUMBER: S123RDIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	410.7	410.6	410.7	410.2	410.7	410.6	410.7	412.6	412.6	412.6	412.8
5°	382.2	382.1	381.5	379.9	381.5	382.1	382.2	382.8	384.3	386.8	386.1
7.5°	357.3	357.0	355.5	355.5	355.5	357.0	357.3	358.8	360.4	362.0	363.8
10°	342.5	342.7	340.5	339.2	340.5	342.7	342.5	343.8	346.3	347.5	348.8
12.5°	328.2	327.4	325.6	324.2	325.6	327.4	328.2	329.2	332.5	334.0	336.4
15°	309.3	307.4	303.1	303.4	303.1	307.4	309.3	308.6	311.9	313.8	314.5
17.5°	287.1	285.7	285.7	283.0	285.7	285.7	287.1	288.5	291.4	293.4	298.7
20°	274.1	273.1	273.5	270.9	273.5	273.1	274.1	277.0	278.8	281.5	285.7
22.5°	263.9	262.9	261.4	260.6	261.4	262.9	263.9	265.9	267.9	271.6	273.9
25°	249.0	247.5	246.1	246.9	246.1	247.5	249.0	250.1	253.7	255.4	258.7
27.5°	234.1	233.0	231.5	231.3	231.5	233.0	234.1	235.1	237.2	240.0	244.0
30°	224.6	223.5	222.8	221.8	222.8	223.5	224.6	225.5	227.6	230.5	233.5
32.5°	215.0	214.8	213.5	213.3	213.5	214.8	215.0	216.5	218.6	221.3	223.9
35°	202.5	201.4	201.0	201.1	201.0	201.4	202.5	203.2	205.0	207.6	210.0
37.5°	190.5	189.1	188.4	187.7	188.4	189.1	190.5	190.7	192.5	194.2	197.5
40°	182.0	180.5	180.1	179.7	180.1	180.5	182.0	181.8	183.8	185.1	188.1
42.5°	172.4	171.8	171.6	170.9	171.6	171.8	172.4	173.4	174.5	176.4	178.6
45°	159.3	159.1	158.0	158.4	158.0	159.1	159.3	159.9	161.8	163.2	165.2
47.5°	145.4	144.7	143.9	144.4	143.9	144.7	145.4	146.2	147.6	149.2	151.9
50°	136.0	135.6	134.0	134.4	134.0	135.6	136.0	136.7	137.7	139.7	142.1
52.5°	126.6	125.2	124.5	124.3	124.5	125.2	126.6	127.3	128.4	130.7	132.5
55°	110.9	109.2	108.5	108.1	108.5	109.2	110.9	112.3	113.7	116.3	118.1
57.5°	95.5	95.1	94.5	94.9	94.5	95.1	95.5	97.7	99.2	101.2	103.5
60°	86.6	86.6	86.6	86.3	86.6	86.6	86.6	88.4	89.7	91.7	94.1
62.5°	79.6	79.1	79.1	79.3	79.1	79.1	79.6	80.4	81.8	83.0	85.2
65°	69.0	68.8	68.1	67.9	68.1	68.8	69.0	69.6	70.7	71.6	73.1
67.5°	59.0	58.4	58.1	57.9	58.1	58.4	59.0	59.5	60.2	61.4	62.2
70°	51.5	51.1	50.0	50.2	50.0	51.1	51.5	52.4	53.2	54.7	55.4
72.5°	43.4	43.0	42.8	42.5	42.8	43.0	43.4	44.3	45.0	46.7	47.8
75°	34.3	34.1	34.0	34.7	34.0	34.1	34.3	34.5	34.7	35.3	35.8
77.5°	27.5	27.5	27.6	27.3	27.6	27.5	27.5	27.5	27.5	27.8	27.9
80°	23.1	23.1	22.9	22.9	22.9	23.1	23.1	23.1	23.1	23.1	22.9
82.5°	18.5	18.6	18.8	18.5	18.8	18.6	18.5	18.8	18.9	18.6	18.8
85°	12.2	12.0	12.4	12.2	12.4	12.0	12.2	12.2	11.8	12.2	12.0
87.5°	10.8	10.5	10.6	10.9	10.6	10.5	10.8	10.4	10.2	10.1	9.7
90°	26.4	26.8	27.2	27.6	27.2	26.8	26.4	26.0	25.3	24.6	23.7
92.5°	29.8	30.1	30.3	30.6	30.3	30.1	29.8	29.5	28.8	27.5	26.1
95°	34.9	34.9	34.9	34.9	34.9	34.9	34.9	34.9	34.2	32.8	31.4
97.5°	37.3	37.5	37.7	37.9	37.7	37.5	37.3	37.1	36.2	34.5	32.9
100°	38.0	38.3	38.4	38.7	38.4	38.3	38.0	37.9	36.9	35.3	33.7
102.5°	38.3	38.7	39.1	39.4	39.1	38.7	38.3	37.9	40.2	45.3	50.4
105°	39.3	39.7	40.1	40.5	40.1	39.7	39.3	38.9	56.7	92.9	129.1
107.5°	209.1	181.7	154.5	127.2	154.5	181.7	209.1	236.3	263.2	289.8	316.3
110°	340.9	311.6	282.3	253.1	282.3	311.6	340.9	370.1	388.1	394.8	401.6



TEST NUMBER: P332264-927

CATALOG NUMBER: S123RDIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	452.7	446.6	440.4	434.2	440.4	446.6	452.7	458.9	462.0	461.8	461.7
115°	538.7	539.6	540.3	541.1	540.3	539.6	538.7	537.9	536.5	534.4	532.3
117.5°	600.7	600.9	601.0	601.2	601.0	600.9	600.7	600.6	599.6	598.0	596.4
120°	642.4	642.4	642.4	642.4	642.4	642.4	642.4	642.4	641.6	639.9	638.3
122.5°	682.4	682.5	682.8	682.9	682.8	682.5	682.4	682.2	681.6	680.5	679.3
125°	738.7	739.2	739.6	740.0	739.6	739.2	738.7	738.3	737.9	737.5	737.1
127.5°	796.1	795.7	795.3	794.8	795.3	795.7	796.1	796.5	796.3	795.7	795.0
130°	831.4	831.0	830.6	830.2	830.6	831.0	831.4	831.8	831.6	830.8	830.0
132.5°	864.3	863.7	863.2	862.5	863.2	863.7	864.3	864.8	864.7	864.0	863.1
135°	913.9	913.3	912.7	912.1	912.7	913.3	913.9	914.6	914.6	913.9	913.3
137.5°	959.9	959.5	959.1	958.6	959.1	959.5	959.9	960.3	960.0	959.0	958.1
140°	987.9	987.5	987.1	986.7	987.1	987.5	987.9	988.2	988.1	987.2	986.4
142.5°	1014.2	1013.5	1013.0	1012.4	1013.0	1013.5	1014.2	1014.7	1014.6	1014.0	1013.4
145°	1051.9	1051.9	1051.9	1051.9	1051.9	1051.9	1051.9	1051.9	1051.8	1051.4	1051.0
147.5°	1084.3	1083.3	1082.4	1081.4	1082.4	1083.3	1084.3	1085.2	1085.4	1085.1	1084.7
150°	1105.3	1104.8	1104.1	1103.5	1104.1	1104.8	1105.3	1106.0	1106.0	1105.6	1105.3
152.5°	1124.0	1123.1	1122.1	1121.2	1122.1	1123.1	1124.0	1125.0	1125.1	1124.3	1123.6
155°	1149.5	1148.3	1147.1	1145.9	1147.1	1148.3	1149.5	1150.7	1150.9	1149.9	1148.8
157.5°	1171.5	1169.8	1168.2	1166.6	1168.2	1169.8	1171.5	1173.1	1173.2	1172.0	1170.8
160°	1184.2	1182.8	1181.3	1179.9	1181.3	1182.8	1184.2	1185.7	1185.7	1184.5	1183.3
162.5°	1196.2	1194.9	1193.7	1192.4	1193.7	1194.9	1196.2	1197.5	1197.5	1196.0	1194.7
165°	1211.8	1210.4	1208.9	1207.5	1208.9	1210.4	1211.8	1213.2	1213.1	1211.5	1209.9
167.5°	1223.3	1221.6	1220.0	1218.4	1220.0	1221.6	1223.3	1225.0	1225.0	1223.3	1221.6
170°	1229.9	1228.3	1226.6	1225.0	1226.6	1228.3	1229.9	1231.5	1231.5	1229.9	1228.3
172.5°	1234.1	1232.3	1230.5	1228.7	1230.5	1232.3	1234.1	1235.9	1236.0	1234.3	1232.7
175°	1239.1	1237.5	1235.9	1234.2	1235.9	1237.5	1239.1	1240.7	1240.9	1239.4	1238.0
177.5°	1240.8	1239.1	1237.5	1235.9	1237.5	1239.1	1240.8	1242.4	1242.5	1241.3	1239.9
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P332264-927

CATALOG NUMBER: S123RDIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	411.5	413.6	415.7	417.6	420.5	421.8	423.7	424.5	426.7	429.9	432.6
5°	386.5	389.4	393.3	396.4	401.4	405.3	409.6	413.6	418.4	425.2	431.3
7.5°	365.3	368.1	372.8	378.7	384.1	389.7	395.5	401.0	407.8	417.6	427.3
10°	351.3	354.7	360.3	366.5	373.4	378.7	385.6	392.5	401.1	412.3	424.0
12.5°	339.1	341.7	348.2	354.1	361.9	368.7	375.3	383.6	393.2	405.2	419.2
15°	319.9	323.5	329.8	336.4	344.6	351.8	360.4	370.4	379.9	394.6	411.5
17.5°	300.5	306.1	312.7	320.1	326.1	336.1	345.5	355.7	367.3	382.9	401.6
20°	288.1	292.6	298.7	309.5	317.4	325.0	333.7	346.4	357.1	374.9	394.2
22.5°	277.6	280.8	287.7	296.7	305.9	314.7	323.5	335.6	348.9	365.7	386.7
25°	262.1	267.3	272.4	278.8	288.8	299.4	309.0	319.3	333.4	351.3	373.9
27.5°	246.9	251.6	256.7	264.6	272.2	282.0	292.1	303.9	318.9	337.9	360.9
30°	237.2	240.7	245.5	255.6	262.4	270.9	282.7	293.3	307.3	327.4	351.8
32.5°	227.1	231.6	236.9	244.7	253.2	261.2	272.0	283.4	297.7	317.5	342.5
35°	212.8	218.2	223.5	229.3	237.7	246.1	255.1	267.6	282.2	301.4	325.9
37.5°	199.6	203.9	208.3	215.4	223.4	231.3	239.8	252.2	265.9	286.6	309.1
40°	191.2	195.1	198.4	205.8	213.6	222.0	230.4	241.2	256.0	275.4	297.1
42.5°	182.0	185.6	190.1	196.2	204.5	211.7	220.0	230.3	244.2	263.9	283.0
45°	168.3	172.4	176.3	182.0	190.3	197.3	204.7	214.4	228.7	244.9	261.9
47.5°	154.0	158.1	162.6	168.1	175.3	182.4	189.8	198.4	211.4	227.4	238.8
50°	144.9	148.2	152.7	158.2	164.9	172.4	179.0	188.5	200.8	213.3	223.3
52.5°	135.5	138.5	143.5	149.3	155.5	162.1	169.1	177.2	188.4	200.2	208.1
55°	120.7	124.4	128.7	134.4	140.5	146.0	152.8	161.1	170.0	178.9	184.2
57.5°	106.9	110.0	113.6	119.5	124.8	131.3	137.5	143.9	152.2	158.8	162.3
60°	96.9	99.7	104.3	109.5	114.4	120.2	127.1	133.6	139.9	145.3	148.0
62.5°	87.5	90.6	94.7	99.4	104.8	110.3	116.4	121.8	127.4	132.0	133.9
65°	75.1	77.7	80.6	85.1	89.5	95.1	99.8	105.4	109.5	112.0	113.7
67.5°	63.9	65.6	67.8	70.8	75.2	80.0	84.6	89.0	92.4	94.1	95.6
70°	56.6	57.8	59.4	62.3	65.7	69.9	74.8	77.9	80.8	82.3	83.8
72.5°	49.4	50.9	52.4	54.7	57.4	60.5	64.0	67.8	69.5	71.2	72.1
75°	37.5	39.5	41.5	43.0	44.8	47.2	50.4	52.8	53.7	55.2	55.4
77.5°	28.3	28.8	30.2	32.0	33.6	35.3	37.3	39.5	39.9	40.6	41.2
80°	23.3	23.3	23.3	24.4	26.2	27.5	29.3	30.4	31.2	31.4	31.5
82.5°	18.7	18.7	18.5	18.8	19.4	20.1	21.8	23.1	23.7	23.5	23.1
85°	12.2	11.8	11.8	11.6	11.8	11.4	11.2	12.0	13.1	13.1	12.8
87.5°	9.6	9.3	8.9	8.2	7.5	6.9	5.9	5.7	5.3	5.5	4.9
90°	22.9	22.1	19.4	16.8	14.1	11.5	9.1	7.1	5.0	2.9	1.0
92.5°	24.9	23.5	21.5	19.6	17.6	15.5	14.8	15.4	16.0	16.6	17.1
95°	29.9	28.5	26.3	24.0	21.8	19.6	22.6	31.0	39.4	47.8	56.2
97.5°	31.3	29.6	44.4	59.1	73.8	88.6	97.8	101.6	105.3	109.1	112.8
100°	32.0	30.3	62.3	94.2	126.1	158.0	171.9	167.8	163.7	159.6	155.5
102.5°	55.5	60.5	95.4	130.2	165.1	199.9	215.9	212.9	210.0	207.1	204.1
105°	165.3	201.5	220.0	238.4	256.7	275.2	283.3	281.0	278.8	276.6	274.3
107.5°	342.9	369.5	366.5	363.6	360.8	357.8	355.5	353.6	351.9	350.1	348.2
110°	408.4	415.1	412.8	410.6	408.4	406.1	404.2	402.5	400.8	399.3	397.6



TEST NUMBER: P332264-927

CATALOG NUMBER: S123RDIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	461.6	461.4	459.2	457.0	454.7	452.5	450.6	449.2	447.7	446.2	444.7
115°	530.4	528.3	526.5	524.6	522.8	520.9	519.4	518.2	516.9	515.7	514.5
117.5°	594.7	593.1	592.2	591.2	590.3	589.3	588.1	586.6	585.0	583.5	582.0
120°	636.7	635.0	634.5	633.8	633.2	632.6	631.4	629.5	627.7	625.8	624.0
122.5°	678.2	677.0	676.2	675.5	674.7	673.9	672.8	671.2	669.7	668.2	666.7
125°	736.7	736.3	735.5	734.7	733.8	733.0	731.8	730.2	728.5	726.9	725.2
127.5°	794.4	793.7	792.7	791.8	790.8	789.8	788.5	786.9	785.2	783.5	782.0
130°	829.2	828.3	827.5	826.7	825.9	825.1	823.8	822.2	820.5	819.0	817.3
132.5°	862.3	861.5	860.8	860.2	859.5	858.8	857.7	856.0	854.4	852.8	851.1
135°	912.7	912.1	911.2	910.5	909.7	908.8	907.8	906.6	905.3	904.1	902.9
137.5°	957.0	956.1	955.6	955.2	954.7	954.3	953.3	951.7	950.1	948.6	947.1
140°	985.6	984.8	984.2	983.6	982.9	982.3	981.4	980.2	979.0	977.7	976.5
142.5°	1012.7	1012.0	1011.5	1010.8	1010.2	1009.6	1008.7	1007.4	1006.2	1005.0	1003.8
145°	1050.5	1050.1	1049.7	1049.3	1048.9	1048.5	1047.6	1046.2	1044.7	1043.3	1041.9
147.5°	1084.3	1083.8	1083.4	1083.0	1082.6	1082.2	1081.5	1080.5	1079.7	1078.7	1077.8
150°	1104.9	1104.5	1104.1	1103.6	1103.2	1102.8	1102.3	1101.7	1101.1	1100.4	1099.9
152.5°	1122.8	1122.1	1121.9	1121.7	1121.3	1121.1	1120.9	1120.5	1120.3	1120.0	1119.7
155°	1147.8	1146.8	1146.6	1146.4	1146.1	1146.0	1146.1	1146.4	1146.8	1147.3	1147.7
157.5°	1169.6	1168.3	1168.5	1168.7	1168.9	1169.1	1169.3	1169.3	1169.3	1169.3	1169.4
160°	1182.1	1180.8	1181.1	1181.2	1181.5	1181.6	1181.9	1182.1	1182.3	1182.5	1182.6
162.5°	1193.3	1191.8	1192.1	1192.3	1192.5	1192.7	1193.0	1193.6	1194.1	1194.7	1195.2
165°	1208.2	1206.6	1206.8	1207.0	1207.2	1207.4	1207.8	1208.5	1209.0	1209.7	1210.3
167.5°	1220.0	1218.4	1218.4	1218.4	1218.4	1218.4	1218.8	1219.6	1220.4	1221.2	1222.1
170°	1226.6	1225.0	1225.0	1225.0	1225.0	1225.0	1225.4	1226.2	1227.1	1227.9	1228.7
172.5°	1231.1	1229.4	1229.2	1229.1	1228.9	1228.8	1229.2	1230.2	1231.1	1232.2	1233.1
175°	1236.6	1235.1	1234.9	1234.7	1234.5	1234.3	1234.7	1235.7	1236.8	1237.8	1238.8
177.5°	1238.7	1237.3	1237.2	1237.0	1236.8	1236.7	1237.0	1237.9	1238.7	1239.4	1240.3
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P332264-927

CATALOG NUMBER: S123RDIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	433.5	435.1	437.2	440.3	442.7	444.7	445.1	445.8	447.3	449.7	451.6
5°	436.3	440.5	447.3	454.0	461.2	467.1	472.7	476.6	480.2	488.0	494.2
7.5°	435.4	444.9	455.6	467.5	479.6	491.2	502.1	511.8	521.5	532.8	545.7
10°	434.8	445.9	460.3	475.6	492.4	508.8	524.7	537.1	551.4	564.4	580.8
12.5°	432.1	448.0	465.2	484.7	505.4	524.3	545.3	562.3	578.8	597.5	616.6
15°	428.3	447.7	469.5	495.5	527.0	549.8	571.2	600.9	621.2	641.5	668.8
17.5°	421.7	445.4	472.5	506.4	532.5	563.3	595.5	619.0	646.3	674.9	699.7
20°	416.4	443.9	474.4	507.6	541.0	574.3	605.5	633.6	661.9	694.9	715.2
22.5°	411.1	438.2	469.9	505.2	541.1	576.3	611.6	644.5	676.3	709.6	735.5
25°	399.7	432.1	466.4	502.4	537.8	576.6	618.6	655.4	694.7	729.0	753.6
27.5°	388.3	418.0	452.1	488.6	528.0	573.8	623.3	665.0	704.4	729.0	736.7
30°	378.0	409.3	440.8	477.8	520.5	571.6	624.2	672.0	704.3	715.0	707.0
32.5°	367.5	395.9	427.0	465.0	510.2	566.1	625.3	667.9	687.3	679.1	646.8
35°	349.0	374.6	404.7	442.8	494.8	563.1	620.5	649.3	644.5	598.3	537.4
37.5°	329.2	350.1	378.0	417.7	478.8	551.1	599.5	603.8	562.2	491.4	421.0
40°	313.5	332.4	361.0	402.5	466.4	539.3	578.5	561.3	496.9	418.0	359.3
42.5°	298.3	314.3	341.8	386.6	454.6	523.2	547.0	509.6	435.3	360.8	307.4
45°	272.6	287.6	315.2	361.2	430.4	492.4	489.3	424.3	349.9	289.9	245.7
47.5°	248.2	261.3	287.2	334.1	402.0	446.2	416.9	347.8	284.7	236.5	204.9
50°	230.9	243.8	269.7	316.0	379.3	411.5	369.7	303.1	245.3	205.4	180.3
52.5°	214.4	227.0	250.6	295.7	351.8	371.1	326.1	264.4	216.2	181.8	160.3
55°	191.2	200.8	222.0	265.2	307.1	311.6	265.9	214.3	174.6	150.6	135.9
57.5°	167.6	175.9	196.9	231.2	260.6	258.3	215.2	170.4	143.7	125.9	115.2
60°	152.3	160.4	178.9	208.3	230.5	222.8	183.1	147.1	124.2	111.1	102.6
62.5°	137.9	144.3	161.6	183.2	199.1	190.3	156.5	126.7	108.5	97.5	90.8
65°	117.2	122.4	136.2	147.5	156.3	147.8	119.8	99.1	86.0	78.3	73.7
67.5°	97.5	100.8	109.5	113.6	119.9	110.5	90.1	76.2	68.8	62.3	59.0
70°	85.1	87.5	92.1	95.5	97.0	87.5	72.3	62.2	55.9	51.3	49.3
72.5°	72.6	74.8	75.7	78.4	77.6	68.6	58.1	50.1	45.6	42.5	39.8
75°	55.5	56.5	55.5	54.4	52.0	45.8	38.6	34.5	31.2	29.7	28.8
77.5°	40.5	40.2	39.0	37.2	33.1	29.2	25.3	23.9	22.5	21.7	21.4
80°	31.2	30.4	29.3	26.5	23.1	20.3	19.4	18.5	17.9	17.0	16.8
82.5°	23.2	22.7	20.9	18.6	16.2	14.8	14.1	13.7	13.2	12.7	12.7
85°	12.4	11.8	9.7	8.5	8.2	7.8	7.6	7.6	6.8	6.7	6.7
87.5°	4.6	4.1	4.4	4.4	4.8	5.1	5.7	5.9	6.3	6.7	6.5
90°	2.9	5.0	7.1	9.1	11.5	14.1	16.8	19.4	22.1	22.9	23.7
92.5°	16.6	16.0	15.4	14.8	15.5	17.6	19.6	21.5	23.5	24.9	26.1
95°	47.8	39.4	31.0	22.6	19.6	21.8	24.0	26.3	28.5	29.9	31.4
97.5°	109.1	105.3	101.6	97.8	88.6	73.8	59.1	44.4	29.6	31.3	32.9
100°	159.6	163.7	167.8	171.9	158.0	126.1	94.2	62.3	30.3	32.0	33.7
102.5°	207.1	210.0	212.9	215.9	199.9	165.1	130.2	95.4	60.5	55.5	50.4
105°	276.6	278.8	281.0	283.3	275.2	256.7	238.4	220.0	201.5	165.3	129.1
107.5°	350.1	351.9	353.6	355.5	357.8	360.8	363.6	366.5	369.5	342.9	316.3
110°	399.3	400.8	402.5	404.2	406.1	408.4	410.6	412.8	415.1	408.4	401.6





TEST NUMBER: P332264-927

CATALOG NUMBER: S123RDIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	446.2	447.7	449.2	450.6	452.5	454.7	457.0	459.2	461.4	461.6	461.7
115°	515.7	516.9	518.2	519.4	520.9	522.8	524.6	526.5	528.3	530.4	532.3
117.5°	583.5	585.0	586.6	588.1	589.3	590.3	591.2	592.2	593.1	594.7	596.4
120°	625.8	627.7	629.5	631.4	632.6	633.2	633.8	634.5	635.0	636.7	638.3
122.5°	668.2	669.7	671.2	672.8	673.9	674.7	675.5	676.2	677.0	678.2	679.3
125°	726.9	728.5	730.2	731.8	733.0	733.8	734.7	735.5	736.3	736.7	737.1
127.5°	783.5	785.2	786.9	788.5	789.8	790.8	791.8	792.7	793.7	794.4	795.0
130°	819.0	820.5	822.2	823.8	825.1	825.9	826.7	827.5	828.3	829.2	830.0
132.5°	852.8	854.4	856.0	857.7	858.8	859.5	860.2	860.8	861.5	862.3	863.1
135°	904.1	905.3	906.6	907.8	908.8	909.7	910.5	911.2	912.1	912.7	913.3
137.5°	948.6	950.1	951.7	953.3	954.3	954.7	955.2	955.6	956.1	957.0	958.1
140°	977.7	979.0	980.2	981.4	982.3	982.9	983.6	984.2	984.8	985.6	986.4
142.5°	1005.0	1006.2	1007.4	1008.7	1009.6	1010.2	1010.8	1011.5	1012.0	1012.7	1013.4
145°	1043.3	1044.7	1046.2	1047.6	1048.5	1048.9	1049.3	1049.7	1050.1	1050.5	1051.0
147.5°	1078.7	1079.7	1080.5	1081.5	1082.2	1082.6	1083.0	1083.4	1083.8	1084.3	1084.7
150°	1100.4	1101.1	1101.7	1102.3	1102.8	1103.2	1103.6	1104.1	1104.5	1104.9	1105.3
152.5°	1120.0	1120.3	1120.5	1120.9	1121.1	1121.3	1121.7	1121.9	1122.1	1122.8	1123.6
155°	1147.3	1146.8	1146.4	1146.1	1146.0	1146.1	1146.4	1146.6	1146.8	1147.8	1148.8
157.5°	1169.3	1169.3	1169.3	1169.3	1169.1	1168.9	1168.7	1168.5	1168.3	1169.6	1170.8
160°	1182.5	1182.3	1182.1	1181.9	1181.6	1181.5	1181.2	1181.1	1180.8	1182.1	1183.3
162.5°	1194.7	1194.1	1193.6	1193.0	1192.7	1192.5	1192.3	1192.1	1191.8	1193.3	1194.7
165°	1209.7	1209.0	1208.5	1207.8	1207.4	1207.2	1207.0	1206.8	1206.6	1208.2	1209.9
167.5°	1221.2	1220.4	1219.6	1218.8	1218.4	1218.4	1218.4	1218.4	1218.4	1220.0	1221.6
170°	1227.9	1227.1	1226.2	1225.4	1225.0	1225.0	1225.0	1225.0	1225.0	1226.6	1228.3
172.5°	1232.2	1231.1	1230.2	1229.2	1228.8	1228.9	1229.1	1229.2	1229.4	1231.1	1232.7
175°	1237.8	1236.8	1235.7	1234.7	1234.3	1234.5	1234.7	1234.9	1235.1	1236.6	1238.0
177.5°	1239.4	1238.7	1237.9	1237.0	1236.7	1236.8	1237.0	1237.2	1237.3	1238.7	1239.9
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8



TEST NUMBER: P332264-927

CATALOG NUMBER: S123RDIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	454.8	454.8	455.3	457.6	457.9	459.8	459.2
5°	499.8	503.3	504.6	510.2	513.4	514.9	512.0
7.5°	554.8	564.7	569.4	575.3	580.4	581.9	577.9
10°	595.0	605.4	614.0	619.4	624.4	627.7	631.9
12.5°	633.8	646.6	654.8	662.3	667.5	671.7	672.4
15°	676.0	695.2	709.8	720.6	725.9	728.6	727.5
17.5°	718.6	736.4	746.8	757.7	765.1	765.5	765.7
20°	742.7	760.0	772.1	780.1	788.5	788.1	790.0
22.5°	758.8	772.5	781.6	787.5	790.4	788.9	789.3
25°	766.3	770.4	768.7	759.3	756.9	748.2	749.7
27.5°	727.5	708.3	688.4	662.9	642.7	626.6	627.4
30°	674.8	640.8	602.1	569.6	540.4	532.3	514.9
32.5°	601.1	550.2	504.8	474.4	449.5	442.7	427.5
35°	476.2	426.7	380.0	352.0	340.9	325.3	325.2
37.5°	370.1	326.5	301.9	280.8	269.8	260.4	259.5
40°	311.3	277.4	258.7	243.6	232.7	225.7	224.0
42.5°	270.3	242.9	225.4	216.0	207.6	204.0	201.3
45°	220.7	202.2	190.1	181.6	177.8	175.0	173.5
47.5°	184.7	172.3	164.0	158.3	155.2	152.3	153.0
50°	165.0	154.9	148.8	143.4	141.0	138.9	139.2
52.5°	149.2	140.1	135.1	131.3	128.3	126.8	126.2
55°	126.6	120.9	115.9	113.1	111.5	109.5	108.9
57.5°	108.0	103.5	99.5	96.4	95.9	94.0	94.3
60°	95.6	91.9	88.6	86.9	85.6	84.0	84.5
62.5°	85.4	82.3	79.3	78.0	76.6	75.4	75.7
65°	69.9	67.0	65.1	64.4	63.8	63.3	62.7
67.5°	55.8	53.9	52.8	51.2	50.1	49.9	49.4
70°	46.9	44.4	42.5	40.4	39.8	39.7	39.8
72.5°	37.5	36.0	35.5	34.5	34.4	33.9	34.2
75°	28.2	27.6	27.3	26.5	26.5	26.5	26.5
77.5°	20.8	20.5	20.3	20.1	20.0	19.6	19.6
80°	16.2	16.1	15.7	15.7	15.5	15.7	15.5
82.5°	12.3	12.2	11.9	11.9	11.6	11.6	11.6
85°	6.3	6.1	6.5	6.1	6.3	5.9	6.3
87.5°	6.7	6.8	6.8	6.9	6.8	7.2	7.0
90°	24.6	25.3	26.0	26.4	26.8	27.2	27.6
92.5°	27.5	28.8	29.5	29.8	30.1	30.3	30.6
95°	32.8	34.2	34.9	34.9	34.9	34.9	34.9
97.5°	34.5	36.2	37.1	37.3	37.5	37.7	37.9
100°	35.3	36.9	37.9	38.0	38.3	38.4	38.7
102.5°	45.3	40.2	37.9	38.3	38.7	39.1	39.4
105°	92.9	56.7	38.9	39.3	39.7	40.1	40.5
107.5°	289.8	263.2	236.3	209.1	181.7	154.5	127.2
110°	394.8	388.1	370.1	340.9	311.6	282.3	253.1



TEST NUMBER: P332264-927

CATALOG NUMBER: S123RDIP-S340D1195U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	461.8	462.0	458.9	452.7	446.6	440.4	434.2
115°	534.4	536.5	537.9	538.7	539.6	540.3	541.1
117.5°	598.0	599.6	600.6	600.7	600.9	601.0	601.2
120°	639.9	641.6	642.4	642.4	642.4	642.4	642.4
122.5°	680.5	681.6	682.2	682.4	682.5	682.8	682.9
125°	737.5	737.9	738.3	738.7	739.2	739.6	740.0
127.5°	795.7	796.3	796.5	796.1	795.7	795.3	794.8
130°	830.8	831.6	831.8	831.4	831.0	830.6	830.2
132.5°	864.0	864.7	864.8	864.3	863.7	863.2	862.5
135°	913.9	914.6	914.6	913.9	913.3	912.7	912.1
137.5°	959.0	960.0	960.3	959.9	959.5	959.1	958.6
140°	987.2	988.1	988.2	987.9	987.5	987.1	986.7
142.5°	1014.0	1014.6	1014.7	1014.2	1013.5	1013.0	1012.4
145°	1051.4	1051.8	1051.9	1051.9	1051.9	1051.9	1051.9
147.5°	1085.1	1085.4	1085.2	1084.3	1083.3	1082.4	1081.4
150°	1105.6	1106.0	1106.0	1105.3	1104.8	1104.1	1103.5
152.5°	1124.3	1125.1	1125.0	1124.0	1123.1	1122.1	1121.2
155°	1149.9	1150.9	1150.7	1149.5	1148.3	1147.1	1145.9
157.5°	1172.0	1173.2	1173.1	1171.5	1169.8	1168.2	1166.6
160°	1184.5	1185.7	1185.7	1184.2	1182.8	1181.3	1179.9
162.5°	1196.0	1197.5	1197.5	1196.2	1194.9	1193.7	1192.4
165°	1211.5	1213.1	1213.2	1211.8	1210.4	1208.9	1207.5
167.5°	1223.3	1225.0	1225.0	1223.3	1221.6	1220.0	1218.4
170°	1229.9	1231.5	1231.5	1229.9	1228.3	1226.6	1225.0
172.5°	1234.3	1236.0	1235.9	1234.1	1232.3	1230.5	1228.7
175°	1239.4	1240.9	1240.7	1239.1	1237.5	1235.9	1234.2
177.5°	1241.3	1242.5	1242.4	1240.8	1239.1	1237.5	1235.9
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

(END OF REPORT)