

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332025

Luminaire Tested: **S123DIP-S1000D805U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332025  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1000D805U835-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6879.4 lumens  
Efficiency: N/A  
Efficacy: 126.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332025

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332025

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	110	110	110	110	102	102	102	102	89	89	89		77	77	77		65	65	65	60
1	100	95	92	88	93	89	86	83	78	75	73		67	65	64		58	56	55	50
2	91	83	77	72	85	78	73	68	68	64	60		59	56	53		51	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51		52	48	45		45	42	39	36
4	76	65	57	51	71	61	54	48	53	48	43		47	42	38		40	37	34	31
5	70	58	50	43	65	54	47	41	48	42	37		42	37	33		36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	33		38	33	29		33	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29		34	30	26		30	26	23	21
8	55	43	35	29	52	40	33	28	36	30	26		31	27	23		27	24	21	18
9	51	39	31	26	48	37	30	25	33	27	23		29	24	21		25	22	19	17
10	48	36	28	24	45	34	27	23	30	25	21		27	22	19		24	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17038	17038	17038
5°	17117	16883	17001
10°	17004	16736	16840
15°	16805	16547	16577
20°	16573	16276	16292
25°	16262	15954	15922
30°	15918	15597	15478
35°	15559	15219	15023
40°	15185	14802	14573
45°	14772	14420	14067
50°	14359	13949	13561
55°	13818	13461	13052
60°	13272	12893	12482
65°	12791	12271	11889
70°	12079	11566	11050
75°	11038	10643	10189
80°	9955	9534	9447
85°	8744	8410	8065



TEST NUMBER: P332025

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	149.1	2.2
10°-20°	421.0	6.1
20°-30°	621.9	9.0
30°-40°	726.5	10.6
40°-50°	730.4	10.6
50°-60°	641.5	9.3
60°-70°	478.0	6.9
70°-80°	272.3	4.0
80°-90°	81.1	1.2
90°-100°	64.8	0.9
100°-110°	194.1	2.8
110°-120°	330.1	4.8
120°-130°	434.2	6.3
130°-140°	488.0	7.1
140°-150°	479.7	7.0
150°-160°	403.8	5.9
160°-170°	268.8	3.9
170°-180°	94.1	1.4
0°-30°	1192.0	17.3
0°-40°	1918.5	27.9
0°-60°	3290.4	47.8
0°-90°	4121.8	59.9
90°-120°	589.0	8.6
90°-150°	1990.8	28.9
90°-180°	2758.0	40.1
0°-180°	6879.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1583	1583	1583	1583	1583	
5°	1584	1577	1562	1575	1573	150
15°	1508	1502	1485	1495	1488	425
25°	1369	1360	1343	1344	1341	630
35°	1184	1175	1158	1150	1143	740
45°	970	964	947	932	924	749
55°	736	734	717	703	696	659
65°	502	495	482	471	467	495
75°	265	260	256	249	245	284
85°	71	68	68	65	65	78
90°	1	9	19	22	24	7
95°	46	52	58	61	61	52
105°	176	178	184	185	186	188
115°	332	334	333	334	333	329
125°	486	488	487	484	481	434
135°	631	635	635	632	630	486
145°	765	767	769	768	765	478
155°	876	876	877	880	875	403
165°	955	952	952	956	952	269
175°	993	990	990	994	989	94
180°	995	995	995	995	995	



TEST NUMBER: P332025

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9
2.5°	1588.3	1587.4	1586.4	1585.4	1584.5	1582.6	1580.0	1577.3	1574.7	1572.0	1574.4
5°	1584.2	1582.7	1581.2	1579.7	1578.2	1575.8	1572.5	1569.1	1565.8	1562.5	1565.5
7.5°	1568.7	1567.2	1565.7	1564.2	1562.7	1560.2	1556.8	1553.3	1549.9	1546.4	1549.1
10°	1555.7	1554.2	1552.6	1551.1	1549.6	1546.9	1543.0	1539.0	1535.1	1531.2	1533.9
12.5°	1538.2	1537.0	1535.7	1534.4	1533.2	1530.7	1527.0	1523.3	1519.6	1515.9	1517.9
15°	1508.0	1506.8	1505.6	1504.4	1503.2	1500.6	1496.7	1492.8	1488.8	1484.9	1487.3
17.5°	1472.9	1471.3	1469.8	1468.2	1466.6	1463.9	1459.9	1456.0	1452.1	1448.1	1449.8
20°	1446.8	1445.0	1443.2	1441.3	1439.5	1436.6	1432.7	1428.8	1424.9	1420.9	1422.1
22.5°	1417.4	1415.6	1413.8	1411.9	1410.1	1407.3	1403.3	1399.4	1395.5	1391.5	1392.5
25°	1369.2	1367.4	1365.6	1363.8	1361.9	1359.1	1355.1	1351.2	1347.3	1343.3	1343.6
27.5°	1317.8	1316.0	1314.2	1312.5	1310.7	1307.7	1303.5	1299.3	1295.0	1290.8	1291.0
30°	1280.7	1279.2	1277.7	1276.2	1274.7	1271.8	1267.6	1263.3	1259.1	1254.9	1254.9
32.5°	1243.7	1241.7	1239.7	1237.7	1235.7	1233.1	1229.8	1226.6	1223.3	1220.0	1218.3
35°	1184.1	1182.3	1180.5	1178.7	1176.8	1174.0	1170.0	1166.1	1162.2	1158.2	1156.4
37.5°	1123.1	1120.8	1118.5	1116.2	1113.9	1110.8	1106.8	1102.8	1098.8	1094.8	1092.6
40°	1080.7	1078.8	1077.0	1075.2	1073.4	1070.4	1066.1	1061.9	1057.7	1053.4	1051.0
42.5°	1038.2	1036.1	1034.1	1032.0	1030.0	1026.8	1022.6	1018.4	1014.1	1009.9	1007.5
45°	970.4	969.2	968.0	966.8	965.6	963.0	959.1	955.1	951.2	947.3	943.7
47.5°	903.2	901.4	899.7	897.9	896.2	893.4	889.8	886.1	882.4	878.7	875.1
50°	857.5	855.9	854.4	852.9	851.4	848.7	844.7	840.8	836.9	833.0	829.6
52.5°	809.5	808.5	807.5	806.5	805.4	802.8	798.7	794.5	790.3	786.1	783.3
55°	736.3	736.0	735.7	735.4	735.1	733.0	729.1	725.1	721.2	717.3	713.9
57.5°	666.6	665.6	664.6	663.6	662.5	660.4	657.3	654.1	651.0	647.9	644.9
60°	616.5	616.2	615.9	615.6	615.3	613.4	609.7	606.1	602.5	598.9	596.1
62.5°	571.9	571.1	570.3	569.5	568.8	566.6	562.9	559.3	555.7	552.0	549.3
65°	502.2	500.7	499.2	497.7	496.2	493.9	490.9	487.9	484.8	481.8	479.4
67.5°	428.5	427.1	425.8	424.5	423.1	421.3	419.0	416.7	414.4	412.1	410.0
70°	383.8	382.0	380.2	378.4	376.6	374.7	372.9	371.1	369.3	367.5	365.4
72.5°	337.0	335.7	334.3	333.0	331.7	330.0	327.9	325.9	323.8	321.7	319.9
75°	265.4	264.2	263.0	261.8	260.6	259.5	258.6	257.7	256.8	255.9	254.4
77.5°	202.0	201.3	200.6	200.0	199.3	198.4	197.4	196.3	195.2	194.1	193.1
80°	160.6	159.7	158.8	157.9	157.0	156.2	155.6	155.0	154.4	153.8	153.5
82.5°	120.3	120.1	120.0	119.8	119.6	119.4	119.3	119.2	119.1	119.0	118.4
85°	70.8	70.2	69.6	69.0	68.4	68.1	68.1	68.1	68.1	68.1	67.4
87.5°	28.5	28.1	27.7	27.3	27.0	26.9	27.1	27.3	27.5	27.7	27.6
90°	0.8	2.5	4.3	6.0	7.7	9.7	12.0	14.2	16.5	18.8	19.5
92.5°	18.9	20.1	21.3	22.5	23.6	24.9	26.2	27.5	28.7	30.0	30.6
95°	46.1	47.3	48.6	49.8	51.0	52.3	53.7	55.1	56.5	57.9	58.6
97.5°	81.9	82.8	83.7	84.6	85.6	86.5	87.5	88.5	89.5	90.5	91.3
100°	106.3	107.4	108.4	109.5	110.5	111.5	112.3	113.2	114.1	114.9	115.5
102.5°	134.5	135.1	135.7	136.4	137.0	137.9	139.0	140.2	141.3	142.5	143.0
105°	175.9	176.3	176.6	177.0	177.3	178.3	179.8	181.4	183.0	184.5	184.5
107.5°	224.1	224.3	224.5	224.7	224.9	225.3	226.0	226.6	227.2	227.8	228.4
110°	254.1	254.4	254.8	255.1	255.5	255.8	256.2	256.5	256.9	257.2	257.9



TEST NUMBER: P332025

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	285.4	285.6	285.8	286.0	286.2	286.3	286.4	286.5	286.6	286.6	287.5
115°	332.3	332.8	333.3	333.8	334.4	334.5	334.1	333.8	333.4	333.1	333.2
117.5°	379.5	379.9	380.2	380.5	380.9	380.8	380.4	379.9	379.5	379.0	379.0
120°	408.9	409.9	411.0	412.0	413.1	413.2	412.3	411.4	410.6	409.7	409.5
122.5°	439.6	440.3	441.1	441.8	442.6	442.8	442.3	441.9	441.4	441.0	440.5
125°	486.3	486.8	487.3	487.9	488.4	488.5	488.1	487.8	487.4	487.1	486.4
127.5°	529.5	530.6	531.7	532.8	533.9	534.3	533.9	533.5	533.1	532.7	531.8
130°	558.2	559.6	561.0	562.4	563.8	564.2	563.7	563.2	562.7	562.1	561.4
132.5°	587.0	588.4	589.8	591.2	592.6	593.1	592.7	592.3	591.9	591.5	590.7
135°	630.9	632.0	633.0	634.1	635.1	635.6	635.4	635.2	635.0	634.9	634.2
137.5°	671.6	672.5	673.3	674.2	675.1	675.7	676.2	676.6	677.1	677.5	676.8
140°	699.7	700.6	701.5	702.4	703.2	703.7	703.9	704.1	704.3	704.4	704.3
142.5°	725.4	726.3	727.1	728.0	728.9	729.5	729.8	730.1	730.4	730.7	730.5
145°	765.4	765.8	766.1	766.5	766.8	767.2	767.8	768.3	768.8	769.3	769.2
147.5°	800.5	801.1	801.7	802.3	803.0	803.5	804.0	804.5	805.0	805.5	805.5
150°	824.8	825.2	825.5	825.9	826.2	826.6	826.9	827.3	827.6	828.0	828.0
152.5°	844.9	845.3	845.8	846.3	846.8	847.2	847.4	847.6	847.8	848.0	848.3
155°	876.4	876.4	876.4	876.4	876.4	876.5	876.7	876.9	877.1	877.2	877.9
157.5°	903.3	903.1	902.9	902.7	902.5	902.5	902.6	902.8	902.9	903.0	903.8
160°	920.2	919.9	919.5	919.2	918.8	918.7	918.7	918.7	918.7	918.7	919.5
162.5°	935.2	934.8	934.3	933.8	933.3	933.1	933.3	933.4	933.5	933.7	934.5
165°	954.6	954.1	953.6	953.1	952.5	952.3	952.3	952.3	952.3	952.3	953.3
167.5°	970.1	969.4	968.7	968.0	967.3	967.1	967.2	967.3	967.5	967.6	968.7
170°	978.9	978.2	977.5	976.8	976.1	975.7	975.7	975.7	975.7	975.7	977.0
172.5°	985.7	985.1	984.4	983.7	983.0	982.6	982.6	982.6	982.6	982.6	983.7
175°	992.9	992.2	991.6	990.9	990.2	989.8	989.8	989.8	989.8	989.8	990.9
177.5°	995.9	995.4	994.8	994.2	993.7	993.4	993.4	993.4	993.4	993.4	994.2
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3



TEST NUMBER: P332025

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9
2.5°	1576.8	1579.3	1581.7	1582.8	1582.5	1582.3	1582.0	1581.8
5°	1568.5	1571.5	1574.6	1575.8	1575.2	1574.6	1574.0	1573.4
7.5°	1551.9	1554.6	1557.3	1558.5	1558.1	1557.8	1557.4	1557.0
10°	1536.6	1539.3	1542.1	1543.1	1542.5	1541.9	1541.3	1540.7
12.5°	1519.9	1521.9	1523.9	1524.7	1524.4	1524.0	1523.6	1523.3
15°	1489.7	1492.1	1494.6	1494.9	1493.1	1491.2	1489.4	1487.6
17.5°	1451.5	1453.2	1454.9	1455.4	1454.8	1454.1	1453.4	1452.8
20°	1423.3	1424.6	1425.8	1425.9	1425.0	1424.1	1423.2	1422.3
22.5°	1393.5	1394.4	1395.4	1395.3	1394.2	1393.0	1391.9	1390.7
25°	1343.9	1344.3	1344.6	1344.3	1343.3	1342.4	1341.5	1340.6
27.5°	1291.3	1291.5	1291.8	1291.3	1290.2	1289.0	1287.9	1286.7
30°	1254.9	1254.9	1254.9	1253.8	1251.7	1249.6	1247.5	1245.3
32.5°	1216.6	1215.0	1213.3	1211.8	1210.7	1209.5	1208.4	1207.2
35°	1154.6	1152.8	1151.0	1149.3	1147.8	1146.3	1144.8	1143.3
37.5°	1090.5	1088.3	1086.1	1084.5	1083.6	1082.6	1081.6	1080.7
40°	1048.6	1046.2	1043.8	1041.9	1040.7	1039.5	1038.3	1037.1
42.5°	1005.0	1002.6	1000.2	998.4	997.2	996.0	994.8	993.6
45°	940.0	936.4	932.8	930.2	928.7	927.2	925.7	924.1
47.5°	871.5	868.0	864.4	862.0	860.6	859.3	858.0	856.6
50°	826.3	823.0	819.6	817.1	815.3	813.4	811.6	809.8
52.5°	780.4	777.6	774.8	772.4	770.6	768.8	767.0	765.2
55°	710.6	707.3	704.0	701.5	700.0	698.5	697.0	695.5
57.5°	641.9	639.0	636.0	633.6	631.9	630.1	628.4	626.6
60°	593.4	590.7	588.0	585.9	584.3	582.8	581.3	579.8
62.5°	546.6	543.9	541.1	539.3	538.2	537.2	536.2	535.2
65°	477.0	474.5	472.1	470.5	469.6	468.7	467.7	466.8
67.5°	407.9	405.8	403.7	402.0	400.7	399.4	398.1	396.9
70°	363.2	361.1	359.0	357.2	355.7	354.2	352.7	351.1
72.5°	318.0	316.1	314.2	312.9	312.1	311.3	310.6	309.8
75°	252.9	251.3	249.8	248.6	247.7	246.8	245.9	245.0
77.5°	192.0	191.0	190.0	189.5	189.5	189.5	189.5	189.5
80°	153.2	152.9	152.6	152.4	152.4	152.4	152.4	152.4
82.5°	117.9	117.3	116.8	116.4	116.1	115.9	115.7	115.4
85°	66.8	66.2	65.6	65.3	65.3	65.3	65.3	65.3
87.5°	27.5	27.4	27.3	27.3	27.3	27.4	27.5	27.6
90°	20.2	20.8	21.5	22.1	22.4	22.8	23.1	23.5
92.5°	31.1	31.7	32.2	32.4	32.2	32.0	31.8	31.6
95°	59.2	59.9	60.6	61.0	61.0	61.0	61.0	61.0
97.5°	92.1	92.9	93.7	94.1	94.0	94.0	93.9	93.8
100°	116.0	116.5	117.0	117.5	117.8	118.1	118.5	118.8
102.5°	143.5	144.0	144.5	144.8	144.7	144.6	144.6	144.5
105°	184.5	184.5	184.5	184.7	185.0	185.4	185.7	186.1
107.5°	228.9	229.5	230.1	230.2	230.0	229.8	229.6	229.4
110°	258.6	259.3	260.0	260.2	259.8	259.5	259.1	258.8





TEST NUMBER: P332025

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	288.3	289.1	290.0	290.3	290.3	290.2	290.1	290.1
115°	333.4	333.6	333.8	333.8	333.6	333.4	333.2	333.1
117.5°	379.0	378.9	378.9	378.6	378.2	377.7	377.2	376.7
120°	409.3	409.2	409.0	408.7	408.4	408.0	407.7	407.3
122.5°	440.1	439.6	439.2	438.7	438.2	437.7	437.2	436.7
125°	485.7	485.0	484.3	483.6	482.9	482.2	481.5	480.8
127.5°	530.8	529.8	528.9	528.0	527.2	526.4	525.6	524.8
130°	560.8	560.1	559.4	558.4	557.2	556.0	554.8	553.5
132.5°	589.9	589.0	588.2	587.3	586.4	585.4	584.5	583.6
135°	633.5	632.8	632.1	631.6	631.2	630.9	630.5	630.2
137.5°	676.1	675.4	674.6	673.9	673.3	672.6	672.0	671.3
140°	704.1	703.9	703.7	703.1	701.8	700.6	699.4	698.2
142.5°	730.4	730.2	730.0	729.5	728.5	727.6	726.6	725.7
145°	769.0	768.8	768.6	768.2	767.5	766.8	766.1	765.4
147.5°	805.5	805.5	805.5	804.9	803.9	802.8	801.8	800.8
150°	828.0	828.0	828.0	827.5	826.4	825.4	824.3	823.3
152.5°	848.5	848.8	849.1	848.8	847.9	847.0	846.1	845.2
155°	878.6	879.3	880.0	879.7	878.5	877.3	876.1	874.9
157.5°	904.5	905.2	905.9	905.8	904.9	903.9	902.9	901.9
160°	920.4	921.3	922.1	922.2	921.5	920.8	920.1	919.4
162.5°	935.4	936.3	937.2	937.0	935.9	934.8	933.7	932.6
165°	954.4	955.4	956.5	956.4	955.2	953.9	952.7	951.5
167.5°	969.8	970.8	971.9	971.9	970.8	969.8	968.7	967.6
170°	978.2	979.4	980.6	980.6	979.4	978.2	977.0	975.7
172.5°	984.8	985.9	986.9	986.9	985.6	984.4	983.2	982.0
175°	991.9	992.9	994.0	993.9	992.7	991.5	990.2	989.0
177.5°	995.1	995.9	996.7	996.7	995.7	994.7	993.8	992.8
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3

(END OF REPORT)