

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831156

Luminaire Tested: S123DIP-S1000D805U835-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831156
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D805U835-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7820.2 lumens
Efficiency: N/A
Efficacy: 140.4 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 55.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831156
CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P831156

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59		
1	100	96	93	89	94	90	87	84	78	76	74	68	66	64	58	57	56	51		
2	92	85	79	74	86	79	74	70	69	66	62	60	57	55	52	50	48	44		
3	84	75	68	63	79	71	64	59	62	57	53	54	50	47	46	44	42	38		
4	78	67	60	54	72	63	56	51	56	50	46	49	45	41	42	39	37	33		
5	72	60	52	47	67	57	50	45	50	45	40	44	40	36	38	35	32	29		
6	66	55	47	41	62	52	44	39	46	40	36	40	36	32	35	32	29	26		
7	62	50	42	37	58	47	40	35	42	36	32	37	33	29	33	29	26	24		
8	58	46	38	33	54	43	36	31	39	33	29	34	30	26	30	27	24	22		
9	54	42	35	30	50	40	33	28	36	30	26	32	27	24	28	25	22	20		
10	50	39	32	27	47	37	30	26	33	28	24	30	25	22	26	23	20	18		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	30870	30870	30870	30870	30870
5°	39041	36847	31147	25099	23064
10°	39419	40611	30938	20007	17484
15°	29690	37706	30729	16944	14785
20°	20686	30511	30336	14818	13431
25°	15775	23464	29667	13632	12598
30°	13646	18641	28599	12795	11926
35°	12661	15738	27367	12189	11454
40°	11987	14119	25638	11612	11294
45°	11587	13067	23440	11163	11224
50°	11387	12234	20837	10752	11164
55°	10963	11626	18282	10365	11213
60°	10572	10973	15756	10000	11031
65°	9931	10356	13593	9610	10812
70°	9171	9571	11560	8963	10178
75°	8301	8580	9906	8330	9299
80°	6850	7507	7835	7259	7835
85°	5422	6076	5755	6163	6249

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 26761 cd/sqm



TEST NUMBER: P831156

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	271.1	3.5
10°-20°	674.5	8.6
20°-30°	798.7	10.2
30°-40°	803.0	10.3
40°-50°	736.8	9.4
50°-60°	608.1	7.8
60°-70°	430.2	5.5
70°-80°	229.6	2.9
80°-90°	60.4	0.8
90°-100°	37.1	0.5
100°-110°	179.4	2.3
110°-120°	439.6	5.6
120°-130°	558.1	7.1
130°-140°	596.2	7.6
140°-150°	557.5	7.1
150°-160°	449.7	5.8
160°-170°	290.2	3.7
170°-180°	100.0	1.3
0°-30°	1744.3	22.3
0°-40°	2547.3	32.6
0°-60°	3892.2	49.8
0°-90°	4612.3	59.0
90°-120°	656.1	8.4
90°-150°	2367.9	30.3
90°-180°	3208.0	41.0
0°-180°	7820.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2868	2868	2868	2868	2868	
5°	3613	3410	2883	2323	2135	344
15°	2664	3384	2758	1520	1327	736
25°	1328	1976	2498	1148	1061	627
35°	964	1198	2083	928	872	605
45°	761	858	1540	733	737	590
55°	584	620	974	552	598	523
65°	390	407	534	377	424	387
75°	200	206	238	200	224	210
85°	44	49	47	50	51	49
90°	24	19	1	19	24	13
95°	30	24	48	24	30	25
105°	34	171	233	171	34	72
115°	460	449	437	449	460	432
125°	629	625	616	625	629	562
135°	775	775	767	775	775	598
145°	894	892	885	892	894	558
155°	973	974	975	974	973	449
165°	1026	1025	1028	1025	1026	290
175°	1048	1049	1052	1049	1048	100
180°	1052	1052	1052	1052	1052	



TEST NUMBER: P831156

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2867.9	2867.9	2867.9	2867.9	2867.9	2867.9	2867.9	2867.9	2867.9	2867.9	2867.9
2.5°	3232.6	3229.2	3225.9	3209.3	3192.6	3184.6	3176.7	3152.7	3128.8	3102.1	3075.5
5°	3613.2	3622.5	3631.8	3621.2	3610.5	3577.9	3545.3	3502.0	3458.8	3410.2	3361.6
7.5°	3788.8	3794.2	3799.5	3792.8	3786.2	3777.5	3768.9	3730.3	3691.7	3641.8	3591.9
10°	3606.5	3618.5	3630.5	3656.4	3682.4	3711.6	3740.9	3735.6	3730.3	3715.6	3701.0
12.5°	3205.9	3220.6	3235.2	3287.1	3339.0	3405.6	3472.1	3529.3	3586.6	3626.5	3666.4
15°	2664.3	2704.9	2745.5	2792.7	2840.0	2937.8	3035.6	3156.0	3276.5	3383.6	3490.7
17.5°	2194.5	2209.8	2225.1	2275.7	2326.3	2449.4	2572.5	2711.5	2850.6	3028.3	3205.9
20°	1805.9	1819.9	1833.9	1900.4	1966.9	2063.4	2159.9	2316.3	2472.7	2663.6	2854.6
22.5°	1517.1	1539.1	1561.0	1598.3	1635.6	1728.1	1820.6	1959.6	2098.7	2309.6	2520.6
25°	1328.2	1344.1	1360.1	1382.7	1405.3	1479.2	1553.1	1667.5	1782.0	1975.6	2169.2
27.5°	1199.1	1205.7	1212.4	1235.0	1257.6	1305.5	1353.4	1451.9	1550.4	1714.8	1879.1
30°	1097.9	1102.6	1107.2	1127.2	1147.2	1179.8	1212.4	1283.6	1354.8	1499.8	1644.9
32.5°	1027.4	1030.7	1034.0	1049.3	1064.7	1087.9	1111.2	1163.1	1215.0	1334.8	1454.6
35°	963.5	965.5	967.5	978.8	990.1	1007.4	1024.7	1064.0	1103.2	1197.7	1292.2
37.5°	907.6	910.3	912.9	919.6	926.2	941.6	956.9	988.1	1019.4	1091.9	1164.5
40°	853.1	857.7	862.4	867.0	871.7	884.3	897.0	920.9	944.9	1004.8	1064.7
42.5°	806.5	811.1	815.8	817.8	819.8	827.1	834.4	856.4	878.3	922.9	967.5
45°	761.2	763.2	765.2	767.2	769.2	775.2	781.2	800.5	819.8	858.4	897.0
47.5°	720.0	720.0	720.0	721.3	722.6	728.0	733.3	747.3	761.2	791.2	821.1
50°	680.0	680.0	680.0	678.1	676.1	679.4	682.7	693.4	704.0	730.6	757.2
52.5°	632.1	632.1	632.1	632.8	633.5	633.5	633.5	642.8	652.1	676.1	700.0
55°	584.2	586.9	589.6	587.6	585.6	586.9	588.2	594.2	600.2	619.5	638.8
57.5°	536.3	537.7	539.0	538.3	537.7	538.3	539.0	544.3	549.6	564.3	578.9
60°	491.1	491.1	491.1	489.7	488.4	489.7	491.1	493.7	496.4	509.7	523.0
62.5°	440.5	441.2	441.8	442.5	443.2	441.8	440.5	443.8	447.2	457.1	467.1
65°	389.9	390.6	391.3	393.3	395.3	393.9	392.6	395.9	399.2	406.6	413.9
67.5°	344.7	343.4	342.0	342.7	343.4	345.3	347.3	348.0	348.7	356.7	364.6
70°	291.4	292.8	294.1	293.4	292.8	293.4	294.1	296.1	298.1	304.1	310.1
72.5°	243.5	244.2	244.9	244.9	244.9	246.2	247.5	249.5	251.5	254.9	258.2
75°	199.6	199.6	199.6	201.0	202.3	202.9	203.6	203.6	203.6	206.3	208.9
77.5°	151.7	155.0	158.4	157.7	157.0	158.4	159.7	161.7	163.7	165.0	166.4
80°	110.5	110.5	110.5	111.1	111.8	113.8	115.8	117.1	118.4	121.1	123.8
82.5°	70.5	71.2	71.9	73.9	75.9	77.2	78.5	80.5	82.5	82.5	82.5
85°	43.9	42.6	41.3	42.6	43.9	45.2	46.6	47.2	47.9	49.2	50.6
87.5°	21.3	21.3	21.3	21.3	21.3	22.0	22.6	22.6	22.6	22.6	22.6
90°	23.5	23.1	22.8	22.4	22.1	21.5	20.8	20.2	19.5	18.8	16.5
92.5°	26.6	26.4	26.2	26.1	25.9	25.2	24.0	22.8	21.5	20.3	18.8
95°	29.7	29.7	29.7	29.7	29.7	29.1	27.9	26.7	25.5	24.2	22.3
97.5°	32.1	31.9	31.7	31.5	31.4	30.6	29.2	27.8	26.4	25.0	33.9
100°	32.8	32.7	32.5	32.3	32.1	31.4	30.0	28.6	27.2	25.8	52.9
102.5°	33.6	33.3	32.9	32.6	32.2	34.9	40.7	46.4	52.1	57.9	88.1
105°	34.4	34.1	33.7	33.4	33.0	48.2	79.0	109.7	140.5	171.2	186.8
107.5°	81.3	104.1	126.8	149.6	172.3	197.1	223.9	250.6	277.4	304.1	301.5
110°	215.0	239.8	264.7	289.5	314.4	329.7	335.4	341.1	346.9	352.6	350.7



TEST NUMBER: P831156

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	407.3	407.7	408.0	408.4	408.7	408.1	406.5	405.0	403.4	401.8	399.9
115°	459.7	459.0	458.3	457.6	456.9	455.7	454.0	452.2	450.5	448.8	447.2
117.5°	501.9	501.7	501.6	501.4	501.2	500.4	499.0	497.7	496.3	494.9	494.0
120°	545.7	545.7	545.7	545.7	545.7	545.0	543.6	542.2	540.8	539.4	538.9
122.5°	588.7	588.5	588.3	588.2	588.0	587.5	586.6	585.7	584.9	584.0	583.3
125°	628.6	628.2	627.9	627.5	627.2	626.8	626.5	626.1	625.8	625.4	624.7
127.5°	667.7	668.0	668.3	668.7	669.0	669.0	668.4	667.9	667.4	666.9	666.0
130°	705.2	705.5	705.9	706.2	706.6	706.4	705.7	705.0	704.3	703.6	702.9
132.5°	739.6	740.1	740.6	741.1	741.7	741.6	740.9	740.2	739.5	738.8	738.3
135°	774.8	775.3	775.8	776.3	776.8	776.8	776.3	775.8	775.3	774.8	774.1
137.5°	808.4	808.7	809.1	809.4	809.8	809.5	808.6	807.8	806.9	806.0	805.7
140°	838.1	838.4	838.8	839.1	839.5	839.3	838.6	837.9	837.2	836.5	836.0
142.5°	865.4	866.0	866.5	867.0	867.5	867.5	867.0	866.5	866.0	865.4	864.9
145°	893.6	893.6	893.6	893.6	893.6	893.4	893.1	892.7	892.4	892.0	891.7
147.5°	913.9	914.8	915.7	916.5	917.4	917.7	917.3	917.0	916.6	916.3	915.9
150°	937.4	937.9	938.4	938.9	939.5	939.5	939.2	938.8	938.5	938.2	937.8
152.5°	956.1	957.0	957.9	958.7	959.6	959.7	959.0	958.3	957.6	956.9	956.7
155°	973.3	974.4	975.4	976.5	977.5	977.6	976.7	975.9	975.0	974.1	973.9
157.5°	988.2	989.6	991.0	992.4	993.7	993.9	992.9	991.8	990.8	989.8	989.9
160°	1002.3	1003.5	1004.7	1005.9	1007.1	1007.2	1006.2	1005.1	1004.1	1003.0	1003.2
162.5°	1015.6	1016.6	1017.6	1018.7	1019.7	1019.6	1018.4	1017.2	1016.0	1014.8	1014.9
165°	1025.7	1026.9	1028.1	1029.4	1030.6	1030.5	1029.1	1027.7	1026.3	1024.9	1025.1
167.5°	1033.5	1034.9	1036.3	1037.7	1039.1	1039.1	1037.7	1036.3	1034.9	1033.5	1033.5
170°	1040.6	1042.0	1043.3	1044.7	1046.1	1046.1	1044.7	1043.3	1042.0	1040.6	1040.6
172.5°	1044.5	1046.0	1047.6	1049.2	1050.7	1050.8	1049.4	1048.0	1046.6	1045.3	1045.1
175°	1048.4	1049.8	1051.2	1052.6	1053.9	1054.0	1052.8	1051.6	1050.4	1049.2	1049.0
177.5°	1049.2	1050.9	1052.6	1054.4	1056.1	1056.3	1054.9	1053.5	1052.1	1050.7	1050.6
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P831156

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2867.9	2867.9	2867.9	2867.9	2867.9	2867.9	2867.9	2867.9	2867.9	2867.9	2867.9
2.5°	3067.5	3059.5	3030.3	3001.0	2967.7	2934.5	2909.8	2885.2	2848.6	2812.0	2782.1
5°	3324.4	3287.1	3225.2	3163.4	3079.5	2995.7	2939.1	2882.6	2806.7	2730.8	2670.3
7.5°	3528.0	3464.1	3377.6	3291.1	3181.3	3071.5	2967.7	2863.9	2748.1	2632.4	2537.9
10°	3657.8	3614.5	3514.7	3414.9	3267.8	3120.8	2975.7	2830.6	2681.6	2532.5	2407.4
12.5°	3670.4	3674.4	3582.6	3490.7	3324.4	3158.0	2981.7	2805.4	2617.7	2430.1	2284.3
15°	3559.3	3627.8	3577.2	3526.7	3359.0	3191.3	2974.4	2757.5	2541.2	2324.9	2156.6
17.5°	3353.0	3500.0	3507.4	3514.7	3347.0	3179.3	2939.1	2698.9	2454.0	2209.2	2032.2
20°	3071.5	3288.4	3363.0	3437.5	3301.1	3164.7	2906.5	2648.3	2374.2	2100.0	1914.4
22.5°	2784.1	3047.6	3184.0	3320.4	3219.2	3118.1	2843.3	2568.5	2279.0	1989.6	1801.3
25°	2456.7	2744.1	2953.7	3163.4	3101.5	3039.6	2768.8	2497.9	2189.9	1881.8	1689.5
27.5°	2171.2	2463.3	2716.2	2969.1	2955.7	2942.4	2673.6	2404.8	2089.4	1774.0	1588.3
30°	1917.0	2189.2	2472.0	2754.8	2787.4	2820.0	2560.5	2301.0	1984.9	1668.8	1489.8
32.5°	1692.1	1929.7	2233.1	2536.5	2600.4	2664.3	2430.1	2195.8	1883.1	1570.4	1398.0
35°	1507.8	1723.4	2026.8	2330.3	2410.1	2490.0	2286.3	2082.7	1778.0	1473.2	1308.9
37.5°	1344.8	1525.1	1821.2	2117.3	2215.1	2313.0	2130.6	1948.3	1662.9	1377.4	1226.3
40°	1209.7	1354.8	1626.9	1899.1	2012.2	2125.3	1974.9	1824.6	1553.7	1282.9	1143.8
42.5°	1096.6	1225.7	1472.5	1719.4	1827.9	1936.3	1809.2	1682.2	1441.3	1200.4	1073.3
45°	1000.1	1103.2	1327.5	1551.7	1654.9	1758.0	1648.9	1539.8	1327.5	1115.2	996.8
47.5°	909.6	998.1	1189.8	1381.4	1473.2	1565.0	1479.9	1394.7	1215.0	1035.4	928.2
50°	828.4	899.6	1067.3	1235.0	1314.8	1394.7	1319.5	1244.3	1096.6	948.9	855.7
52.5°	757.9	815.8	956.2	1096.6	1165.1	1233.7	1169.1	1104.6	987.5	870.4	789.2
55°	688.0	737.3	859.0	980.8	1027.4	1074.0	1024.1	974.2	879.7	785.2	716.6
57.5°	622.8	666.7	766.6	866.4	902.3	938.2	893.0	847.7	776.5	705.3	648.1
60°	558.9	594.9	678.1	761.2	783.2	805.1	768.5	731.9	682.0	632.1	580.9
62.5°	499.7	532.3	594.2	656.1	670.7	685.4	657.4	629.5	591.5	553.6	513.7
65°	438.5	463.1	513.7	564.3	573.6	582.9	558.3	533.7	505.0	476.4	447.2
67.5°	381.9	399.2	440.5	481.8	482.4	483.1	463.1	443.2	427.2	411.2	387.9
70°	326.7	343.4	370.6	397.9	398.6	399.2	383.3	367.3	355.3	343.4	326.1
72.5°	270.2	282.1	302.8	323.4	322.1	320.7	310.7	300.8	291.4	282.1	269.5
75°	218.9	228.9	242.9	256.8	252.9	248.9	243.5	238.2	230.2	222.2	214.3
77.5°	172.3	178.3	186.3	194.3	191.6	189.0	184.3	179.7	173.7	167.7	164.4
80°	126.4	129.1	134.4	139.7	138.4	137.1	131.8	126.4	125.1	123.8	119.1
82.5°	85.8	89.2	90.5	91.8	91.2	90.5	86.5	82.5	81.2	79.8	79.2
85°	51.2	51.9	52.6	53.2	51.2	49.2	47.9	46.6	46.6	46.6	45.9
87.5°	23.3	24.0	24.0	24.0	23.3	22.6	21.3	20.0	20.6	21.3	21.3
90°	14.2	12.0	9.7	7.7	6.0	4.3	2.5	0.8	2.5	4.3	6.0
92.5°	17.2	15.6	14.1	13.8	14.9	15.9	16.9	18.0	16.9	15.9	14.9
95°	20.4	18.5	16.6	19.2	26.3	33.4	40.6	47.7	40.6	33.4	26.3
97.5°	42.7	51.6	60.5	67.3	72.2	77.1	81.9	86.8	81.9	77.1	72.2
100°	80.0	107.1	134.2	146.0	142.5	139.1	135.6	132.1	135.6	139.1	142.5
102.5°	118.3	148.5	178.8	192.8	190.5	188.2	186.0	183.7	186.0	188.2	190.5
105°	202.5	218.1	233.8	240.6	238.7	236.8	234.9	233.0	234.9	236.8	238.7
107.5°	298.9	296.3	293.7	291.6	290.0	288.5	286.9	285.4	286.9	288.5	290.0
110°	348.8	346.9	344.9	343.3	341.9	340.5	339.1	337.7	339.1	340.5	341.9



TEST NUMBER: P831156

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	398.0	396.1	394.2	392.6	391.4	390.2	389.0	387.8	389.0	390.2	391.4
115°	445.6	444.1	442.5	441.2	440.2	439.1	438.1	437.0	438.1	439.1	440.2
117.5°	493.1	492.3	491.4	490.4	489.1	487.9	486.7	485.5	486.7	487.9	489.1
120°	538.4	537.9	537.4	536.3	534.7	533.2	531.6	530.1	531.6	533.2	534.7
122.5°	582.6	581.9	581.2	580.3	579.0	577.8	576.6	575.4	576.6	577.8	579.0
125°	624.0	623.4	622.7	621.6	620.2	618.8	617.4	616.1	617.4	618.8	620.2
127.5°	665.1	664.3	663.4	662.3	660.9	659.5	658.1	656.7	658.1	659.5	660.9
130°	702.2	701.5	700.8	699.8	698.4	697.0	695.6	694.2	695.6	697.0	698.4
132.5°	737.8	737.2	736.7	735.8	734.4	733.0	731.6	730.2	731.6	733.0	734.4
135°	773.4	772.7	772.0	771.1	770.1	769.0	768.0	766.9	768.0	769.0	770.1
137.5°	805.3	805.0	804.6	803.8	802.4	801.0	799.6	798.2	799.6	801.0	802.4
140°	835.5	835.0	834.4	833.7	832.6	831.6	830.5	829.5	830.5	831.6	832.6
142.5°	864.4	863.9	863.4	862.6	861.5	860.5	859.5	858.4	859.5	860.5	861.5
145°	891.3	891.0	890.6	889.9	888.6	887.4	886.2	885.0	886.2	887.4	888.6
147.5°	915.6	915.2	914.9	914.3	913.4	912.5	911.7	910.8	911.7	912.5	913.4
150°	937.5	937.1	936.8	936.3	935.8	935.3	934.8	934.2	934.8	935.3	935.8
152.5°	956.6	956.4	956.2	956.0	955.9	955.7	955.5	955.4	955.5	955.7	955.9
155°	973.8	973.6	973.4	973.5	973.9	974.2	974.6	974.9	974.6	974.2	973.9
157.5°	990.1	990.3	990.4	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5
160°	1003.4	1003.6	1003.7	1003.9	1004.1	1004.3	1004.4	1004.6	1004.4	1004.3	1004.1
162.5°	1015.1	1015.3	1015.5	1015.8	1016.3	1016.9	1017.4	1017.9	1017.4	1016.9	1016.3
165°	1025.3	1025.5	1025.6	1026.0	1026.5	1027.0	1027.5	1028.1	1027.5	1027.0	1026.5
167.5°	1033.5	1033.5	1033.5	1033.9	1034.6	1035.3	1036.0	1036.7	1036.0	1035.3	1034.6
170°	1040.6	1040.6	1040.6	1040.9	1041.6	1042.3	1043.0	1043.7	1043.0	1042.3	1041.6
172.5°	1044.9	1044.7	1044.6	1044.9	1045.8	1046.6	1047.5	1048.4	1047.5	1046.6	1045.8
175°	1048.8	1048.6	1048.5	1048.8	1049.7	1050.6	1051.4	1052.3	1051.4	1050.6	1049.7
177.5°	1050.4	1050.2	1050.0	1050.4	1051.3	1052.1	1053.0	1053.9	1053.0	1052.1	1051.3
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P831156

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2867.9	2867.9	2867.9	2867.9	2867.9	2867.9	2867.9	2867.9	2867.9	2867.9	2867.9
2.5°	2752.1	2726.2	2700.2	2680.3	2660.3	2626.4	2592.4	2584.4	2576.5	2565.2	2553.8
5°	2609.7	2545.9	2482.0	2424.7	2367.5	2322.9	2278.4	2249.1	2219.8	2198.5	2177.2
7.5°	2443.4	2347.6	2251.7	2183.9	2116.0	2051.5	1986.9	1966.3	1945.7	1917.7	1889.8
10°	2282.4	2176.6	2070.8	1982.3	1893.8	1830.5	1767.3	1742.0	1716.8	1681.5	1646.2
12.5°	2138.6	2022.8	1907.1	1817.9	1728.7	1667.5	1606.3	1569.7	1533.1	1513.1	1493.2
15°	1988.2	1864.5	1740.7	1658.2	1575.7	1520.5	1465.2	1433.3	1401.4	1382.1	1362.8
17.5°	1855.2	1732.7	1610.3	1531.1	1451.9	1401.4	1350.8	1322.8	1294.9	1280.2	1265.6
20°	1728.7	1609.0	1489.2	1412.0	1334.8	1293.6	1252.3	1234.3	1216.4	1204.4	1192.4
22.5°	1613.0	1495.2	1377.4	1311.5	1245.6	1212.4	1179.1	1166.5	1153.8	1143.8	1133.9
25°	1497.2	1392.0	1286.9	1231.0	1175.1	1147.8	1120.5	1107.9	1095.3	1085.3	1075.3
27.5°	1402.7	1302.2	1201.7	1153.8	1105.9	1084.6	1063.3	1053.3	1043.4	1034.0	1024.7
30°	1310.9	1221.0	1131.2	1089.9	1048.7	1029.4	1010.1	1000.1	990.1	981.5	972.8
32.5°	1225.7	1148.5	1071.3	1033.4	995.5	979.5	963.5	951.5	939.6	932.9	926.2
35°	1144.5	1075.3	1006.1	974.8	943.5	927.6	911.6	901.6	891.6	886.3	881.0
37.5°	1075.3	1013.4	951.5	921.6	891.6	876.3	861.0	852.4	843.7	841.7	839.7
40°	1004.8	951.5	898.3	869.0	839.7	826.4	813.1	807.8	802.5	801.2	799.8
42.5°	946.2	894.3	842.4	815.8	789.2	777.9	766.6	763.9	761.2	763.2	765.2
45°	878.3	835.1	791.8	767.2	742.6	733.3	724.0	722.0	720.0	724.0	728.0
47.5°	821.1	781.2	741.3	718.0	694.7	688.0	681.4	680.7	680.0	685.4	690.7
50°	762.6	724.0	685.4	666.7	648.1	642.1	636.1	638.1	640.1	648.8	657.4
52.5°	708.0	672.1	636.1	618.8	601.5	597.5	593.5	598.2	602.9	612.2	621.5
55°	648.1	615.5	582.9	569.6	556.3	552.3	548.3	557.6	566.9	575.6	584.2
57.5°	590.9	562.3	533.7	521.7	509.7	509.0	508.4	517.0	525.7	535.0	544.3
60°	529.7	505.7	481.8	472.4	463.1	464.5	465.8	475.8	485.7	493.1	500.4
62.5°	473.8	453.8	433.8	425.2	416.5	419.9	423.2	433.2	443.2	451.8	460.5
65°	417.9	401.2	384.6	378.6	372.6	377.3	381.9	390.6	399.2	405.2	411.2
67.5°	364.6	350.7	336.7	332.0	327.4	332.0	336.7	345.3	354.0	360.0	366.0
70°	308.7	297.4	286.1	282.8	279.5	284.8	290.1	297.4	304.8	310.7	316.7
72.5°	256.8	248.2	239.5	238.9	238.2	242.9	247.5	254.9	262.2	266.2	270.2
75°	206.3	201.6	197.0	196.3	195.6	200.3	204.9	208.9	212.9	216.3	219.6
77.5°	161.0	157.0	153.0	153.7	154.4	157.7	161.0	165.0	169.0	171.0	173.0
80°	114.5	113.1	111.8	113.1	114.5	117.1	119.8	122.4	125.1	126.4	127.8
82.5°	78.5	77.2	75.9	77.9	79.8	81.8	83.8	85.8	87.8	88.5	89.2
85°	45.2	47.2	49.2	49.2	49.2	49.9	50.6	51.2	51.9	51.2	50.6
87.5°	21.3	22.0	22.6	22.6	22.6	23.3	24.0	24.0	24.0	23.3	22.6
90°	7.7	9.7	12.0	14.2	16.5	18.8	19.5	20.2	20.8	21.5	22.1
92.5°	13.8	14.1	15.6	17.2	18.8	20.3	21.5	22.8	24.0	25.2	25.9
95°	19.2	16.6	18.5	20.4	22.3	24.2	25.5	26.7	27.9	29.1	29.7
97.5°	67.3	60.5	51.6	42.7	33.9	25.0	26.4	27.8	29.2	30.6	31.4
100°	146.0	134.2	107.1	80.0	52.9	25.8	27.2	28.6	30.0	31.4	32.1
102.5°	192.8	178.8	148.5	118.3	88.1	57.9	52.1	46.4	40.7	34.9	32.2
105°	240.6	233.8	218.1	202.5	186.8	171.2	140.5	109.7	79.0	48.2	33.0
107.5°	291.6	293.7	296.3	298.9	301.5	304.1	277.4	250.6	223.9	197.1	172.3
110°	343.3	344.9	346.9	348.8	350.7	352.6	346.9	341.1	335.4	329.7	314.4



TEST NUMBER: P831156

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	392.6	394.2	396.1	398.0	399.9	401.8	403.4	405.0	406.5	408.1	408.7
115°	441.2	442.5	444.1	445.6	447.2	448.8	450.5	452.2	454.0	455.7	456.9
117.5°	490.4	491.4	492.3	493.1	494.0	494.9	496.3	497.7	499.0	500.4	501.2
120°	536.3	537.4	537.9	538.4	538.9	539.4	540.8	542.2	543.6	545.0	545.7
122.5°	580.3	581.2	581.9	582.6	583.3	584.0	584.9	585.7	586.6	587.5	588.0
125°	621.6	622.7	623.4	624.0	624.7	625.4	625.8	626.1	626.5	626.8	627.2
127.5°	662.3	663.4	664.3	665.1	666.0	666.9	667.4	667.9	668.4	669.0	669.0
130°	699.8	700.8	701.5	702.2	702.9	703.6	704.3	705.0	705.7	706.4	706.6
132.5°	735.8	736.7	737.2	737.8	738.3	738.8	739.5	740.2	740.9	741.6	741.7
135°	771.1	772.0	772.7	773.4	774.1	774.8	775.3	775.8	776.3	776.8	776.8
137.5°	803.8	804.6	805.0	805.3	805.7	806.0	806.9	807.8	808.6	809.5	809.8
140°	833.7	834.4	835.0	835.5	836.0	836.5	837.2	837.9	838.6	839.3	839.5
142.5°	862.6	863.4	863.9	864.4	864.9	865.4	866.0	866.5	867.0	867.5	867.5
145°	889.9	890.6	891.0	891.3	891.7	892.0	892.4	892.7	893.1	893.4	893.6
147.5°	914.3	914.9	915.2	915.6	915.9	916.3	916.6	917.0	917.3	917.7	917.4
150°	936.3	936.8	937.1	937.5	937.8	938.2	938.5	938.8	939.2	939.5	939.5
152.5°	956.0	956.2	956.4	956.6	956.7	956.9	957.6	958.3	959.0	959.7	959.6
155°	973.5	973.4	973.6	973.8	973.9	974.1	975.0	975.9	976.7	977.6	977.5
157.5°	990.5	990.4	990.3	990.1	989.9	989.8	990.8	991.8	992.9	993.9	993.7
160°	1003.9	1003.7	1003.6	1003.4	1003.2	1003.0	1004.1	1005.1	1006.2	1007.2	1007.1
162.5°	1015.8	1015.5	1015.3	1015.1	1014.9	1014.8	1016.0	1017.2	1018.4	1019.6	1019.7
165°	1026.0	1025.6	1025.5	1025.3	1025.1	1024.9	1026.3	1027.7	1029.1	1030.5	1030.6
167.5°	1033.9	1033.5	1033.5	1033.5	1033.5	1033.5	1034.9	1036.3	1037.7	1039.1	1039.1
170°	1040.9	1040.6	1040.6	1040.6	1040.6	1040.6	1042.0	1043.3	1044.7	1046.1	1046.1
172.5°	1044.9	1044.6	1044.7	1044.9	1045.1	1045.3	1046.6	1048.0	1049.4	1050.8	1050.7
175°	1048.8	1048.5	1048.6	1048.8	1049.0	1049.2	1050.4	1051.6	1052.8	1054.0	1053.9
177.5°	1050.4	1050.0	1050.2	1050.4	1050.6	1050.7	1052.1	1053.5	1054.9	1056.3	1056.1
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3

TEST NUMBER: P831156

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2867.9	2867.9	2867.9	2867.9
2.5°	2549.2	2544.5	2525.9	2507.3
5°	2161.2	2145.3	2140.0	2134.6
7.5°	1888.4	1887.1	1859.2	1831.2
10°	1648.2	1650.2	1624.9	1599.6
12.5°	1476.5	1459.9	1457.9	1455.9
15°	1347.5	1332.1	1329.5	1326.8
17.5°	1256.3	1247.0	1244.3	1241.7
20°	1187.1	1181.8	1177.1	1172.5
22.5°	1127.2	1120.5	1116.6	1112.6
25°	1069.3	1063.3	1062.0	1060.7
27.5°	1017.4	1010.1	1010.1	1010.1
30°	968.2	963.5	961.5	959.5
32.5°	922.3	918.3	918.3	918.3
35°	879.0	877.0	874.3	871.7
37.5°	839.7	839.7	838.4	837.1
40°	801.8	803.8	803.8	803.8
42.5°	767.2	769.2	769.2	769.2
45°	731.3	734.6	735.9	737.3
47.5°	696.0	701.3	702.7	704.0
50°	661.4	665.4	666.1	666.7
52.5°	626.1	630.8	634.1	637.5
55°	588.9	593.5	595.5	597.5
57.5°	549.0	553.6	554.3	555.0
60°	505.0	509.7	511.0	512.4
62.5°	463.1	465.8	467.1	468.4
65°	415.2	419.2	421.9	424.5
67.5°	369.3	372.6	372.6	372.6
70°	318.1	319.4	321.4	323.4
72.5°	270.8	271.5	271.5	271.5
75°	220.9	222.2	222.9	223.6
77.5°	173.7	174.3	174.3	174.3
80°	127.1	126.4	126.4	126.4
82.5°	87.2	85.2	85.2	85.2
85°	49.9	49.2	49.9	50.6
87.5°	22.6	22.6	22.6	22.6
90°	22.4	22.8	23.1	23.5
92.5°	26.1	26.2	26.4	26.6
95°	29.7	29.7	29.7	29.7
97.5°	31.5	31.7	31.9	32.1
100°	32.3	32.5	32.7	32.8
102.5°	32.6	32.9	33.3	33.6
105°	33.4	33.7	34.1	34.4
107.5°	149.6	126.8	104.1	81.3
110°	289.5	264.7	239.8	215.0



TEST NUMBER: P831156

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	408.4	408.0	407.7	407.3
115°	457.6	458.3	459.0	459.7
117.5°	501.4	501.6	501.7	501.9
120°	545.7	545.7	545.7	545.7
122.5°	588.2	588.3	588.5	588.7
125°	627.5	627.9	628.2	628.6
127.5°	668.7	668.3	668.0	667.7
130°	706.2	705.9	705.5	705.2
132.5°	741.1	740.6	740.1	739.6
135°	776.3	775.8	775.3	774.8
137.5°	809.4	809.1	808.7	808.4
140°	839.1	838.8	838.4	838.1
142.5°	867.0	866.5	866.0	865.4
145°	893.6	893.6	893.6	893.6
147.5°	916.5	915.7	914.8	913.9
150°	938.9	938.4	937.9	937.4
152.5°	958.7	957.9	957.0	956.1
155°	976.5	975.4	974.4	973.3
157.5°	992.4	991.0	989.6	988.2
160°	1005.9	1004.7	1003.5	1002.3
162.5°	1018.7	1017.6	1016.6	1015.6
165°	1029.4	1028.1	1026.9	1025.7
167.5°	1037.7	1036.3	1034.9	1033.5
170°	1044.7	1043.3	1042.0	1040.6
172.5°	1049.2	1047.6	1046.0	1044.5
175°	1052.6	1051.2	1049.8	1048.4
177.5°	1054.4	1052.6	1050.9	1049.2
180°	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P831156

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.28	17.19	17.17	18.09	19.23	18.52	19.42	19.41	20.32	21.46
	3H	17.93	18.74	18.83	19.65	20.82	19.95	20.76	20.85	21.67	22.83
	4H	18.51	19.28	19.43	20.19	21.37	20.40	21.17	21.31	22.08	23.26
	6H	18.89	19.59	19.81	20.51	21.70	20.68	21.38	21.60	22.30	23.49
	8H	18.98	19.65	19.92	20.59	21.78	20.74	21.41	21.67	22.35	23.54
	12H	19.03	19.67	19.97	20.60	21.81	20.76	21.40	21.70	22.33	23.54
4H	2H	16.86	17.63	17.78	18.54	19.72	18.69	19.45	19.61	20.37	21.54
	3H	18.70	19.33	19.62	20.28	21.47	20.31	20.95	21.24	21.89	23.08
	4H	19.40	19.98	20.33	20.92	22.13	20.90	21.48	21.84	22.42	23.63
	6H	19.87	20.37	20.83	21.34	22.55	21.31	21.80	22.26	22.77	23.98
	8H	20.01	20.48	20.96	21.44	22.66	21.42	21.88	22.37	22.84	24.07
	12H	20.08	20.50	21.05	21.48	22.71	21.46	21.88	22.44	22.86	24.09
8H	4H	19.67	20.13	20.62	21.09	22.32	21.01	21.47	21.96	22.43	23.66
	6H	20.26	20.64	21.24	21.64	22.87	21.51	21.90	22.49	22.90	24.12
	8H	20.46	20.80	21.45	21.79	23.04	21.69	22.03	22.68	23.02	24.27
	12H	20.59	20.89	21.58	21.87	23.16	21.79	22.09	22.78	23.07	24.37
12H	4H	19.67	20.09	20.64	21.06	22.30	20.98	21.40	21.96	22.38	23.61
	6H	20.31	20.65	21.29	21.64	22.88	21.53	21.86	22.51	22.85	24.10
	8H	20.54	20.84	21.53	21.82	23.12	21.73	22.03	22.72	23.01	24.30