

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332241-927

Luminaire Tested: **S123RDIP-S340D365U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332241-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D365U927-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2061.9 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332241-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332241-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52
1	99	95	91	88	91	88	85	82	75	73	71	63	62	60	52	51	50	45
2	91	83	78	73	84	78	72	68	66	63	59	56	54	51	47	45	43	39
3	83	74	67	61	77	69	63	58	59	55	51	50	47	44	42	40	37	34
4	76	66	58	52	70	61	55	49	53	48	44	45	41	38	38	35	33	29
5	70	59	51	45	65	55	48	43	48	42	38	41	37	33	34	31	29	26
6	65	53	45	40	60	50	43	38	43	38	34	37	33	30	31	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21
8	56	44	36	31	52	41	34	30	36	30	27	31	27	24	27	23	21	19
9	52	40	33	28	48	38	31	26	33	28	24	29	24	21	25	21	19	17
10	49	37	30	25	45	35	28	24	30	25	22	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4640	4640	4640	4640
5°	5532	4660	4105	4660
10°	6907	4634	3707	4634
15°	8107	4586	3381	4586
20°	9049	4515	3103	4515
25°	8904	4441	2932	4441
30°	6400	4373	2757	4373
35°	4273	4282	2643	4282
40°	3147	4175	2525	4175
45°	2641	3987	2411	3987
50°	2331	3739	2251	3739
55°	2044	3457	2029	3457
60°	1819	3186	1858	3186
65°	1597	2896	1729	2896
70°	1253	2637	1580	2637
75°	1102	2304	1443	2304
80°	961	1953	1420	1953
85°	778	1581	1507	1581



TEST NUMBER: P332241-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.4	2.1
10°-20°	132.5	6.4
20°-30°	208.1	10.1
30°-40°	217.1	10.5
40°-50°	185.8	9.0
50°-60°	141.6	6.9
60°-70°	90.8	4.4
70°-80°	43.7	2.1
80°-90°	12.6	0.6
90°-100°	23.2	1.1
100°-110°	69.5	3.4
110°-120°	118.2	5.7
120°-130°	155.5	7.5
130°-140°	174.7	8.5
140°-150°	171.8	8.3
150°-160°	144.6	7.0
160°-170°	96.3	4.7
170°-180°	33.7	1.6
0°-30°	382.9	18.6
0°-40°	600.1	29.1
0°-60°	927.5	45.0
0°-90°	1074.5	52.1
90°-120°	210.9	10.2
90°-150°	712.8	34.6
90°-180°	987.0	47.9
0°-180°	2061.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	431	431	431	431	431	
5°	512	431	380	431	512	53
15°	728	412	303	412	728	206
25°	750	374	247	374	750	322
35°	325	326	201	326	325	213
45°	174	262	158	262	174	136
55°	109	184	108	184	109	98
65°	63	114	68	114	63	62
75°	26	55	35	55	26	28
85°	6	13	12	13	6	7
90°	8	0	8	0	8	4
95°	22	17	22	17	22	22
105°	67	63	67	63	67	71
115°	119	119	119	119	119	118
125°	172	174	172	174	172	154
135°	226	226	226	226	226	173
145°	274	274	274	274	274	171
155°	313	314	313	314	313	144
165°	341	342	341	342	341	96
175°	354	356	354	356	354	34
180°	356	356	356	356	356	



TEST NUMBER: P332241-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	459.2	459.8	457.9	457.6	455.3	454.8	454.8	451.6	449.7	447.3	445.8
5°	512.0	514.9	513.4	510.2	504.6	503.3	499.8	494.2	488.0	480.2	476.6
7.5°	577.9	581.9	580.4	575.3	569.4	564.7	554.8	545.7	532.8	521.5	511.8
10°	631.9	627.7	624.4	619.4	614.0	605.4	595.0	580.8	564.4	551.4	537.1
12.5°	672.4	671.7	667.5	662.3	654.8	646.6	633.8	616.6	597.5	578.8	562.3
15°	727.5	728.6	725.9	720.6	709.8	695.2	676.0	668.8	641.5	621.2	600.9
17.5°	765.7	765.5	765.1	757.7	746.8	736.4	718.6	699.7	674.9	646.3	619.0
20°	790.0	788.1	788.5	780.1	772.1	760.0	742.7	715.2	694.9	661.9	633.6
22.5°	789.3	788.9	790.4	787.5	781.6	772.5	758.8	735.5	709.6	676.3	644.5
25°	749.7	748.2	756.9	759.3	768.7	770.4	766.3	753.6	729.0	694.7	655.4
27.5°	627.4	626.6	642.7	662.9	688.4	708.3	727.5	736.7	729.0	704.4	665.0
30°	514.9	532.3	540.4	569.6	602.1	640.8	674.8	707.0	715.0	704.3	672.0
32.5°	427.5	442.7	449.5	474.4	504.8	550.2	601.1	646.8	679.1	687.3	667.9
35°	325.2	325.3	340.9	352.0	380.0	426.7	476.2	537.4	598.3	644.5	649.3
37.5°	259.5	260.4	269.8	280.8	301.9	326.5	370.1	421.0	491.4	562.2	603.8
40°	224.0	225.7	232.7	243.6	258.7	277.4	311.3	359.3	418.0	496.9	561.3
42.5°	201.3	204.0	207.6	216.0	225.4	242.9	270.3	307.4	360.8	435.3	509.6
45°	173.5	175.0	177.8	181.6	190.1	202.2	220.7	245.7	289.9	349.9	424.3
47.5°	153.0	152.3	155.2	158.3	164.0	172.3	184.7	204.9	236.5	284.7	347.8
50°	139.2	138.9	141.0	143.4	148.8	154.9	165.0	180.3	205.4	245.3	303.1
52.5°	126.2	126.8	128.3	131.3	135.1	140.1	149.2	160.3	181.8	216.2	264.4
55°	108.9	109.5	111.5	113.1	115.9	120.9	126.6	135.9	150.6	174.6	214.3
57.5°	94.3	94.0	95.9	96.4	99.5	103.5	108.0	115.2	125.9	143.7	170.4
60°	84.5	84.0	85.6	86.9	88.6	91.9	95.6	102.6	111.1	124.2	147.1
62.5°	75.7	75.4	76.6	78.0	79.3	82.3	85.4	90.8	97.5	108.5	126.7
65°	62.7	63.3	63.8	64.4	65.1	67.0	69.9	73.7	78.3	86.0	99.1
67.5°	49.4	49.9	50.1	51.2	52.8	53.9	55.8	59.0	62.3	68.8	76.2
70°	39.8	39.7	39.8	40.4	42.5	44.4	46.9	49.3	51.3	55.9	62.2
72.5°	34.2	33.9	34.4	34.5	35.5	36.0	37.5	39.8	42.5	45.6	50.1
75°	26.5	26.5	26.5	26.5	27.3	27.6	28.2	28.8	29.7	31.2	34.5
77.5°	19.6	19.6	20.0	20.1	20.3	20.5	20.8	21.4	21.7	22.5	23.9
80°	15.5	15.7	15.5	15.7	15.7	16.1	16.2	16.8	17.0	17.9	18.5
82.5°	11.6	11.6	11.6	11.9	11.9	12.2	12.3	12.7	12.7	13.2	13.7
85°	6.3	5.9	6.3	6.1	6.5	6.1	6.3	6.7	6.7	6.8	7.6
87.5°	3.2	3.4	3.1	3.2	3.2	3.3	3.2	3.2	3.5	3.2	3.2
90°	8.4	8.2	8.2	8.0	7.9	7.7	7.4	7.2	7.0	6.7	5.9
92.5°	11.3	11.4	11.5	11.6	11.6	11.6	11.3	11.2	10.9	10.8	10.3
95°	21.9	21.9	21.9	21.9	21.9	21.7	21.5	21.2	21.0	20.8	20.2
97.5°	33.6	33.6	33.7	33.7	33.7	33.6	33.3	33.0	32.7	32.4	32.1
100°	42.5	42.5	42.3	42.1	42.1	41.9	41.7	41.5	41.4	41.1	40.9
102.5°	51.7	51.7	51.8	51.8	51.8	51.7	51.6	51.4	51.2	51.0	50.6
105°	66.6	66.5	66.4	66.2	66.1	66.1	66.1	66.1	66.1	66.1	65.5
107.5°	82.1	82.2	82.3	82.4	82.5	82.4	82.1	82.0	81.8	81.6	81.4
110°	92.7	92.8	92.9	93.0	93.2	93.1	92.8	92.6	92.4	92.1	92.0



TEST NUMBER: P332241-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	103.9	103.9	103.9	103.9	103.9	103.9	103.5	103.2	102.9	102.7	102.6
115°	119.2	119.3	119.4	119.5	119.5	119.5	119.5	119.4	119.3	119.2	119.4
117.5°	134.9	135.1	135.2	135.4	135.5	135.7	135.7	135.7	135.7	135.7	135.9
120°	145.8	146.0	146.1	146.2	146.3	146.5	146.5	146.6	146.6	146.7	147.0
122.5°	156.4	156.5	156.7	156.9	157.1	157.2	157.4	157.6	157.7	157.9	158.0
125°	172.1	172.4	172.7	172.9	173.2	173.4	173.6	173.9	174.1	174.4	174.5
127.5°	187.9	188.2	188.5	188.8	189.0	189.3	189.7	190.0	190.4	190.8	190.9
130°	198.2	198.7	199.1	199.6	199.9	200.3	200.5	200.8	201.1	201.3	201.5
132.5°	209.0	209.3	209.6	209.9	210.3	210.6	210.9	211.2	211.5	211.8	211.9
135°	225.6	225.8	225.9	226.0	226.2	226.3	226.6	226.8	227.0	227.4	227.4
137.5°	240.3	240.6	240.8	241.1	241.3	241.5	241.9	242.1	242.3	242.6	242.4
140°	250.0	250.4	250.9	251.3	251.8	252.0	252.1	252.1	252.2	252.2	252.2
142.5°	259.8	260.2	260.5	260.9	261.2	261.4	261.4	261.5	261.6	261.7	261.5
145°	274.1	274.3	274.6	274.8	275.0	275.2	275.3	275.4	275.4	275.4	275.3
147.5°	286.7	287.1	287.5	287.9	288.2	288.4	288.4	288.4	288.4	288.4	288.2
150°	294.8	295.2	295.6	295.9	296.3	296.4	296.4	296.4	296.4	296.4	296.4
152.5°	302.6	302.9	303.2	303.6	303.9	304.0	304.0	303.8	303.7	303.6	303.6
155°	313.2	313.7	314.1	314.6	315.0	315.1	314.8	314.6	314.3	314.1	314.0
157.5°	323.0	323.3	323.7	324.0	324.3	324.4	324.2	323.8	323.6	323.4	323.3
160°	329.2	329.5	329.7	329.9	330.2	330.2	329.9	329.5	329.2	328.9	328.9
162.5°	333.9	334.3	334.7	335.1	335.5	335.6	335.3	334.9	334.6	334.3	334.3
165°	340.7	341.1	341.6	342.0	342.5	342.5	342.1	341.7	341.4	341.0	341.0
167.5°	346.5	346.8	347.2	347.6	348.0	348.0	347.6	347.2	346.8	346.5	346.4
170°	349.4	349.8	350.2	350.7	351.1	351.1	350.7	350.2	349.8	349.4	349.4
172.5°	351.6	352.0	352.5	352.9	353.4	353.4	353.0	352.6	352.2	351.8	351.8
175°	354.1	354.6	355.0	355.5	355.8	355.9	355.5	355.1	354.8	354.4	354.4
177.5°	355.5	355.8	356.2	356.6	356.9	356.9	356.6	356.3	356.0	355.7	355.7
180°	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4



TEST NUMBER: P332241-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	445.1	444.7	442.7	440.3	437.2	435.1	433.5	432.6	429.9	426.7	424.5
5°	472.7	467.1	461.2	454.0	447.3	440.5	436.3	431.3	425.2	418.4	413.6
7.5°	502.1	491.2	479.6	467.5	455.6	444.9	435.4	427.3	417.6	407.8	401.0
10°	524.7	508.8	492.4	475.6	460.3	445.9	434.8	424.0	412.3	401.1	392.5
12.5°	545.3	524.3	505.4	484.7	465.2	448.0	432.1	419.2	405.2	393.2	383.6
15°	571.2	549.8	527.0	495.5	469.5	447.7	428.3	411.5	394.6	379.9	370.4
17.5°	595.5	563.3	532.5	506.4	472.5	445.4	421.7	401.6	382.9	367.3	355.7
20°	605.5	574.3	541.0	507.6	474.4	443.9	416.4	394.2	374.9	357.1	346.4
22.5°	611.6	576.3	541.1	505.2	469.9	438.2	411.1	386.7	365.7	348.9	335.6
25°	618.6	576.6	537.8	502.4	466.4	432.1	399.7	373.9	351.3	333.4	319.3
27.5°	623.3	573.8	528.0	488.6	452.1	418.0	388.3	360.9	337.9	318.9	303.9
30°	624.2	571.6	520.5	477.8	440.8	409.3	378.0	351.8	327.4	307.3	293.3
32.5°	625.3	566.1	510.2	465.0	427.0	395.9	367.5	342.5	317.5	297.7	283.4
35°	620.5	563.1	494.8	442.8	404.7	374.6	349.0	325.9	301.4	282.2	267.6
37.5°	599.5	551.1	478.8	417.7	378.0	350.1	329.2	309.1	286.6	265.9	252.2
40°	578.5	539.3	466.4	402.5	361.0	332.4	313.5	297.1	275.4	256.0	241.2
42.5°	547.0	523.2	454.6	386.6	341.8	314.3	298.3	283.0	263.9	244.2	230.3
45°	489.3	492.4	430.4	361.2	315.2	287.6	272.6	261.9	244.9	228.7	214.4
47.5°	416.9	446.2	402.0	334.1	287.2	261.3	248.2	238.8	227.4	211.4	198.4
50°	369.7	411.5	379.3	316.0	269.7	243.8	230.9	223.3	213.3	200.8	188.5
52.5°	326.1	371.1	351.8	295.7	250.6	227.0	214.4	208.1	200.2	188.4	177.2
55°	265.9	311.6	307.1	265.2	222.0	200.8	191.2	184.2	178.9	170.0	161.1
57.5°	215.2	258.3	260.6	231.2	196.9	175.9	167.6	162.3	158.8	152.2	143.9
60°	183.1	222.8	230.5	208.3	178.9	160.4	152.3	148.0	145.3	139.9	133.6
62.5°	156.5	190.3	199.1	183.2	161.6	144.3	137.9	133.9	132.0	127.4	121.8
65°	119.8	147.8	156.3	147.5	136.2	122.4	117.2	113.7	112.0	109.5	105.4
67.5°	90.1	110.5	119.9	113.6	109.5	100.8	97.5	95.6	94.1	92.4	89.0
70°	72.3	87.5	97.0	95.5	92.1	87.5	85.1	83.8	82.3	80.8	77.9
72.5°	58.1	68.6	77.6	78.4	75.7	74.8	72.6	72.1	71.2	69.5	67.8
75°	38.6	45.8	52.0	54.4	55.5	56.5	55.5	55.4	55.2	53.7	52.8
77.5°	25.3	29.2	33.1	37.2	39.0	40.2	40.5	41.2	40.6	39.9	39.5
80°	19.4	20.3	23.1	26.5	29.3	30.4	31.2	31.5	31.4	31.2	30.4
82.5°	14.1	14.8	16.2	18.6	20.9	22.7	23.2	23.1	23.5	23.7	23.1
85°	7.6	7.8	8.2	8.5	9.7	11.8	12.4	12.8	13.1	13.1	12.0
87.5°	3.4	3.1	3.2	3.1	3.4	3.4	4.2	4.8	5.1	4.6	4.7
90°	5.1	4.3	3.5	2.8	2.1	1.5	0.9	0.3	0.9	1.5	2.1
92.5°	9.8	9.3	8.9	8.5	8.1	7.6	7.2	6.8	7.2	7.6	8.1
95°	19.7	19.3	18.7	18.2	17.8	17.3	17.0	16.6	17.0	17.3	17.8
97.5°	31.7	31.4	31.0	30.7	30.3	30.0	29.6	29.3	29.6	30.0	30.3
100°	40.6	40.2	39.9	39.5	39.2	38.8	38.4	38.1	38.4	38.8	39.2
102.5°	50.2	49.7	49.4	49.0	48.8	48.6	48.4	48.2	48.4	48.6	48.8
105°	65.0	64.4	63.8	63.5	63.4	63.2	63.1	63.0	63.1	63.2	63.4
107.5°	81.1	80.9	80.6	80.6	80.5	80.4	80.3	80.2	80.3	80.4	80.5
110°	91.9	91.7	91.6	91.5	91.3	91.3	91.1	91.0	91.1	91.3	91.3



TEST NUMBER: P332241-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	102.6	102.6	102.5	102.5	102.4	102.3	102.3	102.2	102.3	102.3	102.4
115°	119.5	119.6	119.8	119.7	119.5	119.4	119.1	119.0	119.1	119.4	119.5
117.5°	136.0	136.2	136.3	136.4	136.3	136.2	136.0	135.9	136.0	136.2	136.3
120°	147.3	147.7	147.9	147.9	147.5	147.2	146.8	146.4	146.8	147.2	147.5
122.5°	158.2	158.4	158.5	158.5	158.2	158.0	157.6	157.4	157.6	158.0	158.2
125°	174.7	174.8	174.9	174.9	174.7	174.5	174.3	174.1	174.3	174.5	174.7
127.5°	191.0	191.2	191.3	191.2	190.8	190.4	190.0	189.6	190.0	190.4	190.8
130°	201.7	201.8	202.0	201.8	201.4	200.9	200.3	199.9	200.3	200.9	201.4
132.5°	212.1	212.2	212.4	212.1	211.7	211.2	210.7	210.2	210.7	211.2	211.7
135°	227.4	227.5	227.6	227.4	227.0	226.6	226.3	225.9	226.3	226.6	227.0
137.5°	242.2	242.1	241.9	241.7	241.4	241.1	240.8	240.5	240.8	241.1	241.4
140°	252.1	252.1	252.0	251.8	251.5	251.2	250.9	250.6	250.9	251.2	251.5
142.5°	261.4	261.3	261.2	260.9	260.7	260.4	260.1	259.8	260.1	260.4	260.7
145°	275.1	274.9	274.7	274.6	274.4	274.3	274.2	274.1	274.2	274.3	274.4
147.5°	288.0	287.9	287.7	287.5	287.3	287.1	286.8	286.6	286.8	287.1	287.3
150°	296.2	296.1	296.0	295.9	295.7	295.6	295.5	295.3	295.5	295.6	295.7
152.5°	303.5	303.4	303.3	303.2	303.0	302.9	302.7	302.5	302.7	302.9	303.0
155°	313.9	313.9	313.9	313.9	313.9	313.9	313.9	313.9	313.9	313.9	313.9
157.5°	323.2	323.2	323.1	323.1	323.2	323.3	323.4	323.4	323.4	323.3	323.2
160°	328.9	328.9	328.9	329.0	329.2	329.2	329.4	329.5	329.4	329.2	329.2
162.5°	334.2	334.1	334.1	334.1	334.4	334.5	334.7	334.9	334.7	334.5	334.4
165°	341.0	341.0	341.0	341.0	341.3	341.4	341.7	341.8	341.7	341.4	341.3
167.5°	346.3	346.3	346.3	346.3	346.6	346.9	347.1	347.4	347.1	346.9	346.6
170°	349.4	349.4	349.4	349.5	349.7	350.0	350.2	350.5	350.2	350.0	349.7
172.5°	351.8	351.8	351.8	352.0	352.2	352.4	352.7	353.0	352.7	352.4	352.2
175°	354.4	354.4	354.4	354.6	354.8	355.1	355.3	355.5	355.3	355.1	354.8
177.5°	355.7	355.7	355.7	355.8	356.0	356.2	356.4	356.6	356.4	356.2	356.0
180°	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4



TEST NUMBER: P332241-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	423.7	421.8	420.5	417.6	415.7	413.6	411.5	412.8	412.6	412.6	412.6
5°	409.6	405.3	401.4	396.4	393.3	389.4	386.5	386.1	386.8	384.3	382.8
7.5°	395.5	389.7	384.1	378.7	372.8	368.1	365.3	363.8	362.0	360.4	358.8
10°	385.6	378.7	373.4	366.5	360.3	354.7	351.3	348.8	347.5	346.3	343.8
12.5°	375.3	368.7	361.9	354.1	348.2	341.7	339.1	336.4	334.0	332.5	329.2
15°	360.4	351.8	344.6	336.4	329.8	323.5	319.9	314.5	313.8	311.9	308.6
17.5°	345.5	336.1	326.1	320.1	312.7	306.1	300.5	298.7	293.4	291.4	288.5
20°	333.7	325.0	317.4	309.5	298.7	292.6	288.1	285.7	281.5	278.8	277.0
22.5°	323.5	314.7	305.9	296.7	287.7	280.8	277.6	273.9	271.6	267.9	265.9
25°	309.0	299.4	288.8	278.8	272.4	267.3	262.1	258.7	255.4	253.7	250.1
27.5°	292.1	282.0	272.2	264.6	256.7	251.6	246.9	244.0	240.0	237.2	235.1
30°	282.7	270.9	262.4	255.6	245.5	240.7	237.2	233.5	230.5	227.6	225.5
32.5°	272.0	261.2	253.2	244.7	236.9	231.6	227.1	223.9	221.3	218.6	216.5
35°	255.1	246.1	237.7	229.3	223.5	218.2	212.8	210.0	207.6	205.0	203.2
37.5°	239.8	231.3	223.4	215.4	208.3	203.9	199.6	197.5	194.2	192.5	190.7
40°	230.4	222.0	213.6	205.8	198.4	195.1	191.2	188.1	185.1	183.8	181.8
42.5°	220.0	211.7	204.5	196.2	190.1	185.6	182.0	178.6	176.4	174.5	173.4
45°	204.7	197.3	190.3	182.0	176.3	172.4	168.3	165.2	163.2	161.8	159.9
47.5°	189.8	182.4	175.3	168.1	162.6	158.1	154.0	151.9	149.2	147.6	146.2
50°	179.0	172.4	164.9	158.2	152.7	148.2	144.9	142.1	139.7	137.7	136.7
52.5°	169.1	162.1	155.5	149.3	143.5	138.5	135.5	132.5	130.7	128.4	127.3
55°	152.8	146.0	140.5	134.4	128.7	124.4	120.7	118.1	116.3	113.7	112.3
57.5°	137.5	131.3	124.8	119.5	113.6	110.0	106.9	103.5	101.2	99.2	97.7
60°	127.1	120.2	114.4	109.5	104.3	99.7	96.9	94.1	91.7	89.7	88.4
62.5°	116.4	110.3	104.8	99.4	94.7	90.6	87.5	85.2	83.0	81.8	80.4
65°	99.8	95.1	89.5	85.1	80.6	77.7	75.1	73.1	71.6	70.7	69.6
67.5°	84.6	80.0	75.2	70.8	67.8	65.6	63.9	62.2	61.4	60.2	59.5
70°	74.8	69.9	65.7	62.3	59.4	57.8	56.6	55.4	54.7	53.2	52.4
72.5°	64.0	60.5	57.4	54.7	52.4	50.9	49.4	47.8	46.7	45.0	44.3
75°	50.4	47.2	44.8	43.0	41.5	39.5	37.5	35.8	35.3	34.7	34.5
77.5°	37.3	35.3	33.6	32.0	30.2	28.8	28.3	27.9	27.8	27.5	27.5
80°	29.3	27.5	26.2	24.4	23.3	23.3	23.3	22.9	23.1	23.1	23.1
82.5°	21.8	20.1	19.4	18.8	18.5	18.7	18.7	18.8	18.6	18.9	18.8
85°	11.2	11.4	11.8	11.6	11.8	11.8	12.2	12.0	12.2	11.8	12.2
87.5°	4.7	5.3	5.5	5.9	6.2	6.2	6.4	6.5	6.7	6.7	6.7
90°	2.8	3.5	4.3	5.1	5.9	6.7	7.0	7.2	7.4	7.7	7.9
92.5°	8.5	8.9	9.3	9.8	10.3	10.8	10.9	11.2	11.3	11.6	11.6
95°	18.2	18.7	19.3	19.7	20.2	20.8	21.0	21.2	21.5	21.7	21.9
97.5°	30.7	31.0	31.4	31.7	32.1	32.4	32.7	33.0	33.3	33.6	33.7
100°	39.5	39.9	40.2	40.6	40.9	41.1	41.4	41.5	41.7	41.9	42.1
102.5°	49.0	49.4	49.7	50.2	50.6	51.0	51.2	51.4	51.6	51.7	51.8
105°	63.5	63.8	64.4	65.0	65.5	66.1	66.1	66.1	66.1	66.1	66.1
107.5°	80.6	80.6	80.9	81.1	81.4	81.6	81.8	82.0	82.1	82.4	82.5
110°	91.5	91.6	91.7	91.9	92.0	92.1	92.4	92.6	92.8	93.1	93.2



TEST NUMBER: P332241-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	102.5	102.5	102.6	102.6	102.6	102.7	102.9	103.2	103.5	103.9	103.9
115°	119.7	119.8	119.6	119.5	119.4	119.2	119.3	119.4	119.5	119.5	119.5
117.5°	136.4	136.3	136.2	136.0	135.9	135.7	135.7	135.7	135.7	135.7	135.5
120°	147.9	147.9	147.7	147.3	147.0	146.7	146.6	146.6	146.5	146.5	146.3
122.5°	158.5	158.5	158.4	158.2	158.0	157.9	157.7	157.6	157.4	157.2	157.1
125°	174.9	174.9	174.8	174.7	174.5	174.4	174.1	173.9	173.6	173.4	173.2
127.5°	191.2	191.3	191.2	191.0	190.9	190.8	190.4	190.0	189.7	189.3	189.0
130°	201.8	202.0	201.8	201.7	201.5	201.3	201.1	200.8	200.5	200.3	199.9
132.5°	212.1	212.4	212.2	212.1	211.9	211.8	211.5	211.2	210.9	210.6	210.3
135°	227.4	227.6	227.5	227.4	227.4	227.4	227.0	226.8	226.6	226.3	226.2
137.5°	241.7	241.9	242.1	242.2	242.4	242.6	242.3	242.1	241.9	241.5	241.3
140°	251.8	252.0	252.1	252.1	252.2	252.2	252.2	252.1	252.1	252.0	251.8
142.5°	260.9	261.2	261.3	261.4	261.5	261.7	261.6	261.5	261.4	261.4	261.2
145°	274.6	274.7	274.9	275.1	275.3	275.4	275.4	275.4	275.3	275.2	275.0
147.5°	287.5	287.7	287.9	288.0	288.2	288.4	288.4	288.4	288.4	288.4	288.2
150°	295.9	296.0	296.1	296.2	296.4	296.4	296.4	296.4	296.4	296.4	296.3
152.5°	303.2	303.3	303.4	303.5	303.6	303.6	303.7	303.8	304.0	304.0	303.9
155°	313.9	313.9	313.9	313.9	314.0	314.1	314.3	314.6	314.8	315.1	315.0
157.5°	323.1	323.1	323.2	323.2	323.3	323.4	323.6	323.8	324.2	324.4	324.3
160°	329.0	328.9	328.9	328.9	328.9	328.9	329.2	329.5	329.9	330.2	330.2
162.5°	334.1	334.1	334.1	334.2	334.3	334.3	334.6	334.9	335.3	335.6	335.5
165°	341.0	341.0	341.0	341.0	341.0	341.0	341.4	341.7	342.1	342.5	342.5
167.5°	346.3	346.3	346.3	346.3	346.4	346.5	346.8	347.2	347.6	348.0	348.0
170°	349.5	349.4	349.4	349.4	349.4	349.4	349.8	350.2	350.7	351.1	351.1
172.5°	352.0	351.8	351.8	351.8	351.8	351.8	352.2	352.6	353.0	353.4	353.4
175°	354.6	354.4	354.4	354.4	354.4	354.4	354.8	355.1	355.5	355.9	355.8
177.5°	355.8	355.7	355.7	355.7	355.7	355.7	356.0	356.3	356.6	356.9	356.9
180°	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4



TEST NUMBER: P332241-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	410.7	410.6	410.7	410.2	410.7	410.6	410.7	412.6	412.6	412.6	412.8
5°	382.2	382.1	381.5	379.9	381.5	382.1	382.2	382.8	384.3	386.8	386.1
7.5°	357.3	357.0	355.5	355.5	355.5	357.0	357.3	358.8	360.4	362.0	363.8
10°	342.5	342.7	340.5	339.2	340.5	342.7	342.5	343.8	346.3	347.5	348.8
12.5°	328.2	327.4	325.6	324.2	325.6	327.4	328.2	329.2	332.5	334.0	336.4
15°	309.3	307.4	303.1	303.4	303.1	307.4	309.3	308.6	311.9	313.8	314.5
17.5°	287.1	285.7	285.7	283.0	285.7	285.7	287.1	288.5	291.4	293.4	298.7
20°	274.1	273.1	273.5	270.9	273.5	273.1	274.1	277.0	278.8	281.5	285.7
22.5°	263.9	262.9	261.4	260.6	261.4	262.9	263.9	265.9	267.9	271.6	273.9
25°	249.0	247.5	246.1	246.9	246.1	247.5	249.0	250.1	253.7	255.4	258.7
27.5°	234.1	233.0	231.5	231.3	231.5	233.0	234.1	235.1	237.2	240.0	244.0
30°	224.6	223.5	222.8	221.8	222.8	223.5	224.6	225.5	227.6	230.5	233.5
32.5°	215.0	214.8	213.5	213.3	213.5	214.8	215.0	216.5	218.6	221.3	223.9
35°	202.5	201.4	201.0	201.1	201.0	201.4	202.5	203.2	205.0	207.6	210.0
37.5°	190.5	189.1	188.4	187.7	188.4	189.1	190.5	190.7	192.5	194.2	197.5
40°	182.0	180.5	180.1	179.7	180.1	180.5	182.0	181.8	183.8	185.1	188.1
42.5°	172.4	171.8	171.6	170.9	171.6	171.8	172.4	173.4	174.5	176.4	178.6
45°	159.3	159.1	158.0	158.4	158.0	159.1	159.3	159.9	161.8	163.2	165.2
47.5°	145.4	144.7	143.9	144.4	143.9	144.7	145.4	146.2	147.6	149.2	151.9
50°	136.0	135.6	134.0	134.4	134.0	135.6	136.0	136.7	137.7	139.7	142.1
52.5°	126.6	125.2	124.5	124.3	124.5	125.2	126.6	127.3	128.4	130.7	132.5
55°	110.9	109.2	108.5	108.1	108.5	109.2	110.9	112.3	113.7	116.3	118.1
57.5°	95.5	95.1	94.5	94.9	94.5	95.1	95.5	97.7	99.2	101.2	103.5
60°	86.6	86.6	86.6	86.3	86.6	86.6	86.6	88.4	89.7	91.7	94.1
62.5°	79.6	79.1	79.1	79.3	79.1	79.1	79.6	80.4	81.8	83.0	85.2
65°	69.0	68.8	68.1	67.9	68.1	68.8	69.0	69.6	70.7	71.6	73.1
67.5°	59.0	58.4	58.1	57.9	58.1	58.4	59.0	59.5	60.2	61.4	62.2
70°	51.5	51.1	50.0	50.2	50.0	51.1	51.5	52.4	53.2	54.7	55.4
72.5°	43.4	43.0	42.8	42.5	42.8	43.0	43.4	44.3	45.0	46.7	47.8
75°	34.3	34.1	34.0	34.7	34.0	34.1	34.3	34.5	34.7	35.3	35.8
77.5°	27.5	27.5	27.6	27.3	27.6	27.5	27.5	27.5	27.5	27.8	27.9
80°	23.1	23.1	22.9	22.9	22.9	23.1	23.1	23.1	23.1	23.1	22.9
82.5°	18.5	18.6	18.8	18.5	18.8	18.6	18.5	18.8	18.9	18.6	18.8
85°	12.2	12.0	12.4	12.2	12.4	12.0	12.2	12.2	11.8	12.2	12.0
87.5°	7.1	6.8	6.8	7.0	6.8	6.8	7.1	6.7	6.7	6.7	6.5
90°	8.0	8.2	8.2	8.4	8.2	8.2	8.0	7.9	7.7	7.4	7.2
92.5°	11.6	11.5	11.4	11.3	11.4	11.5	11.6	11.6	11.6	11.3	11.2
95°	21.9	21.9	21.9	21.9	21.9	21.9	21.9	21.9	21.7	21.5	21.2
97.5°	33.7	33.7	33.6	33.6	33.6	33.7	33.7	33.7	33.6	33.3	33.0
100°	42.1	42.3	42.5	42.5	42.5	42.3	42.1	42.1	41.9	41.7	41.5
102.5°	51.8	51.8	51.7	51.7	51.7	51.8	51.8	51.8	51.7	51.6	51.4
105°	66.2	66.4	66.5	66.6	66.5	66.4	66.2	66.1	66.1	66.1	66.1
107.5°	82.4	82.3	82.2	82.1	82.2	82.3	82.4	82.5	82.4	82.1	82.0
110°	93.0	92.9	92.8	92.7	92.8	92.9	93.0	93.2	93.1	92.8	92.6



TEST NUMBER: P332241-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	103.9	103.9	103.9	103.9	103.9	103.9	103.9	103.9	103.9	103.5	103.2
115°	119.5	119.4	119.3	119.2	119.3	119.4	119.5	119.5	119.5	119.5	119.4
117.5°	135.4	135.2	135.1	134.9	135.1	135.2	135.4	135.5	135.7	135.7	135.7
120°	146.2	146.1	146.0	145.8	146.0	146.1	146.2	146.3	146.5	146.5	146.6
122.5°	156.9	156.7	156.5	156.4	156.5	156.7	156.9	157.1	157.2	157.4	157.6
125°	172.9	172.7	172.4	172.1	172.4	172.7	172.9	173.2	173.4	173.6	173.9
127.5°	188.8	188.5	188.2	187.9	188.2	188.5	188.8	189.0	189.3	189.7	190.0
130°	199.6	199.1	198.7	198.2	198.7	199.1	199.6	199.9	200.3	200.5	200.8
132.5°	209.9	209.6	209.3	209.0	209.3	209.6	209.9	210.3	210.6	210.9	211.2
135°	226.0	225.9	225.8	225.6	225.8	225.9	226.0	226.2	226.3	226.6	226.8
137.5°	241.1	240.8	240.6	240.3	240.6	240.8	241.1	241.3	241.5	241.9	242.1
140°	251.3	250.9	250.4	250.0	250.4	250.9	251.3	251.8	252.0	252.1	252.1
142.5°	260.9	260.5	260.2	259.8	260.2	260.5	260.9	261.2	261.4	261.4	261.5
145°	274.8	274.6	274.3	274.1	274.3	274.6	274.8	275.0	275.2	275.3	275.4
147.5°	287.9	287.5	287.1	286.7	287.1	287.5	287.9	288.2	288.4	288.4	288.4
150°	295.9	295.6	295.2	294.8	295.2	295.6	295.9	296.3	296.4	296.4	296.4
152.5°	303.6	303.2	302.9	302.6	302.9	303.2	303.6	303.9	304.0	304.0	303.8
155°	314.6	314.1	313.7	313.2	313.7	314.1	314.6	315.0	315.1	314.8	314.6
157.5°	324.0	323.7	323.3	323.0	323.3	323.7	324.0	324.3	324.4	324.2	323.8
160°	329.9	329.7	329.5	329.2	329.5	329.7	329.9	330.2	330.2	329.9	329.5
162.5°	335.1	334.7	334.3	333.9	334.3	334.7	335.1	335.5	335.6	335.3	334.9
165°	342.0	341.6	341.1	340.7	341.1	341.6	342.0	342.5	342.5	342.1	341.7
167.5°	347.6	347.2	346.8	346.5	346.8	347.2	347.6	348.0	348.0	347.6	347.2
170°	350.7	350.2	349.8	349.4	349.8	350.2	350.7	351.1	351.1	350.7	350.2
172.5°	352.9	352.5	352.0	351.6	352.0	352.5	352.9	353.4	353.4	353.0	352.6
175°	355.5	355.0	354.6	354.1	354.6	355.0	355.5	355.8	355.9	355.5	355.1
177.5°	356.6	356.2	355.8	355.5	355.8	356.2	356.6	356.9	356.9	356.6	356.3
180°	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4



TEST NUMBER: P332241-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	411.5	413.6	415.7	417.6	420.5	421.8	423.7	424.5	426.7	429.9	432.6
5°	386.5	389.4	393.3	396.4	401.4	405.3	409.6	413.6	418.4	425.2	431.3
7.5°	365.3	368.1	372.8	378.7	384.1	389.7	395.5	401.0	407.8	417.6	427.3
10°	351.3	354.7	360.3	366.5	373.4	378.7	385.6	392.5	401.1	412.3	424.0
12.5°	339.1	341.7	348.2	354.1	361.9	368.7	375.3	383.6	393.2	405.2	419.2
15°	319.9	323.5	329.8	336.4	344.6	351.8	360.4	370.4	379.9	394.6	411.5
17.5°	300.5	306.1	312.7	320.1	326.1	336.1	345.5	355.7	367.3	382.9	401.6
20°	288.1	292.6	298.7	309.5	317.4	325.0	333.7	346.4	357.1	374.9	394.2
22.5°	277.6	280.8	287.7	296.7	305.9	314.7	323.5	335.6	348.9	365.7	386.7
25°	262.1	267.3	272.4	278.8	288.8	299.4	309.0	319.3	333.4	351.3	373.9
27.5°	246.9	251.6	256.7	264.6	272.2	282.0	292.1	303.9	318.9	337.9	360.9
30°	237.2	240.7	245.5	255.6	262.4	270.9	282.7	293.3	307.3	327.4	351.8
32.5°	227.1	231.6	236.9	244.7	253.2	261.2	272.0	283.4	297.7	317.5	342.5
35°	212.8	218.2	223.5	229.3	237.7	246.1	255.1	267.6	282.2	301.4	325.9
37.5°	199.6	203.9	208.3	215.4	223.4	231.3	239.8	252.2	265.9	286.6	309.1
40°	191.2	195.1	198.4	205.8	213.6	222.0	230.4	241.2	256.0	275.4	297.1
42.5°	182.0	185.6	190.1	196.2	204.5	211.7	220.0	230.3	244.2	263.9	283.0
45°	168.3	172.4	176.3	182.0	190.3	197.3	204.7	214.4	228.7	244.9	261.9
47.5°	154.0	158.1	162.6	168.1	175.3	182.4	189.8	198.4	211.4	227.4	238.8
50°	144.9	148.2	152.7	158.2	164.9	172.4	179.0	188.5	200.8	213.3	223.3
52.5°	135.5	138.5	143.5	149.3	155.5	162.1	169.1	177.2	188.4	200.2	208.1
55°	120.7	124.4	128.7	134.4	140.5	146.0	152.8	161.1	170.0	178.9	184.2
57.5°	106.9	110.0	113.6	119.5	124.8	131.3	137.5	143.9	152.2	158.8	162.3
60°	96.9	99.7	104.3	109.5	114.4	120.2	127.1	133.6	139.9	145.3	148.0
62.5°	87.5	90.6	94.7	99.4	104.8	110.3	116.4	121.8	127.4	132.0	133.9
65°	75.1	77.7	80.6	85.1	89.5	95.1	99.8	105.4	109.5	112.0	113.7
67.5°	63.9	65.6	67.8	70.8	75.2	80.0	84.6	89.0	92.4	94.1	95.6
70°	56.6	57.8	59.4	62.3	65.7	69.9	74.8	77.9	80.8	82.3	83.8
72.5°	49.4	50.9	52.4	54.7	57.4	60.5	64.0	67.8	69.5	71.2	72.1
75°	37.5	39.5	41.5	43.0	44.8	47.2	50.4	52.8	53.7	55.2	55.4
77.5°	28.3	28.8	30.2	32.0	33.6	35.3	37.3	39.5	39.9	40.6	41.2
80°	23.3	23.3	23.3	24.4	26.2	27.5	29.3	30.4	31.2	31.4	31.5
82.5°	18.7	18.7	18.5	18.8	19.4	20.1	21.8	23.1	23.7	23.5	23.1
85°	12.2	11.8	11.8	11.6	11.8	11.4	11.2	12.0	13.1	13.1	12.8
87.5°	6.4	6.2	6.2	5.9	5.5	5.3	4.7	4.7	4.6	5.1	4.8
90°	7.0	6.7	5.9	5.1	4.3	3.5	2.8	2.1	1.5	0.9	0.3
92.5°	10.9	10.8	10.3	9.8	9.3	8.9	8.5	8.1	7.6	7.2	6.8
95°	21.0	20.8	20.2	19.7	19.3	18.7	18.2	17.8	17.3	17.0	16.6
97.5°	32.7	32.4	32.1	31.7	31.4	31.0	30.7	30.3	30.0	29.6	29.3
100°	41.4	41.1	40.9	40.6	40.2	39.9	39.5	39.2	38.8	38.4	38.1
102.5°	51.2	51.0	50.6	50.2	49.7	49.4	49.0	48.8	48.6	48.4	48.2
105°	66.1	66.1	65.5	65.0	64.4	63.8	63.5	63.4	63.2	63.1	63.0
107.5°	81.8	81.6	81.4	81.1	80.9	80.6	80.6	80.5	80.4	80.3	80.2
110°	92.4	92.1	92.0	91.9	91.7	91.6	91.5	91.3	91.3	91.1	91.0



TEST NUMBER: P332241-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	102.9	102.7	102.6	102.6	102.6	102.5	102.5	102.4	102.3	102.3	102.2
115°	119.3	119.2	119.4	119.5	119.6	119.8	119.7	119.5	119.4	119.1	119.0
117.5°	135.7	135.7	135.9	136.0	136.2	136.3	136.4	136.3	136.2	136.0	135.9
120°	146.6	146.7	147.0	147.3	147.7	147.9	147.9	147.5	147.2	146.8	146.4
122.5°	157.7	157.9	158.0	158.2	158.4	158.5	158.5	158.2	158.0	157.6	157.4
125°	174.1	174.4	174.5	174.7	174.8	174.9	174.9	174.7	174.5	174.3	174.1
127.5°	190.4	190.8	190.9	191.0	191.2	191.3	191.2	190.8	190.4	190.0	189.6
130°	201.1	201.3	201.5	201.7	201.8	202.0	201.8	201.4	200.9	200.3	199.9
132.5°	211.5	211.8	211.9	212.1	212.2	212.4	212.1	211.7	211.2	210.7	210.2
135°	227.0	227.4	227.4	227.4	227.5	227.6	227.4	227.0	226.6	226.3	225.9
137.5°	242.3	242.6	242.4	242.2	242.1	241.9	241.7	241.4	241.1	240.8	240.5
140°	252.2	252.2	252.2	252.1	252.1	252.0	251.8	251.5	251.2	250.9	250.6
142.5°	261.6	261.7	261.5	261.4	261.3	261.2	260.9	260.7	260.4	260.1	259.8
145°	275.4	275.4	275.3	275.1	274.9	274.7	274.6	274.4	274.3	274.2	274.1
147.5°	288.4	288.4	288.2	288.0	287.9	287.7	287.5	287.3	287.1	286.8	286.6
150°	296.4	296.4	296.4	296.2	296.1	296.0	295.9	295.7	295.6	295.5	295.3
152.5°	303.7	303.6	303.6	303.5	303.4	303.3	303.2	303.0	302.9	302.7	302.5
155°	314.3	314.1	314.0	313.9	313.9	313.9	313.9	313.9	313.9	313.9	313.9
157.5°	323.6	323.4	323.3	323.2	323.2	323.1	323.1	323.2	323.3	323.4	323.4
160°	329.2	328.9	328.9	328.9	328.9	328.9	329.0	329.2	329.2	329.4	329.5
162.5°	334.6	334.3	334.3	334.2	334.1	334.1	334.1	334.4	334.5	334.7	334.9
165°	341.4	341.0	341.0	341.0	341.0	341.0	341.0	341.3	341.4	341.7	341.8
167.5°	346.8	346.5	346.4	346.3	346.3	346.3	346.3	346.6	346.9	347.1	347.4
170°	349.8	349.4	349.4	349.4	349.4	349.4	349.5	349.7	350.0	350.2	350.5
172.5°	352.2	351.8	351.8	351.8	351.8	351.8	352.0	352.2	352.4	352.7	353.0
175°	354.8	354.4	354.4	354.4	354.4	354.4	354.6	354.8	355.1	355.3	355.5
177.5°	356.0	355.7	355.7	355.7	355.7	355.7	355.8	356.0	356.2	356.4	356.6
180°	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4



TEST NUMBER: P332241-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	433.5	435.1	437.2	440.3	442.7	444.7	445.1	445.8	447.3	449.7	451.6
5°	436.3	440.5	447.3	454.0	461.2	467.1	472.7	476.6	480.2	488.0	494.2
7.5°	435.4	444.9	455.6	467.5	479.6	491.2	502.1	511.8	521.5	532.8	545.7
10°	434.8	445.9	460.3	475.6	492.4	508.8	524.7	537.1	551.4	564.4	580.8
12.5°	432.1	448.0	465.2	484.7	505.4	524.3	545.3	562.3	578.8	597.5	616.6
15°	428.3	447.7	469.5	495.5	527.0	549.8	571.2	600.9	621.2	641.5	668.8
17.5°	421.7	445.4	472.5	506.4	532.5	563.3	595.5	619.0	646.3	674.9	699.7
20°	416.4	443.9	474.4	507.6	541.0	574.3	605.5	633.6	661.9	694.9	715.2
22.5°	411.1	438.2	469.9	505.2	541.1	576.3	611.6	644.5	676.3	709.6	735.5
25°	399.7	432.1	466.4	502.4	537.8	576.6	618.6	655.4	694.7	729.0	753.6
27.5°	388.3	418.0	452.1	488.6	528.0	573.8	623.3	665.0	704.4	729.0	736.7
30°	378.0	409.3	440.8	477.8	520.5	571.6	624.2	672.0	704.3	715.0	707.0
32.5°	367.5	395.9	427.0	465.0	510.2	566.1	625.3	667.9	687.3	679.1	646.8
35°	349.0	374.6	404.7	442.8	494.8	563.1	620.5	649.3	644.5	598.3	537.4
37.5°	329.2	350.1	378.0	417.7	478.8	551.1	599.5	603.8	562.2	491.4	421.0
40°	313.5	332.4	361.0	402.5	466.4	539.3	578.5	561.3	496.9	418.0	359.3
42.5°	298.3	314.3	341.8	386.6	454.6	523.2	547.0	509.6	435.3	360.8	307.4
45°	272.6	287.6	315.2	361.2	430.4	492.4	489.3	424.3	349.9	289.9	245.7
47.5°	248.2	261.3	287.2	334.1	402.0	446.2	416.9	347.8	284.7	236.5	204.9
50°	230.9	243.8	269.7	316.0	379.3	411.5	369.7	303.1	245.3	205.4	180.3
52.5°	214.4	227.0	250.6	295.7	351.8	371.1	326.1	264.4	216.2	181.8	160.3
55°	191.2	200.8	222.0	265.2	307.1	311.6	265.9	214.3	174.6	150.6	135.9
57.5°	167.6	175.9	196.9	231.2	260.6	258.3	215.2	170.4	143.7	125.9	115.2
60°	152.3	160.4	178.9	208.3	230.5	222.8	183.1	147.1	124.2	111.1	102.6
62.5°	137.9	144.3	161.6	183.2	199.1	190.3	156.5	126.7	108.5	97.5	90.8
65°	117.2	122.4	136.2	147.5	156.3	147.8	119.8	99.1	86.0	78.3	73.7
67.5°	97.5	100.8	109.5	113.6	119.9	110.5	90.1	76.2	68.8	62.3	59.0
70°	85.1	87.5	92.1	95.5	97.0	87.5	72.3	62.2	55.9	51.3	49.3
72.5°	72.6	74.8	75.7	78.4	77.6	68.6	58.1	50.1	45.6	42.5	39.8
75°	55.5	56.5	55.5	54.4	52.0	45.8	38.6	34.5	31.2	29.7	28.8
77.5°	40.5	40.2	39.0	37.2	33.1	29.2	25.3	23.9	22.5	21.7	21.4
80°	31.2	30.4	29.3	26.5	23.1	20.3	19.4	18.5	17.9	17.0	16.8
82.5°	23.2	22.7	20.9	18.6	16.2	14.8	14.1	13.7	13.2	12.7	12.7
85°	12.4	11.8	9.7	8.5	8.2	7.8	7.6	7.6	6.8	6.7	6.7
87.5°	4.2	3.4	3.4	3.1	3.2	3.1	3.4	3.2	3.2	3.5	3.2
90°	0.9	1.5	2.1	2.8	3.5	4.3	5.1	5.9	6.7	7.0	7.2
92.5°	7.2	7.6	8.1	8.5	8.9	9.3	9.8	10.3	10.8	10.9	11.2
95°	17.0	17.3	17.8	18.2	18.7	19.3	19.7	20.2	20.8	21.0	21.2
97.5°	29.6	30.0	30.3	30.7	31.0	31.4	31.7	32.1	32.4	32.7	33.0
100°	38.4	38.8	39.2	39.5	39.9	40.2	40.6	40.9	41.1	41.4	41.5
102.5°	48.4	48.6	48.8	49.0	49.4	49.7	50.2	50.6	51.0	51.2	51.4
105°	63.1	63.2	63.4	63.5	63.8	64.4	65.0	65.5	66.1	66.1	66.1
107.5°	80.3	80.4	80.5	80.6	80.6	80.9	81.1	81.4	81.6	81.8	82.0
110°	91.1	91.3	91.3	91.5	91.6	91.7	91.9	92.0	92.1	92.4	92.6



TEST NUMBER: P332241-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	102.3	102.3	102.4	102.5	102.5	102.6	102.6	102.6	102.7	102.9	103.2
115°	119.1	119.4	119.5	119.7	119.8	119.6	119.5	119.4	119.2	119.3	119.4
117.5°	136.0	136.2	136.3	136.4	136.3	136.2	136.0	135.9	135.7	135.7	135.7
120°	146.8	147.2	147.5	147.9	147.9	147.7	147.3	147.0	146.7	146.6	146.6
122.5°	157.6	158.0	158.2	158.5	158.5	158.4	158.2	158.0	157.9	157.7	157.6
125°	174.3	174.5	174.7	174.9	174.9	174.8	174.7	174.5	174.4	174.1	173.9
127.5°	190.0	190.4	190.8	191.2	191.3	191.2	191.0	190.9	190.8	190.4	190.0
130°	200.3	200.9	201.4	201.8	202.0	201.8	201.7	201.5	201.3	201.1	200.8
132.5°	210.7	211.2	211.7	212.1	212.4	212.2	212.1	211.9	211.8	211.5	211.2
135°	226.3	226.6	227.0	227.4	227.6	227.5	227.4	227.4	227.4	227.0	226.8
137.5°	240.8	241.1	241.4	241.7	241.9	242.1	242.2	242.4	242.6	242.3	242.1
140°	250.9	251.2	251.5	251.8	252.0	252.1	252.1	252.2	252.2	252.2	252.1
142.5°	260.1	260.4	260.7	260.9	261.2	261.3	261.4	261.5	261.7	261.6	261.5
145°	274.2	274.3	274.4	274.6	274.7	274.9	275.1	275.3	275.4	275.4	275.4
147.5°	286.8	287.1	287.3	287.5	287.7	287.9	288.0	288.2	288.4	288.4	288.4
150°	295.5	295.6	295.7	295.9	296.0	296.1	296.2	296.4	296.4	296.4	296.4
152.5°	302.7	302.9	303.0	303.2	303.3	303.4	303.5	303.6	303.6	303.7	303.8
155°	313.9	313.9	313.9	313.9	313.9	313.9	313.9	314.0	314.1	314.3	314.6
157.5°	323.4	323.3	323.2	323.1	323.1	323.2	323.2	323.3	323.4	323.6	323.8
160°	329.4	329.2	329.2	329.0	328.9	328.9	328.9	328.9	328.9	329.2	329.5
162.5°	334.7	334.5	334.4	334.1	334.1	334.1	334.2	334.3	334.3	334.6	334.9
165°	341.7	341.4	341.3	341.0	341.0	341.0	341.0	341.0	341.0	341.4	341.7
167.5°	347.1	346.9	346.6	346.3	346.3	346.3	346.3	346.4	346.5	346.8	347.2
170°	350.2	350.0	349.7	349.5	349.4	349.4	349.4	349.4	349.4	349.8	350.2
172.5°	352.7	352.4	352.2	352.0	351.8	351.8	351.8	351.8	351.8	352.2	352.6
175°	355.3	355.1	354.8	354.6	354.4	354.4	354.4	354.4	354.4	354.8	355.1
177.5°	356.4	356.2	356.0	355.8	355.7	355.7	355.7	355.7	355.7	356.0	356.3
180°	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4



TEST NUMBER: P332241-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	454.8	454.8	455.3	457.6	457.9	459.8	459.2
5°	499.8	503.3	504.6	510.2	513.4	514.9	512.0
7.5°	554.8	564.7	569.4	575.3	580.4	581.9	577.9
10°	595.0	605.4	614.0	619.4	624.4	627.7	631.9
12.5°	633.8	646.6	654.8	662.3	667.5	671.7	672.4
15°	676.0	695.2	709.8	720.6	725.9	728.6	727.5
17.5°	718.6	736.4	746.8	757.7	765.1	765.5	765.7
20°	742.7	760.0	772.1	780.1	788.5	788.1	790.0
22.5°	758.8	772.5	781.6	787.5	790.4	788.9	789.3
25°	766.3	770.4	768.7	759.3	756.9	748.2	749.7
27.5°	727.5	708.3	688.4	662.9	642.7	626.6	627.4
30°	674.8	640.8	602.1	569.6	540.4	532.3	514.9
32.5°	601.1	550.2	504.8	474.4	449.5	442.7	427.5
35°	476.2	426.7	380.0	352.0	340.9	325.3	325.2
37.5°	370.1	326.5	301.9	280.8	269.8	260.4	259.5
40°	311.3	277.4	258.7	243.6	232.7	225.7	224.0
42.5°	270.3	242.9	225.4	216.0	207.6	204.0	201.3
45°	220.7	202.2	190.1	181.6	177.8	175.0	173.5
47.5°	184.7	172.3	164.0	158.3	155.2	152.3	153.0
50°	165.0	154.9	148.8	143.4	141.0	138.9	139.2
52.5°	149.2	140.1	135.1	131.3	128.3	126.8	126.2
55°	126.6	120.9	115.9	113.1	111.5	109.5	108.9
57.5°	108.0	103.5	99.5	96.4	95.9	94.0	94.3
60°	95.6	91.9	88.6	86.9	85.6	84.0	84.5
62.5°	85.4	82.3	79.3	78.0	76.6	75.4	75.7
65°	69.9	67.0	65.1	64.4	63.8	63.3	62.7
67.5°	55.8	53.9	52.8	51.2	50.1	49.9	49.4
70°	46.9	44.4	42.5	40.4	39.8	39.7	39.8
72.5°	37.5	36.0	35.5	34.5	34.4	33.9	34.2
75°	28.2	27.6	27.3	26.5	26.5	26.5	26.5
77.5°	20.8	20.5	20.3	20.1	20.0	19.6	19.6
80°	16.2	16.1	15.7	15.7	15.5	15.7	15.5
82.5°	12.3	12.2	11.9	11.9	11.6	11.6	11.6
85°	6.3	6.1	6.5	6.1	6.3	5.9	6.3
87.5°	3.2	3.3	3.2	3.2	3.1	3.4	3.2
90°	7.4	7.7	7.9	8.0	8.2	8.2	8.4
92.5°	11.3	11.6	11.6	11.6	11.5	11.4	11.3
95°	21.5	21.7	21.9	21.9	21.9	21.9	21.9
97.5°	33.3	33.6	33.7	33.7	33.7	33.6	33.6
100°	41.7	41.9	42.1	42.1	42.3	42.5	42.5
102.5°	51.6	51.7	51.8	51.8	51.8	51.7	51.7
105°	66.1	66.1	66.1	66.2	66.4	66.5	66.6
107.5°	82.1	82.4	82.5	82.4	82.3	82.2	82.1
110°	92.8	93.1	93.2	93.0	92.9	92.8	92.7



TEST NUMBER: P332241-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	103.5	103.9	103.9	103.9	103.9	103.9	103.9
115°	119.5	119.5	119.5	119.5	119.4	119.3	119.2
117.5°	135.7	135.7	135.5	135.4	135.2	135.1	134.9
120°	146.5	146.5	146.3	146.2	146.1	146.0	145.8
122.5°	157.4	157.2	157.1	156.9	156.7	156.5	156.4
125°	173.6	173.4	173.2	172.9	172.7	172.4	172.1
127.5°	189.7	189.3	189.0	188.8	188.5	188.2	187.9
130°	200.5	200.3	199.9	199.6	199.1	198.7	198.2
132.5°	210.9	210.6	210.3	209.9	209.6	209.3	209.0
135°	226.6	226.3	226.2	226.0	225.9	225.8	225.6
137.5°	241.9	241.5	241.3	241.1	240.8	240.6	240.3
140°	252.1	252.0	251.8	251.3	250.9	250.4	250.0
142.5°	261.4	261.4	261.2	260.9	260.5	260.2	259.8
145°	275.3	275.2	275.0	274.8	274.6	274.3	274.1
147.5°	288.4	288.4	288.2	287.9	287.5	287.1	286.7
150°	296.4	296.4	296.3	295.9	295.6	295.2	294.8
152.5°	304.0	304.0	303.9	303.6	303.2	302.9	302.6
155°	314.8	315.1	315.0	314.6	314.1	313.7	313.2
157.5°	324.2	324.4	324.3	324.0	323.7	323.3	323.0
160°	329.9	330.2	330.2	329.9	329.7	329.5	329.2
162.5°	335.3	335.6	335.5	335.1	334.7	334.3	333.9
165°	342.1	342.5	342.5	342.0	341.6	341.1	340.7
167.5°	347.6	348.0	348.0	347.6	347.2	346.8	346.5
170°	350.7	351.1	351.1	350.7	350.2	349.8	349.4
172.5°	353.0	353.4	353.4	352.9	352.5	352.0	351.6
175°	355.5	355.9	355.8	355.5	355.0	354.6	354.1
177.5°	356.6	356.9	356.9	356.6	356.2	355.8	355.5
180°	356.4	356.4	356.4	356.4	356.4	356.4	356.4

(END OF REPORT)