

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332243-927

Luminaire Tested: **S123RDIP-S340D365U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332243-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D365U927-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2178.2 lumens  
Efficiency: N/A  
Efficacy: 107.3 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332243-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332243-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	71	82	75	70	66	64	60	57	53	50	48	42	41	39	34
3	81	72	65	59	75	67	60	55	56	52	48	47	43	41	38	36	34	29
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	22
6	63	51	43	38	58	48	41	35	41	35	31	34	30	27	28	25	23	20
7	58	46	39	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	35	29	50	39	32	28	34	28	24	28	24	21	24	20	18	16
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	16	14
10	47	35	28	24	44	33	27	22	29	23	20	24	20	17	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4899	4899	4899
5°	4917	4850	4878
10°	4889	4790	4773
15°	4837	4677	4628
20°	4765	4537	4431
25°	4691	4380	4240
30°	4593	4197	3967
35°	4491	4016	3720
40°	4398	3801	3413
45°	4276	3589	3136
50°	4141	3349	2825
55°	4003	3076	2535
60°	3877	2781	2217
65°	3713	2463	1897
70°	3509	2068	1533
75°	3211	1626	1443
80°	2858	1444	1327
85°	2421	1272	1186



TEST NUMBER: P332243-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.7	2.0
10°-20°	118.9	5.5
20°-30°	171.2	7.9
30°-40°	192.9	8.9
40°-50°	184.5	8.5
50°-60°	151.1	6.9
60°-70°	101.9	4.7
70°-80°	51.3	2.4
80°-90°	14.6	0.7
90°-100°	13.7	0.6
100°-110°	65.3	3.0
110°-120°	156.8	7.2
120°-130°	199.7	9.2
130°-140°	213.4	9.8
140°-150°	199.5	9.2
150°-160°	160.9	7.4
160°-170°	103.9	4.8
170°-180°	35.8	1.6
0°-30°	332.9	15.3
0°-40°	525.7	24.1
0°-60°	861.4	39.5
0°-90°	1029.2	47.2
90°-120°	235.8	10.8
90°-150°	848.4	38.9
90°-180°	1149.0	52.7
0°-180°	2178.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	455	455	455	455	455	
5°	455	453	449	452	452	43
15°	434	430	420	418	415	122
25°	395	385	369	361	357	182
35°	342	328	306	290	283	214
45°	281	264	236	215	206	217
55°	213	195	164	143	135	191
65°	146	125	97	79	74	144
75°	77	59	39	36	35	82
85°	20	12	10	10	10	22
90°	0	3	7	8	8	2
95°	17	6	9	11	11	21
105°	83	85	61	15	12	88
115°	156	158	161	163	165	154
125°	221	223	224	224	225	197
135°	275	276	277	278	277	211
145°	317	319	319	320	320	198
155°	349	349	349	350	348	161
165°	368	367	367	369	367	104
175°	377	376	376	377	375	36
180°	377	377	377	377	377	



TEST NUMBER: P332243-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1
2.5°	456.6	456.3	456.1	455.8	455.6	455.0	454.2	453.4	452.7	451.9	452.6
5°	455.1	454.7	454.3	453.9	453.4	452.8	451.8	450.8	449.8	448.9	449.6
7.5°	450.9	450.4	450.0	449.6	449.2	448.3	447.0	445.8	444.4	443.1	443.5
10°	447.3	446.8	446.2	445.7	445.0	444.0	442.6	441.1	439.6	438.2	438.2
12.5°	442.4	441.7	441.1	440.5	439.8	438.6	436.7	435.0	433.2	431.3	431.3
15°	434.1	433.2	432.3	431.3	430.5	428.9	426.6	424.3	422.0	419.7	419.3
17.5°	423.7	422.6	421.6	420.5	419.5	417.5	414.5	411.6	408.8	405.8	405.0
20°	416.0	414.7	413.4	412.1	410.7	408.5	405.4	402.3	399.2	396.1	395.0
22.5°	407.4	405.9	404.4	402.9	401.4	399.0	395.7	392.4	389.0	385.7	384.4
25°	395.0	392.9	390.9	388.8	386.7	383.8	380.1	376.3	372.5	368.8	367.0
27.5°	379.9	377.6	375.3	373.0	370.7	367.6	363.4	359.1	354.9	350.7	348.3
30°	369.5	367.0	364.6	362.1	359.7	356.1	351.5	346.9	342.3	337.7	334.9
32.5°	359.2	356.3	353.6	350.8	348.0	344.2	339.3	334.5	329.6	324.7	321.7
35°	341.8	338.8	335.9	333.0	330.0	326.0	320.9	315.8	310.7	305.6	302.1
37.5°	324.2	320.9	317.7	314.4	311.1	306.7	301.3	295.9	290.5	285.0	281.1
40°	313.0	309.4	305.8	302.2	298.6	293.8	288.0	282.2	276.4	270.5	266.3
42.5°	300.3	296.7	293.1	289.5	285.9	281.1	275.0	269.0	263.0	257.0	252.3
45°	280.9	277.2	273.5	269.8	266.1	261.1	254.8	248.5	242.2	235.8	231.2
47.5°	261.5	257.5	253.3	249.3	245.3	240.1	233.8	227.4	221.2	214.8	209.8
50°	247.3	243.4	239.6	235.8	231.9	226.6	220.0	213.3	206.7	200.0	195.0
52.5°	234.6	230.4	226.2	222.0	217.9	212.5	205.9	199.3	192.7	186.2	180.9
55°	213.3	209.3	205.3	201.3	197.3	191.8	184.8	177.8	170.9	163.9	159.1
57.5°	193.7	189.3	185.0	180.5	176.2	170.5	163.5	156.5	149.5	142.5	138.0
60°	180.1	175.6	171.1	166.6	162.1	156.5	149.6	142.8	136.0	129.2	124.8
62.5°	166.5	162.0	157.5	153.0	148.5	142.8	136.0	129.2	122.4	115.6	111.5
65°	145.8	141.3	136.8	132.3	127.8	122.3	115.9	109.5	103.1	96.7	92.7
67.5°	125.1	120.5	115.9	111.4	106.8	101.5	95.3	89.2	83.0	76.9	73.9
70°	111.5	107.0	102.6	98.2	93.8	88.6	82.9	77.2	71.5	65.7	62.8
72.5°	97.9	93.6	89.2	84.8	80.4	75.7	70.4	65.2	60.0	54.7	52.4
75°	77.2	73.2	69.2	65.4	61.4	57.2	52.7	48.2	43.6	39.1	38.3
77.5°	58.2	54.7	51.1	47.5	44.0	40.8	37.9	34.9	32.1	29.2	28.8
80°	46.1	42.8	39.5	36.0	32.7	30.2	28.4	26.7	25.0	23.3	23.0
82.5°	34.6	31.7	28.8	25.9	23.0	21.2	20.4	19.6	18.8	17.9	17.7
85°	19.6	17.7	15.9	14.2	12.4	11.3	11.1	10.9	10.6	10.3	10.1
87.5°	7.1	6.6	5.9	5.4	4.8	4.5	4.7	4.8	5.0	5.1	5.1
90°	0.3	0.9	1.5	2.1	2.8	3.5	4.3	5.1	5.9	6.7	7.0
92.5°	5.2	5.1	4.8	4.7	4.5	4.8	5.3	5.9	6.6	7.1	7.5
95°	17.1	14.5	12.0	9.4	6.9	5.9	6.7	7.3	8.0	8.7	9.1
97.5°	34.3	33.2	32.0	30.9	29.7	26.9	22.4	18.0	13.5	9.0	9.5
100°	47.3	48.6	49.8	51.0	52.3	48.1	38.3	28.7	18.9	9.3	9.7
102.5°	62.1	63.0	63.8	64.8	65.7	60.8	50.2	39.6	29.0	18.5	16.9
105°	83.4	84.1	84.8	85.5	86.2	83.7	78.1	72.5	66.9	61.3	50.3
107.5°	105.9	106.5	107.0	107.6	108.1	108.8	109.7	110.6	111.5	112.3	104.3
110°	121.0	121.4	121.9	122.4	122.9	123.5	124.2	124.8	125.6	126.3	124.2



TEST NUMBER: P332243-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	135.2	135.7	136.2	136.6	137.0	137.6	138.3	139.0	139.7	140.4	140.4
115°	156.5	156.9	157.2	157.6	158.0	158.4	159.0	159.5	160.1	160.7	161.3
117.5°	177.1	177.5	177.9	178.4	178.9	179.3	179.5	179.8	180.1	180.4	180.9
120°	189.8	190.4	190.9	191.5	192.0	192.4	192.6	192.8	193.0	193.1	193.7
122.5°	202.8	203.3	203.7	204.1	204.6	204.9	205.2	205.4	205.7	205.9	206.3
125°	220.6	221.1	221.6	222.0	222.6	222.9	223.2	223.5	223.7	223.9	224.1
127.5°	237.8	238.4	238.8	239.3	239.8	240.2	240.5	240.8	241.1	241.4	241.6
130°	248.6	249.1	249.5	250.1	250.6	251.0	251.2	251.4	251.7	251.9	252.2
132.5°	258.9	259.4	259.9	260.4	260.9	261.2	261.4	261.7	261.8	262.1	262.3
135°	274.6	275.0	275.4	275.8	276.1	276.4	276.6	276.9	277.2	277.4	277.6
137.5°	288.0	288.5	289.0	289.5	289.9	290.3	290.4	290.5	290.7	290.8	291.1
140°	297.0	297.4	297.8	298.1	298.5	298.8	299.0	299.1	299.4	299.5	299.8
142.5°	305.3	305.7	306.0	306.4	306.8	307.0	307.3	307.4	307.6	307.8	308.0
145°	316.9	317.3	317.7	318.2	318.6	318.9	319.0	319.2	319.2	319.4	319.6
147.5°	327.8	328.1	328.4	328.7	328.9	329.2	329.3	329.4	329.5	329.6	329.8
150°	334.5	334.7	334.9	335.1	335.3	335.4	335.6	335.6	335.8	335.9	336.0
152.5°	340.6	340.6	340.7	340.8	340.9	341.0	341.0	341.1	341.2	341.3	341.5
155°	349.1	349.0	348.8	348.7	348.6	348.6	348.6	348.6	348.7	348.8	349.1
157.5°	355.7	355.7	355.7	355.6	355.6	355.6	355.5	355.5	355.4	355.4	355.7
160°	359.7	359.7	359.6	359.5	359.5	359.4	359.3	359.3	359.3	359.2	359.5
162.5°	363.5	363.4	363.2	363.1	362.9	362.7	362.7	362.7	362.6	362.5	362.9
165°	368.1	367.9	367.7	367.6	367.3	367.3	367.2	367.1	367.0	367.0	367.5
167.5°	371.7	371.5	371.2	371.0	370.7	370.6	370.6	370.6	370.6	370.6	371.1
170°	373.7	373.4	373.2	373.0	372.7	372.6	372.6	372.6	372.6	372.6	373.1
172.5°	375.0	374.8	374.5	374.1	373.8	373.8	373.8	373.8	373.9	373.9	374.5
175°	376.8	376.4	376.1	375.9	375.6	375.4	375.5	375.6	375.6	375.7	376.1
177.5°	377.2	377.0	376.8	376.5	376.2	376.1	376.2	376.2	376.3	376.4	376.8
180°	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8



TEST NUMBER: P332243-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1
2.5°	453.3	454.0	454.8	455.0	455.0	454.8	454.6	454.6
5°	450.4	451.1	451.8	452.1	451.9	451.8	451.6	451.5
7.5°	444.0	444.4	444.8	444.9	444.6	444.3	444.0	443.8
10°	438.3	438.4	438.5	438.3	437.9	437.5	437.0	436.7
12.5°	431.3	431.2	431.2	430.9	430.4	429.9	429.4	429.0
15°	418.8	418.4	418.0	417.6	417.0	416.4	415.8	415.3
17.5°	404.1	403.2	402.3	401.5	400.6	399.7	398.9	398.1
20°	394.0	392.8	391.8	390.8	389.8	388.8	387.9	386.8
22.5°	383.1	381.8	380.4	379.3	378.3	377.5	376.5	375.7
25°	365.3	363.6	361.9	360.5	359.7	358.8	357.8	357.0
27.5°	345.9	343.6	341.2	339.3	337.9	336.5	335.2	333.7
30°	332.2	329.4	326.6	324.6	323.2	321.9	320.6	319.2
32.5°	318.6	315.6	312.5	310.3	309.0	307.6	306.2	304.8
35°	298.6	295.0	291.5	289.0	287.6	286.1	284.6	283.1
37.5°	277.0	273.0	269.0	266.1	264.3	262.4	260.6	258.8
40°	262.1	257.8	253.5	250.4	248.5	246.7	244.8	242.9
42.5°	247.6	243.0	238.4	235.2	233.5	231.8	230.1	228.4
45°	226.5	221.8	217.1	213.8	211.9	209.9	207.9	206.0
47.5°	204.6	199.6	194.5	191.1	189.3	187.6	185.8	184.0
50°	189.9	184.8	179.7	176.3	174.4	172.5	170.6	168.7
52.5°	175.6	170.3	165.1	161.6	159.9	158.2	156.5	154.8
55°	154.4	149.6	144.9	141.6	140.1	138.4	136.7	135.1
57.5°	133.5	129.0	124.5	121.5	120.2	118.7	117.4	116.0
60°	120.3	115.9	111.5	108.5	107.2	105.8	104.4	103.0
62.5°	107.3	103.1	98.9	96.1	94.7	93.2	91.7	90.3
65°	88.6	84.7	80.6	78.2	77.2	76.4	75.5	74.5
67.5°	70.9	67.9	64.9	62.9	61.9	61.0	60.0	59.1
70°	60.0	57.1	54.2	52.4	51.4	50.5	49.6	48.7
72.5°	50.1	47.8	45.4	44.0	43.6	43.3	42.9	42.5
75°	37.5	36.7	35.8	35.3	35.2	35.0	34.9	34.7
77.5°	28.3	27.8	27.4	27.1	26.9	26.8	26.6	26.5
80°	22.7	22.5	22.3	22.1	21.9	21.7	21.5	21.4
82.5°	17.4	17.2	17.0	16.8	16.8	16.7	16.7	16.7
85°	10.0	9.8	9.7	9.6	9.6	9.6	9.6	9.6
87.5°	5.1	5.1	5.1	5.1	5.1	5.0	5.0	4.9
90°	7.2	7.4	7.7	7.9	8.0	8.2	8.2	8.4
92.5°	8.0	8.4	8.8	9.0	9.0	9.1	9.2	9.3
95°	9.6	10.0	10.5	10.6	10.6	10.6	10.6	10.6
97.5°	10.0	10.5	11.0	11.2	11.3	11.4	11.5	11.6
100°	10.2	10.7	11.2	11.5	11.6	11.6	11.7	11.7
102.5°	15.4	13.8	12.3	11.6	11.6	11.7	11.9	12.0
105°	39.3	28.3	17.3	11.8	12.0	12.0	12.2	12.3
107.5°	96.3	88.2	80.1	71.9	63.6	55.3	47.0	38.7
110°	122.2	120.1	118.0	112.6	103.7	94.7	85.9	77.0





TEST NUMBER: P332243-927

CATALOG NUMBER: S123RDIP-S340D365U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	140.5	140.5	140.5	139.6	137.7	135.9	134.0	132.1
115°	161.9	162.6	163.2	163.6	163.8	164.1	164.4	164.6
117.5°	181.4	181.9	182.4	182.7	182.7	182.8	182.8	182.8
120°	194.2	194.6	195.1	195.4	195.4	195.4	195.4	195.4
122.5°	206.6	207.0	207.3	207.5	207.6	207.6	207.6	207.7
125°	224.2	224.3	224.4	224.6	224.7	224.8	225.0	225.1
127.5°	241.8	242.0	242.2	242.2	242.1	242.0	241.9	241.8
130°	252.5	252.7	252.9	253.0	252.9	252.8	252.6	252.5
132.5°	262.5	262.8	263.0	263.1	262.8	262.7	262.5	262.4
135°	277.8	278.0	278.1	278.1	278.0	277.8	277.6	277.4
137.5°	291.4	291.7	292.0	292.1	291.9	291.8	291.7	291.6
140°	300.0	300.2	300.6	300.6	300.5	300.3	300.2	300.1
142.5°	308.2	308.4	308.6	308.6	308.5	308.2	308.1	307.9
145°	319.6	319.8	319.9	320.0	320.0	320.0	320.0	320.0
147.5°	329.9	330.0	330.2	330.1	329.8	329.5	329.2	328.9
150°	336.2	336.3	336.4	336.4	336.2	336.0	335.8	335.6
152.5°	341.7	342.0	342.2	342.1	341.9	341.6	341.3	341.0
155°	349.4	349.7	350.1	350.0	349.7	349.3	348.9	348.5
157.5°	356.1	356.5	356.9	356.8	356.3	355.8	355.3	354.8
160°	359.9	360.3	360.7	360.6	360.2	359.7	359.3	358.9
162.5°	363.4	363.8	364.2	364.2	363.8	363.5	363.1	362.7
165°	368.0	368.5	369.0	369.0	368.6	368.1	367.7	367.3
167.5°	371.5	372.1	372.6	372.6	372.1	371.5	371.1	370.6
170°	373.6	374.1	374.5	374.5	374.1	373.6	373.1	372.6
172.5°	374.9	375.4	375.9	375.9	375.3	374.8	374.2	373.7
175°	376.5	377.0	377.4	377.4	376.9	376.4	375.9	375.4
177.5°	377.2	377.6	378.0	377.9	377.4	376.9	376.4	375.9
180°	376.8	376.8	376.8	376.8	376.8	376.8	376.8	376.8

(END OF REPORT)