

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332052

Luminaire Tested: **S123DIP-S1165D365U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332052
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D365U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6004.7 lumens
Efficiency: N/A
Efficacy: 120.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332052

CATALOG NUMBER: S123DIP-S1165D365U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332052

CATALOG NUMBER: S123DIP-S1165D365U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	79
1	104	100	96	92	99	95	92	88	87	85	82	80	78	76	73	72	70	67
2	95	87	81	75	90	83	78	73	77	72	68	70	67	63	64	61	59	56
3	87	77	69	63	82	73	66	61	68	62	57	62	57	53	57	53	50	47
4	79	68	59	53	75	65	58	52	60	54	49	55	50	46	51	47	43	40
5	73	61	52	46	69	58	50	45	54	47	42	50	44	40	46	41	38	35
6	67	55	46	40	64	53	45	39	49	42	37	45	39	35	42	37	33	31
7	62	49	41	35	59	48	40	34	44	38	33	41	35	31	38	33	30	27
8	58	45	37	31	55	44	36	31	41	34	29	38	32	28	35	30	26	24
9	54	41	33	28	52	40	33	27	37	31	26	35	29	25	32	28	24	22
10	51	38	30	25	49	37	30	25	34	28	24	32	27	23	30	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19678	19678	19678
5°	19770	19498	19634
10°	19638	19329	19449
15°	19409	19110	19146
20°	19140	18798	18816
25°	18781	18427	18389
30°	18385	18013	17877
35°	17971	17578	17350
40°	17537	17096	16831
45°	17061	16653	16247
50°	16583	16109	15662
55°	15959	15546	15073
60°	15330	14889	14415
65°	14772	14174	13733
70°	13951	13357	12765
75°	12747	12289	11765
80°	11499	11009	10916
85°	10090	9707	9324



TEST NUMBER: P332052

CATALOG NUMBER: S123DIP-S1165D365U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.2	2.9
10°-20°	486.2	8.1
20°-30°	718.3	12.0
30°-40°	839.0	14.0
40°-50°	843.5	14.0
50°-60°	740.9	12.3
60°-70°	552.0	9.2
70°-80°	314.5	5.2
80°-90°	91.6	1.5
90°-100°	29.3	0.5
100°-110°	87.7	1.5
110°-120°	149.2	2.5
120°-130°	196.2	3.3
130°-140°	220.6	3.7
140°-150°	216.8	3.6
150°-160°	182.5	3.0
160°-170°	121.5	2.0
170°-180°	42.5	0.7
0°-30°	1376.7	22.9
0°-40°	2215.7	36.9
0°-60°	3800.2	63.3
0°-90°	4758.3	79.2
90°-120°	266.2	4.4
90°-150°	899.9	15.0
90°-180°	1246.0	20.8
0°-180°	6004.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1828	1828	1828	1828	1828	
5°	1830	1821	1804	1819	1817	173
15°	1742	1735	1715	1726	1718	491
25°	1581	1571	1552	1553	1548	728
35°	1368	1358	1338	1328	1320	855
45°	1121	1114	1094	1076	1067	865
55°	850	848	828	812	803	761
65°	580	572	556	544	539	572
75°	306	300	296	288	283	328
85°	82	79	79	76	76	90
90°	0	4	8	10	11	6
95°	21	23	26	28	28	23
105°	80	80	83	83	84	85
115°	150	151	150	151	150	149
125°	220	221	220	219	217	196
135°	285	287	287	286	285	220
145°	346	347	348	347	346	216
155°	396	396	396	398	395	182
165°	432	430	430	432	430	122
175°	449	448	447	449	447	43
180°	450	450	450	450	450	



TEST NUMBER: P332052

CATALOG NUMBER: S123DIP-S1165D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1
2.5°	1834.4	1833.3	1832.2	1831.1	1829.9	1827.8	1824.8	1821.7	1818.6	1815.5	1818.3
5°	1829.7	1828.0	1826.2	1824.5	1822.7	1819.9	1816.1	1812.2	1808.4	1804.5	1808.0
7.5°	1811.8	1810.0	1808.3	1806.5	1804.8	1801.9	1797.9	1794.0	1790.0	1786.0	1789.1
10°	1796.7	1794.9	1793.2	1791.4	1789.7	1786.6	1782.0	1777.5	1772.9	1768.4	1771.5
12.5°	1776.6	1775.1	1773.6	1772.2	1770.7	1767.8	1763.6	1759.3	1755.0	1750.8	1753.1
15°	1741.7	1740.3	1738.9	1737.5	1736.1	1733.1	1728.6	1724.0	1719.5	1714.9	1717.7
17.5°	1701.1	1699.3	1697.5	1695.7	1693.8	1690.7	1686.1	1681.6	1677.0	1672.5	1674.5
20°	1670.9	1668.8	1666.7	1664.6	1662.6	1659.2	1654.7	1650.2	1645.6	1641.1	1642.5
22.5°	1637.0	1634.9	1632.8	1630.7	1628.6	1625.3	1620.7	1616.2	1611.7	1607.1	1608.2
25°	1581.3	1579.2	1577.1	1575.0	1573.0	1569.6	1565.1	1560.6	1556.0	1551.5	1551.8
27.5°	1521.9	1519.9	1517.9	1515.8	1513.8	1510.4	1505.5	1500.6	1495.7	1490.8	1491.1
30°	1479.2	1477.4	1475.7	1473.9	1472.2	1468.9	1464.0	1459.1	1454.2	1449.3	1449.3
32.5°	1436.4	1434.1	1431.8	1429.5	1427.2	1424.1	1420.4	1416.6	1412.8	1409.1	1407.1
35°	1367.6	1365.5	1363.4	1361.3	1359.2	1355.9	1351.3	1346.8	1342.2	1337.7	1335.6
37.5°	1297.1	1294.5	1291.8	1289.2	1286.5	1282.9	1278.3	1273.7	1269.1	1264.4	1261.9
40°	1248.1	1246.0	1243.9	1241.8	1239.7	1236.2	1231.3	1226.4	1221.5	1216.7	1213.9
42.5°	1199.0	1196.7	1194.3	1191.9	1189.5	1185.9	1181.0	1176.1	1171.2	1166.4	1163.6
45°	1120.8	1119.4	1118.0	1116.6	1115.2	1112.2	1107.7	1103.1	1098.6	1094.0	1089.9
47.5°	1043.1	1041.1	1039.1	1037.0	1035.0	1031.9	1027.6	1023.3	1019.1	1014.8	1010.7
50°	990.3	988.6	986.8	985.1	983.3	980.2	975.6	971.1	966.5	962.0	958.2
52.5°	935.0	933.8	932.6	931.4	930.2	927.2	922.4	917.6	912.8	907.9	904.6
55°	850.4	850.1	849.7	849.4	849.0	846.6	842.0	837.5	832.9	828.4	824.6
57.5°	769.9	768.7	767.5	766.4	765.2	762.8	759.1	755.5	751.9	748.2	744.8
60°	712.1	711.7	711.4	711.0	710.7	708.4	704.2	700.0	695.8	691.6	688.5
62.5°	660.5	659.6	658.7	657.8	656.9	654.3	650.1	645.9	641.8	637.6	634.4
65°	580.0	578.3	576.5	574.8	573.0	570.4	566.9	563.4	559.9	556.5	553.7
67.5°	494.8	493.3	491.8	490.2	488.7	486.6	483.9	481.3	478.6	476.0	473.5
70°	443.3	441.2	439.1	437.0	434.9	432.8	430.7	428.6	426.5	424.4	422.0
72.5°	389.2	387.7	386.1	384.6	383.1	381.1	378.7	376.3	374.0	371.6	369.4
75°	306.5	305.1	303.7	302.3	300.9	299.7	298.7	297.6	296.6	295.5	293.8
77.5°	233.3	232.5	231.7	231.0	230.2	229.2	227.9	226.7	225.4	224.2	223.0
80°	185.5	184.4	183.4	182.3	181.3	180.4	179.7	179.0	178.3	177.6	177.3
82.5°	139.0	138.7	138.5	138.3	138.1	137.9	137.8	137.7	137.5	137.4	136.8
85°	81.7	81.0	80.3	79.6	78.9	78.6	78.6	78.6	78.6	78.6	77.9
87.5°	32.8	32.1	31.4	30.7	30.0	29.7	29.6	29.5	29.4	29.4	29.1
90°	0.4	1.1	1.9	2.7	3.5	4.4	5.4	6.4	7.5	8.5	8.8
92.5°	8.6	9.1	9.6	10.2	10.7	11.2	11.8	12.4	13.0	13.6	13.8
95°	20.9	21.4	21.9	22.5	23.0	23.6	24.3	24.9	25.5	26.2	26.5
97.5°	37.0	37.4	37.9	38.3	38.7	39.1	39.6	40.0	40.5	40.9	41.3
100°	48.1	48.5	49.0	49.5	49.9	50.4	50.8	51.2	51.6	51.9	52.2
102.5°	60.8	61.1	61.3	61.6	61.9	62.3	62.8	63.4	63.9	64.4	64.6
105°	79.5	79.7	79.8	80.0	80.1	80.6	81.3	82.0	82.7	83.4	83.4
107.5°	101.3	101.4	101.5	101.6	101.7	101.8	102.1	102.4	102.7	103.0	103.2
110°	114.9	115.0	115.2	115.3	115.5	115.6	115.8	116.0	116.1	116.3	116.6



TEST NUMBER: P332052

CATALOG NUMBER: S123DIP-S1165D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	129.0	129.1	129.2	129.3	129.4	129.4	129.5	129.5	129.5	129.6	129.9
115°	150.2	150.4	150.7	150.9	151.1	151.2	151.0	150.9	150.7	150.5	150.6
117.5°	171.5	171.7	171.9	172.0	172.2	172.1	171.9	171.7	171.5	171.3	171.3
120°	184.8	185.3	185.8	186.2	186.7	186.7	186.4	186.0	185.6	185.2	185.1
122.5°	198.7	199.0	199.4	199.7	200.1	200.1	199.9	199.7	199.5	199.3	199.1
125°	219.8	220.0	220.3	220.5	220.8	220.8	220.6	220.5	220.3	220.2	219.8
127.5°	239.3	239.8	240.3	240.8	241.3	241.5	241.3	241.1	241.0	240.8	240.4
130°	252.3	252.9	253.6	254.2	254.8	255.0	254.8	254.6	254.3	254.1	253.8
132.5°	265.3	266.0	266.6	267.2	267.8	268.1	267.9	267.7	267.5	267.4	267.0
135°	285.2	285.7	286.1	286.6	287.1	287.3	287.2	287.1	287.0	287.0	286.6
137.5°	303.6	304.0	304.3	304.7	305.1	305.4	305.6	305.8	306.0	306.2	305.9
140°	316.3	316.7	317.1	317.5	317.9	318.1	318.2	318.2	318.3	318.4	318.3
142.5°	327.9	328.3	328.7	329.1	329.4	329.7	329.9	330.0	330.1	330.3	330.2
145°	346.0	346.1	346.3	346.4	346.6	346.8	347.0	347.3	347.5	347.7	347.7
147.5°	361.8	362.1	362.4	362.7	362.9	363.2	363.4	363.6	363.8	364.1	364.1
150°	372.8	373.0	373.1	373.3	373.5	373.6	373.8	373.9	374.1	374.2	374.2
152.5°	381.9	382.1	382.3	382.5	382.8	382.9	383.0	383.1	383.2	383.3	383.4
155°	396.2	396.2	396.2	396.2	396.2	396.2	396.3	396.3	396.4	396.5	396.8
157.5°	408.3	408.2	408.1	408.0	407.9	407.9	408.0	408.0	408.1	408.2	408.5
160°	415.9	415.8	415.6	415.5	415.3	415.2	415.2	415.2	415.2	415.2	415.6
162.5°	422.7	422.5	422.3	422.1	421.8	421.8	421.8	421.9	422.0	422.0	422.4
165°	431.5	431.3	431.0	430.8	430.5	430.4	430.4	430.4	430.4	430.4	430.9
167.5°	438.5	438.2	437.9	437.5	437.2	437.1	437.2	437.2	437.3	437.4	437.8
170°	442.4	442.1	441.8	441.5	441.2	441.0	441.0	441.0	441.0	441.0	441.6
172.5°	445.6	445.2	444.9	444.6	444.3	444.1	444.1	444.1	444.1	444.1	444.6
175°	448.8	448.5	448.2	447.9	447.6	447.4	447.4	447.4	447.4	447.4	447.9
177.5°	450.1	449.9	449.6	449.4	449.1	449.0	449.0	449.0	449.0	449.0	449.4
180°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9



TEST NUMBER: P332052

CATALOG NUMBER: S123DIP-S1165D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1
2.5°	1821.1	1823.9	1826.7	1828.0	1827.7	1827.4	1827.1	1826.9
5°	1811.5	1815.0	1818.5	1819.9	1819.2	1818.5	1817.8	1817.1
7.5°	1792.3	1795.4	1798.6	1799.9	1799.5	1799.1	1798.7	1798.3
10°	1774.7	1777.8	1781.0	1782.2	1781.5	1780.8	1780.1	1779.4
12.5°	1755.4	1757.7	1760.0	1761.0	1760.5	1760.1	1759.7	1759.3
15°	1720.5	1723.3	1726.1	1726.5	1724.4	1722.3	1720.2	1718.1
17.5°	1676.4	1678.4	1680.3	1680.9	1680.2	1679.4	1678.6	1677.9
20°	1643.9	1645.3	1646.7	1646.8	1645.8	1644.7	1643.7	1642.6
22.5°	1609.4	1610.5	1611.6	1611.5	1610.2	1608.8	1607.5	1606.2
25°	1552.2	1552.5	1552.9	1552.5	1551.5	1550.4	1549.4	1548.3
27.5°	1491.4	1491.6	1491.9	1491.4	1490.1	1488.7	1487.4	1486.1
30°	1449.3	1449.3	1449.3	1448.1	1445.6	1443.2	1440.7	1438.3
32.5°	1405.1	1403.2	1401.2	1399.6	1398.3	1396.9	1395.6	1394.3
35°	1333.5	1331.4	1329.3	1327.4	1325.6	1323.9	1322.1	1320.4
37.5°	1259.4	1256.9	1254.4	1252.6	1251.4	1250.3	1249.2	1248.1
40°	1211.1	1208.3	1205.5	1203.4	1202.0	1200.6	1199.2	1197.8
42.5°	1160.8	1158.0	1155.2	1153.1	1151.7	1150.3	1148.9	1147.5
45°	1085.7	1081.5	1077.3	1074.3	1072.6	1070.8	1069.1	1067.3
47.5°	1006.6	1002.5	998.3	995.5	994.0	992.4	990.9	989.4
50°	954.3	950.5	946.6	943.7	941.6	939.5	937.4	935.3
52.5°	901.4	898.1	894.8	892.1	890.0	887.9	885.8	883.7
55°	820.7	816.9	813.0	810.2	808.5	806.7	805.0	803.2
57.5°	741.4	738.0	734.5	731.8	729.8	727.8	725.7	723.7
60°	685.4	682.2	679.1	676.6	674.9	673.1	671.4	669.6
62.5°	631.3	628.1	625.0	622.8	621.6	620.4	619.3	618.1
65°	550.9	548.1	545.3	543.4	542.3	541.3	540.2	539.2
67.5°	471.1	468.6	466.2	464.2	462.8	461.3	459.8	458.4
70°	419.5	417.1	414.6	412.5	410.8	409.0	407.3	405.6
72.5°	367.3	365.1	362.9	361.4	360.5	359.6	358.7	357.8
75°	292.0	290.3	288.5	287.1	286.1	285.0	284.0	282.9
77.5°	221.8	220.6	219.4	218.8	218.8	218.8	218.8	218.8
80°	176.9	176.6	176.2	176.1	176.1	176.1	176.1	176.1
82.5°	136.1	135.5	134.9	134.4	134.1	133.9	133.6	133.3
85°	77.2	76.5	75.8	75.5	75.5	75.5	75.5	75.5
87.5°	28.9	28.7	28.5	28.4	28.4	28.5	28.5	28.5
90°	9.1	9.4	9.7	10.0	10.1	10.3	10.4	10.6
92.5°	14.1	14.3	14.6	14.7	14.6	14.5	14.4	14.3
95°	26.8	27.1	27.4	27.6	27.6	27.6	27.6	27.6
97.5°	41.6	42.0	42.4	42.5	42.5	42.5	42.4	42.4
100°	52.4	52.7	52.9	53.1	53.2	53.4	53.6	53.7
102.5°	64.9	65.1	65.3	65.4	65.4	65.4	65.3	65.3
105°	83.4	83.4	83.4	83.5	83.6	83.8	84.0	84.1
107.5°	103.5	103.7	104.0	104.1	104.0	103.9	103.8	103.7
110°	116.9	117.2	117.5	117.6	117.4	117.3	117.1	117.0



TEST NUMBER: P332052

CATALOG NUMBER: S123DIP-S1165D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	130.3	130.7	131.1	131.2	131.2	131.2	131.1	131.1
115°	150.7	150.8	150.9	150.9	150.8	150.7	150.6	150.5
117.5°	171.3	171.3	171.3	171.1	170.9	170.7	170.5	170.3
120°	185.0	184.9	184.9	184.7	184.6	184.4	184.3	184.1
122.5°	198.9	198.7	198.5	198.3	198.1	197.8	197.6	197.4
125°	219.5	219.2	218.9	218.6	218.3	218.0	217.6	217.3
127.5°	239.9	239.5	239.0	238.6	238.3	237.9	237.6	237.2
130°	253.5	253.1	252.8	252.4	251.9	251.3	250.8	250.2
132.5°	266.6	266.2	265.9	265.5	265.0	264.6	264.2	263.8
135°	286.3	286.0	285.7	285.5	285.3	285.1	285.0	284.8
137.5°	305.6	305.3	304.9	304.6	304.3	304.0	303.7	303.4
140°	318.2	318.2	318.1	317.8	317.2	316.7	316.1	315.6
142.5°	330.1	330.0	330.0	329.7	329.3	328.9	328.4	328.0
145°	347.6	347.5	347.4	347.2	346.9	346.6	346.3	346.0
147.5°	364.1	364.1	364.1	363.8	363.4	362.9	362.4	361.9
150°	374.2	374.2	374.2	374.0	373.5	373.1	372.6	372.1
152.5°	383.5	383.7	383.8	383.6	383.2	382.8	382.4	382.0
155°	397.1	397.4	397.8	397.6	397.1	396.5	396.0	395.4
157.5°	408.8	409.2	409.5	409.4	409.0	408.6	408.1	407.7
160°	416.0	416.4	416.8	416.8	416.5	416.2	415.9	415.6
162.5°	422.8	423.2	423.6	423.5	423.0	422.5	422.0	421.5
165°	431.4	431.8	432.3	432.3	431.7	431.2	430.6	430.1
167.5°	438.3	438.8	439.3	439.3	438.8	438.3	437.8	437.4
170°	442.1	442.7	443.2	443.2	442.7	442.1	441.6	441.0
172.5°	445.1	445.6	446.1	446.1	445.5	445.0	444.4	443.9
175°	448.3	448.8	449.3	449.2	448.7	448.1	447.6	447.0
177.5°	449.8	450.1	450.5	450.5	450.1	449.6	449.2	448.7
180°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9

(END OF REPORT)