

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332249-927

Luminaire Tested: **S123RDIP-S340D585U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332249-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D585U927-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 585 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2884.4 lumens  
Efficiency: N/A  
Efficacy: 112.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332249-927

CATALOG NUMBER: S123RDIP-S340D585U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332249-927

CATALOG NUMBER: S123RDIP-S340D585U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	104	104	104	104	94	94	94	94	75	75	75		59	59	59		43	43	43	36
1	95	91	87	84	86	82	79	76	66	64	62		52	50	49		38	37	37	31
2	86	79	74	69	78	72	67	63	58	55	52		46	43	41		34	33	31	26
3	79	70	63	57	71	64	58	53	52	47	44		41	38	35		30	28	27	22
4	72	62	54	49	65	56	50	45	46	41	37		36	33	30		27	25	23	19
5	66	55	47	42	60	50	44	38	41	36	32		33	29	26		25	22	20	17
6	61	49	42	36	55	45	38	33	37	32	28		29	26	23		22	20	18	15
7	56	45	37	32	51	41	34	29	34	29	25		27	23	20		20	18	16	13
8	52	40	33	28	47	37	30	26	31	26	22		25	21	18		19	16	14	12
9	49	37	30	25	44	34	27	23	28	23	20		23	19	16		17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18		21	17	15		16	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4899	4899	4899
5°	4917	4850	4878
10°	4889	4790	4773
15°	4837	4677	4628
20°	4765	4537	4431
25°	4691	4380	4240
30°	4593	4197	3967
35°	4491	4016	3720
40°	4398	3801	3413
45°	4276	3589	3136
50°	4141	3349	2825
55°	4003	3076	2535
60°	3877	2781	2217
65°	3713	2463	1897
70°	3509	2068	1533
75°	3211	1626	1443
80°	2858	1444	1327
85°	2421	1272	1186



TEST NUMBER: P332249-927

CATALOG NUMBER: S123RDIP-S340D585U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.7	1.5
10°-20°	118.9	4.1
20°-30°	171.2	5.9
30°-40°	192.9	6.7
40°-50°	184.5	6.4
50°-60°	151.1	5.2
60°-70°	101.9	3.5
70°-80°	51.3	1.8
80°-90°	15.3	0.5
90°-100°	22.1	0.8
100°-110°	105.4	3.7
110°-120°	253.1	8.8
120°-130°	322.3	11.2
130°-140°	344.4	11.9
140°-150°	322.0	11.2
150°-160°	259.8	9.0
160°-170°	167.7	5.8
170°-180°	57.8	2.0
0°-30°	332.9	11.5
0°-40°	525.7	18.2
0°-60°	861.4	29.9
0°-90°	1029.9	35.7
90°-120°	380.6	13.2
90°-150°	1369.4	47.5
90°-180°	1855.0	64.3
0°-180°	2884.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	455	455	455	455	455	
5°	455	453	449	452	452	43
15°	434	430	420	418	415	122
25°	395	385	369	361	357	182
35°	342	328	306	290	283	214
45°	281	264	236	215	206	217
55°	213	195	164	143	135	191
65°	146	125	97	79	74	144
75°	77	59	39	36	35	82
85°	20	12	10	10	10	22
90°	0	5	11	13	14	2
95°	28	10	14	17	17	34
105°	135	137	99	24	20	143
115°	252	255	259	264	266	249
125°	356	360	362	362	363	318
135°	443	446	448	449	448	341
145°	511	515	516	516	516	320
155°	563	563	563	565	562	259
165°	594	593	592	596	593	168
175°	608	606	606	609	606	58
180°	608	608	608	608	608	



TEST NUMBER: P332249-927

CATALOG NUMBER: S123RDIP-S340D585U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1
2.5°	456.6	456.3	456.1	455.8	455.6	455.0	454.2	453.4	452.7	451.9	452.6
5°	455.1	454.7	454.3	453.9	453.4	452.8	451.8	450.8	449.8	448.9	449.6
7.5°	450.9	450.4	450.0	449.6	449.2	448.3	447.0	445.8	444.4	443.1	443.5
10°	447.3	446.8	446.2	445.7	445.0	444.0	442.6	441.1	439.6	438.2	438.2
12.5°	442.4	441.7	441.1	440.5	439.8	438.6	436.7	435.0	433.2	431.3	431.3
15°	434.1	433.2	432.3	431.3	430.5	428.9	426.6	424.3	422.0	419.7	419.3
17.5°	423.7	422.6	421.6	420.5	419.5	417.5	414.5	411.6	408.8	405.8	405.0
20°	416.0	414.7	413.4	412.1	410.7	408.5	405.4	402.3	399.2	396.1	395.0
22.5°	407.4	405.9	404.4	402.9	401.4	399.0	395.7	392.4	389.0	385.7	384.4
25°	395.0	392.9	390.9	388.8	386.7	383.8	380.1	376.3	372.5	368.8	367.0
27.5°	379.9	377.6	375.3	373.0	370.7	367.6	363.4	359.1	354.9	350.7	348.3
30°	369.5	367.0	364.6	362.1	359.7	356.1	351.5	346.9	342.3	337.7	334.9
32.5°	359.2	356.3	353.6	350.8	348.0	344.2	339.3	334.5	329.6	324.7	321.7
35°	341.8	338.8	335.9	333.0	330.0	326.0	320.9	315.8	310.7	305.6	302.1
37.5°	324.2	320.9	317.7	314.4	311.1	306.7	301.3	295.9	290.5	285.0	281.1
40°	313.0	309.4	305.8	302.2	298.6	293.8	288.0	282.2	276.4	270.5	266.3
42.5°	300.3	296.7	293.1	289.5	285.9	281.1	275.0	269.0	263.0	257.0	252.3
45°	280.9	277.2	273.5	269.8	266.1	261.1	254.8	248.5	242.2	235.8	231.2
47.5°	261.5	257.5	253.3	249.3	245.3	240.1	233.8	227.4	221.2	214.8	209.8
50°	247.3	243.4	239.6	235.8	231.9	226.6	220.0	213.3	206.7	200.0	195.0
52.5°	234.6	230.4	226.2	222.0	217.9	212.5	205.9	199.3	192.7	186.2	180.9
55°	213.3	209.3	205.3	201.3	197.3	191.8	184.8	177.8	170.9	163.9	159.1
57.5°	193.7	189.3	185.0	180.5	176.2	170.5	163.5	156.5	149.5	142.5	138.0
60°	180.1	175.6	171.1	166.6	162.1	156.5	149.6	142.8	136.0	129.2	124.8
62.5°	166.5	162.0	157.5	153.0	148.5	142.8	136.0	129.2	122.4	115.6	111.5
65°	145.8	141.3	136.8	132.3	127.8	122.3	115.9	109.5	103.1	96.7	92.7
67.5°	125.1	120.5	115.9	111.4	106.8	101.5	95.3	89.2	83.0	76.9	73.9
70°	111.5	107.0	102.6	98.2	93.8	88.6	82.9	77.2	71.5	65.7	62.8
72.5°	97.9	93.6	89.2	84.8	80.4	75.7	70.4	65.2	60.0	54.7	52.4
75°	77.2	73.2	69.2	65.4	61.4	57.2	52.7	48.2	43.6	39.1	38.3
77.5°	58.2	54.7	51.1	47.5	44.0	40.8	37.9	34.9	32.1	29.2	28.8
80°	46.1	42.8	39.5	36.0	32.7	30.2	28.4	26.7	25.0	23.3	23.0
82.5°	34.6	31.7	28.8	25.9	23.0	21.2	20.4	19.6	18.8	17.9	17.7
85°	19.6	17.7	15.9	14.2	12.4	11.3	11.1	10.9	10.6	10.3	10.1
87.5°	7.2	6.7	6.1	5.6	5.1	5.0	5.2	5.5	5.8	6.0	6.0
90°	0.5	1.4	2.5	3.5	4.4	5.6	6.9	8.2	9.5	10.9	11.2
92.5°	8.4	8.2	7.8	7.5	7.3	7.6	8.6	9.6	10.6	11.6	12.2
95°	27.6	23.4	19.3	15.2	11.1	9.6	10.7	11.8	12.9	14.0	14.7
97.5°	55.4	53.6	51.7	49.8	48.0	43.5	36.2	29.0	21.8	14.6	15.4
100°	76.4	78.3	80.4	82.4	84.4	77.6	61.9	46.3	30.6	14.9	15.7
102.5°	100.2	101.6	103.1	104.6	106.0	98.2	81.0	63.9	46.8	29.7	27.3
105°	134.7	135.8	136.9	137.9	139.0	135.1	126.0	117.0	108.0	98.9	81.2
107.5°	171.0	171.8	172.8	173.6	174.5	175.6	177.1	178.5	179.9	181.3	168.3
110°	195.2	196.0	196.8	197.6	198.4	199.4	200.4	201.5	202.6	203.7	200.4



TEST NUMBER: P332249-927

CATALOG NUMBER: S123RDIP-S340D585U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	218.3	219.0	219.8	220.5	221.2	222.1	223.2	224.3	225.5	226.6	226.6
115°	252.5	253.2	253.7	254.4	255.0	255.7	256.7	257.5	258.4	259.4	260.4
117.5°	285.7	286.5	287.2	288.0	288.7	289.3	289.8	290.3	290.7	291.1	292.0
120°	306.3	307.2	308.2	309.0	310.0	310.5	310.9	311.2	311.5	311.7	312.6
122.5°	327.3	328.0	328.8	329.5	330.3	330.8	331.2	331.6	332.0	332.4	333.0
125°	356.0	356.9	357.7	358.5	359.3	359.9	360.3	360.7	361.1	361.5	361.6
127.5°	383.9	384.7	385.5	386.3	387.1	387.7	388.2	388.7	389.2	389.7	390.0
130°	401.2	402.0	402.8	403.6	404.4	405.0	405.4	405.8	406.2	406.6	407.0
132.5°	417.9	418.7	419.5	420.3	421.0	421.6	421.9	422.2	422.6	422.9	423.3
135°	443.2	443.9	444.4	445.0	445.7	446.2	446.6	446.9	447.3	447.7	448.1
137.5°	464.9	465.7	466.4	467.2	467.9	468.5	468.7	468.9	469.1	469.4	469.8
140°	479.3	480.0	480.6	481.2	481.8	482.3	482.5	482.8	483.2	483.5	483.9
142.5°	492.7	493.4	494.0	494.6	495.2	495.6	495.9	496.2	496.5	496.9	497.2
145°	511.4	512.1	512.9	513.6	514.3	514.8	514.9	515.2	515.3	515.6	515.7
147.5°	529.1	529.6	530.0	530.4	530.9	531.2	531.5	531.6	531.9	532.1	532.3
150°	540.0	540.3	540.5	540.8	541.1	541.4	541.6	541.8	542.0	542.2	542.4
152.5°	549.7	549.9	549.9	550.1	550.2	550.4	550.5	550.6	550.7	550.9	551.2
155°	563.4	563.2	563.0	562.8	562.6	562.6	562.7	562.8	562.8	563.0	563.5
157.5°	574.1	574.1	574.0	574.0	574.0	573.9	573.9	573.8	573.6	573.5	574.2
160°	580.6	580.5	580.4	580.3	580.2	580.1	580.0	579.9	579.8	579.7	580.3
162.5°	586.8	586.5	586.2	586.0	585.7	585.5	585.4	585.3	585.2	585.1	585.8
165°	594.1	593.8	593.6	593.3	592.9	592.7	592.6	592.6	592.5	592.3	593.2
167.5°	599.9	599.5	599.1	598.7	598.3	598.1	598.1	598.1	598.1	598.1	599.0
170°	603.2	602.8	602.4	602.0	601.6	601.3	601.3	601.3	601.3	601.3	602.2
172.5°	605.4	604.9	604.4	603.9	603.4	603.2	603.3	603.4	603.5	603.6	604.4
175°	608.2	607.7	607.1	606.7	606.2	605.9	606.0	606.2	606.3	606.3	607.0
177.5°	608.9	608.5	608.1	607.7	607.3	607.1	607.2	607.3	607.4	607.4	608.1
180°	608.2	608.2	608.2	608.2	608.2	608.2	608.2	608.2	608.2	608.2	608.2



TEST NUMBER: P332249-927

CATALOG NUMBER: S123RDIP-S340D585U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1
2.5°	453.3	454.0	454.8	455.0	455.0	454.8	454.6	454.6
5°	450.4	451.1	451.8	452.1	451.9	451.8	451.6	451.5
7.5°	444.0	444.4	444.8	444.9	444.6	444.3	444.0	443.8
10°	438.3	438.4	438.5	438.3	437.9	437.5	437.0	436.7
12.5°	431.3	431.2	431.2	430.9	430.4	429.9	429.4	429.0
15°	418.8	418.4	418.0	417.6	417.0	416.4	415.8	415.3
17.5°	404.1	403.2	402.3	401.5	400.6	399.7	398.9	398.1
20°	394.0	392.8	391.8	390.8	389.8	388.8	387.9	386.8
22.5°	383.1	381.8	380.4	379.3	378.3	377.5	376.5	375.7
25°	365.3	363.6	361.9	360.5	359.7	358.8	357.8	357.0
27.5°	345.9	343.6	341.2	339.3	337.9	336.5	335.2	333.7
30°	332.2	329.4	326.6	324.6	323.2	321.9	320.6	319.2
32.5°	318.6	315.6	312.5	310.3	309.0	307.6	306.2	304.8
35°	298.6	295.0	291.5	289.0	287.6	286.1	284.6	283.1
37.5°	277.0	273.0	269.0	266.1	264.3	262.4	260.6	258.8
40°	262.1	257.8	253.5	250.4	248.5	246.7	244.8	242.9
42.5°	247.6	243.0	238.4	235.2	233.5	231.8	230.1	228.4
45°	226.5	221.8	217.1	213.8	211.9	209.9	207.9	206.0
47.5°	204.6	199.6	194.5	191.1	189.3	187.6	185.8	184.0
50°	189.9	184.8	179.7	176.3	174.4	172.5	170.6	168.7
52.5°	175.6	170.3	165.1	161.6	159.9	158.2	156.5	154.8
55°	154.4	149.6	144.9	141.6	140.1	138.4	136.7	135.1
57.5°	133.5	129.0	124.5	121.5	120.2	118.7	117.4	116.0
60°	120.3	115.9	111.5	108.5	107.2	105.8	104.4	103.0
62.5°	107.3	103.1	98.9	96.1	94.7	93.2	91.7	90.3
65°	88.6	84.7	80.6	78.2	77.2	76.4	75.5	74.5
67.5°	70.9	67.9	64.9	62.9	61.9	61.0	60.0	59.1
70°	60.0	57.1	54.2	52.4	51.4	50.5	49.6	48.7
72.5°	50.1	47.8	45.4	44.0	43.6	43.3	42.9	42.5
75°	37.5	36.7	35.8	35.3	35.2	35.0	34.9	34.7
77.5°	28.3	27.8	27.4	27.1	26.9	26.8	26.6	26.5
80°	22.7	22.5	22.3	22.1	21.9	21.7	21.5	21.4
82.5°	17.4	17.2	17.0	16.8	16.8	16.7	16.7	16.7
85°	10.0	9.8	9.7	9.6	9.6	9.6	9.6	9.6
87.5°	6.0	6.0	6.1	6.1	6.0	6.0	6.0	5.9
90°	11.6	12.0	12.4	12.8	13.0	13.2	13.4	13.5
92.5°	12.8	13.5	14.1	14.5	14.7	14.7	14.9	15.0
95°	15.4	16.1	16.8	17.2	17.2	17.2	17.2	17.2
97.5°	16.2	17.0	17.7	18.2	18.3	18.4	18.5	18.6
100°	16.5	17.3	18.1	18.5	18.7	18.8	18.9	19.0
102.5°	24.7	22.3	19.8	18.6	18.8	19.0	19.2	19.3
105°	63.4	45.6	27.9	19.1	19.3	19.5	19.6	19.9
107.5°	155.3	142.3	129.2	116.1	102.6	89.2	75.8	62.4
110°	197.2	193.8	190.5	181.6	167.3	153.0	138.6	124.2





TEST NUMBER: P332249-927

CATALOG NUMBER: S123RDIP-S340D585U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	226.6	226.7	226.8	225.3	222.3	219.2	216.2	213.2
115°	261.3	262.4	263.4	264.0	264.4	264.9	265.3	265.7
117.5°	292.8	293.6	294.4	294.9	294.9	295.0	295.1	295.2
120°	313.4	314.2	315.0	315.4	315.4	315.4	315.4	315.4
122.5°	333.5	334.1	334.6	334.9	335.0	335.1	335.2	335.3
125°	361.9	362.0	362.3	362.5	362.7	362.9	363.1	363.3
127.5°	390.3	390.6	390.9	391.0	390.8	390.6	390.4	390.2
130°	407.4	407.8	408.2	408.4	408.1	408.0	407.7	407.6
132.5°	423.7	424.1	424.5	424.6	424.3	424.0	423.7	423.4
135°	448.4	448.7	448.9	448.9	448.7	448.4	448.1	447.7
137.5°	470.3	470.8	471.3	471.4	471.2	471.0	470.8	470.6
140°	484.3	484.7	485.1	485.1	485.0	484.7	484.6	484.3
142.5°	497.5	497.8	498.1	498.1	497.9	497.6	497.3	497.0
145°	515.9	516.1	516.3	516.4	516.4	516.4	516.4	516.4
147.5°	532.5	532.7	532.9	532.7	532.3	531.8	531.4	530.9
150°	542.6	542.8	543.0	543.0	542.6	542.3	542.0	541.8
152.5°	551.6	551.9	552.3	552.2	551.8	551.4	550.9	550.4
155°	564.0	564.5	565.0	564.9	564.4	563.7	563.2	562.5
157.5°	574.7	575.4	576.0	575.8	575.0	574.3	573.5	572.7
160°	580.9	581.5	582.1	582.0	581.4	580.7	580.0	579.2
162.5°	586.5	587.2	587.9	587.9	587.2	586.6	586.0	585.4
165°	594.0	594.8	595.6	595.6	594.9	594.2	593.5	592.8
167.5°	599.8	600.6	601.3	601.3	600.6	599.8	599.0	598.1
170°	603.0	603.8	604.6	604.6	603.8	603.0	602.2	601.3
172.5°	605.1	605.9	606.7	606.7	605.9	605.0	604.0	603.2
175°	607.8	608.5	609.2	609.1	608.3	607.5	606.7	605.9
177.5°	608.7	609.3	610.0	609.9	609.1	608.3	607.5	606.7
180°	608.2	608.2	608.2	608.2	608.2	608.2	608.2	608.2

(END OF REPORT)