

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332054

Luminaire Tested: **S123DIP-S1165D585U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332054  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1165D585U835-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 585 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7239.2 lumens  
Efficiency: N/A  
Efficacy: 131.4 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332054

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332054

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	68
1	102	98	94	90	96	92	89	86	82	80	77	73	71	69	65	63	62	58
2	93	86	80	75	88	81	76	71	73	68	65	65	61	59	57	55	53	49
3	85	76	68	63	80	72	65	60	64	59	55	57	53	50	51	48	45	42
4	78	67	59	53	74	64	57	51	57	52	47	51	47	43	46	42	39	36
5	72	60	52	46	68	57	50	44	52	45	41	46	41	38	41	37	34	32
6	66	54	46	40	63	52	44	39	47	40	36	42	37	33	38	34	30	28
7	62	49	41	35	58	47	39	34	42	36	32	38	33	29	34	30	27	25
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	32	27	24	22
9	53	41	33	28	50	39	32	27	36	30	25	32	27	24	29	25	22	20
10	50	38	30	25	47	36	29	25	33	27	23	30	25	21	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	17460	17460	17460	17460
5°	20822	17535	15540	17535
10°	26063	17446	14036	17446
15°	31967	17306	13067	17306
20°	38080	17087	12441	17087
25°	40435	16820	12302	16820
30°	34657	16625	12367	16625
35°	24103	16348	12496	16348
40°	18156	16024	12456	16024
45°	15075	15541	12298	15541
50°	13504	14555	12188	14555
55°	12624	13495	12035	13495
60°	11842	12385	11911	12385
65°	11130	11291	11530	11291
70°	10439	10043	10980	10043
75°	9349	8792	10069	8792
80°	8182	7209	8672	7209
85°	6410	5236	5829	5236



TEST NUMBER: P332054

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	159.8	2.2
10°-20°	512.4	7.1
20°-30°	859.9	11.9
30°-40°	973.7	13.5
40°-50°	873.2	12.1
50°-60°	704.7	9.7
60°-70°	491.0	6.8
70°-80°	258.1	3.6
80°-90°	65.3	0.9
90°-100°	27.9	0.4
100°-110°	133.0	1.8
110°-120°	319.5	4.4
120°-130°	406.9	5.6
130°-140°	434.7	6.0
140°-150°	406.5	5.6
150°-160°	327.9	4.5
160°-170°	211.6	2.9
170°-180°	72.9	1.0
0°-30°	1532.1	21.2
0°-40°	2505.8	34.6
0°-60°	4083.7	56.4
0°-90°	4898.1	67.7
90°-120°	480.5	6.6
90°-150°	1728.6	23.9
90°-180°	2341.0	32.3
0°-180°	7239.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1622	1622	1622	1622	1622	
5°	1927	1623	1438	1623	1927	200
15°	2869	1553	1173	1553	2869	828
25°	3405	1416	1036	1416	3405	1493
35°	1834	1244	951	1244	1834	1192
45°	990	1021	808	1021	990	784
55°	673	719	641	719	673	604
65°	437	443	453	443	437	435
75°	225	211	242	211	225	241
85°	52	42	47	42	52	62
90°	17	1	17	1	17	10
95°	22	35	22	35	22	18
105°	25	170	25	170	25	57
115°	335	319	335	319	335	310
125°	459	449	459	449	459	410
135°	565	560	565	560	565	436
145°	652	646	652	646	652	407
155°	710	711	710	711	710	327
165°	748	750	748	750	748	211
175°	765	768	765	768	765	73
180°	768	768	768	768	768	



TEST NUMBER: P332054

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1721.5	1720.2	1717.1	1719.6	1714.6	1707.6	1707.0	1700.7	1682.5	1681.2	1676.2
5°	1927.1	1920.8	1920.0	1919.2	1908.2	1893.3	1865.0	1862.6	1824.9	1806.0	1783.3
7.5°	2193.3	2196.6	2185.2	2175.1	2141.5	2119.3	2089.0	2050.2	2003.8	1956.8	1925.5
10°	2384.5	2410.4	2378.2	2356.2	2335.8	2297.2	2252.5	2196.6	2140.8	2075.6	2026.1
12.5°	2589.5	2602.2	2595.7	2575.0	2543.2	2484.6	2405.2	2343.8	2292.4	2183.8	2139.9
15°	2868.6	2916.6	2885.9	2815.2	2816.7	2760.9	2657.2	2543.2	2482.7	2387.6	2258.0
17.5°	3166.0	3172.0	3158.9	3100.0	3060.7	2984.0	2888.3	2779.0	2656.4	2541.4	2403.8
20°	3324.4	3319.7	3292.2	3261.6	3194.0	3134.3	3029.7	2907.9	2750.7	2637.6	2487.4
22.5°	3412.5	3404.6	3391.6	3365.9	3309.7	3245.5	3151.7	3018.6	2868.9	2713.0	2539.6
25°	3404.6	3414.8	3416.4	3409.3	3389.7	3351.2	3277.3	3171.2	3021.9	2821.5	2640.7
27.5°	3096.5	3111.0	3153.0	3190.2	3231.9	3274.3	3268.6	3216.0	3105.5	2932.4	2711.4
30°	2788.4	2757.0	2834.8	2933.1	2999.9	3117.7	3183.8	3187.7	3125.6	2977.1	2761.7
32.5°	2360.9	2395.5	2429.9	2550.8	2696.8	2829.2	2960.6	3066.4	3078.5	2979.6	2791.3
35°	1834.3	1877.6	1940.4	2003.3	2160.5	2295.7	2526.7	2727.9	2888.3	2909.5	2793.9
37.5°	1478.2	1499.5	1539.3	1602.3	1705.1	1865.5	2044.2	2298.5	2530.8	2703.6	2711.1
40°	1292.1	1298.3	1343.1	1391.1	1474.4	1606.4	1767.5	1992.3	2270.5	2511.8	2612.4
42.5°	1152.5	1166.3	1185.3	1231.4	1297.7	1397.1	1546.9	1732.6	1987.6	2265.3	2462.1
45°	990.3	1006.0	1017.8	1048.4	1095.6	1162.4	1266.9	1436.7	1630.8	1917.6	2182.5
47.5°	883.1	884.3	893.1	916.2	948.3	998.4	1072.3	1181.4	1359.6	1592.3	1864.2
50°	806.4	818.9	822.1	840.1	865.3	902.2	963.5	1056.3	1202.5	1406.8	1656.7
52.5°	752.3	756.1	764.9	777.9	799.9	828.7	881.8	954.4	1069.2	1243.3	1473.1
55°	672.7	672.7	681.4	691.6	704.2	730.1	765.5	818.9	906.2	1041.3	1231.5
57.5°	599.2	603.1	609.2	612.4	623.1	640.2	669.8	710.3	775.4	879.4	1030.7
60°	550.1	557.2	556.4	562.7	572.2	585.5	610.7	643.7	701.8	785.1	912.5
62.5°	507.4	506.9	506.8	514.3	523.7	536.5	552.8	581.4	630.8	704.7	813.1
65°	437.0	435.4	440.9	445.6	448.8	458.2	470.8	495.9	528.9	583.9	668.0
67.5°	374.4	369.9	372.8	374.4	379.8	387.1	398.9	414.5	440.7	484.9	548.3
70°	331.7	327.7	326.9	328.5	333.2	338.7	347.4	362.3	386.7	422.0	468.4
72.5°	287.6	285.0	284.8	288.3	290.5	294.1	300.2	313.9	333.2	359.8	403.0
75°	224.8	224.8	224.8	225.6	227.9	231.1	235.8	242.8	257.8	276.6	305.7
77.5°	168.5	168.3	167.4	167.2	170.7	172.1	173.2	179.8	188.1	200.9	222.1
80°	132.0	128.1	129.7	132.0	133.6	134.4	136.8	138.3	145.4	152.5	167.4
82.5°	98.1	94.8	95.1	98.7	99.0	99.8	102.2	104.4	107.0	113.5	121.5
85°	51.9	51.9	52.7	52.7	53.4	52.7	55.0	55.8	55.8	59.7	64.4
87.5°	22.3	21.0	21.6	22.1	21.5	22.0	22.5	23.1	23.6	24.1	24.4
90°	17.1	16.9	16.6	16.4	16.1	15.7	15.2	14.7	14.2	13.7	12.0
92.5°	18.9	18.8	18.6	18.5	18.3	17.8	17.0	16.2	15.4	14.6	13.4
95°	21.7	21.7	21.7	21.7	21.7	21.2	20.3	19.5	18.6	17.7	16.3
97.5°	23.5	23.4	23.2	23.1	23.0	22.4	21.4	20.4	19.4	18.4	27.5
100°	24.0	23.8	23.7	23.6	23.4	22.9	21.9	20.8	19.8	18.8	38.6
102.5°	24.4	24.2	24.0	23.7	23.5	25.0	28.1	31.2	34.4	37.5	59.1
105°	25.1	24.8	24.6	24.3	24.1	35.2	57.6	80.0	102.5	124.9	136.3
107.5°	78.8	95.7	112.6	129.5	146.5	163.1	179.6	196.0	212.5	228.9	227.1
110°	156.8	175.0	193.1	211.2	229.3	240.5	244.7	248.9	253.0	257.2	255.8



TEST NUMBER: P332054

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	269.1	272.9	276.7	280.6	284.4	286.3	286.2	286.1	286.1	286.0	284.6
115°	335.4	334.9	334.4	333.8	333.3	332.5	331.2	329.9	328.7	327.4	326.2
117.5°	372.6	372.5	372.4	372.3	372.2	371.6	370.6	369.6	368.6	367.5	367.0
120°	398.1	398.1	398.1	398.1	398.1	397.6	396.6	395.6	394.6	393.5	393.2
122.5°	423.2	423.1	423.0	422.9	422.8	422.4	421.7	421.0	420.3	419.6	419.1
125°	458.6	458.3	458.1	457.8	457.6	457.3	457.0	456.8	456.5	456.3	455.8
127.5°	492.6	492.8	493.1	493.3	493.6	493.5	493.1	492.7	492.3	491.9	491.3
130°	514.5	514.7	515.0	515.2	515.5	515.3	514.8	514.3	513.8	513.3	512.8
132.5°	534.5	534.9	535.2	535.6	536.0	535.9	535.4	534.9	534.4	533.9	533.4
135°	565.2	565.6	566.0	566.4	566.7	566.7	566.4	566.0	565.6	565.2	564.7
137.5°	594.1	594.3	594.6	594.8	595.1	594.9	594.3	593.7	593.1	592.5	592.2
140°	611.4	611.7	611.9	612.2	612.4	612.3	611.8	611.3	610.8	610.3	609.9
142.5°	627.4	627.7	628.1	628.5	628.8	628.8	628.4	628.0	627.6	627.2	626.8
145°	651.9	651.9	651.9	651.9	651.9	651.8	651.5	651.3	651.0	650.8	650.5
147.5°	670.2	670.8	671.3	671.9	672.5	672.7	672.4	672.2	671.9	671.7	671.4
150°	683.9	684.2	684.6	685.0	685.4	685.4	685.2	684.9	684.7	684.4	684.2
152.5°	694.8	695.4	696.0	696.6	697.1	697.2	696.7	696.3	695.8	695.4	695.2
155°	710.1	710.9	711.6	712.4	713.1	713.2	712.6	711.9	711.3	710.7	710.5
157.5°	723.0	724.0	725.0	725.9	726.9	727.1	726.3	725.5	724.8	724.0	724.1
160°	731.2	732.1	733.0	733.9	734.7	734.8	734.0	733.3	732.5	731.8	731.9
162.5°	739.0	739.7	740.5	741.3	742.1	742.1	741.2	740.3	739.5	738.6	738.7
165°	748.3	749.2	750.1	751.0	751.9	751.8	750.8	749.8	748.8	747.7	747.9
167.5°	755.0	756.1	757.1	758.1	759.1	759.1	758.1	757.1	756.1	755.0	755.0
170°	759.1	760.2	761.2	762.2	763.2	763.2	762.2	761.2	760.2	759.1	759.1
172.5°	761.4	762.5	763.7	764.8	765.9	765.9	764.9	763.9	762.9	761.9	761.8
175°	764.8	765.9	766.9	767.9	768.9	769.0	768.1	767.2	766.3	765.4	765.3
177.5°	765.9	766.9	767.9	768.9	769.9	770.0	769.2	768.4	767.6	766.8	766.7
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P332054

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1672.4	1667.4	1662.4	1653.6	1646.0	1635.3	1632.2	1628.4	1617.1	1607.1	1599.5
5°	1774.6	1755.7	1728.2	1703.1	1682.7	1655.2	1639.4	1622.9	1599.3	1578.1	1560.8
7.5°	1881.5	1844.4	1801.6	1755.4	1712.4	1670.9	1637.4	1607.5	1574.5	1543.2	1518.9
10°	1966.4	1912.9	1853.2	1788.8	1733.7	1680.3	1635.5	1596.2	1553.8	1516.8	1486.2
12.5°	2063.2	1984.0	1901.6	1823.3	1758.3	1684.1	1629.8	1579.9	1531.8	1487.3	1452.9
15°	2177.8	2077.2	1979.7	1872.1	1773.0	1680.3	1615.9	1553.0	1497.2	1451.6	1407.6
17.5°	2282.2	2168.2	2039.8	1908.8	1789.4	1679.4	1589.1	1518.1	1448.3	1392.5	1348.6
20°	2341.3	2211.6	2066.2	1930.2	1798.2	1675.6	1576.6	1491.7	1416.2	1357.3	1307.8
22.5°	2392.2	2240.5	2090.1	1944.7	1797.6	1665.5	1553.3	1465.9	1384.2	1326.5	1273.8
25°	2445.0	2263.5	2112.6	1942.0	1777.8	1641.0	1515.3	1416.2	1334.5	1266.9	1212.7
27.5°	2490.3	2261.9	2082.8	1899.4	1746.6	1609.6	1475.3	1369.1	1282.3	1208.9	1153.9
30°	2520.4	2265.0	2052.0	1870.5	1716.5	1575.0	1444.5	1337.6	1246.5	1171.8	1119.9
32.5°	2539.3	2263.1	2023.7	1830.3	1668.7	1543.5	1411.2	1300.5	1206.9	1133.5	1083.5
35°	2550.3	2249.3	1975.0	1747.1	1591.5	1469.7	1358.9	1244.1	1145.9	1077.5	1020.9
37.5°	2528.3	2220.2	1918.4	1666.9	1496.6	1376.6	1283.4	1185.6	1091.6	1016.4	967.6
40°	2493.7	2201.4	1874.4	1610.4	1431.2	1315.6	1236.3	1140.4	1047.6	976.1	930.5
42.5°	2427.7	2163.0	1826.0	1547.5	1363.3	1247.7	1174.6	1094.5	1006.8	939.6	894.1
45°	2266.6	2079.5	1753.4	1453.2	1263.0	1143.5	1079.1	1020.9	941.5	876.3	837.0
47.5°	2043.1	1954.0	1648.4	1353.7	1158.3	1043.4	976.4	929.6	871.6	818.9	781.2
50°	1887.8	1850.8	1577.3	1285.8	1088.5	976.1	911.7	869.2	827.6	774.9	740.3
52.5°	1708.6	1731.4	1494.4	1215.3	1017.5	907.0	846.3	812.6	774.8	731.5	701.4
55°	1456.3	1538.8	1351.0	1097.1	911.7	806.4	749.0	719.1	697.1	664.9	639.0
57.5°	1220.1	1325.1	1196.0	975.3	807.8	716.9	661.9	629.4	615.2	598.4	578.0
60°	1079.9	1183.6	1085.4	893.6	738.0	651.5	602.8	575.3	561.1	549.4	532.1
62.5°	954.7	1059.7	977.2	810.6	669.4	589.3	546.8	520.0	509.0	502.8	488.1
65°	782.8	873.2	818.1	681.4	571.4	500.6	462.1	443.3	433.0	430.7	421.3
67.5°	637.1	705.9	665.8	565.2	478.6	417.5	384.8	368.8	360.9	360.1	353.0
70°	541.5	605.9	575.3	484.1	409.5	361.5	333.2	319.1	314.4	313.6	309.7
72.5°	467.3	512.3	487.9	411.8	354.1	310.6	289.8	275.1	269.7	270.8	268.2
75°	345.8	379.6	365.5	312.8	266.4	238.1	220.8	211.4	206.7	209.1	205.9
77.5°	248.8	270.2	257.5	221.0	192.4	172.0	159.2	153.4	149.2	149.0	147.6
80°	187.8	200.4	193.3	171.3	147.8	130.5	120.2	116.3	114.0	113.2	112.4
82.5°	133.8	144.5	136.1	121.0	105.0	94.6	88.8	83.6	81.9	82.4	81.6
85°	67.6	71.5	68.4	58.9	52.7	47.9	44.8	42.4	40.9	41.7	40.1
87.5°	25.3	25.6	23.4	20.6	19.1	17.0	16.7	15.2	14.2	14.5	14.1
90°	10.4	8.7	7.1	5.6	4.4	3.1	1.8	0.6	1.8	3.1	4.4
92.5°	12.1	10.9	9.6	9.2	9.5	9.9	10.3	10.6	10.3	9.9	9.5
95°	14.9	13.5	12.1	14.0	19.2	24.4	29.6	34.8	29.6	24.4	19.2
97.5°	36.6	45.7	54.9	60.6	62.9	65.3	67.6	69.9	67.6	65.3	62.9
100°	58.4	78.1	97.9	106.5	104.0	101.5	98.9	96.4	98.9	101.5	104.0
102.5°	80.7	102.3	123.9	133.8	132.0	130.2	128.3	126.5	128.3	130.2	132.0
105°	147.7	159.1	170.5	175.5	174.1	172.8	171.4	170.0	171.4	172.8	174.1
107.5°	225.3	223.5	221.7	220.3	219.2	218.1	216.9	215.8	216.9	218.1	219.2
110°	254.4	253.0	251.7	250.4	249.4	248.4	247.4	246.4	247.4	248.4	249.4





TEST NUMBER: P332054

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	283.2	281.8	280.4	279.2	278.3	277.4	276.5	275.6	276.5	277.4	278.3
115°	325.1	324.0	322.8	321.9	321.1	320.3	319.6	318.8	319.6	320.3	321.1
117.5°	366.4	365.8	365.2	364.4	363.5	362.6	361.6	360.7	361.6	362.6	363.5
120°	392.8	392.4	392.0	391.3	390.1	389.0	387.8	386.7	387.8	389.0	390.1
122.5°	418.6	418.1	417.6	416.9	416.0	415.0	414.1	413.2	414.1	415.0	416.0
125°	455.3	454.8	454.3	453.5	452.5	451.5	450.5	449.4	450.5	451.5	452.5
127.5°	490.7	490.0	489.4	488.6	487.6	486.6	485.6	484.6	485.6	486.6	487.6
130°	512.3	511.8	511.3	510.5	509.5	508.5	507.5	506.5	507.5	508.5	509.5
132.5°	533.0	532.6	532.2	531.5	530.5	529.5	528.5	527.5	528.5	529.5	530.5
135°	564.2	563.7	563.2	562.6	561.8	561.0	560.3	559.5	560.3	561.0	561.8
137.5°	591.9	591.6	591.4	590.7	589.8	588.8	587.9	586.9	587.9	588.8	589.8
140°	609.5	609.1	608.8	608.2	607.4	606.7	605.9	605.1	605.9	606.7	607.4
142.5°	626.4	626.0	625.6	625.1	624.3	623.6	622.8	622.0	622.8	623.6	624.3
145°	650.3	650.0	649.8	649.2	648.3	647.4	646.5	645.6	646.5	647.4	648.3
147.5°	671.1	670.9	670.6	670.2	669.6	669.1	668.5	667.9	668.5	669.1	669.6
150°	683.9	683.7	683.4	683.1	682.7	682.3	682.0	681.6	682.0	682.3	682.7
152.5°	695.1	694.9	694.8	694.6	694.4	694.2	694.1	693.9	694.1	694.2	694.4
155°	710.4	710.3	710.2	710.2	710.5	710.7	711.0	711.2	711.0	710.7	710.5
157.5°	724.3	724.4	724.5	724.6	724.6	724.6	724.7	724.7	724.7	724.6	724.6
160°	732.0	732.1	732.3	732.4	732.5	732.7	732.8	732.9	732.8	732.7	732.5
162.5°	738.9	739.0	739.1	739.3	739.7	740.0	740.3	740.7	740.3	740.0	739.7
165°	748.0	748.1	748.2	748.5	748.9	749.3	749.6	750.0	749.6	749.3	748.9
167.5°	755.0	755.0	755.0	755.3	755.8	756.3	756.8	757.3	756.8	756.3	755.8
170°	759.1	759.1	759.1	759.4	759.9	760.4	760.9	761.4	760.9	760.4	759.9
172.5°	761.7	761.6	761.5	761.7	762.3	762.9	763.6	764.2	763.6	762.9	762.3
175°	765.2	765.0	764.9	765.2	765.8	766.4	767.1	767.7	767.1	766.4	765.8
177.5°	766.6	766.5	766.4	766.6	767.1	767.6	768.1	768.6	768.1	767.6	767.1
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P332054

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1595.1	1590.7	1584.4	1575.0	1567.4	1555.5	1555.5	1557.4	1557.4	1556.8	1555.5
5°	1546.7	1534.9	1520.8	1504.3	1487.0	1469.7	1466.5	1460.2	1455.5	1452.4	1448.5
7.5°	1495.6	1474.7	1454.1	1431.0	1409.9	1392.5	1380.4	1370.3	1363.9	1357.0	1351.9
10°	1461.0	1435.1	1410.7	1386.4	1359.6	1338.4	1325.1	1315.6	1308.6	1302.3	1299.1
12.5°	1420.2	1390.5	1363.6	1340.5	1311.2	1289.4	1276.7	1272.2	1263.9	1250.7	1243.8
15°	1360.4	1332.9	1300.7	1265.3	1251.2	1224.5	1209.5	1202.5	1197.7	1187.5	1184.4
17.5°	1309.3	1273.3	1237.2	1210.8	1184.5	1162.8	1154.5	1145.7	1139.4	1131.1	1128.6
20°	1268.5	1236.3	1203.2	1175.0	1147.4	1123.9	1116.8	1110.5	1104.2	1100.3	1097.1
22.5°	1227.0	1194.8	1167.4	1141.0	1111.6	1096.2	1088.5	1081.6	1077.2	1074.5	1071.4
25°	1168.7	1140.4	1109.7	1086.1	1062.6	1052.3	1047.6	1043.7	1040.6	1036.6	1035.8
27.5°	1116.5	1085.7	1060.8	1038.8	1021.9	1013.4	1008.8	1006.9	1007.6	1009.0	1009.9
30°	1077.5	1049.2	1028.8	1009.9	994.2	986.3	985.5	985.5	988.7	989.5	991.0
32.5°	1041.7	1018.4	998.0	979.7	967.8	962.4	965.4	965.4	967.9	970.0	972.8
35°	989.5	969.0	953.3	937.6	927.4	929.7	931.3	932.9	936.8	941.5	944.7
37.5°	939.6	921.9	905.5	893.3	888.6	892.8	896.6	899.9	904.4	908.1	911.2
40°	903.8	890.4	874.7	863.7	865.3	867.7	870.8	874.7	878.7	881.0	884.2
42.5°	870.5	856.5	844.6	835.4	837.6	840.6	842.5	844.6	849.1	853.4	855.2
45°	819.7	808.7	797.7	792.2	793.8	795.4	796.9	799.3	803.2	806.4	807.1
47.5°	762.7	755.0	747.6	742.2	744.7	744.1	746.2	751.2	752.4	754.3	758.7
50°	726.2	719.1	710.5	708.9	708.9	708.9	709.7	716.0	716.0	719.1	722.3
52.5°	686.0	681.4	675.9	673.1	671.8	671.8	675.1	678.3	679.5	683.9	687.1
55°	626.4	621.7	616.9	614.6	613.0	614.6	620.9	622.4	626.4	628.7	631.1
57.5°	564.3	560.7	556.9	555.6	555.3	557.4	560.8	565.5	566.5	573.7	577.3
60°	523.4	517.9	514.8	514.8	513.2	520.3	518.7	526.6	528.1	532.9	538.4
62.5°	481.3	473.9	472.7	472.7	474.9	476.9	479.1	482.6	486.6	492.6	496.9
65°	413.4	409.5	415.0	414.2	412.6	417.3	417.3	421.3	426.0	431.5	440.1
67.5°	349.1	347.1	347.5	347.5	349.9	352.6	354.8	358.2	363.9	369.7	375.4
70°	305.7	308.1	304.2	307.3	309.7	310.4	312.0	316.7	323.0	326.9	333.2
72.5°	263.6	263.4	263.9	265.2	267.5	268.9	270.5	275.9	282.8	286.1	291.1
75°	202.8	202.0	204.3	204.3	208.3	209.8	211.4	213.8	220.1	224.8	228.7
77.5°	148.1	149.0	148.5	151.2	150.1	150.4	155.3	157.7	158.3	167.6	169.6
80°	111.6	113.2	114.0	114.7	115.5	114.0	119.5	121.8	121.8	127.3	131.2
82.5°	80.2	81.1	83.2	83.9	84.1	85.7	86.1	87.9	89.8	92.1	97.3
85°	40.1	42.4	43.2	42.4	43.2	41.7	44.0	44.8	45.6	45.6	45.6
87.5°	13.7	14.6	14.3	15.3	15.0	15.9	16.0	14.9	15.0	17.0	14.5
90°	5.6	7.1	8.7	10.4	12.0	13.7	14.2	14.7	15.2	15.7	16.1
92.5°	9.2	9.6	10.9	12.1	13.4	14.6	15.4	16.2	17.0	17.8	18.3
95°	14.0	12.1	13.5	14.9	16.3	17.7	18.6	19.5	20.3	21.2	21.7
97.5°	60.6	54.9	45.7	36.6	27.5	18.4	19.4	20.4	21.4	22.4	23.0
100°	106.5	97.9	78.1	58.4	38.6	18.8	19.8	20.8	21.9	22.9	23.4
102.5°	133.8	123.9	102.3	80.7	59.1	37.5	34.4	31.2	28.1	25.0	23.5
105°	175.5	170.5	159.1	147.7	136.3	124.9	102.5	80.0	57.6	35.2	24.1
107.5°	220.3	221.7	223.5	225.3	227.1	228.9	212.5	196.0	179.6	163.1	146.5
110°	250.4	251.7	253.0	254.4	255.8	257.2	253.0	248.9	244.7	240.5	229.3



TEST NUMBER: P332054

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	279.2	280.4	281.8	283.2	284.6	286.0	286.1	286.1	286.2	286.3	284.4
115°	321.9	322.8	324.0	325.1	326.2	327.4	328.7	329.9	331.2	332.5	333.3
117.5°	364.4	365.2	365.8	366.4	367.0	367.5	368.6	369.6	370.6	371.6	372.2
120°	391.3	392.0	392.4	392.8	393.2	393.5	394.6	395.6	396.6	397.6	398.1
122.5°	416.9	417.6	418.1	418.6	419.1	419.6	420.3	421.0	421.7	422.4	422.8
125°	453.5	454.3	454.8	455.3	455.8	456.3	456.5	456.8	457.0	457.3	457.6
127.5°	488.6	489.4	490.0	490.7	491.3	491.9	492.3	492.7	493.1	493.5	493.6
130°	510.5	511.3	511.8	512.3	512.8	513.3	513.8	514.3	514.8	515.3	515.5
132.5°	531.5	532.2	532.6	533.0	533.4	533.9	534.4	534.9	535.4	535.9	536.0
135°	562.6	563.2	563.7	564.2	564.7	565.2	565.6	566.0	566.4	566.7	566.7
137.5°	590.7	591.4	591.6	591.9	592.2	592.5	593.1	593.7	594.3	594.9	595.1
140°	608.2	608.8	609.1	609.5	609.9	610.3	610.8	611.3	611.8	612.3	612.4
142.5°	625.1	625.6	626.0	626.4	626.8	627.2	627.6	628.0	628.4	628.8	628.8
145°	649.2	649.8	650.0	650.3	650.5	650.8	651.0	651.3	651.5	651.8	651.9
147.5°	670.2	670.6	670.9	671.1	671.4	671.7	671.9	672.2	672.4	672.7	672.5
150°	683.1	683.4	683.7	683.9	684.2	684.4	684.7	684.9	685.2	685.4	685.4
152.5°	694.6	694.8	694.9	695.1	695.2	695.4	695.8	696.3	696.7	697.2	697.1
155°	710.2	710.2	710.3	710.4	710.5	710.7	711.3	711.9	712.6	713.2	713.1
157.5°	724.6	724.5	724.4	724.3	724.1	724.0	724.8	725.5	726.3	727.1	726.9
160°	732.4	732.3	732.1	732.0	731.9	731.8	732.5	733.3	734.0	734.8	734.7
162.5°	739.3	739.1	739.0	738.9	738.7	738.6	739.5	740.3	741.2	742.1	742.1
165°	748.5	748.2	748.1	748.0	747.9	747.7	748.8	749.8	750.8	751.8	751.9
167.5°	755.3	755.0	755.0	755.0	755.0	755.0	756.1	757.1	758.1	759.1	759.1
170°	759.4	759.1	759.1	759.1	759.1	759.1	760.2	761.2	762.2	763.2	763.2
172.5°	761.7	761.5	761.6	761.7	761.8	761.9	762.9	763.9	764.9	765.9	765.9
175°	765.2	764.9	765.0	765.2	765.3	765.4	766.3	767.2	768.1	769.0	768.9
177.5°	766.6	766.4	766.5	766.6	766.7	766.8	767.6	768.4	769.2	770.0	769.9
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P332054

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1551.1	1550.5	1554.9	1551.7	1554.9	1550.5	1551.1	1555.5	1556.8	1557.4	1557.4
5°	1443.7	1446.1	1438.2	1438.2	1438.2	1446.1	1443.7	1448.5	1452.4	1455.5	1460.2
7.5°	1348.2	1344.7	1345.0	1340.8	1345.0	1344.7	1348.2	1351.9	1357.0	1363.9	1370.3
10°	1289.7	1285.0	1283.4	1284.2	1283.4	1285.0	1289.7	1299.1	1302.3	1308.6	1315.6
12.5°	1241.3	1240.3	1230.0	1230.1	1230.0	1240.3	1241.3	1243.8	1250.7	1263.9	1272.2
15°	1184.4	1169.5	1167.9	1172.6	1167.9	1169.5	1184.4	1184.4	1187.5	1197.7	1202.5
17.5°	1127.3	1119.5	1119.9	1117.6	1119.9	1119.5	1127.3	1128.6	1131.1	1139.4	1145.7
20°	1097.1	1092.4	1091.6	1086.1	1091.6	1092.4	1097.1	1097.1	1100.3	1104.2	1110.5
22.5°	1069.5	1067.9	1068.4	1062.3	1068.4	1067.9	1069.5	1071.4	1074.5	1077.2	1081.6
25°	1035.1	1039.0	1035.8	1035.8	1035.8	1039.0	1035.1	1035.8	1036.6	1040.6	1043.7
27.5°	1011.8	1011.6	1010.1	1010.1	1010.1	1011.6	1011.8	1009.9	1009.0	1007.6	1006.9
30°	994.2	993.4	995.0	995.0	995.0	993.4	994.2	991.0	989.5	988.7	985.5
32.5°	976.6	977.7	978.0	978.6	978.0	977.7	976.6	972.8	970.0	967.9	965.4
35°	949.4	950.2	952.5	951.0	952.5	950.2	949.4	944.7	941.5	936.8	932.9
37.5°	912.6	916.2	915.4	916.7	915.4	916.2	912.6	911.2	908.1	904.4	899.9
40°	884.9	887.3	886.5	886.5	886.5	887.3	884.9	884.2	881.0	878.7	874.7
42.5°	856.7	858.4	856.3	855.1	856.3	858.4	856.7	855.2	853.4	849.1	844.6
45°	810.3	808.7	811.1	807.9	811.1	808.7	810.3	807.1	806.4	803.2	799.3
47.5°	758.4	760.0	760.6	763.0	760.6	760.0	758.4	758.7	754.3	752.4	751.2
50°	723.8	728.5	728.5	727.8	728.5	728.5	723.8	722.3	719.1	716.0	716.0
52.5°	689.9	692.1	695.2	695.1	695.2	692.1	689.9	687.1	683.9	679.5	678.3
55°	637.4	639.0	640.5	641.3	640.5	639.0	637.4	631.1	628.7	626.4	622.4
57.5°	583.0	582.4	586.1	587.2	586.1	582.4	583.0	577.3	573.7	566.5	565.5
60°	544.6	544.6	550.9	553.3	550.9	544.6	544.6	538.4	532.9	528.1	526.6
62.5°	503.8	506.3	512.6	509.3	512.6	506.3	503.8	496.9	492.6	486.6	482.6
65°	444.0	450.3	449.5	452.7	449.5	450.3	444.0	440.1	431.5	426.0	421.3
67.5°	381.6	385.6	391.2	391.7	391.2	385.6	381.6	375.4	369.7	363.9	358.2
70°	339.5	343.4	346.6	348.9	346.6	343.4	339.5	333.2	326.9	323.0	316.7
72.5°	298.7	300.7	308.2	304.9	308.2	300.7	298.7	291.1	286.1	282.8	275.9
75°	234.2	239.7	244.4	242.1	244.4	239.7	234.2	228.7	224.8	220.1	213.8
77.5°	173.2	178.7	180.9	178.9	180.9	178.7	173.2	169.6	167.6	158.3	157.7
80°	136.8	136.0	140.7	139.9	140.7	136.0	136.8	131.2	127.3	121.8	121.8
82.5°	100.3	99.5	101.7	102.2	101.7	99.5	100.3	97.3	92.1	89.8	87.9
85°	48.7	51.1	47.9	47.2	47.9	51.1	48.7	45.6	45.6	45.6	44.8
87.5°	14.6	14.6	14.1	13.5	14.1	14.6	14.6	14.5	17.0	15.0	14.9
90°	16.4	16.6	16.9	17.1	16.9	16.6	16.4	16.1	15.7	15.2	14.7
92.5°	18.5	18.6	18.8	18.9	18.8	18.6	18.5	18.3	17.8	17.0	16.2
95°	21.7	21.7	21.7	21.7	21.7	21.7	21.7	21.7	21.2	20.3	19.5
97.5°	23.1	23.2	23.4	23.5	23.4	23.2	23.1	23.0	22.4	21.4	20.4
100°	23.6	23.7	23.8	24.0	23.8	23.7	23.6	23.4	22.9	21.9	20.8
102.5°	23.7	24.0	24.2	24.4	24.2	24.0	23.7	23.5	25.0	28.1	31.2
105°	24.3	24.6	24.8	25.1	24.8	24.6	24.3	24.1	35.2	57.6	80.0
107.5°	129.5	112.6	95.7	78.8	95.7	112.6	129.5	146.5	163.1	179.6	196.0
110°	211.2	193.1	175.0	156.8	175.0	193.1	211.2	229.3	240.5	244.7	248.9



TEST NUMBER: P332054

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	280.6	276.7	272.9	269.1	272.9	276.7	280.6	284.4	286.3	286.2	286.1
115°	333.8	334.4	334.9	335.4	334.9	334.4	333.8	333.3	332.5	331.2	329.9
117.5°	372.3	372.4	372.5	372.6	372.5	372.4	372.3	372.2	371.6	370.6	369.6
120°	398.1	398.1	398.1	398.1	398.1	398.1	398.1	398.1	397.6	396.6	395.6
122.5°	422.9	423.0	423.1	423.2	423.1	423.0	422.9	422.8	422.4	421.7	421.0
125°	457.8	458.1	458.3	458.6	458.3	458.1	457.8	457.6	457.3	457.0	456.8
127.5°	493.3	493.1	492.8	492.6	492.8	493.1	493.3	493.6	493.5	493.1	492.7
130°	515.2	515.0	514.7	514.5	514.7	515.0	515.2	515.5	515.3	514.8	514.3
132.5°	535.6	535.2	534.9	534.5	534.9	535.2	535.6	536.0	535.9	535.4	534.9
135°	566.4	566.0	565.6	565.2	565.6	566.0	566.4	566.7	566.7	566.4	566.0
137.5°	594.8	594.6	594.3	594.1	594.3	594.6	594.8	595.1	594.9	594.3	593.7
140°	612.2	611.9	611.7	611.4	611.7	611.9	612.2	612.4	612.3	611.8	611.3
142.5°	628.5	628.1	627.7	627.4	627.7	628.1	628.5	628.8	628.8	628.4	628.0
145°	651.9	651.9	651.9	651.9	651.9	651.9	651.9	651.9	651.8	651.5	651.3
147.5°	671.9	671.3	670.8	670.2	670.8	671.3	671.9	672.5	672.7	672.4	672.2
150°	685.0	684.6	684.2	683.9	684.2	684.6	685.0	685.4	685.4	685.2	684.9
152.5°	696.6	696.0	695.4	694.8	695.4	696.0	696.6	697.1	697.2	696.7	696.3
155°	712.4	711.6	710.9	710.1	710.9	711.6	712.4	713.1	713.2	712.6	711.9
157.5°	725.9	725.0	724.0	723.0	724.0	725.0	725.9	726.9	727.1	726.3	725.5
160°	733.9	733.0	732.1	731.2	732.1	733.0	733.9	734.7	734.8	734.0	733.3
162.5°	741.3	740.5	739.7	739.0	739.7	740.5	741.3	742.1	742.1	741.2	740.3
165°	751.0	750.1	749.2	748.3	749.2	750.1	751.0	751.9	751.8	750.8	749.8
167.5°	758.1	757.1	756.1	755.0	756.1	757.1	758.1	759.1	759.1	758.1	757.1
170°	762.2	761.2	760.2	759.1	760.2	761.2	762.2	763.2	763.2	762.2	761.2
172.5°	764.8	763.7	762.5	761.4	762.5	763.7	764.8	765.9	765.9	764.9	763.9
175°	767.9	766.9	765.9	764.8	765.9	766.9	767.9	768.9	769.0	768.1	767.2
177.5°	768.9	767.9	766.9	765.9	766.9	767.9	768.9	769.9	770.0	769.2	768.4
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P332054

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1555.5	1555.5	1567.4	1575.0	1584.4	1590.7	1595.1	1599.5	1607.1	1617.1	1628.4
5°	1466.5	1469.7	1487.0	1504.3	1520.8	1534.9	1546.7	1560.8	1578.1	1599.3	1622.9
7.5°	1380.4	1392.5	1409.9	1431.0	1454.1	1474.7	1495.6	1518.9	1543.2	1574.5	1607.5
10°	1325.1	1338.4	1359.6	1386.4	1410.7	1435.1	1461.0	1486.2	1516.8	1553.8	1596.2
12.5°	1276.7	1289.4	1311.2	1340.5	1363.6	1390.5	1420.2	1452.9	1487.3	1531.8	1579.9
15°	1209.5	1224.5	1251.2	1265.3	1300.7	1332.9	1360.4	1407.6	1451.6	1497.2	1553.0
17.5°	1154.5	1162.8	1184.5	1210.8	1237.2	1273.3	1309.3	1348.6	1392.5	1448.3	1518.1
20°	1116.8	1123.9	1147.4	1175.0	1203.2	1236.3	1268.5	1307.8	1357.3	1416.2	1491.7
22.5°	1088.5	1096.2	1111.6	1141.0	1167.4	1194.8	1227.0	1273.8	1326.5	1384.2	1465.9
25°	1047.6	1052.3	1062.6	1086.1	1109.7	1140.4	1168.7	1212.7	1266.9	1334.5	1416.2
27.5°	1008.8	1013.4	1021.9	1038.8	1060.8	1085.7	1116.5	1153.9	1208.9	1282.3	1369.1
30°	985.5	986.3	994.2	1009.9	1028.8	1049.2	1077.5	1119.9	1171.8	1246.5	1337.6
32.5°	965.4	962.4	967.8	979.7	998.0	1018.4	1041.7	1083.5	1133.5	1206.9	1300.5
35°	931.3	929.7	927.4	937.6	953.3	969.0	989.5	1020.9	1077.5	1145.9	1244.1
37.5°	896.6	892.8	888.6	893.3	905.5	921.9	939.6	967.6	1016.4	1091.6	1185.6
40°	870.8	867.7	865.3	863.7	874.7	890.4	903.8	930.5	976.1	1047.6	1140.4
42.5°	842.5	840.6	837.6	835.4	844.6	856.5	870.5	894.1	939.6	1006.8	1094.5
45°	796.9	795.4	793.8	792.2	797.7	808.7	819.7	837.0	876.3	941.5	1020.9
47.5°	746.2	744.1	744.7	742.2	747.6	755.0	762.7	781.2	818.9	871.6	929.6
50°	709.7	708.9	708.9	708.9	710.5	719.1	726.2	740.3	774.9	827.6	869.2
52.5°	675.1	671.8	671.8	673.1	675.9	681.4	686.0	701.4	731.5	774.8	812.6
55°	620.9	614.6	613.0	614.6	616.9	621.7	626.4	639.0	664.9	697.1	719.1
57.5°	560.8	557.4	555.3	555.6	556.9	560.7	564.3	578.0	598.4	615.2	629.4
60°	518.7	520.3	513.2	514.8	514.8	517.9	523.4	532.1	549.4	561.1	575.3
62.5°	479.1	476.9	474.9	472.7	472.7	473.9	481.3	488.1	502.8	509.0	520.0
65°	417.3	417.3	412.6	414.2	415.0	409.5	413.4	421.3	430.7	433.0	443.3
67.5°	354.8	352.6	349.9	347.5	347.5	347.1	349.1	353.0	360.1	360.9	368.8
70°	312.0	310.4	309.7	307.3	304.2	308.1	305.7	309.7	313.6	314.4	319.1
72.5°	270.5	268.9	267.5	265.2	263.9	263.4	263.6	268.2	270.8	269.7	275.1
75°	211.4	209.8	208.3	204.3	204.3	202.0	202.8	205.9	209.1	206.7	211.4
77.5°	155.3	150.4	150.1	151.2	148.5	149.0	148.1	147.6	149.0	149.2	153.4
80°	119.5	114.0	115.5	114.7	114.0	113.2	111.6	112.4	113.2	114.0	116.3
82.5°	86.1	85.7	84.1	83.9	83.2	81.1	80.2	81.6	82.4	81.9	83.6
85°	44.0	41.7	43.2	42.4	43.2	42.4	40.1	40.1	41.7	40.9	42.4
87.5°	16.0	15.9	15.0	15.3	14.3	14.6	13.7	14.1	14.5	14.2	15.2
90°	14.2	13.7	12.0	10.4	8.7	7.1	5.6	4.4	3.1	1.8	0.6
92.5°	15.4	14.6	13.4	12.1	10.9	9.6	9.2	9.5	9.9	10.3	10.6
95°	18.6	17.7	16.3	14.9	13.5	12.1	14.0	19.2	24.4	29.6	34.8
97.5°	19.4	18.4	27.5	36.6	45.7	54.9	60.6	62.9	65.3	67.6	69.9
100°	19.8	18.8	38.6	58.4	78.1	97.9	106.5	104.0	101.5	98.9	96.4
102.5°	34.4	37.5	59.1	80.7	102.3	123.9	133.8	132.0	130.2	128.3	126.5
105°	102.5	124.9	136.3	147.7	159.1	170.5	175.5	174.1	172.8	171.4	170.0
107.5°	212.5	228.9	227.1	225.3	223.5	221.7	220.3	219.2	218.1	216.9	215.8
110°	253.0	257.2	255.8	254.4	253.0	251.7	250.4	249.4	248.4	247.4	246.4



TEST NUMBER: P332054

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	286.1	286.0	284.6	283.2	281.8	280.4	279.2	278.3	277.4	276.5	275.6
115°	328.7	327.4	326.2	325.1	324.0	322.8	321.9	321.1	320.3	319.6	318.8
117.5°	368.6	367.5	367.0	366.4	365.8	365.2	364.4	363.5	362.6	361.6	360.7
120°	394.6	393.5	393.2	392.8	392.4	392.0	391.3	390.1	389.0	387.8	386.7
122.5°	420.3	419.6	419.1	418.6	418.1	417.6	416.9	416.0	415.0	414.1	413.2
125°	456.5	456.3	455.8	455.3	454.8	454.3	453.5	452.5	451.5	450.5	449.4
127.5°	492.3	491.9	491.3	490.7	490.0	489.4	488.6	487.6	486.6	485.6	484.6
130°	513.8	513.3	512.8	512.3	511.8	511.3	510.5	509.5	508.5	507.5	506.5
132.5°	534.4	533.9	533.4	533.0	532.6	532.2	531.5	530.5	529.5	528.5	527.5
135°	565.6	565.2	564.7	564.2	563.7	563.2	562.6	561.8	561.0	560.3	559.5
137.5°	593.1	592.5	592.2	591.9	591.6	591.4	590.7	589.8	588.8	587.9	586.9
140°	610.8	610.3	609.9	609.5	609.1	608.8	608.2	607.4	606.7	605.9	605.1
142.5°	627.6	627.2	626.8	626.4	626.0	625.6	625.1	624.3	623.6	622.8	622.0
145°	651.0	650.8	650.5	650.3	650.0	649.8	649.2	648.3	647.4	646.5	645.6
147.5°	671.9	671.7	671.4	671.1	670.9	670.6	670.2	669.6	669.1	668.5	667.9
150°	684.7	684.4	684.2	683.9	683.7	683.4	683.1	682.7	682.3	682.0	681.6
152.5°	695.8	695.4	695.2	695.1	694.9	694.8	694.6	694.4	694.2	694.1	693.9
155°	711.3	710.7	710.5	710.4	710.3	710.2	710.2	710.5	710.7	711.0	711.2
157.5°	724.8	724.0	724.1	724.3	724.4	724.5	724.6	724.6	724.6	724.7	724.7
160°	732.5	731.8	731.9	732.0	732.1	732.3	732.4	732.5	732.7	732.8	732.9
162.5°	739.5	738.6	738.7	738.9	739.0	739.1	739.3	739.7	740.0	740.3	740.7
165°	748.8	747.7	747.9	748.0	748.1	748.2	748.5	748.9	749.3	749.6	750.0
167.5°	756.1	755.0	755.0	755.0	755.0	755.0	755.3	755.8	756.3	756.8	757.3
170°	760.2	759.1	759.1	759.1	759.1	759.1	759.4	759.9	760.4	760.9	761.4
172.5°	762.9	761.9	761.8	761.7	761.6	761.5	761.7	762.3	762.9	763.6	764.2
175°	766.3	765.4	765.3	765.2	765.0	764.9	765.2	765.8	766.4	767.1	767.7
177.5°	767.6	766.8	766.7	766.6	766.5	766.4	766.6	767.1	767.6	768.1	768.6
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P332054

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1632.2	1635.3	1646.0	1653.6	1662.4	1667.4	1672.4	1676.2	1681.2	1682.5	1700.7
5°	1639.4	1655.2	1682.7	1703.1	1728.2	1755.7	1774.6	1783.3	1806.0	1824.9	1862.6
7.5°	1637.4	1670.9	1712.4	1755.4	1801.6	1844.4	1881.5	1925.5	1956.8	2003.8	2050.2
10°	1635.5	1680.3	1733.7	1788.8	1853.2	1912.9	1966.4	2026.1	2075.6	2140.8	2196.6
12.5°	1629.8	1684.1	1758.3	1823.3	1901.6	1984.0	2063.2	2139.9	2183.8	2292.4	2343.8
15°	1615.9	1680.3	1773.0	1872.1	1979.7	2077.2	2177.8	2258.0	2387.6	2482.7	2543.2
17.5°	1589.1	1679.4	1789.4	1908.8	2039.8	2168.2	2282.2	2403.8	2541.4	2656.4	2779.0
20°	1576.6	1675.6	1798.2	1930.2	2066.2	2211.6	2341.3	2487.4	2637.6	2750.7	2907.9
22.5°	1553.3	1665.5	1797.6	1944.7	2090.1	2240.5	2392.2	2539.6	2713.0	2868.9	3018.6
25°	1515.3	1641.0	1777.8	1942.0	2112.6	2263.5	2445.0	2640.7	2821.5	3021.9	3171.2
27.5°	1475.3	1609.6	1746.6	1899.4	2082.8	2261.9	2490.3	2711.4	2932.4	3105.5	3216.0
30°	1444.5	1575.0	1716.5	1870.5	2052.0	2265.0	2520.4	2761.7	2977.1	3125.6	3187.7
32.5°	1411.2	1543.5	1668.7	1830.3	2023.7	2263.1	2539.3	2791.3	2979.6	3078.5	3066.4
35°	1358.9	1469.7	1591.5	1747.1	1975.0	2249.3	2550.3	2793.9	2909.5	2888.3	2727.9
37.5°	1283.4	1376.6	1496.6	1666.9	1918.4	2220.2	2528.3	2711.1	2703.6	2530.8	2298.5
40°	1236.3	1315.6	1431.2	1610.4	1874.4	2201.4	2493.7	2612.4	2511.8	2270.5	1992.3
42.5°	1174.6	1247.7	1363.3	1547.5	1826.0	2163.0	2427.7	2462.1	2265.3	1987.6	1732.6
45°	1079.1	1143.5	1263.0	1453.2	1753.4	2079.5	2266.6	2182.5	1917.6	1630.8	1436.7
47.5°	976.4	1043.4	1158.3	1353.7	1648.4	1954.0	2043.1	1864.2	1592.3	1359.6	1181.4
50°	911.7	976.1	1088.5	1285.8	1577.3	1850.8	1887.8	1656.7	1406.8	1202.5	1056.3
52.5°	846.3	907.0	1017.5	1215.3	1494.4	1731.4	1708.6	1473.1	1243.3	1069.2	954.4
55°	749.0	806.4	911.7	1097.1	1351.0	1538.8	1456.3	1231.5	1041.3	906.2	818.9
57.5°	661.9	716.9	807.8	975.3	1196.0	1325.1	1220.1	1030.7	879.4	775.4	710.3
60°	602.8	651.5	738.0	893.6	1085.4	1183.6	1079.9	912.5	785.1	701.8	643.7
62.5°	546.8	589.3	669.4	810.6	977.2	1059.7	954.7	813.1	704.7	630.8	581.4
65°	462.1	500.6	571.4	681.4	818.1	873.2	782.8	668.0	583.9	528.9	495.9
67.5°	384.8	417.5	478.6	565.2	665.8	705.9	637.1	548.3	484.9	440.7	414.5
70°	333.2	361.5	409.5	484.1	575.3	605.9	541.5	468.4	422.0	386.7	362.3
72.5°	289.8	310.6	354.1	411.8	487.9	512.3	467.3	403.0	359.8	333.2	313.9
75°	220.8	238.1	266.4	312.8	365.5	379.6	345.8	305.7	276.6	257.8	242.8
77.5°	159.2	172.0	192.4	221.0	257.5	270.2	248.8	222.1	200.9	188.1	179.8
80°	120.2	130.5	147.8	171.3	193.3	200.4	187.8	167.4	152.5	145.4	138.3
82.5°	88.8	94.6	105.0	121.0	136.1	144.5	133.8	121.5	113.5	107.0	104.4
85°	44.8	47.9	52.7	58.9	68.4	71.5	67.6	64.4	59.7	55.8	55.8
87.5°	16.7	17.0	19.1	20.6	23.4	25.6	25.3	24.4	24.1	23.6	23.1
90°	1.8	3.1	4.4	5.6	7.1	8.7	10.4	12.0	13.7	14.2	14.7
92.5°	10.3	9.9	9.5	9.2	9.6	10.9	12.1	13.4	14.6	15.4	16.2
95°	29.6	24.4	19.2	14.0	12.1	13.5	14.9	16.3	17.7	18.6	19.5
97.5°	67.6	65.3	62.9	60.6	54.9	45.7	36.6	27.5	18.4	19.4	20.4
100°	98.9	101.5	104.0	106.5	97.9	78.1	58.4	38.6	18.8	19.8	20.8
102.5°	128.3	130.2	132.0	133.8	123.9	102.3	80.7	59.1	37.5	34.4	31.2
105°	171.4	172.8	174.1	175.5	170.5	159.1	147.7	136.3	124.9	102.5	80.0
107.5°	216.9	218.1	219.2	220.3	221.7	223.5	225.3	227.1	228.9	212.5	196.0
110°	247.4	248.4	249.4	250.4	251.7	253.0	254.4	255.8	257.2	253.0	248.9





TEST NUMBER: P332054

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	276.5	277.4	278.3	279.2	280.4	281.8	283.2	284.6	286.0	286.1	286.1
115°	319.6	320.3	321.1	321.9	322.8	324.0	325.1	326.2	327.4	328.7	329.9
117.5°	361.6	362.6	363.5	364.4	365.2	365.8	366.4	367.0	367.5	368.6	369.6
120°	387.8	389.0	390.1	391.3	392.0	392.4	392.8	393.2	393.5	394.6	395.6
122.5°	414.1	415.0	416.0	416.9	417.6	418.1	418.6	419.1	419.6	420.3	421.0
125°	450.5	451.5	452.5	453.5	454.3	454.8	455.3	455.8	456.3	456.5	456.8
127.5°	485.6	486.6	487.6	488.6	489.4	490.0	490.7	491.3	491.9	492.3	492.7
130°	507.5	508.5	509.5	510.5	511.3	511.8	512.3	512.8	513.3	513.8	514.3
132.5°	528.5	529.5	530.5	531.5	532.2	532.6	533.0	533.4	533.9	534.4	534.9
135°	560.3	561.0	561.8	562.6	563.2	563.7	564.2	564.7	565.2	565.6	566.0
137.5°	587.9	588.8	589.8	590.7	591.4	591.6	591.9	592.2	592.5	593.1	593.7
140°	605.9	606.7	607.4	608.2	608.8	609.1	609.5	609.9	610.3	610.8	611.3
142.5°	622.8	623.6	624.3	625.1	625.6	626.0	626.4	626.8	627.2	627.6	628.0
145°	646.5	647.4	648.3	649.2	649.8	650.0	650.3	650.5	650.8	651.0	651.3
147.5°	668.5	669.1	669.6	670.2	670.6	670.9	671.1	671.4	671.7	671.9	672.2
150°	682.0	682.3	682.7	683.1	683.4	683.7	683.9	684.2	684.4	684.7	684.9
152.5°	694.1	694.2	694.4	694.6	694.8	694.9	695.1	695.2	695.4	695.8	696.3
155°	711.0	710.7	710.5	710.2	710.2	710.3	710.4	710.5	710.7	711.3	711.9
157.5°	724.7	724.6	724.6	724.6	724.5	724.4	724.3	724.1	724.0	724.8	725.5
160°	732.8	732.7	732.5	732.4	732.3	732.1	732.0	731.9	731.8	732.5	733.3
162.5°	740.3	740.0	739.7	739.3	739.1	739.0	738.9	738.7	738.6	739.5	740.3
165°	749.6	749.3	748.9	748.5	748.2	748.1	748.0	747.9	747.7	748.8	749.8
167.5°	756.8	756.3	755.8	755.3	755.0	755.0	755.0	755.0	755.0	756.1	757.1
170°	760.9	760.4	759.9	759.4	759.1	759.1	759.1	759.1	759.1	760.2	761.2
172.5°	763.6	762.9	762.3	761.7	761.5	761.6	761.7	761.8	761.9	762.9	763.9
175°	767.1	766.4	765.8	765.2	764.9	765.0	765.2	765.3	765.4	766.3	767.2
177.5°	768.1	767.6	767.1	766.6	766.4	766.5	766.6	766.7	766.8	767.6	768.4
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P332054

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1707.0	1707.6	1714.6	1719.6	1717.1	1720.2	1721.5
5°	1865.0	1893.3	1908.2	1919.2	1920.0	1920.8	1927.1
7.5°	2089.0	2119.3	2141.5	2175.1	2185.2	2196.6	2193.3
10°	2252.5	2297.2	2335.8	2356.2	2378.2	2410.4	2384.5
12.5°	2405.2	2484.6	2543.2	2575.0	2595.7	2602.2	2589.5
15°	2657.2	2760.9	2816.7	2815.2	2885.9	2916.6	2868.6
17.5°	2888.3	2984.0	3060.7	3100.0	3158.9	3172.0	3166.0
20°	3029.7	3134.3	3194.0	3261.6	3292.2	3319.7	3324.4
22.5°	3151.7	3245.5	3309.7	3365.9	3391.6	3404.6	3412.5
25°	3277.3	3351.2	3389.7	3409.3	3416.4	3414.8	3404.6
27.5°	3268.6	3274.3	3231.9	3190.2	3153.0	3111.0	3096.5
30°	3183.8	3117.7	2999.9	2933.1	2834.8	2757.0	2788.4
32.5°	2960.6	2829.2	2696.8	2550.8	2429.9	2395.5	2360.9
35°	2526.7	2295.7	2160.5	2003.3	1940.4	1877.6	1834.3
37.5°	2044.2	1865.5	1705.1	1602.3	1539.3	1499.5	1478.2
40°	1767.5	1606.4	1474.4	1391.1	1343.1	1298.3	1292.1
42.5°	1546.9	1397.1	1297.7	1231.4	1185.3	1166.3	1152.5
45°	1266.9	1162.4	1095.6	1048.4	1017.8	1006.0	990.3
47.5°	1072.3	998.4	948.3	916.2	893.1	884.3	883.1
50°	963.5	902.2	865.3	840.1	822.1	818.9	806.4
52.5°	881.8	828.7	799.9	777.9	764.9	756.1	752.3
55°	765.5	730.1	704.2	691.6	681.4	672.7	672.7
57.5°	669.8	640.2	623.1	612.4	609.2	603.1	599.2
60°	610.7	585.5	572.2	562.7	556.4	557.2	550.1
62.5°	552.8	536.5	523.7	514.3	506.8	506.9	507.4
65°	470.8	458.2	448.8	445.6	440.9	435.4	437.0
67.5°	398.9	387.1	379.8	374.4	372.8	369.9	374.4
70°	347.4	338.7	333.2	328.5	326.9	327.7	331.7
72.5°	300.2	294.1	290.5	288.3	284.8	285.0	287.6
75°	235.8	231.1	227.9	225.6	224.8	224.8	224.8
77.5°	173.2	172.1	170.7	167.2	167.4	168.3	168.5
80°	136.8	134.4	133.6	132.0	129.7	128.1	132.0
82.5°	102.2	99.8	99.0	98.7	95.1	94.8	98.1
85°	55.0	52.7	53.4	52.7	52.7	51.9	51.9
87.5°	22.5	22.0	21.5	22.1	21.6	21.0	22.3
90°	15.2	15.7	16.1	16.4	16.6	16.9	17.1
92.5°	17.0	17.8	18.3	18.5	18.6	18.8	18.9
95°	20.3	21.2	21.7	21.7	21.7	21.7	21.7
97.5°	21.4	22.4	23.0	23.1	23.2	23.4	23.5
100°	21.9	22.9	23.4	23.6	23.7	23.8	24.0
102.5°	28.1	25.0	23.5	23.7	24.0	24.2	24.4
105°	57.6	35.2	24.1	24.3	24.6	24.8	25.1
107.5°	179.6	163.1	146.5	129.5	112.6	95.7	78.8
110°	244.7	240.5	229.3	211.2	193.1	175.0	156.8



TEST NUMBER: P332054

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	286.2	286.3	284.4	280.6	276.7	272.9	269.1
115°	331.2	332.5	333.3	333.8	334.4	334.9	335.4
117.5°	370.6	371.6	372.2	372.3	372.4	372.5	372.6
120°	396.6	397.6	398.1	398.1	398.1	398.1	398.1
122.5°	421.7	422.4	422.8	422.9	423.0	423.1	423.2
125°	457.0	457.3	457.6	457.8	458.1	458.3	458.6
127.5°	493.1	493.5	493.6	493.3	493.1	492.8	492.6
130°	514.8	515.3	515.5	515.2	515.0	514.7	514.5
132.5°	535.4	535.9	536.0	535.6	535.2	534.9	534.5
135°	566.4	566.7	566.7	566.4	566.0	565.6	565.2
137.5°	594.3	594.9	595.1	594.8	594.6	594.3	594.1
140°	611.8	612.3	612.4	612.2	611.9	611.7	611.4
142.5°	628.4	628.8	628.8	628.5	628.1	627.7	627.4
145°	651.5	651.8	651.9	651.9	651.9	651.9	651.9
147.5°	672.4	672.7	672.5	671.9	671.3	670.8	670.2
150°	685.2	685.4	685.4	685.0	684.6	684.2	683.9
152.5°	696.7	697.2	697.1	696.6	696.0	695.4	694.8
155°	712.6	713.2	713.1	712.4	711.6	710.9	710.1
157.5°	726.3	727.1	726.9	725.9	725.0	724.0	723.0
160°	734.0	734.8	734.7	733.9	733.0	732.1	731.2
162.5°	741.2	742.1	742.1	741.3	740.5	739.7	739.0
165°	750.8	751.8	751.9	751.0	750.1	749.2	748.3
167.5°	758.1	759.1	759.1	758.1	757.1	756.1	755.0
170°	762.2	763.2	763.2	762.2	761.2	760.2	759.1
172.5°	764.9	765.9	765.9	764.8	763.7	762.5	761.4
175°	768.1	769.0	768.9	767.9	766.9	765.9	764.8
177.5°	769.2	770.0	769.9	768.9	767.9	766.9	765.9
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7

(END OF REPORT)