

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332292-927

Luminaire Tested: **S123RDIP-S560D1025U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332292-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S560D1025U927-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4482.3 lumens  
Efficiency: N/A  
Efficacy: 100.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 44.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332292-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332292-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32
2	87	80	74	69	79	73	68	63	59	56	53	47	45	42	35	34	33	27
3	79	70	63	58	72	64	58	53	52	48	45	42	39	36	32	30	28	23
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	28	26	24	20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	26	23	21	18
6	61	50	42	36	56	46	39	34	38	33	29	30	27	24	23	21	19	16
7	57	45	37	32	51	41	34	30	34	29	25	28	24	21	21	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	20	17	15	13
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14	11
10	46	34	27	22	42	31	25	21	26	21	18	21	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8054	8054	8054
5°	8084	7973	8018
10°	8039	7873	7847
15°	7952	7689	7608
20°	7834	7458	7285
25°	7712	7201	6969
30°	7549	6901	6524
35°	7384	6603	6116
40°	7231	6250	5611
45°	7030	5903	5154
50°	6807	5508	4644
55°	6583	5056	4168
60°	6374	4573	3645
65°	6105	4050	3123
70°	5766	3402	2521
75°	5273	2674	2371
80°	4705	2374	2182
85°	3977	2100	1951



TEST NUMBER: P332292-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	70.3	1.6
10°-20°	195.5	4.4
20°-30°	281.5	6.3
30°-40°	317.1	7.1
40°-50°	303.3	6.8
50°-60°	248.4	5.5
60°-70°	167.6	3.7
70°-80°	84.3	1.9
80°-90°	25.3	0.6
90°-100°	65.6	1.5
100°-110°	196.3	4.4
110°-120°	333.8	7.4
120°-130°	439.1	9.8
130°-140°	493.6	11.0
140°-150°	485.2	10.8
150°-160°	408.4	9.1
160°-170°	271.9	6.1
170°-180°	95.2	2.1
0°-30°	547.2	12.2
0°-40°	864.3	19.3
0°-60°	1416.1	31.6
0°-90°	1693.3	37.8
90°-120°	595.7	13.3
90°-150°	2013.5	44.9
90°-180°	2789.0	62.2
0°-180°	4482.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	748	748	748	748	748	
5°	748	745	738	743	742	71
15°	714	706	690	687	683	201
25°	649	633	606	594	587	298
35°	562	539	502	477	465	352
45°	462	433	388	354	339	356
55°	351	320	269	236	222	314
65°	240	206	159	130	123	237
75°	127	97	64	58	57	135
85°	32	19	17	16	16	36
90°	1	9	19	22	24	4
95°	47	52	58	62	62	52
105°	178	180	187	187	188	191
115°	336	338	337	338	337	332
125°	492	494	493	489	486	438
135°	638	643	642	639	637	492
145°	774	776	778	777	774	483
155°	886	886	887	890	885	408
165°	966	963	963	967	962	272
175°	1004	1001	1001	1005	1000	95
180°	1007	1007	1007	1007	1007	



TEST NUMBER: P332292-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2
2.5°	750.7	750.2	749.8	749.3	748.9	748.1	746.8	745.4	744.2	742.9	744.1
5°	748.2	747.6	746.9	746.2	745.5	744.4	742.8	741.2	739.5	737.9	739.1
7.5°	741.3	740.6	739.8	739.1	738.4	737.0	734.9	732.8	730.6	728.6	729.2
10°	735.5	734.5	733.6	732.6	731.7	730.0	727.6	725.2	722.7	720.3	720.4
12.5°	727.2	726.2	725.1	724.1	723.0	721.0	718.0	715.1	712.1	709.2	709.1
15°	713.6	712.2	710.7	709.2	707.7	705.0	701.3	697.5	693.7	690.0	689.3
17.5°	696.5	694.8	693.1	691.3	689.6	686.3	681.5	676.8	671.9	667.2	665.7
20°	683.9	681.8	679.6	677.4	675.3	671.6	666.5	661.4	656.2	651.1	649.4
22.5°	669.8	667.3	664.9	662.3	659.9	655.9	650.5	645.0	639.6	634.1	631.9
25°	649.3	645.9	642.5	639.2	635.8	631.1	624.8	618.6	612.4	606.3	603.4
27.5°	624.4	620.7	617.0	613.2	609.5	604.2	597.3	590.4	583.5	576.6	572.7
30°	607.4	603.4	599.4	595.3	591.3	585.4	577.9	570.4	562.8	555.2	550.6
32.5°	590.4	585.9	581.3	576.7	572.1	565.9	557.9	549.9	541.9	533.9	528.9
35°	561.9	557.1	552.2	547.4	542.5	535.9	527.5	519.2	510.8	502.5	496.6
37.5°	533.1	527.7	522.3	516.8	511.4	504.3	495.4	486.5	477.5	468.6	462.0
40°	514.6	508.7	502.7	496.8	490.8	483.1	473.6	464.0	454.4	444.8	437.8
42.5°	493.7	487.7	481.9	475.9	470.0	462.1	452.2	442.3	432.4	422.5	414.8
45°	461.8	455.7	449.6	443.6	437.5	429.3	418.9	408.5	398.2	387.8	380.1
47.5°	429.8	423.2	416.5	409.9	403.2	394.7	384.3	373.9	363.5	353.2	344.8
50°	406.5	400.2	393.9	387.5	381.2	372.6	361.6	350.8	339.8	328.9	320.5
52.5°	385.7	378.8	371.9	365.0	358.2	349.4	338.5	327.7	316.9	306.1	297.4
55°	350.8	344.1	337.5	330.9	324.3	315.3	303.8	292.4	280.9	269.4	261.6
57.5°	318.5	311.2	304.0	296.8	289.6	280.3	268.8	257.3	245.7	234.2	226.9
60°	296.1	288.8	281.3	273.9	266.5	257.1	246.0	234.8	223.6	212.4	205.1
62.5°	273.8	266.4	259.0	251.5	244.2	234.8	223.6	212.5	201.2	190.0	183.2
65°	239.7	232.3	224.9	217.5	210.0	201.1	190.5	180.1	169.5	159.0	152.4
67.5°	205.6	198.1	190.6	183.1	175.6	166.8	156.7	146.6	136.6	126.4	121.5
70°	183.2	175.9	168.7	161.4	154.2	145.8	136.3	126.9	117.5	108.1	103.3
72.5°	160.9	153.8	146.6	139.4	132.2	124.4	115.8	107.2	98.6	90.1	86.2
75°	126.8	120.3	113.9	107.4	100.9	94.0	86.6	79.1	71.8	64.3	63.0
77.5°	95.8	89.9	84.1	78.2	72.3	67.0	62.3	57.5	52.7	47.9	47.2
80°	75.9	70.3	64.8	59.3	53.7	49.6	46.7	43.9	41.0	38.3	37.8
82.5°	57.0	52.1	47.4	42.6	37.8	34.8	33.4	32.2	30.8	29.5	29.1
85°	32.2	29.2	26.2	23.3	20.3	18.6	18.2	17.8	17.4	17.0	16.7
87.5°	11.8	11.0	10.1	9.3	8.5	8.3	8.7	9.2	9.7	10.1	10.1
90°	0.8	2.5	4.3	6.1	7.8	9.8	12.1	14.4	16.7	19.0	19.6
92.5°	19.2	20.4	21.5	22.7	23.9	25.2	26.5	27.7	29.1	30.3	30.9
95°	46.7	47.8	49.1	50.4	51.6	52.9	54.3	55.7	57.1	58.5	59.3
97.5°	82.9	83.8	84.7	85.6	86.5	87.5	88.5	89.5	90.5	91.6	92.4
100°	107.6	108.6	109.6	110.7	111.8	112.7	113.6	114.5	115.3	116.2	116.8
102.5°	136.0	136.7	137.3	137.9	138.6	139.4	140.6	141.7	142.9	144.1	144.6
105°	177.9	178.2	178.6	179.0	179.4	180.3	181.9	183.5	185.1	186.6	186.6
107.5°	226.6	226.9	227.0	227.3	227.5	227.9	228.5	229.2	229.8	230.4	231.0
110°	257.0	257.4	257.7	258.0	258.4	258.7	259.1	259.4	259.8	260.2	260.9



TEST NUMBER: P332292-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	288.6	288.8	289.1	289.2	289.5	289.6	289.7	289.8	289.9	289.9	290.7
115°	336.0	336.6	337.2	337.6	338.2	338.3	337.9	337.5	337.2	336.8	337.1
117.5°	383.8	384.2	384.5	384.9	385.2	385.2	384.8	384.3	383.8	383.3	383.3
120°	413.6	414.6	415.7	416.8	417.8	417.9	417.0	416.1	415.3	414.4	414.2
122.5°	444.6	445.4	446.1	446.9	447.7	447.8	447.3	446.9	446.5	446.0	445.5
125°	491.9	492.4	492.9	493.5	493.9	494.1	493.7	493.4	493.0	492.7	491.9
127.5°	535.5	536.6	537.7	538.8	540.0	540.3	540.0	539.6	539.2	538.8	537.8
130°	564.6	566.0	567.4	568.8	570.2	570.7	570.1	569.6	569.1	568.5	567.8
132.5°	593.7	595.1	596.5	597.9	599.4	599.8	599.4	599.0	598.7	598.3	597.5
135°	638.2	639.2	640.2	641.3	642.4	642.8	642.6	642.5	642.3	642.1	641.4
137.5°	679.3	680.2	681.0	681.9	682.8	683.4	683.9	684.4	684.8	685.2	684.5
140°	707.7	708.6	709.5	710.3	711.2	711.8	711.9	712.1	712.3	712.5	712.3
142.5°	733.6	734.5	735.5	736.3	737.2	737.8	738.1	738.4	738.7	739.0	738.9
145°	774.1	774.5	774.8	775.2	775.5	776.0	776.5	777.1	777.6	778.1	777.9
147.5°	809.6	810.2	810.9	811.5	812.1	812.7	813.2	813.7	814.1	814.7	814.7
150°	834.2	834.6	835.0	835.3	835.7	836.0	836.4	836.7	837.1	837.4	837.4
152.5°	854.5	855.0	855.5	856.0	856.4	856.8	857.1	857.2	857.5	857.7	857.9
155°	886.5	886.5	886.5	886.5	886.5	886.5	886.7	886.8	887.1	887.2	888.0
157.5°	913.6	913.5	913.2	913.0	912.8	912.8	912.9	913.1	913.2	913.3	914.1
160°	930.7	930.3	930.0	929.7	929.3	929.2	929.2	929.2	929.2	929.2	930.0
162.5°	945.9	945.4	944.9	944.4	944.0	943.8	943.9	944.0	944.2	944.4	945.2
165°	965.5	965.0	964.5	963.9	963.5	963.1	963.1	963.1	963.1	963.1	964.2
167.5°	981.2	980.5	979.8	979.1	978.3	978.1	978.3	978.3	978.5	978.7	979.8
170°	990.1	989.4	988.6	987.9	987.2	986.9	986.9	986.9	986.9	986.9	988.1
172.5°	997.0	996.3	995.6	994.9	994.2	993.8	993.8	993.8	993.8	993.8	994.9
175°	1004.2	1003.5	1002.8	1002.2	1001.5	1001.1	1001.1	1001.1	1001.1	1001.1	1002.2
177.5°	1007.3	1006.7	1006.2	1005.6	1005.0	1004.7	1004.7	1004.7	1004.7	1004.7	1005.6
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6



TEST NUMBER: P332292-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2
2.5°	745.3	746.5	747.7	748.1	747.9	747.7	747.5	747.3
5°	740.3	741.6	742.8	743.2	743.0	742.7	742.4	742.1
7.5°	729.9	730.6	731.3	731.3	730.9	730.5	730.0	729.5
10°	720.6	720.7	720.8	720.6	719.9	719.2	718.6	717.9
12.5°	709.0	708.9	708.8	708.4	707.6	706.8	706.1	705.3
15°	688.6	687.9	687.3	686.4	685.5	684.6	683.7	682.7
17.5°	664.3	662.9	661.4	660.0	658.6	657.2	655.8	654.4
20°	647.6	645.9	644.1	642.5	640.8	639.2	637.5	636.0
22.5°	629.8	627.6	625.4	623.5	622.0	620.5	619.0	617.5
25°	600.6	597.7	594.9	592.7	591.3	589.8	588.3	586.8
27.5°	568.7	564.8	560.9	557.8	555.5	553.3	551.0	548.7
30°	546.1	541.5	536.9	533.5	531.4	529.3	527.0	524.9
32.5°	523.9	518.8	513.8	510.2	507.9	505.6	503.4	501.1
35°	490.8	485.1	479.3	475.2	472.7	470.3	467.9	465.4
37.5°	455.4	448.9	442.3	437.5	434.5	431.5	428.5	425.5
40°	430.8	423.7	416.8	411.7	408.6	405.5	402.4	399.3
42.5°	407.2	399.5	391.8	386.6	383.8	381.0	378.3	375.5
45°	372.4	364.7	357.0	351.6	348.3	345.1	341.8	338.6
47.5°	336.4	328.1	319.7	314.1	311.2	308.3	305.5	302.5
50°	312.2	303.8	295.5	289.7	286.6	283.5	280.4	277.3
52.5°	288.8	280.0	271.3	265.6	262.8	260.1	257.3	254.5
55°	253.8	246.0	238.1	232.9	230.2	227.5	224.8	222.1
57.5°	219.4	212.1	204.7	199.9	197.6	195.3	193.0	190.7
60°	197.8	190.5	183.2	178.5	176.2	173.9	171.6	169.3
62.5°	176.3	169.5	162.6	158.0	155.7	153.2	150.8	148.5
65°	145.8	139.2	132.5	128.5	127.1	125.6	124.1	122.6
67.5°	116.6	111.6	106.7	103.5	101.9	100.3	98.7	97.1
70°	98.5	93.9	89.1	86.0	84.5	83.1	81.6	80.1
72.5°	82.3	78.5	74.6	72.4	71.8	71.1	70.5	69.9
75°	61.6	60.3	58.9	58.1	57.8	57.6	57.3	57.0
77.5°	46.5	45.8	45.0	44.5	44.3	44.0	43.7	43.4
80°	37.4	37.0	36.6	36.3	36.0	35.7	35.5	35.2
82.5°	28.7	28.3	27.9	27.6	27.6	27.6	27.5	27.4
85°	16.5	16.2	15.9	15.8	15.8	15.8	15.8	15.8
87.5°	10.1	10.2	10.2	10.2	10.2	10.1	10.1	10.1
90°	20.4	21.1	21.8	22.3	22.7	23.1	23.4	23.7
92.5°	31.5	32.1	32.6	32.8	32.6	32.4	32.2	31.9
95°	59.9	60.6	61.3	61.7	61.7	61.7	61.7	61.7
97.5°	93.2	94.0	94.8	95.1	95.1	95.1	95.0	94.9
100°	117.3	117.8	118.4	118.8	119.1	119.5	119.9	120.2
102.5°	145.1	145.7	146.2	146.4	146.3	146.2	146.2	146.2
105°	186.6	186.6	186.6	186.8	187.1	187.5	187.8	188.2
107.5°	231.6	232.1	232.7	232.8	232.7	232.4	232.2	232.0
110°	261.6	262.3	263.0	263.2	262.8	262.4	262.1	261.7





TEST NUMBER: P332292-927

CATALOG NUMBER: S123RDIP-S560D1025U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	291.6	292.4	293.3	293.7	293.6	293.5	293.4	293.3
115°	337.2	337.4	337.5	337.5	337.4	337.2	337.1	336.8
117.5°	383.3	383.3	383.3	382.9	382.5	382.0	381.5	381.0
120°	414.0	413.8	413.7	413.4	413.0	412.7	412.3	412.0
122.5°	445.0	444.7	444.2	443.7	443.2	442.7	442.2	441.7
125°	491.2	490.5	489.8	489.1	488.5	487.7	487.0	486.3
127.5°	536.9	535.9	534.9	534.0	533.2	532.3	531.6	530.8
130°	567.1	566.4	565.8	564.7	563.6	562.3	561.1	559.8
132.5°	596.6	595.8	594.9	594.1	593.1	592.2	591.2	590.3
135°	640.7	640.0	639.3	638.7	638.4	638.0	637.7	637.4
137.5°	683.8	683.1	682.3	681.6	681.0	680.2	679.6	679.0
140°	712.1	711.9	711.8	711.1	709.9	708.6	707.4	706.2
142.5°	738.7	738.6	738.3	737.8	736.8	735.9	734.9	734.0
145°	777.8	777.6	777.4	777.0	776.3	775.5	774.8	774.1
147.5°	814.7	814.7	814.7	814.1	813.1	812.0	811.0	809.9
150°	837.4	837.4	837.4	836.9	835.8	834.8	833.7	832.7
152.5°	858.3	858.5	858.8	858.5	857.5	856.7	855.7	854.8
155°	888.7	889.4	890.0	889.8	888.6	887.3	886.1	884.9
157.5°	914.8	915.5	916.3	916.2	915.2	914.2	913.2	912.2
160°	930.9	931.8	932.6	932.7	932.1	931.4	930.7	929.9
162.5°	946.1	947.0	947.8	947.7	946.6	945.5	944.4	943.3
165°	965.3	966.3	967.3	967.3	966.1	964.8	963.6	962.3
167.5°	980.8	981.9	983.0	983.0	981.9	980.8	979.8	978.7
170°	989.4	990.5	991.8	991.8	990.5	989.4	988.1	986.9
172.5°	996.0	997.1	998.1	998.1	996.9	995.7	994.4	993.2
175°	1003.2	1004.2	1005.4	1005.2	1004.0	1002.7	1001.6	1000.3
177.5°	1006.5	1007.3	1008.1	1008.1	1007.1	1006.1	1005.1	1004.1
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6

(END OF REPORT)