

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332298-927

Luminaire Tested: **S123RDIP-S560D1195U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332298-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D1195U927-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4940.1 lumens
Efficiency: N/A
Efficacy: 100.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332298-927

CATALOG NUMBER: S123RDIP-S560D1195U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332298-927

CATALOG NUMBER: S123RDIP-S560D1195U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42	34
1	94	90	87	83	85	82	79	76	66	63	62	51	49	48	37	36	36	29
2	86	79	73	68	78	72	67	62	58	54	51	45	43	41	33	32	30	25
3	79	70	63	57	71	63	57	52	51	47	43	40	37	34	29	28	26	21
4	72	62	54	48	65	56	50	44	45	41	37	36	32	30	26	24	23	18
5	66	55	47	41	60	50	43	38	41	36	32	32	28	26	24	22	20	16
6	61	49	41	36	55	45	38	33	37	32	28	29	25	23	22	19	17	14
7	56	44	37	31	51	41	34	29	33	28	24	26	23	20	20	17	16	13
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14	11
9	48	37	29	25	44	34	27	23	28	23	19	22	19	16	17	14	13	10
10	45	34	27	22	41	31	25	20	25	21	17	20	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8054	8054	8054
5°	8084	7973	8018
10°	8039	7873	7847
15°	7952	7689	7608
20°	7834	7458	7285
25°	7712	7201	6969
30°	7549	6901	6524
35°	7384	6603	6116
40°	7231	6250	5611
45°	7030	5903	5154
50°	6807	5508	4644
55°	6583	5056	4168
60°	6374	4573	3645
65°	6105	4050	3123
70°	5766	3402	2521
75°	5273	2674	2371
80°	4705	2374	2182
85°	3977	2100	1951



TEST NUMBER: P332298-927

CATALOG NUMBER: S123RDIP-S560D1195U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.3	1.4
10°-20°	195.5	4.0
20°-30°	281.5	5.7
30°-40°	317.1	6.4
40°-50°	303.3	6.1
50°-60°	248.4	5.0
60°-70°	167.6	3.4
70°-80°	84.3	1.7
80°-90°	25.8	0.5
90°-100°	76.3	1.5
100°-110°	228.5	4.6
110°-120°	388.6	7.9
120°-130°	511.1	10.3
130°-140°	574.5	11.6
140°-150°	564.7	11.4
150°-160°	475.4	9.6
160°-170°	316.5	6.4
170°-180°	110.8	2.2
0°-30°	547.2	11.1
0°-40°	864.3	17.5
0°-60°	1416.1	28.7
0°-90°	1693.8	34.3
90°-120°	693.4	14.0
90°-150°	2343.7	47.4
90°-180°	3246.0	65.7
0°-180°	4940.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	748	748	748	748	748	
5°	748	745	738	743	742	71
15°	714	706	690	687	683	201
25°	649	633	606	594	587	298
35°	562	539	502	477	465	352
45°	462	433	388	354	339	356
55°	351	320	269	236	222	314
65°	240	206	159	130	123	237
75°	127	97	64	58	57	135
85°	32	19	17	16	16	36
90°	1	10	22	26	28	5
95°	54	61	68	72	72	61
105°	207	209	217	217	219	222
115°	391	394	392	393	392	387
125°	572	575	574	570	566	510
135°	743	748	747	744	742	572
145°	901	903	906	905	901	563
155°	1032	1032	1033	1036	1030	475
165°	1124	1121	1121	1126	1120	317
175°	1169	1165	1165	1170	1164	111
180°	1172	1172	1172	1172	1172	



TEST NUMBER: P332298-927

CATALOG NUMBER: S123RDIP-S560D1195U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2
2.5°	750.7	750.2	749.8	749.3	748.9	748.1	746.8	745.4	744.2	742.9	744.1
5°	748.2	747.6	746.9	746.2	745.5	744.4	742.8	741.2	739.5	737.9	739.1
7.5°	741.3	740.6	739.8	739.1	738.4	737.0	734.9	732.8	730.6	728.6	729.2
10°	735.5	734.5	733.6	732.6	731.7	730.0	727.6	725.2	722.7	720.3	720.4
12.5°	727.2	726.2	725.1	724.1	723.0	721.0	718.0	715.1	712.1	709.2	709.1
15°	713.6	712.2	710.7	709.2	707.7	705.0	701.3	697.5	693.7	690.0	689.3
17.5°	696.5	694.8	693.1	691.3	689.6	686.3	681.5	676.8	671.9	667.2	665.7
20°	683.9	681.8	679.6	677.4	675.3	671.6	666.5	661.4	656.2	651.1	649.4
22.5°	669.8	667.3	664.9	662.3	659.9	655.9	650.5	645.0	639.6	634.1	631.9
25°	649.3	645.9	642.5	639.2	635.8	631.1	624.8	618.6	612.4	606.3	603.4
27.5°	624.4	620.7	617.0	613.2	609.5	604.2	597.3	590.4	583.5	576.6	572.7
30°	607.4	603.4	599.4	595.3	591.3	585.4	577.9	570.4	562.8	555.2	550.6
32.5°	590.4	585.9	581.3	576.7	572.1	565.9	557.9	549.9	541.9	533.9	528.9
35°	561.9	557.1	552.2	547.4	542.5	535.9	527.5	519.2	510.8	502.5	496.6
37.5°	533.1	527.7	522.3	516.8	511.4	504.3	495.4	486.5	477.5	468.6	462.0
40°	514.6	508.7	502.7	496.8	490.8	483.1	473.6	464.0	454.4	444.8	437.8
42.5°	493.7	487.7	481.9	475.9	470.0	462.1	452.2	442.3	432.4	422.5	414.8
45°	461.8	455.7	449.6	443.6	437.5	429.3	418.9	408.5	398.2	387.8	380.1
47.5°	429.8	423.2	416.5	409.9	403.2	394.7	384.3	373.9	363.5	353.2	344.8
50°	406.5	400.2	393.9	387.5	381.2	372.6	361.6	350.8	339.8	328.9	320.5
52.5°	385.7	378.8	371.9	365.0	358.2	349.4	338.5	327.7	316.9	306.1	297.4
55°	350.8	344.1	337.5	330.9	324.3	315.3	303.8	292.4	280.9	269.4	261.6
57.5°	318.5	311.2	304.0	296.8	289.6	280.3	268.8	257.3	245.7	234.2	226.9
60°	296.1	288.8	281.3	273.9	266.5	257.1	246.0	234.8	223.6	212.4	205.1
62.5°	273.8	266.4	259.0	251.5	244.2	234.8	223.6	212.5	201.2	190.0	183.2
65°	239.7	232.3	224.9	217.5	210.0	201.1	190.5	180.1	169.5	159.0	152.4
67.5°	205.6	198.1	190.6	183.1	175.6	166.8	156.7	146.6	136.6	126.4	121.5
70°	183.2	175.9	168.7	161.4	154.2	145.8	136.3	126.9	117.5	108.1	103.3
72.5°	160.9	153.8	146.6	139.4	132.2	124.4	115.8	107.2	98.6	90.1	86.2
75°	126.8	120.3	113.9	107.4	100.9	94.0	86.6	79.1	71.8	64.3	63.0
77.5°	95.8	89.9	84.1	78.2	72.3	67.0	62.3	57.5	52.7	47.9	47.2
80°	75.9	70.3	64.8	59.3	53.7	49.6	46.7	43.9	41.0	38.3	37.8
82.5°	57.0	52.1	47.4	42.6	37.8	34.8	33.4	32.2	30.8	29.5	29.1
85°	32.2	29.2	26.2	23.3	20.3	18.6	18.2	17.8	17.4	17.0	16.7
87.5°	11.8	11.1	10.3	9.5	8.7	8.6	9.1	9.7	10.2	10.7	10.8
90°	1.0	2.9	5.0	7.1	9.1	11.5	14.1	16.8	19.4	22.1	22.9
92.5°	22.3	23.7	25.0	26.5	27.8	29.3	30.8	32.3	33.8	35.3	36.0
95°	54.3	55.8	57.2	58.6	60.0	61.6	63.2	64.8	66.5	68.1	68.9
97.5°	96.5	97.5	98.6	99.7	100.7	101.9	103.1	104.3	105.4	106.5	107.5
100°	125.2	126.4	127.6	128.9	130.1	131.2	132.2	133.2	134.3	135.3	135.9
102.5°	158.3	159.1	159.8	160.5	161.3	162.3	163.7	165.0	166.4	167.7	168.3
105°	207.1	207.5	207.9	208.3	208.7	209.8	211.7	213.6	215.4	217.2	217.2
107.5°	263.8	264.0	264.3	264.5	264.7	265.3	266.0	266.7	267.4	268.2	268.9
110°	299.1	299.5	299.9	300.4	300.8	301.2	301.6	302.0	302.4	302.9	303.6



TEST NUMBER: P332298-927

CATALOG NUMBER: S123RDIP-S560D1195U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	336.0	336.2	336.4	336.7	336.9	337.1	337.2	337.2	337.3	337.4	338.4
115°	391.2	391.8	392.4	393.0	393.6	393.7	393.3	392.9	392.5	392.1	392.3
117.5°	446.8	447.2	447.6	448.0	448.4	448.4	447.8	447.3	446.8	446.2	446.2
120°	481.4	482.6	483.9	485.1	486.3	486.4	485.4	484.3	483.3	482.3	482.1
122.5°	517.5	518.3	519.3	520.1	521.1	521.3	520.7	520.1	519.7	519.1	518.6
125°	572.5	573.1	573.7	574.3	575.0	575.0	574.6	574.3	573.9	573.5	572.6
127.5°	623.3	624.6	625.9	627.2	628.5	629.0	628.5	628.0	627.6	627.2	626.1
130°	657.2	658.8	660.4	662.1	663.7	664.2	663.6	663.0	662.4	661.8	661.0
132.5°	691.0	692.7	694.3	695.9	697.6	698.2	697.8	697.3	696.8	696.4	695.4
135°	742.8	744.0	745.2	746.5	747.7	748.2	748.0	747.8	747.6	747.3	746.6
137.5°	790.7	791.6	792.7	793.7	794.7	795.5	796.1	796.5	797.1	797.6	796.8
140°	823.8	824.8	825.9	826.9	827.8	828.5	828.7	828.9	829.1	829.3	829.1
142.5°	854.0	855.0	856.0	857.1	858.1	858.7	859.1	859.5	859.8	860.2	860.0
145°	901.1	901.5	901.9	902.3	902.7	903.2	903.9	904.4	905.1	905.7	905.5
147.5°	942.3	943.1	943.8	944.5	945.3	945.9	946.5	947.1	947.6	948.2	948.2
150°	971.1	971.5	971.8	972.2	972.7	973.1	973.5	973.9	974.3	974.7	974.7
152.5°	994.6	995.2	995.8	996.3	996.9	997.3	997.5	997.8	998.1	998.3	998.6
155°	1031.8	1031.8	1031.8	1031.8	1031.8	1031.9	1032.1	1032.3	1032.5	1032.7	1033.6
157.5°	1063.4	1063.2	1063.0	1062.7	1062.5	1062.4	1062.6	1062.8	1063.0	1063.1	1064.0
160°	1083.3	1082.9	1082.5	1082.1	1081.7	1081.5	1081.5	1081.5	1081.5	1081.5	1082.5
162.5°	1101.0	1100.4	1099.9	1099.3	1098.8	1098.5	1098.7	1098.8	1099.0	1099.2	1100.2
165°	1123.9	1123.2	1122.6	1122.0	1121.4	1121.1	1121.1	1121.1	1121.1	1121.1	1122.3
167.5°	1142.1	1141.2	1140.4	1139.6	1138.8	1138.4	1138.6	1138.8	1138.9	1139.1	1140.3
170°	1152.4	1151.5	1150.7	1149.9	1149.1	1148.7	1148.7	1148.7	1148.7	1148.7	1150.1
172.5°	1160.5	1159.7	1158.8	1158.0	1157.2	1156.8	1156.8	1156.8	1156.8	1156.8	1158.1
175°	1168.9	1168.2	1167.3	1166.5	1165.7	1165.2	1165.2	1165.2	1165.2	1165.2	1166.5
177.5°	1172.4	1171.8	1171.2	1170.4	1169.8	1169.5	1169.5	1169.5	1169.5	1169.5	1170.4
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P332298-927

CATALOG NUMBER: S123RDIP-S560D1195U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2
2.5°	745.3	746.5	747.7	748.1	747.9	747.7	747.5	747.3
5°	740.3	741.6	742.8	743.2	743.0	742.7	742.4	742.1
7.5°	729.9	730.6	731.3	731.3	730.9	730.5	730.0	729.5
10°	720.6	720.7	720.8	720.6	719.9	719.2	718.6	717.9
12.5°	709.0	708.9	708.8	708.4	707.6	706.8	706.1	705.3
15°	688.6	687.9	687.3	686.4	685.5	684.6	683.7	682.7
17.5°	664.3	662.9	661.4	660.0	658.6	657.2	655.8	654.4
20°	647.6	645.9	644.1	642.5	640.8	639.2	637.5	636.0
22.5°	629.8	627.6	625.4	623.5	622.0	620.5	619.0	617.5
25°	600.6	597.7	594.9	592.7	591.3	589.8	588.3	586.8
27.5°	568.7	564.8	560.9	557.8	555.5	553.3	551.0	548.7
30°	546.1	541.5	536.9	533.5	531.4	529.3	527.0	524.9
32.5°	523.9	518.8	513.8	510.2	507.9	505.6	503.4	501.1
35°	490.8	485.1	479.3	475.2	472.7	470.3	467.9	465.4
37.5°	455.4	448.9	442.3	437.5	434.5	431.5	428.5	425.5
40°	430.8	423.7	416.8	411.7	408.6	405.5	402.4	399.3
42.5°	407.2	399.5	391.8	386.6	383.8	381.0	378.3	375.5
45°	372.4	364.7	357.0	351.6	348.3	345.1	341.8	338.6
47.5°	336.4	328.1	319.7	314.1	311.2	308.3	305.5	302.5
50°	312.2	303.8	295.5	289.7	286.6	283.5	280.4	277.3
52.5°	288.8	280.0	271.3	265.6	262.8	260.1	257.3	254.5
55°	253.8	246.0	238.1	232.9	230.2	227.5	224.8	222.1
57.5°	219.4	212.1	204.7	199.9	197.6	195.3	193.0	190.7
60°	197.8	190.5	183.2	178.5	176.2	173.9	171.6	169.3
62.5°	176.3	169.5	162.6	158.0	155.7	153.2	150.8	148.5
65°	145.8	139.2	132.5	128.5	127.1	125.6	124.1	122.6
67.5°	116.6	111.6	106.7	103.5	101.9	100.3	98.7	97.1
70°	98.5	93.9	89.1	86.0	84.5	83.1	81.6	80.1
72.5°	82.3	78.5	74.6	72.4	71.8	71.1	70.5	69.9
75°	61.6	60.3	58.9	58.1	57.8	57.6	57.3	57.0
77.5°	46.5	45.8	45.0	44.5	44.3	44.0	43.7	43.4
80°	37.4	37.0	36.6	36.3	36.0	35.7	35.5	35.2
82.5°	28.7	28.3	27.9	27.6	27.6	27.6	27.5	27.4
85°	16.5	16.2	15.9	15.8	15.8	15.8	15.8	15.8
87.5°	10.9	10.9	10.9	10.9	10.9	10.9	10.9	10.9
90°	23.8	24.6	25.3	26.0	26.4	26.8	27.2	27.6
92.5°	36.7	37.3	37.9	38.2	37.9	37.7	37.4	37.2
95°	69.7	70.6	71.4	71.8	71.8	71.8	71.8	71.8
97.5°	108.4	109.4	110.4	110.7	110.7	110.6	110.5	110.4
100°	136.5	137.1	137.8	138.2	138.7	139.1	139.5	139.9
102.5°	168.9	169.5	170.2	170.4	170.3	170.2	170.2	170.1
105°	217.2	217.2	217.2	217.5	217.9	218.2	218.6	219.0
107.5°	269.5	270.2	270.8	271.0	270.8	270.5	270.3	270.1
110°	304.4	305.3	306.1	306.3	305.9	305.5	305.1	304.7



TEST NUMBER: P332298-927

CATALOG NUMBER: S123RDIP-S560D1195U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	339.4	340.4	341.4	341.8	341.7	341.7	341.6	341.5
115°	392.5	392.7	392.9	392.9	392.7	392.5	392.3	392.1
117.5°	446.2	446.1	446.1	445.8	445.2	444.6	444.0	443.5
120°	481.9	481.7	481.5	481.2	480.8	480.4	480.0	479.5
122.5°	518.1	517.5	517.0	516.4	515.9	515.3	514.7	514.1
125°	571.8	571.0	570.1	569.3	568.5	567.7	566.9	566.1
127.5°	624.9	623.8	622.6	621.5	620.6	619.6	618.7	617.8
130°	660.1	659.3	658.5	657.4	655.9	654.5	653.1	651.6
132.5°	694.4	693.5	692.4	691.4	690.3	689.2	688.1	687.0
135°	745.8	744.9	744.1	743.5	743.1	742.7	742.3	741.9
137.5°	795.9	795.0	794.2	793.4	792.6	791.9	791.1	790.3
140°	828.9	828.7	828.5	827.7	826.2	824.8	823.4	822.0
142.5°	859.8	859.6	859.4	858.7	857.6	856.5	855.5	854.4
145°	905.3	905.1	904.9	904.4	903.6	902.7	901.9	901.1
147.5°	948.2	948.2	948.2	947.6	946.3	945.2	943.9	942.7
150°	974.7	974.7	974.7	974.1	972.9	971.7	970.4	969.2
152.5°	998.9	999.3	999.6	999.3	998.1	997.1	996.0	995.0
155°	1034.4	1035.1	1036.0	1035.7	1034.3	1032.8	1031.4	1029.9
157.5°	1064.8	1065.6	1066.5	1066.4	1065.2	1064.1	1063.0	1061.8
160°	1083.5	1084.6	1085.6	1085.7	1084.9	1084.0	1083.2	1082.4
162.5°	1101.2	1102.2	1103.3	1103.1	1101.8	1100.5	1099.2	1097.9
165°	1123.6	1124.7	1126.0	1125.8	1124.4	1123.0	1121.6	1120.1
167.5°	1141.6	1142.9	1144.1	1144.1	1142.9	1141.6	1140.3	1139.1
170°	1151.5	1153.0	1154.4	1154.4	1153.0	1151.5	1150.1	1148.7
172.5°	1159.4	1160.6	1161.9	1161.8	1160.3	1158.9	1157.5	1156.0
175°	1167.7	1168.9	1170.1	1170.1	1168.6	1167.2	1165.8	1164.3
177.5°	1171.5	1172.4	1173.4	1173.3	1172.2	1171.0	1169.9	1168.8
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7

(END OF REPORT)