

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332275-927

Luminaire Tested: **S123RDIP-S560D365U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332275-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S560D365U927-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2731.8 lumens  
Efficiency: N/A  
Efficacy: 99.3 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332275-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332275-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	97	93	89	94	91	87	84	80	77	75	69	68	66	60	59	57	53
2	92	85	79	74	86	80	74	70	70	66	63	61	58	56	53	51	49	45
3	84	75	68	62	79	71	64	59	62	57	53	55	51	48	48	45	42	39
4	77	67	59	53	72	63	56	50	56	50	46	49	45	41	43	39	37	33
5	71	60	51	46	67	56	49	44	50	44	40	44	39	36	39	35	32	29
6	66	54	46	40	61	51	43	38	45	39	35	40	35	32	35	31	29	26
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	32	28	25	23
8	57	44	37	31	53	42	35	30	38	32	28	34	29	25	30	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	27	24	21	19
10	49	37	30	25	46	36	29	24	32	26	23	29	24	21	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8054	8054	8054
5°	8084	7973	8018
10°	8039	7873	7847
15°	7952	7689	7608
20°	7834	7458	7285
25°	7712	7201	6969
30°	7549	6901	6524
35°	7384	6603	6116
40°	7231	6250	5611
45°	7030	5903	5154
50°	6807	5508	4644
55°	6583	5056	4168
60°	6374	4573	3645
65°	6105	4050	3123
70°	5766	3402	2521
75°	5273	2674	2371
80°	4705	2374	2182
85°	3977	2100	1951



TEST NUMBER: P332275-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	70.3	2.6
10°-20°	195.5	7.2
20°-30°	281.5	10.3
30°-40°	317.1	11.6
40°-50°	303.3	11.1
50°-60°	248.4	9.1
60°-70°	167.6	6.1
70°-80°	84.3	3.1
80°-90°	23.4	0.9
90°-100°	77.0	2.8
100°-110°	217.9	8.0
110°-120°	214.4	7.8
120°-130°	171.0	6.3
130°-140°	134.8	4.9
140°-150°	100.6	3.7
150°-160°	70.1	2.6
160°-170°	41.2	1.5
170°-180°	13.4	0.5
0°-30°	547.2	20.0
0°-40°	864.3	31.6
0°-60°	1416.1	51.8
0°-90°	1691.4	61.9
90°-120°	509.3	18.6
90°-150°	915.7	33.5
90°-180°	1040.0	38.1
0°-180°	2731.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	748	748	748	748	748	
5°	748	745	738	743	742	71
15°	714	706	690	687	683	201
25°	649	633	606	594	587	298
35°	562	539	502	477	465	352
45°	462	433	388	354	339	356
55°	351	320	269	236	222	314
65°	240	206	159	130	123	237
75°	127	97	64	58	57	135
85°	32	19	17	16	16	36
90°	1	3	7	8	8	2
95°	10	31	166	48	32	10
105°	32	48	225	394	356	35
115°	57	72	172	378	433	57
125°	80	94	161	291	342	71
135°	94	112	158	240	277	72
145°	107	122	156	197	216	67
155°	121	131	152	172	179	56
165°	132	136	145	154	156	37
175°	138	138	139	141	141	13
180°	138	138	138	138	138	



TEST NUMBER: P332275-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2
2.5°	750.7	750.2	749.8	749.3	748.9	748.1	746.8	745.4	744.2	742.9	744.1
5°	748.2	747.6	746.9	746.2	745.5	744.4	742.8	741.2	739.5	737.9	739.1
7.5°	741.3	740.6	739.8	739.1	738.4	737.0	734.9	732.8	730.6	728.6	729.2
10°	735.5	734.5	733.6	732.6	731.7	730.0	727.6	725.2	722.7	720.3	720.4
12.5°	727.2	726.2	725.1	724.1	723.0	721.0	718.0	715.1	712.1	709.2	709.1
15°	713.6	712.2	710.7	709.2	707.7	705.0	701.3	697.5	693.7	690.0	689.3
17.5°	696.5	694.8	693.1	691.3	689.6	686.3	681.5	676.8	671.9	667.2	665.7
20°	683.9	681.8	679.6	677.4	675.3	671.6	666.5	661.4	656.2	651.1	649.4
22.5°	669.8	667.3	664.9	662.3	659.9	655.9	650.5	645.0	639.6	634.1	631.9
25°	649.3	645.9	642.5	639.2	635.8	631.1	624.8	618.6	612.4	606.3	603.4
27.5°	624.4	620.7	617.0	613.2	609.5	604.2	597.3	590.4	583.5	576.6	572.7
30°	607.4	603.4	599.4	595.3	591.3	585.4	577.9	570.4	562.8	555.2	550.6
32.5°	590.4	585.9	581.3	576.7	572.1	565.9	557.9	549.9	541.9	533.9	528.9
35°	561.9	557.1	552.2	547.4	542.5	535.9	527.5	519.2	510.8	502.5	496.6
37.5°	533.1	527.7	522.3	516.8	511.4	504.3	495.4	486.5	477.5	468.6	462.0
40°	514.6	508.7	502.7	496.8	490.8	483.1	473.6	464.0	454.4	444.8	437.8
42.5°	493.7	487.7	481.9	475.9	470.0	462.1	452.2	442.3	432.4	422.5	414.8
45°	461.8	455.7	449.6	443.6	437.5	429.3	418.9	408.5	398.2	387.8	380.1
47.5°	429.8	423.2	416.5	409.9	403.2	394.7	384.3	373.9	363.5	353.2	344.8
50°	406.5	400.2	393.9	387.5	381.2	372.6	361.6	350.8	339.8	328.9	320.5
52.5°	385.7	378.8	371.9	365.0	358.2	349.4	338.5	327.7	316.9	306.1	297.4
55°	350.8	344.1	337.5	330.9	324.3	315.3	303.8	292.4	280.9	269.4	261.6
57.5°	318.5	311.2	304.0	296.8	289.6	280.3	268.8	257.3	245.7	234.2	226.9
60°	296.1	288.8	281.3	273.9	266.5	257.1	246.0	234.8	223.6	212.4	205.1
62.5°	273.8	266.4	259.0	251.5	244.2	234.8	223.6	212.5	201.2	190.0	183.2
65°	239.7	232.3	224.9	217.5	210.0	201.1	190.5	180.1	169.5	159.0	152.4
67.5°	205.6	198.1	190.6	183.1	175.6	166.8	156.7	146.6	136.6	126.4	121.5
70°	183.2	175.9	168.7	161.4	154.2	145.8	136.3	126.9	117.5	108.1	103.3
72.5°	160.9	153.8	146.6	139.4	132.2	124.4	115.8	107.2	98.6	90.1	86.2
75°	126.8	120.3	113.9	107.4	100.9	94.0	86.6	79.1	71.8	64.3	63.0
77.5°	95.8	89.9	84.1	78.2	72.3	67.0	62.3	57.5	52.7	47.9	47.2
80°	75.9	70.3	64.8	59.3	53.7	49.6	46.7	43.9	41.0	38.3	37.8
82.5°	57.0	52.1	47.4	42.6	37.8	34.8	33.4	32.2	30.8	29.5	29.1
85°	32.2	29.2	26.2	23.3	20.3	18.6	18.2	17.8	17.4	17.0	16.7
87.5°	11.7	10.7	9.6	8.6	7.5	7.1	7.2	7.4	7.5	7.7	7.5
90°	0.6	1.1	1.7	2.5	3.1	3.6	4.5	5.3	6.2	7.0	6.7
92.5°	3.5	5.1	7.5	9.7	12.0	16.2	23.5	35.6	47.4	43.0	32.5
95°	9.5	10.4	13.5	18.2	25.5	36.4	60.2	101.9	147.8	166.0	134.7
97.5°	16.2	16.5	18.9	23.1	30.3	42.1	64.8	111.8	188.4	257.3	275.2
100°	20.8	21.0	23.0	26.9	33.6	44.5	64.1	105.5	179.2	265.1	320.3
102.5°	25.4	25.9	27.6	31.4	37.4	47.5	65.0	100.1	165.7	250.6	322.5
105°	32.5	33.4	35.0	38.3	43.6	52.4	67.5	96.3	149.2	225.1	305.4
107.5°	40.0	40.8	42.5	45.7	50.7	58.8	72.1	96.0	138.7	202.6	275.5
110°	45.3	46.2	47.6	50.7	55.5	63.3	75.9	97.1	134.7	189.8	256.7



TEST NUMBER: P332275-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	50.3	51.1	52.5	55.6	60.4	68.0	79.7	99.4	132.4	181.3	240.3
115°	57.4	58.5	60.2	63.0	67.7	75.3	86.0	103.0	131.6	172.1	220.6
117.5°	64.5	65.8	67.2	69.8	75.1	82.1	92.6	107.8	132.1	166.8	208.7
120°	69.4	70.3	71.7	74.5	79.8	86.7	96.9	111.4	133.0	164.3	202.4
122.5°	73.7	74.5	75.9	79.0	84.1	91.5	101.3	114.8	134.5	162.8	197.3
125°	79.8	80.3	82.0	85.1	90.4	98.0	107.8	120.1	136.9	160.7	190.7
127.5°	84.4	85.2	87.4	90.5	96.3	103.9	113.4	124.5	139.6	159.7	184.8
130°	87.4	88.2	90.7	94.0	100.0	107.5	116.8	127.4	141.4	159.0	181.6
132.5°	89.6	90.6	93.4	97.4	103.3	110.7	119.6	130.1	142.8	158.8	178.8
135°	93.5	94.6	97.7	101.9	107.8	115.3	124.0	133.6	144.7	158.4	175.0
137.5°	97.2	98.4	101.4	105.8	111.7	118.7	127.1	136.1	146.1	157.8	171.7
140°	99.7	101.1	103.9	108.4	113.9	121.0	129.0	137.4	146.9	157.6	169.6
142.5°	102.3	103.5	106.5	110.6	116.2	122.7	130.6	138.8	147.7	157.2	167.9
145°	106.6	107.5	110.0	114.2	119.0	125.4	132.7	140.2	148.1	156.5	165.4
147.5°	111.1	111.5	114.0	117.6	122.2	127.7	134.4	141.2	148.1	155.4	163.1
150°	113.9	114.2	116.5	120.1	124.0	129.0	135.5	141.4	148.1	154.6	161.5
152.5°	116.8	116.9	119.1	122.3	125.8	130.6	136.2	141.8	147.4	153.4	159.7
155°	121.2	121.2	122.9	125.7	128.8	132.7	137.4	142.0	146.7	151.5	157.0
157.5°	124.7	124.9	126.3	128.7	131.3	134.4	138.2	142.2	145.8	149.7	154.0
160°	127.4	127.4	128.5	130.7	132.7	135.5	138.9	142.2	145.3	148.4	152.0
162.5°	129.4	129.4	130.3	132.1	133.8	136.2	139.1	142.0	144.4	147.0	150.0
165°	132.4	132.1	132.7	134.1	135.2	137.2	139.4	141.4	143.1	145.0	147.3
167.5°	134.7	134.4	134.7	135.7	136.5	137.8	139.3	140.9	141.7	143.0	144.7
170°	136.0	135.5	135.8	136.6	137.2	137.8	139.1	140.2	140.9	141.6	143.1
172.5°	137.0	136.6	136.7	137.3	137.6	137.9	139.1	140.1	140.1	140.5	141.5
175°	138.0	137.8	137.4	138.0	138.0	138.3	138.9	139.4	139.1	139.1	139.7
177.5°	138.6	138.3	138.1	138.3	138.3	138.3	138.6	138.9	138.6	138.3	138.6
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3



TEST NUMBER: P332275-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2
2.5°	745.3	746.5	747.7	748.1	747.9	747.7	747.5	747.3
5°	740.3	741.6	742.8	743.2	743.0	742.7	742.4	742.1
7.5°	729.9	730.6	731.3	731.3	730.9	730.5	730.0	729.5
10°	720.6	720.7	720.8	720.6	719.9	719.2	718.6	717.9
12.5°	709.0	708.9	708.8	708.4	707.6	706.8	706.1	705.3
15°	688.6	687.9	687.3	686.4	685.5	684.6	683.7	682.7
17.5°	664.3	662.9	661.4	660.0	658.6	657.2	655.8	654.4
20°	647.6	645.9	644.1	642.5	640.8	639.2	637.5	636.0
22.5°	629.8	627.6	625.4	623.5	622.0	620.5	619.0	617.5
25°	600.6	597.7	594.9	592.7	591.3	589.8	588.3	586.8
27.5°	568.7	564.8	560.9	557.8	555.5	553.3	551.0	548.7
30°	546.1	541.5	536.9	533.5	531.4	529.3	527.0	524.9
32.5°	523.9	518.8	513.8	510.2	507.9	505.6	503.4	501.1
35°	490.8	485.1	479.3	475.2	472.7	470.3	467.9	465.4
37.5°	455.4	448.9	442.3	437.5	434.5	431.5	428.5	425.5
40°	430.8	423.7	416.8	411.7	408.6	405.5	402.4	399.3
42.5°	407.2	399.5	391.8	386.6	383.8	381.0	378.3	375.5
45°	372.4	364.7	357.0	351.6	348.3	345.1	341.8	338.6
47.5°	336.4	328.1	319.7	314.1	311.2	308.3	305.5	302.5
50°	312.2	303.8	295.5	289.7	286.6	283.5	280.4	277.3
52.5°	288.8	280.0	271.3	265.6	262.8	260.1	257.3	254.5
55°	253.8	246.0	238.1	232.9	230.2	227.5	224.8	222.1
57.5°	219.4	212.1	204.7	199.9	197.6	195.3	193.0	190.7
60°	197.8	190.5	183.2	178.5	176.2	173.9	171.6	169.3
62.5°	176.3	169.5	162.6	158.0	155.7	153.2	150.8	148.5
65°	145.8	139.2	132.5	128.5	127.1	125.6	124.1	122.6
67.5°	116.6	111.6	106.7	103.5	101.9	100.3	98.7	97.1
70°	98.5	93.9	89.1	86.0	84.5	83.1	81.6	80.1
72.5°	82.3	78.5	74.6	72.4	71.8	71.1	70.5	69.9
75°	61.6	60.3	58.9	58.1	57.8	57.6	57.3	57.0
77.5°	46.5	45.8	45.0	44.5	44.3	44.0	43.7	43.4
80°	37.4	37.0	36.6	36.3	36.0	35.7	35.5	35.2
82.5°	28.7	28.3	27.9	27.6	27.6	27.6	27.5	27.4
85°	16.5	16.2	15.9	15.8	15.8	15.8	15.8	15.8
87.5°	7.5	7.4	7.4	7.4	7.2	7.2	7.1	7.0
90°	7.0	7.3	7.5	8.1	7.8	8.1	8.4	8.1
92.5°	23.6	18.7	16.5	15.1	14.6	13.7	14.0	13.5
95°	100.8	68.3	53.5	43.4	38.1	35.6	33.6	32.5
97.5°	251.2	201.2	165.1	131.7	111.0	98.4	90.8	88.4
100°	330.0	307.4	274.6	234.9	206.6	186.2	175.2	175.5
102.5°	356.2	355.5	336.4	311.2	289.2	273.1	264.0	257.5
105°	363.9	391.9	397.2	390.0	377.1	366.5	357.5	356.1
107.5°	341.8	387.3	411.9	421.8	422.1	418.4	415.4	412.9
110°	320.8	372.3	407.6	427.2	435.1	437.3	436.7	436.2





TEST NUMBER: P332275-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	300.0	352.6	392.1	417.3	431.7	438.6	440.8	440.8
115°	272.4	321.1	362.3	392.8	413.8	426.0	431.7	433.1
117.5°	252.4	294.5	331.4	362.3	384.3	398.4	406.4	408.3
120°	241.9	279.6	313.2	341.5	363.6	379.3	386.0	387.7
122.5°	233.6	267.8	298.9	325.2	344.8	358.9	366.3	368.4
125°	222.5	253.1	280.0	302.4	320.3	332.6	339.6	341.5
127.5°	212.9	240.1	264.4	284.8	300.7	311.2	317.6	319.3
130°	206.8	232.1	254.8	273.8	288.6	298.7	304.6	306.8
132.5°	201.3	224.4	245.6	263.7	277.7	287.7	292.9	294.5
135°	193.7	213.6	231.8	247.7	261.5	269.9	274.9	276.9
137.5°	186.8	203.1	218.8	232.7	244.2	252.7	256.9	258.3
140°	182.8	197.1	210.5	222.5	233.2	241.1	245.5	245.3
142.5°	179.0	191.2	202.9	213.3	222.4	229.4	233.4	233.1
145°	174.4	183.6	192.6	200.7	207.7	213.6	215.9	216.4
147.5°	170.6	178.0	185.2	191.0	196.3	200.3	202.4	202.6
150°	167.9	174.4	180.3	185.6	189.8	192.9	194.6	194.6
152.5°	165.5	171.0	176.3	180.7	183.9	186.8	187.8	187.8
155°	161.8	166.3	170.5	173.8	176.3	178.6	179.2	179.4
157.5°	157.9	161.6	164.9	167.5	169.7	171.3	171.8	171.7
160°	155.7	158.8	161.5	163.5	165.4	167.2	167.2	166.8
162.5°	153.0	155.6	158.2	159.9	161.2	162.6	162.6	162.4
165°	149.5	151.1	153.1	154.6	155.7	156.8	156.5	156.5
167.5°	146.5	147.7	148.9	149.9	150.4	151.1	150.9	150.9
170°	144.4	145.3	146.4	146.9	147.3	147.8	147.5	147.5
172.5°	142.7	143.3	144.2	144.5	144.6	145.1	144.7	144.4
175°	140.2	140.5	141.1	141.1	141.1	141.4	141.1	140.9
177.5°	138.7	138.9	139.2	139.2	138.9	139.2	138.7	138.7
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3

(END OF REPORT)