

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332069

Luminaire Tested: **S123DIP-S1165D805U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332069
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D805U835-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7968.9 lumens
Efficiency: N/A
Efficacy: 131.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332069

CATALOG NUMBER: S123DIP-S1165D805U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332069

CATALOG NUMBER: S123DIP-S1165D805U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	60
1	100	95	91	88	93	89	86	83	78	75	73	67	65	64	57	56	55	50
2	91	83	77	72	85	78	73	68	68	64	60	59	56	53	50	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	39	35
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	37	34	30
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	33	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	21
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	24	21	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	17
10	48	36	28	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19678	19678	19678
5°	19770	19498	19634
10°	19638	19329	19449
15°	19409	19110	19146
20°	19140	18798	18816
25°	18781	18427	18389
30°	18385	18013	17877
35°	17971	17578	17350
40°	17537	17096	16831
45°	17061	16653	16247
50°	16583	16109	15662
55°	15959	15546	15073
60°	15330	14889	14415
65°	14772	14174	13733
70°	13951	13357	12765
75°	12747	12289	11765
80°	11499	11009	10916
85°	10090	9707	9324



TEST NUMBER: P332069

CATALOG NUMBER: S123DIP-S1165D805U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.2	2.2
10°-20°	486.2	6.1
20°-30°	718.3	9.0
30°-40°	839.0	10.5
40°-50°	843.5	10.6
50°-60°	740.9	9.3
60°-70°	552.0	6.9
70°-80°	314.5	3.9
80°-90°	93.2	1.2
90°-100°	38.3	0.5
100°-110°	182.3	2.3
110°-120°	438.0	5.5
120°-130°	557.7	7.0
130°-140°	595.9	7.5
140°-150°	557.2	7.0
150°-160°	449.5	5.6
160°-170°	290.1	3.6
170°-180°	100.0	1.3
0°-30°	1376.7	17.3
0°-40°	2215.7	27.8
0°-60°	3800.2	47.7
0°-90°	4759.9	59.7
90°-120°	658.6	8.3
90°-150°	2369.4	29.7
90°-180°	3209.0	40.3
0°-180°	7968.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1828	1828	1828	1828	1828	
5°	1830	1821	1804	1819	1817	173
15°	1742	1735	1715	1726	1718	491
25°	1581	1571	1552	1553	1548	728
35°	1368	1358	1338	1328	1320	855
45°	1121	1114	1094	1076	1067	865
55°	850	848	828	812	803	761
65°	580	572	556	544	539	572
75°	306	300	296	288	283	328
85°	82	79	79	76	76	90
90°	1	9	19	22	24	7
95°	48	18	24	29	30	59
105°	233	237	171	41	34	247
115°	437	442	449	456	460	431
125°	616	622	625	627	629	550
135°	767	772	775	777	775	590
145°	885	890	892	894	894	554
155°	975	973	974	978	973	449
165°	1028	1026	1025	1031	1026	290
175°	1052	1049	1049	1054	1048	100
180°	1052	1052	1052	1052	1052	



TEST NUMBER: P332069

CATALOG NUMBER: S123DIP-S1165D805U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1
2.5°	1834.4	1833.3	1832.2	1831.1	1829.9	1827.8	1824.8	1821.7	1818.6	1815.5	1818.3
5°	1829.7	1828.0	1826.2	1824.5	1822.7	1819.9	1816.1	1812.2	1808.4	1804.5	1808.0
7.5°	1811.8	1810.0	1808.3	1806.5	1804.8	1801.9	1797.9	1794.0	1790.0	1786.0	1789.1
10°	1796.7	1794.9	1793.2	1791.4	1789.7	1786.6	1782.0	1777.5	1772.9	1768.4	1771.5
12.5°	1776.6	1775.1	1773.6	1772.2	1770.7	1767.8	1763.6	1759.3	1755.0	1750.8	1753.1
15°	1741.7	1740.3	1738.9	1737.5	1736.1	1733.1	1728.6	1724.0	1719.5	1714.9	1717.7
17.5°	1701.1	1699.3	1697.5	1695.7	1693.8	1690.7	1686.1	1681.6	1677.0	1672.5	1674.5
20°	1670.9	1668.8	1666.7	1664.6	1662.6	1659.2	1654.7	1650.2	1645.6	1641.1	1642.5
22.5°	1637.0	1634.9	1632.8	1630.7	1628.6	1625.3	1620.7	1616.2	1611.7	1607.1	1608.2
25°	1581.3	1579.2	1577.1	1575.0	1573.0	1569.6	1565.1	1560.6	1556.0	1551.5	1551.8
27.5°	1521.9	1519.9	1517.9	1515.8	1513.8	1510.4	1505.5	1500.6	1495.7	1490.8	1491.1
30°	1479.2	1477.4	1475.7	1473.9	1472.2	1468.9	1464.0	1459.1	1454.2	1449.3	1449.3
32.5°	1436.4	1434.1	1431.8	1429.5	1427.2	1424.1	1420.4	1416.6	1412.8	1409.1	1407.1
35°	1367.6	1365.5	1363.4	1361.3	1359.2	1355.9	1351.3	1346.8	1342.2	1337.7	1335.6
37.5°	1297.1	1294.5	1291.8	1289.2	1286.5	1282.9	1278.3	1273.7	1269.1	1264.4	1261.9
40°	1248.1	1246.0	1243.9	1241.8	1239.7	1236.2	1231.3	1226.4	1221.5	1216.7	1213.9
42.5°	1199.0	1196.7	1194.3	1191.9	1189.5	1185.9	1181.0	1176.1	1171.2	1166.4	1163.6
45°	1120.8	1119.4	1118.0	1116.6	1115.2	1112.2	1107.7	1103.1	1098.6	1094.0	1089.9
47.5°	1043.1	1041.1	1039.1	1037.0	1035.0	1031.9	1027.6	1023.3	1019.1	1014.8	1010.7
50°	990.3	988.6	986.8	985.1	983.3	980.2	975.6	971.1	966.5	962.0	958.2
52.5°	935.0	933.8	932.6	931.4	930.2	927.2	922.4	917.6	912.8	907.9	904.6
55°	850.4	850.1	849.7	849.4	849.0	846.6	842.0	837.5	832.9	828.4	824.6
57.5°	769.9	768.7	767.5	766.4	765.2	762.8	759.1	755.5	751.9	748.2	744.8
60°	712.1	711.7	711.4	711.0	710.7	708.4	704.2	700.0	695.8	691.6	688.5
62.5°	660.5	659.6	658.7	657.8	656.9	654.3	650.1	645.9	641.8	637.6	634.4
65°	580.0	578.3	576.5	574.8	573.0	570.4	566.9	563.4	559.9	556.5	553.7
67.5°	494.8	493.3	491.8	490.2	488.7	486.6	483.9	481.3	478.6	476.0	473.5
70°	443.3	441.2	439.1	437.0	434.9	432.8	430.7	428.6	426.5	424.4	422.0
72.5°	389.2	387.7	386.1	384.6	383.1	381.1	378.7	376.3	374.0	371.6	369.4
75°	306.5	305.1	303.7	302.3	300.9	299.7	298.7	297.6	296.6	295.5	293.8
77.5°	233.3	232.5	231.7	231.0	230.2	229.2	227.9	226.7	225.4	224.2	223.0
80°	185.5	184.4	183.4	182.3	181.3	180.4	179.7	179.0	178.3	177.6	177.3
82.5°	139.0	138.7	138.5	138.3	138.1	137.9	137.8	137.7	137.5	137.4	136.8
85°	81.7	81.0	80.3	79.6	78.9	78.6	78.6	78.6	78.6	78.6	77.9
87.5°	32.9	32.4	31.9	31.4	30.9	30.7	30.9	31.1	31.2	31.4	31.3
90°	0.8	2.5	4.3	6.0	7.7	9.7	12.0	14.2	16.5	18.8	19.5
92.5°	14.5	14.1	13.6	13.1	12.6	13.2	14.9	16.6	18.3	20.0	21.1
95°	47.7	40.6	33.4	26.3	19.2	16.6	18.5	20.4	22.3	24.2	25.5
97.5°	95.8	92.7	89.5	86.3	83.1	75.2	62.7	50.2	37.7	25.2	26.6
100°	132.1	135.6	139.1	142.5	146.0	134.2	107.1	80.0	52.9	25.8	27.2
102.5°	173.4	175.9	178.4	180.9	183.4	169.9	140.3	110.6	81.0	51.4	47.1
105°	233.0	234.9	236.8	238.7	240.6	233.8	218.1	202.5	186.8	171.2	140.5
107.5°	295.8	297.4	298.9	300.4	301.9	303.9	306.4	308.9	311.3	313.8	291.3
110°	337.7	339.1	340.5	341.9	343.3	344.9	346.9	348.8	350.7	352.6	346.9



TEST NUMBER: P332069

CATALOG NUMBER: S123DIP-S1165D805U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	377.8	379.0	380.3	381.5	382.8	384.3	386.3	388.2	390.1	392.0	392.1
115°	437.0	438.1	439.1	440.2	441.2	442.5	444.1	445.6	447.2	448.8	450.5
117.5°	494.4	495.7	497.0	498.3	499.5	500.6	501.4	502.2	503.0	503.8	505.2
120°	530.1	531.6	533.2	534.7	536.3	537.4	537.9	538.4	538.9	539.4	540.8
122.5°	566.3	567.6	568.9	570.2	571.5	572.4	573.1	573.8	574.4	575.1	576.1
125°	616.1	617.4	618.8	620.2	621.6	622.7	623.4	624.0	624.7	625.4	625.8
127.5°	664.2	665.6	667.0	668.4	669.8	670.9	671.7	672.6	673.4	674.2	674.8
130°	694.2	695.6	697.0	698.4	699.8	700.8	701.5	702.2	702.9	703.6	704.3
132.5°	723.0	724.4	725.8	727.2	728.6	729.5	730.1	730.6	731.2	731.8	732.5
135°	766.9	768.0	769.0	770.1	771.1	772.0	772.7	773.4	774.1	774.8	775.3
137.5°	804.5	805.8	807.1	808.4	809.7	810.6	811.0	811.4	811.7	812.1	813.0
140°	829.5	830.5	831.6	832.6	833.7	834.4	835.0	835.5	836.0	836.5	837.2
142.5°	852.6	853.7	854.7	855.8	856.8	857.6	858.1	858.6	859.1	859.7	860.2
145°	885.0	886.2	887.4	888.6	889.9	890.6	891.0	891.3	891.7	892.0	892.4
147.5°	915.5	916.3	917.1	917.9	918.7	919.3	919.6	919.9	920.3	920.6	921.0
150°	934.2	934.8	935.3	935.8	936.3	936.8	937.1	937.5	937.8	938.2	938.5
152.5°	951.1	951.4	951.6	951.9	952.1	952.3	952.5	952.7	953.0	953.2	953.8
155°	974.9	974.6	974.2	973.9	973.5	973.4	973.6	973.8	973.9	974.1	975.0
157.5°	993.3	993.3	993.3	993.2	993.2	993.1	992.9	992.8	992.6	992.4	993.5
160°	1004.6	1004.4	1004.3	1004.1	1003.9	1003.7	1003.6	1003.4	1003.2	1003.0	1004.1
162.5°	1015.2	1014.8	1014.3	1013.9	1013.4	1013.1	1012.9	1012.8	1012.6	1012.4	1013.6
165°	1028.1	1027.5	1027.0	1026.5	1026.0	1025.6	1025.5	1025.3	1025.1	1024.9	1026.3
167.5°	1038.1	1037.4	1036.7	1036.0	1035.3	1034.9	1034.9	1034.9	1034.9	1034.9	1036.3
170°	1043.7	1043.0	1042.3	1041.6	1040.9	1040.6	1040.6	1040.6	1040.6	1040.6	1042.0
172.5°	1047.4	1046.6	1045.8	1044.9	1044.1	1043.8	1043.9	1044.0	1044.2	1044.3	1045.7
175°	1052.3	1051.4	1050.6	1049.7	1048.8	1048.5	1048.6	1048.8	1049.0	1049.2	1050.4
177.5°	1053.5	1052.9	1052.2	1051.5	1050.8	1050.5	1050.6	1050.8	1050.9	1051.0	1052.2
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P332069

CATALOG NUMBER: S123DIP-S1165D805U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1
2.5°	1821.1	1823.9	1826.7	1828.0	1827.7	1827.4	1827.1	1826.9
5°	1811.5	1815.0	1818.5	1819.9	1819.2	1818.5	1817.8	1817.1
7.5°	1792.3	1795.4	1798.6	1799.9	1799.5	1799.1	1798.7	1798.3
10°	1774.7	1777.8	1781.0	1782.2	1781.5	1780.8	1780.1	1779.4
12.5°	1755.4	1757.7	1760.0	1761.0	1760.5	1760.1	1759.7	1759.3
15°	1720.5	1723.3	1726.1	1726.5	1724.4	1722.3	1720.2	1718.1
17.5°	1676.4	1678.4	1680.3	1680.9	1680.2	1679.4	1678.6	1677.9
20°	1643.9	1645.3	1646.7	1646.8	1645.8	1644.7	1643.7	1642.6
22.5°	1609.4	1610.5	1611.6	1611.5	1610.2	1608.8	1607.5	1606.2
25°	1552.2	1552.5	1552.9	1552.5	1551.5	1550.4	1549.4	1548.3
27.5°	1491.4	1491.6	1491.9	1491.4	1490.1	1488.7	1487.4	1486.1
30°	1449.3	1449.3	1449.3	1448.1	1445.6	1443.2	1440.7	1438.3
32.5°	1405.1	1403.2	1401.2	1399.6	1398.3	1396.9	1395.6	1394.3
35°	1333.5	1331.4	1329.3	1327.4	1325.6	1323.9	1322.1	1320.4
37.5°	1259.4	1256.9	1254.4	1252.6	1251.4	1250.3	1249.2	1248.1
40°	1211.1	1208.3	1205.5	1203.4	1202.0	1200.6	1199.2	1197.8
42.5°	1160.8	1158.0	1155.2	1153.1	1151.7	1150.3	1148.9	1147.5
45°	1085.7	1081.5	1077.3	1074.3	1072.6	1070.8	1069.1	1067.3
47.5°	1006.6	1002.5	998.3	995.5	994.0	992.4	990.9	989.4
50°	954.3	950.5	946.6	943.7	941.6	939.5	937.4	935.3
52.5°	901.4	898.1	894.8	892.1	890.0	887.9	885.8	883.7
55°	820.7	816.9	813.0	810.2	808.5	806.7	805.0	803.2
57.5°	741.4	738.0	734.5	731.8	729.8	727.8	725.7	723.7
60°	685.4	682.2	679.1	676.6	674.9	673.1	671.4	669.6
62.5°	631.3	628.1	625.0	622.8	621.6	620.4	619.3	618.1
65°	550.9	548.1	545.3	543.4	542.3	541.3	540.2	539.2
67.5°	471.1	468.6	466.2	464.2	462.8	461.3	459.8	458.4
70°	419.5	417.1	414.6	412.5	410.8	409.0	407.3	405.6
72.5°	367.3	365.1	362.9	361.4	360.5	359.6	358.7	357.8
75°	292.0	290.3	288.5	287.1	286.1	285.0	284.0	282.9
77.5°	221.8	220.6	219.4	218.8	218.8	218.8	218.8	218.8
80°	176.9	176.6	176.2	176.1	176.1	176.1	176.1	176.1
82.5°	136.1	135.5	134.9	134.4	134.1	133.9	133.6	133.3
85°	77.2	76.5	75.8	75.5	75.5	75.5	75.5	75.5
87.5°	31.1	31.0	30.9	30.8	30.9	31.0	31.0	31.1
90°	20.2	20.8	21.5	22.1	22.4	22.8	23.1	23.5
92.5°	22.2	23.3	24.5	25.1	25.3	25.5	25.7	26.0
95°	26.7	27.9	29.1	29.7	29.7	29.7	29.7	29.7
97.5°	28.0	29.3	30.7	31.5	31.7	31.9	32.0	32.2
100°	28.6	30.0	31.4	32.1	32.3	32.5	32.7	32.8
102.5°	42.8	38.5	34.2	32.2	32.5	32.8	33.1	33.5
105°	109.7	79.0	48.2	33.0	33.4	33.7	34.1	34.4
107.5°	268.7	246.2	223.6	200.7	177.6	154.4	131.2	108.0
110°	341.1	335.4	329.7	314.4	289.5	264.7	239.8	215.0



TEST NUMBER: P332069

CATALOG NUMBER: S123DIP-S1165D805U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	392.2	392.3	392.4	389.8	384.6	379.3	374.1	368.9
115°	452.2	454.0	455.7	456.9	457.6	458.3	459.0	459.7
117.5°	506.6	508.0	509.3	510.1	510.3	510.4	510.5	510.7
120°	542.2	543.6	545.0	545.7	545.7	545.7	545.7	545.7
122.5°	577.0	578.0	579.0	579.5	579.7	579.8	580.0	580.1
125°	626.1	626.5	626.8	627.2	627.5	627.9	628.2	628.6
127.5°	675.3	675.9	676.4	676.5	676.2	675.9	675.5	675.2
130°	705.0	705.7	706.4	706.6	706.2	705.9	705.5	705.2
132.5°	733.1	733.8	734.5	734.6	734.2	733.7	733.2	732.7
135°	775.8	776.3	776.8	776.8	776.3	775.8	775.3	774.8
137.5°	813.8	814.6	815.5	815.7	815.4	815.0	814.7	814.3
140°	837.9	838.6	839.3	839.5	839.1	838.8	838.4	838.1
142.5°	860.8	861.3	861.9	861.9	861.4	860.9	860.5	860.0
145°	892.7	893.1	893.4	893.6	893.6	893.6	893.6	893.6
147.5°	921.3	921.7	922.0	921.8	921.0	920.2	919.4	918.6
150°	938.8	939.2	939.5	939.5	938.9	938.4	937.9	937.4
152.5°	954.4	955.0	955.7	955.6	954.8	954.0	953.2	952.4
155°	975.9	976.7	977.6	977.5	976.5	975.4	974.4	973.3
157.5°	994.5	995.5	996.6	996.4	995.1	993.7	992.4	991.0
160°	1005.1	1006.2	1007.2	1007.1	1005.9	1004.7	1003.5	1002.3
162.5°	1014.8	1016.0	1017.1	1017.2	1016.1	1015.0	1014.0	1012.9
165°	1027.7	1029.1	1030.5	1030.6	1029.4	1028.1	1026.9	1025.7
167.5°	1037.7	1039.1	1040.5	1040.5	1039.1	1037.7	1036.3	1034.9
170°	1043.3	1044.7	1046.1	1046.1	1044.7	1043.3	1042.0	1040.6
172.5°	1047.1	1048.5	1049.9	1049.8	1048.3	1046.8	1045.2	1043.7
175°	1051.6	1052.8	1054.0	1053.9	1052.6	1051.2	1049.8	1048.4
177.5°	1053.3	1054.4	1055.5	1055.4	1054.0	1052.6	1051.2	1049.8
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3

(END OF REPORT)