

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332281-927

Luminaire Tested: **S123RDIP-S560D585U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332281-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S560D585U927-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3371.3 lumens  
Efficiency: N/A  
Efficacy: 102.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 32.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332281-927

CATALOG NUMBER: S123RDIP-S560D585U927-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332281-927

CATALOG NUMBER: S123RDIP-S560D585U927-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50																				
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	43																				
2	90	82	76	71	83	76	71	67	65	61	58	54	52	49	45	43	41	36																				
3	82	73	66	60	75	67	61	56	58	53	49	48	45	42	40	37	35	31																				
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31	27																				
5	69	58	50	44	64	54	47	41	46	41	36	39	35	32	32	29	27	24																				
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	29	26	24	21																				
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	24	21	19																				
8	55	43	35	30	51	40	33	28	34	29	25	30	25	22	25	22	19	17																				
9	51	39	32	27	47	36	30	25	32	26	23	27	23	20	23	20	17	15																				
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8054	8054	8054
5°	8084	7973	8018
10°	8039	7873	7847
15°	7952	7689	7608
20°	7834	7458	7285
25°	7712	7201	6969
30°	7549	6901	6524
35°	7384	6603	6116
40°	7231	6250	5611
45°	7030	5903	5154
50°	6807	5508	4644
55°	6583	5056	4168
60°	6374	4573	3645
65°	6105	4050	3123
70°	5766	3402	2521
75°	5273	2674	2371
80°	4705	2374	2182
85°	3977	2100	1951



TEST NUMBER: P332281-927

CATALOG NUMBER: S123RDIP-S560D585U927-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	70.3	2.1
10°-20°	195.5	5.8
20°-30°	281.5	8.3
30°-40°	317.1	9.4
40°-50°	303.3	9.0
50°-60°	248.4	7.4
60°-70°	167.6	5.0
70°-80°	84.3	2.5
80°-90°	24.0	0.7
90°-100°	124.2	3.7
100°-110°	351.7	10.4
110°-120°	346.0	10.3
120°-130°	276.0	8.2
130°-140°	217.6	6.5
140°-150°	162.4	4.8
150°-160°	113.2	3.4
160°-170°	66.5	2.0
170°-180°	21.6	0.6
0°-30°	547.2	16.2
0°-40°	864.3	25.6
0°-60°	1416.1	42.0
0°-90°	1692.0	50.2
90°-120°	822.0	24.4
90°-150°	1478.0	43.8
90°-180°	1679.0	49.8
0°-180°	3371.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	748	748	748	748	748	
5°	748	745	738	743	742	71
15°	714	706	690	687	683	201
25°	649	633	606	594	587	298
35°	562	539	502	477	465	352
45°	462	433	388	354	339	356
55°	351	320	269	236	222	314
65°	240	206	159	130	123	237
75°	127	97	64	58	57	135
85°	32	19	17	16	16	36
90°	1	5	11	13	13	3
95°	15	50	268	78	52	17
105°	52	78	363	635	575	56
115°	93	115	278	609	699	92
125°	129	152	259	470	551	114
135°	151	180	256	387	447	117
145°	172	197	252	317	349	108
155°	196	211	244	278	290	90
165°	214	220	234	248	252	60
175°	223	223	225	228	227	21
180°	223	223	223	223	223	



TEST NUMBER: P332281-927

CATALOG NUMBER: S123RDIP-S560D585U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2
2.5°	750.7	750.2	749.8	749.3	748.9	748.1	746.8	745.4	744.2	742.9	744.1
5°	748.2	747.6	746.9	746.2	745.5	744.4	742.8	741.2	739.5	737.9	739.1
7.5°	741.3	740.6	739.8	739.1	738.4	737.0	734.9	732.8	730.6	728.6	729.2
10°	735.5	734.5	733.6	732.6	731.7	730.0	727.6	725.2	722.7	720.3	720.4
12.5°	727.2	726.2	725.1	724.1	723.0	721.0	718.0	715.1	712.1	709.2	709.1
15°	713.6	712.2	710.7	709.2	707.7	705.0	701.3	697.5	693.7	690.0	689.3
17.5°	696.5	694.8	693.1	691.3	689.6	686.3	681.5	676.8	671.9	667.2	665.7
20°	683.9	681.8	679.6	677.4	675.3	671.6	666.5	661.4	656.2	651.1	649.4
22.5°	669.8	667.3	664.9	662.3	659.9	655.9	650.5	645.0	639.6	634.1	631.9
25°	649.3	645.9	642.5	639.2	635.8	631.1	624.8	618.6	612.4	606.3	603.4
27.5°	624.4	620.7	617.0	613.2	609.5	604.2	597.3	590.4	583.5	576.6	572.7
30°	607.4	603.4	599.4	595.3	591.3	585.4	577.9	570.4	562.8	555.2	550.6
32.5°	590.4	585.9	581.3	576.7	572.1	565.9	557.9	549.9	541.9	533.9	528.9
35°	561.9	557.1	552.2	547.4	542.5	535.9	527.5	519.2	510.8	502.5	496.6
37.5°	533.1	527.7	522.3	516.8	511.4	504.3	495.4	486.5	477.5	468.6	462.0
40°	514.6	508.7	502.7	496.8	490.8	483.1	473.6	464.0	454.4	444.8	437.8
42.5°	493.7	487.7	481.9	475.9	470.0	462.1	452.2	442.3	432.4	422.5	414.8
45°	461.8	455.7	449.6	443.6	437.5	429.3	418.9	408.5	398.2	387.8	380.1
47.5°	429.8	423.2	416.5	409.9	403.2	394.7	384.3	373.9	363.5	353.2	344.8
50°	406.5	400.2	393.9	387.5	381.2	372.6	361.6	350.8	339.8	328.9	320.5
52.5°	385.7	378.8	371.9	365.0	358.2	349.4	338.5	327.7	316.9	306.1	297.4
55°	350.8	344.1	337.5	330.9	324.3	315.3	303.8	292.4	280.9	269.4	261.6
57.5°	318.5	311.2	304.0	296.8	289.6	280.3	268.8	257.3	245.7	234.2	226.9
60°	296.1	288.8	281.3	273.9	266.5	257.1	246.0	234.8	223.6	212.4	205.1
62.5°	273.8	266.4	259.0	251.5	244.2	234.8	223.6	212.5	201.2	190.0	183.2
65°	239.7	232.3	224.9	217.5	210.0	201.1	190.5	180.1	169.5	159.0	152.4
67.5°	205.6	198.1	190.6	183.1	175.6	166.8	156.7	146.6	136.6	126.4	121.5
70°	183.2	175.9	168.7	161.4	154.2	145.8	136.3	126.9	117.5	108.1	103.3
72.5°	160.9	153.8	146.6	139.4	132.2	124.4	115.8	107.2	98.6	90.1	86.2
75°	126.8	120.3	113.9	107.4	100.9	94.0	86.6	79.1	71.8	64.3	63.0
77.5°	95.8	89.9	84.1	78.2	72.3	67.0	62.3	57.5	52.7	47.9	47.2
80°	75.9	70.3	64.8	59.3	53.7	49.6	46.7	43.9	41.0	38.3	37.8
82.5°	57.0	52.1	47.4	42.6	37.8	34.8	33.4	32.2	30.8	29.5	29.1
85°	32.2	29.2	26.2	23.3	20.3	18.6	18.2	17.8	17.4	17.0	16.7
87.5°	11.8	10.9	9.8	8.9	7.9	7.4	7.8	8.0	8.3	8.6	8.4
90°	0.9	1.8	2.7	4.0	5.0	5.9	7.2	8.6	9.9	11.3	10.9
92.5°	5.6	8.3	12.1	15.6	19.4	26.1	37.9	57.4	76.4	69.5	52.4
95°	15.4	16.7	21.7	29.4	41.1	58.7	97.1	164.5	238.6	267.9	217.3
97.5°	26.2	26.7	30.6	37.2	48.8	67.9	104.6	180.5	304.0	415.3	444.3
100°	33.4	33.9	37.1	43.4	54.2	71.9	103.5	170.3	289.1	427.9	516.9
102.5°	41.0	41.8	44.7	50.6	60.4	76.5	104.9	161.7	267.5	404.4	520.5
105°	52.4	53.8	56.5	61.9	70.5	84.5	108.9	155.4	240.8	363.3	493.0
107.5°	64.5	65.9	68.5	73.8	81.9	94.9	116.3	155.0	223.9	326.9	444.7
110°	73.2	74.5	76.8	81.8	89.4	102.1	122.5	156.8	217.3	306.3	414.3



TEST NUMBER: P332281-927

CATALOG NUMBER: S123RDIP-S560D585U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	81.1	82.5	84.8	89.8	97.4	109.7	128.6	160.4	213.7	292.6	387.9
115°	92.6	94.4	97.1	101.6	109.3	121.5	138.7	166.3	212.4	277.9	356.1
117.5°	104.1	106.2	108.4	112.6	121.2	132.5	149.5	174.0	213.2	269.2	336.8
120°	112.1	113.4	115.7	120.2	128.8	140.1	156.3	179.8	214.6	265.2	326.7
122.5°	118.9	120.3	122.6	127.4	135.6	147.7	163.6	185.3	217.1	262.7	318.4
125°	128.8	129.7	132.4	137.4	145.9	158.1	174.0	193.8	220.9	259.4	307.7
127.5°	136.3	137.6	141.0	146.0	155.5	167.7	183.0	200.9	225.3	257.7	298.3
130°	141.0	142.4	146.4	151.8	161.3	173.5	188.4	205.6	228.1	256.7	293.3
132.5°	144.6	146.3	150.8	157.2	166.8	178.6	193.1	209.9	230.4	256.3	288.5
135°	150.9	152.7	157.7	164.5	174.0	186.2	200.2	215.6	233.6	255.7	282.4
137.5°	156.9	158.8	163.7	170.9	180.3	191.5	205.0	219.7	235.8	254.8	277.1
140°	160.9	163.1	167.6	174.8	183.9	195.2	208.3	221.9	237.2	254.4	273.8
142.5°	165.2	167.1	172.0	178.5	187.5	198.1	210.8	224.0	238.3	253.7	270.9
145°	172.1	173.5	177.6	184.3	192.0	202.4	214.2	226.4	239.0	252.5	267.0
147.5°	179.2	180.0	184.0	189.9	197.3	206.1	216.9	227.8	239.0	250.9	263.2
150°	183.9	184.3	188.0	193.8	200.2	208.3	218.7	228.1	239.0	249.4	260.7
152.5°	188.6	188.7	192.3	197.5	203.0	210.8	219.8	228.9	238.0	247.6	257.9
155°	195.7	195.7	198.4	202.9	207.9	214.2	221.9	229.1	236.8	244.5	253.5
157.5°	201.2	201.6	203.7	207.8	212.0	216.9	223.0	229.6	235.2	241.6	248.6
160°	205.6	205.6	207.4	211.0	214.2	218.7	224.1	229.6	234.5	239.5	245.3
162.5°	208.8	208.8	210.3	213.2	215.9	219.8	224.5	229.2	233.1	237.3	242.1
165°	213.7	213.3	214.2	216.4	218.2	221.4	225.0	228.1	230.9	234.1	237.7
167.5°	217.5	216.9	217.3	219.0	220.3	222.3	224.9	227.4	228.7	230.8	233.5
170°	219.6	218.7	219.1	220.5	221.4	222.3	224.6	226.4	227.3	228.6	230.9
172.5°	221.0	220.5	220.6	221.6	222.1	222.7	224.6	226.0	226.2	226.8	228.4
175°	222.8	222.3	221.9	222.8	222.8	223.2	224.1	225.0	224.6	224.6	225.5
177.5°	223.6	223.2	222.8	223.2	223.2	223.2	223.6	224.3	223.6	223.2	223.6
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P332281-927

CATALOG NUMBER: S123RDIP-S560D585U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2
2.5°	745.3	746.5	747.7	748.1	747.9	747.7	747.5	747.3
5°	740.3	741.6	742.8	743.2	743.0	742.7	742.4	742.1
7.5°	729.9	730.6	731.3	731.3	730.9	730.5	730.0	729.5
10°	720.6	720.7	720.8	720.6	719.9	719.2	718.6	717.9
12.5°	709.0	708.9	708.8	708.4	707.6	706.8	706.1	705.3
15°	688.6	687.9	687.3	686.4	685.5	684.6	683.7	682.7
17.5°	664.3	662.9	661.4	660.0	658.6	657.2	655.8	654.4
20°	647.6	645.9	644.1	642.5	640.8	639.2	637.5	636.0
22.5°	629.8	627.6	625.4	623.5	622.0	620.5	619.0	617.5
25°	600.6	597.7	594.9	592.7	591.3	589.8	588.3	586.8
27.5°	568.7	564.8	560.9	557.8	555.5	553.3	551.0	548.7
30°	546.1	541.5	536.9	533.5	531.4	529.3	527.0	524.9
32.5°	523.9	518.8	513.8	510.2	507.9	505.6	503.4	501.1
35°	490.8	485.1	479.3	475.2	472.7	470.3	467.9	465.4
37.5°	455.4	448.9	442.3	437.5	434.5	431.5	428.5	425.5
40°	430.8	423.7	416.8	411.7	408.6	405.5	402.4	399.3
42.5°	407.2	399.5	391.8	386.6	383.8	381.0	378.3	375.5
45°	372.4	364.7	357.0	351.6	348.3	345.1	341.8	338.6
47.5°	336.4	328.1	319.7	314.1	311.2	308.3	305.5	302.5
50°	312.2	303.8	295.5	289.7	286.6	283.5	280.4	277.3
52.5°	288.8	280.0	271.3	265.6	262.8	260.1	257.3	254.5
55°	253.8	246.0	238.1	232.9	230.2	227.5	224.8	222.1
57.5°	219.4	212.1	204.7	199.9	197.6	195.3	193.0	190.7
60°	197.8	190.5	183.2	178.5	176.2	173.9	171.6	169.3
62.5°	176.3	169.5	162.6	158.0	155.7	153.2	150.8	148.5
65°	145.8	139.2	132.5	128.5	127.1	125.6	124.1	122.6
67.5°	116.6	111.6	106.7	103.5	101.9	100.3	98.7	97.1
70°	98.5	93.9	89.1	86.0	84.5	83.1	81.6	80.1
72.5°	82.3	78.5	74.6	72.4	71.8	71.1	70.5	69.9
75°	61.6	60.3	58.9	58.1	57.8	57.6	57.3	57.0
77.5°	46.5	45.8	45.0	44.5	44.3	44.0	43.7	43.4
80°	37.4	37.0	36.6	36.3	36.0	35.7	35.5	35.2
82.5°	28.7	28.3	27.9	27.6	27.6	27.6	27.5	27.4
85°	16.5	16.2	15.9	15.8	15.8	15.8	15.8	15.8
87.5°	8.3	8.3	8.3	8.4	8.2	8.2	8.2	7.9
90°	11.3	11.7	12.2	13.1	12.7	13.1	13.5	13.1
92.5°	38.0	30.2	26.7	24.3	23.5	22.1	22.6	21.8
95°	162.6	110.3	86.3	70.0	61.5	57.4	54.2	52.4
97.5°	405.5	324.8	266.5	212.5	179.1	158.8	146.6	142.7
100°	532.7	496.1	443.2	379.1	333.4	300.5	282.9	283.3
102.5°	575.0	573.9	543.0	502.3	466.8	440.7	426.0	415.6
105°	587.4	632.6	641.2	629.4	608.6	591.4	577.0	574.7
107.5°	551.8	625.2	664.7	680.8	681.2	675.4	670.5	666.4
110°	517.8	600.9	657.9	689.5	702.2	705.8	704.9	703.9





TEST NUMBER: P332281-927

CATALOG NUMBER: S123RDIP-S560D585U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	484.2	569.1	633.0	673.6	696.7	708.0	711.4	711.5
115°	439.7	518.2	584.7	633.9	667.8	687.7	696.7	699.0
117.5°	407.3	475.2	534.9	584.9	620.2	642.9	656.0	659.0
120°	390.4	451.4	505.6	551.3	586.9	612.3	623.1	625.8
122.5°	377.0	432.2	482.4	524.8	556.6	579.3	591.3	594.7
125°	359.2	408.4	451.9	488.0	516.9	536.8	548.1	551.3
127.5°	343.6	387.6	426.7	459.6	485.4	502.3	512.5	515.5
130°	333.9	374.5	411.1	441.9	465.9	482.1	491.6	495.2
132.5°	324.9	362.3	396.3	425.6	448.1	464.4	472.8	475.3
135°	312.7	344.8	374.1	399.9	422.0	435.5	443.7	446.9
137.5°	301.6	327.9	353.2	375.5	394.1	407.8	414.7	416.8
140°	295.1	318.1	339.8	359.2	376.4	389.0	396.2	395.8
142.5°	288.9	308.7	327.5	344.4	359.0	370.3	376.8	376.3
145°	281.5	296.4	310.9	324.0	335.3	344.8	348.4	349.3
147.5°	275.4	287.2	299.0	308.2	316.8	323.2	326.7	327.0
150°	271.1	281.5	291.0	299.6	306.3	311.3	314.0	314.0
152.5°	267.1	276.1	284.5	291.6	296.9	301.6	303.2	303.2
155°	261.2	268.4	275.2	280.6	284.6	288.3	289.1	289.6
157.5°	254.8	260.9	266.2	270.4	273.9	276.6	277.3	277.3
160°	251.2	256.2	260.7	263.9	267.0	269.7	269.7	269.3
162.5°	246.9	251.1	255.3	258.1	260.2	262.5	262.5	262.1
165°	241.3	244.0	247.2	249.4	251.2	253.0	252.5	252.5
167.5°	236.4	238.4	240.3	241.9	242.7	244.0	243.5	243.5
170°	233.1	234.5	236.3	237.2	237.7	238.6	238.1	238.1
172.5°	230.3	231.2	232.7	233.2	233.3	234.2	233.5	233.1
175°	226.4	226.8	227.8	227.8	227.8	228.1	227.8	227.3
177.5°	223.9	224.3	224.7	224.7	224.3	224.7	223.9	223.9
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2

(END OF REPORT)