

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332285-927

Luminaire Tested: **S123RDIP-S560D805U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332285-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D805U927-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4234.8 lumens
Efficiency: N/A
Efficacy: 110.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332285-927

CATALOG NUMBER: S123RDIP-S560D805U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332285-927

CATALOG NUMBER: S123RDIP-S560D805U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	92	88	85	87	84	80	78	68	66	64	55	53	52	42	41	40	34
2	87	80	74	69	79	73	68	64	60	57	54	48	46	44	37	36	34	29
3	80	71	64	58	72	65	59	54	53	49	45	43	40	37	33	31	29	25
4	73	63	55	49	66	57	51	46	48	43	39	38	35	32	30	27	25	22
5	67	56	48	42	61	51	44	39	43	37	34	34	31	28	27	24	22	19
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	22	20	17
7	57	45	38	32	52	42	35	30	35	30	26	28	25	22	22	20	18	15
8	53	41	34	28	48	38	31	27	32	27	23	26	22	19	21	18	16	13
9	49	38	30	25	45	35	28	24	29	24	21	24	20	17	19	16	14	12
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8054	8054	8054
5°	8084	7973	8018
10°	8039	7873	7847
15°	7952	7689	7608
20°	7834	7458	7285
25°	7712	7201	6969
30°	7549	6901	6524
35°	7384	6603	6116
40°	7231	6250	5611
45°	7030	5903	5154
50°	6807	5508	4644
55°	6583	5056	4168
60°	6374	4573	3645
65°	6105	4050	3123
70°	5766	3402	2521
75°	5273	2674	2371
80°	4705	2374	2182
85°	3977	2100	1951



TEST NUMBER: P332285-927

CATALOG NUMBER: S123RDIP-S560D805U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.3	1.7
10°-20°	195.5	4.6
20°-30°	281.5	6.6
30°-40°	317.1	7.5
40°-50°	303.3	7.2
50°-60°	248.4	5.9
60°-70°	167.6	4.0
70°-80°	84.3	2.0
80°-90°	24.6	0.6
90°-100°	30.3	0.7
100°-110°	144.4	3.4
110°-120°	347.0	8.2
120°-130°	441.8	10.4
130°-140°	472.1	11.1
140°-150°	441.4	10.4
150°-160°	356.1	8.4
160°-170°	229.8	5.4
170°-180°	79.2	1.9
0°-30°	547.2	12.9
0°-40°	864.3	20.4
0°-60°	1416.1	33.4
0°-90°	1692.6	40.0
90°-120°	521.7	12.3
90°-150°	1877.0	44.3
90°-180°	2542.0	60.0
0°-180°	4234.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	748	748	748	748	748	
5°	748	745	738	743	742	71
15°	714	706	690	687	683	201
25°	649	633	606	594	587	298
35°	562	539	502	477	465	352
45°	462	433	388	354	339	356
55°	351	320	269	236	222	314
65°	240	206	159	130	123	237
75°	127	97	64	58	57	135
85°	32	19	17	16	16	36
90°	1	7	15	17	19	3
95°	38	14	19	23	24	47
105°	185	188	136	32	27	196
115°	346	350	356	361	364	342
125°	488	493	495	497	498	436
135°	608	611	614	615	614	468
145°	701	705	707	708	708	439
155°	772	771	772	774	771	356
165°	814	813	812	816	812	230
175°	834	831	831	835	830	79
180°	834	834	834	834	834	



TEST NUMBER: P332285-927

CATALOG NUMBER: S123RDIP-S560D805U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2
2.5°	750.7	750.2	749.8	749.3	748.9	748.1	746.8	745.4	744.2	742.9	744.1
5°	748.2	747.6	746.9	746.2	745.5	744.4	742.8	741.2	739.5	737.9	739.1
7.5°	741.3	740.6	739.8	739.1	738.4	737.0	734.9	732.8	730.6	728.6	729.2
10°	735.5	734.5	733.6	732.6	731.7	730.0	727.6	725.2	722.7	720.3	720.4
12.5°	727.2	726.2	725.1	724.1	723.0	721.0	718.0	715.1	712.1	709.2	709.1
15°	713.6	712.2	710.7	709.2	707.7	705.0	701.3	697.5	693.7	690.0	689.3
17.5°	696.5	694.8	693.1	691.3	689.6	686.3	681.5	676.8	671.9	667.2	665.7
20°	683.9	681.8	679.6	677.4	675.3	671.6	666.5	661.4	656.2	651.1	649.4
22.5°	669.8	667.3	664.9	662.3	659.9	655.9	650.5	645.0	639.6	634.1	631.9
25°	649.3	645.9	642.5	639.2	635.8	631.1	624.8	618.6	612.4	606.3	603.4
27.5°	624.4	620.7	617.0	613.2	609.5	604.2	597.3	590.4	583.5	576.6	572.7
30°	607.4	603.4	599.4	595.3	591.3	585.4	577.9	570.4	562.8	555.2	550.6
32.5°	590.4	585.9	581.3	576.7	572.1	565.9	557.9	549.9	541.9	533.9	528.9
35°	561.9	557.1	552.2	547.4	542.5	535.9	527.5	519.2	510.8	502.5	496.6
37.5°	533.1	527.7	522.3	516.8	511.4	504.3	495.4	486.5	477.5	468.6	462.0
40°	514.6	508.7	502.7	496.8	490.8	483.1	473.6	464.0	454.4	444.8	437.8
42.5°	493.7	487.7	481.9	475.9	470.0	462.1	452.2	442.3	432.4	422.5	414.8
45°	461.8	455.7	449.6	443.6	437.5	429.3	418.9	408.5	398.2	387.8	380.1
47.5°	429.8	423.2	416.5	409.9	403.2	394.7	384.3	373.9	363.5	353.2	344.8
50°	406.5	400.2	393.9	387.5	381.2	372.6	361.6	350.8	339.8	328.9	320.5
52.5°	385.7	378.8	371.9	365.0	358.2	349.4	338.5	327.7	316.9	306.1	297.4
55°	350.8	344.1	337.5	330.9	324.3	315.3	303.8	292.4	280.9	269.4	261.6
57.5°	318.5	311.2	304.0	296.8	289.6	280.3	268.8	257.3	245.7	234.2	226.9
60°	296.1	288.8	281.3	273.9	266.5	257.1	246.0	234.8	223.6	212.4	205.1
62.5°	273.8	266.4	259.0	251.5	244.2	234.8	223.6	212.5	201.2	190.0	183.2
65°	239.7	232.3	224.9	217.5	210.0	201.1	190.5	180.1	169.5	159.0	152.4
67.5°	205.6	198.1	190.6	183.1	175.6	166.8	156.7	146.6	136.6	126.4	121.5
70°	183.2	175.9	168.7	161.4	154.2	145.8	136.3	126.9	117.5	108.1	103.3
72.5°	160.9	153.8	146.6	139.4	132.2	124.4	115.8	107.2	98.6	90.1	86.2
75°	126.8	120.3	113.9	107.4	100.9	94.0	86.6	79.1	71.8	64.3	63.0
77.5°	95.8	89.9	84.1	78.2	72.3	67.0	62.3	57.5	52.7	47.9	47.2
80°	75.9	70.3	64.8	59.3	53.7	49.6	46.7	43.9	41.0	38.3	37.8
82.5°	57.0	52.1	47.4	42.6	37.8	34.8	33.4	32.2	30.8	29.5	29.1
85°	32.2	29.2	26.2	23.3	20.3	18.6	18.2	17.8	17.4	17.0	16.7
87.5°	11.8	10.9	10.0	9.0	8.2	7.8	8.2	8.6	9.0	9.3	9.3
90°	0.6	2.0	3.4	4.8	6.1	7.7	9.5	11.2	13.1	14.9	15.4
92.5°	11.5	11.2	10.8	10.4	10.0	10.5	11.8	13.2	14.5	15.8	16.7
95°	37.8	32.2	26.5	20.8	15.2	13.2	14.7	16.2	17.7	19.2	20.2
97.5°	75.9	73.4	70.9	68.4	65.8	59.6	49.7	39.8	29.9	20.0	21.1
100°	104.6	107.4	110.2	112.9	115.7	106.3	84.8	63.4	41.9	20.4	21.5
102.5°	137.4	139.3	141.3	143.3	145.3	134.6	111.1	87.6	64.2	40.7	37.3
105°	184.6	186.1	187.6	189.1	190.6	185.2	172.8	160.4	148.0	135.6	111.3
107.5°	234.3	235.6	236.8	238.0	239.2	240.7	242.7	244.7	246.6	248.6	230.8
110°	267.5	268.6	269.7	270.8	272.0	273.2	274.8	276.3	277.8	279.3	274.8



TEST NUMBER: P332285-927

CATALOG NUMBER: S123RDIP-S560D805U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	299.3	300.2	301.3	302.2	303.2	304.4	306.0	307.5	309.0	310.5	310.6
115°	346.2	347.1	347.8	348.7	349.5	350.5	351.8	353.0	354.3	355.5	356.9
117.5°	391.7	392.7	393.7	394.7	395.7	396.6	397.2	397.8	398.5	399.1	400.2
120°	419.9	421.1	422.4	423.6	424.8	425.7	426.1	426.5	426.9	427.3	428.4
122.5°	448.6	449.6	450.7	451.7	452.7	453.4	454.0	454.6	455.0	455.6	456.4
125°	488.1	489.1	490.2	491.3	492.4	493.3	493.8	494.3	494.9	495.4	495.7
127.5°	526.2	527.3	528.4	529.5	530.6	531.5	532.1	532.8	533.5	534.1	534.6
130°	549.9	551.0	552.2	553.3	554.4	555.2	555.7	556.3	556.8	557.4	557.9
132.5°	572.7	573.9	575.0	576.1	577.2	577.9	578.4	578.8	579.2	579.7	580.3
135°	607.5	608.4	609.2	610.1	610.9	611.6	612.1	612.7	613.2	613.8	614.2
137.5°	637.3	638.3	639.4	640.4	641.4	642.1	642.5	642.8	643.0	643.3	644.0
140°	657.1	657.9	658.8	659.6	660.4	661.0	661.5	661.9	662.3	662.7	663.2
142.5°	675.4	676.3	677.1	677.9	678.7	679.4	679.8	680.2	680.6	681.0	681.4
145°	701.1	702.0	703.0	703.9	705.0	705.5	705.8	706.1	706.4	706.6	706.9
147.5°	725.2	725.9	726.5	727.1	727.8	728.3	728.5	728.7	729.0	729.3	729.6
150°	740.1	740.5	740.9	741.3	741.7	742.1	742.4	742.7	742.9	743.2	743.5
152.5°	753.4	753.7	753.8	754.1	754.2	754.4	754.6	754.7	754.9	755.1	755.6
155°	772.3	772.1	771.7	771.5	771.2	771.1	771.3	771.4	771.5	771.7	772.4
157.5°	786.9	786.9	786.9	786.8	786.8	786.7	786.6	786.5	786.3	786.2	787.0
160°	795.8	795.7	795.6	795.4	795.3	795.1	795.0	794.9	794.7	794.6	795.4
162.5°	804.2	803.9	803.5	803.2	802.8	802.6	802.4	802.3	802.2	802.0	803.0
165°	814.4	814.0	813.6	813.2	812.8	812.5	812.4	812.2	812.1	811.9	813.0
167.5°	822.4	821.8	821.3	820.7	820.1	819.8	819.8	819.8	819.8	819.8	820.9
170°	826.8	826.2	825.7	825.1	824.6	824.3	824.3	824.3	824.3	824.3	825.5
172.5°	829.7	829.1	828.5	827.8	827.1	826.9	827.0	827.0	827.2	827.3	828.4
175°	833.6	832.9	832.3	831.6	830.8	830.6	830.7	830.8	831.0	831.2	832.1
177.5°	834.6	834.1	833.5	833.0	832.4	832.2	832.3	832.4	832.5	832.6	833.5
180°	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6



TEST NUMBER: P332285-927

CATALOG NUMBER: S123RDIP-S560D805U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2
2.5°	745.3	746.5	747.7	748.1	747.9	747.7	747.5	747.3
5°	740.3	741.6	742.8	743.2	743.0	742.7	742.4	742.1
7.5°	729.9	730.6	731.3	731.3	730.9	730.5	730.0	729.5
10°	720.6	720.7	720.8	720.6	719.9	719.2	718.6	717.9
12.5°	709.0	708.9	708.8	708.4	707.6	706.8	706.1	705.3
15°	688.6	687.9	687.3	686.4	685.5	684.6	683.7	682.7
17.5°	664.3	662.9	661.4	660.0	658.6	657.2	655.8	654.4
20°	647.6	645.9	644.1	642.5	640.8	639.2	637.5	636.0
22.5°	629.8	627.6	625.4	623.5	622.0	620.5	619.0	617.5
25°	600.6	597.7	594.9	592.7	591.3	589.8	588.3	586.8
27.5°	568.7	564.8	560.9	557.8	555.5	553.3	551.0	548.7
30°	546.1	541.5	536.9	533.5	531.4	529.3	527.0	524.9
32.5°	523.9	518.8	513.8	510.2	507.9	505.6	503.4	501.1
35°	490.8	485.1	479.3	475.2	472.7	470.3	467.9	465.4
37.5°	455.4	448.9	442.3	437.5	434.5	431.5	428.5	425.5
40°	430.8	423.7	416.8	411.7	408.6	405.5	402.4	399.3
42.5°	407.2	399.5	391.8	386.6	383.8	381.0	378.3	375.5
45°	372.4	364.7	357.0	351.6	348.3	345.1	341.8	338.6
47.5°	336.4	328.1	319.7	314.1	311.2	308.3	305.5	302.5
50°	312.2	303.8	295.5	289.7	286.6	283.5	280.4	277.3
52.5°	288.8	280.0	271.3	265.6	262.8	260.1	257.3	254.5
55°	253.8	246.0	238.1	232.9	230.2	227.5	224.8	222.1
57.5°	219.4	212.1	204.7	199.9	197.6	195.3	193.0	190.7
60°	197.8	190.5	183.2	178.5	176.2	173.9	171.6	169.3
62.5°	176.3	169.5	162.6	158.0	155.7	153.2	150.8	148.5
65°	145.8	139.2	132.5	128.5	127.1	125.6	124.1	122.6
67.5°	116.6	111.6	106.7	103.5	101.9	100.3	98.7	97.1
70°	98.5	93.9	89.1	86.0	84.5	83.1	81.6	80.1
72.5°	82.3	78.5	74.6	72.4	71.8	71.1	70.5	69.9
75°	61.6	60.3	58.9	58.1	57.8	57.6	57.3	57.0
77.5°	46.5	45.8	45.0	44.5	44.3	44.0	43.7	43.4
80°	37.4	37.0	36.6	36.3	36.0	35.7	35.5	35.2
82.5°	28.7	28.3	27.9	27.6	27.6	27.6	27.5	27.4
85°	16.5	16.2	15.9	15.8	15.8	15.8	15.8	15.8
87.5°	9.3	9.3	9.3	9.3	9.2	9.2	9.1	9.0
90°	16.0	16.5	17.0	17.5	17.7	18.1	18.3	18.6
92.5°	17.6	18.5	19.4	19.9	20.0	20.2	20.4	20.6
95°	21.2	22.1	23.1	23.5	23.5	23.5	23.5	23.5
97.5°	22.2	23.2	24.3	25.0	25.1	25.3	25.3	25.5
100°	22.7	23.8	24.9	25.4	25.6	25.7	25.9	26.0
102.5°	33.9	30.5	27.1	25.5	25.7	26.0	26.2	26.5
105°	86.9	62.6	38.2	26.1	26.5	26.7	27.0	27.3
107.5°	212.9	195.0	177.1	159.0	140.7	122.3	103.9	85.6
110°	270.2	265.7	261.2	249.1	229.3	209.7	190.0	170.3



TEST NUMBER: P332285-927

CATALOG NUMBER: S123RDIP-S560D805U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	310.7	310.8	310.9	308.8	304.7	300.5	296.4	292.2
115°	358.2	359.7	361.0	361.9	362.5	363.1	363.6	364.2
117.5°	401.3	402.4	403.5	404.1	404.3	404.3	404.4	404.6
120°	429.5	430.6	431.7	432.3	432.3	432.3	432.3	432.3
122.5°	457.1	457.9	458.7	459.1	459.2	459.3	459.5	459.5
125°	496.0	496.3	496.5	496.9	497.1	497.4	497.6	498.0
127.5°	535.0	535.4	535.8	535.9	535.7	535.4	535.1	534.9
130°	558.5	559.0	559.6	559.8	559.4	559.2	558.9	558.6
132.5°	580.7	581.3	581.9	581.9	581.6	581.2	580.8	580.4
135°	614.6	615.0	615.4	615.4	615.0	614.6	614.2	613.8
137.5°	644.7	645.3	646.0	646.2	645.9	645.6	645.4	645.1
140°	663.8	664.3	664.9	665.0	664.7	664.5	664.2	663.9
142.5°	681.9	682.3	682.8	682.8	682.4	682.0	681.7	681.3
145°	707.2	707.5	707.7	707.9	707.9	707.9	707.9	707.9
147.5°	729.8	730.2	730.4	730.2	729.6	729.0	728.3	727.7
150°	743.7	744.0	744.3	744.3	743.8	743.4	743.0	742.6
152.5°	756.1	756.5	757.1	757.0	756.4	755.7	755.1	754.5
155°	773.1	773.7	774.4	774.4	773.6	772.7	771.9	771.0
157.5°	787.8	788.6	789.5	789.3	788.3	787.2	786.2	785.1
160°	796.2	797.1	797.9	797.8	796.9	795.9	795.0	794.0
162.5°	803.9	804.9	805.7	805.8	804.9	804.1	803.3	802.4
165°	814.1	815.2	816.3	816.4	815.5	814.4	813.5	812.5
167.5°	822.0	823.2	824.3	824.3	823.2	822.0	820.9	819.8
170°	826.5	827.6	828.7	828.7	827.6	826.5	825.5	824.3
172.5°	829.5	830.6	831.7	831.6	830.4	829.3	828.0	826.8
175°	833.1	834.0	835.0	834.9	833.9	832.7	831.6	830.5
177.5°	834.4	835.3	836.1	836.1	835.0	833.9	832.7	831.6
180°	833.6	833.6	833.6	833.6	833.6	833.6	833.6	833.6

(END OF REPORT)