

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331892

Luminaire Tested: **S123DIP-S340D1025U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331892
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D1025U835-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5552.1 lumens
Efficiency: N/A
Efficacy: 148.8 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331892

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331892

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34	26
1	93	88	85	81	82	79	76	73	61	59	58	45	44	43	30	30	29	22
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	68	61	55	50	48	44	40	35	33	31	24	22	21	16
4	70	60	53	47	63	54	48	43	42	38	34	32	29	26	21	20	18	14
5	65	53	46	40	57	48	41	36	38	33	29	28	25	23	19	17	16	12
6	59	48	40	35	53	43	36	32	34	29	26	25	22	20	18	16	14	11
7	55	43	35	30	49	39	32	28	31	26	22	23	20	17	16	14	12	10
8	51	39	32	26	45	35	29	24	28	23	20	21	18	15	15	13	11	9
9	47	35	28	23	42	32	26	21	25	21	18	19	16	14	13	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5175	5175	5175	5175
5°	6172	5198	4606	5198
10°	7725	5172	4161	5172
15°	9475	5129	3874	5129
20°	11287	5065	3688	5065
25°	11986	4986	3646	4986
30°	10274	4928	3665	4928
35°	7144	4846	3704	4846
40°	5382	4749	3693	4749
45°	4468	4606	3646	4606
50°	4002	4315	3612	4315
55°	3742	4001	3567	4001
60°	3511	3670	3531	3670
65°	3298	3347	3418	3347
70°	3094	2977	3254	2977
75°	2770	2608	2986	2608
80°	2424	2139	2572	2139
85°	1902	1556	1729	1556



TEST NUMBER: P331892

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.4	0.9
10°-20°	151.9	2.7
20°-30°	254.9	4.6
30°-40°	288.6	5.2
40°-50°	258.8	4.7
50°-60°	208.9	3.8
60°-70°	145.6	2.6
70°-80°	76.5	1.4
80°-90°	22.5	0.4
90°-100°	48.8	0.9
100°-110°	232.8	4.2
110°-120°	559.2	10.1
120°-130°	712.1	12.8
130°-140°	760.8	13.7
140°-150°	711.5	12.8
150°-160°	573.9	10.3
160°-170°	370.4	6.7
170°-180°	127.6	2.3
0°-30°	454.2	8.2
0°-40°	742.8	13.4
0°-60°	1210.5	21.8
0°-90°	1455.0	26.2
90°-120°	840.8	15.1
90°-150°	3025.2	54.5
90°-180°	4097.0	73.8
0°-180°	5552.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	481	481	481	481	481	
5°	571	481	426	481	571	59
15°	850	460	348	460	850	246
25°	1009	420	307	420	1009	443
35°	544	369	282	369	544	353
45°	294	303	240	303	294	232
55°	199	213	190	213	199	179
65°	130	131	134	131	130	129
75°	67	63	72	63	67	71
85°	15	13	14	13	15	19
90°	30	1	30	1	30	14
95°	38	61	38	61	38	32
105°	44	297	44	297	44	100
115°	587	558	587	558	587	542
125°	802	786	802	786	802	717
135°	989	979	989	979	989	763
145°	1141	1130	1141	1130	1141	712
155°	1243	1245	1243	1245	1243	573
165°	1310	1313	1310	1313	1310	370
175°	1338	1344	1338	1344	1338	127
180°	1344	1344	1344	1344	1344	



TEST NUMBER: P331892

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	510.3	509.9	509.0	509.7	508.2	506.2	506.0	504.1	498.7	498.4	496.9
5°	571.2	569.4	569.1	568.9	565.6	561.2	552.8	552.1	540.9	535.4	528.6
7.5°	650.2	651.1	647.7	644.8	634.8	628.2	619.2	607.7	594.0	580.0	570.8
10°	706.8	714.5	705.0	698.4	692.4	681.0	667.7	651.1	634.6	615.3	600.6
12.5°	767.6	771.3	769.4	763.3	753.9	736.5	713.0	694.7	679.5	647.3	634.3
15°	850.3	864.5	855.4	834.5	834.9	818.4	787.7	753.9	735.9	707.7	669.3
17.5°	938.5	940.2	936.4	918.9	907.3	884.5	856.1	823.8	787.4	753.3	712.5
20°	985.4	984.0	975.9	966.8	946.8	929.1	898.1	862.0	815.4	781.8	737.3
22.5°	1011.5	1009.2	1005.3	997.7	981.1	962.1	934.2	894.8	850.4	804.2	752.8
25°	1009.2	1012.2	1012.7	1010.6	1004.8	993.4	971.5	940.0	895.8	836.3	782.8
27.5°	917.9	922.2	934.6	945.7	958.0	970.6	968.9	953.3	920.5	869.2	803.7
30°	826.6	817.2	840.3	869.4	889.2	924.2	943.7	944.9	926.5	882.5	818.6
32.5°	699.8	710.1	720.3	756.1	799.4	838.6	877.6	908.9	912.5	883.2	827.4
35°	543.7	556.6	575.2	593.8	640.4	680.5	749.0	808.6	856.1	862.4	828.2
37.5°	438.2	444.5	456.3	475.0	505.4	553.0	605.9	681.3	750.2	801.4	803.6
40°	383.0	384.9	398.1	412.3	437.0	476.2	523.9	590.6	673.0	744.6	774.4
42.5°	341.6	345.7	351.4	365.0	384.7	414.1	458.5	513.6	589.2	671.5	729.8
45°	293.5	298.2	301.7	310.8	324.8	344.6	375.5	425.9	483.4	568.4	646.9
47.5°	261.8	262.1	264.7	271.6	281.1	296.0	317.9	350.2	403.0	472.0	552.6
50°	239.0	242.7	243.7	249.0	256.5	267.4	285.6	313.1	356.4	417.0	491.1
52.5°	223.0	224.1	226.7	230.6	237.1	245.6	261.4	282.9	316.9	368.6	436.7
55°	199.4	199.4	202.0	205.0	208.7	216.4	226.9	242.7	268.6	308.7	365.1
57.5°	177.6	178.8	180.6	181.5	184.7	189.8	198.5	210.6	229.8	260.7	305.5
60°	163.1	165.2	164.9	166.8	169.6	173.6	181.0	190.8	208.0	232.7	270.5
62.5°	150.4	150.3	150.2	152.5	155.2	159.0	163.9	172.3	187.0	208.9	241.0
65°	129.5	129.1	130.7	132.1	133.0	135.8	139.5	147.0	156.8	173.1	198.0
67.5°	111.0	109.6	110.5	111.0	112.6	114.8	118.3	122.9	130.6	143.7	162.5
70°	98.3	97.1	96.9	97.4	98.8	100.4	103.0	107.4	114.6	125.1	138.8
72.5°	85.3	84.5	84.4	85.5	86.1	87.2	89.0	93.0	98.8	106.7	119.5
75°	66.6	66.6	66.6	66.9	67.6	68.5	69.9	72.0	76.4	82.0	90.6
77.5°	49.9	49.9	49.6	49.6	50.6	51.0	51.3	53.3	55.8	59.5	65.8
80°	39.1	38.0	38.4	39.1	39.6	39.8	40.5	41.0	43.1	45.2	49.6
82.5°	29.1	28.1	28.2	29.3	29.4	29.6	30.3	30.9	31.7	33.6	36.0
85°	15.4	15.4	15.6	15.6	15.8	15.6	16.3	16.5	16.5	17.7	19.1
87.5°	11.6	11.1	11.2	11.3	11.0	11.1	11.1	11.1	11.1	11.1	10.7
90°	29.9	29.5	29.1	28.6	28.2	27.5	26.6	25.7	24.8	24.0	21.1
92.5°	33.1	32.9	32.6	32.3	32.1	31.2	29.8	28.4	27.0	25.6	23.4
95°	37.9	37.9	37.9	37.9	37.9	37.2	35.6	34.0	32.5	30.9	28.5
97.5°	41.1	40.9	40.7	40.5	40.2	39.2	37.5	35.7	33.9	32.1	48.1
100°	41.9	41.7	41.5	41.3	41.0	40.0	38.3	36.5	34.7	32.9	67.5
102.5°	42.7	42.3	41.9	41.5	41.1	43.7	49.2	54.7	60.2	65.7	103.5
105°	43.9	43.5	43.0	42.6	42.1	61.6	100.8	140.1	179.3	218.6	238.6
107.5°	137.9	167.5	197.1	226.7	256.3	285.5	314.3	343.1	371.9	400.7	397.5
110°	274.5	306.2	337.9	369.6	401.4	420.9	428.2	435.5	442.8	450.2	447.7



TEST NUMBER: P331892

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	470.9	477.6	484.3	491.0	497.7	501.0	500.9	500.7	500.6	500.5	498.0
115°	586.9	586.0	585.1	584.2	583.4	581.8	579.6	577.4	575.2	572.9	570.9
117.5°	652.0	651.8	651.6	651.5	651.3	650.3	648.5	646.8	645.0	643.2	642.2
120°	696.7	696.7	696.7	696.7	696.7	695.8	694.0	692.3	690.5	688.7	688.1
122.5°	740.6	740.4	740.3	740.1	739.9	739.2	738.0	736.7	735.5	734.2	733.4
125°	802.5	802.1	801.6	801.2	800.7	800.3	799.8	799.4	799.0	798.5	797.6
127.5°	862.0	862.4	862.9	863.3	863.8	863.6	862.9	862.2	861.5	860.8	859.7
130°	900.3	900.8	901.2	901.7	902.1	901.9	901.0	900.1	899.2	898.3	897.4
132.5°	935.5	936.1	936.7	937.3	937.9	937.8	936.9	936.0	935.2	934.3	933.6
135°	989.2	989.8	990.5	991.2	991.8	991.8	991.2	990.5	989.8	989.2	988.3
137.5°	1039.7	1040.1	1040.6	1041.0	1041.4	1041.1	1040.1	1039.0	1037.9	1036.9	1036.4
140°	1070.0	1070.5	1070.9	1071.3	1071.8	1071.6	1070.7	1069.8	1068.9	1068.0	1067.4
142.5°	1098.0	1098.6	1099.2	1099.8	1100.4	1100.4	1099.7	1099.0	1098.3	1097.6	1096.9
145°	1140.9	1140.9	1140.9	1140.9	1140.9	1140.7	1140.2	1139.8	1139.3	1138.9	1138.4
147.5°	1172.8	1173.8	1174.9	1175.9	1176.9	1177.2	1176.7	1176.3	1175.9	1175.4	1175.0
150°	1196.8	1197.4	1198.1	1198.8	1199.4	1199.6	1199.1	1198.7	1198.2	1197.8	1197.3
152.5°	1215.9	1217.0	1218.0	1219.0	1220.0	1220.1	1219.3	1218.5	1217.7	1216.9	1216.7
155°	1242.7	1244.0	1245.4	1246.7	1248.0	1248.1	1247.0	1245.9	1244.8	1243.7	1243.5
157.5°	1265.3	1267.0	1268.7	1270.4	1272.2	1272.4	1271.0	1269.7	1268.4	1267.0	1267.3
160°	1279.6	1281.2	1282.7	1284.3	1285.8	1285.9	1284.6	1283.3	1282.0	1280.6	1280.8
162.5°	1293.2	1294.6	1295.9	1297.3	1298.7	1298.6	1297.1	1295.6	1294.1	1292.6	1292.8
165°	1309.6	1311.1	1312.7	1314.2	1315.8	1315.7	1313.9	1312.1	1310.3	1308.6	1308.8
167.5°	1321.3	1323.1	1324.9	1326.7	1328.4	1328.4	1326.7	1324.9	1323.1	1321.3	1321.3
170°	1328.5	1330.3	1332.1	1333.9	1335.6	1335.6	1333.9	1332.1	1330.3	1328.5	1328.5
172.5°	1332.5	1334.5	1336.4	1338.4	1340.3	1340.4	1338.6	1336.9	1335.1	1333.3	1333.1
175°	1338.5	1340.3	1342.1	1343.8	1345.6	1345.7	1344.2	1342.6	1341.1	1339.5	1339.3
177.5°	1340.3	1342.1	1343.9	1345.6	1347.4	1347.6	1346.2	1344.7	1343.3	1341.9	1341.7
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P331892

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	495.7	494.3	492.8	490.2	487.9	484.8	483.8	482.7	479.3	476.4	474.1
5°	526.0	520.4	512.3	504.8	498.8	490.6	486.0	481.1	474.1	467.8	462.7
7.5°	557.7	546.7	534.0	520.4	507.6	495.3	485.4	476.5	466.7	457.5	450.2
10°	582.9	567.0	549.3	530.2	513.9	498.1	484.8	473.2	460.6	449.6	440.5
12.5°	611.6	588.1	563.7	540.5	521.2	499.2	483.1	468.3	454.0	440.9	430.7
15°	645.5	615.7	586.8	554.9	525.6	498.1	479.0	460.3	443.8	430.3	417.2
17.5°	676.5	642.7	604.6	565.8	530.4	497.8	471.1	450.0	429.3	412.8	399.8
20°	694.0	655.6	612.5	572.2	533.0	496.7	467.3	442.2	419.8	402.3	387.7
22.5°	709.1	664.1	619.5	576.4	532.8	493.7	460.4	434.5	410.3	393.2	377.6
25°	724.8	670.9	626.2	575.7	527.0	486.4	449.2	419.8	395.6	375.5	359.5
27.5°	738.2	670.5	617.4	563.0	517.7	477.1	437.3	405.8	380.1	358.3	342.0
30°	747.1	671.4	608.3	554.5	508.8	466.9	428.2	396.5	369.5	347.4	332.0
32.5°	752.7	670.8	599.9	542.5	494.6	457.5	418.3	385.5	357.7	336.0	321.2
35°	756.0	666.7	585.4	517.9	471.8	435.6	402.8	368.8	339.7	319.4	302.6
37.5°	749.4	658.1	568.7	494.1	443.6	408.1	380.4	351.5	323.6	301.3	286.8
40°	739.2	652.5	555.6	477.3	424.2	390.0	366.5	338.0	310.5	289.3	275.8
42.5°	719.6	641.2	541.3	458.7	404.1	369.9	348.2	324.4	298.4	278.5	265.0
45°	671.9	616.4	519.7	430.8	374.4	339.0	319.9	302.6	279.1	259.8	248.1
47.5°	605.6	579.2	488.6	401.3	343.3	309.3	289.4	275.6	258.4	242.7	231.6
50°	559.6	548.6	467.6	381.1	322.7	289.3	270.2	257.7	245.3	229.7	219.5
52.5°	506.5	513.2	443.0	360.3	301.6	268.8	250.9	240.9	229.7	216.8	207.9
55°	431.7	456.1	400.5	325.2	270.2	239.0	222.0	213.2	206.6	197.1	189.4
57.5°	361.7	392.8	354.5	289.1	239.4	212.5	196.2	186.6	182.4	177.4	171.3
60°	320.1	350.8	321.7	264.9	218.8	193.1	178.7	170.5	166.3	162.8	157.7
62.5°	283.0	314.1	289.7	240.3	198.4	174.7	162.1	154.1	150.9	149.1	144.7
65°	232.0	258.8	242.5	202.0	169.4	148.4	137.0	131.4	128.4	127.7	124.9
67.5°	188.8	209.2	197.4	167.5	141.9	123.8	114.1	109.3	107.0	106.7	104.6
70°	160.5	179.6	170.5	143.5	121.4	107.2	98.8	94.6	93.2	93.0	91.8
72.5°	138.5	151.8	144.6	122.1	105.0	92.1	85.9	81.5	80.0	80.3	79.5
75°	102.5	112.5	108.3	92.7	79.0	70.6	65.5	62.7	61.3	62.0	61.0
77.5°	73.8	80.1	76.3	65.5	57.0	51.0	47.2	45.5	44.2	44.2	43.8
80°	55.7	59.4	57.3	50.8	43.8	38.7	35.6	34.5	33.8	33.5	33.3
82.5°	39.7	42.8	40.3	35.9	31.1	28.0	26.3	24.8	24.3	24.4	24.2
85°	20.0	21.2	20.3	17.5	15.6	14.2	13.3	12.6	12.1	12.3	11.9
87.5°	10.5	10.1	9.0	7.8	6.9	5.9	5.5	4.7	4.7	5.2	5.4
90°	18.2	15.3	12.4	9.9	7.7	5.4	3.2	1.0	3.2	5.4	7.7
92.5°	21.2	19.0	16.9	16.1	16.7	17.3	17.9	18.6	17.9	17.3	16.7
95°	26.1	23.6	21.2	24.5	33.6	42.7	51.8	60.9	51.8	42.7	33.6
97.5°	64.1	80.1	96.0	106.0	110.1	114.2	118.3	122.4	118.3	114.2	110.1
100°	102.1	136.7	171.3	186.4	182.0	177.6	173.1	168.7	173.1	177.6	182.0
102.5°	141.3	179.1	216.9	234.2	231.0	227.8	224.6	221.4	224.6	227.8	231.0
105°	258.5	278.5	298.4	307.2	304.8	302.3	299.9	297.4	299.9	302.3	304.8
107.5°	394.4	391.2	388.1	385.5	383.6	381.6	379.7	377.7	379.7	381.6	383.6
110°	445.3	442.8	440.4	438.3	436.5	434.7	433.0	431.2	433.0	434.7	436.5



TEST NUMBER: P331892

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	495.6	493.2	490.7	488.7	487.1	485.5	483.9	482.3	483.9	485.5	487.1
115°	568.9	566.9	565.0	563.3	562.0	560.6	559.3	558.0	559.3	560.6	562.0
117.5°	641.2	640.1	639.1	637.8	636.2	634.5	632.9	631.2	632.9	634.5	636.2
120°	687.4	686.7	686.1	684.7	682.7	680.7	678.7	676.7	678.7	680.7	682.7
122.5°	732.6	731.7	730.9	729.6	728.0	726.3	724.7	723.1	724.7	726.3	728.0
125°	796.7	795.9	795.0	793.6	791.9	790.1	788.3	786.5	788.3	790.1	791.9
127.5°	858.7	857.6	856.5	855.1	853.3	851.6	849.8	848.0	849.8	851.6	853.3
130°	896.6	895.7	894.8	893.5	891.7	889.9	888.1	886.4	888.1	889.9	891.7
132.5°	932.8	932.1	931.4	930.2	928.4	926.6	924.9	923.1	924.9	926.6	928.4
135°	987.4	986.5	985.6	984.5	983.2	981.8	980.5	979.2	980.5	981.8	983.2
137.5°	1035.9	1035.4	1034.9	1033.8	1032.2	1030.5	1028.8	1027.1	1028.8	1030.5	1032.2
140°	1066.7	1066.0	1065.4	1064.4	1063.0	1061.7	1060.4	1059.0	1060.4	1061.7	1063.0
142.5°	1096.2	1095.6	1094.9	1093.9	1092.6	1091.2	1089.9	1088.6	1089.9	1091.2	1092.6
145°	1138.0	1137.6	1137.1	1136.1	1134.6	1133.0	1131.5	1129.9	1131.5	1133.0	1134.6
147.5°	1174.5	1174.1	1173.6	1172.9	1171.9	1170.9	1169.9	1168.8	1169.9	1170.9	1171.9
150°	1196.9	1196.4	1196.0	1195.4	1194.8	1194.1	1193.5	1192.8	1193.5	1194.1	1194.8
152.5°	1216.4	1216.1	1215.9	1215.6	1215.3	1215.0	1214.7	1214.3	1214.7	1215.0	1215.3
155°	1243.2	1243.0	1242.8	1242.9	1243.4	1243.8	1244.2	1244.7	1244.2	1243.8	1243.4
157.5°	1267.5	1267.7	1267.9	1268.1	1268.1	1268.2	1268.2	1268.2	1268.2	1268.2	1268.1
160°	1281.1	1281.3	1281.5	1281.7	1282.0	1282.2	1282.4	1282.6	1282.4	1282.2	1282.0
162.5°	1293.0	1293.3	1293.5	1293.9	1294.5	1295.0	1295.6	1296.2	1295.6	1295.0	1294.5
165°	1309.0	1309.2	1309.5	1309.9	1310.6	1311.2	1311.9	1312.6	1311.9	1311.2	1310.6
167.5°	1321.3	1321.3	1321.3	1321.8	1322.7	1323.6	1324.5	1325.3	1324.5	1323.6	1322.7
170°	1328.5	1328.5	1328.5	1329.0	1329.9	1330.8	1331.6	1332.5	1331.6	1330.8	1329.9
172.5°	1333.0	1332.8	1332.6	1333.1	1334.1	1335.2	1336.3	1337.3	1336.3	1335.2	1334.1
175°	1339.1	1338.8	1338.6	1339.1	1340.2	1341.3	1342.4	1343.5	1342.4	1341.3	1340.2
177.5°	1341.6	1341.4	1341.2	1341.6	1342.4	1343.3	1344.2	1345.1	1344.2	1343.3	1342.4
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P331892

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	472.8	471.5	469.7	466.9	464.6	461.1	461.1	461.6	461.6	461.5	461.1
5°	458.5	455.0	450.8	445.9	440.8	435.6	434.7	432.8	431.5	430.5	429.4
7.5°	443.3	437.1	431.0	424.2	417.9	412.8	409.2	406.2	404.3	402.2	400.7
10°	433.1	425.4	418.2	411.0	403.0	396.7	392.8	390.0	387.9	386.0	385.1
12.5°	421.0	412.2	404.2	397.3	388.7	382.2	378.4	377.1	374.7	370.7	368.7
15°	403.3	395.1	385.6	375.1	370.9	363.0	358.5	356.4	355.0	352.0	351.1
17.5°	388.1	377.5	366.7	358.9	351.1	344.7	342.2	339.6	337.8	335.3	334.5
20°	376.0	366.5	356.7	348.3	340.1	333.1	331.0	329.2	327.3	326.2	325.2
22.5°	363.7	354.2	346.0	338.2	329.5	324.9	322.7	320.6	319.3	318.5	317.6
25°	346.4	338.0	328.9	322.0	315.0	311.9	310.5	309.4	308.4	307.3	307.0
27.5°	331.0	321.8	314.5	307.9	302.9	300.4	299.0	298.5	298.7	299.1	299.4
30°	319.4	311.0	305.0	299.4	294.7	292.4	292.1	292.1	293.1	293.3	293.8
32.5°	308.8	301.9	295.8	290.4	286.9	285.3	286.2	286.2	286.9	287.5	288.4
35°	293.3	287.2	282.6	277.9	274.9	275.6	276.1	276.5	277.7	279.1	280.0
37.5°	278.5	273.3	268.4	264.8	263.4	264.6	265.8	266.7	268.1	269.2	270.1
40°	267.9	263.9	259.3	256.0	256.5	257.2	258.1	259.3	260.5	261.2	262.1
42.5°	258.0	253.9	250.3	247.6	248.3	249.2	249.7	250.3	251.7	253.0	253.5
45°	243.0	239.7	236.5	234.8	235.3	235.8	236.2	236.9	238.1	239.0	239.3
47.5°	226.1	223.8	221.6	220.0	220.8	220.6	221.2	222.7	223.0	223.6	224.9
50°	215.3	213.2	210.6	210.1	210.1	210.1	210.4	212.2	212.2	213.2	214.1
52.5°	203.3	202.0	200.4	199.5	199.1	199.1	200.1	201.0	201.4	202.7	203.7
55°	185.7	184.3	182.9	182.2	181.7	182.2	184.0	184.5	185.7	186.4	187.1
57.5°	167.3	166.2	165.1	164.7	164.6	165.2	166.2	167.6	167.9	170.1	171.1
60°	155.2	153.5	152.6	152.6	152.1	154.2	153.8	156.1	156.6	158.0	159.6
62.5°	142.7	140.5	140.1	140.1	140.8	141.4	142.0	143.0	144.3	146.0	147.3
65°	122.5	121.4	123.0	122.8	122.3	123.7	123.7	124.9	126.3	127.9	130.5
67.5°	103.5	102.9	103.0	103.0	103.7	104.5	105.2	106.2	107.9	109.6	111.3
70°	90.6	91.3	90.2	91.1	91.8	92.0	92.5	93.9	95.7	96.9	98.8
72.5°	78.1	78.1	78.2	78.6	79.3	79.7	80.2	81.8	83.8	84.8	86.3
75°	60.1	59.9	60.6	60.6	61.7	62.2	62.7	63.4	65.2	66.6	67.8
77.5°	43.9	44.2	44.0	44.8	44.5	44.6	46.0	46.7	46.9	49.7	50.3
80°	33.1	33.5	33.8	34.0	34.2	33.8	35.4	36.1	36.1	37.7	38.9
82.5°	23.8	24.0	24.6	24.9	24.9	25.4	25.5	26.0	26.6	27.3	28.8
85°	11.9	12.6	12.8	12.6	12.8	12.3	13.0	13.3	13.5	13.5	13.5
87.5°	5.7	6.4	6.8	7.6	7.9	8.7	8.9	8.7	8.9	9.6	9.0
90°	9.9	12.4	15.3	18.2	21.1	24.0	24.8	25.7	26.6	27.5	28.2
92.5°	16.1	16.9	19.0	21.2	23.4	25.6	27.0	28.4	29.8	31.2	32.1
95°	24.5	21.2	23.6	26.1	28.5	30.9	32.5	34.0	35.6	37.2	37.9
97.5°	106.0	96.0	80.1	64.1	48.1	32.1	33.9	35.7	37.5	39.2	40.2
100°	186.4	171.3	136.7	102.1	67.5	32.9	34.7	36.5	38.3	40.0	41.0
102.5°	234.2	216.9	179.1	141.3	103.5	65.7	60.2	54.7	49.2	43.7	41.1
105°	307.2	298.4	278.5	258.5	238.6	218.6	179.3	140.1	100.8	61.6	42.1
107.5°	385.5	388.1	391.2	394.4	397.5	400.7	371.9	343.1	314.3	285.5	256.3
110°	438.3	440.4	442.8	445.3	447.7	450.2	442.8	435.5	428.2	420.9	401.4



TEST NUMBER: P331892

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	488.7	490.7	493.2	495.6	498.0	500.5	500.6	500.7	500.9	501.0	497.7
115°	563.3	565.0	566.9	568.9	570.9	572.9	575.2	577.4	579.6	581.8	583.4
117.5°	637.8	639.1	640.1	641.2	642.2	643.2	645.0	646.8	648.5	650.3	651.3
120°	684.7	686.1	686.7	687.4	688.1	688.7	690.5	692.3	694.0	695.8	696.7
122.5°	729.6	730.9	731.7	732.6	733.4	734.2	735.5	736.7	738.0	739.2	739.9
125°	793.6	795.0	795.9	796.7	797.6	798.5	799.0	799.4	799.8	800.3	800.7
127.5°	855.1	856.5	857.6	858.7	859.7	860.8	861.5	862.2	862.9	863.6	863.8
130°	893.5	894.8	895.7	896.6	897.4	898.3	899.2	900.1	901.0	901.9	902.1
132.5°	930.2	931.4	932.1	932.8	933.6	934.3	935.2	936.0	936.9	937.8	937.9
135°	984.5	985.6	986.5	987.4	988.3	989.2	989.8	990.5	991.2	991.8	991.8
137.5°	1033.8	1034.9	1035.4	1035.9	1036.4	1036.9	1037.9	1039.0	1040.1	1041.1	1041.4
140°	1064.4	1065.4	1066.0	1066.7	1067.4	1068.0	1068.9	1069.8	1070.7	1071.6	1071.8
142.5°	1093.9	1094.9	1095.6	1096.2	1096.9	1097.6	1098.3	1099.0	1099.7	1100.4	1100.4
145°	1136.1	1137.1	1137.6	1138.0	1138.4	1138.9	1139.3	1139.8	1140.2	1140.7	1140.9
147.5°	1172.9	1173.6	1174.1	1174.5	1175.0	1175.4	1175.9	1176.3	1176.7	1177.2	1176.9
150°	1195.4	1196.0	1196.4	1196.9	1197.3	1197.8	1198.2	1198.7	1199.1	1199.6	1199.4
152.5°	1215.6	1215.9	1216.1	1216.4	1216.7	1216.9	1217.7	1218.5	1219.3	1220.1	1220.0
155°	1242.9	1242.8	1243.0	1243.2	1243.5	1243.7	1244.8	1245.9	1247.0	1248.1	1248.0
157.5°	1268.1	1267.9	1267.7	1267.5	1267.3	1267.0	1268.4	1269.7	1271.0	1272.4	1272.2
160°	1281.7	1281.5	1281.3	1281.1	1280.8	1280.6	1282.0	1283.3	1284.6	1285.9	1285.8
162.5°	1293.9	1293.5	1293.3	1293.0	1292.8	1292.6	1294.1	1295.6	1297.1	1298.6	1298.7
165°	1309.9	1309.5	1309.2	1309.0	1308.8	1308.6	1310.3	1312.1	1313.9	1315.7	1315.8
167.5°	1321.8	1321.3	1321.3	1321.3	1321.3	1321.3	1323.1	1324.9	1326.7	1328.4	1328.4
170°	1329.0	1328.5	1328.5	1328.5	1328.5	1328.5	1330.3	1332.1	1333.9	1335.6	1335.6
172.5°	1333.1	1332.6	1332.8	1333.0	1333.1	1333.3	1335.1	1336.9	1338.6	1340.4	1340.3
175°	1339.1	1338.6	1338.8	1339.1	1339.3	1339.5	1341.1	1342.6	1344.2	1345.7	1345.6
177.5°	1341.6	1341.2	1341.4	1341.6	1341.7	1341.9	1343.3	1344.7	1346.2	1347.6	1347.4
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P331892

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	459.8	459.6	460.9	460.0	460.9	459.6	459.8	461.1	461.5	461.6	461.6
5°	428.0	428.7	426.3	426.3	426.3	428.7	428.0	429.4	430.5	431.5	432.8
7.5°	399.6	398.6	398.7	397.4	398.7	398.6	399.6	400.7	402.2	404.3	406.2
10°	382.3	380.9	380.4	380.7	380.4	380.9	382.3	385.1	386.0	387.9	390.0
12.5°	367.9	367.7	364.6	364.6	364.6	367.7	367.9	368.7	370.7	374.7	377.1
15°	351.1	346.7	346.2	347.6	346.2	346.7	351.1	351.1	352.0	355.0	356.4
17.5°	334.2	331.8	332.0	331.3	332.0	331.8	334.2	334.5	335.3	337.8	339.6
20°	325.2	323.8	323.6	322.0	323.6	323.8	325.2	325.2	326.2	327.3	329.2
22.5°	317.0	316.6	316.7	314.9	316.7	316.6	317.0	317.6	318.5	319.3	320.6
25°	306.8	308.0	307.0	307.0	307.0	308.0	306.8	307.0	307.3	308.4	309.4
27.5°	299.9	299.9	299.4	299.4	299.4	299.9	299.9	299.4	299.1	298.7	298.5
30°	294.7	294.5	294.9	294.9	294.9	294.5	294.7	293.8	293.3	293.1	292.1
32.5°	289.5	289.8	289.9	290.1	289.9	289.8	289.5	288.4	287.5	286.9	286.2
35°	281.4	281.7	282.4	281.9	282.4	281.7	281.4	280.0	279.1	277.7	276.5
37.5°	270.5	271.6	271.4	271.7	271.4	271.6	270.5	270.1	269.2	268.1	266.7
40°	262.3	263.0	262.8	262.8	262.8	263.0	262.3	262.1	261.2	260.5	259.3
42.5°	253.9	254.4	253.8	253.5	253.8	254.4	253.9	253.5	253.0	251.7	250.3
45°	240.2	239.7	240.4	239.5	240.4	239.7	240.2	239.3	239.0	238.1	236.9
47.5°	224.8	225.3	225.5	226.2	225.5	225.3	224.8	224.9	223.6	223.0	222.7
50°	214.6	216.0	216.0	215.7	216.0	216.0	214.6	214.1	213.2	212.2	212.2
52.5°	204.5	205.1	206.1	206.0	206.1	205.1	204.5	203.7	202.7	201.4	201.0
55°	188.9	189.4	189.9	190.1	189.9	189.4	188.9	187.1	186.4	185.7	184.5
57.5°	172.8	172.6	173.7	174.1	173.7	172.6	172.8	171.1	170.1	167.9	167.6
60°	161.4	161.4	163.3	164.0	163.3	161.4	161.4	159.6	158.0	156.6	156.1
62.5°	149.3	150.1	151.9	151.0	151.9	150.1	149.3	147.3	146.0	144.3	143.0
65°	131.6	133.5	133.3	134.2	133.3	133.5	131.6	130.5	127.9	126.3	124.9
67.5°	113.1	114.3	116.0	116.1	116.0	114.3	113.1	111.3	109.6	107.9	106.2
70°	100.6	101.8	102.7	103.4	102.7	101.8	100.6	98.8	96.9	95.7	93.9
72.5°	88.5	89.1	91.4	90.4	91.4	89.1	88.5	86.3	84.8	83.8	81.8
75°	69.4	71.1	72.5	71.8	72.5	71.1	69.4	67.8	66.6	65.2	63.4
77.5°	51.3	53.0	53.6	53.0	53.6	53.0	51.3	50.3	49.7	46.9	46.7
80°	40.5	40.3	41.7	41.5	41.7	40.3	40.5	38.9	37.7	36.1	36.1
82.5°	29.7	29.5	30.1	30.3	30.1	29.5	29.7	28.8	27.3	26.6	26.0
85°	14.4	15.1	14.2	14.0	14.2	15.1	14.4	13.5	13.5	13.5	13.3
87.5°	9.1	9.2	9.1	9.0	9.1	9.2	9.1	9.0	9.6	8.9	8.7
90°	28.6	29.1	29.5	29.9	29.5	29.1	28.6	28.2	27.5	26.6	25.7
92.5°	32.3	32.6	32.9	33.1	32.9	32.6	32.3	32.1	31.2	29.8	28.4
95°	37.9	37.9	37.9	37.9	37.9	37.9	37.9	37.9	37.2	35.6	34.0
97.5°	40.5	40.7	40.9	41.1	40.9	40.7	40.5	40.2	39.2	37.5	35.7
100°	41.3	41.5	41.7	41.9	41.7	41.5	41.3	41.0	40.0	38.3	36.5
102.5°	41.5	41.9	42.3	42.7	42.3	41.9	41.5	41.1	43.7	49.2	54.7
105°	42.6	43.0	43.5	43.9	43.5	43.0	42.6	42.1	61.6	100.8	140.1
107.5°	226.7	197.1	167.5	137.9	167.5	197.1	226.7	256.3	285.5	314.3	343.1
110°	369.6	337.9	306.2	274.5	306.2	337.9	369.6	401.4	420.9	428.2	435.5



TEST NUMBER: P331892

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	491.0	484.3	477.6	470.9	477.6	484.3	491.0	497.7	501.0	500.9	500.7
115°	584.2	585.1	586.0	586.9	586.0	585.1	584.2	583.4	581.8	579.6	577.4
117.5°	651.5	651.6	651.8	652.0	651.8	651.6	651.5	651.3	650.3	648.5	646.8
120°	696.7	696.7	696.7	696.7	696.7	696.7	696.7	696.7	695.8	694.0	692.3
122.5°	740.1	740.3	740.4	740.6	740.4	740.3	740.1	739.9	739.2	738.0	736.7
125°	801.2	801.6	802.1	802.5	802.1	801.6	801.2	800.7	800.3	799.8	799.4
127.5°	863.3	862.9	862.4	862.0	862.4	862.9	863.3	863.8	863.6	862.9	862.2
130°	901.7	901.2	900.8	900.3	900.8	901.2	901.7	902.1	901.9	901.0	900.1
132.5°	937.3	936.7	936.1	935.5	936.1	936.7	937.3	937.9	937.8	936.9	936.0
135°	991.2	990.5	989.8	989.2	989.8	990.5	991.2	991.8	991.8	991.2	990.5
137.5°	1041.0	1040.6	1040.1	1039.7	1040.1	1040.6	1041.0	1041.4	1041.1	1040.1	1039.0
140°	1071.3	1070.9	1070.5	1070.0	1070.5	1070.9	1071.3	1071.8	1071.6	1070.7	1069.8
142.5°	1099.8	1099.2	1098.6	1098.0	1098.6	1099.2	1099.8	1100.4	1100.4	1099.7	1099.0
145°	1140.9	1140.9	1140.9	1140.9	1140.9	1140.9	1140.9	1140.9	1140.7	1140.2	1139.8
147.5°	1175.9	1174.9	1173.8	1172.8	1173.8	1174.9	1175.9	1176.9	1177.2	1176.7	1176.3
150°	1198.8	1198.1	1197.4	1196.8	1197.4	1198.1	1198.8	1199.4	1199.6	1199.1	1198.7
152.5°	1219.0	1218.0	1217.0	1215.9	1217.0	1218.0	1219.0	1220.0	1220.1	1219.3	1218.5
155°	1246.7	1245.4	1244.0	1242.7	1244.0	1245.4	1246.7	1248.0	1248.1	1247.0	1245.9
157.5°	1270.4	1268.7	1267.0	1265.3	1267.0	1268.7	1270.4	1272.2	1272.4	1271.0	1269.7
160°	1284.3	1282.7	1281.2	1279.6	1281.2	1282.7	1284.3	1285.8	1285.9	1284.6	1283.3
162.5°	1297.3	1295.9	1294.6	1293.2	1294.6	1295.9	1297.3	1298.7	1298.6	1297.1	1295.6
165°	1314.2	1312.7	1311.1	1309.6	1311.1	1312.7	1314.2	1315.8	1315.7	1313.9	1312.1
167.5°	1326.7	1324.9	1323.1	1321.3	1323.1	1324.9	1326.7	1328.4	1328.4	1326.7	1324.9
170°	1333.9	1332.1	1330.3	1328.5	1330.3	1332.1	1333.9	1335.6	1335.6	1333.9	1332.1
172.5°	1338.4	1336.4	1334.5	1332.5	1334.5	1336.4	1338.4	1340.3	1340.4	1338.6	1336.9
175°	1343.8	1342.1	1340.3	1338.5	1340.3	1342.1	1343.8	1345.6	1345.7	1344.2	1342.6
177.5°	1345.6	1343.9	1342.1	1340.3	1342.1	1343.9	1345.6	1347.4	1347.6	1346.2	1344.7
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P331892

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	461.1	461.1	464.6	466.9	469.7	471.5	472.8	474.1	476.4	479.3	482.7
5°	434.7	435.6	440.8	445.9	450.8	455.0	458.5	462.7	467.8	474.1	481.1
7.5°	409.2	412.8	417.9	424.2	431.0	437.1	443.3	450.2	457.5	466.7	476.5
10°	392.8	396.7	403.0	411.0	418.2	425.4	433.1	440.5	449.6	460.6	473.2
12.5°	378.4	382.2	388.7	397.3	404.2	412.2	421.0	430.7	440.9	454.0	468.3
15°	358.5	363.0	370.9	375.1	385.6	395.1	403.3	417.2	430.3	443.8	460.3
17.5°	342.2	344.7	351.1	358.9	366.7	377.5	388.1	399.8	412.8	429.3	450.0
20°	331.0	333.1	340.1	348.3	356.7	366.5	376.0	387.7	402.3	419.8	442.2
22.5°	322.7	324.9	329.5	338.2	346.0	354.2	363.7	377.6	393.2	410.3	434.5
25°	310.5	311.9	315.0	322.0	328.9	338.0	346.4	359.5	375.5	395.6	419.8
27.5°	299.0	300.4	302.9	307.9	314.5	321.8	331.0	342.0	358.3	380.1	405.8
30°	292.1	292.4	294.7	299.4	305.0	311.0	319.4	332.0	347.4	369.5	396.5
32.5°	286.2	285.3	286.9	290.4	295.8	301.9	308.8	321.2	336.0	357.7	385.5
35°	276.1	275.6	274.9	277.9	282.6	287.2	293.3	302.6	319.4	339.7	368.8
37.5°	265.8	264.6	263.4	264.8	268.4	273.3	278.5	286.8	301.3	323.6	351.5
40°	258.1	257.2	256.5	256.0	259.3	263.9	267.9	275.8	289.3	310.5	338.0
42.5°	249.7	249.2	248.3	247.6	250.3	253.9	258.0	265.0	278.5	298.4	324.4
45°	236.2	235.8	235.3	234.8	236.5	239.7	243.0	248.1	259.8	279.1	302.6
47.5°	221.2	220.6	220.8	220.0	221.6	223.8	226.1	231.6	242.7	258.4	275.6
50°	210.4	210.1	210.1	210.1	210.6	213.2	215.3	219.5	229.7	245.3	257.7
52.5°	200.1	199.1	199.1	199.5	200.4	202.0	203.3	207.9	216.8	229.7	240.9
55°	184.0	182.2	181.7	182.2	182.9	184.3	185.7	189.4	197.1	206.6	213.2
57.5°	166.2	165.2	164.6	164.7	165.1	166.2	167.3	171.3	177.4	182.4	186.6
60°	153.8	154.2	152.1	152.6	152.6	153.5	155.2	157.7	162.8	166.3	170.5
62.5°	142.0	141.4	140.8	140.1	140.1	140.5	142.7	144.7	149.1	150.9	154.1
65°	123.7	123.7	122.3	122.8	123.0	121.4	122.5	124.9	127.7	128.4	131.4
67.5°	105.2	104.5	103.7	103.0	103.0	102.9	103.5	104.6	106.7	107.0	109.3
70°	92.5	92.0	91.8	91.1	90.2	91.3	90.6	91.8	93.0	93.2	94.6
72.5°	80.2	79.7	79.3	78.6	78.2	78.1	78.1	79.5	80.3	80.0	81.5
75°	62.7	62.2	61.7	60.6	60.6	59.9	60.1	61.0	62.0	61.3	62.7
77.5°	46.0	44.6	44.5	44.8	44.0	44.2	43.9	43.8	44.2	44.2	45.5
80°	35.4	33.8	34.2	34.0	33.8	33.5	33.1	33.3	33.5	33.8	34.5
82.5°	25.5	25.4	24.9	24.9	24.6	24.0	23.8	24.2	24.4	24.3	24.8
85°	13.0	12.3	12.8	12.6	12.8	12.6	11.9	11.9	12.3	12.1	12.6
87.5°	8.9	8.7	7.9	7.6	6.8	6.4	5.7	5.4	5.2	4.7	4.7
90°	24.8	24.0	21.1	18.2	15.3	12.4	9.9	7.7	5.4	3.2	1.0
92.5°	27.0	25.6	23.4	21.2	19.0	16.9	16.1	16.7	17.3	17.9	18.6
95°	32.5	30.9	28.5	26.1	23.6	21.2	24.5	33.6	42.7	51.8	60.9
97.5°	33.9	32.1	48.1	64.1	80.1	96.0	106.0	110.1	114.2	118.3	122.4
100°	34.7	32.9	67.5	102.1	136.7	171.3	186.4	182.0	177.6	173.1	168.7
102.5°	60.2	65.7	103.5	141.3	179.1	216.9	234.2	231.0	227.8	224.6	221.4
105°	179.3	218.6	238.6	258.5	278.5	298.4	307.2	304.8	302.3	299.9	297.4
107.5°	371.9	400.7	397.5	394.4	391.2	388.1	385.5	383.6	381.6	379.7	377.7
110°	442.8	450.2	447.7	445.3	442.8	440.4	438.3	436.5	434.7	433.0	431.2



TEST NUMBER: P331892

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	500.6	500.5	498.0	495.6	493.2	490.7	488.7	487.1	485.5	483.9	482.3
115°	575.2	572.9	570.9	568.9	566.9	565.0	563.3	562.0	560.6	559.3	558.0
117.5°	645.0	643.2	642.2	641.2	640.1	639.1	637.8	636.2	634.5	632.9	631.2
120°	690.5	688.7	688.1	687.4	686.7	686.1	684.7	682.7	680.7	678.7	676.7
122.5°	735.5	734.2	733.4	732.6	731.7	730.9	729.6	728.0	726.3	724.7	723.1
125°	799.0	798.5	797.6	796.7	795.9	795.0	793.6	791.9	790.1	788.3	786.5
127.5°	861.5	860.8	859.7	858.7	857.6	856.5	855.1	853.3	851.6	849.8	848.0
130°	899.2	898.3	897.4	896.6	895.7	894.8	893.5	891.7	889.9	888.1	886.4
132.5°	935.2	934.3	933.6	932.8	932.1	931.4	930.2	928.4	926.6	924.9	923.1
135°	989.8	989.2	988.3	987.4	986.5	985.6	984.5	983.2	981.8	980.5	979.2
137.5°	1037.9	1036.9	1036.4	1035.9	1035.4	1034.9	1033.8	1032.2	1030.5	1028.8	1027.1
140°	1068.9	1068.0	1067.4	1066.7	1066.0	1065.4	1064.4	1063.0	1061.7	1060.4	1059.0
142.5°	1098.3	1097.6	1096.9	1096.2	1095.6	1094.9	1093.9	1092.6	1091.2	1089.9	1088.6
145°	1139.3	1138.9	1138.4	1138.0	1137.6	1137.1	1136.1	1134.6	1133.0	1131.5	1129.9
147.5°	1175.9	1175.4	1175.0	1174.5	1174.1	1173.6	1172.9	1171.9	1170.9	1169.9	1168.8
150°	1198.2	1197.8	1197.3	1196.9	1196.4	1196.0	1195.4	1194.8	1194.1	1193.5	1192.8
152.5°	1217.7	1216.9	1216.7	1216.4	1216.1	1215.9	1215.6	1215.3	1215.0	1214.7	1214.3
155°	1244.8	1243.7	1243.5	1243.2	1243.0	1242.8	1242.9	1243.4	1243.8	1244.2	1244.7
157.5°	1268.4	1267.0	1267.3	1267.5	1267.7	1267.9	1268.1	1268.1	1268.2	1268.2	1268.2
160°	1282.0	1280.6	1280.8	1281.1	1281.3	1281.5	1281.7	1282.0	1282.2	1282.4	1282.6
162.5°	1294.1	1292.6	1292.8	1293.0	1293.3	1293.5	1293.9	1294.5	1295.0	1295.6	1296.2
165°	1310.3	1308.6	1308.8	1309.0	1309.2	1309.5	1309.9	1310.6	1311.2	1311.9	1312.6
167.5°	1323.1	1321.3	1321.3	1321.3	1321.3	1321.3	1321.8	1322.7	1323.6	1324.5	1325.3
170°	1330.3	1328.5	1328.5	1328.5	1328.5	1328.5	1329.0	1329.9	1330.8	1331.6	1332.5
172.5°	1335.1	1333.3	1333.1	1333.0	1332.8	1332.6	1333.1	1334.1	1335.2	1336.3	1337.3
175°	1341.1	1339.5	1339.3	1339.1	1338.8	1338.6	1339.1	1340.2	1341.3	1342.4	1343.5
177.5°	1343.3	1341.9	1341.7	1341.6	1341.4	1341.2	1341.6	1342.4	1343.3	1344.2	1345.1
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P331892

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	483.8	484.8	487.9	490.2	492.8	494.3	495.7	496.9	498.4	498.7	504.1
5°	486.0	490.6	498.8	504.8	512.3	520.4	526.0	528.6	535.4	540.9	552.1
7.5°	485.4	495.3	507.6	520.4	534.0	546.7	557.7	570.8	580.0	594.0	607.7
10°	484.8	498.1	513.9	530.2	549.3	567.0	582.9	600.6	615.3	634.6	651.1
12.5°	483.1	499.2	521.2	540.5	563.7	588.1	611.6	634.3	647.3	679.5	694.7
15°	479.0	498.1	525.6	554.9	586.8	615.7	645.5	669.3	707.7	735.9	753.9
17.5°	471.1	497.8	530.4	565.8	604.6	642.7	676.5	712.5	753.3	787.4	823.8
20°	467.3	496.7	533.0	572.2	612.5	655.6	694.0	737.3	781.8	815.4	862.0
22.5°	460.4	493.7	532.8	576.4	619.5	664.1	709.1	752.8	804.2	850.4	894.8
25°	449.2	486.4	527.0	575.7	626.2	670.9	724.8	782.8	836.3	895.8	940.0
27.5°	437.3	477.1	517.7	563.0	617.4	670.5	738.2	803.7	869.2	920.5	953.3
30°	428.2	466.9	508.8	554.5	608.3	671.4	747.1	818.6	882.5	926.5	944.9
32.5°	418.3	457.5	494.6	542.5	599.9	670.8	752.7	827.4	883.2	912.5	908.9
35°	402.8	435.6	471.8	517.9	585.4	666.7	756.0	828.2	862.4	856.1	808.6
37.5°	380.4	408.1	443.6	494.1	568.7	658.1	749.4	803.6	801.4	750.2	681.3
40°	366.5	390.0	424.2	477.3	555.6	652.5	739.2	774.4	744.6	673.0	590.6
42.5°	348.2	369.9	404.1	458.7	541.3	641.2	719.6	729.8	671.5	589.2	513.6
45°	319.9	339.0	374.4	430.8	519.7	616.4	671.9	646.9	568.4	483.4	425.9
47.5°	289.4	309.3	343.3	401.3	488.6	579.2	605.6	552.6	472.0	403.0	350.2
50°	270.2	289.3	322.7	381.1	467.6	548.6	559.6	491.1	417.0	356.4	313.1
52.5°	250.9	268.8	301.6	360.3	443.0	513.2	506.5	436.7	368.6	316.9	282.9
55°	222.0	239.0	270.2	325.2	400.5	456.1	431.7	365.1	308.7	268.6	242.7
57.5°	196.2	212.5	239.4	289.1	354.5	392.8	361.7	305.5	260.7	229.8	210.6
60°	178.7	193.1	218.8	264.9	321.7	350.8	320.1	270.5	232.7	208.0	190.8
62.5°	162.1	174.7	198.4	240.3	289.7	314.1	283.0	241.0	208.9	187.0	172.3
65°	137.0	148.4	169.4	202.0	242.5	258.8	232.0	198.0	173.1	156.8	147.0
67.5°	114.1	123.8	141.9	167.5	197.4	209.2	188.8	162.5	143.7	130.6	122.9
70°	98.8	107.2	121.4	143.5	170.5	179.6	160.5	138.8	125.1	114.6	107.4
72.5°	85.9	92.1	105.0	122.1	144.6	151.8	138.5	119.5	106.7	98.8	93.0
75°	65.5	70.6	79.0	92.7	108.3	112.5	102.5	90.6	82.0	76.4	72.0
77.5°	47.2	51.0	57.0	65.5	76.3	80.1	73.8	65.8	59.5	55.8	53.3
80°	35.6	38.7	43.8	50.8	57.3	59.4	55.7	49.6	45.2	43.1	41.0
82.5°	26.3	28.0	31.1	35.9	40.3	42.8	39.7	36.0	33.6	31.7	30.9
85°	13.3	14.2	15.6	17.5	20.3	21.2	20.0	19.1	17.7	16.5	16.5
87.5°	5.5	5.9	6.9	7.8	9.0	10.1	10.5	10.7	11.1	11.1	11.1
90°	3.2	5.4	7.7	9.9	12.4	15.3	18.2	21.1	24.0	24.8	25.7
92.5°	17.9	17.3	16.7	16.1	16.9	19.0	21.2	23.4	25.6	27.0	28.4
95°	51.8	42.7	33.6	24.5	21.2	23.6	26.1	28.5	30.9	32.5	34.0
97.5°	118.3	114.2	110.1	106.0	96.0	80.1	64.1	48.1	32.1	33.9	35.7
100°	173.1	177.6	182.0	186.4	171.3	136.7	102.1	67.5	32.9	34.7	36.5
102.5°	224.6	227.8	231.0	234.2	216.9	179.1	141.3	103.5	65.7	60.2	54.7
105°	299.9	302.3	304.8	307.2	298.4	278.5	258.5	238.6	218.6	179.3	140.1
107.5°	379.7	381.6	383.6	385.5	388.1	391.2	394.4	397.5	400.7	371.9	343.1
110°	433.0	434.7	436.5	438.3	440.4	442.8	445.3	447.7	450.2	442.8	435.5



TEST NUMBER: P331892

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	483.9	485.5	487.1	488.7	490.7	493.2	495.6	498.0	500.5	500.6	500.7
115°	559.3	560.6	562.0	563.3	565.0	566.9	568.9	570.9	572.9	575.2	577.4
117.5°	632.9	634.5	636.2	637.8	639.1	640.1	641.2	642.2	643.2	645.0	646.8
120°	678.7	680.7	682.7	684.7	686.1	686.7	687.4	688.1	688.7	690.5	692.3
122.5°	724.7	726.3	728.0	729.6	730.9	731.7	732.6	733.4	734.2	735.5	736.7
125°	788.3	790.1	791.9	793.6	795.0	795.9	796.7	797.6	798.5	799.0	799.4
127.5°	849.8	851.6	853.3	855.1	856.5	857.6	858.7	859.7	860.8	861.5	862.2
130°	888.1	889.9	891.7	893.5	894.8	895.7	896.6	897.4	898.3	899.2	900.1
132.5°	924.9	926.6	928.4	930.2	931.4	932.1	932.8	933.6	934.3	935.2	936.0
135°	980.5	981.8	983.2	984.5	985.6	986.5	987.4	988.3	989.2	989.8	990.5
137.5°	1028.8	1030.5	1032.2	1033.8	1034.9	1035.4	1035.9	1036.4	1036.9	1037.9	1039.0
140°	1060.4	1061.7	1063.0	1064.4	1065.4	1066.0	1066.7	1067.4	1068.0	1068.9	1069.8
142.5°	1089.9	1091.2	1092.6	1093.9	1094.9	1095.6	1096.2	1096.9	1097.6	1098.3	1099.0
145°	1131.5	1133.0	1134.6	1136.1	1137.1	1137.6	1138.0	1138.4	1138.9	1139.3	1139.8
147.5°	1169.9	1170.9	1171.9	1172.9	1173.6	1174.1	1174.5	1175.0	1175.4	1175.9	1176.3
150°	1193.5	1194.1	1194.8	1195.4	1196.0	1196.4	1196.9	1197.3	1197.8	1198.2	1198.7
152.5°	1214.7	1215.0	1215.3	1215.6	1215.9	1216.1	1216.4	1216.7	1216.9	1217.7	1218.5
155°	1244.2	1243.8	1243.4	1242.9	1242.8	1243.0	1243.2	1243.5	1243.7	1244.8	1245.9
157.5°	1268.2	1268.2	1268.1	1268.1	1267.9	1267.7	1267.5	1267.3	1267.0	1268.4	1269.7
160°	1282.4	1282.2	1282.0	1281.7	1281.5	1281.3	1281.1	1280.8	1280.6	1282.0	1283.3
162.5°	1295.6	1295.0	1294.5	1293.9	1293.5	1293.3	1293.0	1292.8	1292.6	1294.1	1295.6
165°	1311.9	1311.2	1310.6	1309.9	1309.5	1309.2	1309.0	1308.8	1308.6	1310.3	1312.1
167.5°	1324.5	1323.6	1322.7	1321.8	1321.3	1321.3	1321.3	1321.3	1321.3	1323.1	1324.9
170°	1331.6	1330.8	1329.9	1329.0	1328.5	1328.5	1328.5	1328.5	1328.5	1330.3	1332.1
172.5°	1336.3	1335.2	1334.1	1333.1	1332.6	1332.8	1333.0	1333.1	1333.3	1335.1	1336.9
175°	1342.4	1341.3	1340.2	1339.1	1338.6	1338.8	1339.1	1339.3	1339.5	1341.1	1342.6
177.5°	1344.2	1343.3	1342.4	1341.6	1341.2	1341.4	1341.6	1341.7	1341.9	1343.3	1344.7
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P331892

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	506.0	506.2	508.2	509.7	509.0	509.9	510.3
5°	552.8	561.2	565.6	568.9	569.1	569.4	571.2
7.5°	619.2	628.2	634.8	644.8	647.7	651.1	650.2
10°	667.7	681.0	692.4	698.4	705.0	714.5	706.8
12.5°	713.0	736.5	753.9	763.3	769.4	771.3	767.6
15°	787.7	818.4	834.9	834.5	855.4	864.5	850.3
17.5°	856.1	884.5	907.3	918.9	936.4	940.2	938.5
20°	898.1	929.1	946.8	966.8	975.9	984.0	985.4
22.5°	934.2	962.1	981.1	997.7	1005.3	1009.2	1011.5
25°	971.5	993.4	1004.8	1010.6	1012.7	1012.2	1009.2
27.5°	968.9	970.6	958.0	945.7	934.6	922.2	917.9
30°	943.7	924.2	889.2	869.4	840.3	817.2	826.6
32.5°	877.6	838.6	799.4	756.1	720.3	710.1	699.8
35°	749.0	680.5	640.4	593.8	575.2	556.6	543.7
37.5°	605.9	553.0	505.4	475.0	456.3	444.5	438.2
40°	523.9	476.2	437.0	412.3	398.1	384.9	383.0
42.5°	458.5	414.1	384.7	365.0	351.4	345.7	341.6
45°	375.5	344.6	324.8	310.8	301.7	298.2	293.5
47.5°	317.9	296.0	281.1	271.6	264.7	262.1	261.8
50°	285.6	267.4	256.5	249.0	243.7	242.7	239.0
52.5°	261.4	245.6	237.1	230.6	226.7	224.1	223.0
55°	226.9	216.4	208.7	205.0	202.0	199.4	199.4
57.5°	198.5	189.8	184.7	181.5	180.6	178.8	177.6
60°	181.0	173.6	169.6	166.8	164.9	165.2	163.1
62.5°	163.9	159.0	155.2	152.5	150.2	150.3	150.4
65°	139.5	135.8	133.0	132.1	130.7	129.1	129.5
67.5°	118.3	114.8	112.6	111.0	110.5	109.6	111.0
70°	103.0	100.4	98.8	97.4	96.9	97.1	98.3
72.5°	89.0	87.2	86.1	85.5	84.4	84.5	85.3
75°	69.9	68.5	67.6	66.9	66.6	66.6	66.6
77.5°	51.3	51.0	50.6	49.6	49.6	49.9	49.9
80°	40.5	39.8	39.6	39.1	38.4	38.0	39.1
82.5°	30.3	29.6	29.4	29.3	28.2	28.1	29.1
85°	16.3	15.6	15.8	15.6	15.6	15.4	15.4
87.5°	11.1	11.1	11.0	11.3	11.2	11.1	11.6
90°	26.6	27.5	28.2	28.6	29.1	29.5	29.9
92.5°	29.8	31.2	32.1	32.3	32.6	32.9	33.1
95°	35.6	37.2	37.9	37.9	37.9	37.9	37.9
97.5°	37.5	39.2	40.2	40.5	40.7	40.9	41.1
100°	38.3	40.0	41.0	41.3	41.5	41.7	41.9
102.5°	49.2	43.7	41.1	41.5	41.9	42.3	42.7
105°	100.8	61.6	42.1	42.6	43.0	43.5	43.9
107.5°	314.3	285.5	256.3	226.7	197.1	167.5	137.9
110°	428.2	420.9	401.4	369.6	337.9	306.2	274.5



TEST NUMBER: P331892

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	500.9	501.0	497.7	491.0	484.3	477.6	470.9
115°	579.6	581.8	583.4	584.2	585.1	586.0	586.9
117.5°	648.5	650.3	651.3	651.5	651.6	651.8	652.0
120°	694.0	695.8	696.7	696.7	696.7	696.7	696.7
122.5°	738.0	739.2	739.9	740.1	740.3	740.4	740.6
125°	799.8	800.3	800.7	801.2	801.6	802.1	802.5
127.5°	862.9	863.6	863.8	863.3	862.9	862.4	862.0
130°	901.0	901.9	902.1	901.7	901.2	900.8	900.3
132.5°	936.9	937.8	937.9	937.3	936.7	936.1	935.5
135°	991.2	991.8	991.8	991.2	990.5	989.8	989.2
137.5°	1040.1	1041.1	1041.4	1041.0	1040.6	1040.1	1039.7
140°	1070.7	1071.6	1071.8	1071.3	1070.9	1070.5	1070.0
142.5°	1099.7	1100.4	1100.4	1099.8	1099.2	1098.6	1098.0
145°	1140.2	1140.7	1140.9	1140.9	1140.9	1140.9	1140.9
147.5°	1176.7	1177.2	1176.9	1175.9	1174.9	1173.8	1172.8
150°	1199.1	1199.6	1199.4	1198.8	1198.1	1197.4	1196.8
152.5°	1219.3	1220.1	1220.0	1219.0	1218.0	1217.0	1215.9
155°	1247.0	1248.1	1248.0	1246.7	1245.4	1244.0	1242.7
157.5°	1271.0	1272.4	1272.2	1270.4	1268.7	1267.0	1265.3
160°	1284.6	1285.9	1285.8	1284.3	1282.7	1281.2	1279.6
162.5°	1297.1	1298.6	1298.7	1297.3	1295.9	1294.6	1293.2
165°	1313.9	1315.7	1315.8	1314.2	1312.7	1311.1	1309.6
167.5°	1326.7	1328.4	1328.4	1326.7	1324.9	1323.1	1321.3
170°	1333.9	1335.6	1335.6	1333.9	1332.1	1330.3	1328.5
172.5°	1338.6	1340.4	1340.3	1338.4	1336.4	1334.5	1332.5
175°	1344.2	1345.7	1345.6	1343.8	1342.1	1340.3	1338.5
177.5°	1346.2	1347.6	1347.4	1345.6	1343.9	1342.1	1340.3
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5

(END OF REPORT)