

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331901

Luminaire Tested: **S123DIP-S340D1195U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331901
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D1195U835-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6224.5 lumens
Efficiency: N/A
Efficacy: 147.5 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331901
CATALOG NUMBER: S123DIP-S340D1195U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331901

CATALOG NUMBER: S123DIP-S340D1195U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32	23
1	92	88	84	81	82	78	75	72	60	58	56	43	42	41	28	27	27	20
2	84	77	71	66	74	68	64	59	53	49	47	38	36	34	25	24	23	17
3	76	67	61	55	68	60	54	50	47	43	39	34	31	29	22	21	20	14
4	70	60	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	12
5	64	53	45	40	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	11	8
8	50	39	31	26	45	35	28	24	27	22	19	20	17	15	13	12	10	8
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	11	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5175	5175	5175	5175
5°	6172	5198	4606	5198
10°	7725	5172	4161	5172
15°	9475	5129	3874	5129
20°	11287	5065	3688	5065
25°	11986	4986	3646	4986
30°	10274	4928	3665	4928
35°	7144	4846	3704	4846
40°	5382	4749	3693	4749
45°	4468	4606	3646	4606
50°	4002	4315	3612	4315
55°	3742	4001	3567	4001
60°	3511	3670	3531	3670
65°	3298	3347	3418	3347
70°	3094	2977	3254	2977
75°	2770	2608	2986	2608
80°	2424	2139	2572	2139
85°	1902	1556	1729	1556



TEST NUMBER: P331901

CATALOG NUMBER: S123DIP-S340D1195U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.4	0.8
10°-20°	151.9	2.4
20°-30°	254.9	4.1
30°-40°	288.6	4.6
40°-50°	258.8	4.2
50°-60°	208.9	3.4
60°-70°	145.6	2.3
70°-80°	76.5	1.2
80°-90°	23.1	0.4
90°-100°	56.9	0.9
100°-110°	271.0	4.4
110°-120°	650.9	10.5
120°-130°	828.8	13.3
130°-140°	885.6	14.2
140°-150°	828.1	13.3
150°-160°	668.0	10.7
160°-170°	431.1	6.9
170°-180°	148.6	2.4
0°-30°	454.2	7.3
0°-40°	742.8	11.9
0°-60°	1210.5	19.4
0°-90°	1455.6	23.4
90°-120°	978.7	15.7
90°-150°	3521.2	56.6
90°-180°	4769.0	76.6
0°-180°	6224.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	481	481	481	481	481	
5°	571	481	426	481	571	59
15°	850	460	348	460	850	246
25°	1009	420	307	420	1009	443
35°	544	369	282	369	544	353
45°	294	303	240	303	294	232
55°	199	213	190	213	199	179
65°	130	131	134	131	130	129
75°	67	63	72	63	67	71
85°	15	13	14	13	15	19
90°	35	1	35	1	35	17
95°	44	71	44	71	44	37
105°	51	346	51	346	51	117
115°	683	650	683	650	683	631
125°	934	916	934	916	934	834
135°	1151	1140	1151	1140	1151	888
145°	1328	1315	1328	1315	1328	829
155°	1446	1449	1446	1449	1446	667
165°	1524	1528	1524	1528	1524	430
175°	1558	1564	1558	1564	1558	148
180°	1564	1564	1564	1564	1564	



TEST NUMBER: P331901

CATALOG NUMBER: S123DIP-S340D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	510.3	509.9	509.0	509.7	508.2	506.2	506.0	504.1	498.7	498.4	496.9
5°	571.2	569.4	569.1	568.9	565.6	561.2	552.8	552.1	540.9	535.4	528.6
7.5°	650.2	651.1	647.7	644.8	634.8	628.2	619.2	607.7	594.0	580.0	570.8
10°	706.8	714.5	705.0	698.4	692.4	681.0	667.7	651.1	634.6	615.3	600.6
12.5°	767.6	771.3	769.4	763.3	753.9	736.5	713.0	694.7	679.5	647.3	634.3
15°	850.3	864.5	855.4	834.5	834.9	818.4	787.7	753.9	735.9	707.7	669.3
17.5°	938.5	940.2	936.4	918.9	907.3	884.5	856.1	823.8	787.4	753.3	712.5
20°	985.4	984.0	975.9	966.8	946.8	929.1	898.1	862.0	815.4	781.8	737.3
22.5°	1011.5	1009.2	1005.3	997.7	981.1	962.1	934.2	894.8	850.4	804.2	752.8
25°	1009.2	1012.2	1012.7	1010.6	1004.8	993.4	971.5	940.0	895.8	836.3	782.8
27.5°	917.9	922.2	934.6	945.7	958.0	970.6	968.9	953.3	920.5	869.2	803.7
30°	826.6	817.2	840.3	869.4	889.2	924.2	943.7	944.9	926.5	882.5	818.6
32.5°	699.8	710.1	720.3	756.1	799.4	838.6	877.6	908.9	912.5	883.2	827.4
35°	543.7	556.6	575.2	593.8	640.4	680.5	749.0	808.6	856.1	862.4	828.2
37.5°	438.2	444.5	456.3	475.0	505.4	553.0	605.9	681.3	750.2	801.4	803.6
40°	383.0	384.9	398.1	412.3	437.0	476.2	523.9	590.6	673.0	744.6	774.4
42.5°	341.6	345.7	351.4	365.0	384.7	414.1	458.5	513.6	589.2	671.5	729.8
45°	293.5	298.2	301.7	310.8	324.8	344.6	375.5	425.9	483.4	568.4	646.9
47.5°	261.8	262.1	264.7	271.6	281.1	296.0	317.9	350.2	403.0	472.0	552.6
50°	239.0	242.7	243.7	249.0	256.5	267.4	285.6	313.1	356.4	417.0	491.1
52.5°	223.0	224.1	226.7	230.6	237.1	245.6	261.4	282.9	316.9	368.6	436.7
55°	199.4	199.4	202.0	205.0	208.7	216.4	226.9	242.7	268.6	308.7	365.1
57.5°	177.6	178.8	180.6	181.5	184.7	189.8	198.5	210.6	229.8	260.7	305.5
60°	163.1	165.2	164.9	166.8	169.6	173.6	181.0	190.8	208.0	232.7	270.5
62.5°	150.4	150.3	150.2	152.5	155.2	159.0	163.9	172.3	187.0	208.9	241.0
65°	129.5	129.1	130.7	132.1	133.0	135.8	139.5	147.0	156.8	173.1	198.0
67.5°	111.0	109.6	110.5	111.0	112.6	114.8	118.3	122.9	130.6	143.7	162.5
70°	98.3	97.1	96.9	97.4	98.8	100.4	103.0	107.4	114.6	125.1	138.8
72.5°	85.3	84.5	84.4	85.5	86.1	87.2	89.0	93.0	98.8	106.7	119.5
75°	66.6	66.6	66.6	66.9	67.6	68.5	69.9	72.0	76.4	82.0	90.6
77.5°	49.9	49.9	49.6	49.6	50.6	51.0	51.3	53.3	55.8	59.5	65.8
80°	39.1	38.0	38.4	39.1	39.6	39.8	40.5	41.0	43.1	45.2	49.6
82.5°	29.1	28.1	28.2	29.3	29.4	29.6	30.3	30.9	31.7	33.6	36.0
85°	15.4	15.4	15.6	15.6	15.8	15.6	16.3	16.5	16.5	17.7	19.1
87.5°	12.6	12.1	12.2	12.3	12.0	12.0	12.0	12.0	11.9	11.9	11.4
90°	34.9	34.3	33.8	33.3	32.8	32.0	31.0	29.9	28.9	27.9	24.5
92.5°	38.6	38.3	38.0	37.6	37.3	36.4	34.7	33.0	31.4	29.7	27.2
95°	44.1	44.1	44.1	44.1	44.1	43.2	41.4	39.6	37.8	36.0	33.2
97.5°	47.9	47.6	47.4	47.1	46.8	45.7	43.6	41.5	39.5	37.4	35.0
100°	48.8	48.5	48.3	48.0	47.8	46.6	44.5	42.5	40.4	38.3	35.6
102.5°	49.7	49.3	48.8	48.3	47.9	50.8	57.2	63.6	70.0	76.4	120.4
105°	51.1	50.6	50.1	49.6	49.1	71.6	117.3	163.0	208.7	254.4	277.7
107.5°	160.6	195.0	229.4	263.9	298.3	332.3	365.8	399.3	432.8	466.4	462.7
110°	319.5	356.4	393.3	430.3	467.2	489.9	498.4	506.9	515.5	524.0	521.1



TEST NUMBER: P331901

CATALOG NUMBER: S123DIP-S340D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	548.1	555.9	563.7	571.5	579.3	583.2	583.0	582.8	582.7	582.5	579.7
115°	683.1	682.1	681.1	680.0	679.0	677.2	674.6	672.0	669.5	666.9	664.6
117.5°	758.9	758.7	758.5	758.3	758.1	756.9	754.9	752.8	750.7	748.7	747.5
120°	810.9	810.9	810.9	810.9	810.9	809.9	807.8	805.8	803.7	801.6	800.9
122.5°	862.1	861.9	861.6	861.4	861.2	860.4	859.0	857.5	856.1	854.6	853.6
125°	934.1	933.6	933.1	932.5	932.0	931.5	931.0	930.5	930.0	929.4	928.4
127.5°	1003.3	1003.9	1004.4	1004.9	1005.4	1005.2	1004.4	1003.6	1002.8	1001.9	1000.7
130°	1048.0	1048.5	1049.0	1049.5	1050.0	1049.8	1048.7	1047.7	1046.7	1045.6	1044.6
132.5°	1088.8	1089.6	1090.3	1091.0	1091.7	1091.6	1090.6	1089.5	1088.5	1087.5	1086.6
135°	1151.4	1152.1	1152.9	1153.7	1154.5	1154.5	1153.7	1152.9	1152.1	1151.4	1150.3
137.5°	1210.1	1210.7	1211.2	1211.7	1212.2	1211.8	1210.6	1209.4	1208.1	1206.9	1206.3
140°	1245.5	1246.0	1246.5	1247.0	1247.5	1247.3	1246.2	1245.2	1244.2	1243.1	1242.4
142.5°	1278.0	1278.7	1279.4	1280.2	1280.9	1280.8	1280.0	1279.2	1278.4	1277.5	1276.8
145°	1327.9	1327.9	1327.9	1327.9	1327.9	1327.7	1327.2	1326.7	1326.1	1325.6	1325.1
147.5°	1365.1	1366.3	1367.5	1368.7	1369.9	1370.2	1369.7	1369.2	1368.7	1368.1	1367.6
150°	1393.0	1393.8	1394.6	1395.3	1396.1	1396.2	1395.7	1395.2	1394.7	1394.2	1393.7
152.5°	1415.3	1416.5	1417.7	1418.9	1420.1	1420.2	1419.3	1418.3	1417.4	1416.5	1416.2
155°	1446.5	1448.0	1449.6	1451.1	1452.6	1452.8	1451.5	1450.2	1448.9	1447.6	1447.4
157.5°	1472.7	1474.7	1476.7	1478.8	1480.8	1481.0	1479.4	1477.9	1476.4	1474.8	1475.1
160°	1489.4	1491.2	1493.1	1494.9	1496.7	1496.8	1495.2	1493.7	1492.2	1490.6	1490.9
162.5°	1505.2	1506.8	1508.4	1510.0	1511.6	1511.6	1509.8	1508.1	1506.3	1504.5	1504.8
165°	1524.3	1526.1	1527.9	1529.7	1531.5	1531.4	1529.3	1527.3	1525.2	1523.1	1523.4
167.5°	1538.0	1540.1	1542.1	1544.2	1546.3	1546.3	1544.2	1542.1	1540.1	1538.0	1538.0
170°	1546.4	1548.4	1550.5	1552.6	1554.6	1554.6	1552.6	1550.5	1548.4	1546.4	1546.4
172.5°	1551.0	1553.3	1555.6	1557.8	1560.1	1560.2	1558.1	1556.1	1554.0	1551.9	1551.7
175°	1558.0	1560.1	1562.1	1564.2	1566.2	1566.4	1564.6	1562.8	1561.0	1559.1	1558.9
177.5°	1560.1	1562.1	1564.2	1566.3	1568.3	1568.5	1566.9	1565.2	1563.6	1561.9	1561.7
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P331901

CATALOG NUMBER: S123DIP-S340D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	495.7	494.3	492.8	490.2	487.9	484.8	483.8	482.7	479.3	476.4	474.1
5°	526.0	520.4	512.3	504.8	498.8	490.6	486.0	481.1	474.1	467.8	462.7
7.5°	557.7	546.7	534.0	520.4	507.6	495.3	485.4	476.5	466.7	457.5	450.2
10°	582.9	567.0	549.3	530.2	513.9	498.1	484.8	473.2	460.6	449.6	440.5
12.5°	611.6	588.1	563.7	540.5	521.2	499.2	483.1	468.3	454.0	440.9	430.7
15°	645.5	615.7	586.8	554.9	525.6	498.1	479.0	460.3	443.8	430.3	417.2
17.5°	676.5	642.7	604.6	565.8	530.4	497.8	471.1	450.0	429.3	412.8	399.8
20°	694.0	655.6	612.5	572.2	533.0	496.7	467.3	442.2	419.8	402.3	387.7
22.5°	709.1	664.1	619.5	576.4	532.8	493.7	460.4	434.5	410.3	393.2	377.6
25°	724.8	670.9	626.2	575.7	527.0	486.4	449.2	419.8	395.6	375.5	359.5
27.5°	738.2	670.5	617.4	563.0	517.7	477.1	437.3	405.8	380.1	358.3	342.0
30°	747.1	671.4	608.3	554.5	508.8	466.9	428.2	396.5	369.5	347.4	332.0
32.5°	752.7	670.8	599.9	542.5	494.6	457.5	418.3	385.5	357.7	336.0	321.2
35°	756.0	666.7	585.4	517.9	471.8	435.6	402.8	368.8	339.7	319.4	302.6
37.5°	749.4	658.1	568.7	494.1	443.6	408.1	380.4	351.5	323.6	301.3	286.8
40°	739.2	652.5	555.6	477.3	424.2	390.0	366.5	338.0	310.5	289.3	275.8
42.5°	719.6	641.2	541.3	458.7	404.1	369.9	348.2	324.4	298.4	278.5	265.0
45°	671.9	616.4	519.7	430.8	374.4	339.0	319.9	302.6	279.1	259.8	248.1
47.5°	605.6	579.2	488.6	401.3	343.3	309.3	289.4	275.6	258.4	242.7	231.6
50°	559.6	548.6	467.6	381.1	322.7	289.3	270.2	257.7	245.3	229.7	219.5
52.5°	506.5	513.2	443.0	360.3	301.6	268.8	250.9	240.9	229.7	216.8	207.9
55°	431.7	456.1	400.5	325.2	270.2	239.0	222.0	213.2	206.6	197.1	189.4
57.5°	361.7	392.8	354.5	289.1	239.4	212.5	196.2	186.6	182.4	177.4	171.3
60°	320.1	350.8	321.7	264.9	218.8	193.1	178.7	170.5	166.3	162.8	157.7
62.5°	283.0	314.1	289.7	240.3	198.4	174.7	162.1	154.1	150.9	149.1	144.7
65°	232.0	258.8	242.5	202.0	169.4	148.4	137.0	131.4	128.4	127.7	124.9
67.5°	188.8	209.2	197.4	167.5	141.9	123.8	114.1	109.3	107.0	106.7	104.6
70°	160.5	179.6	170.5	143.5	121.4	107.2	98.8	94.6	93.2	93.0	91.8
72.5°	138.5	151.8	144.6	122.1	105.0	92.1	85.9	81.5	80.0	80.3	79.5
75°	102.5	112.5	108.3	92.7	79.0	70.6	65.5	62.7	61.3	62.0	61.0
77.5°	73.8	80.1	76.3	65.5	57.0	51.0	47.2	45.5	44.2	44.2	43.8
80°	55.7	59.4	57.3	50.8	43.8	38.7	35.6	34.5	33.8	33.5	33.3
82.5°	39.7	42.8	40.3	35.9	31.1	28.0	26.3	24.8	24.3	24.4	24.2
85°	20.0	21.2	20.3	17.5	15.6	14.2	13.3	12.6	12.1	12.3	11.9
87.5°	11.1	10.6	9.4	8.1	7.2	6.1	5.6	4.7	4.8	5.4	5.7
90°	21.2	17.8	14.5	11.5	8.9	6.3	3.7	1.2	3.7	6.3	8.9
92.5°	24.7	22.2	19.6	18.7	19.4	20.2	20.9	21.6	20.9	20.2	19.4
95°	30.3	27.5	24.7	28.5	39.1	49.7	60.3	70.9	60.3	49.7	39.1
97.5°	74.6	93.2	111.8	123.4	128.2	132.9	137.7	142.4	137.7	132.9	128.2
100°	118.9	159.2	199.4	217.0	211.8	206.7	201.5	196.3	201.5	206.7	211.8
102.5°	164.4	208.4	252.4	272.6	268.8	265.1	261.4	257.7	261.4	265.1	268.8
105°	300.9	324.1	347.4	357.6	354.7	351.9	349.1	346.2	349.1	351.9	354.7
107.5°	459.0	455.4	451.7	448.7	446.4	444.2	441.9	439.6	441.9	444.2	446.4
110°	518.3	515.5	512.6	510.2	508.1	506.0	504.0	501.9	504.0	506.0	508.1



TEST NUMBER: P331901

CATALOG NUMBER: S123DIP-S340D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	576.9	574.0	571.2	568.8	567.0	565.1	563.2	561.4	563.2	565.1	567.0
115°	662.2	659.9	657.6	655.6	654.1	652.5	651.0	649.5	651.0	652.5	654.1
117.5°	746.3	745.1	743.9	742.4	740.5	738.5	736.6	734.7	736.6	738.5	740.5
120°	800.1	799.3	798.6	797.0	794.7	792.4	790.0	787.7	790.0	792.4	794.7
122.5°	852.7	851.7	850.7	849.3	847.3	845.4	843.5	841.6	843.5	845.4	847.3
125°	927.4	926.3	925.3	923.8	921.7	919.6	917.6	915.5	917.6	919.6	921.7
127.5°	999.5	998.2	997.0	995.3	993.3	991.2	989.1	987.1	989.1	991.2	993.3
130°	1043.6	1042.5	1041.5	1039.9	1037.9	1035.8	1033.8	1031.7	1033.8	1035.8	1037.9
132.5°	1085.8	1085.0	1084.1	1082.7	1080.6	1078.6	1076.5	1074.4	1076.5	1078.6	1080.6
135°	1149.3	1148.3	1147.2	1145.9	1144.4	1142.8	1141.3	1139.7	1141.3	1142.8	1144.4
137.5°	1205.8	1205.2	1204.6	1203.4	1201.4	1199.4	1197.5	1195.5	1197.5	1199.4	1201.4
140°	1241.6	1240.8	1240.0	1238.9	1237.3	1235.8	1234.2	1232.7	1234.2	1235.8	1237.3
142.5°	1276.0	1275.2	1274.4	1273.3	1271.7	1270.2	1268.6	1267.1	1268.6	1270.2	1271.7
145°	1324.6	1324.1	1323.6	1322.4	1320.6	1318.8	1317.0	1315.2	1317.0	1318.8	1320.6
147.5°	1367.1	1366.6	1366.1	1365.2	1364.0	1362.9	1361.7	1360.5	1361.7	1362.9	1364.0
150°	1393.1	1392.6	1392.1	1391.5	1390.7	1389.9	1389.1	1388.4	1389.1	1389.9	1390.7
152.5°	1415.9	1415.5	1415.2	1414.9	1414.5	1414.2	1413.8	1413.5	1413.8	1414.2	1414.5
155°	1447.1	1446.8	1446.6	1446.7	1447.2	1447.7	1448.3	1448.8	1448.3	1447.7	1447.2
157.5°	1475.3	1475.6	1475.8	1476.0	1476.0	1476.1	1476.1	1476.2	1476.1	1476.1	1476.0
160°	1491.1	1491.4	1491.6	1491.9	1492.2	1492.4	1492.7	1492.9	1492.7	1492.4	1492.2
162.5°	1505.1	1505.3	1505.6	1506.0	1506.7	1507.4	1508.1	1508.7	1508.1	1507.4	1506.7
165°	1523.6	1523.9	1524.2	1524.7	1525.5	1526.2	1527.0	1527.8	1527.0	1526.2	1525.5
167.5°	1538.0	1538.0	1538.0	1538.5	1539.6	1540.6	1541.6	1542.7	1541.6	1540.6	1539.6
170°	1546.4	1546.4	1546.4	1546.9	1547.9	1549.0	1550.0	1551.0	1550.0	1549.0	1547.9
172.5°	1551.5	1551.3	1551.1	1551.6	1552.9	1554.1	1555.4	1556.6	1555.4	1554.1	1552.9
175°	1558.6	1558.4	1558.1	1558.6	1559.9	1561.2	1562.5	1563.8	1562.5	1561.2	1559.9
177.5°	1561.5	1561.3	1561.1	1561.5	1562.6	1563.6	1564.6	1565.7	1564.6	1563.6	1562.6
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P331901

CATALOG NUMBER: S123DIP-S340D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	472.8	471.5	469.7	466.9	464.6	461.1	461.1	461.6	461.6	461.5	461.1
5°	458.5	455.0	450.8	445.9	440.8	435.6	434.7	432.8	431.5	430.5	429.4
7.5°	443.3	437.1	431.0	424.2	417.9	412.8	409.2	406.2	404.3	402.2	400.7
10°	433.1	425.4	418.2	411.0	403.0	396.7	392.8	390.0	387.9	386.0	385.1
12.5°	421.0	412.2	404.2	397.3	388.7	382.2	378.4	377.1	374.7	370.7	368.7
15°	403.3	395.1	385.6	375.1	370.9	363.0	358.5	356.4	355.0	352.0	351.1
17.5°	388.1	377.5	366.7	358.9	351.1	344.7	342.2	339.6	337.8	335.3	334.5
20°	376.0	366.5	356.7	348.3	340.1	333.1	331.0	329.2	327.3	326.2	325.2
22.5°	363.7	354.2	346.0	338.2	329.5	324.9	322.7	320.6	319.3	318.5	317.6
25°	346.4	338.0	328.9	322.0	315.0	311.9	310.5	309.4	308.4	307.3	307.0
27.5°	331.0	321.8	314.5	307.9	302.9	300.4	299.0	298.5	298.7	299.1	299.4
30°	319.4	311.0	305.0	299.4	294.7	292.4	292.1	292.1	293.1	293.3	293.8
32.5°	308.8	301.9	295.8	290.4	286.9	285.3	286.2	286.2	286.9	287.5	288.4
35°	293.3	287.2	282.6	277.9	274.9	275.6	276.1	276.5	277.7	279.1	280.0
37.5°	278.5	273.3	268.4	264.8	263.4	264.6	265.8	266.7	268.1	269.2	270.1
40°	267.9	263.9	259.3	256.0	256.5	257.2	258.1	259.3	260.5	261.2	262.1
42.5°	258.0	253.9	250.3	247.6	248.3	249.2	249.7	250.3	251.7	253.0	253.5
45°	243.0	239.7	236.5	234.8	235.3	235.8	236.2	236.9	238.1	239.0	239.3
47.5°	226.1	223.8	221.6	220.0	220.8	220.6	221.2	222.7	223.0	223.6	224.9
50°	215.3	213.2	210.6	210.1	210.1	210.1	210.4	212.2	212.2	213.2	214.1
52.5°	203.3	202.0	200.4	199.5	199.1	199.1	200.1	201.0	201.4	202.7	203.7
55°	185.7	184.3	182.9	182.2	181.7	182.2	184.0	184.5	185.7	186.4	187.1
57.5°	167.3	166.2	165.1	164.7	164.6	165.2	166.2	167.6	167.9	170.1	171.1
60°	155.2	153.5	152.6	152.6	152.1	154.2	153.8	156.1	156.6	158.0	159.6
62.5°	142.7	140.5	140.1	140.1	140.8	141.4	142.0	143.0	144.3	146.0	147.3
65°	122.5	121.4	123.0	122.8	122.3	123.7	123.7	124.9	126.3	127.9	130.5
67.5°	103.5	102.9	103.0	103.0	103.7	104.5	105.2	106.2	107.9	109.6	111.3
70°	90.6	91.3	90.2	91.1	91.8	92.0	92.5	93.9	95.7	96.9	98.8
72.5°	78.1	78.1	78.2	78.6	79.3	79.7	80.2	81.8	83.8	84.8	86.3
75°	60.1	59.9	60.6	60.6	61.7	62.2	62.7	63.4	65.2	66.6	67.8
77.5°	43.9	44.2	44.0	44.8	44.5	44.6	46.0	46.7	46.9	49.7	50.3
80°	33.1	33.5	33.8	34.0	34.2	33.8	35.4	36.1	36.1	37.7	38.9
82.5°	23.8	24.0	24.6	24.9	24.9	25.4	25.5	26.0	26.6	27.3	28.8
85°	11.9	12.6	12.8	12.6	12.8	12.3	13.0	13.3	13.5	13.5	13.5
87.5°	6.0	6.8	7.3	8.1	8.6	9.5	9.7	9.5	9.7	10.5	9.9
90°	11.5	14.5	17.8	21.2	24.5	27.9	28.9	29.9	31.0	32.0	32.8
92.5°	18.7	19.6	22.2	24.7	27.2	29.7	31.4	33.0	34.7	36.4	37.3
95°	28.5	24.7	27.5	30.3	33.2	36.0	37.8	39.6	41.4	43.2	44.1
97.5°	123.4	111.8	93.2	74.6	56.0	37.4	39.5	41.5	43.6	45.7	46.8
100°	217.0	199.4	159.2	118.9	78.6	38.3	40.4	42.5	44.5	46.6	47.8
102.5°	272.6	252.4	208.4	164.4	120.4	76.4	70.0	63.6	57.2	50.8	47.9
105°	357.6	347.4	324.1	300.9	277.7	254.4	208.7	163.0	117.3	71.6	49.1
107.5°	448.7	451.7	455.4	459.0	462.7	466.4	432.8	399.3	365.8	332.3	298.3
110°	510.2	512.6	515.5	518.3	521.1	524.0	515.5	506.9	498.4	489.9	467.2



TEST NUMBER: P331901

CATALOG NUMBER: S123DIP-S340D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	568.8	571.2	574.0	576.9	579.7	582.5	582.7	582.8	583.0	583.2	579.3
115°	655.6	657.6	659.9	662.2	664.6	666.9	669.5	672.0	674.6	677.2	679.0
117.5°	742.4	743.9	745.1	746.3	747.5	748.7	750.7	752.8	754.9	756.9	758.1
120°	797.0	798.6	799.3	800.1	800.9	801.6	803.7	805.8	807.8	809.9	810.9
122.5°	849.3	850.7	851.7	852.7	853.6	854.6	856.1	857.5	859.0	860.4	861.2
125°	923.8	925.3	926.3	927.4	928.4	929.4	930.0	930.5	931.0	931.5	932.0
127.5°	995.3	997.0	998.2	999.5	1000.7	1001.9	1002.8	1003.6	1004.4	1005.2	1005.4
130°	1039.9	1041.5	1042.5	1043.6	1044.6	1045.6	1046.7	1047.7	1048.7	1049.8	1050.0
132.5°	1082.7	1084.1	1085.0	1085.8	1086.6	1087.5	1088.5	1089.5	1090.6	1091.6	1091.7
135°	1145.9	1147.2	1148.3	1149.3	1150.3	1151.4	1152.1	1152.9	1153.7	1154.5	1154.5
137.5°	1203.4	1204.6	1205.2	1205.8	1206.3	1206.9	1208.1	1209.4	1210.6	1211.8	1212.2
140°	1238.9	1240.0	1240.8	1241.6	1242.4	1243.1	1244.2	1245.2	1246.2	1247.3	1247.5
142.5°	1273.3	1274.4	1275.2	1276.0	1276.8	1277.5	1278.4	1279.2	1280.0	1280.8	1280.9
145°	1322.4	1323.6	1324.1	1324.6	1325.1	1325.6	1326.1	1326.7	1327.2	1327.7	1327.9
147.5°	1365.2	1366.1	1366.6	1367.1	1367.6	1368.1	1368.7	1369.2	1369.7	1370.2	1369.9
150°	1391.5	1392.1	1392.6	1393.1	1393.7	1394.2	1394.7	1395.2	1395.7	1396.2	1396.1
152.5°	1414.9	1415.2	1415.5	1415.9	1416.2	1416.5	1417.4	1418.3	1419.3	1420.2	1420.1
155°	1446.7	1446.6	1446.8	1447.1	1447.4	1447.6	1448.9	1450.2	1451.5	1452.8	1452.6
157.5°	1476.0	1475.8	1475.6	1475.3	1475.1	1474.8	1476.4	1477.9	1479.4	1481.0	1480.8
160°	1491.9	1491.6	1491.4	1491.1	1490.9	1490.6	1492.2	1493.7	1495.2	1496.8	1496.7
162.5°	1506.0	1505.6	1505.3	1505.1	1504.8	1504.5	1506.3	1508.1	1509.8	1511.6	1511.6
165°	1524.7	1524.2	1523.9	1523.6	1523.4	1523.1	1525.2	1527.3	1529.3	1531.4	1531.5
167.5°	1538.5	1538.0	1538.0	1538.0	1538.0	1538.0	1540.1	1542.1	1544.2	1546.3	1546.3
170°	1546.9	1546.4	1546.4	1546.4	1546.4	1546.4	1548.4	1550.5	1552.6	1554.6	1554.6
172.5°	1551.6	1551.1	1551.3	1551.5	1551.7	1551.9	1554.0	1556.1	1558.1	1560.2	1560.1
175°	1558.6	1558.1	1558.4	1558.6	1558.9	1559.1	1561.0	1562.8	1564.6	1566.4	1566.2
177.5°	1561.5	1561.1	1561.3	1561.5	1561.7	1561.9	1563.6	1565.2	1566.9	1568.5	1568.3
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P331901

CATALOG NUMBER: S123DIP-S340D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	459.8	459.6	460.9	460.0	460.9	459.6	459.8	461.1	461.5	461.6	461.6
5°	428.0	428.7	426.3	426.3	426.3	428.7	428.0	429.4	430.5	431.5	432.8
7.5°	399.6	398.6	398.7	397.4	398.7	398.6	399.6	400.7	402.2	404.3	406.2
10°	382.3	380.9	380.4	380.7	380.4	380.9	382.3	385.1	386.0	387.9	390.0
12.5°	367.9	367.7	364.6	364.6	364.6	367.7	367.9	368.7	370.7	374.7	377.1
15°	351.1	346.7	346.2	347.6	346.2	346.7	351.1	351.1	352.0	355.0	356.4
17.5°	334.2	331.8	332.0	331.3	332.0	331.8	334.2	334.5	335.3	337.8	339.6
20°	325.2	323.8	323.6	322.0	323.6	323.8	325.2	325.2	326.2	327.3	329.2
22.5°	317.0	316.6	316.7	314.9	316.7	316.6	317.0	317.6	318.5	319.3	320.6
25°	306.8	308.0	307.0	307.0	307.0	308.0	306.8	307.0	307.3	308.4	309.4
27.5°	299.9	299.9	299.4	299.4	299.4	299.9	299.9	299.4	299.1	298.7	298.5
30°	294.7	294.5	294.9	294.9	294.9	294.5	294.7	293.8	293.3	293.1	292.1
32.5°	289.5	289.8	289.9	290.1	289.9	289.8	289.5	288.4	287.5	286.9	286.2
35°	281.4	281.7	282.4	281.9	282.4	281.7	281.4	280.0	279.1	277.7	276.5
37.5°	270.5	271.6	271.4	271.7	271.4	271.6	270.5	270.1	269.2	268.1	266.7
40°	262.3	263.0	262.8	262.8	262.8	263.0	262.3	262.1	261.2	260.5	259.3
42.5°	253.9	254.4	253.8	253.5	253.8	254.4	253.9	253.5	253.0	251.7	250.3
45°	240.2	239.7	240.4	239.5	240.4	239.7	240.2	239.3	239.0	238.1	236.9
47.5°	224.8	225.3	225.5	226.2	225.5	225.3	224.8	224.9	223.6	223.0	222.7
50°	214.6	216.0	216.0	215.7	216.0	216.0	214.6	214.1	213.2	212.2	212.2
52.5°	204.5	205.1	206.1	206.0	206.1	205.1	204.5	203.7	202.7	201.4	201.0
55°	188.9	189.4	189.9	190.1	189.9	189.4	188.9	187.1	186.4	185.7	184.5
57.5°	172.8	172.6	173.7	174.1	173.7	172.6	172.8	171.1	170.1	167.9	167.6
60°	161.4	161.4	163.3	164.0	163.3	161.4	161.4	159.6	158.0	156.6	156.1
62.5°	149.3	150.1	151.9	151.0	151.9	150.1	149.3	147.3	146.0	144.3	143.0
65°	131.6	133.5	133.3	134.2	133.3	133.5	131.6	130.5	127.9	126.3	124.9
67.5°	113.1	114.3	116.0	116.1	116.0	114.3	113.1	111.3	109.6	107.9	106.2
70°	100.6	101.8	102.7	103.4	102.7	101.8	100.6	98.8	96.9	95.7	93.9
72.5°	88.5	89.1	91.4	90.4	91.4	89.1	88.5	86.3	84.8	83.8	81.8
75°	69.4	71.1	72.5	71.8	72.5	71.1	69.4	67.8	66.6	65.2	63.4
77.5°	51.3	53.0	53.6	53.0	53.6	53.0	51.3	50.3	49.7	46.9	46.7
80°	40.5	40.3	41.7	41.5	41.7	40.3	40.5	38.9	37.7	36.1	36.1
82.5°	29.7	29.5	30.1	30.3	30.1	29.5	29.7	28.8	27.3	26.6	26.0
85°	14.4	15.1	14.2	14.0	14.2	15.1	14.4	13.5	13.5	13.5	13.3
87.5°	10.0	10.1	10.0	10.0	10.0	10.1	10.0	9.9	10.5	9.7	9.5
90°	33.3	33.8	34.3	34.9	34.3	33.8	33.3	32.8	32.0	31.0	29.9
92.5°	37.6	38.0	38.3	38.6	38.3	38.0	37.6	37.3	36.4	34.7	33.0
95°	44.1	44.1	44.1	44.1	44.1	44.1	44.1	44.1	43.2	41.4	39.6
97.5°	47.1	47.4	47.6	47.9	47.6	47.4	47.1	46.8	45.7	43.6	41.5
100°	48.0	48.3	48.5	48.8	48.5	48.3	48.0	47.8	46.6	44.5	42.5
102.5°	48.3	48.8	49.3	49.7	49.3	48.8	48.3	47.9	50.8	57.2	63.6
105°	49.6	50.1	50.6	51.1	50.6	50.1	49.6	49.1	71.6	117.3	163.0
107.5°	263.9	229.4	195.0	160.6	195.0	229.4	263.9	298.3	332.3	365.8	399.3
110°	430.3	393.3	356.4	319.5	356.4	393.3	430.3	467.2	489.9	498.4	506.9



TEST NUMBER: P331901

CATALOG NUMBER: S123DIP-S340D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	571.5	563.7	555.9	548.1	555.9	563.7	571.5	579.3	583.2	583.0	582.8
115°	680.0	681.1	682.1	683.1	682.1	681.1	680.0	679.0	677.2	674.6	672.0
117.5°	758.3	758.5	758.7	758.9	758.7	758.5	758.3	758.1	756.9	754.9	752.8
120°	810.9	810.9	810.9	810.9	810.9	810.9	810.9	810.9	809.9	807.8	805.8
122.5°	861.4	861.6	861.9	862.1	861.9	861.6	861.4	861.2	860.4	859.0	857.5
125°	932.5	933.1	933.6	934.1	933.6	933.1	932.5	932.0	931.5	931.0	930.5
127.5°	1004.9	1004.4	1003.9	1003.3	1003.9	1004.4	1004.9	1005.4	1005.2	1004.4	1003.6
130°	1049.5	1049.0	1048.5	1048.0	1048.5	1049.0	1049.5	1050.0	1049.8	1048.7	1047.7
132.5°	1091.0	1090.3	1089.6	1088.8	1089.6	1090.3	1091.0	1091.7	1091.6	1090.6	1089.5
135°	1153.7	1152.9	1152.1	1151.4	1152.1	1152.9	1153.7	1154.5	1154.5	1153.7	1152.9
137.5°	1211.7	1211.2	1210.7	1210.1	1210.7	1211.2	1211.7	1212.2	1211.8	1210.6	1209.4
140°	1247.0	1246.5	1246.0	1245.5	1246.0	1246.5	1247.0	1247.5	1247.3	1246.2	1245.2
142.5°	1280.2	1279.4	1278.7	1278.0	1278.7	1279.4	1280.2	1280.9	1280.8	1280.0	1279.2
145°	1327.9	1327.9	1327.9	1327.9	1327.9	1327.9	1327.9	1327.9	1327.7	1327.2	1326.7
147.5°	1368.7	1367.5	1366.3	1365.1	1366.3	1367.5	1368.7	1369.9	1370.2	1369.7	1369.2
150°	1395.3	1394.6	1393.8	1393.0	1393.8	1394.6	1395.3	1396.1	1396.2	1395.7	1395.2
152.5°	1418.9	1417.7	1416.5	1415.3	1416.5	1417.7	1418.9	1420.1	1420.2	1419.3	1418.3
155°	1451.1	1449.6	1448.0	1446.5	1448.0	1449.6	1451.1	1452.6	1452.8	1451.5	1450.2
157.5°	1478.8	1476.7	1474.7	1472.7	1474.7	1476.7	1478.8	1480.8	1481.0	1479.4	1477.9
160°	1494.9	1493.1	1491.2	1489.4	1491.2	1493.1	1494.9	1496.7	1496.8	1495.2	1493.7
162.5°	1510.0	1508.4	1506.8	1505.2	1506.8	1508.4	1510.0	1511.6	1511.6	1509.8	1508.1
165°	1529.7	1527.9	1526.1	1524.3	1526.1	1527.9	1529.7	1531.5	1531.4	1529.3	1527.3
167.5°	1544.2	1542.1	1540.1	1538.0	1540.1	1542.1	1544.2	1546.3	1546.3	1544.2	1542.1
170°	1552.6	1550.5	1548.4	1546.4	1548.4	1550.5	1552.6	1554.6	1554.6	1552.6	1550.5
172.5°	1557.8	1555.6	1553.3	1551.0	1553.3	1555.6	1557.8	1560.1	1560.2	1558.1	1556.1
175°	1564.2	1562.1	1560.1	1558.0	1560.1	1562.1	1564.2	1566.2	1566.4	1564.6	1562.8
177.5°	1566.3	1564.2	1562.1	1560.1	1562.1	1564.2	1566.3	1568.3	1568.5	1566.9	1565.2
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P331901

CATALOG NUMBER: S123DIP-S340D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	461.1	461.1	464.6	466.9	469.7	471.5	472.8	474.1	476.4	479.3	482.7
5°	434.7	435.6	440.8	445.9	450.8	455.0	458.5	462.7	467.8	474.1	481.1
7.5°	409.2	412.8	417.9	424.2	431.0	437.1	443.3	450.2	457.5	466.7	476.5
10°	392.8	396.7	403.0	411.0	418.2	425.4	433.1	440.5	449.6	460.6	473.2
12.5°	378.4	382.2	388.7	397.3	404.2	412.2	421.0	430.7	440.9	454.0	468.3
15°	358.5	363.0	370.9	375.1	385.6	395.1	403.3	417.2	430.3	443.8	460.3
17.5°	342.2	344.7	351.1	358.9	366.7	377.5	388.1	399.8	412.8	429.3	450.0
20°	331.0	333.1	340.1	348.3	356.7	366.5	376.0	387.7	402.3	419.8	442.2
22.5°	322.7	324.9	329.5	338.2	346.0	354.2	363.7	377.6	393.2	410.3	434.5
25°	310.5	311.9	315.0	322.0	328.9	338.0	346.4	359.5	375.5	395.6	419.8
27.5°	299.0	300.4	302.9	307.9	314.5	321.8	331.0	342.0	358.3	380.1	405.8
30°	292.1	292.4	294.7	299.4	305.0	311.0	319.4	332.0	347.4	369.5	396.5
32.5°	286.2	285.3	286.9	290.4	295.8	301.9	308.8	321.2	336.0	357.7	385.5
35°	276.1	275.6	274.9	277.9	282.6	287.2	293.3	302.6	319.4	339.7	368.8
37.5°	265.8	264.6	263.4	264.8	268.4	273.3	278.5	286.8	301.3	323.6	351.5
40°	258.1	257.2	256.5	256.0	259.3	263.9	267.9	275.8	289.3	310.5	338.0
42.5°	249.7	249.2	248.3	247.6	250.3	253.9	258.0	265.0	278.5	298.4	324.4
45°	236.2	235.8	235.3	234.8	236.5	239.7	243.0	248.1	259.8	279.1	302.6
47.5°	221.2	220.6	220.8	220.0	221.6	223.8	226.1	231.6	242.7	258.4	275.6
50°	210.4	210.1	210.1	210.1	210.6	213.2	215.3	219.5	229.7	245.3	257.7
52.5°	200.1	199.1	199.1	199.5	200.4	202.0	203.3	207.9	216.8	229.7	240.9
55°	184.0	182.2	181.7	182.2	182.9	184.3	185.7	189.4	197.1	206.6	213.2
57.5°	166.2	165.2	164.6	164.7	165.1	166.2	167.3	171.3	177.4	182.4	186.6
60°	153.8	154.2	152.1	152.6	152.6	153.5	155.2	157.7	162.8	166.3	170.5
62.5°	142.0	141.4	140.8	140.1	140.1	140.5	142.7	144.7	149.1	150.9	154.1
65°	123.7	123.7	122.3	122.8	123.0	121.4	122.5	124.9	127.7	128.4	131.4
67.5°	105.2	104.5	103.7	103.0	103.0	102.9	103.5	104.6	106.7	107.0	109.3
70°	92.5	92.0	91.8	91.1	90.2	91.3	90.6	91.8	93.0	93.2	94.6
72.5°	80.2	79.7	79.3	78.6	78.2	78.1	78.1	79.5	80.3	80.0	81.5
75°	62.7	62.2	61.7	60.6	60.6	59.9	60.1	61.0	62.0	61.3	62.7
77.5°	46.0	44.6	44.5	44.8	44.0	44.2	43.9	43.8	44.2	44.2	45.5
80°	35.4	33.8	34.2	34.0	33.8	33.5	33.1	33.3	33.5	33.8	34.5
82.5°	25.5	25.4	24.9	24.9	24.6	24.0	23.8	24.2	24.4	24.3	24.8
85°	13.0	12.3	12.8	12.6	12.8	12.6	11.9	11.9	12.3	12.1	12.6
87.5°	9.7	9.5	8.6	8.1	7.3	6.8	6.0	5.7	5.4	4.8	4.7
90°	28.9	27.9	24.5	21.2	17.8	14.5	11.5	8.9	6.3	3.7	1.2
92.5°	31.4	29.7	27.2	24.7	22.2	19.6	18.7	19.4	20.2	20.9	21.6
95°	37.8	36.0	33.2	30.3	27.5	24.7	28.5	39.1	49.7	60.3	70.9
97.5°	39.5	37.4	56.0	74.6	93.2	111.8	123.4	128.2	132.9	137.7	142.4
100°	40.4	38.3	78.6	118.9	159.2	199.4	217.0	211.8	206.7	201.5	196.3
102.5°	70.0	76.4	120.4	164.4	208.4	252.4	272.6	268.8	265.1	261.4	257.7
105°	208.7	254.4	277.7	300.9	324.1	347.4	357.6	354.7	351.9	349.1	346.2
107.5°	432.8	466.4	462.7	459.0	455.4	451.7	448.7	446.4	444.2	441.9	439.6
110°	515.5	524.0	521.1	518.3	515.5	512.6	510.2	508.1	506.0	504.0	501.9



TEST NUMBER: P331901

CATALOG NUMBER: S123DIP-S340D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	582.7	582.5	579.7	576.9	574.0	571.2	568.8	567.0	565.1	563.2	561.4
115°	669.5	666.9	664.6	662.2	659.9	657.6	655.6	654.1	652.5	651.0	649.5
117.5°	750.7	748.7	747.5	746.3	745.1	743.9	742.4	740.5	738.5	736.6	734.7
120°	803.7	801.6	800.9	800.1	799.3	798.6	797.0	794.7	792.4	790.0	787.7
122.5°	856.1	854.6	853.6	852.7	851.7	850.7	849.3	847.3	845.4	843.5	841.6
125°	930.0	929.4	928.4	927.4	926.3	925.3	923.8	921.7	919.6	917.6	915.5
127.5°	1002.8	1001.9	1000.7	999.5	998.2	997.0	995.3	993.3	991.2	989.1	987.1
130°	1046.7	1045.6	1044.6	1043.6	1042.5	1041.5	1039.9	1037.9	1035.8	1033.8	1031.7
132.5°	1088.5	1087.5	1086.6	1085.8	1085.0	1084.1	1082.7	1080.6	1078.6	1076.5	1074.4
135°	1152.1	1151.4	1150.3	1149.3	1148.3	1147.2	1145.9	1144.4	1142.8	1141.3	1139.7
137.5°	1208.1	1206.9	1206.3	1205.8	1205.2	1204.6	1203.4	1201.4	1199.4	1197.5	1195.5
140°	1244.2	1243.1	1242.4	1241.6	1240.8	1240.0	1238.9	1237.3	1235.8	1234.2	1232.7
142.5°	1278.4	1277.5	1276.8	1276.0	1275.2	1274.4	1273.3	1271.7	1270.2	1268.6	1267.1
145°	1326.1	1325.6	1325.1	1324.6	1324.1	1323.6	1322.4	1320.6	1318.8	1317.0	1315.2
147.5°	1368.7	1368.1	1367.6	1367.1	1366.6	1366.1	1365.2	1364.0	1362.9	1361.7	1360.5
150°	1394.7	1394.2	1393.7	1393.1	1392.6	1392.1	1391.5	1390.7	1389.9	1389.1	1388.4
152.5°	1417.4	1416.5	1416.2	1415.9	1415.5	1415.2	1414.9	1414.5	1414.2	1413.8	1413.5
155°	1448.9	1447.6	1447.4	1447.1	1446.8	1446.6	1446.7	1447.2	1447.7	1448.3	1448.8
157.5°	1476.4	1474.8	1475.1	1475.3	1475.6	1475.8	1476.0	1476.0	1476.1	1476.1	1476.2
160°	1492.2	1490.6	1490.9	1491.1	1491.4	1491.6	1491.9	1492.2	1492.4	1492.7	1492.9
162.5°	1506.3	1504.5	1504.8	1505.1	1505.3	1505.6	1506.0	1506.7	1507.4	1508.1	1508.7
165°	1525.2	1523.1	1523.4	1523.6	1523.9	1524.2	1524.7	1525.5	1526.2	1527.0	1527.8
167.5°	1540.1	1538.0	1538.0	1538.0	1538.0	1538.0	1538.5	1539.6	1540.6	1541.6	1542.7
170°	1548.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.9	1547.9	1549.0	1550.0	1551.0
172.5°	1554.0	1551.9	1551.7	1551.5	1551.3	1551.1	1551.6	1552.9	1554.1	1555.4	1556.6
175°	1561.0	1559.1	1558.9	1558.6	1558.4	1558.1	1558.6	1559.9	1561.2	1562.5	1563.8
177.5°	1563.6	1561.9	1561.7	1561.5	1561.3	1561.1	1561.5	1562.6	1563.6	1564.6	1565.7
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P331901

CATALOG NUMBER: S123DIP-S340D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	483.8	484.8	487.9	490.2	492.8	494.3	495.7	496.9	498.4	498.7	504.1
5°	486.0	490.6	498.8	504.8	512.3	520.4	526.0	528.6	535.4	540.9	552.1
7.5°	485.4	495.3	507.6	520.4	534.0	546.7	557.7	570.8	580.0	594.0	607.7
10°	484.8	498.1	513.9	530.2	549.3	567.0	582.9	600.6	615.3	634.6	651.1
12.5°	483.1	499.2	521.2	540.5	563.7	588.1	611.6	634.3	647.3	679.5	694.7
15°	479.0	498.1	525.6	554.9	586.8	615.7	645.5	669.3	707.7	735.9	753.9
17.5°	471.1	497.8	530.4	565.8	604.6	642.7	676.5	712.5	753.3	787.4	823.8
20°	467.3	496.7	533.0	572.2	612.5	655.6	694.0	737.3	781.8	815.4	862.0
22.5°	460.4	493.7	532.8	576.4	619.5	664.1	709.1	752.8	804.2	850.4	894.8
25°	449.2	486.4	527.0	575.7	626.2	670.9	724.8	782.8	836.3	895.8	940.0
27.5°	437.3	477.1	517.7	563.0	617.4	670.5	738.2	803.7	869.2	920.5	953.3
30°	428.2	466.9	508.8	554.5	608.3	671.4	747.1	818.6	882.5	926.5	944.9
32.5°	418.3	457.5	494.6	542.5	599.9	670.8	752.7	827.4	883.2	912.5	908.9
35°	402.8	435.6	471.8	517.9	585.4	666.7	756.0	828.2	862.4	856.1	808.6
37.5°	380.4	408.1	443.6	494.1	568.7	658.1	749.4	803.6	801.4	750.2	681.3
40°	366.5	390.0	424.2	477.3	555.6	652.5	739.2	774.4	744.6	673.0	590.6
42.5°	348.2	369.9	404.1	458.7	541.3	641.2	719.6	729.8	671.5	589.2	513.6
45°	319.9	339.0	374.4	430.8	519.7	616.4	671.9	646.9	568.4	483.4	425.9
47.5°	289.4	309.3	343.3	401.3	488.6	579.2	605.6	552.6	472.0	403.0	350.2
50°	270.2	289.3	322.7	381.1	467.6	548.6	559.6	491.1	417.0	356.4	313.1
52.5°	250.9	268.8	301.6	360.3	443.0	513.2	506.5	436.7	368.6	316.9	282.9
55°	222.0	239.0	270.2	325.2	400.5	456.1	431.7	365.1	308.7	268.6	242.7
57.5°	196.2	212.5	239.4	289.1	354.5	392.8	361.7	305.5	260.7	229.8	210.6
60°	178.7	193.1	218.8	264.9	321.7	350.8	320.1	270.5	232.7	208.0	190.8
62.5°	162.1	174.7	198.4	240.3	289.7	314.1	283.0	241.0	208.9	187.0	172.3
65°	137.0	148.4	169.4	202.0	242.5	258.8	232.0	198.0	173.1	156.8	147.0
67.5°	114.1	123.8	141.9	167.5	197.4	209.2	188.8	162.5	143.7	130.6	122.9
70°	98.8	107.2	121.4	143.5	170.5	179.6	160.5	138.8	125.1	114.6	107.4
72.5°	85.9	92.1	105.0	122.1	144.6	151.8	138.5	119.5	106.7	98.8	93.0
75°	65.5	70.6	79.0	92.7	108.3	112.5	102.5	90.6	82.0	76.4	72.0
77.5°	47.2	51.0	57.0	65.5	76.3	80.1	73.8	65.8	59.5	55.8	53.3
80°	35.6	38.7	43.8	50.8	57.3	59.4	55.7	49.6	45.2	43.1	41.0
82.5°	26.3	28.0	31.1	35.9	40.3	42.8	39.7	36.0	33.6	31.7	30.9
85°	13.3	14.2	15.6	17.5	20.3	21.2	20.0	19.1	17.7	16.5	16.5
87.5°	5.6	6.1	7.2	8.1	9.4	10.6	11.1	11.4	11.9	11.9	12.0
90°	3.7	6.3	8.9	11.5	14.5	17.8	21.2	24.5	27.9	28.9	29.9
92.5°	20.9	20.2	19.4	18.7	19.6	22.2	24.7	27.2	29.7	31.4	33.0
95°	60.3	49.7	39.1	28.5	24.7	27.5	30.3	33.2	36.0	37.8	39.6
97.5°	137.7	132.9	128.2	123.4	111.8	93.2	74.6	56.0	37.4	39.5	41.5
100°	201.5	206.7	211.8	217.0	199.4	159.2	118.9	78.6	38.3	40.4	42.5
102.5°	261.4	265.1	268.8	272.6	252.4	208.4	164.4	120.4	76.4	70.0	63.6
105°	349.1	351.9	354.7	357.6	347.4	324.1	300.9	277.7	254.4	208.7	163.0
107.5°	441.9	444.2	446.4	448.7	451.7	455.4	459.0	462.7	466.4	432.8	399.3
110°	504.0	506.0	508.1	510.2	512.6	515.5	518.3	521.1	524.0	515.5	506.9



TEST NUMBER: P331901

CATALOG NUMBER: S123DIP-S340D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	563.2	565.1	567.0	568.8	571.2	574.0	576.9	579.7	582.5	582.7	582.8
115°	651.0	652.5	654.1	655.6	657.6	659.9	662.2	664.6	666.9	669.5	672.0
117.5°	736.6	738.5	740.5	742.4	743.9	745.1	746.3	747.5	748.7	750.7	752.8
120°	790.0	792.4	794.7	797.0	798.6	799.3	800.1	800.9	801.6	803.7	805.8
122.5°	843.5	845.4	847.3	849.3	850.7	851.7	852.7	853.6	854.6	856.1	857.5
125°	917.6	919.6	921.7	923.8	925.3	926.3	927.4	928.4	929.4	930.0	930.5
127.5°	989.1	991.2	993.3	995.3	997.0	998.2	999.5	1000.7	1001.9	1002.8	1003.6
130°	1033.8	1035.8	1037.9	1039.9	1041.5	1042.5	1043.6	1044.6	1045.6	1046.7	1047.7
132.5°	1076.5	1078.6	1080.6	1082.7	1084.1	1085.0	1085.8	1086.6	1087.5	1088.5	1089.5
135°	1141.3	1142.8	1144.4	1145.9	1147.2	1148.3	1149.3	1150.3	1151.4	1152.1	1152.9
137.5°	1197.5	1199.4	1201.4	1203.4	1204.6	1205.2	1205.8	1206.3	1206.9	1208.1	1209.4
140°	1234.2	1235.8	1237.3	1238.9	1240.0	1240.8	1241.6	1242.4	1243.1	1244.2	1245.2
142.5°	1268.6	1270.2	1271.7	1273.3	1274.4	1275.2	1276.0	1276.8	1277.5	1278.4	1279.2
145°	1317.0	1318.8	1320.6	1322.4	1323.6	1324.1	1324.6	1325.1	1325.6	1326.1	1326.7
147.5°	1361.7	1362.9	1364.0	1365.2	1366.1	1366.6	1367.1	1367.6	1368.1	1368.7	1369.2
150°	1389.1	1389.9	1390.7	1391.5	1392.1	1392.6	1393.1	1393.7	1394.2	1394.7	1395.2
152.5°	1413.8	1414.2	1414.5	1414.9	1415.2	1415.5	1415.9	1416.2	1416.5	1417.4	1418.3
155°	1448.3	1447.7	1447.2	1446.7	1446.6	1446.8	1447.1	1447.4	1447.6	1448.9	1450.2
157.5°	1476.1	1476.1	1476.0	1476.0	1475.8	1475.6	1475.3	1475.1	1474.8	1476.4	1477.9
160°	1492.7	1492.4	1492.2	1491.9	1491.6	1491.4	1491.1	1490.9	1490.6	1492.2	1493.7
162.5°	1508.1	1507.4	1506.7	1506.0	1505.6	1505.3	1505.1	1504.8	1504.5	1506.3	1508.1
165°	1527.0	1526.2	1525.5	1524.7	1524.2	1523.9	1523.6	1523.4	1523.1	1525.2	1527.3
167.5°	1541.6	1540.6	1539.6	1538.5	1538.0	1538.0	1538.0	1538.0	1538.0	1540.1	1542.1
170°	1550.0	1549.0	1547.9	1546.9	1546.4	1546.4	1546.4	1546.4	1546.4	1548.4	1550.5
172.5°	1555.4	1554.1	1552.9	1551.6	1551.1	1551.3	1551.5	1551.7	1551.9	1554.0	1556.1
175°	1562.5	1561.2	1559.9	1558.6	1558.1	1558.4	1558.6	1558.9	1559.1	1561.0	1562.8
177.5°	1564.6	1563.6	1562.6	1561.5	1561.1	1561.3	1561.5	1561.7	1561.9	1563.6	1565.2
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P331901

CATALOG NUMBER: S123DIP-S340D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	506.0	506.2	508.2	509.7	509.0	509.9	510.3
5°	552.8	561.2	565.6	568.9	569.1	569.4	571.2
7.5°	619.2	628.2	634.8	644.8	647.7	651.1	650.2
10°	667.7	681.0	692.4	698.4	705.0	714.5	706.8
12.5°	713.0	736.5	753.9	763.3	769.4	771.3	767.6
15°	787.7	818.4	834.9	834.5	855.4	864.5	850.3
17.5°	856.1	884.5	907.3	918.9	936.4	940.2	938.5
20°	898.1	929.1	946.8	966.8	975.9	984.0	985.4
22.5°	934.2	962.1	981.1	997.7	1005.3	1009.2	1011.5
25°	971.5	993.4	1004.8	1010.6	1012.7	1012.2	1009.2
27.5°	968.9	970.6	958.0	945.7	934.6	922.2	917.9
30°	943.7	924.2	889.2	869.4	840.3	817.2	826.6
32.5°	877.6	838.6	799.4	756.1	720.3	710.1	699.8
35°	749.0	680.5	640.4	593.8	575.2	556.6	543.7
37.5°	605.9	553.0	505.4	475.0	456.3	444.5	438.2
40°	523.9	476.2	437.0	412.3	398.1	384.9	383.0
42.5°	458.5	414.1	384.7	365.0	351.4	345.7	341.6
45°	375.5	344.6	324.8	310.8	301.7	298.2	293.5
47.5°	317.9	296.0	281.1	271.6	264.7	262.1	261.8
50°	285.6	267.4	256.5	249.0	243.7	242.7	239.0
52.5°	261.4	245.6	237.1	230.6	226.7	224.1	223.0
55°	226.9	216.4	208.7	205.0	202.0	199.4	199.4
57.5°	198.5	189.8	184.7	181.5	180.6	178.8	177.6
60°	181.0	173.6	169.6	166.8	164.9	165.2	163.1
62.5°	163.9	159.0	155.2	152.5	150.2	150.3	150.4
65°	139.5	135.8	133.0	132.1	130.7	129.1	129.5
67.5°	118.3	114.8	112.6	111.0	110.5	109.6	111.0
70°	103.0	100.4	98.8	97.4	96.9	97.1	98.3
72.5°	89.0	87.2	86.1	85.5	84.4	84.5	85.3
75°	69.9	68.5	67.6	66.9	66.6	66.6	66.6
77.5°	51.3	51.0	50.6	49.6	49.6	49.9	49.9
80°	40.5	39.8	39.6	39.1	38.4	38.0	39.1
82.5°	30.3	29.6	29.4	29.3	28.2	28.1	29.1
85°	16.3	15.6	15.8	15.6	15.6	15.4	15.4
87.5°	12.0	12.0	12.0	12.3	12.2	12.1	12.6
90°	31.0	32.0	32.8	33.3	33.8	34.3	34.9
92.5°	34.7	36.4	37.3	37.6	38.0	38.3	38.6
95°	41.4	43.2	44.1	44.1	44.1	44.1	44.1
97.5°	43.6	45.7	46.8	47.1	47.4	47.6	47.9
100°	44.5	46.6	47.8	48.0	48.3	48.5	48.8
102.5°	57.2	50.8	47.9	48.3	48.8	49.3	49.7
105°	117.3	71.6	49.1	49.6	50.1	50.6	51.1
107.5°	365.8	332.3	298.3	263.9	229.4	195.0	160.6
110°	498.4	489.9	467.2	430.3	393.3	356.4	319.5



TEST NUMBER: P331901

CATALOG NUMBER: S123DIP-S340D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	583.0	583.2	579.3	571.5	563.7	555.9	548.1
115°	674.6	677.2	679.0	680.0	681.1	682.1	683.1
117.5°	754.9	756.9	758.1	758.3	758.5	758.7	758.9
120°	807.8	809.9	810.9	810.9	810.9	810.9	810.9
122.5°	859.0	860.4	861.2	861.4	861.6	861.9	862.1
125°	931.0	931.5	932.0	932.5	933.1	933.6	934.1
127.5°	1004.4	1005.2	1005.4	1004.9	1004.4	1003.9	1003.3
130°	1048.7	1049.8	1050.0	1049.5	1049.0	1048.5	1048.0
132.5°	1090.6	1091.6	1091.7	1091.0	1090.3	1089.6	1088.8
135°	1153.7	1154.5	1154.5	1153.7	1152.9	1152.1	1151.4
137.5°	1210.6	1211.8	1212.2	1211.7	1211.2	1210.7	1210.1
140°	1246.2	1247.3	1247.5	1247.0	1246.5	1246.0	1245.5
142.5°	1280.0	1280.8	1280.9	1280.2	1279.4	1278.7	1278.0
145°	1327.2	1327.7	1327.9	1327.9	1327.9	1327.9	1327.9
147.5°	1369.7	1370.2	1369.9	1368.7	1367.5	1366.3	1365.1
150°	1395.7	1396.2	1396.1	1395.3	1394.6	1393.8	1393.0
152.5°	1419.3	1420.2	1420.1	1418.9	1417.7	1416.5	1415.3
155°	1451.5	1452.8	1452.6	1451.1	1449.6	1448.0	1446.5
157.5°	1479.4	1481.0	1480.8	1478.8	1476.7	1474.7	1472.7
160°	1495.2	1496.8	1496.7	1494.9	1493.1	1491.2	1489.4
162.5°	1509.8	1511.6	1511.6	1510.0	1508.4	1506.8	1505.2
165°	1529.3	1531.4	1531.5	1529.7	1527.9	1526.1	1524.3
167.5°	1544.2	1546.3	1546.3	1544.2	1542.1	1540.1	1538.0
170°	1552.6	1554.6	1554.6	1552.6	1550.5	1548.4	1546.4
172.5°	1558.1	1560.2	1560.1	1557.8	1555.6	1553.3	1551.0
175°	1564.6	1566.4	1566.2	1564.2	1562.1	1560.1	1558.0
177.5°	1566.9	1568.5	1568.3	1566.3	1564.2	1562.1	1560.1
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8

(END OF REPORT)