

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832317

Luminaire Tested: S123RDIP-S775D1025U927-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832317
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D1025U927-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5868.7 lumens
Efficiency: N/A
Efficacy: 113.3 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 51.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832317

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P832317

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45				
1	97	93	90	86	89	86	83	80	71	69	67	58	57	56	46	45	45	39				
2	89	82	77	72	82	76	71	67	64	60	57	52	50	48	42	40	39	34				
3	82	73	66	61	75	67	62	57	57	52	49	47	44	41	38	36	34	30				
4	75	65	58	52	69	60	54	49	51	46	42	42	39	36	34	32	30	26				
5	69	59	51	45	64	54	48	43	46	41	37	38	35	32	31	29	27	23				
6	64	53	45	40	59	49	42	37	42	37	33	35	31	28	29	26	24	21				
7	60	48	41	35	55	45	38	33	38	33	29	32	28	26	27	24	22	19				
8	56	44	37	32	51	41	34	30	35	30	27	30	26	23	25	22	20	18				
9	52	40	33	28	48	38	31	27	33	28	24	28	24	21	23	20	18	16				
10	49	37	30	26	45	35	29	24	30	25	22	26	22	19	22	19	17	15				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	21288	21288	21288	21288	21288
5°	25276	24470	21421	17316	16077
10°	22900	24855	21315	13874	11903
15°	15767	21311	21089	11340	9415
20°	10969	16408	20665	9562	8276
25°	8359	12505	20050	8499	7627
30°	7276	9998	19280	7891	7065
35°	6681	8433	18188	7378	6553
40°	6095	7531	16760	6875	6084
45°	5504	6888	15219	6400	5616
50°	4997	6355	13402	5933	5037
55°	4519	5836	11656	5478	4322
60°	4049	5307	10125	4975	4084
65°	3739	4709	8716	4470	3861
70°	3037	4069	7604	4044	3138
75°	2666	3236	6442	3356	2766
80°	2411	2740	5275	2814	2616
85°	2198	2408	4001	2556	2408

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 16058 cd/sqm



TEST NUMBER: P832317

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.3	3.1
10°-20°	417.1	7.1
20°-30°	478.6	8.2
30°-40°	471.7	8.0
40°-50°	416.0	7.1
50°-60°	320.0	5.5
60°-70°	210.4	3.6
70°-80°	102.2	1.7
80°-90°	27.9	0.5
90°-100°	37.5	0.6
100°-110°	181.4	3.1
110°-120°	444.6	7.6
120°-130°	564.5	9.6
130°-140°	603.0	10.3
140°-150°	563.9	9.6
150°-160°	454.8	7.8
160°-170°	293.5	5.0
170°-180°	101.2	1.7
0°-30°	1076.0	18.3
0°-40°	1547.7	26.4
0°-60°	2283.7	38.9
0°-90°	2624.2	44.7
90°-120°	663.5	11.3
90°-150°	2394.9	40.8
90°-180°	3244.0	55.3
0°-180°	5868.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1978	1978	1978	1978	1978	
5°	2339	2265	1982	1603	1488	214
15°	1415	1912	1892	1018	845	399
25°	704	1053	1688	716	642	332
35°	508	642	1384	562	499	317
45°	362	452	1000	420	369	281
55°	241	311	621	292	230	216
65°	147	185	342	176	152	144
75°	64	78	155	81	66	69
85°	18	20	32	21	20	19
90°	24	19	1	19	24	11
95°	30	24	48	24	30	25
105°	35	173	236	173	35	72
115°	465	454	442	454	465	437
125°	636	633	623	633	636	568
135°	784	784	776	784	784	604
145°	904	902	895	902	904	564
155°	984	985	986	985	984	454
165°	1037	1037	1040	1037	1037	293
175°	1060	1061	1064	1061	1060	101
180°	1064	1064	1064	1064	1064	



TEST NUMBER: P832317

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1977.7	1977.7	1977.7	1977.7	1977.7	1977.7	1977.7	1977.7	1977.7	1977.7	1977.7
2.5°	2191.7	2184.8	2177.9	2175.9	2173.9	2167.4	2160.9	2146.3	2131.7	2116.7	2101.7
5°	2339.3	2340.1	2340.9	2338.9	2336.9	2328.4	2319.8	2302.0	2284.2	2264.7	2245.2
7.5°	2293.9	2306.9	2319.8	2322.3	2324.7	2331.2	2337.7	2333.6	2329.6	2322.3	2315.0
10°	2095.2	2094.4	2093.6	2108.2	2122.8	2166.2	2209.6	2231.9	2254.2	2274.0	2293.9
12.5°	1770.9	1772.1	1773.3	1821.2	1869.0	1910.0	1950.9	2007.7	2064.4	2125.6	2186.9
15°	1414.9	1434.8	1454.7	1497.2	1539.8	1601.4	1663.0	1739.3	1815.5	1912.4	2009.3
17.5°	1161.9	1170.5	1179.0	1219.9	1260.9	1319.2	1377.6	1464.0	1550.3	1675.2	1800.1
20°	957.6	965.3	973.0	1002.6	1032.2	1088.2	1144.1	1226.4	1308.7	1432.4	1556.0
22.5°	799.5	814.5	829.5	849.4	869.2	909.8	950.3	1034.2	1118.2	1230.9	1343.6
25°	703.8	710.7	717.6	734.6	751.7	790.6	829.5	885.0	940.6	1052.9	1165.2
27.5°	638.9	641.0	643.0	655.6	668.1	693.3	718.4	769.9	821.4	913.8	1006.3
30°	585.4	589.1	592.7	602.5	612.2	630.4	648.7	685.2	721.7	804.4	887.1
32.5°	544.1	546.1	548.1	556.2	564.4	577.7	591.1	619.9	648.7	711.9	775.2
35°	508.4	508.8	509.2	515.3	521.4	534.3	547.3	571.2	595.2	641.8	688.4
37.5°	467.9	470.7	473.5	478.0	482.5	493.8	505.2	524.6	544.1	582.6	621.1
40°	433.8	436.2	438.7	443.9	449.2	458.1	467.0	484.9	502.7	536.0	569.2
42.5°	399.7	401.4	403.0	408.3	413.5	424.5	435.4	449.6	463.8	491.4	518.9
45°	361.6	365.7	369.7	375.4	381.1	390.4	399.7	414.3	428.9	452.5	476.0
47.5°	330.0	332.0	334.1	338.9	343.8	355.2	366.5	379.5	392.5	414.3	436.2
50°	298.4	299.2	300.0	304.5	308.9	319.1	329.2	344.2	359.2	379.5	399.7
52.5°	268.4	270.4	272.4	276.9	281.4	288.3	295.1	310.6	326.0	345.8	365.7
55°	240.8	242.0	243.3	246.5	249.7	257.8	266.0	279.3	292.7	311.0	329.2
57.5°	214.9	216.5	218.1	220.6	223.0	230.3	237.6	249.3	261.1	279.3	297.6
60°	188.1	190.1	192.2	195.0	197.8	203.5	209.2	219.7	230.3	246.5	262.7
62.5°	168.7	169.1	169.5	171.9	174.3	178.4	182.4	191.0	199.5	215.7	231.9
65°	146.8	148.0	149.2	150.4	151.6	154.9	158.1	165.4	172.7	184.9	197.0
67.5°	124.1	125.3	126.5	128.5	130.5	133.4	136.2	141.1	146.0	157.3	168.7
70°	96.5	96.5	96.5	99.7	103.0	107.8	112.7	116.4	120.0	129.3	138.7
72.5°	78.7	79.1	79.5	79.9	80.3	83.1	85.9	92.0	98.1	103.8	109.5
75°	64.1	64.5	64.9	65.3	65.7	66.5	67.3	69.3	71.4	77.8	84.3
77.5°	51.1	51.5	51.9	52.3	52.7	53.5	54.3	55.1	55.9	58.4	60.8
80°	38.9	39.3	39.7	40.1	40.5	40.9	41.4	42.2	43.0	44.2	45.4
82.5°	28.4	28.4	28.4	28.4	28.4	29.2	30.0	30.0	30.0	30.8	31.6
85°	17.8	17.8	17.8	18.2	18.6	18.6	18.6	19.1	19.5	19.5	19.5
87.5°	8.1	7.7	7.3	7.7	8.1	8.1	8.1	8.5	8.9	8.9	8.9
90°	23.7	23.4	23.0	22.7	22.3	21.8	21.1	20.4	19.7	19.0	16.7
92.5°	26.9	26.7	26.5	26.4	26.2	25.5	24.2	23.0	21.8	20.6	19.0
95°	30.0	30.0	30.0	30.0	30.0	29.4	28.2	27.0	25.7	24.5	22.6
97.5°	32.4	32.2	32.1	31.9	31.7	30.9	29.5	28.1	26.7	25.3	34.3
100°	33.2	33.0	32.9	32.7	32.5	31.7	30.3	28.9	27.5	26.1	53.5
102.5°	34.0	33.6	33.3	32.9	32.6	35.3	41.1	46.9	52.7	58.5	89.1
105°	34.8	34.4	34.1	33.7	33.4	48.8	79.9	111.0	142.1	173.2	189.0
107.5°	82.2	105.3	128.3	151.3	174.3	199.3	226.4	253.5	280.5	307.6	305.0
110°	217.4	242.6	267.7	292.8	318.0	333.4	339.2	345.0	350.8	356.6	354.7

TEST NUMBER: P832317

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	412.0	412.3	412.7	413.0	413.4	412.8	411.2	409.6	408.0	406.4	404.5
115°	464.9	464.2	463.5	462.8	462.1	460.9	459.1	457.4	455.6	453.9	452.3
117.5°	507.6	507.5	507.3	507.1	506.9	506.1	504.7	503.3	501.9	500.5	499.6
120°	551.9	551.9	551.9	551.9	551.9	551.2	549.8	548.4	547.0	545.6	545.1
122.5°	595.4	595.2	595.1	594.9	594.7	594.2	593.3	592.4	591.5	590.7	590.0
125°	635.7	635.4	635.0	634.7	634.3	634.0	633.6	633.3	632.9	632.6	631.9
127.5°	675.3	675.6	676.0	676.3	676.7	676.6	676.1	675.5	675.0	674.5	673.6
130°	713.2	713.6	713.9	714.3	714.6	714.5	713.8	713.0	712.3	711.6	710.9
132.5°	748.0	748.5	749.1	749.6	750.1	750.0	749.3	748.6	747.9	747.2	746.7
135°	783.6	784.1	784.7	785.2	785.7	785.7	785.2	784.7	784.1	783.6	782.9
137.5°	817.6	817.9	818.3	818.7	819.0	818.7	817.9	817.0	816.1	815.2	814.9
140°	847.6	848.0	848.3	848.7	849.1	848.9	848.2	847.5	846.8	846.1	845.5
142.5°	875.3	875.8	876.4	876.9	877.4	877.4	876.9	876.4	875.8	875.3	874.8
145°	903.8	903.8	903.8	903.8	903.8	903.6	903.3	902.9	902.6	902.2	901.9
147.5°	924.3	925.2	926.1	927.0	927.9	928.1	927.8	927.4	927.1	926.7	926.4
150°	948.1	948.6	949.1	949.6	950.2	950.3	949.9	949.6	949.2	948.9	948.5
152.5°	967.0	967.9	968.8	969.7	970.6	970.6	969.9	969.2	968.5	967.8	967.7
155°	984.4	985.5	986.5	987.6	988.7	988.7	987.9	987.0	986.1	985.2	985.1
157.5°	999.5	1000.9	1002.3	1003.7	1005.1	1005.3	1004.2	1003.2	1002.1	1001.0	1001.2
160°	1013.7	1014.9	1016.2	1017.4	1018.6	1018.7	1017.6	1016.6	1015.5	1014.5	1014.7
162.5°	1027.1	1028.2	1029.2	1030.3	1031.4	1031.3	1030.0	1028.8	1027.6	1026.3	1026.5
165°	1037.4	1038.6	1039.9	1041.1	1042.3	1042.2	1040.8	1039.4	1038.0	1036.6	1036.8
167.5°	1045.3	1046.7	1048.1	1049.5	1050.9	1050.9	1049.5	1048.1	1046.7	1045.3	1045.3
170°	1052.4	1053.8	1055.3	1056.7	1058.1	1058.1	1056.7	1055.3	1053.8	1052.4	1052.4
172.5°	1056.4	1058.0	1059.6	1061.1	1062.7	1062.8	1061.4	1060.0	1058.6	1057.2	1057.0
175°	1060.3	1061.8	1063.2	1064.6	1066.0	1066.1	1064.8	1063.6	1062.4	1061.1	1061.0
177.5°	1061.1	1062.9	1064.7	1066.4	1068.2	1068.3	1066.9	1065.5	1064.1	1062.7	1062.5
180°	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3



TEST NUMBER: P832317

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1977.7	1977.7	1977.7	1977.7	1977.7	1977.7	1977.7	1977.7	1977.7	1977.7	1977.7
2.5°	2099.7	2097.7	2078.2	2058.7	2039.7	2020.6	2006.4	1992.3	1968.3	1944.4	1929.4
5°	2229.8	2214.4	2183.6	2152.8	2106.6	2060.4	2021.4	1982.5	1933.1	1883.6	1842.2
7.5°	2302.4	2289.8	2252.5	2215.2	2154.0	2092.8	2032.0	1971.2	1898.2	1825.2	1762.8
10°	2304.4	2315.0	2284.2	2253.3	2184.4	2115.5	2032.8	1950.1	1852.0	1753.9	1673.2
12.5°	2232.3	2277.7	2271.2	2264.7	2194.6	2124.4	2023.9	1923.3	1802.9	1682.5	1581.6
15°	2097.3	2185.2	2211.2	2237.1	2179.2	2121.2	2006.8	1892.5	1751.0	1609.5	1493.6
17.5°	1923.3	2046.6	2115.1	2183.6	2141.4	2099.3	1974.0	1848.7	1689.4	1530.1	1404.0
20°	1717.4	1878.7	1986.2	2093.6	2078.2	2062.8	1933.5	1804.1	1632.2	1460.3	1323.7
22.5°	1513.9	1684.1	1832.5	1980.9	1996.7	2012.5	1882.0	1751.4	1563.3	1375.2	1236.1
25°	1338.3	1511.4	1688.2	1865.0	1900.6	1936.3	1812.2	1688.2	1493.2	1298.2	1159.9
27.5°	1170.9	1335.5	1530.1	1724.7	1789.5	1854.4	1740.9	1627.4	1424.3	1221.1	1083.3
30°	1034.2	1181.4	1380.1	1578.7	1669.1	1759.5	1655.3	1551.2	1349.7	1148.2	1013.2
32.5°	906.9	1038.7	1238.2	1437.6	1542.6	1647.6	1557.6	1467.6	1273.8	1080.0	946.7
35°	806.4	924.4	1110.5	1296.5	1414.1	1531.7	1457.9	1384.1	1194.8	1005.5	879.4
37.5°	720.0	819.0	993.7	1168.4	1293.3	1418.2	1356.5	1294.9	1116.9	939.0	819.8
40°	648.7	728.1	890.7	1053.3	1175.7	1298.2	1245.5	1192.8	1033.4	874.1	762.6
42.5°	587.5	656.0	801.9	947.9	1060.2	1172.5	1137.6	1102.8	958.4	814.1	710.7
45°	533.5	591.1	719.6	848.1	951.5	1054.9	1027.3	999.8	875.3	750.8	656.0
47.5°	485.7	535.2	649.9	764.6	857.5	950.3	924.8	899.2	796.3	693.3	606.9
50°	441.9	484.1	579.8	675.4	759.0	842.5	821.4	800.3	715.2	630.0	555.4
52.5°	400.6	435.4	521.4	607.3	674.6	741.9	725.7	709.5	643.8	578.1	510.4
55°	361.2	393.3	465.8	538.4	596.0	653.5	637.3	621.1	570.0	518.9	459.3
57.5°	325.6	353.5	412.3	471.1	516.9	562.7	555.0	547.3	504.8	462.2	413.1
60°	287.9	313.0	363.7	414.3	451.2	488.1	479.2	470.3	439.9	409.5	367.3
62.5°	254.2	276.5	317.0	357.6	387.6	417.6	411.1	404.6	381.5	358.4	323.5
65°	218.9	240.8	273.7	306.5	330.0	353.5	347.9	342.2	324.7	307.3	279.3
67.5°	186.9	205.1	233.5	261.9	277.7	293.5	290.3	287.0	273.7	260.3	238.4
70°	154.5	170.3	193.8	217.3	228.3	239.2	240.4	241.6	229.5	217.3	201.1
72.5°	122.0	134.6	156.5	178.4	186.9	195.4	195.0	194.6	187.3	180.0	165.4
75°	93.7	103.0	120.0	137.0	144.3	151.6	153.3	154.9	148.0	141.1	133.0
77.5°	67.3	73.8	86.8	99.7	107.8	116.0	116.8	117.6	114.3	111.1	103.4
80°	47.4	49.5	57.6	65.7	74.2	82.7	83.9	85.1	81.9	78.7	73.8
82.5°	32.8	34.1	36.9	39.7	46.6	53.5	55.1	56.8	55.1	53.5	48.2
85°	19.9	20.3	21.5	22.7	25.9	29.2	30.8	32.4	31.6	30.8	28.0
87.5°	8.9	8.9	9.3	9.7	10.5	11.4	13.4	15.4	14.2	13.0	11.8
90°	14.4	12.1	9.8	7.8	6.1	4.3	2.5	0.8	2.5	4.3	6.1
92.5°	17.4	15.8	14.2	14.0	15.0	16.1	17.1	18.2	17.1	16.1	15.0
95°	20.6	18.7	16.8	19.4	26.6	33.8	41.0	48.2	41.0	33.8	26.6
97.5°	43.2	52.2	61.1	68.1	73.0	77.9	82.8	87.8	82.8	77.9	73.0
100°	80.9	108.3	135.7	147.7	144.2	140.7	137.1	133.6	137.1	140.7	144.2
102.5°	119.7	150.2	180.8	195.0	192.7	190.4	188.1	185.8	188.1	190.4	192.7
105°	204.8	220.6	236.4	243.4	241.4	239.5	237.6	235.6	237.6	239.5	241.4
107.5°	302.3	299.7	297.0	294.9	293.4	291.8	290.2	288.6	290.2	291.8	293.4
110°	352.7	350.8	348.9	347.2	345.8	344.4	343.0	341.6	343.0	344.4	345.8



TEST NUMBER: P832317

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	402.6	400.6	398.7	397.1	395.9	394.7	393.4	392.2	393.4	394.7	395.9
115°	450.7	449.1	447.5	446.2	445.2	444.1	443.1	442.0	443.1	444.1	445.2
117.5°	498.8	497.9	497.0	496.0	494.7	493.5	492.3	491.0	492.3	493.5	494.7
120°	544.5	544.0	543.5	542.4	540.8	539.3	537.7	536.1	537.7	539.3	540.8
122.5°	589.3	588.6	587.9	586.9	585.7	584.4	583.2	582.0	583.2	584.4	585.7
125°	631.2	630.5	629.8	628.7	627.3	625.9	624.5	623.1	624.5	625.9	627.3
127.5°	672.7	671.8	671.0	669.8	668.4	667.0	665.6	664.2	665.6	667.0	668.4
130°	710.2	709.5	708.8	707.8	706.4	705.0	703.6	702.2	703.6	705.0	706.4
132.5°	746.2	745.6	745.1	744.1	742.7	741.3	739.9	738.5	739.9	741.3	742.7
135°	782.2	781.5	780.8	779.9	778.9	777.8	776.7	775.7	776.7	777.8	778.9
137.5°	814.5	814.2	813.8	812.9	811.5	810.1	808.7	807.3	808.7	810.1	811.5
140°	845.0	844.5	844.0	843.2	842.1	841.1	840.0	838.9	840.0	841.1	842.1
142.5°	874.3	873.7	873.2	872.4	871.4	870.3	869.3	868.2	869.3	870.3	871.4
145°	901.5	901.1	900.8	900.0	898.8	897.5	896.3	895.1	896.3	897.5	898.8
147.5°	926.0	925.7	925.3	924.7	923.8	922.9	922.1	921.2	922.1	922.9	923.8
150°	948.2	947.8	947.4	947.0	946.5	946.0	945.4	944.9	945.4	946.0	946.5
152.5°	967.5	967.3	967.1	967.0	966.8	966.6	966.4	966.3	966.4	966.6	966.8
155°	984.9	984.7	984.5	984.6	985.0	985.3	985.7	986.0	985.7	985.3	985.0
157.5°	1001.4	1001.6	1001.7	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8	1001.8
160°	1014.8	1015.0	1015.2	1015.4	1015.5	1015.7	1015.9	1016.1	1015.9	1015.7	1015.5
162.5°	1026.7	1026.9	1027.0	1027.4	1027.9	1028.5	1029.0	1029.5	1029.0	1028.5	1027.9
165°	1037.0	1037.2	1037.3	1037.7	1038.2	1038.7	1039.3	1039.8	1039.3	1038.7	1038.2
167.5°	1045.3	1045.3	1045.3	1045.7	1046.4	1047.1	1047.8	1048.5	1047.8	1047.1	1046.4
170°	1052.4	1052.4	1052.4	1052.8	1053.5	1054.2	1054.9	1055.6	1054.9	1054.2	1053.5
172.5°	1056.8	1056.7	1056.5	1056.8	1057.7	1058.6	1059.5	1060.3	1059.5	1058.6	1057.7
175°	1060.8	1060.6	1060.4	1060.8	1061.7	1062.5	1063.4	1064.3	1063.4	1062.5	1061.7
177.5°	1062.4	1062.2	1062.0	1062.4	1063.2	1064.1	1065.0	1065.9	1065.0	1064.1	1063.2
180°	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3



TEST NUMBER: P832317

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1977.7	1977.7	1977.7	1977.7	1977.7	1977.7	1977.7	1977.7	1977.7	1977.7	1977.7
2.5°	1914.4	1891.3	1868.2	1851.6	1834.9	1814.3	1793.6	1792.8	1792.0	1776.6	1761.2
5°	1800.9	1760.8	1720.6	1681.3	1642.0	1602.6	1563.3	1554.4	1545.5	1532.1	1518.7
7.5°	1700.3	1636.3	1572.2	1522.0	1471.7	1432.4	1393.0	1366.3	1339.5	1318.8	1298.2
10°	1592.5	1513.0	1433.6	1372.8	1312.0	1269.4	1226.8	1196.0	1165.2	1150.6	1136.0
12.5°	1480.6	1394.3	1307.9	1248.3	1188.7	1137.6	1086.5	1058.6	1030.6	1010.3	990.0
15°	1377.6	1284.8	1191.9	1128.7	1065.5	1017.6	969.8	941.8	913.8	893.6	873.3
17.5°	1277.9	1184.2	1090.6	1026.5	962.5	919.1	875.7	848.6	821.4	808.8	796.3
20°	1187.1	1092.6	998.2	937.7	877.3	834.8	792.2	777.6	763.0	751.3	739.5
22.5°	1097.1	1006.3	915.4	857.5	799.5	768.7	737.9	726.1	714.4	705.4	696.5
25°	1021.7	931.3	840.8	790.2	739.5	715.6	691.7	684.0	676.2	667.3	658.4
27.5°	945.4	859.5	773.5	733.0	692.5	673.0	653.5	643.8	634.1	626.8	619.5
30°	878.1	798.7	719.2	685.6	651.9	634.9	617.9	607.3	596.8	589.9	583.0
32.5°	813.3	742.7	672.2	643.4	614.6	598.0	581.4	571.2	561.1	553.0	544.9
35°	753.3	692.1	630.8	604.5	578.1	561.5	544.9	534.8	524.6	516.5	508.4
37.5°	700.6	645.0	589.5	564.8	540.0	525.4	510.8	500.3	489.8	481.2	472.7
40°	651.1	602.1	553.0	529.1	505.2	489.3	473.5	464.2	454.9	447.2	439.5
42.5°	607.3	562.3	517.3	493.8	470.3	455.3	440.3	429.3	418.4	413.9	409.5
45°	561.1	521.4	481.6	458.9	436.2	420.4	404.6	395.3	386.0	381.9	377.9
47.5°	520.6	483.7	446.8	424.5	402.2	388.0	373.8	366.5	359.2	353.5	347.9
50°	480.8	445.2	409.5	388.0	366.5	354.3	342.2	333.3	324.3	320.3	316.2
52.5°	442.7	410.3	377.9	356.0	334.1	322.3	310.6	302.9	295.1	286.6	278.1
55°	399.7	371.4	343.0	323.5	304.1	291.9	279.7	270.8	261.9	253.0	244.1
57.5°	364.1	336.1	308.1	290.7	273.3	261.5	249.7	240.0	230.3	223.0	215.7
60°	325.2	300.8	276.5	259.5	242.4	231.1	219.7	210.4	201.1	197.4	193.8
62.5°	288.7	266.0	243.3	228.3	213.3	202.3	191.4	185.3	179.2	176.8	174.3
65°	251.4	231.9	212.4	198.7	184.9	175.5	166.2	163.4	160.5	158.5	156.5
67.5°	216.5	199.9	183.3	171.1	158.9	152.4	146.0	142.7	139.5	137.0	134.6
70°	184.9	170.3	155.7	145.1	134.6	128.5	122.4	119.6	116.8	112.3	107.8
72.5°	150.8	139.5	128.1	120.0	111.9	106.6	101.4	95.7	90.0	85.9	81.9
75°	124.9	113.5	102.2	94.5	86.8	80.7	74.6	72.6	70.5	69.3	68.1
77.5°	95.7	85.9	76.2	70.1	64.1	61.2	58.4	57.2	55.9	55.5	55.1
80°	68.9	60.8	52.7	49.5	46.2	45.4	44.6	43.8	43.0	42.6	42.2
82.5°	43.0	38.9	34.9	34.1	33.2	32.8	32.4	32.0	31.6	31.2	30.8
85°	25.1	23.5	21.9	21.5	21.1	20.7	20.3	20.3	20.3	20.3	20.3
87.5°	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.1	9.7
90°	7.8	9.8	12.1	14.4	16.7	19.0	19.7	20.4	21.1	21.8	22.3
92.5°	14.0	14.2	15.8	17.4	19.0	20.6	21.8	23.0	24.2	25.5	26.2
95°	19.4	16.8	18.7	20.6	22.6	24.5	25.7	27.0	28.2	29.4	30.0
97.5°	68.1	61.1	52.2	43.2	34.3	25.3	26.7	28.1	29.5	30.9	31.7
100°	147.7	135.7	108.3	80.9	53.5	26.1	27.5	28.9	30.3	31.7	32.5
102.5°	195.0	180.8	150.2	119.7	89.1	58.5	52.7	46.9	41.1	35.3	32.6
105°	243.4	236.4	220.6	204.8	189.0	173.2	142.1	111.0	79.9	48.8	33.4
107.5°	294.9	297.0	299.7	302.3	305.0	307.6	280.5	253.5	226.4	199.3	174.3
110°	347.2	348.9	350.8	352.7	354.7	356.6	350.8	345.0	339.2	333.4	318.0



TEST NUMBER: P832317

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	397.1	398.7	400.6	402.6	404.5	406.4	408.0	409.6	411.2	412.8	413.4
115°	446.2	447.5	449.1	450.7	452.3	453.9	455.6	457.4	459.1	460.9	462.1
117.5°	496.0	497.0	497.9	498.8	499.6	500.5	501.9	503.3	504.7	506.1	506.9
120°	542.4	543.5	544.0	544.5	545.1	545.6	547.0	548.4	549.8	551.2	551.9
122.5°	586.9	587.9	588.6	589.3	590.0	590.7	591.5	592.4	593.3	594.2	594.7
125°	628.7	629.8	630.5	631.2	631.9	632.6	632.9	633.3	633.6	634.0	634.3
127.5°	669.8	671.0	671.8	672.7	673.6	674.5	675.0	675.5	676.1	676.6	676.7
130°	707.8	708.8	709.5	710.2	710.9	711.6	712.3	713.0	713.8	714.5	714.6
132.5°	744.1	745.1	745.6	746.2	746.7	747.2	747.9	748.6	749.3	750.0	750.1
135°	779.9	780.8	781.5	782.2	782.9	783.6	784.1	784.7	785.2	785.7	785.7
137.5°	812.9	813.8	814.2	814.5	814.9	815.2	816.1	817.0	817.9	818.7	819.0
140°	843.2	844.0	844.5	845.0	845.5	846.1	846.8	847.5	848.2	848.9	849.1
142.5°	872.4	873.2	873.7	874.3	874.8	875.3	875.8	876.4	876.9	877.4	877.4
145°	900.0	900.8	901.1	901.5	901.9	902.2	902.6	902.9	903.3	903.6	903.8
147.5°	924.7	925.3	925.7	926.0	926.4	926.7	927.1	927.4	927.8	928.1	927.9
150°	947.0	947.4	947.8	948.2	948.5	948.9	949.2	949.6	949.9	950.3	950.2
152.5°	967.0	967.1	967.3	967.5	967.7	967.8	968.5	969.2	969.9	970.6	970.6
155°	984.6	984.5	984.7	984.9	985.1	985.2	986.1	987.0	987.9	988.7	988.7
157.5°	1001.8	1001.7	1001.6	1001.4	1001.2	1001.0	1002.1	1003.2	1004.2	1005.3	1005.1
160°	1015.4	1015.2	1015.0	1014.8	1014.7	1014.5	1015.5	1016.6	1017.6	1018.7	1018.6
162.5°	1027.4	1027.0	1026.9	1026.7	1026.5	1026.3	1027.6	1028.8	1030.0	1031.3	1031.4
165°	1037.7	1037.3	1037.2	1037.0	1036.8	1036.6	1038.0	1039.4	1040.8	1042.2	1042.3
167.5°	1045.7	1045.3	1045.3	1045.3	1045.3	1045.3	1046.7	1048.1	1049.5	1050.9	1050.9
170°	1052.8	1052.4	1052.4	1052.4	1052.4	1052.4	1053.8	1055.3	1056.7	1058.1	1058.1
172.5°	1056.8	1056.5	1056.7	1056.8	1057.0	1057.2	1058.6	1060.0	1061.4	1062.8	1062.7
175°	1060.8	1060.4	1060.6	1060.8	1061.0	1061.1	1062.4	1063.6	1064.8	1066.1	1066.0
177.5°	1062.4	1062.0	1062.2	1062.4	1062.5	1062.7	1064.1	1065.5	1066.9	1068.3	1068.2
180°	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3	1064.3



TEST NUMBER: P832317

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1977.7	1977.7	1977.7	1977.7
2.5°	1757.1	1753.1	1751.4	1749.8
5°	1506.2	1493.6	1490.7	1487.9
7.5°	1292.9	1287.6	1270.2	1252.8
10°	1119.8	1103.6	1096.3	1089.0
12.5°	975.0	960.0	957.6	955.2
15°	862.7	852.2	848.6	844.9
17.5°	789.0	781.7	777.2	772.7
20°	734.2	729.0	725.7	722.5
22.5°	692.5	688.4	686.0	683.5
25°	652.3	646.2	644.2	642.2
27.5°	614.2	608.9	606.9	604.9
30°	578.5	574.1	571.2	568.4
32.5°	539.6	534.3	532.7	531.1
35°	505.2	501.9	500.3	498.7
37.5°	468.7	464.6	462.2	459.8
40°	437.5	435.4	434.2	433.0
42.5°	405.8	402.2	401.8	401.4
45°	374.2	370.6	369.7	368.9
47.5°	344.6	341.4	341.0	340.6
50°	311.8	307.3	304.1	300.8
52.5°	274.1	270.0	267.2	264.3
55°	239.6	235.1	232.7	230.3
57.5°	213.7	211.6	210.4	209.2
60°	192.6	191.4	190.5	189.7
62.5°	173.1	171.9	171.9	171.9
65°	155.3	154.1	152.8	151.6
67.5°	132.2	129.7	129.3	128.9
70°	104.2	100.5	100.1	99.7
72.5°	81.5	81.1	80.3	79.5
75°	67.3	66.5	66.5	66.5
77.5°	54.3	53.5	53.5	53.5
80°	41.8	41.4	41.8	42.2
82.5°	30.8	30.8	30.4	30.0
85°	19.9	19.5	19.5	19.5
87.5°	9.7	9.7	9.7	9.7
90°	22.7	23.0	23.4	23.7
92.5°	26.4	26.5	26.7	26.9
95°	30.0	30.0	30.0	30.0
97.5°	31.9	32.1	32.2	32.4
100°	32.7	32.9	33.0	33.2
102.5°	32.9	33.3	33.6	34.0
105°	33.7	34.1	34.4	34.8
107.5°	151.3	128.3	105.3	82.2
110°	292.8	267.7	242.6	217.4



TEST NUMBER: P832317

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	413.0	412.7	412.3	412.0
115°	462.8	463.5	464.2	464.9
117.5°	507.1	507.3	507.5	507.6
120°	551.9	551.9	551.9	551.9
122.5°	594.9	595.1	595.2	595.4
125°	634.7	635.0	635.4	635.7
127.5°	676.3	676.0	675.6	675.3
130°	714.3	713.9	713.6	713.2
132.5°	749.6	749.1	748.5	748.0
135°	785.2	784.7	784.1	783.6
137.5°	818.7	818.3	817.9	817.6
140°	848.7	848.3	848.0	847.6
142.5°	876.9	876.4	875.8	875.3
145°	903.8	903.8	903.8	903.8
147.5°	927.0	926.1	925.2	924.3
150°	949.6	949.1	948.6	948.1
152.5°	969.7	968.8	967.9	967.0
155°	987.6	986.5	985.5	984.4
157.5°	1003.7	1002.3	1000.9	999.5
160°	1017.4	1016.2	1014.9	1013.7
162.5°	1030.3	1029.2	1028.2	1027.1
165°	1041.1	1039.9	1038.6	1037.4
167.5°	1049.5	1048.1	1046.7	1045.3
170°	1056.7	1055.3	1053.8	1052.4
172.5°	1061.1	1059.6	1058.0	1056.4
175°	1064.6	1063.2	1061.8	1060.3
177.5°	1066.4	1064.7	1062.9	1061.1
180°	1064.3	1064.3	1064.3	1064.3



TEST NUMBER: P832317

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.85	11.62	11.86	12.64	13.99	15.52	16.29	16.53	17.30	18.65
	3H	12.07	12.76	13.09	13.78	15.15	17.01	17.70	18.03	18.72	20.09
	4H	12.45	13.10	13.48	14.12	15.50	17.50	18.15	18.53	19.17	20.55
	6H	12.73	13.32	13.77	14.36	15.74	17.81	18.41	18.85	19.44	20.82
	8H	12.81	13.38	13.86	14.43	15.81	17.88	18.45	18.93	19.50	20.88
	12H	12.86	13.40	13.92	14.44	15.85	17.91	18.45	18.97	19.49	20.90
4H	2H	11.57	12.22	12.61	13.24	14.62	15.50	16.15	16.55	17.18	18.56
	3H	12.93	13.47	13.98	14.53	15.92	17.16	17.70	18.21	18.75	20.14
	4H	13.39	13.88	14.44	14.93	16.34	17.76	18.26	18.82	19.30	20.71
	6H	13.75	14.17	14.81	15.24	16.65	18.20	18.62	19.26	19.69	21.10
	8H	13.87	14.27	14.94	15.33	16.75	18.33	18.72	19.39	19.78	21.21
	12H	13.95	14.30	15.03	15.38	16.81	18.39	18.74	19.47	19.82	21.25
8H	4H	13.70	14.09	14.76	15.15	16.57	17.72	18.12	18.79	19.18	20.60
	6H	14.16	14.48	15.24	15.59	17.01	18.22	18.54	19.31	19.65	21.07
	8H	14.35	14.64	15.44	15.72	17.16	18.40	18.69	19.50	19.78	21.22
	12H	14.49	14.74	15.58	15.82	17.30	18.52	18.77	19.61	19.85	21.33
12H	4H	13.70	14.06	14.79	15.14	16.56	17.67	18.03	18.75	19.10	20.53
	6H	14.22	14.50	15.31	15.59	17.03	18.19	18.48	19.29	19.57	21.01
	8H	14.43	14.68	15.53	15.76	17.24	18.38	18.63	19.48	19.72	21.20