

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332325-927

Luminaire Tested: **S123RDIP-S775D1195U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332325-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S775D1195U927-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5662.1 lumens  
Efficiency: N/A  
Efficacy: 99.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332325-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot



57% Up

43% Dn



TEST NUMBER: P332325-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	43																				
1	97	93	89	86	88	85	82	79	70	68	66	57	55	54	44	43	43	37																				
2	88	81	76	71	81	75	70	65	62	58	55	50	48	46	40	38	37	32																				
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	27																				
4	74	64	56	51	68	59	52	47	49	44	41	40	37	34	32	30	28	24																				
5	68	57	49	44	62	53	46	41	44	39	35	36	33	30	29	27	24	21																				
6	63	51	44	38	57	47	41	36	40	35	31	33	29	26	27	24	22	19																				
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17																				
8	54	42	35	30	49	39	32	28	33	28	24	28	24	21	22	20	18	15																				
9	50	39	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16	14																				
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10428	10428	10428	10428
5°	12431	10472	9223	10472
10°	15522	10413	8332	10413
15°	18219	10307	7598	10307
20°	20333	10148	6975	10148
25°	20009	9980	6590	9980
30°	14382	9825	6196	9825
35°	9603	9625	5941	9625
40°	7075	9382	5675	9382
45°	5934	8958	5416	8958
50°	5238	8403	5056	8403
55°	4592	7767	4560	7767
60°	4090	7160	4179	7160
65°	3591	6507	3889	6507
70°	2820	5926	3550	5926
75°	2483	5178	3244	5178
80°	2163	4395	3186	4395
85°	1741	3532	3384	3532



TEST NUMBER: P332325-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.3	1.7
10°-20°	297.7	5.3
20°-30°	467.6	8.3
30°-40°	487.9	8.6
40°-50°	417.5	7.4
50°-60°	318.2	5.6
60°-70°	204.0	3.6
70°-80°	98.1	1.7
80°-90°	29.4	0.5
90°-100°	76.3	1.3
100°-110°	228.5	4.0
110°-120°	388.6	6.9
120°-130°	511.1	9.0
130°-140°	574.5	10.1
140°-150°	564.7	10.0
150°-160°	475.4	8.4
160°-170°	316.5	5.6
170°-180°	110.8	2.0
0°-30°	860.6	15.2
0°-40°	1348.4	23.8
0°-60°	2084.2	36.8
0°-90°	2415.7	42.7
90°-120°	693.4	12.2
90°-150°	2343.7	41.4
90°-180°	3246.0	57.3
0°-180°	5662.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	969	969	969	969	969	
5°	1150	969	854	969	1150	119
15°	1635	925	682	925	1635	464
25°	1685	840	555	840	1685	724
35°	731	732	452	732	731	479
45°	390	588	356	588	390	307
55°	245	414	243	414	245	221
65°	141	256	153	256	141	139
75°	60	124	78	124	60	64
85°	14	29	27	29	14	17
90°	28	1	28	1	28	14
95°	72	54	72	54	72	74
105°	219	207	219	207	219	232
115°	392	391	392	391	392	388
125°	566	572	566	572	566	506
135°	742	743	742	743	742	570
145°	901	901	901	901	901	562
155°	1030	1032	1030	1032	1030	474
165°	1120	1124	1120	1124	1120	316
175°	1164	1169	1164	1169	1164	111
180°	1172	1172	1172	1172	1172	



TEST NUMBER: P332325-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1031.9	1033.2	1028.9	1028.3	1023.3	1021.9	1021.9	1014.9	1010.7	1005.0	1001.7
5°	1150.5	1157.1	1153.8	1146.4	1133.9	1131.0	1123.2	1110.7	1096.6	1079.2	1070.9
7.5°	1298.6	1307.7	1304.2	1292.7	1279.7	1269.2	1246.9	1226.2	1197.3	1171.9	1150.2
10°	1420.1	1410.6	1403.1	1391.9	1379.9	1360.3	1337.1	1305.2	1268.3	1239.3	1206.9
12.5°	1511.0	1509.4	1500.0	1488.4	1471.5	1452.9	1424.4	1385.5	1342.6	1300.7	1263.7
15°	1634.9	1637.4	1631.2	1619.1	1595.1	1562.3	1519.2	1503.0	1441.7	1396.1	1350.4
17.5°	1720.7	1720.2	1719.4	1702.7	1678.2	1654.9	1614.9	1572.3	1516.7	1452.5	1391.0
20°	1775.1	1771.0	1771.8	1753.1	1734.9	1707.9	1669.0	1607.2	1561.5	1487.3	1423.8
22.5°	1773.8	1773.0	1776.2	1769.7	1756.4	1735.8	1705.1	1653.0	1594.7	1519.8	1448.3
25°	1684.7	1681.4	1700.9	1706.3	1727.4	1731.2	1722.0	1693.4	1638.2	1561.1	1472.7
27.5°	1410.0	1408.2	1444.3	1489.6	1547.0	1591.7	1634.7	1655.6	1638.2	1583.0	1494.5
30°	1157.1	1196.1	1214.4	1279.9	1352.9	1440.0	1516.3	1588.9	1606.7	1582.7	1510.1
32.5°	960.8	994.7	1010.0	1066.2	1134.2	1236.3	1350.8	1453.5	1526.1	1544.5	1500.8
35°	730.8	731.2	766.0	790.9	854.0	958.9	1070.1	1207.8	1344.6	1448.3	1459.0
37.5°	583.1	585.2	606.3	631.1	678.3	733.9	831.7	946.2	1104.3	1263.5	1356.8
40°	503.5	507.2	523.0	547.5	581.5	623.4	699.7	807.6	939.4	1116.5	1261.2
42.5°	452.4	458.4	466.6	485.4	506.5	545.7	607.4	690.7	810.6	978.1	1145.1
45°	389.8	393.2	399.4	408.1	427.2	454.6	496.1	552.0	651.6	786.4	953.5
47.5°	343.9	342.1	348.7	355.8	368.4	387.1	414.9	460.7	531.6	639.8	781.6
50°	312.8	312.3	316.9	322.3	334.3	348.0	370.8	405.2	461.6	551.2	681.0
52.5°	283.5	285.1	288.4	295.1	303.7	314.8	335.3	360.0	408.5	485.8	594.1
55°	244.7	246.0	250.5	254.2	260.5	271.6	284.6	305.2	338.4	392.4	481.5
57.5°	211.8	211.3	215.6	216.6	223.6	232.7	242.7	258.8	282.9	322.9	382.9
60°	190.0	188.7	192.4	195.4	199.1	206.5	214.8	230.6	249.7	279.1	330.6
62.5°	170.1	169.4	172.2	175.1	178.2	185.0	191.9	204.1	219.1	244.0	284.8
65°	141.0	142.3	143.5	144.7	146.4	150.5	157.2	165.5	175.9	193.3	222.7
67.5°	110.8	112.1	112.5	115.0	118.6	121.2	125.2	132.6	139.8	154.6	171.3
70°	89.6	89.2	89.6	90.9	95.4	100.0	105.4	110.7	115.3	125.6	139.7
72.5°	77.0	76.2	77.3	77.6	79.8	81.0	84.4	89.5	95.4	102.4	112.6
75°	59.7	59.7	59.7	59.7	61.4	62.2	63.5	64.7	66.8	70.1	77.6
77.5°	44.1	44.2	44.8	45.2	45.6	46.0	46.8	48.0	48.8	50.5	53.8
80°	34.9	35.3	34.9	35.3	35.3	36.0	36.5	37.7	38.2	40.2	41.5
82.5°	26.2	26.0	26.2	26.6	26.6	27.5	27.6	28.4	28.5	29.6	30.9
85°	14.1	13.3	14.1	13.7	14.5	13.7	14.1	14.9	14.9	15.4	17.0
87.5°	8.9	9.4	8.7	9.0	8.9	9.0	8.9	8.7	9.2	8.7	8.6
90°	27.6	27.2	26.8	26.4	26.0	25.3	24.6	23.8	22.9	22.1	19.4
92.5°	37.2	37.4	37.7	37.9	38.2	37.9	37.3	36.7	36.0	35.3	33.8
95°	71.8	71.8	71.8	71.8	71.8	71.4	70.6	69.7	68.9	68.1	66.5
97.5°	110.4	110.5	110.6	110.7	110.7	110.4	109.4	108.4	107.5	106.5	105.4
100°	139.9	139.5	139.1	138.7	138.2	137.8	137.1	136.5	135.9	135.3	134.3
102.5°	170.1	170.2	170.2	170.3	170.4	170.2	169.5	168.9	168.3	167.7	166.4
105°	219.0	218.6	218.2	217.9	217.5	217.2	217.2	217.2	217.2	217.2	215.4
107.5°	270.1	270.3	270.5	270.8	271.0	270.8	270.2	269.5	268.9	268.2	267.4
110°	304.7	305.1	305.5	305.9	306.3	306.1	305.3	304.4	303.6	302.9	302.4



TEST NUMBER: P332325-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	341.5	341.6	341.7	341.7	341.8	341.4	340.4	339.4	338.4	337.4	337.3
115°	392.1	392.3	392.5	392.7	392.9	392.9	392.7	392.5	392.3	392.1	392.5
117.5°	443.5	444.0	444.6	445.2	445.8	446.1	446.1	446.2	446.2	446.2	446.8
120°	479.5	480.0	480.4	480.8	481.2	481.5	481.7	481.9	482.1	482.3	483.3
122.5°	514.1	514.7	515.3	515.9	516.4	517.0	517.5	518.1	518.6	519.1	519.7
125°	566.1	566.9	567.7	568.5	569.3	570.1	571.0	571.8	572.6	573.5	573.9
127.5°	617.8	618.7	619.6	620.6	621.5	622.6	623.8	624.9	626.1	627.2	627.6
130°	651.6	653.1	654.5	655.9	657.4	658.5	659.3	660.1	661.0	661.8	662.4
132.5°	687.0	688.1	689.2	690.3	691.4	692.4	693.5	694.4	695.4	696.4	696.8
135°	741.9	742.3	742.7	743.1	743.5	744.1	744.9	745.8	746.6	747.3	747.6
137.5°	790.3	791.1	791.9	792.6	793.4	794.2	795.0	795.9	796.8	797.6	797.1
140°	822.0	823.4	824.8	826.2	827.7	828.5	828.7	828.9	829.1	829.3	829.1
142.5°	854.4	855.5	856.5	857.6	858.7	859.4	859.6	859.8	860.0	860.2	859.8
145°	901.1	901.9	902.7	903.6	904.4	904.9	905.1	905.3	905.5	905.7	905.1
147.5°	942.7	943.9	945.2	946.3	947.6	948.2	948.2	948.2	948.2	948.2	947.6
150°	969.2	970.4	971.7	972.9	974.1	974.7	974.7	974.7	974.7	974.7	974.3
152.5°	995.0	996.0	997.1	998.1	999.3	999.6	999.3	998.9	998.6	998.3	998.1
155°	1029.9	1031.4	1032.8	1034.3	1035.7	1036.0	1035.1	1034.4	1033.6	1032.7	1032.5
157.5°	1061.8	1063.0	1064.1	1065.2	1066.4	1066.5	1065.6	1064.8	1064.0	1063.1	1063.0
160°	1082.4	1083.2	1084.0	1084.9	1085.7	1085.6	1084.6	1083.5	1082.5	1081.5	1081.5
162.5°	1097.9	1099.2	1100.5	1101.8	1103.1	1103.3	1102.2	1101.2	1100.2	1099.2	1099.0
165°	1120.1	1121.6	1123.0	1124.4	1125.8	1126.0	1124.7	1123.6	1122.3	1121.1	1121.1
167.5°	1139.1	1140.3	1141.6	1142.9	1144.1	1144.1	1142.9	1141.6	1140.3	1139.1	1138.9
170°	1148.7	1150.1	1151.5	1153.0	1154.4	1154.4	1153.0	1151.5	1150.1	1148.7	1148.7
172.5°	1156.0	1157.5	1158.9	1160.3	1161.8	1161.9	1160.6	1159.4	1158.1	1156.8	1156.8
175°	1164.3	1165.8	1167.2	1168.6	1170.1	1170.1	1168.9	1167.7	1166.5	1165.2	1165.2
177.5°	1168.8	1169.9	1171.0	1172.2	1173.3	1173.4	1172.4	1171.5	1170.4	1169.5	1169.5
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P332325-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1000.4	999.3	994.7	989.4	982.5	977.8	974.1	972.2	966.2	958.9	953.9
5°	1062.2	1049.7	1036.5	1020.3	1005.4	990.0	980.5	969.2	955.6	940.2	929.5
7.5°	1128.4	1104.0	1077.7	1050.6	1023.7	999.7	978.5	960.3	938.5	916.5	901.1
10°	1179.2	1143.4	1106.5	1068.8	1034.4	1002.0	977.2	952.7	926.5	901.3	882.2
12.5°	1225.3	1178.3	1135.8	1089.4	1045.4	1006.7	970.8	942.1	910.6	883.7	861.9
15°	1283.7	1235.6	1184.1	1113.6	1055.1	1006.2	962.7	924.9	886.8	853.6	832.4
17.5°	1338.2	1265.8	1196.7	1137.9	1061.9	1000.8	947.6	902.5	860.6	825.5	799.4
20°	1360.8	1290.7	1215.6	1140.6	1065.9	997.4	935.6	885.9	842.3	802.6	778.5
22.5°	1374.4	1295.0	1215.9	1135.3	1056.0	984.8	923.8	868.9	821.8	783.9	754.2
25°	1390.2	1295.7	1208.6	1128.9	1048.1	970.9	898.3	840.3	789.3	749.0	717.5
27.5°	1400.7	1289.4	1186.5	1098.0	1016.0	939.1	872.6	811.1	759.3	716.8	682.9
30°	1402.6	1284.4	1169.6	1073.8	990.4	919.9	849.4	790.5	735.8	690.5	659.0
32.5°	1405.3	1272.2	1146.7	1044.9	959.6	889.7	825.9	769.6	713.5	669.0	636.8
35°	1394.4	1265.4	1111.9	995.0	909.5	841.9	784.3	732.5	677.3	634.1	601.3
37.5°	1347.3	1238.4	1075.9	938.7	849.4	786.8	739.8	694.6	644.0	597.5	566.6
40°	1299.8	1211.9	1048.1	904.6	811.3	746.9	704.6	667.7	618.8	575.3	542.1
42.5°	1229.2	1175.8	1021.5	868.7	768.1	706.2	670.5	635.9	592.9	548.7	517.5
45°	1099.5	1106.5	967.2	811.7	708.4	646.2	612.6	588.5	550.4	513.9	482.0
47.5°	936.9	1002.8	903.4	750.8	645.4	587.0	557.7	536.7	511.0	475.2	446.0
50°	830.8	924.9	852.3	710.0	605.9	547.9	518.9	501.8	479.4	451.2	423.4
52.5°	732.8	834.0	790.6	664.6	563.2	510.1	481.7	467.7	449.9	423.3	398.2
55°	597.6	700.1	690.1	596.0	498.9	451.2	429.7	413.9	401.9	382.0	362.1
57.5°	483.5	580.6	585.7	519.7	442.4	395.2	376.7	364.8	357.0	341.9	323.5
60°	411.5	500.6	518.0	468.3	401.9	360.4	342.1	332.6	326.4	314.4	300.3
62.5°	351.7	427.6	447.3	411.5	363.1	324.2	310.0	300.8	296.5	286.1	273.7
65°	269.2	332.2	351.3	331.4	306.1	275.0	263.4	255.5	251.8	246.0	236.8
67.5°	202.4	248.3	269.3	255.2	246.1	226.5	219.0	214.8	211.5	207.6	199.9
70°	162.6	196.6	218.2	214.4	207.0	196.6	191.2	188.3	185.0	181.6	175.0
72.5°	130.7	154.2	174.4	176.3	170.2	168.0	163.3	162.1	160.1	156.1	152.5
75°	86.7	102.8	116.9	122.3	124.8	126.9	124.8	124.5	124.0	120.7	118.6
77.5°	56.8	65.5	74.4	83.6	87.5	90.3	91.0	92.5	91.4	89.7	88.6
80°	43.6	45.6	51.8	59.7	65.9	68.4	70.1	70.9	70.5	70.1	68.4
82.5°	31.6	33.4	36.3	41.8	47.1	51.2	52.2	52.0	52.9	53.2	51.8
85°	17.0	17.4	18.2	19.1	21.9	26.5	27.8	28.6	29.5	29.5	26.9
87.5°	8.6	7.8	7.9	7.4	8.1	8.0	9.6	10.8	11.6	10.6	11.0
90°	16.8	14.1	11.5	9.1	7.1	5.0	2.9	1.0	2.9	5.0	7.1
92.5°	32.3	30.8	29.3	27.8	26.5	25.0	23.7	22.3	23.7	25.0	26.5
95°	64.8	63.2	61.6	60.0	58.6	57.2	55.8	54.3	55.8	57.2	58.6
97.5°	104.3	103.1	101.9	100.7	99.7	98.6	97.5	96.5	97.5	98.6	99.7
100°	133.2	132.2	131.2	130.1	128.9	127.6	126.4	125.2	126.4	127.6	128.9
102.5°	165.0	163.7	162.3	161.3	160.5	159.8	159.1	158.3	159.1	159.8	160.5
105°	213.6	211.7	209.8	208.7	208.3	207.9	207.5	207.1	207.5	207.9	208.3
107.5°	266.7	266.0	265.3	264.7	264.5	264.3	264.0	263.8	264.0	264.3	264.5
110°	302.0	301.6	301.2	300.8	300.4	299.9	299.5	299.1	299.5	299.9	300.4





TEST NUMBER: P332325-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	337.2	337.2	337.1	336.9	336.7	336.4	336.2	336.0	336.2	336.4	336.7
115°	392.9	393.3	393.7	393.6	393.0	392.4	391.8	391.2	391.8	392.4	393.0
117.5°	447.3	447.8	448.4	448.4	448.0	447.6	447.2	446.8	447.2	447.6	448.0
120°	484.3	485.4	486.4	486.3	485.1	483.9	482.6	481.4	482.6	483.9	485.1
122.5°	520.1	520.7	521.3	521.1	520.1	519.3	518.3	517.5	518.3	519.3	520.1
125°	574.3	574.6	575.0	575.0	574.3	573.7	573.1	572.5	573.1	573.7	574.3
127.5°	628.0	628.5	629.0	628.5	627.2	625.9	624.6	623.3	624.6	625.9	627.2
130°	663.0	663.6	664.2	663.7	662.1	660.4	658.8	657.2	658.8	660.4	662.1
132.5°	697.3	697.8	698.2	697.6	695.9	694.3	692.7	691.0	692.7	694.3	695.9
135°	747.8	748.0	748.2	747.7	746.5	745.2	744.0	742.8	744.0	745.2	746.5
137.5°	796.5	796.1	795.5	794.7	793.7	792.7	791.6	790.7	791.6	792.7	793.7
140°	828.9	828.7	828.5	827.8	826.9	825.9	824.8	823.8	824.8	825.9	826.9
142.5°	859.5	859.1	858.7	858.1	857.1	856.0	855.0	854.0	855.0	856.0	857.1
145°	904.4	903.9	903.2	902.7	902.3	901.9	901.5	901.1	901.5	901.9	902.3
147.5°	947.1	946.5	945.9	945.3	944.5	943.8	943.1	942.3	943.1	943.8	944.5
150°	973.9	973.5	973.1	972.7	972.2	971.8	971.5	971.1	971.5	971.8	972.2
152.5°	997.8	997.5	997.3	996.9	996.3	995.8	995.2	994.6	995.2	995.8	996.3
155°	1032.3	1032.1	1031.9	1031.8	1031.8	1031.8	1031.8	1031.8	1031.8	1031.8	1031.8
157.5°	1062.8	1062.6	1062.4	1062.5	1062.7	1063.0	1063.2	1063.4	1063.2	1063.0	1062.7
160°	1081.5	1081.5	1081.5	1081.7	1082.1	1082.5	1082.9	1083.3	1082.9	1082.5	1082.1
162.5°	1098.8	1098.7	1098.5	1098.8	1099.3	1099.9	1100.4	1101.0	1100.4	1099.9	1099.3
165°	1121.1	1121.1	1121.1	1121.4	1122.0	1122.6	1123.2	1123.9	1123.2	1122.6	1122.0
167.5°	1138.8	1138.6	1138.4	1138.8	1139.6	1140.4	1141.2	1142.1	1141.2	1140.4	1139.6
170°	1148.7	1148.7	1148.7	1149.1	1149.9	1150.7	1151.5	1152.4	1151.5	1150.7	1149.9
172.5°	1156.8	1156.8	1156.8	1157.2	1158.0	1158.8	1159.7	1160.5	1159.7	1158.8	1158.0
175°	1165.2	1165.2	1165.2	1165.7	1166.5	1167.3	1168.2	1168.9	1168.2	1167.3	1166.5
177.5°	1169.5	1169.5	1169.5	1169.8	1170.4	1171.2	1171.8	1172.4	1171.8	1171.2	1170.4
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P332325-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	952.3	947.9	945.0	938.3	934.0	929.4	924.7	927.7	927.4	927.0	927.0
5°	920.4	910.8	902.1	890.9	883.8	875.1	868.5	867.7	869.3	863.5	860.2
7.5°	888.7	875.6	863.2	850.9	837.8	827.4	820.8	817.7	813.5	809.9	806.2
10°	866.4	851.0	839.0	823.7	809.6	797.2	789.3	783.9	780.9	778.1	772.7
12.5°	843.5	828.5	813.2	795.8	782.4	767.9	762.1	756.0	750.4	747.2	739.8
15°	810.0	790.5	774.4	756.1	741.2	727.1	718.7	706.7	705.0	700.9	693.5
17.5°	776.4	755.3	732.9	719.5	702.6	687.9	675.3	671.2	659.3	654.9	648.4
20°	749.9	730.4	713.4	695.5	671.1	657.4	647.5	642.1	632.5	626.7	622.5
22.5°	727.0	707.2	687.5	666.7	646.5	631.1	623.8	615.4	610.3	602.1	597.6
25°	694.3	672.7	649.1	626.7	612.2	600.6	588.9	581.5	574.0	570.3	562.0
27.5°	656.3	633.7	611.6	594.7	576.9	565.4	554.8	548.2	539.2	533.0	528.4
30°	635.4	608.9	589.8	574.4	551.6	540.8	533.0	524.7	518.0	511.4	506.8
32.5°	611.2	586.9	568.9	549.9	532.3	520.6	510.4	503.1	497.4	491.2	486.6
35°	573.1	552.9	534.2	515.1	502.2	490.2	478.2	472.0	466.6	460.8	456.6
37.5°	538.8	519.8	502.1	484.0	468.1	458.3	448.6	443.9	436.6	432.7	428.4
40°	517.6	498.9	479.8	462.5	445.8	438.4	429.7	422.6	416.0	413.1	408.5
42.5°	494.4	475.7	459.6	440.8	427.3	417.2	409.1	401.4	396.4	392.2	389.6
45°	459.9	443.4	427.6	408.9	396.1	387.4	378.3	371.2	366.6	363.8	359.2
47.5°	426.5	410.0	394.0	377.6	365.2	355.3	346.2	341.3	335.2	331.6	328.6
50°	402.3	387.4	370.3	355.5	343.0	333.0	325.6	319.3	313.9	309.4	307.4
52.5°	380.1	364.2	349.4	335.6	322.4	311.2	304.4	297.8	293.7	288.5	286.1
55°	343.4	328.0	315.6	301.9	289.1	279.6	271.2	265.5	261.3	255.5	252.2
57.5°	309.0	295.2	280.4	268.5	255.2	247.2	240.3	232.4	227.4	222.8	219.6
60°	285.7	270.0	257.1	246.0	234.3	223.9	217.8	211.5	206.1	201.5	198.7
62.5°	261.6	247.8	235.6	223.4	212.8	203.7	196.5	191.3	186.6	183.6	180.8
65°	224.3	213.6	201.1	191.2	181.3	174.6	168.8	164.2	160.9	158.8	156.4
67.5°	190.2	179.7	168.9	159.1	152.5	147.4	143.6	139.7	138.0	135.4	133.7
70°	167.9	157.2	147.7	140.2	133.6	129.8	127.3	124.5	122.8	119.5	117.8
72.5°	143.8	135.9	129.0	122.9	117.6	114.2	111.1	107.5	104.9	101.2	99.6
75°	113.2	106.2	100.8	96.6	93.3	88.7	84.2	80.5	79.2	78.0	77.6
77.5°	83.9	79.4	75.5	72.0	67.9	64.6	63.5	62.7	62.4	61.8	61.8
80°	65.9	61.8	58.9	54.7	52.3	52.3	52.3	51.4	51.8	51.8	51.8
82.5°	49.0	45.2	43.6	42.1	41.7	42.0	42.0	42.1	41.9	42.5	42.2
85°	25.3	25.7	26.5	26.1	26.5	26.5	27.4	26.9	27.4	26.5	27.4
87.5°	11.1	12.6	13.5	14.3	15.1	15.4	15.8	16.0	16.6	16.7	16.8
90°	9.1	11.5	14.1	16.8	19.4	22.1	22.9	23.8	24.6	25.3	26.0
92.5°	27.8	29.3	30.8	32.3	33.8	35.3	36.0	36.7	37.3	37.9	38.2
95°	60.0	61.6	63.2	64.8	66.5	68.1	68.9	69.7	70.6	71.4	71.8
97.5°	100.7	101.9	103.1	104.3	105.4	106.5	107.5	108.4	109.4	110.4	110.7
100°	130.1	131.2	132.2	133.2	134.3	135.3	135.9	136.5	137.1	137.8	138.2
102.5°	161.3	162.3	163.7	165.0	166.4	167.7	168.3	168.9	169.5	170.2	170.4
105°	208.7	209.8	211.7	213.6	215.4	217.2	217.2	217.2	217.2	217.2	217.5
107.5°	264.7	265.3	266.0	266.7	267.4	268.2	268.9	269.5	270.2	270.8	271.0
110°	300.8	301.2	301.6	302.0	302.4	302.9	303.6	304.4	305.3	306.1	306.3



TEST NUMBER: P332325-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	336.9	337.1	337.2	337.2	337.3	337.4	338.4	339.4	340.4	341.4	341.8
115°	393.6	393.7	393.3	392.9	392.5	392.1	392.3	392.5	392.7	392.9	392.9
117.5°	448.4	448.4	447.8	447.3	446.8	446.2	446.2	446.2	446.1	446.1	445.8
120°	486.3	486.4	485.4	484.3	483.3	482.3	482.1	481.9	481.7	481.5	481.2
122.5°	521.1	521.3	520.7	520.1	519.7	519.1	518.6	518.1	517.5	517.0	516.4
125°	575.0	575.0	574.6	574.3	573.9	573.5	572.6	571.8	571.0	570.1	569.3
127.5°	628.5	629.0	628.5	628.0	627.6	627.2	626.1	624.9	623.8	622.6	621.5
130°	663.7	664.2	663.6	663.0	662.4	661.8	661.0	660.1	659.3	658.5	657.4
132.5°	697.6	698.2	697.8	697.3	696.8	696.4	695.4	694.4	693.5	692.4	691.4
135°	747.7	748.2	748.0	747.8	747.6	747.3	746.6	745.8	744.9	744.1	743.5
137.5°	794.7	795.5	796.1	796.5	797.1	797.6	796.8	795.9	795.0	794.2	793.4
140°	827.8	828.5	828.7	828.9	829.1	829.3	829.1	828.9	828.7	828.5	827.7
142.5°	858.1	858.7	859.1	859.5	859.8	860.2	860.0	859.8	859.6	859.4	858.7
145°	902.7	903.2	903.9	904.4	905.1	905.7	905.5	905.3	905.1	904.9	904.4
147.5°	945.3	945.9	946.5	947.1	947.6	948.2	948.2	948.2	948.2	948.2	947.6
150°	972.7	973.1	973.5	973.9	974.3	974.7	974.7	974.7	974.7	974.7	974.1
152.5°	996.9	997.3	997.5	997.8	998.1	998.3	998.6	998.9	999.3	999.6	999.3
155°	1031.8	1031.9	1032.1	1032.3	1032.5	1032.7	1033.6	1034.4	1035.1	1036.0	1035.7
157.5°	1062.5	1062.4	1062.6	1062.8	1063.0	1063.1	1064.0	1064.8	1065.6	1066.5	1066.4
160°	1081.7	1081.5	1081.5	1081.5	1081.5	1081.5	1082.5	1083.5	1084.6	1085.6	1085.7
162.5°	1098.8	1098.5	1098.7	1098.8	1099.0	1099.2	1100.2	1101.2	1102.2	1103.3	1103.1
165°	1121.4	1121.1	1121.1	1121.1	1121.1	1121.1	1122.3	1123.6	1124.7	1126.0	1125.8
167.5°	1138.8	1138.4	1138.6	1138.8	1138.9	1139.1	1140.3	1141.6	1142.9	1144.1	1144.1
170°	1149.1	1148.7	1148.7	1148.7	1148.7	1148.7	1150.1	1151.5	1153.0	1154.4	1154.4
172.5°	1157.2	1156.8	1156.8	1156.8	1156.8	1156.8	1158.1	1159.4	1160.6	1161.9	1161.8
175°	1165.7	1165.2	1165.2	1165.2	1165.2	1165.2	1166.5	1167.7	1168.9	1170.1	1170.1
177.5°	1169.8	1169.5	1169.5	1169.5	1169.5	1169.5	1170.4	1171.5	1172.4	1173.4	1173.3
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P332325-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	923.1	922.7	923.1	921.7	923.1	922.7	923.1	927.0	927.0	927.4	927.7
5°	859.0	858.5	857.3	853.6	857.3	858.5	859.0	860.2	863.5	869.3	867.7
7.5°	803.0	802.4	798.8	798.8	798.8	802.4	803.0	806.2	809.9	813.5	817.7
10°	769.8	770.2	765.2	762.3	765.2	770.2	769.8	772.7	778.1	780.9	783.9
12.5°	737.6	735.7	731.7	728.5	731.7	735.7	737.6	739.8	747.2	750.4	756.0
15°	695.1	690.9	681.0	681.8	681.0	690.9	695.1	693.5	700.9	705.0	706.7
17.5°	645.1	642.1	641.8	636.0	641.8	642.1	645.1	648.4	654.9	659.3	671.2
20°	615.9	613.9	614.7	608.9	614.7	613.9	615.9	622.5	626.7	632.5	642.1
22.5°	593.0	591.0	587.5	585.7	587.5	591.0	593.0	597.6	602.1	610.3	615.4
25°	559.5	556.2	552.9	554.9	552.9	556.2	559.5	562.0	570.3	574.0	581.5
27.5°	526.0	523.5	520.1	519.8	520.1	523.5	526.0	528.4	533.0	539.2	548.2
30°	504.8	502.2	500.6	498.5	500.6	502.2	504.8	506.8	511.4	518.0	524.7
32.5°	483.2	482.7	479.7	479.3	479.7	482.7	483.2	486.6	491.2	497.4	503.1
35°	455.0	452.5	451.6	452.1	451.6	452.5	455.0	456.6	460.8	466.6	472.0
37.5°	428.2	424.8	423.3	421.9	423.3	424.8	428.2	428.4	432.7	436.6	443.9
40°	408.9	405.6	404.8	403.9	404.8	405.6	408.9	408.5	413.1	416.0	422.6
42.5°	387.4	386.0	385.6	384.0	385.6	386.0	387.4	389.6	392.2	396.4	401.4
45°	357.9	357.5	355.1	355.8	355.1	357.5	357.9	359.2	363.8	366.6	371.2
47.5°	326.9	325.1	323.4	324.5	323.4	325.1	326.9	328.6	331.6	335.2	341.3
50°	305.7	304.8	301.1	301.9	301.1	304.8	305.7	307.4	309.4	313.9	319.3
52.5°	284.5	281.3	279.9	279.4	279.9	281.3	284.5	286.1	288.5	293.7	297.8
55°	249.3	245.5	243.8	243.0	243.8	245.5	249.3	252.2	255.5	261.3	265.5
57.5°	214.8	213.7	212.5	213.3	212.5	213.7	214.8	219.6	222.8	227.4	232.4
60°	194.5	194.5	194.5	194.1	194.5	194.5	194.5	198.7	201.5	206.1	211.5
62.5°	179.0	177.9	177.6	178.2	177.6	177.9	179.0	180.8	183.6	186.6	191.3
65°	155.1	154.7	153.0	152.7	153.0	154.7	155.1	156.4	158.8	160.9	164.2
67.5°	132.6	131.1	130.6	130.1	130.6	131.1	132.6	133.7	135.4	138.0	139.7
70°	115.7	114.9	112.4	112.8	112.4	114.9	115.7	117.8	119.5	122.8	124.5
72.5°	97.4	96.6	96.2	95.5	96.2	96.6	97.4	99.6	101.2	104.9	107.5
75°	77.2	76.8	76.3	78.0	76.3	76.8	77.2	77.6	78.0	79.2	80.5
77.5°	61.8	61.8	62.0	61.4	62.0	61.8	61.8	61.8	61.8	62.4	62.7
80°	51.8	51.8	51.4	51.4	51.4	51.8	51.8	51.8	51.8	51.8	51.4
82.5°	41.6	41.9	42.1	41.5	42.1	41.9	41.6	42.2	42.5	41.9	42.1
85°	27.4	26.9	27.8	27.4	27.8	26.9	27.4	27.4	26.5	27.4	26.9
87.5°	17.6	17.0	17.0	17.4	17.0	17.0	17.6	16.8	16.7	16.6	16.0
90°	26.4	26.8	27.2	27.6	27.2	26.8	26.4	26.0	25.3	24.6	23.8
92.5°	37.9	37.7	37.4	37.2	37.4	37.7	37.9	38.2	37.9	37.3	36.7
95°	71.8	71.8	71.8	71.8	71.8	71.8	71.8	71.8	71.4	70.6	69.7
97.5°	110.7	110.6	110.5	110.4	110.5	110.6	110.7	110.7	110.4	109.4	108.4
100°	138.7	139.1	139.5	139.9	139.5	139.1	138.7	138.2	137.8	137.1	136.5
102.5°	170.3	170.2	170.2	170.1	170.2	170.2	170.3	170.4	170.2	169.5	168.9
105°	217.9	218.2	218.6	219.0	218.6	218.2	217.9	217.5	217.2	217.2	217.2
107.5°	270.8	270.5	270.3	270.1	270.3	270.5	270.8	271.0	270.8	270.2	269.5
110°	305.9	305.5	305.1	304.7	305.1	305.5	305.9	306.3	306.1	305.3	304.4



TEST NUMBER: P332325-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	341.7	341.7	341.6	341.5	341.6	341.7	341.7	341.8	341.4	340.4	339.4
115°	392.7	392.5	392.3	392.1	392.3	392.5	392.7	392.9	392.9	392.7	392.5
117.5°	445.2	444.6	444.0	443.5	444.0	444.6	445.2	445.8	446.1	446.1	446.2
120°	480.8	480.4	480.0	479.5	480.0	480.4	480.8	481.2	481.5	481.7	481.9
122.5°	515.9	515.3	514.7	514.1	514.7	515.3	515.9	516.4	517.0	517.5	518.1
125°	568.5	567.7	566.9	566.1	566.9	567.7	568.5	569.3	570.1	571.0	571.8
127.5°	620.6	619.6	618.7	617.8	618.7	619.6	620.6	621.5	622.6	623.8	624.9
130°	655.9	654.5	653.1	651.6	653.1	654.5	655.9	657.4	658.5	659.3	660.1
132.5°	690.3	689.2	688.1	687.0	688.1	689.2	690.3	691.4	692.4	693.5	694.4
135°	743.1	742.7	742.3	741.9	742.3	742.7	743.1	743.5	744.1	744.9	745.8
137.5°	792.6	791.9	791.1	790.3	791.1	791.9	792.6	793.4	794.2	795.0	795.9
140°	826.2	824.8	823.4	822.0	823.4	824.8	826.2	827.7	828.5	828.7	828.9
142.5°	857.6	856.5	855.5	854.4	855.5	856.5	857.6	858.7	859.4	859.6	859.8
145°	903.6	902.7	901.9	901.1	901.9	902.7	903.6	904.4	904.9	905.1	905.3
147.5°	946.3	945.2	943.9	942.7	943.9	945.2	946.3	947.6	948.2	948.2	948.2
150°	972.9	971.7	970.4	969.2	970.4	971.7	972.9	974.1	974.7	974.7	974.7
152.5°	998.1	997.1	996.0	995.0	996.0	997.1	998.1	999.3	999.6	999.3	998.9
155°	1034.3	1032.8	1031.4	1029.9	1031.4	1032.8	1034.3	1035.7	1036.0	1035.1	1034.4
157.5°	1065.2	1064.1	1063.0	1061.8	1063.0	1064.1	1065.2	1066.4	1066.5	1065.6	1064.8
160°	1084.9	1084.0	1083.2	1082.4	1083.2	1084.0	1084.9	1085.7	1085.6	1084.6	1083.5
162.5°	1101.8	1100.5	1099.2	1097.9	1099.2	1100.5	1101.8	1103.1	1103.3	1102.2	1101.2
165°	1124.4	1123.0	1121.6	1120.1	1121.6	1123.0	1124.4	1125.8	1126.0	1124.7	1123.6
167.5°	1142.9	1141.6	1140.3	1139.1	1140.3	1141.6	1142.9	1144.1	1144.1	1142.9	1141.6
170°	1153.0	1151.5	1150.1	1148.7	1150.1	1151.5	1153.0	1154.4	1154.4	1153.0	1151.5
172.5°	1160.3	1158.9	1157.5	1156.0	1157.5	1158.9	1160.3	1161.8	1161.9	1160.6	1159.4
175°	1168.6	1167.2	1165.8	1164.3	1165.8	1167.2	1168.6	1170.1	1170.1	1168.9	1167.7
177.5°	1172.2	1171.0	1169.9	1168.8	1169.9	1171.0	1172.2	1173.3	1173.4	1172.4	1171.5
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P332325-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	924.7	929.4	934.0	938.3	945.0	947.9	952.3	953.9	958.9	966.2	972.2
5°	868.5	875.1	883.8	890.9	902.1	910.8	920.4	929.5	940.2	955.6	969.2
7.5°	820.8	827.4	837.8	850.9	863.2	875.6	888.7	901.1	916.5	938.5	960.3
10°	789.3	797.2	809.6	823.7	839.0	851.0	866.4	882.2	901.3	926.5	952.7
12.5°	762.1	767.9	782.4	795.8	813.2	828.5	843.5	861.9	883.7	910.6	942.1
15°	718.7	727.1	741.2	756.1	774.4	790.5	810.0	832.4	853.6	886.8	924.9
17.5°	675.3	687.9	702.6	719.5	732.9	755.3	776.4	799.4	825.5	860.6	902.5
20°	647.5	657.4	671.1	695.5	713.4	730.4	749.9	778.5	802.6	842.3	885.9
22.5°	623.8	631.1	646.5	666.7	687.5	707.2	727.0	754.2	783.9	821.8	868.9
25°	588.9	600.6	612.2	626.7	649.1	672.7	694.3	717.5	749.0	789.3	840.3
27.5°	554.8	565.4	576.9	594.7	611.6	633.7	656.3	682.9	716.8	759.3	811.1
30°	533.0	540.8	551.6	574.4	589.8	608.9	635.4	659.0	690.5	735.8	790.5
32.5°	510.4	520.6	532.3	549.9	568.9	586.9	611.2	636.8	669.0	713.5	769.6
35°	478.2	490.2	502.2	515.1	534.2	552.9	573.1	601.3	634.1	677.3	732.5
37.5°	448.6	458.3	468.1	484.0	502.1	519.8	538.8	566.6	597.5	644.0	694.6
40°	429.7	438.4	445.8	462.5	479.8	498.9	517.6	542.1	575.3	618.8	667.7
42.5°	409.1	417.2	427.3	440.8	459.6	475.7	494.4	517.5	548.7	592.9	635.9
45°	378.3	387.4	396.1	408.9	427.6	443.4	459.9	482.0	513.9	550.4	588.5
47.5°	346.2	355.3	365.2	377.6	394.0	410.0	426.5	446.0	475.2	511.0	536.7
50°	325.6	333.0	343.0	355.5	370.3	387.4	402.3	423.4	451.2	479.4	501.8
52.5°	304.4	311.2	322.4	335.6	349.4	364.2	380.1	398.2	423.3	449.9	467.7
55°	271.2	279.6	289.1	301.9	315.6	328.0	343.4	362.1	382.0	401.9	413.9
57.5°	240.3	247.2	255.2	268.5	280.4	295.2	309.0	323.5	341.9	357.0	364.8
60°	217.8	223.9	234.3	246.0	257.1	270.0	285.7	300.3	314.4	326.4	332.6
62.5°	196.5	203.7	212.8	223.4	235.6	247.8	261.6	273.7	286.1	296.5	300.8
65°	168.8	174.6	181.3	191.2	201.1	213.6	224.3	236.8	246.0	251.8	255.5
67.5°	143.6	147.4	152.5	159.1	168.9	179.7	190.2	199.9	207.6	211.5	214.8
70°	127.3	129.8	133.6	140.2	147.7	157.2	167.9	175.0	181.6	185.0	188.3
72.5°	111.1	114.2	117.6	122.9	129.0	135.9	143.8	152.5	156.1	160.1	162.1
75°	84.2	88.7	93.3	96.6	100.8	106.2	113.2	118.6	120.7	124.0	124.5
77.5°	63.5	64.6	67.9	72.0	75.5	79.4	83.9	88.6	89.7	91.4	92.5
80°	52.3	52.3	52.3	54.7	58.9	61.8	65.9	68.4	70.1	70.5	70.9
82.5°	42.0	42.0	41.7	42.1	43.6	45.2	49.0	51.8	53.2	52.9	52.0
85°	27.4	26.5	26.5	26.1	26.5	25.7	25.3	26.9	29.5	29.5	28.6
87.5°	15.8	15.4	15.1	14.3	13.5	12.6	11.1	11.0	10.6	11.6	10.8
90°	22.9	22.1	19.4	16.8	14.1	11.5	9.1	7.1	5.0	2.9	1.0
92.5°	36.0	35.3	33.8	32.3	30.8	29.3	27.8	26.5	25.0	23.7	22.3
95°	68.9	68.1	66.5	64.8	63.2	61.6	60.0	58.6	57.2	55.8	54.3
97.5°	107.5	106.5	105.4	104.3	103.1	101.9	100.7	99.7	98.6	97.5	96.5
100°	135.9	135.3	134.3	133.2	132.2	131.2	130.1	128.9	127.6	126.4	125.2
102.5°	168.3	167.7	166.4	165.0	163.7	162.3	161.3	160.5	159.8	159.1	158.3
105°	217.2	217.2	215.4	213.6	211.7	209.8	208.7	208.3	207.9	207.5	207.1
107.5°	268.9	268.2	267.4	266.7	266.0	265.3	264.7	264.5	264.3	264.0	263.8
110°	303.6	302.9	302.4	302.0	301.6	301.2	300.8	300.4	299.9	299.5	299.1



TEST NUMBER: P332325-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	338.4	337.4	337.3	337.2	337.2	337.1	336.9	336.7	336.4	336.2	336.0
115°	392.3	392.1	392.5	392.9	393.3	393.7	393.6	393.0	392.4	391.8	391.2
117.5°	446.2	446.2	446.8	447.3	447.8	448.4	448.4	448.0	447.6	447.2	446.8
120°	482.1	482.3	483.3	484.3	485.4	486.4	486.3	485.1	483.9	482.6	481.4
122.5°	518.6	519.1	519.7	520.1	520.7	521.3	521.1	520.1	519.3	518.3	517.5
125°	572.6	573.5	573.9	574.3	574.6	575.0	575.0	574.3	573.7	573.1	572.5
127.5°	626.1	627.2	627.6	628.0	628.5	629.0	628.5	627.2	625.9	624.6	623.3
130°	661.0	661.8	662.4	663.0	663.6	664.2	663.7	662.1	660.4	658.8	657.2
132.5°	695.4	696.4	696.8	697.3	697.8	698.2	697.6	695.9	694.3	692.7	691.0
135°	746.6	747.3	747.6	747.8	748.0	748.2	747.7	746.5	745.2	744.0	742.8
137.5°	796.8	797.6	797.1	796.5	796.1	795.5	794.7	793.7	792.7	791.6	790.7
140°	829.1	829.3	829.1	828.9	828.7	828.5	827.8	826.9	825.9	824.8	823.8
142.5°	860.0	860.2	859.8	859.5	859.1	858.7	858.1	857.1	856.0	855.0	854.0
145°	905.5	905.7	905.1	904.4	903.9	903.2	902.7	902.3	901.9	901.5	901.1
147.5°	948.2	948.2	947.6	947.1	946.5	945.9	945.3	944.5	943.8	943.1	942.3
150°	974.7	974.7	974.3	973.9	973.5	973.1	972.7	972.2	971.8	971.5	971.1
152.5°	998.6	998.3	998.1	997.8	997.5	997.3	996.9	996.3	995.8	995.2	994.6
155°	1033.6	1032.7	1032.5	1032.3	1032.1	1031.9	1031.8	1031.8	1031.8	1031.8	1031.8
157.5°	1064.0	1063.1	1063.0	1062.8	1062.6	1062.4	1062.5	1062.7	1063.0	1063.2	1063.4
160°	1082.5	1081.5	1081.5	1081.5	1081.5	1081.5	1081.7	1082.1	1082.5	1082.9	1083.3
162.5°	1100.2	1099.2	1099.0	1098.8	1098.7	1098.5	1098.8	1099.3	1099.9	1100.4	1101.0
165°	1122.3	1121.1	1121.1	1121.1	1121.1	1121.1	1121.4	1122.0	1122.6	1123.2	1123.9
167.5°	1140.3	1139.1	1138.9	1138.8	1138.6	1138.4	1138.8	1139.6	1140.4	1141.2	1142.1
170°	1150.1	1148.7	1148.7	1148.7	1148.7	1148.7	1149.1	1149.9	1150.7	1151.5	1152.4
172.5°	1158.1	1156.8	1156.8	1156.8	1156.8	1156.8	1157.2	1158.0	1158.8	1159.7	1160.5
175°	1166.5	1165.2	1165.2	1165.2	1165.2	1165.2	1165.7	1166.5	1167.3	1168.2	1168.9
177.5°	1170.4	1169.5	1169.5	1169.5	1169.5	1169.5	1169.8	1170.4	1171.2	1171.8	1172.4
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P332325-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	974.1	977.8	982.5	989.4	994.7	999.3	1000.4	1001.7	1005.0	1010.7	1014.9
5°	980.5	990.0	1005.4	1020.3	1036.5	1049.7	1062.2	1070.9	1079.2	1096.6	1110.7
7.5°	978.5	999.7	1023.7	1050.6	1077.7	1104.0	1128.4	1150.2	1171.9	1197.3	1226.2
10°	977.2	1002.0	1034.4	1068.8	1106.5	1143.4	1179.2	1206.9	1239.3	1268.3	1305.2
12.5°	970.8	1006.7	1045.4	1089.4	1135.8	1178.3	1225.3	1263.7	1300.7	1342.6	1385.5
15°	962.7	1006.2	1055.1	1113.6	1184.1	1235.6	1283.7	1350.4	1396.1	1441.7	1503.0
17.5°	947.6	1000.8	1061.9	1137.9	1196.7	1265.8	1338.2	1391.0	1452.5	1516.7	1572.3
20°	935.6	997.4	1065.9	1140.6	1215.6	1290.7	1360.8	1423.8	1487.3	1561.5	1607.2
22.5°	923.8	984.8	1056.0	1135.3	1215.9	1295.0	1374.4	1448.3	1519.8	1594.7	1653.0
25°	898.3	970.9	1048.1	1128.9	1208.6	1295.7	1390.2	1472.7	1561.1	1638.2	1693.4
27.5°	872.6	939.1	1016.0	1098.0	1186.5	1289.4	1400.7	1494.5	1583.0	1638.2	1655.6
30°	849.4	919.9	990.4	1073.8	1169.6	1284.4	1402.6	1510.1	1582.7	1606.7	1588.9
32.5°	825.9	889.7	959.6	1044.9	1146.7	1272.2	1405.3	1500.8	1544.5	1526.1	1453.5
35°	784.3	841.9	909.5	995.0	1111.9	1265.4	1394.4	1459.0	1448.3	1344.6	1207.8
37.5°	739.8	786.8	849.4	938.7	1075.9	1238.4	1347.3	1356.8	1263.5	1104.3	946.2
40°	704.6	746.9	811.3	904.6	1048.1	1211.9	1299.8	1261.2	1116.5	939.4	807.6
42.5°	670.5	706.2	768.1	868.7	1021.5	1175.8	1229.2	1145.1	978.1	810.6	690.7
45°	612.6	646.2	708.4	811.7	967.2	1106.5	1099.5	953.5	786.4	651.6	552.0
47.5°	557.7	587.0	645.4	750.8	903.4	1002.8	936.9	781.6	639.8	531.6	460.7
50°	518.9	547.9	605.9	710.0	852.3	924.9	830.8	681.0	551.2	461.6	405.2
52.5°	481.7	510.1	563.2	664.6	790.6	834.0	732.8	594.1	485.8	408.5	360.0
55°	429.7	451.2	498.9	596.0	690.1	700.1	597.6	481.5	392.4	338.4	305.2
57.5°	376.7	395.2	442.4	519.7	585.7	580.6	483.5	382.9	322.9	282.9	258.8
60°	342.1	360.4	401.9	468.3	518.0	500.6	411.5	330.6	279.1	249.7	230.6
62.5°	310.0	324.2	363.1	411.5	447.3	427.6	351.7	284.8	244.0	219.1	204.1
65°	263.4	275.0	306.1	331.4	351.3	332.2	269.2	222.7	193.3	175.9	165.5
67.5°	219.0	226.5	246.1	255.2	269.3	248.3	202.4	171.3	154.6	139.8	132.6
70°	191.2	196.6	207.0	214.4	218.2	196.6	162.6	139.7	125.6	115.3	110.7
72.5°	163.3	168.0	170.2	176.3	174.4	154.2	130.7	112.6	102.4	95.4	89.5
75°	124.8	126.9	124.8	122.3	116.9	102.8	86.7	77.6	70.1	66.8	64.7
77.5°	91.0	90.3	87.5	83.6	74.4	65.5	56.8	53.8	50.5	48.8	48.0
80°	70.1	68.4	65.9	59.7	51.8	45.6	43.6	41.5	40.2	38.2	37.7
82.5°	52.2	51.2	47.1	41.8	36.3	33.4	31.6	30.9	29.6	28.5	28.4
85°	27.8	26.5	21.9	19.1	18.2	17.4	17.0	17.0	15.4	14.9	14.9
87.5°	9.6	8.0	8.1	7.4	7.9	7.8	8.6	8.6	8.7	9.2	8.7
90°	2.9	5.0	7.1	9.1	11.5	14.1	16.8	19.4	22.1	22.9	23.8
92.5°	23.7	25.0	26.5	27.8	29.3	30.8	32.3	33.8	35.3	36.0	36.7
95°	55.8	57.2	58.6	60.0	61.6	63.2	64.8	66.5	68.1	68.9	69.7
97.5°	97.5	98.6	99.7	100.7	101.9	103.1	104.3	105.4	106.5	107.5	108.4
100°	126.4	127.6	128.9	130.1	131.2	132.2	133.2	134.3	135.3	135.9	136.5
102.5°	159.1	159.8	160.5	161.3	162.3	163.7	165.0	166.4	167.7	168.3	168.9
105°	207.5	207.9	208.3	208.7	209.8	211.7	213.6	215.4	217.2	217.2	217.2
107.5°	264.0	264.3	264.5	264.7	265.3	266.0	266.7	267.4	268.2	268.9	269.5
110°	299.5	299.9	300.4	300.8	301.2	301.6	302.0	302.4	302.9	303.6	304.4





TEST NUMBER: P332325-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	336.2	336.4	336.7	336.9	337.1	337.2	337.2	337.3	337.4	338.4	339.4
115°	391.8	392.4	393.0	393.6	393.7	393.3	392.9	392.5	392.1	392.3	392.5
117.5°	447.2	447.6	448.0	448.4	448.4	447.8	447.3	446.8	446.2	446.2	446.2
120°	482.6	483.9	485.1	486.3	486.4	485.4	484.3	483.3	482.3	482.1	481.9
122.5°	518.3	519.3	520.1	521.1	521.3	520.7	520.1	519.7	519.1	518.6	518.1
125°	573.1	573.7	574.3	575.0	575.0	574.6	574.3	573.9	573.5	572.6	571.8
127.5°	624.6	625.9	627.2	628.5	629.0	628.5	628.0	627.6	627.2	626.1	624.9
130°	658.8	660.4	662.1	663.7	664.2	663.6	663.0	662.4	661.8	661.0	660.1
132.5°	692.7	694.3	695.9	697.6	698.2	697.8	697.3	696.8	696.4	695.4	694.4
135°	744.0	745.2	746.5	747.7	748.2	748.0	747.8	747.6	747.3	746.6	745.8
137.5°	791.6	792.7	793.7	794.7	795.5	796.1	796.5	797.1	797.6	796.8	795.9
140°	824.8	825.9	826.9	827.8	828.5	828.7	828.9	829.1	829.3	829.1	828.9
142.5°	855.0	856.0	857.1	858.1	858.7	859.1	859.5	859.8	860.2	860.0	859.8
145°	901.5	901.9	902.3	902.7	903.2	903.9	904.4	905.1	905.7	905.5	905.3
147.5°	943.1	943.8	944.5	945.3	945.9	946.5	947.1	947.6	948.2	948.2	948.2
150°	971.5	971.8	972.2	972.7	973.1	973.5	973.9	974.3	974.7	974.7	974.7
152.5°	995.2	995.8	996.3	996.9	997.3	997.5	997.8	998.1	998.3	998.6	998.9
155°	1031.8	1031.8	1031.8	1031.8	1031.9	1032.1	1032.3	1032.5	1032.7	1033.6	1034.4
157.5°	1063.2	1063.0	1062.7	1062.5	1062.4	1062.6	1062.8	1063.0	1063.1	1064.0	1064.8
160°	1082.9	1082.5	1082.1	1081.7	1081.5	1081.5	1081.5	1081.5	1081.5	1082.5	1083.5
162.5°	1100.4	1099.9	1099.3	1098.8	1098.5	1098.7	1098.8	1099.0	1099.2	1100.2	1101.2
165°	1123.2	1122.6	1122.0	1121.4	1121.1	1121.1	1121.1	1121.1	1121.1	1122.3	1123.6
167.5°	1141.2	1140.4	1139.6	1138.8	1138.4	1138.6	1138.8	1138.9	1139.1	1140.3	1141.6
170°	1151.5	1150.7	1149.9	1149.1	1148.7	1148.7	1148.7	1148.7	1148.7	1150.1	1151.5
172.5°	1159.7	1158.8	1158.0	1157.2	1156.8	1156.8	1156.8	1156.8	1156.8	1158.1	1159.4
175°	1168.2	1167.3	1166.5	1165.7	1165.2	1165.2	1165.2	1165.2	1165.2	1166.5	1167.7
177.5°	1171.8	1171.2	1170.4	1169.8	1169.5	1169.5	1169.5	1169.5	1169.5	1170.4	1171.5
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7



TEST NUMBER: P332325-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1021.9	1021.9	1023.3	1028.3	1028.9	1033.2	1031.9
5°	1123.2	1131.0	1133.9	1146.4	1153.8	1157.1	1150.5
7.5°	1246.9	1269.2	1279.7	1292.7	1304.2	1307.7	1298.6
10°	1337.1	1360.3	1379.9	1391.9	1403.1	1410.6	1420.1
12.5°	1424.4	1452.9	1471.5	1488.4	1500.0	1509.4	1511.0
15°	1519.2	1562.3	1595.1	1619.1	1631.2	1637.4	1634.9
17.5°	1614.9	1654.9	1678.2	1702.7	1719.4	1720.2	1720.7
20°	1669.0	1707.9	1734.9	1753.1	1771.8	1771.0	1775.1
22.5°	1705.1	1735.8	1756.4	1769.7	1776.2	1773.0	1773.8
25°	1722.0	1731.2	1727.4	1706.3	1700.9	1681.4	1684.7
27.5°	1634.7	1591.7	1547.0	1489.6	1444.3	1408.2	1410.0
30°	1516.3	1440.0	1352.9	1279.9	1214.4	1196.1	1157.1
32.5°	1350.8	1236.3	1134.2	1066.2	1010.0	994.7	960.8
35°	1070.1	958.9	854.0	790.9	766.0	731.2	730.8
37.5°	831.7	733.9	678.3	631.1	606.3	585.2	583.1
40°	699.7	623.4	581.5	547.5	523.0	507.2	503.5
42.5°	607.4	545.7	506.5	485.4	466.6	458.4	452.4
45°	496.1	454.6	427.2	408.1	399.4	393.2	389.8
47.5°	414.9	387.1	368.4	355.8	348.7	342.1	343.9
50°	370.8	348.0	334.3	322.3	316.9	312.3	312.8
52.5°	335.3	314.8	303.7	295.1	288.4	285.1	283.5
55°	284.6	271.6	260.5	254.2	250.5	246.0	244.7
57.5°	242.7	232.7	223.6	216.6	215.6	211.3	211.8
60°	214.8	206.5	199.1	195.4	192.4	188.7	190.0
62.5°	191.9	185.0	178.2	175.1	172.2	169.4	170.1
65°	157.2	150.5	146.4	144.7	143.5	142.3	141.0
67.5°	125.2	121.2	118.6	115.0	112.5	112.1	110.8
70°	105.4	100.0	95.4	90.9	89.6	89.2	89.6
72.5°	84.4	81.0	79.8	77.6	77.3	76.2	77.0
75°	63.5	62.2	61.4	59.7	59.7	59.7	59.7
77.5°	46.8	46.0	45.6	45.2	44.8	44.2	44.1
80°	36.5	36.0	35.3	35.3	34.9	35.3	34.9
82.5°	27.6	27.5	26.6	26.6	26.2	26.0	26.2
85°	14.1	13.7	14.5	13.7	14.1	13.3	14.1
87.5°	8.9	9.0	8.9	9.0	8.7	9.4	8.9
90°	24.6	25.3	26.0	26.4	26.8	27.2	27.6
92.5°	37.3	37.9	38.2	37.9	37.7	37.4	37.2
95°	70.6	71.4	71.8	71.8	71.8	71.8	71.8
97.5°	109.4	110.4	110.7	110.7	110.6	110.5	110.4
100°	137.1	137.8	138.2	138.7	139.1	139.5	139.9
102.5°	169.5	170.2	170.4	170.3	170.2	170.2	170.1
105°	217.2	217.2	217.5	217.9	218.2	218.6	219.0
107.5°	270.2	270.8	271.0	270.8	270.5	270.3	270.1
110°	305.3	306.1	306.3	305.9	305.5	305.1	304.7



TEST NUMBER: P332325-927

CATALOG NUMBER: S123RDIP-S775D1195U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	340.4	341.4	341.8	341.7	341.7	341.6	341.5
115°	392.7	392.9	392.9	392.7	392.5	392.3	392.1
117.5°	446.1	446.1	445.8	445.2	444.6	444.0	443.5
120°	481.7	481.5	481.2	480.8	480.4	480.0	479.5
122.5°	517.5	517.0	516.4	515.9	515.3	514.7	514.1
125°	571.0	570.1	569.3	568.5	567.7	566.9	566.1
127.5°	623.8	622.6	621.5	620.6	619.6	618.7	617.8
130°	659.3	658.5	657.4	655.9	654.5	653.1	651.6
132.5°	693.5	692.4	691.4	690.3	689.2	688.1	687.0
135°	744.9	744.1	743.5	743.1	742.7	742.3	741.9
137.5°	795.0	794.2	793.4	792.6	791.9	791.1	790.3
140°	828.7	828.5	827.7	826.2	824.8	823.4	822.0
142.5°	859.6	859.4	858.7	857.6	856.5	855.5	854.4
145°	905.1	904.9	904.4	903.6	902.7	901.9	901.1
147.5°	948.2	948.2	947.6	946.3	945.2	943.9	942.7
150°	974.7	974.7	974.1	972.9	971.7	970.4	969.2
152.5°	999.3	999.6	999.3	998.1	997.1	996.0	995.0
155°	1035.1	1036.0	1035.7	1034.3	1032.8	1031.4	1029.9
157.5°	1065.6	1066.5	1066.4	1065.2	1064.1	1063.0	1061.8
160°	1084.6	1085.6	1085.7	1084.9	1084.0	1083.2	1082.4
162.5°	1102.2	1103.3	1103.1	1101.8	1100.5	1099.2	1097.9
165°	1124.7	1126.0	1125.8	1124.4	1123.0	1121.6	1120.1
167.5°	1142.9	1144.1	1144.1	1142.9	1141.6	1140.3	1139.1
170°	1153.0	1154.4	1154.4	1153.0	1151.5	1150.1	1148.7
172.5°	1160.6	1161.9	1161.8	1160.3	1158.9	1157.5	1156.0
175°	1168.9	1170.1	1170.1	1168.6	1167.2	1165.8	1164.3
177.5°	1172.4	1173.4	1173.3	1172.2	1171.0	1169.9	1168.8
180°	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7	1171.7

(END OF REPORT)