

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331865

Luminaire Tested: **S123DIP-S340D365U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331865
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D365U835-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2903.1 lumens
Efficiency: N/A
Efficacy: 143.0 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331865

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331865

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50																				
1	98	94	90	87	90	87	84	81	73	71	69	61	60	58	50	49	48	43																				
2	89	82	76	71	82	76	71	67	65	61	58	54	51	49	44	42	41	36																				
3	82	72	65	60	75	67	61	56	57	53	49	48	45	42	40	37	35	31																				
4	75	64	56	51	69	60	53	48	51	46	42	43	39	36	35	33	30	27																				
5	69	57	49	43	63	53	46	41	46	40	36	39	34	31	32	29	26	23																				
6	63	51	43	38	58	48	41	36	41	36	31	35	31	27	29	26	23	21																				
7	59	47	39	33	54	43	36	31	37	32	28	32	27	24	27	23	21	18																				
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19	16																				
9	51	39	31	26	47	36	29	25	31	26	22	27	23	19	23	19	17	15																				
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	15	13																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5175	5175	5175	5175
5°	6172	5198	4606	5198
10°	7725	5172	4161	5172
15°	9475	5129	3874	5129
20°	11287	5065	3688	5065
25°	11986	4986	3646	4986
30°	10274	4928	3665	4928
35°	7144	4846	3704	4846
40°	5382	4749	3693	4749
45°	4468	4606	3646	4606
50°	4002	4315	3612	4315
55°	3742	4001	3567	4001
60°	3511	3670	3531	3670
65°	3298	3347	3418	3347
70°	3094	2977	3254	2977
75°	2770	2608	2986	2608
80°	2424	2139	2572	2139
85°	1902	1556	1729	1556



TEST NUMBER: P331865

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.4	1.6
10°-20°	151.9	5.2
20°-30°	254.9	8.8
30°-40°	288.6	9.9
40°-50°	258.8	8.9
50°-60°	208.9	7.2
60°-70°	145.6	5.0
70°-80°	76.5	2.6
80°-90°	20.0	0.7
90°-100°	17.3	0.6
100°-110°	82.4	2.8
110°-120°	198.0	6.8
120°-130°	252.1	8.7
130°-140°	269.3	9.3
140°-150°	251.9	8.7
150°-160°	203.2	7.0
160°-170°	131.1	4.5
170°-180°	45.2	1.6
0°-30°	454.2	15.6
0°-40°	742.8	25.6
0°-60°	1210.5	41.7
0°-90°	1452.6	50.0
90°-120°	297.7	10.3
90°-150°	1071.0	36.9
90°-180°	1450.0	49.9
0°-180°	2903.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	481	481	481	481	481	
5°	571	481	426	481	571	59
15°	850	460	348	460	850	246
25°	1009	420	307	420	1009	443
35°	544	369	282	369	544	353
45°	294	303	240	303	294	232
55°	199	213	190	213	199	179
65°	130	131	134	131	130	129
75°	67	63	72	63	67	71
85°	15	13	14	13	15	18
90°	11	0	11	0	11	6
95°	13	22	13	22	13	11
105°	16	105	16	105	16	36
115°	208	198	208	198	208	192
125°	284	278	284	278	284	254
135°	350	347	350	347	350	270
145°	404	400	404	400	404	252
155°	440	441	440	441	440	203
165°	464	465	464	465	464	131
175°	474	476	474	476	474	45
180°	476	476	476	476	476	



TEST NUMBER: P331865

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	510.3	509.9	509.0	509.7	508.2	506.2	506.0	504.1	498.7	498.4	496.9
5°	571.2	569.4	569.1	568.9	565.6	561.2	552.8	552.1	540.9	535.4	528.6
7.5°	650.2	651.1	647.7	644.8	634.8	628.2	619.2	607.7	594.0	580.0	570.8
10°	706.8	714.5	705.0	698.4	692.4	681.0	667.7	651.1	634.6	615.3	600.6
12.5°	767.6	771.3	769.4	763.3	753.9	736.5	713.0	694.7	679.5	647.3	634.3
15°	850.3	864.5	855.4	834.5	834.9	818.4	787.7	753.9	735.9	707.7	669.3
17.5°	938.5	940.2	936.4	918.9	907.3	884.5	856.1	823.8	787.4	753.3	712.5
20°	985.4	984.0	975.9	966.8	946.8	929.1	898.1	862.0	815.4	781.8	737.3
22.5°	1011.5	1009.2	1005.3	997.7	981.1	962.1	934.2	894.8	850.4	804.2	752.8
25°	1009.2	1012.2	1012.7	1010.6	1004.8	993.4	971.5	940.0	895.8	836.3	782.8
27.5°	917.9	922.2	934.6	945.7	958.0	970.6	968.9	953.3	920.5	869.2	803.7
30°	826.6	817.2	840.3	869.4	889.2	924.2	943.7	944.9	926.5	882.5	818.6
32.5°	699.8	710.1	720.3	756.1	799.4	838.6	877.6	908.9	912.5	883.2	827.4
35°	543.7	556.6	575.2	593.8	640.4	680.5	749.0	808.6	856.1	862.4	828.2
37.5°	438.2	444.5	456.3	475.0	505.4	553.0	605.9	681.3	750.2	801.4	803.6
40°	383.0	384.9	398.1	412.3	437.0	476.2	523.9	590.6	673.0	744.6	774.4
42.5°	341.6	345.7	351.4	365.0	384.7	414.1	458.5	513.6	589.2	671.5	729.8
45°	293.5	298.2	301.7	310.8	324.8	344.6	375.5	425.9	483.4	568.4	646.9
47.5°	261.8	262.1	264.7	271.6	281.1	296.0	317.9	350.2	403.0	472.0	552.6
50°	239.0	242.7	243.7	249.0	256.5	267.4	285.6	313.1	356.4	417.0	491.1
52.5°	223.0	224.1	226.7	230.6	237.1	245.6	261.4	282.9	316.9	368.6	436.7
55°	199.4	199.4	202.0	205.0	208.7	216.4	226.9	242.7	268.6	308.7	365.1
57.5°	177.6	178.8	180.6	181.5	184.7	189.8	198.5	210.6	229.8	260.7	305.5
60°	163.1	165.2	164.9	166.8	169.6	173.6	181.0	190.8	208.0	232.7	270.5
62.5°	150.4	150.3	150.2	152.5	155.2	159.0	163.9	172.3	187.0	208.9	241.0
65°	129.5	129.1	130.7	132.1	133.0	135.8	139.5	147.0	156.8	173.1	198.0
67.5°	111.0	109.6	110.5	111.0	112.6	114.8	118.3	122.9	130.6	143.7	162.5
70°	98.3	97.1	96.9	97.4	98.8	100.4	103.0	107.4	114.6	125.1	138.8
72.5°	85.3	84.5	84.4	85.5	86.1	87.2	89.0	93.0	98.8	106.7	119.5
75°	66.6	66.6	66.6	66.9	67.6	68.5	69.9	72.0	76.4	82.0	90.6
77.5°	49.9	49.9	49.6	49.6	50.6	51.0	51.3	53.3	55.8	59.5	65.8
80°	39.1	38.0	38.4	39.1	39.6	39.8	40.5	41.0	43.1	45.2	49.6
82.5°	29.1	28.1	28.2	29.3	29.4	29.6	30.3	30.9	31.7	33.6	36.0
85°	15.4	15.4	15.6	15.6	15.8	15.6	16.3	16.5	16.5	17.7	19.1
87.5°	7.7	7.3	7.5	7.6	7.4	7.5	7.7	7.8	7.9	8.0	8.0
90°	10.6	10.4	10.3	10.1	10.0	9.7	9.4	9.1	8.8	8.5	7.5
92.5°	11.7	11.6	11.5	11.4	11.4	11.1	10.6	10.1	9.5	9.0	8.3
95°	13.4	13.4	13.4	13.4	13.4	13.2	12.6	12.1	11.5	11.0	10.1
97.5°	14.6	14.5	14.4	14.3	14.2	13.9	13.3	12.6	12.0	11.4	17.0
100°	14.8	14.8	14.7	14.6	14.5	14.2	13.5	12.9	12.3	11.7	23.9
102.5°	15.1	15.0	14.8	14.7	14.6	15.5	17.4	19.4	21.3	23.3	36.6
105°	15.5	15.4	15.2	15.1	14.9	21.8	35.7	49.6	63.5	77.4	84.5
107.5°	48.8	59.3	69.8	80.3	90.7	101.1	111.3	121.5	131.6	141.8	140.7
110°	97.2	108.4	119.6	130.9	142.1	149.0	151.6	154.2	156.8	159.4	158.5



TEST NUMBER: P331865

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	166.7	169.1	171.5	173.8	176.2	177.4	177.3	177.3	177.2	177.2	176.3
115°	207.8	207.5	207.2	206.8	206.5	206.0	205.2	204.4	203.6	202.8	202.1
117.5°	230.8	230.8	230.7	230.6	230.6	230.2	229.6	229.0	228.3	227.7	227.4
120°	246.7	246.7	246.7	246.7	246.7	246.3	245.7	245.1	244.5	243.8	243.6
122.5°	262.2	262.1	262.1	262.0	261.9	261.7	261.3	260.8	260.4	259.9	259.6
125°	284.1	284.0	283.8	283.6	283.5	283.3	283.2	283.0	282.9	282.7	282.4
127.5°	305.2	305.3	305.5	305.6	305.8	305.8	305.5	305.2	305.0	304.7	304.4
130°	318.7	318.9	319.1	319.2	319.4	319.3	319.0	318.7	318.3	318.0	317.7
132.5°	331.2	331.4	331.6	331.8	332.1	332.0	331.7	331.4	331.1	330.8	330.5
135°	350.2	350.4	350.7	350.9	351.1	351.1	350.9	350.7	350.4	350.2	349.9
137.5°	368.1	368.2	368.4	368.5	368.7	368.6	368.2	367.8	367.5	367.1	366.9
140°	378.8	379.0	379.1	379.3	379.4	379.4	379.0	378.7	378.4	378.1	377.9
142.5°	388.7	388.9	389.1	389.4	389.6	389.6	389.3	389.1	388.8	388.6	388.3
145°	403.9	403.9	403.9	403.9	403.9	403.8	403.7	403.5	403.4	403.2	403.0
147.5°	415.2	415.6	415.9	416.3	416.7	416.8	416.6	416.4	416.3	416.1	416.0
150°	423.7	423.9	424.2	424.4	424.6	424.7	424.5	424.4	424.2	424.0	423.9
152.5°	430.5	430.8	431.2	431.6	431.9	432.0	431.7	431.4	431.1	430.8	430.7
155°	439.9	440.4	440.9	441.4	441.8	441.9	441.5	441.1	440.7	440.3	440.2
157.5°	447.9	448.5	449.2	449.8	450.4	450.5	450.0	449.5	449.0	448.6	448.6
160°	453.0	453.6	454.1	454.7	455.2	455.3	454.8	454.3	453.8	453.4	453.5
162.5°	457.8	458.3	458.8	459.3	459.8	459.7	459.2	458.7	458.1	457.6	457.7
165°	463.6	464.2	464.7	465.3	465.8	465.8	465.2	464.5	463.9	463.3	463.3
167.5°	467.8	468.4	469.0	469.7	470.3	470.3	469.7	469.0	468.4	467.8	467.8
170°	470.3	471.0	471.6	472.2	472.8	472.8	472.2	471.6	471.0	470.3	470.3
172.5°	471.7	472.4	473.1	473.8	474.5	474.5	473.9	473.3	472.7	472.0	472.0
175°	473.9	474.5	475.1	475.8	476.4	476.4	475.9	475.3	474.8	474.2	474.1
177.5°	474.5	475.1	475.8	476.4	477.0	477.1	476.6	476.1	475.6	475.1	475.0
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6



TEST NUMBER: P331865

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	495.7	494.3	492.8	490.2	487.9	484.8	483.8	482.7	479.3	476.4	474.1
5°	526.0	520.4	512.3	504.8	498.8	490.6	486.0	481.1	474.1	467.8	462.7
7.5°	557.7	546.7	534.0	520.4	507.6	495.3	485.4	476.5	466.7	457.5	450.2
10°	582.9	567.0	549.3	530.2	513.9	498.1	484.8	473.2	460.6	449.6	440.5
12.5°	611.6	588.1	563.7	540.5	521.2	499.2	483.1	468.3	454.0	440.9	430.7
15°	645.5	615.7	586.8	554.9	525.6	498.1	479.0	460.3	443.8	430.3	417.2
17.5°	676.5	642.7	604.6	565.8	530.4	497.8	471.1	450.0	429.3	412.8	399.8
20°	694.0	655.6	612.5	572.2	533.0	496.7	467.3	442.2	419.8	402.3	387.7
22.5°	709.1	664.1	619.5	576.4	532.8	493.7	460.4	434.5	410.3	393.2	377.6
25°	724.8	670.9	626.2	575.7	527.0	486.4	449.2	419.8	395.6	375.5	359.5
27.5°	738.2	670.5	617.4	563.0	517.7	477.1	437.3	405.8	380.1	358.3	342.0
30°	747.1	671.4	608.3	554.5	508.8	466.9	428.2	396.5	369.5	347.4	332.0
32.5°	752.7	670.8	599.9	542.5	494.6	457.5	418.3	385.5	357.7	336.0	321.2
35°	756.0	666.7	585.4	517.9	471.8	435.6	402.8	368.8	339.7	319.4	302.6
37.5°	749.4	658.1	568.7	494.1	443.6	408.1	380.4	351.5	323.6	301.3	286.8
40°	739.2	652.5	555.6	477.3	424.2	390.0	366.5	338.0	310.5	289.3	275.8
42.5°	719.6	641.2	541.3	458.7	404.1	369.9	348.2	324.4	298.4	278.5	265.0
45°	671.9	616.4	519.7	430.8	374.4	339.0	319.9	302.6	279.1	259.8	248.1
47.5°	605.6	579.2	488.6	401.3	343.3	309.3	289.4	275.6	258.4	242.7	231.6
50°	559.6	548.6	467.6	381.1	322.7	289.3	270.2	257.7	245.3	229.7	219.5
52.5°	506.5	513.2	443.0	360.3	301.6	268.8	250.9	240.9	229.7	216.8	207.9
55°	431.7	456.1	400.5	325.2	270.2	239.0	222.0	213.2	206.6	197.1	189.4
57.5°	361.7	392.8	354.5	289.1	239.4	212.5	196.2	186.6	182.4	177.4	171.3
60°	320.1	350.8	321.7	264.9	218.8	193.1	178.7	170.5	166.3	162.8	157.7
62.5°	283.0	314.1	289.7	240.3	198.4	174.7	162.1	154.1	150.9	149.1	144.7
65°	232.0	258.8	242.5	202.0	169.4	148.4	137.0	131.4	128.4	127.7	124.9
67.5°	188.8	209.2	197.4	167.5	141.9	123.8	114.1	109.3	107.0	106.7	104.6
70°	160.5	179.6	170.5	143.5	121.4	107.2	98.8	94.6	93.2	93.0	91.8
72.5°	138.5	151.8	144.6	122.1	105.0	92.1	85.9	81.5	80.0	80.3	79.5
75°	102.5	112.5	108.3	92.7	79.0	70.6	65.5	62.7	61.3	62.0	61.0
77.5°	73.8	80.1	76.3	65.5	57.0	51.0	47.2	45.5	44.2	44.2	43.8
80°	55.7	59.4	57.3	50.8	43.8	38.7	35.6	34.5	33.8	33.5	33.3
82.5°	39.7	42.8	40.3	35.9	31.1	28.0	26.3	24.8	24.3	24.4	24.2
85°	20.0	21.2	20.3	17.5	15.6	14.2	13.3	12.6	12.1	12.3	11.9
87.5°	8.2	8.2	7.4	6.5	5.9	5.2	5.1	4.5	4.3	4.5	4.5
90°	6.4	5.4	4.4	3.5	2.7	1.9	1.1	0.4	1.1	1.9	2.7
92.5°	7.5	6.7	6.0	5.7	5.9	6.1	6.4	6.6	6.4	6.1	5.9
95°	9.2	8.4	7.5	8.7	11.9	15.1	18.3	21.6	18.3	15.1	11.9
97.5°	22.7	28.3	34.0	37.5	39.0	40.4	41.9	43.3	41.9	40.4	39.0
100°	36.2	48.4	60.7	66.0	64.4	62.9	61.3	59.7	61.3	62.9	64.4
102.5°	50.0	63.4	76.8	82.9	81.8	80.6	79.5	78.4	79.5	80.6	81.8
105°	91.5	98.6	105.7	108.8	107.9	107.0	106.2	105.3	106.2	107.0	107.9
107.5°	139.6	138.5	137.4	136.5	135.8	135.1	134.4	133.7	134.4	135.1	135.8
110°	157.6	156.8	155.9	155.2	154.5	153.9	153.3	152.7	153.3	153.9	154.5



TEST NUMBER: P331865

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	175.5	174.6	173.7	173.0	172.4	171.9	171.3	170.7	171.3	171.9	172.4
115°	201.4	200.7	200.0	199.4	198.9	198.5	198.0	197.5	198.0	198.5	198.9
117.5°	227.0	226.6	226.3	225.8	225.2	224.6	224.1	223.5	224.1	224.6	225.2
120°	243.4	243.1	242.9	242.4	241.7	241.0	240.3	239.6	240.3	241.0	241.7
122.5°	259.3	259.0	258.7	258.3	257.7	257.1	256.6	256.0	256.6	257.1	257.7
125°	282.1	281.8	281.4	281.0	280.3	279.7	279.1	278.5	279.1	279.7	280.3
127.5°	304.0	303.6	303.2	302.7	302.1	301.5	300.9	300.2	300.9	301.5	302.1
130°	317.4	317.1	316.8	316.3	315.7	315.0	314.4	313.8	314.4	315.0	315.7
132.5°	330.3	330.0	329.7	329.3	328.7	328.1	327.4	326.8	327.4	328.1	328.7
135°	349.6	349.2	348.9	348.5	348.1	347.6	347.1	346.7	347.1	347.6	348.1
137.5°	366.7	366.6	366.4	366.0	365.4	364.8	364.2	363.6	364.2	364.8	365.4
140°	377.6	377.4	377.2	376.8	376.3	375.9	375.4	374.9	375.4	375.9	376.3
142.5°	388.1	387.9	387.6	387.3	386.8	386.3	385.9	385.4	385.9	386.3	386.8
145°	402.9	402.7	402.6	402.2	401.7	401.1	400.6	400.0	400.6	401.1	401.7
147.5°	415.8	415.7	415.5	415.2	414.9	414.5	414.2	413.8	414.2	414.5	414.9
150°	423.7	423.6	423.4	423.2	423.0	422.7	422.5	422.3	422.5	422.7	423.0
152.5°	430.6	430.5	430.5	430.3	430.2	430.1	430.0	429.9	430.0	430.1	430.2
155°	440.1	440.1	440.0	440.0	440.2	440.3	440.5	440.7	440.5	440.3	440.2
157.5°	448.7	448.8	448.9	448.9	448.9	449.0	449.0	449.0	449.0	449.0	448.9
160°	453.5	453.6	453.7	453.8	453.8	453.9	454.0	454.1	454.0	453.9	453.8
162.5°	457.8	457.8	457.9	458.1	458.3	458.5	458.7	458.9	458.7	458.5	458.3
165°	463.4	463.5	463.6	463.7	464.0	464.2	464.4	464.7	464.4	464.2	464.0
167.5°	467.8	467.8	467.8	467.9	468.3	468.6	468.9	469.2	468.9	468.6	468.3
170°	470.3	470.3	470.3	470.5	470.8	471.1	471.4	471.7	471.4	471.1	470.8
172.5°	471.9	471.8	471.8	471.9	472.3	472.7	473.1	473.4	473.1	472.7	472.3
175°	474.1	474.0	473.9	474.1	474.5	474.8	475.2	475.6	475.2	474.8	474.5
177.5°	474.9	474.9	474.8	474.9	475.3	475.6	475.9	476.2	475.9	475.6	475.3
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6



TEST NUMBER: P331865

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	472.8	471.5	469.7	466.9	464.6	461.1	461.1	461.6	461.6	461.5	461.1
5°	458.5	455.0	450.8	445.9	440.8	435.6	434.7	432.8	431.5	430.5	429.4
7.5°	443.3	437.1	431.0	424.2	417.9	412.8	409.2	406.2	404.3	402.2	400.7
10°	433.1	425.4	418.2	411.0	403.0	396.7	392.8	390.0	387.9	386.0	385.1
12.5°	421.0	412.2	404.2	397.3	388.7	382.2	378.4	377.1	374.7	370.7	368.7
15°	403.3	395.1	385.6	375.1	370.9	363.0	358.5	356.4	355.0	352.0	351.1
17.5°	388.1	377.5	366.7	358.9	351.1	344.7	342.2	339.6	337.8	335.3	334.5
20°	376.0	366.5	356.7	348.3	340.1	333.1	331.0	329.2	327.3	326.2	325.2
22.5°	363.7	354.2	346.0	338.2	329.5	324.9	322.7	320.6	319.3	318.5	317.6
25°	346.4	338.0	328.9	322.0	315.0	311.9	310.5	309.4	308.4	307.3	307.0
27.5°	331.0	321.8	314.5	307.9	302.9	300.4	299.0	298.5	298.7	299.1	299.4
30°	319.4	311.0	305.0	299.4	294.7	292.4	292.1	292.1	293.1	293.3	293.8
32.5°	308.8	301.9	295.8	290.4	286.9	285.3	286.2	286.2	286.9	287.5	288.4
35°	293.3	287.2	282.6	277.9	274.9	275.6	276.1	276.5	277.7	279.1	280.0
37.5°	278.5	273.3	268.4	264.8	263.4	264.6	265.8	266.7	268.1	269.2	270.1
40°	267.9	263.9	259.3	256.0	256.5	257.2	258.1	259.3	260.5	261.2	262.1
42.5°	258.0	253.9	250.3	247.6	248.3	249.2	249.7	250.3	251.7	253.0	253.5
45°	243.0	239.7	236.5	234.8	235.3	235.8	236.2	236.9	238.1	239.0	239.3
47.5°	226.1	223.8	221.6	220.0	220.8	220.6	221.2	222.7	223.0	223.6	224.9
50°	215.3	213.2	210.6	210.1	210.1	210.1	210.4	212.2	212.2	213.2	214.1
52.5°	203.3	202.0	200.4	199.5	199.1	199.1	200.1	201.0	201.4	202.7	203.7
55°	185.7	184.3	182.9	182.2	181.7	182.2	184.0	184.5	185.7	186.4	187.1
57.5°	167.3	166.2	165.1	164.7	164.6	165.2	166.2	167.6	167.9	170.1	171.1
60°	155.2	153.5	152.6	152.6	152.1	154.2	153.8	156.1	156.6	158.0	159.6
62.5°	142.7	140.5	140.1	140.1	140.8	141.4	142.0	143.0	144.3	146.0	147.3
65°	122.5	121.4	123.0	122.8	122.3	123.7	123.7	124.9	126.3	127.9	130.5
67.5°	103.5	102.9	103.0	103.0	103.7	104.5	105.2	106.2	107.9	109.6	111.3
70°	90.6	91.3	90.2	91.1	91.8	92.0	92.5	93.9	95.7	96.9	98.8
72.5°	78.1	78.1	78.2	78.6	79.3	79.7	80.2	81.8	83.8	84.8	86.3
75°	60.1	59.9	60.6	60.6	61.7	62.2	62.7	63.4	65.2	66.6	67.8
77.5°	43.9	44.2	44.0	44.8	44.5	44.6	46.0	46.7	46.9	49.7	50.3
80°	33.1	33.5	33.8	34.0	34.2	33.8	35.4	36.1	36.1	37.7	38.9
82.5°	23.8	24.0	24.6	24.9	24.9	25.4	25.5	26.0	26.6	27.3	28.8
85°	11.9	12.6	12.8	12.6	12.8	12.3	13.0	13.3	13.5	13.5	13.5
87.5°	4.4	4.8	4.8	5.2	5.2	5.6	5.7	5.4	5.4	6.0	5.3
90°	3.5	4.4	5.4	6.4	7.5	8.5	8.8	9.1	9.4	9.7	10.0
92.5°	5.7	6.0	6.7	7.5	8.3	9.0	9.5	10.1	10.6	11.1	11.4
95°	8.7	7.5	8.4	9.2	10.1	11.0	11.5	12.1	12.6	13.2	13.4
97.5°	37.5	34.0	28.3	22.7	17.0	11.4	12.0	12.6	13.3	13.9	14.2
100°	66.0	60.7	48.4	36.2	23.9	11.7	12.3	12.9	13.5	14.2	14.5
102.5°	82.9	76.8	63.4	50.0	36.6	23.3	21.3	19.4	17.4	15.5	14.6
105°	108.8	105.7	98.6	91.5	84.5	77.4	63.5	49.6	35.7	21.8	14.9
107.5°	136.5	137.4	138.5	139.6	140.7	141.8	131.6	121.5	111.3	101.1	90.7
110°	155.2	155.9	156.8	157.6	158.5	159.4	156.8	154.2	151.6	149.0	142.1



TEST NUMBER: P331865

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	173.0	173.7	174.6	175.5	176.3	177.2	177.2	177.3	177.3	177.4	176.2
115°	199.4	200.0	200.7	201.4	202.1	202.8	203.6	204.4	205.2	206.0	206.5
117.5°	225.8	226.3	226.6	227.0	227.4	227.7	228.3	229.0	229.6	230.2	230.6
120°	242.4	242.9	243.1	243.4	243.6	243.8	244.5	245.1	245.7	246.3	246.7
122.5°	258.3	258.7	259.0	259.3	259.6	259.9	260.4	260.8	261.3	261.7	261.9
125°	281.0	281.4	281.8	282.1	282.4	282.7	282.9	283.0	283.2	283.3	283.5
127.5°	302.7	303.2	303.6	304.0	304.4	304.7	305.0	305.2	305.5	305.8	305.8
130°	316.3	316.8	317.1	317.4	317.7	318.0	318.3	318.7	319.0	319.3	319.4
132.5°	329.3	329.7	330.0	330.3	330.5	330.8	331.1	331.4	331.7	332.0	332.1
135°	348.5	348.9	349.2	349.6	349.9	350.2	350.4	350.7	350.9	351.1	351.1
137.5°	366.0	366.4	366.6	366.7	366.9	367.1	367.5	367.8	368.2	368.6	368.7
140°	376.8	377.2	377.4	377.6	377.9	378.1	378.4	378.7	379.0	379.4	379.4
142.5°	387.3	387.6	387.9	388.1	388.3	388.6	388.8	389.1	389.3	389.6	389.6
145°	402.2	402.6	402.7	402.9	403.0	403.2	403.4	403.5	403.7	403.8	403.9
147.5°	415.2	415.5	415.7	415.8	416.0	416.1	416.3	416.4	416.6	416.8	416.7
150°	423.2	423.4	423.6	423.7	423.9	424.0	424.2	424.4	424.5	424.7	424.6
152.5°	430.3	430.5	430.5	430.6	430.7	430.8	431.1	431.4	431.7	432.0	431.9
155°	440.0	440.0	440.1	440.1	440.2	440.3	440.7	441.1	441.5	441.9	441.8
157.5°	448.9	448.9	448.8	448.7	448.6	448.6	449.0	449.5	450.0	450.5	450.4
160°	453.8	453.7	453.6	453.5	453.5	453.4	453.8	454.3	454.8	455.3	455.2
162.5°	458.1	457.9	457.8	457.8	457.7	457.6	458.1	458.7	459.2	459.7	459.8
165°	463.7	463.6	463.5	463.4	463.3	463.3	463.9	464.5	465.2	465.8	465.8
167.5°	467.9	467.8	467.8	467.8	467.8	467.8	468.4	469.0	469.7	470.3	470.3
170°	470.5	470.3	470.3	470.3	470.3	470.3	471.0	471.6	472.2	472.8	472.8
172.5°	471.9	471.8	471.8	471.9	472.0	472.0	472.7	473.3	473.9	474.5	474.5
175°	474.1	473.9	474.0	474.1	474.1	474.2	474.8	475.3	475.9	476.4	476.4
177.5°	474.9	474.8	474.9	474.9	475.0	475.1	475.6	476.1	476.6	477.1	477.0
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6



TEST NUMBER: P331865

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	459.8	459.6	460.9	460.0	460.9	459.6	459.8	461.1	461.5	461.6	461.6
5°	428.0	428.7	426.3	426.3	426.3	428.7	428.0	429.4	430.5	431.5	432.8
7.5°	399.6	398.6	398.7	397.4	398.7	398.6	399.6	400.7	402.2	404.3	406.2
10°	382.3	380.9	380.4	380.7	380.4	380.9	382.3	385.1	386.0	387.9	390.0
12.5°	367.9	367.7	364.6	364.6	364.6	367.7	367.9	368.7	370.7	374.7	377.1
15°	351.1	346.7	346.2	347.6	346.2	346.7	351.1	351.1	352.0	355.0	356.4
17.5°	334.2	331.8	332.0	331.3	332.0	331.8	334.2	334.5	335.3	337.8	339.6
20°	325.2	323.8	323.6	322.0	323.6	323.8	325.2	325.2	326.2	327.3	329.2
22.5°	317.0	316.6	316.7	314.9	316.7	316.6	317.0	317.6	318.5	319.3	320.6
25°	306.8	308.0	307.0	307.0	307.0	308.0	306.8	307.0	307.3	308.4	309.4
27.5°	299.9	299.9	299.4	299.4	299.4	299.9	299.9	299.4	299.1	298.7	298.5
30°	294.7	294.5	294.9	294.9	294.9	294.5	294.7	293.8	293.3	293.1	292.1
32.5°	289.5	289.8	289.9	290.1	289.9	289.8	289.5	288.4	287.5	286.9	286.2
35°	281.4	281.7	282.4	281.9	282.4	281.7	281.4	280.0	279.1	277.7	276.5
37.5°	270.5	271.6	271.4	271.7	271.4	271.6	270.5	270.1	269.2	268.1	266.7
40°	262.3	263.0	262.8	262.8	262.8	263.0	262.3	262.1	261.2	260.5	259.3
42.5°	253.9	254.4	253.8	253.5	253.8	254.4	253.9	253.5	253.0	251.7	250.3
45°	240.2	239.7	240.4	239.5	240.4	239.7	240.2	239.3	239.0	238.1	236.9
47.5°	224.8	225.3	225.5	226.2	225.5	225.3	224.8	224.9	223.6	223.0	222.7
50°	214.6	216.0	216.0	215.7	216.0	216.0	214.6	214.1	213.2	212.2	212.2
52.5°	204.5	205.1	206.1	206.0	206.1	205.1	204.5	203.7	202.7	201.4	201.0
55°	188.9	189.4	189.9	190.1	189.9	189.4	188.9	187.1	186.4	185.7	184.5
57.5°	172.8	172.6	173.7	174.1	173.7	172.6	172.8	171.1	170.1	167.9	167.6
60°	161.4	161.4	163.3	164.0	163.3	161.4	161.4	159.6	158.0	156.6	156.1
62.5°	149.3	150.1	151.9	151.0	151.9	150.1	149.3	147.3	146.0	144.3	143.0
65°	131.6	133.5	133.3	134.2	133.3	133.5	131.6	130.5	127.9	126.3	124.9
67.5°	113.1	114.3	116.0	116.1	116.0	114.3	113.1	111.3	109.6	107.9	106.2
70°	100.6	101.8	102.7	103.4	102.7	101.8	100.6	98.8	96.9	95.7	93.9
72.5°	88.5	89.1	91.4	90.4	91.4	89.1	88.5	86.3	84.8	83.8	81.8
75°	69.4	71.1	72.5	71.8	72.5	71.1	69.4	67.8	66.6	65.2	63.4
77.5°	51.3	53.0	53.6	53.0	53.6	53.0	51.3	50.3	49.7	46.9	46.7
80°	40.5	40.3	41.7	41.5	41.7	40.3	40.5	38.9	37.7	36.1	36.1
82.5°	29.7	29.5	30.1	30.3	30.1	29.5	29.7	28.8	27.3	26.6	26.0
85°	14.4	15.1	14.2	14.0	14.2	15.1	14.4	13.5	13.5	13.5	13.3
87.5°	5.4	5.4	5.3	5.1	5.3	5.4	5.4	5.3	6.0	5.4	5.4
90°	10.1	10.3	10.4	10.6	10.4	10.3	10.1	10.0	9.7	9.4	9.1
92.5°	11.4	11.5	11.6	11.7	11.6	11.5	11.4	11.4	11.1	10.6	10.1
95°	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.2	12.6	12.1
97.5°	14.3	14.4	14.5	14.6	14.5	14.4	14.3	14.2	13.9	13.3	12.6
100°	14.6	14.7	14.8	14.8	14.8	14.7	14.6	14.5	14.2	13.5	12.9
102.5°	14.7	14.8	15.0	15.1	15.0	14.8	14.7	14.6	15.5	17.4	19.4
105°	15.1	15.2	15.4	15.5	15.4	15.2	15.1	14.9	21.8	35.7	49.6
107.5°	80.3	69.8	59.3	48.8	59.3	69.8	80.3	90.7	101.1	111.3	121.5
110°	130.9	119.6	108.4	97.2	108.4	119.6	130.9	142.1	149.0	151.6	154.2



TEST NUMBER: P331865

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	173.8	171.5	169.1	166.7	169.1	171.5	173.8	176.2	177.4	177.3	177.3
115°	206.8	207.2	207.5	207.8	207.5	207.2	206.8	206.5	206.0	205.2	204.4
117.5°	230.6	230.7	230.8	230.8	230.8	230.7	230.6	230.6	230.2	229.6	229.0
120°	246.7	246.7	246.7	246.7	246.7	246.7	246.7	246.7	246.3	245.7	245.1
122.5°	262.0	262.1	262.1	262.2	262.1	262.1	262.0	261.9	261.7	261.3	260.8
125°	283.6	283.8	284.0	284.1	284.0	283.8	283.6	283.5	283.3	283.2	283.0
127.5°	305.6	305.5	305.3	305.2	305.3	305.5	305.6	305.8	305.8	305.5	305.2
130°	319.2	319.1	318.9	318.7	318.9	319.1	319.2	319.4	319.3	319.0	318.7
132.5°	331.8	331.6	331.4	331.2	331.4	331.6	331.8	332.1	332.0	331.7	331.4
135°	350.9	350.7	350.4	350.2	350.4	350.7	350.9	351.1	351.1	350.9	350.7
137.5°	368.5	368.4	368.2	368.1	368.2	368.4	368.5	368.7	368.6	368.2	367.8
140°	379.3	379.1	379.0	378.8	379.0	379.1	379.3	379.4	379.4	379.0	378.7
142.5°	389.4	389.1	388.9	388.7	388.9	389.1	389.4	389.6	389.6	389.3	389.1
145°	403.9	403.9	403.9	403.9	403.9	403.9	403.9	403.9	403.8	403.7	403.5
147.5°	416.3	415.9	415.6	415.2	415.6	415.9	416.3	416.7	416.8	416.6	416.4
150°	424.4	424.2	423.9	423.7	423.9	424.2	424.4	424.6	424.7	424.5	424.4
152.5°	431.6	431.2	430.8	430.5	430.8	431.2	431.6	431.9	432.0	431.7	431.4
155°	441.4	440.9	440.4	439.9	440.4	440.9	441.4	441.8	441.9	441.5	441.1
157.5°	449.8	449.2	448.5	447.9	448.5	449.2	449.8	450.4	450.5	450.0	449.5
160°	454.7	454.1	453.6	453.0	453.6	454.1	454.7	455.2	455.3	454.8	454.3
162.5°	459.3	458.8	458.3	457.8	458.3	458.8	459.3	459.8	459.7	459.2	458.7
165°	465.3	464.7	464.2	463.6	464.2	464.7	465.3	465.8	465.8	465.2	464.5
167.5°	469.7	469.0	468.4	467.8	468.4	469.0	469.7	470.3	470.3	469.7	469.0
170°	472.2	471.6	471.0	470.3	471.0	471.6	472.2	472.8	472.8	472.2	471.6
172.5°	473.8	473.1	472.4	471.7	472.4	473.1	473.8	474.5	474.5	473.9	473.3
175°	475.8	475.1	474.5	473.9	474.5	475.1	475.8	476.4	476.4	475.9	475.3
177.5°	476.4	475.8	475.1	474.5	475.1	475.8	476.4	477.0	477.1	476.6	476.1
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6



TEST NUMBER: P331865

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	461.1	461.1	464.6	466.9	469.7	471.5	472.8	474.1	476.4	479.3	482.7
5°	434.7	435.6	440.8	445.9	450.8	455.0	458.5	462.7	467.8	474.1	481.1
7.5°	409.2	412.8	417.9	424.2	431.0	437.1	443.3	450.2	457.5	466.7	476.5
10°	392.8	396.7	403.0	411.0	418.2	425.4	433.1	440.5	449.6	460.6	473.2
12.5°	378.4	382.2	388.7	397.3	404.2	412.2	421.0	430.7	440.9	454.0	468.3
15°	358.5	363.0	370.9	375.1	385.6	395.1	403.3	417.2	430.3	443.8	460.3
17.5°	342.2	344.7	351.1	358.9	366.7	377.5	388.1	399.8	412.8	429.3	450.0
20°	331.0	333.1	340.1	348.3	356.7	366.5	376.0	387.7	402.3	419.8	442.2
22.5°	322.7	324.9	329.5	338.2	346.0	354.2	363.7	377.6	393.2	410.3	434.5
25°	310.5	311.9	315.0	322.0	328.9	338.0	346.4	359.5	375.5	395.6	419.8
27.5°	299.0	300.4	302.9	307.9	314.5	321.8	331.0	342.0	358.3	380.1	405.8
30°	292.1	292.4	294.7	299.4	305.0	311.0	319.4	332.0	347.4	369.5	396.5
32.5°	286.2	285.3	286.9	290.4	295.8	301.9	308.8	321.2	336.0	357.7	385.5
35°	276.1	275.6	274.9	277.9	282.6	287.2	293.3	302.6	319.4	339.7	368.8
37.5°	265.8	264.6	263.4	264.8	268.4	273.3	278.5	286.8	301.3	323.6	351.5
40°	258.1	257.2	256.5	256.0	259.3	263.9	267.9	275.8	289.3	310.5	338.0
42.5°	249.7	249.2	248.3	247.6	250.3	253.9	258.0	265.0	278.5	298.4	324.4
45°	236.2	235.8	235.3	234.8	236.5	239.7	243.0	248.1	259.8	279.1	302.6
47.5°	221.2	220.6	220.8	220.0	221.6	223.8	226.1	231.6	242.7	258.4	275.6
50°	210.4	210.1	210.1	210.1	210.6	213.2	215.3	219.5	229.7	245.3	257.7
52.5°	200.1	199.1	199.1	199.5	200.4	202.0	203.3	207.9	216.8	229.7	240.9
55°	184.0	182.2	181.7	182.2	182.9	184.3	185.7	189.4	197.1	206.6	213.2
57.5°	166.2	165.2	164.6	164.7	165.1	166.2	167.3	171.3	177.4	182.4	186.6
60°	153.8	154.2	152.1	152.6	152.6	153.5	155.2	157.7	162.8	166.3	170.5
62.5°	142.0	141.4	140.8	140.1	140.1	140.5	142.7	144.7	149.1	150.9	154.1
65°	123.7	123.7	122.3	122.8	123.0	121.4	122.5	124.9	127.7	128.4	131.4
67.5°	105.2	104.5	103.7	103.0	103.0	102.9	103.5	104.6	106.7	107.0	109.3
70°	92.5	92.0	91.8	91.1	90.2	91.3	90.6	91.8	93.0	93.2	94.6
72.5°	80.2	79.7	79.3	78.6	78.2	78.1	78.1	79.5	80.3	80.0	81.5
75°	62.7	62.2	61.7	60.6	60.6	59.9	60.1	61.0	62.0	61.3	62.7
77.5°	46.0	44.6	44.5	44.8	44.0	44.2	43.9	43.8	44.2	44.2	45.5
80°	35.4	33.8	34.2	34.0	33.8	33.5	33.1	33.3	33.5	33.8	34.5
82.5°	25.5	25.4	24.9	24.9	24.6	24.0	23.8	24.2	24.4	24.3	24.8
85°	13.0	12.3	12.8	12.6	12.8	12.6	11.9	11.9	12.3	12.1	12.6
87.5°	5.7	5.6	5.2	5.2	4.8	4.8	4.4	4.5	4.5	4.3	4.5
90°	8.8	8.5	7.5	6.4	5.4	4.4	3.5	2.7	1.9	1.1	0.4
92.5°	9.5	9.0	8.3	7.5	6.7	6.0	5.7	5.9	6.1	6.4	6.6
95°	11.5	11.0	10.1	9.2	8.4	7.5	8.7	11.9	15.1	18.3	21.6
97.5°	12.0	11.4	17.0	22.7	28.3	34.0	37.5	39.0	40.4	41.9	43.3
100°	12.3	11.7	23.9	36.2	48.4	60.7	66.0	64.4	62.9	61.3	59.7
102.5°	21.3	23.3	36.6	50.0	63.4	76.8	82.9	81.8	80.6	79.5	78.4
105°	63.5	77.4	84.5	91.5	98.6	105.7	108.8	107.9	107.0	106.2	105.3
107.5°	131.6	141.8	140.7	139.6	138.5	137.4	136.5	135.8	135.1	134.4	133.7
110°	156.8	159.4	158.5	157.6	156.8	155.9	155.2	154.5	153.9	153.3	152.7



TEST NUMBER: P331865

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	177.2	177.2	176.3	175.5	174.6	173.7	173.0	172.4	171.9	171.3	170.7
115°	203.6	202.8	202.1	201.4	200.7	200.0	199.4	198.9	198.5	198.0	197.5
117.5°	228.3	227.7	227.4	227.0	226.6	226.3	225.8	225.2	224.6	224.1	223.5
120°	244.5	243.8	243.6	243.4	243.1	242.9	242.4	241.7	241.0	240.3	239.6
122.5°	260.4	259.9	259.6	259.3	259.0	258.7	258.3	257.7	257.1	256.6	256.0
125°	282.9	282.7	282.4	282.1	281.8	281.4	281.0	280.3	279.7	279.1	278.5
127.5°	305.0	304.7	304.4	304.0	303.6	303.2	302.7	302.1	301.5	300.9	300.2
130°	318.3	318.0	317.7	317.4	317.1	316.8	316.3	315.7	315.0	314.4	313.8
132.5°	331.1	330.8	330.5	330.3	330.0	329.7	329.3	328.7	328.1	327.4	326.8
135°	350.4	350.2	349.9	349.6	349.2	348.9	348.5	348.1	347.6	347.1	346.7
137.5°	367.5	367.1	366.9	366.7	366.6	366.4	366.0	365.4	364.8	364.2	363.6
140°	378.4	378.1	377.9	377.6	377.4	377.2	376.8	376.3	375.9	375.4	374.9
142.5°	388.8	388.6	388.3	388.1	387.9	387.6	387.3	386.8	386.3	385.9	385.4
145°	403.4	403.2	403.0	402.9	402.7	402.6	402.2	401.7	401.1	400.6	400.0
147.5°	416.3	416.1	416.0	415.8	415.7	415.5	415.2	414.9	414.5	414.2	413.8
150°	424.2	424.0	423.9	423.7	423.6	423.4	423.2	423.0	422.7	422.5	422.3
152.5°	431.1	430.8	430.7	430.6	430.5	430.5	430.3	430.2	430.1	430.0	429.9
155°	440.7	440.3	440.2	440.1	440.1	440.0	440.0	440.2	440.3	440.5	440.7
157.5°	449.0	448.6	448.6	448.7	448.8	448.9	448.9	448.9	449.0	449.0	449.0
160°	453.8	453.4	453.5	453.5	453.6	453.7	453.8	453.8	453.9	454.0	454.1
162.5°	458.1	457.6	457.7	457.8	457.8	457.9	458.1	458.3	458.5	458.7	458.9
165°	463.9	463.3	463.3	463.4	463.5	463.6	463.7	464.0	464.2	464.4	464.7
167.5°	468.4	467.8	467.8	467.8	467.8	467.8	467.9	468.3	468.6	468.9	469.2
170°	471.0	470.3	470.3	470.3	470.3	470.3	470.5	470.8	471.1	471.4	471.7
172.5°	472.7	472.0	472.0	471.9	471.8	471.8	471.9	472.3	472.7	473.1	473.4
175°	474.8	474.2	474.1	474.1	474.0	473.9	474.1	474.5	474.8	475.2	475.6
177.5°	475.6	475.1	475.0	474.9	474.9	474.8	474.9	475.3	475.6	475.9	476.2
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6



TEST NUMBER: P331865

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	483.8	484.8	487.9	490.2	492.8	494.3	495.7	496.9	498.4	498.7	504.1
5°	486.0	490.6	498.8	504.8	512.3	520.4	526.0	528.6	535.4	540.9	552.1
7.5°	485.4	495.3	507.6	520.4	534.0	546.7	557.7	570.8	580.0	594.0	607.7
10°	484.8	498.1	513.9	530.2	549.3	567.0	582.9	600.6	615.3	634.6	651.1
12.5°	483.1	499.2	521.2	540.5	563.7	588.1	611.6	634.3	647.3	679.5	694.7
15°	479.0	498.1	525.6	554.9	586.8	615.7	645.5	669.3	707.7	735.9	753.9
17.5°	471.1	497.8	530.4	565.8	604.6	642.7	676.5	712.5	753.3	787.4	823.8
20°	467.3	496.7	533.0	572.2	612.5	655.6	694.0	737.3	781.8	815.4	862.0
22.5°	460.4	493.7	532.8	576.4	619.5	664.1	709.1	752.8	804.2	850.4	894.8
25°	449.2	486.4	527.0	575.7	626.2	670.9	724.8	782.8	836.3	895.8	940.0
27.5°	437.3	477.1	517.7	563.0	617.4	670.5	738.2	803.7	869.2	920.5	953.3
30°	428.2	466.9	508.8	554.5	608.3	671.4	747.1	818.6	882.5	926.5	944.9
32.5°	418.3	457.5	494.6	542.5	599.9	670.8	752.7	827.4	883.2	912.5	908.9
35°	402.8	435.6	471.8	517.9	585.4	666.7	756.0	828.2	862.4	856.1	808.6
37.5°	380.4	408.1	443.6	494.1	568.7	658.1	749.4	803.6	801.4	750.2	681.3
40°	366.5	390.0	424.2	477.3	555.6	652.5	739.2	774.4	744.6	673.0	590.6
42.5°	348.2	369.9	404.1	458.7	541.3	641.2	719.6	729.8	671.5	589.2	513.6
45°	319.9	339.0	374.4	430.8	519.7	616.4	671.9	646.9	568.4	483.4	425.9
47.5°	289.4	309.3	343.3	401.3	488.6	579.2	605.6	552.6	472.0	403.0	350.2
50°	270.2	289.3	322.7	381.1	467.6	548.6	559.6	491.1	417.0	356.4	313.1
52.5°	250.9	268.8	301.6	360.3	443.0	513.2	506.5	436.7	368.6	316.9	282.9
55°	222.0	239.0	270.2	325.2	400.5	456.1	431.7	365.1	308.7	268.6	242.7
57.5°	196.2	212.5	239.4	289.1	354.5	392.8	361.7	305.5	260.7	229.8	210.6
60°	178.7	193.1	218.8	264.9	321.7	350.8	320.1	270.5	232.7	208.0	190.8
62.5°	162.1	174.7	198.4	240.3	289.7	314.1	283.0	241.0	208.9	187.0	172.3
65°	137.0	148.4	169.4	202.0	242.5	258.8	232.0	198.0	173.1	156.8	147.0
67.5°	114.1	123.8	141.9	167.5	197.4	209.2	188.8	162.5	143.7	130.6	122.9
70°	98.8	107.2	121.4	143.5	170.5	179.6	160.5	138.8	125.1	114.6	107.4
72.5°	85.9	92.1	105.0	122.1	144.6	151.8	138.5	119.5	106.7	98.8	93.0
75°	65.5	70.6	79.0	92.7	108.3	112.5	102.5	90.6	82.0	76.4	72.0
77.5°	47.2	51.0	57.0	65.5	76.3	80.1	73.8	65.8	59.5	55.8	53.3
80°	35.6	38.7	43.8	50.8	57.3	59.4	55.7	49.6	45.2	43.1	41.0
82.5°	26.3	28.0	31.1	35.9	40.3	42.8	39.7	36.0	33.6	31.7	30.9
85°	13.3	14.2	15.6	17.5	20.3	21.2	20.0	19.1	17.7	16.5	16.5
87.5°	5.1	5.2	5.9	6.5	7.4	8.2	8.2	8.0	8.0	7.9	7.8
90°	1.1	1.9	2.7	3.5	4.4	5.4	6.4	7.5	8.5	8.8	9.1
92.5°	6.4	6.1	5.9	5.7	6.0	6.7	7.5	8.3	9.0	9.5	10.1
95°	18.3	15.1	11.9	8.7	7.5	8.4	9.2	10.1	11.0	11.5	12.1
97.5°	41.9	40.4	39.0	37.5	34.0	28.3	22.7	17.0	11.4	12.0	12.6
100°	61.3	62.9	64.4	66.0	60.7	48.4	36.2	23.9	11.7	12.3	12.9
102.5°	79.5	80.6	81.8	82.9	76.8	63.4	50.0	36.6	23.3	21.3	19.4
105°	106.2	107.0	107.9	108.8	105.7	98.6	91.5	84.5	77.4	63.5	49.6
107.5°	134.4	135.1	135.8	136.5	137.4	138.5	139.6	140.7	141.8	131.6	121.5
110°	153.3	153.9	154.5	155.2	155.9	156.8	157.6	158.5	159.4	156.8	154.2



TEST NUMBER: P331865

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	171.3	171.9	172.4	173.0	173.7	174.6	175.5	176.3	177.2	177.2	177.3
115°	198.0	198.5	198.9	199.4	200.0	200.7	201.4	202.1	202.8	203.6	204.4
117.5°	224.1	224.6	225.2	225.8	226.3	226.6	227.0	227.4	227.7	228.3	229.0
120°	240.3	241.0	241.7	242.4	242.9	243.1	243.4	243.6	243.8	244.5	245.1
122.5°	256.6	257.1	257.7	258.3	258.7	259.0	259.3	259.6	259.9	260.4	260.8
125°	279.1	279.7	280.3	281.0	281.4	281.8	282.1	282.4	282.7	282.9	283.0
127.5°	300.9	301.5	302.1	302.7	303.2	303.6	304.0	304.4	304.7	305.0	305.2
130°	314.4	315.0	315.7	316.3	316.8	317.1	317.4	317.7	318.0	318.3	318.7
132.5°	327.4	328.1	328.7	329.3	329.7	330.0	330.3	330.5	330.8	331.1	331.4
135°	347.1	347.6	348.1	348.5	348.9	349.2	349.6	349.9	350.2	350.4	350.7
137.5°	364.2	364.8	365.4	366.0	366.4	366.6	366.7	366.9	367.1	367.5	367.8
140°	375.4	375.9	376.3	376.8	377.2	377.4	377.6	377.9	378.1	378.4	378.7
142.5°	385.9	386.3	386.8	387.3	387.6	387.9	388.1	388.3	388.6	388.8	389.1
145°	400.6	401.1	401.7	402.2	402.6	402.7	402.9	403.0	403.2	403.4	403.5
147.5°	414.2	414.5	414.9	415.2	415.5	415.7	415.8	416.0	416.1	416.3	416.4
150°	422.5	422.7	423.0	423.2	423.4	423.6	423.7	423.9	424.0	424.2	424.4
152.5°	430.0	430.1	430.2	430.3	430.5	430.5	430.6	430.7	430.8	431.1	431.4
155°	440.5	440.3	440.2	440.0	440.0	440.1	440.1	440.2	440.3	440.7	441.1
157.5°	449.0	449.0	448.9	448.9	448.9	448.8	448.7	448.6	448.6	449.0	449.5
160°	454.0	453.9	453.8	453.8	453.7	453.6	453.5	453.5	453.4	453.8	454.3
162.5°	458.7	458.5	458.3	458.1	457.9	457.8	457.8	457.7	457.6	458.1	458.7
165°	464.4	464.2	464.0	463.7	463.6	463.5	463.4	463.3	463.3	463.9	464.5
167.5°	468.9	468.6	468.3	467.9	467.8	467.8	467.8	467.8	467.8	468.4	469.0
170°	471.4	471.1	470.8	470.5	470.3	470.3	470.3	470.3	470.3	471.0	471.6
172.5°	473.1	472.7	472.3	471.9	471.8	471.8	471.9	472.0	472.0	472.7	473.3
175°	475.2	474.8	474.5	474.1	473.9	474.0	474.1	474.1	474.2	474.8	475.3
177.5°	475.9	475.6	475.3	474.9	474.8	474.9	474.9	475.0	475.1	475.6	476.1
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6



TEST NUMBER: P331865

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	506.0	506.2	508.2	509.7	509.0	509.9	510.3
5°	552.8	561.2	565.6	568.9	569.1	569.4	571.2
7.5°	619.2	628.2	634.8	644.8	647.7	651.1	650.2
10°	667.7	681.0	692.4	698.4	705.0	714.5	706.8
12.5°	713.0	736.5	753.9	763.3	769.4	771.3	767.6
15°	787.7	818.4	834.9	834.5	855.4	864.5	850.3
17.5°	856.1	884.5	907.3	918.9	936.4	940.2	938.5
20°	898.1	929.1	946.8	966.8	975.9	984.0	985.4
22.5°	934.2	962.1	981.1	997.7	1005.3	1009.2	1011.5
25°	971.5	993.4	1004.8	1010.6	1012.7	1012.2	1009.2
27.5°	968.9	970.6	958.0	945.7	934.6	922.2	917.9
30°	943.7	924.2	889.2	869.4	840.3	817.2	826.6
32.5°	877.6	838.6	799.4	756.1	720.3	710.1	699.8
35°	749.0	680.5	640.4	593.8	575.2	556.6	543.7
37.5°	605.9	553.0	505.4	475.0	456.3	444.5	438.2
40°	523.9	476.2	437.0	412.3	398.1	384.9	383.0
42.5°	458.5	414.1	384.7	365.0	351.4	345.7	341.6
45°	375.5	344.6	324.8	310.8	301.7	298.2	293.5
47.5°	317.9	296.0	281.1	271.6	264.7	262.1	261.8
50°	285.6	267.4	256.5	249.0	243.7	242.7	239.0
52.5°	261.4	245.6	237.1	230.6	226.7	224.1	223.0
55°	226.9	216.4	208.7	205.0	202.0	199.4	199.4
57.5°	198.5	189.8	184.7	181.5	180.6	178.8	177.6
60°	181.0	173.6	169.6	166.8	164.9	165.2	163.1
62.5°	163.9	159.0	155.2	152.5	150.2	150.3	150.4
65°	139.5	135.8	133.0	132.1	130.7	129.1	129.5
67.5°	118.3	114.8	112.6	111.0	110.5	109.6	111.0
70°	103.0	100.4	98.8	97.4	96.9	97.1	98.3
72.5°	89.0	87.2	86.1	85.5	84.4	84.5	85.3
75°	69.9	68.5	67.6	66.9	66.6	66.6	66.6
77.5°	51.3	51.0	50.6	49.6	49.6	49.9	49.9
80°	40.5	39.8	39.6	39.1	38.4	38.0	39.1
82.5°	30.3	29.6	29.4	29.3	28.2	28.1	29.1
85°	16.3	15.6	15.8	15.6	15.6	15.4	15.4
87.5°	7.7	7.5	7.4	7.6	7.5	7.3	7.7
90°	9.4	9.7	10.0	10.1	10.3	10.4	10.6
92.5°	10.6	11.1	11.4	11.4	11.5	11.6	11.7
95°	12.6	13.2	13.4	13.4	13.4	13.4	13.4
97.5°	13.3	13.9	14.2	14.3	14.4	14.5	14.6
100°	13.5	14.2	14.5	14.6	14.7	14.8	14.8
102.5°	17.4	15.5	14.6	14.7	14.8	15.0	15.1
105°	35.7	21.8	14.9	15.1	15.2	15.4	15.5
107.5°	111.3	101.1	90.7	80.3	69.8	59.3	48.8
110°	151.6	149.0	142.1	130.9	119.6	108.4	97.2



TEST NUMBER: P331865

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	177.3	177.4	176.2	173.8	171.5	169.1	166.7
115°	205.2	206.0	206.5	206.8	207.2	207.5	207.8
117.5°	229.6	230.2	230.6	230.6	230.7	230.8	230.8
120°	245.7	246.3	246.7	246.7	246.7	246.7	246.7
122.5°	261.3	261.7	261.9	262.0	262.1	262.1	262.2
125°	283.2	283.3	283.5	283.6	283.8	284.0	284.1
127.5°	305.5	305.8	305.8	305.6	305.5	305.3	305.2
130°	319.0	319.3	319.4	319.2	319.1	318.9	318.7
132.5°	331.7	332.0	332.1	331.8	331.6	331.4	331.2
135°	350.9	351.1	351.1	350.9	350.7	350.4	350.2
137.5°	368.2	368.6	368.7	368.5	368.4	368.2	368.1
140°	379.0	379.4	379.4	379.3	379.1	379.0	378.8
142.5°	389.3	389.6	389.6	389.4	389.1	388.9	388.7
145°	403.7	403.8	403.9	403.9	403.9	403.9	403.9
147.5°	416.6	416.8	416.7	416.3	415.9	415.6	415.2
150°	424.5	424.7	424.6	424.4	424.2	423.9	423.7
152.5°	431.7	432.0	431.9	431.6	431.2	430.8	430.5
155°	441.5	441.9	441.8	441.4	440.9	440.4	439.9
157.5°	450.0	450.5	450.4	449.8	449.2	448.5	447.9
160°	454.8	455.3	455.2	454.7	454.1	453.6	453.0
162.5°	459.2	459.7	459.8	459.3	458.8	458.3	457.8
165°	465.2	465.8	465.8	465.3	464.7	464.2	463.6
167.5°	469.7	470.3	470.3	469.7	469.0	468.4	467.8
170°	472.2	472.8	472.8	472.2	471.6	471.0	470.3
172.5°	473.9	474.5	474.5	473.8	473.1	472.4	471.7
175°	475.9	476.4	476.4	475.8	475.1	474.5	473.9
177.5°	476.6	477.1	477.0	476.4	475.8	475.1	474.5
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6

(END OF REPORT)