

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331872

Luminaire Tested: **S123DIP-S340D365U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331872
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D365U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2657.8 lumens
Efficiency: N/A
Efficacy: 130.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331872

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331872

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53				
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50	45				
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	37				
3	82	72	65	59	75	67	61	55	58	53	48	49	45	42	40	38	36	32				
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	31	27				
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27	23				
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	30	26	23	21				
7	58	46	38	32	54	43	36	31	37	32	27	32	27	24	27	24	21	18				
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19	16				
9	51	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17	15				
10	47	35	28	23	44	33	26	22	29	23	20	25	21	17	21	18	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5833	5833	5833
5°	5861	5780	5820
10°	5821	5729	5766
15°	5753	5665	5675
20°	5674	5573	5577
25°	5567	5462	5451
30°	5450	5340	5299
35°	5327	5210	5143
40°	5199	5067	4990
45°	5057	4937	4816
50°	4915	4776	4642
55°	4731	4609	4468
60°	4545	4413	4273
65°	4378	4200	4070
70°	4135	3959	3783
75°	3780	3643	3489
80°	3409	3267	3236
85°	2989	2878	2766



TEST NUMBER: P331872

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.0	1.9
10°-20°	144.1	5.4
20°-30°	212.9	8.0
30°-40°	248.7	9.4
40°-50°	250.0	9.4
50°-60°	219.6	8.3
60°-70°	163.6	6.2
70°-80°	93.2	3.5
80°-90°	28.1	1.1
90°-100°	29.3	1.1
100°-110°	87.7	3.3
110°-120°	149.2	5.6
120°-130°	196.2	7.4
130°-140°	220.6	8.3
140°-150°	216.8	8.2
150°-160°	182.5	6.9
160°-170°	121.5	4.6
170°-180°	42.5	1.6
0°-30°	408.1	15.4
0°-40°	656.8	24.7
0°-60°	1126.5	42.4
0°-90°	1411.4	53.1
90°-120°	266.2	10.0
90°-150°	899.9	33.9
90°-180°	1246.0	46.9
0°-180°	2657.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	542	542	542	542	542	
5°	542	540	535	539	539	51
15°	516	514	508	512	509	145
25°	469	466	460	460	459	216
35°	405	402	396	394	391	254
45°	332	330	324	319	316	256
55°	252	251	246	241	238	226
65°	172	170	165	161	160	170
75°	91	89	88	85	84	97
85°	24	23	23	22	22	27
90°	0	4	8	10	11	3
95°	21	23	26	28	28	23
105°	80	80	83	83	84	85
115°	150	151	150	151	150	149
125°	220	221	220	219	217	196
135°	285	287	287	286	285	220
145°	346	347	348	347	346	216
155°	396	396	396	398	395	182
165°	432	430	430	432	430	122
175°	449	448	447	449	447	43
180°	450	450	450	450	450	



TEST NUMBER: P331872

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9
2.5°	543.8	543.4	543.1	542.8	542.4	541.8	540.9	540.0	539.1	538.2	539.0
5°	542.4	541.8	541.3	540.8	540.3	539.5	538.3	537.2	536.0	534.9	535.9
7.5°	537.1	536.5	536.0	535.5	535.0	534.1	533.0	531.8	530.6	529.4	530.3
10°	532.6	532.1	531.5	531.0	530.5	529.6	528.2	526.9	525.5	524.2	525.1
12.5°	526.6	526.2	525.7	525.3	524.9	524.0	522.8	521.5	520.2	519.0	519.7
15°	516.3	515.9	515.4	515.0	514.6	513.7	512.4	511.0	509.7	508.4	509.2
17.5°	504.2	503.7	503.2	502.6	502.1	501.2	499.8	498.5	497.1	495.8	496.3
20°	495.3	494.7	494.1	493.4	492.8	491.8	490.5	489.1	487.8	486.5	486.9
22.5°	485.2	484.6	484.0	483.4	482.8	481.8	480.4	479.1	477.7	476.4	476.7
25°	468.7	468.1	467.5	466.9	466.3	465.3	463.9	462.6	461.2	459.9	460.0
27.5°	451.1	450.5	449.9	449.3	448.7	447.7	446.3	444.8	443.4	441.9	442.0
30°	438.5	437.9	437.4	436.9	436.4	435.4	434.0	432.5	431.1	429.6	429.6
32.5°	425.8	425.1	424.4	423.7	423.1	422.1	421.0	419.9	418.8	417.7	417.1
35°	405.4	404.8	404.1	403.5	402.9	401.9	400.6	399.2	397.9	396.5	395.9
37.5°	384.5	383.7	382.9	382.1	381.4	380.3	378.9	377.5	376.2	374.8	374.1
40°	370.0	369.3	368.7	368.1	367.5	366.4	365.0	363.5	362.1	360.6	359.8
42.5°	355.4	354.7	354.0	353.3	352.6	351.5	350.1	348.6	347.2	345.7	344.9
45°	332.2	331.8	331.4	331.0	330.6	329.7	328.3	327.0	325.6	324.3	323.1
47.5°	309.2	308.6	308.0	307.4	306.8	305.9	304.6	303.3	302.1	300.8	299.6
50°	293.5	293.0	292.5	292.0	291.5	290.5	289.2	287.9	286.5	285.2	284.0
52.5°	277.1	276.8	276.4	276.1	275.7	274.8	273.4	272.0	270.6	269.1	268.2
55°	252.1	252.0	251.9	251.8	251.7	250.9	249.6	248.2	246.9	245.6	244.4
57.5°	228.2	227.9	227.5	227.2	226.8	226.1	225.0	223.9	222.9	221.8	220.8
60°	211.1	211.0	210.9	210.8	210.7	210.0	208.7	207.5	206.3	205.0	204.1
62.5°	195.8	195.5	195.3	195.0	194.7	194.0	192.7	191.5	190.2	189.0	188.1
65°	171.9	171.4	170.9	170.4	169.9	169.1	168.1	167.0	166.0	164.9	164.1
67.5°	146.7	146.2	145.8	145.3	144.9	144.2	143.5	142.7	141.9	141.1	140.4
70°	131.4	130.8	130.2	129.5	128.9	128.3	127.7	127.0	126.4	125.8	125.1
72.5°	115.4	114.9	114.5	114.0	113.5	113.0	112.3	111.6	110.9	110.2	109.5
75°	90.9	90.4	90.0	89.6	89.2	88.8	88.5	88.2	87.9	87.6	87.1
77.5°	69.1	68.9	68.7	68.5	68.2	67.9	67.6	67.2	66.8	66.4	66.1
80°	55.0	54.7	54.4	54.1	53.7	53.5	53.3	53.1	52.9	52.7	52.5
82.5°	41.2	41.1	41.1	41.0	40.9	40.9	40.8	40.8	40.8	40.7	40.5
85°	24.2	24.0	23.8	23.6	23.4	23.3	23.3	23.3	23.3	23.3	23.1
87.5°	9.8	9.7	9.6	9.5	9.4	9.4	9.5	9.7	9.8	9.9	9.9
90°	0.4	1.1	1.9	2.7	3.5	4.4	5.4	6.4	7.5	8.5	8.8
92.5°	8.6	9.1	9.6	10.2	10.7	11.2	11.8	12.4	13.0	13.6	13.8
95°	20.9	21.4	21.9	22.5	23.0	23.6	24.3	24.9	25.5	26.2	26.5
97.5°	37.0	37.4	37.9	38.3	38.7	39.1	39.6	40.0	40.5	40.9	41.3
100°	48.1	48.5	49.0	49.5	49.9	50.4	50.8	51.2	51.6	51.9	52.2
102.5°	60.8	61.1	61.3	61.6	61.9	62.3	62.8	63.4	63.9	64.4	64.6
105°	79.5	79.7	79.8	80.0	80.1	80.6	81.3	82.0	82.7	83.4	83.4
107.5°	101.3	101.4	101.5	101.6	101.7	101.8	102.1	102.4	102.7	103.0	103.2
110°	114.9	115.0	115.2	115.3	115.5	115.6	115.8	116.0	116.1	116.3	116.6



TEST NUMBER: P331872

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	129.0	129.1	129.2	129.3	129.4	129.4	129.5	129.5	129.5	129.6	129.9
115°	150.2	150.4	150.7	150.9	151.1	151.2	151.0	150.9	150.7	150.5	150.6
117.5°	171.5	171.7	171.9	172.0	172.2	172.1	171.9	171.7	171.5	171.3	171.3
120°	184.8	185.3	185.8	186.2	186.7	186.7	186.4	186.0	185.6	185.2	185.1
122.5°	198.7	199.0	199.4	199.7	200.1	200.1	199.9	199.7	199.5	199.3	199.1
125°	219.8	220.0	220.3	220.5	220.8	220.8	220.6	220.5	220.3	220.2	219.8
127.5°	239.3	239.8	240.3	240.8	241.3	241.5	241.3	241.1	241.0	240.8	240.4
130°	252.3	252.9	253.6	254.2	254.8	255.0	254.8	254.6	254.3	254.1	253.8
132.5°	265.3	266.0	266.6	267.2	267.8	268.1	267.9	267.7	267.5	267.4	267.0
135°	285.2	285.7	286.1	286.6	287.1	287.3	287.2	287.1	287.0	287.0	286.6
137.5°	303.6	304.0	304.3	304.7	305.1	305.4	305.6	305.8	306.0	306.2	305.9
140°	316.3	316.7	317.1	317.5	317.9	318.1	318.2	318.2	318.3	318.4	318.3
142.5°	327.9	328.3	328.7	329.1	329.4	329.7	329.9	330.0	330.1	330.3	330.2
145°	346.0	346.1	346.3	346.4	346.6	346.8	347.0	347.3	347.5	347.7	347.7
147.5°	361.8	362.1	362.4	362.7	362.9	363.2	363.4	363.6	363.8	364.1	364.1
150°	372.8	373.0	373.1	373.3	373.5	373.6	373.8	373.9	374.1	374.2	374.2
152.5°	381.9	382.1	382.3	382.5	382.8	382.9	383.0	383.1	383.2	383.3	383.4
155°	396.2	396.2	396.2	396.2	396.2	396.2	396.3	396.3	396.4	396.5	396.8
157.5°	408.3	408.2	408.1	408.0	407.9	407.9	408.0	408.0	408.1	408.2	408.5
160°	415.9	415.8	415.6	415.5	415.3	415.2	415.2	415.2	415.2	415.2	415.6
162.5°	422.7	422.5	422.3	422.1	421.8	421.8	421.8	421.9	422.0	422.0	422.4
165°	431.5	431.3	431.0	430.8	430.5	430.4	430.4	430.4	430.4	430.4	430.9
167.5°	438.5	438.2	437.9	437.5	437.2	437.1	437.2	437.2	437.3	437.4	437.8
170°	442.4	442.1	441.8	441.5	441.2	441.0	441.0	441.0	441.0	441.0	441.6
172.5°	445.6	445.2	444.9	444.6	444.3	444.1	444.1	444.1	444.1	444.1	444.6
175°	448.8	448.5	448.2	447.9	447.6	447.4	447.4	447.4	447.4	447.4	447.9
177.5°	450.1	449.9	449.6	449.4	449.1	449.0	449.0	449.0	449.0	449.0	449.4
180°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9



TEST NUMBER: P331872

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9
2.5°	539.8	540.7	541.5	541.9	541.8	541.7	541.6	541.5
5°	537.0	538.0	539.1	539.5	539.3	539.1	538.8	538.6
7.5°	531.3	532.2	533.1	533.5	533.4	533.3	533.2	533.0
10°	526.1	527.0	527.9	528.3	528.1	527.9	527.7	527.5
12.5°	520.3	521.0	521.7	522.0	521.9	521.7	521.6	521.5
15°	510.0	510.8	511.7	511.8	511.1	510.5	509.9	509.3
17.5°	496.9	497.5	498.1	498.3	498.0	497.8	497.6	497.4
20°	487.3	487.7	488.1	488.2	487.8	487.5	487.2	486.9
22.5°	477.0	477.4	477.7	477.7	477.3	476.9	476.5	476.1
25°	460.1	460.2	460.3	460.2	459.9	459.6	459.3	459.0
27.5°	442.1	442.2	442.2	442.1	441.7	441.3	440.9	440.5
30°	429.6	429.6	429.6	429.2	428.5	427.8	427.1	426.3
32.5°	416.5	415.9	415.4	414.9	414.5	414.1	413.7	413.3
35°	395.3	394.7	394.0	393.5	393.0	392.4	391.9	391.4
37.5°	373.3	372.6	371.8	371.3	371.0	370.6	370.3	370.0
40°	359.0	358.2	357.3	356.7	356.3	355.9	355.5	355.1
42.5°	344.1	343.2	342.4	341.8	341.4	341.0	340.6	340.1
45°	321.8	320.6	319.3	318.5	317.9	317.4	316.9	316.4
47.5°	298.4	297.2	295.9	295.1	294.6	294.2	293.7	293.3
50°	282.9	281.7	280.6	279.7	279.1	278.5	277.9	277.2
52.5°	267.2	266.2	265.2	264.4	263.8	263.2	262.6	262.0
55°	243.3	242.1	241.0	240.2	239.7	239.1	238.6	238.1
57.5°	219.8	218.7	217.7	216.9	216.3	215.7	215.1	214.5
60°	203.2	202.2	201.3	200.6	200.0	199.5	199.0	198.5
62.5°	187.1	186.2	185.3	184.6	184.3	183.9	183.6	183.2
65°	163.3	162.5	161.6	161.1	160.8	160.4	160.1	159.8
67.5°	139.6	138.9	138.2	137.6	137.2	136.7	136.3	135.9
70°	124.4	123.6	122.9	122.3	121.8	121.3	120.7	120.2
72.5°	108.9	108.2	107.6	107.1	106.9	106.6	106.3	106.0
75°	86.6	86.0	85.5	85.1	84.8	84.5	84.2	83.9
77.5°	65.7	65.4	65.0	64.9	64.9	64.9	64.9	64.9
80°	52.4	52.3	52.2	52.2	52.2	52.2	52.2	52.2
82.5°	40.4	40.2	40.0	39.8	39.8	39.7	39.6	39.5
85°	22.9	22.7	22.5	22.4	22.4	22.4	22.4	22.4
87.5°	9.9	9.8	9.8	9.8	9.9	9.9	9.9	9.9
90°	9.1	9.4	9.7	10.0	10.1	10.3	10.4	10.6
92.5°	14.1	14.3	14.6	14.7	14.6	14.5	14.4	14.3
95°	26.8	27.1	27.4	27.6	27.6	27.6	27.6	27.6
97.5°	41.6	42.0	42.4	42.5	42.5	42.5	42.4	42.4
100°	52.4	52.7	52.9	53.1	53.2	53.4	53.6	53.7
102.5°	64.9	65.1	65.3	65.4	65.4	65.4	65.3	65.3
105°	83.4	83.4	83.4	83.5	83.6	83.8	84.0	84.1
107.5°	103.5	103.7	104.0	104.1	104.0	103.9	103.8	103.7
110°	116.9	117.2	117.5	117.6	117.4	117.3	117.1	117.0



TEST NUMBER: P331872

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	130.3	130.7	131.1	131.2	131.2	131.2	131.1	131.1
115°	150.7	150.8	150.9	150.9	150.8	150.7	150.6	150.5
117.5°	171.3	171.3	171.3	171.1	170.9	170.7	170.5	170.3
120°	185.0	184.9	184.9	184.7	184.6	184.4	184.3	184.1
122.5°	198.9	198.7	198.5	198.3	198.1	197.8	197.6	197.4
125°	219.5	219.2	218.9	218.6	218.3	218.0	217.6	217.3
127.5°	239.9	239.5	239.0	238.6	238.3	237.9	237.6	237.2
130°	253.5	253.1	252.8	252.4	251.9	251.3	250.8	250.2
132.5°	266.6	266.2	265.9	265.5	265.0	264.6	264.2	263.8
135°	286.3	286.0	285.7	285.5	285.3	285.1	285.0	284.8
137.5°	305.6	305.3	304.9	304.6	304.3	304.0	303.7	303.4
140°	318.2	318.2	318.1	317.8	317.2	316.7	316.1	315.6
142.5°	330.1	330.0	330.0	329.7	329.3	328.9	328.4	328.0
145°	347.6	347.5	347.4	347.2	346.9	346.6	346.3	346.0
147.5°	364.1	364.1	364.1	363.8	363.4	362.9	362.4	361.9
150°	374.2	374.2	374.2	374.0	373.5	373.1	372.6	372.1
152.5°	383.5	383.7	383.8	383.6	383.2	382.8	382.4	382.0
155°	397.1	397.4	397.8	397.6	397.1	396.5	396.0	395.4
157.5°	408.8	409.2	409.5	409.4	409.0	408.6	408.1	407.7
160°	416.0	416.4	416.8	416.8	416.5	416.2	415.9	415.6
162.5°	422.8	423.2	423.6	423.5	423.0	422.5	422.0	421.5
165°	431.4	431.8	432.3	432.3	431.7	431.2	430.6	430.1
167.5°	438.3	438.8	439.3	439.3	438.8	438.3	437.8	437.4
170°	442.1	442.7	443.2	443.2	442.7	442.1	441.6	441.0
172.5°	445.1	445.6	446.1	446.1	445.5	445.0	444.4	443.9
175°	448.3	448.8	449.3	449.2	448.7	448.1	447.6	447.0
177.5°	449.8	450.1	450.5	450.5	450.1	449.6	449.2	448.7
180°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9

(END OF REPORT)