

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331873

Luminaire Tested: **S123DIP-S340D365U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331873  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S340D365U835-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2724.8 lumens  
Efficiency: N/A  
Efficacy: 134.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331873

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331873

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	98	94	90	86	91	87	83	80	74	71	69	62	60	59	51	50	49	43
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	45	43	41	36
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	40	37	35	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26
5	68	57	48	42	63	53	45	40	45	40	35	38	34	31	32	29	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	25	47	36	29	24	31	25	22	27	22	19	22	19	17	14
10	47	35	28	23	44	33	26	22	29	23	19	25	20	17	21	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5833	5833	5833
5°	5861	5780	5820
10°	5821	5729	5766
15°	5753	5665	5675
20°	5674	5573	5577
25°	5567	5462	5451
30°	5450	5340	5299
35°	5327	5210	5143
40°	5199	5067	4990
45°	5057	4937	4816
50°	4915	4776	4642
55°	4731	4609	4468
60°	4545	4413	4273
65°	4378	4200	4070
70°	4135	3959	3783
75°	3780	3643	3489
80°	3409	3267	3236
85°	2989	2878	2766



TEST NUMBER: P331873

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.0	1.9
10°-20°	144.1	5.3
20°-30°	212.9	7.8
30°-40°	248.7	9.1
40°-50°	250.0	9.2
50°-60°	219.6	8.1
60°-70°	163.6	6.0
70°-80°	93.2	3.4
80°-90°	28.1	1.0
90°-100°	97.2	3.6
100°-110°	275.1	10.1
110°-120°	270.6	9.9
120°-130°	215.9	7.9
130°-140°	170.2	6.2
140°-150°	127.0	4.7
150°-160°	88.5	3.2
160°-170°	52.0	1.9
170°-180°	16.9	0.6
0°-30°	408.1	15.0
0°-40°	656.8	24.1
0°-60°	1126.5	41.3
0°-90°	1411.4	51.8
90°-120°	642.9	23.6
90°-150°	1155.9	42.4
90°-180°	1313.0	48.2
0°-180°	2724.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	542	542	542	542	542	
5°	542	540	535	539	539	51
15°	516	514	508	512	509	145
25°	469	466	460	460	459	216
35°	405	402	396	394	391	254
45°	332	330	324	319	316	256
55°	252	251	246	241	238	226
65°	172	170	165	161	160	170
75°	91	89	88	85	84	97
85°	24	23	23	22	22	27
90°	1	4	9	10	10	2
95°	12	39	210	61	41	13
105°	41	61	284	497	450	44
115°	72	90	217	477	547	72
125°	101	119	203	368	431	89
135°	118	141	200	303	350	91
145°	135	154	198	248	273	84
155°	153	165	191	217	226	70
165°	167	172	183	194	198	47
175°	174	174	176	178	178	17
180°	175	175	175	175	175	



TEST NUMBER: P331873

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9
2.5°	543.8	543.4	543.1	542.8	542.4	541.8	540.9	540.0	539.1	538.2	539.0
5°	542.4	541.8	541.3	540.8	540.3	539.5	538.3	537.2	536.0	534.9	535.9
7.5°	537.1	536.5	536.0	535.5	535.0	534.1	533.0	531.8	530.6	529.4	530.3
10°	532.6	532.1	531.5	531.0	530.5	529.6	528.2	526.9	525.5	524.2	525.1
12.5°	526.6	526.2	525.7	525.3	524.9	524.0	522.8	521.5	520.2	519.0	519.7
15°	516.3	515.9	515.4	515.0	514.6	513.7	512.4	511.0	509.7	508.4	509.2
17.5°	504.2	503.7	503.2	502.6	502.1	501.2	499.8	498.5	497.1	495.8	496.3
20°	495.3	494.7	494.1	493.4	492.8	491.8	490.5	489.1	487.8	486.5	486.9
22.5°	485.2	484.6	484.0	483.4	482.8	481.8	480.4	479.1	477.7	476.4	476.7
25°	468.7	468.1	467.5	466.9	466.3	465.3	463.9	462.6	461.2	459.9	460.0
27.5°	451.1	450.5	449.9	449.3	448.7	447.7	446.3	444.8	443.4	441.9	442.0
30°	438.5	437.9	437.4	436.9	436.4	435.4	434.0	432.5	431.1	429.6	429.6
32.5°	425.8	425.1	424.4	423.7	423.1	422.1	421.0	419.9	418.8	417.7	417.1
35°	405.4	404.8	404.1	403.5	402.9	401.9	400.6	399.2	397.9	396.5	395.9
37.5°	384.5	383.7	382.9	382.1	381.4	380.3	378.9	377.5	376.2	374.8	374.1
40°	370.0	369.3	368.7	368.1	367.5	366.4	365.0	363.5	362.1	360.6	359.8
42.5°	355.4	354.7	354.0	353.3	352.6	351.5	350.1	348.6	347.2	345.7	344.9
45°	332.2	331.8	331.4	331.0	330.6	329.7	328.3	327.0	325.6	324.3	323.1
47.5°	309.2	308.6	308.0	307.4	306.8	305.9	304.6	303.3	302.1	300.8	299.6
50°	293.5	293.0	292.5	292.0	291.5	290.5	289.2	287.9	286.5	285.2	284.0
52.5°	277.1	276.8	276.4	276.1	275.7	274.8	273.4	272.0	270.6	269.1	268.2
55°	252.1	252.0	251.9	251.8	251.7	250.9	249.6	248.2	246.9	245.6	244.4
57.5°	228.2	227.9	227.5	227.2	226.8	226.1	225.0	223.9	222.9	221.8	220.8
60°	211.1	211.0	210.9	210.8	210.7	210.0	208.7	207.5	206.3	205.0	204.1
62.5°	195.8	195.5	195.3	195.0	194.7	194.0	192.7	191.5	190.2	189.0	188.1
65°	171.9	171.4	170.9	170.4	169.9	169.1	168.1	167.0	166.0	164.9	164.1
67.5°	146.7	146.2	145.8	145.3	144.9	144.2	143.5	142.7	141.9	141.1	140.4
70°	131.4	130.8	130.2	129.5	128.9	128.3	127.7	127.0	126.4	125.8	125.1
72.5°	115.4	114.9	114.5	114.0	113.5	113.0	112.3	111.6	110.9	110.2	109.5
75°	90.9	90.4	90.0	89.6	89.2	88.8	88.5	88.2	87.9	87.6	87.1
77.5°	69.1	68.9	68.7	68.5	68.2	67.9	67.6	67.2	66.8	66.4	66.1
80°	55.0	54.7	54.4	54.1	53.7	53.5	53.3	53.1	52.9	52.7	52.5
82.5°	41.2	41.1	41.1	41.0	40.9	40.9	40.8	40.8	40.8	40.7	40.5
85°	24.2	24.0	23.8	23.6	23.4	23.3	23.3	23.3	23.3	23.3	23.1
87.5°	9.8	9.7	9.6	9.6	9.5	9.5	9.6	9.7	9.8	10.0	9.8
90°	0.7	1.4	2.1	3.2	3.9	4.6	5.7	6.7	7.8	8.8	8.5
92.5°	4.4	6.5	9.5	12.2	15.2	20.4	29.7	44.9	59.8	54.3	41.0
95°	12.0	13.1	17.0	23.0	32.2	45.9	76.0	128.6	186.6	209.6	170.0
97.5°	20.5	20.8	23.9	29.1	38.2	53.1	81.8	141.1	237.8	324.8	347.4
100°	26.2	26.5	29.0	33.9	42.4	56.2	80.9	133.2	226.2	334.7	404.3
102.5°	32.1	32.7	34.9	39.6	47.2	59.9	82.1	126.4	209.2	316.3	407.1
105°	41.0	42.1	44.2	48.4	55.1	66.1	85.2	121.6	188.4	284.1	385.5
107.5°	50.5	51.5	53.6	57.7	64.0	74.2	91.0	121.2	175.1	255.7	347.8
110°	57.2	58.3	60.1	64.0	70.0	79.9	95.8	122.6	170.0	239.6	324.1



TEST NUMBER: P331873

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	63.5	64.5	66.3	70.2	76.2	85.8	100.6	125.5	167.1	228.8	303.4
115°	72.4	73.9	76.0	79.5	85.5	95.1	108.5	130.0	166.1	217.3	278.5
117.5°	81.4	83.0	84.8	88.1	94.8	103.6	116.9	136.1	166.7	210.5	263.4
120°	87.6	88.7	90.5	94.0	100.7	109.5	122.3	140.6	167.9	207.4	255.5
122.5°	93.0	94.1	95.8	99.7	106.1	115.5	127.9	144.9	169.8	205.5	249.0
125°	100.7	101.4	103.5	107.4	114.1	123.7	136.1	151.6	172.8	202.8	240.7
127.5°	106.6	107.6	110.3	114.2	121.6	131.2	143.1	157.1	176.2	201.6	233.3
130°	110.3	111.3	114.5	118.7	126.2	135.7	147.4	160.8	178.5	200.7	229.3
132.5°	113.1	114.4	117.9	123.0	130.4	139.7	151.0	164.2	180.2	200.4	225.7
135°	118.0	119.4	123.3	128.6	136.1	145.6	156.5	168.6	182.7	200.0	220.9
137.5°	122.7	124.2	128.0	133.6	141.0	149.8	160.4	171.8	184.4	199.2	216.7
140°	125.8	127.6	131.1	136.8	143.8	152.7	162.9	173.5	185.5	199.0	214.1
142.5°	129.2	130.7	134.5	139.6	146.7	154.9	164.9	175.2	186.4	198.4	211.9
145°	134.6	135.7	138.9	144.2	150.2	158.3	167.5	177.0	186.9	197.5	208.8
147.5°	140.2	140.8	143.9	148.5	154.3	161.2	169.6	178.2	186.9	196.2	205.9
150°	143.8	144.2	147.0	151.6	156.5	162.9	171.0	178.5	186.9	195.1	203.9
152.5°	147.5	147.6	150.4	154.4	158.8	164.9	171.9	179.0	186.1	193.7	201.6
155°	153.0	153.0	155.1	158.7	162.6	167.5	173.5	179.2	185.2	191.2	198.2
157.5°	157.4	157.7	159.4	162.5	165.8	169.6	174.4	179.5	184.0	189.0	194.4
160°	160.8	160.8	162.2	165.0	167.5	171.0	175.3	179.5	183.4	187.3	191.9
162.5°	163.3	163.3	164.5	166.7	168.9	171.9	175.6	179.2	182.3	185.6	189.3
165°	167.1	166.8	167.5	169.3	170.7	173.2	176.0	178.5	180.6	183.1	185.9
167.5°	170.0	169.6	170.0	171.3	172.3	173.9	175.9	177.9	178.9	180.5	182.6
170°	171.7	171.0	171.4	172.4	173.2	173.9	175.6	177.0	177.8	178.8	180.6
172.5°	172.9	172.4	172.5	173.3	173.7	174.1	175.6	176.8	176.9	177.4	178.6
175°	174.2	173.9	173.5	174.2	174.2	174.6	175.3	176.0	175.6	175.6	176.3
177.5°	174.9	174.6	174.3	174.6	174.6	174.6	174.9	175.4	174.9	174.6	174.9
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6



TEST NUMBER: P331873

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9
2.5°	539.8	540.7	541.5	541.9	541.8	541.7	541.6	541.5
5°	537.0	538.0	539.1	539.5	539.3	539.1	538.8	538.6
7.5°	531.3	532.2	533.1	533.5	533.4	533.3	533.2	533.0
10°	526.1	527.0	527.9	528.3	528.1	527.9	527.7	527.5
12.5°	520.3	521.0	521.7	522.0	521.9	521.7	521.6	521.5
15°	510.0	510.8	511.7	511.8	511.1	510.5	509.9	509.3
17.5°	496.9	497.5	498.1	498.3	498.0	497.8	497.6	497.4
20°	487.3	487.7	488.1	488.2	487.8	487.5	487.2	486.9
22.5°	477.0	477.4	477.7	477.7	477.3	476.9	476.5	476.1
25°	460.1	460.2	460.3	460.2	459.9	459.6	459.3	459.0
27.5°	442.1	442.2	442.2	442.1	441.7	441.3	440.9	440.5
30°	429.6	429.6	429.6	429.2	428.5	427.8	427.1	426.3
32.5°	416.5	415.9	415.4	414.9	414.5	414.1	413.7	413.3
35°	395.3	394.7	394.0	393.5	393.0	392.4	391.9	391.4
37.5°	373.3	372.6	371.8	371.3	371.0	370.6	370.3	370.0
40°	359.0	358.2	357.3	356.7	356.3	355.9	355.5	355.1
42.5°	344.1	343.2	342.4	341.8	341.4	341.0	340.6	340.1
45°	321.8	320.6	319.3	318.5	317.9	317.4	316.9	316.4
47.5°	298.4	297.2	295.9	295.1	294.6	294.2	293.7	293.3
50°	282.9	281.7	280.6	279.7	279.1	278.5	277.9	277.2
52.5°	267.2	266.2	265.2	264.4	263.8	263.2	262.6	262.0
55°	243.3	242.1	241.0	240.2	239.7	239.1	238.6	238.1
57.5°	219.8	218.7	217.7	216.9	216.3	215.7	215.1	214.5
60°	203.2	202.2	201.3	200.6	200.0	199.5	199.0	198.5
62.5°	187.1	186.2	185.3	184.6	184.3	183.9	183.6	183.2
65°	163.3	162.5	161.6	161.1	160.8	160.4	160.1	159.8
67.5°	139.6	138.9	138.2	137.6	137.2	136.7	136.3	135.9
70°	124.4	123.6	122.9	122.3	121.8	121.3	120.7	120.2
72.5°	108.9	108.2	107.6	107.1	106.9	106.6	106.3	106.0
75°	86.6	86.0	85.5	85.1	84.8	84.5	84.2	83.9
77.5°	65.7	65.4	65.0	64.9	64.9	64.9	64.9	64.9
80°	52.4	52.3	52.2	52.2	52.2	52.2	52.2	52.2
82.5°	40.4	40.2	40.0	39.8	39.8	39.7	39.6	39.5
85°	22.9	22.7	22.5	22.4	22.4	22.4	22.4	22.4
87.5°	9.8	9.8	9.8	9.9	9.8	9.9	9.9	9.9
90°	8.8	9.2	9.5	10.2	9.9	10.2	10.6	10.2
92.5°	29.8	23.6	20.8	19.0	18.4	17.3	17.7	17.0
95°	127.2	86.2	67.5	54.8	48.1	44.9	42.4	41.0
97.5°	317.1	254.0	208.4	166.2	140.1	124.2	114.6	111.6
100°	416.6	388.0	346.7	296.5	260.8	235.0	221.2	221.6
102.5°	449.7	448.8	424.7	392.9	365.1	344.7	333.2	325.0
105°	459.4	494.7	501.4	492.3	476.0	462.6	451.3	449.5
107.5°	431.5	488.9	519.9	532.5	532.8	528.2	524.4	521.2
110°	405.0	470.0	514.5	539.3	549.2	552.0	551.3	550.6





TEST NUMBER: P331873

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	378.7	445.1	495.0	526.8	544.9	553.7	556.4	556.5
115°	343.8	405.3	457.3	495.8	522.3	537.8	544.9	546.7
117.5°	318.6	371.7	418.3	457.4	485.1	502.9	513.0	515.4
120°	305.3	353.0	395.4	431.1	459.0	478.8	487.3	489.4
122.5°	294.9	338.0	377.3	410.5	435.3	453.1	462.4	465.1
125°	280.9	319.5	353.4	381.7	404.3	419.8	428.7	431.1
127.5°	268.8	303.1	333.7	359.5	379.6	392.9	400.9	403.1
130°	261.1	293.0	321.6	345.6	364.3	377.1	384.5	387.3
132.5°	254.1	283.3	310.0	332.9	350.5	363.2	369.8	371.8
135°	244.5	269.6	292.6	312.7	330.1	340.7	347.0	349.5
137.5°	235.8	256.4	276.2	293.7	308.2	319.0	324.3	326.0
140°	230.8	248.8	265.7	280.9	294.4	304.3	309.9	309.6
142.5°	226.0	241.4	256.1	269.3	280.8	289.6	294.6	294.3
145°	220.2	231.8	243.1	253.4	262.2	269.6	272.5	273.2
147.5°	215.4	224.7	233.8	241.1	247.8	252.8	255.5	255.8
150°	212.0	220.2	227.6	234.3	239.6	243.5	245.6	245.6
152.5°	208.9	215.9	222.5	228.1	232.2	235.8	237.1	237.1
155°	204.3	209.9	215.2	219.4	222.6	225.5	226.2	226.5
157.5°	199.3	204.0	208.1	211.5	214.2	216.3	216.9	216.8
160°	196.5	200.4	203.9	206.4	208.8	211.0	211.0	210.6
162.5°	193.1	196.4	199.7	201.9	203.5	205.3	205.3	205.0
165°	188.7	190.8	193.3	195.1	196.5	197.9	197.5	197.5
167.5°	184.9	186.5	187.9	189.2	189.8	190.8	190.5	190.5
170°	182.3	183.4	184.8	185.5	185.9	186.6	186.2	186.2
172.5°	180.1	180.9	182.0	182.4	182.5	183.2	182.6	182.3
175°	177.0	177.4	178.1	178.1	178.1	178.5	178.1	177.8
177.5°	175.1	175.4	175.7	175.7	175.4	175.7	175.1	175.1
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6

(END OF REPORT)