

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331874

Luminaire Tested: **S123DIP-S340D585U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331874
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D585U835-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3794.5 lumens
Efficiency: N/A
Efficacy: 148.2 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331874

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331874

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	87	84	86	83	80	77	68	65	63	53	52	51	40	40	39	33
2	87	80	74	69	79	73	68	63	59	56	53	47	45	43	36	34	33	28
3	79	70	63	58	72	64	58	53	53	48	45	42	39	36	32	30	28	24
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	29	26	24	20
5	67	55	48	42	60	51	44	39	42	37	33	34	30	27	26	23	21	18
6	61	50	42	36	56	46	39	34	38	32	29	30	27	24	23	21	19	16
7	57	45	37	32	51	41	34	29	34	29	25	28	24	21	21	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	20	17	15	12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5175	5175	5175	5175
5°	6172	5198	4606	5198
10°	7725	5172	4161	5172
15°	9475	5129	3874	5129
20°	11287	5065	3688	5065
25°	11986	4986	3646	4986
30°	10274	4928	3665	4928
35°	7144	4846	3704	4846
40°	5382	4749	3693	4749
45°	4468	4606	3646	4606
50°	4002	4315	3612	4315
55°	3742	4001	3567	4001
60°	3511	3670	3531	3670
65°	3298	3347	3418	3347
70°	3094	2977	3254	2977
75°	2770	2608	2986	2608
80°	2424	2139	2572	2139
85°	1902	1556	1729	1556



TEST NUMBER: P331874

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.4	1.2
10°-20°	151.9	4.0
20°-30°	254.9	6.7
30°-40°	288.6	7.6
40°-50°	258.8	6.8
50°-60°	208.9	5.5
60°-70°	145.6	3.8
70°-80°	76.5	2.0
80°-90°	20.9	0.5
90°-100°	27.9	0.7
100°-110°	133.0	3.5
110°-120°	319.5	8.4
120°-130°	406.9	10.7
130°-140°	434.7	11.5
140°-150°	406.5	10.7
150°-160°	327.9	8.6
160°-170°	211.6	5.6
170°-180°	72.9	1.9
0°-30°	454.2	12.0
0°-40°	742.8	19.6
0°-60°	1210.5	31.9
0°-90°	1453.4	38.3
90°-120°	480.5	12.7
90°-150°	1728.6	45.6
90°-180°	2341.0	61.7
0°-180°	3794.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	481	481	481	481	481	
5°	571	481	426	481	571	59
15°	850	460	348	460	850	246
25°	1009	420	307	420	1009	443
35°	544	369	282	369	544	353
45°	294	303	240	303	294	232
55°	199	213	190	213	199	179
65°	130	131	134	131	130	129
75°	67	63	72	63	67	71
85°	15	13	14	13	15	19
90°	17	1	17	1	17	9
95°	22	35	22	35	22	18
105°	25	170	25	170	25	57
115°	335	319	335	319	335	310
125°	459	449	459	449	459	410
135°	565	560	565	560	565	436
145°	652	646	652	646	652	407
155°	710	711	710	711	710	327
165°	748	750	748	750	748	211
175°	765	768	765	768	765	73
180°	768	768	768	768	768	



TEST NUMBER: P331874

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	510.3	509.9	509.0	509.7	508.2	506.2	506.0	504.1	498.7	498.4	496.9
5°	571.2	569.4	569.1	568.9	565.6	561.2	552.8	552.1	540.9	535.4	528.6
7.5°	650.2	651.1	647.7	644.8	634.8	628.2	619.2	607.7	594.0	580.0	570.8
10°	706.8	714.5	705.0	698.4	692.4	681.0	667.7	651.1	634.6	615.3	600.6
12.5°	767.6	771.3	769.4	763.3	753.9	736.5	713.0	694.7	679.5	647.3	634.3
15°	850.3	864.5	855.4	834.5	834.9	818.4	787.7	753.9	735.9	707.7	669.3
17.5°	938.5	940.2	936.4	918.9	907.3	884.5	856.1	823.8	787.4	753.3	712.5
20°	985.4	984.0	975.9	966.8	946.8	929.1	898.1	862.0	815.4	781.8	737.3
22.5°	1011.5	1009.2	1005.3	997.7	981.1	962.1	934.2	894.8	850.4	804.2	752.8
25°	1009.2	1012.2	1012.7	1010.6	1004.8	993.4	971.5	940.0	895.8	836.3	782.8
27.5°	917.9	922.2	934.6	945.7	958.0	970.6	968.9	953.3	920.5	869.2	803.7
30°	826.6	817.2	840.3	869.4	889.2	924.2	943.7	944.9	926.5	882.5	818.6
32.5°	699.8	710.1	720.3	756.1	799.4	838.6	877.6	908.9	912.5	883.2	827.4
35°	543.7	556.6	575.2	593.8	640.4	680.5	749.0	808.6	856.1	862.4	828.2
37.5°	438.2	444.5	456.3	475.0	505.4	553.0	605.9	681.3	750.2	801.4	803.6
40°	383.0	384.9	398.1	412.3	437.0	476.2	523.9	590.6	673.0	744.6	774.4
42.5°	341.6	345.7	351.4	365.0	384.7	414.1	458.5	513.6	589.2	671.5	729.8
45°	293.5	298.2	301.7	310.8	324.8	344.6	375.5	425.9	483.4	568.4	646.9
47.5°	261.8	262.1	264.7	271.6	281.1	296.0	317.9	350.2	403.0	472.0	552.6
50°	239.0	242.7	243.7	249.0	256.5	267.4	285.6	313.1	356.4	417.0	491.1
52.5°	223.0	224.1	226.7	230.6	237.1	245.6	261.4	282.9	316.9	368.6	436.7
55°	199.4	199.4	202.0	205.0	208.7	216.4	226.9	242.7	268.6	308.7	365.1
57.5°	177.6	178.8	180.6	181.5	184.7	189.8	198.5	210.6	229.8	260.7	305.5
60°	163.1	165.2	164.9	166.8	169.6	173.6	181.0	190.8	208.0	232.7	270.5
62.5°	150.4	150.3	150.2	152.5	155.2	159.0	163.9	172.3	187.0	208.9	241.0
65°	129.5	129.1	130.7	132.1	133.0	135.8	139.5	147.0	156.8	173.1	198.0
67.5°	111.0	109.6	110.5	111.0	112.6	114.8	118.3	122.9	130.6	143.7	162.5
70°	98.3	97.1	96.9	97.4	98.8	100.4	103.0	107.4	114.6	125.1	138.8
72.5°	85.3	84.5	84.4	85.5	86.1	87.2	89.0	93.0	98.8	106.7	119.5
75°	66.6	66.6	66.6	66.9	67.6	68.5	69.9	72.0	76.4	82.0	90.6
77.5°	49.9	49.9	49.6	49.6	50.6	51.0	51.3	53.3	55.8	59.5	65.8
80°	39.1	38.0	38.4	39.1	39.6	39.8	40.5	41.0	43.1	45.2	49.6
82.5°	29.1	28.1	28.2	29.3	29.4	29.6	30.3	30.9	31.7	33.6	36.0
85°	15.4	15.4	15.6	15.6	15.8	15.6	16.3	16.5	16.5	17.7	19.1
87.5°	9.0	8.6	8.7	8.9	8.6	8.7	8.8	8.9	9.0	9.1	8.9
90°	17.1	16.9	16.6	16.4	16.1	15.7	15.2	14.7	14.2	13.7	12.0
92.5°	18.9	18.8	18.6	18.5	18.3	17.8	17.0	16.2	15.4	14.6	13.4
95°	21.7	21.7	21.7	21.7	21.7	21.2	20.3	19.5	18.6	17.7	16.3
97.5°	23.5	23.4	23.2	23.1	23.0	22.4	21.4	20.4	19.4	18.4	17.5
100°	24.0	23.8	23.7	23.6	23.4	22.9	21.9	20.8	19.8	18.8	18.6
102.5°	24.4	24.2	24.0	23.7	23.5	25.0	28.1	31.2	34.4	37.5	59.1
105°	25.1	24.8	24.6	24.3	24.1	35.2	57.6	80.0	102.5	124.9	136.3
107.5°	78.8	95.7	112.6	129.5	146.5	163.1	179.6	196.0	212.5	228.9	227.1
110°	156.8	175.0	193.1	211.2	229.3	240.5	244.7	248.9	253.0	257.2	255.8



TEST NUMBER: P331874

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	269.1	272.9	276.7	280.6	284.4	286.3	286.2	286.1	286.1	286.0	284.6
115°	335.4	334.9	334.4	333.8	333.3	332.5	331.2	329.9	328.7	327.4	326.2
117.5°	372.6	372.5	372.4	372.3	372.2	371.6	370.6	369.6	368.6	367.5	367.0
120°	398.1	398.1	398.1	398.1	398.1	397.6	396.6	395.6	394.6	393.5	393.2
122.5°	423.2	423.1	423.0	422.9	422.8	422.4	421.7	421.0	420.3	419.6	419.1
125°	458.6	458.3	458.1	457.8	457.6	457.3	457.0	456.8	456.5	456.3	455.8
127.5°	492.6	492.8	493.1	493.3	493.6	493.5	493.1	492.7	492.3	491.9	491.3
130°	514.5	514.7	515.0	515.2	515.5	515.3	514.8	514.3	513.8	513.3	512.8
132.5°	534.5	534.9	535.2	535.6	536.0	535.9	535.4	534.9	534.4	533.9	533.4
135°	565.2	565.6	566.0	566.4	566.7	566.7	566.4	566.0	565.6	565.2	564.7
137.5°	594.1	594.3	594.6	594.8	595.1	594.9	594.3	593.7	593.1	592.5	592.2
140°	611.4	611.7	611.9	612.2	612.4	612.3	611.8	611.3	610.8	610.3	609.9
142.5°	627.4	627.7	628.1	628.5	628.8	628.8	628.4	628.0	627.6	627.2	626.8
145°	651.9	651.9	651.9	651.9	651.9	651.8	651.5	651.3	651.0	650.8	650.5
147.5°	670.2	670.8	671.3	671.9	672.5	672.7	672.4	672.2	671.9	671.7	671.4
150°	683.9	684.2	684.6	685.0	685.4	685.4	685.2	684.9	684.7	684.4	684.2
152.5°	694.8	695.4	696.0	696.6	697.1	697.2	696.7	696.3	695.8	695.4	695.2
155°	710.1	710.9	711.6	712.4	713.1	713.2	712.6	711.9	711.3	710.7	710.5
157.5°	723.0	724.0	725.0	725.9	726.9	727.1	726.3	725.5	724.8	724.0	724.1
160°	731.2	732.1	733.0	733.9	734.7	734.8	734.0	733.3	732.5	731.8	731.9
162.5°	739.0	739.7	740.5	741.3	742.1	742.1	741.2	740.3	739.5	738.6	738.7
165°	748.3	749.2	750.1	751.0	751.9	751.8	750.8	749.8	748.8	747.7	747.9
167.5°	755.0	756.1	757.1	758.1	759.1	759.1	758.1	757.1	756.1	755.0	755.0
170°	759.1	760.2	761.2	762.2	763.2	763.2	762.2	761.2	760.2	759.1	759.1
172.5°	761.4	762.5	763.7	764.8	765.9	765.9	764.9	763.9	762.9	761.9	761.8
175°	764.8	765.9	766.9	767.9	768.9	769.0	768.1	767.2	766.3	765.4	765.3
177.5°	765.9	766.9	767.9	768.9	769.9	770.0	769.2	768.4	767.6	766.8	766.7
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P331874

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	495.7	494.3	492.8	490.2	487.9	484.8	483.8	482.7	479.3	476.4	474.1
5°	526.0	520.4	512.3	504.8	498.8	490.6	486.0	481.1	474.1	467.8	462.7
7.5°	557.7	546.7	534.0	520.4	507.6	495.3	485.4	476.5	466.7	457.5	450.2
10°	582.9	567.0	549.3	530.2	513.9	498.1	484.8	473.2	460.6	449.6	440.5
12.5°	611.6	588.1	563.7	540.5	521.2	499.2	483.1	468.3	454.0	440.9	430.7
15°	645.5	615.7	586.8	554.9	525.6	498.1	479.0	460.3	443.8	430.3	417.2
17.5°	676.5	642.7	604.6	565.8	530.4	497.8	471.1	450.0	429.3	412.8	399.8
20°	694.0	655.6	612.5	572.2	533.0	496.7	467.3	442.2	419.8	402.3	387.7
22.5°	709.1	664.1	619.5	576.4	532.8	493.7	460.4	434.5	410.3	393.2	377.6
25°	724.8	670.9	626.2	575.7	527.0	486.4	449.2	419.8	395.6	375.5	359.5
27.5°	738.2	670.5	617.4	563.0	517.7	477.1	437.3	405.8	380.1	358.3	342.0
30°	747.1	671.4	608.3	554.5	508.8	466.9	428.2	396.5	369.5	347.4	332.0
32.5°	752.7	670.8	599.9	542.5	494.6	457.5	418.3	385.5	357.7	336.0	321.2
35°	756.0	666.7	585.4	517.9	471.8	435.6	402.8	368.8	339.7	319.4	302.6
37.5°	749.4	658.1	568.7	494.1	443.6	408.1	380.4	351.5	323.6	301.3	286.8
40°	739.2	652.5	555.6	477.3	424.2	390.0	366.5	338.0	310.5	289.3	275.8
42.5°	719.6	641.2	541.3	458.7	404.1	369.9	348.2	324.4	298.4	278.5	265.0
45°	671.9	616.4	519.7	430.8	374.4	339.0	319.9	302.6	279.1	259.8	248.1
47.5°	605.6	579.2	488.6	401.3	343.3	309.3	289.4	275.6	258.4	242.7	231.6
50°	559.6	548.6	467.6	381.1	322.7	289.3	270.2	257.7	245.3	229.7	219.5
52.5°	506.5	513.2	443.0	360.3	301.6	268.8	250.9	240.9	229.7	216.8	207.9
55°	431.7	456.1	400.5	325.2	270.2	239.0	222.0	213.2	206.6	197.1	189.4
57.5°	361.7	392.8	354.5	289.1	239.4	212.5	196.2	186.6	182.4	177.4	171.3
60°	320.1	350.8	321.7	264.9	218.8	193.1	178.7	170.5	166.3	162.8	157.7
62.5°	283.0	314.1	289.7	240.3	198.4	174.7	162.1	154.1	150.9	149.1	144.7
65°	232.0	258.8	242.5	202.0	169.4	148.4	137.0	131.4	128.4	127.7	124.9
67.5°	188.8	209.2	197.4	167.5	141.9	123.8	114.1	109.3	107.0	106.7	104.6
70°	160.5	179.6	170.5	143.5	121.4	107.2	98.8	94.6	93.2	93.0	91.8
72.5°	138.5	151.8	144.6	122.1	105.0	92.1	85.9	81.5	80.0	80.3	79.5
75°	102.5	112.5	108.3	92.7	79.0	70.6	65.5	62.7	61.3	62.0	61.0
77.5°	73.8	80.1	76.3	65.5	57.0	51.0	47.2	45.5	44.2	44.2	43.8
80°	55.7	59.4	57.3	50.8	43.8	38.7	35.6	34.5	33.8	33.5	33.3
82.5°	39.7	42.8	40.3	35.9	31.1	28.0	26.3	24.8	24.3	24.4	24.2
85°	20.0	21.2	20.3	17.5	15.6	14.2	13.3	12.6	12.1	12.3	11.9
87.5°	9.0	8.8	7.9	6.9	6.3	5.5	5.2	4.6	4.5	4.7	4.8
90°	10.4	8.7	7.1	5.6	4.4	3.1	1.8	0.6	1.8	3.1	4.4
92.5°	12.1	10.9	9.6	9.2	9.5	9.9	10.3	10.6	10.3	9.9	9.5
95°	14.9	13.5	12.1	14.0	19.2	24.4	29.6	34.8	29.6	24.4	19.2
97.5°	36.6	45.7	54.9	60.6	62.9	65.3	67.6	69.9	67.6	65.3	62.9
100°	58.4	78.1	97.9	106.5	104.0	101.5	98.9	96.4	98.9	101.5	104.0
102.5°	80.7	102.3	123.9	133.8	132.0	130.2	128.3	126.5	128.3	130.2	132.0
105°	147.7	159.1	170.5	175.5	174.1	172.8	171.4	170.0	171.4	172.8	174.1
107.5°	225.3	223.5	221.7	220.3	219.2	218.1	216.9	215.8	216.9	218.1	219.2
110°	254.4	253.0	251.7	250.4	249.4	248.4	247.4	246.4	247.4	248.4	249.4



TEST NUMBER: P331874

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	283.2	281.8	280.4	279.2	278.3	277.4	276.5	275.6	276.5	277.4	278.3
115°	325.1	324.0	322.8	321.9	321.1	320.3	319.6	318.8	319.6	320.3	321.1
117.5°	366.4	365.8	365.2	364.4	363.5	362.6	361.6	360.7	361.6	362.6	363.5
120°	392.8	392.4	392.0	391.3	390.1	389.0	387.8	386.7	387.8	389.0	390.1
122.5°	418.6	418.1	417.6	416.9	416.0	415.0	414.1	413.2	414.1	415.0	416.0
125°	455.3	454.8	454.3	453.5	452.5	451.5	450.5	449.4	450.5	451.5	452.5
127.5°	490.7	490.0	489.4	488.6	487.6	486.6	485.6	484.6	485.6	486.6	487.6
130°	512.3	511.8	511.3	510.5	509.5	508.5	507.5	506.5	507.5	508.5	509.5
132.5°	533.0	532.6	532.2	531.5	530.5	529.5	528.5	527.5	528.5	529.5	530.5
135°	564.2	563.7	563.2	562.6	561.8	561.0	560.3	559.5	560.3	561.0	561.8
137.5°	591.9	591.6	591.4	590.7	589.8	588.8	587.9	586.9	587.9	588.8	589.8
140°	609.5	609.1	608.8	608.2	607.4	606.7	605.9	605.1	605.9	606.7	607.4
142.5°	626.4	626.0	625.6	625.1	624.3	623.6	622.8	622.0	622.8	623.6	624.3
145°	650.3	650.0	649.8	649.2	648.3	647.4	646.5	645.6	646.5	647.4	648.3
147.5°	671.1	670.9	670.6	670.2	669.6	669.1	668.5	667.9	668.5	669.1	669.6
150°	683.9	683.7	683.4	683.1	682.7	682.3	682.0	681.6	682.0	682.3	682.7
152.5°	695.1	694.9	694.8	694.6	694.4	694.2	694.1	693.9	694.1	694.2	694.4
155°	710.4	710.3	710.2	710.2	710.5	710.7	711.0	711.2	711.0	710.7	710.5
157.5°	724.3	724.4	724.5	724.6	724.6	724.6	724.7	724.7	724.7	724.6	724.6
160°	732.0	732.1	732.3	732.4	732.5	732.7	732.8	732.9	732.8	732.7	732.5
162.5°	738.9	739.0	739.1	739.3	739.7	740.0	740.3	740.7	740.3	740.0	739.7
165°	748.0	748.1	748.2	748.5	748.9	749.3	749.6	750.0	749.6	749.3	748.9
167.5°	755.0	755.0	755.0	755.3	755.8	756.3	756.8	757.3	756.8	756.3	755.8
170°	759.1	759.1	759.1	759.4	759.9	760.4	760.9	761.4	760.9	760.4	759.9
172.5°	761.7	761.6	761.5	761.7	762.3	762.9	763.6	764.2	763.6	762.9	762.3
175°	765.2	765.0	764.9	765.2	765.8	766.4	767.1	767.7	767.1	766.4	765.8
177.5°	766.6	766.5	766.4	766.6	767.1	767.6	768.1	768.6	768.1	767.6	767.1
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P331874

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	472.8	471.5	469.7	466.9	464.6	461.1	461.1	461.6	461.6	461.5	461.1
5°	458.5	455.0	450.8	445.9	440.8	435.6	434.7	432.8	431.5	430.5	429.4
7.5°	443.3	437.1	431.0	424.2	417.9	412.8	409.2	406.2	404.3	402.2	400.7
10°	433.1	425.4	418.2	411.0	403.0	396.7	392.8	390.0	387.9	386.0	385.1
12.5°	421.0	412.2	404.2	397.3	388.7	382.2	378.4	377.1	374.7	370.7	368.7
15°	403.3	395.1	385.6	375.1	370.9	363.0	358.5	356.4	355.0	352.0	351.1
17.5°	388.1	377.5	366.7	358.9	351.1	344.7	342.2	339.6	337.8	335.3	334.5
20°	376.0	366.5	356.7	348.3	340.1	333.1	331.0	329.2	327.3	326.2	325.2
22.5°	363.7	354.2	346.0	338.2	329.5	324.9	322.7	320.6	319.3	318.5	317.6
25°	346.4	338.0	328.9	322.0	315.0	311.9	310.5	309.4	308.4	307.3	307.0
27.5°	331.0	321.8	314.5	307.9	302.9	300.4	299.0	298.5	298.7	299.1	299.4
30°	319.4	311.0	305.0	299.4	294.7	292.4	292.1	292.1	293.1	293.3	293.8
32.5°	308.8	301.9	295.8	290.4	286.9	285.3	286.2	286.2	286.9	287.5	288.4
35°	293.3	287.2	282.6	277.9	274.9	275.6	276.1	276.5	277.7	279.1	280.0
37.5°	278.5	273.3	268.4	264.8	263.4	264.6	265.8	266.7	268.1	269.2	270.1
40°	267.9	263.9	259.3	256.0	256.5	257.2	258.1	259.3	260.5	261.2	262.1
42.5°	258.0	253.9	250.3	247.6	248.3	249.2	249.7	250.3	251.7	253.0	253.5
45°	243.0	239.7	236.5	234.8	235.3	235.8	236.2	236.9	238.1	239.0	239.3
47.5°	226.1	223.8	221.6	220.0	220.8	220.6	221.2	222.7	223.0	223.6	224.9
50°	215.3	213.2	210.6	210.1	210.1	210.1	210.4	212.2	212.2	213.2	214.1
52.5°	203.3	202.0	200.4	199.5	199.1	199.1	200.1	201.0	201.4	202.7	203.7
55°	185.7	184.3	182.9	182.2	181.7	182.2	184.0	184.5	185.7	186.4	187.1
57.5°	167.3	166.2	165.1	164.7	164.6	165.2	166.2	167.6	167.9	170.1	171.1
60°	155.2	153.5	152.6	152.6	152.1	154.2	153.8	156.1	156.6	158.0	159.6
62.5°	142.7	140.5	140.1	140.1	140.8	141.4	142.0	143.0	144.3	146.0	147.3
65°	122.5	121.4	123.0	122.8	122.3	123.7	123.7	124.9	126.3	127.9	130.5
67.5°	103.5	102.9	103.0	103.0	103.7	104.5	105.2	106.2	107.9	109.6	111.3
70°	90.6	91.3	90.2	91.1	91.8	92.0	92.5	93.9	95.7	96.9	98.8
72.5°	78.1	78.1	78.2	78.6	79.3	79.7	80.2	81.8	83.8	84.8	86.3
75°	60.1	59.9	60.6	60.6	61.7	62.2	62.7	63.4	65.2	66.6	67.8
77.5°	43.9	44.2	44.0	44.8	44.5	44.6	46.0	46.7	46.9	49.7	50.3
80°	33.1	33.5	33.8	34.0	34.2	33.8	35.4	36.1	36.1	37.7	38.9
82.5°	23.8	24.0	24.6	24.9	24.9	25.4	25.5	26.0	26.6	27.3	28.8
85°	11.9	12.6	12.8	12.6	12.8	12.3	13.0	13.3	13.5	13.5	13.5
87.5°	4.9	5.3	5.5	6.0	6.1	6.7	6.8	6.5	6.6	7.2	6.6
90°	5.6	7.1	8.7	10.4	12.0	13.7	14.2	14.7	15.2	15.7	16.1
92.5°	9.2	9.6	10.9	12.1	13.4	14.6	15.4	16.2	17.0	17.8	18.3
95°	14.0	12.1	13.5	14.9	16.3	17.7	18.6	19.5	20.3	21.2	21.7
97.5°	60.6	54.9	45.7	36.6	27.5	18.4	19.4	20.4	21.4	22.4	23.0
100°	106.5	97.9	78.1	58.4	38.6	18.8	19.8	20.8	21.9	22.9	23.4
102.5°	133.8	123.9	102.3	80.7	59.1	37.5	34.4	31.2	28.1	25.0	23.5
105°	175.5	170.5	159.1	147.7	136.3	124.9	102.5	80.0	57.6	35.2	24.1
107.5°	220.3	221.7	223.5	225.3	227.1	228.9	212.5	196.0	179.6	163.1	146.5
110°	250.4	251.7	253.0	254.4	255.8	257.2	253.0	248.9	244.7	240.5	229.3



TEST NUMBER: P331874

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	279.2	280.4	281.8	283.2	284.6	286.0	286.1	286.1	286.2	286.3	284.4
115°	321.9	322.8	324.0	325.1	326.2	327.4	328.7	329.9	331.2	332.5	333.3
117.5°	364.4	365.2	365.8	366.4	367.0	367.5	368.6	369.6	370.6	371.6	372.2
120°	391.3	392.0	392.4	392.8	393.2	393.5	394.6	395.6	396.6	397.6	398.1
122.5°	416.9	417.6	418.1	418.6	419.1	419.6	420.3	421.0	421.7	422.4	422.8
125°	453.5	454.3	454.8	455.3	455.8	456.3	456.5	456.8	457.0	457.3	457.6
127.5°	488.6	489.4	490.0	490.7	491.3	491.9	492.3	492.7	493.1	493.5	493.6
130°	510.5	511.3	511.8	512.3	512.8	513.3	513.8	514.3	514.8	515.3	515.5
132.5°	531.5	532.2	532.6	533.0	533.4	533.9	534.4	534.9	535.4	535.9	536.0
135°	562.6	563.2	563.7	564.2	564.7	565.2	565.6	566.0	566.4	566.7	566.7
137.5°	590.7	591.4	591.6	591.9	592.2	592.5	593.1	593.7	594.3	594.9	595.1
140°	608.2	608.8	609.1	609.5	609.9	610.3	610.8	611.3	611.8	612.3	612.4
142.5°	625.1	625.6	626.0	626.4	626.8	627.2	627.6	628.0	628.4	628.8	628.8
145°	649.2	649.8	650.0	650.3	650.5	650.8	651.0	651.3	651.5	651.8	651.9
147.5°	670.2	670.6	670.9	671.1	671.4	671.7	671.9	672.2	672.4	672.7	672.5
150°	683.1	683.4	683.7	683.9	684.2	684.4	684.7	684.9	685.2	685.4	685.4
152.5°	694.6	694.8	694.9	695.1	695.2	695.4	695.8	696.3	696.7	697.2	697.1
155°	710.2	710.2	710.3	710.4	710.5	710.7	711.3	711.9	712.6	713.2	713.1
157.5°	724.6	724.5	724.4	724.3	724.1	724.0	724.8	725.5	726.3	727.1	726.9
160°	732.4	732.3	732.1	732.0	731.9	731.8	732.5	733.3	734.0	734.8	734.7
162.5°	739.3	739.1	739.0	738.9	738.7	738.6	739.5	740.3	741.2	742.1	742.1
165°	748.5	748.2	748.1	748.0	747.9	747.7	748.8	749.8	750.8	751.8	751.9
167.5°	755.3	755.0	755.0	755.0	755.0	755.0	756.1	757.1	758.1	759.1	759.1
170°	759.4	759.1	759.1	759.1	759.1	759.1	760.2	761.2	762.2	763.2	763.2
172.5°	761.7	761.5	761.6	761.7	761.8	761.9	762.9	763.9	764.9	765.9	765.9
175°	765.2	764.9	765.0	765.2	765.3	765.4	766.3	767.2	768.1	769.0	768.9
177.5°	766.6	766.4	766.5	766.6	766.7	766.8	767.6	768.4	769.2	770.0	769.9
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P331874

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	459.8	459.6	460.9	460.0	460.9	459.6	459.8	461.1	461.5	461.6	461.6
5°	428.0	428.7	426.3	426.3	426.3	428.7	428.0	429.4	430.5	431.5	432.8
7.5°	399.6	398.6	398.7	397.4	398.7	398.6	399.6	400.7	402.2	404.3	406.2
10°	382.3	380.9	380.4	380.7	380.4	380.9	382.3	385.1	386.0	387.9	390.0
12.5°	367.9	367.7	364.6	364.6	364.6	367.7	367.9	368.7	370.7	374.7	377.1
15°	351.1	346.7	346.2	347.6	346.2	346.7	351.1	351.1	352.0	355.0	356.4
17.5°	334.2	331.8	332.0	331.3	332.0	331.8	334.2	334.5	335.3	337.8	339.6
20°	325.2	323.8	323.6	322.0	323.6	323.8	325.2	325.2	326.2	327.3	329.2
22.5°	317.0	316.6	316.7	314.9	316.7	316.6	317.0	317.6	318.5	319.3	320.6
25°	306.8	308.0	307.0	307.0	307.0	308.0	306.8	307.0	307.3	308.4	309.4
27.5°	299.9	299.9	299.4	299.4	299.4	299.9	299.9	299.4	299.1	298.7	298.5
30°	294.7	294.5	294.9	294.9	294.9	294.5	294.7	293.8	293.3	293.1	292.1
32.5°	289.5	289.8	289.9	290.1	289.9	289.8	289.5	288.4	287.5	286.9	286.2
35°	281.4	281.7	282.4	281.9	282.4	281.7	281.4	280.0	279.1	277.7	276.5
37.5°	270.5	271.6	271.4	271.7	271.4	271.6	270.5	270.1	269.2	268.1	266.7
40°	262.3	263.0	262.8	262.8	262.8	263.0	262.3	262.1	261.2	260.5	259.3
42.5°	253.9	254.4	253.8	253.5	253.8	254.4	253.9	253.5	253.0	251.7	250.3
45°	240.2	239.7	240.4	239.5	240.4	239.7	240.2	239.3	239.0	238.1	236.9
47.5°	224.8	225.3	225.5	226.2	225.5	225.3	224.8	224.9	223.6	223.0	222.7
50°	214.6	216.0	216.0	215.7	216.0	216.0	214.6	214.1	213.2	212.2	212.2
52.5°	204.5	205.1	206.1	206.0	206.1	205.1	204.5	203.7	202.7	201.4	201.0
55°	188.9	189.4	189.9	190.1	189.9	189.4	188.9	187.1	186.4	185.7	184.5
57.5°	172.8	172.6	173.7	174.1	173.7	172.6	172.8	171.1	170.1	167.9	167.6
60°	161.4	161.4	163.3	164.0	163.3	161.4	161.4	159.6	158.0	156.6	156.1
62.5°	149.3	150.1	151.9	151.0	151.9	150.1	149.3	147.3	146.0	144.3	143.0
65°	131.6	133.5	133.3	134.2	133.3	133.5	131.6	130.5	127.9	126.3	124.9
67.5°	113.1	114.3	116.0	116.1	116.0	114.3	113.1	111.3	109.6	107.9	106.2
70°	100.6	101.8	102.7	103.4	102.7	101.8	100.6	98.8	96.9	95.7	93.9
72.5°	88.5	89.1	91.4	90.4	91.4	89.1	88.5	86.3	84.8	83.8	81.8
75°	69.4	71.1	72.5	71.8	72.5	71.1	69.4	67.8	66.6	65.2	63.4
77.5°	51.3	53.0	53.6	53.0	53.6	53.0	51.3	50.3	49.7	46.9	46.7
80°	40.5	40.3	41.7	41.5	41.7	40.3	40.5	38.9	37.7	36.1	36.1
82.5°	29.7	29.5	30.1	30.3	30.1	29.5	29.7	28.8	27.3	26.6	26.0
85°	14.4	15.1	14.2	14.0	14.2	15.1	14.4	13.5	13.5	13.5	13.3
87.5°	6.6	6.7	6.5	6.4	6.5	6.7	6.6	6.6	7.2	6.6	6.5
90°	16.4	16.6	16.9	17.1	16.9	16.6	16.4	16.1	15.7	15.2	14.7
92.5°	18.5	18.6	18.8	18.9	18.8	18.6	18.5	18.3	17.8	17.0	16.2
95°	21.7	21.7	21.7	21.7	21.7	21.7	21.7	21.7	21.2	20.3	19.5
97.5°	23.1	23.2	23.4	23.5	23.4	23.2	23.1	23.0	22.4	21.4	20.4
100°	23.6	23.7	23.8	24.0	23.8	23.7	23.6	23.4	22.9	21.9	20.8
102.5°	23.7	24.0	24.2	24.4	24.2	24.0	23.7	23.5	25.0	28.1	31.2
105°	24.3	24.6	24.8	25.1	24.8	24.6	24.3	24.1	35.2	57.6	80.0
107.5°	129.5	112.6	95.7	78.8	95.7	112.6	129.5	146.5	163.1	179.6	196.0
110°	211.2	193.1	175.0	156.8	175.0	193.1	211.2	229.3	240.5	244.7	248.9



TEST NUMBER: P331874

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	280.6	276.7	272.9	269.1	272.9	276.7	280.6	284.4	286.3	286.2	286.1
115°	333.8	334.4	334.9	335.4	334.9	334.4	333.8	333.3	332.5	331.2	329.9
117.5°	372.3	372.4	372.5	372.6	372.5	372.4	372.3	372.2	371.6	370.6	369.6
120°	398.1	398.1	398.1	398.1	398.1	398.1	398.1	398.1	397.6	396.6	395.6
122.5°	422.9	423.0	423.1	423.2	423.1	423.0	422.9	422.8	422.4	421.7	421.0
125°	457.8	458.1	458.3	458.6	458.3	458.1	457.8	457.6	457.3	457.0	456.8
127.5°	493.3	493.1	492.8	492.6	492.8	493.1	493.3	493.6	493.5	493.1	492.7
130°	515.2	515.0	514.7	514.5	514.7	515.0	515.2	515.5	515.3	514.8	514.3
132.5°	535.6	535.2	534.9	534.5	534.9	535.2	535.6	536.0	535.9	535.4	534.9
135°	566.4	566.0	565.6	565.2	565.6	566.0	566.4	566.7	566.7	566.4	566.0
137.5°	594.8	594.6	594.3	594.1	594.3	594.6	594.8	595.1	594.9	594.3	593.7
140°	612.2	611.9	611.7	611.4	611.7	611.9	612.2	612.4	612.3	611.8	611.3
142.5°	628.5	628.1	627.7	627.4	627.7	628.1	628.5	628.8	628.8	628.4	628.0
145°	651.9	651.9	651.9	651.9	651.9	651.9	651.9	651.9	651.8	651.5	651.3
147.5°	671.9	671.3	670.8	670.2	670.8	671.3	671.9	672.5	672.7	672.4	672.2
150°	685.0	684.6	684.2	683.9	684.2	684.6	685.0	685.4	685.4	685.2	684.9
152.5°	696.6	696.0	695.4	694.8	695.4	696.0	696.6	697.1	697.2	696.7	696.3
155°	712.4	711.6	710.9	710.1	710.9	711.6	712.4	713.1	713.2	712.6	711.9
157.5°	725.9	725.0	724.0	723.0	724.0	725.0	725.9	726.9	727.1	726.3	725.5
160°	733.9	733.0	732.1	731.2	732.1	733.0	733.9	734.7	734.8	734.0	733.3
162.5°	741.3	740.5	739.7	739.0	739.7	740.5	741.3	742.1	742.1	741.2	740.3
165°	751.0	750.1	749.2	748.3	749.2	750.1	751.0	751.9	751.8	750.8	749.8
167.5°	758.1	757.1	756.1	755.0	756.1	757.1	758.1	759.1	759.1	758.1	757.1
170°	762.2	761.2	760.2	759.1	760.2	761.2	762.2	763.2	763.2	762.2	761.2
172.5°	764.8	763.7	762.5	761.4	762.5	763.7	764.8	765.9	765.9	764.9	763.9
175°	767.9	766.9	765.9	764.8	765.9	766.9	767.9	768.9	769.0	768.1	767.2
177.5°	768.9	767.9	766.9	765.9	766.9	767.9	768.9	769.9	770.0	769.2	768.4
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P331874

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	461.1	461.1	464.6	466.9	469.7	471.5	472.8	474.1	476.4	479.3	482.7
5°	434.7	435.6	440.8	445.9	450.8	455.0	458.5	462.7	467.8	474.1	481.1
7.5°	409.2	412.8	417.9	424.2	431.0	437.1	443.3	450.2	457.5	466.7	476.5
10°	392.8	396.7	403.0	411.0	418.2	425.4	433.1	440.5	449.6	460.6	473.2
12.5°	378.4	382.2	388.7	397.3	404.2	412.2	421.0	430.7	440.9	454.0	468.3
15°	358.5	363.0	370.9	375.1	385.6	395.1	403.3	417.2	430.3	443.8	460.3
17.5°	342.2	344.7	351.1	358.9	366.7	377.5	388.1	399.8	412.8	429.3	450.0
20°	331.0	333.1	340.1	348.3	356.7	366.5	376.0	387.7	402.3	419.8	442.2
22.5°	322.7	324.9	329.5	338.2	346.0	354.2	363.7	377.6	393.2	410.3	434.5
25°	310.5	311.9	315.0	322.0	328.9	338.0	346.4	359.5	375.5	395.6	419.8
27.5°	299.0	300.4	302.9	307.9	314.5	321.8	331.0	342.0	358.3	380.1	405.8
30°	292.1	292.4	294.7	299.4	305.0	311.0	319.4	332.0	347.4	369.5	396.5
32.5°	286.2	285.3	286.9	290.4	295.8	301.9	308.8	321.2	336.0	357.7	385.5
35°	276.1	275.6	274.9	277.9	282.6	287.2	293.3	302.6	319.4	339.7	368.8
37.5°	265.8	264.6	263.4	264.8	268.4	273.3	278.5	286.8	301.3	323.6	351.5
40°	258.1	257.2	256.5	256.0	259.3	263.9	267.9	275.8	289.3	310.5	338.0
42.5°	249.7	249.2	248.3	247.6	250.3	253.9	258.0	265.0	278.5	298.4	324.4
45°	236.2	235.8	235.3	234.8	236.5	239.7	243.0	248.1	259.8	279.1	302.6
47.5°	221.2	220.6	220.8	220.0	221.6	223.8	226.1	231.6	242.7	258.4	275.6
50°	210.4	210.1	210.1	210.1	210.6	213.2	215.3	219.5	229.7	245.3	257.7
52.5°	200.1	199.1	199.1	199.5	200.4	202.0	203.3	207.9	216.8	229.7	240.9
55°	184.0	182.2	181.7	182.2	182.9	184.3	185.7	189.4	197.1	206.6	213.2
57.5°	166.2	165.2	164.6	164.7	165.1	166.2	167.3	171.3	177.4	182.4	186.6
60°	153.8	154.2	152.1	152.6	152.6	153.5	155.2	157.7	162.8	166.3	170.5
62.5°	142.0	141.4	140.8	140.1	140.1	140.5	142.7	144.7	149.1	150.9	154.1
65°	123.7	123.7	122.3	122.8	123.0	121.4	122.5	124.9	127.7	128.4	131.4
67.5°	105.2	104.5	103.7	103.0	103.0	102.9	103.5	104.6	106.7	107.0	109.3
70°	92.5	92.0	91.8	91.1	90.2	91.3	90.6	91.8	93.0	93.2	94.6
72.5°	80.2	79.7	79.3	78.6	78.2	78.1	78.1	79.5	80.3	80.0	81.5
75°	62.7	62.2	61.7	60.6	60.6	59.9	60.1	61.0	62.0	61.3	62.7
77.5°	46.0	44.6	44.5	44.8	44.0	44.2	43.9	43.8	44.2	44.2	45.5
80°	35.4	33.8	34.2	34.0	33.8	33.5	33.1	33.3	33.5	33.8	34.5
82.5°	25.5	25.4	24.9	24.9	24.6	24.0	23.8	24.2	24.4	24.3	24.8
85°	13.0	12.3	12.8	12.6	12.8	12.6	11.9	11.9	12.3	12.1	12.6
87.5°	6.8	6.7	6.1	6.0	5.5	5.3	4.9	4.8	4.7	4.5	4.6
90°	14.2	13.7	12.0	10.4	8.7	7.1	5.6	4.4	3.1	1.8	0.6
92.5°	15.4	14.6	13.4	12.1	10.9	9.6	9.2	9.5	9.9	10.3	10.6
95°	18.6	17.7	16.3	14.9	13.5	12.1	14.0	19.2	24.4	29.6	34.8
97.5°	19.4	18.4	27.5	36.6	45.7	54.9	60.6	62.9	65.3	67.6	69.9
100°	19.8	18.8	38.6	58.4	78.1	97.9	106.5	104.0	101.5	98.9	96.4
102.5°	34.4	37.5	59.1	80.7	102.3	123.9	133.8	132.0	130.2	128.3	126.5
105°	102.5	124.9	136.3	147.7	159.1	170.5	175.5	174.1	172.8	171.4	170.0
107.5°	212.5	228.9	227.1	225.3	223.5	221.7	220.3	219.2	218.1	216.9	215.8
110°	253.0	257.2	255.8	254.4	253.0	251.7	250.4	249.4	248.4	247.4	246.4



TEST NUMBER: P331874

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	286.1	286.0	284.6	283.2	281.8	280.4	279.2	278.3	277.4	276.5	275.6
115°	328.7	327.4	326.2	325.1	324.0	322.8	321.9	321.1	320.3	319.6	318.8
117.5°	368.6	367.5	367.0	366.4	365.8	365.2	364.4	363.5	362.6	361.6	360.7
120°	394.6	393.5	393.2	392.8	392.4	392.0	391.3	390.1	389.0	387.8	386.7
122.5°	420.3	419.6	419.1	418.6	418.1	417.6	416.9	416.0	415.0	414.1	413.2
125°	456.5	456.3	455.8	455.3	454.8	454.3	453.5	452.5	451.5	450.5	449.4
127.5°	492.3	491.9	491.3	490.7	490.0	489.4	488.6	487.6	486.6	485.6	484.6
130°	513.8	513.3	512.8	512.3	511.8	511.3	510.5	509.5	508.5	507.5	506.5
132.5°	534.4	533.9	533.4	533.0	532.6	532.2	531.5	530.5	529.5	528.5	527.5
135°	565.6	565.2	564.7	564.2	563.7	563.2	562.6	561.8	561.0	560.3	559.5
137.5°	593.1	592.5	592.2	591.9	591.6	591.4	590.7	589.8	588.8	587.9	586.9
140°	610.8	610.3	609.9	609.5	609.1	608.8	608.2	607.4	606.7	605.9	605.1
142.5°	627.6	627.2	626.8	626.4	626.0	625.6	625.1	624.3	623.6	622.8	622.0
145°	651.0	650.8	650.5	650.3	650.0	649.8	649.2	648.3	647.4	646.5	645.6
147.5°	671.9	671.7	671.4	671.1	670.9	670.6	670.2	669.6	669.1	668.5	667.9
150°	684.7	684.4	684.2	683.9	683.7	683.4	683.1	682.7	682.3	682.0	681.6
152.5°	695.8	695.4	695.2	695.1	694.9	694.8	694.6	694.4	694.2	694.1	693.9
155°	711.3	710.7	710.5	710.4	710.3	710.2	710.2	710.5	710.7	711.0	711.2
157.5°	724.8	724.0	724.1	724.3	724.4	724.5	724.6	724.6	724.6	724.7	724.7
160°	732.5	731.8	731.9	732.0	732.1	732.3	732.4	732.5	732.7	732.8	732.9
162.5°	739.5	738.6	738.7	738.9	739.0	739.1	739.3	739.7	740.0	740.3	740.7
165°	748.8	747.7	747.9	748.0	748.1	748.2	748.5	748.9	749.3	749.6	750.0
167.5°	756.1	755.0	755.0	755.0	755.0	755.0	755.3	755.8	756.3	756.8	757.3
170°	760.2	759.1	759.1	759.1	759.1	759.1	759.4	759.9	760.4	760.9	761.4
172.5°	762.9	761.9	761.8	761.7	761.6	761.5	761.7	762.3	762.9	763.6	764.2
175°	766.3	765.4	765.3	765.2	765.0	764.9	765.2	765.8	766.4	767.1	767.7
177.5°	767.6	766.8	766.7	766.6	766.5	766.4	766.6	767.1	767.6	768.1	768.6
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P331874

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	483.8	484.8	487.9	490.2	492.8	494.3	495.7	496.9	498.4	498.7	504.1
5°	486.0	490.6	498.8	504.8	512.3	520.4	526.0	528.6	535.4	540.9	552.1
7.5°	485.4	495.3	507.6	520.4	534.0	546.7	557.7	570.8	580.0	594.0	607.7
10°	484.8	498.1	513.9	530.2	549.3	567.0	582.9	600.6	615.3	634.6	651.1
12.5°	483.1	499.2	521.2	540.5	563.7	588.1	611.6	634.3	647.3	679.5	694.7
15°	479.0	498.1	525.6	554.9	586.8	615.7	645.5	669.3	707.7	735.9	753.9
17.5°	471.1	497.8	530.4	565.8	604.6	642.7	676.5	712.5	753.3	787.4	823.8
20°	467.3	496.7	533.0	572.2	612.5	655.6	694.0	737.3	781.8	815.4	862.0
22.5°	460.4	493.7	532.8	576.4	619.5	664.1	709.1	752.8	804.2	850.4	894.8
25°	449.2	486.4	527.0	575.7	626.2	670.9	724.8	782.8	836.3	895.8	940.0
27.5°	437.3	477.1	517.7	563.0	617.4	670.5	738.2	803.7	869.2	920.5	953.3
30°	428.2	466.9	508.8	554.5	608.3	671.4	747.1	818.6	882.5	926.5	944.9
32.5°	418.3	457.5	494.6	542.5	599.9	670.8	752.7	827.4	883.2	912.5	908.9
35°	402.8	435.6	471.8	517.9	585.4	666.7	756.0	828.2	862.4	856.1	808.6
37.5°	380.4	408.1	443.6	494.1	568.7	658.1	749.4	803.6	801.4	750.2	681.3
40°	366.5	390.0	424.2	477.3	555.6	652.5	739.2	774.4	744.6	673.0	590.6
42.5°	348.2	369.9	404.1	458.7	541.3	641.2	719.6	729.8	671.5	589.2	513.6
45°	319.9	339.0	374.4	430.8	519.7	616.4	671.9	646.9	568.4	483.4	425.9
47.5°	289.4	309.3	343.3	401.3	488.6	579.2	605.6	552.6	472.0	403.0	350.2
50°	270.2	289.3	322.7	381.1	467.6	548.6	559.6	491.1	417.0	356.4	313.1
52.5°	250.9	268.8	301.6	360.3	443.0	513.2	506.5	436.7	368.6	316.9	282.9
55°	222.0	239.0	270.2	325.2	400.5	456.1	431.7	365.1	308.7	268.6	242.7
57.5°	196.2	212.5	239.4	289.1	354.5	392.8	361.7	305.5	260.7	229.8	210.6
60°	178.7	193.1	218.8	264.9	321.7	350.8	320.1	270.5	232.7	208.0	190.8
62.5°	162.1	174.7	198.4	240.3	289.7	314.1	283.0	241.0	208.9	187.0	172.3
65°	137.0	148.4	169.4	202.0	242.5	258.8	232.0	198.0	173.1	156.8	147.0
67.5°	114.1	123.8	141.9	167.5	197.4	209.2	188.8	162.5	143.7	130.6	122.9
70°	98.8	107.2	121.4	143.5	170.5	179.6	160.5	138.8	125.1	114.6	107.4
72.5°	85.9	92.1	105.0	122.1	144.6	151.8	138.5	119.5	106.7	98.8	93.0
75°	65.5	70.6	79.0	92.7	108.3	112.5	102.5	90.6	82.0	76.4	72.0
77.5°	47.2	51.0	57.0	65.5	76.3	80.1	73.8	65.8	59.5	55.8	53.3
80°	35.6	38.7	43.8	50.8	57.3	59.4	55.7	49.6	45.2	43.1	41.0
82.5°	26.3	28.0	31.1	35.9	40.3	42.8	39.7	36.0	33.6	31.7	30.9
85°	13.3	14.2	15.6	17.5	20.3	21.2	20.0	19.1	17.7	16.5	16.5
87.5°	5.2	5.5	6.3	6.9	7.9	8.8	9.0	8.9	9.1	9.0	8.9
90°	1.8	3.1	4.4	5.6	7.1	8.7	10.4	12.0	13.7	14.2	14.7
92.5°	10.3	9.9	9.5	9.2	9.6	10.9	12.1	13.4	14.6	15.4	16.2
95°	29.6	24.4	19.2	14.0	12.1	13.5	14.9	16.3	17.7	18.6	19.5
97.5°	67.6	65.3	62.9	60.6	54.9	45.7	36.6	27.5	18.4	19.4	20.4
100°	98.9	101.5	104.0	106.5	97.9	78.1	58.4	38.6	18.8	19.8	20.8
102.5°	128.3	130.2	132.0	133.8	123.9	102.3	80.7	59.1	37.5	34.4	31.2
105°	171.4	172.8	174.1	175.5	170.5	159.1	147.7	136.3	124.9	102.5	80.0
107.5°	216.9	218.1	219.2	220.3	221.7	223.5	225.3	227.1	228.9	212.5	196.0
110°	247.4	248.4	249.4	250.4	251.7	253.0	254.4	255.8	257.2	253.0	248.9



TEST NUMBER: P331874

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	276.5	277.4	278.3	279.2	280.4	281.8	283.2	284.6	286.0	286.1	286.1
115°	319.6	320.3	321.1	321.9	322.8	324.0	325.1	326.2	327.4	328.7	329.9
117.5°	361.6	362.6	363.5	364.4	365.2	365.8	366.4	367.0	367.5	368.6	369.6
120°	387.8	389.0	390.1	391.3	392.0	392.4	392.8	393.2	393.5	394.6	395.6
122.5°	414.1	415.0	416.0	416.9	417.6	418.1	418.6	419.1	419.6	420.3	421.0
125°	450.5	451.5	452.5	453.5	454.3	454.8	455.3	455.8	456.3	456.5	456.8
127.5°	485.6	486.6	487.6	488.6	489.4	490.0	490.7	491.3	491.9	492.3	492.7
130°	507.5	508.5	509.5	510.5	511.3	511.8	512.3	512.8	513.3	513.8	514.3
132.5°	528.5	529.5	530.5	531.5	532.2	532.6	533.0	533.4	533.9	534.4	534.9
135°	560.3	561.0	561.8	562.6	563.2	563.7	564.2	564.7	565.2	565.6	566.0
137.5°	587.9	588.8	589.8	590.7	591.4	591.6	591.9	592.2	592.5	593.1	593.7
140°	605.9	606.7	607.4	608.2	608.8	609.1	609.5	609.9	610.3	610.8	611.3
142.5°	622.8	623.6	624.3	625.1	625.6	626.0	626.4	626.8	627.2	627.6	628.0
145°	646.5	647.4	648.3	649.2	649.8	650.0	650.3	650.5	650.8	651.0	651.3
147.5°	668.5	669.1	669.6	670.2	670.6	670.9	671.1	671.4	671.7	671.9	672.2
150°	682.0	682.3	682.7	683.1	683.4	683.7	683.9	684.2	684.4	684.7	684.9
152.5°	694.1	694.2	694.4	694.6	694.8	694.9	695.1	695.2	695.4	695.8	696.3
155°	711.0	710.7	710.5	710.2	710.2	710.3	710.4	710.5	710.7	711.3	711.9
157.5°	724.7	724.6	724.6	724.6	724.5	724.4	724.3	724.1	724.0	724.8	725.5
160°	732.8	732.7	732.5	732.4	732.3	732.1	732.0	731.9	731.8	732.5	733.3
162.5°	740.3	740.0	739.7	739.3	739.1	739.0	738.9	738.7	738.6	739.5	740.3
165°	749.6	749.3	748.9	748.5	748.2	748.1	748.0	747.9	747.7	748.8	749.8
167.5°	756.8	756.3	755.8	755.3	755.0	755.0	755.0	755.0	755.0	756.1	757.1
170°	760.9	760.4	759.9	759.4	759.1	759.1	759.1	759.1	759.1	760.2	761.2
172.5°	763.6	762.9	762.3	761.7	761.5	761.6	761.7	761.8	761.9	762.9	763.9
175°	767.1	766.4	765.8	765.2	764.9	765.0	765.2	765.3	765.4	766.3	767.2
177.5°	768.1	767.6	767.1	766.6	766.4	766.5	766.6	766.7	766.8	767.6	768.4
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P331874

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	506.0	506.2	508.2	509.7	509.0	509.9	510.3
5°	552.8	561.2	565.6	568.9	569.1	569.4	571.2
7.5°	619.2	628.2	634.8	644.8	647.7	651.1	650.2
10°	667.7	681.0	692.4	698.4	705.0	714.5	706.8
12.5°	713.0	736.5	753.9	763.3	769.4	771.3	767.6
15°	787.7	818.4	834.9	834.5	855.4	864.5	850.3
17.5°	856.1	884.5	907.3	918.9	936.4	940.2	938.5
20°	898.1	929.1	946.8	966.8	975.9	984.0	985.4
22.5°	934.2	962.1	981.1	997.7	1005.3	1009.2	1011.5
25°	971.5	993.4	1004.8	1010.6	1012.7	1012.2	1009.2
27.5°	968.9	970.6	958.0	945.7	934.6	922.2	917.9
30°	943.7	924.2	889.2	869.4	840.3	817.2	826.6
32.5°	877.6	838.6	799.4	756.1	720.3	710.1	699.8
35°	749.0	680.5	640.4	593.8	575.2	556.6	543.7
37.5°	605.9	553.0	505.4	475.0	456.3	444.5	438.2
40°	523.9	476.2	437.0	412.3	398.1	384.9	383.0
42.5°	458.5	414.1	384.7	365.0	351.4	345.7	341.6
45°	375.5	344.6	324.8	310.8	301.7	298.2	293.5
47.5°	317.9	296.0	281.1	271.6	264.7	262.1	261.8
50°	285.6	267.4	256.5	249.0	243.7	242.7	239.0
52.5°	261.4	245.6	237.1	230.6	226.7	224.1	223.0
55°	226.9	216.4	208.7	205.0	202.0	199.4	199.4
57.5°	198.5	189.8	184.7	181.5	180.6	178.8	177.6
60°	181.0	173.6	169.6	166.8	164.9	165.2	163.1
62.5°	163.9	159.0	155.2	152.5	150.2	150.3	150.4
65°	139.5	135.8	133.0	132.1	130.7	129.1	129.5
67.5°	118.3	114.8	112.6	111.0	110.5	109.6	111.0
70°	103.0	100.4	98.8	97.4	96.9	97.1	98.3
72.5°	89.0	87.2	86.1	85.5	84.4	84.5	85.3
75°	69.9	68.5	67.6	66.9	66.6	66.6	66.6
77.5°	51.3	51.0	50.6	49.6	49.6	49.9	49.9
80°	40.5	39.8	39.6	39.1	38.4	38.0	39.1
82.5°	30.3	29.6	29.4	29.3	28.2	28.1	29.1
85°	16.3	15.6	15.8	15.6	15.6	15.4	15.4
87.5°	8.8	8.7	8.6	8.9	8.7	8.6	9.0
90°	15.2	15.7	16.1	16.4	16.6	16.9	17.1
92.5°	17.0	17.8	18.3	18.5	18.6	18.8	18.9
95°	20.3	21.2	21.7	21.7	21.7	21.7	21.7
97.5°	21.4	22.4	23.0	23.1	23.2	23.4	23.5
100°	21.9	22.9	23.4	23.6	23.7	23.8	24.0
102.5°	28.1	25.0	23.5	23.7	24.0	24.2	24.4
105°	57.6	35.2	24.1	24.3	24.6	24.8	25.1
107.5°	179.6	163.1	146.5	129.5	112.6	95.7	78.8
110°	244.7	240.5	229.3	211.2	193.1	175.0	156.8



TEST NUMBER: P331874

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	286.2	286.3	284.4	280.6	276.7	272.9	269.1
115°	331.2	332.5	333.3	333.8	334.4	334.9	335.4
117.5°	370.6	371.6	372.2	372.3	372.4	372.5	372.6
120°	396.6	397.6	398.1	398.1	398.1	398.1	398.1
122.5°	421.7	422.4	422.8	422.9	423.0	423.1	423.2
125°	457.0	457.3	457.6	457.8	458.1	458.3	458.6
127.5°	493.1	493.5	493.6	493.3	493.1	492.8	492.6
130°	514.8	515.3	515.5	515.2	515.0	514.7	514.5
132.5°	535.4	535.9	536.0	535.6	535.2	534.9	534.5
135°	566.4	566.7	566.7	566.4	566.0	565.6	565.2
137.5°	594.3	594.9	595.1	594.8	594.6	594.3	594.1
140°	611.8	612.3	612.4	612.2	611.9	611.7	611.4
142.5°	628.4	628.8	628.8	628.5	628.1	627.7	627.4
145°	651.5	651.8	651.9	651.9	651.9	651.9	651.9
147.5°	672.4	672.7	672.5	671.9	671.3	670.8	670.2
150°	685.2	685.4	685.4	685.0	684.6	684.2	683.9
152.5°	696.7	697.2	697.1	696.6	696.0	695.4	694.8
155°	712.6	713.2	713.1	712.4	711.6	710.9	710.1
157.5°	726.3	727.1	726.9	725.9	725.0	724.0	723.0
160°	734.0	734.8	734.7	733.9	733.0	732.1	731.2
162.5°	741.2	742.1	742.1	741.3	740.5	739.7	739.0
165°	750.8	751.8	751.9	751.0	750.1	749.2	748.3
167.5°	758.1	759.1	759.1	758.1	757.1	756.1	755.0
170°	762.2	763.2	763.2	762.2	761.2	760.2	759.1
172.5°	764.9	765.9	765.9	764.8	763.7	762.5	761.4
175°	768.1	769.0	768.9	767.9	766.9	765.9	764.8
177.5°	769.2	770.0	769.9	768.9	767.9	766.9	765.9
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7

(END OF REPORT)