

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332304-927

Luminaire Tested: **S123RDIP-S775D365U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332304-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D365U927-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3298.9 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332304-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332304-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR	0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	75	75	75	75	75	75	75	75	70		
	1	103	98	95	91	97	93	90	87	84	81	79	75	73	71	67	65	64	64	64	64	64	64	60		
	2	94	87	80	75	89	82	77	72	74	70	66	66	63	60	59	57	55	55	55	55	55	55	51		
	3	86	77	69	63	81	73	66	61	66	60	56	59	55	51	53	50	47	47	47	47	47	47	44		
	4	79	68	60	54	74	65	58	52	59	53	48	53	48	44	48	44	41	41	41	41	41	41	38		
	5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	43	39	36	36	36	36	36	36	33		
	6	67	55	47	41	63	52	45	40	48	42	37	43	38	34	39	35	32	32	32	32	32	32	29		
	7	62	50	42	36	59	48	40	35	44	37	33	40	34	31	36	32	28	28	28	28	28	28	26		
	8	58	46	38	32	55	44	36	31	40	34	29	36	31	27	33	29	26	26	26	26	26	26	23		
	9	54	42	34	29	51	40	33	28	37	31	26	34	28	25	31	26	23	23	23	23	23	23	21		
	10	51	38	31	26	48	37	30	26	34	28	24	31	26	23	28	24	21	21	21	21	21	21	19		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11009	11009	11009
5°	11051	10899	10962
10°	10989	10762	10726
15°	10871	10510	10399
20°	10709	10195	9958
25°	10542	9841	9526
30°	10320	9434	8918
35°	10093	9025	8360
40°	9884	8543	7669
45°	9608	8068	7046
50°	9306	7529	6348
55°	8997	6912	5697
60°	8714	6250	4982
65°	8344	5535	4266
70°	7884	4648	3446
75°	7207	3656	3244
80°	6428	3242	2982
85°	5434	2865	2655



TEST NUMBER: P332304-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.0	2.9
10°-20°	267.2	8.1
20°-30°	384.8	11.7
30°-40°	433.4	13.1
40°-50°	414.6	12.6
50°-60°	339.6	10.3
60°-70°	229.1	6.9
70°-80°	115.3	3.5
80°-90°	31.5	1.0
90°-100°	23.2	0.7
100°-110°	69.5	2.1
110°-120°	118.2	3.6
120°-130°	155.5	4.7
130°-140°	174.7	5.3
140°-150°	171.8	5.2
150°-160°	144.6	4.4
160°-170°	96.3	2.9
170°-180°	33.7	1.0
0°-30°	748.0	22.7
0°-40°	1181.5	35.8
0°-60°	1935.6	58.7
0°-90°	2311.5	70.1
90°-120°	210.9	6.4
90°-150°	712.8	21.6
90°-180°	987.0	29.9
0°-180°	3298.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1023	1023	1023	1023	1023	
5°	1023	1018	1009	1016	1014	97
15°	976	966	943	939	933	275
25°	888	866	829	812	802	408
35°	768	737	687	652	636	481
45°	631	592	530	484	463	487
55°	479	437	368	322	304	430
65°	328	281	217	178	168	324
75°	173	133	88	80	78	185
85°	44	27	23	22	22	49
90°	0	3	7	8	8	3
95°	17	18	21	22	22	19
105°	63	64	66	66	67	67
115°	119	120	119	120	119	118
125°	174	175	174	173	172	155
135°	226	228	227	226	226	174
145°	274	275	275	275	274	171
155°	314	314	314	315	313	144
165°	342	341	341	342	341	96
175°	356	354	354	356	354	34
180°	356	356	356	356	356	



TEST NUMBER: P332304-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8
2.5°	1026.0	1025.5	1024.8	1024.3	1023.7	1022.5	1020.7	1019.0	1017.2	1015.4	1017.1
5°	1022.8	1021.8	1020.9	1020.0	1019.1	1017.5	1015.3	1013.0	1010.8	1008.7	1010.3
7.5°	1013.3	1012.3	1011.3	1010.3	1009.3	1007.3	1004.5	1001.6	998.8	995.9	996.8
10°	1005.4	1004.0	1002.7	1001.5	1000.1	997.8	994.5	991.3	987.9	984.6	984.8
12.5°	994.0	992.6	991.2	989.8	988.3	985.6	981.5	977.5	973.4	969.3	969.2
15°	975.5	973.4	971.4	969.4	967.3	963.8	958.6	953.5	948.2	943.1	942.2
17.5°	952.0	949.7	947.4	945.0	942.6	938.2	931.6	925.0	918.5	912.0	910.0
20°	934.9	931.8	928.9	926.0	923.1	918.1	911.0	904.0	897.1	890.0	887.6
22.5°	915.6	912.2	908.8	905.4	902.0	896.6	889.1	881.7	874.3	866.8	863.8
25°	887.6	883.0	878.3	873.7	869.1	862.5	854.1	845.6	837.1	828.6	824.7
27.5°	853.5	848.4	843.4	838.3	833.2	825.9	816.5	807.1	797.6	788.1	782.8
30°	830.3	824.7	819.3	813.7	808.2	800.3	790.0	779.6	769.3	759.0	752.7
32.5°	807.1	800.8	794.6	788.3	782.0	773.4	762.5	751.6	740.7	729.8	722.9
35°	768.1	761.4	754.8	748.2	741.6	732.5	721.1	709.6	698.2	686.8	678.9
37.5°	728.6	721.2	713.8	706.5	699.1	689.4	677.2	665.0	652.8	640.6	631.5
40°	703.4	695.3	687.1	679.1	671.0	660.4	647.3	634.2	621.1	608.0	598.4
42.5°	674.9	666.8	658.6	650.5	642.5	631.6	618.1	604.5	591.0	577.5	567.0
45°	631.2	623.0	614.7	606.3	598.0	586.8	572.6	558.4	544.2	530.0	519.5
47.5°	587.6	578.5	569.4	560.3	551.2	539.6	525.4	511.1	496.9	482.8	471.3
50°	555.7	547.1	538.4	529.7	521.1	509.3	494.4	479.4	464.5	449.6	438.2
52.5°	527.2	517.8	508.4	499.0	489.6	477.5	462.7	448.0	433.2	418.4	406.5
55°	479.4	470.4	461.4	452.3	443.3	430.9	415.3	399.7	384.0	368.3	357.6
57.5°	435.3	425.5	415.7	405.8	395.9	383.2	367.4	351.6	335.9	320.2	310.1
60°	404.8	394.7	384.5	374.4	364.2	351.5	336.2	320.9	305.6	290.3	280.4
62.5°	374.2	364.1	353.9	343.8	333.7	321.0	305.7	290.4	275.1	259.8	250.4
65°	327.6	317.5	307.4	297.2	287.1	274.8	260.5	246.1	231.7	217.3	208.3
67.5°	281.1	270.8	260.5	250.3	240.0	228.0	214.2	200.4	186.6	172.9	166.1
70°	250.5	240.6	230.6	220.6	210.7	199.2	186.3	173.5	160.6	147.7	141.2
72.5°	220.0	210.2	200.3	190.5	180.8	170.0	158.3	146.6	134.8	123.1	117.8
75°	173.3	164.5	155.7	146.8	138.0	128.5	118.4	108.2	98.1	87.9	86.1
77.5°	130.9	122.9	114.9	106.9	98.9	91.7	85.1	78.6	72.1	65.5	64.6
80°	103.7	96.1	88.6	81.0	73.4	67.7	63.8	60.0	56.2	52.3	51.7
82.5°	77.8	71.3	64.7	58.2	51.7	47.5	45.7	43.9	42.1	40.3	39.8
85°	44.0	39.9	35.9	31.8	27.7	25.4	24.9	24.3	23.8	23.2	22.9
87.5°	16.0	14.5	13.0	11.5	10.0	9.3	9.5	9.7	9.8	10.0	9.9
90°	0.3	0.9	1.5	2.1	2.8	3.5	4.3	5.1	5.9	6.7	7.0
92.5°	6.8	7.2	7.6	8.1	8.5	8.9	9.3	9.8	10.3	10.8	10.9
95°	16.6	17.0	17.3	17.8	18.2	18.7	19.3	19.7	20.2	20.8	21.0
97.5°	29.3	29.6	30.0	30.3	30.7	31.0	31.4	31.7	32.1	32.4	32.7
100°	38.1	38.4	38.8	39.2	39.5	39.9	40.2	40.6	40.9	41.1	41.4
102.5°	48.2	48.4	48.6	48.8	49.0	49.4	49.7	50.2	50.6	51.0	51.2
105°	63.0	63.1	63.2	63.4	63.5	63.8	64.4	65.0	65.5	66.1	66.1
107.5°	80.2	80.3	80.4	80.5	80.6	80.6	80.9	81.1	81.4	81.6	81.8
110°	91.0	91.1	91.3	91.3	91.5	91.6	91.7	91.9	92.0	92.1	92.4



TEST NUMBER: P332304-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	102.2	102.3	102.3	102.4	102.5	102.5	102.6	102.6	102.6	102.7	102.9
115°	119.0	119.1	119.4	119.5	119.7	119.8	119.6	119.5	119.4	119.2	119.3
117.5°	135.9	136.0	136.2	136.3	136.4	136.3	136.2	136.0	135.9	135.7	135.7
120°	146.4	146.8	147.2	147.5	147.9	147.9	147.7	147.3	147.0	146.7	146.6
122.5°	157.4	157.6	158.0	158.2	158.5	158.5	158.4	158.2	158.0	157.9	157.7
125°	174.1	174.3	174.5	174.7	174.9	174.9	174.8	174.7	174.5	174.4	174.1
127.5°	189.6	190.0	190.4	190.8	191.2	191.3	191.2	191.0	190.9	190.8	190.4
130°	199.9	200.3	200.9	201.4	201.8	202.0	201.8	201.7	201.5	201.3	201.1
132.5°	210.2	210.7	211.2	211.7	212.1	212.4	212.2	212.1	211.9	211.8	211.5
135°	225.9	226.3	226.6	227.0	227.4	227.6	227.5	227.4	227.4	227.4	227.0
137.5°	240.5	240.8	241.1	241.4	241.7	241.9	242.1	242.2	242.4	242.6	242.3
140°	250.6	250.9	251.2	251.5	251.8	252.0	252.1	252.1	252.2	252.2	252.2
142.5°	259.8	260.1	260.4	260.7	260.9	261.2	261.3	261.4	261.5	261.7	261.6
145°	274.1	274.2	274.3	274.4	274.6	274.7	274.9	275.1	275.3	275.4	275.4
147.5°	286.6	286.8	287.1	287.3	287.5	287.7	287.9	288.0	288.2	288.4	288.4
150°	295.3	295.5	295.6	295.7	295.9	296.0	296.1	296.2	296.4	296.4	296.4
152.5°	302.5	302.7	302.9	303.0	303.2	303.3	303.4	303.5	303.6	303.6	303.7
155°	313.9	313.9	313.9	313.9	313.9	313.9	313.9	313.9	314.0	314.1	314.3
157.5°	323.4	323.4	323.3	323.2	323.1	323.1	323.2	323.2	323.3	323.4	323.6
160°	329.5	329.4	329.2	329.2	329.0	328.9	328.9	328.9	328.9	328.9	329.2
162.5°	334.9	334.7	334.5	334.4	334.1	334.1	334.1	334.2	334.3	334.3	334.6
165°	341.8	341.7	341.4	341.3	341.0	341.0	341.0	341.0	341.0	341.0	341.4
167.5°	347.4	347.1	346.9	346.6	346.3	346.3	346.3	346.3	346.4	346.5	346.8
170°	350.5	350.2	350.0	349.7	349.5	349.4	349.4	349.4	349.4	349.4	349.8
172.5°	353.0	352.7	352.4	352.2	352.0	351.8	351.8	351.8	351.8	351.8	352.2
175°	355.5	355.3	355.1	354.8	354.6	354.4	354.4	354.4	354.4	354.4	354.8
177.5°	356.6	356.4	356.2	356.0	355.8	355.7	355.7	355.7	355.7	355.7	356.0
180°	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4



TEST NUMBER: P332304-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8
2.5°	1018.7	1020.3	1021.9	1022.6	1022.3	1022.0	1021.7	1021.4
5°	1011.9	1013.6	1015.3	1015.9	1015.6	1015.2	1014.8	1014.5
7.5°	997.8	998.6	999.6	999.7	999.1	998.5	997.8	997.2
10°	985.0	985.2	985.3	985.0	984.0	983.1	982.2	981.3
12.5°	969.1	969.0	968.9	968.3	967.3	966.1	965.1	964.0
15°	941.3	940.3	939.4	938.3	937.1	935.7	934.5	933.2
17.5°	908.0	906.1	904.1	902.2	900.2	898.3	896.4	894.5
20°	885.3	882.8	880.4	878.1	875.9	873.7	871.5	869.3
22.5°	860.9	857.9	854.8	852.3	850.2	848.2	846.1	844.1
25°	820.9	817.1	813.2	810.2	808.2	806.1	804.1	802.1
27.5°	777.4	772.1	766.7	762.4	759.3	756.2	753.1	750.0
30°	746.5	740.1	733.9	729.3	726.4	723.4	720.4	717.5
32.5°	716.1	709.2	702.3	697.4	694.3	691.2	688.1	685.0
35°	671.0	663.1	655.1	649.5	646.2	642.9	639.5	636.2
37.5°	622.5	613.5	604.5	598.0	593.9	589.8	585.7	581.6
40°	588.8	579.2	569.7	562.8	558.5	554.3	550.0	545.8
42.5°	556.5	546.1	535.6	528.5	524.7	520.9	517.1	513.3
45°	509.1	498.5	488.0	480.5	476.1	471.7	467.3	462.9
47.5°	459.9	448.5	437.0	429.4	425.4	421.4	417.6	413.6
50°	426.7	415.3	403.9	396.0	391.8	387.5	383.3	379.1
52.5°	394.7	382.8	370.9	363.1	359.3	355.5	351.6	347.8
55°	346.9	336.2	325.5	318.3	314.7	310.9	307.3	303.6
57.5°	300.0	289.9	279.8	273.1	270.1	266.9	263.7	260.6
60°	270.4	260.5	250.5	244.0	240.8	237.7	234.6	231.4
62.5°	241.1	231.7	222.4	216.0	212.7	209.5	206.2	202.9
65°	199.2	190.2	181.2	175.6	173.6	171.6	169.6	167.5
67.5°	159.4	152.7	145.8	141.4	139.3	137.0	134.9	132.7
70°	134.8	128.3	121.8	117.6	115.6	113.5	111.5	109.5
72.5°	112.6	107.3	102.0	98.9	98.1	97.3	96.4	95.5
75°	84.2	82.4	80.6	79.5	79.1	78.7	78.3	78.0
77.5°	63.5	62.5	61.6	60.8	60.5	60.1	59.7	59.4
80°	51.2	50.6	50.1	49.6	49.2	48.9	48.5	48.1
82.5°	39.2	38.7	38.1	37.8	37.7	37.6	37.5	37.5
85°	22.5	22.1	21.8	21.5	21.5	21.5	21.5	21.5
87.5°	9.7	9.7	9.6	9.5	9.3	9.2	9.1	9.0
90°	7.2	7.4	7.7	7.9	8.0	8.2	8.2	8.4
92.5°	11.2	11.3	11.6	11.6	11.6	11.5	11.4	11.3
95°	21.2	21.5	21.7	21.9	21.9	21.9	21.9	21.9
97.5°	33.0	33.3	33.6	33.7	33.7	33.7	33.6	33.6
100°	41.5	41.7	41.9	42.1	42.1	42.3	42.5	42.5
102.5°	51.4	51.6	51.7	51.8	51.8	51.8	51.7	51.7
105°	66.1	66.1	66.1	66.1	66.2	66.4	66.5	66.6
107.5°	82.0	82.1	82.4	82.5	82.4	82.3	82.2	82.1
110°	92.6	92.8	93.1	93.2	93.0	92.9	92.8	92.7



TEST NUMBER: P332304-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	103.2	103.5	103.9	103.9	103.9	103.9	103.9	103.9
115°	119.4	119.5	119.5	119.5	119.5	119.4	119.3	119.2
117.5°	135.7	135.7	135.7	135.5	135.4	135.2	135.1	134.9
120°	146.6	146.5	146.5	146.3	146.2	146.1	146.0	145.8
122.5°	157.6	157.4	157.2	157.1	156.9	156.7	156.5	156.4
125°	173.9	173.6	173.4	173.2	172.9	172.7	172.4	172.1
127.5°	190.0	189.7	189.3	189.0	188.8	188.5	188.2	187.9
130°	200.8	200.5	200.3	199.9	199.6	199.1	198.7	198.2
132.5°	211.2	210.9	210.6	210.3	209.9	209.6	209.3	209.0
135°	226.8	226.6	226.3	226.2	226.0	225.9	225.8	225.6
137.5°	242.1	241.9	241.5	241.3	241.1	240.8	240.6	240.3
140°	252.1	252.1	252.0	251.8	251.3	250.9	250.4	250.0
142.5°	261.5	261.4	261.4	261.2	260.9	260.5	260.2	259.8
145°	275.4	275.3	275.2	275.0	274.8	274.6	274.3	274.1
147.5°	288.4	288.4	288.4	288.2	287.9	287.5	287.1	286.7
150°	296.4	296.4	296.4	296.3	295.9	295.6	295.2	294.8
152.5°	303.8	304.0	304.0	303.9	303.6	303.2	302.9	302.6
155°	314.6	314.8	315.1	315.0	314.6	314.1	313.7	313.2
157.5°	323.8	324.2	324.4	324.3	324.0	323.7	323.3	323.0
160°	329.5	329.9	330.2	330.2	329.9	329.7	329.5	329.2
162.5°	334.9	335.3	335.6	335.5	335.1	334.7	334.3	333.9
165°	341.7	342.1	342.5	342.5	342.0	341.6	341.1	340.7
167.5°	347.2	347.6	348.0	348.0	347.6	347.2	346.8	346.5
170°	350.2	350.7	351.1	351.1	350.7	350.2	349.8	349.4
172.5°	352.6	353.0	353.4	353.4	352.9	352.5	352.0	351.6
175°	355.1	355.5	355.9	355.8	355.5	355.0	354.6	354.1
177.5°	356.3	356.6	356.9	356.9	356.6	356.2	355.8	355.5
180°	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4

(END OF REPORT)