

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332305-927

Luminaire Tested: **S123RDIP-S775D365U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332305-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S775D365U927-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3352.0 lumens  
Efficiency: N/A  
Efficacy: 95.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332305-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332305-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	74	74	74	69
1	102	98	94	91	97	93	90	87	83	81	78	74	72	70	66	64	63	59
2	94	86	80	75	88	82	76	72	73	69	66	66	62	60	58	56	54	50
3	86	76	69	63	81	72	66	61	65	60	56	58	54	51	52	49	46	43
4	79	68	60	54	74	65	57	52	58	52	48	52	48	44	47	43	40	37
5	73	61	53	47	68	58	50	45	52	46	42	47	42	38	42	38	35	33
6	67	55	47	41	63	52	45	39	47	41	37	43	38	34	39	35	31	29
7	62	50	42	36	59	47	40	35	43	37	33	39	34	30	35	31	28	26
8	58	45	37	32	55	43	36	31	40	33	29	36	31	27	33	28	25	23
9	54	42	34	29	51	40	33	28	36	30	26	33	28	25	30	26	23	21
10	51	38	31	26	48	37	30	25	34	28	24	31	26	22	28	24	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11009	11009	11009
5°	11051	10899	10962
10°	10989	10762	10726
15°	10871	10510	10399
20°	10709	10195	9958
25°	10542	9841	9526
30°	10320	9434	8918
35°	10093	9025	8360
40°	9884	8543	7669
45°	9608	8068	7046
50°	9306	7529	6348
55°	8997	6912	5697
60°	8714	6250	4982
65°	8344	5535	4266
70°	7884	4648	3446
75°	7207	3656	3244
80°	6428	3242	2982
85°	5434	2865	2655



TEST NUMBER: P332305-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.0	2.9
10°-20°	267.2	8.0
20°-30°	384.8	11.5
30°-40°	433.4	12.9
40°-50°	414.6	12.4
50°-60°	339.6	10.1
60°-70°	229.1	6.8
70°-80°	115.3	3.4
80°-90°	31.6	0.9
90°-100°	77.0	2.3
100°-110°	217.9	6.5
110°-120°	214.4	6.4
120°-130°	171.0	5.1
130°-140°	134.8	4.0
140°-150°	100.6	3.0
150°-160°	70.1	2.1
160°-170°	41.2	1.2
170°-180°	13.4	0.4
0°-30°	748.0	22.3
0°-40°	1181.5	35.2
0°-60°	1935.6	57.7
0°-90°	2311.5	69.0
90°-120°	509.3	15.2
90°-150°	915.7	27.3
90°-180°	1040.0	31.0
0°-180°	3352.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1023	1023	1023	1023	1023	
5°	1023	1018	1009	1016	1014	97
15°	976	966	943	939	933	275
25°	888	866	829	812	802	408
35°	768	737	687	652	636	481
45°	631	592	530	484	463	487
55°	479	437	368	322	304	430
65°	328	281	217	178	168	324
75°	173	133	88	80	78	185
85°	44	27	23	22	22	49
90°	1	3	7	8	8	3
95°	10	31	166	48	32	10
105°	32	48	225	394	356	35
115°	57	72	172	378	433	57
125°	80	94	161	291	342	71
135°	94	112	158	240	277	72
145°	107	122	156	197	216	67
155°	121	131	152	172	179	56
165°	132	136	145	154	156	37
175°	138	138	139	141	141	13
180°	138	138	138	138	138	



TEST NUMBER: P332305-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8
2.5°	1026.0	1025.5	1024.8	1024.3	1023.7	1022.5	1020.7	1019.0	1017.2	1015.4	1017.1
5°	1022.8	1021.8	1020.9	1020.0	1019.1	1017.5	1015.3	1013.0	1010.8	1008.7	1010.3
7.5°	1013.3	1012.3	1011.3	1010.3	1009.3	1007.3	1004.5	1001.6	998.8	995.9	996.8
10°	1005.4	1004.0	1002.7	1001.5	1000.1	997.8	994.5	991.3	987.9	984.6	984.8
12.5°	994.0	992.6	991.2	989.8	988.3	985.6	981.5	977.5	973.4	969.3	969.2
15°	975.5	973.4	971.4	969.4	967.3	963.8	958.6	953.5	948.2	943.1	942.2
17.5°	952.0	949.7	947.4	945.0	942.6	938.2	931.6	925.0	918.5	912.0	910.0
20°	934.9	931.8	928.9	926.0	923.1	918.1	911.0	904.0	897.1	890.0	887.6
22.5°	915.6	912.2	908.8	905.4	902.0	896.6	889.1	881.7	874.3	866.8	863.8
25°	887.6	883.0	878.3	873.7	869.1	862.5	854.1	845.6	837.1	828.6	824.7
27.5°	853.5	848.4	843.4	838.3	833.2	825.9	816.5	807.1	797.6	788.1	782.8
30°	830.3	824.7	819.3	813.7	808.2	800.3	790.0	779.6	769.3	759.0	752.7
32.5°	807.1	800.8	794.6	788.3	782.0	773.4	762.5	751.6	740.7	729.8	722.9
35°	768.1	761.4	754.8	748.2	741.6	732.5	721.1	709.6	698.2	686.8	678.9
37.5°	728.6	721.2	713.8	706.5	699.1	689.4	677.2	665.0	652.8	640.6	631.5
40°	703.4	695.3	687.1	679.1	671.0	660.4	647.3	634.2	621.1	608.0	598.4
42.5°	674.9	666.8	658.6	650.5	642.5	631.6	618.1	604.5	591.0	577.5	567.0
45°	631.2	623.0	614.7	606.3	598.0	586.8	572.6	558.4	544.2	530.0	519.5
47.5°	587.6	578.5	569.4	560.3	551.2	539.6	525.4	511.1	496.9	482.8	471.3
50°	555.7	547.1	538.4	529.7	521.1	509.3	494.4	479.4	464.5	449.6	438.2
52.5°	527.2	517.8	508.4	499.0	489.6	477.5	462.7	448.0	433.2	418.4	406.5
55°	479.4	470.4	461.4	452.3	443.3	430.9	415.3	399.7	384.0	368.3	357.6
57.5°	435.3	425.5	415.7	405.8	395.9	383.2	367.4	351.6	335.9	320.2	310.1
60°	404.8	394.7	384.5	374.4	364.2	351.5	336.2	320.9	305.6	290.3	280.4
62.5°	374.2	364.1	353.9	343.8	333.7	321.0	305.7	290.4	275.1	259.8	250.4
65°	327.6	317.5	307.4	297.2	287.1	274.8	260.5	246.1	231.7	217.3	208.3
67.5°	281.1	270.8	260.5	250.3	240.0	228.0	214.2	200.4	186.6	172.9	166.1
70°	250.5	240.6	230.6	220.6	210.7	199.2	186.3	173.5	160.6	147.7	141.2
72.5°	220.0	210.2	200.3	190.5	180.8	170.0	158.3	146.6	134.8	123.1	117.8
75°	173.3	164.5	155.7	146.8	138.0	128.5	118.4	108.2	98.1	87.9	86.1
77.5°	130.9	122.9	114.9	106.9	98.9	91.7	85.1	78.6	72.1	65.5	64.6
80°	103.7	96.1	88.6	81.0	73.4	67.7	63.8	60.0	56.2	52.3	51.7
82.5°	77.8	71.3	64.7	58.2	51.7	47.5	45.7	43.9	42.1	40.3	39.8
85°	44.0	39.9	35.9	31.8	27.7	25.4	24.9	24.3	23.8	23.2	22.9
87.5°	16.0	14.5	13.0	11.6	10.1	9.3	9.5	9.7	9.8	10.1	9.8
90°	0.6	1.1	1.7	2.5	3.1	3.6	4.5	5.3	6.2	7.0	6.7
92.5°	3.5	5.1	7.5	9.7	12.0	16.2	23.5	35.6	47.4	43.0	32.5
95°	9.5	10.4	13.5	18.2	25.5	36.4	60.2	101.9	147.8	166.0	134.7
97.5°	16.2	16.5	18.9	23.1	30.3	42.1	64.8	111.8	188.4	257.3	275.2
100°	20.8	21.0	23.0	26.9	33.6	44.5	64.1	105.5	179.2	265.1	320.3
102.5°	25.4	25.9	27.6	31.4	37.4	47.5	65.0	100.1	165.7	250.6	322.5
105°	32.5	33.4	35.0	38.3	43.6	52.4	67.5	96.3	149.2	225.1	305.4
107.5°	40.0	40.8	42.5	45.7	50.7	58.8	72.1	96.0	138.7	202.6	275.5
110°	45.3	46.2	47.6	50.7	55.5	63.3	75.9	97.1	134.7	189.8	256.7



TEST NUMBER: P332305-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	50.3	51.1	52.5	55.6	60.4	68.0	79.7	99.4	132.4	181.3	240.3
115°	57.4	58.5	60.2	63.0	67.7	75.3	86.0	103.0	131.6	172.1	220.6
117.5°	64.5	65.8	67.2	69.8	75.1	82.1	92.6	107.8	132.1	166.8	208.7
120°	69.4	70.3	71.7	74.5	79.8	86.7	96.9	111.4	133.0	164.3	202.4
122.5°	73.7	74.5	75.9	79.0	84.1	91.5	101.3	114.8	134.5	162.8	197.3
125°	79.8	80.3	82.0	85.1	90.4	98.0	107.8	120.1	136.9	160.7	190.7
127.5°	84.4	85.2	87.4	90.5	96.3	103.9	113.4	124.5	139.6	159.7	184.8
130°	87.4	88.2	90.7	94.0	100.0	107.5	116.8	127.4	141.4	159.0	181.6
132.5°	89.6	90.6	93.4	97.4	103.3	110.7	119.6	130.1	142.8	158.8	178.8
135°	93.5	94.6	97.7	101.9	107.8	115.3	124.0	133.6	144.7	158.4	175.0
137.5°	97.2	98.4	101.4	105.8	111.7	118.7	127.1	136.1	146.1	157.8	171.7
140°	99.7	101.1	103.9	108.4	113.9	121.0	129.0	137.4	146.9	157.6	169.6
142.5°	102.3	103.5	106.5	110.6	116.2	122.7	130.6	138.8	147.7	157.2	167.9
145°	106.6	107.5	110.0	114.2	119.0	125.4	132.7	140.2	148.1	156.5	165.4
147.5°	111.1	111.5	114.0	117.6	122.2	127.7	134.4	141.2	148.1	155.4	163.1
150°	113.9	114.2	116.5	120.1	124.0	129.0	135.5	141.4	148.1	154.6	161.5
152.5°	116.8	116.9	119.1	122.3	125.8	130.6	136.2	141.8	147.4	153.4	159.7
155°	121.2	121.2	122.9	125.7	128.8	132.7	137.4	142.0	146.7	151.5	157.0
157.5°	124.7	124.9	126.3	128.7	131.3	134.4	138.2	142.2	145.8	149.7	154.0
160°	127.4	127.4	128.5	130.7	132.7	135.5	138.9	142.2	145.3	148.4	152.0
162.5°	129.4	129.4	130.3	132.1	133.8	136.2	139.1	142.0	144.4	147.0	150.0
165°	132.4	132.1	132.7	134.1	135.2	137.2	139.4	141.4	143.1	145.0	147.3
167.5°	134.7	134.4	134.7	135.7	136.5	137.8	139.3	140.9	141.7	143.0	144.7
170°	136.0	135.5	135.8	136.6	137.2	137.8	139.1	140.2	140.9	141.6	143.1
172.5°	137.0	136.6	136.7	137.3	137.6	137.9	139.1	140.1	140.1	140.5	141.5
175°	138.0	137.8	137.4	138.0	138.0	138.3	138.9	139.4	139.1	139.1	139.7
177.5°	138.6	138.3	138.1	138.3	138.3	138.3	138.6	138.9	138.6	138.3	138.6
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3



TEST NUMBER: P332305-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8
2.5°	1018.7	1020.3	1021.9	1022.6	1022.3	1022.0	1021.7	1021.4
5°	1011.9	1013.6	1015.3	1015.9	1015.6	1015.2	1014.8	1014.5
7.5°	997.8	998.6	999.6	999.7	999.1	998.5	997.8	997.2
10°	985.0	985.2	985.3	985.0	984.0	983.1	982.2	981.3
12.5°	969.1	969.0	968.9	968.3	967.3	966.1	965.1	964.0
15°	941.3	940.3	939.4	938.3	937.1	935.7	934.5	933.2
17.5°	908.0	906.1	904.1	902.2	900.2	898.3	896.4	894.5
20°	885.3	882.8	880.4	878.1	875.9	873.7	871.5	869.3
22.5°	860.9	857.9	854.8	852.3	850.2	848.2	846.1	844.1
25°	820.9	817.1	813.2	810.2	808.2	806.1	804.1	802.1
27.5°	777.4	772.1	766.7	762.4	759.3	756.2	753.1	750.0
30°	746.5	740.1	733.9	729.3	726.4	723.4	720.4	717.5
32.5°	716.1	709.2	702.3	697.4	694.3	691.2	688.1	685.0
35°	671.0	663.1	655.1	649.5	646.2	642.9	639.5	636.2
37.5°	622.5	613.5	604.5	598.0	593.9	589.8	585.7	581.6
40°	588.8	579.2	569.7	562.8	558.5	554.3	550.0	545.8
42.5°	556.5	546.1	535.6	528.5	524.7	520.9	517.1	513.3
45°	509.1	498.5	488.0	480.5	476.1	471.7	467.3	462.9
47.5°	459.9	448.5	437.0	429.4	425.4	421.4	417.6	413.6
50°	426.7	415.3	403.9	396.0	391.8	387.5	383.3	379.1
52.5°	394.7	382.8	370.9	363.1	359.3	355.5	351.6	347.8
55°	346.9	336.2	325.5	318.3	314.7	310.9	307.3	303.6
57.5°	300.0	289.9	279.8	273.1	270.1	266.9	263.7	260.6
60°	270.4	260.5	250.5	244.0	240.8	237.7	234.6	231.4
62.5°	241.1	231.7	222.4	216.0	212.7	209.5	206.2	202.9
65°	199.2	190.2	181.2	175.6	173.6	171.6	169.6	167.5
67.5°	159.4	152.7	145.8	141.4	139.3	137.0	134.9	132.7
70°	134.8	128.3	121.8	117.6	115.6	113.5	111.5	109.5
72.5°	112.6	107.3	102.0	98.9	98.1	97.3	96.4	95.5
75°	84.2	82.4	80.6	79.5	79.1	78.7	78.3	78.0
77.5°	63.5	62.5	61.6	60.8	60.5	60.1	59.7	59.4
80°	51.2	50.6	50.1	49.6	49.2	48.9	48.5	48.1
82.5°	39.2	38.7	38.1	37.8	37.7	37.6	37.5	37.5
85°	22.5	22.1	21.8	21.5	21.5	21.5	21.5	21.5
87.5°	9.7	9.7	9.6	9.5	9.3	9.2	9.1	9.0
90°	7.0	7.3	7.5	8.1	7.8	8.1	8.4	8.1
92.5°	23.6	18.7	16.5	15.1	14.6	13.7	14.0	13.5
95°	100.8	68.3	53.5	43.4	38.1	35.6	33.6	32.5
97.5°	251.2	201.2	165.1	131.7	111.0	98.4	90.8	88.4
100°	330.0	307.4	274.6	234.9	206.6	186.2	175.2	175.5
102.5°	356.2	355.5	336.4	311.2	289.2	273.1	264.0	257.5
105°	363.9	391.9	397.2	390.0	377.1	366.5	357.5	356.1
107.5°	341.8	387.3	411.9	421.8	422.1	418.4	415.4	412.9
110°	320.8	372.3	407.6	427.2	435.1	437.3	436.7	436.2





TEST NUMBER: P332305-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	300.0	352.6	392.1	417.3	431.7	438.6	440.8	440.8
115°	272.4	321.1	362.3	392.8	413.8	426.0	431.7	433.1
117.5°	252.4	294.5	331.4	362.3	384.3	398.4	406.4	408.3
120°	241.9	279.6	313.2	341.5	363.6	379.3	386.0	387.7
122.5°	233.6	267.8	298.9	325.2	344.8	358.9	366.3	368.4
125°	222.5	253.1	280.0	302.4	320.3	332.6	339.6	341.5
127.5°	212.9	240.1	264.4	284.8	300.7	311.2	317.6	319.3
130°	206.8	232.1	254.8	273.8	288.6	298.7	304.6	306.8
132.5°	201.3	224.4	245.6	263.7	277.7	287.7	292.9	294.5
135°	193.7	213.6	231.8	247.7	261.5	269.9	274.9	276.9
137.5°	186.8	203.1	218.8	232.7	244.2	252.7	256.9	258.3
140°	182.8	197.1	210.5	222.5	233.2	241.1	245.5	245.3
142.5°	179.0	191.2	202.9	213.3	222.4	229.4	233.4	233.1
145°	174.4	183.6	192.6	200.7	207.7	213.6	215.9	216.4
147.5°	170.6	178.0	185.2	191.0	196.3	200.3	202.4	202.6
150°	167.9	174.4	180.3	185.6	189.8	192.9	194.6	194.6
152.5°	165.5	171.0	176.3	180.7	183.9	186.8	187.8	187.8
155°	161.8	166.3	170.5	173.8	176.3	178.6	179.2	179.4
157.5°	157.9	161.6	164.9	167.5	169.7	171.3	171.8	171.7
160°	155.7	158.8	161.5	163.5	165.4	167.2	167.2	166.8
162.5°	153.0	155.6	158.2	159.9	161.2	162.6	162.6	162.4
165°	149.5	151.1	153.1	154.6	155.7	156.8	156.5	156.5
167.5°	146.5	147.7	148.9	149.9	150.4	151.1	150.9	150.9
170°	144.4	145.3	146.4	146.9	147.3	147.8	147.5	147.5
172.5°	142.7	143.3	144.2	144.5	144.6	145.1	144.7	144.4
175°	140.2	140.5	141.1	141.1	141.1	141.4	141.1	140.9
177.5°	138.7	138.9	139.2	139.2	138.9	139.2	138.7	138.7
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3

(END OF REPORT)